



Product Number: 54237

Order Abbreviation: 50MR16/IR/WFL60/C 12V

General Description: Tungsten Halogen Tru-Aim MR16 IR UV-Filter Capsule Axial Filament Hard Dichroic Reflector GU5.3 Bi-Pin Base 50Watt 12Volt WFL Beam

Product Information

Abbrev. With Packaging Info.	50MR16IRWFL60C 12V 20/CS 1/SKU
Average Rated Life (hr)	5000
Base	GU5.3 Bipin
Beam Angle (deg)	60
Beam Type	VWFL
Bulb	MR16
Centerbeam Candlepower (cp)	1430
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	3000
Diameter (in)	2.008
Diameter (mm)	51.00
Ecologic	YES
Family Brand Name	TRU-AIM® IR
Filament	AXIAL
Horizontal Beam Angle (deg)	60
Lamp Finish	Covered
Maximum Overall Length - MOL (in)	1.750
Maximum Overall Length - MOL (mm)	45
Nominal Voltage (V)	12.00
Nominal Wattage (W)	50.00
Vertical Beam Angle (deg)	60



Footnotes

- Infrared lamp technology
- Max. seal temperature 370 C (662F)
- UV Filter capsule with axial filament in covered constant color, hard coated dichroic reflector and infrared reflective coating on the lamp capsule.
- Max pin temperature 250 C.
- Max temperature at lens reflector joint 240 C.