



### 6637304-962: Four Light Island Pendant



**Collection:** Elmwood Park

**UPC #:** 785652069994

**Finish:** Brushed Nickel (962)

#### Dimensions:

**Length:** 40"  
**Width:** 4 3/8"  
**Height:** 24 3/4"  
**Weight:** 10.6 lbs.

**Overall Height:** 67 3/4"  
**Wire:** 72" (color/Clear Silver)  
**Mounting Proc.:** Screw Collar - Stem  
**Connection:** Mounted To Box

#### Bulbs:

4 - Medium A19 75w Max. 120v - Not included

#### Features:

- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

#### Material List:

1 Body - Steel - Brushed Nickel  
1 6" Stem - Steel - Brushed Nickel  
3 12" Stem - Steel - Brushed Nickel

#### Safety Listing:

Safety Listed for Damp Locations

#### Instruction Sheets:

Trilingual (English, Spanish, and French) (990CH6637304-EWP)

#### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Satin Etched	4				5 1/2	3 1/8				
Shade	Glass	Clear	4				5 7/8	4 3/8				

#### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	3/4			5		

#### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	3113704-778	1	785652069994	42	11.25	10	2.734	12.7	175	Yes
NJ Pallet		24		48	40	72	80	304		No
NV Pallet		24		48	40	72	80	304		No