




RIGID-IMC FITTINGS

MALLEABLE IRON 90° PULL ELBOWS

Download
Specification Sheet
(https://www.sepco-usa.com/wp-content/uploads/2017/03/page_081.pdf)



Print



PEF50

Trade Size	1/2"
Dim A	2.188
Dim B	2.188
Unit Pack	10
Master Pack	100
Lbs. / 100 Pcs.	36
UPC	13701
Competitor Part Number	FL-50, 820, ML-141-1, FF-050

APPLICATION FEATURES

or	Raintight
connecting	Furnished
rigid conduit	with
or IMC to	Neoprene
rigid	gasketed
conduit or	steel cover
IMC to form	Threaded
90° bend.	for rigid
	conduit and
	IMC (Female-
	NPT)

STANDARD STANDARD

MATERIALS FINISH

Malleable	Zinc Plated
Iron	

UL LISTED

E198258

