



Measurements:

<u>Width</u>	<u>Height</u>			
8.00"	9.75"			
<u>Max OAH</u>				
130.00"				
<u>Hanging Weight</u>	<u>Canopy Width</u>	<u>Canopy Height</u>	<u>Canopy Length</u>	
2.21 lb	4.75"	1.25"	4.75"	

Lamping:

1.00 of Bulbs
 40W
 40 total watt
 500 Rated Lumens
 2900 Color Temperature
 Input Voltage: 120

Dimmable : Standard Dimmer

Finish:

Polished Chrome PC

Glass:

Beveled Crystal BC

Material:

Stainless Steel + Steel

Certification:

Dry Location

Additional:

G9 (Included)
 Slope: 120