




RIGID-IMC FITTINGS

MALLEABLE IRON 90° PULL ELBOWS

Download
Specification Sheet
(https://www.sepco-usa.com/wp-content/uploads/2017/03/page_081.pdf)



Print



PEF150

Trade Size	1-1/2"
Dim A	4.125
Dim B	4.125
Unit Pack	-
Master Pack	10
Lbs. / 100 Pcs.	200
UPC	13707
	FL-150,
Competitor Part Number	824, ML-141-5, FF-150

APPLICATION FEATURES

or Raintight
connecting Furnished
rigid conduit with
or IMC to Neoprene
rigid gasketed
conduit or steel cover
IMC to form Threaded
90° bend. for rigid
conduit and
IMC (Female-
NPT)

STANDARD MATERIALS STANDARD FINISH

Malleable Iron Zinc Plated

UL LISTED

E198258

