

Item # 7930-61	UPC Code: 747396023397
Product Family Name:	Finish: Vintage Rust™
Category: PIER MOUNT	Category Type:
Certification	
Patents:	
Notes:	



Image File Name: 7930-61.jpg



MEASUREMENTS

Width: 5.75	Length: 5.75	Height: 3.5	Extension:
Height Adjustable: Min Overall Height:		Max Overall Height:	Slope: No
Wire Length:	Chain Length:	Safety Cable Included: No	Net Weight: 0.44
Canopy Width:	Canopy Height:	Canopy Length:	Center to Bottom:
Backplate Width:	Backplate Height:	Center to Top:	

LAMPING

No. of Bulbs: 0	Light Type:			
Max Bulb Wattage:	Socket:			
Dimmable: No	Ballast:	Rated Life Hours:	Photocell Included: No	Bulb/LED Included:
Bulb/LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:


SHADE / GLASS

Description:	Material:	
Part No.:	Quantity:	
Width:	Height:	Length:



SHIPPING

Carton Width: 6.38	Carton Height: 4.0	Carton Length: 6.38	
Carton Weight: 0.77	Carton Cubic Feet: 0.094	Small Package Shippable: Yes	
Master Pack Width: 13.25	Master Pack Height: 14.0	Master Pack Length: 13.25	
Master Pack Weight: 9.5	Master Cubic Feet: 1.422	Multi-Pack: 1	Master Pack: 12

 **WARNING:** Handling this product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. Wash hands with soap and water after installing, handling, cleaning or otherwise touching this product. For more information go to: www.P65Warnings.ca.gov.

For additional information, please contact Customer Care: 1-800-221-7977 | Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties.