



<b>TRUMAN 4027AN</b>
ANTIQUE NICKEL

WIDTH:	5.3"
HEIGHT:	8.3"
WEIGHT:	3.0 LBS
MATERIAL:	METAL
GLASS:	ETCHED OPAL
CANOPY:	5.75" DIA.
SOCKET:	1-100W MED.
MAX HEIGHT:	40.3"
LEADWIRE:	120.0"
DOWN RODS:	1-6", 2-12"
CERTIFICATION:	C-US DRY RATED
VOLTAGE:	120V
UPC:	640665402704
INSTALL OPTIONS:	UP, INSTALL ON SLOPED CEILING 90°

AT HINKLEY, WE EMBRACE THE DESIGN PHILOSOPHY THAT YOU CAN MERGE TOGETHER THE LIGHTING, FURNITURE, ART, COLORS AND ACCESSORIES YOU LOVE INTO A BEAUTIFUL ENVIRONMENT THAT DEFINES YOUR OWN PERSONAL STYLE. WE HOPE YOU WILL BE INSPIRED BY OUR COMMITMENT TO KEEP YOUR 'LIFE AGLOW.'

*life*AGLOW®