



Measurements:

Width

15.75"

Max OAH

130.00"

Hanging Weight

8.58 lb

Lamping:

7 of Bulbs

40W

280 total watt

Dimmable : Standard Dimmer

Height

10.00"

Min OAH

18.00"

1,330 Rated Lumens

2900 Color Temperature

Finish:

Polished Chrome PC

Glass:

Clear/White 10

Material:

Stainless Steel + Steel

Certification:

Dry Location

Additional:

G9 (Included)

