

MINKA-LAVERY®

Item # 412	UPC Code: 747396663241
Product Family Name:	Finish: Brushed Nickel
Category: WALL SCONCE	Category Type: Sconce
Certification 3057374	
Patents:	
Notes:	



Image File Name: 412.jpg



MEASUREMENTS

Width: 8	Length: 8	Height: 5.5	Extension: 4
Height Adjustable: Min Overall Height: No		Max Overall Height: No	Slope: No
Wire Length: 7"	Chain Length:	Safety Cable Included: No	Net Weight: 1.32
Canopy Width:	Canopy Height:	Canopy Length:	Center to Bottom: 3.5
Backplate Width: 4.25	Backplate Height: 4.25	Center to Top: 2.0	

LAMPING

No. of Bulbs: 1	Light Type: G16.5			
Max Bulb Wattage: 60	Socket: E12 CAND			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included: No	Bulb/LED Included: N
Bulb/LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description: Etched Marble	Material: GLASS
Part No.: G412	Quantity: 1
Width: 8.0	Height: 4.38
	Length:



SHIPPING

Carton Width: 5.5	Carton Height: 6.0	Carton Length: 10.5
Carton Weight: 1.78	Carton Cubit Feet: 0.201	Small Package Shippable: Yes
Master Pack Width: 11.0	Master Pack Height: 13.0	Master Pack Length: 17.5
Master Pack Weight: 11.55	Master Cubic Feet: 1.448	Multi-Pack: Master Pack: 6



**ADA
Compliant**



**Damp
Location**



Title 17



**ETL
Intertek**

For additional information, please contact Customer Care: 1-800-221-7977 | Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties