



79434BLE-962: One Light Ceiling Flush Mount



Collections: Nash (Primary)
Driscoll

Direct Replacement: 75434EN-962

Three Light Fluorescent Flush Fixture in Heirloom Bronze Finish with Satin Etched Glass Shade

UPC #:785652159138

Finish: Brushed Nickel (962)

Dimensions:

Diameter: 11 1/2" **Wire:** 6 1/2"
Height: 4" **Mounting Proc.:** Cap Nuts
Weight: 4.3 lbs. **Connection:** Mounted To Box

Bulbs:

1 - Fluorescent GU24 Self Ballasted CFL 13w Max. 120v - included

Features:

- ENERGY STAR® Qualified
- Offers energy saving fluorescent lighting
- Meets Title 24 energy efficiency standards
- Sleek architectural look with exclusive 'twist-lock' design makes installation and relamping easy with no exposed screws

Material List:

1 Body - Steel - Brushed Nickel

Safety Listing:

Safety Listed for Damp Locations
Safety Listed for Damp Locations

Instruction Sheets:

English (HC-1503)
French (f-003)
Trilingual (English, Spanish, and French) (990C7943_BLE-NSH)
Trilingual (English, Spanish, and French) (A-779FB)

Shade / Glass / Diffuser Details:

| Part | Material | Finish | Quantity | Item Number | Length | Width | Height | Diameter | Fitter Diameter | Shade Top Length | Shade Top Width | Shade Top Diameter |
|----------|----------|--------------|----------|-------------|--------|-------|--------|----------|-----------------|------------------|-----------------|--------------------|
| Diffuser | Glass | Satin Etched | 1 | | | | 3 3/16 | 8 15/16 | | | | |

Replacement Bulb Data:

| Product # | | | Type | Base | Watts | Watts Consumed | Volts | Hours | Lumens | Temp (°K) | CRI |
|-----------|--------------------|--|--------------------|------|-------|----------------|-------|-------|--------|-----------|-----|
| 97102 | Frosted Glass Lens | | Self Ballasted CFL | GU24 | 13 | 13 | 120v | 10000 | 900 | 2700 | 81 |

Shipping Information:

| Package Type | Product # | Quantity | UPC | Length | Width | Height | Cube | Weight | Fr. Class | UPS Ship |
|--------------|--------------|----------|--------------|--------|-------|--------|--------|--------|-----------|----------|
| Individual | 79434BLE-962 | 1 | 785652159138 | 13.58 | 13.58 | 5.25 | 0.56 | 4 | 125 | Yes |
| NJ Pallet | | 114 | | 48 | 40 | 71.75 | 79.722 | 456 | | No |
| NV Pallet | | 132 | | 48 | 40 | 71.75 | 79.722 | 528 | | No |