



T8 Plus

F17T8/TL865 PLUS/ALTO 30PK

Philips PLUS T8 lamps are energy-efficient lighting solutions and offer long life.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	42000 h
Life 12-Hr Instant Start [Hrs]	36000 h
Life 3-Hr Program Start [Hrs]	36000 h
Life 3-Hr Instant Start [Hrs]	30000 h
Features	ALTO® Plus

Light Technical	
Color Code	TL865 [CCT of 6500K (865)]
Initial lumen (Nom)	1300 lm
Color Designation	TL865
Design Mean Lumens	1235 lm
Correlated Color Temperature (Nom)	6500 K
Color Rendering Index (Nom)	82

Operating and Electrical	
Power (Rated) (Nom)	17 W

Mechanical and Housing	
Cap-Base Information	Green Base

Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	46 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg

Product Data	
Order product name	F17T8/TL865 PLUS/ALTO 30PK
EAN/UPC - Product	046677281939
Order code	281931
Local order code	TEST
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927850186502
Net Weight (Piece)	0.001 kg

Warnings and Safety


- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

T8 Plus

Dimensional drawing

Product

F17T8/L865 PLUS/ALTO 30PK



F17T8/865 24 ALTO Plus ES

