



Powering Business Worldwide

pe.eaton.com

30.5 mm, Heavy-Duty Assembled Control Station

10250TGS

UPC:782113401768

Dimensions:

- **Height:** 5.1 IN
- **Length:** 9.9 IN
- **Width:** 5.8 IN

Weight:3.15 LB

Notes:Gray Enclosure. Breaking glass closes contact.

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator:** Break glass
- **Actuator Color:** Clear
- **Contact Configuration:** 1NC (logic level)
- **Enclosure Material:** Die cast
- **Legend:** EMERGENCY OFF
- **Mounting:** Surface
- **Number Of Elements:** 1
- **Rating:** NEMA 4, 4X, 12, 13
- **Series:** 10250T

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250TGS](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- CE Marked



