



Representative

Catalog Number: 54913BE
Product ID: 7TAH007900R0009
UPC Number: 78621089817
EAN Number: 05415022246438
Status: Active

Copper One-Hole Lug, Long Barrel, Blind End, Tongue Length 1.25 Inches, Max 35kV, Wire Size 250 kcmil, 1/2 Inch Bolt Size, Tin Plated, Die Code 62, Die Color Code Yellow

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Long Barrel Copper Lug
Standard	UL E9809
Cable Size	250 kcmil
Stud Size	1/2 Inch
Number Of Holes	1
Material	Copper
Color	Yellow

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
Insulated	N
With sight-hole	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

Packaging

Inner Quantity	10
Inner Dimensions (inches)	3.5x3x3
Outer Quantity	100
Outer Dimensions (inches)	16.79x8x4
Weight Uom	16 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website
Instruction Sheet 1	ta01025-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com