



Powering Business Worldwide

pe.eaton.com

CH 3/4-inch main loadcenter

CH42B200R

UPC:782113098227

Dimensions:

- **Height:** 5.19 IN
- **Length:** 37 IN
- **Width:** 14.31 IN

Notes:Furnished with hub closure plates.
Loadcenter contains single insulated/bondable neutral.

Warranties:

- Limited lifetime

Specifications:

- **Special Features:** Standard
- **Type:** Main breaker
- **Amperage Rating:** 200A
- **Box Size:** K
- **Bus Material:** Copper
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** CSR
- **Number Of Circuits:** 42
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2-300 kcmil
- **Feed Type:** Overhead

Supporting documents:

- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - CH42B200R](#)
- [Dimensional Drawing - CH 3/4 LOADCENTER,](#)



CSR MAIN BREAKER, OUTDOOR NEMA 3R,
120/240 VAC, 1 PH

Certifications:

- UL 67
- UL 50

Product compliance: No Data

© 2016 Eaton. All rights reserved.