

# Carlon®

## Liquidtight Flexible Non-Metallic Conduit & Fittings

T&B Catalog Number:

LN20EA

UPC Number:

03448104396

Status:

Active

Description:

3/4 Inch, 90 Degree, One-Piece Liquidtight Non-Metallic Fitting, CSA, UL E32447, Temperatures up to 60 Degrees C, PVC, Grey

### Features

Unique design, the simple one-piece body requires no disassembly of components for installation. The system is so strong that there is no need for a compression nut.

PVC construction of the fitting and locknut provides unparalleled protection from water, oil and dust.

Non-conductive and will not corrode or rust.

Temperatures up to 140 degree F (60 degree C)

### General

Trade Size (inches)	3/4
Material	Non-Metallic
Thread Size	3/4 - 14 NPT

### Dimension Information

Degree of Bend	90
A (inches)	0.56
B (inches)	1.73
C (inches)	2.25
D (inches)	1.63
E (inches)	1.44

### Packaging

T&B Order Multiple	50
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	3.44 lbs. per 100

### Application Support

T&B Sales Drawings	wsd-ac00828
Product Overview-Carflex Liquidtight Flex-Available on Website	
ible Tubing	

### Certifications


RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:  
E 32447

For further technical assistance, please contact us...



8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)