



Product Number: 16743

Order Abbr eviation: 70PAR38/HAL/S/NFL25 120V

General Description: Tungsten Halogen PAR38 Reflector Lamp 70Watt 120Volt Medium Skirted Base NarrowFlood25 Beam

#### Product Information

Abbrev. With Packaging Info.	70PAR38HALSNFL25 120V 10/CS 1/SKU
Approx. Lumens	1305
Average Rated Life (hr)	1500
Base	E26 Medium Skirted
Beam Angle (deg)	25
Beam Type	NFL
Bulb	PAR38
Centerbeam Candlepower (cp)	5100
Class	YES
Color Rendering Index (CRI)	99
Color Temperature/CCT (K)	2925
Diameter (in)	4.752
Diameter (mm)	120.70
Family Brand Name	CAPSYLITE® PAR38
Filament	CC-8
Horizontal Beam Angle (deg)	25
Lamp Finish	Reflector
Maximum Overall Length - MOL (in)	5.313
Maximum Overall Length - MOL (mm)	134.9375
Nominal Voltage (V)	120.00
Nominal Wattage (W)	70.00
Vertical Beam Angle (deg)	25



#### Footnotes

- State of the Art SPL Optics
- To avoid electric shock and/or skin burns, turn off power and allow bulb to cool before handling or attempting replacement.
- In base up operation, heat may eventually deteriorate paper-lined or plastic sockets.