

**IMAGE  
COMING  
SOON**

Product Number: 59012

Order Abbr eviation: 20AR70/FL25 12V

General Description: Tungsten Halogen Aluminum Reflector AR70 BA15 Base 20Watt 12Volt Flood Beam

#### Product Information

Abbrev. With Packaging Info.	20AR70FL25 12V 10/CS 1/SKU
Average Rated Life (hr)	3000
Base	BA15d Double Contact Bayonet
Beam Angle (deg)	24
Beam Type	FL
Bulb	AR70
Centerbeam Candlepower (cp)	900
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2800
Diameter (in)	2.776
Diameter (mm)	70.50
Ecologic	YES
Family Brand Name	AR70
Filament	C-8
Horizontal Beam Angle (deg)	25
Lamp Finish	Reflector
Maximum Overall Length - MOL (in)	1.97
Maximum Overall Length - MOL (mm)	50
Nominal Voltage (V)	12.00
Nominal Wattage (W)	20.00
Vertical Beam Angle (deg)	25

#### Footnotes

- UV Filter capsule with axial filament in precisely engineered aluminum reflector.
- Suitable for use in unshielded fixtures. Consult most recent luminaire standards for your area to determine luminaire requirements.