

Wynberg Collection
Wynberg 3 Light Chandelier - NI
 3293NI (Brushed Nickel)

Project Name: _____
 Location: _____
 Type: _____
 Qty: _____
 Comments: _____



Ordering Information

Product ID	3293NI
Finish	Brushed Nickel
Available Finishes	NIA, OZ, OZU, NI
Collection	Wynberg Collection

Dimensions

Base Backplate	5.00 DIA
Chain/Stem Length	72.00"
Weight	5.85 LBS

Specifications

Material	Steel
Diffuser Description	Satin Etched

Electrical

Voltage	120V
Lead Wire Length	59.00"

Qualifications

Safety Rated	Dry
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
# of Bulbs/LED Modules	3
Max or Nominal Watt	100W
Socket Wire	150
Socket Type	Medium
Lamp Type	A19

Dimensions

Height	13.00"
Overall Height	87.00"
Width	22.00"

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	9-13W		