


## GFTR2-IGO

SmartlockPro Isolated Ground GFCI Duplex Receptacle Outlet, Extra Heavy-Duty Hospital Grade, Tamper-Resistant, Power Indication, 20 Amp, 125 Volt, Back or Side Wire, NEMA 5-20R, 2-Pole, 3-Wire, Self-Grounding - Orange



UPC Code: 07847772406

Country Of Origin: China

NEMA:  
5-20R



### Technical Information

#### AC Horsepower Ratings

**At Rated Voltage:** 1 HP

#### Electrical Specifications

**Grounding:** Self-Grounding

**Pole:** 2

**Wire:** 3

**Short Circuit Current Rating:** 10kA

**Amperage:** 20 A

**Voltage:** 125 VAC

#### Environmental Specifications

**Flammability:** Rated V-0 per UL 94

**Operating Temperature:** -35C to +66C

#### Material Specifications

**Face Material:** PBT

**Body Material:** Polycarbonate

**Terminal Screws:** Plated Steel

**Terminal Clamp:** Brass

**Line Contacts:** Brass

**Grounding Screw:** Plated Steel

**Strap Material:** Galvanized Steel

**Ground Clips:** Brass

**Shutter Mechanism:** Delrin® Acetal

#### Mechanical Specifications

**Terminal ID:** Brass-Hot, Green-Ground, Silver-Neutral

**Terminal Accom.:** 14-10 AWG solid or stranded

**Product ID:** Ratings are permanently marked on device

**Termination:** Back or Side Wire

#### Product Features

**Color:** Orange

**NEMA:** 5-20R

**Brand:** SmartlockPro

**Function:** Isolated Ground GFCI

**Device Type:** Duplex Receptacle Outlet

**Grade:** Extra Heavy-Duty Hospital Grade

**Feature 2:** Tamper-Resistant

**Feature 3:** Power Indication

#### Standards and Certifications

**NEMA:** WD-1 & WD-6

**ANSI:** C-73

**Certification/Listing:** UL, CSA, NOM-ANCE

**Applicable Standards:** UL 943, UL 498, CSA C22.2 No. 42 & 144, FedSpec W-C-596


#### Warranty

**Product Warranty:** 2-Year Limited

Patents\*

CA2341552	US6788173
CA2358721	US6864766
CA2425810	US6944001
CA2427366	US7336458
CA2515035	US7355117
CA2621644	US7400479
CA2677283	US7463124
MX234458	US7697252
MX251584	US7737809
MX269232	US7764151
MX276411	US7820909
MX276626	US7868719
MX302458	US7907371
MX308495	US8004804
MX315596	US8054595
US6040967	US8130480
US6246558	US8242362
US6282070	US8547126
US6381112	US8587914
US6437953	US8599522
US6646838	US9053886
US6657834	US9077091

\*This list is provided for patent marking purposes only. A good faith effort is made to maintain the accuracy and completeness of this list. No legal inference should be drawn from the omission of a patent from this list.



**SPECIFICATION SUBMITTAL**

JOB NAME:		CATALOG NUMBERS:	
<input type="text"/>		<input type="text"/>	<input type="text"/>
JOB NUMBER:		<input type="text"/>	<input type="text"/>

**Leviton Manufacturing Co., Inc.**

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):  
+1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·  
FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-  
1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

**Visit our Website at: [www.leviton.com](http://www.leviton.com)**

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

**Leviton has a global presence.**

If you would like to know where your local Leviton office is located please go to:  
[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

