

Eaton type BR solar power center meter breaker

MBE2040PV200BTF

UPC:786685690315

Dimensions:

- **Height:** 36.06 IN
- **Length:** 5.91 IN
- **Width:** 14.27 IN

Weight:45 LB

Warranties:

- 10 year

Specifications:

- **Special Features:** Side by side construction
- **Type:** BR solar-ready
- **Amperage Rating:** 200A
- **Mounting:** Flush
- **Number Of Spaces:** 20
- **Voltage Rating:** 120/240V
- **Number Of Sockets:** 1
- **Phase:** Single-phase
- **Used With:** Type BR breakers
- **Bus Rating:** 225 A
- **Input:** 70 max PV input
- **Number Of Circuits:** 40
- **Bus Material:** Copper
- **Enclosure:** NEMA 3R
- **Feed Type:** Top/bottom
- **Main Circuit Breaker:** CSR

Supporting documents:

- [Solar power centers](#)
- [Eaton's Volume 15-Solar Inverters and Electrical Balance of System](#)
- [Eaton Specification Sheet - MBE2040PV200BTF](#)



Certifications:

- UL Listed

Product compliance:

- EUSERC Approved

© 2016 Eaton. All rights reserved.