



Specifications


Dimensions	1/4" X 1/2" (6mm X 12mm).
PVC body colour	Clear
LED spacing	1" (25.4mm)
Color Specifications	5300K - 6000K
Voltage	24 volt
Cutting Lengths	6" (152.4mm)
Maximum Length	90' (27.4m)
Power Consumption	0.96 watts/ft
Average LED Life	40,000 hours rated life at L70
Lumens	65lm/ft
Type LED	3020
CRI	70
Beam Angle	120°
Dimmable	Yes
Warranty	2 years
Min/Max Surface temperature for Mounting	-40°C – 40°C (-40°F – 104°F)




LES-003-2
(END CAP)



LES-001
(POWER CORD)



LES-002
(IN-LINE CONNECTOR)



Revisions:

4		
3		
2		
1		

Project:

Part number: LES-XX-CW

Scale: NTS

Product: LED ESTRIP COOL WHITE, SPACING 1"

Type:

Date: