


All Purpose Type Split Bolts - N-1/0SP

Drawn - SD	
Approved - KM	
Material - Copper / Finish: Tin Plated	
Title - All Purpose Type Split Bolts	
	
Max Run To Max Tap	1/0 - 1/0 Str AL CU
Min Run To Min Tap	2 - 10 Str AL CU
Max Run To Min Tap	1/0 - 10 Str AL CU
Min Equal Run - Tap	4 - 4 Str AL CU
4	Spacer Electrolytical Copper
3	Nut Bronze
2	Rider Bronze
1	Body Electrolytical Copper

