


## Vinyl Butt Connectors



**Drawn - SD**

**Approved - KM**

**Material - Copper Tube / Vinyl Insulation**

**Title - Vinyl Butt Connectors**



Part Number	Wire Range	Insulated Color	Electrical Rating Max	L	F	d	D
B22-V	22-18 AWG	Red	75C / 300V	1.024	0.591	0.063	0.161
B16-V	16-14 AWG	Blue	75C / 300V	1.024	0.591	0.091	0.177
B12-V	12-10 AWG	Yellow	75C / 300V	1.024	0.591	0.142	0.256
B8-V	8 AWG	Red	75C / 300V	1.398	0.827	0.177	0.335