



MBE1212L200BF  
MBE1212L200BS

DIMENSIONS TYPICAL ALL CAT. NO'S.



CMBE1212L200BF  
CMBE1212L200BS








TOP ENDWALL (SURFACE)	
DS200H2	
DS250H2	
DS300H2	
DS900AP (ADAPTER PLATE)	
HUB PROVISION	

TOP ENDWALL (STUCCO)	
1-1/4", 1-1/2", 2", 2-1/2"	1
1", 1-1/4", 1-1/2"	1
1/2", 3/4", 1"	1
1/2", 3/4"	5
1/2"	7
KNOCKOUT SIZE	QTY.

BOTTOM ENDWALL	
1/2"	7
1/2", 3/4"	4
1/2", 3/4", 1"	1
1", 1-1/4", 1-1/2", 2"	1
1-1/4", 1-1/2", 2", 2-1/2", 3"	1
KNOCKOUT SIZE	QTY.

MBE1212L200BS & F WIRE CONNECTORS			
	#6-250	LINE A, B & N	3
	#6-2/0	MOUNTS ON NEUT. BAR	4
	14-#4	NEUTRAL BAR	14
CAT. NO.	RANGE	LOCATION	QTY.

CMBE1212L200BS & F			
	#6-250	LINE A, B	3
	#6-2/0	MOUNTS ON NEUT. BAR	4
	#14-#4	NEUTRAL BAR	20
CAT. NO.	RANGE	LOCATION	QTY.



FILE DESCRIPTION	METER BREAKER WEST COAST STYLE	DRAWING NUMBER	96-5442	DATE (YYMMDD)	2013/12/16
THE INFORMATION ON THIS DRAWING IS DISCLOSED IN CONFIDENCE AND IS NOT TO BE REPRODUCED, USED OR DISCLOSED, EXCEPT FOR THE PURPOSE WHICH FURNISHED.			SCALE	N/A	SHEET 1 OF 1
<small>© 2013 Eaton Corporation. All Rights Reserved.</small>		<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS IN INCHES</small>		<small>DBD, DPM, ACAD, WEB, DWG</small>	