



SCREW: NONE	MATERIAL: COPPER	REV: R	 800-776-9775 www.ilSCO.com
CAT. NO.: SEE CHART	PLATING: EL-TIN	DRAWN BY: NN	
INFORMATION SHEET: FORM 155	MARKING: SEE DRAWING	DATE: 3/10/2008	
		SCALE:	DWG NO: R1571 THRU R1609,
		SIZE: B	SHEET: 3 OF 3 R1847 & R1848



MANUFACTURING SPECS										
ILSCO PART	CATALOG #	WIRE SIZE	OVERALL LENGTH	PAD THICKNESS	PAD WIDTH	HOLE SIZE	TIP TO HOLE CENTER	BARREL LENGTH (MIN)	FLEX WIRE SIZE	INK MARK COLOR
			B	C	D	E	G	H		
R1600C00T	CCL-2/0-38	2/0	2.060	.11	.815	.402	.430	.650	2/0 AWG / 1/0 FLEX	BLACK
R1600C00T	CRA-1/0-38M	2/0	2.060	.11	.815	.402	.430	.650	2/0 AWF / 1/0 FLEX	BLACK
R1600C01T		2/0	2.060	.11	.815	.402	.430	.650	2/0 AWG / 1/0 FLEX	BLACK
R1601C00T	CCL-2/0-12	2/0	2.060	.11	.815	.522	.430	.650	2/0 AWG / 1/0 FLEX	BLACK
R1601C00T	CRA-1/0-12M	2/0	2.060	.11	.815	.522	.430	.650	2/0 AWG / 1/0 FLEX	BLACK
R1601C01T		2/0	2.060	.11	.815	.522	.430	.650	2/0 AWG / 1/0 FLEX	BLACK
R1602C00T	CCL-3/0-14	3/0	2.160	.12	.895	.276	.465	.675	3/0 AWG / 2/0 FLEX	ORANGE
R1602C00T	CRA-2/0-14M	3/0	2.160	.12	.895	.276	.465	.675	3/0 AWG / 2/0 FLEX	ORANGE
R1602C01T		3/0	2.160	.12	.895	.276	.465	.675	3/0 AWG / 2/0 FLEX	ORANGE
R1603C00T	CCL-3/0-516	3/0	2.610	.12	.895	.338	.465	.675	3/0 AWG / 2/0 FLEX	ORANGE
R1603C00T	CRA-2/0-516M	3/0	2.160	.12	.895	.338	.465	.675	3/0 AWG / 2/0 FLEX	ORANGE
R1603C01T		3/0	2.160	.12	.895	.338	.465	.675	3/0 AWG / 2/0 FLEX	ORANGE
R1604C00T	CCL-3/0-38	3/0	2.160	.12	.895	.402	.465	.675	3/0 AWG / 2/0 FLEX	ORANGE
R1604C00T	CRA-2/0-38M	3/0	2.160	.12	.895	.402	.465	.675	3/0 AWG / 2/0 FLEX	ORANGE
R1604C01T		3/0	2.160	.12	.895	.402	.465	.675	3/0 AWG / 2/0 FLEX	ORANGE
R1605C00T	CCL-3/0-12	3/0	2.160	.12	.895	.522	.465	.675	3/0 AWG / 2/0 FLEX	ORANGE
R1605C00T	CRA-2/0-12M	3/0	2.160	.12	.895	.522	.465	.675	3/0 AWG / 2/0 FLEX	ORANGE
R1605C01T		3/0	2.160	.12	.895	.522	.465	.675	3/0 AWG / 2/0 FLEX	ORANGE
R1606C00T	CCL-4/0-14	4/0	2.390	.13	1.035	.276	.525	.700	4/0 AWG / 3/0 FLEX	PURPLE
R1606C01T		4/0	2.390	.13	1.035	.276	.525	.700	4/0 AWG / 3/0 FLEX	PURPLE
R1607C00T	CCL-4/0-516	4/0	2.390	.13	1.035	.338	.525	.700	4/0 AWG / 3/0 FLEX	PURPLE
R1607C01T		4/0	2.390	.13	1.035	.338	.525	.700	4/0 AWG / 3/0 FLEX	PURPLE
R1608C00T	CCL-4/0-38	4/0	2.390	.13	1.035	.402	.525	.700	4/0 AWG / 3/0 FLEX	PURPLE
R1608C00T	CRA-3/0-38M	4/0	2.390	.13	1.035	.402	.525	.700	4/0 AWG / 3/0 FLEX	PURPLE
R1608C01T		4/0	2.390	.13	1.035	.402	.525	.700	4/0 AWG / 3/0 FLEX	PURPLE
R1609C00T	CCL-4/0-12	4/0	2.390	.13	1.035	.522	.525	.700	4/0 AWG / 3/0 FLEX	PURPLE
R1609C00T	CRA-3/0-12M	4/0	2.390	.13	1.035	.522	.525	.700	4/0 AWG / 3/0 FLEX	PURPLE
R1609C01T		4/0	2.390	.13	1.035	.522	.525	.700	4/0 AWG / 3/0 FLEX	PURPLE
R1847C00T	CRA-4/0-12M	250	2.650	.130	1.200	.522	.605	.725	250kcmil / 4/0 FLEX	YELLOW
R1848C00T	CRA-4/0-38M	250	2.650	.130	1.200	.402	.605	.725	250 kcmil / 4/0 FLEX	YELLOW