



## September 2018

### Counter Days & Events

September 12th  
Northeast Marketing  
Fairfield 7-10

Klein  
Norwalk 7-10

Leviton  
Hartford 7-10

September 18th  
Old Saybrook 7-10

September 19th  
ETI & Keystone  
New London 7-10

September 20th  
Acuity  
New London 7-10

September 25th  
Acuity  
Middletown 7-10

Rack-a-Tier  
Old Saybrook 7-10


September 26th  
Northeast Marketing  
Bristol 7-10:30

September 27th  
RAB  
Norwich 11-1

[Click Here to View More](#)

## What's New at EW?

### ECommerce Update



Did you know that you can shop from pre-made lists for top ordered products and jobs on our website? Simply click on "Shop By Lists" in the top left hand corner. Select from lists such as: Ballasts, Bathroom Fans, Conduit Run, Datacom, Electric Heat, LED Retrofit, Receptacles, Switches, and Wall plates, Residential Service Entrance, Tools, and Wire and Wiring Supplies. Search through a short list of frequently purchased products to find what you need. Ordering supplies has never been easier. Order by 7pm for next day pick-up/delivery when your items show in stock through our live pricing and inventory tool!

**Register Today at [www.ew-ct.com](http://www.ew-ct.com)**



## Bill Trust



Click Here to view More...

## Price Increases

Throughout September, the following vendors will be implementing price increases:

- Acme
- B-line
- Broan Nutone
- Bussman
- Konkore
- Lambro
- Nuheat/Raychem
- Rabo/Bell
- Wiegmann
- IlSCO
- Quazite
- Killark
- Wattstopper
- GE/ABB
- Hubbell Wiring Devices



Making a payment on your account has never been easier. With our online Bill Trust system, you can check your account balance with a simple log in. Never worry the night before your balance becomes overdue. Our online Bill Trust website is open for payment 24/7. To sign up, all you need is your EW Account Number and a recent invoice number. After you have created your Bill Trust account, you will be able to access your protected account from anywhere you choose.

**Register for Bill Trust Here!**

## Featured Products

### Tamper Resistant Receptacles

INSTALL

#### Leviton: How-to Install

T5320, T5820, Decora® T5325 and T5825 and Renu® RER15 and RER20 Tamper Resistant Receptacles



#### T5320 I/W/T

- Designed for chic appearance
- Quick installation
- Durable
- Long service life
- High performance in homes, offices, schools, and other settings
- Impact-resistant thermoplastic nylon face and body

### EPANL LED Flat Panel



#### EPANL 22-34L-40K

- Fully luminous lens offers glare free light
- Access plate on the back of the fixture for easy access to electrical compartment
- Long-life LED system is coupled with driver for enhanced performance
- Driver dims to 10%
- Suitable for my applications, including schools

[Click Here to Learn More](#)

Now on Sale at Your Local EW!



[Click Here to Learn More](#)

Available Now at Our CDC!



## New Products

### Breakaway Ground Rod Clamp



#### G5810B

- Breakaway bolt head for better torque and tamper resistance
- Body made of silicone bronze
- Suitable for direct burial applications
- Clamp is UL Listed
- 5/8" ground rod support
- Accommodates a conductor of size 1/10-8 AWG

[Click Here to Learn More](#)



### Plenum Rated Control Cable



#### G101602-PG

- Solid bare copper plenum rated control cable
- Has two solid conductors of size 16 AWG
- 100% layer 1 Duofoil® tape aluminum foil-polyester tape
- 65% layer 2 braid tinned copper shielding
- Voltage rating of 300V
- Suitable for power limited control circuits

[Click Here to Learn More](#)

### LIL LED Wall Luminaire

#### LIL-LED-30K-MVOLT-DBBTXD-M12 & LIL-LED-40K-MVOLT-DBBTXD-M12

- Compact and energy efficient
- Photocell and battery pack options
- Great for installation above doors, balconies, garage or warehouse entrances, and security applications
- Easily mounts to recessed junction boxes or for surface mounting and conduit entry

[Click Here to Learn More](#)



### Offset Al Mech Pin Adapter



#### KAPO350 & KAPO1/0

- AL9CU Dual Rated for both copper and aluminum conductor
- Listed to UL Wire Connector Standard UL 486A-486B
- Rated for use with Fine Strand Conductor
- 600 Volt Rated
- Range taking conductor port

[Click Here to Learn More](#)

## Self-Regulating Heating Cable



### SR51J250, SR52J250, SR52J750

- Self regulating, pre-terminated cable
- Suitable for use on asphalt or wood shingles, metal roofing, or "membrane" type roofing, and downspouts that freeze and clog
- For commercial and residential applications
- All cable outer jackets are constructed of waterproof polyolefin material
- Applicable for freeze protection and temperature maintenance of metal and non-metallic pipe

[Click Here to Learn More](#)

### Also Available: SR-P Power Connection Kit

- Includes the SRP/SRPC power/splice connection kit, SRST in-line splice connection kit, SRES end seal kit, SRTCS tape and "caution" signs, GFST1 line plug, SRME end seal kit, and SRMPY power end connection kit.

[Click Here to Learn More](#)

## Ground Clamp to Steel Connector



### GCS26

- Direct burial rated for installation into earth and concrete
- Accepts beam thickness: .125 - .625" (1/8 to 5/8")
- Conductor range from #6 to 2/0
- Versatile, allows parallel or perpendicular conductor orientation
- Stainless steel hardware
- Applicable for use in "extremely volatile environments"
- No special tooling required for installation

[Click Here to Learn More](#)