

September
2018

Plug Into Zimmies

Electrical Newsletter



This month:

- Industry News
- Safety Message
- ECommerce Message
- Counter Days and Events
- Price Increases
- New Products



IDEAL announce that the 2018 National Championship qualifying round has been extended to October 19th. The "Nationals" has been extremely popular across Canada, and with this extension IDEAL will be better able to meet the demand to hold qualifying events, particularly from colleges and trade schools.

[Click Here to Read on](#)



Most contractors may know the code requirements but do not understand the correct detector type for all applications nor the limitation for the detector types. For example, the spot-type smoke detector has a maximum allowed spacing of 30 feet on center and 15 feet from a wall; however, does this spacing work for all applications? The short answer is no. The spacing should first be determined based on the detection goals of the owner.

[Click Here to Read on](#)

Counter Days and Events



September 13th
Meriden Tent Day
2:00pm - 6:00pm

Price Increases



The following vendors will have price increases starting September 1st:

- Acme
- B-Line
- Broan Nutone
- Bussman
- Konkore
- Lambro
- Nuheat/Raychem
- Quazite
- Raco/Bell
- Wiegmann


Purchase your next Smoke Detector Here



Did you know that you can shop from pre-made lists for top ordered products and jobs on our website? Simply click on "Shop By Lists" in the top left hand corner. Select from lists such as: "Ballasts", "Conduit", "Receptacles, Switches, and Wall Plates", "Tools," and "Wire and Wiring Supplies." Search through a short list of frequently purchased products to find what you need. Ordering supplies has never been easier. Order by 7pm for next day pick-up/delivery when your items show in stock through our live pricing and inventory tool!

Start Ordering Now!

- IlSCO
- Killark
- P&S
- Wattstopper
- Hubbell Wiring Devices



Download our Mobile App!



Featured Products

Tamper Resistant Receptacle


INSTALL

Leviton: How-to Install

T5320, T5820, Decora® T5325 and T5825 and Renu® RER15 and RER20 Tamper Resistant Receptacles



EPANL LED Flat Panel



EPANL LED Flat Panel

T5320 I/W/T

- Designed for chic appearance
- Quick installation
- Durable
- Long service life
- High performance in homes, offices, schools, and other settings

EPANL 22-34L-40K

- Fully luminous lens offers glare free light
- Access plate on the back of the fixture for easy access to electrical compartment
- Long-life LED system is coupled with driver for enhanced performance
- Driver dims to 10%

- Impact-resistant thermoplastic nylon face and body

[Click Here to Learn More](#)

Now on Sale at Your Local HZ!



- Suitable for many applications, including schools

[Click Here to Learn More](#)

Now Available at Our CDC!



New Products

Breakaway Ground Rod Clamp



G5810B

- Breakaway bolt head for better torque and tamper resistance
- Body made of silicone bronze
- Suitable for direct burial applications
- Clamp is UL Listed
- 5/8" ground rod support
- Accommodates a conductor of size 1/10-8 AWG

[Click Here to Learn More](#)



Control Cable



G101602-PG

- Solid bare copper plenum rated control cable
- Has two solid conductors of size 16 AWG
- 100% layer 1 Duofoil® tape aluminum foil-polyester tape
- 65% layer 2 braided tinned copper shielding
- Voltage rating of 300V
- Suitable for power limited control circuits

Lil LED Wall Luminaire



LIL-LED-30K-MVOLT-DDBTXD-M12 & LIL-LED-40K-MVOLT-DDBTXD-M12

- Compact and energy efficient
- Photocell and batter pack options
- Great for installation above doors, balconies, garage or warehouse entrances, and security applications
- Easily mounts to recessed junction boxes or for surface mounting and conduit entry

[Click Here to Learn More](#)



Offset Al Mech Pin Adapter



KAPO350 & KAPO1/0

- AL9Cu Dual Rated for both copper and aluminum conductor

[Click Here to Learn More](#)

OMNICABLE

Self-Regulating Heating Cable



SR51J250, SR52J250, SR52J750

- Self regulating, pre-terminated cable
- Suitable for use on asphalt or wood shingles, metal roofing, or "membrane" type roofing, and downspouts that freeze and clog
- For commercial and residential applications
- All cable outer jackets are constructed of waterproof polyolefin material
- Applicable for freeze protection and temperature maintenance of metal and non-metallic pipe

[Click Here to Learn More](#)

Also Available SR-P Power Connection Kit

- Includes the SRP/SRPC power/splice connection kit, SRST in-line splice connection kit, SRES end seal kit, SRTCS tape and "caution" signs, GFST1 line plug, SRME end seal kit, and SRMPY power end connection kit.

[Click Here to Learn More](#)


EMERSON[™]

- Listed to UL Wire Connector Standard UL 486A-486B
- Rated for use with Fine Strand Conductor
- 600 Volt Rated
- Range taking conductor port

[Click Here to Learn More](#)


BURNDY[®]

Ground Clamp to Steel Connector



GCS26

- Direct burial rated for installation into earth and concrete
- Accepts beam thickness .125 - .625" (1/8 to 5/8")
- Conductor range from #6 to 2/0
- Versatile, allows parallel or perpendicular conductor orientation
- Stainless steel hardware
- Applicable for use in "extremely volatile environments"
- No special tooling required for installation

[Click Here to Learn More](#)


BURNDY[®]