

**USA PRODUCT GUIDE**  
VEHICLE AND MOBILE  
STORAGE SYSTEMS






# ROLA-CASE

## MULTIPLE STORAGE SYSTEMS

The world's market & technology leader  
of vehicle & mobile storage systems

- Innovative & flexible
- Robust design
- Smart design principle
- Safe and quiet in transit
- High load capabilities
- Engineer designed



### 4 Step System

- 1.** Measure the height of your vehicle. If your vehicle height is  $60 \frac{19}{32}$ " or lower, then the appropriate post height is 1539. If your vehicle height is between  $60 \frac{19}{32}$ " &  $78 \frac{31}{32}$ ", then the appropriate post height is 2006. All posts can be cut down in  $1 \frac{1}{32}$ " intervals to achieve your desired height.
- 2.** Determine the length of space in your cargo area. You always start with a start frame e.g. RSSFR/HD/80/1539. If you want to grow it further, then you simply add an extension frame, which can be any length e.g. RSEFR/HD/40/1539.
- 3.** Choose how many shelves you require to fit into your bay/s.
- 4.** Choose your plastic bins & accessories (if required).

# ROLA•Shelf

## VEHICLE STORAGE SOLUTIONS




The ultimate solution in van racking, shelving, vehicle accessories & mobile storage systems. Engineer designed, tested & manufactured in Australia since 1985.

**ROLA•CASE & ROLA•Shelf** is recognized across Australia & internationally as a leading manufacturer of shelving, racking & storage solutions for vehicles, boats & the workplace. Our modular van shelving & tool storage design principle creates flexible solutions unique to your mobile & static application.

10 year warranty on **ROLA•Shelf** van racking products. See online for terms & conditions.




## The ultimate in vehicle and mobile storage systems



- |                            |   |   |   |
|----------------------------|---|---|---|
| <b>1</b> RSSFR/HD/40/1539  | 4 Series Heavy duty start frame                   | <b>19</b> RSSHL/84                                    | Mid mount shelf with 2 x RP120 plastic bins                           |
| <b>2</b> RSEFR/HD/40/1539  | 4 Series Heavy duty extension frame               | <b>20</b> RSLBX/84                                    | Lockable box mounted horizontally                                     |
| <b>3</b> RSEFR/HD/80/1539  | 8 Series Heavy duty extension frame               | <b>21</b> RCSK2/C + RCSK3/C + 1 x RSBAR/80            | Rola-Case cabinet kits  |
| <b>4</b> RSEFR/HD/120/1539 | 12 Series Heavy duty extension frame              | <b>22</b> RSFLE + RS840A                              | Floor enclosure with removable front angle                            |
| <b>5</b> RSGAC/41          | Vented Gas, Oxy and Acetylene storage cabinet     | <b>23</b> RSCAB/81                                    | Large 3 shelf lockable cabinet with contoured body                    |
| <b>6</b> RCSK6/C           | Rola-Case cabinet kit                             | <b>24</b> RSSHL/86                                    | Floor mount shelf with 2 x RP240 plastic bins (dividers not included) |
| <b>7</b> RSFLE + RS420A    | Floor enclosure with removable front angle        | <b>25</b> RSSHL/85 + RSSHL/81/FR                      | Mid mount shelf with file retainer                                    |
| <b>8</b> RSSHL/43          | High mount shelf with 3 x RP25 plastic bins       | <b>26</b> RCSK5/C + RCSK4/C + 2 x RSBAR/80 + 2 x RC5D | Cabinet kits  |
| <b>9</b> RSSHL/44          | Mid mount shelf with 1 x RP120                    | <b>27</b> RSSHL/87                                    | Low mount shelf with 2 x Rolacases & RS/87/FW- Foam                   |
| <b>10</b> RSSHL/45         | Low mount shelf with 4 x RP100 plastic bins       | <b>28</b> RSCDH/81                                    | Adjustable cable Reel holder  |
| <b>11</b> RSSHL/48         | Low mount shelf with 2 x RP400x200 plastic bins   | <b>29</b> RSSHL/123                                   | High mount shelf with 9 x RP25 plastic bins                           |
| <b>12</b> RSGBH/41         | Gas bottle holder (gas bottle not included)       | <b>30</b> RSSHL/124                                   | Mid mount shelf with 3 x RP120  |
| <b>13</b> RSLBX/81         | Lockable box mounted vertically                   | <b>31</b> RSSHL/125                                   | Low mount shelf with 12 x RP100 plastic bins                          |
| <b>14</b> RSCDH/41         | Adjustable cable Reel holder                      | <b>32</b> RSSHL/128                                   | Floor mount shelf with 6 x RP400x200 plastic bins                     |
| <b>15</b> RSSHL/83         | High mount shelf with 6 x RP25 plastic bins       | <b>33</b> RSSHL/126                                   | Floor mount shelf with 3 x RP240 plastic bins & 3 x RP240/D Dividers  |
| <b>16</b> RSSHL/85         | Low mount shelf with 8 x RP100 plastic bins       |   |   |
| <b>17</b> RCBKE/3          | Holds 3 x RC001 cases (Inc. rubber mat and strap) |   |   |
| <b>18</b> RSSHL/88         | Floor mount shelf with 8 x RP400x200 plastic bins |   |   |

**Disclaimer** If any product is installed incorrectly or used in an incorrect manner, no liability will be taken for product malfunction or personal injury.

# The system that grows with you



34 1/16"

50 19/32"



▲ The configuration of shelves and plastic bins depicted above allows for storage of large, medium and small components typical of today's tradesman and technician's requirements.

**ROLA-Shelf** will fit all vehicles where shelving is required including; commercial vans, Box Trucks & trailers.

Honda off road vehicle at the Dakar event in South America. Rolacase products in picture include 4 x RCSR5/C cabinet kits

*Glenn Hoffman : Honda Dakar Rally*

*I've been using the RolaCase System now for well over 12 years taking the cabinet kits all over the world twice with the off- road Darker Rally and through some of the toughest terrain known to men. There is no doubt the RolaCase systems are built to last.*



# Contents



## Contents

- 07** RolaCase Introduction
- 08** Cases
- 09** Drawer Cabinets
- 10** Cabinet Kits
- 11** 12 Series Van Shelving
- 12** 8 Series Van Shelving
- 13** 4 Series Van Shelving
- 14** End Panels & Accessories
- 15 - 16** Sample Builds
- 17** Sliding Platforms





# ROLA-CASE

Cases & Cabinets



**1**

**SELECT YOUR CASE(S)**

**2**

**SELECT YOUR CABINET**

**3**

**SECURE YOUR CABINET**

**ROLA-CASE** is a versatile storage system for the transfer & handling of components, tools & instruments.

The range includes mobile workstations that allow the movement of tools and equipment in a workshop or service area. The cabinet and metal drawer systems are ideal for vehicle and static use.

Cabinets are ideally secured to the inside of vehicles, truck bodies, ships & the workplace.



**Limited lifetime warranty\***

On **ROLA-CASE** cases & cabinets.



**Made in Australia**

Engineer designed, tested & manufactured



**Cabinet Versatility**

Cabinets & frames can be joined vertically & / or horizontally, as well as having the ability to be fixed/mounted to any object.



**Ready to use**

Cabinets come pre-assembled



Works with **ROLA-Shelf**

**ROLA-CASE** products fit into the **ROLA-Shelf** vehicle equipment



**Available Worldwide**

\* Please refer to website for full terms & conditions





# ROLA-CASE

MULTIPLE STORAGE SYSTEMS

## Cases

All cases are manufactured from engineering polymers, ABS, Polycarbonate & Nylon 66. They are also moulded with a 3-5mm wall section & use stainless steel for the hinge & latch-spring to ensure extended product life.

- Sturdy locking clips
- Corrosion proof
- Divided cases do not allow contents to mix when shaken or turned upside down
- Various configurations
- Adjustable compartments
- Lid opens (180°)
- Movable Handle

**RCTRY**.....



Small tray with 4 adjustable compartments. Suits **RC001** series cases. Includes new clear micro component storage unit.



**RC001/CH-CL**



20 adjustable compartments, 1 tool compartment in front of case. Comes with 9 **RCPLD** dividers. Polycarbonate lid  
Dimensions: W:  $14 \frac{9}{16}$ ", D:  $14 \frac{9}{16}$ ", H:  $3 \frac{11}{32}$ "

**RC001/CH**



20 adjustable compartments, 1 tool compartment in front of case. Comes with 9 **RCPLD** dividers  
Dimensions: W:  $14 \frac{9}{16}$ ", D:  $14 \frac{9}{16}$ ", H:  $3 \frac{11}{32}$ "

**RC001**



20 adjustable compartments, 1 tool compartment in front of case. Comes with 9 **RCPLD** dividers  
Dimensions: W:  $14 \frac{9}{16}$ ", D:  $14 \frac{9}{16}$ ", H:  $3 \frac{11}{32}$ "

**RC001/CL**



20 adjustable compartments, 1 tool compartment in front of case. Comes with 9 **RCPLD** dividers. Polycarbonate lid  
Dimensions: W:  $14 \frac{9}{16}$ ", D:  $14 \frac{9}{16}$ ", H:  $3 \frac{11}{32}$ "

**RC002**



1 large compartment, 1 tool compartment in front of case.  
Dimensions: W:  $14 \frac{9}{16}$ ", D:  $14 \frac{9}{16}$ ", H:  $3 \frac{11}{32}$ "

**RC002/CL**



1 large compartment, 1 tool compartment in front of case. Polycarbonate lid.  
Dimensions: W:  $14 \frac{9}{16}$ ", D:  $14 \frac{9}{16}$ ", H:  $3 \frac{11}{32}$ "

**RC003/QK**



1 large compartment, plus 3 compartment lift-out tray with further compartments below, 1 tool compartment. Includes Quik Kit (**QK001/B**)  
Dimensions: W:  $14 \frac{9}{16}$ ", D:  $14 \frac{9}{16}$ ", H:  $5 \frac{1}{8}$ "

**RC003/CL**



1 large tool compartment, plus 3 compartment lift-out tray with further compartments below. Polycarbonate lid  
Dimensions: W:  $14 \frac{9}{16}$ ", D:  $14 \frac{9}{16}$ ", H:  $5 \frac{1}{8}$ "  
Accessories: **RC003/D** (3 dividers for case. Sold Separately)

**RC003**



1 large tool compartment, plus 3 compartment lift-out tray with further compartments below. Polycarbonate lid  
Dimensions: W:  $14 \frac{9}{16}$ ", D:  $14 \frac{9}{16}$ ", H:  $5 \frac{1}{8}$ "  
Accessories: **RC003/D** (3 dividers for case. Sold Separately)

**RC003/D**



Dividers to suit **RC003** cases. Each case holds max. 3 dividers.

**RCPLD**



Available in Orange & Charcoal  
Divider for **RC001** cases

**QK001**



10 small compartments, 1 large tool compartment in front of case.  
Dimensions: W:  $12 \frac{13}{64}$ ", D:  $8 \frac{17}{64}$ ", H:  $1 \frac{31}{32}$ "

**QK001/B**

**RCVCH**



Vertical Case Holder. Holds **RC001**, **RC002** or **RC003** series cases. Ideal for wall or end panel mounting.  
Dimensions: H:  $5 \frac{29}{32}$ " W:  $14 \frac{9}{16}$ "





**ROLA-CASE**  
MULTIPLE STORAGE SYSTEMS

# Drawer Cabinets

## RC2DC



Holds 2 x **RC001** or **RC002** series cases  
Dimensions: W. 16 1/2", D. 18 7/64", H. 9 1/16"

## RC3DC



Holds 3 x **RC001** or **RC002** series cases  
Dimensions: W. 16 1/2", D. 18 7/64", H. 12 51/64"

## RC3DC/2D



Holds 2 x **RC003** series cases  
Dimensions: W. 16 1/2", D. 18 7/64", H. 12 51/64"

## RC4DC



Holds 4 x **RC001** or **RC002** series cases  
Dimensions: W. 16 1/2", D. 18 7/64", H. 16 17/32"

## RC4DC/3D



Holds 2 x **RC003** and 1 x **RC001** series cases  
Dimensions: W. 16 1/2", D. 18 7/64", H. 16 17/32"

## RC5DC



Holds 5 x **RC001** or **RC002** series cases  
Dimensions: W. 16 1/2", D. 18 7/64", H. 21 17/32"

## RC5DC/4D



Holds 2 x **RC001** or **RC002** & 2 x **RC003** series cases  
Dimensions: W. 16 1/2", D. 18 7/64", H. 21 17/32"

## RC7DC



Holds 7 x **RC001** or **RC002** series cases  
Dimensions: W. 16 1/2", D. 18 7/64", H. 29 1/4"

## RC7DC/PN



Trolley with 8 21/32" pneumatic tires. Ideal for stairs or uneven surfaces.

Holds 7 x **RC001** & **RC002** series cases

Dimensions: W. 16 1/2", D. 18 7/64", H. 39 3/8"

## RC7DC/PN/6D



Holds 4 x **RC001** & **RC002** cases and 2 x **RC003** series cases  
Dimensions: W. 16 1/2", D. 18 7/64", H. 39 3/8"

## RC7DC/DM



Holds 7 x **RC001** or **RC002** cases & 2 x **RC003** series cases  
Dimensions: W. 32 63/64", D. 18 7/64", H. 39 3/8"  
(Shelf not included)

## RCC/TT/40

Top Tray Fits to Rolacase Cabinets



## RCC/TT/40/T

Top Tray Fits to Rolacase single Trolleys





# ROLA-CASE

MULTIPLE STORAGE SYSTEMS

# Cabinet Kits

**ROLA-CASE** cabinet kits can be fitted with a lockable door (order separately) for added security

The **ROLA-CASE** cabinet kits can be joined vertically &/or horizontally to create nearly any modular configuration & come with a durable latch locking mechanism.

- All cabinets are compatible with the 4 series shelving
- 2 cabinets can be joined horizontally to fit the 8 series shelving  
(1 x RCJNR/C & 1 x RSBAR/80 will be required)

## RCSK1/C



1 x RC2DC, 1 x RC001/CL & 1 x RC002/CL  
Dimensions:  
W: 16 1/2", D: 18 7/64", H: 9 1/16"

## RCSK2/C



1 x RC3DC & 3 x RC001/CL series cases  
Dimensions:  
W: 16 1/2", D: 18 7/64", H: 12 51/64"

## RCSK3/C



1 x RD3DC/2D, 1 x RC003/CL & 1 x RC003/QK.  
Dimensions:  
W: 16 1/2", D: 18 7/64", H: 12 51/64"

## RCSK4/C



1 x RC5DC & 5 x RC001/CL series cases  
Dimensions:  
W: 16 1/2", D: 18 7/64", H: 21 17/32"

## RCSK5/C



1 x RC5DC/4D & 1 x RC001/CL, 1 x RC002/CL, 1 x RC003/CL & 1 x RC003/QK series cases  
Dimensions: W: 16 1/2", D: 18 7/64", H: 21 17/32"

## RCSK6/C



1 x RC4DC, 2 x RC001/CL & 2 x RC002/CL  
Dimensions:  
W: 16 1/2", D: 18 7/64", H: 16 17/32"

## RCSK7/C



1 x RC4DC/3D, 1 x RC001/CL, 1 x RC003/CL & 1 x RC003/QK  
Dimensions: W: 16 1/2", D: 18 7/64", H: 16 17/32"

## RCSK8/C



1 x RC7DC, 7 x RC001/CL  
Dimensions:  
W: 16 1/2", D: 18 7/64", H: 29 1/4"

## RCKIT40/5



RC3/40 cabinet with 2 x RC401 metal drawers, 1 x RC001/CL  
Dimensions: W: 16 1/2", D: 18 7/64", H: 12 51/64"

## RCKIT40/8



RC4/40 cabinet with 2 x RC403 & 1 x RC401 metal drawers.  
Dimensions:  
W: 16 1/2", D: 18 7/64", H: 16 17/32"

## RCSK7PN/C

Trolley with 8 21/32" pneumatic tires. Ideal for stairs or uneven surfaces.  
1 x RC7DC/PN, 4 x RC001/CL & 3 x RC002/CL.



Dimensions: W: 16 1/2", D: 18 7/64", H: 39 3/8"

## RC7DC/PN/6D

Trolley with 8 21/32" pneumatic tires. Ideal for stairs or uneven surfaces.  
1 x RC7DC/PN/6D, 2 x RC001/CL & 2 x RC002/CL, 1 x RC003/CL & 1 x RC003/QK with carpet insert.



Dimensions: W: 16 1/2", D: 18 7/64", H: 39 3/8"

## RCDK7M/C

1 x RC7DC/DM (dual trolley), 4 x RC002/CL, 3 x RC001/CL & 1 x RC003/QK & 1 x RC003/CL



Dimensions: W: 32 63/64", D: 18 7/64", H: 39 3/8"

## RC3D



Door to fit: RC3DC, RC3DC/2D, RCSK2/C, RCSK3/C

## RC4D



Door to fit: RCSK7/C, RCSK6/C, RC4DC/3D, RC4DC

## RC5D



Door to fit: RC5DC, RC5DC/4D, RCSK5/C, RCSK4/C

## RC7D



Door to fit: RC7DC/PN, RCDK7M/C (X2), RCSK7PN/C, RCSK7PN6D/C, RCSK8/C, RC7DC

## RCWHL/PN



Pneumatic wheel kit for single modular mobile workstation. Comes with 2 x 8 21/32" pneumatic tires, 2 x swivel locking wheels & all necessary bracing & fixing components.

## RCHDL



Single mobile hands to fit pneumatic wheels kit.

## RCJNR/C



Vertical joining brackets for connecting ROLA-CASE cabinets vertically. (4 per kit plus screws)





### 4 Step System

- 1:** Measure the height of your vehicle. If your vehicle height is  $60 \frac{19}{32}$ " or lower, then the appropriate post height is 1539. If your vehicle height is between  $60 \frac{19}{32}$ " &  $78 \frac{31}{32}$ ", then the appropriate post height is 2006. All posts can be cut down in  $1 \frac{1}{32}$ " intervals to achieve your desired height.
- 2:** Determine the length of space in your cargo area. You always start with a start frame i.e. RSSFR/HD/120/1539. If you want to grow it further, then you simply add an extension frame, which can be any length e.g. RSEFR/HD/40/1539.
- 3:** Choose how many shelves you require to fit into your bay/s.
- 4:** Choose your plastic bins & accessories (if required).

CAT NO;	HEIGHT (inches)	LENGTH (inches)	DESCRIPTION
RSSFR/HD/120/2006	$78 \frac{31}{32}$ "	$51 \frac{37}{64}$ "	12 Series Dual Post Heavy Duty Start Frame
RSSFR/HD/120/1539	$60 \frac{19}{32}$ "		
RSEFR/HD/120/2006	$78 \frac{31}{32}$ "	$50 \frac{19}{32}$ "	12 Series Dual Post Heavy Duty Extension Frame
RSEFR/HD/120/1539	$60 \frac{19}{32}$ "		

Post Height Adjustment	
Height	Cut at $1 \frac{1}{32}$ " Intervals
$78 \frac{31}{32}$ "	← → $60 \frac{19}{32}$ "
$60 \frac{19}{32}$ "	← → $42 \frac{1}{4}$ "

Frame Purchase Example: **RSSFR/HD/120/1539**  
 If you want to extend then you would add a **RSEFR/HD/120/1539**  
 All components are zinc annealed & powder coated, complete with instructions & mounting hardware.

SHELF	CAT NO;	DESCRIPTION	HEIGHT	LENGTH	WIDTH	PLASTIC BINS
	RSSHL/123	High mount shelf	Rear $3 \frac{35}{64}$ " Front $1 \frac{49}{64}$ "	$49 \frac{9}{16}$ "	$9 \frac{1}{16}$ "	Holds 9 x <b>RP25</b> bins
	RSSHL/124	Mid mount shelf	Rear $3 \frac{35}{64}$ " Front $1 \frac{49}{64}$ "	$49 \frac{9}{16}$ "	$10 \frac{3}{64}$ "	Holds 3 x <b>RP120</b> bins or 6 x <b>RP60</b>
	RSSHL/125	Low mount shelf	Rear $3 \frac{35}{64}$ " Front $1 \frac{49}{64}$ "	$49 \frac{9}{16}$ "	$12 \frac{1}{64}$ "	Holds 6 x <b>RP200</b> bins or 12 x <b>RP100</b>
	RSSHL/126	Floor mount shelf	Rear $6 \frac{39}{64}$ " Front $3 \frac{5}{32}$ "	$49 \frac{9}{16}$ "	$15 \frac{15}{16}$ "	Holds 6 x <b>RP400x200</b> or Holds 3 x <b>RP240</b> bins
	RSSHL/128	Floor mount shelf	Rear $3 \frac{25}{64}$ " Front $2 \frac{9}{16}$ "	$49 \frac{9}{16}$ "	$15 \frac{15}{16}$ "	Holds 6 x <b>RP400x200</b> or 12 x <b>RP400x100</b>

### ACCESSORIES FOR 12 SERIES:

#### RSCDH/121



Adjustable Cable Drum Holder for 12 Series Shelving

#### RSWB/120



Mid mount work bench. 1.9mm galvanised steel

#### RSLBX/122



Lockable box for 12 Series shelving

Dimensions:

A:  $15 \frac{1}{2}$ "

B:  $16 \frac{17}{32}$ "

C:  $49 \frac{9}{16}$ "

\*with TShelf



Example Order:  
**RSLBX/122/TS**

Please refer to "End Panels & Accessories page" for all the other accessories and plastic bins




# ROLA-CASE

MULTIPLE STORAGE SYSTEMS

## 8 Series Van Shelving

- 1:** Choose your bay length 4, 8 or 12 series. You always start with a start frame & then add an extension frame to add length.
- 2:** Choose your post heights. **78 31/32"** or **60 19/32"**. Both can be cut down to suit any vehicle model.
- 3:** Choose how many shelves you require to fit into the bay.
- 4:** Choose your plastic bins & accessories (if required).
  - 2 cabinets can be joined horizontally to fit the 8 series shelving (1 x **RCJNR/C** & 1 x **RSBAR/80** will be required)



CAT NO;	HEIGHT (inches)	LENGTH (inches)	DESCRIPTION
<b>RSSFR/HD/80/2006</b>	78 31/32"	35 3/64"	8 Series Dual Post Heavy Duty Start Frame
<b>RSSFR/HD/80/1539</b>	60 19/32"		
<b>RSEFR/HD/80/2006</b>	78 31/32"	34 1/16"	8 Series Dual Post Heavy Duty Extension Frame
<b>RSEFR/HD/80/1539</b>	60 19/32"		

Post Height Adjustment	
Height	Cut at 1 1/32" Intervals
78 31/32"	← → 60 19/32"
60 19/32"	← → 42 1/4"

Frame Purchase Example: **RSSFR/HD/80/1539**  
 If you want to extend then you would add a **RSEFR/HD/80/1539**  
 All components are zinc annealed & powder coated, complete with instructions & mounting hardware.

SHELF	CAT NO;	DESCRIPTION	HEIGHT	LENGTH	WIDTH	PLASTIC BINS
	RSSHL/81/FR	8 Series File Retainer	-	-	-	-
	RSSHL/83	High mount shelf	Rear 3 35/64" Front 1 49/64"	33 1/32"	7 7/8"	Holds 6 x <b>RP25</b> bins
	RSSHL/84	Mid mount shelf	Rear 3 35/64" Front 1 49/64"	33 1/32"	9 29/64"	Holds 2 x <b>RP120</b> bins or 4 x <b>RP60</b>
	RSSHL/85	Low mount shelf	Rear 3 35/64" Front 1 49/64"	33 1/32"	12 1/64"	Holds 4 x <b>RP200</b> bins or 8 x <b>RP100</b>
	RSSHL/86	Floor mount shelf	Rear 6 39/64" Front 3 5/32"	33 1/32"	15 15/16"	Holds 4 x <b>RP400x200</b> or Holds 2 x <b>RP240</b> bins
	RSSHL/87	Low mount shelf	Rear 3 35/64" Front 0 63/64"	33 1/32"	14 27/32"	Holds 2 x <b>RC001</b> or <b>RC002</b> Rolacases <b>RS/87/FW</b> -Foam
	RSSHL/88	Floor mount shelf	Rear 3 39/64" Front 2 9/16"	33 1/32"	15 15/16"	Holds 8 x <b>RP400x100</b> or 4 x <b>RP400x200</b>

### ACCESSORIES FOR 8 SERIES: Please refer to page 14 for more accessories.


#### RSCDH/81



Adjustable diameter cable drum holder  
Ideal for 8 Series shelving

Dimensions: H: 6 11/16" D: 14 9/16" L: 33 1/32"

#### RSLBX/84



CAT No.	A	B	C
<b>RSLBX/82</b>	A: 15 1/2"	B: 16 17/32"	C: 33 1/32"
<b>RSLBX/84</b>	A: 15 1/2"	B: 9 27/32"	C: 33 1/32"

2 x **RCSK5/C**  
 1 x **RCJNR/C** (Joining Bracket)  
 1 x **RSBAR/80**



#### RSBAR/80

Mounting bar for **ROLA-CASE** 8 series shelving. Only required for when dual cabinets are being fitted.

#### RCJNR/C

Vertical joining bracket for connecting **ROLA-CASE** cabinets vertically. (4 per kit plus screws)

\*Refer to page 10 for **ROLA-CASE** cabinet information






# ROLA-CASE

## MULTIPLE STORAGE SYSTEMS

# 4 Series Van Shelving

- 1:** Choose your bay length 4, 8 or 12 series. You always start with a start frame & then add an extension frame to add length.
- 2:** Choose your post heights. **78** <sup>31</sup>/<sub>32</sub>" or **60** <sup>19</sup>/<sub>32</sub>". Both can be cut down to suit any vehicle model.
- 3:** Choose how many shelves you require to fit into the bay.
- 4:** Choose your plastic bins & accessories (if required).
  - All cabinets are compatible with the 4 series shelving.



CAT NO;	HEIGHT (inches)	LENGTH (inches)	DESCRIPTION
RSSFR/HD/40/2006	78 <sup>31</sup> / <sub>32</sub> "	18 <sup>1</sup> / <sub>2</sub> "	4 Series Dual Post Heavy Duty Start Frame
RSSFR/HD/40/1539	60 <sup>19</sup> / <sub>32</sub> "		
RSEFR/HD/40/2006	78 <sup>31</sup> / <sub>32</sub> "	17 <sup>33</sup> / <sub>64</sub> "	4 Series Dual Post Heavy Duty Extension Frame
RSEFR/HD/40/1539	60 <sup>19</sup> / <sub>32</sub> "		

Post Height Adjustment	
Height	Cut at 1 <sup>1</sup> / <sub>32</sub> " Intervals
78 <sup>31</sup> / <sub>32</sub> "	↔ 60 <sup>19</sup> / <sub>32</sub> "
60 <sup>19</sup> / <sub>32</sub> "	↔ 42 <sup>1</sup> / <sub>4</sub> "

Frame Purchase Example: **RSSFR/HD/40/1539**  
 If you want to extend then you would add a **RSEFR/HD/40/1539**  
 All components are zinc annealed & powder coated, complete with instructions & mounting hardware.

SHELF	CAT NO;	DESCRIPTION	HEIGHT	LENGTH	WIDTH	PLASTIC BINS
	RSSHL/43	High mount shelf	Rear 3 <sup>35</sup> / <sub>64</sub> " Front 1 <sup>49</sup> / <sub>64</sub> "	16 <sup>1</sup> / <sub>2</sub> "	7 <sup>7</sup> / <sub>8</sub> "	Holds 3 x <b>RP25</b> bins
	RSSHL/44	Mid mount shelf	Rear 3 <sup>35</sup> / <sub>64</sub> " Front 1 <sup>49</sup> / <sub>64</sub> "	16 <sup>1</sup> / <sub>2</sub> "	9 <sup>29</sup> / <sub>64</sub> "	Holds 1 x <b>RP120</b> or 2 x <b>RP60</b>
	RSSHL/45	Low mount shelf	Rear 3 <sup>35</sup> / <sub>64</sub> " Front 1 <sup>49</sup> / <sub>64</sub> "	16 <sup>1</sup> / <sub>2</sub> "	12 <sup>1</sup> / <sub>64</sub> "	Holds 4 x <b>RP100</b> or 2 x <b>RP200</b>
	RSSHL/46	Floor mount shelf	Rear 6 <sup>39</sup> / <sub>64</sub> " Front 3 <sup>5</sup> / <sub>32</sub> "	16 <sup>1</sup> / <sub>2</sub> "	15 <sup>15</sup> / <sub>16</sub> "	Holds 2 <b>RP400x200</b> or Holds 1 x <b>RP240</b> bins

## ACCESSORIES FOR 4 SERIES: Please refer to page 14 for more accessories.


<p><b>RP25</b></p> <p>Small Plastic Bin 1 Compartment</p>	<p><b>RP240</b></p> <p>X - Large Plastic Bin 3 Adjustable Compartments. (Dividers RP240/D sold separately)</p>	<p><b>RP400X200</b></p> <p>Large Plastic Bin 3 Adjustable Compartments</p>	<p><b>RSGBH/41</b></p> <p>Gas bottle holder for any acetylene or small bottles. Includes rubber mat and strap.</p>
<p><b>RSCDH/41</b></p> <p>Adjustable diameter cable drum holder. Ideal for 4 Series shelving</p> <p>Dimensions: H: 6 <sup>11</sup>/<sub>16</sub>" D: 14 <sup>9</sup>/<sub>16</sub>" L: 16 <sup>1</sup>/<sub>2</sub>"</p>	<p><b>RCKIT40/9</b></p> <p><b>RC4/40</b> cabinet with 3 x <b>RC401</b> &amp; 1 x <b>RC001/CL</b></p> <p>Dimensions: W - 16 <sup>1</sup>/<sub>2</sub>" D - 18 <sup>7</sup>/<sub>64</sub>" H - 16 <sup>7</sup>/<sub>32</sub>"</p>	<p><b>RCKIT40/14</b></p> <p><b>RC5/40</b> cabinet with 2 x <b>RC403</b> &amp; 2 x <b>RC001/CL</b></p> <p>Dimensions: W - 16 <sup>1</sup>/<sub>2</sub>" D - 18 <sup>7</sup>/<sub>64</sub>" H - 21 <sup>1</sup>/<sub>32</sub>"</p>	<p><b>RCKIT40/18</b></p> <p><b>RC7/40</b> cabinet with 2 x <b>RC403</b> &amp; 4 x <b>RC001/CL</b></p> <p>Dimensions: W - 16 <sup>1</sup>/<sub>2</sub>" D - 18 <sup>7</sup>/<sub>64</sub>" H - 29 <sup>1</sup>/<sub>4</sub>"</p>

\*Refer to page 10 for **ROLA-CASE** cabinet information



### END PANELS

Construction: 1.1mm zinc coated steel  
All Fixing Components Included.



#### RSPEP/HK



Lead Hook - Holds extension leads, hoses, etc.

#### RSPEP/MH



Tool Rack - Holds tools of different shapes and sizes.

#### RSPEP/TY



Tool Tray - Holds loose tools and/or equipment

#### RSGBH/9KG




Tank Holder  
Comes with vibration insert, rubber pinch-weld and strap. Floor mount.

Dimensions:  
Width: 14 49/64"  
Depth: 13 3/16"  
Height: 11 39/64"


\*Gas Bottle Not Included

Construction: 1.1mm zinc coated steel. All fixing components included.


**RSFLE** - Floor mount end panels and strap.  
**RS420A** - Adapting bracket to suit 4 series frame.



**RSFLE** - Floor mount end panels and strap.  
**RS840A** - Adapting bracket to suit 8 series frame.




**RSFLE** - Floor mount end panels and strap.  
**RS120A** - Adapting bracket to suit 12 series frame.




Both part numbers will be required to make full floor mount enclosure kit

#### RP25




Small Plastic Bin  
1 Compartment

#### RP60




Med Plastic Bin  
1 Compartment

#### RP120



Large Plastic Bin  
3 Adjustable Compartments

#### RP240



X - Large Plastic Bin  
3 Adjustable Compartments  
(Dividers RP240/D sold separately)

#### RP100



Small Plastic Bin  
3 Adjustable Compartments

#### RP200



Med Plastic Bin  
3 Adjustable Compartments

#### RP400X100



Large Plastic Bin  
3 Adjustable Compartments

#### RP400X200



Large Plastic Bin  
3 Adjustable Compartments





ALL SHELVING IS HEAVY DUTY. ALL FRAMES & END PANELS ARE POWDER COATED

The **ROLA-Shelf** vehicle shelving offers a wide range of products to suit all sectors, service technicians & vehicle types

- Fit any make or model of van or truck.
- Comes complete with anchor & fitment kit
- Contours to the shape of your van optimizing the vehicles space

- Simple system to adjust shelves to suit your needs
- Enhance the professional image of you & your business
- Multiple vehicle position options

### 01

Frame:  
1 x **RSSF/HD/80/1539 or 2006**  
1 x **RSEFR/HD/80/1539 or 2006**

Shelves:  
2 x **RSSH/83**  
2 x **RSSH/84**  
3 x **RSSH/85**  
2 x **RSSH/86**

Bins:  
12 x **RP25**  
4 x **RP120**  
4 x **RP200**

78 <sup>31</sup>/<sub>32</sub>" (2006)  
60 <sup>19</sup>/<sub>32</sub>" (1539)  
69 <sup>3</sup>/<sub>32</sub>"

### 02

Frame:  
1 x **RSSF/HD/80/1539 or 2006**  
1 x **RSEFR/HD/120/1539 or 2006**

Shelves:  
1 x **RSSH/83**  
1 x **RSSH/84**  
1 x **RSSH/85**  
1 x **RSSH/86**  
1 x **RSSH/123**  
1 x **RSSH/124**  
1 x **RSSH/125**  
1 x **RSSH/126**

Bins:  
15 x **RP25**  
5 x **RP120**  
6 x **RP200**

Accessories:  
1 x **RSFLE**  
1 x **RS840A**

78 <sup>31</sup>/<sub>32</sub>" (2006)  
60 <sup>19</sup>/<sub>32</sub>" (1539)  
85 <sup>5</sup>/<sub>8</sub>"

### 03

Frame:  
1 x **RSSH/HD/80/1539 or 2006**

Shelves:  
1 x **RSSH/83**  
1 x **RSSH/84**  
1 x **RSSH/85**  
1 x **RSSH/86**

Accessories:  
1 x **RSPEP/LEFT**  
2 x **RSPEP/HK**  
1 x **RSPEP/MH**

78 <sup>31</sup>/<sub>32</sub>" (2006)  
60 <sup>19</sup>/<sub>32</sub>" (1539)  
35 <sup>3</sup>/<sub>64</sub>"

### 04

Frame:  
1 x **RSSF/HD/80/1539 or 2006**

Shelves:  
1 x **RSSH/83**  
1 x **RSSH/84**  
2 x **RSSH/86**

Bins:  
6 x **RP25**  
2 x **RP120**  
4 x **RP400X200**  
2 x **RP240**

Accessories:  
1 x **RSPEP/LEFT**  
2 x **RSPEP/HK**  
1 x **RSPEP/MH**

78 <sup>31</sup>/<sub>32</sub>" (2006)  
60 <sup>19</sup>/<sub>32</sub>" (1539)  
35 <sup>3</sup>/<sub>64</sub>"

### 05

Frame:  
1 x **RSSF/HD/120/1539 or 2006**

Shelves:  
1 x **RSSH/123**  
1 x **RSSH/124**  
1 x **RSSH/125**  
1 x **RSSH/126**

78 <sup>31</sup>/<sub>32</sub>" (2006)  
60 <sup>19</sup>/<sub>32</sub>" (1539)  
51 <sup>37</sup>/<sub>64</sub>"

### 06

Frame:  
1 x **RSSF/HD/120/1539 or 2006**

Shelves:  
1 x **RSSH/123**  
1 x **RSSH/124**  
2 x **RSSH/126**

Bins:  
9 x **RP25**  
3 x **RP120**  
6 x **RP400X200**  
3 x **RP240**

78 <sup>31</sup>/<sub>32</sub>" (2006)  
60 <sup>19</sup>/<sub>32</sub>" (1539)  
51 <sup>37</sup>/<sub>64</sub>"





The **ROLA-Shelf** vehicle shelving offers a wide range of products to suit all sectors, service technicians & vehicle types

- Fit any make or model of van or truck.
- Comes complete with anchor & fitment kit
- Contours to the shape of your van optimizing the vehicles space
- Simple system to adjust shelves to suit your needs
- Enhance the professional image of you & your business
- Multiple vehicle position options

**07**

78 31/32"  
(2006)



Frame:  
1 x **RSSFR/HD/120/1539 or 2006**

Shelves :  
1 x **RSSH/123**  
1 x **RSSH/124**  
1 x **RSSH/125**  
1 x **RSSH/126**

Accessories:  
1 x **REPEP/LEFT**  
2 x **RSPEP/HK**  
1 x **RSPEP/MH**

51 37/64"

**08**

78 31/32"  
(2006)



Frame:  
1 x **RSSFR/HD/120/1539 or 2006**

Shelves:  
1 x **RSSH/123**  
1 x **RSSH/124**  
2 x **RSSH/126**

Bins:  
9 x **RP25**  
3 x **RP120**  
6 x **RP400X200**  
4 x **RP240**

Accessories:  
1 x **RSPEP/LEFT**  
2 x **RSPEP/HK**  
1 x **RSPEP/MH**

51 37/64"

**09**

78 31/32"  
(2006)



Frame:  
1 x **RSSFR/HD/80/1539 or 2006**

Shelves :  
1 x **RSSH/83**  
1 x **RSSH/84**  
1 x **RSSH/85**  
1 x **RSSH/86**

Bins:  
6 x **RP25**  
2 x **RP120**  
4 x **RP200**  
2 x **RP240**

Cabinet Kit:  
1 x **RCSK3/C**  
1 x **RCSK2/C**  
1 x **RCBAR/80**

35 3/64"

**10**

78 31/32"  
(2006)



Frame:  
1 x **RSSFR/HD/80/1539 or 2006**

Shelves:  
1 x **RSSH/83**  
2 x **RSSH/84**  
2 x **RSSH/85**  
1 x **RSSH/86**

Bins:  
6 x **RP25**  
4 x **RP120**  
8 x **RP200**  
2 x **RP240**

35 3/64"







**ROLA-Shelf** sliding platforms are the ultimate way to maximise your loadability. Sliding platforms give you instant access to tools and equipment without having to crawl in and out of your vehicle. Engineer designed, tested & manufactured in Australia for vehicle use, ideal for van & ute canopy.

- All platforms come with mounting brackets
- Quality powder coated steel
- Side rails and tie down points
- Up to 7 position locking mechanism
- Ideal for kerbside loading & unloading
- Fitted to the side or rear door openings
- Wide handle with one handed locking mechanism
- 100% extendable, easy installation & can be used in conjunction with **ROLA-CASE** products



### Sliding Platform Options

PRODUCT CODE	PRODUCT	TRAVEL LENGTH	HEIGHT	WIDTH	WEIGHT (Pounds)	LOAD RATING (Pounds)
<b>RSSPF/1300x510</b>	Single sliding Platform	<b>53</b> <sup>11</sup> / <sub>32</sub> "	<b>6</b> <sup>1</sup> / <sub>32</sub> "	<b>19</b> <sup>11</sup> / <sub>16</sub> "	110.23	220.46
<b>RSEPF/1300x1000</b>	Double sliding Platform	<b>53</b> <sup>11</sup> / <sub>32</sub> "	<b>6</b> <sup>1</sup> / <sub>32</sub> "	<b>39</b> <sup>3</sup> / <sub>8</sub> "	187.39	330.69
<b>RSSPF/950x510</b>	Single sliding Platform	<b>37</b> <sup>13</sup> / <sub>32</sub> "	<b>6</b> <sup>1</sup> / <sub>32</sub> "	<b>19</b> <sup>11</sup> / <sub>16</sub> "	83.77	275.57
<b>RSEPF/950x1000</b>	Double sliding Platform	<b>37</b> <sup>13</sup> / <sub>32</sub> "	<b>6</b> <sup>1</sup> / <sub>32</sub> "	<b>39</b> <sup>3</sup> / <sub>8</sub> "	141.09	330.69



**ROLA-CASE**  
MULTIPLE STORAGE SYSTEMS



**ROLA-Shelf**  
VEHICLE STORAGE SOLUTIONS

**Email:** [enquiry@rolacase.com](mailto:enquiry@rolacase.com)

**Web:** [www.rolacase.us](http://www.rolacase.us)

The perfect solution for transporting power tools & small components.

Engineer designed, tested & manufactured in Australia since 1982.



**U.S. Electrical**  
Services Inc.