

HOT PRODUCT BULLETIN



ULTIMATE Enclosures

Hubbell-Wiegmann ULTIMATE Series Enclosures are designed to house and protect electrical and electronic components from harsh, dirty environments. For use in installations where dirt, dust, oil, water, or other contaminants are present. Streamlined styling, flush latching, and attractive durable finish complement any high tech electronic equipment.

- Increased tub opening for better access
- Concealed hinges
- Continuously plasma welded seams
- Removable and interchangeable doors
- Print Pocket
- ANSI 61 Polyester Finish
- Optional solid or plexiglass viewing doors
- CSA Certified
- Larger sub panels to accommodate bigger footprints
- Bodies and doors fabricated from 14 gauge steel
- Poured-in-place polyurethane gasket
- 1/4-turn semi-flush oil tight latches
- Mounting holes in rear of enclosure
- Optional 304/316 Stainless Grained finish
- UL 508 Listed
- Meets Type 4, 4X, 12 & 13



N412C SINGLE DOOR ENCLOSURES, LESS SUB PANEL, ANSI 61 POLYESTER POWDER		
Part Number	Size	Description
N412121206C	12 x 12 x 6	N412C, N4, 12 & 13 Single Door Encl. Gray
N412161206C	16 x 12 x 6	N412C, N4, 12 & 13 Single Door Encl. Gray
N412161606C	16 x 16 x 6	N412C, N4, 12 & 13 Single Door Encl. Gray
N412162006C	16 x 20 x 6	N412C, N4, 12 & 13 Single Door Encl. Gray
N412201606C	20 x 16 x 6	N412C, N4, 12 & 13 Single Door Encl. Gray
N412202006C	20 x 20 x 6	N412C, N4, 12 & 13 Single Door Encl. Gray
N412241606C	24 x 16 x 6	N412C, N4, 12 & 13 Single Door Encl. Gray
N412242006C	24 x 20 x 6	N412C, N4, 12 & 13 Single Door Encl. Gray
N412242406C	24 x 24 x 6	N412C, N4, 12 & 13 Single Door Encl. Gray
N412161208C	16 x 12 x 8	N412C, N4, 12 & 13 Single Door Encl. Gray
N412161608C	16 x 16 x 8	N412C, N4, 12 & 13 Single Door Encl. Gray
N412162008C	16 x 20 x 8	N412C, N4, 12 & 13 Single Door Encl. Gray
N412201608C	20 x 16 x 8	N412C, N4, 12 & 13 Single Door Encl. Gray
N412202008C	20 x 20 x 8	N412C, N4, 12 & 13 Single Door Encl. Gray
N412202408C	20 x 24 x 8	N412C, N4, 12 & 13 Single Door Encl. Gray
N412241608C	24 x 16 x 8	N412C, N4, 12 & 13 Single Door Encl. Gray
N412242008C	24 x 20 x 8	N412C, N4, 12 & 13 Single Door Encl. Gray
N412242408C	24 x 24 x 8	N412C, N4, 12 & 13 Single Door Encl. Gray
N412243008C	24 x 30 x 8	N412C, N4, 12 & 13 Single Door Encl. Gray
N412302008C	30 x 20 x 8	N412C, N4, 12 & 13 Single Door Encl. Gray
N412302408C	30 x 24 x 8	N412C, N4, 12 & 13 Single Door Encl. Gray
N412303008C	30 x 30 x 8	N412C, N4, 12 & 13 Single Door Encl. Gray
N412362408C	36 x 24 x 8	N412C, N4, 12 & 13 Single Door Encl. Gray

Hubbell-Wiegmann

501 West Apple St.

Freeburg, IL 62243

618.539.3193

Fax 618.539.5794

WIEGMANN[®]

www.hubbell-wiegmann.com



N412C SINGLE DOOR ENCLOSURES, LESS SUB PANEL, ANSI 61 POLYESTER POWDER cont'd.

Part Number	Size	Description
N412363008C	36 x 30 x 8	N412C, N4, 12 & 13 Single Door Encl. Gray
N412363608C	36 x 36 x 8	N412C, N4, 12 & 13 Single Door Encl. Gray
N412161210C	16 x 12 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412161610C	16 x 16 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412162010C	16 x 20 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412201610C	20 x 16 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412202010C	20 x 20 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412202410C	20 x 24 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412241610C	24 x 16 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412242010C	24 x 20 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412242410C	24 x 24 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412243010C	24 x 30 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412302010C	30 x 20 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412302410C	30 x 24 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412303010C	30 x 30 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412362410C	36 x 24 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412363010C	36 x 30 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412363610C	36 x 36 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412423610C	42 x 36 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412482410C	48 x 24 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412483610C	48 x 36 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412603610C	60 x 36 x 10	N412C, N4, 12 & 13 Single Door Encl. Gray
N412202012C	20 x 20 x 12	N412C, N4, 12 & 13 Single Door Encl. Gray
N412242012C	24 x 20 x 12	N412C, N4, 12 & 13 Single Door Encl. Gray
N412242412C	24 x 24 x 12	N412C, N4, 12 & 13 Single Door Encl. Gray
N412302412C	30 x 24 x 12	N412C, N4, 12 & 13 Single Door Encl. Gray
N412303012C	30 x 30 x 12	N412C, N4, 12 & 13 Single Door Encl. Gray
N412362412C	36 x 24 x 12	N412C, N4, 12 & 13 Single Door Encl. Gray
N412363012C	36 x 30 x 12	N412C, N4, 12 & 13 Single Door Encl. Gray
N412363612C	36 x 36 x 12	N412C, N4, 12 & 13 Single Door Encl. Gray
N412402412C	40 x 24 x 12	N412C, N4, 12 & 13 Single Door Encl. Gray
N412423612C	42 x 36 x 12	N412C, N4, 12 & 13 Single Door Encl. Gray
N412482412C	48 x 24 x 12	N412C, N4, 12 & 13 Single Door Encl. Gray
N412483612C	48 x 36 x 12	N412C, N4, 12 & 13 Single Door Encl. Gray
N412603612C	60 x 36 x 12	N412C, N4, 12 & 13 Single Door Encl. Gray
N412242416C	24 x 24 x 16	N412C, N4, 12 & 13 Single Door Encl. Gray
N412363016C	36 x 30 x 16	N412C, N4, 12 & 13 Single Door Encl. Gray
N412483616C	48 x 36 x 16	N412C, N4, 12 & 13 Single Door Encl. Gray
N412242420C	24 x 24 x 20	N412C, N4, 12 & 13 Single Door Encl. Gray
N412302420C	30 x 24 x 20	N412C, N4, 12 & 13 Single Door Encl. Gray
N412363020C	36 x 30 x 20	N412C, N4, 12 & 13 Single Door Encl. Gray

N412WC, SINGLE DOOR NEMA 4, WITH WINDOW, LESS SUB PANEL, ANSI 61 POLYESTER POWDER .

Part Number	Size	Description
N412121206WC	12 x 12 x 6	N412WC, Single Door Wall x Mount w/Window
N412161206WC	16 x 12 x 6	N412WC, Single Door Wall x Mount w/Window
N412201606WC	20 x 16 x 6	N412WC, Single Door Wall x Mount w/Window
N412202006WC	20 x 20 x 6	N412WC, Single Door Wall x Mount w/Window
N412242006WC	24 x 20 x 6	N412WC, Single Door Wall x Mount w/Window
N412242406WC	24 x 24 x 6	N412WC, Single Door Wall x Mount w/Window
N412302406WC	30 x 24 x 6	N412WC, Single Door Wall x Mount w/Window
N412121208WC	12 x 12 x 8	N412WC, Single Door Wall x Mount w/Window
N412161208WC	16 x 12 x 8	N412WC, Single Door Wall x Mount w/Window
N412201608WC	20 x 16 x 8	N412WC, Single Door Wall x Mount w/Window
N412202008WC	20 x 20 x 8	N412WC, Single Door Wall x Mount w/Window

Hubbell-Wiegmann

501 West Apple St.

Freeburg, IL 62243

618.539.3193

Fax 618.539.5794

WIEGMANN®www.hubbell-wiegmann.com

N412WC, SINGLE DOOR NEMA 4, WITH WINDOW, LESS SUB PANEL, ANSI 61 POLYESTER POWDER *cont'd.*

Part Number	Size	Description
N412242008WC	24 x 20 x 8	N412WC, Single Door Wall x Mount w/Window
N412242408WC	24 x 24 x 8	N412WC, Single Door Wall x Mount w/Window
N412302408WC	30 x 24 x 8	N412WC, Single Door Wall x Mount w/Window
N412161210WC	16 x 12 x 10	N412WC, Single Door Wall x Mount w/Window
N412201610WC	20 x 16 x 10	N412WC, Single Door Wall x Mount w/Window
N412202010WC	20 x 20 x 10	N412WC, Single Door Wall x Mount w/Window
N412242010WC	24 x 20 x 10	N412WC, Single Door Wall x Mount w/Window
N412242410WC	24 x 24 x 10	N412WC, Single Door Wall x Mount w/Window
N412302410WC	30 x 24 x 10	N412WC, Single Door Wall x Mount w/Window
N412202012WC	20 x 20 x 12	N412WC, Single Door Wall x Mount w/Window
N412242012WC	24 x 20 x 12	N412WC, Single Door Wall x Mount w/Window
N412242412WC	24 x 24 x 12	N412WC, Single Door Wall x Mount w/Window
N412302412WC	30 x 24 x 12	N412WC, Single Door Wall x Mount w/Window
N412242416WC	24 x 24 x 16	N412WC, Single Door Wall x Mount w/Window
N412242420WC	24 x 24 x 20	N412WC, Single Door Wall x Mount w/Window
N412302420WC	30 x 24 x 20	N412WC, Single Door Wall x Mount w/Window

N412SSC, SINGLE DOOR WALL MOUNT, NEMA 4X, 304SS, LESS SUB PANEL

Part Number	Size	Description
N412121206SSC	12 x 12 x 6	N412SSC, S.S. Single Door Enclosure
N412161206SSC	16 x 12 x 6	N412SSC, S.S. Single Door Enclosure
N412161606SSC	16 x 16 x 6	N412SSC, S.S. Single Door Enclosure
N412201606SSC	20 x 16 x 6	N412SSC, S.S. Single Door Enclosure
N412202006SSC	20 x 20 x 6	N412SSC, S.S. Single Door Enclosure
N412161208SSC	16 x 12 x 8	N412SSC, S.S. Single Door Enclosure
N412161608SSC	16 x 16 x 8	N412SSC, S.S. Single Door Enclosure
N412162008SSC	16 x 20 x 8	N412SSC, S.S. Single Door Enclosure
N412201608SSC	20 x 16 x 8	N412SSC, S.S. Single Door Enclosure
N412202008SSC	20 x 20 x 8	N412SSC, S.S. Single Door Enclosure
N412241608SSC	24 x 16 x 8	N412SSC, S.S. Single Door Enclosure
N412242008SSC	24 x 20 x 8	N412SSC, S.S. Single Door Enclosure
N412242408SSC	24 x 24 x 8	N412SSC, S.S. Single Door Enclosure
N412302408SSC	30 x 24 x 8	N412SSC, S.S. Single Door Enclosure
N412303008SSC	30 x 30 x 8	N412SSC, S.S. Single Door Enclosure
N412362408SSC	36 x 24 x 8	N412SSC, S.S. Single Door Enclosure
N412363008SSC	36 x 30 x 8	N412SSC, S.S. Single Door Enclosure
N412161210SSC	16 x 12 x 10	N412SSC, S.S. Single Door Enclosure
N412161610SSC	16 x 16 x 10	N412SSC, S.S. Single Door Enclosure
N412162010SSC	16 x 20 x 10	N412SSC, S.S. Single Door Enclosure
N412201610SSC	20 x 16 x 10	N412SSC, S.S. Single Door Enclosure
N412202010SSC	20 x 20 x 10	N412SSC, S.S. Single Door Enclosure
N412241610SSC	24 x 16 x 10	N412SSC, S.S. Single Door Enclosure
N412242010SSC	24 x 20 x 10	N412SSC, S.S. Single Door Enclosure
N412242410SSC	24 x 24 x 10	N412SSC, S.S. Single Door Enclosure
N412302410SSC	30 x 24 x 10	N412SSC, S.S. Single Door Enclosure
N412303010SSC	30 x 30 x 10	N412SSC, S.S. Single Door Enclosure
N412362410SSC	36 x 24 x 10	N412SSC, S.S. Single Door Enclosure
N412363010SSC	36 x 30 x 10	N412SSC, S.S. Single Door Enclosure
N412363610SSC	36 x 36 x 10	N412SSC, S.S. Single Door Enclosure
N412423610SSC	42 x 36 x 10	N412SSC, S.S. Single Door Enclosure
N412483610SSC	48 x 36 x 10	N412SSC, S.S. Single Door Enclosure
N412603610SSC	60 x 36 x 10	N412SSC, S.S. Single Door Enclosure
N412202012SSC	20 x 20 x 12	N412SSC, S.S. Single Door Enclosure
N412242412SSC	24 x 24 x 12	N412SSC, S.S. Single Door Enclosure
N412302412SSC	30 x 24 x 12	N412SSC, S.S. Single Door Enclosure

Hubbell-Wiegmann

501 West Apple St.

Freeburg, IL 62243

618.539.3193

Fax 618.539.5794

WIEGMANN®www.hubbell-wiegmann.com

N412SSC, SINGLE DOOR WALL MOUNT, NEMA 4X, 304SS, LESS SUB PANEL cont'd.

Part Number	Size	Description
N412362412SSC	36 x 24 x 12	N412SSC, S.S. Single Door Enclosure
N412363012SSC	36 x 30 x 12	N412SSC, S.S. Single Door Enclosure
N412363612SSC	36 x 36 x 12	N412SSC, S.S. Single Door Enclosure
N412423612SSC	42 x 36 x 12	N412SSC, S.S. Single Door Enclosure
N412483612SSC	48 x 36 x 12	N412SSC, S.S. Single Door Enclosure
N412603612SSC	60 x 36 x 12	N412SSC, S.S. Single Door Enclosure

N412SSAC, SINGLE DOOR WALL MOUNT, 316SS, NEMA 4X, LESS SUB PANEL

Part Number	Size	Description
N412121206SSAC	12 x 12 x 6	N412SSAC, S.S. Single Door Enclosure, 316
N412161206SSAC	16 x 12 x 6	N412SSAC, S.S. Single Door Enclosure, 316
N412161606SSAC	16 x 16 x 6	N412SSAC, S.S. Single Door Enclosure, 316
N412201606SSAC	20 x 16 x 6	N412SSAC, S.S. Single Door Enclosure, 316
N412202006SSAC	20 x 20 x 6	N412SSAC, S.S. Single Door Enclosure, 316
N412161208SSAC	16 x 12 x 8	N412SSAC, S.S. Single Door Enclosure, 316
N412161608SSAC	16 x 16 x 8	N412SSAC, S.S. Single Door Enclosure, 316
N412162008SSAC	16 x 20 x 8	N412SSAC, S.S. Single Door Enclosure, 316
N412201608SSAC	20 x 16 x 8	N412SSAC, S.S. Single Door Enclosure, 316
N412202008SSAC	20 x 20 x 8	N412SSAC, S.S. Single Door Enclosure, 316
N412241608SSAC	24 x 16 x 8	N412SSAC, S.S. Single Door Enclosure, 316
N412242008SSAC	24 x 20 x 8	N412SSAC, S.S. Single Door Enclosure, 316
N412242408SSAC	24 x 24 x 8	N412SSAC, S.S. Single Door Enclosure, 316
N412302408SSAC	30 x 24 x 8	N412SSAC, S.S. Single Door Enclosure, 316
N412303008SSAC	30 x 30 x 8	N412SSAC, S.S. Single Door Enclosure, 316
N412362408SSAC	36 x 24 x 8	N412SSAC, S.S. Single Door Enclosure, 316
N412363008SSAC	36 x 30 x 8	N412SSAC, S.S. Single Door Enclosure, 316
N412202012SSAC	20 x 20 x 12	N412SSAC, S.S. Single Door Enclosure, 316
N412242412SSAC	24 x 24 x 12	N412SSAC, S.S. Single Door Enclosure, 316
N412302412SSAC	30 x 24 x 12	N412SSAC, S.S. Single Door Enclosure, 316
N412362412SSAC	36 x 24 x 12	N412SSAC, S.S. Single Door Enclosure, 316
N412363012SSAC	36 x 30 x 12	N412SSAC, S.S. Single Door Enclosure, 316
N412363612SSAC	36 x 36 x 12	N412SSAC, S.S. Single Door Enclosure, 316
N412423612SSAC	42 x 36 x 12	N412SSAC, S.S. Single Door Enclosure, 316
N412483612SSAC	48 x 36 x 12	N412SSAC, S.S. Single Door Enclosure, 316
N412603612SSAC	60 x 36 x 12	N412SSAC, S.S. Single Door Enclosure, 316

N412WSSC, SINGLE DOOR WALL MOUNT, NEMA 4X, 304SS, WITH WINDOW, LESS SUB PANEL

Part Number	Size	Description
N412121206WSSC	12 x 12 x 6	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412161206WSSC	16 x 12 x 6	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412201606WSSC	20 x 16 x 6	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412202006WSSC	20 x 20 x 6	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412242006WSSC	24 x 20 x 6	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412242406WSSC	24 x 24 x 6	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412302406WSSC	30 x 24 x 6	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412161208WSSC	16 x 12 x 8	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412201608WSSC	20 x 16 x 8	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412202008WSSC	20 x 20 x 8	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412242008WSSC	24 x 20 x 8	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412242408WSSC	24 x 24 x 8	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412302408WSSC	30 x 24 x 8	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412161210WSSC	16 x 12 x 10	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412201610WSSC	20 x 16 x 10	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412202010WSSC	20 x 20 x 10	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412242010WSSC	24 x 20 x 10	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window

Hubbell-Wiegmann

501 West Apple St.

Freeburg, IL 62243

618.539.3193

Fax 618.539.5794

WIEGMANN®www.hubbell-wiegmann.com

N412WSSC, SINGLE DOOR WALL MOUNT, NEMA 4X, 304SS, WITH WINDOW, LESS SUB PANEL <i>cont'd.</i>		
Part Number	Size	Description
N412242410WSSC	24 x 24 x 10	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412302410WSSC	30 x 24 x 10	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412202012WSSC	20 x 20 x 12	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412242012WSSC	24 x 20 x 12	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412242412WSSC	24 x 24 x 12	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412302412WSSC	30 x 24 x 12	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412242416WSSC	24 x 24 x 16	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412242420WSSC	24 x 24 x 20	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window
N412302420WSSC	30 x 24 x 20	N412WSSC, Stainless Steel Single Door Wall x Mount w/Window

NPC, SUB PANEL WHITE POLYESTER POWDER		
Part Number	Size	Description
NP1212C	10.2 x 10.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP1612C	14.2 x 10.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP1616C	14.2 x 14.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP2016C	18.2 x 14.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP2416C	22.2 x 14.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP2020C	18.2 x 18.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP2420C	22.2 x 18.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP3020C	28.2 x 18.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP2424C	22.2 x 22.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP3024C	28.2 x 22.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP3624C	34.2 x 22.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP3642C	34.2 x 40.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP4024C	38.2 x 22.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP4824C	46.2 x 22.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP3030C	28.2 x 28.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP3630C	34.2 x 28.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP3636C	34.2 x 34.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP4236C	40.2 x 34.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP4836C	46.2 x 34.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC
NP6036C	58.2 x 34.2	NPC Panel for N412C, N412WC, N412SSC, N412WSSC

NPSSC, 304 STAINLESS STEEL SUB PANELS		
Part Number	Size	Description
NP1612SSC	14.2 x 10.2	NPSSC, Panel, 304 Stainless Steel
NP1616SSC	14.2 x 14.2	NPSSC, Panel, 304 Stainless Steel
NP2016SSC	18.2 x 14.2	NPSSC, Panel, 304 Stainless Steel
NP2020SSC	18.2 x 18.2	NPSSC, Panel, 304 Stainless Steel
NP2416SSC	22.2 x 14.2	NPSSC, Panel, 304 Stainless Steel
NP2420SSC	22.2 x 18.2	NPSSC, Panel, 304 Stainless Steel
NP2424SSC	22.2 x 22.2	NPSSC, Panel, 304 Stainless Steel
NP3024SSC	28.2 x 22.2	NPSSC, Panel, 304 Stainless Steel
NP3030SSC	28.2 x 28.2	NPSSC, Panel, 304 Stainless Steel
NP3624SSC	34.2 x 22.2	NPSSC, Panel, 304 Stainless Steel
NP3630SSC	34.2 x 28.2	NPSSC, Panel, 304 Stainless Steel
NP3636SSC	34.2 x 34.2	NPSSC, Panel, 304 Stainless Steel
NP4236SSC	40.2 x 34.2	NPSSC, Panel, 304 Stainless Steel
NP4836SSC	46.2 x 34.2	NPSSC, Panel, 304 Stainless Steel
NP6036SSC	58.2 x 34.2	NPSSC, Panel, 304 Stainless Steel

MFK, MFKSS, MOUNTING FOOT KITS FOR N412 SERIES		
Part Number	Size	Description
N412MFK		Pltd. Mounting Feet For N412 Series
N412MFKSS		S.S. Mounting Feet For N412 Series

Hubbell-Wiegmann

501 West Apple St.

Freeburg, IL 62243

618.539.3193

Fax 618.539.5794

WIEGMANN®

www.hubbell-wiegmann.com

