



Light for Life

For over 40 years, Maxim Lighting has defined lifestyle lighting, offering a variety of high-quality, decorative fixtures for the home, including chandeliers, sconces, pendants, ceiling mounts, and bath vanities. Design inspiration from around the world characterizes our collections from the traditional to the unusual. Our exclusive products complement your distinct sense of style and add a touch of flair to every setting. Whether it's an elegant chandelier to complete your dining room or a set of beautiful pendants to enhance your kitchen, you're certain to discover just the right product at Maxim Lighting.

MAXIM  LIGHTING®

TABLE OF CONTENTS

Signature Collections

Genoa.....11 Paradise.....7

Allentown.....139 Fremont.....37 Notre Dame.....101
 Apollo.....77 Grove.....127 Palazzo.....73
 Aspen.....95 Hampton.....15 Portofino.....81
 Augusta.....55 Island.....111 Richmond.....41
 Barcelona.....89 Java.....85 Sausalito.....47
 Beaumont.....69 Katherine.....117 Soho.....157
 Boca.....153 La Salle.....65 Southern.....105
 Brighton.....135 La Scalla.....51 Symphony.....119
 Cambridge.....19 Larchmont.....118 Tahoe.....109
 Cosmopolitan.....123 Loft.....149 Towne.....151
 Dresden.....29 Manor.....143 Verona.....103
 Elegante.....113 Monaco.....83 Via Roma.....129
 Empress.....45 Morocco.....87

Traditional Collections

Bel Air.....247 Cupola.....259 Nova.....229
 Bolero.....205 Deco.....189 Oak Harbor.....197
 Brentwood.....249 Diamante.....209 Ophelia.....173
 Bristol.....239 Duo.....169 Pacific.....223
 Canyon Rim.....213 Infinity.....177 Piedmont.....233
 Celeste.....161 Linda.....253 Portello.....201
 Chelsea.....181 Luminous.....165 South Bend.....243
 Classique.....219 Mission Bay.....193 Stratus.....251
 Contour.....235 Moda.....185 Vail.....261

Transitional Collections

Contemporary Collections

Arc.....277 Cilandro.....277 Progetto.....269
 Aurora.....265 Elite.....273 Spectra.....275
 Avant.....271

Expression Collections

Asiana.....281 Desert Wind.....291 Sherwood.....293
 Bali.....295 French Country.....279
 Country French.....285 Pine Grove.....287

Basic Collections

Basix.....299 Fans.....324 Pendants.....311
 Bound Glass.....322 Malibu.....315 Spots.....313
 Builder Basics.....305 Newburg.....304 Track.....314
 Builder Essentials.....309 Newport.....319

Energy Saving Lighting

Basix ES.....333 Wall Sconces.....353 Low Profile Plus ES.....348
 Classic ES.....344 Flair ES.....343 Luna ES.....351
 Cloud ES.....350 Illuminare.....331 Rim ES.....345
 Flush Mounts.....341 Linda ES.....337 Rim Plus ES.....346
 Mini Pendants.....353 Low Profile ES.....347 Wrap Around ES.....349

Counter and Task Lighting

CounterMax.....355
 StarStrand.....363

Categorical View

Bath & Vanity.....382 Flush Mounts.....403 Mini Pendants.....412
 Wall Sconces.....394 Semi Flush Mounts.. 408

References, Displays & Index

Bulbs.....425 Glass.....424 Selling Cases.....418
 Displays.....416 Index.....419 Shades.....424
 Finishes.....423 Legend.....425 Warranty.....426

MAXIM LIGHTING®



Allentown.....139



Apollo.....77



Arc.....277



Asiana.....281



Aspen.....95



Augusta.....55



Aurora.....265



Avant.....271



Bali.....295



Barcelona.....89



Basic-Max.....325



Basix.....299



Basix ES.....333



Beaumont.....69



Bel Air.....247



Boca.....153



Bolero.....205



Bound Glass.....322



Brentwood.....249



Brighton.....135



Bristol.....239



Builder Basics...305



Builder Essentials...309



Cambridge.....19



Canyon Rim.....213



Celeste.....161



Chelsea.....181



Cilandro.....277



Classic ES.....344



Classique.....219



Cloud ES.....350



Contour.....235



Cosmopolitan...123



CounterMax™...355



Country French...285



Cupola.....259



Deco.....189



Desert Wind.....291



Diamante.....209



Dresden.....29



Duo.....169



Elegante.....113



Elite.....273



Empress.....45



Flair ES.....343



Fremont37



French Country...279



Genoa.....11



Grove.....127



Hampton.....15

COLLECTIONS



Illuminare.....331



Infinity.....177



Island.....111



Java85



Katherine117



La Salle65



La Scala51



Larchmont.....118



Linda.....253



Linda ES.....337



Loft.....149



Low Profile ES...347



LowProfile Plus ES.348



Luminous.....165



Luna ES.....351



Malibu.....315



Manor.....143



Mission Bay.....193



Moda.....185



Monaco.....83



Morocco.....87



Newburg.....304



Newport.....319



Notre Dame.....101



Nova.....229



Oak Harbor.....197



Ophelia.....173



Pacific.....223



Palazzo.....73



Paradise.....7



Pendant.....311



Piedmont.....233



Pine Grove.....287



Portello.....201



Portofino.....81



Progetto.....269




Richmond.....41



Rim ES.....345



Rim Plus ES.....346



Sausalito.....47




Sherwood.....293



Soho.....157



South Bend.....243



Southern.....105



Spectra.....275



Spots.....313



StarStrand.....363



Stratus.....251



Super-Max.....324



Symphony.....119



Tahoe.....109



Towne.....151



Track.....314



Vail.....261



Verona.....103



Via Roma.....129



WrapAround ES...349

MAXIM LIGHTING®

For over 40 years, Maxim Lighting has defined lifestyle lighting, offering a variety of high-quality, decorative fixtures for the home, including chandeliers, sconces, pendants, ceiling mounts, and bath vanities. Design inspiration from around the world characterizes our collections from the traditional to the unusual. Our exclusive products complement your distinct sense of style and add a touch of flair to every setting. Whether it's an elegant chandelier to complete your dining room or a set of beautiful pendants to enhance your kitchen, you're certain to discover just the right product at Maxim Lighting.



Maxim Lighting's newly designed Web Site is your resource for detailed product information, including specification data, spec sheets, and high resolution images with detailed zoom features. Visit www.maximlighting.com today!

Catalog Legend

See Page 425 for detailed legend information.



Energy Star
Certified



CA
T24 California
Title 24



Installs
Up or Down



Installs on
Slope Ceiling



Diffuser
Available



KIT Conversion Kit

Table of Contents *alphabetically*

Allentown.....139	Builder Essentials.....309	Energy Saving Mini Pendant	Manor.....143	Sherwood.....293
Apollo.....77	Cambridge.....19	and Wall Sconce.....353	Mission Bay.....193	Soho.....157
Arc.....277	Canyon Rim.....213	Flair ES.....343	Moda.....185	South Bend.....243
Asiana.....281	Celeste.....161	Fremont.....37	Monaco.....83	Southern.....105
Aspen.....95	Chelsea.....181	French Country.....279	Morocco.....87	Spectra.....275
Augusta.....55	Cilandro.....277	Genoa.....11	Newburg.....304	Spots.....313
Aurora.....265	Classic ES.....344	Grove.....127	Newport.....319	StarStrand.....363
Avant.....271	Classique.....219	Hampton.....15	Notre Dame.....101	Stratus.....251
Bali.....295	Cloud ES.....350	Illuminare.....331	Nova.....229	Super-Max Fan.....324
Barcelona.....89	Contour.....235	Infinity.....177	Oak Harbor.....197	Symphony.....119
Basic-Max Fan.....325	Cosmopolitan.....123	Island.....111	Ophelia.....173	Tahoe.....109
Basic-Max Outdoor Fan	CounterMax.....355	Java.....85	Pacific.....223	Towne.....151
.....326	Country French.....285	Katherine.....117	Palazzo.....73	Track.....314
Basix.....299	Cupola.....259	La Salle.....65	Paradise.....7	Vail.....261
Basix ES.....333	Deco.....189	La Scalla.....51	Pendants.....311	Verona.....103
Beaumont.....69	Desert Wind.....291	Larchmont.....118	Piedmont.....233	Via Roma.....129
Bel Air.....247	Diamante.....209	Linda.....253	Pine Grove.....287	Wrap Around ES.....349
Boca.....153	Dresden.....29	Linda ES.....337	Portello.....201	
Bolero.....205	Duo.....169	Loft.....149	Portofino.....81	
Bound Glass.....322	Elegante.....113	Low Profile ES.....347	Progetto.....269	
Brentwood.....249	Elite.....273	Low Profile Plus ES.....348	Richmond.....41	
Brighton.....135	Empress.....45	Luminous.....165	Rim ES.....345	
Bristol.....239	Energy Saving Flush Mounts	Luna ES.....351	Rim Plus ES.....346	
Builder Basics.....305341	Malibu.....315	Sausalito.....47	



MAXIM LIGHTING®

Maxim Lighting's Signature Collections embody beauty and sophistication with design features reflecting old world charm and modern-day elegance. Intricate details include highly polished metals, beveled crystals, hand-cut bobeches, and artisan-painted accents. These fixtures distinguish themselves in any showroom and create a focal point in any home, as each piece bends and curves in a graceful flow of artistry, casting warm light below. For those who demand more from their lighting than just lighting, the Signature Collections delivers unique, upscale styling for today's most elegant homes.

Paradise

In an exclusive design, bent, Beveled Crystal pairs with a highly Plated Silver finish in a fountain of eye-catching splendor. Our proprietary crystal mounting system and hand-cut bobeches, fonts, and canopy covers make the Paradise Collection one of a kind.



800.486.2946

maximlighting.com

39947BCPS 15-Light Chandelier
Plated Silver
46"W x 45"H
15 x 40w CA Bulbs

Design And Utility Patent Pending



39944BCPS 4-Light Chandelier
Plated Silver
22"W x 22"H
4 x 60w CABulbs



Cut Beveled Crystal



39946BCPS 9-Light Chandelier
Plated Silver
37.5"W x 37"H
9 x 60w CABulbs

Design And Utility Patent Pending

39948BCPS 5-Light Chandelier
Plated Silver
28"W x 28"H
5 x 60w CA Bulbs



39945BCPS 6-Light Chandelier
Plated Silver
34"W x 34.5"H
6 x 60w CA Bulbs



Design And Utility Patent Pending



39942BCPS 3-Light Wall Sconce
Plated Silver
18"W x 20"H x 11.5"Ext.
3 x 60w CA Bulbs



39943CYBCPS 4-Light Pendant
Plated Silver
31.5"W x 40"H
4 x 100w MB Bulbs



39940CYBCPS 3-Light Semi-Flush
Plated Silver
20"W x 12"H
3 x 100w MB Bulbs

Design And Utility Patent Pending

Genoa

Inspired by old world artisans, the Genoa exhibits a combination of fine craftsmanship and attention to detail. From the boldness of the cast metal medallions to the fine intricacy of the hand-painted accents, this collection was designed for the finest of homes. The multi-step process of the Modello finish blends perfect tones of gold and browns in a mottled texture that adds depth and warmth. The included hand-painted crystals contrast beautifully with the finish and add graceful elegance. The Mocha Cloud glass found on some models casts a beautiful soft light in the room.

17006MD 9-Light Chandelier
Modello
35.5"W x 42"H
9 x 60w CA Bulbs
Crystals Included



800.486.2946

maximlighting.com



17002MD 2-Light Wall Sconce
 Modello
 11.5"W x 20.5"H x 6.5"Ext.
 2 x 60w CABulbs
 Crystals Included



17003MD 3-Light Wall Sconce
 Modello
 15"W x 21"H x 7.5"Ext.
 3 x 60w CABulbs
 Crystals Included



17005MD 6-Light Chandelier
 Modello
 30"W x 38.25"H
 6 x 60w CABulbs
 Crystals Included



17001MCMD
3-Light Semi-Flush
Modello
20"W x 19.5"H
3 x 100w MB Bulbs
Crystals Included



17000MCMD
3-Light Flush Mount
Modello
17"W x 11.25"H
3 x 100w MB Bulbs



17004MD 6-Light Cage
Modello
19"W x 40"H
6 x 60w CA Bulbs
Crystals Included

17008MD 6-Light Chandelier
Modello
40.5"L x 23.25"W x 32.5"H
6 x 60w CA Bulbs
Crystals Included





MAXIM LIGHTING®

Like fine art, traditional style lighting characterizes a home as a place of rich heritage and time-honored customs. Each piece stands alone as a decorative element in its own right, filling rooms with diffused warmth and subtle tones. Evoking images of elaborate European mansions or historic American homes, Maxim pairs elaborate globes, shades, and bases with classic finishes reminiscent of bygone eras. Chandeliers and pendants, sconces and table lamps all carry the unmistakable stamp of impeccable craftsmanship inherent in all Maxim products.

Hampton

Playfully regal, the Hampton's slender metalwork finished in Auburn Dusk swirls around a clear resin column that mirrors ambient lights and images. Each metallic vine dangles sparkling clear crystals that reflect light from a wreath of "candles."

12027AD 15-Light Chandelier
Auburn Dusk
45"W x 52"H
15 x 40w CA Bulbs
Crystals Included



800.486.2946

maximlighting.com



12024AD 3-Light Chandelier
 Auburn Dusk
 15"W x 18"H
 3 x 60w CA Bulbs
Crystals Included



12025AD 6-Light Chandelier
 Auburn Dusk
 27"W x 32"H
 6 x 60w CA Bulbs
Crystals Included



12026AD 9-Light Chandelier
 Auburn Dusk
 32"W x 39"H
 9 x 60w CA Bulbs
Crystals Included

12032AD 2-Light Wall Sconce
Auburn Dusk
11.5"W x 14"H x 6"Ext.
2 x 60w CA Bulbs
Crystals Included



12020FTAD 3-Light Flush Mount
Auburn Dusk
13.5"W x 7.5"H
3 x 60w MB Bulbs

12023FTAD 3-Light Pendant
Auburn Dusk
28"W x 31.5"H
3 x 100w MB Bulbs
Crystals Included



12021FTAD 3-Light Semi-Flush
Auburn Dusk
20"W x 13"H
3 x 60w MB Bulbs



12028AD 3-Light Cage
 Auburn Dusk
 16"W x 19.5"H
 3 x 60w CABulbs
Crystals Included



12029AD 6-Light Cage
 Auburn Dusk
 26"W x 33"H
 6 x 60w CABulbs
Crystals Included



12030AD 8-Light Cage
 Auburn Dusk
 30.5"W x 40.25"H
 8 x 60w CABulbs
Crystals Included

Cambridge

Our Brighton finish accentuates the intricate leaf details in the Cambridge Collection. Tiers of Mocha Cloud glass cast a warm glow and make a bold statement. Optional crystals, which are antiqued to match the center column finials, and the optional Golden Sheen shades, are also available.



SHD91GS Shade
3"Top x 6.5"Base x 6"H



30558BN 15-Light Chandelier
30558BN/SHD91 With Shade
Brighton
46"W x 50"H
15 x 40w CA Bulbs
Shades Optional-SHD91GS
Crystal Optional-CRY106

800.486.2946

maximlighting.com



SHD90GS Shade
3"Top x 6.5"Base x 5"H



30554BN 3-Light Chandelier
30554BN/SHD90 With Shade
Brighton
21.5"W x 21"H
3 x 60w CA Bulbs
Shades Optional-SHD90GS
Crystal Optional-CRY102



30555BN 5-Light Chandelier
30555BN/SHD91 With Shade
Brighton
32.5"W x 34.5"H
5 x 60w CA Bulbs
Shades Optional-SHD91GS
Crystal Optional-CRY104

30557BN 9-Light Chandelier
30557BN/SHD91 With Shade
 Brighton
 36"W x 40"H
 9 x 60w CABulbs
Shades Optional-SHD91GS
Crystal Optional-CRY105



30552BN 2-Light Wall Sconce
30552BN/SHD91 With Shade
 Brighton
 14"W x 16"H x 8.5"Ext.
 2 x 60w CABulbs
Shades Optional-SHD91GS
Crystal Optional-CRY108



30551BN 1-Light Wall Sconce
30551BN/SHD91 With Shade
 Brighton
 5"W x 19"H x 8.5"Ext.
 1 x 60w CABulb
Shade Optional-SHD91GS
Crystal Optional-CRY107



30545BN 3-Light Cage
 Brighton
 12.5"W x 21.5"H
 3 x 60w CABulbs
Crystal Optional-CRY113



30547BN 6-Light Cage
 Brighton
 26.5"W x 39"H
 6 x 60w CABulbs
Crystal Optional-CRY105



30546BN 6-Light Cage
 Brighton
 19.5"W x 32"H
 6 x 60w CABulbs
Crystal Optional-CRY114

30538MCBN 15-Light Chandelier
Brighton
46"W x 50"H
15 x 40w MB Bulbs
Crystal Optional-CRY106



30535MCBN 5-Light Chandelier
 Brighton
 26.5"W x 24"H
 5 x 100w MB Bulbs
Crystal Optional-CRY103



30536MCBN 5-Light Chandelier
 Brighton
 32.5"W x 34.5"H
 5 x 100w MB Bulbs
Crystal Optional-CRY104

30534MCBN 3-Light Chandelier
Brighton
21.5"W x 21"H
3 x 100w MB Bulbs
Crystal Optional-CRY102



30537MCBN 9-Light Chandelier
Brighton
36"W x 40"H
9 x 60w MB Bulbs
Crystal Optional-CRY105





30533MCBN 4-Light Pendant
Brighton
31"W x 34"H
4 x 100w MB Bulbs
Crystal Optional-CRY101



30532MCBN 4-Light Pendant
Brighton
27"W x 33"H
4 x 100w MB Bulbs
Crystal Optional-CRY101



90540MCBN 1-Light Mini Pendant
Brighton
6.5"W
1 x 100w MB Bulb
Crystal Optional-CRY110
Additional stems available:
6" order STR06206BN
12" order STR06212BN
One 6" stem and three 12"
stems included



30530MCBN
2-Light Flush Mount
Brighton
14.5"W x 9"H
2 x 100w MB Bulbs



30531MCBN 3-Light Semi-Flush
Brighton
25"W x 16"H
3 x 100w MB Bulbs
Crystal Optional-CRY100



30541MCBN 1-Light Wall Sconce
Brighton
6.5"W x 20"H x 8.5"Ext.
1 x 100w MB Bulb
Crystal Optional-CRY107



30542MCBN 2-Light Bath Vanity
Brighton
15.5"W x 10.5"H x 9.5"Ext.
2 x 100w MB Bulbs
Crystal Optional-CRY107



30543MCBN 3-Light Bath Vanity
Brighton
24"W x 10.5"H x 9.5"Ext.
3 x 100w MB Bulbs
Crystal Optional-CRY110



30544MCBN 4-Light Bath Vanity
Brighton
32.5"W x 10.5"H x 9.5"Ext.
4 x 100w MB Bulbs
Crystal Optional-CRY108



Dresden

With Old World charm, Dresden's Flemish metalwork in Filbert finish gracefully curves around a center column of translucent antique glass, and its amber crystal pendants and candle-like lamps warm the room. Choose classic A-line shades or frosted Ember glass.

22288FL 15-Light Chandelier
22288FL/SHD91 With Shade
Filbert
47"W x 53"H
15 x 40w CA Bulbs
*Shades Optional-SHD91GS
Crystals Included*



SHD91GS Shade
3"Top x 6.5"Base x 6"H



800.486.2946

maximlighting.com



SHD90GS Shade
3"Top x 6.5"Base x 5"H



22283FL 3-Light Chandelier
22283FL/SHD90 With Shade
Filbert
20"W x 23"H
3 x 60w CA Bulbs
Shades Optional-SHD90GS
Crystals Included



22285FL 6-Light Chandelier
22285FL/SHD91 With Shade
Filbert
29.5"W x 33.5"H
6 x 60w CA Bulbs
Shades Optional-SHD91GS
Crystals Included

22282FL 2-Light Wall Sconce
22282FL/SHD91 With Shade
Filbert
13.5"W x 15"H x 8"Ext.
2 x 60w CABulbs
Shades Optional-SHD91GS
Crystals Included



22281FL 1-Light Wall Sconce
22281FL/SHD91 With Shade
Filbert
4"W x 13.5"H x 9"Ext.
1 x 60w CABulb
Shades Optional-SHD91GS
Crystals Included



22286FL 9-Light Chandelier
22286FL/SHD91 With Shade
Filbert
34"W x 39.5"H
9 x 60w CABulbs
Shades Optional-SHD91GS
Crystals Included

22263EMFL 4-Light Pendant
 Filbert
 33.5"W x 39"H
 4 x 60w MB Bulbs
Crystals Included



22260EMFL 3-Light Flush Mount
 Filbert
 22"W x 9.5"H
 3 x 60w MB Bulbs
Crystals Included




22262EMFL 3-Light Pendant
 Filbert
 28"W x 33.5"H
 3 x 100w MB Bulbs
Crystals Included



22261EMFL 3-Light Semi-Flush
 Filbert
 21.5"W x 14.5"H
 3 x 60w MB Bulbs
Crystals Included

22264EMFL 5-Light Chandelier
Filbert
27"W x 27"H
5 x 100w MB Bulbs
Crystals Included



22268EMFL 15-Light Chandelier
Filbert
47"W x 53"H
15 x 40w MB Bulbs
Crystals Included





22265EMFL 6-Light Chandelier
Filbert
30"W x 33"H
6 x 100w MB Bulbs
Crystals Included



22266EMFL 9-Light Chandelier
Filbert
34.5"W x 39.5"H
9 x 60w MB Bulbs
Crystals Included



22272EMFL 2-Light Wall Sconce
Filbert
16"W x 15"H x 9"Ext.
2 x 100w MB Bulbs
Crystals Included



22271EMFL 1-Light Wall Sconce
Filbert
7"W x 14"H x 9"Ext.
1 x 100w MB Bulb
Crystals Included



22269EMFL 3-Light Island Pendant
Filbert
45.5"W x 22"H
3 x 100w MB Bulbs
Crystals Included



22273EMFL 2-Light Bath Vanity
 Filbert
 20.5"W x 10"H x 9"Ext.
 2 x 100w MB Bulbs



22274EMFL 3-Light Bath Vanity
 Filbert
 31"W x 10"H x 9"Ext.
 3 x 100w MB Bulbs



22275EMFL 4-Light Bath Vanity
 Filbert
 41.5"W x 10"H x 9"Ext.
 4 x 100w MB Bulbs



92270EMFL
 1-Light Mini Pendant
 Filbert
 7"W
 1 x 100w MB Bulb
*Additional stems available:
 6" order STR06206FL
 12" order STR06212FL
 One 6" stem and three 12"
 stems included.*



Fremont

A curvaceous metal frame finished in Platinum Dusk tastefully support fluted Wilshire glass shades.

22245WSPD 5-Light Chandelier
Platinum Dusk
25"W x 27.5"H
5 x 100w MB Bulbs



22248WSPD 24-Light Chandelier
Platinum Dusk
58"W x 66.5"H
24 x 40w MB Bulbs



800.486.2946

maximlighting.com

22246WSPD 9-Light Chandelier
Platinum Dusk
34"W x 37"H
9 x 100w MB Bulbs



22247WSPD 15-Light Chandelier
Platinum Dusk
46"W x 50"H
15 x 60w MB Bulbs

22240WSPD 2-Light Flush Mount
Platinum Dusk
15"W x 6"H
2 x 75w MB Bulbs



22241WSPD 3-Light Semi-Flush
Platinum Dusk
21"W x 12"H
3 x 60w MB Bulbs



22243WSPD
3-Light Pendant
Platinum Dusk
25.5"W x 31.5"H
3 x 100w MB Bulbs



22242WSPD 4-Light Semi-Flush
Platinum Dusk
31"W x 19.5"H
4 x 100w MB Bulbs



22250WSPD 4-Light Pendant
Platinum Dusk
31"W x 38.5"H
4 x 100w MB Bulbs



22251WSPD 1-Light Wall Sconce
Platinum Dusk
7"W x 17.5"H x 10"Ext.
1 x 100w MB Bulb



22244WSPD
3-Light Chandelier
Platinum Dusk
23"W x 20.5"H
3 x 100w MB Bulbs



22252WSPD 2-Light Bath Vanity
Platinum Dusk
18"W x 10"H x 8"Ext.
2 x 100w MB Bulbs



92240WSPD
1-Light Mini Pendant
Platinum Dusk
7"W
1 x 100w MB Bulb



22253WSPD
3-Light Bath Vanity
Platinum Dusk
29"W x 10"H x 8"Ext.
3 x 100w MB Bulbs



22254WSPD 4-Light Bath Vanity
Platinum Dusk
39"W x 11"H x 8"Ext.
4 x 100w MB Bulbs

Richmond

Simplicity meets elegance in this new collection of forged iron frames hand painted in our new Colonial Umber finish. The optional large scale crystals add a touch of class while the addition of shades creates the perfect lighting effect. Some styles also feature our ever popular Wilshire glass.

31007
Optional-CRY085



31007CU 15-Light Chandelier
31007CU/SHD62 With Shade
Colonial Umber
50.5"W x 54"H
15 x 40w CA Bulbs
Shades *Optional-SHD62TN*
Crystal *Optional-CRY085, CRY095*
Metal and Drip Candle Covers Included

800.486.2946

maximlighting.com



MED003CU
Colonial Umber
18"W x 1.5"H
With 4" opening



MED002CU
Colonial Umber
26.5"W x 1.5"H
With 4" opening



SHD62TN Shade
3"Top x 6.5"Base x 6"H
Candle FOB Mount



*Drip Candle Cover
(Included)*



*Metal Candle Cover
(Included)*



*Clear Beveled Crystal
(Optional)*



*Gold Luster Pendants
(Optional)*



31006CU 9-Light Chandelier
31006CU/SHD62 With Shade
Colonial Umber
37.5"W x 44"H
9 x 60w CA Bulbs
*Shades Optional-SHD62TN
Crystal Optional-CRY083,CRY094
Metal and Drip Candle Covers Included*



31006
Optional-CRY094



31005
Optional-CRY083



31005CU 6-Light Chandelier
31005CU/SHD62 With Shade
Colonial Umber
30.5"W x 36"H
6 x 60w CABulbs
Shades *Optional-SHD62TN*
Crystal *Optional-CRY083, CRY094*
Metal and Drip Candle Covers Included



31009
Optional-CRY083



31009CU 6-Light Chandelier
31009CU/SHD62 With Shade
Colonial Umber
40"L x 19.5"W x 26"H
6 x 60w CABulbs
Shades *Optional-SHD62TN*
Crystal *Optional-CRY083, CRY094*
Metal and Drip Candle Covers Included



31001WSCU 3-Light Semi-Flush
Colonial Umber
22.5"W x 13.5"H
3 x 60w MB Bulbs



31000WSCU 2-Light Flush Mount
Colonial Umber
14"W x 6.5"H
2 x 75w MB Bulbs



31003
Optional-CRY082



31003WSCU 3-Light Pendant
Colonial Umber
26"W x 27.5"H
3 x 60w MB Bulbs
Crystal Optional-CRY082, CRY098



93101WSCU 1-Light Mini Pendant
Colonial Umber
7"W
1 x 100w MB Bulb
*Additional stems available:
6" order STR06206CU
12" order STR06212CU
One 6" stem and three 12"
stems included.*



Empress

These open air entry lanterns are classically styled and finished in Colonial Umber. This finish blends well with a number of Maxim families. Three sizes to choose from with scale to fit a variety of size homes.



20744CU 8-Light Cage
Colonial Umber
26.5"W x 49"H
8 x 60w CA Bulbs

800.486.2946

maximlighting.com

20743CU 6-Light Cage
Colonial Umber
21"W x 39.5"H
6 x 60w CA Bulbs



20742CU 3-Light Cage
Colonial Umber
11"W x 21.5"H
3 x 60w CA Bulbs

Sausalito

Flowing ribbons of oval tubular steel
switchback to create
a harmonious form hand painted in
a warm Filbert finish.
The warm glow from the Mocha
Cloud glass will create
ambience in any room of the home.

21127MCFL 15-Light Chandelier
Filbert
49"W x 61"H
15 x 60w MB Bulbs



800.486.2946

maximlighting.com



21124MCFL 3-Light Chandelier
Filbert
20"W x 27.5"H
3 x 100w MB Bulbs



21125MCFL 5-Light Chandelier
Filbert
27.5"W x 39"H
5 x 100w MB Bulbs



21126MCFL 9-Light Chandelier
Filbert
34"W x 48.5"H
9 x 100w MB Bulbs

21120MCFL 3-Light Semi-Flush
Filbert
16"W x 9.5"H
3 x 60w MB Bulbs



21121MCFL 3-Light Semi-Flush
Filbert
18"W x 15.5"H
3 x 60w MB Bulbs



91120MCFL
1-Light Mini Pendant
Filbert
5"W
1 x 100w MB Bulb
*Additional stems available:
6" order STR06206FL
12" order STR06212FL
One 6" stem and three 12"
stems included.*



21123MCFL 3-Light Pendant
Filbert
27"W x 31.5"H
3 x 100w MB Bulbs



21133MCFL 3-Light Bath Vanity
 Filbert
 29"W x 12"H x 7"Ext.
 3 x 100w MB Bulbs



21134MCFL 4-Light Bath Vanity
 Filbert
 38"W x 12"H x 7"Ext.
 4 x 100w MB Bulbs



21131MCFL 1-Light Wall Sconce
 Filbert
 5"W x 15"H x 8"Ext.
 1 x 100w MB Bulb



21132MCFL 2-Light Bath Vanity
 Filbert
 18.5"W x 12"H x 7"Ext.
 2 x 100w MB Bulbs



La Scalla

Classically simplistic frames
finished in Weathered Copper
and featuring our ever-popular
Mocha Cloud glass.



11765MCWC 9-Light Chandelier
Weathered Copper
32"W x 33"H
9 x 100w MB Bulbs

800.486.2946

maximlighting.com

11764MCWC 6-Light Chandelier
 Weathered Copper
 28.5"W x 26"H
 6 x 100w MB Bulbs



11769MCWC 2-Light Island Pendant
 Weathered Copper
 42"L x 16"W x 26"H 37"OAH
 2 x 100w MB Bulbs
 Shown with 6" stem
 Additional stems available:
 6" stem order-STR10006WC
 12" stem order-STR10012WC

120°





11760MCWC 2-Light Flush Mount
Weathered Copper
13"W x 8"H
2 x 75w MB Bulbs



11763MCWC 3-Light Pendant
Weathered Copper
26.5"W x 28"H
3 x 100w MB Bulbs



11766MCWC 3-Light Pendant
Weathered Copper
22"W x 39.5"H
3 x 100w MB Bulbs



11761MCWC 3-Light Semi-Flush
Weathered Copper
20"W x 18"H
3 x 100w MB Bulbs
KIT

11767MCWC 1-Light Wall Sconce
Weathered Copper
6.5"W x 12"H x 8"Ext.
1 x 100w MB Bulb



11771MCWC 2-Light Bath Vanity
Weathered Copper
15"W x 8.5"H x 6.5"Ext.
2 x 100w MB Bulbs



11772MCWC 3-Light Bath Vanity
Weathered Copper
23"W x 8.5"H x 6.5"Ext.
3 x 100w MB Bulbs



11773MCWC 4-Light Bath Vanity
Weathered Copper
31"W x 8.5"H x 6.5"Ext.
4 x 100w MB Bulbs



91005MCWC
1-Light Mini Pendant
Weathered Copper
6.5"W
1 x 100w MB Bulb



Augusta

Graceful sweeping arms complimented by acanthus leaves which can be truly enhanced by the addition of optional crystal and shades. Some models feature the subtle warmth of our Café glass and all are brought to life with our new Auburn Florentine finish.



13579AF 27-Light Chandelier
13579AF/SHD62 *With Shade*
Auburn Florentine
60.5"W x 69.5"H
27 x 25w CA Bulbs
Shades Optional-SHD62TN
Crystal Optional-CRY091

800.486.2946

maximlighting.com



SHD62TN Shade
3"Top x 6.5"Base x 6"H
Candle FOB Mount



13577AF 15-Light Chandelier
13577AF/SHD62 With Shade
Auburn Florentine
50"W x 61"H
15 x 40w CA Bulbs
Shades Optional-SHD62TN
Crystal Optional-CRY081

13584AF 3-Light Chandelier
13584AF/SHD62 *With Shade*
Auburn Florentine
19.5"W x 22"H
3 x 60w CABulbs
Shades Optional-SHD62TN
Crystal Optional-CRY092



13575AF 5-Light Chandelier
13575AF/SHD62 *With Shade*
Auburn Florentine
27"W x 37.5"H
5 x 60w CABulbs
Shades Optional-SHD62TN
Crystal Optional-CRY079





SHD62TN Shade
 3"Top x 6.5"Base x 6"H
 Candle FOB Mount



13576AF 9-Light Chandelier
13576AF/SHD62 With Shade
 Auburn Florentine
 34"W x 44.5"H
 9 x 60w CA Bulbs
 Shades Optional-SHD62TN
 Crystal Optional-CRY080



13569CFAF 27-Light Chandelier
Auburn Florentine
60.5"W x 69.5"H
27 x 40w MB Bulbs
Crystal Optional-CRY091



13567CFAF 15-Light Chandelier
Auburn Florentine
50"W x 57"H
15 x 60w MB Bulbs
Crystal Optional-CRY081

13561CFAF 2-Light Flush Mount
Auburn Florentine
15"W x 6.5"H
2 x 75w MB Bulbs



13562CFAF 3-Light Semi-Flush
Auburn Florentine
21"W x 14.5"H
3 x 60w MB Bulbs
Crystal Optional-CRY077



13560CFAF
2-Light Flush Mount
Auburn Florentine
13"W x 6.5"H
2 x 60w MB Bulbs



13583CFAF 3-Light Pendant
Auburn Florentine
31"W x 37"H
3 x 100w MB Bulbs
Crystal Optional-CRY093



13563CFAF 3-Light Pendant
Auburn Florentine
25.5"W x 30"H
3 x 60w MB Bulbs
Crystal Optional-CRY078

13585CFAF 3-Light Chandelier
 Auburn Florentine
 20"W x 22"H
 3 x 100w MB Bulbs
Crystal Optional-CRY092



13566CFAF 9-Light Chandelier
 Auburn Florentine
 34.5"W x 48"H
 9 x 100w MB Bulbs
Crystal Optional-CRY080



MED001AF
Auburn Florentine
23.5"W x 2.5"H
With 4" opening



13564CF AF
5-Light Chandelier
Auburn Florentine
26.5"W x 19.5"H
5 x 100w MB Bulbs

13565CF AF 5-Light Chandelier
Auburn Florentine
28"W x 35.5"H
5 x 100w MB Bulbs
Crystal Optional-CRY079





13571CFAF
 1-Light Wall Sconce
 Auburn Florentine
 7"W x 12"H x 9"Ext.
 1 x 100w MB Bulb
 Crystal Optional-CRY087



13572CFAF
 2-Light Wall Sconce
 Auburn Florentine
 16"W x 12"H x 8.5"Ext.
 2 x 100w MB Bulbs
 Crystal Optional-CRY088



13573CFAF 3-Light Bath Vanity
 Auburn Florentine
 28.5"W x 9"H x 10"Ext.
 3 x 100w MB Bulbs
 Crystal Optional-CRY089



91560CFAF
 1-Light Mini Pendant
 Auburn Florentine
 7"W
 1 x 100w MB Bulb
 Additional stems available:
 6" order STR06206AF
 12" order STR06212AF
 One 6"stem and three 12"
 stems included.



13574CFAF 4-Light Bath Vanity
 Auburn Florentine
 37.5"W x 9"H x 10"Ext.
 4 x 100w MB Bulbs
 Crystal Optional-CRY090



La Salle

Twisted metal arms hand painted in our Honey Auburn finish cradle a fluted Mocha Cloud glass shade.



16007MCHA 20-Light Chandelier
Honey Auburn
48"W x 49"H
20 x 60w MB Bulbs

800.486.2946

maximlighting.com




16006MCHA 9-Light Chandelier
Honey Auburn
33.5"W x 40"H
9 x 100w MB Bulbs

16005MCHA 5-Light Chandelier
Honey Auburn
26"W x 30"H
5 x 100w MB Bulbs



16004MCHA 3-Light Chandelier
Honey Auburn
26"W x 23"H
3 x 100w MB Bulbs



91600MCHA 1-Light Mini Pendant
Honey Auburn
8"W
1 x 100w MB Bulb
*Additional stems available:
6" order STR06206HA
12" order STR06212HA
One 6" stem and three 12"
stems included.*





16000MCHA 2-Light Flush Mount
Honey Auburn
17"W x 10"H
2 x 60w MB Bulbs



16002MCHA
3-Light Pendant
Honey Auburn
25"W x 32"H
3 x 100w MB bulbs



16003MCHA 3-Light Pendant
Honey Auburn
31"W x 42"H
3 x 100w MB Bulbs



16001MCHA 3-Light Semi-Flush
Honey Auburn
22"W x 16"H
3 x 100w MB bulbs

Beaumont

This versatile family gives you the option of with glass . when the room design calls for it. The multi tone Golden Fawn finish adds richness and depth while the soft glow of the Café glass adds ambience to the room.

24105CFGF 5-Light Chandelier
Golden Fawn
30"W x 36.5"H
5 x 100w MB Bulbs



MED003GF
Golden Fawn
18"W x 1.5"H
With 4" opening



24107CFGF 15-Light Chandelier
Golden Fawn
42"W x 58"H
15 x 60w MB Bulbs

800.486.2946

maximlighting.com



24106CFGF
 9-Light Chandelier
 Golden Fawn
 34.5"W x 44.5"H
 9 x 100w MB Bulbs



24108CFGF 3-Light Chandelier
 Golden Fawn
 18.5"W x 22"H
 3 x 100w MB Bulbs



24109CFGF 6-Light Chandelier
 Golden Fawn
 40"L x 24"W x 27"H
 6 x 100w MB Bulbs

24100CFGF 2-Light Flush Mount
Golden Fawn
13"W x 6.5"H
2 x 60w MB Bulbs



24101CFGF
2-Light Flush Mount
Golden Fawn
15"W x 6.5"H
2 x 75w MB Bulbs



24102CFGF 3-Light Semi-Flush
Golden Fawn
22.5"W x 13"H
3 x 60w MB Bulbs



24104CFGF 3-Light Pendant
Golden Fawn
29.5"W x 36.5"H
3 x 100w MB Bulbs



24103CFGF 3-Light Pendant
Golden Fawn
26"W x 32.5"H
3 x 60w MB Bulbs



24111CFGF 1-Light Wall Sconce
Golden Fawn
7"W x 12"H x 8"Ext.
1 x 100w MB Bulb



24112CFGF 2-Light Wall Sconce
Golden Fawn
15"W x 12"H x 8"Ext.
2 x 100w MB Bulbs



24113CFGF 3-Light Bath Vanity
Golden Fawn
29"W x 9.5"H x 10"Ext.
3 x 100w MB Bulbs



24114CFGF 4-Light Bath Vanity
Golden Fawn
37"W x 9.5"H x 10"Ext.
4 x 100w MB Bulbs



94100CFGF 1-Light Mini Pendant
Golden Fawn
6.5"W
1 x 100w MB Bulb

*Additional stems available:
6" order STR06206GF
12" order STR06212GF
One 6" stem and three 12"
stems included.*



Palazzo

The soft glow from this Vanilla Swirl glass creates such ambiance. The old world frame is hand painted in an Antique Pecan finish.



12292VSAP 21-Light Chandelier
Antique Pecan
43"W x 48"H
21 x 60w MB Bulbs


800.486.2946

maximlighting.com


12294VSAP 5-Light Chandelier
 Antique Pecan
 26.5"W x 27.5"H
 5 x 100w MB Bulbs



12295VSAP 9-Light Chandelier
 Antique Pecan
 31.5"W x 31"H
 9 x 100w MB Bulbs



12293VSAP 3-Light Chandelier
Antique Pecan
19"W x 20"H
3 x 100w MB Bulbs



12290VSAP 2-Light Island Pendant
Antique Pecan
41"L x 14"W x 27.5"H 43.5"OAH
2 x 100w MB Bulbs
*Additional stems available:
6" stem order-STR10006AP
12" stem order-STR10012AP*

120°





12281VSAP 3-Light Semi-Flush
 Antique Pecan
 17.5"W x 15"H
 3 x 100w MB Bulbs




12280VSAP 3-Light Flush Mount
 Antique Pecan
 15"W x 9"H
 3 x 60w MB Bulbs



92290VSAP
 1-Light Mini Pendant
 Antique Pecan
 5"W
 1 x 100w MB Bulb
*One 6" stem and three 12"
 Stems Included
 Additional stems available:
 6" order STR06206AP
 12" order STR06212AP*

120°



12282VSAP 3-Light Pendant
 Antique Pecan
 27"W x 31.5"H
 3 x 100w MB Bulbs

Apollo

Our Greek Bronze finish brings out the detail and accents the Scroll work in this collection. Beautiful White Alabaster is the perfect compliment.



2225WHGB 8-Light Chandelier
Greek Bronze
28"W x 28"H
6 x 75w MB Bulbs + 2 x 60w MB Bulbs

800.486.2946

maximlighting.com



2226WHGB 5-Light Chandelier
Greek Bronze
28"W x 23.5"H
5 x 75w MB Bulbs



2228WHGB 1-Light Wall Sconce
Greek Bronze
14"W x 15"H x 7"Ext.
1 x 60w MB Bulb



2223WHGB 2-Light Pendant
Greek Bronze
17"W x 30.5"H
2 x 60w MB Bulbs



2221WHGB 6-Light Pendant
Greek Bronze
33"W x 47"H
6 x 60w MB Bulbs



2224WHGB 3-Light Pendant
Greek Bronze
20"W x 35"H
3 x 60w MB Bulbs

2222WHGB 3-Light Flush Mount
 Greek Bronze
 20"W x 10"H
 3 x 60w MB Bulbs



2220WHGB 3-Light Flush Mount
 Greek Bronze
 16"W x 9"H
 3 x 60w MB Bulbs



2229WHGB 3-Light Semi-Flush
 Greek Bronze
 17"W x 16.5"H
 3 x 100w MB Bulbs



2227WHGB 4-Light Pendant
 Greek Bronze
 27"W x 32"H
 4 x 100w MB Bulbs

Portofino


The focal point of this lovely family is the ornately detailed rim finished in our Oil Rubbed Bronze finish that supports the Vintage Amber glass.

20280VAOI 3-Light Flush Mount
Oil Rubbed Bronze
16.75"W x 7"H
3 x 100w MB Bulbs



SHD40BL Shade
3"Top x 7"Bottom x 4.5"H
Sit On

20285VAOI 8-Light Chandelier
20285VAOI/SHD40 With Shade
Oil Rubbed Bronze
26.5"W x 29"H
5 x 60w CABulbs + 3 x 60w MB Bulbs
Shades Optional-**SHD40BL**



20286VAOI 9-Light Chandelier
20286VAOI/SHD40 With Shade
Oil Rubbed Bronze
36.5"W x 36"H
6 x 60w CABulbs + 3 x 60w MB Bulbs
Shades Optional-**SHD40BL**



20281VAOI 3-Light Semi-Flush
 Oil Rubbed Bronze
 17.5"W x 15"H
 3 x 100w MB Bulbs
 KIT



20284VAOI 2-Light Pendant
 Oil Rubbed Bronze
 15"W x 35"H
 2 x 100w MB Bulbs



20289VAOI 1-Light Floor Lamp
 Oil Rubbed Bronze
 19.5"W x 70"H
 1 x 150w MB Bulb
 With Dimmer Switch



20283VAOI 4-Light Pendant
 Oil Rubbed Bronze
 33.5"W x 29"H
 4 x 100w MB Bulbs

Monaco

Sweeping rounded arms with delicate candelabra lights are the trademark of this stylish collection. Delicate gold leaf designs accent the rich Windsor Bronze finish.



2890WB 2-Light Wall Sconce
2890WB/CRY 005
Windsor Bronze
13"W x 18"H x 7"Ext.
2 x 60w CABulbs
Shades Optional-SHD 46VN
Crystal Optional



2891WB 3-Light Wall Sconce
2891WB/CRY 004
Windsor Bronze
15"W x 19"H x 9.5"Ext.
3 x 60w CABulbs
Shades Optional-SHD 46VN
Crystal Optional



2899WB 24-Light Chandelier
2899WB/CRY 025
Windsor Bronze
61"W x 77"H
24 x 40w CABulbs
Shades Optional-SHD 46VN
Crystal Optional

800.486.2946

maximlighting.com



SHD46VN Shade
 3.5"Top x 6.5"Base x 6"H
 Sit On

2896WB 8-Light Chandelier
2896WB/CRY 023
 Windsor Bronze
 30"W x 40"H
 8 x 60w CABulbs
 Shades Optional-SHD 46VN
 Crystal Optional



2897WB 12-Light Chandelier
2897WB/CRY 024
 Windsor Bronze
 40"W x 42"H
 12 x 60w CABulbs
 Shades Optional-SHD 46VN
 Crystal Optional

Java

A bold collection featuring classic styling. Beautiful Java swirl glass designed specifically for our Vintage Copper finish.

2594JAVC 3-Light Pendant
Vintage Copper
14.5"W x 23"H
3 x 75w MB Bulbs



2595JAVC 8-Light Chandelier
Vintage Copper
30"W x 23"H
6 x 100w MB Bulbs
+ 2 x 60w MB Bulbs



800.486.2946

maximlighting.com



2590JAVC 2-Light Flush Mount
Vintage Copper
14.5"W x 7.5"H
2 x 75w MB Bulbs



2596JAVC 1-Light Wall Sconce
Vintage Copper
7"W x 11"H x 10"Ext.
1 x 100w MB Bulb



2597JAVC 2-Light Wall Sconce
Vintage Copper
16"W x 11"H x 10"Ext.
2 x 100w MB Bulbs



Morocco

An ornate design with middle European influences and a sturdy finish in beautiful Windsor Bronze. Some fixtures offered with warm Vintage Amber glass.

20676WB 6-Light Chandelier
Windsor Bronze
33"W x 30.5"H
6 x 60w CA Bulbs



20677WB 9-Light Chandelier
Windsor Bronze
40.5"W x 35.5"H
9 x 60w CA Bulbs



20674VAWB 4-Light Pendant
Windsor Bronze
32"W x 31.5"H
4 x 100w MB Bulbs

20673WB 3-Light Wall Sconce
Windsor Bronze
15.5"W x 18.5"H x 10.5"Ext.
3 x 60w CA Bulbs



20671WB 1-Light Wall Sconce
Windsor Bronze
5.5"W x 17.5"H x 10.5"Ext.
1 x 60w CA Bulb



20678VAWB 3-Light Semi-Flush
Windsor Bronze
23.75"W x 21"H
3 x 100w MB Bulbs
K₁T

Barcelona

Heavy hand forged frames finished in Oil Rubbed Bronze is warmed by the glow of our new Amber Ice glass.



13417AIOI 21-Light Chandelier
Oil Rubbed Bronze
60"W x 55"H
21 x 60w MB bulbs

800.486.2946

maximlighting.com

13416AIOI 9-Light Chandelier
 Oil Rubbed Bronze
 32.5"W x 29.5"H
 9 x 100w MB bulbs



13413AIOI 3-Light Chandelier
 Oil Rubbed Bronze
 20"W x 17"H
 3 x 100w MB bulbs



13415AIOI 5-Light Chandelier
 Oil Rubbed Bronze
 26.5"W x 24.5"H
 5 x 100w MB bulbs

13411AIOI 3-Light Pendant
Oil Rubbed Bronze
21"W x 26"H
3 x 100w MB bulbs



13418AIOI 12-Light Chandelier
Oil Rubbed Bronze
40.5"W x 37.5"H
12 x 60w MB bulbs






13421AIOI 4-Light Pendant
 Oil Rubbed Bronze
 27.5"W x 34.5"H
 4 x 100w MB bulbs



13414AIOI 5-Light Chandelier
 Oil Rubbed Bronze
 24.5"W x 22"H
 5 x 100w MB bulbs



13412AIOI 4-Light Pendant
 Oil Rubbed Bronze
 37.5"W x 38.5"H
 4 x 100w MB bulbs



8993001
Oil Rubbed Bronze
Maple/ Walnut Blades
FKT2341AIOI
12"W x 6.5"H
3 x 60w CA Bulbs



13410AIOI 3-Light Semi-Flush
Oil Rubbed Bronze
15.5"W x 9"H
3 x 60w MB Bulbs



13420AIOI 2-Light Island Pendant
Oil Rubbed Bronze
44"L x 15.5"W x 32.5"H
2 x 100w MB Bulbs



13419AIOI 1-Light Wall Sconce
 Oil Rubbed Bronze
 7"W x 22"H x 9"Ext.
 1 x 100w MB Bulb



13422AIOI
 2-Light Wall Sconce
 Oil Rubbed Bronze
 16.5"W x 12.5"H x 9"Ext.
 2 x 100w MB Bulbs



13423AIOI 3-Light Bath Vanity
 Oil Rubbed Bronze
 26"W x 9.5"H x 7.5"Ext.
 3 x 100w MB Bulbs



13424AIOI 4-Light Bath Vanity
 Oil Rubbed Bronze
 35"W x 10.5"H x 7.5"Ext.
 4 x 100w MB Bulbs



91412AIOI 1-Light Mini Pendant
 Oil Rubbed Bronze
 7"W
 1 x 100w MB Bulb
*Additional stems available:
 6" order STR06206OI
 12" order STR06212OI
 One 6" stem and two 12"
 stems included.*



Aspen

Warm and inviting, this collection features Vintage Amber glass and our Oil Rubbed Bronze finish.


20607VAOI 6-Light Chandelier
Oil Rubbed Bronze
30"W x 25"H
6 x 100w MB Bulbs



20614VAOI 12-Light Chandelier
Oil Rubbed Bronze
38"W x 37"H
12 x 100w MB Bulbs

800.486.2946

maximlighting.com



20613VAOI 9-Light Chandelier
Oil Rubbed Bronze
30"W x 32"H
6 x 100w MB Bulbs + 3 x 60w MB Bulbs




20610VAOI 8-Light Chandelier
Oil Rubbed Bronze
35"W x 35.5"H
8 x 100w MB Bulbs

20620OI 12-Light Chandelier
Oil Rubbed Bronze
36"W x 37"H
12 x 60w CA Bulbs



20612OI 6-Light Chandelier
Oil Rubbed Bronze
28.5"W x 25"H
6 x 60w CA Bulbs

20606VAOI 3-Light Pendant
 Oil Rubbed Bronze
 24"W x 31"H
 3 x 100w MB Bulbs



20601VAOI 2-Light Flush Mount
 Oil Rubbed Bronze
 13"W x 9"H
 2 x 100w MB Bulbs


91044VAOI 1-Light Mini Pendant
 Oil Rubbed Bronze
 6"W
 1 x 100w MB Bulb



20602VAOI 3-Light Flush Mount
 Oil Rubbed Bronze
 16"W x 9"H
 3 x 100w MB Bulbs



20618VAOI 1-Light Wall Sconce
Oil Rubbed Bronze
6W x 25H x 7E xt.
1 x 100w MB Bulb



20617VAOI
1-Light Wall Sconce
Oil Rubbed Bronze
15"W x 7.5H x 7E xt.
1 x 100w MB Bulb



20619VAOI 3-Light Wall Sconce
Oil Rubbed Bronze
16.5"W x 26"H x 7"Ext.
3 x 100w MB Bulbs



20628VAOI 1-Light Floor Lamp
 Oil Rubbed Bronze
 19W x 72H
 1 x 150w MB Bulb
 With Dimmer Switch



20627GTOI 1-Light Table Lamp
 Oil Rubbed Bronze
 18W x 32H
 1 x 150w MB Bulb
 SHD 32GT
 3-Way Switch

Notre Dame

The hand crafted nature of this series is evident in the support rods which are masterfully forged twists finished in our Oil Rubbed Bronze finish. The Wilshire candle shades add an authentic touch to this look.



10976WSOI 8-Light Chandelier
Oil Rubbed Bronze
29.5"W x 30.5"H
8 x 60w CA Bulbs



10975WSOI 6-Light Chandelier
Oil Rubbed Bronze
24"W x 24.5"H
6 x 60w CA Bulbs



91084WSOI 1-Light Mini Pendant
Oil Rubbed Bronze
7"W
1 x 60w CA Bulb



10977WSOI 12-Light Chandelier
Oil Rubbed Bronze
32W x 44H
12 x 60w CA Bulbs

800.486.2946

maximlighting.com



10970WSOI 1-Light Wall Sconce
 Oil Rubbed Bronze
 7.5"W x 8"H x 8"Ext.
 1 x 60w CA Bulb



10971WSOI 2-Light Bath Vanity
 Oil Rubbed Bronze
 13.5"W x 10"H x 8"Ext.
 2 x 60w CA Bulbs



10972WSOI 3-Light Bath Vanity
 Oil Rubbed Bronze
 17"W x 10"H x 9"Ext.
 3 x 60w CA Bulbs



10973WSOI 4-Light Bath Vanity
 Oil Rubbed Bronze
 28.5"W x 10"H x 8.5"Ext.
 4 x 60w CA Bulbs

Verona

Decorative and bold, this collection features Vintage Amber glass and our popular Oil Rubbed Bronze finish.



20635OI 6-Light Chandelier
Oil Rubbed Bronze
30"W x 27"H
6 x 60w CA Bulbs

800.486.2946

maximlighting.com



20633OI 2-Light Wall Sconce
Oil Rubbed Brozne
14"W x 11"H x 9"Ext.
2 x 60w CA Bulbs



20637VAOI 3-Light Island Pendant
Oil Rubbed Brozne
48"L x 13"W x 24.5"H 102"OAH
3 x 100w MB Bulbs

Southern

Classic form marrying ornate trim with the gentle curve of bent metal painted in Kentucky Bronze. The smooth lines of the Latte glass shades add softness to the overall look. Newly added 3-tier chandelier complete this family.



2936LTKB 15-Light Chandelier
Kentucky Bronze
48"W x 46"H
15 x 60w MB Bulbs

800.486.2946

maximlighting.com

2934LTKB 5-Light Chandelier
Kentucky Bronze
29"W x 24.5"H
5 x 100w MB Bulbs



2935LTKB 9-Light Chandelier
Kentucky Bronze
32"W x 28"H
9 x 100w MB Bulbs





2939LTKB 2-Light Wall Sconce
 Kentucky Bronze
 15.5"W x 9.5"H x 9.5"Ext.
 2 x 100w MB Bulbs



2931LTKB 2-Light Pendant
 Kentucky Bronze
 16"W x 21.5"H
 2 x 100w MB Bulbs



2933LTKB 3-Light Chandelier
 Kentucky Bronze
 19"W x 17"H
 3 x 100w MB Bulbs



91092LTKB 1-Light Mini Pendant
 Kentucky Bronze
 7"W
 1 x 100w MB Bulb
 Additional stems available:
 6" order STR06206KB
 12" order STR06212KB
 One 6" stem and
 three 12" stems included.



2932LTKB 2-Light Island Pendant
 Kentucky Bronze
 33"L x 14"W x 18.5"H
 2 x 100w MB Bulbs



2938KB 8-Light Cage
Kentucky Bronze
31"W x 51"H
8 x 60w CABulbs



2937KB 4-Light Cage
Kentucky Bronze
22"W x 32.5"H
4 x 60w CABulbs

Tahoe

Elegant iron and metal shades provide a functional yet decorative presence. Finished in Kentucky Bronze.

7738BK 5-Light Chandelier
Black
26"W x 21"H
5 x 60w CABulbs
Shades Optional
SHD 28KB
Round



7750KB 6-Light Chandelier
Kentucky Bronze
38"L x 31"W x 24"H
6 x 60w CABulbs
Shades Optional
SHD 28KB
Oval

800.486.2946

maximlighting.com



20165KB 1-Light Pendant
Kentucky Bronze
12"W x 19.5"H
1 x 60w CABulb



7763KB 1-Light Pendant
Kentucky Bronze
11.25"W x 16.5"H
1 x 60w CABulb



7760KB 6-Light Chandelier
Kentucky Bronze
28.5"W x 22"H
6 x 60w CABulbs
Shades Optional
SHD 28KB
Round

Island

7755KB 6-Light Chandelier
Kentucky Bronze
38"L x 29.5"W x 21.5"H
4 x 60w CA Bulbs
2 x 50w MB R20 Bulbs
Shades Included
SHD 23KB
Hooks Included
HOK 02KB
Oval



SHD23KB Shade
3"Top x 6"Base x 5"H
Sit on Candle Cover (1 inch)

800.486.2946

maximlighting.com

7756KB 8-Light Chandelier
Kentucky Bronze
44"L x 32"W x 25.5"H
6 x 60w CA Bulbs
2 x 50w MB R20 Bulbs
Shades Included
SHD 23KB
Hooks Included
HOK 02KB
Oval





HOK04 SN, BZ (Accessory)
1.5"W x 5.5"H

7751 BZ, SN 2-Light Chandelier
32"L x 17"W x 17"H
2 x 50w MB R20 Bulbs
Hooks Included
HOK04BZ, SN



7759SN 8-Light Chandelier
Satin Nickel
44.5"L x 29.5"W x 17"H
6 x 60w CABulbs
2 x 50w MB R20 Bulbs
3-Way Switch
Hooks Included
HOK04SN

Elegante

One of our most popular collections, Elegante combines lighting with decorating. Delicate leaves and crystals tip the wrap-around vines. Offered in Etruscan Gold or Oil Rubbed Bronze.

2852 EG, OI 9-Light Chandelier
29"W x 30.5"H
9 x 60w CA Bulbs



2853 EG, OI 12-Light Chandelier
38"W x 37"H
12 x 60w CA Bulbs



91053 EG, OI
1-Light Mini Pendant
8"W
1 x 100w MB Bulb





2855 EG, OI 3-Light Chandelier
 14"W x 14.5"H
 3 x 60w CA Bulbs



2850 EG, OI 3-Light Chandelier
 18.5"W x 18"H
 3 x 60w CA Bulbs



2851 EG, OI 6-Light Chandelier
 26.5"W x 28.5"H
 6 x 60w CA Bulbs



2859 EG, OI 3-Light Semi-Flush
 16.5"W x 10.5"H
 3 x 60w CA Bulbs



2857 EG, OI 2-Light Wall Sconce
12"W x 9.5"H x 6.5"Ext.
2 x 60w CA Bulbs



2849OI Mirror
Oil Rubbed Bronze
20"W x 33.5"H



2858 EG, OI 2-Light Wall Sconce
11"W x 34"H x 8.5"Ext.
2 x 60w CA Bulbs



2863 FIEG, FIOI 1-Light Wall Sconce
 7.5"W x 8.5"H x 9"Ext.
 1 x 100w MB Bulb



2864 FIEG, FIOI 2-Light Bath Vanity
 17.5"W x 8.5"H x 9"Ext.
 2 x 100w MB Bulbs



2865 FIEG, FIOI 3-Light Bath Vanity
 28"W x 8.5"H x 9"Ext.
 3 x 100w MB Bulbs



2866 FIEG, FIOI 4-Light Bath Vanity
 38.5"W x 8.5"H x 9"Ext.
 4 x 100w MB Bulbs



Katherine

Fine, sparkling crystal adorns this collection. From the beaded strings to the delicate hanging crystal, this collection will add sparkle to any room. Finished in rich Oil Rubbed Bronze.

20052OI 4-Light Chandelier
Oil Rubbed Bronze
14"W x 15.5"H
4 x 60w CA Bulbs
Crystal Included



20054OI 4-Light Chandelier
Oil Rubbed Bronze
15"W x 16.5"H
4 x 60w CA Bulbs
Crystal Included



20117WTVI 2-Light Wall Sconce
 Vienna Ivory
 16"W x 13.5"H x 7.5"Ext.
 2 x 60w CA Bulbs
Shades Included
 SHD 49WT

Larchmont

Bright and ethereal, Vienna Ivory finish and White beaded shades makes this series a beatific crowning touch to any room.



SHD49WT Shade
 3.5"Top x 6.5"Base x 4.5"H
Sit On Candle Cover (1 inch)



20116WTVI 1-Light Wall Sconce
 Vienna Ivory
 6.5"W x 13.5"H x 8"Ext.
 1 x 60w CA Bulb
Shade Included
 SHD 49WT



20113WTVI 3-Light Chandelier
 Vienna Ivory
 21W x 23H
 3 x 60w CA Bulbs
Shades Included
 SHD 49WT

800.486.2946

maximlighting.com

Symphony

In either Screen Amber or Soft Vanilla Glass, the sharp angles of the Oil Rubbed Bronze body modernizes and inspires.

11244 SAOI, SVOI 5-Light Chandelier
26W x 27H
5 x 100w MB Bulbs



11239 SAOI, SVOI 15-Light Chandelier
49W x 51H
15 x 60w MB Bulbs

800.486.2946

maximlighting.com

11245 SAOI, SVOI 9-Light Chandelier
 32W x 32H
 9 x 100w MB Bulbs



11235 SAOI, SVOI 3-Light Chandelier
 19"W x 21.5"H
 3 x 100w MB Bulbs




11238 SAOI, SVOI 12-Light Chandelier
 30W x 46H
 12 x 60w MB Bulbs

11241 SAOI, SVOI 3-Light Semi-Flush
 22.5"W x 13"H
 3 x 60w MB Bulbs



11240 SAOI, SVOI 2-Light Flush Mont
 19"W x 7.5"H
 2 x 60w MB Bulbs



91049 SAOI, SVOI
 1-Light Mini Pendant
 7"W
 1 x 100w MB Bulb
One 6" stem and three 12" stems included.
Additional stems available:
 6" order STR06206OI
 12" order STR06212OI



11242 SAOI, SVOI
 3-Light Pendant
 27"W x 29.5"H
 3 x 60w MB Bulbs



11234 SAOI, SVOI
 3-Light Chandelier
 19"W x 21.5"H
 3 x 100w MB Bulbs



11246 SAOI, SVOI 1-Light Wall Sconce
7"W x 11"H x 11"Ext.
1 x 100w MB Bulb



11230 SAOI, SVOI 1-Light Wall Sconce
7"W x 9.5"H x 10"Ext.
1 x 100w MB Bulb



Elegant detail in rich Screen Amber



11247 SAOI, SVOI 2-Light Wall Sconce
16W x 11H x 9"Ext.
2 x 100w MB Bulbs



11231 SAOI, SVOI 2-Light Bath Vanity
18"W x 8.5"H x 10"Ext.
2 x 100w MB Bulbs



11232 SAOI, SVOI 3-Light Bath Vanity
26"W x 8.5"H x 10"Ext.
3 x 100w MB Bulbs



11233 SAOI, SVOI 4-Light Bath Vanity
37"W x 8.5"H x 10"Ext.
4 x 100w MB Bulbs

Cosmopolitan

Befitting its name, this series has worldly design elements that start with the authentic Grand Canyon crackle finish and ends with the earthiness Frosted Ivory glass shades.



11258FIGC 7-Light Chandelier
Grand Canyon
29W x 27H
5 x 100w MB Bulbs + 2 x 60w MB Bulbs



11259FIGC 9-Light Chandelier
Grand Canyon
29W x 27H
9 x 60w MB Bulbs

800.486.2946

maximlighting.com



11257FIGC 5-Light Chandelier
Grand Canyon
26W x 24H
5 x 100w MB Bulbs



11255FIGC 3-Light Chandelier
Grand Canyon
19.5"W x 20"H
3 x 100w MB Bulbs



11256FIGC 5-Light Chandelier
Grand Canyon
27W x 25H
5 x 100w MB Bulbs



11250FIGC 2-Light Flush Mount
Grand Canyon
13W x 7H
2 x 75w MB Bulbs



11268FIGC 2-Light Island Pendant
Grand Canyon
30"L x 13"W x 16.5"H 88"OAH
2 x 100w MB Bulbs



11253FIGC 3-Light Pendant
Grand Canyon
20.5"W x 28"H
3 x 60w MB Bulbs

11269FIGC
3-Light Island Pendant
Grand Canyon
44"L x 16.5"W x 20"H 90"OAH
3 x 100w MB Bulbs





91052FIGC
 1-Light Mini Pendant
 Grand Canyon
 7"W
 1 x 100w MB Bulb
*One 6" stem and three 12"
 stems included.*
*Additional stems available:
 6" order STR06206GC
 12" order STR06212GC*



11262FIGC 2-Light Bath Vanity
 Grand Canyon
 16"W x 9"H x 8.5"Ext.
 2 x 100w MB Bulbs



11263FIGC 2-Light Bath Vanity
 Grand Canyon
 18"W x 8.5"H x 8"Ext.
 2 x 100w MB Bulbs



11264FIGC 3-Light Bath Vanity
 Grand Canyon
 26"W x 8.5"H x 8"Ext.
 3 x 100w MB Bulbs



11265FIGC 4-Light Bath Vanity
 Grand Canyon
 36"W x 8.5"H x 8"Ext.
 4 x 100w MB Bulbs



Grove

The leaves of this grove in Oil Rubbed Bronze are accented with a crown of crystal drops and a bloom of faux wax candles.

88350I 6-Light Chandelier
Oil Rubbed Bronze
26.5"W x 27"H
6 x 60w CA Bulbs
Crystal Included



88360I 9-Light Chandelier
Oil Rubbed Bronze
32"W x 30.5"H
9 x 60w CA Bulbs
Crystal Included

800.486.2946

maximlighting.com



8832OI 3-Light Chandelier
Oil Rubbed Bronze
14"W x 15.5"H
3 x 60w CA Bulbs
Crystal Included



8837OI 1-Light Wall Sconce
Oil Rubbed Bronze
5"W x 13"H x 7"Ext.
1 x 60w CA Bulb
Crystal Included



8839OI 2-Light Wall Sconce
Oil Rubbed Bronze
10"W x 30"H x 8"Ext.
2 x 60w CA Bulbs
Crystal Included



8833OI 3-Light Chandelier
Oil Rubbed Bronze
18"W x 19.5"H
3 x 60w CA Bulbs
Crystal Included



8838OI 2-Light Wall Sconce
Oil Rubbed Bronze
12.5"W x 13"H x 7"Ext.
2 x 60w CA Bulbs
Crystal Included

Via Roma

Italian influence at its best with classic Greek Bronze finish and Soft Vanilla glass.



2778SVGB 12-Light Chandelier
Greek Bronze
30"W x 46"H
12 x 60w MB Bulbs

800.486.2946

maximlighting.com



2777SVGB 3-Light Chandelier
 Greek Bronze
 20"W x 21.5"H
 3 x 100w MB Bulbs



2774SVGB 5-Light Chandelier
 Greek Bronze
 27"W x 24"H
 5 x 100w MB Bulbs



2776SVGB 7-Light Chandelier
 Greek Bronze
 26.5"W x 28"H
 7 x 60w MB Bulbs

2773SVGB 5-Light Chandelier
Greek Bronze
27W x 24H
5 x 100w MB Bulbs



2783SVGB 3-Light Chandelier
Greek Bronze
20"W x 21.5"H
3 x 100w MB Bulbs



2775SVGB 9-Light Chandelier
Greek Bronze
30W x 28H
9 x 100w MB Bulbs



91071SVGB
 1-Light Mini Pendant
 Greek Bronze
 7"W
 1 x 100w MB Bulb
*One 6" stem and three 12"
 stems included*
Additional stems available:
 6" Order-STR06206GB
 12" Order-STR06212GB

120°



2779SVGB
 2-Light Island Pendant
 Greek Bronze
 29.5"L x 13"W x 19.5"H
 2 x 100w MB Bulbs



2782SVGB
 3-Light Island Pendant
 Greek Bronze
 45"L x 13"W x 21"H
 3 x 100w MB Bulbs



2780SVGB 2-Light Flush Mount
Greek Bronze
13W x 6.5H
2 x 75w MB Bulbs



2781SVGB 2-Light Semi-Flush
Greek Bronze
18"W x 12.5"H
2 x 75w MB Bulbs



2772SVGB 2-Light Pendant
Greek Bronze
20W x 27H
2 x 100w MB Bulbs



2786SVGB 1-Light Wall Sconce
 Greek Bronze
 7"W x 14"H x 8.5"Ext.
 1 x 100w MB Bulb



2787SVGB 2-Light Bath Vanity
 Greek Bronze
 21"W x 9.5"H x 8.5"Ext.
 2 x 100w MB Bulbs



2788SVGB 3-Light Bath Vanity
 Greek Bronze
 25"W x 9.5"H x 8.5"Ext.
 3 x 100w MB Bulbs



2789SVGB 4-Light Bath Vanity
 Greek Bronze
 37"W x 9.5"H x 8.5"Ext.
 4 x 100w MB Bulbs



Brighton

The steeply sloped Oil Rubbed Bronze body and lipped Embossed Vanilla Glass on this transitional group are distinctive and bold.



11177EVOI 9-Light Chandelier
Oil Rubbed Bronze
29"W x 30.5"H
9 x 100w MB Bulbs

800.486.2946

maximlighting.com



11173EVOI 3-Light Chandelier
 Oil Rubbed Bronze
 19"W x 18.5"H
 3 x 100w MB Bulbs



11175EVOI 5-Light Chandelier
 Oil Rubbed Bronze
 25.5"W x 25"H
 5 x 100w MB Bulbs



11176EVOI 5-Light Chandelier
 Oil Rubbed Bronze
 24"W x 20.5"H
 5 x 100w MB Bulbs



11170EVOI 2-Light Flush Mount
Oil Rubbed Bronze
13"W x 7"H
2 x 75w MB Bulbs



11171EVOI
3-Light Flush Mount
Oil Rubbed Bronze
16"W x 8"H
3 x 60w MB Bulbs



11174EVOI 3-Light Pendant
Oil Rubbed Bronze
20.5"W x 27.5"H
3 x 100w MB Bulbs



11172EVOI 3-Light Semi-Flush
Oil Rubbed Bronze
16"W x 12"H
3 x 60w MB Bulbs



Delicate designs in Embossed Vanilla



11181EVOI 1-Light Wall Sconce
Oil Rubbed Bronze
7"W x 10"H x 10"Ext.
1 x 100w MB Bulb



11182EVOI 2-Light Bath Vanity
Oil Rubbed Bronze
17"W x 10"H x 8"Ext.
2 x 100w MB Bulbs

Allentown

Sculptured Wilshire glass shades adorn this metal frame painted in our Oil Rubbed Bronze finish make this competitively price family a sure fired winner.



800.486.2946

maximlighting.com

13507WSOI 20-Light Chandelier
Oil Rubbed Bronze
50"W x 48"H
20 x 60w MB Bulbs

13505WSOI 5-Light Chandelier
Oil Rubbed Bronze
27"W x 25"H
5 x 100w MB Bulbs



13506WSOI 9-Light Chandelier
Oil Rubbed Bronze
31.5"W x 31"H
9 x 100w MB Bulbs




13500WSOI 2-Light Flush Mount
Oil Rubbed Bronze
15W x 8.5H
2 x 60w MB Bulbs



13503WSOI
3-Light Pendant
Oil Rubbed Bronze
24.5"W x 28"H
3 x 100w MB Bulbs

13504WSOI 3-Light Chandelier
Oil Rubbed Bronze
23W x 18H
3 x 100w MB Bulbs



13509WSOI 2-Light Island Pendant
Oil Rubbed Bronze
48"L x 18"W x 29"H
2 x 100w MB Bulbs



13501WSOI 3-Light Semi-Flush
Oil Rubbed Bronze
18W x 14H
3 x 100w MB Bulbs



13512WSOI 2-Light Bath Vanity
 Oil Rubbed Bronze
 17"W x 11"H x 10"Ext.
 2 x 100w MB Bulbs



93505WSOI 1-Light Mini Pendant
 Oil Rubbed Bronze
 8"W
 1 x 100w MB Bulb



13514WSOI 4-Light Bath Vanity
 Oil Rubbed Bronze
 36"W x 10"H x 10"Ext.
 4 x 100w MB Bulbs



13513WSOI 3-Light Bath Vanity
 Oil Rubbed Bronze
 26"W x 10"H x 10"Ext.
 3 x 100w MB Bulbs



13511WSOI 1-Light Wall Sconce
 Oil Rubbed Bronze
 7"W x 10"H x 9"Ext.
 1 x 100w MB Bulb



Manor

This decorative classic in Oil Rubbed Bronze finish is both dramatic and subtle, with or without shades.



SHD123WH Shade
3"Top x 7"Base x 6"H
Sit On Candle Cover(1 inch)



122190I 15-Light Chandelier
Oil Rubbed Bronze
45"W x 47.5"H
15 x 40w CA Bulbs
Shades Optional
SHD123WH

800.486.2946

maximlighting.com



12203FIOI 3-Light Chandelier
 Oil Rubbed Bronze
 19"W x 20.5"H
 3 x 100w MB Bulbs



12215OI 5-Light Chandelier
 Oil Rubbed Bronze
 26"W x 28"H
 5 x 60w CA Bulbs
 Shades Optional
 SHD123WH



12216OI 9-Light Chandelier
 Oil Rubbed Bronze
 29"W x 31.5"H
 9 x 60w CA Bulbs
 Shades Optional
 SHD123WH



12218OI 2-Light Wall Sconce
 Oil Rubbed Bronze
 13"W x 14.5"H x 9.5"Ext.
 2 x 60w CA Bulbs
 Shades Optional
 SHD123WH



12217OI 1-Light Wall Sconce
 Oil Rubbed Bronze
 7"W x 14.5"H x 9.5"Ext.
 1 x 60w CA Bulb
 Shade Optional
 SHD123WH



12205FIOI 5-Light Chandelier
 Oil Rubbed Bronze
 25.5"W x 28"H
 5 x 100w MB Bulbs



12204FIOI 3-Light Chandelier
 Oil Rubbed Bronze
 21"W x 24"H
 3 x 100w MB Bulbs




12202FIOI 3-Light Pendant
 Oil Rubbed Bronze
 23"W x 26.5"H
 3 x 100w MB Bulbs

12209FIOI 15-Light Chandelier
Oil Rubbed Bronze
45"W x 47.5"H
15 x 60w MB Bulbs



12207FIOI 9-Light Chandelier
Oil Rubbed Bronze
33"W x 32"H
9 x 100w MB Bulbs



12206FIOI 5-Light Chandelier
Oil Rubbed Bronze
25.5"W x 24"H
5 x 100w MB Bulbs



12201FIOI 2-Light Semi-Flush
Oil Rubbed Bronze
19.5"W x 15"H
2 x 100w MB Bulbs



12208FIOI 3-Light Island Pendant
Oil Rubbed Bronze
45"L x 13"W x 26"H
3 x 100w MB Bulbs

12211FIOI 1-Light Wall Sconce
 Oil Rubbed Bronze
 7"W x 13.5"H x 8.5"Ext.
 1 x 100w MB Bulb



12212FIOI 2-Light Wall Sconce
 Oil Rubbed Bronze
 15.5"W x 13.5"H x 8.5"Ext.
 2 x 100w MB Bulbs



92200FIOI
 1-Light Mini Pendant
 Oil Rubbed Bronze
 7"W
 1 x 100w MB Bulb
*Additional stems available:
 6" Order STR06206OI
 12" order STR06212OI
 One 6" stem and three
 12" stems included*



12213FIOI 3-Light Bath Vanity
 Oil Rubbed Bronze
 29"W x 10.5"H x 9.5"Ext.
 3 x 100w MB Bulbs



12214FIOI 4-Light Bath Vanity
 Oil Rubbed Bronze
 37"W x 10.5"H x 9.5"Ext.
 4 x 100w MB Bulbs



Loft

Simple yet stylish,
this collection is perfect for any decor.
Offered in Oil Rubbed Bronze or Satin Nickel finishes.



70006 OI,SN 9-Light Chandelier
29.5"W x 29"H
9 x 60w CA Bulbs

800.486.2946

maximlighting.com



70002 OI,SN 2-Light Wall Sconce
 10"W x 8"H x 6"Ext.
 2 x 60w CA Bulbs



70003 OI,SN 3-Light Chandelier
 14"W x 16"H
 3 x 60w CA Bulbs



70005 OI,SN 5-Light Chandelier
 25"W x 23"H
 5 x 60w CA Bulbs



70001 OI,SN
 1-Light Wall Sconce
 5"W x 8"H x 7"Ext.
 1 x 60w CA Bulb

Towne

This unique collection offers candelabra styling with the decorative flexibility of a chandelier. Finished in Oil Rubbed Bronze



110350I 9-Light Chandelier
Oil Rubbed Bronze
28"W x 31"H
9 x 60w CA Bulbs

800.486.2946

maximlighting.com



11032OI 2-Light Wall Sconce
 Oil Rubbed Bronze
 10"W x 9"H x 7"Ext.
 2 x 60w CA Bulbs



11033OI 3-Light Chandelier
 Oil Rubbed Bronze
 14"W x 17.5"H
 3 x 60w CA Bulbs



11034OI 6-Light Chandelier
 Oil Rubbed Bronze
 24.5"W x 25.5"H
 6 x 60w CA Bulbs



11031OI 1-Light Wall Sconce
 Oil Rubbed Bronze
 4.5"W x 9"H x 8"Ext.
 1 x 60w CA Bulb

Boca

A touch of class and simplicity describes this collection. Finished in Light Gold and offered with warm Latte glass.



11675LTLG 9-Light Chandelier
Light Gold
28.5"W x 28.5"H
9 x 100w MB Bulbs

800.486.2946

maximlighting.com

11674LTLG 5-Light Chandelier
Light Gold
28"W x 22"H
5 x 100w MB Bulbs




11673LTLG 3-Light Chandelier
Light Gold
20"W x 18"H
3 x 100w MB Bulbs




11671LTLG 3-Light Semi-Flush
Light Gold
16"W x 14"H
3 x 60w MB Bulbs
KJT

11672LTLG 3-Light Pendant
Light Gold
20"W x 25.5"H
3 x 100w MB Bulbs



11670LTLG 3-Light Island Pendant
Light Gold
36"L x 9.5"W x 24.5"H
3 x 100w MB Bulbs

11679LTLG 5-Light Chandelier
 Light Gold
 28"W x 22"H
 5 x 100w MB Bulbs



91091LTLG 1-Light Mini Pendant
 Light Gold
 7"W
 1 x 100w MB Bulb
One 6" stem and three 12" stems included.
Additional stems available:
 6" order STR06206LG
 12" order STR06212LG



11677LTLG 1-Light Wall Sconce
 Light Gold
 7"W x 10.5"H x 8.5"Ext.
 1 x 100w MB Bulb



Soho

A beautifully styled collection offered in Satin Nickel or our popular Oil Rubbed Bronze finish.

11053 SVOI,SVSN 5-Light Chandelier
25"W x 25.5"H
5 x 100w MB Bulbs



11054 SVOI,SVSN 9-Light Chandelier
30W x 31H
9 x 100w MB Bulbs

800.486.2946

maximlighting.com



11051 SVOI,SVSN 3-Light Chandelier
 19.5"W x 14"H
 3 x 100w MB Bulbs



11050 SVOI,SVSN
 2-Light Flush Mount
 14"W x 7.5"H
 2 x 60w MB Bulbs



11052 SVOI,SVSN
 2-Light Semi-Flush
 15.75"W x 21"H
 2 x 100w MB Bulbs



11049 SVOI,SVSN
 3-Light Chandelier
 19.5"W x 14"H
 3 x 100w MB Bulbs

11056 SVOI,SVSN 1-Light Wall Sconce
 6"W x 9"H x 9"Ext.
 1 x 100w MB Bulb



91059 SVOI,SVSN
 1-Light Mini Pendant
 6"W
 1 x 100w MB Bulb
*One 6" stem and three 12"
 Stem Included.*
*Additional stems available:
 6" order STR06206 SN, OI
 12" order STR06212 SN, OI*



11057 SVOI,SVSN 2-Light Bath Vanity
 15.5"W x 9"H x 10"Ext.
 2 x 100w MB Bulbs



11058 SVOI,SVSN 3-Light Bath Vanity
 23.5"W x 9"H x 10"Ext.
 3 x 100w MB Bulbs



11059 SVOI,SVSN 4-Light Bath Vanity
 31"W x 9"H x 10"Ext.
 4 x 100w MB Bulbs






MAXIM LIGHTING®

When traditional seems too antiquated and contemporary too stark, transitional style lighting finds an aesthetic middle ground that synthesizes the best of both worlds. Bold but classic materials like steel and iron curve into simple shapes and lines without falling into the trendy trap of extremism. The result: warmth and elegance without opulence, simplicity without starkness. The transitional style suits those who prefer the sophisticated and classy with a twist of nonconformity. Diverse and creative, Maxim's collection of transitional lighting fixtures defies labels and stereotypes, opening up a whole new world of style options.

Celeste

As much a sculpture as a lighting collection, Celeste's stunning laser-cut flat metal forms cleverly conceal the internal wire so all the eye sees is the graceful curves of the frame. The carved detail of the bobeches and caps adds an interesting contrast of style. Rustic Textured Terra finish and warm Ember glass round out the eclectic approach making this collection a perfect match for any design scheme.

14276EMTT 9-Light Chandelier
Textured Terra
35"W x 32"H
9 x 60w MB Bulbs



800.486.2946

maximlighting.com



14275EMTT 5-Light Chandelier
Textured Terra
32.5"W x 27.75"H
5 x 100w MB Bulbs



14271EMTT 3-Light Semi-Flush
Textured Terra
19.5"W x 16.75"H
3 x 100w MB Bulbs



14272EMTT 3-Light Pendant
Textured Terra
25"W x 32"H
3 x 100w MB Bulbs



14273EMTT 4-Light Pendant
Textured Terra
30.5"W x 32"H
4 x 100w MB Bulbs



14281EMTT 1-Light Wall Sconce
Textured Terra
7"W x 17.5"H x 12"Ext.
1 x 100w MB Bulb



14282EMTT 2-Light Bath Vanity
Textured Terra
20"W x 9"H x 10"Ext.
2 x 100w MB Bulbs



14233EMTT 3-Light Bath Vanity
Textured Terra
28"W x 9"H x 10"Ext.
3 x 100w MB Bulbs



14284EMTT 4-Light Bath Vanity
Textured Terra
37.5"W x 9"H x 10"Ext.
4 x 100w MB Bulbs

Luminous

Simple straight line frames fashioned in minimalist style finished in our Rustic Ebony are electrified by the warmth and beauty of the Stone Candle shades. These shades are carved out of solid stone and each has a personality of its own.

21147SCRE* 12-Light Chandelier
Rustic Ebony
32"W x 32.5"H (body only)
12 x 60w MB Bulbs
Shown with 12" stem
Total drop as shown 49.5"



**Additional stems available: STR06206RE 6" stem or STR06212RE 12" stem. Fixture includes one 6" stem and three 12" stems.*



21144SCRE
 Shown without stems
 Total drop as shown 20"



21144SCRE* 4-Light Chandelier
 Rustic Ebony
 24"W x 20"H(body only)
 4 x 100w MB Bulbs
 Shown with 12" stem
 Total drop as shown 37"
 Can be installed
 without stems




21145SCRE* 8-Light Chandelier
 Rustic Ebony
 28.5"W x 24.5"H(body only)
 8 x 100w MB Bulbs
 Shown with 12" stem
 Total drop as shown 41.5"





21140SCRE 2-Light Flush Mount
Rustic Ebony
14"W x 6.5"H
2 x 75w MB Bulbs



21149SCRE 10-Light Chandelier
Rustic Ebony
37"L x 16.5"W x 16.5"H
10 x 60w MB Bulbs



21148SCRE 6-Light Chandelier
Rustic Ebony
45"L x 5"W x 17"H
6 x 60w MB Bulbs



21141SCRE 1-Light Wall Sconce
Rustic Ebony
5"W x 7"H x 6.5"Ext.
1 x 100w MB Bulb



21142SCRE 2-Light Bath Vanity
Rustic Ebony
11"W x 7.5"H x 6"Ext.
2 x 100w MB Bulbs

Duo

Sweeping lines of square metal tubing mirrored by flat ribbons of steel finished in Auburn Dusk that support a duo of glass shades featuring Textured Clear on the outside and a Dusky White interior glass. This contemporary delight is powered by G9 Xenon lamps which are included.

11526TCAD 9-Light Chandelier
Auburn Dusk
41.5"W x 39.5"H
9 x 60w, G9 Xenon Incl.



800.486.2946

maximlighting.com

11524TCAD 3-Light Chandelier
 Auburn Dusk
 27"W x 25"H
 3 x 60w, G9 Xenon Incl.



11525TCAD 5-Light Chandelier
 Auburn Dusk
 32.5"W x 32"H
 5 x 60w, G9 Xenon Incl.



11523TCAD 3-Light Chandelier
Auburn Dusk
19.5"W x 21"H
3 x 60w, G9 Xenon Incl.



11522TCAD 4-Light Pendant
Auburn Dusk
30"W x 32.5"H
4 x 60w, G9 Xenon Incl.





11521TCAD 2-Light Semi-Flush
 Auburn Dusk
 17"W x 10"H
 2 x 60w, G9 Xenon Incl.



11528TCAD
 1-Light Wall Sconce
 Auburn Dusk
 7"W x 11.5"H x 9.5"Ext.
 1 x 60w, G9 Xenon Incl.



11529TCAD 2-Light Wall Sconce
 Auburn Dusk
 16.5"W x 11.5"H x 8.5"Ext.
 2 x 60w, G9 Xenon Incl.


Ophelia

Heavy forged iron designed with intricate detail is finished in our Colonial UMBER finish. The soft curve of the Burnished Lichen glass compliments flowing motion of the frame. This complete family features styles for every room.

32303BLCU 3-Light Chandelier
Colonial UMBER
27"W x 25"H
3 x 100w MB Bulbs



32307BLCU 15-Light Chandelier
Colonial UMBER
45"W x 46"H
15 x 60w MB Bulbs



800.486.2946

maximlighting.com

32305BLCU 6-Light Chandelier
 Colonial Umber
 32"W x 35"H
 6 x 100w MB Bulbs



MED002CU
 Colonial Umber
 26.5"W x 1.5"H
 With 4" opening

32306BLCU 9-Light Chandelier
 Colonial Umber
 35"W x 40"H
 9 x 100w MB Bulbs





32302BLCU
4-Light Pendant
Colonial Umber
28"W x 34"H
4 x 60w MB Bulbs



32300BLCU
2-Light Flush Mount
Colonial Umber
14"W x 6.5"H
2 x 75w MB Bulbs



32301BLCU
3-Light Semi-Flush
Colonial Umber
22.5"W x 13.5"H
3 x 60w MB Bulbs



32309BLCU
2-Light Island Pendant
Colonial Umber
45"L x 16"W x 21.5"H
2 x 100w MB Bulbs



92300BLCU
 1-Light Mini Pendant
 Colonial Umber
 8"W
 1 x 100w MB Bulb
*Additional stems available:
 6" order STR06206CU
 12" order STR06212CU
 One 6" stem and three 12"
 stems included.*

120°

32311BLCU
 1-Light Wall Sconce
 Colonial Umber
 6"W x 19"H x 7.5"Ext.
 1 x 100w MB Bulb



32312BLCU
 2-Light Bath Vanity
 Colonial Umber
 14.5"W x 11"H x 8.5"Ext.
 2 x 100w MB Bulbs



32313BLCU
 3-Light Bath Vanity
 Colonial Umber
 23"W x 11"H x 8.5"Ext.
 3 x 100w MB Bulbs



32314BLCU
 4-Light Bath Vanity
 Colonial Umber
 31"W x 11"H x 8.5"Ext.
 4 x 100w MB Bulbs



Infinity

Classic transitional design using oval shaped tubing finished in our popular Oil Rubbed Bronze with stately Wilshire glass shades.

21307WSOI 15-Light Chandelier

Oil Rubbed Bronze

49"W x 50.5"H

15 x 60w MB Bulbs



800.486.2946

maximlighting.com



21304WSOI 3-Light Chandelier
Oil Rubbed Bronze
15.5"W x 25"H
3 x 100w MB Bulbs



21306WSOI 9-Light Chandelier
Oil Rubbed Bronze
32.5"W x 40.5"H
9 x 100w MB Bulbs



21302WSOI 3-Light Semi-Flush
Oil Rubbed Bronze
18"W x 14.5"H
3 x 60w MB Bulbs

21303WSOI 3-Light Pendant
Oil Rubbed Bronze
26.5"W x 36.5"H
3 x 100w MB Bulbs



21305WSOI 5-Light Chandelier
Oil Rubbed Bronze
25"W x 32.5"H
5 x 100w MB Bulbs





21311WSOI
 1-Light Wall Sconce
 Oil Rubbed Bronze
 6.5"W x 16"H x 9"Ext.
 1 x 100w MB Bulb



21312WSOI
 2-Light Bath Vanity
 Oil Rubbed Bronze
 15.5"W x 9.5"H x 8.5"Ext.
 2 x 100w MB Bulbs



21313WSOI
 3-Light Bath Vanity
 Oil Rubbed Bronze
 24.5"W x 9.5"H x 8.5"Ext.
 3 x 100w MB Bulbs



21314WSOI
 4-Light Bath Vanity
 Oil Rubbed Bronze
 33"W x 9.5"H x 8.5"Ext.
 4 x 100w MB Bulbs



91305WSOI 1-Light Mini Pendant
 Oil Rubbed Bronze
 5.5"W
 1 x 100w MB Bulb

*Additional stems available:
 6" order STR06206OI
 12" order STR06212OI
 One 6" stem and three 12"
 stems included.*



Chelsea

Clean simple lines allows this family to transition from classic traditional to soft contemporary. The Wilshire glass compliments the warmth of the Weathered Russet finish.




20887WSWR 15-Light Chandelier
Weathered Russet
44"W x 41"H
15 x 60w MB Bulbs

800.486.2946

maximlighting.com

20885WSWR 6-Light Chandelier
Weathered Russet
28.25"W x 22.5"H
6 x 100w MB Bulbs



20886WSWR 9-Light Chandelier
Weathered Russet
32"W x 32.5"H
9 x 100w MB Bulbs






20880WSWR 2-Light Flush Mount
Weathered Russet
16"W x 8"H
2 x 75w MB Bulbs



20881WSWR 2-Light Semi-Flush
Weathered Russet
16"W x 14"H
2 x 100w MB Bulbs



20883WSWR 4-Light Pendant
Weathered Russet
21.5"W x 29"H
4 x 100w MB Bulbs

20888WSWR 1-Light Wall Sconce
Weathered Russet
6"W x 11"H x 8"Ext.
1 x 100w MB Bulb



20990WSWR 2-Light Bath Vanity
Weathered Russet
15"W x 11"H x 7"Ext.
2 x 100w MB Bulbs



20991WSWR 3-Light Bath Vanity
Weathered Russet
22.5"W x 11"H x 7.75"Ext.
3 x 100w MB Bulbs



20992WSWR 4-Light Bath Vanity
Weathered Russet
30"W x 11"H x 7"Ext.
4 x 100w MB Bulbs



91880WSWR
1-Light Mini Pendant
Weathered Russet
6.5"W
1 x 100w MB Bulb
*Additional stems available:
6" order STR06206WR
12" order STR06212WR
One 6" stem and three 12"
stems included.*



Moda


Soft flowing lines accentuate the classic six-sided Karmel glass. This modern package is made complete by the beautiful Florentine finish.

12317KLFN 15-Light Chandelier

Florentine

42.5"W x 49"H

15 x 60w MB Bulbs



800.486.2946

maximlighting.com

12304KLFN 3-Light Chandelier
 Florentine
 20"W x 22"H
 3 x 100w MB Bulbs



12305KLFN 5-Light Chandelier
 Florentine
 24.5"W x 25.5"H
 5 x 100w MB Bulbs



12306KLFN 9-Light Chandelier
 Florentine
 32"W x 34.5"H
 9 x 100w MB Bulbs



12302KLFN 3-Light Chandelier
Florentine
20"W x 17.5"H
3 x 100w MB Bulbs



12301KLFN 2-Light Semi-Flush
Florentine
16"W x 15.5"H
2 x 100w MB Bulbs



12307KLFN 3-Light Pendant
Florentine
20"W x 23"H
3 x 100w MB Bulbs



12300KLFN
2-Light Flush Mount
Florentine
18"W x 8.5"H
2 x 75w MB Bulbs



12312KLFN 2-Light Wall Sconce
 Florentine
 14.5"W x 13.5"H x 8"Ext.
 2 x 100w MB Bulbs



12311KLFN 1-Light Wall Sconce
 Florentine
 6"W x 11"H x 9"Ext.
 1 x 100w MB Bulb



12314KLFN 3-Light Bath Vanity
 Florentine
 22"W x 9"H x 8"Ext.
 3 x 100w MB Bulbs



12313KLFN 2-Light Bath Vanity
 Florentine
 15"W x 9"H x 7"Ext.
 2 x 100w MB Bulbs



12315KLFN 4-Light Bath Vanity
 Florentine
 30"W x 9"H x 8"Ext.
 4 x 100w MB Bulbs



91230KLFN 1-Light Mini Pendant
 Florentine
 6.25"W
 1 x 100w MB Bulb



Deco

Inspired by the Art Deco era, this classic series features Wilshire glass shades and hand painted with our classic Florentine finish.



12706WSFN 9-Light Chandelier
Florentine
30"W x 27.5"H
9 x 100w MB Bulbs

800.486.2946

maximlighting.com

12704WSFN 3-Light Chandelier
Florentine
19"W x 19"H
3 x 100w MB Bulbs



12705WSFN 5-Light Chandelier
Florentine
26"W x 23"H
5 x 100w MB Bulbs



12700WSFN 2-Light Flush Mount
Florentine
14"W x 7.5"H
2 x 75w MB Bulbs



12702WSFN 3-Light Pendant
Florentine
17.5"W x 28"H
3 x 100w MB Bulbs



12711WSFN 2-Light Island Pendant
Florentine
40"L x 13"W x 25.5"H (body only)
2 x 100w MB Bulbs
Shown with 6" stem
Total height with stem and canopy - 35.5"
Additional stems available:
6" stem order-STR10006FN
12" stem order-STR10012FN



92703WSFN
1-Light Mini Pendant
Florentine
5.5"W
1 x 100w MB Bulb
Additional stems available:
6" order STR06206FN
12" order STR06212FN
One 6" stem and three 12"
stems included.



12703WSFN 1-Light Wall Sconce
 Florentine
 5.5"W x 8"H x 7"Ext.
 1 x 100w MB Bulb



12708WSFN 2-Light Bath Vanity
 Florentine
 15"W x 8.5"H x 6.5"Ext.
 2 x 100w MB Bulbs



12709WSFN 3-Light Bath Vanity
 Florentine
 25"W x 8.5"H x 6.5"Ext.
 3 x 100w MB Bulbs



12710WSFN 4-Light Bath Vanity
 Florentine
 35.5"W x 8.5"H x 6.5"Ext.
 4 x 100w MB Bulbs



Mission Bay

Soft curves meet straight lines in this arts and crafts inspired design. The frame is finished in Heirloom Brass and enhanced by the flowing lines of the Frost Lichen glass.



12426FLHB 9-Light Chandelier
Heirloom Brass
35"W x 32.5"H
9 x 60w MB Bulbs

800.486.2946

maximlighting.com

12425FLHB 5-Light Chandelier
Heirloom Brass
27.5"W x 27"H
5 x 100w MB Bulbs



12429FLHB 2-Light Island Pendant
Heirloom Brass
38.5"L x 13.5"W x 13"H
2 x 100w MB Bulbs






12420FLHB 2-Light Semi-Flush
 Heirloom Brass
 13"W x 10"H
 2 x 100w MB Bulbs



12422FLHB 2-Light Pendant
 Heirloom Brass
 22"W x 31.5"H
 2 x 100w MB Bulbs



92420FLHB 1-Light Mini Pendant
 Heirloom Brass
 8"W
 1 x 100w MB Bulb
*Additional stems available:
 6" order STR06206HB
 12" order STR06212HB
 One 6" stem and three 12"
 stems included.*



12423FLHB 3-Light Chandelier
 Heirloom Brass
 25"W x 22.5"H
 3 x 100w MB Bulbs



12431FLHB 1-Light Wall Sconce
Heirloom Brass
5.5"W x 9"H x 7.5"Ext.
1 x 100w MB Bulb



12432FLHB 2-Light Bath Vanity
Heirloom Brass
15.5"W x 8.5"H x 7.5"Ext.
2 x 100w MB Bulbs



12433FLHB 3-Light Bath Vanity
Heirloom Brass
24.5"W x 8.5"H x 7.5"Ext.
3 x 100w MB Bulbs



12434FLHB 4-Light Bath Vanity
Heirloom Brass
34"W x 8.5"H x 7.5"Ext.
4 x 100w MB Bulbs



Oak Harbor

Tapered metal ribbons forged into a flowing form and finished in a heavy textured Rustic Burnished finish. The beveled soft square Frost Lichen shades enhance this bold and masculine look.




21067FLRB 15-Light Chandelier
Rustic Burnished
44"W x 42"H
15 x 60w MB Bulbs

800.486.2946

maximlighting.com

21065FLRB 5-Light Chandelier
Rustic Burnished
28"W x 26"H
5 x 100w MB Bulbs



21066FLRB 9-Light Chandelier
Rustic Burnished
31.5"W x 32.5"H
9 x 100w MB Bulbs





21076FLRB 2-Light Semi-Flush
Rustic Burnished
18"W x 13"H
2 x 100w MB Bulbs



21077FLRB 4-Light Pendant
Rustic Burnished
20"W x 28"H
4 x 100w MB Bulbs



21079FLRB 3-Light Island Pendant
Rustic Burnished
45"L x 14"W x 43"H (body only)
3 x 100w MB Bulbs
Shown with 12" stem
Total height with stem and canopy - 58.5"
Additional stems available:
6" stem order-STR10006RB
12" stem order-STR10012RB

120°



21075FLRB 2-Light Flush Mount
Rustic Burnished
16.5"W x 7.5"H
2 x 75w MB Bulbs



21063FLRB
 1-Light Wall Sconce
 Rustic Burnished
 6"W x 11"H x 7.5"Ext.
 1 x 100w MB Bulb



92060FLRB
 1-Light Mini Pendant
 Rustic Burnished
 6"W
 1 x 100w MB Bulb
*Additional stems available:
 6" order STR06206RB
 12" order STR06212RB
 One 6" stem and three 12"
 stems included.*



21072FLRB 2-Light Bath Vanity
 Rustic Burnished
 15"W x 9.5"H x 7.5"Ext.
 2 x 100w MB Bulbs



21073FLRB 3-Light Bath Vanity
 Rustic Burnished
 23.5"W x 9.5"H x 7.5"Ext.
 3 x 100w MB Bulbs



21074FLRB 4-Light Bath Vanity
 Rustic Burnished
 31.5"W x 9.5"H x 7.5"Ext.
 4 x 100w MB Bulbs



Portello

Gracefully formed metal frames finished in Mahogany cradle our Wilshire glass creating a unique collection for the discriminate homeowner.



11745WSMA 9-Light Chandelier

Mahogany
32"W x 31"H
9 x 100w MB Bulbs

800.486.2946

maximlighting.com

11743WSMA 3-Light Pendant
 Mahogany
 24"W x 25"H
 3 x 100w MB Bulbs



11744WSMA 5-Light Chandelier
 Mahogany
 20"W x 26.5"H
 5 x 100w MB Bulbs





11739WSMA 3-Light Flush Mount
Mahogany
17.5"W x 8.5"H
3 x 60w MB Bulbs



11740WSMA 2-Light Flush Mount
Mahogany
13.5"W x 9"H
2 x 75w MB Bulbs



11741WSMA 2-Light Semi-Flush
Mahogany
16"W x 17"H
2 x 100w MB Bulbs



91006WSMA 1-Light Mini Pendant
Mahogany
7"W
1 x 100w MB Bulb





11747WSMA 1-Light Wall Sconce
 Mahogany
 7"W x 17"H x 8"Ext.
 1 x 100w MB Bulb



11742WSMA 2-Light Bath Vanity
 Mahogany
 14.5"W x 11"H x 7"Ext.
 2 x 100w MB Bulbs



11746WSMA 3-Light Bath Vanity
 Mahogany
 23.5"W x 11"H x 7"Ext.
 3 x 100w MB Bulbs



11748WSMA 4-Light Bath Vanity
 Mahogany
 31.5"W x 11"H x 7"Ext.
 4 x 100w MB Bulbs

Bolero

A myriad of elongated Oil Rubbed Bronze arms and Wisshire Glass rises elegantly towards the heavens, both sleek and stylish.

11297WSOI 20-Light Chandelier

Oil Rubbed Bronze
45"W x 55"H
20 x 60w MB Bulbs



800.486.2946

maximlighting.com



11292WSOI 3-Light Chandelier
Oil Rubbed Bronze
14"W x 23"H
3 x 100w MB Bulbs



11296WSOI 12-Light Chandelier
Oil Rubbed Bronze
31.5"W x 39"H
12 x 60w MB Bulbs

11293WSOI 5-Light Chandelier
Oil Rubbed Bronze
21"W x 31"H
5 x 100w MB Bulbs



11294WSOI 7-Light Chandelier
Oil Rubbed Bronze
24"W x 33"H
7 x 100w MB Bulbs



11290WSOI 2-Light Flush Mount
 Oil Rubbed Bronze
 13.5"W x 6.5"H
 2 x 75w MB Bulbs



11291WSOI 3-Light Semi-Flush
 Oil Rubbed Bronze
 17"W x 13"H
 3 x 100w MB Bulbs



11295WSOI 3-Light Pendant
 Oil Rubbed Bronze
 17"W x 23"H
 3 x 100w MB Bulbs

Diamante

Whether transitional to contemporary is your theme this collection is sure to please. Geometric accents contrast the soft flowing curves of the frame and Wilshire glass. The frame is painted in a rich Oiled Rubbed Bronze.



30606WSOI 9-Light Chandelier
Oil Rubbed Bronze
32.5"W x 35.5"H
9 x 100w MB Bulbs

800.486.2946

maximlighting.com



30605WSOI 5-Light Chandelier
Oil Rubbed Bronze
27"W x 25.5"H
5 x 100w MB Bulbs



30609WSOI
2-Light Island Pendant
Oil Rubbed Bronze
42"L x 15.5"W x 20"H
2 x 100w MB Bulbs



30601WSOI 3-Light Semi-Flush
Oil Rubbed Bronze
16"W x 17"H
3 x 60w MB Bulbs



30604WSOI 3-Light Chandelier
Oil Rubbed Bronze
25"W x 19"H
3 x 100w MB Bulbs



30600WSOI 3-Light Flush Mount
Oil Rubbed Bronze
17.5"W x 11.5"H
3 x 60w MB Bulbs



30603WSOI 3-Light Pendant
Oil Rubbed Bronze
27"W x 35"H
3 x 100w MB Bulbs



30614WSOI 4-Light Bath Vanity
Oil Rubbed Bronze
31"W x 9"H x 8"Ext.
4 x 100w MB Bulbs



30613WSOI 3-Light Bath Vanity
Oil Rubbed Bronze
22.5"W x 9"H x 8"Ext.
3 x 100w MB Bulbs



30612WSOI
2-Light Bath Vanity
Oil Rubbed Bronze
14"W x 9"H x 8"Ext.
2 x 100w MB Bulbs

30611WSOI
1-Light Wall Sconce
Oil Rubbed Bronze
6"W x 10"H x 8"Ext.
1 x 100w MB Bulb



90600WSOI
1-Light Mini Pendant
Oil Rubbed Bronze
7.5"W
1 x 100w MB Bulb
*Additional stems available:
6" order STR06206OI
12" order STR06212OI
One 6" stem and three 12"
stems included.*



Canyon Rim

Bold and beautiful, this collection features flowing double wrapped arms finished in Canyon Rock with Soft Vanilla glass.

2759SVCR 18-Light Chandelier
Canyon Rock
42"W x 44"H
18 x 60w MB Bulbs



800.486.2946

maximlighting.com

2756SVCR 8-Light Chandelier
Canyon Rock
29"W x 30"H
5 x 100w + 3 x 60w MB Bulbs



2758SVCR 9-Light Chandelier
Canyon Rock
32.5"W x 32"H
9 x 60w MB Bulbs



2755SVCR 5-Light Chandelier
Canyon Rock
27"W x 25"H
5 x 100w MB Bulbs



2757SVCR 5-Light Chandelier
Canyon Rock
27"W x 23"H
5 x 100w MB Bulbs



27512SVCR 3-Light Chandelier
Canyon Rock
20"W x 18"H
3 x 100w MB Bulbs



2750SVCR
2-Light Flush Mount
Canyon Rock
13"W x 8"H
2 x 60w MB Bulbs



27510SVCR
3-Light Flush Mount
Canyon Rock
15.5"W x 8.5"H
3 x 60w MB Bulbs



2754SVCR 3-Light Pendant
Canyon Rock
20"W x 25.5"H
3 x 100w MB Bulbs



2752SVCR 3-Light Semi-Flush
Canyon Rock
17"W x 13.5"H
3 x 100w MB Bulbs



2751SVCR
 2-Light Island Pendant
 Canyon Rock
 32"L x 13"W x 19"H(Body Only)
 86"OAH
 2 x 100w MB Bulbs



27511SVCR 1-Light Pendant
 Canyon Rock
 16"W x 15"H
 1 x 100w MB Bulb



91057SVCR
 1-Light Mini Pendant
 Canyon Rock
 7"W
 1 x 100w MB Bulb
*One 6" stem and three 12" stems included.
 Additional stems available:
 6" order-STR06206CR
 12" order-STR06212CR*



2753SVCR 3-Light Island Pendant
 Canyon Rock
 40"L x 13"W x 25"H(Body Only)
 91"OAH
 3 x 100w MB Bulbs



8027SVCR 2-Light Bath Vanity
 Canyon Rock
 15.5"W x 8.5"H x 8"Ext.
 2 x 100w MB Bulbs



8031SVCR 2-Light Bath Vanity
 Canyon Rock
 16"W x 10"H x 8"Ext.
 2 x 100w MB Bulbs



8030SVCR
 1-Light Wall Sconce
 Canyon Rock
 6.5"W x 9"H x 8"Ext.
 1 x 100w MB Bulb



8028SVCR
 3-Light Bath Vanity
 Canyon Rock
 24.5"W x 8.5"H x 8"Ext.
 3 x 100w MB Bulbs



8029SVCR
 4-Light Bath Vanity
 Canyon Rock
 32"W x 8.5"H x 8"Ext.
 4 x 100w MB Bulbs



Classique

Greek Bronze finish with Amber Vanilla glass combine for a truly classic look.

2769AVGB 15-Light Chandelier

Greek Bronze
49"W x 49.5"H
15 x 60w MB Bulbs



800.486.2946

maximlighting.com



2765AVGB 5-Light Chandelier
 Greek Bronze
 26"W x 27"H
 5 x 100w MB Bulbs



2764AVGB 3-Light Chandelier
 Greek Bronze
 19"W x 22.5"H
 3 x 100w MB Bulbs



2766AVGB 9-Light Chandelier
 Greek Bronze
 33"W x 36"H
 9 x 100w MB Bulbs




2761AVGB 3-Light Semi-Flush
Greek Bronze
18"W x 16.5"H
3 x 60w MB Bulbs



2763AVGB 3-Light Pendant
Greek Bronze
18.5"W x 24"H
3 x 60w MB Bulbs



2762AVGB 5-Light Chandelier
Greek Bronze
26"W x 27"H
5 x 100w MB Bulbs



91065AVGB
 1-Light Mini Pendant
 Greek Bronze
 7" W
 1 x 100w MB Bulb
*One 6" stem and three 12"
 stems included*
Additional stems available;
 6" Order-STR06206GB
 12" Order -STR06212GB



2760AVGB 3-Light Flush Mount
 Greek Bronze
 16"W x 10"H
 3 x 60w MB Bulbs



2767AVGB 1-Light Wall Sconce
 Greek Bronze
 7"W x 12.5"H x 8.5"Ext.
 1 x 100w MB Bulb



2768AVGB 2-Light Bath Vanity
 Greek Bronze
 15.5"W x 11"H x 8"Ext.
 2 x 100w MB Bulbs



Pacific

Simple, elegant designs offered in our Kentucky Bronze, Pewter, or Acorn finishes with marbled glass or Kentucky Bronze with Wilshire glass.



2659 MRAC, MRKB, MRPE, WSKB
12-Light Chandelier
30"W x 43"H
12 x 60w MB Bulbs

800.486.2946

maximlighting.com



2655 MRAC, MRKB, MRPE, WSKB
5-Light Chandelier
29"W x 21"H
5 x 100w MB Bulbs



2658 MRAC, MRKB, MRPE, WSKB
9-Light Chandelier
30.5"W x 26.5"H
9 x 60w MB Bulbs

2656 MRAC, MRKB, MRPE, WSKB
7-Light Chandelier
27"W x 28"H
5 x 100w + 2 x 60w MB Bulbs



2657 MRAC, MRKB, MRPE, WSKB
5-Light Chandelier
26"W x 21.5"H
5 x 100w MB Bulbs





C, MRKB, MRPE, WSKB
 ndant
 28.5"H
 3 Bulbs



2651 MRAC, MRKB, MRPE, WSKB
 2-Light Island Pendant
 30"L x 13"W x 16"H88"OAH
 2 x 100w MB Bulbs



2653 MRAC, MRKB, MRPE, WSKB
 3-Light Island Pendant
 44"L x 13"W x 20.5"H89"OAH
 3 x 100w MB Bulbs



DIF001WT



8025 MRAC, MRSN, MRKB, WSKB
1-Light Wall Sconce
16"W x 4.5"H x 8"Ext.
1 x 100w MB Bulb



DIF001WT



DIF002WT



8026 MRSN
1-Light Wall Sconce
Satin Nickel
13"W x 4.5"H x 8"Ext.
1 x 100w MB Bulb



DIF002WT



2652 MRAC, MRKB, MRPE, WSKB
3-Light Semi-Flush
18.5"W x 15"H
3 x 75w MB Bulbs



2650 MRAC, MRKB, MRPE, WSKB
2-Light Flush Mount
13"W x 7"H
2 x 60w MB Bulbs



91068 MRAC, MRPE, MRKB, WSKB
1-Light Mini Pendant
7"W
1 x 100w MB Bulb
One 6" stem and three 12" stems included.
Additional stems available:
6" order
STR06206AC, PE, KB
12" order
STR06212AC, PE, KB



120°



8021 MRAC, MRKB, MRPE, WSKB
 1-Light Wall Sconce
 7.5"W x 8.5"H x 9"Ext.
 1 x 100w MB Bulb



8022 MRAC, MRKB, MRPE, WSKB
 2-Light Bath Vanity
 18"W x 8"H x 8"Ext.
 2 x 100w MB Bulbs



8020 MRAC, MRKB, MRPE, WSKB
 2-Light Bath Vanity
 16"W x 9"H x 9"Ext.
 2 x 100w MB Bulbs



8023 MRAC, MRKB, MRPE, WSKB
 3-Light Bath Vanity
 26"W x 8"H x 8"Ext.
 3 x 100w MB Bulbs



8024 MRAC, MRKB, MRPE, WSKB
 4-Light Bath Vanity
 36"W x 8"H x 8"Ext.
 4 x 100w MB Bulbs



Nova

Beautiful flowing arms provide a clean, elegant look to this collection offered in Satin Nickel with Marbleized glass or Oil Rubbed Bronze with Wilshire glass.



11045 MRSN, WSOI 15-Light Chandelier
42"W x 41.5"H
15 x 60w MB Bulbs

800.486.2946

maximlighting.com



11041 MRSN, WSOI
 7-Light Chandelier
 28"W x 27.5"H
 (5+2) x 100w MB Bulbs



11046 MRSN, WSOI
 9-Light Chandelier
 30.5"W x 31"H
 9 x 100w MB Bulbs



11044 MRSN, WSOI 5-Light Chandelier
25"W x 26"H
5 x 100w MB Bulbs



11043 MRSN, WSOI 5-Light Chandelier
25.5"W x 28.5"H
5 x 100w MB Bulbs



11047 MRSN, WSOI
 1-Light Wall Sconce
 6"W x 12.5"H x 8"Ext.
 1 x 100w MB Bulb



11048 MRSN, WSOI
 2-Light Wall Sconce
 14"W x 12.5"H x 8"Ext.
 2 x 100w MB Bulbs



11042 MRSN, WSOI 3-Light Chandelier
 18"W x 18.5"H
 3 x 100w MB Bulbs

Piedmont


11544ICSN 5-Light Chandelier
Satin Nickel
28"W x 23"H
5 x 100w MB Bulbs



11541ICSN 3-Light Chandelier
Satin Nickel
18.5"W x 19"H
3 x 100w MB Bulbs



11545ICSN 9-Light Chandelier
Satin Nickel
31.5"W x 28"H
9 x 100w MB Bulbs



800.486.2946

maximlighting.com

11542ICSN 5-Light Chandelier

Satin Nickel
26"W x 26"H
5 x 100w MB Bulbs



91090ICSN 1-Light Mini Pendant

Satin Nickel
6"W
1 x 100w MB Bulb
One 6" stem and three 12" stems included.
Additional stems available:
6" order STR06206SN
12" order STR06212SN



11547ICSN 1-Light Wall Sconce

Satin Nickel
6.5"W x 9.5"H x 9.5"Ext.
1 x 100w MB Bulb



11543ICSN 3-Light Pendant

Satin Nickel
16"W x 23"H
3 x 100w MB Bulbs

Contour

Sleek modern form available in your choice of Oil Rubbed Bronze or Satin Nickel finish. The Frost glass shade gently melts into the flowing lines of the frame.



21267 FTOI, FTSN 15-Light Chandelier
45.5"W x 37.5"H
15 x 60w MB Bulbs

800.486.2946

maximlighting.com

21265 FTOI, FTSN 5-Light Chandelier
26.5"W x 20"H
5 x 100w MB Bulbs



21266 FTOI, FTSN 9-Light Chandelier
34"W x 26.5"H
9 x 100w MB Bulbs





5840 FTOI, FTSN
1-Light Flush Mount
11.5"W x 6"H
1 x 60w MB Bulb



21261 FTOI, FTSN
2-Light Semi-Flush
17.75"W x 9.25"H
2 x 60w MB Bulbs



5841 FTOI, FTSN
2-Light Flush Mount
13.5"W x 6"H
2 x 60w MB Bulbs



5842 FTOI, FTSN
3-Light Flush Mount
15.5"W x 6"H
3 x 60w MB Bulbs



21263 FTOI, FTSN
3-Light Pendant
26"W x 29"H
3 x 100w MB Bulbs



21264 FTOI, FTSN 3-Light Chandelier
24"W x 16.5"H
3 x 100w MB Bulbs



21271 FTOI, FTSN 1-Light Wall Sconce
 7.5"W x 7"H x 9"Ext.
 1 x 100w MB Bulb



21272 FTOI, FTSN 2-Light Bath Vanity
 18.5"W x 7"H x 9"Ext.
 2 x 100w MB Bulbs



92260 FTOI, FTSN 1-Light Mini Pendant
 7.5"W
 1 x 100w MB Bulb
*Additional stems available:
 6" order STR06206OI, SN
 12" order STR06212OI, SN
 One 6" stem and three 12"
 stems included.*



21273 FTOI, FTSN 3-Light Bath Vanity
 28.5"W x 7"H x 9"Ext.
 3 x 100w MB Bulbs



21274 FTOI, FTSN 4-Light Bath Vanity
 38.5"W x 7"H x 9"Ext.
 4 x 100w MB Bulbs



Bristol

Reminiscent of early America, this collection makes itself at home in today's classic style house. The Black Gold finish has the look and feel of naturally aged brass, and lends an air of authenticity to the collection. Contrasting Java Fog glass breathes life into art while casting a natural warm light below.

21326JFBG 9-Light Chandelier
Black Gold
29"W x 34.5"H
9 x 60w MB Bulbs



800.486.2946

maximlighting.com



21325JFBG 5-Light Chandelier
Black Gold
25"W x 25"H
5 x 100w MB Bulbs



21323JFBG 3-Light Chandelier
Black Gold
20.75"W x 22.75"H
3 x 100w MB Bulbs



21322JFBG 3-Light Pendant
Black Gold
18"W x 26"H
3 x 100w MB Bulbs



21321JFBG 3-Light Semi-Flush
Black Gold
14"W x 14"H
3 x 100w MB Bulbs



91320JFBG
 1-Light Mini Pendant
 Black Gold
 6.25"W
 1 x 100w MB Bulb
*Additional stems available:
 6" order STR06206BG
 12" order STR06212BG
 One 6" stem and three 12"
 stems included.*

120°



21327JFBG 1-Light Wall Sconce
 Black Gold
 6.25"W x 9.5"H x 9"Ext.
 1 x 100w MB Bulb



21328JFBG 2-Light Bath Vanity
 Black Gold
 15.25"W x 9.75"H x 8.5"Ext.
 2 x 100w MB Bulbs



21329JFBG 3-Light Bath Vanity
 Black Gold
 24"W x 9.75"H x 8.5"Ext.
 3 x 100w MB Bulbs



21330JFBG 4-Light Bath Vanity
 Black Gold
 33"W x 9.75"H x 8.5"Ext.
 4 x 100w MB Bulbs



South Bend

Accented with curiously jointed curvatures, this collection of Frosted Glass and Satin Nickel or Wilshire Glass and Oil Rubbed Bronze is both modern and versatile.

10154 FTSN, WSOI 3-Light Chandelier
22"W x 18"H
3 x 100w MB Bulbs



10155 FTSN, WSOI 5-Light Chandelier
25"W x 20"H
5 x 100w MB Bulbs



800.486.2946

maximlighting.com



91010 FTSN, WSOI
 1-Light Mini Pendant
 7.5"W
 1 x 100w MB Bulb
*One 6" stem
 and three 12"
 stems included.
 Additional
 stems available:
 6" order
 STR06206OI, SN
 12" order
 STR06212OI, SN*



10160 FTSN, WSOI
 3-Light Island Pendant
 35"L x 9"W x 43"H
 3 x 100w MB Bulbs



10151 FTSN, WSOI 2-Light Semi-Flush
12.75"W x 9"H
2 x 100w MB Bulbs



10152 FTSN, WSOI
1-Light Pendant
15"W x 10.5"H
1 x 100w MB Bulb



10153 FTSN, WSOI 2-Light Pendant
19"W x 20.5"H
2 x 60w MB Bulbs



10150 FTSN, WSOI
1-Light Semi-Flush
12"L x 9.5"W x 15.5"H
1 x 100w MB Bulb



10156 FTSN, WSOI
 1-Light Wall Sconce
 7.5"W x 8.5"H x 9"Ext.
 1 x 100w MB Bulb



10157 FTSN, WSOI
 2-Light Bath Vanity
 18"W x 8.5"H x 9"Ext.
 2 x 100w MB Bulbs



10158 FTSN, WSOI
 3-Light Bath Vanity
 28"W x 8.5"H x 9"Ext.
 3 x 100w MB Bulbs



10159 FTSN, WSOI 4-Light Bath Vanity
 38"W x 8.5"H x 9"Ext.
 4 x 100w MB Bulbs



10161 FTSN, WSOI 5-Light Bath Vanity
 48"W x 8.5"H x 9"Ext.
 5 x 100w MB Bulbs

Bel Air

Beautifully crafted with round stems and offered in our Satin Nickel or Oil Rubbed Bronze finishes. Both available with soft vanilla glass.

11092 SVOI, SVSN
2-Light Island Pendant
30.5"L x 13"W x 44"H
2 x 100w MB Bulbs

120°




11084 SVOI, SVSN
5-Light Chandelier
27.5"W x 44.5"H
5 x 100w MB Bulbs

120°



800.486.2946

maximlighting.com



91062 SVOI, SVSN 1-Light Pendant
13"W x 41"H
1 x 100w MB Bulb

120°



11093 SVOI, SVSN 3-Light Island Pendant
44"L x 13"W x 44.5"H
3 x 100w MB Bulbs

120°

*Additional stems available
for all items on this page:
6" stem order - STR10006 OI,SN
12" stem order - STR10012 OI,SN
One 6" stem and two 12" stems included.*




11086 SVOI, SVSN, WTPC
 1-Light Wall Sconce
 6.5"W x 10"H x 7"Ext.
 1 x 100w MB Bulb



11087 SVOI, SVSN, WTPC
 2-Light Bath Vanity
 15.5"W x 10"H x 7"Ext.
 2 x 100w MB Bulbs



11088 SVOI, SVSN, WTPC
 3-Light Bath Vanity
 22.5"W x 10"H x 7"Ext.
 3 x 100w MB Bulbs



11089 SVOI, SVSN, WTPC
 4-Light Bath Vanity
 30.5"W x 10"H x 7"Ext.
 4 x 100w MB Bulbs



Brentwood

Popular pendant lighting at its best. Trendy square stems are available in a variety of lengths. Finished in Satin Nickel or Oil Rubbed Bronze with Frost glass.

11072 FTOI, FTSN
2-Light Island Pendant
30"L x 13"W x 44"H
2 x 100w MB Bulbs

120°



11074 FTOI, FTSN
4-Light Chandelier
22.5"W x 45"H
4 x 100w MB Bulbs

120°

*Additional stems available for all items on this page:
6" stem order - STS10006 OI, SN
12" stem order - STS10012 OI, SN
One 6" stem and two 12" stems included.*



800.486.2946

11073 FTOI, FTSN
3-Light Island Pendant
44.5"L x 13"W x 45"H
3 x 100w MB Bulbs

120°



maximlighting.com



11076 FTOI, FTSN
 1-Light Wall Sconce
 5.5"W x 9.5"H x 6.5"Ext.
 1 x 100w MB Bulb



11077 FTOI, FTSN
 2-Light Bath Vanity
 13"W x 9.5"H x 6.5"Ext.
 2 x 100w MB Bulbs



91040 FTOI, FTSN
 1-Light Pendant
 13"W x 41.5"H
 1 x 100w MB Bulb
Additional stems available:
 6" stem order -
 STS10006 OI,SN
 12" stem order -
 STS10012 OI,SN
 One 6" stem and two
 12" stems included.



11078 FTOI, FTSN
 3-Light Bath Vanity
 20.5"W x 9.5"H x 6.5"Ext.
 3 x 100w MB Bulbs



11079 FTOI, FTSN
 4-Light Bath Vanity
 28"W x 9.5"H x 6.5"Ext.
 4 x 100w MB Bulbs



Stratus

Clean Lines are simply stated in this collection. Offered in Marble glass with your choice of Bronze or Pewter finishes.

2671MRBZ 6-Light Pendant
Bronze
32"W x 30.5"H
6 x 100w MB Bulbs



2674MRBZ 6-Light Pendant
Bronze
27.5"W x 30.5"H
6 x 100w MB Bulbs



2673MRBZ 5-Light Pendant
Bronze
24.5"W x 29.5"H
5 x 100w MB Bulbs



2672MRBZ 4-Light Pendant
Bronze
20"W x 25"H
4 x 100w MB Bulbs



800.486.2946

maximlighting.com



2676MRBZ 1-Light Wall Sconce
 12"W x 4.5"H x 6"Ext.
 1 x 100w MB Bulb



2670 MRBZ, MRPE
 3-Light Semi-Flush
 14.5"W x 9.5"H
 3 x 100w MB Bulbs



2677MRBZ 2-Light Bath Vanity
 Bronze
 24"W x 4.5"H x 6"Ext.
 2 x 100w MB Bulbs



2678MRBZ 3-Light Bath Vanity
 Bronze
 36"W x 4.5"H x 6"Ext.
 3 x 100w MB Bulbs



2679MRBZ 4-Light Bath Vanity
 Bronze
 48"W x 4.5"H x 6"Ext.
 4 x 100w MB Bulbs

Linda

A beautiful transitional collection with long flowing arms. Cool Ice glass perfectly compliments the rich Black finish.

11809ICBK 15-Light Chandelier
Black
46"W x 49.5"H
15 x 60w MB Bulbs



800.486.2946

maximlighting.com



11804ICBK 3-Light Chandelier
Black
19"W x 21.5"H
3 x 100w MB Bulbs



11806ICBK 9-Light Chandelier
Black
32.5"W x 34"H
9 x 100w MB Bulbs

11805ICBK 5-Light Chandelier

Black
26"W x 27"H
5 x 100w MB Bulbs



11815ICBK 5-Light Chandelier

Black
25"W x 26.5"H
5 x 100w MB Bulbs



11812ICBK
1-Light Pendant
Black
16"W x 10"H
1 x 100w MB Bulb



11801ICBK
3-Light Semi-Flush
Black
19"W x 16.5"H
3 x 100w MB Bulbs



11802ICBK
3-Light Pendant
Black
19"W x 24.5"H
3 x 60w MB Bulbs



11799ICBK 2-Light Flush Mount

Black
13"W x 8"H
2 x 60w MB Bulbs



11800ICBK 3-Light Flush Mount

Black
16"W x 10"H
3 x 60w MB Bulbs

91009ICBK 1-Light Mini Pendant

Black
6"W
1 x 100w MB Bulb
One 6" stem and three 12" stems included.
Additional stems available:
6" order STR06206BK
12" order STR06212BK





11807ICBK
1-Light Wall Sconce
Black
6"W x 9.5"H x 7.5"Ext.
1 x 100w MB Bulb



11808ICBK 2-Light Bath Vanity
Black
14.5"W x 10"H x 7.5"Ext.
2 x 100w MB Bulbs



11810ICBK 3-Light Bath Vanity
Black
23.5"W x 9"H x 9"Ext.
3 x 100w MB Bulbs



11811ICBK 4-Light Bath Vanity
Black
31.5"W x 9"H x 9"Ext.
4 x 100w MB Bulbs



Cupola

A contemporary statement features large scale Frost lichen glass shades symmetrically balanced on a metal frame finished in Oil Rubbed Bronze.

22104 FLOI 3-Light Chandelier
Oil Rubbed Bronze
24.5"W x 26"H
3 x 100w MB Bulbs



22105 FLOI 3-Light Chandelier
Oil Rubbed Bronze
34"W x 26"H
3 x 100w MB Bulbs



22106 FLOI 6-Light Chandelier
Oil Rubbed Bronze
34"W x 28.5"H
6 x 100w MB Bulbs



800.486.2946

maximlighting.com



92105FLOI 1-Light Mini Pendant
 Oil Rubbed Bronze
 10" W
 1 x 100w MB Bulb
*Additional stems available:
 6" order STR06206OI
 12" order STR06212OI
 One 6" stem and three 12"
 stems included.*

120°



22103FLOI 4-Light Pendant
 Oil Rubbed Bronze
 24"W x 22.5"H
 4 x 100w MB Bulbs



22100FLOI 3-Light Flush Mount
 Oil Rubbed Bronze
 14.5"W x 7"H
 3 x 60w MB Bulbs



22107FLOI 1-Light Wall Sconce
 Oil Rubbed Bronze
 10"W x 8"H x 10"Ext.
 1 x 100w MB Bulb

150°



22101FLOI 3-Light Semi-Flush
 Oil Rubbed Bronze
 15"W x 12"H
 3 x 100w MB Bulbs

Vail

Whether rustic chalet or urban loft Vail works with its forged metal frame in Natural Iron with Clear Ice.

12505CINI 5-Light Chandelier

Natural Iron
24"W x 19"H
5 x 100w MB Bulbs



12506CINI 9-Light Chandelier

Natural Iron
29"W x 24.5"H
9 x 100w MB Bulbs



800.486.2946

maximlighting.com



12500CINI 2-Light Semi-Flush
 Natural Iron
 13"W x 6.5"H
 2 x 100w MB Bulbs



12508CINI 3-Light Pendant
 Natural Iron
 16.5"W x 18"H
 3 x 100w MB Bulbs



92500CINI
 1-Light Mini Pendant
 Natural Iron
 7"W
 1 x 100w MB Bulb
*Additional stems available:
 6" Order-STR06206NI
 12" order-STR06212NI
 One 6" stem and three
 12" stems included*





12502CINI 2-Light Bath Vanity
 Natural Iron
 14.5"W x 8.5"H x 6.5"Ext.
 2 x 100w MB Bulbs



12501CINI 1-Light Wall Sconce
 Natural Iron
 6"W x 8.5"H x 6.5"Ext.
 1 x 100w MB Bulb



12503CINI 3-Light Bath Vanity
 Natural Iron
 23"W x 8.5"H x 6.5"Ext.
 3 x 100w MB Bulbs



12504CINI 4-Light Bath Vanity
 Natural Iron
 31"W x 8.5"H x 6.5"Ext.
 4 x 100w MB Bulbs





Practical and efficient, contemporary lighting focuses on function and minimizes form. Simple task lighting gets a creative flair with Maxim's full line of contemporary fixtures that compliment today's streamlined home and office designs. Marbleized, frosted, and metallic effects add character to sleek lines in every pendant and sconce. Geometrical shapes of clear and colored crystal cast focused rays of light that illuminate space effectively and elegantly. In the contemporary kitchen, spacious areas and clean countertops call for discreet fixtures that won't detract from the beauty of simplicity. Maxim delivers the utmost in efficiency and ambience.

Aurora

Straight lines and curves make this contemporary series a classic. Square metal tubing finished in your choice of Oil Rubbed Bronze or Satin Nickel support tapered square Frost glass shades.



20097 FTOI, FTSN 15-Light Chandelier
45"W x 42"H
15 x 60w MB Bulbs

800.486.2946

maximlighting.com



20095 FTOI, FTSN 5-Light Chandelier
 26"W x 23.5"H
 5 x 100w MB Bulbs



20094 FTOI, FTSN 3-Light Chandelier
 22.5"W x 16"H
 3 x 100w MB Bulbs



20096 FTOI, FTSN 9-Light Chandelier
 31.5"W x 30"H
 9 x 100w MB Bulbs



5840 FTOI, FTSN
1-Light Flush Mount
11.5"W x 6"H
1 x 60w MB Bulb



5842 FTOI, FTSN
3-Light Flush Mount
15.5"W x 6"H
3 x 60w MB Bulbs



5841 FTOI, FTSN
2-Light Flush Mount
13.5"W x 6"H
2 x 60w MB Bulbs



20091 FTOI, FTSN 2-Light Semi-Flush
13"W x 9"H
2 x 60w MB Bulbs



20093 FTOI, FTSN 2-Light Pendant
16"W x 24.5"H
2 x 60w MB Bulbs



20098 FTOI, FTSN
1-Light Wall Sconce
5.5"W x 10"H x 7"Ext.
1 x 100w MB Bulb




20099 FTOI, FTSN
2-Light Bath Vanity
13.5"W x 7"H x 8.5"Ext.
2 x 100w MB Bulbs



20100 FTOI, FTSN 3-Light Bath Vanity
21.5"W x 7"H x 8.5"Ext.
3 x 100w MB Bulbs



20101 FTOI, FTSN
4-Light Bath Vanity
29.5"W x 7"H x 8.5"Ext.
4 x 100w MB Bulbs



92090 FTOI, FTSN
1-Light mini Pendant
8"W
1 x 100w MB Bulb
Additional stems available:
6" order STR06206OI, SN
12" order STR06212OI, SN
One 6" stem and three 12"
stems included.



Progetto

Form follows function in this ideal expression of contemporary engineering as personified by its White Ice Glass and the way it curves to the contours of its Satin Nickel frame. All fixtures include G9 Xenon lamps.



23003WISN
shown without stems.
Total drop as shown 16.5"



23003WISN*
4-Light Chandelier
Satin Nickel
16"W x 16.5"H (Body Only)
4 x 60w G9 Xenon Incl.
Shown with 12" stem
Total drop as shown 33.5"
Can be installed without stems



23005WISN* 8-Light Chandelier
Satin Nickel
33"W x 24"H (Body Only)
8 x 60w G9 Xenon Incl.
Shown with 12" stem
Total drop as shown 38.5"



*Additional stems available: **STR06206SN** 6" stem or **STR06212SN** 12" stem.
Fixture includes one 6" stem and three 12" stems.

800.486.2946

maximlighting.com



23011WISN 1-Light Wall Sconce
Satin Nickel
6.5"W x 6.5"H x 5"Ext.
1 x 60w G9 Xenon Incl.



23012WISN 2-Light Bath Vanity
Satin Nickel
15.5"W x 5"H x 5"Ext.
2 x 60w G9 Xenon Incl.



23013WISN 3-Light Bath Vanity
Satin Nickel
24.5"W x 5"H x 5"Ext.
3 x 60w G9 Xenon Incl.



23014WISN 4-Light Bath Vanity
Satin Nickel
33.5"W x 5"H x 5"Ext.
4 x 60w G9 Xenon Incl.

Avant

New wave contemporary design features a metal frame in Golden Auburn finish and topped with Champagne fabric shades.

21253CHGA 3-Light Pendant
Golden Auburn
21"W x 26"H
3 x 100w MB Bulbs



21255CHGA 5-Light Chandelier
Golden Auburn
26"W x 24"H
5 x 60w CABulbs



800.486.2946

maximlighting.com



21251CHGA 3-Light Semi-Flush
Golden Auburn
17"W x 14.5"H
3 x 60w CA Bulbs



21258CHGA 1-Light Wall Sconce
Golden Auburn
6.5"W x 12"H x 9.5"Ext.
1 x 60w CABulb




21259CHGA 2-Light Island Pendant
Golden Auburn
39"L x 13"W x 28"H 37"OAH
2 x 100w MB Bulbs
Additional stems available:
6"stem order-STR10006GA
12"stem order-STR10012GA



Elite

This elegant family features
Optic Crystal on a graceful frame finished
in our Plated Silver finish.
The Black Tie shades are created using
a pleated black shear fabric and are included.

32004BTPS 3-Light Pendant
Plated Silver
24"W x 31"H
3 x 100w MB Bulbs



32006BTPS 9-Light Chandelier
Plated Silver
32"W x 32.5"H
9 x 60w CA Bulbs



800.486.2946

maximlighting.com



32003BTPS 2-Light Wall Sconce
Plated Silver
16.5"W x 14"H x 9"Ext.
2 x 60w CABulbs



32001BTPS 2-Light Semi-Flush
Plated Silver
16"W x 12"H
2 x 100w MB Bulbs



32005BTPS 5-Light Chandelier
Plated Silver
26"W x 26"H
5 x 60w CABulbs



32002BTPS 1-Light Wall Sconce
Plated Silver
7"W x 14"H x 9"Ext.
1 x 60w CABulb

Spectra

Beautiful flowing arms provide a clean, elegant look to this collection offered in Satin Nickel finish with Marbleized glass.


2734MRSN 3-Light Chandelier
Satin Nickel
15"W x 14"H
3 x 100w MB Bulbs



2735MRSN 6-Light Chandelier
Satin Nickel
24"W x 17"H
5 x 100w MB Bulbs + 1 x 50w R20 Bulb
3-Way Switch



2736MRSN 1-Light Wall Sconce
Satin Nickel
7"W x 9"H x 8"Ext.
1 x 100w MB Bulb



91063MRSN 1-Light Mini Pendant
Satin Nickel
7"W
1 x 100w MB Bulb
One 6" stem and three 12"
stems Included.
Additional stems available:
6" order STR06206 SN
12" order STR06212 SN

120°



2737MRSN 2-Light Bath Vanity
Satin Nickel
19"W x 9"H x 8"Ext.
2 x 100w MB Bulbs

120°



2738MRSN 3-Light Bath Vanity
Satin Nickel
25"W x 9"H x 8"Ext.
3 x 100w MB Bulbs

120°



2739MRSN 4-Light Bath Vanity
Satin Nickel
37"W x 9"H x 8"Ext.
4 x 100w MB Bulbs

120°

Cilandro

53009WTSN 1-Light Mini Pendant
Satin Nickel
5"W
1 x 60w MB T10 Bulb (Included)



53006WTSN 1-Light Wall Sconce
Satin Nickel
4.7"W x 11"H x 4.3"Ext.
1 x 60w MB T10 Bulb (Included)



800.486.2946

Arc



5002 FTOI,FTSST
2-Light Wall
6.5"W x 12"H x 4"Ext.
2 x 60w MB Bulbs



5000 FTOI,FTSST
1-Light Wall
6"W x 9"H x 4"Ext.
1 x 60w MB Bulb

maximlighting.com



MAXIM LIGHTING®

For those who shrug off conventionality and opt for an eclectic design for hearth and home, the Maxim Expression Collections confidently fills the niche. From French Country charm to mystic Asian to old English woodsman, these fixtures reject the rules and blend together unusual materials to create unique show pieces certain to spark interest and conversation. No matter the theme or genre, these collections possess the uncanny ability to simultaneously fit in and stand out in any room.

French Country

For generations, the French have looked to their country's picturesque landscapes for inspiration when designing their homes. This family features a hand painted French Floral pattern on a soft white frame with complimentary design carried forward on the Country Cottage shades. The pendant and flush mount features Frost glass.



21434CCFF 3-Light Chandelier
French Floral
15"W x 19"H
3 x 60w CA Bulbs
Shades Included



21436CCFF 9-Light Chandelier
French Floral
35"W x 41.5"H
9 x 60w CA Bulbs
Shades Included

21435CCFF 6-Light Chandelier
 French Floral
 26.5"W x 31.5"H
 6 x 60w CABulbs
Shades Included



21442CCFF 2-Light Wall Sconce
 French Floral
 14.5"W x 18"H x 9.5"Ext.
 2 x 60w CABulbs
Shades Included



21430FTFF 2-Light Flush Mount
 French Floral
 15"W x 7.5"H
 2 x 60w MB Bulbs



21433FTFF 3-Light Pendant
 French Floral
 19.5"W x 29"H
 3 x 60w MB Bulbs



21441CCFF 1-Light Wall Sconce
 French Floral
 6"W x 18"H x 10.5"Ext.
 1 x 60w CABulb
Shade Included



Asiana

Influenced by Far Eastern design, this series features square tube metal work finished in Roasted Chestnut. The soft square Wilshire glass blends well with the roving curves of the body design.



10986WSRC 9-Light Chandelier
Roasted Chestnut
33"W x 36"H
9 x 60w MB Bulbs

800.486.2946

maximlighting.com

10985WSRC 6-Light Chandelier
 Roasted Chestnut
 27"W x 24"H
 6 x 100w MB Bulbs



10989WSRC 2-Light Island Pendant
 Roasted Chestnut
 39.5"L x 13"W x 49"H
 2 x 100w MB Bulbs
*Additional stems available:
 6" stem order-STR10006RC
 12" stem order-STR10012RC*

120°




10981WSRC 2-Light Semi-Flush
Roasted Chestnut
13"W x 15"H
2 x 100w MB Bulbs
KIT



10998VNRC
1-Light Table Lamp
Roasted Chestnut
18"W x 32"H
1 x 100w MB Bulb
Shade Included
SHD 65VN



91082WSRC
1-Light Mini Pendant
Roasted Chestnut
5.5"W
1 x 100w MB Bulb
120°



10987WSRC
1-Light Floor Lamp
Roasted Chestnut
23.5"W x 72"H
1 x 150w MB Bulb
With Dimmer Switch



10982WSRC
1-Light Pendant
Roasted Chestnut
13"W x 17"H
1 x 100w MB Bulb



10984WSRC
3-Light Pendant
Roasted Chestnut
16.5"W x 25"H
3 x 100w MB Bulbs



10992WSRC 2-Light Bath Vanity
 Roasted Chestnut
 17.5"W x 11.5"H x 6.5"Ext.
 2 x 100w MB Bulbs



10996WSRC 1-Light Wall Sconce
 Roasted Chestnut
 5.5"W x 12"H x 6.5"Ext.
 1 x 100w MB Bulb



10993WSRC 3-Light Bath Vanity
 Roasted Chestnut
 23.5"W x 11.5"H x 6.5"Ext.
 3 x 100w MB Bulbs



10994WSRC 4-Light Bath Vanity
 Roasted Chestnut
 32"W x 11.5"H x 6.5"Ext.
 4 x 100w MB Bulbs



Country French

A country-look inspired collection in classic iron and finished in Kentucky Bronze.



7766KB 1-Light Wall Sconce
Kentucky Bronze
10.75"W x 16.25"H x 9"Ext.
1 x 60w CABulb
Shade Included
SHD 28KB



7767KB 2-Light Wall Sconce
Kentucky Bronze
15.5"W x 16"H x 8"Ext.
2 x 60w CABulbs
Shades Included
SHD 28KB



7764KB 6-Light Chandelier
Kentucky Bronze
36"L x 25.5"W x 37"H
6 x 60w CABulbs
Shades Included
SHD 28KB

800.486.2946

maximlighting.com



8762BK 6-Light Chandelier
8762BK/SHD45 With Shade
 Black
 28.5"W x 17"H
 6 x 60w CA Bulbs
Shades Optional-SHD45BI



7765KB 6-Light Chandelier
 Kentucky Bronze
 28"L x 23.5"W x 31"H
 6 x 60w CA Bulbs
Shades Included
SHD 28KB
Oval

Pine Grove

Faux pine branches in Pine Tree finish with Amber Vanilla glass or optional faux leather shades with stitched trim bring the forest home.



SHD42PD Shade
3.5"Top x 6.5"Bottom x 5"H
Sit On Candle Cover(1")



20707PT 12-Light Chandelier
20707PT/SHD42 *With Shade*
Pine Tree
36"W x 34"H
12 x 60w CA Bulbs
Shades Optional
SHD 42PD



20700AVPT 2-Light Flush Mount
Pine Tree
15"W x 6"H
2 x 75w MB Bulbs



20706AVPT 1-Light Wall Sconce
Pine Tree
14"W x 6"H x 7"Ext.
1 x 100w MB Bulb



20705PT 5-Light Chandelier
20705PT/SHD42 With Shade
Pine Tree
27"W x 25.5"H
5 x 60w CA Bulbs
Shades Optional
SHD 42PD



91051AVPT 1-Light Mini Pendant
Pine Tree
8"W
1 x 100w MB Bulb





5520VAPT
 1-Light Flush Mont
 Pine Tree
 10"W x 7.5"H
 1 x 100w MB Bulb



5520CDPT
 3-Light Flush Mont
 Pine Tree
 10"W x 7.5"H
 3 x 60w CA Bulbs



97006PT Mirror
 Pine Tree
 33.5"W x 49.5"H x 3.5"Ext.



20708AVPT 1-Light Wall Sconce
 Pine Tree
 10.5"W x 9.5"H x 4.5"Ext.
 1 x 100w MB Bulb



20702AVPT 3-Light Pendant
 Pine Tree
 27"W x 32"H
 3 x 100w MB Bulbs



20716AVPT 1-Light Wall Sconce
 Pine Tree
 12"W x 12"H x 8"Ext.
 1 x 100w MB Bulb



20717AVPT 2-Light Bath Vanity
 Pine Tree
 17.5"W x 10"H x 8"Ext.
 2 x 100w MB Bulbs



20718AVPT 3-Light Bath Vanity
 Pine Tree
 26"W x 11"H x 8"Ext.
 3 x 100w MB Bulbs



20719AVPT 4-Light Bath Vanity
 Pine Tree
 36"W x 11"H x 8"Ext.
 4 x 100w MB Bulbs



Desert Wind

A contemporary twist on traditional Southwest style. Vintage Amber glass shades are the perfect compliment to the C

11905
Deser
28"W;
6 x 10"



800.486.2946

maximlighting.com



11904VADB 3-Light Chandelier
Desert Bronze
24"W x 24"H
3 x 100w MB Bulbs



11901VADB 1-Light Wall Sconce
Desert Bronze
6"W x 13"H x 9.5"Ext
1 x 100w MB Bulb



11903VADB 1-Light Mini Pendant
Desert Bronze
7"W
1 x 100w MB Bulb



11900VADB 3-Light Semi-Flush
Desert Bronze
18"W x 10"H
3 x 100w MB Bulbs



11902VADB 4-Light Semi-Flush
Desert Bronze
24.5"W x 18"H
4 x 100w MB Bulbs

Sherwood

Inspired to bring the outdoors in this collection will add uniqueness to any room. Forged metal frames painted in Platinum Dusk support hand formed and rolled Early Frost glass shades.



32446EFPD
9-Light Chandelier
Platinum Dusk
31.5"W x 39"H
9 x 100w MB Bulbs



32447EFPD 12-Light Chandelier
Platinum Dusk
33.5"W x 48"H
12 x 60w MB Bulbs



32448EFPD 1-Light Wall Sconce
Platinum Dusk
6.5"W x 17"H x 9.5"Ext.
1 x 100w MB Bulb

800.486.2946

maximlighting.com



32441EFPD 3-Light Semi-Flush
 Platinum Dusk
 16"W x 9"H
 3 x 60w MB Bulbs



32443EFPD 3-Light Pendant
 Platinum Dusk
 31"W x 33.5"H
 3 x 100w MB Bulbs



32445EFPD 6-Light Chandelier
 Platinum Dusk
 28.5"W x 35"H
 6 x 100w MB Bulbs

Bali

Inspired by the cool tropical breeze of the islands, this series features a bamboo look frame painted in Bali Collection finish and topped with a split bamboo shade. Some pieces also feature Screen Ivory glass.

20203RTBC 3-Light Chandelier
Bali Collection
18"W x 20.5"H
3 x 60w CA Bulbs
Shades Included
SHD 51RT



20205RTBC
9-Light Chandelier
Bali Collection
32"W x 32.5"H
9 x 60w CA Bulbs
Shades Included
SHD 51RT



800.486.2946

maximlighting.com



20200SIBC 2-Light Flush Mount
Bali Collection
16.5"W x 9"H
2 x 75w MB Bulbs



20202SIBC 3-Light Pendant
Bali Collection
16.5"W x 20.5"H
3 x 100w MB Bulbs



20204RTBC 5-Light Chandelier
Bali Collection
28"W x 28"H
5 x 60w CA Bulbs
Shades Included
SHD 51RT



20209RTBC
 1-Light Floor Lamp
 Bali Collection
 17"W x 60"H
 1 x 150w MB Bulb
 Shade Included
 SHD 53RT
 With Dimmer Switch

20207RTBC 2-Light Wall Sconce
 Bali Collection
 16"W x 14"H x 9"Ext.
 2 x 60w CA Bulbs
 Shades Included
 SHD 51RT



20206RTBC 1-Light Wall Sconce
 Bali Collection
 7"W x 15.5"H x 10"Ext.
 1 x 60w CA Bulb
 Shade Included
 SHD 51RT



20208RTBC 1-Light Table Lamp
 Bali Collection
 16"W x 31"H
 1 x 100w MB Bulb
 Shade Included
 SHD 52RT



Maxim Lighting's commitment to both the residential lighting and the home building industries will assure you a product line that is focused on your customer's needs and offers programs that will be beneficial to your bottom line. Our Basic Collections is our way of recognizing the need for quality lighting that is well designed, well priced and readily available.

Basix

Contemporary collection with sweeping arms and clean lines. Offered in Ice glass and Satin Nickel finish or Wilshire glass and Oil Rubbed Bronze finish.



10123 ICSN, WSOI
3-Light Chandelier
19"W x 18.5"H
3 x 100w MB Bulbs

10129 ICSN, WSOI
15-Light Chandelier
42"W x 40"H
15 x 60w MB Bulbs



800.486.2946

maximlighting.com



10128 ICSN, WSOI
 9-Light Chandelier
 32"W x 31.5"H
 9 x 100w MB Bulbs



10122 ICSN, WSOI
 3-Light Chandelier
 19"W x 17"H
 3 x 100w MB Bulbs



10125 ICSN, WSOI
 5-Light Chandelier
 26"W x 22.5"H
 5 x 100w MB Bulbs

10124 ICSN, WSOI
5-Light Chandelier
25"W x 21"H
5 x 100w MB Bulbs



10131 ICSN, WSOI
4-Light Pendant
16.5"W x 32"H
4 x 60w CABulbs



10121 ICSN, WSOI
3-Light Pendant
17"W x 22.5"H
3 x 100w MB Bulbs



10130 ICSN, WSOI
2-Light Pendant
13"W x 25.5"H
2 x 60w CABulbs



10120 ICSN, WSOI
2-Light Semi-Flush
14"W x 10"H
2 x 100w MB Bulbs
KIT Optional - See Page 423



FKT2012WSOI
 3-Light Fan Kit
 14"W x 7"H
 3 x 60w CA Bulbs
Fan Sold Separately



10127 ICSN, WSOI
 3-Light Island Pendant
 48"L x 13"W x 33" H
 3 x 100w MB Bulbs



10126 ICSN, WSOI
 2-Light Island Pendant
 36"L x 13"W x 29.5" H
 2 x 100w MB Bulbs



5840 ICSN, WSOI
 1-Light Flush Mount
 11.5"W X 6"H
 1 x 60w MB Bulbs



5841 ICSN, WSOI
 2-Light Flush Mount
 13.5"W X 6"H
 2 x 60w MB Bulbs



91064 ICSN, WSOI
 1-Light Mini Pendant
 6.5"W
 1 x 100w MB Bulb
*One 6" stem and three
 12" stems included.
 Additional stems available
 6" order STR06206OI, SN
 12" order STR06212OI, SN*



5842 ICSN, WSOI
 3-Light Flush Mount
 15.5"W X 6"H
 3 x 60w MB Bulbs



2120 ICPC, ICSN, WSOI
 1-Light Wall Sconce
 6"W x 8"H X 9"Ext.
 1 x 100w MB Bulb



2121 ICPC, ICSN, WSOI
 2-Light Bath Vanity
 13.5"W x 8"H X 9"Ext.
 2 x 100w MB Bulbs



2122 ICPC, ICSN, WSOI
 3-Light Bath Vanity
 19"W x 8"H X 9"Ext.
 3 x 100w MB Bulbs



2123 ICPC, ICSN, WSOI
 4-Light Bath Vanity
 27.5"W x 8"H X 9"Ext.
 4 x 100w MB Bulbs



Newburg

20326 MROI, MRSN 3-Light Chandelier
22.5"W x 17.5"H
3 x 100w MB Bulbs



20325 MROI, MRSN 5-Light Chandelier
24.75"W x 17.5"H
5 x 100w MB Bulbs

800.486.2946

maximlighting.com

Builder Basics

91193 CLPB, CLSN 3-Light Chandelier
22"W x 14"H
3 x 100w MB Bulbs



800.486.2946

maximlighting.com



91102 CLPB, CLSN
1-Light Pendant
16.5"W x 11.5"H
1 x 100w MB Bulb



91195 CLPB, CLSN 5-Light Chandelier
24"W x 14"H
5 x 100w MB Bulbs



711501 5-Light Chandelier
 Oil Rubbed Bronze
 23"W x 15"H
 5 x 60w CA Bulbs



91197 MRSN, WSOI
 5-Light Chandelier
 21"W x 14"H
 5 x 100w MB Bulbs



91196 MRSN, WSOI
 3-Light Chandelier
 21"W x 14"H
 3 x 100w MB Bulbs


7105PB 20-Light Chandelier
Polished Brass
32"W x 28.5"H
20 x 60w CA Bulbs



7103PB 5-Light Chandelier
Polished Brass
23"W x 17.5"H
5 x 60w CA Bulbs



7101PB 8-Light Chandelier
Polished Brass
27.5"W x 17.5"H
8 x 60w CA Bulbs



7102PB 6-Light Chandelier
Polished Brass
23"W x 17.5"H
6 x 60w CA Bulbs



Builder Essentials



5840 FIOI,FTOI,FTSN,
ICBK,ICSN,MRAC,
MROI,MRPB,MRPE,
MRSN,MRTW,MRWT,WSOI
1-Light Flushmount
11.5"W x 6"H
1 x 60w MB Bulb



5841 FIOI,FTOI,FTSN,
ICBK,ICSN,MRAC,
MROI,MRPB,MRPE,
MRSN,MRTW,MRWT,WSOI
2-Light Flushmount
13.5"W x 6"H
2 x 60w MB Bulbs



5842 FIOI,FTOI,FTSN,
ICBK,ICSN,MRAC,
MROI,MRPB,MRPE,
MRSN,MRTW,MRWT,WSOI
3-Light Flushmount
15.5"W x 6"H
3 x 60w MB Bulbs



5849 MROI,MRSN
2-Light Flushmount
11.5"W x 6"H
2 x 60w MB Bulbs



5843 MRAC, MROI,
MRPB, MRPE, MRSN,
MRWT, WSOI
2-Light Semi-Flush
14.5"W x 14"H
2 x 100w MB Bulbs
KT Optional - See Page 423

5846 MRAC, MROI,MRPB,
MRPE, MRSN, WSOI
3-Light Pendant
20"W x 24"H
3 x 100w MB Bulbs



5844 MROI, MRSN
3-Light Semi-Flush
17"W x 14"H
3 x 100w MB Bulbs

5845 MRAC, MROI,MRPB,
MRPE, MRSN,WSOI
3-Light Pendant
15"W x 24"H
3 x 100w MB Bulbs



800.486.2946

maximlighting.com



5830 FTOI, FTPB, FTPE, FTSN, FTTW, FTWT
1-Light Flushmount
11.5"W x 6"H
1 x 60w MB Bulb




5831 FTOI, FTPB, FTPE, FTSN, FTTW, FTWT
2-Light Flushmount
13.5"W x 6"H
2 x 60w MB Bulbs



5832 FTOI, FTPB, FTPE, FTSN, FTTW, FTWT
3-Light Flushmount
15.5"W x 6"H
3 x 60w MB Bulbs



5833 FTOI, FTPB, FTPE, FTSN, FTTW, FTWT
2-Light Semi-Flush
14.5"W x 14"H
2 x 100w MB Bulbs
KIT Optional - See Page 423



FT Glass



5835 FTOI, FTPE, FTSN, FTTW, FTWT
3-Light Pendant
15"W x 24"H
3 x 100w MB Bulbs



5826CLSN
1-Light Flushmount
Satin Nickel
11.5"W x 6"H
1 x 60w MB Bulb



5827CLSN
2-Light Flushmount
Satin Nickel
13.5"W x 6"H
2 x 60w MB Bulbs



5828CLSN
3-Light Flushmount
Satin Nickel
15.5"W x 6"H
3 x 60w MB Bulbs



5824CLSN 3-Light Pendant
Satin Nickel
15"W x 24"H
3 x 100w MB Bulbs




5829CLSN 2-Light Semi-Flush
Satin Nickel
14.5"W x 14"H
2 x 100w MB Bulbs

Pendants



91000 OI, SN
 3-Light Canopy Kit
 33"L x 4.5"W x 1"H
Pendants Sold Separately.



800.486.2946



91061 MROI, MRSN, WSOI
 1-Light Pendant
 13.25"W x 13"H
 1 x 100w MB Bulb



91076 MRAC, MRCS, MROI, MRPB, MRSN, WSOI
 1-Light Pendant
 16"W x 11"H
 1 x 100w MB Bulb



90188PB 1-Light Pendant
 Polished Brass
 16.5"W x 8"H
 1 x 150w MB Bulb



91078MRSN 1-Light Pendant
 Satin Nickel
 18"W x 9.5"H
 1 x 100w MB Bulb



91101CLPB 1-Light Pendant
 Polished Brass
 15"W x 11.5"H
 1 x 100w MB Bulb

maximlighting.com



15846 ICSN, WSOI
 3-Light Pendant
 28"W x 28.5"H
 3 x 100w MB Bulbs



15845 ICSN, WSOI
 3-Light Pendant
 24"W x 24.5"H
 3 x 100w MB Bulbs



15844 ICSN, WSOI
 3-Light Pendant
 19.5"W x 21"H
 3 x 100w MB Bulbs

Spots



92011 BK, WT
2-Light Wall/Flush Mount
16.5"W x 9.5"H x 8.5"Ext.
2 x 100w MB R30 Bulbs



92010 BK, WT
1-Light Wall/Flush Mount
5"W x 8.5"H x 8.5"Ext.
1 x 100w MB R30 Bulb



92310WT
3-Light Track Kit
White
48"W x 10"H x 4.5"Ext.
3 x 75w MB R30 Bulbs

800.486.2946

maximlighting.com

Track



92320WT
3-Light Track Kit
White
48"W x 8"H x 4.5"Ext.
3 x 75w MB R30 Bulbs



92305WT
3-Light Track Kit
White
48"W x 10"H x 4.5"Ext.
3 x 75w MB R30 Bulbs



92315WT
3-Light Track Kit
White
48"W x 10"H x 4.5"Ext.
3 x 75w MB R30 Bulbs

800.486.2946

maximlighting.com

Malibu

Intricate contemporary designs offered in Polished Brass, Satin Nickel, Oil Rubbed Bronze with Marbleized glass and Oil Rubbed Bronze with Wilshire glass.

2685 MROI, MRPB, MRSN, WSOI
9-Light Chandelier
31.5"W x 16.5"H
9 x 60w MB Bulbs



2683 MROI, MRPB, MRSN, WSOI
15-Light Chandelier
39"W x 30"H
15 x 60w MB Bulbs



800.486.2946

maximlighting.com



2697 MROI, MRPB, MRSN, WSOI
 3-Light Chandelier
 20"W x 15.5"H
 3 x 100w MB Bulbs



2698 MROI, MRPB, MRSN, WSOI
 5-Light Chandelier
 24"W x 17"H
 5 x 100w MB Bulbs



2684 MROI, MRPB, MRSN, WSOI
 6-Light Chandelier
 26"W x 14"H
 6 x 100w MB Bulbs



2699 MROI, MRPB, MRSN, WSOI
 5-Light Chandelier
 25"W x 16"H
 5 x 100w MB Bulbs



11060 MROI, MRPB, MRSN, MRWT, WSOI
4-Light Flush Mount
20"W x 6"H
4 x 60w MB Bulbs



2680 MROI, MRPB, MRSN, MRWT, WSOI
2-Light Flush Mount
12.5"W x 4.25"H
2 x 60w MB Bulbs



2681 MROI, MRPB, MRSN, MRWT, WSOI
3-Light Flush Mount
16"W x 4"H
3 x 60w MB Bulbs



90182 MRPB, MRSN
1-Light Pendant
10"W x 19.5"H
1 x 100w MB Bulb




90180 MRPB, MRSN
1-Light Pendant
8"W x 18"H
1 x 60w MB Bulb



2682 MROI, MRPB, MRSN, WSOI
3-Light Pendant
16"W x 24.5"H
3 x 100w MB Bulbs



2686 MROI, MRPB, MRSN, WSOI
 1-Light Wall Sconce
 6"W x 6.5"H x 9"Ext.
 1 x 100w MB Bulb



2687 MROI, MRPB, MRSN, WSOI
 2-Light Bath Vanity
 13.25"W x 6"H x 8"Ext.
 2 x 100w MB Bulbs



2688 MROI, MRPB, MRSN, WSOI
 3-Light Bath Vanity
 Polished Brass
 19.5"W x 6"H x 8"Ext.
 3 x 100w MB Bulbs




2689 MROI, MRPB, MRSN, WSOI
 4-Light Bath Vanity
 29"W x 6"H x 8"Ext.
 4 x 100w MB Bulbs



Newport

A classic yet modern collection offered in Satin Nickel or our popular Oil Rubbed Bronze finish complimented by Marble glass.

11061 MROI, MRSN, WSOI 3-Light Chandelier
19.5"W x 13.5"H
3 x 100w MB Bulbs



11065 MROI, MRSN, WSOI
9-Light Chandelier
31"W x 30.5"H
9 x 100w MB Bulbs



800.486.2946

maximlighting.com



11063 MROI, MRSN, WSOI
 5-Light Chandelier
 25"W x 17"H
 5 x 100w MB Bulbs



11062 MROI, MRSN, WSOI
 5-Light Chandelier
 25"W x 17.5"H
 5 x 100w MB Bulbs



11064 MROI, MRSN, WSOI
 6-Light Chandelier
 24"W x 19"H
 5 x 100w MB Bulbs
 1 x 50w MB R20 Bulb
 3-Way Switch



11067 MROI, MRSN, WSOI
2-Light Bath vanity
16.5"W x 10"H x 7.5"Ext.
2 x 100w MB Bulbs



11066 MROI, MRSN, WSOI
1-Light Wall Sconce
6.75"W x 10"H x 9"Ext.
1 x 100w MB Bulb



11068 MROI, MRSN, WSOI 3-Light Bath vanity
22.5"W x 10"H x 9"Ext.
3 x 100w MB Bulbs



91064 MROI, MRSN, WSOI
1-Light Mini Pendant
6.5"W
1 x 100w MB Bulb
One 6" stem and three 12" stems included.
*Additional stems available:
6" order STR06206OI, SN
12" order STR06212OI, SN*



11069 MROI, MRSN, WSOI 4-Light Bath vanity
31W x 10H x 9E xt.
4 x 100w MB Bulbs



60201 CLOI,CLPB 9-Light Pendant
16.5"W x 32.5"H
9 x 25w CA Bulbs
White Candle Covers



Bound Glass

Beautiful bound glass presents a touch of elegance in any setting, but it truly shines as an entry fixture. All are offered in Polished Brass, and several are available in Country Stone and White.

61601 CLPB,CLOI,CLSN
6-Light Pendant
13"W x 30.5"H
6 x 40w CA Bulbs
White Candle Covers



61501CLPB
3-Light Pendant
Polished Brass
9"W x 21"H
3 x 40w CA Bulbs
White Candle Covers



6151 CLOI,CLPB,CLSN
3-Light Pendant
9"W x 14.5"H
3 x 40w CA Bulbs



90350 CLCS,CLPB,CLWT
3-Light Pendant
13"W x 20.5"H
3 x 40w CA Bulbs

800.486.2946

maximlighting.com



90329CLPB 7-Light Pendant
Polished Brass
22"W x 18"H
6 x 40w CA Bulbs
1 x 50w MB R20 Bulb



90328CLPB 6-Light Pendant
Polished Brass
17.5"W x 16"H
5 x 40w CA Bulbs
1 x 50w MB R20 Bulb



90330CLPB 7-Light Pendant
Polished Brass
23"W x 17"H
6 x 40w CA Bulbs
1 x 50w MB R20 Bulb

Super-Max Fan

Easy and quick installation makes the Super-Max fan the right choice for your ceiling fan needs.



89930OI Ceiling Fan
Oil Rubbed Bronze
52"W x 12.5"H
Maple/Walnut Blades

- Remote Control Adaptable (FCTHAND)
- Heavy Duty Motor
- Easy Install Blade Holders
- Fan Installation in Less than 5 Minutes
- Light Kit Adaptable
- Reversible Wood Blades



89930SN Ceiling Fan
Satin Nickel
52"W x 12.5"H
Espresso/Brushed Nickel Blades

800.486.2946

maximlighting.com

Basic-Max Fan

The Basic-Max Fan features the ability to be installed three different ways: close mount, standard stem, and optional stems up to 72" long.

- Remote Control Adaptable (FCTHAND)
- Light Kit Adaptable
- Reversible Blades
- 3 Speeds with Reverse



89905SN Ceiling Fan
Satin Nickel
52"W x 12.5"H
Silver/Natural Blades



89905MW Ceiling Fan
Matte White
52"W x 12.5"H
White/White Blades
Light kit optional



89905OI Ceiling Fan
Oil Rubbed Bronze
52"W x 12.5"H
Light Oak/Medium Oak Blades

800.486.2946

maximlighting.com

Basic-Max Outdoor Fan

Basic-Max Outdoor Fan Our Basic-Max Outdoor Fans are wet rated and can be exposed directly to rain. They are not only great for outdoor patios, but can also be installed under a gazebo, lanai or a patio that is only partially covered.

89915OI Outdoor Ceiling Fan
Oil Rubbed Bronze
52"W x 12.5"H
Oil Rubbed Bronze Blades



- Remote Control Adaptable (FCTHAND)
- Suitable for Wet Location
- A.B.S. Blades
- Light Kit Adaptable*

* Use Light Kit FKT206OI for Damp Location Installation

Remote Control

The optional Ceiling Fan Remote Control is compatible with our Super-Max, Basic-Max and Basic-Max Outdoor Fan Collections. Controls include the ability to change fan speed and turn on/off optional installed light kit.



FCTHAND

Ceiling Fan Hand-Held Remote Control
Control Fan Speed and Optional Light Kits

800.486.2946

maximlighting.com

Basic-Max Downrods

Our Basic-Max Fan Downrods give you the versatility you need when installing your Basic-Max fan in a room with high ceilings.

Ceiling Height	Downrod Length
10'	12"
11'	18"
12'	24"
13'	36"
14'	48"
15'	60"
16'	72"

For Basic-Max Fans with Light Kits installed, reduce the length of the downrod by 12". Longer downrods are available on special order.

800.486.2946

maximlighting.com

FRD12 OI, SN, MW

12" Ceiling Fan Down Rod
.75"W x 12"L

Compatible with Basic-Max Fan Collection

FRD18 OI, SN, MW

18" Ceiling Fan Down Rod
.75"W x 18"L

Compatible with Basic-Max Fan Collection

FRD24 OI, SN, MW

24" Ceiling Fan Down Rod
.75"W x 24"L

Compatible with Basic-Max Fan Collection

FRD36 OI, SN, MW

36" Ceiling Fan Down Rod
.75"W x 36"L

Compatible with Basic-Max Fan Collection

FRD48 OI, SN, MW

48" Ceiling Fan Down Rod
.75"W x 48"L

Compatible with Basic-Max Fan Collection

FRD60 OI, SN, MW

60" Ceiling Fan Down Rod
.75"W x 60"L

Compatible with Basic-Max Fan Collection

FRD72 OI, SN, MW

72" Ceiling Fan Down Rod
.75"W x 72"L

Compatible with Basic-Max Fan Collection

Light Kits

Ceiling Fan light kits can add both functionality and beauty to our line of Basic-Max, Basic-Max Outdoor and Super-max Fans, and are available in a variety of shapes and designs.



FKT206 MW, OI, SN
1-Light Outdoor Fan Kit
7"W
1 x 60w CABulb
*Damp Location Rated White Glass
Pull Chain Switch*



FKT205 MW, OI, SN
2-Light Fan Kit
13"W
2 x 60w CABulbs
Pull Chain Switch



FKT207 MW, OI, SN
3-Light Fan Kit
3 x 60w CABulbs
Pull Chain Switch

800.486.2946

maximlighting.com

FKT2012WSOI



FKT2012ICSN



FKT2012 ICSN, WSOI
3-Light Fan Kit
14"W x 7"H
3 x 60w CABulbs



FKT2341AIOI
2-Light Fan Kit
Oil Rubbed Bronze
12"W x 6.5"H
3 x 60w CABulbs

FKT2210AIOI



FKT2210CISN



FKT2210 CISN, AIOI
3-Light Fan Kit
13.5"W x 7.5"H
3 x 60w CABulbs



Energy Saving Collections

MAXIM LIGHTING®

Those committed to preserving the world's natural resources appreciate Maxim's contemporary line of energy efficient lighting. Designed with conservation in mind, the Energy-Saving collection blends visionary ideals with practical action. Through efficient bulbs that minimize watt usage and innovative designs that optimize utilization, Maxim allows homeowners to go green without sacrificing style.

Illuminare

State of the art LED flush mount fixtures which can be installed on the ceiling or wall feature metal bases finished in Satin Nickel and heavy spun Frost glass shades. The light source incorporates LED technology featuring .075 watt diodes mounted on a circuit board. These boards have 50,000+ hour life expectancy and are replaceable.

- 50,000 Rated Life Hours
- 3000K Color Temperature
- Ceiling or Wall Mountable



53034FTSN
Satin Nickel
5"W x 2.5"H
6 Watts
500 Rated Lumens



53035FTSN
Satin Nickel
7.5"W x 3"H
10.5 Watts
900 Rated Lumens



53036FTSN
Satin Nickel
9"W x 3"H
15 Watts
1200 Rated Lumens

53030FTSN
Satin Nickel
6"D x 2.5"H
6 Watts
500 Rated Lumens



The LED Difference

- 90% Less power consumption than incandescent
- 30% Less power consumption than fluorescent
- Lasts 80 times longer than incandescent
- Lasts over 6 times longer than fluorescent
- Less maintenance costs
- Less environmental impact

53031FTSN
Satin Nickel
9"D x 3"H
10.5 Watts
900 Rated Lumens



53032FTSN
Satin Nickel
11"D x 3"H
15 Watts
1200 Rated Lumens



Basix ES

Contemporary collection with sweeping arms and clean lines. Offered in Ice glass and Satin Nickel finish and now available in a Energy Star fluorescent version.

- *Electronic NPF Ballast*
- *2700K Color Temperature*
- *10,000 Rated Life Hours*



851281CSN 9-Light Chandelier
Satin Nickel
32"W x 31.5"H
9 x 13w GU24 Bulbs (Included)
7200 Rated Lumens



800.486.2946

maximlighting.com




851251CSN 5-Light Chandelier
Satin Nickel
25"W x 21"H
5 x 13w GU24 Bulbs (Included)
4000 Rated Lumens

CA 
T24



85120ICSN 2-Light Semi-Flush
Satin Nickel
14"W x 10"H
2 x 13w GU24 Bulbs (Included)
1600 Rated Lumens



85139ICSN 1-Light Mini Pendant
Satin Nickel
6.5"W
1 x 13w GU24 Bulb (Included)
800 Rated Lumens
Additional stems available:
6" order STR06206SN
12" order STR06212SN
One 6" stem and
three 12" stems included.



85121ICSN 3-Light Pendant
Satin Nickel
17"W x 22.5"H
3 x 13w GU24 Bulbs (Included)
2400 Rated Lumens





85131ICSN 1-Light Wall Sconce
 Satin Nickel
 6"W x 8"H x 9" Ext.
 1 x 13w GU24 Bulb (Included)
 800 Rated Lumens



85132ICSN 2-Light Bath Vanity
 Satin Nickel
 13.5"W x 8"H x 9" Ext.
 2 x 13w GU24 Bulbs (Included)
 1600 Rated Lumens



85133ICSN 3-Light Bath Vanity
 Satin Nickel
 19"W x 8"H x 9" Ext.
 3 x 13w GU24 Bulbs (Included)
 2400 Rated Lumens



85134ICSN 4-Light Bath Vanity
 Satin Nickel
 27.5"W x 8"H x 9" Ext.
 4 x 13w GU24 Bulbs (Included)
 3200 Rated Lumens



Linda ES

A beautiful transitional energy saving collection with long flowing arms. Warm Wilshire glass perfectly complements the Oil Rubbed Bronze finish.

- *Electronic NPF Ballast*
- *2700K Color Temperature*
- *10,000 Rated Life Hours*



85806WSOI 9-Light Chandelier
Oil Rubbed Bronze
31.5"W x 36"H
9 x 13w GU24 Bulbs (Included)
7200 Rated Lumens



800.486.2946

maximlighting.com



85800WSOI 2-Light Flush Mount
Oil Rubbed Bronze
13"W x 7"H
2 x 13w GU24 Bulbs (Included)
1600 Rated Lumens



85801WSOI 3-Light Flush Mount
Oil Rubbed Bronze
16"W x 9"H
3 x 13w GU24 Bulbs (Included)
2400 Rated Lumens



85805WSOI 5-Light Chandelier
Oil Rubbed Bronze
23.5"W x 27"H
5 x 13w GU24 Bulbs (Included)
4000 Rated Lumens





85802WSOI 3-Light Semi-Flush
Oil Rubbed Bronze
19"W x 16.5"H
3 x 13w GU24 Bulbs (Included)
2400 Rated Lumens

CA
T24



85803WSOI 4-Light Pendant
Oil Rubbed Bronze
25"W x 31"H
4 x 13w GU24 Bulbs (Included)
3200 Rated Lumens

CA
T24



85804WSOI 3-Light Chandelier
Oil Rubbed Bronze
16.5"W x 23.5"H
3 x 13w GU24 Bulbs (Included)
2400 Rated Lumens

CA
T24




85810WSOI 4-Light Bath Vanity
Oil Rubbed Bronze
32"W x 9"H x 8"Ext.
4 x 13w GU24 Bulbs (Included)
3200 Rated Lumens

CA T24  



85809WSOI 3-Light Bath Vanity
Oil Rubbed Bronze
24"W x 9"H x 8"Ext.
3 x 13w GU24 Bulbs (Included)
2400 Rated Lumens

CA T24  



85004WSOI
1-Light Mini Pendant
Oil Rubbed Bronze
6"W
1 x 13w GU24 Bulb (Included)
800 Rated Lumens
Additional stems available:
6" order STR06206OI
12" order STR06212OI

CA T24  



85808WSOI 2-Light Bath Vanity
Oil Rubbed Bronze
14.5"W x 8.5"H x 9"Ext.
2 x 13w GU24 Bulbs (Included)
1600 Rated Lumens

CA T24  




85807WSOI 1-Light Wall Sconce
Oil Rubbed Bronze
6"W x 9.5"H x 7.5"Ext.
1 x 13w GU24 Bulb (Included)
800 Rated Lumens

CA T24  


Energy Saving Flush Mounts

- *Electronic NPF Ballast*
- *2700K Color Temperature*
- *10,000 Rated Life Hours*




85830 FTTW, FTPB
 1-Light Flush Mount
 11.5"W x 6"H
 1 x 13w GU24 Bulb (Included)
 800 Rated Lumens
 CA T24 




85840 MROI, MRSN, WSOI
 1-Light Flush Mount
 11.5"W x 6"H
 1 x 13w GU24 Bulb (Included)
 800 Rated Lumens
 CA T24 




85831 FTTW, FTPB
 2-Light Flush Mount
 13.5"W x 6"H
 2 x 13w GU24 Bulbs (Included)
 1600 Rated Lumens
 CA T24 




85841 MROI, MRSN, WSOI
 2-Light Flush Mount
 13.5"W x 6"H
 2 x 13w GU24 Bulbs (Included)
 1600 Rated Lumens
 CA T24 



85832 FTTW, FTPB
 3-Light Flush Mount
 15.5"W x 6"H
 3 x 13w GU24 Bulbs (Included)
 2400 Rated Lumens
 CA T24 




85842 MROI, MRSN, WSOI
 3-Light Flush Mount
 15.5"W x 6"H
 3 x 13w GU24 Bulbs (Included)
 2400 Rated Lumens
 CA T24 


800.486.2946

maximlighting.com




82681MRSN 3-Light Flush Mount
Satin Nickel
16"W x 4"H
3 x 13w GU24 Bulbs (Included)
2400 Rated Lumens
CA T24 




85880WTWT
1-Light Flush Mount
White
7.5"W x 4.5"H
1 x 13w GU24 Bulb (Included)
800 Rated Lumens
CA T24 



85881WTWT
2-Light Flush Mount
White
9"W x 5"H
2 x 13w GU24 Bulbs (Included)
1600 Rated Lumens
CA T24 



85889WTWT
1-Light Flush Mount
White
6"W x 7"H
1 x 13w GU24 Bulb (Included)
800 Rated Lumens
CA T24 

Flair ES

- *Electronic NPF Ballast*
- *2700K Color Temperature*
- *10,000 Rated Life Hours*



87951 MROI, MRSN, MRTW
2-Light Flush Mount
14"W x 5"H
2 x 13w GU24 Bulbs (Included)
1600 Rated Lumens



800.486.2946



MRTW



87952 MROI, MRSN, MRTW
3-Light Flush Mount
17"W x 5"H
3 x 13w GU24 Bulbs (Included)
2400 Rated Lumens



maximlighting.com

- T-5 High Lumen Technology
- 3000K Color Temperature
- 10,000 Rated Life Hours
- Acrylic Lens

Classic ES



87015 SN, WT
 1-Light Flush Mount
 14"W x 4"H
 1 x 22w T5 Circline Bulb (Included)
 1339 Rated Lumens
 Electronic HPF ballast



87016 SN, WT
 2-Light Flush Mount
 17"W x 4"H
 1 x 22w T5 Circline Bulb (Included)
 1 x 32w T5 Circline Bulb (Included)
 3761 Rated Lumens
 Electronic HPF ballast



87017 SN, WT
 2-Light Flush Mount
 22.5"W x 4"H
 1 x 32w T5 Circline Bulb (Included)
 1 x 40w T5 Circline Bulb (Included)
 5249 Rated Lumens
 Electronic NPF ballast



800.486.2946

maximlighting.com

Rim ES

- 3100K Color Temperature
- 10,000 Rated Life Hours
- Acrylic Lens



87210 OI,SN,WT
1-Light Flush Mount
13"W x 3"H
1 x 22w T9 Circline Bulb (Included)
1040 Rated Lumens
Electronic HPF Ballast
CA T24



87211 OI,SN,WT
2-Light Flush Mount
17"W x 3"H
1 x 22w T9 Circline Bulb (Included)
1 x 32w T9 Circline Bulb (Included)
2980 Rated Lumens
Electronic HPF Ballast
CA T24



87212 OI,SN,WT
2-Light Flush Mount
21"W x 3"H
1 x 32w T9 Circline Bulb (Included)
1 x 40w T9 Circline Bulb (Included)
3675 Rated Lumens
Electronic NPF Ballast
CA T24

800.486.2946

maximlighting.com

Rim Plus ES

- T-5 High Lumen Technology
- 3000K Color Temperature
- 10,000 Rated Life Hours
- Acrylic Lens



87011 OI,SN,WT
2-Light Flush Mount
17"W x 3"H
1 x 22w T5 Circline Bulb (Included)
1 x 32w T5 Circline Bulb (Included)
3761 Rated Lumens
Electronic HPF Ballast



87012 OI,SN,WT
2-Light Flush Mount
21"W x 3"H
1 x 32w T5 Circline Bulb (Included)
1 x 40w T5 Circline Bulb (Included)
5249 Rated Lumens
Electronic NPF Ballast



800.486.2946

maximlighting.com

Low Profile ES

- Slim 2.5" Profile
- No Flicker Ballast
- 3100K Color Temperature
- 10,000 Rated Life Hours
- UV Rated Acrylic Lens
- Ceiling or Wall Mountable



87200WT 1-Light Flush Mount
White
11.5"W x 2.5"H
1 x 22w T9 Circline Bulb (Included)
1040 Rated Lumens
Electronic HPF Ballast
For residential use only



87207WT 2-Light Wall Sconce
White
19.5"W x 2.5"H
1 x 32w T9 Circline Bulb (Included)
1 x 40w T9 Circline Bulb (Included)
3675 Rated Lumens
Electronic NPF Ballast



87201WT 2-Light Flush Mount
White
14"W x 2.5"H
1 x 22w T9 Circline Bulb (Included)
1 x 32w T9 Circline Bulb (Included)
2980 Rated Lumens
Electronic HPF Ballast
For residential use only



87206WT 2-Light Wall Sconce
White
14.5"W x 2.5"H
1 x 22w T9 Circline Bulb (Included)
1 x 32w T9 Circline Bulb (Included)
2980 Rated Lumens
Electronic HPF Ballast



87202WT 2-Light Flush Mount
White
19"W x 2.5"H
1 x 32w T9 Circline Bulb (Included)
1 x 40w T9 Circline Bulb (Included)
3675 Rated Lumens
Electronic HPF Ballast
For residential use only



87205WT 1-Light Wall Sconce
White
12"W x 2.5"H
1 x 22w T9 Circline Bulb (Included)
1040 Rated Lumens
Electronic HPF Ballast



Low Profile Plus ES

- T-5 High Lumen Technology
- Slim 2.5" Profile
- No Flicker Ballast
- 3000K Color Temperature
- 10,000 Rated Life Hours
- UV Rated Acrylic Lens
- Ceiling or Wall Mountable



87005WT 1-Light Wall Sconce
White
12"W x 2.5"H
1 x 22w T5 Circline Bulb (Included)
1335 Rated Lumens
Electronic HPF Ballast



87006WT 2-Light Wall Sconce
White
14.5"W x 2.5"H
1 x 22w T5 Circline Bulb (Included)
1 x 32w T5 Circline Bulb (Included)
3761 Rated Lumens
Electronic HPF Ballast



87007WT 2-Light Wall Sconce
White
19.5"W x 2.5"H
1 x 32w T5 Circline Bulb (Included)
1 x 40w T5 Circline Bulb (Included)
5249 Rated Lumens
Electronic NPF Ballast



800.486.2946

maximlighting.com

Wrap Around ES

- *Electronic Ballast*
- *24,000 Rated Life Hours*
- *Acrylic Lens*
- *Bulbs Not Included*



87520WT 2-Light Flush Mount
White
25"L x 8.5"W x 2.5"H
2 x 17w T8 Bulbs
1400 Rated Lumens



87521WT 2-Light Flush Mount
White
49"L x 8.5"W x 2.5"H
2 x 32w T8 Bulbs
5200 Rated Lumens



87522WT 4-Light Flush Mount
White
48"L x 14"W x 2.75"H
4 x 32w T8 Bulbs
10400 Rated Lumens

800.486.2946


maximlighting.com

Cloud ES

- *Electronic Ballast*
- *24,000 Rated Life Hours*
- *Acrylic Lens*
- *Bulbs Not Included*



87530WT 2-Light Flush Mount
White
48"L x 7"W x 3.25"H
2 x 32w T8 Bulbs
5200 Rated Lumens



87531WT 4-Light Flush Mount
White
48"L x 12.5"W x 4"H
4 x 32w T8 Bulbs
10400 Rated Lumens

800.486.2946

maximlighting.com

Luna ES

- *Electronic Ballast*
- *2700K Color Temperature*
- *10,000 Rated Life Hours*
- *Suitable for Damp Location*



85217WTBM 2-Light Flush Mount
Brushed Metal
11"W x 5"H
2 x 13w GU24 Bulbs (Included)
1600 Rated Lumens



85222WTNI 2-Light Flush Mount
Natural Iron
10"W x 5"H
2 x 13w GU24 Bulbs (Included)
1600 Rated Lumens

800.486.2946



85216WTBM 2-Light Wall Sconce
Brushed Metal
9"W x 21"H x 4"Ext.
2 x 13w GU24 Bulbs (Included)
1600 Rated Lumens



85215WTBM 1-Light Wall Sconce
Brushed Metal
9"W x 12"H x 4"Ext.
1 x 13w GU24 Bulb (Included)
800 Rated Lumens

maximlighting.com



85213WTBM 1-Light Pendant
 Brushed Metal
 7.5"W x 15"H
 1 x 18w GU24 Bulb (Included)
 1100 Rated Lumens



85214WTBM 1-Light Pendant
 Brushed Metal
 9.5"W x 22.5"H
 1 x 26w GU24 Bulb (Included)
 1680 Rated Lumens



85218WSOI 1-Light Wall Sconce
 Oil Rubbed Bronze
 7"W x 12"H x 4"Ext.
 1 x 13w GU24 Bulb (Included)
 800 Rated Lumens



85219WSOI 2-Light Wall Sconce
 Oil Rubbed Bronze
 7"W x 21"H x 4"Ext.
 2 x 13w GU24 Bulbs (Included)
 1600 Rated Lumens

Energy Saving Mini Pendant and Wall Sconce

- *Electronic NPF ballast*
- *2700K Color Temperature*
- *10,000 Rated Life Hours*



85585 MRWT, WTWT
1-Light Wall Sconce
10.5"W x 5.5"H x 4"Ext.
1 x 13w GU24 Bulb (Included)
800 Rated Lumens



85066MRSN
1-Light Mini Pendant
Satin Nickel
7"W
1 x 13w GU24 Bulb (Included)
800 Rated Lumens
One 6" Stem STR06206SN (Included)
Three 12" Stems STR06212SN (Included)



800.486.2946

maximlighting.com



Counter & Task Lighting

MAXIM  LIGHTING®

Maxim Lighting's full line of under cabinet and task lighting cast the perfect light throughout the home. In kitchens, granite countertops sparkle under the direct beam and food preparation becomes safer and more enjoyable. In bathrooms and studies, they brighten the room with a warm indirect glow. They even eliminate unwanted shadows in wet bars, curio cabinets, and bookcases with sleek profiles that conceal so discreetly you will never see the source of the gentle light.

MX-L Series **COUNTERMAX™** LED Under Cabinet Lighting

This state-of-the-art LED light bar raises under cabinet lighting to a whole new level. The crisp white light illuminates without shadows, and its direct wire plug in and easy clip installation make it convenient as well as beautiful.



30" LED Light Kit

87906WT White
87906SA Satin Aluminum
87906MB Bronze
 28.5"L x 2"W x 1"H
 6 x 1w

*Includes connector cord,
 coupler and direct wire box*



20" LED Light Kit

87904WT White
87904SA Satin Aluminum
87904MB Bronze
 19.125"L x 2"W x 1"H
 4 x 1w

*Includes connector cord,
 coupler and direct wire box*



10" LED Light Kit

87902WT White
87902SA Satin Aluminum
87902MB Bronze
 9.75"L x 2"W x 1"H
 2 x 1w

*Includes connector cord,
 coupler and direct wire box*



MXInterLink2 Direct Wire Box

87803WT White
87803BK Black
 4"W x 2"L x 1"H



MXInterLink2 Connector Cord

18" **87819WT** White
 18" **87819BK** Black
 9" **87818WT** White
 9" **87818BK** Black



MXInterLink2 Coupler

87820WT White
87820BK Black
 2"W x .5"L x .375"H



MXInterLink2 Power Cord

87817WT White
87817BK Black
 72"

800.486.2946

maximlighting.com

COUNTERMAX™

MX-L120 Series LED Under Cabinet Lighting

FEATURES

- Warm white 3000K light
- Cool to touch
- CRI 70-75, 120° beam spread
- 50,000 life hours
- Multiple, full size knock outs
- 4-Way dimming switch, Hi-Med-Low-Off
- Linkable with or without cords using MXInterLink3

With a sleek profile and direct wiring, this state-of-the-art direct wire unit installs easily under the cabinet and emits a crisp white light which illuminates without shadows. The hinged top gives easy access for installation and wiring. Cabinets stay cool and safe with LED light output.



7" 2-Light LED Direct Wire
87912WT White
87912MB Bronze
 7"L x 5"W x 1.25"H
 2 x 1W



13" 4-Light LED Direct Wire
87913WT White
87913MB Bronze
 12.875"L x 5"W x 1.25"H
 4 x 1W



21" 6-Light LED Direct Wire
87914WT White
87914MB Bronze
 21"L x 5"W x 1.25"H
 6 x 1W



30" 8-Light LED Direct Wire
87916WT White
87916MB Bronze
 30"L x 5"W x 1.25"H
 8 x 1W



MXInterLink3 Direct Wire Box
87850WT White
87850BK Black
 2.25"L x 5"W x 1"H



MXInterLink3 Connector Cord
 9" **87856WT** White 18" **87857WT** White
 9" **87856BK** Black 18" **87857BK** Black
 24" **87858WT** White
 24" **87858BK** Black



MXInterLink3 Power Cord
87860WT White
87860BK Black
 72"L

800.486.2946

maximlighting.com

MX-LD Series LED Discs

The CounterMax MX-LD Series LED discs mount easily under any cabinet and can link up to 30 discs without additional hardware using MXInterLink2. The energy efficient LED disc uses only 1.7 watts, requires no additional driver, and stays cool to the touch marking it safer than both halogen and xenon. The warm white color lasts long and compliments any room.

COUNTERMAX™



1-Light Disc Add On

87881WT White
87881SV Silver
87881BK Black
 3.125"W x .875"H
 1 x 1.7 w

Includes one 18" connector cord and Installation Hardware



MXInterLink2 Connector Cord

18" **87819WT** White
 18" **87819BK** Black
 9" **87818WT** White
 9" **87818BK** Black



MXInterLink2 Direct Wire Box

87803WT White
87803BK Black
 4"W x 2"L x 1"H



MXInterLink2 Coupler

87820WT White
87820BK Black
 2"W x .5"L x .375"H

800.486.2946

maximlighting.com



Silver



Black



White



3-Light Disc Kit

87883WT White
87883SV Silver
87883BK Black
 5.1w Total

*Includes On/Off switch
 two 18" connector cords
 and one 72" power cord*

MX-X12 Series Starter Kits 12V Xenon Under Cabinet Lighting

This ultra low-profile design conceals long-lasting, low-voltage Xenon bulbs that distribute a crisp bright light. Hinged tops allow for convenient bulb replacement, and push-in wire connectors in the junction box make either direct wire or plug-in installation quick and simple.



MXInterLink3 Direct Wire Box
87850WT White
87850BK Black
 2.25"L x 5"W x 1"H



MXInterLink3 Connector Cord
 24" **87858WT** White
 24" **87858BK** Black
 18" **87857WT** White
 18" **87857BK** Black
 9" **87856WT** White
 9" **87856BK** Black



MXInterLink3 Power Cord
87860WT White
87860BK Black
 72"L



7" 1-Light 12V Xenon Starter Kit
87849WT White
87849MB Bronze
 7"L x 5"W x 1.125"H
 1 x 18w Xenon Bulb (Included)
Includes one direct wire box and one 18" connector cord



13" 2-Light 12V Xenon Starter Kit
87851WT White
87851MB Bronze
 12.875"L x 5"W x 1.125"H
 2 x 18w Xenon Bulb (Included)
Includes one direct wire box and one 18" connector cord

21" 3-Light 12V Xenon Starter Kit
87852WT White
87852MB Bronze
 21"L x 5"W x 1.125"H
 3 x 18w Xenon Bulb (Included)
Includes one direct wire box and one 18" connector cord

30" 4-Light 12V Xenon Starter Kit
87853WT White
87853MB Bronze
 30"L x 5"W x 1.125"H
 4 x 18w Xenon Bulb (Included)
Includes one direct wire box and one 18" connector cord

800.486.2946

maximlighting.com

MX-X12 Series Add-Ons

12V Xenon Under Cabinet Lighting

COUNTERMAX™

This ultra low-profile design conceals long-lasting, low-voltage Xelogen bulbs that distribute a crisp bright light. Hinged tops allow for convenient bulb replacement, and push-in wire connectors in the junction box make either direct wire or plug-in installation quick and simple.



7" 1-Light 12V Xenon Add-On
87859WT White
87859MB Bronze
7"L x 5"W x 1.125"H
1 x 18w Xenon Bulb (Included)



13" 2-Light 12V Xenon Add-On
87861WT White
87861MB Bronze
12.875"L x 5"W x 1.125"H
2 x 18w Xenon Bulb (Included)



21" 3-Light 12V Xenon Add-On
87862WT White
87862MB Bronze
21"L x 5"W x 1.125"H
3 x 18w Xenon Bulb (Included)



30" 4-Light 12V Xenon Add-On
87863WT White
87863MB Bronze
30"L x 5"W x 1.125"H
4 x 18w Xenon Bulb (Included)

800.486.2946

maximlighting.com

MX-X120 Series 120V Xenon Under Cabinet Lighting

With a sleek profile and direct wiring, this unit installs easily under the cabinet and emits a warm light.

The hinged top gives easy access to the long-lasting Xenon bulbs and wiring. Cabinets stay cool and safe due to the unique airflow design that limits heat transfer.

7" 1-Light 120V Xenon

87830WT White

87830MB Bronze

7"L x 5"W x 1.25"H

1 x 20w Xenon Bulb (Included)

13" 2-Light 120V Xenon

87831WT White

87831MB Bronze

12.875"L x 5"W x 1.25"H

2 x 20w Xenon Bulb (Included)

30" 4-Light 120V Xenon

87833WT White

87833MB Bronze

30"L x 5"W x 1.25"H

4 x 20w Xenon Bulb (Included)

21" 3-Light 120V Xenon

87832WT White

87832MB Bronze

21"L x 5"W x 1.25"H

3 x 20w Xenon Bulb (Included)

40" 5-Light 120V Xenon

87834WT White

87834MB Bronze

40"L x 5"W x 1.25"H

5 x 20w Xenon Bulb (Included)




MX-FD Series


COUNTERMAX™

Direct Wire Fluorescent Undercabinet Lighting


This direct wire collection of fluorescent under cabinet lights boasts T-5 high lumen technology in sizes from 12" to 43" in length. Full size knock outs allow for easy installation in any application.




43" 1-Light Fluorescent
87809WT White
43"L x 5"W x 1.25"H
1 F26 T5 (Included) /
2700 Lumens / 7,500 Hours




12" 1-Light Fluorescent
87805WT White
12"L x 5"W x 1.25"H
1 F8 T5 (Included) / 400 Lumens / 6,000 Hours



21" 1-Light Fluorescent
87806WT White
21"L x 5"W x 1.25"H
1 F13 T5 (Included) / 870 Lumens / 7,500 Hours



24" 1-Light Fluorescent
87807WT White
24"L x 5"W x 1.25"H
1 F16 T5 (Included) / 1360 Lumens / 7,500 Hours



35" 1-Light Fluorescent
87808WT White
35"L x 5"W x 1.25"H
1 F21 T5 (Included) / 2100 Lumens / 7,500 Hours

800.486.2946

maximlighting.com

Series Details

Series	Item	Description	Type	Install	Bulb	Fixture Wattage	Fixture Lumens	Color Temp	Avg Life Hours	Maxim Bulb tem
MX-L Series	87902	10"Under Cabinet	LED	CP2, DW2, IL2	N/A	2	160	3000K	50,000	N/A
	87904	20"Under Cabinet	LED	CP2, DW2, IL2	N/A	4	320	3000K	50,000	N/A
	87906	30"Under Cabinet	LED	CP2, DW2, IL2	N/A	6	480	3000K	50,000	N/A
MX-L120 Series	87912	7"Under Cabinet	LED	DW	N/A	2	160	3000K	50,000	N/A
	87913	13"Under Cabinet	LED	DW	N/A	4	320	3000K	50,000	N/A
	87914	21"Under Cabinet	LED	DW	N/A	6	480	3000K	50,000	N/A
	87916	30"Under Cabinet	LED	DW	N/A	8	640	3000K	50,000	N/A
MX-LD Series	87883	Set of Three 3"Discs	LED	CP2, DW2, IL2	N/A	5.1	390	3500K	30,000	N/A
	87881	Add On 3"Disc	LED	CP2, DW2, IL2	N/A	1.7	130	3500K	30,000	N/A
MX-X12 Series	87849	7"Under Cabinet Kit	Xenon	CP3, DW3, IL3	Xelogen Wedge	18	264	2800K	10,000	BUX20023
	87851	13"Under Cabinet Kit	Xenon	CP3, DW3, IL3	Xelogen Wedge	36	528	2800K	10,000	BUX20023
	87852	21"Under Cabinet Kit	Xenon	CP3, DW3, IL3	Xelogen Wedge	54	792	2800K	10,000	BUX20023
	87853	30"Under Cabinet Kit	Xenon	CP3, DW3, IL3	Xelogen Wedge	72	1056	2800K	10,000	BUX20023
	87859	7"Under Cabinet	Xenon	CP3, DW3, IL3	Xelogen Wedge	18	264	2800K	10,000	BUX20023
	87861	13"Under Cabinet	Xenon	CP3, DW3, IL3	Xelogen Wedge	36	528	2800K	10,000	BUX20023
	87862	21"Under Cabinet	Xenon	CP3, DW3, IL3	Xelogen Wedge	54	792	2800K	10,000	BUX20023
	87863	30"Under Cabinet	Xenon	CP3, DW3, IL3	Xelogen Wedge	72	1056	2800K	10,000	BUX20023
MX-X120 Series	87830	7"Under Cabinet	Xenon	DW	Bi-Pin	20	225	2900K	3,500	BUX20016
	87831	13"Under Cabinet	Xenon	DW	Bi-Pin	40	450	2900K	3,500	BUX20016
	87832	21"Under Cabinet	Xenon	DW	Bi-Pin	60	675	2900K	3,500	BUX20016
	87833	30"Under Cabinet	Xenon	DW	Bi-Pin	80	900	2900K	3,500	BUX20016
	87834	40"Under Cabinet	Xenon	DW	Bi-Pin	100	1125	2900K	3,500	BUX20016
MX-FD Series	87805	12"Under Cabinet	Fluorescent	DW	F8 T5	8	400	3100K	6,000	BUFT508011
	87806	21"Under Cabinet	Fluorescent	DW	F13 T5	13	870	3100K	7,500	BUFT513012
	87807	24"Under Cabinet	Fluorescent	DW	F16 T5	16	1360	3100K	7,600	BUFT516013
	87808	35"Under Cabinet	Fluorescent	DW	F21 T5	21	2100	3100K	7,600	BUFT521014
	87809	43"Under Cabinet	Fluorescent	DW	F26 T5	26	2700	3100K	7,500	BUFT526015

Cord and Plug

CP - Cord/Plug
 CP2 - MXInterLink2 Cord/Plug
 CP3 - MXInterLink3 Cord/Plug

Direct Wire

DW - Direct Wire
 DW2 - MXInterLink2 Direct Wire Box
 DW3 - MXInterLink3 Direct Wire Box

Link Connector

IL2 - MXInterLink2 Connector Cord
 IL3 - MXInterLink3 Connector Cord

Basic Star

STARSTRAND™


The most economical way to illuminate with LED, StarStrand™ Basic Star comes on a convenient reel and can be easily cut every two inches as needed.

A soldered power connector on the end of each reel, two additional power feeds, and a splicer for joining sections together round out the standard model, and additional power feeds and splicer are available. The minimum single run for Basic Star is 1' and the maximum is 33' (*Driver Requirements on Page 377*).

The copper PC board is backed with an adhesive 3M tape for easy installation.




Model	Length	Diodes	Wattage	Lumens	Color Temp	CRI	PC Board	Beam	Current
53200	16 ft. 4 in.	300	24	1350	3500K	70-75	Copper	120°	20mA



800.486.2946



Backed with 3M Tape for easy installation



Markings for ease of cutting



Cutable every 2 inches



Basic Star comes on a reel



maximlighting.com

STARSTRAND™



60w Indoor Plug-In Driver 53275


- 120V/240V Input | 12V Output
- Includes one 72" output cord and one 72" powercord

Power Cord with On/Off Switch 53252



3' Aluminum Channel 53254

- Creates valance to conceal tape
- Irregular surfaces installation
- Includes screws for installation



75w Indoor DirectWire Driver 53276

- 120V/240V Input | 12V Output
- Includes one 72" output cord



Silicone End Cap 53269

- Placed on run termination
- Protects against dust and damage
- Package of 10



Indoor Dimming Controller 53282

- Full range dimming & On/Off control
- RF remote control included
- 140w Max

Replacement Remote 53292



End Power Feed 53260

- Required if ends is cut
- Package of 6
- Two included with 53200



Tape Splicer 53261

- Joins two sections if tape is cut
- Package of 10
- One included with 53200



Flexible Connector 53259

- Use for corners and angles
- Package of 6



Indoor Connecting Cords

53265 3"
53266 7"
53267 13"
53268 73"

- Extend distance between driver and tape
- Connect sections of tape together



Plastic Wire Clip 53255

- Used to secure Connecting Cords & driver output cords to surface
- Backed with 3M Adhesive tape
- Package of 10



Male/Male Adapter 53262

- Changes female end to male
- Package of 10



Rough In Terminal Block 53257 3"

- Rough in for new installations construction
- Female connector on one end, with 4 wire quick connector on opposite end



4-Way Connector 53263

- Allows for L, T & X installations
- A power block for branching
- Includes two 53264 and one 53262



Heat Shrink Wrap 53256

- Secure connections when in walls
- Waterproof in damp location installations
- Heat gun required for installation



Male End Cap 53264

- Use on female end of run termination
- Protects against dust and damage
- Package of 10

Super Star


STARSTRAND™

With over twice the lumen output of the basic tape, and the added benefit of it being covered in a pliable clear plastic, StarStrand™ Super Star, with StarChip™ technology, excels in performance and durability. The plastic cover keeps dust and dirt from landing directly on the board and makes keeping it clean easy. Super Star is available in pre-manufactured lengths with 4 pin connectors installed at each end for fast and sure installation. The minimum single run for Super Star is 1', and the maximum run is 50' (*Driver Requirements on Page 377*). The black PC board is backed with 3M adhesive tape for easy installation.



Model	Length	Diodes	Wattage	Lumens	Color Temp	CRI	PC Board	Beam	Current
53210	2 in.	3	.48	28.5	3500K	70-75	Black	120°	40mA
53211	12 in.	18	2.88	171	3500K	70-75	Black	120°	40mA
53212	5 ft.	90	14.4	855	3500K	70-75	Black	120°	40mA
53213	10 ft.	180	28.8	1710	3500K	70-75	Black	120°	40mA
53214	20 ft.	360	57.6	3420	3500K	70-75	Black	120°	40mA

800.486.2946



FEATURES

- Laminated LED tape system
- No exposed circuit board
- Easy to install with multiple lengths to choose from
- Warm color temperature enhances room interiors
- Perfect for accent lighting in alcoves, toe-kick, and under counter
- Flexible design that forms to contours
- Safe and economical to operate
- Long life LED average 50,000 hours life
- Tested to UL standards for both US and Canada



Cuttable every 2 inches



Perfect for cove and ceiling illumination

maximlighting.com

STARSTRAND™



**60w Indoor Plug-In Driver
53275**
 • 120V/240V Input | 12V Output
 • Includes one 72" output cord and one 72" powercord
**Power Cord with On/Off Switch
53252**



**Male End Cap
53264**
 • Placed on female end of run termination
 • Protects against dust and damage
 • Package of 10



**75w Indoor DirectWire Driver
53276**
 • 120V/240V Input | 12V Output
 • Includes one 72" output cord



**3' Aluminum Channel
53254**
 • Creates valance to conceal tape
 • Irregular surfaces installation
 • Includes screws for installation



**150w Indoor DirectWire Driver
53277**
 • 120V/240V Input | 12V Output
 • Includes one 72" output cord



**Silicone End Cap
53269**
 • Placed on run termination
 • Protects against dust and damage
 • One included in 53212, 53213 & 53214
 • Package of 10



**Indoor Dimming Controller
53282**
 • Full range dimming & On/Off control
 • RF remote control included
 • 140w Max
**Replacement Remote
53292**



**Plastic Wire Clip
53255**
 • Used to secure Connecting Cords & driver output cords to surface
 • Backed with 3M Adhesive tape
 • Package of 10



Indoor Connecting Cords
53265 3"
53266 7"
53267 13"
53268 73"
 • Extend distance between driver and tape
 • Connect sections of tape together



**Mounting clip
53272**
 • Use on irregular surfaces when 3M tape is not sufficient
 • Package of 20



**Male/Male Adapter
53262**
 • Changes female end to male
 • Package of 10



**Heat Shrink Wrap
53256**
 • Secure Connections when in walls
 • Waterproof in damp location installations
 • Heat gun required for installation
 • Package of 10



**4-Way Connector
53263**
 • Allows for L, T & X installations
 • A power block for branching
 • Includes two 53264 and one 53262



**Rough In Terminal Block
53257 3"**
 • Rough in for new installations construction
 • Female connector on one end, with 4 wire quick connector on opposite end

Ultra Star


STARSTRAND™

StarStrand™ Ultra Star, with StarChip™ technology, is for applications requiring additional light output. Ultra Star produces over 3 times the lumens of Basic Star and 50% more than Super Star. This product is also covered with a pliable plastic and features an easy to install 3M tape backed unique white PC board for ultimate light reflection. Ultra Star is available in pre-manufactured lengths with 4 pin connectors installed at each end for fast and sure installation. The minimum single run for Ultra Star is 1' and the maximum run is 32' (*Driver Requirements on Page 377*).



Model	Length	Diodes	Wattage	Lumens	Color Temp	CRI	PC Board	Beam	Current
53220	2 in.	3	.72	45	3500K	70-75	White	120°	60mA
53221	12 in.	18	4.32	270	3500K	70-75	White	120°	60mA
53224	18 in.	27	6.48	405	3500K	70-75	White	120°	60mA
53222	5 ft.	90	21.6	1350	3500K	70-75	White	120°	60mA
53223	10 ft.	180	43.2	2700	3500K	70-75	White	120°	60mA

800.486.2946



FEATURES

- High lumen laminated LED tape system
- No exposed circuit board
- Easy to install with multiple lengths to choose from
- Warm color temperature enhances room interiors
- Perfect for task applications in under counter, and general room illumination
- Flexible design that forms to contours
- Safe and economical to operate
- Long life LED average 50,000 hours life
- Tested to UL standards for both US and Canada



Cuttable every 2 inches

maximlighting.com

STARSTRAND™



60w Indoor Plug-In Driver 53275

- 120V/240V Input | 12V Output
 - Includes one 72" output cord and one 72" powercord
- ### Power Cord with On/Off Switch 53252



Male End Cap 53264

- Placed on female end of run termination
- Protects against dust and damage
- Package of 10



75w Indoor DirectWire Driver 53276

- 120V/240V Input | 12V Output
- Includes one 72" output cord



3' Aluminum Channel 53254

- Creates valance to conceal tape
- Irregular surfaces installation
- Includes screws for installation



150w Indoor DirectWire Driver 53277

- 120V/240V Input | 12V Output
- Includes one 72" output cord



Silicone End Cap 53269

- Placed on run termination
- Protects against dust and damage
- One included in 53212, 53213 & 53214
- Package of 10



Indoor Dimming Controller 53282

- Full range dimming & On/Off control
- RF remote control included
- 140w Max

Replacement Remote 53292



Plastic Wire Clip 53255

- Used to secure Connecting Cords & driver output cords to surface
- Backed with 3M Adhesive tape
- Package of 10



Indoor Connecting Cords

- 53265 3"
- 53266 7"
- 53267 13"
- 53268 73"

- Extend distance between driver and tape
- Connect sections of tape together



Mounting clip 53272

- Use on irregular surfaces when 3M tape is not sufficient
- Package of 20



Male/Male Adapter 53262

- Changes female end to male
- Package of 10



Heat Shrink Wrap 53256

- Secure Connections when in walls
- Waterproof in damp location installations
- Heat gun required for installation
- Package of 10



4-Way Connector 53263

- Allows for L, T & X installations
- A power block for branching
- Includes two 53264 and one 53262



Rough In Terminal Block 53257 3"

- Rough in for new installations construction
- Female connector on one end, with 4 wire quick connector on opposite end

Rainbow RGB Star


STARSTRAND™

StarStrand™ Rainbow Star, with StarChip™ technology, includes the same construction and light output as Ultra Star with the addition of RGB color. With the optional controller, a rainbow of colors including white can be created- red, green, blue and any combination of the three-by remote control. Rainbow Star comes in pre-manufactured lengths with four pin connectors at each end for fast and sure installation. Minimum single run for Rainbow Star is 1', and maximum is 20' (*Driver Requirements on Page 377*). The white PC board is backed with 3M adhesive tape for easy installation.




Model	Length	Diodes	Wattage	Lumens	PC Board	Beam	Current
53230	2 in.	3	.72	R3 G10 B2.5	White	120°	60mA
53231	12 in.	18	4.32	R18 G60 B15	White	120°	60mA
53232	5 ft.	90	21.6	R90 G320 B75	White	120°	60mA
53233	10 ft.	180	43.2	R180 G630 B150	White	120°	60mA

800.486.2946



FEATURES

- Color LED tape system
- One tape hundreds of colors
- Automatically changes colors
- Perfect for restaurants, lounges, game rooms, theater room and retail
- Flexible design that forms to contours
- Safe and economical to operate
- Long life LED average 50,000 hours life
- Tested to UL standards for both US and Canada



Cuttable every 2 inches



maximlighting.com

STARSTRAND™



60w Indoor Plug-In Driver 53275

- 120V/240V Input | 12V Output
- Includes one 72" output cord and one 72" powercord

Power Cord with On/Off Switch 53252



Male End Cap 53264

- Placed on female end of run termination
- Protects against dust and damage
- Package of 10



75w Indoor DirectWire Driver 53276

- 120V/240V Input | 12V Output
- Includes one 72" output cord



3' Aluminum Channel 53254

- Creates valance to conceal tape
- Irregular surfaces installation
- Includes screws for installation



150w Indoor DirectWire Driver 53277

- 120V/240V Input | 12V Output
- Includes one 72" output cord



Silicone End Cap 53269

- Placed on run termination
- Protects against dust and damage
- One included in 53212, 53213 & 53214
- Package of 10



Indoor RGB Controller 53284

- Control color, intensity & speed
- RF remote control included
- 140w Max

Replacement Remote 53294



Plastic Wire Clip 53255

- Used to secure Connecting Cords & driver output cords to surface
- Backed with 3M Adhesive tape
- Package of 10



Indoor Connecting Cords


53265 3"
53266 7"
53267 13"
53268 73"

- Extend distance between driver and tape
- Connect sections of tape together



Mounting clip 53272

- Use on irregular surfaces when 3M tape is not sufficient
- Package of 20



Male/Male Adapter 53262

- Changes female end to male
- Package of 10



Heat Shrink Wrap 53256

- Secure Connections when in walls
- Waterproof in damp location installations
- Heat gun required for installation
- Package of 10



4-Way Connector 53263

- Allows for L, T & X installations
- A power block for branching
- Includes two 53264 and one 53262



Rough In Terminal Block 53257 3"

- Rough in for new installations construction
- Female connector on one end, with 4 wire quick connector on opposite end

Aqua Star

STARSTRAND™

For outdoor applications, StarStrand™ Aqua Star, with StarChip™ technology, comes completely surrounded by a pliable plastic coating for use in all weather conditions.

Pre-manufactured lengths with water-tight connectors at each end make Aqua Star safe to submerge under water.


The minimum single run for this strip is 1' and the maximum 20'.

The black PC board is backed with heavy duty adhesive 3M tape for easy installation.



Model	Length	Diodes	Wattage	Lumens	Color Temp	CRI	PC Board	Beam	Current
53241	1 ft.	18	2.88	171	3500K	70-75	Black	120°	40mA
53242	5 ft.	90	14.4	855	3500K	70-75	Black	120°	40mA
53243	10 ft.	180	28.8	1710	3500K	70-75	Black	120°	40mA

800.486.2946



FEATURES

- Sealed outdoor LED tape system
- Includes watertight connectors
- Perfect for fountains, pool areas, patios, landscapes, and walkways
- Flexible design that forms to contours
- Safe and economical to operate
- Long life LED average 50,000 hours life
- Tested to UL standards for both US and Canada



Cuttable every 2 inches



Flexible outdoor applications



Completely submersible

maximlighting.com

STARSTRAND™



30w Weatherproof Driver

53278

- 120V/240V Input | 12V Output
- UL approved for wet locations
- Includes one 72" output cord and one 72" powercord



60w Weatherproof Driver

53279

- 120V/240V Input | 12V Output
- UL approved for wet locations
- Includes one 72" output cord and one 72" powercord



Weatherproof Connector Cord

53270 48"

53271 144"

- Increase distance between driver & tape
- Connect sections of tape together



3' Aluminum Channel

53254

- Creates valance to conceal tape
- Irregular surfaces installation
- Includes screws for installation



Mounting clip

53272

- Use on irregular surfaces when 3M tape is not sufficient
- Package of 20

Super Star 24


STARSTRAND™

StarStrand™ Super Star 24, with StarChip™ technology, is destined to become the standard in LED tape. Covered in a pliable clear plastic, this product excels in performance and durability. The plastic cover keeps dust and dirt from landing directly on the board and makes keeping it clean a breeze. Super Star 24 is available in pre-manufactured lengths with 6 pin connectors installed at each end for fast and sure installation. The minimum single run for Super Star 24 is 5', and the maximum run is 150' (*Driver Requirements on Page 378*). The black PC board is backed with 3M adhesive tape for easy installation.



Model	Length	Diodes	Wattage	Lumens	Color Temp	CRI	PC Board	Beam	Current
53410	6 in.	6	.96	75	3500K	70-75	Black	120°	40mA
53411	12 in.	12	1.92	150	3500K	70-75	Black	120°	40mA
53412	5 ft.	60	9.6	750	3500K	70-75	Black	120°	40mA
53413	10 ft.	120	19.2	1500	3500K	70-75	Black	120°	40mA
53414	20 ft.	240	38.4	3000	3500K	70-75	Black	120°	40mA

800.486.2946



Cuttable every 12 inches

FEATURES

- Long distance laminated LED tape system
- 24V design allows for long runs and large installation
- Easy to install with multiple lengths to choose from
- Warm color temperature enhances room interiors
- Perfect for accent lighting in alcoves, toe-kick, and under counter
- Flexible design that forms to contours
- Safe and economical to operate
- Long life, high efficiency LED average 50,000 hours life
- Tested to UL standards for both US and Canada



maximlighting.com

STARSTRAND™



**150w Indoor Direct Wire Driver
53287**
 • 120V/240V Input | 24V Output
 • Includes one 72" output cord
**Additional Output Cord
53253**



**Silicone End Cap
53469**
 • Placed on run termination
 • Protects against dust and damage
 • One included in 53412, 53413 & 53414
 • Package of 10



**320w Indoor Direct Wire Driver
53288**
 • 120V/240V Input | 24V Output
 • Includes two 72" output cord



**3' Aluminum Channel
53254**
 • Creates valance to conceal tape
 • Irregular surfaces installation
 • Includes screws for installation



Indoor Connecting Cords
53465 5"
53467 13"
53468 73"
 • Extend distance between driver & tape
 • Connect sections of tape together



**Plastic Wire Clip
53255**
 • Used to secure Connecting Cords & driver output cords to surface
 • Backed with 3M Adhesive tape
 • Package of 10



**Mounting clip
53273**
 • Use on irregular surfaces when 3M tape is not sufficient
 • Package of 20



**90° Connector
53464**
 • Used for 90° corner, reversible for left or right
 • One end male, one end female
 • Includes 3M tape for easy mounting

Ultra Star 24


STARSTRAND™

StarStrand™ Ultra Star 24, with StarChip™ technology, is for applications requiring additional light output. Ultra Star produces over 50% more lumens than Super Star 24. This product is also covered with a pliable plastic and features a unique white PC board for ultimate light reflection. Ultra Star 24 is available in pre-manufactured lengths with 6 pin connectors installed at each end for fast and sure installation. The minimum single run for Ultra Star 24 is 5' and the maximum run is 110' (Driver Requirements on Page 378). The white PC board is backed with an adhesive 3M tape for easy installation.



Model	Length	Diodes	Wattage	Lumens	Color Temp	CRI	PC Board	Beam	Current
53420	6 in.	6	1.44	120	3500K	70-75	White	120°	60mA
53421	12 in.	12	2.88	240	3500K	70-75	White	120°	60mA
53422	5 ft.	60	14.4	1200	3500K	70-75	White	120°	60mA
53423	10 ft.	120	28.8	2400	3500K	70-75	White	120°	60mA
53424	20 ft.	240	57.6	4800	3500K	70-75	White	120°	60mA

800.486.2946



FEATURES

- High lumen long distance laminated LED tape system
- No exposed circuit board
- Easy to install with multiple lengths to choose from
- Warm color temperature enhances room interiors
- Perfect for task applications in under counter, and general room illumination
- Flexible design that forms to contours
- Safe and economical to operate
- Long life, high efficiency LED average 50,000 hours life
- Tested to UL standards for both US and Canada



Cuttable every 12 inches



maximlighting.com

STARSTRAND™



**150w Indoor Direct Wire Driver
53287**

- 120V/240V Input | 24V Output
- Includes one 72" output cord

**Additional Output Cord
53253**



**Silicone End Cap
53469**

- Placed on run termination
- Protects against dust and damage
- One included in 53412, 53413 & 53414
- Package of 10



**320w Indoor Direct Wire Driver
53288**

- 120V/240V Input | 24V Output
- Includes two 72" output cord



**3' Aluminum Channel
53254**

- Creates valance to conceal tape
- Irregular surfaces installation
- Includes screws for installation



Indoor Connecting Cords

53465 5"
53467 13"
53468 73"

- Extend distance between driver & tape
- Connect sections of tape together



**Plastic Wire Clip
53255**

- Used to secure Connecting Cords & driver output cords to surface
- Backed with 3M Adhesive tape
- Package of 10



**Mounting clip
53273**

- Use on irregular surfaces when 3M tape is not sufficient
- Package of 20



**90° Connector
53464**


- Used for 90° corner, reversible for left or right
- One end male, one end female
- Includes 3M tape for easy mounting

12V Maximum Run


STARSTRAND™

Series	Using Driver	Single Maximum Run	Maximum Run Using 53263 in Middle/Corner
Basic Star	53275 StarStrand 60w Plug-In Driver	16.5 Feet	
	53276 StarStrand 75w Direct WireDriver	16.5 Feet	33 Feet
Super Star	53275 StarStrand 60w Plug-In Driver	21 Feet	
	53276 StarStrand 75w Direct WireDriver	25 Feet	
	53277 StarStrand 150w Direct WireDriver	25 Feet	50 Feet
	53282 StarStrand Indoor Dimming Controller	20 Feet	
Ultra Star	53275 StarStrand 60w Plug-In Driver	14 Feet	
	53276 StarStrand 75w Direct WireDriver	18 Feet	
	53277 StarStrand 150w Direct WireDriver	18 Feet	32 Feet
	53282 StarStrand Indoor Dimming Controller	13 Feet	
Rainbow Star	53275 StarStrand 60w Plug-In Driver	14 Feet	
	53276 StarStrand 75w Direct WireDriver	18 Feet	
	53277 StarStrand 150w Direct Wire Driver	20 Feet	
Aqua Star	53278 StarStrand 30w Plug-In Waterproof Driver	10 Feet	
	53279 StarStrand 60w Plug-In Waterproof Driver	20 Feet	

800.486.2946



Using 53263
Powered From Corner



Using 53263
Powered From Middle

12V Direct Wire Drivers in Detail



**StarStrand 75w Direct Wire Driver
53276**
5"L x 3.75"W x 1.5"H

- 120V/240V input
- 12V, 6 Amp output
- Includes one 72' output cord




**StarStrand 150w Direct Wire Driver
53277**
7.75"L x 3.75"W x 1.5"H

- 120V/240V input
- 12V, 12.5 Amp output
- Includes one 72' output cord

maximlighting.com

Series	Using Driver	Maximum Run	
		Single Maximum Run	Using 320W Driver with 2 Outputs
Super Star 24V	53287 StarStrand 24V 150w Direct Wire Driver	75 Feet	
	53288 StarStrand 24V 320w Direct Wire Driver		150 Feet**
Ultra Star 24V	53287 StarStrand 24V 150w Direct Wire Driver	50 Feet	
	53288 StarStrand 24V 320w Direct Wire Driver		110 Feet**
	53288 StarStrand 24V 320w Direct Wire Driver	60 Feet	

** Must be powered in the middle/corner utilizing the two power output cords from the driver



24V Direct Wire Drivers in Detail

Maxim Lighting's StarStrand Drivers are UL/TUV/CE approved, feature short circuit protection, overload protection, over voltage protection, 158° F high operating temperature, and 100% full load burn-in testing.



StarStrand 24V 150w Direct Wire Driver
53287
 7.75"L x 3.75"W x 1.5"H
 • 120V/240V input
 • 24V, 6.5 Amp output
 • Includes one 72' output cord
Additional Output Cord
53253



StarStrand 24V 320w Direct Wire Driver
53288
 8.5"L x 4.5"W x 2.25"H
 • 120V/240V input
 • 24V, 12.5 Amp output
 • Includes two 72' output cords


12V Instructions & Installation

- Star Strip tapes can be field cut every 2". With the exception of Basic Star, you cannot add power connector or rejoin to start a new section to cut pieces.
- Polarity must be maintained. Each tape has + positive pin. Connectors are marked with + symbol. Positive polarity must be maintained or a section will not light. It is recommended to install all sections and power up to make sure polarity is correct before adhering to surface.
- Use the 4 way connector and 2" sections to get to 90° angles and turns. Interior connector cords can also be used for corners and around obstacles.
- The 4 way connector can also be used to power branched runs up to the maximum. Positioning of the driver is critical to limit the amount of drivers required for each installation. Position driver in middle of or corners of runs and power the 4 way connector.
- Connector cords can be used between the driver and the first tape section as well as between sections. Use connector cords to go around corners also to extend runs.
- Channel and clips can be used to install on irregular surfaces and also areas where tape will be visible and needs to be concealed.
- End caps should be used at every termination whether tape is cut or not.
- RGB controller is necessary for every RGB installation and is installed after the driver and before the first section of Rainbow Star tape. RGB controller will only work on Rainbow Star. There is a maximum 140 watt capacity to this device and a maximum single run of 20'.
- Dimming controller will work on all tapes except Aqua Star. Dimming controller is installed after the driver and before the first section of tape. There is a 140 watt capacity to this device and a maximum single run of 20'.
- Starstrand tape can be installed in any open interior application. Starstrand tape should not be installed inside a cabinet or other enclosure. Starstrand should not be installed in a wet location. Make sure water is kept well away from installation.
- Direct wire drivers should be installed into a U.L. listed wire junction box.

800.486.2946

maximlighting.com


STARSTRAND™



24V Instructions & Installation

- Star Strip 24 tapes can be field cut every 12". You cannot add power connector or rejoin to start a new section to cut pieces.
- Connector cords can be used between the driver and the first tape section as well as between sections. Use connector cords to go around corners also to extend runs.
- Channel and clips can be used to install on irregular surfaces and also areas where tape will be visible and needs to be concealed.
- End caps should be used at every termination whether tape is cut or not.
- Starstrand 24 tape can be installed in any open interior application. Starstrand 24 tape should not be installed inside a cabinet or other enclosure. Starstrand 24 should not be installed in a wet location. Make sure water is kept well away from installation.
- Direct wire drivers should be installed into a U.L. listed wire junction box.

STARSTRAND™



- A. StarStrand 24V 320w Direct Wire Driver (53288)
B. 6-Prong 90° Connector (53464)
C. Silicone End Cap (53469)


800.486.2946

maximlighting.com

Categorical View



A categorical view of Maxim Lighting's complete line of Wall sconces, bath vanities, flush mounts, semi flush mounts and mini pendants.





7141 FTOI,FTSN
9.5"W x 9.5"H x 6.5"Ext.
1 x 100wMB Bulb



7144 FTOI,FTSN
39.5"W x 9.5"H x 6.5"Ext.
4 x 100wMB Bulbs



7142 FTOI,FTSN
19.5"W x 9.5"H x 6.5"Ext.
2 x 100wMB Bulbs



7143 FTOI,FTSN
29.5"W x 9.5"H x 6.5"Ext.
3 x 100wMB Bulbs



**8013 MROI,MRPB,
MRPC, MRSN,WSOI**
24"W x 7"H x 8"Ext.
3 x 100wMB Bulbs



**8014 MROI,MRPB,
MRPC, MRSN,WSOI**
30"W x 7"H x 8"Ext.
4 x 100wMB Bulbs



**8015 MROI,MRPB,
MRPC, MRSN,WSOI**
36"W x 7"H x 8"Ext.
5 x 100wMB Bulbs



**8012 MROI,MRPB,
MRPC, MRSN,WSOI**
18"W x 7"H x 8"Ext.
2 x 100wMB Bulbs



**8016 MROI,MRPB,
MRPC, MRSN,WSOI**
48"W x 7"H x 8"Ext.
7 x 100wMB Bulbs



**8011 MROI,MRPB,
MRPC, MRSN,WSOI**
6"W x 9.5"H x 8"Ext.
1 x 100wMB Bulb





7135 MRPC, MRSN, WSOI
 5"W x 8"H x 6.5"Ext.
 1 x 100w MB Bulb



7136 MRPC, MRSN, WSOI
 14"W x 7.5"H x 6.5"Ext.
 2 x 100w MB Bulbs



7137 MRPC, MRSN, WSOI
 24"W x 7.5"H x 6.5"Ext.
 3 x 100w MB Bulbs



7138 MRPC, MRSN, WSOI
 30"W x 7.5"H x 6.5"Ext.
 4 x 100w MB Bulbs



7139 MRPC, MRSN, WSOI
 36"W x 8"H x 7"Ext.
 5 x 100w MB Bulbs



7123 CS, OI, PB, PB/PC, PC, PE, SN
 18"W x 4.5"H x 5"Ext.
 3 x 100w MB Bulbs



7124 CS, OI, PB, PB/PC, PC, PE, SN
 24"W x 4.5"H x 5"Ext.
 4 x 100w MB Bulbs



7126 CS, OI, PB, PB/PC, PC, PE, SN
 36"W x 4.5"H x 5"Ext.
 6 x 100w MB Bulbs



7128 CS, OI, PB, PB/PC, PC, PE, SN
 48"W x 4.5"H x 5"Ext.
 8 x 100w MB Bulbs



7129 CS, PB, PB/PC, PC, PE, SN
 60"W x 4.5"H x 5"Ext.
 10 x 100w MB Bulbs





4454 PB,PC
24"W x 4.25"H x 2.5"Ext.
4 x 60w MB Bulbs



4453 PB,PC
18"W x 4.25"H x 2.5"Ext.
3 x 60w MB Bulbs



4455 PB,PC
30"W x 4"H x 2.5"Ext.
5 x 60w MB Bulbs



4456 PB,PC
36"W x 4.25"H x 2.5"Ext.
6 x 60w MB Bulbs



4458 PB,PC
48"W x 4.25"H x 2.5"Ext.
8 x 60w MB Bulbs



Via Roma Collection
(Page 134)



2786SVGB
7"W x 14"H x 8.5"Ext.
1 x 100w MB Bulb



2789SVGB
37"W x 9.5"H x 8.5"Ext.
4 x 100w MB Bulbs



2788SVGB
25"W x 9.5"H x 8.5"Ext.
3 x 100w MB Bulbs



2787SVGB
21"W x 9.5"H x 8.5"Ext.
2 x 100w MB Bulbs

Vail Collection
(Page 263)



12501CINI
6"W x 8.5"H x 6.5"Ext.
1 x 100w MB Bulb



12504CINI
31"W x 8.5"H x 6.5"Ext.
4 x 100w MB Bulbs



12502CINI
14.5"W x 8.5"H x 6.5"Ext.
2 x 100w MB Bulbs



12503CINI
23"W x 8.5"H x 6.5"Ext.
3 x 100w MB Bulbs

Symphony Collection
(Page 122)



11230 SAOI,SVOI
7"W x 9.5"H x 10"Ext.
1 x 100w MB Bulb



11231 SAOI,SVOI
18"W x 8.5"H x 10"Ext.
2 x 100w MB Bulbs



11246 SAOI,SVOI
7"W x 11"H x 11"Ext.
1 x 100w MB Bulb



11247 SAOI,SVOI
16"W x 11"H x 9"Ext.
2 x 100w MB Bulbs



11232 SAOI,SVOI
26"W x 8.5"H x 10"Ext.
3 x 100w MB Bulbs



11233 SAOI,SVOI
37"W x 8.5"H x 10"Ext.
4 x 100w MB Bulbs

Stratus Collection
(Page 252)



2676MRBZ
12"W x 4.5"H x 6"Ext.
1 x 100w MB Bulb



2677MRBZ
24"W x 4.5"H x 6"Ext.
2 x 100w MB Bulbs



2678MRBZ
36"W x 4.5"H x 6"Ext.
3 x 100w MB Bulbs



2679MRBZ
48"W x 4.5"H x 6"Ext.
4 x 100w MB Bulbs

Spectra Collection
(Page 276)



2736MRSN
7"W x 9"H x 8"Ext.
1 x 100w MB Bulb



2739MRSN
37"W x 9"H x 8"Ext.
4 x 100w MB Bulbs



2737MRSN
19"W x 9"H x 8"Ext.
2 x 100w MB Bulbs



2738MRSN
25"W x 9"H x 8"Ext.
3 x 100w MB Bulbs

South Bend Collection
(Page 246)



10156 FTSN, WSOI
7.5"W x 8.5"H x 9"Ext.
1 x 100w MB Bulb



10157 FTSN, WSOI
18"W x 8.5"H x 9"Ext.
2 x 100w MB Bulbs



10159 FTSN, WSOI
38"W x 8.5"H x 9"Ext.
4 x 100w MB Bulbs



10158 FTSN, WSOI
28"W x 8.5"H x 9"Ext.
3 x 100w MB Bulbs



10161 FTSN, WSOI
45.5"W x 8.5"H x 9"Ext.
5 x 100w MB Bulbs

Soho Collection
(Page 159)



11057 SVOI, SVSN
15.5"W x 9"H x 10"Ext.
2 x 100w MB Bulbs



11058 SVOI, SVSN
23.5"W x 9"H x 10"Ext.
3 x 100w MB Bulbs



11056 SVOI, SVSN
6"W x 9"H x 9"Ext.
1 x 100w MB Bulb



11059 SVOI, SVSN
31"W x 9"H x 10"Ext.
4 x 100w MB Bulbs

Sausalito Collection
(Page 50)



21132MCFL
18.5"W x 12"H x 7"Ext.
2 x 100w MB Bulbs



21133MCFL
29"W x 12"H x 7"Ext.
3 x 100w MB Bulbs



21131MCFL
5"W x 15"H x 8"Ext.
1 x 100w MB Bulb



21134MCFL
38"W x 12"H x 7"Ext.
4 x 100w MB Bulbs

Progetto Collection
(Page 270)



23011WISN
6.5"W x 6.5"H x 5"Ext.
1 x 60w G9 Bulb



23014WISN
33.5"W x 5"H x 5"Ext.
4 x 60w G9 Bulbs



23012WISN
15.5"W x 5"H x 5"Ext.
2 x 60w G9 Bulbs



23013WISN
24.5"W x 5"H x 5"Ext.
3 x 60w G9 Bulbs

Portello Collection
(Page 204)



11747WSMA
7"W x 17"H x 8"Ext.
1 x 100w MB Bulb



11748WSMA
31.5" W x 11"H x 7"Ext.
4 x 100w MB Bulbs



11742WSMA
14.5" W x 11"H x 7"Ext.
2 x 100w MB Bulbs



11746WSMA
23.5" W x 11"H x 7"Ext.
3 x 100w MB Bulbs

Pine Grove Collection
(Page 290)



20717AVPT
17.5"W x 10"H x 8"Ext.
2 x 100w MB Bulbs



20718AVPT
26"W x 11"H x 8"Ext.
3 x 100w MB Bulbs



20716AVPT
12"W x 12"H x 8"Ext.
1 x 100w MB Bulb



20719AVPT
36"W x 11"H x 8"Ext.
4 x 100w MB Bulbs

Bristol Collection
(Page 242)



21328JEBG
15.25"W x 9.75"H x 8.5"Ext.
2 x 100w MB Bulbs



21329JEBG
24"W x 9.75"H x 8.5"Ext.
3 x 100w MB Bulbs



21327JEBG
6.25"W x 9.5"H x 9"Ext.
1 x 100w MB Bulb



21330JEBG
33"W x 9.75"H x 8.5"Ext.
4 x 100w MB Bulbs

Pacific Collection
(Page 228)



8021 MRAC, MRKB, MRPE, WSKB
7.5"W x 8.5"H x 9"Ext.
1 x 100w MB Bulb



8020 MRAC, MRKB, MRPE, WSKB
16"W x 9"H x 9"Ext.
2 x 100w MB Bulbs



8022 MRAC, MRKB, MRPE, WSKB
18"W x 8"H x 8"Ext.
2 x 100w MB Bulbs



8023 MRAC, MRKB, MRPE, WSKB
26"W x 8"H x 8"Ext.
3 x 100w MB Bulbs



8024 MRAC, MRKB, MRPE, WSKB
36"W x 8"H x 8"Ext.
4 x 100w MB Bulbs

Ophelia Collection
(Page 176)



32312BLCU
14.5"W x 11"H x 8.5"Ext.
2 x 100w MB Bulbs



32313BLCU
23"W x 11"H x 8.5"Ext.
3 x 100w MB Bulbs



32311BLCU
6"W x 19"H x 7.5"Ext.
1 x 100w MB Bulb



32314BLCU
31"W x 11"H x 8.5"Ext.
4 x 100w MB Bulbs

Oak Harbor Collection
(Page 200)



21063FLRB
6"W x 11"H x 7.5"Ext.
1 x 100w MB Bulb



21074FLRB
31.5"W x 9.5"H x 7.5"Ext.
4 x 100w MB Bulbs



21072FLRB
15"W x 9.5"H x 7.5"Ext.
2 x 100w MB Bulbs



21073FLRB
23.5"W x 9.5"H x 7.5"Ext.
3 x 100w MB Bulbs

Notre Dame Collection
(Page 102)



10970WSOI
7.5"W x 8"H x 8"Ext.
1 x 60w CA Bulb



10973WSOI
28.5"W x 10"H x 8.5"Ext.
4 x 60w CA Bulbs



10971WSOI
13.5"W x 10"H x 8"Ext.
2 x 60w CA Bulbs



10972WSOI
17"W x 10"H x 9"Ext.
3 x 60w CA Bulbs

Newport Collection
(Page 321)



11067 MROI, MRSN, WSOI
16.5"W x 10"H x 7.5"Ext.
2 x 100w MB Bulbs



11068 MROI, MRSN, WSOI
22.5"W x 10"H x 9"Ext.
3 x 100w MB Bulbs



11066 MROI, MRSN, WSOI
6.5"W x 10"H x 9"Ext.
1 x 100w MB Bulb



11069 MROI, MRSN, WSOI
30"W x 10"H x 9"Ext.
4 x 100w MB Bulbs

Moda Collection
(Page 188)



12313KLFN
15"W x 9"H x 7"Ext.
2 x 100w MB Bulbs



12314KLFN
22"W x 9"H x 8"Ext.
3 x 100w MB Bulbs



12311KLFN
6"W x 11"H x 9"Ext.
1 x 100w MB Bulb



12315KLFN
30"W x 9"H x 8"Ext.
4 x 100w MB Bulbs

Mission Bay Collection
(Page 196)



12432FLHB
15.5"W x 8.5"H x 7.5"Ext.
2 x 100w MB Bulbs



12433FLHB
24.5"W x 8.5"H x 7.5"Ext.
3 x 100w MB Bulbs



12431FLHB
5.5"W x 9"H x 7.5"Ext.
1 x 100w MB Bulb



12434FLHB
34"W x 8.5"H x 7.5"Ext.
4 x 100w MB Bulbs

Allentown Collection
(Page 142)



13512WSOI
17"W x 11"H x 10"Ext.
2 x 100w MB Bulbs



13513WSOI
26"W x 10"H x 10"Ext.
3 x 100w MB Bulbs



13511WSOI
7"W x 10"H x 9"Ext.
1 x 100w MB Bulb



13514WSOI
36"W x 10"H x 10"Ext.
4 x 100w MB Bulbs

Manor Collection
(Page 148)



12211FIOI
7"W x 13.5"H x 8.5"Ext.
1 x 100w MB Bulb



12214FIOI
37"W x 10.5"H x 9.5"Ext.
4 x 100w MB Bulbs



12212FIOI
15.5"W x 13.5"H x 8.5"Ext.
2 x 100w MB Bulbs



12213FIOI
29"W x 10.5"H x 9.5"Ext.
3 x 100w MB Bulbs

Malibu Collection
(Page 318)



2687 MROI, MRPB, MRSN, WSOI
13"W x 6"H x 8"Ext.
2 x 100wMB Bulbs



2688 MROI, MRPB, MRSN, WSOI
19.5"W x 6"H x 8"Ext.
3 x 100wMB Bulbs



2686 MROI, MRPB, MRSN, WSOI
6"W x 6.5"H x 9"Ext.
1 x 100wMB Bulb



2689 MROI, MRPB, MRSN, WSOI
29"W x 6"H x 8"Ext.
4 x 100wMB Bulbs

Luminous Collection
(Page 168)



21141SCRE
5"W x 7"H x 6.5"Ext.
1 x 100wMB Bulb



21142SCRE
11"W x 7.5"H x 6"Ext.
2 x 100wMB Bulbs

Linda ES Collection
(Page 340)



85808WSOI
14.5"W x 8.5"H x 9"Ext.
2 x 13wGU24 Bulbs



85809WSOI
24"W x 9"H x 8"Ext.
3 x 13wGU24 Bulbs



85807WSOI
6"W x 9.5"H x 7.5"Ext.
1 x 13wGU24 Bulb



85810WSOI
32"W x 9"H x 8"Ext.
4 x 13wGU24 Bulbs

Linda Collection
(Page 258)



11807ICBK
6"W x 9.5"H x 7.5"Ext.
1 x 100wMB Bulb



11811ICBK
31.5"W x 9"H x 9"Ext.
4 x 100wMB Bulbs



11808ICBK
14.5"W x 10"H x 7.5"Ext.
2 x 100wMB Bulbs



11810ICBK
23.5"W x 9"H x 9"Ext.
3 x 100wMB Bulbs

La Scalla Collection
(Page 54)



11771MCWC
15"W x 8.5"H x 6.5"Ext.
2 x 100wMB Bulbs



11772MCWC
23"W x 8.5"H x 6.5"Ext.
3 x 100wMB Bulbs



11767MCWC
6.5"W x 12"H x 8"Ext.
1 x 100wMB Bulb



11773MCWC
31"W x 8.5"H x 6.5"Ext.
4 x 100wMB Bulbs

Celeste Collection
(Page 164)



14282EMTT
20"W x 9"H x 10"Ext.
2 x 100wMB Bulbs



14283EMTT
28"W x 9"H x 10"Ext.
3 x 100wMB Bulbs



14281EMTT
7"W x 17.5"H x 12"Ext.
1 x 100wMB Bulb



14284EMTT
37.5"W x 9"H x 10"Ext.
4 x 100wMB Bulbs

Infinity Collection
(Page 180)



21311WSOI
6.5"W x 16"H x 9"Ext.
1 x 100wMB Bulb



21314WSOI
33"W x 9.5"H x 8.5"Ext.
4 x 100wMB Bulbs



21312WSOI
15.5"W x 9.5"H x 8.5"Ext.
2 x 100wMB Bulbs



21313WSOI
24.5"W x 9.5"H x 8.5"Ext.
3 x 100wMB Bulbs

Fremont Collection
(Page 40)



22252WSPD
18"W x 10"H x 8"Ext.
2 x 100wMB Bulbs



22253WSPD
29"W x 10"H x 8"Ext.
3 x 100wMB Bulbs



22251WSPD
7"W x 17.5"H x 10"Ext.
1 x 100wMB Bulb



22254WSPD
39"W x 11"H x 8"Ext.
4 x 100wMB Bulbs

Elegante Collection
(Page 116)



2864 FIEG, FIOI
17.5"W x 8.5"H x 9"Ext.
2 x 100wMB Bulbs



2865 FIEG, FIOI
28"W x 8.5"H x 9"Ext.
3 x 100wMB Bulbs



2863 FIEG, FIOI
7.5"W x 8.5"H x 9"Ext.
1 x 100wMB Bulb



2866 FIEG, FIOI
38.5"W x 8.5"H x 9"Ext.
4 x 100wMB Bulbs

Diamante Collection
(Page 212)



30612WSOI
14"W x 9"H x 8"Ext.
2 x 100wMB Bulbs



30613WSOI
22.5"W x 9"H x 8"Ext.
3 x 100wMB Bulbs



30611WSOI
6"W x 10"H x 8"Ext.
1 x 100wMB Bulb



30614WSOI
31"W x 9"H x 8"Ext.
4 x 100wMB Bulbs

Dresden Collection
(Page 35)



22272EMFL
16"W x 15"H x 9"Ext.
2 x 100wMB Bulbs



22271EMFL
7"W x 14"H x 9"Ext.
1 x 100wMB Bulb



22274EMFL
31"W x 10"H x 9"Ext.
3 x 100wMB Bulbs



22273EMFL
20.5"W x 10"H x 9"Ext.
2 x 100wMB Bulbs



22275EMFL
41.5"W x 10"H x 9"Ext.
4 x 100wMB Bulbs

Deco Collection
(Page 192)



12708WSFN
15"W x 8.5"H x 6.5"Ext.
2 x 100w MB Bulbs



12709WSFN
25"W x 8.5"H x 6.5"Ext.
3 x 100w MB Bulbs



12703WSFN
5.5"W x 8"H x 7"Ext.
1 x 100w MB Bulb



12710WSFN
35.5"W x 8.5"H x 6.5"Ext.
4 x 100w MB Bulbs

Cosmopolitan Collection
(Page 126)



11262FIGC
16"W x 9"H x 8.5"Ext.
2 x 100w MB Bulbs



11264FIGC
26"W x 8.5"H x 8"Ext.
3 x 100w MB Bulbs



11263FIGC
18"W x 8.5"H x 8"Ext.
2 x 100w MB Bulbs



11265FIGC
36"W x 8.5"H x 8"Ext.
4 x 100w MB Bulbs

Contour Collection
(Page 238)



21272 FTOI,FTSN
18.5"W x 7"H x 9"Ext.
2 x 100w MB Bulbs



21273 FTOI,FTSN
28.5"W x 7"H x 9"Ext.
3 x 100w MB Bulbs



21271 FTOI,FTSN
7.5"W x 7"H x 9"Ext.
1 x 100w MB Bulb



21274 FTOI,FTSN
38.5"W x 7"H x 9"Ext.
4 x 100w MB Bulbs

Classique Collection
(Page 222)



2767AVGB
7"W x 12.5"H x 8.5"Ext.
1 x 100w MB Bulb



2768AVGB
15.5"W x 11"H x 8"Ext.
2 x 100w MB Bulbs

Chelsea Collection
(Page 184)



20990WSWR
15"W x 11"H x 7"Ext.
2 x 100w MB Bulbs



20991WSWR
22.5"W x 11"H x 7.75"Ext.
3 x 100w MB Bulbs



20888WSWR
6"W x 11"H x 8"Ext.
1 x 100w MB Bulb



20992WSWR
30"W x 11"H x 7"Ext.
4 x 100w MB Bulbs

Cambridge Collection
(Page 28)



30543MCBN
24"W x 10.5"H x 9.5"Ext.
3 x 100w MB Bulbs



30542MCBN
15.5"W x 10.5"H x 9.5"Ext.
2 x 100w MB Bulbs



30541MCBN
6.5"W x 20"H x 8.5"Ext.
1 x 100w MB Bulb



30544MCBN
32.5"W x 10.5"H x 9.5"Ext.
4 x 100w MB Bulbs

Canyon Rim Collection
(Page 218)



8030SVCR
6.5"W x 9"H x 8"Ext.
1 x 100w MB Bulb



8027SVCR
15.5"W x 8.5"H x 8"Ext.
2 x 100w MB Bulbs



8031SVCR
16"W x 10"H x 8"Ext.
2 x 100w MB Bulbs



8028SVCR
24.5"W x 8.5"H x 8"Ext.
3 x 100w MB Bulbs



8029SVCR
32"W x 8.5"H x 8"Ext.
4 x 100w MB Bulbs

Brighton Collection
(Page 138)



11181EVOI
7"W x 10"H x 10"Ext.
1 x 100w MB Bulb



11182EVOI
17"W x 10"H x 8"Ext.
2 x 100w MB Bulbs

Brentwood Collection
(Page 250)



11077 FTOI,FTSN
13"W x 9.5"H x 6.5"Ext.
2 x 100w MB Bulbs



11078 FTOI,FTSN
20.5"W x 9.5"H x 6.5"Ext.
3 x 100w MB Bulbs



11076 FTOI,FTSN
5.5"W x 9.5"H x 6.5"Ext.
1 x 100w MB Bulb



11079 FTOI,FTSN
28"W x 9.5"H x 6.5"Ext.
4 x 100w MB Bulbs

Bel Air Collection
(Page 248)



11087 SVOI,SVSN,WTPC
15.5"W x 10"H x 7"Ext.
2 x 100w MB Bulbs



11088 SVOI,SVSN,WTPC
22.5"W x 10"H x 7"Ext.
3 x 100w MB Bulbs



24112CFGF
15"W x 12"H x 8"Ext.
2 x 100w MB Bulbs



24113CFGF
29"W x 9.5"H x 10"Ext.
3 x 100w MB Bulbs



11086 SVOI,SVSN,WTPC
6.5"W x 10"H x 7"Ext.
1 x 100w MB Bulb



11089 SVOI,SVSN,WTPC
30.5"W x 10"H x 7"Ext.
4 x 100w MB Bulbs



24111CFGF
7"W x 12"H x 8"Ext.
1 x 100w MB Bulb



24114CFGF
37"W x 9.5"H x 10"Ext.
4 x 100w MB Bulbs

Basix ES Collection
(Page 336)



85132ICSN
13.5"W x 8"H x 9" Ext.
2 x 13w GU24 Bulbs



85133ICSN
19"W x 8"H x 9" Ext.
3 x 13w GU24 Bulbs



85131ICSN
6"W x 8"H x 9" Ext.
1 x 13w GU24 Bulb



85134ICSN
27.5"W x 8"H x 9" Ext.
4 x 13w GU24 Bulbs

Basix Collection
(Page 303)



2121 ICPC, ICSN, WSOI
13.5"W x 8"H x 9" Ext.
2 x 100w MB Bulbs



2122 ICPC, ICSN, WSOI
19"W x 8"H x 9" Ext.
3 x 100w MB Bulbs



2120 ICPC, ICSN, WSOI
6"W x 8"H x 9" Ext.
1 x 100w MB Bulb



2123 ICPC, ICSN, WSOI
27.5"W x 8"H x 9" Ext.
4 x 100w MB Bulbs

Barcelona Collection
(Page 94)



13422AIOI
16.5"W x 12.5"H x 9" Ext.
2 x 100w MB Bulbs



13423AIOI
26"W x 9.5"H x 7.5" Ext.
3 x 100w MB Bulbs



13424AIOI
35"W x 10.5"H x 7.5" Ext.
4 x 100w MB Bulbs

Aurora Collection
(Page 268)



20100 FTOI, FTSN
21.5"W x 7"H x 8.5" Ext.
3 x 100w MB Bulbs



20099 FTOI, FTSN
13.5"W x 7"H x 8.5" Ext.
2 x 100w MB Bulbs



20101 FTOI, FTSN
29.5"W x 7"H x 8.5" Ext.
4 x 100w MB Bulbs



20098 FTOI, FTSN
5.5"W x 10"H x 7" Ext.
1 x 100w MB Bulb

Augusta Collection
(Page 64)



13572CFAF
16"W x 12"H x 8.5" Ext.
2 x 100w MB Bulbs



13573CFAF
28.5"W x 9"H x 10" Ext.
3 x 100w MB Bulbs



13571CFAF
7"W x 12"H x 9" Ext.
1 x 100w MB Bulb



13574CFAF
37.5"W x 9"H x 10" Ext.
4 x 100w MB Bulbs

Asiana Collection
(Page 284)



10996WSRC
5.5"W x 12"H x 6.5" Ext.
1 x 100w MB Bulb



10994WSRC
32"W x 11.5"H x 6.5" Ext.
4 x 100w MB Bulbs



10992WSRC
17.5"W x 11.5"H x 6.5" Ext.
2 x 100w MB Bulbs



10993WSRC
23.5"W x 11.5"H x 6.5" Ext.
3 x 100w MB Bulbs

Allentown Collection
(Page 142)**13511WSOI**
7"W x 10"H x 9"Ext.
1 x 100w MB Bulb**Allentown Collection**
(Page 142)**13512WSOI**
17"W x 11"H x 10"Ext.
2 x 100w MB Bulbs**Apollo Collection**
(Page 79)**2228WHGB**
14"W x 15"H x 7"Ext.
1 x 60w MB Bulb**Asiana Collection**
(Page 284)**10992WSRC**
17.5"W x 11.5"H x 6.5"Ext.
2 x 100w MB Bulbs**Asiana Collection**
(Page 284)**10996WSRC**
5.5"W x 12"H x 6.5"Ext.
1 x 100w MB Bulb**Aspen Collection**
(Page 99)**20617VAOI**
15"W x 7.5"H x 7"Ext.
1 x 100w MB Bulb**Aspen Collection**
(Page 99)**20618VAOI**
6"W x 25"H x 7"Ext.
1 x 100w MB Bulb**Aspen Collection**
(Page 99)**20619VAOI**
16.5"W x 26"H x 7"Ext.
3 x 100w MB Bulbs**Augusta Collection**
(Page 64)**13571CFAP**
7"W x 12"H x 9"Ext.
1 x 100w MB Bulb**Augusta Collection**
(Page 64)**13572CFAP**
16"W x 12"H x 8.5"Ext.
2 x 100w MB Bulbs**Aurora Collection**
(Page 268)**20098 FTOI, FTSN**
5.5"W x 10"H x 7"Ext.
1 x 100w MB Bulb**Aurora Collection**
(Page 268)**20099 FTOI, FTSN**
13.5"W x 7"H x 8.5"Ext.
2 x 100w MB Bulbs**Avant Collection**
(Page 272)**21258CHGA**
6.5"W x 12"H x 9.5"Ext.
1 x 60w CA Bulb**Bali Collection**
(Page 297)**20206RTBC**
7"W x 15.5"H x 10"Ext.
1 x 60w CA Bulb**Bali Collection**
(Page 297)**20207RTBC**
16"W x 14"H x 9"Ext.
2 x 60w CA Bulbs**Barcelona Collection**
(Page 94)**13419AIOI**
7"W x 22"H x 9"Ext.
1 x 100w MB Bulb**Barcelona Collection**
(Page 94)**13422AIOI**
16.5"W x 12.5"H x 9"Ext.
2 x 100w MB Bulbs**Basix Collection**
(Page 303)**2120 ICPC, ICSN, WSOI**
6"W x 8"H x 9"Ext.
1 x 100w MB Bulb**Basix Collection**
(Page 303)**2121 ICPC, ICSN, WSOI**
13.5"W x 8"H x 9"Ext.
2 x 100w MB Bulbs**Basix ES Collection**
(Page 336)**85131ICSN**
6"W x 8"H x 9"Ext.
1 x 13w GU24 Bulb

Basix ES Collection
(Page 336)



85132ICSN
13.5"W x 8"H x 9"Ext.
2 x 13wGU24 Bulbs

Beaumont Collection
(Page 72)



24111CFGF
7"W x 12"H x 8"Ext.
1 x 100wMB Bulb

Beaumont Collection
(Page 72)



24112CFGF
15"W x 12"H x 8"Ext.
2 x 100wMB Bulbs

Bel Air Collection
(Page 248)



11086 SVOI,SVSN,WTPC
6.5"W x 10"H x 7"Ext.
1 x 100wMB Bulb

Bel Air Collection
(Page 248)



11087 SVOI,SVSN,WTPC
15.5"W x 10"H x 7"Ext.
2 x 100wMB Bulbs

Boca Collection
(Page 156)



11677LTLG
7"W x 10.5"H x 8.5"Ext.
1 x 100wMB Bulb

Brentwood Collection
(Page 250)



11076 FTOI,FTSN
5.5"W x 9.5"H x 6.5"Ext.
1 x 100wMB Bulb

Brentwood Collection
(Page 250)



11077 FTOI,FTSN
13"W x 9.5"H x 6.5"Ext.
2 x 100wMB Bulbs

Brighton Collection
(Page 138)



11181EVOI
7"W x 10"H x 10"Ext.
1 x 100wMB Bulb

Brighton Collection
(Page 138)



11182EVOI
17"W x 10"H x 8"Ext.
2 x 100wMB Bulbs

Bristol Collection
(Page 242)



21327JFBG
6.25"W x 9.5"H x 9"Ext.
1 x 100wMB Bulb

Bristol Collection
(Page 242)



21328JFBG
15.25"W x 9.75"H x 8.5"Ext.
2 x 100wMB Bulbs

Cambridge Collection
(Page 28)



30541MCBN
6.5"W x 20"H x 8.5"Ext.
1 x 100w MB Bulb

Cambridge Collection
(Page 28)



30542MCBN
15.5"W x 10.5"H x 9.5"Ext.
2 x 100w MB Bulbs

Cambridge Collection
(Page 21)



30551BN
5"W x 19"H x 8.5"Ext.
1 x 60w CA Bulb

Cambridge Collection
(Page 21)



30551BN/SHD91
5"W x 19"H x 8.5"Ext.
1 x 60w CA Bulb

Cambridge Collection
(Page 21)



30552BN
14"W x 16"H x 8.5"Ext.
2 x 60wCA Bulbs

Cambridge Collection
(Page 21)



30552BN/SHD91
14"W x 16"H x 8.5"Ext.
2 x 60wCA Bulbs

Canyon Rim Collection
(Page 218)



8027SVCR
15.5"W x 8.5"H x 8"Ext.
2 x 100wMB Bulbs

Canyon Rim Collection
(Page 218)



8030SVCR
6.5"W x 9"H x 8"Ext.
1 x 100wMB Bulb

Celeste Collection
 (Page 164)


14281EMTT
 7"W x 17.5"H x 12"Ext.
 1 x 100w MB Bulb

Celeste Collection
 (Page 164)


14282EMTT
 20"W x 9"H x 10"Ext.
 2 x 100w MB Bulbs

Chelsea Collection
 (Page 184)


20888WSWR
 6"W x 11"H x 8"Ext.
 1 x 100w MB Bulb

Chelsea Collection
 (Page 184)


20990WSWR
 15"W x 11"H x 7"Ext.
 2 x 100w MB Bulbs

Cilandro Collection
 (Page 277)


53006WTSN
 4.7"W x 11"H x 4.3"Ext.
 1 x 60w MB T10 Bulb

Classique Collection
 (Page 222)


2767AVGB
 7"W x 12.5"H x 8.5"Ext.
 1 x 100w MB Bulb

Contour Collection
 (Page 238)


21271 FTOI,FTSN
 7.5"W x 7"H x 9"Ext.
 1 x 100w MB Bulb

Cosmopolitan Collection
 (Page 126)


11262FIGC
 16"W x 9"H x 8.5"Ext.
 2 x 100w MB Bulbs

Country French Collection
 (Page 285)


7766KB
 10.75"W x 16.25"H x 9"Ext.
 1 x 60w CA Bulb

Country French Collection
 (Page 285)


7767KB
 15.5"W x 16"H x 8"Ext.
 2 x 60w CA Bulbs

Cupole Collection
 (Page 260)


22107FLOI
 10"W x 8"H x 10"Ext.
 1 x 100w MB Bulb

Deco Collection
 (Page 192)


12703WSFN
 5.5"W x 8"H x 7"Ext.
 1 x 100w MB Bulb

Deco Collection
 (Page 192)


12708WSFN
 15"W x 8.5"H x 6.5"Ext.
 2 x 100w MB Bulbs

Desert Wind Collection
 (Page 292)


11901VADB
 6"W x 13"H x 9.5"Ext.
 1 x 100w MB Bulb

Diamante Collection
 (Page 212)


30611WSOI
 6"W x 10"H x 8"Ext.
 1 x 100w MB Bulb

Diamante Collection
 (Page 212)


30612WSOI
 14"W x 9"H x 8"Ext.
 2 x 100w MB Bulbs

Dresden Collection
 (Page 35)


22271EMFL
 7"W x 14"H x 9"Ext.
 1 x 100w MB Bulb

Dresden Collection
 (Page 35)


22272EMFL
 16"W x 15"H x 9"Ext.
 2 x 100w MB Bulbs

Dresden Collection
 (Page 31)


22281FL
 4"W x 13.5"H x 9"Ext.
 1 x 60w CABulb

Dresden Collection
 (Page 31)


22281FL/SHD91
 4"W x 13.5"H x 9"Ext.
 1 x 60w CABulb

Dresden Collection
(Page 31)

22282FL
13.5"W x 15"H x 8"Ext.
2 x 60w CABulbs

Dresden Collection
(Page 31)

22282FL/SHD91
13.5"W x 15"H x 8"Ext.
2 x 60w CABulbs

Duo Collection
(Page 172)

11528TCAD
7"W x 11.5"H x 9.5"Ext.
1 x 60w, G9 Xenon Incl.

Duo Collection
(Page 172)

11529TCAD
16.5"W x 11.5"H x 8.5"Ext.
2 x 60w, G9 Xenon Incl.

Elegante Collection
(Page 115)

2857 EG,OI
12"W x 9.5"H x 6.5"Ext.
2 x 60wCA Bulbs

Elegante Collection
(Page 115)

2858 EG,OI
11"W x 34"H x 8.5"Ext.
2 x 60wCA Bulbs

Elegante Collection
(Page 116)

2863 FIEG,FIOI
7.5"W x 8.5"H x 9"Ext.
1 x 100w MB Bulb

Elite Collection
(Page 274)

32002BTPS
7"W x 14"H x 9"Ext.
1 x 60wCA Bulb

Elite Collection
(Page 274)

32003BTPS
16.5"W x 14"H x 9"Ext.
2 x 60wCA Bulbs

Fremont Collection
(Page 40)

22251WSPD
7"W x 17.5"H x 10"Ext.
1 x 100wMB Bulb

Fremont Collection
(Page 40)

22252WSPD
18"W x 10"H x 8"Ext.
2 x 100wMB Bulbs

French Country Collection
(Page 280)

21441CCFF
6"W x 18"H x 10.5"Ext.
1 x 60wCA Bulb

French Country Collection
(Page 280)

21442CCFF
14.5"W x 18"H x 9.5"Ext.
2 x 60wCA Bulbs

Genoa Collection
(Page 12)

17002MD
11.5"W x 20.5"H x 6.5"Ext.
2 x 60wCA Bulbs

Genoa Collection
(Page 12)

17003MD
15"W x 21"H x 7.5"Ext.
3 x 60wCA Bulbs

Grove Collection
(Page 128)

8837OI
5"W x 13"H x 7"Ext.
1 x 60wCA Bulb

Grove Collection
(Page 128)

8838OI
12.5"W x 13"H x 7"Ext.
2 x 60wCA Bulbs

Grove Collection
(Page 128)

8839OI
10"W x 30"H x 8"Ext.
2 x 60wCA Bulbs

Hampton Collection
(Page 17)

12032AD
11.5"W x 14"H x 6"Ext.
2 x 60wCA Bulbs

Infinity Collection
(Page 180)

21311WSOI
6.5"W x 16"H x 9"Ext.
1 x 100wMB Bulb

Infinity Collection
(Page 180)


21312WSOI
 15.5"W x 9.5"H x 8.5"Ext.
 2 x 100w MB Bulbs

Java Collection
(Page 86)


2596JAVC
 7"W x 11"H x 10"Ext.
 1 x 100w MB Bulb

Java Collection
(Page 86)


2597JAVC
 16"W x 11"H x 10"Ext.
 2 x 100w MB Bulbs

La Scalla Collection
(Page 54)


11767MCWC
 6.5"W x 12"H x 8"Ext.
 1 x 100w MB Bulb

La Scalla Collection
(Page 54)


11771MCWC
 15"W x 8.5"H x 6.5"Ext.
 2 x 100w MB Bulbs

Larchmont Collection
(Page 118)


20116WTVI
 6.5"W x 13.5"H x 8"Ext.
 1 x 60w CA Bulb

Larchmont Collection
(Page 118)


20117WTVI
 16"W x 13.5"H x 7.5"Ext.
 2 x 60w CA Bulbs

Linda Collection
(Page 258)


11807ICBK
 6"W x 9.5"H x 7.5"Ext.
 1 x 100w MB Bulb

Linda Collection
(Page 258)


11808ICBK
 14.5"W x 10"H x 7.5"Ext.
 2 x 100w MB Bulbs

Linda ES Collection
(Page 340)


85807WSOI
 6"W x 9.5"H x 7.5"Ext.
 1 x 13w GU24 Bulb

Linda ES Collection
(Page 340)


85808WSOI
 14.5"W x 8.5"H x 9"Ext.
 2 x 13w GU24 Bulbs

Loft Collection
(Page 150)


70001 OI,SN
 5"W x 8"H x 9"Ext.
 1 x 60w CA Bulb

Loft Collection
(Page 150)


70002 OI,SN
 10"W x 8"H x 6"Ext.
 2 x 60w CA Bulbs

Luminous Collection
(Page 168)


21141SCRE
 5"W x 7"H x 6.5"Ext.
 1 x 100w MB Bulb

Luminous Collection
(Page 168)


21142SCRE
 11"W x 7.5"H x 6"Ext.
 2 x 100w MB Bulbs

Malibu Collection
(Page 318)


**2686 MROI,MRPB,
 MRSN,WSOI**
 6"W x 6.5"H x 9"Ext.
 1 x 100w MB Bulb

Malibu Collection
(Page 318)


**2687 MROI,MRPB,
 MRSN,WSOI**
 13"W x 6"H x 8"Ext.
 2 x 100w MB Bulbs

Manor Collection
(Page 148)


12211FIOI
 7"W x 13.5"H x 8.5"Ext.
 1 x 100w MB Bulb

Manor Collection
(Page 148)


12212FIOI
 15.5"W x 13.5"H x 8.5"Ext.
 2 x 100w MB Bulbs

Manor Collection
(Page 145)


12217OI, OI/SHD123
 7"W x 14.5"H x 9.5"Ext.
 1 x 60w CA Bulb

Manor Collection
 (Page 145)


12218OI, OI/SHD123
 13"W x 14.5"H x 9.5"Ext.
 2 x 60wCA Bulbs

Mission Bay Collection
 (Page 196)


12431FLHB
 5.5"W x 9"H x 7.5"Ext.
 1 x 100wMB Bulb

Mission Bay Collection
 (Page 196)


12432FLHB
 15.5"W x 8.5"H x 7.5"Ext.
 2 x 100wMB Bulbs

Moda Collection
 (Page 188)


12311KLFN
 6"W x 11"H x 9"Ext.
 1 x 100wMB Bulb

Moda Collection
 (Page 188)


12312KLFN
 14.5"W x 13.5"H x 8"Ext.
 2 x 100wMB Bulbs

Monaco Collection
 (Page 83)


2890WB
2890WB/CRY 005
 13"W x 18"H x 7"Ext.
 2 x 60w CABulbs

Monaco Collection
 (Page 83)


2891WB
2891WB/CRY 004
 15"W x 19"H x 9.5"Ext.
 3 x 60w CABulbs

Morocco Collection
 (Page 88)


20671WB
 5.5"W x 17.5"H x 10.5"Ext.
 1 x 60wCA Bulb

Morocco Collection
 (Page 88)


20673WB
 15.5"W x 18.5"H x 10.5"Ext.
 3 x 60wCA Bulbs

Newport Collection
 (Page 321)


11066 MROI, MRSN, WSOI
 6.5"W x 10"H x 9"Ext.
 1 x 100wMB Bulb

Newport Collection
 (Page 321)


11067 MROI, MRSN, WSOI
 16.5"W x 10"H x 7.5"Ext.
 2 x 100wMB Bulbs

Notre Dame Collection
 (Page 102)


10970WSOI
 7.5"W x 8"H x 8"Ext.
 1 x 60wCA Bulb

Notre Dame Collection
 (Page 102)


10971WSOI
 13.5"W x 10"H x 8"Ext.
 2 x 60wCA Bulbs

Nova Collection
 (Page 232)


11047 MRSN, WSOI
 6"W x 12.5"H x 8"Ext.
 1 x 100wMB Bulb

Nova Collection
 (Page 232)


11048 MRSN, WSOI
 14"W x 12.5"H x 8"Ext.
 2 x 100wMB Bulbs

Oak Harbor Collection
 (Page 200)


21063FLRB
 6"W x 11"H x 7.5"Ext.
 1 x 100wMB Bulb

Oak Harbor Collection
 (Page 200)


21072FLRB
 15"W x 9.5"H x 7.5"Ext.
 2 x 100wMB Bulbs

Ophelia Collection
 (Page 176)


32311BLCU
 6"W x 19"H x 7.5"Ext.
 1 x 100wMB Bulb

Ophelia Collection
 (Page 176)


32312BLCU
 14.5"W x 11"H x 8.5"Ext.
 2 x 100wMB Bulbs

Pacific Collection
 (Page 228)


**8020 MRAC, MRKB,
 MRPE, WSKB**
 16"W x 9"H x 9"Ext.
 2 x 100wMB Bulbs

Pacific Collection
(Page 228)


**8021 MRAC, MRKB,
MRPE, WSKB**
7.5"W x 8.5"H x 9"Ext.
1 x 100w MB Bulb

Pacific Collection
(Page 227)


**8025 MRAC, MRSN
MRKB, WSKB**
16"W x 4.5"H x 8"Ext.
1 x 100w MB Bulb

Pacific Collection
(Page 227)


8026 MRSN
13"W x 4.5"H x 8"Ext.
1 x 100w MB Bulb

Paradise Collection
(Page 10)


39942 BCPS
18"W x 20"H x 11.5"Ext.
3 x 60w CA Bulbs

Piedmont Collection
(Page 234)


115471 CSN
6.5"W x 9.5"H x 9.5"Ext.
1 x 100w MB Bulb

Pine Grove Collection
(Page 288)


20706 AVPT
14"W x 6"H x 7"Ext.
1 x 100w MB Bulb

Pine Grove Collection
(Page 289)


20708 AVPT
10.5"W x 9.5"H x 4.5"Ext.
1 x 100w MB Bulb

Pine Grove Collection
(Page 290)


20716 AVPT
12"W x 12"H x 8"Ext.
1 x 100w MB Bulb

Pine Grove Collection
(Page 290)


20717 AVPT
17.5"W x 10"H x 8"Ext.
2 x 100w MB Bulbs

Portello Collection
(Page 204)


11742 WSMA
14.5"W x 11"H x 7"Ext.
2 x 100w MB Bulbs

Portello Collection
(Page 204)


11747 WSMA
7"W x 17"H x 8"Ext.
1 x 100w MB Bulb

Progetto Collection
(Page 270)


23011 WISN
6.5"W x 6.5"H x 5"Ext.
1 x 60w G9 Bulb

Sausalito Collection
(Page 50)


21131 MCFL
5"W x 15"H x 8"Ext.
1 x 100w MB Bulb

Sausalito Collection
(Page 50)


21132 MCFL
18.5"W x 12"H x 7"Ext.
2 x 100w MB Bulbs

Sherwood Collection
(Page 293)


32448 EFPD
6.5"W x 17"H x 9.5"Ext.
1 x 100w MB Bulb

Soho Collection
(Page 159)


11056 SVOI, SVSN
6"W x 9"H x 9"Ext.
1 x 100w MB Bulb

Soho Collection
(Page 159)


11057 SVOI, SVSN
15.5"W x 9"H x 10"Ext.
2 x 100w MB Bulbs

South Bend Collection
(Page 246)


10156 FTSN, WSOI
7.5"W x 8.5"H x 9"Ext.
1 x 100w MB Bulb

South Bend Collection
(Page 246)


10157 FTSN, WSOI
18"W x 8.5"H x 9"Ext.
2 x 100w MB Bulbs

Southern Collection
(Page 107)


2939 LTKB
15.5"W x 9.5"H x 9.5"Ext.
2 x 100w MB Bulbs

Spectra Collection
(Page 276)



2736MRSN
7"W x 9"H x 8"Ext.
1 x 100w MB Bulb

Spectra Collection
(Page 276)



2737MRSN
19"W x 9"H x 8"Ext.
2 x 100w MB Bulbs

Stratus Collection
(Page 252)



2676MRBZ
12"W x 4.5"H x 6"Ext.
1 x 100w MB Bulb

Symphony Collection
(Page 122)



11230 SAOI,SVOI
7"W x 9.5"H x 10"Ext.
1 x 100w MB Bulb

Symphony Collection
(Page 122)



11246 SAOI,SVOI
7"W x 11"H x 11"Ext.
1 x 100w MB Bulb

Symphony Collection
(Page 122)



11247 SAOI,SVOI
16"W x 11"H x 9"Ext.
2 x 100w MB Bulbs

Towne Collection
(Page 152)



11031OI
4.5"W x 9"H x 8"Ext.
1 x 60w CA Bulb

Towne Collection
(Page 152)



11032OI
10"W x 9"H x 7"Ext.
2 x 60w CA Bulbs

Vail Collection
(Page 263)



12501CINI
6"W x 8.5"H x 6.5"Ext.
1 x 100w MB Bulb

Vail Collection
(Page 263)



12502CINI
14.5"W x 8.5"H x 6.5"Ext.
2 x 100w MB Bulbs

Verona Collection
(Page 104)



20633OI
14"W x 11"H x 9"Ext.
2 x 60w CA Bulbs

Via Roma Collection
(Page 134)



2786SVGB
7"W x 14"H x 8.5"Ext.
1 x 100w MB Bulb

Via Roma Collection
(Page 134)



2787SVGB
21"W x 9.5"H x 8.5"Ext.
2 x 100w MB Bulbs



2252WH
12"W x 6"H x 6"Ext.
1 x 100w MB Bulb



7135 MRPC,MRSN,WSOI
5"W x 8"H x 6.5"Ext.
1 x 100w MB Bulb



8011 MROI,MRPB,MRPC,MRSN,WSOI
6"W x 9.5"H x 8"Ext.
1 x 100w MB Bulb



8816EG/CRY059
4.5"W x 15"H x 8.5"Ext.
1 x 60w CA Bulb



8817EG/CRY060
11"W x 15"H x 8.5"Ext.
2 x 60w CA Bulbs



20580 MROI,MRPE
8"W x 10.5"H x 4"Ext.
1 x 100w MB Bulb



20581 MROI,MRPE,MRSN
10"W x 11"H x 4"Ext.
1 x 100w MB Bulb



20582 MROI,MRPE,MRTW
 13"W x 6"H x 6"Ext.
 1 x 100wMB Bulb



20583 MROI,MRPE
 16"W x 7"H x 7"Ext.
 1 x 100wMB Bulb



20585 MRWT,WTWT
 10.5"W x 5.5"H x 5.5"Ext.
 1 x 100wMB Bulb



75137GRCH
 8"W x 14"H x 4"Ext.
 1 x 100wMB Bulb



85585 MRWT, WTWT
 10.5"W x 5.5"H x 4"Ext.
 1 x 13w GU24 Bulb



Allentown Collection
(Page 141)**13500WSOI**
15"W x 8.5"H
2 x 60wMB Bulbs**Apollo Collection**
(Page 80)**2220WHGB**
16"W x 9"H
3 x 60wMB Bulbs**Apollo Collection**
(Page 80)**2222WHGB**
20"W x 10"H
3 x 60wMB Bulbs**Aspen Collection**
(Page 98)**20601VAOI**
13"W x 9"H
2 x 100wMB Bulbs**Aspen Collection**
(Page 98)**20602VAOI**
16"W x 9"H
3 x 100wMB Bulbs**Augusta Collection**
(Page 61)**13560CFAF**
13"W x 6.5"H
2 x 60wMB Bulbs**Augusta Collection**
(Page 61)**13561CFAF**
15"W x 6.5"H
2 x 75wMB Bulbs**Bali Collection**
(Page 296)**20200SIBC**
16.5"W x 9"H
2 x 75wMB Bulbs**Beaumont Collection**
(Page 71)**24100CFGF**
13"W x 6.5"H
2 x 60wMB Bulbs**Beaumont Collection**
(Page 71)**24101CFGF**
15"W x 6.5"H
2 x 75wMB Bulbs**Bolero Collection**
(Page 208)**11290WSOI**
13.5"W x 6.5"H
2 x 75wMB Bulbs**Brighton Collection**
(Page 137)**11170EVOI**
13"W x 7"H
2 x 75wMB Bulbs**Brighton Collection**
(Page 137)**11171EVOI**
16"W x 8"H
3 x 60wMB Bulbs**Cambridge Collection**
(Page 27)**30530MCBN**
14.5"W x 9"H
2 x 100wMB Bulbs**Canyon Rim Collection**
(Page 216)**2750SVCR**
13"W x 8"H
2 x 60wMB Bulbs**Canyon Rim Collection**
(Page 216)**27510SVCR**
15.5"W x 8.5"H
3 x 60wMB Bulbs**Chelsea Collection**
(Page 183)**20880WSWR**
16"W x 8"H
2 x 75wMB Bulbs**Classique Collection**
(Page 222)**2760AVGB**
16"W x 10"H
3 x 60wMB Bulbs**Cosmopolitan Collection**
(Page 125)**11250FIGC**
13"W x 7"H
2 x 75wMB Bulbs**Cupola Collection**
(Page 260)**22100FLOI**
14.5"W x 7"H
3 x 60wMB Bulbs

Deco Collection
(Page 191)**12700WSFN**
14"W x 7.5"H
2 x 75w MB Bulbs**Diamante Collection**
(Page 211)**30600WSOI**
17.5"W x 11.5"H
3 x 60w MB Bulbs**Dresden Collection**
(Page 32)**22260EMFL**
22"W x 9.5"H
3 x 60w MB Bulbs**Fremont Collection**
(Page 39)**22240WSPD**
15"W x 6"H
2 x 75w MB Bulbs**French Country Collection**
(Page 280)**21430FTFF**
15"W x 7.5"H
2 x 60w MB Bulbs**Genoa Collection**
(Page 13)**17000MCMD**
17"W x 11.25"H
3 x 100w MB Bulbs**Hampton Collection**
(Page 17)**12020FTAD**
13.5"W x 7.5"H
3 x 60w MB Bulbs**Illuminare Collection**
(Page 332)**53030FTSN**
6"D x 2"H
6w LED**Illuminare Collection**
(Page 332)**53031FTSN**
9"D x 3"H
10.5w LED**Illuminare Collection**
(Page 332)**53032FTSN**
11"D x 3"H
15w LED**Illuminare Collection**
(Page 331)**53034FTSN**
5"W x 2.5"H
6w LED**Illuminare Collection**
(Page 331)**53035FTSN**
7.5"W x 3"H
10.5w LED**Illuminare Collection**
(Page 331)**53036FTSN**
9"W x 3"H
15w LED**Java Collection**
(Page 86)**2590JAVC**
14.5"W x 7.5"H
2 x 75w MB Bulbs**La Salle Collection**
(Page 68)**16000MCHA**
17"W x 10"H
2 x 60w MB Bulbs**La Scalla Collection**
(Page 53)**11760MCWC**
13"W x 8"H
2 x 75w MB Bulbs**Linda Collection**
(Page 257)**11799ICBK**
13"W x 8"H
2 x 60w MB Bulbs**Linda Collection**
(Page 257)**11800ICBK**
16"W x 10"H
3 x 60w MB Bulbs**Linda ES Collection**
(Page 338)**85800WSOI**
13"W x 7"H
2 x 13w GU24 Bulbs**Linda ES Collection**
(Page 338)**85801WSOI**
16"W x 9"H
3 x 13w GU24 Bulbs

Luminous Collection
(Page 167)


21140SCRE
 14"W x 6.5"H
 2 x 75wMB Bulbs

Malibu Collection
(Page 317)


**2680 MROI,MRPB,
 MRSN, MRWT,WSOI**
 12.5"W x 4.25"H
 2 x 60wMB Bulbs

Malibu Collection
(Page 317)


**2681 MROI,MRPB,
 MRSN, MRWT,WSOI**
 16"W x 4"H
 3 x 60wMB Bulbs

Malibu Collection
(Page 317)


**11060 MROI,MRPB,
 MRSN, MRWT,WSOI**
 20"W x 6"H
 4 x 60wMB Bulbs

Moda Collection
(Page 187)


12300KLFN
 18"W x 8.5"H
 2 x 75wMB Bulbs

Oak Harbor Collection
(Page 199)


21075FLRB
 16.5"W x 7.5"H
 2 x 75wMB Bulbs

Ophelia Collection
(Page 175)


32300BLCU
 14"W x 6.5"H
 2 x 75wMB Bulbs

Pacific Collection
(Page 227)


**2650 MRAC,MRPE,
 MRKB,WSKB**
 13"W x 7"H
 2 x 60wMB Bulbs

Palazzo Collection
(Page 76)


12280VSAP
 15"W x 9"H
 3 x 60wMB Bulbs

Pine Grove Collection
(Page 288)


20700AVPT
 15"W x 6"H
 2 x 75wMB Bulbs

Pine Grove Collection
(Page 289)


5520 CDPT,VAPT
 10"W x 7.5"H
 1 x 100wMB Bulb

Portello Collection
(Page 203)


11739WSMA
 17.5"W x 8.5"H
 3 x 60wMB Bulbs

Portello Collection
(Page 203)


11740WSMA
 13.5"W x 9"H
 2 x 75wMB Bulbs

Portofino Collection
(Page 81)


20280VAOI
 16.75"W x 7"H
 3 x 100wMB Bulbs

Richmond Collection
(Page 44)


31000WSCU
 14"W x 6.5"H
 2 x 75wMB Bulbs

Soho Collection
(Page 158)


11050 SVOI,SVSN
 14"W x 7.5"H
 2 x 60wMB Bulbs

Symphony Collection
(Page 121)


11240 SAOI,SVOI
 19"W x 7.5"H
 2 x 60wMB Bulbs

Via Roma Collection
(Page 133)


2780SVGB
 13"W x 6.5"H
 2 x 75wMB Bulbs



5826CLSN
 11.5"W x 6"H
 1 x 60wMB Bulb



5827CLSN
 13.5"W x 6"H
 2 x 60wMB Bulbs



5828CLSN
15.5"W x 6"H
3 x 60w MB Bulbs



5830 FTOI,FTPB,
FTPE,FTSN,FTTW,FTWT
11.5"W x 6"H
1 x 60w MB Bulb



5831 FTOI,FTPB,
FTPE,FTSN,FTTW,FTWT
13.5"W x 6"H
2 x 60w MB Bulbs



5832 FTOI,FTPB,
FTPE,FTSN,FTTW,FTWT
15.5"W x 6"H
3 x 60w MB Bulbs



5840 FIOI,FTOI,FTSN,
ICBK,ICSN,MRAC,MRCS
11.5"W x 6"H
1 x 60w MB Bulb



5840 MROI,MRPB,MRPE,
MRSN,MRTW,MRWT,WSOI
11.5"W x 6"H
1 x 60w MB Bulb



5841 FIOI,FTOI,FTSN,
ICBK,ICSN,MRAC
13.5"W x 6"H
2 x 60w MB Bulbs



5841 MROI,MRPB,MRPE,
MRSN,MRTW,MRWT,WSOI
13.5"W x 6"H
2 x 60w MB Bulbs



5842 FIOI,FTOI,FTSN,
ICBK,ICSN,MRAC,MRCS
15.5"W x 6"H
3 x 60w MB Bulbs



5842 MROI,MRPB,MRPE,
MRSN,MRTW,MRWT,WSOI
15.5"W x 6"H
3 x 60w MB Bulbs



5849 MROI,MRSN
11.5"W x 16"H
2 x 60w MB Bulbs



5850 MRAC,MROI,
MRSN,MRTW
12"W x 4"H
1 x 75w MB Bulb



5851 MRAC,MROI,
MRSN,MRTW
14"W x 5"H
2 x 75w MB Bulbs



5852 MRAC,MROI,
MRSN,MRTW
17"W x 5"H
3 x 60w MB Bulbs



5855 LTKB,LTOI
13.5"W x 6"H
2 x 75w MB Bulbs



5856 LTKB,LTOI
15.5"W x 6"H
3 x 60w MB Bulbs



5880 WTPB,WTPE,WTWT
7.5"W x 4.5"H
1 x 60w MB Bulb



5881 WTCS,WTOI,WTPB,
WTPE,WTSN,WTWT
9"W x 5"H
2 x 60w MB Bulbs



5882 CLPB,CLWT
7.5"W x 4.5"H
1 x 60w MB Bulb



5883 CLPB,CLWT
9.5"W x 4.5"H
2 x 60w MB Bulbs



5884 MROI,MRPB,MRSN
7.5"W x 4.5"H
1 x 60w MB Bulb



5885 MROI,MRPB,MRSN
9"W x 5"H
2 x 60w MB Bulbs



5886 WSOI
7.5"W x 4.5"H
1 x 60w MB Bulb



5887 WSOI
9"W x 5"H
2 x 60w MB Bulbs



5889 WTPB,WTWT
6"W x 7"H
1 x 60w MB Bulb



6503 CLCS, CLPB
9.5"W x 6"H
3 x 25w CA Bulbs



6504 CLCS, CLPB
11.5"W x 6.5"H
4 x 25w CA Bulbs



11000SN
14"W x 7.5"H
2 x 75w MB Bulbs



11001SN
17.5"W x 7.5"H
3 x 75w MB Bulbs



82681MRSN
16"W x 4"H
3 x 13w GU24 Bulbs



85830 FTTW, FTPB
11.5"W x 6"H
1 x 13w GU24 Bulb



85831 FTTW, FTPB
13.5"W x 6"H
2 x 13w GU24 Bulbs



85832 FTTW, FTPB
15.5"W x 6"H
3 x 13w GU24 Bulbs



85840 MROI, MRSN, WSOI
11.5"W x 6"H
1 x 13w GU24 Bulb



85841 MROI, MRSN, WSOI
13.5"W x 6"H
2 x 13w GU24 Bulbs



85842 MROI, MRSN, WSOI
15.5"W x 6"H
3 x 13w GU24 Bulbs

Allentown Collection
(Page 141)**13501WSOI**
18"W x 14"H | 3 x 100w MB**Apollo Collection**
(Page 80)**2229WHGB**
17"W x 16.5"H | 3 x 100w MB**Asiana Collection**
(Page 283)**10981WSRC**
13"W x 15"H | 2 x 100w MB**Augusta Collection**
(Page 61)**13562CFAF**
21"W x 14.5"H | 3 x 60w MB**Aurora Collection**
(Page 267)**20091 FTOI,FTSN**
13"W x 9"H | 2 x 60w MB**Avant Collection**
(Page 272)**21251CHGA**
17"W x 14.5"H | 3 x 60w CA**Barcelona Collection**
(Page 93)**13410AIOI**
15.5"W x 9"H | 3 x 60w MB**Basix Collection**
(Page 301)**10120 ICSN, WSOI**
14"W x 10"H | 2 x 100w MB**Basix ES Collection**
(Page 335)**85120ICSN**
14"W x 10"H | 2 x 13wGU24**Beaumont Collection**
(Page 71)**24102CFGF**
22.5"W x 13"H | 3 x 60w MB**Boca Collection**
(Page 155)**11671LTLG**
16"W x 14"H | 3 x 60w MB**Bolero Collection**
(Page 208)**11291WSOI**
17"W x 13"H | 3 x 100w MB**Brighton Collection**
(Page 137)**11172EVOI**
16"W x 12"H | 3 x 60w MB**Bristol Collection**
(Page 2)**21321JFBG**
14"W x 14"H | 3 x 60w MB**Cambridge Collection**
(Page 27)**30531MCBN**
25"W x 16"H | 3 x 100w MB**Canyon Rim Collection**
(Page 216)**2752SVCR**
17"W x 13.5"H | 3 x 100w MB**Celeste Collection**
(Page 163)**14271EMTT**
19.5"W x 16.75"H | 3 x 100w MB**Chelsea Collection**
(Page 183)**20881WSWR**
16"W x 14"H | 2 x 100w MB**Classique Collection**
(Page 221)**2761AVGB**
18"W x 16.5"H | 3 x 60w MB**Contour Collection**
(Page 237)**21261 FTOI,FTSN**
17.75"W x 9.25"H | 2 x 60w MB

Cupola Collection
(Page 260)

22101FLOI
 15"W x 12"H | 3 x 100w MB

Dresden Collection
(Page 32)

22261EMFL
 21.5"W x 14.5"H | 3 x 60w MB

Desert Wind Collection
(Page 292)

11900VADB
 18"W x 10"H | 3 x 100w MB

Desert Wind Collection
(Page 292)

11902VADB
 24.5"W x 18"H | 4 x 100w MB

Diamante Collection
(Page 211)

30601WSOI
 16"W x 17"H | 3 x 60w MB

Duo Collection
(Page 172)

11521TCAD
 17"W x 10"H | 2 x 60w, G9 Xenon Incl.

Elegante Collection
(Page 114)

2859 EG, OI
 16.5"W x 10.5"H | 3 x 60w CA

Elite Collection
(Page 274)

32001BTPS
 16"W x 12"H | 2 x 100w MB

Fremont Collection
(Page 39)

22241WSPD
 21"W x 12"H | 3 x 60w MB

Fremont Collection
(Page 39)

22242WSPD
 31"W x 19.5"H | 4 x 100w MB

Genoa Collection
(Page 13)

17001MCMD
 20"W x 19.5"H | 3 x 100w MB

Hampton Collection
(Page 17)

12021FTAD
 20"W x 13"H | 3 x 60w MB

Infinity Collection
(Page 179)

21302WSOI
 18"W x 14.5"H | 3 x 60w MB

La salle Collection
(Page 68)

16001MCHA
 22"W x 16"H | 3 x 100w MB

La Scalla Collection
(Page 53)

11761MCWC
 20"W x 18"H | 3 x 100w MB

Linda Collection
(Page 256)

11801ICBK
 19"W x 16.5"H | 3 x 100w MB

Linda ES Collection
(Page 256)

85802WSOI
 19"W x 16.5"H | 3 x 13w GU24

Manor Collection
(Page 147)

12201FIOI
 19.5"W x 15"H | 2 x 100w MB

Mission Bay Collection
(Page 195)

12420FLHB
 13"W x 10"H | 2 x 100w MB

Moda Collection
(Page 187)

12301KLFN
 16"W x 15.5"H | 2 x 100w MB

Morocco Collection
(Page 88)**20678VAWB**
23.75"W x 21"H | 3 x 100w MB**Oak Harbor Collection**
(Page 199)**21076FLRB**
18"W x 13"H | 2 x 100w MB**Ophelia Collection**
(Page 175)**32301BLCU**
22.5"W x 13.5"H | 3 x 60w MB**Pacific Collection**
(Page 227)**2652 MRAC, MRPE**
18.5"W x 15"H | 3 x 75w MB**Pacific Collection**
(Page 227)**2652 MRKB, WSKB**
18.5"W x 15"H | 3 x 75w MB**Palazzo Collection**
(Page 76)**12281VSAP**
17.5"W x 15"H | 3 x 100w MB**Paradise Collection**
(Page 10)**39940CYBCPS**
20"W x 12"H | 3 x 100w MB**Portello Collection**
(Page 223)**11741WSMA**
16"W x 17"H | 2 x 100w MB**Portofino Collection**
(Page 82)**20281VAOI**
17.5"W x 15"H | 3 x 100w MB**Richmond Collection**
(Page 44)**31001WSCU**
22.5"W x 13.5"H | 3 x 60w MB**Sausalito Collection**
(Page 49)**21120MCFL**
16"W x 9.5"H | 3 x 60w MB**Sausalito Collection**
(Page 49)**21121MCFL**
18"W x 15.5"H | 3 x 60w MB**Sherwood Collection**
(Page 294)**32441EFPD**
16"W x 9"H | 3 x 60w MB**Soho Collection**
(Page 158)**11052 SVOI, SVSN**
15.75"W x 21"H | 2 x 100w MB**South Bend Collection**
(Page 245)**10150 FTSN, WSOI**
12"L x 9.5"W x 15.5"H | 1 x 100w MB**South Bend Collection**
(Page 245)**10151 FTSN, WSOI**
12.75"W x 9"H | 2 x 100w MB**Stratus Collection**
(Page 252)**2670 MRBZ, MRPE**
14.5"W x 9.5"H | 3 x 100w MB**Symphony Collection**
(Page 121)**11241 SAOI, SVOI**
22.5"W x 13"H | 3 x 60w MB**Vail Collection**
(Page 262)**12500CINI**
13"W x 6.5"H | 2 x 100w MB**Via Roma Collection**
(Page 133)**2781SVGB**
18"W x 12.5"H | 2 x 75w MB



5829 CLPB, CLSN
14.5"W x 14"H | 2 x 100w MB



KIT

5833 FTOI, FTPB, FTPE
14.5"W x 14"H | 2 x 100w MB



KIT

5833 FTSN, FTTW, FTWT
14.5"W x 14"H | 2 x 100w MB



KIT

5843 MRAC, MRCS, MROI
17"W x 14"H | 3 x 100w MB



KIT

5843 MRPB, MRPE, MRSN
17"W x 14"H | 3 x 100w MB



KIT

5843 MRWT, WSOI
17"W x 14"H | 3 x 100w MB



5844 MROI, MRSN
17"W x 14"H | 3 x 100w MB

Allentown Collection
(Page 142)**93505WSOI**
8"W | 1 x 100w MB**Asiana Collection**
(Page 283)**91082WSRC**
5.5"W | 1 x 100w MB**Aspen Collection**
(Page 98)**91044VAOI**
6"W | 1 x 100w MB**Augusta Collection**
(Page 64)**91560CFAN**
7"W | 1 x 100w MB**Aurora Collection**
(Page 268)**92090 FTOI,FTSN**
8"W | 1 x 100w MB**Barcelona Collection**
(Page 94)**91412AIOI**
7"W | 1 x 100w MB**Basix Collection**
(Page 303)**91064 ICSN, WSOI**
6.5"W | 1 x 100w MB**Basix ES Collection**
(Page 336)**85139ICSN**
6.5"W | 1 x 13w GU24**Beaumont Collection**
(Page 72)**94100CFGF**
6.5"W | 1 x 100w MB**Boca Collection**
(Page 156)**91091LTLG**
7"W | 1 x 100w MB**Bristol Collection**
(Page 242)**91320JFBG**
6.25"W | 1 x 100w MB**Cambridge Collection**
(Page 27)**90540MCBN**
6.5"W | 1 x 100w MB**Canyon Rim Collection**
(Page 217)**91057SVCR**
7"W | 1 x 100w MB**Chelsea Collection**
(Page 184)**91880WSWR**
6.5"W | 1 x 100w MB**Cilandro Collection**
(Page 227)**53009WTSN**
5"W | 1 x 60w MB T10**Classique Collection**
(Page 222)**91065AVGB**
7"W | 1 x 100w MB**Contour Collection**
(Page 238)**92260 FTOI,FTSN**
7.5"W | 1 x 100w MB**Cosmopolitan Collection**
(Page 126)**91052FIGC**
7"W | 1 x 100w MB**Cupola Collection**
(Page 260)**92105FLOI**
10"W | 1 x 100w MB**Deco Collection**
(Page 191)**92703WSFN**
5.5"W | 1 x 100w MB

Desert Wind Collection
(Page 292)**11903VADB**
7"W | 1 x 100 w MB**Diamante Collection**
(Page 212)**90600WSOI**
7.5"W | 1 x 100 w MB**Dresden Collection**
(Page 36)**92270EMFL**
7"W | 1 x 100 w MB**Elegante Collection**
(Page 113)**91053 EG, OI**
8"W | 1 x 100 w MB**Fremont Collection**
(Page 40)**92240WSPD**
7"W | 1 x 100 w MB**Infinity Collection**
(Page 180)**91305WSOI**
5.5"W | 1 x 100 w MB**La Salle Collection**
(Page 67)**91600MCHA**
8"W | 1 x 100 w MB**La Scala Collection**
(Page 54)**91005MCWC**
6.5"W | 1 x 100 w MB**Linda Collection**
(Page 257)**91009ICBK**
6"W | 1 x 100 w MB**Linda ES Collection**
(Page 340)**85004WSOI**
6"W | 1 x 13w GU24**Manor Collection**
(Page 148)**92200FIOI**
7"W | 1 x 100 w MB**Mission Bay Collection**
(Page 195)**92420FLHB**
8"W | 1 x 100 w MB**Moda Collection**
(Page 188)**91230KLFN**
6.25"W | 1 x 100 w MB**Newport Collection**
(Page 321)**91064 MROI, MRSN**
6.5"W | 1 x 100 w MB**Notre Dame Collection**
(Page 101)**91084WSOI**
7"W | 1 x 60w CA**Oak Harbor Collection**
(Page 200)**92060FLRB**
6"W | 1 x 100 w MB**Ophelia Collection**
(Page 176)**92300BLCU**
8"W | 1 x 100 w MB**Pacific Collection**
(Page 227)**91068 MRAC, MRKB**
7"W | 1 x 100 w MB**Pacific Collection**
(Page 227)**91068 MRPE, WSKB**
7"W | 1 x 100 w MB**Palazzo Collection**
(Page 76)**92290VSAP**
5"W | 1 x 100 w MB

Piedmont Collection
(Page 234)



91090ICSN
6"W | 1 x 100w MB

Pine Grove Collection
(Page 288)



91051AVPT
8"W | 1 x 100w MB

Portello Collection
(Page 203)



91006WSMA
7"W | 1 x 100w MB

Richmond Collection
(Page 44)



93101WSCU
7"W | 1 x 100w MB

Sausalito Collection
(Page 49)



91120MCFL
5"W | 1 x 100w MB

Soho Collection
(Page 159)



91059 SVOI,SVSN
6"W | 1 x 100w MB

South Bend Collection
(Page 244)



91010 FTSN,WSOI
7.5"W | 1 x 100w MB

Southern Collection
(Page 107)



91092LTKB
7"W | 1 x 100w MB

Spectra Collection
(Page 276)



91063MRSN
7"W | 1 x 100w MB Bulb

Symphony Collection
(Page 121)



91049 SAOI,SVOI
7"W | 1 x 100w MB

Vail Collection
(Page 262)



92500CINI
7"W | 1 x 100w MB

Via Roma Collection
(Page 132)



91071SVGB
7"W | 1 x 100w MB



85066MRSN
7"W | 1 x 13w GU24



91066 MRAC, MRCS, MROI
7"W | 1 x 100w MB



91066 MRPB, MRPE, MRSN
7"W | 1 x 100w MB



91066WSOI
7"W | 1 x 100w MB



91069 MRAC, MRPE
7"W | 1 x 100w MB



91069 MRPB, MRSN
7"W | 1 x 100w MB

References, Displays & Index



Displays



DSP022L MX-L Series Display
White
24"W x 12"H x 12"L

DSP022X12 MX-X12 Series Display
White
24"W x 12"H x 12"L

DSP022X120 MX-X120 Series Display
White
24"W x 12"H x 12"L

DSP024WT Display Riser
White
24"W x 6"H x 9"L



DSP025WT Storage Cabinet
White
24"W x 30"H x 18"L
Interior Shelf



DSP022L120 MX-L120 Series Display
White
24"W x 12"H x 12"L



DSP022FD MX-FD Series Display
White
24"W x 12"H x 12"L

800.486.2946

maximlighting.com



DSP015SV
MX-LD Series Display
Silver
14"W x 12"H x 6"L



DSP010SV
StarStrand Display
Silver
14"W x 12"H x 6"L



DSP002BK Hanging Cloud
Black
60"L x 60"W



DSP001BE Floor Stand
Beige
49"W x 80"H

Selling Cases



DSP016ALSV
CounterMax Selling Case
Silver
27"W x 7"H x 16.5"L



DSP011AL
StarStrand Selling Case
Silver
16.5"W x 4.75"H x 12.5"L

800.486.2946

maximlighting.com

2120...303,393,394	2753.....217	4454.....384	7142.....382	10156..246,386,400
2121...303,393,394	2754.....216	4455.....384	7143.....382	10157..246,386,400
2122.....303,393	2755.....215	4456.....384	7144.....382	10158.....246,386
2123.....303,393	2756.....214	4458.....384	7738.....109	10159.....246,386
2220.....80,403	2757.....215	5000.....277	7750.....109	10160.....244
2221.....79	2758.....214	5002.....277	7751.....112	10161.....246,386
2222.....80,403	2759.....213	5520.....289,405	7755.....111	10970..102,388,399
2223.....79	2760.....222,403	5824.....310	7756.....111	10971..102,388,399
2224.....79	2761.....221,408	5826.....310,405	7759.....112	10972.....102,388
2225.....77	2762.....221	5827.....310,405	7760.....110	10973.....102,388
2226.....78	2763.....221	5828.....310,406	7763.....110	10975.....101
2227.....80	2764.....220	5829.....310,411	7764.....285	10976.....101
2228.....79,394	2765.....220	5830.....310,406	7765.....286	10977.....101
2229.....80,408	2766.....220	5831.....310,406	7766.....285,396	10981.....283,408
2252.....401	2767...222,391,396	5832.....310,406	7767.....285,396	10982.....283
2590.....86,404	2768.....222,391	5833.....310,411	8011.....382,401	10984.....283
2594.....85	2769.....219	5835.....310	8012.....382	10985.....282
2595.....85	2772.....133	5840.....237	8013.....382	10986.....281
2596.....86,398	2773.....131	267,303,309,406	8014.....382	10987.....283
2597.....86,398	2774.....130	5841.....237	8015.....382	10989.....282
2650.....227,405	2775.....131	267,303,309,406	8016.....382	10992..284,393,394
2651.....226	2776.....130	5842.....237	8020...228,387,399	10993.....284,393
2652.....227,410	2777.....130	267,303,309,406	8021...228,387,400	10994.....284,393
2653.....226	2778.....129	5843.....309,411	8022.....228,387	10996..284,393,394
2654.....226	2779.....132	5844.....309,411	8023.....228,387	10998.....283
2655.....224	2780.....133,405	5845.....309	8024.....228,387	11000.....407
2656.....225	2781.....133,410	5846.....309	8025.....227,400	11001.....407
2657.....225	2782.....132	5849.....309,406	8026.....227,400	11031.....152,401
2658.....224	2783.....131	5850.....406	8027...218,392,395	11032.....152,401
2659.....223	2786...134,385,401	5851.....406	8028.....218,392	11033.....152
2670.....252,410	2787...134,385,401	5852.....406	8029.....218,392	11034.....152
2671.....251	2788.....134,385	5855.....406	8030...218,392,395	11035.....151
2672.....251	2789.....134,385	5856.....406	8031.....218,392	11041.....230
2673.....251	2849.....115	5880.....406	8762.....286	11042.....232
2674.....251	2850.....114	5881.....406	8816.....401	11043.....231
2676...252,385,401	2851.....114	5882.....406	8817.....401	11044.....231
2677.....252,385	2852.....113	5883.....406	8832.....128	11045.....229
2678.....252,385	2853.....113	5884.....407	8833.....128	11046.....230
2679.....252,385	2855.....114	5885.....407	8835.....127	11047.....232,399
2680.....317,405	2857.....115,397	5886.....407	8836.....127	11048.....232,399
2681.....317,405	2858.....115,397	5887.....407	8837.....128,397	11049.....158
2682.....317	2859.....114,409	5889.....407	8838.....128,397	11050.....158,405
2683.....315	2863...116,390,397	6151.....322	8839.....128,397	11051.....158
2684.....316	2864.....116,390	6503.....407	10120.....301,408	11052.....158,410
2685.....315	2865.....116,390	6504.....407	10121.....301	11053.....157
2686...318,389,398	2866.....116,390	7101.....308	10122.....300	11054.....157
2687...318,389,398	2890.....83,399	7102.....308	10123.....299	11056..159,386,400
2688.....318,389	2891.....83,399	7103.....307	10124.....301	11057..159,386,400
2689.....318,389	2896.....84	7105.....307	10125.....300	11058.....159,386
2697.....316	2897.....84	7115.....306	10126.....302	11059.....159,386
2698.....316	2899.....83	7123.....383	10127.....302	11060.....317,405
2699.....316	2931.....107	7124.....383	10128.....300	11061.....319
2734.....275	2932.....107	7126.....383	10129.....299	11062.....320
2735.....275	2933.....107	7128.....383	10130.....301	11063.....320
2736...276,385,401	2934.....106	7129.....383	10131.....301	11064.....320
2737...276,385,401	2935.....106	7135.....383,401	10150.....245,410	11065.....319
2738.....276,385	2936.....105	7136.....383	10151.....245,410	11066..321,388,399
2739.....276,385	2937.....108	7137.....383	10152.....245	11067..321,388,399
2750.....216,403	2938.....108	7138.....383	10153.....245	11068.....321,388
2751.....217	2939.....107,400	7139.....383	10154.....243	11069.....321,388
2752.....216,408	4453.....384	7141.....382	10155.....243	11072.....249

11073.....	249	11523.....	171	12020.....	17,404	12501.....	263,385,401	13583.....	61
11074.....	249	11524.....	170	12021.....	17,409	12502.....	263,385,401	13584.....	57
11076.....	250,392,395	11525.....	170	12023.....	17	12503.....	263,385	13585.....	62
11077.....	250,392,395	11526.....	169	12024.....	16	12504.....	263,385	14271.....	163,408
11078.....	250,392	11528.....	172,397	12025.....	16	12505.....	261	14272.....	163
11079.....	250,392	11529.....	172,397	12026.....	16	12506.....	261	14273.....	163
11084.....	247	11541.....	233	12027.....	15	12508.....	262	14275.....	162
11086.....	248,392,395	11542.....	234	12028.....	18	12700.....	191,404	14276.....	161
11087.....	248,392,395	11543.....	234	12029.....	18	12702.....	191	14281.....	164,389,396
11088.....	248,392	11544.....	233	12030.....	18	12703.....	192,391,396	14282.....	164,389,396
11089.....	248,392	11545.....	233	12032.....	17,397	12704.....	190	14283.....	164,389
11092.....	247	11547.....	234,400	12201.....	147,409	12705.....	190	14284.....	164,389
11093.....	247	11670.....	155	12202.....	145	12706.....	189	15844.....	312
11170.....	137,403	11671.....	155,408	12203.....	144	12708.....	192,391,396	15845.....	312
11171.....	137,403	11672.....	155	12204.....	145	12709.....	192,391	15846.....	312
11172.....	137,408	11673.....	154	12205.....	145	12710.....	192,391	16000.....	68,404
11173.....	136	11674.....	154	12206.....	147	12711.....	191	16001.....	68,409
11174.....	137	11675.....	153	12207.....	147	13410.....	93,408	16002.....	68
11175.....	136	11677.....	156,395	12208.....	147	13411.....	91	16003.....	68
11176.....	136	11679.....	156	12209.....	146	13412.....	92	16004.....	67
11177.....	135	11739.....	203,405	12211.....	148,388,398	13413.....	90	16005.....	67
11181.....	138,392,395	11740.....	203,405	12212.....	148,388,398	13414.....	92	16006.....	66
11182.....	138,392,395	11741.....	203,410	12213.....	148,388	13415.....	90	16007.....	65
11230.....	122,385,401	11742.....	204,386,400	12214.....	148,388	13416.....	90	17000.....	13,404
11231.....	122,385	11743.....	202	12215.....	144	13417.....	89	17001.....	13,409
11232.....	122,385	11744.....	202	12216.....	144	13418.....	91	17002.....	12,397
11233.....	122,385	11745.....	201	12217.....	145,398	13419.....	94,394	17003.....	12,397
11234.....	121	11746.....	204,386	12218.....	145,399	13420.....	93	17004.....	13
11235.....	120	11747.....	204,386,400	12219.....	143	13421.....	92	17005.....	12
11238.....	120	11748.....	204,386	12280.....	76,405	13422.....	94,393,394	17006.....	11
11239.....	119	11760.....	53,404	12281.....	76,410	13423.....	94,393	17008.....	13
11240.....	121,405	11761.....	53,409	12282.....	76	13424.....	94,393	20052.....	117
11241.....	121,410	11763.....	53	12290.....	75	13500.....	141,403	20054.....	117
11242.....	121	11764.....	52	12292.....	73	13501.....	141,408	20091.....	267,408
11244.....	119	11765.....	51	12293.....	75	13503.....	141	20093.....	267
11245.....	120	11766.....	53	12294.....	74	13504.....	141	20094.....	266
11246.....	122,385,401	11767.....	54,389,398	12295.....	74	13505.....	140	20095.....	266
11247.....	122,385,401	11769.....	52	12300.....	187,405	13506.....	140	20096.....	266
11250.....	125,403	11771.....	54,389,398	12301.....	187,409	13507.....	139	20097.....	265
11253.....	125	11772.....	54,389	12302.....	187	13509.....	141	20098.....	268,393,394
11255.....	124	11773.....	54,389	12304.....	186	13511.....	142,388,394	20099.....	268,393,394
11256.....	124	11799.....	257,404	12305.....	186	13512.....	142,388,394	20100.....	268,393
11257.....	124	11800.....	257,404	12306.....	186	13513.....	142,388	20101.....	268,393
11258.....	123	11801.....	256,409	12307.....	187	13514.....	142,388	20113.....	118
11259.....	123	11802.....	256	12311.....	188,388,399	13560.....	61,403	20116.....	118,398
11262.....	126,391,396	11804.....	254	12312.....	188,399	13561.....	61,403	20117.....	118,398
11263.....	126,391	11805.....	255	12313.....	188,388	13562.....	61,408	20165.....	110
11264.....	126,391	11806.....	254	12314.....	188,388	13563.....	61	20200.....	296,403
11265.....	126,391	11807.....	258,389,398	12315.....	188,388	13564.....	63	20202.....	296
11268.....	125	11808.....	258,389,398	12317.....	185	13565.....	63	20203.....	295
11269.....	125	11809.....	253	12420.....	195,409	13566.....	62	20204.....	296
11290.....	208,403	11810.....	258,389	12422.....	195	13567.....	60	20205.....	295
11291.....	208,408	11811.....	258,389	12423.....	195	13569.....	59	20206.....	297,394
11292.....	206	11812.....	256	12425.....	194	13571.....	64,393,394	20207.....	297,394
11293.....	207	11815.....	255	12426.....	193	13572.....	64,393,394	20208.....	297
11294.....	207	11900.....	292,409	12429.....	194	13573.....	64,393	20209.....	297
11295.....	208	11901.....	292,396	12431.....	196,388,399	13574.....	64,393	20280.....	81,405
11296.....	206	11902.....	292,409	12432.....	196,388,399	13575.....	57	20281.....	82,410
11297.....	205	11903.....	292,413	12433.....	196,388	13576.....	58	20283.....	82
11521.....	172,409	11904.....	291	12434.....	196,388	13577.....	56	20284.....	82
11522.....	171	11905.....	291	12500.....	262,410	13579.....	55	20285.....	81

20286.....	8 1	21074.....	200,387	21435.....	280	24111....	72,392,395	323 11..	176,387,399
20289.....	8 2	21075.....	199,405	21436.....	279	24112....	72,392,395	323 12.....	176,387
20325.....	304	21076.....	199,410	21441.....	280,397	24113.....	72,392	323 13..	176,387,399
20326.....	304	21077.....	199	21442.....	280,397	24114.....	72,392	323 14.....	176,387
20580.....	401	21079.....	199	22100.....	260,403	27510.....	216,403	32441.....	294,410
20581.....	401	21120.....	49,410	22101.....	260,409	27511.....	217	32443.....	294
20582.....	402	21121.....	49,410	22103.....	260	27512.....	215	32445.....	294
20583.....	402	21123.....	49	22104.....	259	30530.....	27,403	32446.....	293
20585.....	402	21124.....	48	22105.....	259	30531.....	27,408	32447.....	293
20601.....	98,403	21125.....	48	22106.....	259	30532.....	26	32448.....	293,400
20602.....	98,403	21126.....	48	22107.....	260,396	30533.....	26	39940.....	10,410
20606.....	98	21127.....	47	22240.....	39,404	30534.....	25	39942.....	10,400
20607.....	95	21131.....	50,386,400	22241.....	39,409	30535.....	24	39943.....	10
20610.....	96	21132.....	50,386,400	22242.....	39,409	30536.....	24	39944.....	8
20612.....	97	21133.....	50,386	22243.....	39	30537.....	25	39945.....	9
20613.....	96	21134.....	50,386	22244.....	40	30538.....	23	39946.....	8
20614.....	95	21140.....	167,405	22245.....	37	30541....	28,391,395	39947.....	7
20617.....	99,394	21141.....	168,389,398	22246.....	38	30542....	28,391,395	39948.....	9
20618.....	99,394	21142.....	168,389,398	22247.....	38	30543.....	28,391	53006.....	277,396
20619.....	99,384	21144.....	166	22248.....	37	30544.....	28,391	53009.....	277,412
20620.....	97	21145.....	166	22250.....	39	30545.....	22	53030.....	332,404
20627.....	100	21147.....	165	22251.....	40,390,397	30546.....	22	53031.....	332,404
20628.....	100	21148.....	168	22252.....	40,390,397	30547.....	22	53032.....	332,404
20633.....	104,401	21149.....	167	22253.....	40,390	30551.....	21,395	53034.....	331,404
20635.....	103	21251.....	272,408	22254.....	40,390	30552.....	21,395	53035.....	331,404
20637.....	104	21253.....	271	22260.....	32,404	30554.....	20	53036.....	331,404
20671.....	88,399	21255.....	271	22261.....	32,409	30555.....	20	53200.....	363
20673.....	88,399	21258.....	272,394	22262.....	32	30557.....	21	53210.....	365
20674.....	88	21259.....	272	22263.....	32	30558.....	19	53211.....	365
20676.....	87	21261.....	237,408	22264.....	33	30600.....	211,404	53212.....	365
20677.....	87	21263.....	237	22265.....	34	30601.....	216,409	53213.....	365
20678.....	88,410	21264.....	237	22266.....	34	30603.....	211	53214.....	365
20700.....	288,405	21265.....	236	22268.....	33	30604.....	211	53220.....	367
20702.....	289	21266.....	236	22269.....	35	30605.....	210	53221.....	367
20705.....	288	21267.....	235	22271.....	35,390,396	30606.....	209	53222.....	367
20706.....	288,400	21271.....	238,391,396	22272.....	35,390,396	30609.....	210	53223.....	367
20707.....	287	21272.....	238,391	22273.....	36,390	30611....	212,390,396	53224.....	367
20708.....	289,400	21273.....	238,391	22274.....	36,390	30612....	212,390,396	53230.....	369
20716....	290,387,400	21274.....	238,391	22275.....	36,390	30613.....	212,390	53231.....	369
20717....	290,387,400	21302.....	179,409	22281.....	31,396	30614.....	212,390	53232.....	369
20718.....	290,387	21303.....	179	22282.....	31,397	31000.....	44,405	53233.....	369
20719.....	290,387	21304.....	178	22283.....	30	31001.....	44,410	53241.....	371
20742.....	46	21305.....	179	22285.....	30	31003.....	44	53242.....	371
20743.....	46	21306.....	178	22286.....	31	31005.....	43	53243.....	371
20744.....	45	21307.....	177	22288.....	29	31006.....	42	53252.....	364
20880.....	183,403	21311....	180,390,397	23003.....	269	31007.....	41		366,368,370
20881.....	183,408	21312....	180,390,398	23005.....	269	31009.....	43	53253.....	374,376,378
20883.....	183	21313.....	180,390	23011....	270,386,400	32001.....	274,409	53254....	364,366,368
20885.....	182	21314.....	180,390	23012.....	270,386	32002.....	274,397		370,372,374,376
20886.....	182	21321.....	241,408	23013.....	270,386	32003.....	274,397	53255.....	364,366
20887.....	181	21322.....	241	23014.....	270,386	32004.....	273		368,370,374,376
20888....	184,391,396	21323.....	241	24100.....	71,403	32005.....	274	53256.....	364
20990....	184,391,396	21325.....	240	24101.....	71,403	32006.....	273		366,368,370
20991.....	184,391	21326.....	239	24102.....	71,408	32300.....	175,405	53257.....	364
20992.....	184,391	21327....	242,387,395	24103.....	71	32301.....	175,410	53257....	366,368,370
21063....	200,387,399	21328....	242,387,395	24104.....	71	32302.....	175	53259.....	364
21065.....	198	21329.....	242,387	24105.....	69	32303.....	173	53260.....	364
21066.....	198	21330.....	242,387	24106.....	70	32305.....	174	53261.....	364
21067.....	197	21430.....	280,404	24107.....	69	32306.....	174	53262.....	364
21072....	200,387,399	21433.....	280	24108.....	70	32307.....	173		366,368,370
21073.....	200,387	21434.....	279	24109.....	70	32309.....	175	53263.....	364,366

53263.....	368,370	85121.....	335	87807.....	361	91059.....	159,414	DSP016ALSV... 4 18
53264.....	364	85125.....	334	87808.....	361	91061.....	311	DSP022FD..... 4 16
	366,368,370	85128.....	333	87809.....	361	91062.....	247	DSP022L..... 4 16
53265.....	364	85131..	336,393,394	87817.....	355	91063.....	276,414	DSP022L120... 4 1 6
	366,368,370	85132..	336,393,395	87818.....	355,357	91064.....	303	DSP022X12..... 4 1 6
53266.....	364	85133.....	336,393	87819.....	355,357		321,412,413	DSP022X120... 4 1 6
	366,368,370	85134.....	336,393	87820.....	355,357	91065.....	222,412	DSP 02 4W T..... 4 1 6
53267.....	364	85139.....	335,412	87830.....	360	91066.....	414	DSP 02 5W T..... 4 1 6
	366,368,370	85213.....	352	87831.....	360	91068.....	227,413	FCTHAND..... 3 2 6
53268.....	364	85214.....	352	87832.....	360	91069.....	414	FKT205..... 3 2 8
	366,368,370	85215.....	351	87833.....	360	91071.....	132,414	FKT206..... 3 2 8
53269.....	364	85216.....	351	87834.....	360	91076.....	311	FKT207..... 3 2 8
	366,368,370	85217.....	351	87849.....	358	91078.....	311	FKT2012... 3 0 2, 3 2 9
53270.....	372	85218.....	352	87850.....	356,358	91082.....	283,412	FKT2210..... 3 2 9
53271.....	372	85219.....	352	87851.....	358	91084.....	101,413	FKT2341..... 3 2 9
53272.....	366	85222.....	351	87852.....	358	91090.....	234,414	FRD12..... 3 2 7
	368,370,372	85585.....	353,402	87853.....	358	91091.....	156,412	FRD18..... 3 2 7
53273.....	374,376	85800.....	338,404	87856.....	356,358	91092.....	107,414	FRD24..... 3 2 7
53275.....	364	85801.....	338,404	87857.....	356,358	91101.....	311	FRD36..... 3 2 7
	366,368,370	85802.....	339,409	87858.....	356,358	91102.....	305	FRD48..... 3 2 7
53276.....	364	85803.....	339	87859.....	359	91120.....	49,414	FRD60..... 3 2 7
	366,368,370,377	85804.....	339	87860.....	356,358	91193.....	305	FRD72..... 3 2 7
53277.....	366	85805.....	338	87861.....	359	91195.....	305	HOK04 SN..... 1 1 2
	368,370,377	85806.....	337	87862.....	359	91196.....	306	MED00 1AF..... 6 3
53278.....	372	85807..	340,389,398	87863.....	359	91197.....	306	MED002CU.. 4 2, 17 4
53279.....	372	85808..	340,389,398	87881.....	357	91230.....	188,413	MED003CU..... 4 2
53282..	364,366,368	85809.....	340,389	87883.....	357	91305.....	180,413	MED003GF..... 6 9
53284.....	370	85810.....	340,389	87902.....	355	91320.....	242,412	SHD123WH..... 143
53287..	374,376,378	85830.....	341,407	87904.....	355	91412.....	94,412	SHD23KB..... 111
53288..	374,376,378	85831.....	341,407	87906.....	355	91560.....	64,412	SHD40BL..... 81
53292..	364,366,368	85832.....	341,407	87912.....	356	91600.....	67,413	SHD42PD..... 287
53294.....	370	85840.....	341,407	87913.....	356	91880.....	184,412	SHD46VN..... 84
53410.....	373	85841.....	341,407	87914.....	356	92010.....	313	SHD49WT..... 118
53411.....	373	85842.....	341,407	87916.....	356	92011.....	313	SHD62TN.. 4 2, 5 6, 5 8
53412.....	373	85880.....	342	87951.....	343	92060.....	200,413	SHD90 GS..... 20, 30
53413.....	373	85881.....	342	87952.....	343	92090.....	268,412	SHD91 GS..... 19, 29
53414.....	373	85889.....	342	89905.....	325	92105.....	260,412	
53420.....	375	87005.....	348	89915.....	326	92200.....	148,413	
53421.....	375	87006.....	348	89930.....	324	92240.....	40,413	
53422.....	375	87007.....	348	89930/FKT2341... 93		92260.....	238,412	
53423.....	375	87011.....	346	90180.....	317	92270.....	36,413	
53424.....	375	87012.....	346	90182.....	317	92290.....	76,413	
53464.....	374,376	87015.....	344	90188.....	311	92300.....	176,413	
53465.....	374,376	87016.....	344	90328.....	323	92305.....	314	
53467.....	374,376	87017.....	344	90329.....	323	92310.....	313	
53468.....	374,376	87200.....	347	90330.....	323	92315.....	314	
53469.....	374,376	87201.....	347	90350.....	322	92320.....	314	
60201.....	322	87202.....	347	90540.....	27,412	92420.....	195,413	
61501.....	322	87205.....	347	90600.....	212,413	92500.....	262,414	
61601.....	322	87206.....	347	91000.....	311	92703.....	191,412	
70001.....	150,398	87207.....	347	91005.....	54,413	93101.....	44,414	
70002.....	150,398	87210.....	345	91006.....	203,414	93505.....	142,412	
70003.....	150	87211.....	345	91009.....	257,413	94100.....	72,412	
70005.....	150	87212.....	345	91010.....	244,414	97006.....	289	
70006.....	149	87521.....	349	91040.....	250	DIF001WT..... 227		
75137.....	402	87522.....	349	91044.....	98,412	DIF002WT..... 227		
82681.....	342,407	87530.....	350	91049.....	121,414	DSP001BE..... 417		
85004.....	340,413	87531.....	350	91051.....	288,414	DSP002BK..... 417		
85066.....	353,414	87803.....	355,357	91052.....	126,412	DSP010SV..... 417		
87520.....	349	87805.....	361	91053.....	113,413	DSP011AL..... 418		
85120.....	335,408	87806.....	361	91057.....	217,412	DSP015SV..... 417		

Conversion Kits

Conversion Kits are available to convert specified semi-flush mounts to invert bowl pendants. Included in the kit is a canopy, chain and extra loop to screw to the top of the semi-flush mount, all in matching finish.

CKT001AC Conversion Kit
Acorn
Compatible with **5843MRAC**

CKT001CS Conversion Kit
Country Stone
Compatible with **5843MRCS**

CKT001OI Conversion Kit
Oil Rubbed Bronze
Compatible with **5833FTOI, 5843MROI, 5843WSOI & 10120WSOI**

CKT001PE Conversion Kit
Pewter
Compatible with **5833FTPE, 5843MRPE**

CKT001SN Conversion Kit
Satin Nickel
Compatible with **5833FTSN, 5843MRSN & 10120ICSN**

Diffusers

Diffusers are used to conceal light clusters in pendants and wall sconces. Many of Maxim Lighting's invert bowl pendants have diffusers built in or included. Optional diffusers are also available.



DIF001WT Diffuser
White
Compatible with **8025MRAC, 8025MRBK, 8025MRKB, 8025MRSN and 8025WSKB**



DIF002WT Diffuser
White
Compatible with **8026MRSN**

Finishes

AC Acorn	EG Etruscan Gold	MW Matte White	SST Stainless Steel
AD Auburn Dusk	FF French Floral	NI Natural Iron	SV Silver
AF Auburn Florentine	FL Filbert	OI Oil Rubbed Bronze	TT Textured Terra
AP Antique Pecan	FN Florentine	PB Polished Brass	TW Textured White
BC Bali Collection	GA Golden Auburn	PBPC Polished Brass/Chrome	VC Vintage Copper
BG Black Gold	GB Greek Bronze	PC Polished Chrome	VI Vienna Ivory
BK Black	GC Grand Canyon	PD Platinum Dusk	WB Windsor Bronze
BM Brushed Metal	GF Golden Fawn	PE Pewter	WC Weathered Copper
BN Brighton	HA Honey Auburn	PS Plated Silver	WR Weathered Russet
BZ Bronze	HB Heirloom Brass	PT Pine Tree	WT White
CH Chocolate	KB Kentucky Bronze	RB Rustic Burnished	
CR Canyon Rock	LG Light Gold	RC Roasted Chestnut	
CS Country Stone	MA Mahogany	RE Rustic Ebony	
CU Colonial Umber	MB Metallic Bronze	SA Satin Aluminum	
DB Desert Bronze	MD Modello	SN Satin Nickel	

Glass

AI	Amber Ice	EF	Early Frost	JF	Java Fog	SV	Soft Vanilla
AV	Amber Vanilla	EM	Ember	KL	Karmel	TC	Textured Clear
BL	Burnished Lichen	EV	Embossed Vanilla	LT	Latte	VA	Vintage Amber
CD	Seedy	FI	Frosted Ivory	MC	Mocha Cloud	VS	Vanilla Swirl
CF	Cafe	FL	Frost Lichen	MR	Marble	WH	Wheat
CI	Clear Ice	FT	Frosted	SA	Screen Amber	WI	White Ice
CL	Clear	IC	Ice	SC	Stone Candle	WS	Wilshire
CY	Crystal	JA	Java Swirl	SI	Screen Ivory	WT	White

Shades

BI	Burnt Ivory	CH	Champagne	KB	Kentucky Bronze	VN	Vanilla
BL	Beige Linen	GR	Grass Reed	PD	Ponderosa	WH	Wheat
BT	Black Tie	GS	Golden Sheen	RT	Rattan	WT	White
CC	Country Cottage	GT	Golden Taupe	TN	Tan		



Catalog Legend



Energy Star
Certified

Installing new ENERGY STAR qualified light fixtures is a smart way to save energy and money. Maxim Lighting is proud to be a ENERGY STAR partner. Look for this ENERGY STAR logo to find Maxim Lighting fixtures that use 1/4 of the energy of traditional incandescent fixtures and last up to 10 times longer. More information on ENERGY STAR can be found on the ENERGY STAR web site at energystar.gov.



California
Title 24

All new homes, additions, alterations and most commercial buildings in California must meet minimum energy efficiency standards contained in Title 24, Part 6 of the California Code of Regulations. When you see the California Title 24 symbol next to a Maxim Lighting fixture, you can be assured that the fixture complies. More information on California Title 24 can be found on the California Energy Commission web site at energy.ca.gov/title24.



Installs
Up or Down



Installs
on Slope
Ceiling

















Diffuser
Available




Conversion
Kit

Lamping Guide

Code	Description	Type	Code	Description	Type
 R20	R Shape Medium Base 2.5" W	Incandescent	 R30	R Shape Medium Base 3.75" W	Incandescent
 CA	Candelabra Base	Incandescent	 T5	Tubular Mini Bipin Base .625" W	Fluorescent
 G9	T Shape Bi-Pin (G9) Base .5" W	Xenon	 T8	Tubular Medium Bipin Base 1" W	Fluorescent
 GU24	CFL GU24 Bi-Pin Base	Fluorescent	 Circline T9	Tubular Circline 4 Pin Base 1.125" W	Fluorescent
 MB	Medium Base	Incandescent	 Circline T5	Tubular Circline 2GX13 Base .625" W	Fluorescent
 MBT10	T Shape Medium Base 1.25" W	Incandescent	 G8	T4 Bi-Pin (G8) Base	Xenon
 PAR30	PAR Shape Short Neck Medium Base 3.75" W	Halogen	 Wedge	T5 Mini Wedge Base	Xenon

Replacement Bulbs

Item	Type	Code	Note	Watts
BUFPL13004	Fluorescent	GU24	Long Shape	13
BUFPL13026	Fluorescent	GU24	Squat Shape	13
BUFPL18005	Fluorescent	GU24	Long Shape	18
BUFPL26006	Fluorescent	GU24	Long Shape	26
BUFT508011	Fluorescent	T5	12" Long	8
BUFT513012	Fluorescent	T5	21" Long	13
BUFT516013	Fluorescent	T5	24" Long	16
BUFT521014	Fluorescent	T5	36" Long	21
BUFT522001	Fluorescent	Circline T5		22
BUFT526015	Fluorescent	T5	48" Long	26
BUFT532002	Fluorescent	Circline T5		32
BUFT540003	Fluorescent	Circline T5		40
BUFT922018	Fluorescent	Circline T9		22
BUFT932019	Fluorescent	Circline T9		32
BUFT940020	Fluorescent	Circline T9		40
BUX20016	Xenon	G8		20
BUX20023	Xenon	Wedge		20
BUX40024	Xenon	G9	Clear	40
BUX60028	Xenon	G9	Frosted	60
BUX60029	Incandescent	MBT10		60



Maxim Lighting is a registered trademark of Maxim Lighting International, Inc. CounterMax and StarStrand are trademarks of Maxim Lighting International, Inc. All designs, logos, products and images © Copyright 2010 Maxim Lighting International, Inc. All Rights Reserved.

LMXCAT0910
\$5.00



Maxim Lighting International

253 North Vineland Avenue
City of Industry, California
91746
USA

General Info: 626.956.4200
Customer Service: 800.486.2946
General Fax: 626.956.4235

Dallas Trade Mart: 214.748.8455
Showroom: 3901
Email: info@maximlighting.com
Web: www.maximlighting.com

Maxim Lighting and all designs, logos and images ©2010 Maxim Lighting International. All Rights Reserved. Printed in China