


RACK-A-TIERS®
SPECIALTY ELECTRICAL TOOLS



2015-2016 PRODUCT CATALOGUE



RELIABLE RUGGED RUSTPROOF VERSATILE
WATERPROOF INTERLOCKING PAIRS EASY SETUP

E-Z ROLL


The E-Z Roll Wire Rack is the ultra compact and collapsible wheeled wire dispenser. When you're ready to pull wire, wheel the E-Z Roll into position and dispense wire directly from your pipe bender or 1" EMT.



*PIPE NOT INCLUDED
Part# 55455

- FEATURES:**
- Rigid steel construction
 - Light-weight design
 - Compact (fits in any job box)
 - 150 lbs load tested
 - Holds reels up to 24"
 - Replacement wheels available

GET THE ONE TOOL



THAT DOES IT ALL

BIG EZ

The Big E-Z Wire Rack is the ultra compact and collapsible wheeled wire dispenser. When you're ready to pull wire, wheel the Big EZ into position and dispense wire directly from your pipe bender or 1" EMT.



(Pipe Not Included)
Part# 55632


- FEATURES:**
- Rigid steel construction
 - Light-weight design
 - Compact (fits in any job box)
 - Holds up to 32"
 - 300 lbs load tested
 - Durable steel wheels



RACK-A-TIERS WIRE DISPENSER

Part# 11455

THE RACK-A-TIERS WIRE DISPENSER IS THE ONE TOOL THAT DOES IT ALL. IT'S NO SURPRISE THAT WE'VE SOLD HUNDREDS OF THOUSANDS OF THEM TO ELECTRICIANS EVERYWHERE. THIS GENIUS INVENTION IS MOST COMMONLY USED FOR DISPENSING WIRE FROM SPOOLS OF VARIOUS SIZES. SEE FOR YOURSELF ITS MANY OTHER USES!



THE RACK-N-GO

GET MOVING WITH THE RACK-N-GO!

Easily mount your Rack-A-Tiers wire dispenser onto the mobile Rack-N-Go framework. The Rack-N-Go expands supporting up to a 42" wide spindle.

- Locking casters keeps your Racks in place while dispensing
- Roll your wire spools and dispensers easily through a building
- Collapsed 16" x 32"
- Expanded 16" x 52"
- 320 lbs load tested



Part# 11460

Hooker

PIPE WRENCH ADAPTER

The Hooker Pipe Wrench Adaptor lets you turn your Rack-A-Tiers Wire Dispensers into a pipe vise.

FEATURES


- Light weight
- Easy to use
- Fast implementation
- Inexpensive
- To be used with an 18" rigid pipe wrench



Part# 10455

The X-Dispenser

FOLDING WIRE CADDY



Features:

- Folds to 1" wide to easily fit in your van
- Easy to carry: 1" x 23"
- Holds up to six reels of wire

Maximum spool quantity: 6 reels
 500' of #10 AWG wire
 Maximum spool diameter: 8"
 Max spool width: 9"



Part# 11655

THE STICK

STUD MOUNTED WIRE DISPENSER

The Stick installs quickly & easily to any standard stud. Its compact design allows for easy storage once the job is complete.

Part# 11555



FEATURES:

- Weight capacity: 200Lbs.
- Maximum 15" reel width

Part# 18455

WIRE TUB

The Wire Tub allows you to easily dispense and rewind wire. Don't waste a single foot of wire -- rewind it in the Wire Tub and get ready for installation!

FEATURES

- 360 degree feed adjusts automatically for easy dispensing
- 3-way adjustable center hub
- Removable top plate has a handle for rewinding wire!
- Large 24" diameter capacity
- Great for data cable



THREE EASY STEPS! 1. SCREW TO BASE OF REEL 2. FLIP OVER REEL 3. PULL WIRE!



TUG WISE

STANDARD MODEL (15" x 15")

- 4 screw holes for easy attachment
- Works with wooden and plastic reels
- Standard model can handle up to 1000 lbs


Part# 11931

TUG WISE Deluxe

DELUXE MODEL (21.5" x 21.5")

- 4 screw holes for easy attachment
- Works with wooden and plastic reels
- Deluxe model can handle up to 2000 lbs
- Deluxe model is made of 3/8" thick aluminum alloy and built to handle anything

Part# 11932



See It In Action



Pocket Kart



Save your fingertips! Start using the Pocket Kart to easily carry wire reels of all sizes. Just slip it in and pick it up.

FEATURES

- Light weight
- Swivelling handle
- Folds up when not in use
- Fits in pouches
- Fits in pockets
- Holds up to 200 lbs



Part# 56000

Top Seller

CADDY MAC 2

CADDY MAC #2 HOLDS 16 SPOOLS OF #10 AWG OR 24 SPOOLS OF #12 AWG. HINGE DESIGN ALLOWS EASY ACCESS TO ALL SPOOLS FOR WIRE DISPENSING AND FOLDS FOR COMPACT STORAGE.

SPINDLES SWING OUT TO SET POSITION FOR CONVENIENT LOADING OF WIRE SPOOLS.

INNER SPINDLES STORE IN SPECIAL LOOPS WHICH CAN HOLD FOUR PIECES AND WILL NOT FALL OUT DURING TRANSPORTATION.



Part# 11902

Number of Spools	Max Spool Dia	Load Capacity	Weight	Width	Additional Features
16-#10 awg. or 24-#12 awg.	7.5 in 19 cm	400 lbs 180 Kg.	64 lb. 29 kg.	26 in 66 cm	Folds up for compact storage.



REEL MAC THE REAL JACK

REEL MAC 70

Screw type telescoping reel jack for 46 to 96" diameter reels.

REEL MAC 60

Screw type telescoping reel jack for 26-56" diameter reels.

REEL MAC 80

Heavy duty ratchet drive reel jack for reels up to 90" in diameter. Convenient, detachable ratchet handle stores in base when not in use.



Reel Mac 60 - Part# 11860 Reel Mac 70 - Part# 11870 Reel Mac 80 - Part# 11880

REEL MAC SPLINDLES

Used with Reel Mac reel jacks. (Sold separately)



REEL MAC & JACK-A-TIER				
Description	Part #	Reel Diameter	Capacity	Weight
Reel Mac #60	11860	26-56"	2500lb	27lbs
Reel Mac #70	11870	46-96"	2500lb	46lbs
Reel Mac #80	11880	up to 90"	3750lb	99lbs
Jack-A-Tiers #75	11875	46-92"	2500lb	34lbs

Corresponding SPINDLES				
Description	Part #	Dimensions	Capacity	Weight
#61	11861	2 3/8" x 62"	5000lb	39lbs
#71	11871	2 3/8" x 76"	5000lb	47lbs
#81	11881	3 1/2" x 100"	7500lb	119lbs
#71	11871	2 3/8" x 76"	5000lb	47lbs

THE MAC LINE

SPOOL MAC

Part# 11900

FEATURES:

- All steel frame construction
- 10" wheels
- Easy set-up for cable dispensing
- No loose pieces
- Compact storage
- Fits through 32" (81 cm) doorways
- 350 lb (160 kg) load capacity
- Priced right – built to last

Max Reel Width	Max Spool Dia.	Reel Capacity	Weight	Width	Additional Features
25 in 63.5 cm	40 in 101 cm	350 lbs 160 kg	80 lbs 36.4 kg	31.5 in 80 cm	All steel frame, easy set-up for cable dispensing. Compact storage. Ship weight: 150 lbs



CADDY MAC 1

Part#11901

- Caddy Mac #1 transports spools on spindles and works as a dolly! Wire is dispensed while laying flat.
- 1/2" solid spindles are attached to cart, no loose pieces. Spindles lock in place, even during transportation.
- Spindles swing out to set position for convenient loading of wire spools.

Number of Spools	Max Spool Dia.	Load Capacity	Weight	Width	Additional Features
8-#10 awg. or 12-#12 awg.	7.5 in 19 cm	200 lbs 90 kg	50 lbs 23 kg	26 in 66 cm	Transports spools on spindles and works as a dolly. Wire is dispensed while laying flat.

CADDY MAC 4

Part# 11904

- Easy loading of wire spools
- Patented spindle locking system ... no loose clips
- Convenient storage
- Loops contain up to 5 spindles
- Solid frame construction
- Large 10" wheels
- Dual wire guides

Capacity	Weight	Width	Additional Features
6-500' spools - 8" diameter	67 lbs	27 in	A large capacity cart, dispenses wire while laying flat.
6-2,500' spools - 16" diameter	30.5 kg	69 cm	



CABLE TRUCK & CABLE CADDY

- Constructed of rugged 1" steel tubing.
- Both are 43" tall with 7" rubber wheels.
- Both can accommodate spools up to 16" wide on solid steel 1/2" axles.
- Cable Caddy features 6 axle positions for unlimited versatility.
- Cable Truck has 4 axle positions and a solid steel plate for transporting material.



Cable Truck - Part# CT1100
Cable Caddy - Part# CC1200

CABLE DOLLY

CABLE DOLLY

Features 8-12" wide spindles to accommodate a wide assortment of reel sizes.

Durable locking casters are rated up to 1200 lbs

Made to order

CABLE DOLLY JR.

Features 4-12" wide spindles. Extensions also available.

8 PIECE SPINDLE EXTENSION SET

With tube connectors. (17" extensions)



Cable Dolly - Part# CD3000
Cable Dolly Jr. - Part# CD3100
Ext. Set - Part# CD3000-EXT



CABLE CARTS

- Comes with interchangeable 1" and 3/4" axles.
- Holds up to 30 spools of THHN.

- Vertical racks swing forward for easy loading
- Space for plywood work table on top

Dimensions: 43" H x 41 1/2" L x 28" W / Shipping weight: 150 lbs

Cable Cart - Part# CC2000
Cable Cart (Data)- Part# CC2000D



COPPER WIRE STRIPPERS

COPPER WIRE STRIPPER 1

The CWS-1 is the largest wire stripper available from Rack-A-Tiers. Powered by a 1 HP motor and with the ability to strip up to 3" in diameter, there isn't much this wire stripper can't handle.

FEATURES:

- Strips 14 AWG to up to 3" in diameter
- 1 HP motor
- All aluminum frame
- Hardened one piece blade
- Strips solid core or braided wire
- Blade made from tool steel
- Blade easily re-sharpened
- Fully adjustable wire guide
- Bench model - anti-slip base
- Made in Canada

Part# 47100

COPPER WIRE STRIPPER 2

The top selling CWS-2 model weighs in at only 45lbs. This wire stripper is compact enough to easily move around, but still has the ability to strip a wide range of wire.

FEATURES:

- Strips from 14 AWG to 500MCM
- 1/2 HP Motor
- All aluminum frame
- Hardened one piece blade
- Strips solid core or braided wire
- Blade made from tool steel
- Blade easily re-sharpened
- Fully adjustable wire guide
- Bench model - anti-slip base
- Made in Canada

Part# 47200

COPPER WIRE STRIPPER JR.

A low cost alternative to the CWS-2, the Copper Wire Stripper Jr. is the money making tool that you need in your warehouse. Driven by a standard power drill, you'll get more than double the money from your scrap wire. It's that simple!

FEATURES:

- Wire Range: 14 AWG - 4/0
- Strips NMSC 14 AWG - 10 AWG
- All aluminum frame
- Hardened one piece blade
- Strips solid core or braided wire
- Blade made from tool steel
- Blade easily re-sharpened
- Fully adjustable wire guide
- Made in Canada

Part# 47030

EASY STRIPPER

Strip the cover off your scrap wire in minutes with the Easy Stripper! Increase your earnings on every single job you complete. Remove the cover in minutes with the Easy Stripper.

FEATURES:

- Less than 10% of the price of a standard motorized wire stripper
- Powered by any normal power drill
- Way easier and faster than using your knife!
- Environmentally friendly - no burning required (For Light Use Only)

Part# 47020

REPLACEMENT PARTS

CWS-1

Replacement Blade - Part# 47100B
Red Feed Guide - Part# 47100G
Replacement Pulling Wheels - Part# 47100W

CWS JR.

Replacement Blade - Part# 47030B
Red Feed Guide - Part# 47030G
Replacement Pulling Wheels - Part# 47030W

CWS-2

Replacement Blade - Part# 47200B
Red Feed Guide - Part# 47200G
Replacement Pulling Wheels - Part# 47200W

EASY STRIPPER

Replacement Blade 1st Edition - Part# 47020B
Replacement Blade 2nd Edition - Part# 47020B2



Bend-All

SAVE YOUR KNUCKLES BY USING OUR BEND-ALL CABLE BENDER! MADE WITH MACHINED AIRCRAFT ALUMINUM, THIS CABLE BENDER IS EXTREMELY STRONG AND DURABLE. IT CONNECTS TO YOUR STANDARD 1/2" RATCHET, MAKING CABLE BENDING A BREEZE FOR YOU.



BENDS UP TO 500 MCM!

Part# 77455

The Bulldog Bender is designed and manufactured by an electrician for electricians. Used for bending wire in panels, disconnects, LBs & wire-ways. The Bulldog Bender will prove to be a valuable tool to add to your arsenal. As with any specialty tool, with practice you will learn how to use the Bender to its full bending potential.

See It In Action!

PART #	DESCRIPTION	SIZE
78500	BULLDOG ORIGINAL	UP TO 500 MCM
78501	BULLDOG PRO WITH ADAPTOR	UP TO 500 MCM
78502	BULLDOG 3-PIECE SET (ORIGINAL + PRO)	UP TO 500 MCM
78600	BULLDOG BIG DADDY 3-PIECE SET	UP TO 750 MCM

ALL BULLDOGS SHIPPED WITH KNURLED DOWELS - SMOOTH DOWELS AVAILABLE



HOPPY BENDER

EASY AS 1,2,3!

THE HOPPY BENDER IS HANDS DOWN THE MOST INNOVATIVE AND SMARTEST BENDER ON THE MARKET. WE HAVE REVOLUTIONIZED THE WAY ELECTRICIANS BEND PIPE -- IT HAS NEVER BEEN EASIER OR FASTER THAN IT IS NOW WITH THE HOPPY BENDER.

STEP ONE

READ TABLE AND MARK PIPE

Desired offset	Mark conduit	Set stop on
3/8	3/4	18
1/2	1	8
3/4	1 1/4	8
1	1 1/2	8
1 1/8	1 3/4	6
1 1/4	2	6
1 1/2	2 1/4	6
1 3/4	2 1/2	4
2	2 3/4	4
2 1/4	3	4
2 1/2	3 1/4	4
2 3/4	3 1/2	2
3	3 3/4	2
3 1/4	4	2
3 1/2	4 1/4	2
3 3/4	4 1/2	2
4	4 3/4	2
4 1/4	5	2
4 1/2	5 1/4	2
4 3/4	5 1/2	2
5	5 3/4	2
5 1/4	6	2
5 1/2	6 1/4	2

STEP TWO

SET STOP



STEP THREE

Get Bent

FEATURES

- A "Stop" attached to the Bender head used to create exact & repeatable bends every time.
- Simplified "Multipliers" engraved into the bender for placing the "Stop" prior to making offsets & four-point saddles.
- Special 22.5 and 45 degree marks engraved into the bender for placement of conduit bend marks as well as standard degree marks for stop placement. Used together for bending three-point saddles without reversing the conduit in the shoe.
- Handy reference charts attached to the handle for locating bend marks.

- Part#
- 57050 - 1/2" Hoppy Bender
 - 57075 - 3/4" Hoppy Bender
 - 57002 - Replacement Handle
 - 57005 - Replacement Thumb Screw
 - 57005 - 1/2" Replacement Label
 - 57057 - 1/2" Replacement Swing-Stop
 - 57075lab - 3/4" Replacement Label
 - 57077 - 3/4" Replacement Swing-Stop

See it in action!



GOLD BEND RIGID PVC PIPE WITHOUT PIPE COLLAPSE OR FRACTURE!

PIPE VIPER



HOW?

Simply insert the spring into the pipe & bend across your knee!

- NO HEAT GUNS
- NO HEAT BLANKETS
- FEWER PVC FITTINGS

MFG NOTE:

Needs to be at least 50 degrees Fahrenheit to work effectively



- 58050 - 1/2" PVC Spring Bender
- 58075 - 3/4" PVC Spring Bender
- 58100 - 1" PVC Spring Bender
- 58125 - 1 1/4" PVC Spring Bender
- 58150 - 1 1/2" PVC Spring Bender
- 58200 - 2" PVC Spring Bender
- 58250 - 2 1/2" PVC Spring Bender
- 58300 - 3" PVC Spring Bender
- 58350 - 3 1/2" PVC Spring Bender
- 58400 - 4" PVC Spring Bender

PIPER

Conduit Tracking System


TRACK CONDUIT WITH EASE.

THE PIPER EMITS A LOUD NOISE THROUGH THE PIPE ALLOWING FOR QUICK LOCATING OF THE OTHER END.

FEATURES

- TRACKS CONDUITS IN MINUTES
- WORKS IN UNOBSTRUCTED 1/2" TO 6" EMT, RIGID, OR PLASTIC PIPES TO WELL OVER 300 FEET
- FIND PIPE ENDS THAT WOULD BE IMPOSSIBLE TO LOCATE BY THE OLD "STUFF THE FISH DOWN THE PIPE" METHOD

- Part#
- 99005 - Piper - Conduit Tracking System (1/2" - 1")
 - 99009 - Piper Adaptor 1 1/4"
 - 99010 - Piper Adaptor 1 1/2"
 - 99011 - Piper Adaptor 2"



"FOUND IT!"



MAGNEPULL

EXTREMELY POWERFUL, YET DELICATE, MAGNETIC WIRE SNAKE FOR FISHING WIRE THROUGH WALLS. IT EVEN WORKS THROUGH INSULATION! THIS NEW VERSION HAS A MUCH STRONGER MAGNET AND A SMOOTHER ROLLING SURFACE.

FEATURES:

- Hand roller with powerful magnet & smooth finish to avoid damaging walls
- 6' ball chain included
- Flexible leader with magnet head
- Also makes a great stud finder

MFG NOTE

Any fiberfish can easily be threaded onto the magnet head. This will help push through dense insulation and guide through fire-block drill holes.



See it in action!

Part# 42800

MAGNESPOT

THE MAGNESPOT IS A REFERENCE POINT LOCATOR THAT GIVES USERS COMPLETE SELF-ASSURANCE BEFORE DRILLING, CUTTING, OR ANY OTHER TASK YOU MAY PREVIOUSLY HAD TO DO BLINDLY.

Place the Magnespot Transmitter on the wall, ceiling, or floor that you need to drill. On the other side hold the Receiver in the general direction of the transmitter, the red LED arrows on the Receiver will indicate to you which direction to move. When all 4 Arrows illuminate, the Transmitter and Receiver are lined up within a 1/2 inch.

Senses up to 18" through concrete

Part# 42900

See it in action!




ALIGNMENT TOOL

BEFORE

AFTER




UTILIZING RARE EARTH MAGNETS, THE ALIGNMENT TOOL EASILY SNAPS INTO PLACE AND ALLOWS YOU TO ALIGN ALL YOUR 3/4" CONDUIT WITHOUT THE NEED FOR A LEVEL OR MEASURING TAPE.




Part# 68075

GD CENTER FINDER



The GD Center Finder is a new product that revolutionizes the installation of electrical panels & junction boxes. No need to learn a new installation process. Pull your layout just as you always have, but this time aided with the GD Center Finder. Your center point will always be level and clearly identified. The days of "close enough" are over. Finally a center tool that works!



Part# 67500

FLEX PULLER



The Flex Puller easily screws onto the exterior of MC cable and provides a hook to pull cable. No more getting caught up in insulation or other obstacles!

MFG NOTE
Can be used on #14, #12, & #10 MC Cable!



Part# 42620

ConeHeads



Easy way to pull flexible conduit. Simply thread into the interior of flexible conduit, hook onto your string or fish tape & pull!

Part# 42600
Kit includes 1 each for 1/2" & 3/4" Flex

IT'S SIMPLE... FOAM LINE CARRIERS ARE EXPENSIVE

BAG PIPERS

ARE CHEAPER AND WORK MUCH BETTER

3 sizes available to fit conduit 1/2" up to 6"


Part#
BP05-125 (sm) 1/2" x 1 1/4"
BP150-40 (med) 1 1/2" x 4"
BP20-60 (lg) 2" x 6"
BP05-600 (multi-pack) 1/2" - 6"



THE ALL AMERICAN PULL BUDDY SHOEHORNS FOR YOUR WIRE



FEATURES:
Reduces Time and Labor
Reduces the chance of damaging wires
Turns wire pulling into a one person job



Part#
42000 - Multi-Pack
42050 - 1/2" Blue
42075 - 3/4" Red
42100 - 1" White

THE PENGUIN PULLER

The Penguin Puller Sr. and Penguin Puller Jr. are revolutionary new tools designed to aid in easily pulling in large cables. The sleek, bullet shape allows for seamless pulling, no tape or crimps required. Utilizing three slots and allen-key set screws, the Penguin Puller Sr. and Penguin Puller Jr. are rated for 5000 lbs. of pull strength. These tools are the cool new kids on the block and here to stay when it comes to pulling wire!



Part#
69700 - Penguin Puller Sr. For Pipe 2 1/2" and Larger
69705 - Penguin Puller Jr. For Pipe 2" and Larger

FEATURES:
5000 LBS. MAX PULL STRENGTH
Penguin Puller Sr. - 3/0 to 350 MCM Copper or Aluminum
Penguin Puller Jr. - 2/0 to 4/0 Copper or Aluminum
No tape, no crimps, no mess
Reusable

LB Wire Guide

THE LB WIRE GUIDE IS A "SHOE HORN" FOR 2" LB'S.



See It In Action!



FEATURES

- ASSISTS WHILE WORKING ON YOUR OWN
- FOR PVC LB FITTINGS AND IS ADAPTABLE TO MOST METAL LB'S
- FAST FOR ONE PERSON CONDUCTOR INSTALLATIONS
- INSTALLS IN TWO POSITIONS TO FIT BOTH "ENDS" OF THE LB

MFG NOTE

TWO HUNDRED AMP SERVICES (3/0 WIRE) CAN BE HARD ON YOUR KNUCKLES. THE LB WIRE GUIDE PUTS THE WIRE IN THE PIPE AND LEAVES THE SKIN ON YOUR FINGERS.

Part# 42200



ROPEMATIC PRO
THE SMART WAY TO PULL



**STOP HURTING YOUR HANDS AND WRISTS.
STOP BREAKING EXPENSIVE FISH TAPE.
PULL ROPE AND FISH TAPE THE SMART WAY WITH THE ROPEMATIC.**

The Ropematic has a durable latch that grabs rope or fish tape when you are pulling down. As you pull back up, the latch loosens and easily slides up the rope or fish tape. You can then pull down again and the Ropematic will grab the rope or fish tape, pulling it down.

PART# 42400



EASILY FIX AND IMPROVE BROKEN FISH TAPE ENDS

The Flex Flyer features a quick change swivel head that installs on the end of a fish tape in 20 seconds by twisting the fish tape with two pairs of pliers. The loop technology allows the leader to move smoothly through all types of conduit as well as flex. The standard 1/4" - 28 threads allow for other types of leaders to be attached to the quick change head.

Part#
69050 - 1/2" Flex flyer
69075 - 3/4" Flex flyer



WIRE PULLING & FISHING

FISH HEADS

Tired of your fish tape getting snagged or breaking? Try 'FishHeads' an economical fish tape improvement.

FEATURES

- Tested for 500+ pounds
- Complete spherical head reduces the chance of it getting stuck
- Installs in seconds

Part# 69010

SNATCH STRAP

Use the Snatch strap for fast attachment on conduit pulls. No stripping or taping required!


FEATURES

- Pull more conductors with less effort
- Can be chained together
- Colour coded for easy circuit and phase identification

Part# 69455



SNATCHSTRAP



StingRay

SNAP IN PLACE AND PULL YOUR WIRE



- PROTECTS EXPENSIVE AND FRAGILE CABLES
- PROTECTS CEILING FROM TWISTING AND MARRING
- PREVENTS CABLES FROM TANGLING WITH THE CEILING, SAVING TIME AND LABOR
- SMOOTH INTERIOR CREATES AN ALMOST FRICTIONLESS CHASE
- SIDE SLIT ALLOWS FOR EASY CABLE REMOVAL AT ANY TIME
- EASY TO INSTALL AND REMOVE

Part# 40400

WIRE VORTEX



If you need an extra pair of hands on the job, try the Wire Vortex. This wire pulling guide fits on 4" square boxes and saves you tons of time when pulling wire.

Features

- Protects wire from damage when pulling
- Can pull wire in all 4 directions
- Use for standard (shallow) or deep boxes
- Built with durable, impact-resistant plastic
- Easy to slip on and off




Part# 40001

Learn More Here!



SUPER ROD

TIRED OF YOUR FISH RODS FLAKING AND GIVING YOU SPLINTERS? SUPER-ROD HAS GOT YOU COVERED. MADE WITH SPECIALLY FORMULATED RESIN THAT COATS THE CORE FIBREGLASS - GREATLY REDUCING THE CHANCE OF SPLINTERS AND RODS BREAKING.



Part #	Description
2S516	Standard 5 Rod Set: 16 FT of rods, 2 attachments
2S619	Super Six Rod Set: 19 FT of rods, 6 attachments
2GSKIT	Goose-Neck Kit: 3 sizes of flexible attachments
2GLIDE	Glider: Whisk easy glide attachment
2GRIP	Triple Pack Super Grip: 3 pack grip attachments
2LIGHT	Cable Rod Beam: Light up rod end attachment

PLASTIC COATED FIBERFISH AND GLOWFISH

Our Fiberfish and Glowfish rods with a durable plastic coating offer the same great performance with no risk of splintering or slivering of the fiberglass.

PLASTIC COATED FIBERFISH II

3/16" DIAMETER ORANGE RODS

The most versatile of the Fiberfish with our new plastic coating process. Perfect for a wide range of installation situations and challenges.

KITS

- PCF207 Fiberfish Kit contains: 1 - 6' B/F, 4 - 6' M/F w/ tips
- PCF208 3' Fiberfish Kit contains: 1 - 3' B/F, 7 - 3' M/F rods w/ tips
- PCF230 "FourPack" contains: 1 - 3' B/F, 3 - 3' M/F, tip, and FishHook in vinyl pouch

REPLACEMENT RODS

- PCF206 6' Bullnose/Female (B/F) rod
- PCF210 6' Male/Female (M/F) rod
- PCF214 3' Bullnose/Female (B/F) rod
- PCF215 3' Male/Female (M/F) rod



PLASTIC COATED GLOWFISH II

5/32" DIAMETER LUMINOUS RODS

Super flexible glow-in-the-dark rods with our new plastic coating process. Great for tight jobs. The handy clear carry case keeps them constantly "charged" and ready.

KITS

- GLF407 Glowfish Kit contains: 1 - 6' B/F, 4 - 6' M/F w/ tips
- GLF408 3' Glowfish Kit contains: 1 - 3' B/F, 7 - 3' M/F rods w/ tips

REPLACEMENT RODS

- GLF403 6' Bullnose/Bullnose (B/B) rod
- GLF406 6' Bullnose/Female (B/F) rod
- GLF410 6' Male/Female (M/F) rod
- GLF414 3' Bullnose/Female (B/F) rod
- GLF415 3' Male/Female (M/F) rod



DELUXE SET 15

Part# SS15

INCLUDES:

- 4 x 3/16" Orange fiberfish Rods
- 1 x 5/32" Glow In The Dark Fiberfish Rod
- 1 Flexfish Leader
- 1 Fish Hook
- 1 Pull Ring
- 1 Bull Nose Tip
- 1 Carrying Case



DELUXE SET 18

Part# SS18

INCLUDES:

- 1 x 1/4" x 36" Yellow fiberfish Rod
- 3 x 3/16" Orange Fiberfish Rod
- 2 x 5/32" Glow In The Dark Fiberfish Rod
- 1 Flexfish Leader
- 1 Fish Hook
- 1 Pull Ring
- 1 Bull Nose Tip
- 1 Carrying Case



ATTACHMENTS & ACCESSORIES

We've re-engineered the attachments to fit both the 3/16" rods and the 5/32" rods. They will still be compatible with all existing parts in the field, and the cost remains the same.

UNIVERSAL ATTACHMENTS

for ALL (3/16" rods) AND (5/32" rods)

- FIB505 - Fish Hook
- FIB511 - Directional Tool
- FIB512 - Magnet Head
- FIB518 - Pull Ring
- FIB519 - Ball Chain
- FIB522 - Wisp Head
- FIB525 - Screw Tip



FishHook - Use to retrieve or snag wire & cable.

Directional Tool - Offset bend helps guide the Fiberfish around obstructions in walls.

Magnet Head - Used with Fish Finder or to catch the ball chain inside wall cavities.

Pull Ring - Used to attach multiple wires for larger pulls.

Ball Chain - Attach to Fiberfish for interior wall pulls — can be retrieved through small access hole in wall with magnet or Flex-Fish.

Wisp Head - Use over suspended ceilings — won't catch on T-bars.

Screw Tip - Screws into the end of small communication wires for faster and easier pulls.

ATTACHMENT KIT

Contains:

- FishHook
- Directional Tool
- Magnet Head
- Pull Ring
- Ball Chain
- 2 replacement tips
- Stored in convenient vinyl pouch



FIB520 Universal Attachment Kit for ALL (3/16" rods) & (5/32" rods)

FIBERSNAKES

Fibersnake, Fishtapes and Rodders are designed for use in conduit. The reinforced fiberglass core is jacketed with a plastic coating for superior flexibility and durability. Non-conductive, so it's great for conduit with existing wiring. Rust-proof brass tips and fittings.

3/16" FIBERSNAKE

- | | |
|-------------------------|------------------------------------|
| FIBT50 50' Fibersnake | RT50 50' Replacement Rodder only |
| FIBT100 100' Fibersnake | RT100 100' Replacement Rodder only |
| FIBT150 150' Fibersnake | RT150 150' Replacement Rodder only |
| FIBT200 200' Fibersnake | RT200 200' Replacement Rodder only |
| FIBT250 250' Fibersnake | RT250 250' Replacement Rodder only |
| FIBT300 300' Fibersnake | RT300 300' Replacement Rodder only |

1/4" FIBERSNAKE

- | | |
|-------------------------|------------------------------------|
| FIBR200 200' Fibersnake | RR200 200' Replacement Rodder only |
| FIBR250 250' Fibersnake | RR250 250' Replacement Rodder only |
| FIBR300 300' Fibersnake | RR300 300' Replacement Rodder only |
| FIBR350 350' Fibersnake | RR350 350' Replacement Rodder only |
| FIBR400 400' Fibersnake | RR400 400' Replacement Rodder only |
| FIBR450 450' Fibersnake | RR450 450' Replacement Rodder only |
| FIBR500 500' Fibersnake | RR500 500' Replacement Rodder only |
| FIBR550 550' Fibersnake | RR550 550' Replacement Rodder only |
| FIBR600 600' Fibersnake | RR600 600' Replacement Rodder only |

5/16" FIBERSNAKE

Fibersnakes and Replacement Rodders are available in 400'-1000'

Fibersnakes Part # FIBL400-FIBL1000

Replacement Rodder Part # RL400-RL1000



1/2" FIBERSNAKES AVAILABLE

Rodder Diameter	Recommended conduit sizes (in inches)	Maximum Length
(FIBT) 3/16"	1/2, 3/4, 1, 1 1/4	300'
(FIBR) 1/4"	1, 1 1/4, 1 1/2, 2, 2 1/2	600'
(FIBL) 5/16"	1 1/2, 2, 2 1/2, 3, 3 1/2, 4	1000'

Note: We do not replace Fibersnakes broken due to improper use. However, we will send a repair kit at no extra charge.

Our 5/16" Fibersnakes are made to order. Returns due to the wrong size being ordered will **NOT** be accepted. Please order carefully.

Fibersnakes are designed to pull fish line or rope. They are not recommended for pulling wire and cable.

NYLON FISH TAPE

NYLON FISH TAPE Ø4MM WITH M5 THREADED INTERCHANGEABLE TERMINALS
FLEXIBLE STARTING SPINNER WITH EYELET AND EYELET ON THE BACK SIDE OF THE FISH TAPE.

AVAILABLE LENGTHS: 15M (49FT) & 30M (98FT)

Part# EN050.BK

Part# EN098.BK

NYLON FISH TAPE PLUS

NYLON "PLUS" FISH TAPES 4MM, WITH M5 THREADED BRONZE INTERCHANGEABLE TERMINALS
FLEXIBLE METALLIC STARTING SPINNER WITH EYELET AND EYELET ON THE BACK SIDE OF THE FISH TAPE.

- Reinforced eyelet with special formation which facilitates excellent tying of cables.

- Available lengths: 15M (49FT) & 20M (65FT)

Part# EN050.OR

Part# EN065.OR

POLYESTER FISH TAPES

POLYESTER "3 STRAND WIRE" FISH TAPES Ø5MM, WITH FIXED TERMINALS
FLEXIBLE STARTING SPINNER WITH EYELET AND EYELET AT THE BACK SIDE OF THE FISH TAPE.

- Available length 30M (98 FT.)

Part# EP098.YW

THE MOST INNOVATIVE TOOL BELTS ON THE MARKET



COMBO TOOL BELT



Find Out More!

INCLUDES:
Molded support belt, Electrician's tool pouch, Large 9 pocket tool pouch, Hammer holster and tape holder

FEATURES:
- Reinforced with bar-tack stitching & heavy duty metal rivets
- 1250 denier DuraTek fabric with high density nylon webbing around pocket openings.

- Part#
- 43241 - Small Combo
 - 43242 - Medium Combo
 - 43243 - Large Combo
 - 43244 - X-Large Combo
 - 43245 - XX-Large Combo
 - 43246 - XXX-Large Combo
 - 43201 - Electrician's tool pouch
 - 43202 - Lrg Nine Pocket Tool Pouch

MOLDED AIR-CHANNEL SUPPORT BELT



- 43401 - Small Belt
- 43402 - Medium Belt
- 43403 - Large Belt
- 43404 - X-Large Belt
- 43409 - XX-Large Belt
- 43410 - XXX-Large Belt

FEATURES:

- The first ever 'Molded Air-Channel Tool Belt' that offers incredible comfort, support, & ventilation for your back.
- The high density nylon 'Web Core' inside the padded belt provides strength to stitching & stress points.
- Metal rings are stitched to the belt's web core with high-density nylon webbing that provides the strongest way possible to attach suspenders.
- All stress points are reinforced with 'bar-tack' stitching along with heavy duty rivets.
- Double metal buckles that add strength and dependability.
- All of our belts and bags are made from double layered 1250 denier DuraTek fabric.
- Available in sizes from 26" to 54"

MOLDED AIR-CHANNEL SUSPENDERS

Part# 43606



FEATURES:

Our popular padded suspenders easily clip onto the sturdy metal rings that are built into our tool belts. The padded shoulder straps make these the ideal set of suspenders for your tool belt rig.

INCLUDES:

- Adjustable thick molded foam shoulder pads
- 2" wide adjustable nylon straps
- leather crossover divider
- Heavy duty spring hooks that attach to the rings on the molded air-Channel belts

POCKET TOOL HOLDERS

FEATURES:
- Quick to put on & COMFORTABLE!
- Tool pouches fit in your pocket
- Made of ballistic nylon
- Lightweight & durable



MINI
Part# 43015



GRANDE
Part# 43095



PAPA GRANDE
Part# 43100

ELECTRICIAN'S HOLSTER

Part# 43055



- Durable nylon double-pronged belt with rubber carrying handle
- Stands upright or wears as a belt
- 1200 Denier Polyester

LARGE 44 POCKET TRAY TOOL CARRIER

FEATURES:
- 29 exterior pockets
- 1 large clear pocket
- 16 interior compartments and pockets
- 27" x 5 1/2" twelve-compartment plastic trays
- Includes shoulder strap
Part# 43706



SMALL 25 POCKET TRAY TOOL CARRIER

FEATURES:
- Twenty nine exterior pockets
- One large clear pocket
- Sixteen interior compartments and pockets
- Two 7" x 5 1/2" twelve-compartment plastic trays
- Includes shoulder strap
Part# 43707



KNEE PADS



GEL IMPLANTED RACKSY PADS

FEATURES:
- Sturdy
- Comfortable
- Hook & Loop Straps
Part# 66455

BOOTY PACK

Kit includes: 6 pairs of booties, 4 pairs of nitrile gloves, 4 pairs of vinyl gloves, and 3 N95 respirators

- BOOTY PACK - 47099
- BOOTIES ONLY 47099B
- SIX PACK OF BOOTIES - 47099BB



BIGG LUGG 2

The Next generation in tool carriers, it holds tools anywhere on your belt. Nail guns, cordless drills, nail drivers, saws, paint buckets, PDA's, survey equipment, even fishing poles!

Part# 43002



LIFT N LOK

PROFESSIONAL QUALITY ORGANIZATION

This tool box makes life EASY for the electrician. Turn the handle one way, and all the drawers lock in place. The compartments are designed to keep everything inside organized -- nothing will move when it is locked. Then, just simply flip the handle the other way to unlock the drawers and get at your tools.

FEATURES

- No mixing between drawer compartments
- Extremely strong
- Easy to operate
- Made in USA
- Very light-weight!

Part# 66536

LASER PLUMB BOB

LOOKING FOR A BETTER WAY TO LAY OUT COMPLEX CEILING AND HIGH BAYS? THE LASER PLUMB BOB, THE SELF LEVELING VERTICAL LASER FROM RACK-A-TIERS IS THE ANSWER!




FEATURES

- Solid brass construction
- Factory aligned laser module calibrated to precise 0.15 accuracy
- Magnetic damping for quick stabilization
- Self leveling and aligning (vertically)
- Durable plastic carry case
- Battery included

MFG NOTE:

For all commercial, industrial, or residential installations. Great for laying out ceiling lights.



PART#
88455 - LASER PLUMB BOB
REPLACEMENT PART#
88-ARM - LASER PLUMB BOB ARM WITH MAGNET ATTACHED
88-BASE - LASER PLUMB BOB BASE
88-BAT - LASER PLUMB BOB BATTERY CR 123

SHOPPE ROCKET

This tool offers a better, faster, more cost effective solution for tasks commonly performed by electricians, plumbers, pipe fitters, metal fabricators, carpenters, iron workers, general contractors, hobbyist & do-it-yourselfers. Trade professionals will now have a multi-function tool that is designed to perform a number of tasks simultaneously & accurately, while increasing efficiency and reducing material waste.



- Multi-function leveling system provides an easier and faster way to create multiple bends on a single conduit.
- Built with aerospace engineered high impact polymer resin, this durable material will provide years of use for all trade professionals.
- Our protractor can be read from both sides for quick, accurate angle locating.
- Quick reference industrial grade level vials provide at a glance positioning for any assembly or construction task.
- Low light capturing polycarbonate bezels and 360° day-glow pointer allow reading degrees in limited illumination environments.
- Super grip rare earth magnets for hands free use on any magnetic surface.



Part# 45200

TESTERS

PLUG MASTER

The Plug Master combines a full function dual-outlet circuit tester with 220V detection and multiple direction bubble-levels. Eliminate the need for multiple tools to test and straighten any wall outlets.

Features:

- Acts as horizontal and vertical level
- Use for diagnostics
- Perform quick wiring checks
- Panel identifies conditions shown by LED indicators
- Removable side panels cover outlet during insertion




Part# 99102

SENSORS

AC SENSOR & ULTIMATE AC SENSOR

- Non-contact detection of 50-1000 VAC
- Troubleshoot electrical circuits
- A simple way to locate dangerous defective grounds
- Hand held device for determining presence or absence of 50-1000 Volts AC in insulated wires, wall receptacles, fuses, junction boxes and voltage carrying electrical systems
- Outstanding safety instruments that locate defective grounds, energized circuits, induced voltage. Senses voltage without metallic contact
- 2 replaceable "AAA" alkaline batteries included



AC Sensor

50-1000 Volts AC
Bright red glow indicates AC voltage.

Ultimate AC Sensor

50-1000 Volts AC
Bright red glow indicates AC voltage AND audio alert.

NOTE: BEFORE USING THE AC SENSOR OR ULTIMATE AC SENSOR, ALWAYS TEST IT ON A KNOWN LIVE VOLTAGE SOURCE TO ENSURE PROPER OPERATION.

Part#
AC SENSOR - 99000
ULTIMATE AC SENSOR - 99001

EZ GENERATOR SWITCH

Manual generator transfer switch for all standard generators – 15 Amp, 125-Volt

- Most affordable and efficient transfer switch on the market
- Easily transfer power to important loads such as a fridge, and heating system in the event of a power outage
- Connects with standard extension cord
- No backfeeding or touching existing circuit breakers
- Unswitched neutral Unit matches floating neutral generators



Part# 99215

EFERGY ELITE CLASSIC – WIRELESS HOME POWER MONITOR

- No need to install a second meter base to monitor certain circuits
- Includes 2 XL - 200 A sensors
- Portable compact display can be placed anywhere in the home
- View your real time energy consumption (cost, CO2 and kWh)
- View historical daily, weekly or monthly data (cost, CO2 and kWh)
- View daily, weekly or monthly average (cost, CO2 and kWh)
- ETL Listed for USA & Canada



Part# EF003 - Meter
Part# EF012 - 200 AMP
Current sensor for 3 phase

LEVELS

STRAIGHT SHOT

Remember, a good tradesman requires a good level! The Straight Shot is equipped with 3 precision vials (0°, 45°, 90°) and strong magnets that will hold throughout the job.

Features:

- Three rare earth magnets
- Extra large "V" grooved edge remain parallel on surfaces up to 10" diameter
- Laser designed to locate reference points when installing raceways
- Makes a great laser pointer for bossing around apprentices!



Part# 45303

JET LEVEL

This convenient and strong pocket level comes with 4 precision vials of 0, 30, 45, & 90 degrees.

Features:

- CNC milled from 6061 aluminum extra large "VD" groove, straddles up to 10" diameter
- Rare Earth magnets for extra holding
- Water and shock resistant



Part# 45404



STAPLESHARK

PART# 52455

FEATURES:

- Includes a handy staple puller and pry bar for multi-purpose use!
- Ruler for quick on the job measurements.
- Use as a quick carpenter's square.
- Holds staples in tight spots and will open a beer bottle at the end of the day.



STAPLE PULLER!



HOLDS STAPLES!




PRY BAR!



RULER!



BEER OPENER!



THE ROUGH-IN STICK

The Rough-In stick allows you to mark out devices conveniently and efficiently by utilizing specifically designed holes to fit your felt marker. The Rod also features a telescopic pole for those tricky fishes.

FEATURES:

- Easily mark stud walls for device installation
- No need to use your tape measure while laying out devices
- Telescopic pole aids in pulling wire above ceiling grids and areas of limited access
- Retrieve metal tools and objects with the magnet attachment
- Extends up to 20"

Coming Soon



NEEDLE NOSE WIRE STRIPPERS

Sometimes referred to as the best wire strippers on the market, the Croc's Needle Nose Wire Strippers will impress even the toughest critics. These strippers have countless features, each designed to make your job easier and more productive.

FEATURES:

- GLOW IN THE DARK HANDLES
- ERGONOMIC HANDLE DESIGN FOR MAXIMUM COMFORT
- NEEDLE NOSE TIPS
- STRIP FROM 22-10 AWG
- BARREL SLEEVE CRIMPER
- NMSC CUTTER NEAR THE "NOSE" OF THE STRIPPER
- 8-32 AND 6-32 BOLT CUTTERS

PART# 47000



Introducing the Croc's Jr., A compact and light-weight version of the original. This model serves as an affordable predecessor to the original without skimping on its numerous applications.

FEATURES:

- GLOW IN THE DARK HANDLES
- ERGONOMIC HANDLE DESIGN FOR MAXIMUM COMFORT
- COMPACT DESIGN
- STRIP FROM 22-8 AWG
- 8-32 AND 6-32 BOLT CUTTERS

PART# 47002



V-CUTTER

ELECTRICIAN'S ADD-ON CABLE STRIPPER

STRIPS CABLE IN OR OUT OF ELECTRICAL BOXES WITH EASY TO PUSH ACTION

One of the smartest inventions to come to market this decade is the V-Cutter. This simple little blade attaches to most wire strippers and allows you to strip cable with a single swipe.

FEATURES:

- A NEW WAY TO STRIP NMSC CABLE
- EASILY ATTACHES TO MOST WIRE STRIPPERS
- STRIPS CABLE IN OR OUT OF ELECTRICAL BOXES WITH ACTION
- VIRTUALLY ELIMINATES NICKING OR CUTTING THE WIRE INSULATOR

Part# 47010

EXTENDO NUT DRIVER

The Extendo Nut Driver kit is designed to adapt a standard 1/2" conduit into an extension nut driver for threaded rod. Utilizing the concept of a hollow shank nut driver, the Extendo Nut Driver gives you the flexibility to cut the conduit any length you need to drive the nut up the full length of threaded rod. With this tool on hand, you no longer need to buy multiple size hollow shank nut drivers! Save yourself time and money with this complete extension nut driver kit.

FEATURES:

- Kit includes: 7/16", 9/16" sockets, and 1/4" adaptor
- No need to buy multiple hollow shank nut drivers
- Drill attachment designed for 3/8" chuck, will fit quick change drills
- Made from hardened steel
- Adaptable to any length nut driver needed
- Extends up to 10'



DRILL ARBOR

EMT

NUT DRIVER

THREADED ROD

Part# NT1050

LADDER MATE

MULTI-USE LADDER ORGANIZER

TOOL HOLDER & PAINT TRAY WITH ADJUSTABLE DIVIDERS



LADDER MATE

The Ladder-Mate saves you time and energy by storing your tools and material while working from a ladder. This multi-use product featuring adjustable dividers is great for any tradesman.

EASY TO ATTACH

Adapter clips included
Works with most fiberglass, aluminum and wooden step ladders

Part# 65300

SHINMATE LADDER GUARD

The Shinmate provides SUPERIOR COMFORT & BETTER BALANCE. Designed by a tradesman for tradesmen, electricians, painters, carpenters & window washers, or anyone who works on ladders for hours on end will benefit from the ShinMate.

Step Ladder ShinMate - Part# 65100
Ext. Ladder ShinMate - Part# 65200



FLASHLIGHTS

THE STICK BUG

The Pocket Light just got brighter, stronger and better. Some call it supercharged! With the new technology of COB LED technology, it has 150/160 lumens - 2 times the amount of the original pocket light. With the durable and strong pocket clip and improved magnetic base, you'll never be left out in the dark again.

FEATURES

- COB LED
- 160 Lumens
- Operates on (3) AAA batteries
- Up to 7 hours run time
- Water resistant button

160 lumens - Part# 53600
Stick Bug Jr - 60 lumens - Part# 53500

FIREFLY

The Fire Fly is a compact aluminum flashlight that features 3 light outputs with and has an output of 120 lumens.

FEATURES

- 120 lumen output
- Light Modes: High output, low output, flash
- Mechanical zoom function

Part# 53400

THE OWL EYE

The Owl Eye is a multifunction flashlight with the ability to dim and strobe.

Takes 3X AAA Batteries (not included)

FEATURES

- Waterproof
- Dust-proof

Part# 53300

THE GOPHER II

LED Rechargeable Flashlight

- One high powered LED bulb outputs 35 lumens of light
- Weather-resistant compact body design
- Anodized aluminum sturdy construction
- Built-in rechargeable batteries
- Charges directly from cigarette lighter socket.
- 120 minutes usage, full recharge in 6-8 hours.

Part# 53020

BULB CADDY

SAVE TIME, EFFORT, AS WELL AS YOUR FLUORESCENT & LED TUBE LIGHTS WITH THE BRAND NEW BULB CADDY - THE CONVENIENT LADDER ATTACHMENT THAT HOLDS A VARIETY OF SIZES TO HELP YOU GET THE JOB DONE NEATLY, QUICKLY AND INEXPENSIVELY.

Part# 65000



NUT BLASTER

NUTBLASTER

Universal Wire Connector

- Fast, easy Installation
- Prevents sore fingers and cramping hands
- Fits all brands; yellow, tan, red, grey & blue

Part#

XL - 72101
XXL - 72102



BREAKER LOK

Secure any circuit breaker in the ON Position with ease!

- Universal lock fits most breakers & standard toggle switches.
- Set screw and rigid leg prevents lock from slipping off breaker.
- Reusable & corrosion resistant.

Part# 75000



QWIK-LOK

The Qwik-Lok guarantees that extension cords and tools are LOCKED together. It is the toughest, strongest, most reliable 120V - 15A connector on the market.

- The locking end that eliminates tied, frayed, burned out or ruined cords and connectors
- Works with common two or three pronged plugs
- Eliminates need for "twist-lock" devices
- Delivers consistent, reliable power at all times for demanding industries & trades

Part# 97008



PENCIL

Show up your buddies on the job site with your Rack-A-Tiers branded carpenter's pencil. They do the job and look great.

Part# 52466



PANEL BUDDY KNOCKOUT KIT

Tired of trying to remove knockouts? Let the Panel Buddy take care of them for you. This simple but genius tool removes knockouts in half the time, with half the effort.

- Kit removes knockouts on electrical, security, alarm, and datacom panels
- Works with lipped and non-lipped panels

Part# 7WBK100



QUICK DRAW FELT PEN

Complete your tool kit with a black felt marker from Rack-A-Tiers. These things come in handy and ours won't run dry on you.

Part# 52486



QWIK-LOK



TIRED OF TRYING TO REMOVE KNOCKOUTS?

PANEL BUDDY

Knockout System



• KIT REMOVES KNOCKOUTS ON ELECTRICAL, SECURITY, ALARM & DATACOM PANELS
• WORKS WITH LIPPED AND UNLIPPED PANELS



LASERLINE

REDUCE EFFORT IMPROVE PRODUCTION CUT LABOR EXPENSES



Tired of wiggling through a crawl space or popping out a bunch of ceiling tiles just to drag your wire to the other end? Fire the Laserline, attach your wire, then walk around and pull it across while standing. It's that easy!

The CO2 powered gun shoots a foam dart with a line attached to it up to 200ft. Stop climbing your ladder and moving it every ten feet to pull your wire across a t-bar ceiling. Pull your wire the entire distance in one shot with the Laserline!

FEATURES

- Accurately install a pull line up to 200ft
- Cuts labor costs and improves production
- Ability to span over heavy and hard to move objects found in many commercial structures
- Replacement line and darts available

MFG NOTE

- The Laserline Kit includes 1 gun, 2 spools of line (1200 ft each),
- 2 darts and 2 CO2 cartridges.

PART

- 83000 - LASERLINE KIT
- 83001 - REPLACEMENT LINE 2-1200FT
- 83003 - DART 3 PACK

PLATE WISE

- 1" Pipe & Conduit
- 1 1/4" - 1 1/2" Pipe & Conduit
- 2"x2", 2"x4", 2"x6" Lumber
- 3"- 4" Pipe Conduit
- 4"x4" Lumber & 4" Angle Iron & Tubing
- 1"x2" Lumber & 7/8" Unistrut
- 2" - 2 1/2" Pipe & Conduit & 2" angle Iron & Tubing
- 1/2" - 3/4" Pipe & Conduit

I SURE COULD HAVE USED THAT LAST WEEK

Part#13355



STUD BALL

MAGNETIC STUD FINDER

The Stud Ball is a protected magnetic stud finder that will outperform and other types of magnetic stud finder on the market. Unlike other steel stud finders, the Stud Ball can detect metal through 1/2" or 5/8" drywall or other thicker building materials. Will also work through ceramic tiling and up to 3/4" plywood paneling.

- Rare Earth magnets with 27 lbs of pull.
- Detects metal through 1/2" or 5/8" drywall, ceramic tile & 3/4" plywood.
- Detects screws or nails in wood frame walls.



Part# 52300

SLUGGOOX™

THE SLUGGO-OX IS THE ULTIMATE GROUND ROD DRIVING TOOL.

Just one piece and incredibly strong. It delivers the kind of power and strength you need to easily install ground rods, rebar, & other metal objects.

- Incredibly strong: made of 3" hot-rolled, heat-treated, hardened steel
- 3 1/2" bore to accept 3/4" and 5/8" ground rods
- 80% more striking surface
- One piece, light-weight (7 lbs)
- Yellow zinc chromate surface to deter rust



"I THINK IT'S TIME WE GOT A SLUGGO-OX!"

Part# 67119

WE'VE GOT THE HOLE THING COVERED!

BRICK, FIBERGLASS, PLYWOOD, PLASTIC, ROOFING, TILE, MDF FIBRE CEMENT BOARD, LAMINATES, OSB, CONCRETE BLOCK, ALUMINUM, STEEL, STAINLESS STEEL, HARDIE BOARD, STUCCO, SHEETROCK, HARD WOODS, SOFT WOODS, FLAGSTONE, SLATE, NONFERROUS METALS, SHEET METAL & MORE...

MEGA TCT HOLE SAWS

Hole Saws for cutting wood, laminates, plaster, OSB, MDF, fiberglass, chipboard, sheetrock, perforated brick, roofing tile, stucco, and more.

Features:

- Carbide tipped
- Works with all standard hole saw arbors
- Arbors bits are also available
- Works as a nail cutter

Mfg Note

Aggressive cutting action with TCT teeth & deep side gullets for fast plug removal.

Available sizes 1" - 4 1/8"
Please visit website for Part#'s

THE GID-O

The Gid-O allows you to enlarge holes utilizing a pilot bit the same size as the existing hole. Utilizing a pilot bit that matches up to the existing hole, the hole cutter will stay centred while drilling the new, larger hole.

Features:

- Fits most standard carbide hole cutters
- Kit includes 1/2", 3/4", 1", and 1-1/4" pilot bits
- Made from carbon steel



Coming Soon

- Part #
- 94200 - Gid-O Hole Cutter Guide Kit (Includes 1/2", 3/4", 1", and 1-1/4")
 - 94050 - Gid-O Hole Cutter Guide 1/2"
 - 94075 - Gid-O Hole Cutter Guide 3/4"
 - 94100 - Gid-O Hole Cutter Guide 1"
 - 94125 - Gid-O Hole Cutter Guide 1-1/4"

HIGH PERFORMANCE CARBIDE TIPPED STEEL CUTTERS

Features

- Ejector spring
- Tapered center drill

Available in sizes 5/8" - 2 1/2"
Please visit website for Part#s



MULTI BIT (STEP DRILLS)

Hardened stepped bits for clean cuts in sheet metal, electrical boxes, arborite, etc. Handy for creating knockouts.


- Part# MLT1 - Size: 1/8" - 1/2" 13 Step
- Part# MLT3 - Size: 1/4" - 3/4" 9 Step
- Part# MLT4 - Size: 3/16" - 7/8" 12 Step
- Part# MLT5 - Size: 7/16" - 1 1/8" 12 Step
- Part# MLT7 - Size: 1/4" - 1 1/2" 11 Step



HEAVY DUTY TCT MASONRY HOLE SAWS

- Cuts through heavy duty brick and cinderblock
- All hole cutters have a 2-3/8" cutting depth
- Engineered for fast cutting through stucco or FRP / fiberglass as well as metal lath and plywood
- Perfect for use with 18 volt hand drills to cut holes up to 4-1/4" diameter

Available in sizes 1 1/4" - 4 1/4"
Please visit website for Part#s



JAVELIN

ALL IN ONE DRILLING EXTENSION



The Javelin is a product that is changing the way we drill holes. Never get caught in a drilling extension jam again! This all-in-one extension drill can reach up to 10 feet. It comes with a fully adjustable hole cutter and auger bit extension kit. Just cut a 3/8" - 16 threaded rod to any length you need.

FEATURES:

- Holds drivers bits
- Holds nut drivers
- Holds drill bits
- Reaches up to 10 feet long

KIT INCLUDES:

- The hole saw arbor and pilot bit
- The 1/4" hex arbor
- The connector
- 3/8-16 x 1 1/4" threaded rod
- 3/8-16 x 6" threaded rod
- 3/8-16 jam nuts (4)
- Allen wrench
- Tube

Part# 95000



REVBIT

SAFER FASTER BETTER

The RevBit takes a common item, the pilot bit, and perfects it. By being reverse threaded the RevBit eliminates any bending, breaking and mess caused by hole saw teeth catching once your pilot bit goes through the material.

FEATURES:

- Reverse threaded pilot bit for a soft landing once the pilot bit breaches the work surface
- 4" in length
- Works with any standard hole saw
- Will not tear sheet-rock, or finished wall surface
- Preserves the hole saw teeth, for the entire life of the tool
- Made in the USA

Specs.

- Left hand / reverse twist pilot bit
- 1/4" (6.35mm)
- 135 deg. Split point
- Made from high speed steel

Part# 91700



SWITCH BITS

INTERCHANGEABLE FLEX BITS

Rack-A-Tiers is proud to announce the Switch Bit line, our newest line of flexible installer bits. Quickly and easily customize your own set with these flexible bits featuring interchangeable heads and different shank lengths to fit any job.

ETS31621	SINGLE SHANK	3/16"	21"
ETS31633	SINGLE SHANK	3/16"	33"
ETS31654	SINGLE SHANK	3/16"	51"
ETS31669	SINGLE SHANK	3/16"	69"
ETS1421	SINGLE SHANK	1/4"	21"
ETS1433	SINGLE SHANK	1/4"	33"
ETS1454	SINGLE SHANK	1/4"	51"
ETB38316	INTERCHANGEABLE HEAD	3/8"	
ETB916316	INTERCHANGEABLE HEAD	9/16"	
ETB3414	INTERCHANGEABLE HEAD	3/4"	

ETC38S316	SWITCHBIT COMBO HEAD (3/8") & SHANK (3/16" x 33")
ETC916S316	SWITCHBIT COMBO HEAD (9/16") & SHANK (3/16" x 33")
ETC34S14	SWITCHBIT COMBO HEAD (3/4") & SHANK (1/4" x 33")

PIRANHABITS

Piranhabits have 3/16" flexible shafts so they can bend while rotating. This allows drilling inside wall cavities, through box cut-outs or through other small openings.

QUATTRO FLEX AUGER BITS

Fast and aggressive self feed auger bits, welded to a flexible shaft. Cuts clean holes. Crossbored at both ends for easy wire pulling. Use for wood only.

Part# QTT3824	3/8"x24"	Part# QTT1224	1/2"x24"	Part# QTT91624	9/16"x24"	Part# QTT3424	3/4"x24"
Part# QTT3836	3/8"x36"	Part# QTT1236	1/2"x36"	Part# QTT91636	9/16"x36"	Part# QTT3436	3/4"x36"
Part# QTT3848	3/8"x48"	Part# QTT1248	1/2"x48"	Part# QTT91648	9/16"x48"	Part# QTT3448	3/4"x48"
Part# QTT3854	3/8"x54"	Part# QTT1254	1/2"x54"	Part# QTT91654	9/16"x54"	Part# QTT3454	3/4"x54"
Part# QTT3872	3/8"x72"	Part# QTT1272	1/2"x72"	Part# QTT91672	9/16"x72"	Part# QTT3472	3/4"x72"

More sizes available

HIGH SPEED STEEL

Superior quality M-2 High Speed Steel drill bit welded to a flexible shaft. Cuts both metal and wood. No need to worry about hidden nails or metal studs when drilling.

Part# FLX1424	1/4"x24"	Part# FLX3824	3/8"x24"	Part# FLX1224	1/2"x24"
Part# FLX1436	1/4"x36"	Part# FLX3836	3/8"x36"	Part# FLX1236	1/2"x36"
Part# FLX1448	1/4"x48"	Part# FLX3848	3/8"x48"	Part# FLX1248	1/2"x48"
Part# FLX1454	1/4"x54"	Part# FLX3854	3/8"x54"	Part# FLX1254	1/2"x54"
Part# FLX1472	1/4"x72"	Part# FLX3872	3/8"x72"	Part# FLX1272	1/2"x72"

GUIDE TOOL

Allows the Piranhabits to bend for drilling from outside the wall cavity.



Part# FIB-GUD

OverDRIVE™

FAST BORING AUGER BITS

The Over-Drive boring auger bits are specifically designed to not bog down your battery drill. Designed with a 1/4" chuck and available in 3/4" and 7/8".

Features:

- Available in 7" lengths
- 1/4" drill chuck
- Designed to put less strain on your battery drill

Part# AW340D-3/4" x 7"
AW780D-7/8" x 7"

AUGER FILE

DON'T THROW AWAY EXPENSIVE AUGER BITS!

Save those precious auger bits from being another dull tool lying around your shop or work truck. Save time and money by sharpening your bits from the comfort of your own home.

Features

- Top teeth for auger's main cutters
- Side teeth for sharpening tip

DIRT AUGER SYSTEM

USE FOR AUGURING AND INSTALLING WIRE OR PIPE UNDER SIDEWALKS AND DRIVEWAYS

Features:

- Fish hole for easy retrieval of wire
- Custom heat treated drill bit designed for organic material
- Long taper for easy retrieval
- Interchangeable lengths
- Custom heat treated spring steel shank for optimum memory

Applications:

- Cable Installation
- Landscape Lighting
- Sprinkling Systems
- Landscape Feeding Stakes

Part# ETD034

Part# AUFILE

18" AUGER BITS


Part# AW3818	3/8"
Part# AW1218	1/2"
Part# AW11618	11/16"
Part# AW3418	3/4"
Part# AW7818	7/8"
Part# AW118	1"
Part# AW1418	1 1/4"

7 1/2" AUGER BITS

Part# AW3807	3/8"
Part# AW1207	1/2"
Part# AW11607	11/16"
Part# AW3407	3/4"
Part# AW7807	7/8"
Part# AW107	1"

NAIL CHIPPER & STANDARD CHIP AUGER


NAIL CHIPPER SHIP AUGER



TRI-CUT design with 3 precision ground edges for fast, smooth cutting without resistance.

REDUCES NAILS TO CHIPS without grabbing and leaves a clean hole with minimal "blowout."

STANDARD SHIP AUGER



Precision ground cutting edge for fast cutting of clean holes in wood.


Burr-free lead screw for easy starts and pull-through without material build-up.

BUMPER BALLS

AUGER SHAFT CENTERING TOOL

- No more bit walking, nail hitting, wall patching or carpet replacing
- Fits all 3/16" shaft auger bits
- Includes 1 each of 1-3/4" & 2-1/4" Balls (Drill Bits not included)

Part# BB3412



BEFORE AFTER



HOLE PRO

MULTI-FUNCTION HOLE CUTTER

The dust has finally cleared... we've worked out the growing pains with the new improved nylon bushing.

SAVE YOUR LUNGS! CUTTING HOLES WITHOUT PROTECTION CAN BE HAZARDOUS TO YOUR HEALTH. PROTECT YOU & YOUR CREW WITH THE HOLE PRO.

CUTS THROUGH:

- Plywood
- Fiber cement board
- Sheetrock
- Up to 20 GA. sheet metal
- Fiberglass
- Aluminum

Part# 90200 - Hole Pro 1 7/8" to 9"
 Part# 90300 - Hole Pro 1 7/8" to 12"
 Part# 90400 - Hole Pro 1 7/8" to 17"

REPLACEMENT BLADES



Part# 90-VH HSS
 Part# 90-VT Carbide

Compare Features	Other Hole Saw Kits	HOLE PRO
Adjusts to exact hole size needed	NO Van full of dull hole saws	YES! 1 7/8" - 9", 1 7/8" - 12" & 1 7/8" - 17
Dust collector shield	NO Lady finds new contractor	YES! Clean job
Designed to reduce kickback	NO Jaw breaker	YES! Non-jaw breaker
Economical replaceable blades	NO Sharpen a bunch of little teeth	YES! Sharpen only two blades
Price	\$300.00	LESS THAN HALF!

HOLE SAW ACCESSORIES

HOLE SAW DUST SHIELD

- Has a ABS shield that collects all the dust and shavings when using a hole saw.
- Has a 7 3/4" OD and 6 3/8" ID supporting a hole saw up to 6 1/4" in diameter and up to 2 1/2" cutting depth.
- Saw and vacuum adapter sold separately

Part# 90103



VACUUM ADAPTER FOR ALL HOLE PRO DUST SHIELDS

- Reusable plug to re-seal shield hole
- Perfect addition to hole-pro shields, power series X & XL models
- Attaches to standard 1" power tool vacuum hose

Part# 90101



ARBOR HOLE SAW ADAPTER FOR ALL HOLE CUTTER MODELS

- Covers any hole cutters for use with any hole saw
- Unique dual head design allows mounting 1/2"-20" or 5/8"-18" threaded hole saws

Part# 90105



CHIP CATCHER

- INCREASES SAFETY
- MAGNET BASE ATTACHES TO METAL SURFACES & CATCHES METAL SHAVINGS
- QUICK & CONVENIENT CLEAN-UP

Part# 84100



***NOT TO BE USED ON LIVE PANELS**

DIRT BAG



ELECTRICAL SAFETY DRILLING TOOL

- Increases safety
- Easily attaches to metal surfaces
- Made from non-conductive material
- Removable magnet included in bag pocket
- Fits most panels

The Dirt Bag is specifically designed to eliminate metal shavings from spreading throughout a panel while drilling. The Dirt Bag is a portable solution, that will save you time and reduce damage to electrical components.

Part# 84000

NO MORE MESS EASY DISPOSAL OF DEBRIS WORKS WITH HOLE SAW UP TO 8" AND DRILL BITS TOO!

Driller's Dustbowl

THE FLEXIBLE DRILLER'S DUST BOWL COMPRESSES AGAINST THE WORK SURFACE AND TRAPS ALL DUST AND DEBRIS AS YOU DRILL. THE BOWL FITS YOUR DRILL AND HOLE SAW WITHOUT ANY ADJUSTMENTS NEEDED.

MFG NOTE:
 YOU MAY ENJOY A FACE FULL OF DRYWALL DUST, BUT YOUR CUSTOMERS MIGHT NOT. PUT AN END TO "UNPROTECTED HOLE SAWING" AND WRAP UP WITH THE DRILLER'S DUST BOWL.



PART# 48000



Exploding GARBAGE CAN

Part# 51000

ONE OF OUR CLASSIC TOOLS THAT EVERYBODY LOVES, THE EXPLODING GARBAGE CAN COMES IN USE EVERY SINGLE DAY. THIS COLLAPSIBLE TRASH CONTAINER, FEATURING AN INTERNAL SUPPORT SPRING THAT "SPRINGS INTO ACTION", IS MADE OF HEAVY DUTY, TEAR RESISTANT POLYTUF™ FABRIC.

FEATURES

- Size of 19" x 24" when open
- Size of 1 1/2" x 24" when collapsed

RACKY BITS

COLOR CODED DRIVER BITS

It's so simple but it works.

Racky Bits are easier to use and harder to lose. If that's not enough, our genuine Robertson® RACKY BITS have hardened tips that fit better and last longer.

GENUINE ROBERTSON BITS



DOUBLE ENDED HEX BIT



Part# 72564RY

IMPACT BITS



MAGNETIC HEX BITS



DOUBLE ENDED HEX BITS



PHILLIPS BITS



#0 YELLOW ROBERTSON® SQUARE BIT PART#'S

- 3" Bulk Bit - 70030Y
- 4" Bulk Bit - 70040Y
- 3" Packaged Bit - 70030YP1
- 4" Packaged Bit - 70040YP1

#1 GREEN ROBERTSON® SQUARE BIT PART#'S

- 3" Bulk Bit - 70130G
- 4" Bulk Bit - 70140G
- 6" Bulk Bit - 70160G
- 3" Packaged Bit - 70130GP1
- 3" Packaged Bits (Qty 2) - 70130GP2
- 4" Packaged Bit - 70140GP1
- 4" Packaged Bits (Qty 2) - 70140GP2
- 6" Packaged Bit - 70160GP1
- 6" Packaged Bits (Qty 2) - 70160GP2

#2 RED ROBERTSON® SQUARE BIT PART#'S

- 3" Bulk Bit - 70230R
- 4" Bulk Bit - 70240R
- 6" Bulk Bit - 70260R
- 3" Packaged Bit - 70230RP1
- 3" Packaged Bits (Qty 2) - 70230RP2
- 4" Packaged Bit - 70240RP1
- 4" Packaged Bits (Qty 2) - 70240RP2
- 6" Packaged Bit - 70260RP1
- 6" Packaged Bits (Qty 2) - 70260RP2

#3 BLACK ROBERTSON® SQUARE BIT PART#'S

- 4" Bulk Bit - 70340BK
- 6" Bulk Bit - 70360BK
- 4" Packaged Bit - 70340BKP1
- 6" Packaged Bit - 70360BKP1

#4 ORANGE ROBERTSON® SQUARE BIT PART#

70430P

1/4" RED HEX BIT PART#'S

- 2.5" Bulk Hex Bit - 70531R
- 6" Bulk Hex Bit - 70561R
- 2.5" Packaged Hex Bit - 70531RP1
- 6" Packaged Hex Bit - 70561RP1

5/16" YELLOW HEX BIT PART#'S

- 2.5" Bulk Hex Bit - 70631Y
- 6" Bulk Hex Bit - 70661Y
- 2.5" Packaged Hex Bit - 70631YP1
- 6" Packaged Hex Bit - 70661YP1

3/8" BLUE HEX BITS PART#'S

- 2.5" Bulk Hex Bit - 70731BL
- 6" Bulk Hex Bit - 70761BL
- 2.5" Packaged Hex Bit - 70731BLP1
- 6" Packaged Hex Bit - 70761BLP1

7/16" BROWN HEX BIT PART#'S

- 2.5" Bulk Hex Bit - 70831BR
- 6" Bulk Hex Bit - 70861BR
- 2.5" Packaged Hex Bit - 70831BRP1
- 6" Packaged Hex Bit - 70861BRP1

1/2" BLACK HEX BIT PART#'S

- 2.5" Bulk Hex Bit - 70931BK
- 6" Bulk Hex Bit - 70961BK
- 2.5" Packaged Hex Bit - 70931BKP1
- 6" Packaged Hex Bit - 70961BKP1

DOUBLE HEX BIT PART#

5/16" & 1/4" Hex Bit - 72564RY

#1 & #2 DOUBLE ENDED SQUARE BIT PART#'S

- 4" Bulk Bit - 72124GR
- 6" Bulk Bit - 72126GR
- 4" Packaged Bit - 72124GRP1
- 4" Packaged Bits (Qty 2) - 72124GRP2
- 6" Packaged Bit - 72126GRP1
- 6" Packaged Bits (Qty 2) - 72126GRP2

#2 PHILLIPS & 1/4" SLOT DOUBLE ENDED BIT PART#'S

- 4" Bulk Bit - 72204BY
- 6" Bulk Bit - 72206BY
- 4" Packaged Bit - 72204BYP1
- 4" Packaged Bits (Qty 2) - 72204BYP2
- 6" Packaged Bit - 72206BYP1
- 6" Packaged Bits (Qty 2) - 72206BYP2

#1 LIGHT BLUE PHILLIPS BIT PART#'S

- 4" Bulk Bit - 70141LB
- 4" Packaged Bit - 70141LBP1
- 4" Packaged Bits (Qty 2) - 70141LBP2

IMPACT DRIVER BITS PART#'S

- Impact Driver Bit - Phillips #1 x 1" - 7011PI
- Impact Driver Bit - Phillips #1 x 2" - 7012PI
- Impact Driver Bit - Square Green #1x1" - 7011RI
- Impact Driver Bit - Square Green #1 x 2" - 7012RI
- Impact Driver Bit - Phillips #2 x 1" - 7021PI
- Impact Driver Bit - Phillips #2 x 2" - 7022PI
- Impact Driver Bit - Square Red #2 x 1" - 7021RI
- Impact Driver Bit - Square Red #2 x 2" - 7022RI
- Impact Driver Bit - Square Black #3 x 1" - 7031RI
- Impact Driver Bit - Square Black #3 x 2" - 7032RI

HOLDSaBIT

Every moment during a project that you spend looking for the right tool is wasted time and results in frustration and bad decisions. If you've lost your temper while trying to find a screw bit or drill bit, We know what you mean!



The ingenious HOLDSaBIT slips on or off a drill in seconds. Simply pull one loop over the front of the drill and pull the second loop to the back of the drill.

The HOLDSaBIT will hold any 1/4" hex shank item as well as pencils, nut drivers and hex shank drill bits. Tips and bits are easily inserted and removed. They will hold in the channels even when the drill is turned upside down.

This handy item keeps your drill bit accessories "Where you need them - When you need them".


The four channels allow you to customize the holder as needed for each particular job. The two loops also allow for the HOLDSaBIT to be used on a tool belt, keeping your accessories close by.

Part# 70000 (Bits Not Included)
Part# 700.kit (includes 1-7014G, 1-70240R, 1-70241BL, 1-70531R, 1-70631Y & 1-72133P)

lockHARD bit

The lockHARD bit has two strategically placed wings on the sides of its square bit end. This allows it to lock into place and makes sure you NEVER strip another screw.

PART#
72133P - 3" BULK BIT
72134P - 4" BULK BIT





PICQUIC®



SIXPAC plus

- 7 - 3" LENGTH, 1/4" HEX POWERBITS
- 11.5" TOTAL LENGTH

PART# P88001



DASH 7

- 7 - 2" LENGTH, 1/4" HEX POWERBITS
- COMES IN 4 BRIGHT NEW COLORS

PART# P05001



STUBBY

- SOLID, COMFORTABLE, HIGH TORQUE HANDLE
- 6 HIGH QUALITY 1.3" LENGTH INSERT BITS
- IDEAL FOR WORK IN CLOSE QUARTERS

PART# P91000



Roberston®



GREEN ROBBY

- #5-6-7 SQUARE DRIVE

PART# SD110G



RED ROBBY

- #8-9-10 SQUARE DRIVE

PART# SD210R



BLACK ROBBY

- #12-13-14 SQUARE DRIVE

PART# SD310BK



DEMAGNETIZER

MAGNETIZES OR DEMAGNETIZES DRIVER BITS, TOOLS AND SMALL STEEL PARTS INSTANTLY!
Part# 70988

MAGNETIC BIT HOLDER



QUICK CHANGE MAGNETIC BIT HOLDER
PART# 72000

- WORKS ON JAGGED, UNEVEN AND ROUGH BREAKS
- SELF CENTERING TIP, NO WALKING
- COMPATIBLE WITH QUICK CONNECT CHUCK SYSTEMS
- EASY TO USE WITH 3/8" VARIABLE SPEED REVERSIBLE DRILL
- EXTRACTS SCREWS UP TO 4 INCHES



proGrabit

DAMAGED SCREW REMOVER

PART# 72120

ROLGEAR

MULTIBIT RATCHET SCREWDRIVER / 15 TIPS (DOUBLE ENDED BITS)

- Slotted: 3/16", 1/4"
- Square: 1, 2, 3, 4
- Phillips: 1, 2, 3, 4
- Torx: 10, 15, 20, 25
- Smooth and silent ratcheting
- Single-handed ratchet adjustments from forward, locked, & backward
- Ergonomic, cushion comfort handle
- Magnetic components for drop-safe bit changing
- Stainless steel bit adapter

PART# SDR14



AERIAL TOOL BIN



- Made with reinforced, high density, non-conductive, UV protected, light-weight durable orange polypropylene plastic nearly as strong as steel
- Attaches to square or rounded 90° corners and is secured to railings with two locking bolts
- Provides maximum working area, with the triangular shape nicely tucked into a 90° corner, leaving platform floors free from clutter



PART# ATB1312

BOLT TEMPLATE



The Bolt Template helps you easily lay out bolts to be used in concrete for future installation of poles or beams. The template is multi-functional and has an easy guide for centering bolts.

- Has a whopping 41 templates!
- Quick, easy, and reusable
- Weather resistant ABS plastic
- Sets poles and beams 8" - 24"



Part# 67441

GLOW SAFE 360



The Glow Safe 360 attaches to any hard hat and produces a ring of light around the wearer, enabling him or her to be easily seen in all directions.

FEATURES:

- Shadow-free, panoramic visibility
- Non-slip hard hat attachment
- Only 40 grams (1.4 oz) extra hard hat weight
- Powered by two button cells or rechargeable LED
- Operates up to 24 hours with premium brand batteries or USB Charger




Rechargeable
Glow Safe
Part# 54020

Battery Powered
Glow Safe
Part# 54000

MAG DADDY

MAGNETIC FASTENERS



MAG DADDY MAGNETIC FASTENERS UTILIZE ULTRA-STRONG MAGNETS TO STRAP WIRE AND CABLE. MAG DADDY MAGNETS WILL STAY ATTACHED THROUGH OIL, GREASE, PAINT OR DIRT. A VARIETY OF CONFIGURATIONS ARE AVAILABLE TO SUIT YOUR NEEDS.

CABLE HOLDERS



Magnetic Cable Holder
 Part# RM050BK - 1/2" Black
 Part# RM050WT - 1/2" White
 Part# RM075BK - 3/4" Black
 Part# RM075WT - 3/4" White
 Part# RM100BK - 1" Black
 Part# RM100WT - 1" White



Magnetic Clamp
 Magnetic Strength: 15 lbs.
 Part# RM051BK - 1/2" Black



Female Magnet Mount
 1/4-20
 Part# RM420FM



Magnetic Cable Tie Mount
 Holds Standard Zip Ties
 Part# RM110BK - 10 lb Black
 Part# RM110WT - 10 lb White
 Part# RM115BK - 15 lb Black
 Part# RM115WT - 15 lb White



3/4" Wide Cable Mount
 Part# RM215BK - 15 lbs Black



Cable Hanger
 Cable Hanging Tool
 Part# RM300HT



Magnet Mounts
 Part# RM164SL - 19 mm/16 lb Silver
 Part# RM265SL - 23 mm/26 lb Silver
 Part# RM266SL - 26 mm 26 lb Silver



Mini Magnet Cable Tie Mount
 Color: Black
 Magnetic Strength: 5 lbs
 Part# RM020BK

TOP J-HOOKS



360° Rotation
 Part# RMJ075T - 3/4"
 Part# RMJ131T - 1 5/16"
 Part# RMJ200T - 2"

SIDE J-HOOKS



360° Rotation
 Part# RMJ075S - 3/4"
 Part# RMJ131S - 1 5/16"
 Part# RMJ200S - 2"

BRIDLE RINGS



Magnetic Bridle Ring
 Part# RM125BR - 1.25" 1/4-20
 Part# RM200BR - 2" 1/4-20

RACKY STRAPS



Racky Strap utility straps hold almost anything wherever you need them. These are handy on any site with several wires or other loose items.

Features

- Holds anything up to 33lb per sq. inch
- Quality hook and loop may be used with soft side up or down
- Available in 1/2" x 8" and 1"x12" strips
- Great for data cable

Part# RS1005 - 1/2" x 8" Straps
 Part# RS1010 - 1" x 12" Straps

VAN MAGNETS

VAN MAGNET STEEL TRI-ANGLE DISPLAY STAND
 Includes:
 1 x RV010
 1 x RV025
 1 x RV050
 1 x Steel Stand
 Part# RVDisplay

*All Van Magnets
 Include carabiner



Part# RV010 - 10 lbs



Part# RV025 - 25 lbs



Part# RV050 - 50 lbs



FLOOR & COUNTERTOP BOXES



Introducing Rack-A-Tiers new Pop-Up boxes. The sleek and compact design offers a great option for installing a pop-up outlet into a countertop or floor. Pops up while in use and is out of the way and flush when pushed down.

Countertop Boxes



Countertop Pop-Up Box With 20 Amp GFI Receptacle:

- VPU.BK Black
- VPU.SS Stainless Steel
- VPU.WT White
- VPU.BR Brass

Countertop Pop-Up Box With Single 15 Amp Power / 2USB

- VPU.BK.2USB Black
- VPU.SS.2USB Stainless Steel
- VPU.WT.2USB White
- VPU.BR.2USB Brass

Countertop Pop-Up Box With 20 Amp GFI Receptacle and Nightlight Feature:

- VPU.BK.NL Black
- VPU.SS.NL Stainless Steel
- VPU.WT.NL White
- VPU.BR.NL Brass

(Available in Red by special order)

Floor Boxes

6" Stainless steel pop out floor plate with 15 Amp (TR) GFI receptacle
Part# VPU.FB.SS

6" Stainless steel pop out floor plate with 6-Comm./Data ports
Part# VPU.FC.SS

6" Brass pop out floor plate with 15 Amp (TR) GFI receptacle
Part# VPU.FB.BR

6" Brass pop out floor plate with 6-Comm./Data ports
Part# VPC.FC.BR

6" Brass Pop out floor plate with 15 Amp (TR) Decora receptacle
Part# VPU.FD.BR

VPU.WB - Wood floor box for FB, FC & FD series

VPU.CB - Concrete floor box for FB, FC & FD series

6" Brass Pop out floor plate with 15 Amp (TR) Decora receptacle
Part# VPU.FD.BR

6" Stainless Steel pop out floor plate with 15 Amp (TR) Decora receptacle
Part# VPU.FD.SS

Also Available:



CAST IRON FLOOR BOXES




NOZZLES



DESKTOP BOXES

Call for details

6.5 BLANK PLATE



- Installs in seconds with rare earth magnets - snaps in place to metal clips (included)
- White decorative plate covers any 5-1/2" square hole or electrical box
- Can also be used to cover a round hole with up to a 5-1/2" diameter
- Visually appealing white decorative plate - no need to paint metal covers

Part# D612

AIRCRAFT CABLE & WIRE CRIMPS



- AVAILABLE IN 500 AND 1,000 FEET.
- NO NEED TO GO ANYWHERE ELSE - BUY IT FROM US!

Part# SC500 - Aircraft Seismic Cable 500'
Part# SC1000 - Aircraft Seismic Cable 1000'
Part# SCC116 - Aircraft Seismic Cable Clamps

DRYCONN®

WATERPROOF CONNECTORS



FILLED CONNECTORS FOR OUTDOOR USE

Part #	Selling Unit	Wire Range
62110	Card of 6	22 — 12
62125	Bag of 25	22 — 12
62210	Card of 5	22 — 8
62225	Bag of 20	22 — 8
62310	Card of 3	14 — 6
62335	Bag of 50	14 — 6

"One-Step"® Installations
Corrosion Proof
Reduces Risk of Fire
CSA certified as a Pressure Type Connector

Suitable for all wire splices, especially those exposed to condensation, water, vapors or dust.

FILLED CONNECTORS FOR DIRECT BURY USE

Part #	Selling Unit	Wire Range
10600	Card of 2	22 — 8
10666	Bag of 10	22 — 8
10999	Bag of 8	14 — 6
10444	Bag of 10	18 — 12
10555	Bag of 10	14 — 10

"One-Step" Installations
CSA certified as a Pressure Type Connector
CSA certified as Direct Bury
Corrosion proof

FILLERS & CONNECTORS

KO KILLERS: PLASTIC KNOCKOUT FILLERS

Fits thin (1/32") and thick (1/8") wall thickness.

Features

- No tools required
- Snap in and out with ease
- Non-conductive, safer



- Part# KOK50 - 1/2" Filler (50/bag)
- Part# KOK75 - 3/4" Filler (50/bag)
- Part# KOK100 - 1" Filler (25/bag)
- Part# KOK125 - 1 1/4" Filler (25/bag)
- Part# KOK150 - 1 1/2" Filler (25/bag)
- Part# KOK200 - 2" Filler (25/bag)
- Part# KOK999 - Assorted Fillers Kit (25/bag)

RAT 500

Rapid Fire NMSC connector

Suitable for all 1/2" knockouts
Fast and Easy. No tools required

Features

- 100/bag
- Single cables
- Two cables
- Install from outside

RAT 750

Rapid Fire NMSC connector

Suitable for all 3/4" knockouts
Fast and Easy. No tools required

Features

- 50/bag
- Single cables
- Install from outside



- Part# RAT500 1/2" Connector
- Part# RAT750 3/4" Connector

TT500

NMSC Two Way 1/2" Connector

Installs from inside and outside the box

Features:

- 100/bag
- Single cables
- Two cables

- Part# TT500



STUD BUDDIES

Why Square Bushing? 70% More cross sectional area! More cables, easier pulls.

- One piece
- One hand installation
- Fits all standard steel studs & punches
- Fire rated V.O.
- Faster, easier to use

- Part# ROUND - SB200
- Part# SQUARE - SB400



LEVEL JACK

Alignment tabs reach across wood/metal studs to level low voltage outlets with A.C. boxes.

Features

- No tape measure
- No level required



- Part# LJ50R - 1/2"
- Part# LJ58R - 5/8"
- Part# LJ100R - 1"



ROBERTSON SCREWS

The Original Robertson screw is the only one that guarantees a perfect "Cling Fit"

Please Call For Part Numbers

FLAT HEAD WOOD SCREWS



PAN HEAD SHEET METAL SCREWS



ROUND HEAD MACHINE SCREWS



CAMTAP® SELF-DRILLING SCREWS



TRUSS HEAD SCREWS



ANCHORS, WASHERS, NUTS & BOLTS



USE THEM WITH OUR ROBERTSON DRIVER BITS.

NEVER DROP A SCREW AGAIN!

GO GREEN WITH REUSABLE CONTAINERS FROM RACK-A-TIERS!

No more spilling screws on the job because of a flimsy box. Reusable Containers from Rack-A-Tiers are a great way to organize your van and go green at the same time!

Part# REJAR



The EZ-Clip is a snap-on protection plate designed specifically for steel studs. Its one size fits all design will quickly and easily snap on to any steel stud. **NO SCREWS REQUIRED!**

- CSA approved for Canada and the U.S.
- Made from 1.6mm galvanized metal
- Protects your wire from drywall screws
- Fast, easy and simple
- No screws required
- Made in Canada

- Part# SPE100 - 100 PACK
- Part# SPE25 - 25 PACK

CABLE EZE

- Protection from radius bends for all data cables
- Rapid ease of installation (seconds to install, saves time and money)
- No tools required for installation (no need to cut and compromise the strength of basket tray)
- Ability to utilise Cable Eze anywhere on tray
- Can be retro fitted or installed after cable rough in
- Made from nylon
- Can be removed and reinstalled where necessary
- Fits all brands of 100mm x 50mm cable trays



Part# 42240

ULTRA-SIDEWINDER

CABLE PROTECTION SYSTEMS

FEATURES:

- ARTICULATION PIECES OFFER FLEXIBLE DESIGN - CURVES, CORNERS & S-CURVES ARE EASILY MADE WHILE MAINTAINING A COMPLETELY FLAT PROFILE.
- SIMPLE INSTALLATION. NO TOOLS REQUIRED.
- AVAILABLE IN BLACK, YELLOW, BROWN, AND GRAY.
- FULLY-CUSTOMIZABLE LENGTH - FROM 4.5" TO AN UNLIMITED LENGTH.



Cavity Size: 3/4" W x 3/8" H

Part#	Description
U1800BY	3 FT System W/ Endcaps - Black & Yellow
U1802BK	3 FT System W/ Endcaps - Black
U1804BR	3 FT System W/ Endcaps - Brown
U1806G	3 FT System W/ Endcaps - Gray
U1801BY	1 FT Extension System - Black & Yellow
U1803BK	1 FT Extension System - Black
U1805BR	1 FT Extension System - Brown
U1807G	1 FT Extension System - Gray

TEMPORARY CABLE GUARD

5' LONG X 4.5" WIDE X 1.25" HIGH

Accommodates cable up to .75" in diameter. Withstands heavy vehicle traffic. Part# TCG5

The Temporary Cable Guard withstands heavy vehicle traffic without damaging cable. Easily anchored with concrete screws if needed. The Temporary Cable Guard helps you restore services quickly by allowing you to run temporary cables over most any surface. It reduces truck rolls and eliminates downtime due to cable cuts, storm damage, traffic or roadway activities.

5' LONG X 10.5" WIDE X 2.75" HIGH

Accommodates a cable/bundle up to 2.25". Withstands heavy vehicle traffic. Part# TPG5

ELECTRICAL CODE SIMPLIFIED PS KNIGHT

FEATURES:


- Now over 1200 pages
- Over 1000 code rules & revisions, clearly explained & indexed
- Code tables & practice exam
- 400 questions & answers added

MFG NOTE

The industry's most comprehensive publication on Canadian electrical code that clarifies the New Code Rules.

Electrical Code Simplified Part# 73129

Electrical Code Simplified - Residential Part# 73115



Part#	Description	Page	Part#	Description	Page
10455	Hooker - Wrench Adaptor	2	72120	ProGrabit	37
11455	Rack-A-Tiers	1	7213series	LockHard Bits	36
11460	Rack-N-Go	2	75000	Breaker Lok	26
11555	Stick	3	77455	Bend-All	8
11655	X-Dispenser	3	78series	Bulldog Benders, The	8
13355	Plate Vise	27	7bitseries	Racky Driver Bits	35-36
18455	Wire Tub	3	7WBK100	Panel Buddy Knockout Kit	26
118series	Reel Macs & Spindles	6	83000	LaserLine	27
119series	Spool Mac & Caddy Mac Line	5	84000, 84100	Dirt Bag & Chip Catcher	34
11931, 11932	Tug Wise Standard and Deluxe	4	88455	Laser Plumb Bob	21
2Super Rod Series	Super Rod	16	90101	Vacuum Adapter	33
40001	Wire Vortex	16	90103	Hole Saw Dust Shield	33
40400	Stingray	16	90105	Arbor Hole Saw Adapter	33
42200	LB Wire Guide	14	90200, 90300, 90400	Hole Pro - Hole Cutters	33
42240	Cable Eze	43	914series	TCT Masonry Hole Cutters	29
42400	Ropematic Pro	14	916series	TCT Mega Hole Cutters	29
42600	Cone Heads	13	91700	Rev-Bit	30
42620	Flex Puller	13	93series	Steel Cutters	29
42800, 42900	Magnepull & Magnespot	11	94series	Gid-O	29
42series	All-American Pull Buddies	14	95000	Javelin	30
43002	Big Lugg 2	20	97008	Qwik Lok	26
43015, 43095, 43100	Butt Pouches	19	99000, 99001	AC Sensor & Ultimate AC Sensor	22
43055	Electrician's Holster	19	99005	Piper Conduit	10
432series	Combo Tool Belt & Pouches	19	99101	Circuit Siren	22
434series	Support Belt	19	99102	Plug Master	22
43606	Suspenders	19	99215	EZ Generator Switch	22
43706, 43707	Tool Carriers	19	ATB1312	Aerial Tool Bin	38
45200	Shoppe Rocket	21	AUFILE	Auger Bit File	32
45303	Straight Shot	22	AW34OD, AW78OD	OverDrive Bits	32
45404	Jet Level	22	AWseries	Auger - Standard & Tri-Cut	32
47000, 47002	Croc's Needle Nose Wire Strippers & Jr.	24	BB3412	Bumper Balls	32
47010	V-Cutter	24	BPseries	Bag Pipers	13
47020	Easy Stripper	7	CC1200, CT1100	Cable Caddy & Cable Truck	6
47030	Copper Wire Stripper Jr.	7	CC2000, CC2000D	Cable Cart & Cable Cart Data	6
47099	Booty Pack	20	CD3000, CD3100	Cable Dolly & Jr	6
47100	CWS-1 Copper Wire Stripper	7	D612	Magnetic Drywall Plate Cover Kit	42
47200	CWS-2 Copper Wire Stripper	7	EF003	Efergy Elite Classic	22
48000	Driller's Dust Bowl	33	ENseries	Nylon Fish Tapes & Polyester Fish Tapes	18
51000	Exploding Garbage Can	34	ETD034	Dirt Auger System	32
52300	Stud Ball	28	ETseries	Switch Bits	31
52455	Staple Shark	23	FIB-GUD	Guide Tool	31
52466, 52486	Pencil & Quick Draw Felt Pen	26	FIBseries	Fiberfish Attachments	17
53020	Gopher 2	25	FIBLseries	Fibersnakes 5/16"	18
53300, 53400	Owl Eye & Fire Fly	25	FIBRseries	Fibersnakes 1/4"	18
53500, 53600	Stick Bug & Jr.	25	FIBTseries	Fibersnakes 3/16" 50' - 300'	18
54000, 54020	Glow Safe 360	38	FLXseries	Piranhabits - High Speed Steel	31
55455	E-Z Roll	2	Fseries	Robertson Screws	44
55632	Big E-Z	2	GLFseries	Plastic Coated Glowfish	17
56000	Pocket-Kart	4	KOKseries	KO Killers Connectors	43
57050, 57075	Hoppy Bender	9	LJseries	Level Jacks	43
58series	Pipe Vipers	10	MLTseries	Multi-Bit Step Drills	29
65000	Bulb Caddy	25	NT1050	Extendo Nut Driver	24
65100, 65200	Shinmates	25	Pseries	Picquic Screwdrivers	37
65300	Ladder-Mate	25	PCFseries	Plastic Coated Fiberfish	17
66455	Knee Pads	20	QTTseries	Quattro Flex Auger Bits	31
66536	Lift-N-Lok Tool Box	20	RAT500, RAT750	NMSC Connectors	43
67119	Sluggo-Ox	28	RMseries	Mag Daddy	39-40
67441	Bolt Template	38	RS10series	Racky Straps	40
67500	GD Center Finder	12	RVseries	Van Magnets	39-40
68075	Alignment Tool	12	SBseries	Stud Buddies Connectors	43
69010	Fish Heads	15	SCseries	Aircraft Cable & Wire Crimps	42
69050, 69075	Flex Flyers	15	SDR14	Rolgear Screwdriver	37
69455	Snatch Strap	15	SDseries	Robertson Screwdrivers	37
69700, 69705	Penguin Puller Sr. & Jr.	13	SPEseries	EZ Clip	43
70000	Holdsabit	36	SS1series	Standard Super Set, Super Set 18	17
70988	Magnetizer / Demagnetizer	37	TPG5, TCG5	Temporary Cable Guard	45
72000	Magnetic Bit Holder	37	TT500	Tom Two-Way Connector	43
72101, 72102	Nut Blaster XL and XXL	26	U18series	Sidewinders	45

ATTENTION ALL WHOLESALERS!

SPRUCE UP YOUR SHOWROOM WITH A GREAT LOOKING DISPLAY FROM **RACK-A-TIERS**



MOBILE 12 DISPLAY
Part# MOBILEDISPLAY12



16" X 36" METAL PANEL WALL DISPLAY
Part# WALLDISPLAY16



RACKY BITS
COUNTERTOP DISPLAY
PART# 70SKE12



24" X 48" PAPER WALL PANELS
Part# WALLPAPER-BK (24"x 48")

RackRewards

CONTRACTOR REWARDS PROGRAM

BUY RACK-A-TIERS PRODUCTS

Visit your favourite electrical wholesaler and purchase eligible Rack-A-Tiers products.

REGISTER YOUR PRODUCT CODES

Find the 10 digit code on your product packaging and enter it on the "Enter a Code" page. Volts are automatically added to your account!

XXX-XXXX-XX-XXXXXX

GET REWARDS! (FREE STUFF)

Volts are just like money. Redeem your Volts for items in the Rewards Store. You'll find tons of different rewards like free Rack-A-Tiers Products, Electronics and More!



INVENTOR'S CORNER

Find yourself flipping through the Rack-A-Tiers catalog wishing you thought of that tool, or frustrated that you thought of that idea first? Well, here's your chance to put your ideas into action. Rack-A-Tiers launched Inventor's Corner for creative folks like you to pitch ideas and read testimonials from past inventors.

We pride ourselves on being the most innovative and unique tool company in the electrical industry. As we continue to grow, more and more electricians approach us with great ideas. We would love to see every electrician get his or her idea into the market and will do everything in our power to make that happen. Even if Rack-A-Tiers is unable to add your idea to our product line, we have the experience and knowledge to provide advice for your next move as an inventor.

Check out the Inventor's Corner at rack-a-tiers.com/inventors and who knows maybe in next year's catalog your product could have a full-page spread.

