



PROGRESS<sup>®</sup>  
LIGHTING



LIGHTING SOLUTIONS





# BATH VAN

CLEAN, CLASSIC DESIGNS INSPIRE TRENDS IN BATH AND VANITY DÉCOR. LIGHTING CAN BE USED TO CREATE A DRAMATIC, GLAMOROUS ENVIRONMENT OR A MORE SUBDUED IN-HOME SPA AMBIANCE.

WALL SCONCES, RECESSED LIGHTING, PENDANTS AND CHANDELIERS WORK TOGETHER TO CREATE A LAYERED LIGHTING DESIGN, WHICH ILLUMINATES DIFFERENT AREAS OF THE BATHROOM, WHILE CREATING AN INVITING ATMOSPHERE.



# ELINA



P2099-104

TALL TRUMPETED OPAL GLASS. K-9 GLASS ORB ACCENTS WITH A POLISHED NICKEL FINISH.



P2100-104

### ONE-LIGHT BATH

**P2099-104** Polished Nickel  
Size: 4-1/2" W., 19" ht.  
Extends 6". H/CTR 9-5/8".  
Lamp: One medium base lamp, 100w max.

### THREE-LIGHT BATH

**P2100-104** Polished Nickel  
Size: 23" W., 10-1/4" ht.  
Extends 6-1/4". H/CTR 4".  
Lamps: Three medium base lamps, 100w max.

Chandelier  
pg 12



# THE POINTE

WITH ALTERNATING CLEAR AND CHAMPAGNE TINTED K-9 GLASS ACCENTS, THE POINTE CELEBRATES THE ELEMENT OF SPARKLE.



P7134-15

### ONE-LIGHT BATH

**P7134-15** Polished Chrome  
Size: 6-1/2" W., 6-1/4" ht.  
Extends 5-7/8". H/CTR 3-1/8".  
Lamp: One candelabra base lamp, 60w max.

### FOUR-LIGHT BATH

**P2098-15** Polished Chrome  
Size: 24-7/8" W., 4-5/8" ht.  
Extends 6". H/CTR 2-1/4".  
Lamps: Four candelabra base lamps, each 60w max.



P2098-15

Chandelier  
pg 8



# CARESS

CHIC SOPHISTICATION WITH CYLINDRICAL GLASS SHADES. ETCHED GLASS DIFFUSER INSIDE CLEAR WATER GLASS FLOATS IN A TRADITIONAL PROFILE.



**ONE-LIGHT BATH**  
**P7046-104WB** Polished Nickel  
 Size: 8" W., 15" ht.  
 Extends 9-1/2". H/CTR 8-7/8".  
 Lamp: One E12 base krypton lamp, 60w max., included.

**TWO-LIGHT BATH**  
**P3076-104WB** Polished Nickel  
 Size: 18-1/2" W., 5-5/8" ht.  
 Extends 7". H/CTR 2-3/4".  
 Lamps: Two E12 base krypton lamps, each 60w max., included.

**THREE-LIGHT BATH**  
**P3077-104WB** Polished Nickel  
 Size: 26-1/2" W., 5-5/8" ht.  
 Extends 7". H/CTR 2-3/4".  
 Lamps: Three E12 base krypton lamps, each 60w max., included.

**FOUR-LIGHT BATH**  
**P3078-104WB** Polished Nickel  
 Size: 34-1/2" W., 5-5/8" ht.  
 Extends 7". H/CTR 2-3/4".  
 Lamps: Four E12 base krypton lamps, each 60w max., included.



P7046-104WB



P3076-104WB



P3077-104WB



P3078-104WB

Chandelier  
 pg 22



Close-to-ceiling  
 pg 302



\* P7807-01 replacement lamp recommended.

ELEGANT OVAL SHAPED, ETCHED  
OPAL GLASS SHADES, ACCENTED  
WITH CLEAR GLASS DISCS ON A  
POLISHED NICKEL FINISH.

# NISSÉ



#### ONE-LIGHT BATH

**P2012-104** Polished Nickel  
Size: 5-1/4" W., 9" ht.  
Extends 5-1/4", H/CTR 6-5/8".  
Lamp: One medium base  
lamp, 100w max.

#### TWO-LIGHT BATH

**P2013-104** Polished Nickel  
Size: 14-5/8" W., 9" ht.  
Extends 5-1/4", H/CTR 6-5/8".  
Lamps: Two medium base  
lamps, each 100w max.

#### THREE-LIGHT BATH

**P2014-104** Polished Nickel  
Size: 24" W., 9" ht.  
Extends 5-1/4", H/CTR 6-5/8".  
Lamps: Three medium base  
lamps, each 100w max.

#### FOUR-LIGHT BATH

**P2015-104** Polished Nickel  
Size: 33-1/2" W., 9" ht.  
Extends 5-1/4", H/CTR 6-5/8".  
Lamps: Four medium base  
lamps, each 100w max.



P2013-104



P2014-104

Shown: P2012-104 bath bracket



P2015-104



P2012-104

Close-to-ceiling

pg 302



Mini-pendant

pg 262



YOUR BATH AND VANITY AREA CAN SHINE WITH HOLLYWOOD GLAMOUR AND ROXBURY'S SLEEK FORMS. CLASSIC SILVER FINISH AND CLEAR CRYSTAL GLASS SHADES AND ACCENTS.

# ROXBURY



**ONE-LIGHT BATH**  
**P2724-101** Classic Silver  
Size: 7" W., 8-7/8" ht.  
Extends 8".  
Lamp: One medium base lamp, 100w max.



P2724-101

**TWO-LIGHT BATH**  
**P2726-101** Classic Silver  
Size: 16-1/2" W., 8-5/8" ht.  
Extends 7-3/4".  
Lamps: Two medium base lamps, each 100w max.



P2726-101

**THREE-LIGHT BATH**  
**P2727-101** Classic Silver  
Size: 26" W., 8-5/8" ht.  
Extends 7-3/4".  
Lamps: Three medium base lamps, each 100w max.

**FOUR-LIGHT BATH**  
**P2728-101** Classic Silver  
Size: 35-1/2" W., 8-5/8" ht.  
Extends 7-3/4".  
Lamps: Four medium base lamps, each 100w max.



P2728-101

Chandelier

pg 34



Close-to-ceiling

pg 303



P2727-101

CLEAR, BEAUTIFUL SOLID K-9 GLASS SPHERES ACCENT THE ETCHED OPAL GLASS SHADES IN A POLISHED NICKEL FINISH.

# FORTUNE



Shown: P2920-104 bath brackets

## ONE-LIGHT BATH

**P7049-104WB** Polished Nickel  
Size: 5-7/8" W., 8-3/4" ht.  
Extends 7-3/4". H/CTR 4-5/8".  
Lamp: One krypton lamp, 60w max., included.

## TWO-LIGHT BATH

**P2920-104WB** Polished Nickel  
Size: 15" W., 7-3/8" ht.  
Extends 7-7/8". H/CTR 4".  
Lamps: Two krypton lamps, each 60w max., included.

## THREE-LIGHT BATH

**P2927-104WB** Polished Nickel  
Size: 23-1/2" W., 9" ht.  
Extends 7-3/4". H/CTR 4".  
Lamps: Three krypton lamps, each 60w max., included.



Close-to-ceiling

P304



Chandelier

pg 46





# Ashbury

TRADITIONAL STYLE WITH A MODERN TWIST. CURVING DETAILS HIGHLIGHTED BY SILVER RIDGE FINISH. UNIQUE DOUBLE DRUM GLASS SHADES WITH LINEN FINISH.

**ONE-LIGHT BATH**  
**P2885-134WB** Silver Ridge  
 Size: 6" W., 9" ht.  
 Extends 8". H/CTR 5-1/2".  
 Lamp: One candelabra base krypton lamp, 60w max., included.



P2885-134WB

**TWO-LIGHT BATH**  
**P2886-134WB** Silver Ridge  
 Size: 16" W., 9" ht.  
 Extends 8". H/CTR 5-1/2".  
 Lamps: Two candelabra base krypton lamps, each 60w max., included.



P2886-134WB

**THREE-LIGHT BATH**  
**P2887-134WB** Silver Ridge  
 Size: 23-1/2" W., 9" ht.  
 Extends 8". H/CTR 5-1/2".  
 Lamps: Three candelabra base krypton lamps, each 60w max., included.



P2887-134WB

**FOUR-LIGHT BATH**  
**P2888-134WB** Silver Ridge  
 Size: 31" W., 9" ht.  
 Extends 8". H/CTR 5-1/2".  
 Lamps: Four candelabra base krypton lamps, each 60w max., included.



P2888-134WB

Chandelier  
 pg 70



Close-to-ceiling  
 pg 307



# Compass

FIND YOUR FRAME OF REFERENCE WITH THE COMPASS COLLECTION. LINEAR DETAILS AND CIRCULAR K9 GLASS ACCENTS, WITH ETCHED WHITE GLASS SHADES COMPLETE THE FIXTURE.



## ONE-LIGHT BATH

**P2046-20** Antique Bronze  
Size: 4-1/2" W., 11-5/8" ht. Extends 6". H/CTR 7-5/8".  
Lamp: One medium base lamp, 100w max.

## TWO-LIGHT BATH

**P2047-20** Antique Bronze  
Size: 16" W., 9-3/8" ht. Extends 6-1/4". H/CTR 5-5/8".  
Lamps: Two medium base lamps, each 100w max.

## THREE-LIGHT BATH

**P2048-20** Antique Bronze  
Size: 24" W., 9-3/8" ht. Extends 6-1/4". H/CTR 5-5/8".  
Lamps: Three medium base lamps, each 100w max.

## FOUR-LIGHT BATH

**P2049-20** Antique Bronze  
Size: 32" W., 9-3/8" ht. Extends 6-1/4". H/CTR 5-5/8".  
Lamps: Four medium base lamps, each 100w max.



P2049-20

Close-to-ceiling

pg 321



Chandelier

pg 66



All fixtures on these pages mount up or down.

INDULGE FEATURES CLEAR GLASS SHADES WITH ETCHED DETAILING ON THE INSIDE OF THE GLASS. A SINOUS ANTIQUE BRONZE FINISHED FRAME HIGHLIGHTS CLEAR BOBECHEs AND FINIALS.

# INDULGE



**ONE-LIGHT BATH**  
**P3101-20** Antique Bronze  
 Size: 5" W., 8-3/8" ht. Extends 7-3/8". H/CTR 5-3/4".  
 Lamp: One medium base lamp, 100w max.



P3102-20

**TWO-LIGHT BATH**  
**P3102-20** Antique Bronze  
 Size: 14-5/8" W., 8-3/8" ht. Extends 6-1/2". H/CTR 5-3/8".  
 Lamps: Two medium base lamps, each 60w max.

**THREE-LIGHT BATH**  
**P3103-20** Antique Bronze  
 Size: 24-1/4" W., 8-3/8" ht. Extends 6-1/2". H/CTR 5-3/8".  
 Lamps: Three medium base lamps, each 60w max.



P3105-20

**FOUR-LIGHT BATH**  
**P3104-20** Antique Bronze  
 Size: 33-7/8" W., 8-3/8" ht. Extends 6-1/2". H/CTR 5-3/8".  
 Lamps: Four medium base lamps, each 60w max.



P3104-20

**FIVE-LIGHT BATH**  
**P3105-20** Antique Bronze  
 Size: 43-1/2" W., 8-3/8" ht. Extends 6-1/2". H/CTR 5-3/8".  
 Lamps: Five medium base lamps, each 60w max.

Chandelier  
 pg 48



Close-to-ceiling  
 pg 304



# Draper

POLISHED DETAILING AND TUBULAR FORMS CONTRIBUTE TO THE SIMPLE MID-CENTURY DESIGN.

## ONE-LIGHT BATH

**P2101-20** Antique Bronze with Natural Brass accents

**P2101-104** Polished Nickel

Size: 4-1/2" W., 8" ht. Extends 4-1/8". H/CTR 4".

Lamp: One candelabra base lamp, 60w max.



P2101-20



P2101-104

## FOUR-LIGHT BATH

**P2102-20** Antique Bronze with Natural Brass accents

**P2102-104** Polished Nickel

Size: 24" W., 5-1/8" ht. Extends 4-1/8". H/CTR 2-1/4".

Lamps: Four candelabra base lamps, each 60w max.



P2102-20



P2102-104

*All fixtures on these pages mount up or down.*

# Lucky

LUCKY'S DISTINCTIVE DESIGN EVOKES A VINTAGE FLAIR WITH FINELY CRAFTED DETAILS. LIGHT IS BEAUTIFULLY ILLUMINATED THROUGH DOUBLE PRISMATIC FROSTED GLASS SHADES.



P2115-09



P2115-15



P2117-09



P2116-09



P2116-15

## ONE-LIGHT BATH

**P2115-09** Brushed Nickel  
**P2115-15** Polished Chrome  
 Size: 5" W., 8" ht. Extends 6-5/8". H/CTR 4".  
 Lamp: One medium base lamp, 100w max.

## TWO-LIGHT BATH

**P2116-09** Brushed Nickel  
**P2116-15** Polished Chrome  
 Size: 14-1/2" W., 7-5/8" ht. Extends 6-5/8". H/CTR 3-7/8".  
 Lamps: Two medium base lamps, each 100w max.

## THREE-LIGHT BATH

**P2117-09** Brushed Nickel  
**P2117-15** Polished Chrome  
 Size: 24" W., 7-5/8" ht. Extends 6-5/8". H/CTR 3-7/8".  
 Lamps: Three medium base lamps, each 100w max.

## FOUR-LIGHT BATH

**P2118-09** Brushed Nickel  
**P2118-15** Polished Chrome  
 Size: 33-5/8" W., 7-5/8" ht. Extends 6-5/8". H/CTR 3-7/8".  
 Lamps: Four medium base lamps, each 100w max.



P2118-09



P2118-15

A WELCOMED BLAST FROM THE PAST  
RETURNING A DESIGN GROUNDED IN  
AESTHETIC AUTHENTICITY. FINELY CRAFTED  
STRAP AND KNOB DETAILS WITH CLEAR DOUBLE  
PRISMATIC GLASS.

# Archie



## ONE-LIGHT BATH

**P2989-15** Polished Chrome  
**P2989-74** Venetian Bronze  
**P2989-81** Antique Nickel  
Size: 5-3/4" W., 8-1/4" ht.  
Extends 7". H/CTR 5-1/4".  
Lamp: One medium base  
lamp, 100w max.

## TWO-LIGHT BATH

**P2991-15** Polished Chrome  
**P2991-74** Venetian Bronze  
**P2991-81** Antique Nickel  
Size: 17" W., 8-3/4" ht.  
Extends 7". H/CTR 5-1/4".  
Lamps: Two medium base  
lamps, each 100w max.



P2991-15



P2991-74



P2991-81



P2989-74



P2989-15



P2989-81

Chandelier  
pg 154



Close-to-ceiling  
pg 316



All fixtures on these pages mount up or down.



P2992-81



P2992-15

**THREE-LIGHT BATH**

**P2992-15** Polished Chrome  
**P2992-74** Venetian Bronze  
**P2992-81** Antique Nickel  
Size: 26-1/4" W., 8-3/4" ht.  
Extends 7". H/CTR 5-1/4".  
Lamps: Three medium base lamps, each 100w max.



P2992-74

**FOUR-LIGHT BATH**

**P2997-15** Polished Chrome  
**P2997-74** Venetian Bronze  
**P2997-81** Antique Nickel  
Size: 35-1/2" W., 8-3/4" ht.  
Extends 7". H/CTR 5-1/4".  
Lamps: Four medium base lamps, each 100w max.



P2997-74



P2997-81



P2997-15

# Revive

OFFERS A FUN TWIST ON TRADITIONAL STYLING. ETCHED FLUTED GLASS COMPLEMENTS ELEGANTLY EXAGGERATED ARM SHAPE.

## ONE-LIGHT BATH

**P2074-09** Brushed Nickel  
**P2074-20** Antique Bronze  
 Size: 4-3/8" W., 9-1/4" ht.  
 Extends 7-1/2". H/CTR 5-3/8".  
 Lamp: One medium base lamp, 100w max.



P2074-20

P2074-09

## TWO-LIGHT BATH

**P2075-09** Brushed Nickel  
**P2075-20** Antique Bronze  
 Size: 13-3/8" W., 10-1/8" ht.  
 Extends 7-7/8". H/CTR 7-5/8".  
 Lamps: Two medium base lamps, each 100w max.



P2075-09



P2075-20



P2076-20

## THREE-LIGHT BATH

**P2076-09** Brushed Nickel  
**P2076-20** Antique Bronze  
 Size: 20-7/8" W., 10-1/8" ht.  
 Extends 7-7/8". H/CTR 7-5/8".  
 Lamps: Three medium base lamps, each 100w max.

## FOUR-LIGHT BATH

**P2077-09** Brushed Nickel  
**P2077-20** Antique Bronze  
 Size: 28-1/4" W., 10-1/8" ht.  
 Extends 7-7/8". H/CTR 7-5/8".  
 Lamps: Four medium base lamps, each 100w max.



P2076-09



P2077-20



P2077-09

Chandelier  
 pg 150



All fixtures on these pages mount up or down.



# Renovations

FLOWING ARMS AND CYLINDRICAL ACCENTS FORM TO CREATE AN UNCLUTTERED VICTORIAN DESIGN. ETCHED RIBBED GLASS OFFERS A HINT OF DETAIL TO COMPLETE THE VINTAGE FEEL.



**ONE-LIGHT BATH**  
**P3016-77** Forged Bronze  
**P3016-81** Antique Nickel  
 Size: 6" W., 9" ht.  
 Extends 8".  
 Lamp: One medium base lamp, 100w max.

**TWO-LIGHT BATH**  
**P2730-77** Forged Bronze  
**P2730-81** Antique Nickel  
 Size: 14" W., 8-1/4" ht.  
 Extends 8-1/8".  
 Lamps: Two medium base lamps, each 100w max.

**THREE-LIGHT BATH**  
**P2731-77** Forged Bronze  
**P2731-81** Antique Nickel  
 Size: 24-1/2" W., 8-1/2" ht.  
 Extends 7-1/4".  
 Lamps: Three medium base lamps, each 100w max.

**FOUR-LIGHT BATH**  
**P2732-77** Forged Bronze  
**P2732-81** Antique Nickel  
 Size: 32-1/2" W., 8-1/2" ht.  
 Extends 7-1/4".  
 Lamps: Four medium base lamps, each 100w max.

Chandelier  
 pg 146



Close-to-ceiling  
 pg 315



P3016-81

P3016-77

P2730-81

P2731-77

P2730-77

P2731-81



P2732-77



P2732-81



P3027-74



P3027-09



P3027-15



Shown: P3027-09 bath brackets

Close-to-ceiling

pg 315



All fixtures on these pages mount up or down.

[progresslighting.com](http://progresslighting.com)

# Victorian

VERSATILE VICTORIAN  
FIXTURES FEATURE A CLASSIC,  
TIMELESS ARCHITECTURE THAT  
COORDINATES WITH DELTA'S  
VICTORIAN FAUCET COLLECTION.  
WHITE OPAL GLASS.



## ONE-LIGHT BATH

**P3027-09** Brushed Nickel  
**P3027-15** Polished Chrome  
**P3027-74** Venetian Bronze  
Size: 5-5/8" W., 8-1/2" ht.  
Extends 7-1/4".  
Lamp: One medium base  
lamp, 100w max.

## TWO-LIGHT BATH

**P3028-09** Brushed Nickel  
**P3028-15** Polished Chrome  
**P3028-74** Venetian Bronze  
Size: 16-1/2" W., 8-1/2" ht.  
Extends 7-1/4".  
Lamps: Two medium base  
lamps, each 100w max.



## THREE-LIGHT BATH

**P3029-09** Brushed Nickel  
**P3029-15** Polished Chrome  
**P3029-74** Venetian Bronze  
Size: 24-1/2" W., 8-1/2" ht.  
Extends 7-1/4".  
Lamps: Three medium base  
lamps, each 100w max.



## FOUR-LIGHT BATH

**P3041-09** Brushed Nickel  
**P3041-15** Polished Chrome  
**P3041-74** Venetian Bronze  
Size: 32-1/2" W., 8-1/2" ht.  
Extends 7-1/4".  
Lamps: Four medium base  
lamps, each 100w max.



# Academy

A TRADITIONAL SCHOOL-HOUSE PROFILE IS UPDATED WITH LAYERED GLASS. POLISHED CHROME FINISH WITH CLEAR SEEDED OUTER GLASS SHADES AND ETCHED GLASS DIFFUSER. ANTIQUE BRONZE FINISH WITH LIGHT UMBER SEEDED GLASS SHADES AND ETCHED GLASS DIFFUSER.

## ONE-LIGHT BATH

**P2810-15WB** Polished Chrome

**P2810-20WB** Antique Bronze  
Size: 5-3/8" W., 8" ht. Extends 6-7/8". H/CTR 2-3/4".

Lamp: One G9 base halogen lamp, 35w max., included.

## TWO-LIGHT BATH

**P2811-15WB** Polished Chrome

**P2811-20WB** Antique Bronze  
Size: 13-7/8" W., 6-1/4" ht. Extends 6-7/8". H/CTR 2-3/4".

Lamps: Two G9 base halogen lamps, each 35w max., included.

## THREE-LIGHT BATH

**P2812-15WB** Polished Chrome

**P2812-20WB** Antique Bronze  
Size: 22" W., 6-1/4" ht. Extends 6-7/8". H/CTR 2-3/4".

Lamps: Three G9 base halogen lamps, each 35w max., included.

## FOUR-LIGHT BATH

**P2813-15WB** Polished Chrome

**P2813-20WB** Antique Bronze  
Size: 30-1/4" W., 6-1/4" ht. Extends 6-7/8". H/CTR 2-3/4".

Lamps: Four G9 base halogen lamps, each 35w max., included.



P2811-20WB



P2811-15WB



P2812-20WB



P2810-15WB



P2812-15WB



P2813-15WB



P2810-20WB



P2813-20WB

All fixtures on this page mount up or down.

# REIGN

CLEAR, TEXTURED, CURVED GLASS PANELS FLOAT IN FRONT OF CUSTOM ETCHED GLASS DIFFUSER.

# CLICHÉ

REFLECTIONS OF THE CLEAR, PILLOW-GLASS PATTERN CREATE THE ILLUSION OF A FULL CIRCLE OF FLOATING GLASS. GLASS ARCS FLOAT IN FRONT OF A CUSTOM ETCHED GLASS DIFFUSER.




P2852-20WB



P2823-15WB




P2845-20WB




P2824-15WB



P2842-20WB



P2844-20WB



P2825-15WB

## ONE-LIGHT BATH

**P2842-20WB** Antique Bronze  
Size: 7-1/2" W., 5-1/2" ht.  
Extends 4-3/4". H/CTR 2-3/4".  
Lamp: One G9 base halogen lamp, 35w max., included.

## TWO-LIGHT BATH


**P2844-20WB** Antique Bronze  
Size: 14-7/8" W., 5-1/2" ht.  
Extends 4-1/2". H/CTR 2-3/4".  
Lamps: Two G9 base halogen lamps, each 35w max., included.

## THREE-LIGHT BATH

**P2845-20WB** Antique Bronze  
Size: 22-1/4" W., 5-1/2" ht.  
Extends 4-1/2". H/CTR 2-3/4".  
Lamps: Three G9 base halogen lamps, each 35w max., included.

## FOUR-LIGHT BATH

**P2852-20WB** Antique Bronze  
Size: 29-3/4" W., 5-1/2" ht.  
Extends 4-1/2". H/CTR 2-3/4".  
Lamps: Four G9 base halogen lamps, each 35w max., included.



P2826-15WB

## ONE-LIGHT BATH

**P2823-15WB** Polished Chrome  
Size: 7-1/2" W., 5-1/2" ht.  
Extends 4-3/4". H/CTR 2-3/4".  
Lamp: One G9 base halogen lamp, 35w max., included.

## TWO-LIGHT BATH

**P2824-15WB** Polished Chrome  
Size: 14-7/8" W., 5-1/2" ht.  
Extends 4-3/4". H/CTR 2-3/4".  
Lamps: Two G9 base halogen lamps, each 35w max., included.

## THREE-LIGHT BATH

**P2825-15WB** Polished Chrome  
Size: 22-1/4" W., 5-1/2" ht.  
Extends 4-3/4". H/CTR 2-3/4".  
Lamps: Three G9 base halogen lamps, each 35w max., included.

## FOUR-LIGHT BATH

**P2826-15WB** Polished Chrome  
Size: 29-3/4" W., 5-1/2" ht.  
Extends 4-1/2". H/CTR 2-3/4".  
Lamps: Four G9 base halogen lamps, each 35w max., included.

# Santiago

THE SANTIAGO COLLECTION OFFERS SPIRALED DETAILING AND SUBTLE TWISTS. ROASTED JAVA OR FORGED BLACK FINISH WITH JASMINE MIST GLASS.



### ONE-LIGHT BATH

**P2752-80** Forged Black  
**P2752-102** Roasted Java  
Size: 6-3/8" W., 11" ht.  
Extends 7".  
Lamp: One medium base lamp, 100w max.

### TWO-LIGHT BATH

**P2753-80** Forged Black  
**P2753-102** Roasted Java  
Size: 14" W., 11" ht. Extends 7".  
Lamps: Two medium base lamps, each 100w max.

### THREE-LIGHT BATH

**P2754-80** Forged Black  
**P2754-102** Roasted Java  
Size: 21" W., 11" ht. Extends 7".  
Lamps: Three medium base lamps, each 100w max.



P2753-102



P2752-102



P2754-102



P2754-80



P2752-80



P2753-80

Chandelier

pg 96



Close-to-ceiling

pg 310



*Mounts in up position only.*

progresslighting.com

# Melbourne

A BLEND OF RICH GOLD HIGHLIGHTS AND DARK BROWN TONES CREATE THE MELBOURNE FAMILY. SCULPTED WATERMARK GLASS OFFERS WARM, ROMANTIC FEEL.

**ONE-LIGHT BATH**  
**P2918-84** Espresso  
 Size: 6-3/8" W., 11-1/2" ht.  
 Extends 9".  
 Lamp: One medium base lamp, 100w max.

**TWO-LIGHT BATH**  
**P3022-84** Espresso  
 Size: 24" W., 8-1/2" ht.  
 Extends 8".  
 Lamps: Two medium base lamps, each 100w max.

**THREE-LIGHT BATH**  
**P3023-84** Espresso  
 Size: 18" W., 8-1/2" ht.  
 Extends 8".  
 Lamps: Three medium base lamps, each 100w max.

**FOUR-LIGHT BATH**  
**P3024-84** Espresso  
 Size: 36" W., 8-1/2" ht.  
 Extends 8".  
 Lamps: Four medium base lamps, each 100w max.



P2918-84



P3022-84



P3023-84



P3024-84

Chandelier  
 pg 110



Close-to-ceiling  
 pg 312



All fixtures on this page mount up or down.

# Stroll

PEBBLES FINISH HIGHLIGHTS AN ARTFULLY SCROLLED FRAME WITH OPAL GLASS.

**ONE-LIGHT BATH**

**P2132-144** Pebbles  
Size: 5" W., 9-1/2" ht.  
Extends 7-1/2". H/CTR 5-3/4".  
Lamp: One medium base lamp, 100w max.

**TWO-LIGHT BATH**

**P2133-144** Pebbles  
Size: 13-7/8" W., 9-1/2" ht.  
Extends 7-1/2". H/CTR 5-3/4".  
Lamps: Two medium base lamps, each 100w max.

**THREE-LIGHT BATH**

**P2134-144** Pebbles  
Size: 23" W., 9-1/2" ht. Extends 7-1/2". H/CTR 5-3/4".  
Lamps: Three medium base lamps, each 100w max.



P2133-144



P2132-144



P2134-144

Chandelier

pg 84



Close-to-ceiling

pg 309



# BLISS

K9 BEADS COMPLIMENT AN ANTIQUE BRONZE FRAME AND FLUTED, CLEAR OPTIC GLASS SHADES. MOUNT UP ONLY.

**ONE-LIGHT BATH**

**P2139-20** Antique Bronze  
Size: 6-3/4" W., 13" ht. Extends 9-5/8". H/CTR 6-3/4".  
Lamp: One candelabra base lamp, 60w max.



P2139-20

**THREE-LIGHT BATH**

**P2141-20** Antique Bronze  
Size: 24" W., 10" ht. Extends 8". H/CTR 6-1/4".  
Lamps: Three candelabra base lamps, each 60w max.



P2141-20

Chandelier

pg 86



All fixtures on these pages mount up or down unless otherwise noted.



# Applause

APPLAUSE IS A FINE AND HANDSOME COLLECTION THAT FEATURES NATURAL PARCHMENT GLASS WHILE CONVEYING A FUN AND POSITIVE FEEL.



P2095-20

### ONE-LIGHT BATH

**P2095-20** Antique Bronze  
Size: 7" W., 9-1/8" ht.  
Extends 7-7/8". H/CTR 5-3/4".  
Lamp: One medium base lamp, 100w max.



P2096-20

### TWO-LIGHT BATH

**P2096-20** Antique Bronze  
Size: 16-1/4" W., 8-1/2" ht.  
Extends 9". H/CTR 5-5/8".  
Lamps: Two medium base lamps, each 100w max.

### THREE-LIGHT BATH

**P2097-20** Antique Bronze  
Size: 24" W., 8-1/2" ht.  
Extends 8-7/8". H/CTR 5-3/4".  
Lamps: Three medium base lamps, each 100w max.



P2097-20

Chandelier

pg 106



Close-to-ceiling

pg 309



# Legend



P2087-20



P2087-09



P2088-09



P2088-20

## ONE-LIGHT BATH

**P2087-09** Brushed Nickel

**P2087-20** Antique Bronze

Size: 7" W., 8-3/4" ht.

Extends 8". H/CTR 5-1/4".

Lamp: One medium base lamp, 100w max.

## TWO-LIGHT BATH

**P2088-09** Brushed Nickel

**P2088-20** Antique Bronze

Size: 16-1/8" W., 7-3/8" ht.

Extends 7-3/4". H/CTR 5-1/8".

Lamps: Two medium base lamps, each 100w max.



P2090-09

*All fixtures on these pages mount up or down.*

THE CRAFTSMANSHIP OF SCULPTED GLASS IN THIS STUNNING FIXTURE DEFINES THE LEGEND COLLECTION. SMOOTH AND POLISHED ON THE OUTSIDE, YET DISPLAYING A SUBTLE, NATURE-INSPIRED PATTERN ON THE INSIDE, THIS ELEGANT FIXTURE APPEARS TO COME ALIVE WHEN ILLUMINATED.



P2089-09



P2089-20

**THREE-LIGHT BATH**

**P2089-09** Brushed Nickel  
**P2089-20** Antique Bronze  
 Size: 25-1/4" W., 7-3/8" ht.  
 Extends 7-3/4". H/CTR 5-1/8".  
 Lamps: Three medium base lamps, each 100w max.

**FOUR-LIGHT BATH**

**P2090-09** Brushed Nickel  
**P2090-20** Antique Bronze  
 Size: 34-1/2" W., 7-3/8" ht.  
 Extends 7-3/4". H/CTR 5-1/8".  
 Lamps: Four medium base lamps, each 100w max.



P2090-20

Chandelier

pg 132



Close-to-ceiling

pg 313



RIVERSIDE OFFERS A CASUAL FEEL WITH MODERN SENSIBILITY. THE HEIRLOOM FINISH COMPLEMENTS THE LINEAR FORM AND WAVE PATTERNED GLASS WITH NATURAL UNDERTONES.

# Riverside



#### ONE-LIGHT BATH

**P3092-88** Heirloom  
Size: 4-3/4" W., 12-7/8" ht.  
Extends 7-1/8".  
Lamp: One medium base lamp, 100w max.

#### TWO-LIGHT BATH

**P3093-88** Heirloom  
Size: 13" W., 9-1/4" ht.  
Extends 7-1/4".  
Lamps: Two medium base lamps, each 100w max.

#### THREE-LIGHT BATH

**P3094-88** Heirloom  
Size: 21-1/2" W., 9-1/4" ht.  
Extends 7-1/4".  
Lamps: Three medium base lamps, each 100w max.

#### FOUR-LIGHT BATH

**P3095-88** Heirloom  
Size: 29-7/8" W., 9-1/4" ht.  
Extends 7-1/4".  
Lamps: Four medium base lamps, each 100w max.



P3092-88



P3093-88



P3094-88



P3095-88

#### Close-to-ceiling

pg 311



#### Chandelier

pg 116



All fixtures on this page mount up or down.

# Arts & Crafts

LINEAR, GEOMETRIC FORM IN WEATHERED BRONZE FINISH. LIGHT HONEY ART GLASS PANELS.



P3003-46



P3002-46  
P7138-46EB



P3004-46



P3005-46

**ONE-LIGHT BATH \***  
**P3002-46** Weathered Bronze  
Size: 14-1/4" W., 5" ht. Extends 4".  
Lamp: One medium base lamp, 100w max.  
ADA

**THREE-LIGHT BATH**  
**P3003-46** Weathered Bronze  
Size: 28-1/2" W., 5" ht. Extends 4".  
Lamps: Three medium base lamps, each 100w max.  
ADA

**FIVE-LIGHT BATH**  
**P3004-46** Weathered Bronze  
Size: 40-1/2" W., 5" ht. Extends 4".  
Lamps: Five medium base lamps, each 100w max.  
ADA

**SIX-LIGHT BATH**  
**P3005-46** Weathered Bronze  
Size: 52-1/2" W., 5" ht. Extends 4".  
Lamps: Six medium base lamps, each 100w max.  
ADA

**ONE-LIGHT CFL BATH \***  
**P7138-46EB** Weathered Bronze  
Size: 14-1/4" W., 5" ht. Extends 4".  
Lamp: One 26w GU24 CFL lamp.  
ADA



\* Can be installed horizontally or vertically.  
Light honey art glass on all sides.

All fixtures other than one-light have etched glass on bottom and are open at the top.

These fixtures are wall mount only.

progresslighting.com

Close-to-ceiling

pg 310



Chandelier

pg 114



LE JARDIN IS A DRAMATIC BLEND OF TRADITIONAL CRAFTSMANSHIP AND STYLING. FORGED IRON ARMS WITH SWEEPING DETAIL SUPPORT WEATHERED SANDSTONE GLASS.

# Le Jardin



#### ONE-LIGHT BATH

**P3012-84** Espresso  
Size: 7" W., 11-1/2" ht.  
Extends 9-1/2".  
Lamp: One medium base lamp, 100w max.



P3012-84

#### TWO-LIGHT BATH

**P2967-84** Espresso  
Size: 16-7/8" W., 10" ht.  
Extends 8-7/8".  
Lamps: Two medium base lamps, each 100w max.



P2967-84

#### THREE-LIGHT BATH

**P2968-84** Espresso  
Size: 24-5/8" W., 10" ht.  
Extends 8-7/8".  
Lamps: Three medium base lamps, each 100w max.



P2968-84

#### FOUR-LIGHT BATH

**P2969-84** Espresso  
Size: 33-3/4" W., 10" ht.  
Extends 8-7/8".  
Lamps: Four medium base lamps, each 100w max.



P2969-84

Chandelier

pg 104



Close-to-ceiling

pg 311



# Torino

ELEGANT RECTANGULAR SCROLLED ARMS WITH CASUAL UNDERTONES. FORGED BRONZE WITH TEA STAINED GLASS OR BRUSHED NICKEL WITH ETCHED GLASS.



P2881-77



P2881-09

**ONE-LIGHT BATH**  
**P2881-09** Brushed Nickel  
**P2881-77** Forged Bronze  
 Size: 7" W., 8-1/4" ht.  
 Extends 9-1/4".  
 Lamp: One medium base lamp, 100w max.



P2882-77



P2882-09

**TWO-LIGHT BATH**  
**P2882-09** Brushed Nickel  
**P2882-77** Forged Bronze  
 Size: 16" W., 7-5/8" ht.  
 Extends 9-1/4".  
 Lamps: Two medium base lamps, each 100w max.



P2883-09

**THREE-LIGHT BATH**  
**P2883-09** Brushed Nickel  
**P2883-77** Forged Bronze  
 Size: 25" W., 7-5/8" ht.  
 Extends 9-1/4".  
 Lamps: Three medium base lamps, each 100w max.



P2884-09

**FOUR-LIGHT BATH**  
**P2884-09** Brushed Nickel  
**P2884-77** Forged Bronze  
 Size: 34" W., 7-5/8" ht.  
 Extends 9-1/4".  
 Lamps: Four medium base lamps, each 100w max.



P2883-77

Chandelier  
 pg 128



Close-to-ceiling  
 pg 314



P2884-77

# Cantata

## ONE-LIGHT BATH

**P3216-09** Brushed Nickel

**P3216-77** Forged Bronze

Size: 4-3/4" W., 12-7/8" ht.  
Extends 7-1/8".

Lamp: One medium base lamp, 100w max.



P3216-77



P3216-09

## TWO-LIGHT BATH

**P3222-09** Brushed Nickel

**P3222-77** Forged Bronze

Size: 13" W., 9-1/4" ht.  
Extends 7-1/4".

Lamps: Two medium base lamps, each 100w max.



P3222-09



P3222-77

## FOUR-LIGHT BATH

**P3249-09** Brushed Nickel

**P3249-77** Forged Bronze

Size: 29-7/8" W., 9-1/4" ht.  
Extends 7-1/4".

Lamps: Four medium base lamps, each 100w max.



P3248-09

*All fixtures on these pages mount up or down.*



MODERN RUSTIC STYLING FINISHED IN FORGED BRONZE WITH SEEDED TOPAZ GLASS OR BRUSHED NICKEL WITH ETCHED WHITE GLASS OFFERS A WARM, ILLUMINATED GLOW.



P3248-77



P3249-09



P3249-77

Close-to-ceiling

pg 312



Chandelier

pg 140



# Kensington



## ONE-LIGHT BATH

**P2783-09** Brushed Nickel  
**P2783-77** Forged Bronze  
Size: 6" W., 9-1/2" ht.  
Extends 7".  
Lamp: One medium base lamp, 100w max.

## TWO-LIGHT BATH

**P2784-09** Brushed Nickel  
**P2784-77** Forged Bronze  
Size: 15" W., 9-1/2" ht.  
Extends 7-5/8".  
Lamps: Two medium base lamps, each 100w max.



P2783-77



P2783-09



P2784-09



P2784-77

Chandelier

pg 120



406

Close-to-ceiling

pg 313



All fixtures on these pages mount up or down.

progresslighting.com

KENSINGTON FEATURES SCROLLED ARMS WITH TRUMPET-SHAPED GLASS SHADES. FROSTED CARAMEL SHADES IN FORGED BRONZE FINISH AND ETCHED WHITE GLASS SHADES IN BRUSHED NICKEL.



P2786-77

**THREE-LIGHT BATH**

**P2785-09** Brushed Nickel  
**P2785-77** Forged Bronze  
Size: 24-1/8" W., 9-1/2" ht.  
Extends 7-5/8".  
Lamps: Three medium base lamps, each 100w max.

**FOUR-LIGHT BATH**

**P2786-09** Brushed Nickel  
**P2786-77** Forged Bronze  
Size: 33" W., 9-1/2" ht.  
Extends 7-5/8".  
Lamps: Four medium base lamps, each 100w max.



P2786-09



P2785-77



P2785-09

*Insite*



**TWO-LIGHT BATH**

**P2078-09** Brushed Nickel

**P2078-20** Antique Bronze

Size: 14-1/2" W., 7-3/8" ht.  
Extends 7-1/2". H/CTR 4-7/8".

Lamps: Two medium base lamps, each 100w max.

**THREE-LIGHT BATH**

**P2079-09** Brushed Nickel

**P2079-20** Antique Bronze

Size: 23-1/2" W., 7-3/8" ht.  
Extends 7-1/2". H/CTR 4-7/8".

Lamps: Three medium base lamps, each 100w max.



P2078-09



P2078-20



P2079-09




P2079-20



P2081-09

*All fixtures on these pages mount up or down.*

DUAL-LAYER ETCHED GLASS AND MYLAR DRUM SHADES ON A BRUSHED NICKEL OR ANTIQUE BRONZE FRAME.



P2041-09

P2041-20

**ONE-LIGHT BATH**

**P2041-09** Brushed Nickel  
**P2041-20** Antique Bronze  
 Size: 6-1/2" W., 11-1/2" ht.  
 Extends 8-1/4". H/CTR 3-3/4".  
 Lamp: One medium base lamp, 100w max.

**FOUR-LIGHT BATH**

**P2080-09** Brushed Nickel  
**P2080-20** Antique Bronze  
 Size: 32-1/2" W., 7-3/8" ht.  
 Extends 7-1/2". H/CTR 4-7/8".  
 Lamps: Four medium base lamps, each 100w max.

**FIVE-LIGHT BATH**

**P2081-09** Brushed Nickel  
**P2081-20** Antique Bronze  
 Size: 41-1/2" W., 7-3/8" ht. Extends 7-1/2". H/CTR 4-7/8".  
 Lamps: Five medium base lamps, each 100w max.



P2080-09



P2081-20

Chandelier  
pg 160



Close-to-ceiling  
pg 316



P2080-20

# Arch

## ONE-LIGHT BATH

**P2061-0930K9** Brushed Nickel  
Size: 7-1/4" W., 6" ht.  
Extends 3". H/CTR 3".  
Lamp: One integral 17w LED  
module included.  
ADA



P2062-0930K9



P2061-0930K9

## TWO-LIGHT BATH

**P2062-0930K9** Brushed Nickel  
Size: 14-1/2" W., 6" ht.  
Extends 3". H/CTR 3".  
Lamps: Two integral 17w LED  
modules included.  
ADA



P2063-0930K9

## THREE-LIGHT BATH

**P2063-0930K9** Brushed Nickel  
Size: 21-3/4" W., 6" ht.  
Extends 3". H/CTR 3".  
Lamps: Three integral 17w LED  
modules included.  
ADA



## LED FEATURES

- 120v AC, replaceable module
- 1211 lumens, 71.2 lumens/watt
- 3000K color temperature;  
90 CRI
- Dimmable to 10% brightness with  
ELV type dimmers
- ENERGY STAR and Title 24  
Compliant (designated models)

## FOUR-LIGHT BATH

**P2064-0930K9** Brushed Nickel  
Size: 29" W., 6" ht. Extends 3".  
H/CTR 3".  
Lamps: Four integral 17w LED  
modules included.  
ADA



P2064-0930K9

ARCH LED IS AN INNOVATIVE SERIES OF ACRYLIC LED WALL SCONCES THAT OPTIMIZES AESTHETIC APPEAL. SCREEN-PRINTED LENS ACCESSORIES – IN FABRIC LINEN OR NATURE-INSPIRED PATTERNS – CAN BE INSERTED INTO THE FIXTURES FOR A UNIQUE EFFECT. A PERFORATED METAL MESH END CAP DIFFUSES LIGHT ABOVE AND BELOW THE FIXTURE TO PROVIDE EVEN ILLUMINATION.



P2061-0930K9  
Shown with P8932-01 shade

ACCESSORY SHADE

**P8932-01** Fabric linen screen print  
Size: 6-7/8" W., 6" ht.  
Extends 2-1/4".

ACCESSORY SHADE


**P8934-01** Scroll screen print  
Size: 6-7/8" W., 6" ht.  
Extends 2-1/4".



P2062-0930K9  
Shown with P8932-01 shades



P2061-0930K9  
Shown with P8934-01 shade



P2063-0930K9  
Shown with P8932-01 shades



P2062-0930K9  
Shown with P8934-01 shades



P2064-0930K9  
Shown with P8934-01 shades

SOFT ACRYLIC LENS AND A BRUSHED NICKEL FINISH ARE HIGHLIGHTS OF THESE ENERGY STAR FIXTURES. FIXTURES CAN BE WALL OR CEILING MOUNTED. CAN BE INSTALLED VERTICALLY OR HORIZONTALLY.


# BALANCE

## ONE-LIGHT BATH

**P2091-0930K9** Brushed Nickel  
Size: 6" W., 5" ht.  
Extends 3". H/CTR 2-1/2".  
Lamp: One integral 9w LED module included.




P2091-0930K9



P2093-0930K9

## TWO-LIGHT BATH

**P2092-0930K9** Brushed Nickel  
Size: 11-1/2" W., 5" ht.  
Extends 3". H/CTR 2-1/2".  
Lamps: Two integral 9w LED modules included.



P2094-0930K9

## THREE-LIGHT BATH

**P2093-0930K9** Brushed Nickel  
Size: 16-3/4" W., 5" ht.  
Extends 3". H/CTR 2-1/2".  
Lamps: Three integral 9w LED modules included.



P2092-0930K9



P2093-0930K9



P2094-0930K9

## FOUR-LIGHT BATH

**P2094-0930K9** Brushed Nickel  
Size: 22" W., 5" ht. Extends 3".  
H/CTR 2-1/2".  
Lamps: Four integral 9w LED modules included.



## LED FEATURES

- 120v AC, replaceable module
- 623 lumens, 69.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% brightness with ELV type dimmers
- ENERGY STAR and Title 24 Compliant (designated models)





# HELIUM

SLEEK, FINELY RIBBED ETCHED GLASS SHADES WITH METAL STUDS SUPPORT THIS HEAVENLY STRUCTURE. CAN BE INSTALLED VERTICALLY OR HORIZONTALLY.



*Shown: P2901-09*

**TWO-LIGHT BATH**  
**P2901-09** Brushed Nickel  
 Size: 20" W., 6" ht.  
 Extends 5-3/8". H/CTR 3".  
 Lamps: Two medium base lamps, each 75w max.

**FOUR-LIGHT BATH**  
**P2905-09** Brushed Nickel  
 Size: 34" W., 6" ht.  
 Extends 5-7/8". H/CTR 3".  
 Lamps: Four medium base lamps, each 75w max.

Chandelier  
 pg 81



**P2901-09**  
*shown vertically*



**P2905-09**  
*shown vertically*




**P2905-09**  
*shown horizontally*



**P2901-09**  
*shown horizontally*

STREAMING OFFERS A CLEAN AND UNCLUTTERED DESIGN. FEATURES NO VISIBLE HARDWARE, CLEAR GLASS ETCHED INSIDE, AND A BRUSHED NICKEL FINISH. A PEEK OF LIGHT STREAMS THROUGH THE MINIMALIST FRAME.

# STREAMING



## ONE-LIGHT BATH

**P2123-09** Brushed Nickel  
Size: 6" W., 5" ht.  
Extends 5". H/CTR 2-1/2".  
Lamp: One krypton candelabra lamp, 60w max. \*



P2123-09

## TWO-LIGHT BATH


**P2124-09** Brushed Nickel  
Size: 14" W., 5" ht.  
Extends 4-3/4". H/CTR 2-1/2".  
Lamps: Two krypton candelabra lamps, each 60w max. \*



P2124-09

## THREE-LIGHT BATH

**P2125-09** Brushed Nickel  
Size: 22" W., 5" ht.  
Extends 4-3/4". H/CTR 2-1/2".  
Lamps: Three krypton candelabra lamps, each 60w max. \*



P2125-09

## FOUR-LIGHT BATH

**P2126-09** Brushed Nickel  
Size: 29-3/8" W., 5" ht.  
Extends 4-3/4". H/CTR 2-1/2".  
Lamps: Four krypton candelabra lamps, each 60w max. \*



P2126-09

\* P7807-01 lamps recommended

All fixtures on these pages mount up or down.

# SYNC

UPDATE YOUR BATH AND VANITY AREAS WITH A NEW COLLECTION THAT FEATURES SUPER CLEAR, POLISHED GLASS SHADES WITH LINEAR FORMS.



P2119-09



P2120-09



P2121-09

## ONE-LIGHT BATH

**P2119-09** Brushed Nickel  
 Size: 6" W., 5-3/4" ht.  
 Extends 6-1/8". H/CTR 2-1/2".  
 Lamp: One krypton E12 lamp, 60w max. \*

## TWO-LIGHT BATH

**P2120-09** Brushed Nickel  
 Size: 17" W., 5-3/4" ht.  
 Extends 6-1/8". H/CTR 2-1/2".  
 Lamps: Two krypton E12 lamps, each 60w max. \*

## THREE-LIGHT BATH

**P2121-09** Brushed Nickel  
 Size: 25" W., 5-3/4" ht.  
 Extends 6-1/8". H/CTR 2-1/2".  
 Lamps: Three krypton E12 lamps, each 60w max. \*

## FOUR-LIGHT BATH

**P2122-09** Brushed Nickel  
 Size: 33" W., 5-3/4" ht.  
 Extends 6-1/8". H/CTR 2-1/2".  
 Lamps: Four krypton E12 lamps, each 60w max. \*

\* P7807-01 lamps recommended



P2122-09

Rizu

CAST ANGULAR FIXTURES WITH WHITE GLASS SHADES. COORDINATES WITH DELTA'S RIZU FAUCET COLLECTION.



P2805-09

ONE-LIGHT BATH

P2805-09 Brushed Nickel

P2805-15 Polished Chrome

Size: 6" W., 7-1/4" ht.

Extends 6-3/4". H/CTR 3-3/4".

Lamp: One medium base lamp, 100w max.



P2805-15

TWO-LIGHT BATH

P2806-09 Brushed Nickel

P2806-15 Polished Chrome

Size: 13-1/2" W., 7-1/4" ht.

Extends 7". H/CTR 3-3/4".

Lamps: Two medium base lamps, each 100w max.



P2806-15



P2806-09

THREE-LIGHT BATH

P2807-09 Brushed Nickel

P2807-15 Polished Chrome

Size: 22-1/2" W., 7-1/4" ht.

Extends 7". H/CTR 3-3/4".

Lamps: Three medium base lamps, each 100w max.



P2807-15



P2807-09

FOUR-LIGHT BATH

P2808-09 Brushed Nickel

P2808-15 Polished Chrome

Size: 31-1/2" W., 7-1/4" ht.

Extends 7". H/CTR 3-3/4".

Lamps: Four medium base lamps, each 100w max.



P2808-15



All fixtures on these pages mount up or down.

progresslighting.com

# Syzyie

DELICATE CLASSIC CHROME FINISHED ARMS. ETCHED WHITE OPAL GLASS IN AN OVAL SHAPE FINISH THIS ELEGANT FIXTURE.

**ONE-LIGHT BATH**  
**P2801-15** Polished Chrome  
Size: 5-1/4" W., 10-3/8" ht.  
Extends 5-5/8".  
Lamp: One medium base lamp, 100w max.

**TWO-LIGHT BATH**  
**P2802-15** Polished Chrome  
Size: 14-1/2" W., 11-1/8" ht.  
Extends 5-5/8".  
Lamps: Two medium base lamps, each 100w max.

**THREE-LIGHT BATH**  
**P2803-15** Polished Chrome  
Size: 24" W., 11-1/8" ht.  
Extends 5-5/8".  
Lamps: Three medium base lamps, each 100w max.

**FOUR-LIGHT BATH**  
**P2804-15** Polished Chrome  
Size: 33-1/4" W., 11-1/8" ht.  
Extends 5-5/8".  
Lamps: Four medium base lamps, each 100w max.



P2802-15

P2801-15



P2803-15



P2804-15

# Engage

VANITY FIXTURES FEATURE A FUN GRAPHIC REPRESENTATION AND COORDINATE WITH POPULAR BATH ACCESSORIES AND PATTERNS. AVAILABLE IN BRUSHED NICKEL OR ANTIQUE BRONZE FINISHES WITH ETCHED WHITE GLASS.

## ONE-LIGHT BATH

**P2033-09** Brushed Nickel  
**P2033-20** Antique Bronze  
Size: 7" W., 7" ht.  
Extends 5-1/4". H/CTR 3-1/2".  
Lamp: One krypton E12 lamp, 60w max.



P2033-09



P2033-20

## TWO-LIGHT BATH

**P2034-09** Brushed Nickel  
**P2034-20** Antique Bronze  
Size: 15" W., 7" ht.  
Extends 5-1/4". H/CTR 3-1/2".  
Lamps: Two krypton E12 lamps, each 60w max.



P2034-09



P2034-20

## THREE-LIGHT BATH

**P2035-09** Brushed Nickel  
**P2035-20** Antique Bronze  
Size: 24-1/8" W., 7" ht.  
Extends 5-1/4". H/CTR 3-1/2".  
Lamps: Three krypton E12 lamps, each 60w max.



P2035-09

## FOUR-LIGHT BATH

**P2036-09** Brushed Nickel  
**P2036-20** Antique Bronze  
Size: 33-1/8" W., 7" ht.  
Extends 5-1/4". H/CTR 3-1/2".  
Lamps: Four krypton E12 lamps, each 60w max.



P2035-20



P2036-20



P2036-09

*All fixtures on these pages mount up or down.*

# Arise

ARISE GREET'S YOU WITH FLOWING LINES AND OVAL ETCHED OPAL GLASS SHADES. AVAILABLE IN POLISHED CHROME OR ANTIQUE BRONZE FINISHES.

**ONE-LIGHT BATH**  
**P2037-15WB** Polished Chrome  
**P2037-20WB** Antique Bronze  
 Size: 6" W., 8-1/2" ht.  
 Extends 4-7/8". H/CTR 4-1/4".  
 Lamp: One G9 base halogen lamp, 60w max., included.

**TWO-LIGHT BATH**  
**P2038-15WB** Polished Chrome  
**P2038-20WB** Antique Bronze  
 Size: 17" W., 5-1/2" ht. Extends 4-3/4". H/CTR 2-1/4".  
 Lamps: Two G9 base halogen lamps, each 60w max., included.

**THREE-LIGHT BATH**  
**P2039-15WB** Polished Chrome  
**P2039-20WB** Antique Bronze  
 Size: 26" W., 5-1/2" ht. Extends 4-3/4". H/CTR 2-1/4".  
 Lamps: Three G9 base halogen lamps, each 60w max., included.

**FOUR-LIGHT BATH**  
**P2040-15WB** Polished Chrome  
**P2040-20WB** Antique Bronze  
 Size: 35" W., 5-3/4" ht. Extends 4-3/4". H/CTR 2-1/4".  
 Lamps: Four G9 base halogen lamps, each 60w max., included.



# Calven

SCULPTED PROFILE WITH BOLD EXPRESSIVE CURVES. ETCHED OPAL GLASS SHADES WITH FORGED BLACK OR BRUSHED NICKEL ARMS CREATE AN URBAN FEEL.

## ONE-LIGHT BATH

**P3209-09WB** Brushed Nickel  
**P3209-80WB** Forged Black \*  
 Size: 6-3/8" W., 11-1/2" ht.  
 Extends 7-5/8". H/CTR 6".  
 Lamp: One G9 base halogen lamp, 60w max., included.



P3209-09WB

## TWO-LIGHT BATH

**P3210-09WB** Brushed Nickel  
**P3210-80WB** Forged Black  
 Size: 18" W., 6" ht. Extends 7-7/8". H/CTR 3".  
 Lamps: Two G9 base halogen lamps, each 60w max., included.



P3210-80WB




P3209-80WB\*

## THREE-LIGHT BATH

**P3223-09WB** Brushed Nickel  
**P3223-80WB** Forged Black  
 Size: 25" W., 6" ht. Extends 7-7/8". H/CTR 3".  
 Lamps: Three G9 base halogen lamps, each 60w max., included.



P3223-80WB



P3210-09WB



P3223-09WB

## FOUR-LIGHT BATH

**P3236-09WB** Brushed Nickel  
**P3236-80WB** Forged Black  
 Size: 34-3/8" W., 6-1/2" ht.  
 Extends 7-7/8". H/CTR 3".  
 Lamps: Four G9 base halogen lamps, each 60w max., included.



P3236-80WB



P3236-09WB

Close-to-ceiling

pg 319



Chandelier

pg 166



\*P3209-80WB comes with both fabric and glass shades

All fixtures on these pages mount up or down.



# Rave

RAVE DISPLAYS A CONTEMPORARY STYLE. IDEAL FOR BATH AND VANITY AREAS. A BRUSHED NICKEL FINISH HIGHLIGHTS THE FIXTURES' SOFT CURVES AND ETCHED OPAL GLASS SHADES.

**ONE-LIGHT BATH**  
**P2070-09** Brushed Nickel  
 Size: 7" W., 10-7/8" ht.  
 Extends 8-3/4". H/CTR 5-1/4".  
 Lamp: One krypton E12 lamp, 60w max.

**TWO-LIGHT BATH**  
**P2071-09** Brushed Nickel  
 Size: 16-3/8" W., 7-1/8" ht.  
 Extends 8-7/8". H/CTR 2-3/8".  
 Lamps: Two krypton E12 lamps, each 60w max.

**THREE-LIGHT BATH**  
**P2072-09** Brushed Nickel  
 Size: 26" W., 7-1/8" ht. Extends 8-3/4". H/CTR 2-3/8".  
 Lamps: Three krypton E12 lamps, each 60w max.

**FOUR-LIGHT BATH**  
**P2073-09** Brushed Nickel  
 Size: 35-1/8" W., 7-1/8" ht. Extends 8-3/4". H/CTR 2-3/8".  
 Lamps: Four krypton E12 lamps, each 60w max.



P2070-09



P2071-09



P2072-09



P2073-09

Close-to-ceiling

pg 319



Chandelier

pg 176



\*P7807-01 lamp recommended.

# Alexa

FEATURING A TRANSITIONAL DESIGN STYLE, THIS COLLECTION OFFERS THE BEST OF TRADITIONAL AND MODERN DETAILS. ETCHED LINEN AND CLEAR GLASS.



#### ONE-LIGHT BATH

**P2959-09** Brushed Nickel  
Size: 4-1/2" W., 9-1/4" ht.  
Extends 6-1/8".  
Lamp: One medium base lamp, 100w max.

#### TWO-LIGHT BATH

**P2977-09** Brushed Nickel  
Size: 13" W., 9-3/8" ht.  
Extends 6-1/8".  
Lamps: Two medium base lamps, each 100w max.

#### THREE-LIGHT BATH

**P2978-09** Brushed Nickel  
Size: 22" W., 9-3/8" ht.  
Extends 6-1/8".  
Lamps: Three medium base lamps, each 100w max.

#### FOUR-LIGHT BATH

**P2998-09** Brushed Nickel  
Size: 31" W., 9-1/2" ht.  
Extends 6-1/8".  
Lamps: Four medium base lamps, each 100w max.



P2977-09



P2959-09



P2978-09



P2998-09

Chandelier

pg 178



Close-to-ceiling

pg 320



All fixtures on these pages mount up or down.

# Wisten

SIMPLE, MODERN AND ELEGANT, THE WISTEN FAMILY FEATURES A SCULPTURED LINEAR LOOK. ETCHED GLASS FOR SOFT CONTEMPORARY FEEL.



P2794-20  
P2794-20EBWB



P2796-20  
P2796-20EBWB



P2795-20



P2794-09  
P2794-09EBWB



P2797-09



P2795-09

**ONE-LIGHT BATH**  
**P2794-09** Brushed Nickel  
**P2794-20** Antique Bronze  
 Size: 4-3/4" W., 8-1/4" ht.  
 Extends 6-1/4".  
 Lamp: One medium base lamp, 100w max.

**ONE-LIGHT CFL BATH**  
**P2794-09EBWB** Brushed Nickel  
**P2794-20EBWB** Antique Bronze  
 Size: 4-3/4" W., 8-1/4" ht.  
 Extends 6-1/4".  
 Lamp: One 13w GU24 CFL lamp included.



**TWO-LIGHT BATH**  
**P2795-09** Brushed Nickel  
**P2795-20** Antique Bronze  
 Size: 12-1/2" W., 8-1/4" ht.  
 Extends 6-1/4".  
 Lamps: Two medium base lamps, each 100w max.

**THREE-LIGHT BATH**  
**P2796-09** Brushed Nickel  
**P2796-20** Antique Bronze  
 Size: 21" W., 8-1/4" ht.  
 Extends 6-1/4".  
 Lamps: Three medium base lamps, each 100w max.

**THREE-LIGHT CFL BATH**  
**P2796-09EBWB** Brushed Nickel  
**P2796-20EBWB** Antique Bronze  
 Size: 21" W., 8-1/4" ht.  
 Extends 6-1/4".  
 Lamps: Three 13w GU24 CFL lamps included.



**FOUR-LIGHT BATH**  
**P2797-09** Brushed Nickel  
**P2797-20** Antique Bronze  
 Size: 29-1/2" W., 8-1/4" ht.  
 Extends 6-1/4".  
 Lamps: Four medium base lamps, each 100w max.



P2796-09  
P2796-09EBWB

Chandelier  
pg 170



Close-to-ceiling  
pg 319



# Orbitz

ENJOY THIS CLASSIC STYLE WHEN SURROUNDED BY THE ELEGANT DETAILS OF THE ORBITZ FAMILY. OPAL GLASS SHADES FLOAT ON A CIRCULAR FRAME.



**ONE-LIGHT BATH**  
**P3030-09** Brushed Nickel  
**P3030-20** Antique Bronze  
Size: 5-1/2" W., 7-1/4" ht.  
Extends 6". H/CTR 5".  
Lamp: One medium base lamp, 100w max.

**TWO-LIGHT BATH**  
**P3057-09** Brushed Nickel  
**P3057-20** Antique Bronze  
Size: 13" W., 7-1/4" ht.  
Extends 6". H/CTR 5".  
Lamps: Two medium base lamps, each 100w max.

**THREE-LIGHT BATH**  
**P3058-09** Brushed Nickel  
**P3058-20** Antique Bronze  
Size: 21-3/4" W., 7-1/4" ht.  
Extends 8-1/4". H/CTR 5".  
Lamps: Three medium base lamps, each 100w max.



P3030-20



P3030-09



P3057-20



P3058-09



P3057-09



P3058-20

Chandelier  
pg 162



Close-to-ceiling  
pg 317



# Bounty

RECTANGULAR SCALLOPED OPAL GLASS SITS UPON A PEDESTAL FRAME. AVAILABLE IN BRUSHED NICKEL OR ANTIQUE BRONZE FINISHES.



P2107-09



P2107-20



P2109-20



P2109-09



P2108-20



P2108-09

**ONE-LIGHT BATH**  
**P2107-09** Brushed Nickel  
**P2107-20** Antique Bronze  
 Size: 6-5/8" W., 6-3/4" ht.  
 Extends 6-1/4". H/CTR 3-3/8".  
 Lamp: One medium base lamp, 100w max.

**FOUR-LIGHT BATH**  
**P2110-09** Brushed Nickel  
**P2110-20** Antique Bronze  
 Size: 33-1/2" W., 7" ht.  
 Extends 6-3/8". H/CTR 4-5/8".  
 Lamps: Four medium base lamps, each 100w max.

**TWO-LIGHT BATH**  
**P2108-09** Brushed Nickel  
**P2108-20** Antique Bronze  
 Size: 15-5/8" W., 7" ht.  
 Extends 6-3/8". H/CTR 4-5/8".  
 Lamps: Two medium base lamps, each 100w max.

**THREE-LIGHT BATH**  
**P2109-09** Brushed Nickel  
**P2109-20** Antique Bronze  
 Size: 24-5/8" W., 7" ht.  
 Extends 6-3/8". H/CTR 4-5/8".  
 Lamps: Three medium base lamps, each 100w max.



P2110-20

# Sahara



P2758-09



P2758-74



P2758-15



## ONE-LIGHT BATH

**P2758-09** Brushed Nickel  
**P2758-15** Polished Chrome  
**P2758-74** Venetian Bronze  
Size: 5-7/8" W., 10-7/16" ht.  
Extends 7-1/2".  
Lamp: One medium base  
lamp, 100w max.

Close-to-ceiling  
pg 318



All fixtures on these pages mount up or down.

[progresslighting.com](http://progresslighting.com)

THIS TIMELESS DESIGN WORKS WITH A VARIETY OF BATH DECORS AND COORDINATES WITH DELTA'S POPULAR LAHARA FAUCET COLLECTION. ETCHED GLASS GIVES THIS SLEEK AND DRAMATIC DESIGN A SOFTENED EDGE.



Shown: P2758-09 one-light bath and P2760-09 three-light bath



P2759-09



P2759-74



P2759-15



P2760-74



P2760-09



P2760-15

**TWO-LIGHT BATH**

**P2759-09** Brushed Nickel  
**P2759-15** Polished Chrome  
**P2759-74** Venetian Bronze  
 Size: 15-5/8" W., 10-3/8" ht.  
 Extends 7-1/2".  
 Lamps: Two medium base lamps, each 100w max.

**THREE-LIGHT BATH**

**P2760-09** Brushed Nickel  
**P2760-15** Polished Chrome  
**P2760-74** Venetian Bronze  
 Size: 25-5/8" W., 10-3/8" ht.  
 Extends 7-1/2".  
 Lamps: Three medium base lamps, each 100w max.

# Addison



P2846-74



P2846-15



P2846-09



## ONE-LIGHT BATH

**P2846-09** Brushed Nickel  
**P2846-15** Polished Chrome  
**P2846-74** Venetian Bronze  
Size: 5-1/2" W., 9-3/8" ht.  
Extends 6-3/4".  
Lamp: One medium base  
lamp, 100w max.



Shown: P2846-74 one-light bath and P2847-74 two-light bath fixtures with Delta's Addison faucets.

Close-to-ceiling  
pg 318





INSPIRED BY THE SCALLOPED CUTS IN A SEASHELL. ADDISON FEATURES GRACEFUL, CURVED ARMS TOPPED WITH SCALLOPED GLASS SHADES WITH AN ETCHED FINISH. COORDINATES WITH DELTA'S ADDISON FAUCET COLLECTION.



P2847-15



P2847-09



P2847-74



P2848-74



P2848-09



P2848-15

**TWO-LIGHT BATH**

**P2847-09** Brushed Nickel  
**P2847-15** Polished Chrome  
**P2847-74** Venetian Bronze  
 Size: 15-7/8" W., 9" ht.  
 Extends 6-3/4".  
 Lamps: Two medium base lamps, each 100w max.

**THREE-LIGHT BATH**

**P2848-09** Brushed Nickel  
**P2848-15** Polished Chrome  
**P2848-74** Venetian Bronze  
 Size: 26" W., 9" ht.  
 Extends 6-3/4".  
 Lamps: Three medium base lamps, each 100w max.

# Glenmont



P3135-09



P3135-74



P3135-15



## ONE-LIGHT BATH

**P3135-09** Brushed Nickel  
**P3135-15** Polished Chrome  
**P3135-74** Venetian Bronze  
Size: 5-3/4" W., 8-3/4" ht.  
Extends 7-3/4".  
Lamp: One medium base  
lamp, 100w max.

Shown: P3135-74 one-light bath and P3137-74 three-light bath fixtures and Delta's Dryden faucets.

A CLEAN LINE WITH GEOMETRIC FORMS LENDS THE GLENMONT COLLECTION TO A VARIETY OF TODAY'S LIFESTYLES. COORDINATES WITH DELTA'S DRYDEN COLLECTION. ANGULAR ETCHED OPAL GLASS BLENDS WITH MINIMALIST DESIGN.



**TWO-LIGHT BATH**

**P3136-09** Brushed Nickel  
**P3136-15** Polished Chrome  
**P3136-74** Venetian Bronze  
 Size: 14-3/4" W., 8-3/4" ht.  
 Extends 7-3/4".  
 Lamps: Two medium base lamps, each 100w max.

**THREE-LIGHT BATH**

**P3137-09** Brushed Nickel  
**P3137-15** Polished Chrome  
**P3137-74** Venetian Bronze  
 Size: 21" W., 8-1/4" ht.  
 Extends 7-3/4".  
 Lamps: Three medium base lamps, each 100w max.



P3137-09



P3137-74

# North Park

CLEAN LINEAR FORMS OFFER A MODERN INTERPRETATION OF TWO BLENDED STYLES – CRAFTSMAN AND MISSION. SQUARE ETCHED GLASS SHADES GIVE NOD TO A CLASSIC FEEL.



### ONE-LIGHT BATH

**P2733-09** Brushed Nickel  
**P2733-74** Venetian Bronze  
Size: 5-1/2" W., 10-1/8" ht.  
Extends 7-1/8".  
Lamp: One medium base lamp, 100w max.

### TWO-LIGHT BATH

**P2738-09** Brushed Nickel  
**P2738-74** Venetian Bronze  
Size: 14-1/4" W., 9" ht.  
Extends 7-1/8".  
Lamps: Two medium base lamps, each 100w max.

### THREE-LIGHT BATH

**P2743-09** Brushed Nickel  
**P2743-74** Venetian Bronze  
Size: 23" W., 9" ht. Extends 7-1/8".  
Lamps: Three medium base lamps, each 100w max.



### FOUR-LIGHT BATH

**P2745-09** Brushed Nickel  
**P2745-74** Venetian Bronze  
Size: 32-1/8" W., 9" ht.  
Extends 7-1/8".  
Lamps: Four medium base lamps, each 100w max.



All fixtures on these pages mount up or down.

# Pavilion

THE PAVILION COLLECTION FEATURES PLAYFUL ACCENTS WITH FLOWING LINES – IDEAL FOR A VARIETY OF BATH AND VANITY AREAS. DOUBLE ARMS WITH CURLING ACCENTS. FINISHED IN BRUSHED NICKEL OR ANTIQUE BRONZE WITH ETCHED WATERMARK GLASS.



**ONE-LIGHT BATH**  
**P3265-09** Brushed Nickel  
**P3265-20** Antique Bronze  
 Size: 8-3/4" W., 9-1/4" ht.  
 Extends 10-1/8".  
 Lamp: One medium base lamp, 100w max.

**TWO-LIGHT BATH**  
**P3270-09** Brushed Nickel  
**P3270-20** Antique Bronze  
 Size: 20-5/8" W., 8-7/8" ht.  
 Extends 10-1/8".  
 Lamps: Two medium base lamps, each 100w max.

**THREE-LIGHT BATH**  
**P3294-09** Brushed Nickel  
**P3294-20** Antique Bronze  
 Size: 32-3/4" W., 8-7/8" ht.  
 Extends 10-1/8/8".  
 Lamps: Three medium base lamps, each 100w max.



P3294-09



P3294-20

Chandelier  
 pg 204



Close-to-ceiling  
 pg 321



# Fairfield

THE FAIRFIELD COLLECTION FEATURES SIMPLE, ELEGANT DETAILS. GENTLY SWEEPING ETCHED OPAL GLASS HIGHLIGHTED IN POLISHED CHROME OR BRUSHED NICKEL.



P3131-15



P3131-09



P3132-15



P3132-09



P3133-09

## ONE-LIGHT BATH

**P3131-09** Brushed Nickel  
**P3131-15** Polished Chrome  
Size: 5-3/4" W., 9-3/8" ht.  
Extends 6-3/4".  
Lamp: One medium base lamp, 100w max.

## FOUR-LIGHT BATH

**P3134-09** Brushed Nickel  
**P3134-15** Polished Chrome  
Size: 34-1/2" W., 9" ht.  
Extends 6-3/4".  
Lamps: Four medium base lamps, each 100w max.

## TWO-LIGHT BATH

**P3132-09** Brushed Nickel  
**P3132-15** Polished Chrome  
Size: 15-1/2" W., 9" ht.  
Extends 6-3/4".  
Lamps: Two medium base lamps, each 100w max.

## THREE-LIGHT BATH

**P3133-09** Brushed Nickel  
**P3133-15** Polished Chrome  
Size: 25" W., 9" ht.  
Extends 6-3/4".  
Lamps: Three medium base lamps, each 100w max.



P3133-15

All fixtures on these pages mount up or down.

Oasis

SIMPLE AND ELEGANT, THE OASIS VANITY COLLECTION CAN TURN ANY BATH AREA INTO A SPA-LIKE ENVIRONMENT. THE CHROME ARM AND BACK PLATE REFLECT BEVELED DETAILING PAIRED WITH SQUARE FLUTED GLASS SHADES.



P2111-15

**ONE-LIGHT BATH**

**P2111-15** Polished Chrome  
 Size: 5" W., 7-3/4" ht.  
 Extends 6-3/4". H/CTR 4-1/2".  
 Lamp: One medium base lamp,  
 100w max.



P2112-15

**TWO-LIGHT BATH**

**P2112-15** Polished Chrome  
 Size: 14-5/8" W., 7-3/4" ht.  
 Extends 6-3/4". H/CTR 5-1/2".  
 Lamps: Two medium base  
 lamps, 100w max.



P2113-15

**THREE-LIGHT BATH**

**P2113-15** Polished Chrome  
 Size: 24-1/8" W., 7-3/4" ht.  
 Extends 6-3/4". H/CTR 5-1/2".  
 Lamps: Three medium base  
 lamps, 100w max.

**FOUR-LIGHT BATH**

**P2114-15** Polished Chrome  
 Size: 33-3/4" W., 7-3/4" ht.  
 Extends 6-3/4". H/CTR 5-1/2".  
 Lamps: Four medium base  
 lamps, 100w max.



P2114-15

# JOY

ETCHED LIGHT UMBER GLASS PAIRED WITH AN ANTIQUE BRONZE FINISH OR ETCHED WHITE GLASS WITH A BRUSHED NICKEL FINISH COMPLEMENT THE FASHION FORWARD FRAME.



P2000-09



P2000-20



P2002-20



P2001-09



P2001-20



P2002-09



P2003-09



P2003-20

## ONE-LIGHT BATH

**P2000-09** Brushed Nickel  
**P2000-20** Antique Bronze  
 Size: 6" W., 9-1/2" ht.  
 Extends 7". H/CTR 6".  
 Lamp: One medium base lamp, 100w max.

## TWO-LIGHT BATH

**P2001-09** Brushed Nickel  
**P2001-20** Antique Bronze  
 Size: 14" W., 7-5/8" ht.  
 Extends 8-1/8". H/CTR 4-1/8".  
 Lamps: Two medium base lamps, each 100w max.

## THREE-LIGHT BATH

**P2002-09** Brushed Nickel  
**P2002-20** Antique Bronze  
 Size: 22" W., 7-5/8" ht.  
 Extends 8-1/8". H/CTR 4-1/8".  
 Lamps: Three medium base lamps, each 100w max.

## FOUR-LIGHT BATH

**P2003-09** Brushed Nickel  
**P2003-20** Antique Bronze  
 Size: 30" W., 7-5/8" ht.  
 Extends 8-1/8". H/CTR 4-1/8".  
 Lamps: Four medium base lamps, each 100w max.

Chandelier  
 pg 184





# Savannah<sup>®</sup>

FEATURING HOSPITABLE PINEAPPLE ACCENTS AND LUXURIOUS DETAILS, THE SAVANNAH COLLECTION EVOKES A TROPICAL FEEL FOR ANY BATH AND VANITY STYLE. ANTIQUE ALABASTER GLASS WITH ROUNDED FEATURES FOR SOFT FEEL.

**ONE-LIGHT BATH**  
**P3204-42** Seabrook  
**P3204-86** Burnished Chestnut  
 Size: 8-3/4" W., 9-1/4" ht.  
 Extends 9-1/4".  
 Lamp: One medium base lamp, 100w max.

**TWO-LIGHT BATH**  
**P3205-42** Seabrook  
**P3205-86** Burnished Chestnut  
 Size: 16-1/4" W., 9-1/8" ht.  
 Extends 9".  
 Lamps: Two medium base lamps, each 100w max.

**THREE-LIGHT BATH**  
**P3206-42** Seabrook  
**P3206-86** Burnished Chestnut  
 Size: 25-1/4" W., 9-1/8" ht.  
 Extends 9".  
 Lamps: Three medium base lamps, each 100w max.

**FOUR-LIGHT BATH**  
**P3207-42** Seabrook  
**P3207-86** Burnished Chestnut  
 Size: 34-1/4" W., 9-1/8" ht.  
 Extends 9".  
 Lamps: Four medium base lamps, each 100w max.



Close-to-ceiling  
pg 324

Chandelier  
pg 212

# Spirit



P2135-20



P2135-144



P2136-20



P2136-144



P2138-20

*All fixtures on these pages mount up or down.*

THE SPIRIT OF CRAFTSMANSHIP PREVAILS WITH SUBTLE FORMS. LIGHT UMBER ETCHED GLASS SHADES IN GALVANIZED METAL. PEBBLES OR ANTIQUE BRONZE FINISH.



P2137-20



P2137-144

**ONE-LIGHT BATH**

**P2135-20** Antique Bronze

**P2135-144** Pebbles

Size: 7-1/8" W., 10" ht. Extends 8-5/8". H/CTR 5".

Lamp: One medium base lamp, 100w max.

**TWO-LIGHT BATH**

**P2136-20** Antique Bronze

**P2136-144** Pebbles

Size: 17" W., 7-3/4" ht. Extends 8-1/4". H/CTR 5-1/4".

Lamps: Two medium base lamps, each 100w max.

**THREE-LIGHT BATH**

**P2137-20** Antique Bronze

**P2137-144** Pebbles

Size: 27-1/2" W., 7-3/4" ht. Extends 8-1/4". H/CTR 5-1/4".

Lamps: Three medium base lamps, each 100w max.

**FOUR-LIGHT BATH**

**P2138-20** Antique Bronze

**P2138-144** Pebbles

Size: 37-3/4" W., 7-3/4" ht. Extends 8-1/4". H/CTR 5-1/4".

Lamps: Four medium base lamps, each 100w max.



P2138-144

Close-to-ceiling

pg 323



Chandelier

pg 208



# Madison

## ONE-LIGHT BATH

**P3161-09** Brushed Nickel  
**P3161-15** Polished Chrome  
**P3161-20** Antique Bronze  
Size: 7-5/8" W, 8" ht.  
Extends 8-1/4".  
Lamp: One medium base lamp, 100w max.

## TWO-LIGHT BATH

**P3162-09** Brushed Nickel  
**P3162-15** Polished Chrome  
**P3162-20** Antique Bronze  
Size: 17-1/2" W, 8" ht.  
Extends 9".  
Lamps: Two medium base lamps, each 100w max.

## THREE-LIGHT BATH

**P3163-09** Brushed Nickel  
**P3163-15** Polished Chrome  
**P3163-20** Antique Bronze  
Size: 27-1/2" W, 8" ht.  
Extends 9".  
Lamps: Three medium base lamps, each 100w max.

## FOUR-LIGHT BATH

**P3164-09** Brushed Nickel  
**P3164-15** Polished Chrome  
**P3164-20** Antique Bronze  
Size: 37-1/2" W, 8" ht.  
Extends 9".  
Lamps: Four medium base lamps, each 100w max.



P3162-20



P3162-09



P3162-15



P3163-15



P3163-09



P3163-20

Chandelier  
pg 220




Close-to-ceiling  
pg 325



All fixtures on these pages mount up or down.

AUTHENTIC AND HANDSOME DETAILS  
REPRESENT A THROWBACK TO A SIMPLER TIME.  
ETCHED GLASS OFFERS RETRO STYLING.



# Trinity

**ONE-LIGHT BATH**

**P3190-09** Brushed Nickel

**P3190-15** Polished Chrome

**P3190-20** Antique Bronze

Size: 6-1/2" W., 7-1/2" ht.

Extends 9".

Lamp: One medium base lamp, 100w max.

**ONE-LIGHT CFL BATH**

**P3190-09EBWB** Brushed Nickel

**P3190-20EBWB** Antique Bronze

Size: 6-1/2" W., 7-1/2" ht.

Extends 9".

Lamp: One 13w GU24 CFL lamp, included.



**TWO-LIGHT BATH**

**P3191-09** Brushed Nickel

**P3191-15** Polished Chrome

**P3191-20** Antique Bronze

Size: 17-1/2" W., 8-1/8" ht.

Extends 7-1/2".

Lamps: Two medium base lamps, each 100w max.

**TWO-LIGHT CFL BATH**

**P3191-09EBWB** Brushed Nickel

**P3191-20EBWB** Antique Bronze

Size: 17-1/2" W., 8-1/8" ht.

Extends 7-1/2".

Lamps: Two 13w GU24 CFL lamps, included.



P3190-15



P3190-20  
P3190-20EBWB



P3190-09  
P3190-09EBWB



P3192-09  
P3192-09EBWB



P3191-15



P3191-09  
P3191-09EBWB



P3191-20  
P3191-20EBWB

**Chandelier**

pg 226



**Close-to-ceiling**

pg 326



All fixtures on these pages mount up or down.

SOFT ANGLES AND CURVED LINES IN THE TRINITY COLLECTION ARE IDEAL FOR TODAY'S UNDERSTATED INTERIORS. ETCHED GLASS SHADES THAT CURVE OUT CAN BE MOUNTED UPWARD OR DOWNWARD.



P3192-20  
P3192-20EBWB

P3192-15



P3193-15



P3193-20  
P3193-20EBWB



P3193-09  
P3193-09EBWB

#### THREE-LIGHT BATH

**P3192-09** Brushed Nickel  
**P3192-15** Polished Chrome  
**P3192-20** Antique Bronze  
 Size: 24" W., 8-1/8" ht.  
 Extends 7-1/2".  
 Lamps: Three medium base lamps, each 100w max.

#### THREE-LIGHT CFL BATH

**P3192-09EBWB** Brushed Nickel  
**P3192-20EBWB** Antique Bronze  
 Size: 24" W., 8-1/8" ht.  
 Extends 7-1/2".  
 Lamps: Three 13w GU24 CFL lamps, included.



#### FOUR-LIGHT BATH

**P3193-09** Brushed Nickel  
**P3193-15** Polished Chrome  
**P3193-20** Antique Bronze  
 Size: 33-1/4" W., 8-1/8" ht.  
 Extends 7-1/2".  
 Lamps: Four medium base lamps, each 100w max.

#### FOUR-LIGHT CFL BATH

**P3193-09EBWB** Brushed Nickel  
**P3193-20EBWB** Antique Bronze  
 Size: 33-1/4" W., 8-1/8" ht.  
 Extends 7-1/2".  
 Lamps: Four 13w GU24 CFL lamps, included.



# Bravo

**ONE-LIGHT BATH**

**P2004-09** Brushed Nickel  
**P2004-20** Antique Bronze  
 Size: 7-1/4" W., 9" ht.  
 Extends 8-3/4". H/CTR 4-1/2".  
 Lamp: One medium base lamp, 100w max.

**ONE-LIGHT CFL BATH**

**P2004-09WB** Brushed Nickel  
 Size: 7-1/4" W., 9" ht.  
 Extends 8-3/4". H/CTR 4-1/2".  
 Lamp: One 13w GU24 CFL, included.



**TWO-LIGHT BATH**

**P2005-09** Brushed Nickel  
**P2005-20** Antique Bronze  
 Size: 17" W., 8-1/2" ht.  
 Extends 8-3/4". H/CTR 6-1/8".  
 Lamps: Two medium base lamps, each 100w max.

**TWO-LIGHT CFL BATH**

**P2005-09WB** Brushed Nickel  
 Size: 17" W., 8-1/2" ht.  
 Extends 8-3/4". H/CTR 6-1/8".  
 Lamps: Two 13w GU24 CFL, included.



**THREE-LIGHT BATH**

**P2006-09** Brushed Nickel  
**P2006-20** Antique Bronze  
 Size: 26-3/4" W., 8-3/4" ht.  
 Extends 8-3/4". H/CTR 6-3/8".  
 Lamps: Three medium base lamps, each 100w max.

**THREE-LIGHT CFL BATH**

**P2006-09WB** Brushed Nickel  
 Size: 26-3/4" W., 8-3/4" ht.  
 Extends 8-3/4". H/CTR 6-3/8".  
 Lamps: Three 13w GU24 CFL, included.



**FOUR-LIGHT BATH**

**P2007-09** Brushed Nickel  
**P2007-20** Antique Bronze  
 Size: 37-1/4" W., 9" ht.  
 Extends 8-3/4". H/CTR 6-1/2".  
 Lamps: Four medium base lamps, each 100w max.

**FIVE-LIGHT BATH**

**P2016-09** Brushed Nickel  
**P2016-20** Antique Bronze  
 Size: 46-1/4" W., 8-7/8" ht.  
 Extends 8-3/4". H/CTR 6-3/8".  
 Lamps: Five medium base lamps, each 100w max.



P2004-20



P2004-09  
 P2004-09WB



P2005-20



P2005-09  
 P2005-09WB



P2016-09




P2016-20



FREE FLOWING ARMS WITH FLUTED SHAPED GLASS. BRUSHED NICKEL FINISH HAS ETCHED GLASS. ANTIQUE BRONZE FEATURES ETCHED, UMBER LINEN GLASS.



P2006-09  
P2006-09WB



P2006-20



P2007-09



P2007-20

All fixtures on these pages mount up or down.

progresslighting.com

Chandelier

pg 190



# Inspire



P2018-09



P2018-20



P2018-15



P2019-20



P2019-09



P2019-15



P2021-15

Chandelier  
pg 232



Close-to-ceiling  
pg 325



UPDATED TRADITIONAL  
INSPIRATION WITH GRACIOUS,  
FLOWING OVAL ARMS  
AND ETCHED GLASS SHADES.



P2020-20



P2020-15



P2020-09



P2021-20



P2021-09

**ONE-LIGHT BATH**

**P2018-09** Brushed Nickel  
**P2018-15** Polished Chrome  
**P2018-20** Antique Bronze  
Size: 4-5/8" W., 7-1/2" ht.  
Extends 7-3/8". H/CTR 3-3/4".  
Lamp: One medium base lamp, 100w max.

**TWO-LIGHT BATH**

**P2019-09** Brushed Nickel  
**P2019-15** Polished Chrome  
**P2019-20** Antique Bronze  
Size: 15" W., 8-1/2" ht.  
Extends 6-7/8". H/CTR 6-1/8".  
Lamps: Two medium base lamps, each 100w max.

**THREE-LIGHT BATH**

**P2020-09** Brushed Nickel  
**P2020-15** Polished Chrome  
**P2020-20** Antique Bronze  
Size: 22-3/8" W., 8-1/4" ht.  
Extends 6-7/8". H/CTR 5-1/2".  
Lamps: Three medium base lamps, each 100w max.

**FOUR-LIGHT BATH**

**P2021-09** Brushed Nickel  
**P2021-15** Polished Chrome  
**P2021-20** Antique Bronze  
Size: 31-3/8" W., 8-1/2" ht.  
Extends 6-7/8". H/CTR 6-1/8".  
Lamps: Four medium base lamps, each 100w max.

# Heart

HEART WILL BRING ROMANCE TO THE VANITY, WITH FLOWING ARMS THAT GENTLY CRADLE ETCHED GLASS BOWLS.



P2913-15



P2913-09



P2913-20



P2919-20



P2919-09



P2915-20



P2919-15



P2915-09



P2928-09



P2928-20

## ONE-LIGHT BATH

**P2913-09** Brushed Nickel  
**P2913-15** Polished Chrome  
**P2913-20** Antique Bronze  
 Size: 6" W., 9-1/16" ht.  
 Extends 8". H/CTR 4-1/2".  
 Lamp: One medium base lamp,  
 100w max.

## TWO-LIGHT BATH

**P2915-09** Brushed Nickel  
**P2915-15** Polished Chrome  
**P2915-20** Antique Bronze  
 Size: 14" W., 8-3/8" ht.  
 Extends 8". H/CTR 2-1/2".  
 Lamps: Two medium base  
 lamps, each 100w max.

## THREE-LIGHT BATH

**P2919-09** Brushed Nickel  
**P2919-15** Polished Chrome  
**P2919-20** Antique Bronze  
 Size: 22" W., 8-1/2" ht.  
 Extends 8". H/CTR 8-3/8".  
 Lamps: Three medium base  
 lamps, each 100w max.

## FOUR-LIGHT BATH

**P2928-09** Brushed Nickel  
**P2928-15** Polished Chrome  
**P2928-20** Antique Bronze  
 Size: 29-7/8" W., 8-1/2" ht.  
 Extends 8". H/CTR 8-3/8".  
 Lamps: Four medium base  
 lamps, each 100w max.

## Chandelier

pg 242



All fixtures on these pages mount up or down.

# Avalon

SOFT CURVES AND SOPHISTICATED  
DETAILING WITH ALABASTER STYLE  
GLASS CURVES TO COMPLEMENT  
A VARIETY OF BATH AND VANITY  
AREAS.



P3266-20



P3266-09  
P3153-09EBWB



P3268-09  
P3155-09EBWB



P3267-09  
P3154-09EBWB



P3269-09  
P3156-09EBWB



P3267-20



P3268-20







P3269-20

Chandelier

pg 218



Product No.	Finish	Description	Size	Lamp(s)
P3266-09	Brushed Nickel	One-light	7-3/4" W., 12" ht.	1 medium base, 100w max.
P3266-20	Antique Bronze		Extends 8-3/4".	
P3267-09	Brushed Nickel	Two-light	18" W., 7" ht.	2 medium base, each 100w max.
P3267-20	Antique Bronze		Extends 8-3/4".	
P3268-09	Brushed Nickel	Three-light	24" W., 7" ht.	3 medium base, each 100w max.
P3268-20	Antique Bronze		Extends 8-3/4".	
P3269-09	Brushed Nickel	Four-light	36" W., 7" ht.	4 medium base, each 100w max.
P3269-20	Antique Bronze		Extends 8-3/4".	

Product No.	Finish	Description	Size	Lamp(s)
P3153-09EBWB	Brushed Nickel	One-light	7-3/4" W., 12" ht. Ext. 8-3/4".	One 13w GU24 CFL lamp included 
P3154-09EBWB	Brushed Nickel	Two-light	18" W., 7" ht. Ext. 8-3/4".	Two 13w GU24 CFL lamps included 
P3155-09EBWB	Brushed Nickel	Three-light	24" W., 7" ht. Ext. 8-3/4".	Three 13w GU24 CFL lamps included 
P3156-09EBWB	Brushed Nickel	Four-light	36" W., 7" ht. Ext. 8-3/4".	Four 13w GU24 CFL lamps included 

# Adorn

## ONE-LIGHT BATH

**P2008-09** Brushed Nickel

**P2008-15** Polished Chrome

**P2008-20** Antique Bronze

Size: 5-1/4" W., 6-3/4" ht.

Extends 7". H/CTR 3-3/8".

Lamp: One medium base lamp, 100w max.



P2008-09



P2008-15



P2008-20

## TWO-LIGHT BATH

**P2009-09** Brushed Nickel

**P2009-15** Polished Chrome

**P2009-20** Antique Bronze

Size: 13-1/4" W., 6-5/8" ht.

Extends 6-1/4". H/CTR 4-3/8".

Lamps: Two medium base lamps, each 100w max.



P2009-20



P2009-15



P2009-09



P2010-09

Chandelier

pg 184



450

Close-to-ceiling

pg 322



All fixtures on these pages mount up or down.

CREATED TO EASILY COORDINATE WITH MANY POPULAR FAUCET STYLES, ADORN FEATURES FLUTED ETCHED GLASS SHADES THAT MOUNT UP OR DOWN ON A CURVING FRAME.



P2010-20

**THREE-LIGHT BATH**

**P2010-09** Brushed Nickel  
**P2010-15** Polished Chrome  
**P2010-20** Antique Bronze  
 Size: 21-1/2" W., 6-5/8" ht.  
 Extends 7-1/2". H/CTR 4-3/8".  
 Lamps: Three medium base lamps, each 100w max.



P2010-15

**FOUR-LIGHT BATH**

**P2011-09** Brushed Nickel  
**P2011-15** Polished Chrome  
**P2011-20** Antique Bronze  
 Size: 28-1/4" W., 6-5/8" ht.  
 Extends 7-1/2". H/CTR 4-3/8".  
 Lamps: Four medium base lamps, each 100w max.



P2011-09



P2011-20



P2011-15

# Gather

SIMPLIFIED FRAME WITH UPDATED STYLING AND ELEGANT ETCHED GLASS SHADES. ENERGY STAR FIXTURES AVAILABLE.



P2706-09  
P2706-09EBWB



P2706-15  
P2706-15EBWB



P2706-20  
P2706-20EBWB



P2714-09



P2714-15



P2714-20

## ONE-LIGHT BATH

**P2706-09** Brushed Nickel  
**P2706-15** Polished Chrome  
**P2706-20** Antique Bronze  
Size: 5" W., 7-1/2" ht.  
H/CTR 2-5/8". Extends 6-1/2".  
Lamp: One medium base lamp, 100w max.

## THREE-LIGHT BATH

**P2708-09** Brushed Nickel  
**P2708-15** Polished Chrome  
**P2708-20** Antique Bronze  
Size: 24" W., 7-1/2" ht.  
H/CTR 2-1/2". Extends 6-1/2".  
Lamps: Three medium base lamps, each 100w max.

## FIVE-LIGHT BATH

**P2713-09** Brushed Nickel  
**P2713-15** Polished Chrome  
**P2713-20** Antique Bronze  
Size: 36" W., 7-1/2" ht.  
Extends 6-1/2". H/CTR 2-1/2".  
Lamps: Five medium base lamps, each 100w max.

## TWO-LIGHT BATH

**P2707-09** Brushed Nickel  
**P2707-15** Polished Chrome  
**P2707-20** Antique Bronze  
Size: 12" W., 7-1/2" ht.  
H/CTR 2-1/2". Extends 6-1/2".  
Lamps: Two medium base lamps, each 100w max.

## FOUR-LIGHT BATH

**P2709-09** Brushed Nickel  
**P2709-15** Polished Chrome  
**P2709-20** Antique Bronze  
Size: 30" W., 7-1/2" ht.  
H/CTR 2-1/2". Extends 6-1/2".  
Lamps: Four medium base lamps, each 100w max.

## SIX-LIGHT BATH

**P2714-09** Brushed Nickel  
**P2714-15** Polished Chrome  
**P2714-20** Antique Bronze  
Size: 48" W., 7-1/2" ht.  
Extends 6-1/2". H/CTR 2-1/2".  
Lamps: Six medium base lamps, each 100w max.

Chandelier  
pg 236



All fixtures on these pages mount up or down.





P2708-15  
P2708-15EBWB



P2707-20  
P2707-20EBWB



P2709-15  
P2709-15EBWB



P2707-15  
P2707-15EBWB



P2709-09  
P2709-09EBWB



P2707-09  
P2707-09EBWB



P2713-20



P2713-09

**ONE-LIGHT CFL BATH**

**P2706-09EBWB** Brushed Nickel  
**P2706-15EBWB** Polished Chrome  
**P2706-20EBWB** Antique Bronze  
 Size: 5" W., 7-1/2" ht.  
 Extends 6-1/2". H/CTR 2-5/8".  
 Lamp: One 13w GU24 CFL,  
 included.



**TWO-LIGHT CFL BATH**

**P2707-09EBWB** Brushed Nickel  
**P2707-15EBWB** Polished Chrome  
**P2707-20EBWB** Antique Bronze  
 Size: 12" W., 7-1/2" ht.  
 Extends 6-1/2". H/CTR 2-1/2".  
 Lamps: Two 13w GU24 CFL,  
 included.



**THREE-LIGHT CFL BATH**

**P2708-09EBWB** Brushed Nickel  
**P2708-15EBWB** Polished Chrome  
**P2708-20EBWB** Antique Bronze  
 Size: 24" W., 7-1/2" ht.  
 Extends 6-1/2". H/CTR 2-1/2".  
 Lamps: Three 13w GU24 CFL,  
 included.



**FOUR-LIGHT CFL BATH**

**P2709-09EBWB** Brushed Nickel  
**P2709-15EBWB** Polished Chrome  
**P2709-20EBWB** Antique Bronze  
 Size: 30" W., 7-1/2" ht.  
 Extends 6-1/2". H/CTR 2-1/2".  
 Lamps: Four 13w GU24 CFL,  
 included.



# Alabaster Glass



P3051-09  
P3051-09EBWB

P3051-20



P3053-09  
P3053-09EBWB



P3052-20



P3052-09  
P3052-09EBWB



P3053-20

Product No.	Finish	Description	Size	Lamp(s)
<b>P3051-09</b> <b>P3051-20</b>	Brushed Nickel Antique Bronze	One-light	5-1/4" W., 9" ht. Extends 7-1/4".	1 medium base, 100w max.
<b>P3052-09</b> <b>P3052-20</b>	Brushed Nickel Antique Bronze	Two-light	18" W., 7-1/4" ht. Extends 7-1/4".	2 medium base, each 100w max.
<b>P3053-09</b> <b>P3053-20</b>	Brushed Nickel Antique Bronze	Three-light	24" W., 7-1/4" ht. Extends 7-1/4".	3 medium base, each 100w max.
<b>P3054-09</b> <b>P3054-20</b>	Brushed Nickel Antique Bronze	Four-light	30" W., 7-1/4" ht. Extends 7-1/4".	4 medium base, each 100w max.
<b>P3055-09</b> <b>P3055-20</b>	Brushed Nickel Antique Bronze	Five-light	36" W., 7-1/4" ht. Extends 7-1/4".	5 medium base, each 100w max.
<b>P3056-09</b> <b>P3056-20</b>	Brushed Nickel Antique Bronze	Six-light	48" W., 7-1/4" ht. Extends 7-1/4".	6 medium base, each 100w max.

Product No.	Finish	Description	Size	Lamp(s)
<b>P3051-09EBWB</b>	Brushed Nickel	One-light	5-1/4" W., 9" ht. Extends 7-1/4".	1 GU24 CFL lamp, each 13w max, included
<b>P3052-09EBWB</b>	Brushed Nickel	Two-light	18" W., 7-1/4" ht. Extends 7-1/4".	2 GU24 CFL lamps, each 13w max, included
<b>P3053-09EBWB</b>	Brushed Nickel	Three-light	24" W., 7-1/4" ht. Extends 7-1/4".	3 GU24 CFL lamps, each 13w max, included
<b>P3054-09EBWB</b>	Brushed Nickel	Four-light	30" W., 7-1/4" ht. Extends 7-1/4".	4 GU24 CFL lamps, each 13w max, included

Close-to-ceiling

pg 315



ETCHED ALABASTER GLASS WITH  
SOFT CURVES. BRUSHED NICKEL OR  
ANTIQUÉ BRONZE COMPLEMENT  
STEPPED BACKPLATES.



# Bedford

BRUSHED NICKEL OR ANTIQUE BRONZE FINISH HIGHLIGHT CURVED DOUBLE ARMS AND ETCHED ALABASTER GLASS.

# Etched Glass

WHITE ETCHED GLASS FEATURES HINT OF SOPHISTICATION. BRUSHED NICKEL FINISH HIGHLIGHTS ANGULAR ARMS.



P3367-09



P3369-09  
P3188-09EBWB



P3367-20



P3368-20



P3368-09  
P3187-09EBWB



P3369-20



P3301-09



P3302-09



P3303-09

Product No.	Finish	Description	Size	Lamp(s)
P3367-09	Brushed Nickel	One-light	5-1/4" W., 8-1/2" ht.	1 medium base,
P3367-20	Antique Bronze		Extends 7-1/4".	100w max.
P3368-09	Brushed Nickel	Two-light	14" W., 8-1/4" ht.	2 medium base,
P3368-20	Antique Bronze		Extends 6-1/4".	each 100w max.
P3369-09	Brushed Nickel	Three-light	16" W., 8-1/4" ht.	3 medium base,
P3369-20	Antique Bronze		Extends 9".	each 100w max.

Product No.	Finish	Description	Size	Lamp(s)
P3301-09	Brushed Nickel	One-light	6" W., 8-7/8" ht. Extends 7-5/8".	1 medium base, 100w max.
P3302-09	Brushed Nickel	Two-light	13-1/2" W., 8-3/4" ht. Extends 7-1/2".	2 medium base, each 100w max.
P3303-09	Brushed Nickel	Three-light	18-3/4" W., 8-7/8" ht. Extends 7-1/2".	3 medium base, each 100w max.

Product No.	Finish	Description	Size	Ballast	Lamp(s)
P3187-09EBWB	Brushed Nickel	Two-light	14-5/8" W., 9" ht. Extends 6-1/2".	120V NPF electronic	2 GU24 CFL lamps, each 13w max., included
P3188-09EBWB	Brushed Nickel	Three-light	17" W., 8-5/8" ht. Extends 9-3/8".	120V NPF electronic	3 GU24 CFL lamps, each 13w max., included

Close-to-ceiling

pg 326



All fixtures on these pages mount up or down.

## Opal Glass

BELL-SHAPED OPAL GLASS DESIGNED WITH PLAYFUL ANGLES IN MIND.



Product No.	Finish	Description	Size	Lamp(s)
<b>P3373-10</b>	Polished Brass	One-light	5-1/4" W., 8-1/4" ht.	1 medium base,
<b>P3373-15</b>	Polished Chrome		Extends 8".	100w max.
<b>P3374-15</b>	Polished Chrome	Two-light	14" W., 8-1/4" ht.	2 medium base,
			Extends 6-1/4".	each 100w max.
<b>P3375-10</b>	Polished Brass	Three-light	16" W., 8-1/4" ht.	3 medium base,
<b>P3375-15</b>	Polished Chrome		Extends 9".	each 100w max.
<b>P3376-15</b>	Polished Chrome	Four-light	24-1/2" W., 8-1/4" ht.	4 medium base,
			Extends 7-1/2".	each 100w max.

## Fluted Glass

RIBBED DETAILING OFFERS A SUBTLE TEXTURE FOR THE CLEAR FLUTED GLASS.



Product No.	Finish	Description	Size	Lamp(s)
<b>P3287-09</b>	Brushed Nickel	One-light	5-1/4" W.,	1 medium base,
<b>P3287-15</b>	Polished Chrome		8-1/4" ht.	100w max.
<b>P3287-20</b>	Antique Bronze		Extends 8".	
<b>P3288-09</b>	Brushed Nickel	Two-light	11-3/4" W.,	2 medium base,
<b>P3288-15</b>	Polished Chrome		8-1/4" ht.	each 100w max.
<b>P3288-20</b>	Antique Bronze		Extends 8-1/4".	
<b>P3289-09</b>	Brushed Nickel	Three-light	16" W.,	3 medium base,
<b>P3289-15</b>	Polished Chrome		8-1/4" ht.	each 100w max.
<b>P3289-20</b>	Antique Bronze		Extends 8-1/4".	

# Deluxe Hollywood Marquee Lights

G LAMPS RECOMMENDED. WALL MOUNT ONLY.



P3026-15



P3038-15



P3025-15



P3025-20



P3040-09



P3026-09



P3026-20



P3025-09



P3040-20

Product No.	Finish	Description	Size	Lamp(s)
P3038-15	Polished Chrome	Three-light	18" L., 4-1/2" ht.	3 medium base G-lamps, each 60w max.
P3025-09	Brushed Nickel	Four-light	24" L., 4-3/4" ht.	4 medium base G-lamps, each 60w max.
P3025-15	Polished Chrome			
P3025-20	Antique Bronze			
P3026-09	Brushed Nickel	Six-light	36" L., 4-3/4" ht.	6 medium base G-lamps, each 60w max.
P3026-15	Polished Chrome			
P3026-20	Antique Bronze			
P3040-09	Brushed Nickel	Eight-light	48" L., 4-3/4" ht.	8 medium base G-lamps, each 60w max.
P3040-15	Polished Chrome			
P3040-20	Antique Bronze			

*All fixtures on these pages mount up or down.*

# Deluxe Broadway Lights

SOCKETS ON 6" CENTERS. MEDIUM BASE G-LAMPS RECOMMENDED. WALL MOUNT ONLY.

# Economy Broadway Lights

SOCKETS ON 7-1/2" CENTERS. MEDIUM BASE G-LAMPS RECOMMENDED. WALL MOUNT ONLY.



P3300-15



P3114-15



P3335-15



P3115-15



P3298-15



P3116-15



P3298-30



P3117-15



P3333-15



P3333-30



P3118-15


Product No.	Finish	Description	Size	Lamp(s)
<b>P3333-15</b> <b>P3333-30</b>	Polished Chrome White	Three-light	18" L., 4-1/4" ht.	3 medium base G-lamps, each 60w max.
<b>P3298-15</b> <b>P3298-30</b>	Polished Chrome White	Four-light	24" L., 4-1/4" ht.	4 medium base G-lamps, each 60w max.
<b>P3335-15</b>	Polished Chrome	Five-light	30" L., 4-1/4" ht.	5 medium base G-lamps, each 60w max.
<b>P3299-15</b>	Polished Chrome	Six-light	36" L., 4-1/4" ht.	6 medium base G-lamps, each 60w max.
<b>P3300-15</b> <b>P3300-30</b>	Polished Chrome White	Eight-light	48" L., 4-1/4" ht.	8 medium base G-lamps, each 60w max.

Product No.	Finish	Description	Size	Lamp(s)
<b>P3114-15</b>	Polished Chrome	Three-light	24" L., 4-1/4" ht.	3 medium base G-lamps, each 60w max.
<b>P3115-15</b>	Polished Chrome	Four-light	30" L., 4-1/4" ht.	4 medium base G-lamps, each 60w max.
<b>P3116-15</b>	Polished Chrome	Five-light	36" L., 4-1/4" ht.	5 medium base G-lamps, each 60w max.
<b>P3117-15</b>	Polished Chrome	Six-light	48" L., 4-1/4" ht.	6 medium base G-lamps, each 60w max.
<b>P3118-15</b>	Polished Chrome	Eight-light	60" L., 4-1/4" ht.	8 medium base G-lamps, each 60w max.


# Linear Fluorescent Bath

ETCHED GLASS IN SLEEK, LINEAR FORM WITH BRUSHED NICKEL FINISH. ENERGY STAR.

Product No.	Finish	Description	Size	Lamp(s)
P7211-09EB	Brushed Nickel	One-light	25-5/8" W., 5-1/4" ht. Extends 4".	1-F17T8 ADA
P7212-09EB	Brushed Nickel	One-light	37-5/8" W., 5-1/4" ht. Extends 4".	1-F25T8 ADA



P7212-09EB



P7211-09EB

# Maier

CLEAN CYLINDER SILHOUETTES IN BRUSHED NICKEL WITH WHITE SATIN ACRYLIC SHADE. CAN BE INSTALLED HORIZONTALLY OR VERTICALLY. TITLE 24 COMPLIANT.

Product No.	Finish	Description	Size	Lamp(s)
P7025-09EB	Brushed Nickel w/white acrylic	Two-light	30" W., 5" ht. Extends 5". H/CTR 2-1/2".	2 4-pin CFL, 2G11 base lamps, 24w max.



P7025-09EB

P7025-09EB  
vertically mounted

Close-to-ceiling  
pg 344



# Contemporary Acrylic

BRUSHED NICKEL END CAPS FINISHED WITH TWIN LINEAR DETAILING. ACRYLIC DIFFUSER. WALL MOUNT ONLY. ENERGY STAR.

Product No.	Finish	Size	Ballast	Lamp(s)
P7227-09EB	Brushed Nickel	25-1/4" L., 5-1/4" ht. Extends 4-1/2".	120V NPF electronic	2-F17T8
P7228-09EB	Brushed Nickel	37-1/4" L., 5-1/4" ht. Extends 4-1/2".	120V NPF electronic	2-F25T8
P7229-09EB	Brushed Nickel	49-1/4" L., 5-1/4" ht. Extends 4-1/2".	120V NPF electronic	2-F32T8



P7227-09EB



P7228-09EB





P7229-09EB

All fixtures on these pages mount up or down.



## Ribbed Linear Bath

WALL OR CEILING MOUNT. WHITE RIBBED ACRYLIC DIFFUSER. CAN BE INSTALLED HORIZONTALLY OR VERTICALLY.

Product No.	Finish	Description	Size	Lamp(s)	ADA
<b>P7218-09EB</b>	Brushed Nickel	Two-light	25" W., 6-1/2" ht. Extends 4".	2-F17T8	ADA 
<b>P7221-09EB</b>	Brushed Nickel	Two-light	49" W., 6-1/2" ht. Extends 4".	2-F32T8	ADA 




P7218-09EB



P7221-09EB





P7218-09EB  
*vertical*



P7218-09EB  
*ceiling mount*

## Linear Fluorescent Bath

WHITE ACRYLIC DIFFUSER WITH BRUSHED NICKEL ENDS. CAN BE INSTALLED HORIZONTALLY OR VERTICALLY.

Product No.	Finish	Description	Size	Lamp(s)	ADA
<b>P7236-09</b>	Brushed Nickel	Two-light	33-1/2" W., 4-3/8" ht. Extends 3-7/8".	2-F14T5	ADA 
<b>P7237-09</b>	Brushed Nickel	Two-light	45-1/4" W., 4" ht. Extends 3-7/8".	2-F21T5	ADA 



P7236-09



P7237-09



P7236-09  
*vertical*

## Metal Edge

SLEEK POLISHED CHROME METAL END CAPS. ACRYLIC DIFFUSER. WALL MOUNT ONLY.

## Soft Clouds

WHITE ACRYLIC DIFFUSERS CAN BE INSTALLED HORIZONTALLY OR VERTICALLY. PROVIDE LIGHT OUT AND DOWN. WALL MOUNT ONLY.




P7230-15EB



P7231-15EB




P7232-15EB









P7114-60EB



P7115-60EB



P7116-60EB

Product No.	Finish	Size	Ballast	Lamp(s)	Product No.	Finish	Size	Ballast	Lamp(s)
<b>P7230-15EB</b>	Polished Chrome	24-1/2" L., 3-1/4" ht. Extends 5-1/4".	120/277V HPF electronic	2-F17T8 	<b>P7114-60EB</b>	White	26-3/4" L., 6" ht. Extends 4-1/4".	120V HPF electronic	2-F17T8 
<b>P7231-15EB</b>	Polished Chrome	36-1/2" L., 3-1/4" ht. Extends 5-1/4".	120/277V HPF electronic	2-F25T8 	<b>P7115-60EB</b>	White	38-3/4" L., 6" ht. Extends 4-1/4".	120V HPF electronic	2-F25T8 
<b>P7232-15EB</b>	Polished Chrome	48-1/2" L., 3-1/4" ht. Extends 5-1/4".	120/277V HPF electronic	2-F32T8 	<b>P7116-60EB</b>	White	50-3/4" L., 6" ht. Extends 4-1/4".	120V HPF electronic	2-F32T8 

All fixtures on these pages mount up or down.

## Slim Profile

WHITE ACRYLIC DIFFUSER INSTALLS HORIZONTALLY OR VERTICALLY AND SNAPS IN PLACE. WHITE END CAPS. WALL MOUNT ONLY.



## Squared Bracket

EXTRUDED RIBBED WHITE ACRYLIC DIFFUSER AND WHITE END CAPS. KNOCKOUT FOR G.C.O. AND SWITCH. INSTALL HORIZONTALLY OR VERTICALLY. WALL MOUNT ONLY.



Product No.	Finish	Size	Ballast	Lamp(s)	ADA
<b>P7094-30EB</b>	White	25-5/8" L., 4-3/4" ht. Extends 4".	120V NPF electronic	2-F17T8	ADA
<b>P7095-30EB</b>	White	37-5/8" L., 4-3/4" ht. Extends 4".	120V NPF electronic	2-F25T8	ADA
<b>P7096-30EB</b>	White	49-5/8" L., 4-3/4" ht. Extends 4".	120V NPF electronic	2-F32T8	ADA

Product No.	Finish	Size	Ballast	Lamp(s)	ADA
<b>P7128-30EB</b>	White	24-3/8" L., 4-5/8" ht. Extends 4".	120V NPF electronic	1-F17T8	
<b>P7129-30EB</b>	White	24-3/8" L., 4-5/8" ht. Extends 4".	120V HPF electronic	2-F17T8	
<b>P7130-30EB</b>	White	36-3/8" L., 4-5/8" ht. Extends 4".	120V NPF electronic	1-F25T8	
<b>P7131-30EB</b>	White	36-3/8" L., 4-5/8" ht. Extends 4".	120V HPF electronic	2-F25T8	
<b>P7132-30EB</b>	White	48-3/8" L., 4-5/8" ht. Extends 4".	120V HPF electronic	1-F32T8	
<b>P7133-30EB</b>	White	48-3/8" L., 4-5/8" ht. Extends 4".	120V HPF electronic	2-F32T8	

## White Glass

Product No.	Finish	Description	Size	Lamp(s)
<b>P3813-30</b>	White	White glass. Rotary switch on socket.	4-3/4" W., 7-1/2" ht. Extends 4".	1 medium base, 100w max. ADA




P3813-30

## Channel Glass

WHITE BATH AND VANITY GLASS FIXTURE WITH CURVED EDGES.

Product No.	Finish	Description	Size	Lamp(s)
<b>P3111-30</b>	White Glass	Two-light. K.O. for switch and G.C.O.	13" W., 4-1/4" ht. Extends 4-1/2".	2 medium base, each 75w max.
<b>P3110-30</b>	White Glass	Four-light. K.O. for switch and G.C.O.	24" W., 4-1/4" ht. Extends 4-3/4".	4 medium base, each 75w max.



P3110-30



P3111-30

## Satin-Etched Glass

ANTIQUÉ BRASS WITH SATIN ETCHED GLASS OFFERS OLD WORLD FEEL.

Product No.	Finish	Description	Size	Lamp
<b>P3832-11</b>	Antique Brass	One-light	5-3/8" W., 7-7/8" ht. Extends 6".	1 medium base, 100w max.



P3832-11

## Victorian Glass

ETCHED GLASS SHADE WITH SCALLOPED EDGES AND ON-OFF SWITCH.

Product No.	Finish	Description	Size	Lamp(s)
<b>P3830-10</b>	Polished Brass	One-light	4-1/2" W., 8-1/2" ht. Extends 4-1/2".	1 medium base, 100w max.



P3830-10

*All fixtures on these pages mount up or down.*

# Bath Fans

FANS CAN BE CEILING OR WALL MOUNTED.  
UL/CUL LISTED.

## Decorative Bath Fan

DECORATIVE BATH/  
EXHAUST FAN/LIGHT  
COMBINATION UNITS

Round decorative design with frosted low-profile glass. Smooth finish for easy cleaning. Damp location listed.

**PV008-09STRWB** Brushed Nickel  
70 cfm energy efficient bath fan with frosted glass.  
Recommended bath size 65 sq. ft.  
Sound level rating 2.0 Sones.  
4" duct adapter.  
Decorative glass/fan size:  
13" dia., 5-9/16" ht.  
Back box: 7-1/2" L., 7-5/16" W.,  
5-5/16" ht.  
Lamps: Two 13w GU24 CFL,  
2700K, included.



**PV008-09STRWB**  
*(decorative bath fan shown complete with housing and fixture)*

## EnergyStar Bath Fans

**PV020-30** Textured White  
80 cfm bath fan  
Recommended bath size 75 sq. ft.  
Sound level rating 1.0 Sones  
4" duct fitting  
Grille size: 12-3/4" sq., 7/8" deep  
Back box: 9-1/4" L., 11-5/8" W.,  
8" ht.



PV020-30

**PV021-30WB** Textured White  
80 cfm bath fan with light  
Recommended bath size 75 sq. ft.  
Sound level rating 1.0 Sones  
4" duct fitting  
Grille size: 21-5/8" sq., 4" deep  
Back box: 9-1/4" L., 11-5/8" W.,  
8" ht.  
Lamp: One 13w GU24, 2700K,  
included.



PV021-30WB

The PV020-30 and PV021-30 are Energy Star qualified bath fans that offer the best combination of energy efficiency and quiet operation. Both models are rated for 80CFM air flow at 0.1" Ps accommodating 72ft<sup>2</sup> rooms with 8' ceiling heights, and have sound ratings ≤1 sone. Air and sound ratings have been verified and listed by the Home Ventilating Institute.

Motors are encased and permanently lubricated for continuous operation. Diffusers are white and are retained by torsion springs to ensure a tight fit against the ceiling and easy installation. Both models accommodate 2" x 8" joist construction, and are shipped with bar hangers that can be adjusted for 24" joist spans.

## Important notice regarding lamping information in this catalog:

In 2007, Congress passed the Energy Independence and Security Act – this legislation has commonly been referred to as the “Ban the Bulb” law. [Canada’s Parliament enacted similar efficiency laws in this same time period.] While the act requires manufacturers to offer more efficient incandescent lamps, it does not “ban” them.

In general, the following wattages are now available in the market for medium base A lamps:

Legacy wattage	New wattage*	Brightness*
100	72	1490 lumens
75	53	1050 lumens
60	43	750 lumens
40	29	380 lumens

\* Actual wattage and brightness will vary according to brand and finish (soft white, clear, etc.)

Underwriters Laboratories (UL) and the Canadian Standards Association (CSA) have not yet adopted standards to offer “certified” lamps in these new wattages to manufacturers for product testing. As a result, the values cited in this catalog still refer to the legacy wattages. Due to the growing number of choices of lamps available to consumers (LED, CFL, etc.), UL/CSA have incorporated into their safety standard an accommodation. The modification allows for use of any of these lamp types – provided the wattage of the alternate lamp does not exceed the MAX rated wattage on the fixture label.

It is at our customers’ discretion to choose to install CFL/LED lamps. Customers should pay careful attention to the bulb manufacturer’s warning/caution statements on the packaging or printed on the lamp. For example, many lamps will indicate on the packaging that they cannot be used in an enclosed fixture, a photocell or with a dimmer.

It is an exciting time to be part of the lighting industry as we advance best practices and make these technological leaps. Progress Lighting is committed to providing safe products that deliver on our customers’ expectations of having beautiful, functional lighting products to choose from – for any style, budget or home application.

*Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.*

*UL Listed or Classified or CSA Certified unless otherwise noted.*

*Bulbs not included with fixtures unless specified. Specifications subject to change without notice.*

*Metal finishes not specified as “solid” have quality plated or painted finishes.*

*Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.*

*©Progress Lighting 2015  
All rights reserved.  
International Copyright Secured.*