

2015-2016



QUOIZEL®

*Artisans* in Lighting...since 1930

# MAIN CATALOG 2015-16

# QUOIZEL.

*Artisans in Lighting...since 1930*



## Welcome!

We are proud to share our newest decorative lighting introductions with all of you. As you peruse our latest catalog, you will notice that in addition to our classic designs, we have expanded our Platinum section featuring more contemporary designs.

In addition, our artisans have done it once again, adding to our handmade Naturals and Tiffany collections. As always, you will find a plethora of beautifully designed lighting products to enhance the décor of your living spaces.

On behalf of the entire Quozel family, thank you for making our products part of your home.

Sincerely,

A handwritten signature in blue ink that reads "Rick".

Rick Seidman  
President / CEO

## Q U O I Z E L

**Since 1930,** Quoizel has made it a practice to keep in step with evolving fashion trends in home décor and interior design around the world.

As an industry leader in home lighting for over 80 years, we at Quoizel repeatedly offer successful product lines ranging in style from traditional to contemporary, keeping hand-crafted artistry, cutting-edge innovation and enduring quality at our very core.


### Our Board of Directors



**Rick Seidman**  
*President & CEO*



**Ira Phillips**  
*Chairman of the Board*



**Toni Phillips**  
*Executive Vice President*



**Todd Phillips**  
*Executive Vice President*



**Ed Clark**  
*Senior Vice President*



**Tim Hensch**  
*Vice President/Operations*

### Our Locations



*Charleston, SC*



*Hauppauge, NY*

Follow **QUOIZEL** on social media:



*Scan with your smart phone or tablet to view informative videos relating to our product line and catalog!*



TIFFANY



MICA



PEN SHELL



AGATE STONE



ONYX



RATIAN

# Guide to icons & reference codes



## TRUCK ITEM



## TITLE 20 COMPLIANT

All portable lamps shipped into the state of California will contain an energy-efficient fluorescent light bulb.



## TITLE 24 COMPLIANT ENERGY-EFFICIENT

- 13W, 18W or 23W Compact Fluorescent Included
- CFL Spring Self-Ballasted GU 24

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying this logo. (Medium base bulbs only)



## FIXTURE EXCEEDS 50 POUNDS



## DIFFUSER INCLUDED



## DAMP LOCATION



## WET LOCATION



## ADA APPROVED

© Copyright    ❖ Patent Number    ◆ Patent Pending

### Bulbs:

- Bulbs not included unless otherwise noted.
- Vintage Bulbs supplied are not necessarily the maximum wattage allowed.
- Wattages stated are the maximum recommended; however, you may use lower wattages to suit your lighting needs.
- Many candelabra bulbs are not suitable for base-up applications. OSRAM SYLVANIA® bulbs can be used for these purposes without effecting performance.
- Products requiring halogen bulb(s) come with bulb(s) in carton.
- Halogen bulbs should always be handled with care. When installing a halogen bulb, do not touch the bulb with your bare hands. When removing a halogen bulb, always allow the bulb sufficient time to cool. Handling the bulb with a cloth will help prevent premature bulb failure.
- For the prolonged life of G9 bulbs, compatible bath fixtures should only be mounted face-up.

### LED:

- LED information chart provided wherever applicable.

### Chain:

- (Single Tier) Chandelier, Dinette, Mini Chandeliers, Pendants, Mini Pendants and Island Lights come with 8' of wire and 4' of chain.
- (Two & Three Tier) Chandeliers and Foyer Fixtures come with 12' of wire and 8' of chain.
- All Outdoor Hanging Fixtures come with 12' of wire and 8' of chain.
- All Chain-Hung Mini Pendants come with 8' of wire and 4' of chain.

### Other:

- All Rod-Hung Mini Pendants come with 8' of wire.
- All Cord-Hung Mini Pendants come with 8' of cord.
- All Cable-Hung Mini Pendants come with 8' of cable.

### Damp / Wet Locations:

- Flush-mounted fixtures are "Damp Location" listed.
- All outdoor wall and post lights are "Wet Location" listed.

### Electrical:

- All electrical fixtures are rated at 120-volt AC unless otherwise noted.
- Unless specified, all electrical fixtures are cUL listed.
- All fixtures operate on standard dimmers unless otherwise noted.

### Hardware:

- Backplate information and HCWO (Height from Center of Wall Opening) included for most wall fixtures (including outdoor) and bath fixtures.
- Canopy information included on almost all fixtures.
- All mirrors come with mounting hardware.

### Tiffany / Naturals:

- Glass color in Tiffany lighting products vary in color. No two pieces are identical.
- Products that use natural materials are perfect for those seeking the aesthetics of natural variations. Due to its authenticity, the material may vary from pictured items.

### Glass / Shades:

- Will appear darker when not illuminated.

*In our efforts to constantly improve our products, changes may be made throughout the year that vary from printed information in the catalog.*

# Contents

## COLLECTIONS

Adonis . . . . .	<b>38</b>	La Parra . . . . .	<b>84</b>
Aliza . . . . .	<b>43</b>	Laila . . . . .	<b>88</b>
Ambrose . . . . .	<b>48</b>	Marquette . . . . .	<b>90</b>
Armelle . . . . .	<b>50</b>	Monterey Mosaic . . . . .	<b>94</b>
Downtown . . . . .	<b>52</b>	New England . . . . .	<b>100</b>
Duchess . . . . .	<b>58</b>	Riverside . . . . .	<b>102</b>
Dury . . . . .	<b>64</b>	Sophia . . . . .	<b>104</b>
Emery . . . . .	<b>68</b>	Taylor . . . . .	<b>107</b>
Jolene . . . . .	<b>72</b>	Trilogy . . . . .	<b>112</b>
Kendra . . . . .	<b>74</b>	Whitney . . . . .	<b>116</b>
Kyle . . . . .	<b>78</b>		

## MINI-COLLECTIONS

Noble . . . . .	<b>120</b>	Grant . . . . .	<b>132</b>
Union Station . . . . .	<b>122</b>	New Harbor . . . . .	<b>135</b>
Alexandria . . . . .	<b>124</b>	Milbank . . . . .	<b>136</b>
Genova . . . . .	<b>125</b>	Palmer . . . . .	<b>138</b>
Cabin . . . . .	<b>126</b>	Remi . . . . .	<b>139</b>
Castile . . . . .	<b>127</b>	Wesley . . . . .	<b>140</b>
Tricia . . . . .	<b>128</b>	Wilder . . . . .	<b>142</b>
Eastvale . . . . .	<b>130</b>	Tavern . . . . .	<b>144</b>
Baron . . . . .	<b>131</b>		

## ADDITIONAL PRODUCTS & ACCESSORIES

*Red number represents the category's appearance in our **New Photo Index** immediately following this page.  
Black number represents actual appearance in catalog.*

The Platinum Collection . . . . .	<b>8, 145</b>	Mini Pendants . . . . .	<b>20, 315</b>
Dining & Foyer and More . . . . .	<b>9, 161</b>	Semi-Flush Mounts . . . . .	<b>22, 325</b>
Island Lights . . . . .	<b>10, 187</b>	Flush Mounts . . . . .	<b>25, 340</b>
Tiffany . . . . .	<b>11, 197</b>	Track Lighting . . . . .	<b>27, 351</b>
Quoizel Naturals . . . . .	<b>15, 259</b>	Wall Fixtures . . . . .	<b>27, 357</b>
Designer Showcase:		Bath Fixtures . . . . .	<b>29, 361</b>
Carolyn Kinder . . . . .	<b>16, 280</b>	Outdoor Fixtures . . . . .	<b>32, 413</b>
UPTOWN / Sergio Orozco . . . . .	<b>17, 289</b>	Accessories . . . . .	<b>498</b>
Pendants . . . . .	<b>18, 301</b>	Full Product Index . . . . .	<b>502</b>

# Collections



**Adonis (ADS)** 38-42



**Aliza (ALZ)** 43-47



**Ambrose (AMB)** 48-49



**Armelle (AME)** 50-51



**Downtown (DW)** 52-57



**Duchess (DH)** 58-63



**Dury (RDY)** 64-66



**Emery (ER)** 67-71



**Jolene (JLE)** 72-73



**Kendra (KD)** 74-77



**Kyle (KY)** 78-83



**La Parra (LP)** 84-86



**Laila (LLA)** 87-89



**Marquette (MQ)** 90-93



**Monterey Mosaic (MY)**  
94-99



**New England (NA)**  
100-101



**Riverside (RVE)**  
102-103



**Sophia (SPH)** 104-106



**Taylor (TY)** 107-111



**Trilogy (TRG)** 112-115



**Whitney (WHI)** 116-118



**Noble (NBE)** 120-121



**Union Station (UST)**  
122-123



**Alexandria (AX)** 124



**Genova (GE)** 125



**Cabin (CBN)** 126



**Castile (CS)** 127



**Tricia (TCA)** 128-129



**Eastvale (EVE)** 130



**Baron (BRO)** 131



**Grant (GRT)** 132-134



**New Harbor (NHR)** 135



**Milbank (MBK)** 136-137



**Palmer (PLR)** 138



**Remi (REM)** 139



**Wesley (WSY)** 140-141



**Wilder (WLR)** 142-143



**Tavern (TVN)** 144





**Bordeaux (BRX) 146**



**Shimmer (PCSR) 147**



**Aura (PCAR) 147**



**Paragon (PRN) 147**




**Beaumont (BMT) 148**



**Countess (PCCT) 148**



**Empress (EMP) 148**



**Galaxy (PCGX) 149**



**Valla (VLA) 149**



**Highrise (PCHE) 150**



**Ella (PEL) 150**



**Janelle (PCJL) 150**



**Taper (PCTR) 151**



**Superior (PCSP) 151**



**Ribbons (RBN) 152-155**



**Cascade (PCCS) 156**



**Abode (PCCS) 156**



**Avanti (PCAT) 156**



**Bravado (PCBV) 157**



**Array (PCAY) 157**



**Stellar (PCSL) 157**

# Dining & Foyer

## PHOTO INDEX



**Auburn (ABN)** 161-163



**Voyager (VYR)** 164-165



**Carrabelle (CRE)**  
166-167



**Silhouette (SLT)** 168



**Serenity (SER)** 169



**Mirren (MRN)** 170



**Canyon (CYN)** 171



**Atrium (ATM)** 172-173



**Wyndmoor (WDM)** 173



**Bandelier (BDR)** 173



**Bordergate (BRG)** 174



**Ridge Manor (QF)** 174



**Knotting (QF)** 175



**Regina (QF)** 175



**Anchor (ANR)** 176



**Hampshire (HMP)** 176



**Frontier (FTR)** 177



**Paddock (QF)** 177



**Planter (QF)** 177



**Holbrook (HK)** 178-179



**Laramie (LRM)** 179



**Majesty (MJY)** 180



**Capri (CP)** 180



**Yuma (YU)** 180



**Collins (QF)** 181

# Dining & Foyer



Woodrow (QF) 181



Fort Quinn (FQ) 182



Gentry (GY) 183



Kayden (KDN) 183



Biltmore (QF) 183



Alston (QMC) 184-185



Capulin (CPN) 185



Kemper (KPR) 186



Celestial (CLT) 186

# Island Lighting



Eastvale (EVE) 188



Tavern (TVN) 187-188



New Harbor (NHR) 188



Adonis (ADS) 189



Emery (ER) 189



Deluxe (DX) 190-191



Taylor (TY) 191



Remi (REM) 191



Duchess (DH) 192



Laguna (MCLG) 192

# Island Lights

## PHOTO INDEX



**Luxe (TFLU) 192**



**Kyle (KY) 193**



**LaParra (LP) 193**



**Belle Fleur (TFBF) 194**



**Asheville (TFAS) 194**



**Classic Craftsman (TFCC) 194**



**Inglenook (TFIK) 195**



**Confetti (CKCF) 196**



**Marisol (CKMS) 196**



**Alexandria (AX) 196**

# Tiffany



**Inglenook (TFIK) 198-201**



**Asheville (TFAS) 202-205**



**Kami (TFKM) 206-208**



**Stephen (TFST) 209-212**



**Alahambre 213**



**Belle Fleur (TFBF) 214-215**



**Arden (TFAN) 216**



**Samara (TFSM) 217**



**Larissa (TFLR) 218-219**



**West End 220-221**



**Classic Craftsman (TFCC)**  
222



**Chastain (TFCS)**  
223



**Cambridge (TFGB)**  
224



**Dayton (TFDN)**  
225



**Rosa (TFRA)** 226



**Belle (TFBL)** 227



**Hyacinth** 228-229



**Jewel Dragonfly (TFJD)** 230



**King** 231



**Jonas** 231



**Autumn Dragonfly** 232



**Green Dragonfly** 232



**Summer Dragonfly** 232



**Copperfly** 233



**Jewel** 233



**Berkshire** 233



**Montclair** 234



**Adriana** 235



**Florentine** 235



**Bartlett** 235



**Mariah** 236



**Palazzo** 236



**Rosecliffe** 237



**Red Brier** 237



**Purple Wisteria** 237



Laburnum 238



Lucia 238



Wild Vines 238



Queens Meadow 239



Fowler 239



Campton 239



Pueblo 240-241



Montgomery 240



Aberdeen 242



Bryant 242



Sunrise 243



Holcomb 243



Viking 243



Pomeroy 244



Gotham 244



Grove Park 245



Macey 245



Navajo (TFNO) 246



Timber 246



Revere 246



Finton 247



Holmes 247



Arlington 247



Westlake 248



Indus 248

# Tiffany



**Bragg Creek 248**



**Hillworth 249**



**Grand Bay 249**



**India 250**



**Kings Pointe 250**



**Palmetto 250**



**Pearson 251**



**Lynch 251**



**Jewel Heart 251**



**Ross 252**



**Sea Shell 252**



**Crowley 253**



**Stinson 253**



**Carroll 254**



**Felice 254**



**Ava 254**



**Graham 255**



**Reed 255**



**Luxe 255**



**Lennon 256**



**Fields 256**



**Connie 256**



**Elephant 257**



**Rainbow Butterfly**

257



**Flower Turtle**

257



**Orange Butterfly**  
257



**Green Frog** 257



**Flowered Ladybug** 257



**Lounging Frog** 257

## Salamander Art Glass



**White Reef** 258



**Carra** 258



**Vargas** 258



**Hatley** 258



**Maritime** 258

## Naturals



**Laguna (MCLG)** 260-263



**Cyrus (MCCS)** 264



**Kingsford (MCKD)** 265



**Morrow** 265



**Mica Leaf** 266



**Highland** 266



**Vega** 266



**Bandelier (BDR)** 267



**Warwick** 267



**Flagstaff** 267



# Naturals



**Alistar 267**



**Pomez 268-269**



**Chamber 270**



**Ruckman (MCRM) 271**



**Zen (ZE) 272-273**



**Zephyr 274**



**Carwyn 274**



**Whispering Wood 275**



**Ariella (ARL) 275**



**Kendra (KD) 276**



**Kyle (KY) 277**



**Monterey Mosaic (MY)  
278**

# Carolyn Kinder



**Confetti (CKCF) 281-283**



**Metro (CKMO)  
284-285**



**Marisol (CKMS) 286-287**



**Nikos (CKNK) 288**



**Sonia (CKSN) 288**



**Gaston (CKGN) 288**



**Ultra (CKUT) 288**



**Theater Row (UPTR)**  
289-290



**Penn Station (UPPS)** 291



**Carnegie (UPCN)**  
292-293



**Wall Street (UPWS)** 294



**Fulton (UPFT)** 294



**Tribeca (UPTB)** 294



**Ritz (UPRZ)** 295



**Third Avenue (UPTA)**  
295



**Madison Manor (UPMM)**  
296-297



**Sutton Place (UPSP)**  
296



**Columbus Circle (UPCC)**  
298



**Seaport (UPSE)** 298



**Empire (UPEP)** 298



**East Village (UPEV)** 299



**Apollo (UPAP)** 299



**Holita (UPHL)** 300




**Chelsea (UPCE)** 300



**Williamsburg (UPWB)** 300

# Pendants



**Adonis (ADS) 42**



**Aliza (ALZ) 45**



**Ambrose (AMB) 49**



**Downtown (DW) 56**



**Duchess (DH) 60-61**



**Dury (RDY) 65**



**Emery (ER) 71**



**Jolene (JLE) 73**



**Kendra (KD) 77**



**Kyle (KY) 82**



**Monterey Mosaic (MY) 98**



**Riverside (RVE) 103**



**Trilogy (TRG) 115**



**Alexandria (AX) 124**



**Eastvale (EVE) 130**



**Grant (GRT) 134**



**Millbank (MBK) 137**



**Palmer (PLR) 138**



**Wilder (WLR) 142**



**Bordeaux (BRX) 146**



**Aura (PCAR) 147**



**Galaxy (PCGX) 149**



**Valla (VLA) 149**



**Janelle (PCJL) 150**



**Taper (PCTR) 151**

# Pendants

## PHOTO INDEX



**Superior (PCSP) 151**



**Ribbons (RBN) 152**



**Cascade (PCCS) 156**



**Abode (PCAE) 156**



**Tiffany -  
many styles available  
See section starting on  
p.197**



**Laguna 260**



**Cyrus 264**



**Morrow 265**



**Kingsford 265**



**Bandelier 267**



**Pomez 269**



**Ruckman (MCRM) 271**



**Zen (ZE) 272**



**Ariella (ARL) 275**



**Carolyn Kinder  
Confetti (CKCF) 282**



**Carolyn Kinder  
Metro (CKMO) 284**



**Carolyn Kinder  
Marisol (CKMS) 287**



**Uptown Penn Station  
(UPPS) 291**



**Uptown Fulton (UPFT)  
294**



**Uptown Apollo (UPAP)  
299**



**Catherine (CTN) 302**



**Josslyn (JS) 302**



**Cloverdale (CRA) 303**



**Long Beach (LBH) 303**



**Brown Lattice (BWL) 305**

# Pendants



**Portland (PTD) 304-305**



**Capri (CP) 306**



**Bound (BND) 306**



**Railway (RLY) 306**



**Mirage (MIR) 307**



**Aiden 307**



**Cody (CDY) 307**

# Mini-Pendants



**Adonis (ADS) 40**



**Aliza (ALZ) 45**



**Downtown (DW) 56**



**Duchess (DH) 62**



**Dury (RDY) 65**



**Emery (ER) 71**



**Kendra (KD) 77**



**Kyle (KY) 83**



**La Parra (LP) 86**



**Laila (LLA) 89**

# Mini-Pendants

## PHOTO INDEX



**Monterey Mosaic (MY) 95**



**New England (NA) 101**



**Riverside (RVE) 103**



**Sophia (SPH) 106**



**Taylor (TY) 110**



**Trilogy (TRG) 114**



**Union Station (UST) 123**



**Genova (GE) 125**



**Eastvale (EVE) 130**



**Grant (GRT) 134**



**Wilder (WLR) 143**



**Taper (PCTR) 151**



**Ribbons 152**



**Tiffany -  
many styles available  
See section starting on  
p.197**



**Laguna 261**



**Kingsford 265**



**Pomez 269**



**Ruckman 271**



**Carolyn Kinder  
Confetti (CKCF) 283**



**Carolyn Kinder  
Nikos (CKNK) 288**



**Carolyn Kinder  
Gaston (CKGN) 288**



**Carolyn Kinder  
Sonia (CKSN) 288**



**Uptown Penn Station  
(UPPS) 291**



**Uptown Seaport (UPSE)  
298**



**Catherine (CTN) 316**

# Mini-Pendants



**Brown Lattice (BWL) 316**



**Ferndale (FE) 316**



**Kayden (KDN) 316**



**Cody (CDY) 317**



**Ibsen (IE) 317**



**Delray (DY) 317**



**Manderson (MDN) 318**



**Mercer 319**



**Marine (MRE) 319**



**Railway (RLY) 319**



**Keaton 320**



**Steadman (SDN) 320-321**



**Ridley 320**

# Semi-Flush Mounts



**Adonis (ADS) 42**



**Aliza (ALZ) 45**



**Downtown (DW) 56**



**Duchess (DH) 62**



**Dury (RDY) 65**

# Semi-Flush Mounts

## PHOTO INDEX



**Jolene (JLE) 73**



**Kendra (KD) 77**



**Kyle (KY) 82**



**Monterey Mosaic (MY) 98**



**New England (NA) 101**



**Riverside (RVE) 103**



**Taylor (TY) 110**



**Trilogy (TRG) 115**



**Whitney (WH) 118**



**Union Station (UST) 123**



**Castile (CS) 127**



**Baron (BRO) 131**



**New Harbor (NHR) 135**



**Milbank (MBK) 137**



**Palmer (PLR) 138**



**Wesley (WS) 141**



**Wilder (WLR) 143**



**Tavern (TVN) 144**



**Shimmer (PCSR) 147**



**Superior (PCSP) 151**



**Array (PCAY) 157**



**Laguna (MCLG) 260**



**Cyrus (MCCS) 264**



**Kingsford (MCKD) 265**



**Tiffany -  
many styles available  
See section starting on  
p.197**



# Semi-Flush Mounts



**Ruckman (MCRM) 271**



**Zen (ZE) 272**



**Carolyn Kinder  
Confetti (CKCF) 283**



**Carolyn Kinder  
Metro (CKMO) 284**



**Carolyn Kinder  
Marisol (CKMS) 287**



**Uptown Theater Row  
(UPTR) 290**



**Uptown Penn Station  
(UPPS) 291**



**Uptown Tribeca (UPTB)  
294**



**Uptown Wall Street  
(UPWS) 294**



**Griffin (GF) 326**



**Ashland 327**



**Ozark (OZ) 327**



**Belcourt 328**



**Chantilly 328**



**Warren 329**



**Cody (CDY) 329**



**Electra (EL) 329**



**Mirage (MIR) 330**



**Nova 330**



**Brown Lattice (BWL) 331**



**Josslyn (JS) 331**



**Frontier (FTR) 331**



**Waverly (WV) 332**



**Deluxe (DX) 332**



**Cloverdale (CRA) 332**

# Semi-Flush Mounts

## PHOTO INDEX



Norwood 333



Celestial 333



Caitlyn (CTL) 334



Sailor (SLR) 334



Castle 335

# Flush Mounts



Adonis (ADS) 42



Duchess (DH) 62



Laila (LLA) 89



Monterey Mosaic (MY) 98



New England (NA) 101



Cabin (CBN) 126



Bordeaux (BRX) 146



Paragon (PRN) 147



Beaumont (BMT) 148



Empress (EMP) 148



Countess (PCCT) 148



Valla (VLA) 149



Ella (PCEL) 150



Highrise (PCHE) 150



Ribbons (RBN) 153

# Flush Mounts



**Avanti (PCAT) 156**



**Bravado (PCBV) 157**



**Stelar (PCSL) 157**



**Tiffany - many styles available**  
See section starting on p.197



**Laguna (PCSL) 261**



**Chamber (CHB) 270**



**Zen (ZE) 272**



**Alabaster Melon (AL) 340**



**Wilson (WLS) 340**



**Griffin (GF) 341**



**Melon (ML) 342**



**Manor (MNR) 343**



**Summit (SMT) 344**



**Josslyn (JS) 345**



**Majesty (MJY) 345**



**Bound (BND) 345**



**Ozark (OZ) 346-347**



**Triad 346**

# Track Lighting

## PHOTO INDEX



Taylor (TY) 352



Pacifica (PF) 352



Denning (QTR) 352



Eastvale (EVE) 353



Kyle (KY) 353



Monterey Mosaic (MY) 353



Duchess (DH) 354-355



Aliza (ALZ) 355



Asheville (TFAS) 356



Inglenook (TFIK) 356



Stephen (TFST) 356

# Wall Lighting



Adonis (ADS) 40



Armelle (AME) 51



Kendra (KD) 76



Kyle (KY) 83



La Parra (LP) 85

# Wall Lighting



**Marquette (MQ) 92**



**Monterey Mosaic (MY) 99**



**Sophia (SPH) 106**



**Taylor (TY) 110**



**Trilogy (TRG) 114**



**Whitney (WHI) 118**



**Noble (NBE) 121**



**Tricia (TCA) 129**



**Remi (REM) 139**



**Carwyn (CWN) 274**



**Tiffany - many styles available**

See section starting on p.197



**Uptown Theater Row (UPTR) 290**



**Uptown Sutton Place (UPSP) 296**



**Uptown Madison Manor (UPMM) 296**



**Uptown Seaport (UPSE) 298**



**Uptown East Village (UPEV) 299**



**Uptown Holita (UPHL) 300**



**Millenium (LSMP) 358**



**Yuma (YU) 358**

# Bath Lighting

## PHOTO INDEX



**Aliza (ALZ) 362-363**



**Adano (AN) 364**



**Broadgate (BGT) 365**



**Ayers (AYR) 366-367**



**Bower (BWR) 368**



**Clarke (CLE) 369**



**Duchess (DH) 370-371**



**Demitri (DI) 372-374**



**Devlin (DVN) 375**



**Downtown (DW) 376**



**Deluxe (DX) 377**



**Edison (EDS) 378**



**Ellis (EI) 379**



**Erin (ERN) 380**



**Hollister (HS) 381**

# Bath Lighting



**Kolt (KLT) 382**



**Loft (LFT) 383**



**Melody (MLD) 384**



**North Gate (NGT) 385**



**Nicholas (NL) 386**



**Nolan (NN) 387**



**Parallel (PRL) 388**



**Perry (PY) 389**



**Pacifica (PF) 390-391**



**Quinton (QI) 392**



**Sophia (SPH) 393**



**Stowe (STE) 394**



**Tranquil Bay (TB) 395**



**Tatum (TU) 396**



**Tritan (TT) 397**

# Bath Lighting

## PHOTO INDEX



**Taylor (TY) 398-399**



**Pierre (PCP) 400**



**Royale (RYE) 400**



**Shimmer (PCSR) 401**



**Paragon (PRN) 402**



**Alexa (PCAX) 403**



**Endless (PCED) 403**



**Evermore (EME) 404-405**



**Ribbons (RBN) 406**



**Cosmic (PCCI) 407**



**Barron (PCBA) 408**



**Dash (PCDH) 409**



**Glacial (PCGL) 409**



**Exton (PCEN) 410**



**Pace (PCPC) 411**



**Promenade (PCPE) 411**



**Uptown 3rd Avenue (UPTA) 412**



# Outdoor Lighting



**Newbury (NY)** 414-419



**Hunter (HTR)** 420-421



**Marblehead (MBH)**  
422-423



**Stonington (SNN)**  
424-425



**Fort Quinn (FQ)**  
426-429



**Oasis (OAS)** 430-431



**Harmony (HY)** 432-433



**Hillcrest (HC)** 434-437



**Lodge (LDG)** 438-439



**Langston (LNG)** 440-441



**Millhouse (MHE)** 442-443



**Rue De Royal (RO)**  
444-445



**Chalmers (CM)** 446-447



**Cooper (COR)** 448-449



**Marine (MRE)** 450-451



**Devon (DE)** 452-454



**Seaford (SFD)** 455



**Ridge (RGE)** 456-457



**Rutledge (RJ)** 458-459



**Bedford (BFD)** 460-461



**Byron (BRN)** 462-463



**Steadman (SDN)**  
464-465



**Galen (GLN)** 466-468



**Chancellor (CCR)** 469



**Tudor (TDR)** 470-471

# PHOTO INDEX



**Trumbull (TML) 472-473**



**Province (PRV) 474-475**



**Powell (PWL) 476-477**



**Bain (BAN) 478-480**



**Cole (COE) 481**



**Zephyr (ZP) 481**



**Grover (GVR) 482-483**



**Carleton (CAR) 484-485**



**Georgetown (GT) 486-487**



**Cortland (CTD) 488-489**



**Bradley (BRY) 490-491**



**Carson (CAN) 492-493**



**Chimera (CHI) 494-495**



**Alto (ALT) 496**



**Ryland (RYD) 496**



**Milan (MLN) 497**



**New England (NA) 497**

*At Quoizel, we constantly strive to ensure that the metal and glass finishes shown in the catalog match our actual products. However, variations in printing and chemical finishes may cause some differences between the printed images and actual product.*




# QUOIZEL

*Artisans in Lighting... since 1930*



# NEW FOR 2015!

QUOIZEL.  
*Artists in Lighting... since 1930*



Portable Lighting  
2015-2016 and Mirrors

Browse our complete line of table lamps,  
floor lamps & mirrors in one convenient catalog!

*Contact Quoizel for a copy today!*

# COLLECTIONS | QUOIZEL



Whether your décor is traditional, contemporary, or somewhere in the middle, Quoizel presents a diverse offering of coordinated lighting solutions which will complement and enhance your home.

Browse the pages which follow and find that unique **Quoizel Collection** which fits your own personal style!



From the **WHITNEY COLLECTION** (page 118)  
Hanging Fixture: **WHI5005IS** Wall Fixture: **WHI8701IS**

# Adonis COLLECTION

**FINISH:**  
Dark Cherry

**GLASS:**  
Opal Etched and Clear Water

ADS5015DC 



*The beauty of clear water glass will add a delicate touch of elegance to any home.*



ADS5009DC



ADS639DC



## Adonis COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ADS5009DC	30" H, 30.5" W, 30.5" Dp.	6" D	9-60W Cand. Base
ADS5015DC	40" H, 40" W, 40" Dp.	6" D	15-60W Cand. Base
ADS639DC	19" H*, 39" W, 19.5" Dp.	8" L x 4.5" W	6-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain. Rod-hung fixtures come with 8' of wire. \*Comes with 4 (6") and (4) 12" Rods.



# Adonis COLLECTION

**FINISH:**  
Dark Cherry

**GLASS:**  
Opal Etched and Clear Water

ADS5005DC



ADS1504DC DAMP



DAMP ADS8701DC



# Adonis COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
ADS1504DC	7.5" H*, 4.5" W, 4.5" Dp.	6" D	-	1-100W Med. Base or 23W CFL
ADS5005DC	22" H, 26" W, 26" Dp.	6" D	-	5-60W Cand. Base
ADS8701DC	14" H, 5.5" W, 7" Dp.	5.5" D	9.75"	1-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. \*Comes with (2) 6" and (2) 12" Rods. Rod-hung fixtures come with 8' of wire.



# Adonis COLLECTION

**FINISH:**  
Dark Cherry


**GLASS:**  
Opal Etched and Clear Water

 **ADS2818DC**



 **ADS1715DC**



 **ADS1615DC**

# Adonis COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
<b>ADS1615DC</b>	9" H, 15" W, 15" Dp.	-	2-60W Med. Base or 13W CFL
<b>ADS1715DC</b>	15" H, 15" W, 15" Dp.	6" D	3-60W Med. Base or 13W CFL
<b>ADS2818DC</b>	28" H, 18" W, 18" Dp.	6" D	3-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.

# Aliza COLLECTION

COLLECTIONS

**FINISH:**  
Palladian Bronze

**GLASS:**  
Gradient Amber Mist

ALZ5009PN DAMP



## Aliza COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ALZ5009PN	34" H, 34.5" W, 34.5" Dp.	6.5" D	9-100W Med. Base or 23W CFL

Chain-hung fixtures come with 12' of wire and 8' of chain.

# Aliza COLLECTION

**FINISH:**

Palladian Bronze

**GLASS:**

Gradient Amber Mist

ALZ5005PN DAMP



ALZ5105PN DAMP





ALZ1507PN DAMP



DAMP ALZ1718PN



ALZ2823PN DAMP



ALZ1404PN DAMP

All Quoizel Track Lights Swivel

# Aliza COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ALZ1404PN	13" H, 41.5" W, 6" Dp.	8" L x 4.5" W	4-100W Med. Base or 23W CFL
ALZ1507PN	10.5" H*, 7" W, 7" Dp.	6.5" D	1-100W Med. Base or 23W CFL
ALZ1718PN	14.5" H, 18.5" W, 18.5" Dp.	6.375" D	3-100W Med. Base or 23W CFL
ALZ2823PN	29" H, 23" W, 23" Dp.	6.5" D	4-100W Med. Base or 23W CFL
ALZ5005PN	22.5" H, 28.5" W, 28.5" Dp.	6.5" D	5-100W Med. Base or 23W CFL
ALZ5105PN	24" H, 25" W, 25" Dp.	6.5" D	5-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain. \*Comes with (2) 12" and (2) 6" Rods. Rod-hung fixtures come with 8' of wire.

# Aliza COLLECTION

**FINISH:**

Palladian Bronze

**GLASS:**

Gradient Amber Mist

*Aliza bath fixtures  
can be mounted as  
uplights or downlights*

**ALZ8601PN**

*Enlarged for detail*



**ALZ8602PN**



**ALZ8603PN**

**ALZ8604PN**



# Aliza COLLECTION

PRODUCT	DIMENSIONS	BACKPLATE	HCWO	BULBS
ALZ8601PN	7.5" H, 6" W, 7.5" Dp.	4.5" W x 6.5" H	3.5"	1-100W Med. Base or 23W CFL
ALZ8602PN	8" H, 16" W, 8" Dp.	6.5" W x 4.5" H	5"	2-100W Med. Base or 23W CFL
ALZ8603PN	8" H, 24" W, 8" Dp.	6.5" W x 4.5" H	5"	3-100W Med. Base or 23W CFL
ALZ8604PN	8" H, 33" W, 8" Dp.	6.5" W x 4.5" H	5"	4-100W Med. Base or 23W CFL



From the **ALIZA COLLECTION** Vanity Light: **ALZ8603PN**

Also shown: **Breckenridge Mirror QR1419PN**  
(See Quoizel Portables Catalog, p.106)



# Ambrose COLLECTION

**FINISH:**  
Vintage Gold

AMB5009VG





AMB5005VG



AMB5303VG



HANGING  
GLASS ACCENTS

AMB2822VG DAMP

# Ambrose COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
AMB2822VG	29" H, 22.5" W, 22.5" Dp.	5" D	4-100W Med. Base or 23W CFL	Etched Painted White Inside
AMB5005VG*	26" H, 27" W, 27" Dp.	5" D	5-60W Cand. Base	-
AMB5009VG**	33.5" H, 33" W, 33" Dp.	5" D	9-60W Cand. Base	-
AMB5303VG	21.5" H, 16" W, 16" Dp.	5" D	3-60W Cand. Base	-

\*Chain-hung fixture comes with 8' of wire and 4' of chain. \*\*Chain-hung fixture comes with 12' of wire and 8' of chain.

# Armelle COLLECTION

**FINISH:**  
Imperial Bronze

**SHADE:**  
Butterscotch Onyx

AME5018IB 

SCALOPE  
EDGES



QUOIZEL  
**NATURALS**  
**ONYX**



AME5009IB



AME5005IB

AME5303IB



QUOIZEL  
NATURALS  
ONYX

DAMP AME8701IB



Armelle COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
AME5005IB*	23" H, 28" W, 28" Dp.	5" D	-	5-60W Cand. Base
AME5009IB**	33" H, 33" W, 33" Dp.	5" D	-	9-60W Cand. Base
AME5018IB**	48" H, 48" W, 48" Dp.	6" D	-	18-60W Cand. Base
AME5303IB*	19.5" H, 20" W, 20" Dp.	5" D	-	3-60W Cand. Base
AME8701IB	9.5" H, 5" W, 6.5" Dp.	4.625" W x 7" H	4"	1-60W Cand. Base

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixtures come with 12' of wire and 8' of chain.  
Due to natural properties, glass color may vary.

# Downtown COLLECTION

**FINISH:**  
Polished Chrome

**GLASS:**  
Opal Etched

OPTIC  
CRYSTAL

DW5015C  



## Downtown COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
DW5015C	41.5" H, 44" W, 44" Dp.	6" D	15-100W Med. Base or 23W CFL

Chain-hung fixture comes with 12' of wire and 8' of chain.



From the **DOWNTOWN COLLECTION:**  
**DW5005C**  
*Photo courtesy of Innovative Custom Homes*

# Downtown COLLECTION

**FINISH:**  
Polished Chrome

**GLASS:**  
Opal Etched

DW5009C 



 DW5005C



 DW5004C





**DW43222BN**

**Finish:** Brushed Nickel

**Glass:** Beveled

**DW8603C** DAMP



**DW8604C** DAMP



**DW8602C** DAMP

DAMP **DW8701C**

*Enlarged for detail*



**D**owntown COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
<b>DW43222BN</b>	32" H, 22" W, 1.5" Dp.	-	-	-
<b>DW5004C*</b>	19.5" H, 22" W, 22" Dp.	6" D	-	4-100W Med. Base or 23W CFL
<b>DW5005C*</b>	26" H, 28" W, 28" Dp.	6" D	-	5-100W Med. Base or 23W CFL
<b>DW5009C**</b>	33" H, 36" W, 36" Dp.	6" D	-	9-100W Med. Base or 23W CFL
<b>DW8602C</b>	7.5" H, 15" W, 7" Dp.	8" W x 5" H	5"	2-60W Frosted G9 Halogen*
<b>DW8603C</b>	7.5" H, 24.5" W, 7" Dp.	8" W x 5" H	5"	3-60W Frosted G9 Halogen*
<b>DW8604C</b>	7.5" H, 33.5" W, 7" Dp.	8" W x 5" H	5"	4-60W Frosted G9 Halogen*
<b>DW8701C</b>	11.5" H, 6" W, 8" Dp.	6" D	7.75"	1-100W Med. Base or 23W CFL

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixture comes with 12' of wire and 8' of chain.

\*Bulbs Supplied. For prolonged life of the bulb, all G9-compatible bath fixtures should be mounted face-up.



# Downtown COLLECTION

**FINISH:**

Polished Chrome

**GLASS:** Opal Etched (DW1506C)

**SHADE:** Cream Linen Fabric  
(DW1717C, DW1824C, DW2817C)



**DW1506C** 



 **DW2817C**

 **DW1824C**



 **DW1717C**



# Downtown COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
<b>DW1506C</b>	12.5" H*, 6" W, 6" Dp.	5.5" D	1-100W Med. Base or 23W CFL	-
<b>DW1717C</b>	13.5" H, 17" W, 17" Dp.	8" D	3-100W Med. Base or 23W CFL	17" x 5.5"
<b>DW1824C</b>	33" H, 24" W, 24" Dp.	6" D	4-100W Med. Base or 23W CFL	24" x 8"
<b>DW2817C</b>	24" H, 17" W, 17" Dp.	6" D	3-75W Med. Base or 18W CFL	17" x 7.5"

Chain-hung fixtures come with 8' of wire and 4' of chain. \*Comes with (2) 12" and (2) 6" Rods. Rod-hung fixtures come with 8' of wire.



From the **DOWNTOWN COLLECTION:**  
**DW2817C**  
*Photo courtesy of Phil Kean Design Group*

# Duchess COLLECTION

**FINISH:**

**AN** Antique Nickel

**PN** Palladian Bronze

**GLASS:**

**AN** Grey Marble

**PN** Champagne Marble

DH5009AN DAMP



DH5018PN   

*Swooping antique nickel swirls and the beauty of grey marble glass give the Duchess AN finish an unrivaled elegance.*

DH5005PN 

DH5105AN



## Duchess COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
DH5005AN/PN*	22.5" H, 24.5" W, 24.5" Dp.	6.5" D	5-100W Med. Base or 23W CFL
DH5009AN/PN**	31" H, 30.5" W, 30.5" Dp.	6.5" D	9-100W Med. Base or 23W CFL
DH5018AN/PN**	39" H, 41" W, 41" Dp.	6.5" D	18-100W Med. Base or 23W CFL
DH5105AN/PN*	21" H, 24.5" W, 24.5" Dp.	6.5" D	5-100W Med. Base or 23W CFL

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixtures come with 12' of wire and 8' of chain.

# Duchess COLLECTION

**FINISH:**

- AN** Antique Nickel
- PN** Palladian Bronze

**GLASS:**

- AN** Grey Marble
- PN** Champagne Marble

**DAMP** DH5103PN



**DAMP** DH2820AN



**DAMP** DH348PN



# Duchess COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
DH2820AN/PN	24" H, 20" W, 20" Dp.	6.5" D	4-100W Med. Base or 23W CFL
DH348AN/PN	27" H, 48" W, 14" Dp.	6.5" D	3-100W Med. Base or 23W CFL
DH5103AN/PN	20" H, 23" W, 23" Dp.	6" D	3-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.



# Duchess COLLECTION

**FINISH:**

- AN** Antique Nickel
- PN** Palladian Bronze

**GLASS:**

- AN** Grey Marble
- PN** Champagne Marble

**DAMP** DH1718PN



**DAMP** DH1616AN



DH1722AN



**DAMP** DH1506PN



**DAMP** DH1404AN



All Quoizel Track Lights Swivel



**DH8601AN** DAMP

*Enlarged for detail*



DAMP **DH8602PN**

*Duchess bath fixtures can be mounted as uplights or downlights.*



**DH8604PN** DAMP



**DH8603AN** DAMP

**DH44030PN**



# Duchess COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	GLASS
DH1404AN/PN	12.5" H, 36.5" W, 6" Dp.	6.5" L x 4.5" W	-	4-100W Med. Base or 23W CFL	-
DH1506AN/PN	11" H**, 6" W, 6" Dp.	5.5" D	-	1-100W Med. Base or 23W CFL	-
DH1616AN/PN	8" H, 15" W, 15" Dp.	-	-	2-60W Med. Base or 13W CFL	-
DH1718AN/PN	11" H, 17.5" W, 17.5" Dp.	5.5" D	-	3-100W Med. Base or 23W CFL	-
DH1722AN/PN	13" H, 22" W, 22" Dp.	5.5" D	-	3-100W Med. Base or 23W CFL	-
DH43024PN*	30" H, 24" W, 1.5" Dp.	-	-	-	Beveled
DH44030PN	40" H, 30" W, 1.5" Dp.	-	-	-	Beveled
DH8601AN/PN	11" H, 6" W, 8" Dp.	4.75" W x 6.75" H	7.5"	1-100W Med. Base or 23W CFL	-
DH8602AN/PN	11" H, 16" W, 7.5" Dp.	9" W x 5" H x 1" Dp	7.5"	2-100W Med. Base or 23W CFL	-
DH8603AN/PN	11" H, 23" W, 7.5" Dp.	9" W x 5" H x 1" Dp	7.5"	3-100W Med. Base or 23W CFL	-
DH8604AN/PN	11" H, 31.5" W, 7.5" Dp.	9" W x 5" H x 1" Dp	7.5"	4-100W Med. Base or 23W CFL	-

\*Not Shown. \*\*Comes with (2) 6" and (2) 12" Rods.

All rod-hung fixtures come with 8' of wire. Mirrors may be hung vertically or horizontally.



# Dury COLLECTION

**FINISH:**

**CS** Century Silver Leaf

**PN** Palladian Bronze **NEW!**

**RDY5208PN**

**NEW!**

FOR ♦ 2015





RDY1506CS



**NEW!**  
FOR ♦ 2015



RDY2823PN

**NEW!**  
FOR ♦ 2015



RDY1714PN **DAMP**

FAUX  
MELTED WAX  
CANDLES



RDY2821CS

Dury COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
RDY1506CS*	11" H, 6.5" W, 6.5" Dp.	5" D	1-60W Vintage Bulb (Supplied)†
RDY1714CS/PN	14.5" H, 14.5" W, 14.5" Dp.	5.5" D x .75" H	3-60W Cand. Base
RDY2821CS/PN*	14.5" H, 21" W, 21" Dp.	5" D x 1" H	4-60W Cand. Base
RDY2823CS/PN*	20" H, 23" W, 23" Dp.	5" D x 1" H	4-60W Cand. Base
RDY5208CS/PN**	36" H, 23" W, 23" Dp.	5.5" D x 1" H	8-60W Cand. Base

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixture comes with 12' of wire and 8' of chain.

†Max wattage: 100W Med. Base or 23W CFL.



From the **DURY COLLECTION:**  
RDY1714CS



From the **EMERY COLLECTION:**  
ER1814IS

*Photo courtesy of Letitia Little Interior Design*

# Emery COLLECTION

**FINISH:**

**BN** Brushed Nickel

**IS** Imperial Silver

**PN** Palladian Bronze

**WS** Weathered Brass **NEW!**

**SHADE:** Metal

**ER5103WS** **DAMP**

*Enlarged for detail*

**NEW!**

**FOR ♦ 2015**



ER5103BN DAMP



ER5103IS DAMP



ER5103PN DAMP



*Emery* COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ER5103BN/IS/PN/WS	15" H*, 24" W, 24" Dp.	5" D	3-100W Med. Base or 23W CFL

Rod-hung fixtures come with 8' of wire. \*Comes with (2) 12" and (2) 6" Rods.

# Emery COLLECTION

**FINISH:**

**BN** Brushed Nickel

**IS** Imperial Silver

**PN** Palladian Bronze

**WS** Weathered Brass **NEW!**

**SHADE:** Metal

**ER353WS**  

*Enlarged for detail*

**NEW!**

FOR ♦ 2015



**ER353PN**  



**ER353IS**  



**ER353BN**  





ER1508IS DAMP



ER1508PN DAMP



ER1508BN DAMP

Enlarged for detail



DAMP ER1814BN

DAMP ER1814IS



DAMP ER1814WS  
Enlarged for detail



Pendant converts to Semi-Flush Mount



(all finishes)

**NEW!**  
FOR ♦ 2015

# Emery COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ER1508BN/IS/PN/WS	9" H*, 8" W, 8" Dp.	5" D	1-100W Med. Base or 23W CFL
ER1814BN/IS/PN/WS	11.5" H*, 13.5" W, 13.5" Dp.	5" D	1-100W Med. Base or 23W CFL
ER353BN/IS/PN/WS	23.5" H**, 52.5" W, 13" Dp.	9" L x 4.5" W	3-100W Med. Base or 23W CFL

Rod-hung fixtures come with 8' of wire. \*Comes with (2) 12" and (2) 6" Rods. \*\*Comes with (4) 12" and (4) 6" Rods.



# olene COLLECTION

**FINISH:**  
Imperial Silver

**JLE5004IS**





**JLE2812IS**



**JLE1709IS**

**JLE2809IS**



## Jolene COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
<b>JLE1709IS</b>	13.5" H, 9.5" W, 9.5" Dp.	4.5" D	2-60W Cand. Base
<b>JLE2809IS</b>	19" H, 9" W, 9" Dp.	5" D	2-60W Cand. Base
<b>JLE2812IS</b>	22" H, 12" W, 12" Dp.	5" D	3-60W Cand. Base
<b>JLE5004IS</b>	21" H, 20" W, 20" Dp.	4.5" D	4-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain.

# Kendra COLLECTION

**FINISH:**  
Mottled Silver

**SHADE:**  
Oyster Mica

ELONGATED  
CRYSTAL  
DROPS

 **KD5015MM**

QUOIZEL  
**NATURALS**  
**MICA**



# Kendra COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
<b>KD5015MM</b>	53" H, 44" W, 44" Dp.	5.5" D	15-60W Cand. Base	4.5" x 6.5" x 5.5"

Chain-hung fixtures come with 12' of wire and 8' of chain.



# Kendra COLLECTION

**FINISH:**  
Mottled Silver

**SHADE:**  
Oyster Mica

QUOIZEL  
**NATURALS**  
**MICA**

**KD5009MM** DAMP



DAMP **KD5005MM**



DAMP **KD8701MM**



QUOIZEL  
**NATURALS**  
**MICA**

 **KD1507MM**

 **KD2824MM**

 **KD2816MM**

 **KD1716MM**


## Kendra COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	SHADE DIMS.
<b>KD1507MM</b>	12" H <sup>1</sup> , 7" W, 7" Dp.	5.5" D	-	1-100W Med. Base or 23W CFL	5.5" x 7" x 5.5"
<b>KD1716MM</b>	12.5" H, 16" W, 16" Dp.	5.5" D	-	3-60W Med. Base or 13W CFL	13.5" x 5.5"
<b>KD2816MM*</b>	22" H, 17" W, 17" Dp.	5.5" D	-	2-100W Med. Base or 23W CFL	14.5" x 5.5"
<b>KD2824MM*</b>	29" H, 24" W, 24" Dp.	5.5" D	-	4-60W Med. Base or 13W CFL	20" x 7"
<b>KD5005MM*</b>	31" H, 27" W, 27" Dp.	5.5" D	-	5-60W Cand. Base	4.5" x 6.5" x 5.5"
<b>KD5009MM**</b>	39" H, 34" W, 34" Dp.	5.5" D	-	9-60W Cand. Base	4.5" x 6.5" x 5.5"
<b>KD8701MM</b>	13.5" H, 6" W, 10" Dp.	4.5" W x 6.5" H	6.25"	1-60W Cand. Base	4.5" x 6.5" x 5.5"

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixture comes with 12' of wire and 8' of chain.  
 Rod-hung fixture comes with 8' of wire. †Comes with (2) 6" and (2) 12" Rods. Due to natural properties, shade color may vary.

# Kyle COLLECTION

**FINISH:**

**IB** Imperial Bronze

**IN** Iron Gate

**SHADE:**

**IB** Butterscotch Onyx

**IN** White Onyx

QUOIZEL  
**NATURALS**  
**ONYX**



**KY5016IB**



# Kyle COLLECTION

**PRODUCT**

**KY5016IB**

**DIMENSIONS**

48" H, 42" W, 42" Dp.

**CANOPY**

7" D

**BULBS**

16-100W Med. Base or 23W CFL

Chain-hung fixture comes with 12' of wire and 8' of chain.



From the **KYLE COLLECTION:**  
Hanging Fixture: **KY2822IB** Mini Pendant: **KY15071B**  
*Photo courtesy of Devane Design*



# Kyle COLLECTION

**FINISH:**

**IB** Imperial Bronze

**IN** Iron Gate

**SHADE:**

**IB** Butterscotch Onyx

**IN** White Onyx

   **KY5009IN**



 **KY5106IB**



**NEW!**

FOR ♦ 2015

**KY5006IN**  



QUOIZEL  
**NATURALS**  
**ONYX**


**DAMP** KY5103IN

Enlarged for detail



*Quoizel artisans take the natural beauty of onyx and create unique solutions for home lighting.*

**DAMP** KY433IB



**DAMP** KY540IN



QUOIZEL  
**NATURALS**  
**ONYX**

*Kyle* COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
KY433IB*	18.5" H, 33" W, 4.5" Dp.	8" L x 4.5" W	4-100W Med. Base or 23W CFL
KY5006IB/IN*	28" H, 28" W, 28" Dp.	5.5" D	6-100W Med. Base or 23W CFL
KY5009IB/IN**	34.5" H, 35" W, 35" Dp.	5.5" D	9-100W Med. Base or 23W CFL
KY5103IB/IN*	22" H, 20" W, 20" Dp.	5.5" D	3-100W Med. Base or 23W CFL
KY5106IB*	24" H, 24" W, 24" Dp.	5.5" D x 1.25" H	6-100W Med. Base or 23W CFL
KY540IB/IN*	23" H, 40" W, 5.5" Dp.	11.75" L x 4.75" W	5-100W Med. Base or 23W CFL

\*Chain-hung fixtures come with 8' of wire and 4' of chain.

\*\*Chain-hung fixture comes with 12' of wire and 8' of chain. Due to natural properties, shade color may vary.

# Kyle COLLECTION

**FINISH:**

**IB** Imperial Bronze

**IN** Iron Gate

**SHADE:**

**IB** Butterscotch Onyx

**IN** White Onyx

**DAMP** KY5506IB



**DAMP** KY5503IB



**DAMP** KY2822IB



QUOIZEL  
**NATURALS**  
**ONYX**

**KY1716IB** **DAMP**



**KY1404IB** **DAMP**



All Quoizel Track Lights Swivel



**KY8801IN** DAMP

*Enlarged for detail*



DAMP **KY1507IB**



DAMP **KY1508IN**



QUOIZEL  
**NATURALS**  
**ONYX**

**KY6328IB**



DAMP **KY8701IN**

*Xyle*COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
<b>KY1404IB</b>	14.5" H, 36" W, 4.5" Dp.	8.25" L x 4.5" W	-	4-100W Med. Base or 23W CFL
<b>KY1507IB/IN</b>	7" H*, 5" W, 5" Dp.	5" D	-	1-100W Med. Base or 23W CFL
<b>KY1508IB/IN</b>	7" H*, 5" W, 5" Dp.	5" D	-	1-100W Med. Base or 23W CFL
<b>KY1716IB</b>	11" H, 16" W, 16" Dp.	5" D	-	3-100W Med. Base or 23W CFL
<b>KY2822IB</b>	22.5" H, 24" W, 24" Dp.	5.5" D	-	5-75W Med. Base or 18W CFL
<b>KY5503IB</b>	19.5" H, 17" W, 17" Dp.	5.5" D	-	3-100W Med. Base or 23W CFL
<b>KY5506IB</b>	23" H, 23" W, 23" Dp.	5.5" D	-	6-100W Med. Base or 23W CFL
<b>KY6328IB</b>	30" H, 14" W, 14" Dp.	-	-	2-100W Med. Base or 23W CFL
<b>KY8701IB/IN</b>	16" H, 4.5" W, 5.5" Dp.	4.5" W x 8.25" H	9"	1-100W Med. Base or 23W CFL
<b>KY8801IB/IN</b>	11" H, 8.5" W, 4.5" Dp.	4.75" D	5.5"	1-75W Med. Base or 18W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain. \*Comes with (2) 12" and (2) 6" Rods.  
Rod-hung fixtures come with 8' of wire. Due to natural properties, shade color may vary.

# La Parra COLLECTION

**FINISH:**  
Imperial Bronze

**GLASS:**  
Candella Scavo



LP5018IB   



LP5009IB **DAMP** **50**



LP5006IB **DAMP**



LP8601IB **DAMP**

*Enlarged for detail*

## La Parra COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HWCO	BULBS
LP5006IB*	30" H, 28" W, 28" Dp.	9" D	-	6-100W Med. Base or 23W CFL
LP5009IB**	37" H, 30" W, 30" Dp.	9" D	-	9-100W Med. Base or 23W CFL
LP5018IB*	56" H, 47.5" W, 47.5" Dp.	9" D	-	18-100W Med. Base or 23W CFL
LP8601IB	9" H, 5" W, 7" Dp.	5" W x 8" H	4.8"	1-100W Med. Base or 23W CFL

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixture comes with 12' of wire and 8' of chain.

# La Parra COLLECTION

**FINISH:**  
Imperial Bronze

**GLASS:**  
Candella Scavo

**DAMP LP5003IB**



**DAMP LP639IB**



**DAMP LP1505IB**



# La Parra COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
LP1505IB	14.5" H, 5" W, 5" Dp.	5.25" D	1-100W Med. Base or 23W CFL
LP5003IB	23" H, 18.5" W, 18.5" Dp.	9" D	3-100W Med. Base or 23W CFL
LP639IB	46" H, 38" W, 19" Dp.	7" L x 4.5" W	6-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.



From the **LAILA COLLECTION:**  
LLA5006RA



# Laila COLLECTION

**FINISH:**  
Rustic Antique Bronze

LLA5006RA





LLA5205RA



LLA5203RA



LLA5204RA

LLA1615RA DAMPDAMP LLA1508RA

## Laila COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
LLA1508RA*	11.5" H, 8.5" W, 8.5" Dp.	5.5" D	1-100W Med. Base or 23W CFL
LLA1615RA	14.5" H, 15" W, 15" Dp.	8" D	3-60W Cand. Base
LLA5006RA*	30" H, 25" W, 25" Dp.	5.5" D	6-60W Cand. Base
LLA5203RA**	20" H, 15" W, 15" Dp.	5.5" D	3-60W Cand. Base
LLA5204RA**	21" H, 18" W, 18" Dp.	5" D	4-60W Cand. Base
LLA5205RA**	26.5" H, 22" W, 22" Dp.	5.5" D	5-60W Cand. Base

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixtures come with 12' of wire and 8' of chain.

# Marquette COLLECTION

**FINISH:**  
Heirloom

MQ5020HL  



CRYSTAL  
DROPS

## Marquette COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
MQ5020HL	60" H, 50" W, 50" Dp.	9" D	20-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain.



From the **MARQUETTE COLLECTION:**  
MQ5003HL  
*Photo courtesy of Designs on Madison*

# Marquette COLLECTION

**FINISH:**  
Heirloom

MQ5009HL



MQ5006HL



DAMP MQ8701HL






MQ5208HL 



MQ5206HL



 MQ5003HL

# Marquette COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
MQ5003HL*	24" H, 17" W, 17" Dp.	7" D	-	3-60W Cand. Base
MQ5006HL*	38" H, 28" W, 28" Dp.	7" D	-	6-60W Cand. Base
MQ5009HL**	41" H, 32" W, 32" Dp.	7" D	-	9-60W Cand. Base
MQ5206HL**	41.5" H, 20.5" W, 20.5" Dp.	7" D	-	6-60W Cand. Base
MQ5208HL**	55" H, 27" W, 27" Dp.	7" D	-	8-60W Cand. Base
MQ8701HL	21.5" H, 8.5" W, 7.5" Dp.	6" D x 1" Dp	13.75"	1-60W Cand. Base

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixtures come with 12' of wire and 8' of chain.

# MontereyMosaic COLLECTION

**FINISH:**

Malaga


**SHADE:**

Pen Shell Mosaic

QUOIZEL  
**NATURALS**  
**PEN SHELL**

DAMP    MY5016ML

GENUINE  
PEN SHELL



*The Monterey Mosaic Collection is made with Pen Shell and is perfect for those seeking the aesthetics of natural variations. Due to its authenticity, the material may vary from pictured items.*



MY5009ML DAMP



DAMP MY1506ML



MY5103ML DAMP



MY5005ML DAMP

# MontereyMosaicCOLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
MY1506ML	18" H <sup>1</sup> , 6" W, 6" Dp.	5" D	1-100W Med. Base or 23W CFL
MY5005ML*	28.5" H, 25" W, 25" Dp.	5" D	5-100W Med. Base or 23W CFL
MY5009ML**	38" H, 34" W, 34" Dp.	5" D	9-100W Med. Base or 23W CFL
MY5016ML**	52" H, 44" W, 44" Dp.	5" D	16-100W Med. Base or 23W CFL
MY5103ML*	24" H, 24" W, 24" Dp.	5" D	3-100W Med. Base or 23W CFL

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixtures come with 12' of wire and 8' of chain.  
 †Comes with (2) 12" and (2) 6" Rods. Rod-hung fixture comes with 8' of wire.





QUOIZEL  
**NATURALS**  
**PEN SHELL**



*Quoizel artisans take the natural beauty of pen shell and bring the wonder of the ocean to your home décor.*



From the **MONTEREY MOSAIC COLLECTION:**

Mirror: **MY430241ML** Table Lamp: **MY6325ML** Wall Sconce: **MY8801ML** Dinette Fixture: **MY5103ML**

*The Monterey Mosaic Collection is made with Pen Shell and is perfect for those seeking the aesthetics of natural variations. Due to its authenticity, the material may vary from pictured items.*

# MontereyMosaic COLLECTION

**FINISH:**

Malaga

**SHADE:**

Pen Shell Mosaic

**DAMP** MY2816ML



**DAMP** MY2824ML



MY1723ML



MY1718ML **DAMP**



**DAMP** MY1618ML



QUOIZEL  
**NATURALS**  
**PEN SHELL**

**DAMP** MY1613ML



**MY8801ML**



**MY430241ML**



**MY6325ML**



**MY430242ML**



**MY1404ML**

All Quoizel Track Lights Swivel

## MontereyMosaicCOLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	GLASS
<b>MY1404ML</b>	16.5" H, 43.5" W, 5" Dp.	7.25" D	-	4-100W Med. Base or 23W CFL	-
<b>MY1613ML</b>	7" H, 16" W, 16" Dp.	11" D	-	3-60W Med. Base or 13W CFL	-
<b>MY1618ML</b>	7" H, 18" W, 18" Dp.	-	-	4-60W Med. Base or 13W CFL	-
<b>MY1718ML</b>	13" H, 18" W, 18" Dp.	6" D x 2" H	-	4-100W Med. Base or 23W CFL	-
<b>MY1723ML</b>	14" H, 24" W, 24" Dp.	6" D x 2" H	-	5-100W Med. Base or 23W CFL	-
<b>MY2816ML</b>	22" H, 18" W, 18" Dp.	5" D	-	3-100W Med. Base or 23W CFL	-
<b>MY2824ML</b>	28" H, 23.5" W, 23.5" Dp.	5" D	-	4-100W Med. Base or 23W CFL	-
<b>MY430241ML</b>	30" H, 24" W, 1.5" Dp.	-	-	-	Beveled
<b>MY430242ML</b>	30" H, 24" W, 1.5" Dp.	-	-	-	Beveled
<b>MY6325ML</b>	25" H, 18" W, 18" Dp.	-	-	3-60W Med. Base or 13W CFL	-
<b>MY8801ML</b>	12" H, 9" W, 5" Dp.	4.5" W x 7" H	4.75"	2-60W Cand. Base	-

Chain-hung fixtures come with 8' of wire and 4' of chain. Due to natural properties, shade color may vary.

# New England COLLECTION

**FINISH:**

**BN** Brushed Nickel

**PN** Palladian Bronze

**GLASS:**

Acid Etched

NA5103BN DAMP



*This collection gives a nod to timeless nautical style of the magnificent ocean liners of the 20's and 30's, but is updated for today's homes. A handsome classic that is always in fashion.*



NA1716BN DAMP



DAMP NA1616BN



NA1514BN DAMP

DAMP NA1510BN



NA8409PN WET

**NEW!**  
FOR ♦ 2015

INDOOR  
OUTDOOR

WET NA8414PN



## NewEngland COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
NA1510BN	11" H*, 9.5" W, 9.5" Dp.	5.25" D	-	1-100W Med. Base or 23W CFL
NA1514BN	9.5" H*, 14" W, 14" Dp.	5.25" D	-	1-100W Med. Base or 23W CFL
NA1616BN	6" H, 16" W, 16" Dp.	-	-	3-60W Med. Base or 13W CFL
NA1716BN	13.5" H, 16" W, 16" Dp.	5" D	-	3-100W Med. Base or 23W CFL
NA5103BN	22.5" H, 25" W, 25" Dp.	5" D	-	3-100W Med. Base or 23W CFL
NA8409PN	9.5" H, 9.5" W, 10" Dp.	5.25" D	4.5"	1-100W Med. Base or 23W CFL
NA8414PN	11.5" H, 14.5" W, 15.5" Dp.	7" D	5.5"	1-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire.  
\*Comes with (2) 12" and (2) 6" Rods.

# Riverside COLLECTION

**FINISH:**

Polished Antique Nickel

**GLASS:**

Etched Painted White Inside

Opal Etched (RVE5005PA and RVE5009PA)

RVE5009PA 



RVE5005PA  RVE5103PARVE1508PA  RVE2820PA RVE1716PA

## Riverside COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
RVE1508PA <sup>†</sup>	12.5" H*, 9" W, 9" Dp.	5.5" D	1-100W Med. Base or 23W CFL
RVE1716PA	13" H, 17" W, 17" Dp.	6" D	3-100W Med. Base or 23W CFL
RVE2820PA <sup>†</sup>	21.5" H*, 20.5" W, 20.5" Dp.	5.5" D	4-100W Med. Base or 23W CFL
RVE5005PA <sup>†</sup>	20" H, 24** W, 24" Dp.	5.5" D	5-100W Med. Base or 23W CFL
RVE5009PA <sup>††</sup>	32" H*, 32" W, 32" Dp.	5.5" D	9-100W Med. Base or 23W CFL
RVE5103PA <sup>†</sup>	19" H*, 23.5" W, 23.5" Dp.	5.5" D	3-100W Med. Base or 23W CFL

\*Comes with (2) 12" and (2) 6" Rods. <sup>†</sup>Rod-hung fixtures come with 8' of wire.

<sup>††</sup>Rod-hung fixture comes with 12' of wire.



# Sophia COLLECTION

**FINISH:**

**BN** Brushed Nickel

**PN** Palladian Bronze

**GLASS:**

Etched Glass Painted White Inside

SPH5009BN DAMP



## Sophia COLLECTION

**PRODUCT**

SPH5009BN/PN

**DIMENSIONS**

33.5" H, 32" W, 32" Dp.

**CANOPY/BACKPLATE**

5.75" D

**BULBS**

9-100W Med. Base or 23W CFL

All chain-hung fixtures come with 12' of wire and 8' of chain.



From the **SOPHIA COLLECTION:**  
SPH5009PN

# Sophia COLLECTION

**FINISH:**

- BN** Brushed Nickel
- PN** Palladian Bronze

**GLASS:**

Etched Glass Painted White Inside

**DAMP** SPH5005BN



**DAMP** SPH8701BN

*Enlarged for detail*



**DAMP** SPH1508PN



**DAMP** SPH8703BN

*All Sophia bath fixtures can be mounted as uplights or downlights.*



**DAMP** SPH8702BN

**DAMP** SPH8704BN

# Sophia COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
SPH1508BN/PN	13" H*, 8" W, 8" Dp.	5.75" D	-	1-100W Med. Base or 23W CFL
SPH5005BN/PN	23" H, 26.5" W, 26.5" Dp.	5.5" D	-	5-100W Med. Base or 23W CFL
SPH8701BN	10.5" H, 6" W, 8.5" Dp.	5" W x 7" H	7"	1-100W Med. Base or 23W CFL
SPH8702BN	9" H, 16" W, 8" Dp.	7" W x 4.75" H	8"	2-100W Med. Base or 23W CFL
SPH8703BN	9" H, 25" W, 8" Dp.	7" W x 4.75" H	8"	3-100W Med. Base or 23W CFL
SPH8704BN	9" H, 35" W, 8" Dp.	7" W x 4.75" H	8"	4-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire. \*Comes with (2) 12" and (2) 6" Rods.

# Taylor COLLECTION

COLLECTIONS

**FINISH:**

**AN** Antique Nickel

**WT** Western Bronze

**GLASS:**

Opal Etched



TY5005AN DAMP

# Taylor COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS
TY5005AN	20" H*, 25" W, 25" Dp.	5.5" D x 0.875" H	5-100W Med. Base or 23W CFL

\*Comes with (2) 12" and (2) 6" Rods. Rod-hung fixtures come with 8' of wire.





From the **TAYLOR COLLECTION**  
Mirror: **TY43625AN** Wall Fixture: **TY8501AN** Chandelier: **TY5005AN**

# Taylor COLLECTION

**FINISH:**

- AN** Antique Nickel
- WT** Western Bronze
- C** Polished Chrome

**GLASS:**

Opal Etched

**TY628AN**



**TY1716WT**



**TY1721AN**



**TY1504AN**



**TY8501AN**



**TY1404AN**



All Quoizel Track Lights Swivel





**TY43625AN**

**DAMP TY8601C**

*Enlarged for detail*

*All Taylor bath fixtures can be mounted as uplights or downlights.*



**TY8602C** **DAMP**



**DAMP TY8603C**

*Taylor bath fixtures are also available in Antique Nickel and Western Bronze finishes.*



**DAMP TY8604C**



# Taylor COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	GLASS
<b>TY1404AN</b>	8.5" H, 43" W, 3" Dp.	9" L x 4.75" W x .875" H	-	4-60W Frosted G9 Halogen†	-
<b>TY1504AN</b>	14.5" H*, 4" W, 4" Dp.	5.5" D x .875" H	-	1-100W Med. Base or 23W CFL	-
<b>TY1716AN/WT</b>	11.5" H, 16.5" W, 16.5" Dp.	5.5" D x .875" H	-	3-100W Med. Base or 23W CFL	Etched Painted White Inside
<b>TY1721AN</b>	13.5" H, 21" W, 21" Dp.	5.5" D x .875" H	-	4-100W Med. Base or 23W CFL	Etched Painted White Inside
<b>TY43625AN</b>	35.5" H, 25.5" W, 2" Dp.	-	-	-	Beveled
<b>TY628AN</b>	16.5" H**, 28" W, 16" Dp.	9" L x 4.75" W x .875" H	-	6-100W Med. Base or 23W CFL	-
<b>TY8501AN</b>	19.5" H, 5.5" W, 5" Dp.	5.5" D x .875" Dp.	10"	1-100W Med. Base or 23W CFL	-
<b>TY8601AN/C/WT</b>	7.5" H, 4.5" W, 5.5" Dp.	4.5" W x 5" H	5"	1-100W Med. Base or 23W CFL	-
<b>TY8602AN/C/WT</b>	7.5" H, 13.5" W, 4.5" Dp.	7" W x 4.5" H	5.5"	2-100W Med. Base or 23W CFL	-
<b>TY8603AN/C/WT</b>	7.5" H, 21" W, 5.5" Dp.	7" W x 4.5" H	5.5"	3-100W Med. Base or 23W CFL	-
<b>TY8604AN/C/WT</b>	7.5" H, 30" W, 5.5" Dp.	7" W x 4.5" H	5.5"	4-100W Med. Base or 23W CFL	-

Rod-hung fixtures come with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods. \*\*Comes with (4) 6" and (4) 12" Rods.

†Bulbs Supplied.



# Trilogy COLLECTION

**FINISH:**  
Old Bronze


**GLASS:**  
Clear Seedy

TRG5105OZ DAMP

**NEW!**

FOR ♦ 2015

VINTAGE STYLE  
bulb included



CLEAR  
SEEDY  
GLASS



## Trilogy COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
TRG5105OZ	9" H, 26.5" W, 26.5" Dp.	5" D	5-60W Vintage Bulb (Supplied)* or 23W CFL

Chain-hung fixture comes with 8' of wire and 4' of chain. \*Max Wattage: 100W Med. Base or 23W CFL



From the **TRIOLOGY COLLECTION:**  
**TRG51030Z**

# Trilogy COLLECTION


**FINISH:**  
Old Bronze

**GLASS:**  
Clear Seedy

**DAMP** TRG5103OZ



**DAMP** TRG1508OZ



**VINTAGE STYLE**  
bulb included



**TRG8701OZ**

*Enlarged for detail*

**DAMP** TRG1816OZ



**DAMP** TRG1716OZ



**DAMP** TRG1712OZ



## Trilogy COLLECTION



PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
TRG1508OZ	7.5" H*, 8" W, 8" Dp.	5" D	-	1-60W Vintage Bulb (Supplied)**
TRG1712OZ	10" H, 12" W, 12" Dp.	5" D	-	1-60W Vintage Bulb (Supplied)**
TRG1716OZ	12" H, 16" W, 16" Dp.	5" D	-	3-60W Vintage Bulb (Supplied)**
TRG1816OZ	20" H, 16" W, 16" Dp.	5" D	-	3-60W Vintage Bulb (Supplied)**
TRG5103OZ	17.5" H, 22" W, 22" Dp.	5" D	-	3-60W Vintage Bulb (Supplied)**
TRG8701OZ	9.5" H, 8" W, 9" Dp.	5" D	3"	1-60W Vintage Bulb (Supplied)**

All chain-hung fixtures come with 8' of wire and 4' of chain. \*Comes with (2) 6" and (2) 12" Rods. Rod-hung fixtures come with 8' of wire. \*\*Max Wattage: 100W Med. Base or 23W CFL.

# Whitney COLLECTION

**FINISH:**  
Imperial Silver

**SHADE:**  
White Organza with Dark Grey Trim

WHI5012IS  





WHI5009IS

CRYSTAL  
DROPS



WHI5005IS

# Whitney COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
WHI5005IS*	27" H, 28" W, 28" Dp.	6.5" D	5-60W Cand. Base	4.5" x 5" x 5"
WHI5009IS**	33" H, 32" W, 32" Dp.	6" D	9-60W Cand. Base	4.5" x 5" x 5"
WHI5012IS**	38" H, 39" W, 39" Dp.	6" D	12-60W Cand. Base	4.5" x 5" x 5"

\*Chain-hung fixture comes with 8' of wire and 4' of chain. \*\*Chain-hung fixtures come with 12' of wire and 8' of chain.

# Whitney COLLECTION

**FINISH:**

Imperial Silver

**SHADE:**

White Organza with Dark Grey Trim



**WHI8701IS**

**WHI5003IS**



**WHI1716IS** DAMP

# Whitney COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	SHADE DIMS.
<b>WHI1716IS</b>	16.5" H, 16" W, 16" Dp.	6" D	-	3-60W Cand. Base	14.5" x 16" x 6"
<b>WHI5003IS</b>	26" H, 16" W, 16" Dp.	6" D	-	3-60W Cand. Base	5" x 5"
<b>WHI8701IS</b>	16" H, 7" W, 7" Dp.	4.5" W x 7" H	12"	1-60W Cand. Base	4.5" x 5" x 5"

Chain-hung fixtures come with 8' of wire and 4' of chain.

M

INI-COLLECTIONS

QUOIZEL



From the **UNION STATION COLLECTION**: UST5003WT (p.122)



# Noble COLLECTION

**FINISH:**  
Rustic Black

NBE5009RK

SOLID WOOD  
CANDLE  
HOLDERS



**NBE5008RK**



**NBE8702RK**

**NBE5303RK**



**NBE5005RK**



*Noble* COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
NBE5005RK*	25.5" H, 24" W, 24" Dp.	5" D x 1" H	-	5-60W Cand. Base
NBE5008RK*	31" H, 32" W, 32" Dp.	5" D	-	8-60W Cand. Base
NBE5009RK**	36" H, 32" W, 32" Dp.	5" D	-	9-60W Cand. Base
NBE5303RK*	19.5" H, 15" W, 15" Dp.	5" D	-	3-60W Cand. Base
NBE8702RK	13" H, 11.5" W, 8" Dp.	5" D	2.5"	2-60W Cand. Base

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixture comes with 12' of wire and 8' of chain.

# UnionStationCOLLECTION

**FINISH:**

Western Bronze

**SHADE:**

Metal Mesh

**VINTAGE STYLE**  
bulb included



**DAMP** UST5003WT




BRASS  
ACCENTS



UST6127WT

**NEW!**  
FOR ♦ 2015



DAMP UST1505WT

UST1716WT



## UnionStation COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
UST1505WT	8" H*, 5" W, 5" Dp.	5" D	1-60W Vintage Bulbs (Supplied)**	-
UST1716WT	11.5" H, 16" W, 16" Dp.	5.5" D	3-60W Vintage Bulbs (Supplied)**	-
UST5003WT	20" H, 28" W, 28" Dp.	5" D	3-60W Vintage Bulbs + 1-50W MR-16 w/GU10 Base Shielded (Supplied)**	-
UST6127WT	26.5" H, 15.5" W, 15.5" Dp.	-	1-60W Vintage Bulbs (Supplied)**	15.5" x 15.5" x 9"

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.  
\*\*Max Wattage: 100W Med. Base or 23W CFL.

# Alexandria COLLECTION

**FINISH:**  
Palladian Bronze

**AX2826PN**

DANGUNG  
GLASS  
ACCENTS

**NEW!**  
FOR ♦ 2015

**AX2820PN**



**AX434PN**



# Alexandria COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
AX2820PN	8" H*, 20" W, 20" Dp.	5" D x 0.75" H	5-100W Med. Base or 23W CFL
AX2826PN	14" H*, 26" W, 26" Dp.	5" D x 0.75" H	6-100W Med. Base or 23W CFL
AX434PN	8" H**, 34" W, 15" Dp.	19.25" L x 4.5" W	4-100W Med. Base or 23W CFL

Rod-hung fixtures come with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods. \*\*Comes with (4) 6" and (4) 12" Rods.

# Genova COLLECTION

MINI-COLLECTIONS

**FINISH:**

Stonehedge

**GLASS:**

Twisted Amber Scavo

**DAMP** GE5006SE



GE5103SE **DAMP**



**DAMP** GE1507SE



# Genova COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
GE1507SE	12.5" H*, 7" W, 7" Dp.	5.5" D	1-100W Med. Base or 23W CFL
GE5006SE	27" H, 26" W, 26" Dp.	8.5" D	6-100W Med. Base or 23W CFL
GE5103SE	22" H, 23" W, 23" Dp.	5" D	3-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.

# Cabin COLLECTION

**FINISH:**

Latte

**DAMP** CBN5204LT



**DAMP** CBN5202LT



**NEW!**

FOR ♦ 2015

**DAMP** CBN1612LT

# Cabin COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
CBN1612LT	6" H, 12" W, 12" Dp.	-	2-60W Med. Base or 13W CFL	Clear Seedy
CBN5202LT	16.5" H, 8.5" W, 8.5" Dp.	6" D	2-60W Cand. Base	-
CBN5204LT	26.5" H, 15" W, 15" Dp.	6" D	4-60W Cand. Base	-

Chain-hung fixtures come with 12' of wire and 8' of chain.

# Castile COLLECTION

MINI-COLLECTIONS

**FINISH:**  
Rustic Black

**NEW!**  
FOR ♦ 2015

QUOIZEL  
**NATURALS**  
**WOOD**

CS5012RK



CS5006RK



DAMP CS1718RK

# Castile COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
CS1718RK	15.5" H, 18" W, 18" Dp.	5" D x 0.75" H	4-60W Cand. Base
CS5006RK*	22.5" H, 29" W, 29" Dp.	5" D x 0.75" H	6-60W Cand. Base
CS5012RK**	27" H, 35.5" W, 35.5" Dp.	6.5" D x 1.25" H	12-60W Cand. Base

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixtures come with 12' of wire and 8' of chain.



# Tricia COLLECTION

**FINISH:**  
Vintage Silver

  TCA5009VP



GLASS  
DROPS



TCA8701VP DAMP

TCA5006VP



TCA5004VP

*Tricia* COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
TCA5004VP*	31.5" H, 21" W, 21" Dp.	7" D	-	4-60W Cand. Base
TCA5006VP*	36" H, 27" W, 27" Dp.	7" D	-	6-60W Cand. Base
TCA5009VP**	41.5" H, 31" W, 31" Dp.	7" D	-	9-60W Cand. Base
TCA8701VP	24.5" H, 3" W, 6.5" Dp.	4.5" W x 11.5" H	9.5"	1-60W Cand. Base

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixtures come with 12' of wire and 8' of chain.

# Eastvale COLLECTION

**FINISH:**  
Palladian Bronze


**SHADE:**  
Metal

Pendant converts  
to Semi-Flush Mount



**EVE240PN**

**EVE2815PN**



RIBBED  
GLASS  
DIFFUSER

**EVE1508PN**

**EVE1404PN**

All Quoizel Track Lights Swivel

# Eastvale COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
EVE1404PN	10.5" H, 36.5" W, 3.5" Dp.	7" L x 5" W	4-50W MR-16 with GU10 Base Shielded (Supplied)
EVE1508PN <sup>†</sup>	9.5" H*, 8" W, 8" Dp.	6" D	1-100W Med. Base or 23W CFL
EVE240PN <sup>††</sup>	29" H*, 40" W, 14.5" Dp.	6" D	2-100W Med. Base or 23W CFL
EVE2815PN <sup>†</sup>	12" H*, 14.5" W, 14.5" Dp.	6" D	1-100W Med. Base or 23W CFL

<sup>†</sup>Rod-hung fixtures come with 8' of wire. <sup>††</sup>Rod-hung fixtures come with 12' of wire. \*Comes with (2) 6" and (2) 12" Rods.

# Baron COLLECTION

MINI-COLLECTIONS

**FINISH:**  
Marcado Black

QUOIZEL  
**NATURALS**  
**WOOD**



**BRO5203MK**

**NEW!**  
FOR ♦ 2015



**BRO5204MK**



**BRO1715MK** DAMP

# Baron COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
<b>BRO1715MK</b>	14.5" H, 15" W, 15" Dp.	5" D	3-60W Cand. Base
<b>BRO5203MK</b>	26.5" H, 15.5" W, 15.5" Dp.	5" D	3-60W Cand. Base
<b>BRO5204MK</b>	38" H, 18" W, 18" Dp.	5" D	6-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain.

# Grant COLLECTION

**FINISH:**

**BN** Brushed Nickel

**IS** Imperial Silver

**PN** Palladian Bronze

**WS** Weathered Brass **NEW!**

**GLASS:**

Opal Etched

**GRT5103BN** DAMP





**Grant** COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
GRT5103BN/IS/PN/WS	15" H*, 24" W, 24" Dp.	5" D	3-100W Med. Base or 23W CFL

Rod-hung fixtures come with 8' of wire. \*Comes with 2 (6)" and (2) 12" Rods.

# Grant COLLECTION

**FINISH:**

**BN** Brushed Nickel

**IS** Imperial Silver

**PN** Palladian Bronze

**WS** Weathered Brass **NEW!**

**GLASS:**

Opal Etched


**DAMP** GRT1508IS



**DAMP** GRT2814PN



**DAMP** GRT2814BN



**DAMP** GRT1508WS



**NEW!**  
FOR ♦ 2015

# Grant COLLECTION

**PRODUCT**

GRT1508BN/IS/PN/WS

**DIMENSIONS**

9.5" H\*, 8" W, 8" Dp.

**CANOPY**

5" D

**BULBS**

1-100W Med. Base or 23W CFL

GRT2814BN/IS/PN/WS

11.5" H\*, 13.5" W, 13.5" Dp.

5" D

1-100W Med. Base or 23W CFL

Rod-hung fixtures come with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.

# New Harbor COLLECTION

MINI-COLLECTIONS

**FINISH:**  
Western Bronze

**DAMP** NHR1718WT



**DAMP** NHR5204WT



**VINTAGE STYLE**  
bulb included



**DAMP** NHR538WT

# New Harbor COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS
NHR1718WT	10.5" H, 18" W, 18" Dp.	4.75" D	4-60W Vintage Bulbs (Supplied)
NHR5204WT <sup>†</sup>	23.5" H*, 14" W, 14" Dp.	5" Sq.	4-60W Vintage Bulbs (Supplied)
NHR538WT <sup>††</sup>	9.5" H**, 38" W, 12" Dp.	9" L x 4.75" W x .75" H	5-60W Vintage Bulbs (Supplied)

\*Comes with (2) 6" and (2) 12" Rods. \*\*Comes with (4) 6" and (4) 12" Rods. †Rod-hung fixture comes with 12' of wire. ††Rod-hung fixture comes with 8' of wire. Max Wattage: 100W Med. Base or 23W CFL.





From the **MILBANK COLLECTION:**  
**MBK5005VG**

# Milbank COLLECTION

MINI-COLLECTIONS

**FINISH:**  
Vintage Gold

**GLASS:**  
Opal Etched

**DAMP MBK5005VG**



**MBK2820VG DAMP**



**DAMP MBK1716VG**



# Milbank COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS
MBK1716VG	11" H, 16" W, 16" Dp.	5.5" D	3-100W Med. Base or 23W CFL
MBK2820VG	26" H, 20.5" W, 20.5" Dp.	5.5" D	4-100W Med. Base or 23W CFL
MBK5005VG	26.5" H, 25" W, 25" Dp.	5.25" D	5-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.

# Palmer COLLECTION

**FINISH:**

Palladian Bronze

**SHADE:**

Outer: Light Amber Organza  
Inner: Brown Trim and Etched

PLR5005PN



PLR2820PN DAMP



DAMP PLR1716PN



# Palmer COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS
PLR1716PN	14.5" H, 16" W, 16" Dp.	4.25" D	3-100W Med. Base or 23W CFL
PLR2820PN	23.5" H, 20" W, 20" Dp.	5" D	3-100W Med. Base or 23W CFL
PLR5005PN	21" H, 25" W, 25" Dp.	5" D	5-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain.

# RemiCOLLECTION

MINI-COLLECTIONS

**FINISH:**  
Polished Chrome

**SHADE:**  
White Fabric

**REM345C** DAMP



DAMP **REM5004C**



DAMP **REM8701C**

*Enlarged for detail*

# RemiCOLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	SHADE DIMS.
REM345C	10" H, 44.5" W, 5.5" Dp.	18" L x 4.5" W	-	3-75W Med. Base or 18W CFL	10.5" x 5.5" x 6"
REM5004C	13.5" H*, 29" W, 29" Dp.	4.5" Sq.	-	4-75W Med. Base or 18W CFL	10.5" x 5.5" x 6"
REM8701C	11" H, 10.5" W, 6.5" Dp.	4.5" Sq.	8.5"	1-60W Med. Base or 13W CFL	10.5" x 5.5" x 6"

\*Comes with (2) 6" and (2) 12" Rods. Cable-hung fixtures come with 12' of wire.

# Wesley COLLECTION

**FINISH:**  
Italian Fresco

**GLASS:**  
India Scavo

 WSY5012IF



**WSY5008IF**



**DAMP WSY1716IF**



**WSY5003IF**



**WSY5005IF**



**Wesley** COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS
<b>WSY1716IF</b>	12.5" H, 16" W, 16" Dp.	5.5" D	3-100W Med. Base or 23W CFL
<b>WSY5003IF*</b>	20" H, 18" W, 18" Dp.	5" D	3-60W Cand. Base
<b>WSY5005IF*</b>	27" H, 26" W, 26" Dp.	5" D	5-60W Cand. Base
<b>WSY5008IF*</b>	30" H, 30" W, 30" Dp.	5.5" D	8-60W Cand. Base
<b>WSY5012IF**</b>	36" H, 36" W, 36" Dp.	7" D	12-60W Cand. Base

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixture comes with 12' of wire and 8' of chain.

# Wilder COLLECTION

**FINISH:**

Mottled Black

**WLR2820MB**





**WLR5204MB** DAMP



DAMP **WLR1506MB**



DAMP **WLR1716MB**

## Wilder COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
WLR1506MB	8.5" H*, 6" W, 6" Dp.	5" D	1-60W Vintage Bulb (Supplied)
WLR1716MB	13.5" H, 16" W, 16" Dp.	5" D	3-60W Vintage Bulbs (Supplied)
WLR2820MB†	24.5" H, 20.5" W, 20.5" Dp.	5" D	4-60W Vintage Bulbs (Supplied)
WLR5204MB††	33" H, 16" W, 16" Dp.	5" D	4-60W Vintage Bulbs (Supplied)

†Chain-hung fixture comes with 8' of wire and 4' of chain. ††Chain-hung fixtures come with 12' of wire and 8' of chain. Rod-hung fixtures come with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods. Max Wattage: 100W Med Base or 23W CFL.



# Favern COLLECTION

**FINISH:**

Darkest Bronze

VINTAGE STYLE  
bulb included



DAMP TVN5005DK



QUOIZEL  
NATURALS  
WOOD

DAMP TVN232DK



DAMP TVN1717DK

# Favern COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
TVN1717DK	14.5" H, 17" W, 17" Dp.	5.5" D	3-60W Vintage Bulbs (Supplied)
TVN232DK	10.5" H*, 32" W, 12" Dp.	10.5" L x 4.5" W	6-60W Vintage Bulbs (Supplied)
TVN5005DK	13" H**, 26" W, 26" Dp.	6" D	5-60W Vintage Bulbs (Supplied)

Rod-hung fixtures come with 8' of wire. \*Comes with (4) 6" and (4) 12" Rods. \*\*Comes with (2) 6" and (2) 12" Rods.  
Max Wattage: 100W Med. Base or 23W CFL.

# PLATINUM

by QUOIZEL



From the **ABODE COLLECTION:**  
PCAE2820C (p.156)

# Bordeaux COLLECTION

**FINISH:**

Polished Chrome

**BRX2818C**

*Pendant converts to Semi-Flush Mount*

**NEW!**  
FOR ♦ 2015



**BRX1619C**



**BRX1614C**

*This product will be available in September 2015*

**PLATINUM**  
by QUOIZEL

CRYSTAL ♦ COLLECTION



**BRX1626C**

**NEW!**  
FOR ♦ 2015

# Bordeaux COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
BRX1614C	8" H, 14" W, 14" Dp.	14" D	4-40W Clear G9 Xenon*
BRX1619C	9" H, 19.5" W, 19.5" Dp.	17" D x 1" H	5-40W Clear G9 Xenon*
BRX1626C	8.5" H, 25.5" W, 25.5" Dp.	23.5" D x 1" H	7-40W Clear G9 Xenon*
BRX2818C	8" H, 17.5" W, 17.5" Dp.	4.75" D x 1" H	5-40W Clear G9 Xenon*

\*Bulb Supplied.

CRYSTAL ♦ COLLECTION

- ◆ Dramatic lighting created by faceted crystal pendants
- ◆ Free of contaminant colors such as iron for clarity and purity allowing the light to radiate to its greatest potential
- ◆ Bulbs are positioned in the most strategic locations, maximizing the radiance of the light emanating through the crystal
- ◆ Highly polished mirrored chrome maximizes the reflectivity of the projected light
- ◆ The highest quality G4 and G9 bulbs create a great intensity of light

*S*himmer

**FINISH:** Polished Chrome  
**SHADE:** Crystal Studded

DAMP **PCSR1716C**



See matching bath products on page 401

*A*ura

**FINISH:** Polished Chrome

Pendant converts to Semi-Flush Mount



**PCAR2818C** DAMP

DAMP **PRN1614C**



**NEW!**  
FOR ♦ 2015

*P*aragon

**FINISH:** Polished Chrome

See matching bath products on page 402

PRODUCT	DIMENSIONS	CANOPY	BULBS
<b>PCAR2818C</b>	17" H*, 18" W, 18" Dp.	5" D	4-40W Clear G9 Xenon**
<b>PCSR1716C</b>	7" H, 18" W, 18" Dp.	4.5" D	3-40W Clear G9 Xenon**
<b>PRN1614C</b>	6" H, 14.5" W, 14.5" Dp.	-	4-40W Clear G9 Xenon**

\*Comes with (2) 6" and (2) 12" Rods. Rod-hung fixtures come with 8' of wire. \*\*Bulb Supplied.

DAMP BMT1617C



*Seaumont*  
FINISH: Polished Chrome

DAMP PCCT1623C



*Countess*  
FINISH: Polished Chrome



PCCT1616C DAMP

DAMP EMP1623C

*Empress*  
FINISH: Polished Chrome




DAMP EMP1616C



PRODUCT	DIMENSIONS	CANOPY	BULBS
BMT1617C	11" H, 18" W, 18" Dp.	14" D	9-20W Clear G4 Xenon*
EMP1616C	6" H, 16" W, 16" Dp.	14" D	9-20W Clear G4 Xenon*
EMP1623C	10" H, 23.5" W, 23.5" Dp.	21.75" D	18-20W Clear G4 Xenon*
PCCT1616C	8.5" H, 16.5" W, 16.5" Dp.	13.75" D	9-20W Clear G4 Xenon*
PCCT1623C	8" H, 23" W, 23" Dp.	19.5" D	18-20W Clear G4 Xenon*

\*Bulb Supplied.



PCGX1826C **50**



PCGX1817C

**Galaxy**  
FINISH: Polished Chrome

**NEW!**  
FOR ♦ 2015

**PLATINUM**  
by QUOIZEL  
CRYSTAL ♦ COLLECTION

**Valla**  
FINISH: Polished Chrome



**VLA1618C**  
*Enlarged for detail*

**VLA2820C**

*Pendant converts to Semi-Flush Mount*



PRODUCT	DIMENSIONS	CANOPY	BULBS
PCGX1817C	38" H, 17.5" W, 17.5" Dp.	5.875" D	5-50W MR-16 with GU10 Base Shielded*
PCGX1826C	53" H, 26" W, 26" Dp.	5.875" D	7-50W MR-16 with GU10 Base Shielded*
VLA1618C	7.5" H, 18.5" W, 18.5" Dp.	13.75" Sq.	9-20W Clear G4 Xenon*
VLA2820C	10" H, 20" W, 20" Dp.	4.75" D x 1" H	6-40W Clear G9 Xenon*

\*Bulb Supplied.



# Highrise

FINISH: Polished Chrome



**NEW!**  
FOR ♦ 2015

DAMP **PCHE1620C**



DAMP **PCHE1616C**

**PLATINUM**  
by QUOIZEL

CRYSTAL ♦ COLLECTION



# Ella

FINISH: Polished Chrome

DAMP **PCEL1623C**

**PCJL2820C**



# Janelle

FINISH: Polished Chrome

**PCEL1616C** DAMP

	PCJL2820C	PCHE1616C	PCHE1620C
Lumens	1080	2040	3080
Total Watts	12W	24W	37W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	3100K	3000K	3000K
Dimmable	No	Yes	Yes


PRODUCT	DIMENSIONS	CANOPY	BULBS/LIGHT SOURCE
<b>PCEL1616C</b>	14" H, 16.5" W, 16.5" Dp.	14" D	9-20W Clear G4 Xenon**
<b>PCEL1623C</b>	18" H, 23" W, 23" Dp.	19.5" D	18-20W Clear G4 Xenon**
<b>PCHE1616C</b>	10.5" H, 16" W, 16" Dp.	13.75" D	See LED chart
<b>PCHE1620C</b>	10.5" H, 20" W, 20" Dp.	18" D	See LED chart
<b>PCJL2820C</b>	14.5" H*, 20" W, 20" Dp.	5" D	3-100W Med. Base or 23W CFL + LED (Optic Crystal Ring only)

\*Comes with (2) 6" and (2) 12" rods. Rod-hung fixtures come with 8' of wire. \*\*Bulb Supplied.

*Taper*

**FINISH:** Polished Chrome  
**SHADE:** Clear Crystal

**PCTR1502C**



**PCSP2823C**

*Pendant converts to Semi-Flush Mount*

*Superior*

**FINISH:** Polished Chrome

**PCTR1816C**

*Pendant converts to Semi-Flush Mount*



**PCSP1718C** DAMP

**PLATINUM**  
by QUOIZEL  
CRYSTAL ♦ COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
PCSP1718C	15.5" H, 18" W, 18" Dp.	5" D	4-40W Clear G9 Xenon**
PCSP2823C	23.5" H*, 23" W, 23" Dp.	6" D	6-40W Clear G9 Xenon**
PCTR1502C	8.5" H, 1.5" W, 1.5" Dp.	5" D	1-20W Clear G4 Xenon**
PCTR1816C	8.5" H, 16" W, 16" Dp.	14" D	6-20W Clear G4 Xenon**

\*Comes with (2) 12" and (2) 6" Rods. Rod-hung fixtures come with 8' of wire. \*\*Bulb Supplied.



# Ribbons COLLECTION

**NEW!**  
FOR 2015

**FINISH:**  
Crystal Chrome

**RBN2823CRC**



**RBN2831CRC**



*All Ribbons pendants (all finishes)  
convert to Semi-Flush Mounts*

**PLATINUM**  
by QUOIZEL  
CRYSTAL ♦ COLLECTION



**RBN2817CRC**

**RBN1512CRC**



DAMP RBN1616CRC




**PLATINUM**  
by QUOIZEL  
CRYSTAL ♦ COLLECTION



DAMP RBN1622CRC

DAMP RBN1628CRC



*Playful swirls  
and crystal  
accents make  
Ribbons an  
elegant must  
for the  
distinguished  
home décor.*



**Ribbons** COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
RBN1512CRC	12" H, 12" W, 12" Dp.	5" D x 1" H	3-50W Clear G9 Xenon*
RBN1616CRC	9.5" H, 18.5" W, 18.5" Dp.	4.75" D	4-40W Clear G9 Xenon*
RBN1622CRC	11" H, 22" W, 22" Dp.	5.75" D	5-40W Clear G9 Xenon*
RBN1628CRC	16" H, 27.5" W, 27.5" Dp.	8" D	6-40W Clear G9 Xenon*
RBN2817CRC	17" H, 17" W, 17" Dp.	4.75" D x 1" H	5-40W Clear G9 Xenon*
RBN2823CRC	23" H, 23" W, 23" Dp.	4.75" D x 1" H	12-40W Clear G9 Xenon*
RBN2831CRC	31" H, 31" W, 31" Dp.	4.75" D x 1" H	12-40W Clear G9 Xenon*

\*Bulb Supplied.

# Ribbons COLLECTION

**FINISH:**

**C** Polished Chrome

**MN** Millenia

**SG** Satin Copper


**W** White Lustre **NEW!**

**WT** Western Bronze **NEW!**

**PLATINUM**  
by QUOIZEL

**RBN2831WT**

*All Ribbons pendants (all finishes)  
convert to Semi-Flush Mounts*






RBN1512SG

**NEW!**  
FOR ♦ 2015

RBN2817W



DAMP RBN1616WT



**PLATINUM**  
by QUOIZEL

**NEW!**  
FOR ♦ 2015

RBN2823MN



RBN1622MN DAMP



DAMP RBN1628W

**Ribbons** COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
RBN1512C/MN/SG/W/WT	12" H, 12" W, 12" Dp.	5" D x 1" H	3-50W Frosted G9 Xenon*
RBN1616C/MN/SG/W/WT	8" H, 16.5" W, 16.5" Dp.	4.75" D	4-40W Frosted G9 Xenon*
RBN1622C/MN/SG/W/WT	11" H, 22" W, 22" Dp.	5.75" D	5-40W Frosted G9 Xenon*
RBN1628C/MN/SG/W/WT	16" H, 27.5" W, 27.5" Dp.	8" D	6-40W Frosted G9 Xenon*
RBN2817C/MN/SG/W/WT	17" H, 17" W, 17" Dp.	4.75" D x 1" H	5-40W Frosted G9 Xenon*
RBN2823C/MN/SG/W/WT	23" H, 23" W, 23" Dp.	4.75" D x 1" H	12-40W Frosted G9 Xenon*
RBN2831C/MN/SG/W/WT	31" H, 31" W, 31" Dp.	4.75" D x 1" H	12-40W Frosted G9 Xenon*

\*Bulb Supplied.

# Cascade

**FINISH:** Polished Chrome

**SHADE:** C Black Fabric

C1 White Fabric

PCAE2820C

PCCS2824C

PCCS2816C1

# Abode

**FINISH:** Polished Chrome

**SHADE:** White Organza with Silver Trim

**PLATINUM**  
by QUOIZEL

DAMP PCAT1617C

# Avanti

**FINISH:** Polished Chrome

**GLASS:** Etched Painted Inside



PRODUCT

DIMENSIONS

CANOPY

BULBS

SHADE DIMS.

PCAE2820C

18" H\*, 20" W, 20" Dp.

5" D

3-100W Med. Base or 23W CFL

15.5" x 5.5"

PCCS2816C/C1

17" H\*, 16" W, 16" Dp.

5" D x 1.25" H

3-60W Med. Base or 13W CFL

16" x 16" x 7"

PCCS2824C/C1

19" H\*, 24" W, 24" Dp.

5" D x 1.25" H

5-60W Med. Base or 13W CFL

24" x 24" x 8"

PCAT1617C

4.5" H, 16.5" W, 16.5" Dp.

-

3-60W Med. Base or 13W CFL

-

\*Comes with (2) 12" and (2) 6" Rods. Rod-hung fixtures come with 8' of wire.

# Bravado

**FINISH:** Polished Chrome  
**GLASS:** Etched Painted Inside



**PCBV1613C** DAMP



**PCBV1617C** DAMP

# Array

**FINISH:** Polished Chrome



**PCAY1722C** DAMP



**PCSL1616C** DAMP

# Stellar

**FINISH:** Polished Chrome  
**GLASS:** Etched Painted White Inside

PRODUCT	DIMENSIONS	CANOPY	BULBS
PCBV1613C	5" H, 12.5" W, 12.5" Dp.	-	2-60W Med. Base or 13W CFL
PCBV1617C	5" H, 16.5" W, 16.5" Dp.	-	3-60W Med. Base or 13W CFL
PCAY1722C	9" H, 22" W, 22" Dp.	4.75" D x 1" H	3-60W Cand. Base
PCSL1616C	4.5" H, 16" W, 16" Dp.	-	3-60W Med. Base or 13W CFL

Please see referenced page numbers for larger images and full descriptions of these products.

## Pierre



CRYSTAL ♦ COLLECTION

**PCPR8522BN**

**PCPR8530BN**

See page 400

## Royale



CRYSTAL ♦ COLLECTION

**RYE8604C**

**RYE8605C**

See page 400

## Shimmer



CRYSTAL ♦ COLLECTION

**PCSR8602C**

**PCSR8603C**

**PCSR8604C**

See page 401

## Paragon



CRYSTAL ♦ COLLECTION

**PRN8604C**

**PRN8606C**

**PRN8608C**

See page 402

## Alexa



CRYSTAL ♦ COLLECTION

**PCAX8603C**

**PCAX8604C**

See page 403

## Endless



CRYSTAL ♦ COLLECTION

**PCED8517C**

**PCED8521C**

**PCED8528C**

See page 403

Please see referenced page numbers for larger images and full descriptions of these products.

*E*vermore



CRYSTAL ♦ COLLECTION

**EME8604C**  
**EME8606C**  
**EME8608C**  
*See page 405*

*R*ibbons

**NEW!**  
FOR ♦ 2015



**RBN8603MN**  
**RBN8605MN**  
**RBN8607MN**  
*See page 406*

*C*osmic




**PCCI8602C**  
**PCCI8603C**  
**PCCI8604C**  
*See page 407*

*B*arron



**PCBA8603C**  
**PCBA8604C**  
**PCBA8605C**  
*See page 408*

*D*ash



**PCDH8522BN**  
**PCDH8530BN**  
*See page 409*

*G*lacial

**NEW!**  
FOR ♦ 2015



**PCGL8522BN**  
**PCGL8530BN**  
*See page 409*



*Please see referenced page numbers for larger images and full descriptions of these products.*

*Ex*ton



**PCEN8602BN**

**PCEN8603BN**

**PCEN8604BN**

*See page 410*

*P*ace



**PCPC8527C**

**PCPC8533C**

*See page 411*

*P*romenade



**PCPE8524C**

**PCPE8536C**

*See page 411*



From the **AUBURN COLLECTION:**  
ABN5006RK (p. 162)

*D*INING & FOYER  
*and More!*

QUOIZEL

# Auburn COLLECTION

**FINISH:**  
Rustic Black

QUOIZEL  
**NATURALS**  
**WOOD**

  **ABN5024RK**

WALNUT STAIN  
HIGHLIGHTS






ABN5012RK



ABN5303RK



ABN5006RK

# Auburn COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
ABN5006RK*	28" H, 28" W, 28" Dp.	5" D	6-60W Cand. Base
ABN5012RK**	31" H, 36" W, 36" Dp.	5" D	12-60W Cand. Base
ABN5024RK**	45" H, 48" W, 48" Dp.	5.5" D	24-60W Cand. Base
ABN5303RK*	21" H, 17.5" W, 17.5" Dp.	5.5" D	3-60W Cand. Base


\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixtures come with 12' of wire and 8' of chain.

# Voyager COLLECTION

**FINISH:**  
Malaga

VYR5024ML

TAPERED  
METAL CANDLE  
SLEEVES



VYR5012ML



VYR5008ML



VYR5006ML



Voyager COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
VYR5006ML*	26" H, 28" W, 28" Dp.	6" D	6-60W Cand. Base
VYR5008ML*	28" H, 36" W, 20" Dp.	8" L x 5" W	8-60W Cand. Base
VYR5012ML**	36" H, 36" W, 36" Dp.	5" D	12-60W Cand. Base
VYR5024ML**	52" H, 48" W, 48" Dp.	6" D	24-60W Cand. Base

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixtures come with 12' of wire and 8' of chain.



From the **CARRABELLE COLLECTION:**  
QMC1199FR

# Carrabelle COLLECTION

DINING & FOYER

**FINISH:**  
French Bronze

CRE5008FR



OPTIC  
CRYSTAL



CRE5004FR

QMC1199FR



# Carrabelle COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE	SHADE DIMS.
CRE5004FR	24" H, 24" W, 24" Dp.	5.5" D	4-60W Cand. Base	Silver Organza Chiffon	21" x 24" x 7"
CRE5008FR	27" H, 20" W, 20" Dp.	5.5" D	8-60W Cand. Base	-	-
QMC1199FR	23.5" H, 18" W, 18" Dp.	5.5" D	5-60W Cand. Base	-	-

Chain-hung fixtures come with 8' of wire and 4' of chain.



# Silhouette COLLECTION

**FINISH:**  
Italian Fresco

**SHADE:**  
Sliver Organza Chiffon

SLT5006IF

**NEW!**  
FOR ♦ 2015

CRYSTAL  
TEARDROPS



SLT5004IF



SLT5303IF

# Silhouette COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
SLT5004IF	28" H, 24" W, 24" Dp.	5.5" D x 1" H	4-60W Cand. Base	24" x 24" x 6.5"
SLT5006IF	33.5" H, 28" W, 28" Dp.	5.5" D x 1" H	6-60W Cand. Base	30" x 30" x 9"
SLT5303IF	24" H, 18" W, 18" Dp.	5.5" D x 1" H	3-60W Cand. Base	18" x 18" x 6"

Chain-hung fixtures come with 8' of wire and 4' of chain.

# Serenity COLLECTION

DINING & FOYER

**FINISH:**  
Italian Fresco

**SER5009IF**



**SER5006IF**



**SER5004IF**



## Serenity COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
SER5004IF*	24" H, 20" W, 20" Dp.	5" D x 1.25" H	4-60W Cand. Base
SER5006IF*	27.5" H, 26.5" W, 26.5" Dp.	5" D x 1.25" H	6-60W Cand. Base
SER5009IF**	34" H, 30" W, 30" Dp.	5" D	9-60W Cand. Base

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixture comes with 12' of wire and 8' of chain.

# Mirren COLLECTION

**FINISH:**  
Imperial Bronze

**MRN5008IB**



**MRN5006IB**



**MRN5005IB**



# Mirren COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
MRN5005IB	18" H, 21" W, 21" Dp.	5" D	5-60W Cand. Base
MRN5006IB	23" H, 28" W, 28" Dp.	5" D	6-60W Cand. Base
MRN5008IB	28" H, 32" W, 32" Dp.	5" D	8-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain.

# Canyon COLLECTION

DINING & FOYER


**FINISH:**  
Mottled Black

WOOD CANDLE  
SLEEVE  
COVER

CYN5009MB

CYN5006MB

CYN5304MB



# Canyon COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS
CYN5006MB*	32" H, 26" W, 26" Dp.	5" D	6-60W Cand. Base
CYN5009MB**	38.5" H, 28.5" W, 28.5" Dp.	6" D	9-60W Cand. Base
CYN5304MB*	19.5" H, 15" W, 15" Dp.	5" D	4-60W Cand. Base

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixture comes with 12' of wire and 8' of chain.



From the **ATRIUM COLLECTION:**  
ATM5005K



# Atrium

FINISH: Mottled Black

See matching Chandelier in setting on opposite page

ATM5304K

HAND FORGED IRON

QUOIZEL  
NATURALS  
WOOD

WDM5005WT



# Wyndmoor

FINISH: Western Bronze



SPIRALED ROPE CANDLE SLEEVES

BDR5006IB

# Bandelier

FINISH: Imperial Bronze

See matching pendant **BDR2820IB** in the Quoizel Naturals section on page 267.

PRODUCT	DIMENSIONS	CANOPY	BULBS
ATM5005K*	22" H, 27" W, 27" Dp.	6.5" D	5-60W Cand. Base
ATM5304K**	18" H, 12" W, 12" Dp.	6.5" D	4-60W Cand. Base
BDR5006IB*	24" H, 26" W, 26" Dp.	5.5" D	6-60W Cand. Base
WDM5005WT*	30" H, 28" W, 28" Dp.	5" D	5-60W Cand. Base

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixture comes with 12' of wire and 8' of chain.

BRG5206WT




# Bordergate

FINISH: Western Bronze

BRG5204WT



BRASS ACCENTS



# RidgeManor

FINISH: Mottled Black

QF1820MB



PRODUCT	DIMENSIONS	CANOPY	BULBS
BRG5204WT	29" H, 13" W, 13" Dp.	5" D	4-60W Cand. Base
BRG5206WT	35" H, 16" W, 16" Dp.	5" D	6-60W Cand. Base
QF1820MB	27" H, 18" W, 18" Dp.	6" D	4-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain.

# Knotted

**FINISH:**

**VG** Vintage Gold

**WT** Western Bronze

**VINTAGE STYLE**  
bulb included



**QF1829WT/VG**



*Also available in  
Vintage Gold*

**QF1687IB**



# Regina

**FINISH:** Imperial Bronze

**QF1686IB**



PRODUCT	DIMENSIONS	CANOPY	BULBS
<b>QF1829VG/WT<sup>†</sup></b>	22" H*, 18.5" W, 18.5" Dp.	4.75" Sq.	4-60W Vintage Bulbs (Supplied)**
<b>QF1686IB</b>	18.5" H, 12" W, 12" Dp.	5" D	4-60W Cand. Base
<b>QF1687IB</b>	23" H, 17" W, 17" Dp.	5" D	6-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain. <sup>†</sup>Rod-hung fixtures come with 12' of wire.  
\*Comes with (2) 6" and (2) 12" Rods. \*\*Max Wattage: 100W Med. Base or 23W CFL.



VINTAGE STYLE  
bulb included



ANR5010IB

# Anchor

FINISH: Imperial Bronze

ANR5006IB



QUOIZEL  
NATURALS  
WOOD

HMP5005WT

# Hampshire

FINISH: Western Bronze



ANTIQUE  
IVORY  
CANDLE  
SLEEVES

PRODUCT	DIMENSIONS	CANOPY	BULBS
ANR5006IB	24.5" H*, 22.5" W, 22.5" Dp.	5" D	6-60W Vintage Bulb** (Supplied)
ANR5010IB	27.5" H*, 28" W, 28" Dp.	5" D	10-60W Vintage Bulb** (Supplied)
HMP5005WT	21" H, 25" W, 25" Dp.	5" D	5-60W Cand. Base

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire. \*\*Max Wattage: 100W Med. Base or 23W CFL.

# Frontier

FINISH: Imperial Bronze

**NEW!**  
FOR ♦ 2015

See page 331 for  
matching semi-flush mount



FTR5204IB

QF1821WMG

# Paddock

FINISH: Warm Gold



# Planter

FINISH: Rustic Black



QF1840RK

QUOIZEL  
**NATURALS**  
**WOOD**

PRODUCT	DIMENSIONS	CANOPY	BULBS
FTR5204IB	23.5" H*, 13" W, 13" Dp.	5" D	4-60W Cand. Base
QF1821WMG	32" H, 14.5" W, 14.5" Dp.	5" Sq.	4-60W Cand. Base
QF1840RK	26" H, 12.5" W, 12.5" Dp.	5" D	3-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain. Rod-hung fixtures come with 8' of wire.  
\*Comes with (2) 6" and (2) 12" Rods.



From the **HOLBROOK COLLECTION:**  
HK5005TC

HK5008TC

# Holbrook

FINISH: Tuscon Brown



QUOIZEL  
NATURALS  
WOOD

HK5005TC



BRASS  
ACCENTS

LRM5006WT

# Laramie

FINISH: Western Bronze

PRODUCT	DIMENSIONS	CANOPY	BULBS
HK5005TC*	14" H, 24" W, 24" Dp.	5.5" D	5-60W Cand. Base
HK5008TC**	19.5" *, 29" W, 29" Dp.	5.5" D	8-60W Cand. Base
LRM5006WT*	31.5" H, 30" W, 30" Dp.	5" D	6-60W Cand. Base

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixtures come with 12' of wire and 8' of chain.

**NEW!**

FOR ♦ 2015

See matching pendant on page 306


# Majesty

FINISH: Vintage Gold

**NEW!**

FOR ♦ 2015

CP50061B



MJY5304VG

See matching semi-flush on page 345.

# Capri

FINISH: Imperial Bronze

HAND FORGED ACCENTS

YU51491B

# Yuma

FINISH: Imperial Bronze

GLASS: Amber Scavo



PRODUCT

DIMENSIONS

CANOPY/BACKPLATE

BULBS

CP50061B

22" H\*, 32" W, 16.5" Dp.

5" D x 0.75" H

6-60W Cand. Base

MJY5304VG

19" H, 12" W, 12" Dp.

5" D

4-60W Cand. Base

YU51491B

24" H, 29" W, 29" Dp.

7" D

6-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.

QF1402CMU



# Collins

FINISH: **BN** Brushed Nickel  
**MU** Musuem Bronze

QF1402CBN



QF1839RK



# Woodrow


FINISH: Rustic Black

PRODUCT	DIMENSIONS	CANOPY	BULBS
QF1402CBN/CMU	29.5" H, 16.5" W, 16.5" Dp.	5.5" D	4-60W Cand. Base
QF1839RK	22" H, 12" W, 12" Dp.	5.5" D	4-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain.

# FortQuinn COLLECTION

**FINISH:**  
Marcado Black

 **FQ1931MK01**



**FQ1920MK01** 

**INDOOR  
OUTDOOR**



See matching Fort Quinn products  
on pages 426-429.

# FortQuinn COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS
FQ1920MK01	41" H, 19" W, 19" Dp.	5" D	4-60W Cand. Base
FQ1931MK01	52" H, 31" W, 31" Dp.	5" D	8-60W Cand. Base

All outdoor hanging fixtures come with 12' of wire and 8' of chain.

# Gentry

**FINISH:** Mystic Black  
**GLASS:** Clear Beveled



**GY5204K**

# Kayden

**FINISH:** Brushed Nickel  
**GLASS:** Clear Seedy

QUOIZEL  
**NATURALS**  
**WOOD**



**KDN5004BN**

See matching mini-pendant  
on page 316.

**QF1838IBC**



# Siltmore

**FINISH:** Imperial Bronze & Aged Copper  
**GLASS:** Clear Seedy

PRODUCT	DIMENSIONS	CANOPY	BULBS
<b>GY5204K</b>	26.5" H, 17" W, 17" Dp.	5" D	4-60W Cand. Base
<b>KDN5004BN</b>	18.5" H*, 19.5" W, 19.5" Dp.	5" D	4-60W Cand. Base
<b>QF1838IBC</b>	28.5" H, 14.5" W, 14.5" Dp.	5" D	4-60W Cand. Base

Chain-hung fixtures come with 12' of wire and 8' of chain. Rod-hung fixtures come with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.





From the **ALSTON COLLECTION:**  
**QMC404B0**

# Alston

FINISH: Bolivian Bronze



QMC404BO

OPTIC  
CRYSTAL

CPN5004EG

# Capulin

FINISH: Empire Gold



CPN5006EG

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS
CPN5004EG*	20" H, 16" W, 16" Dp.	5" D	4-60W Cand. Base
CPN5006EG*	26.5" H, 25" W, 25" Dp.	5" D	6-60W Cand. Base
QMC404BO**	21" H, 18" W, 18" Dp.	5" D	4-60W Cand. Base

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixtures come with 12' of wire and 8' of chain.

# Kemper

**FINISH:** Brushed Nickel  
**GLASS:** Etched Painted White Inside



**KPR5005BN**



**KPR5009BN**

**CLT5004BN**



DOWNLIGHT

# Celestial

**FINISH:** Brushed Nickel  
**GLASS:** Opal Etched

See matching semi-flush  
on page 333.

PRODUCT	DIMENSIONS	CANOPY	BULBS
CLT5004BN†	16" H*, 25" W, 25" Dp.	5" D	4-100W Med. Base or 23W CFL
KPR5005BN†	18.5" H*, 25" W, 25" Dp.	6.5" D	5-100W Med. Base or 23W CFL + 1-50W MR-16 w/ Guio Base Shielded**
KPR5009BN††	31.5" H*, 34" W, 34" Dp.	6.5" D	9-100W Med. Base or 23W CFL + 1-50W MR-16 w/ Guio Base Shielded**

†All rod-hung fixtures come with 8' of wire. ††Rod-hung fixtures come with 12' of wire. \*Comes with (2) 6" and (2) 12" Rods. \*\*Bulb Supplied.

ISLAND LIGHTS

QUOIZEL



From the **TAVERN COLLECTION:**  
TVN232DK (p. 188)

# Tavern

FINISH: Darkest Bronze

See matching Tavern styles on p. 144

TVN232DK



QUOIZEL  
NATURALS  
WOOD

# Eastvale

FINISH: Palladian Bronze

See matching Eastvale styles on p. 130

EVE240PN



VINTAGE STYLE  
bulb included



NHR538WT

# NewHarbor

FINISH: Western Bronze

See matching New Harbor styles on p. 135



PRODUCT	DIMENSIONS	CANOPY	BULBS
EVE240PN	29" H*, 40" W, 14.5" Dp.	6" D	2-100W Med. Base or 23W CFL
NHR538WT	9.5" H**, 38" W, 12" Dp.	9" L x 4.75" W x .75" H	5-60W Vintage Bulbs (Supplied)†
TVN232DK	10.5" H**, 32" W, 12" Dp.	10.5" L x 4.5" W	6-60W Vintage Bulbs (Supplied)†

Rod-hung fixtures come with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods. \*\*Comes with (4) 6" and (4) 12" Rods. †Max Wattage: 100W Med. Base or 23W CFL.

ADS639DC

# Adonis

**FINISH:** Dark Cherry  
**GLASS:** Opal Etched + Clear Water

*See matching Adonis styles starting on p. 38*



# Emery

**FINISH:** **BN** Brushed Nickel  
**IS** Imperial Silver  
**PN** Palladian Bronze  
**WS** Weathered Brass **NEW!**

**SHADE:** Metal

ER353WS 

*ER353 is available in FOUR finishes!*



*See matching Emery styles starting on p. 68*

**NEW!**

**FOR ♦ 2015**



PRODUCT	DIMENSIONS	CANOPY	BULBS
ADS639DC	19" H*, 39" W, 19.5" Dp.	8" L x 4.5" W	6-60W Cand. Base
ER353BN/IS/PN/WS	23.5" H*, 52.5" W, 13" Dp.	9" L x 4.5" W	3-100W Med. Base or 23W CFL

Rod-hung fixtures come with 8' of wire. \*Comes with (4) 6" and (4) 12" Rods.



From the **DELUXE COLLECTION: DX348C**  
*Photo Courtesy of Natalie Howe Design.*

See matching  
Deluxe styles  
on p. 332 and p.377

# Deluxe

**FINISH:** Polished Chrome  
**SHADE:** Cream Linen Hardback

**DX348C**



CRYSTAL  
ACCENTS

# Taylor

**FINISH:** Antique Nickel  
**GLASS:** Opal Etched

**TY628AN**

See matching  
Taylor styles  
starting on p. 107



# Remi

**FINISH:** Polished Chrome  
**SHADE:** White Fabric

See matching  
Remi styles  
on p. 139

**REM345C**



PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
<b>DX348C</b>	33" H, 48" W, 12" Dp.	8" D	3-150W Med. Base <b>or</b> 40W CFL	48" x 12" x 10"
<b>REM345C</b>	10" H, 44.5" W, 5.5" Dp.	18" L x 4.5" W	3-75W Med. Base <b>or</b> 18W CFL	10.5" x 5.5" x 6"
<b>TY628AN*</b>	16.5" H*, 28" W, 16" Dp.	9" L x 4.75" W x 0.875" H	6-100W Med. Base <b>or</b> 23W CFL	-

Chain-hung fixture comes with 8' of wire and 4' of chain. Rod-hung fixture comes with 8' of wire.  
Cord-hung fixture comes with 8' of wire. \*Comes with (4) 6" and (4) 12" Rods.



# Duchess

**FINISH:** AN Antique Nickel    PN Palladian Bronze  
**SHADE:** AN Grey Marble    PN Champagne Marble

See matching Duchess products in the Collections section on pages 58-63.

DH348PN



MCLG337RC



# Laguna

**FINISH:** Renaissance Copper  
**SHADE:** Mica and Mosaic Tile

See matching Laguna styles in the Quoizel Naturals section on pages 260-261.

QUOIZEL  
**NATURALS**  
**MICA**

# Luxe

**FINISH:** Mystic Black

TFLU433K




PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
DH348AN/PN	27" H, 48" W, 14" Dp.	6.5" D	3-100W Med. Base or 23W CFL	-
MCLG337RC	21" H*, 37" W, 16" Dp.	7.5" L x 4.5" W	3-100W Med. Base or 23W CFL	-
TFLU433K	21" H*, 32.5" W, 8.5" Dp.	8.75" L x 6" W	4-100W Med. Base or 23W CFL	Contains 33 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire. \*Comes with (4) 6" and (4) 12" Rods.



KY540IN

QUOIZEL  
**NATURALS**  
**ONYX**



KY433IB

## Kyle

**FINISH:** **IB** Imperial Bronze    **IN** Iron Gate  
**SHADE:** **IB** Butterscotch Onyx    **IN** White Onyx

See matching Kyle styles in the Collections section on pages 78-83.



LP639IB

## La Parra

**FINISH:** Imperial Bronze  
**SHADE:** Candella Scavo

PRODUCT	DIMENSIONS	CANOPY	BULBS
KY433IB	18.5" H, 33" W, 4.5" Dp.	8" L x 4.5" W	4-100W Med. Base or 23W CFL
KY540IB/IN	23" H, 40" W, 5.5" Dp.	11.75" L x 4.75" W	5-100W Med. Base or 23W CFL
LP639IB	46" H, 38" W, 19" Dp.	7" L x 4.5" W	6-100W Med. Base or 23W CFL

Chain-hung fixtures come with 8' of wire and 4' of chain.

# Belle Fleur

**FINISH:** Vintage Bronze

See matching Belle Fleur styles starting on page 214

**TFBF348VB**



# Asheville

**FINISH:** Valiant Bronze

See matching Asheville styles starting on page 202

**TFAS344VA**



# Classic Craftsman

**FINISH:** Valiant Bronze

See matching Classic Craftsman styles on page 222

**TFCC348VA**



PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
<b>TFAS344VA</b>	29" H, 44" W, 19" Dp.	10" L x 4.5" W x 1" H	3-100W Med. Base or 23W CFL	Contains 316 Pieces of Tiffany Glass
<b>TFBF348VB</b>	18" H, 48" W, 16" Dp.	8" L x 4.5" W	3-100W Med. Base or 23W CFL	Contains 884 Pieces of Tiffany Glass
<b>TFCC348VA</b>	18" H, 47.5" W, 16" Dp.	8.125" L x 4.625" W	3-100W Med. Base or 23W CFL	Contains 938 Pieces of Tiffany Glass
<b>TFIK348VA</b>	17.5" H, 47.5" W, 16" Dp.	8" L x 4.5" W	3-100W Med. Base or 23W CFL	Contains 496 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.

ISLAND LIGHTS



From the **INGLENOOK COLLECTION:**  
**TFIK348VA**

**FINISH:** Valiant Bronze



CKCF3390S

Carolyn Kinder  
INTERNATIONAL



CKMS442TM

## Confetti

**FINISH:** OS Old Silver

**SHADE:** Outer: Metal Confetti  
Inner: Off-White Linen

See matching Confetti  
styles starting on page 282



## Marisol

**FINISH:** Teco Marrone

**SHADE:** Beige Hardback Linen

See matching Marisol styles  
starting on page 286

**NEW!**  
FOR ♦ 2015

AX434PN



## Alexandria

**FINISH:** Palladian Bronze

See matching Alexandria  
styles on page 124

PRODUCT	DIMENSIONS	CANOPY	BULBS	SHADE DIMS.
AX434PN	8" H*, 34" W, 15" Dp.	19.25" L x 4.5" W	4-100W Med. Base or 23W CFL	-
CKMS442TM	32.5" H, 42" W, 11" Dp.	9.75" L x 5" W	5-100W Med. Base or 23W CFL	39.5" x 8" x 8.5"
CKCF3390S	9" H**, 39.5" W, 8" Dp.	34.5" L x 4.5" W x 0.75" H	3-100W Med. Base or 23W CFL	-

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire.

\*Comes with (4) 6" and (4) 12" Rods. \*\*Comes with (6) 6" and (6) 12" Rods.

# TIFFANY | QUOIZEL



From the **HYACINTH COLLECTION** (p.229)

**TF1438VB**

Photo courtesy of Enmark Construction Ltd.

*Glass color in Tiffany lighting products may vary from images shown.*

*Shade colors will appear darker when not illuminated.*

# Englenook COLLECTION

**FINISH:**  
Valiant Bronze

**TFIK1817VA**



**TFIK2817VA**



**TFIK348VA**



**TFIK1508VA**



**TFIK1714VA** DAMP

**NEW!**  
FOR ♦ 2015

DAMP **TFIK1617VA**



**TFIK8802** DAMP



**NEW!**  
FOR ♦ 2015

DAMP **TFIK1404VA**



All Quoizel Track Lights Swivel

## Inglennook COLLECTION

PRODUCT	DIMENSIONS	CANOPY	HCWO	BULBS	GLASS
TFIK1404VA	14" H, 42" W, 6" Dp.	9.5" L x 4.5" W x 0.75" H	-	4-100W Med. Base or 23W CFL	Each Shade Contains 184 Pieces of Tiffany Glass
TFIK1508VA	7" H*, 8" W, 8" Dp.	5.5" D	-	1-100W Med. Base or 23W CFL	Contains 208 Pieces of Tiffany Glass
TFIK1617VA	6" H, 16.5" W, 16.5" Dp.	7" D x 1" H	-	2-75W Med. Base or 18W CFL	Contains 253 Pieces of Tiffany Glass
TFIK1714VA	8" H, 14" W, 14" Dp.	6.5" Sq.	-	2-60W Med. Base or 13W CFL	Contains 248 Pieces of Tiffany Glass
TFIK1817VA	12.5" H, 17" W, 17" Dp.	8" D	-	3-100W Med. Base or 23W CFL	Contains 248 Pieces of Tiffany Glass
TFIK2817VA	25.5" H, 17.5" W, 17.5" Dp.	7" D	-	3-100W Med. Base or 23W CFL	Contains 248 Pieces of Tiffany Glass
TFIK348VA	17.5" H, 47.5" W, 16" Dp	8" L x 4.5" W	-	3-100W Med. Base or 23W CFL	Contains 496 Pieces of Tiffany Glass
TFIK8802	7" H, 16" W, 5.5" Dp.	-	3"	2-60W Cand. Base	Contains 110 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.  
Rod-hung fixtures come with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.




# Englenook COLLECTION

**FINISH:**

Valiant Bronze



**TFF16191A5VA** 



**TFIK9471VA** 



**TFT16191A1VA** 

*Enlarged for detail*

# Englenook COLLECTION

**PRODUCT**

**DIMENSIONS**

**BULBS**

**GLASS**

TFF16191A5VA

62" H, 17" W, 17" Dp.

2-75W Med. Base or 18W CFL

Contains 260 Pieces of Tiffany Glass

TFIK9471VA

71" H, 16" W, 16" Dp.

1-150W Med. Base or 40W CFL

Contains 249 Pieces of Tiffany Glass

TFT16191A1VA

25" H, 16" W, 16" Dp.

2-75W Med. Base or 18W CFL

Contains 248 Pieces of Tiffany Glass

T I F F A N Y



From the **INGLENOOK COLLECTION:**  
TFIK2817VA

# Asheville

COLLECTION

**FINISH:**

Valiant Bronze

*The Asheville Tiffany Collection is a perfect example of understated elegance and class.*



TFAS5003VA





**TFAS1615VA**

**NEW!**  
FOR ♦ 2015



**TFAS1507VA**



**TFAS2817VA**



**TFAS344VA**

## Asheville COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TFAS1507VA	11.5" H*, 7" W, 7" Dp.	5" Sq.	1-100W Med. Base or 23W CFL	Contains 44 Pieces of Tiffany Glass
TFAS1615VA	6.5" H, 15" W, 15" Dp.	-	2-60W Med. Base or 13W CFL	Contains 60 Pieces of Tiffany Glass
TFAS2817VA	23" H, 17" W, 17" Dp.	5" Sq.	3-100W Med. Base or 23W CFL	Contains 44 Pieces of Tiffany Glass
TFAS344VA	29" H, 44" W, 19" Dp.	10" L x 4.5" W x 1" H	3-100W Med. Base or 23W CFL	Contains 316 Pieces of Tiffany Glass
TFAS5003VA	22.5" H, 23" W, 23" Dp.	5" Sq.	3-100W Med. Base or 23W CFL	Each Shade Contains 44 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.  
Rod-hung fixtures come with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.

# Asheville COLLECTION

**FINISH:**  
Valiant Bronze

**TFAS1714VA**



**TF1180TVA**



**TFAS9360VA**



**TFAS1404VA**



**NEW!**  
FOR ♦ 2015

All Quoizel Track Lights Swivel

# Asheville COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TF1180TVA	25" H, 16" W, 16" Dp.	-	2-75W Med. Base or 18W CFL	Contains 44 Pieces of Tiffany Glass
TFAS1404VA	13.5" H, 43.5" W, 7" Dp.	5.5" Sq. x 1.75" H	4-100W Med. Base or 23W CFL	Each Shade Contains 44 Pieces of Tiffany Glass
TFAS1714VA	12" H, 14" W, 14" Dp	5.5" Sq.	2-100W Med. Base or 23W CFL	Contains 44 Pieces of Tiffany Glass
TFAS9360VA	60" H, 17" W, 17" Dp.	-	2-100W Med. Base or 23W CFL	Contains 44 Pieces of Tiffany Glass

T I F F A N Y



From the ASHEVILLE COLLECTION:  
TF1180TVA

# Kami COLLECTION

**FINISH:**

Vintage Bronze

TFKM5103VB





TF878SVB DAMP



DAMP TFKM2820VB



TFKM1508VB



KamiCOLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TF878CVB†	10.5" H, 20" W, 20" Dp.	5.5" D	3-100W Med. Base or 23W CFL	Contains 360 Pieces of Tiffany Glass
TF878SVB	16" H, 14" W, 14" Dp.	7" D	2-100W Med. Base or 23W CFL	Contains 348 Pieces of Tiffany Glass
TFKM1508VB	8.5" H*, 8" W, 8" Dp.	5.5" D	1-100W Med. Base or 23W CFL	Contains 159 Pieces of Tiffany Glass
TFKM2820VB†	27.5" H, 20" W, 20" Dp.	5.25" D	3-100W Med. Base or 23W CFL	Contains 360 Pieces of Tiffany Glass
TFKM2840VB††	33.5" H, 40" W, 40" Dp.	5.25" D	8-100W Med. Base or 23W CFL	Contains 532 Pieces of Tiffany Glass
TFKM5103VB†	22.5" H, 24.5" W, 24.5" Dp.	5.125" D	3-100W Med. Base or 23W CFL	Each Shade Contains 159 Pieces of Tiffany Glass

†Chain-hung fixtures come with 8' of wire and 4' of chain. ††Chain-hung fixture comes with 12' of wire and 8' of chain. Rod-hung fixtures come with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.



# KamiCOLLECTION

**FINISH:**

Vintage Bronze

 **TF1396SVB**



 **TF878T**

*Enlarged for detail*



 **TF878F**

 **TF878UVB**



# KamiCOLLECTION

PRODUCT	DIMENSIONS	BULBS	GLASS
TF1396SVB	6" H, 17" W, 17" Dp.	2-75W Med. Base or 18W CFL	Contains 367 Pieces of Tiffany Glass
TF878F	62" H, 18" W, 18" Dp.	2-100W Med. Base or 23W CFL	Contains 366 Pieces of Tiffany Glass
TF878T	23" H, 16" W, 16" Dp.	2-75W Med. Base or 18W CFL	Contains 366 Pieces of Tiffany Glass
TF878UVB	70" H, 14" W, 14" Dp.	1-150W Med. Base 3-Way	Contains 366 Pieces of Tiffany Glass

# Stephen COLLECTION

T I F F A N Y

**FINISH:**  
Vintage Bronze

**54 TFST2840VB**



**TFST2822VB**



**TF885CVB**



**TFST5103VB**



# Stephen COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TF885CVB*	10" H, 18" W, 18" Dp.	6.25" Sq.	3-100W Med. Base or 23W CFL	Contains 256 Pieces of Tiffany Glass
TFST2822VB*	27.5" H, 21.5" W, 21.5" Dp.	7"D	4-100W Medium Base or 23W CFL	Contains 368 Pieces of Tiffany Glass
TFST2840VB**	43" H, 40" W, 40" Dp.	7.75" D	8-100W Med. Base or 23W CFL	Contains 615 Pieces of Tiffany Glass
TFST5103VB*	19.5" H, 19" W, 19" Dp.	5.125" D	3-100W Med. Base or 23W CFL	Each Shade Contains 152 Pieces of Tiffany Glass

\*Chain-hung fixtures come with 8' of wire and 4' of chain. \*\*Chain-hung fixture comes with 12' of wire and 8' of chain.

# Stephen COLLECTION

**FINISH:**

Vintage Bronze

**TFST8701VB**



**TF885SVB**



**TFST1508VB**



**NEW!**

FOR ♦ 2015

**TFST1404VB**



All Quoizel Track Lights Swivel

# Stephen COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	GLASS
TF885SVB	14.5" H, 14" W, 14" Dp.	6.5" Sq.	-	2-100W Med. Base or 23W CFL	Contains 248 Pieces of Tiffany Glass
TFST1404VB	14" H, 41.5" W, 6" Dp.	9.5" L x 4.5" W x 0.75" H	-	4-100W Med. Base or 23W CFL	Each Shade Contains 125 Pieces of Tiffany Glass
TFST1508VB	6" H*, 8" W, 8" Dp.	5.5" D	-	1-100W Med. Base or 23W CFL	Contains 152 Pieces of Tiffany Glass
TFST8701VB	10" H, 8" W, 10.5" Dp.	5" Sq.	7.5"	1-100W Med. Base or 23W CFL	Contains 152 Pieces of Tiffany Glass

Rod-hung fixture comes with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.

T I F F A N Y



From the **STEPHEN COLLECTION:**  
TF885T

# Stephen COLLECTION

**FINISH:**

Vintage Bronze



 **TF885UVB**



 **TF885T**



 **TF885F**



**TF1018TVB** 

# Stephen COLLECTION

PRODUCT	DIMENSIONS	BULBS	GLASS
TF1018TVB	12" H, 5" W, 5" Dp.	1-25W Cand. Base	Contains 124 Pieces of Tiffany Glass
TF885F	59.5" H, 18" W, 18" Dp.	2-100W Med. Base or 23W CFL	Contains 256 Pieces of Tiffany Glass
TF885T	23" H, 16" W, 16" Dp.	2-75W Med. Base or 18W CFL	Contains 248 Pieces of Tiffany Glass
TF885UVB	70" H, 14" W, 14" Dp.	1-150W Med. Base or 40W CFL	Contains 252 Pieces of Tiffany Glass

# Ahambre COLLECTION

T I F F A N Y

**FINISH:**  
Burnt Cinnamon

**TF1816VB**



**TF9343BC**



**TFT13993EBC**



**TF6855BC**



# Ahambre COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TF1816VB	25" H, 22" W, 22" Dp.	5.5" D	4-100W Med. Base or 23W CFL	Contains 128 Pieces of Tiffany Glass
TF6855BC	21" H, 16.5" W, 16.5" Dp.	-	2-75W Med. Base or 18W CFL	Contains 96 Pieces of Tiffany Glass
TF9343BC	62" H, 18" W, 18" Dp.	-	2-100W Med. Base or 23W CFL	Contains 96 Pieces of Tiffany Glass
TFT13993EBC	28" H, 18" W, 18" Dp.	-	2-75W Med. Base or 18W CFL	Contains 96 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.



From the **BELLE FLEUR COLLECTION:**  
TF1781VB

# BelleFleur COLLECTION

T I F F A N Y

**FINISH:**  
Vintage Bronze



**TF1511SVB**



**TF1511TVB**



**TFBF9362VB**



**TFBF348VB**

# BelleFleur COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TF1511SVB	17" H, 16" W, 16" Dp	5.25" D	2-100W Med. Base or 23W CFL	Contains 256 Pieces of Tiffany Glass
TF1511TVB	27" H, 18" W, 18" Dp.	-	2-75W Med. Base or 18W CFL	Contains 504 Pieces of Tiffany Glass
TF1781VB	28" H, 23" W, 23" Dp.	6" D	4-100W Med. Base or 23W CFL	Contains 608 Pieces of Tiffany Glass
TFBF348VB	18" H, 48" W, 16" Dp.	8" L x 4.5" W	3-100W Med. Base or 23W CFL	Contains 884 Pieces of Tiffany Glass
TFBF9362VB	62" H, 20" W, 20" Dp.	-	3-100W Med. Base or 23W CFL	Contains 532 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.



# Arden COLLECTION

**FINISH:**  
Russet



**TF1135F** 



**TFAN1714RS**



**TFAN1506RS**

**TFAN2818RS**



 **TF1135T**

# Arden COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TF1135F	59.5" H, 18" W, 18" Dp.	-	2-100W Med. Base or 23W CFL	Contains 192 Pieces of Tiffany Glass
TF1135T	23.5" H, 16" W, 16" Dp.	-	2-60W Med. Base or 13W CFL	Contains 192 Pieces of Tiffany Glass
TFAN1506RS	6.5" H*, 6" W, 6" Dp.	5" Sq.	1-100W Med. Base or 23W CFL	Contains 186 Pieces of Tiffany Glass
TFAN1714RS	12.5" H, 16" W, 16" Dp.	5.5" Sq.	2-60W Med. Base or 13W CFL	Contains 186 Pieces of Tiffany Glass
TFAN2818RS	24" H, 19" W, 19" Dp.	5.5" Sq.	3-60W Med. Base or 13W CFL	Contains 192 Pieces of Tiffany Glass

Chain-hung fixture comes with 8' of wire and 4' of chain. Rod-hung fixture comes with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.

# Samara COLLECTION

T I F F A N Y

**FINISH:**  
Vintage Bronze

**TFSM5004VB**



**TFSM1818VB**



**TFSM1509VB**



**TFSM1615VB**

**TFSM8701VB**



# Samara COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS	GLASS
TFSM1509VB	11.5" H*, 8.5" W, 8.5" Dp.	5.5" D	-	1-100W Med. Base or 23W CFL	Contains 28 Pieces of Tiffany Glass
TFSM1615VB	8.5" H, 15" W, 15" Dp.	-	-	2-75W Med. Base or 18W CFL	Contains 120 Pieces of Tiffany Glass
TFSM1818VB	12" H*, 18" W, 18" Dp.	6" D	-	3-100W Med. Base or 23W CFL	Contains 56 Pieces of Tiffany Glass
TFSM5004VB	28" H, 28" W, 28" Dp.	5.25" D	-	4-100W Med. Base or 23W CFL	Each Shade Contains 28 Pieces of Tiffany Glass
TFSM8701VB	12" H, 8.5" W, 10.5" Dp.	5" Sq.	9.5"	1-100W Med. Base or 23W CFL	Contains 28 Pieces of Tiffany Glass

Chain-hung fixture comes with 8' of wire and 4' of chain. Rod-hung fixtures come with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.

# Larissa COLLECTION


**FINISH:**

Vintage Bronze



**TF879F**

**TFLR5103VB**



**TF879CVB**



**TFLR1508VB**



**TFLR2840VB**



# Larissa COLLECTION


PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TF879CVB†	27.5" H, 20" W, 20 Dp.	5.5" D	3-100W Med. Base or 23W CFL	Contains 444 Pieces of Tiffany Glass
TF879F	62" H, 18" W, 18" Dp.	-	2-100W Med. Base or 23W CFL	Contains 426 Pieces of Tiffany Glass
TF879T	23" H, 16" W, 16" Dp.	-	2-75W Med. Base or 18W CFL	Contains 426 Pieces of Tiffany Glass
TFLR1508VB	8.5" H*, 8" W, 8" Dp.	5.5" D	1-100W Med. Base or 23W CFL	Contains 159 Pieces of Tiffany Glass
TFLR2840VB††	40" H, 40" W, 40" Dp.	7.75" D	8-100W Med. Base or 23W CFL	Contains 564 Pieces of Tiffany Glass
TFLR5103VB†	22.5" H, 24" W, 24" Dp.	5.125" D	3-100W Med. Base or 23W CFL	Contains 159 Pieces of Tiffany Glass

†Chain-hung fixtures come with 8' of wire and 4' of chain. ††Chain-hung fixtures come with 12' of wire and 8' of chain. Rod-hung fixture comes with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.

T I F F A N Y



From the **LARISSA COLLECTION:**

 **TF879T**



From the **WEST END COLLECTION:**  
TF1541VB

# WestEnd COLLECTION

T I F F A N Y

**FINISH:**

**VB** Vintage Bronze **BB** Brushed Bullion

TF1541VB



TF9320BB



TF6660BB



TF1400SVB

# WestEnd COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TF1400SVB	6" H, 17" W, 17" Dp.	-	2-75W Med. Base or 18W CFL	Contains 262 Pieces of Tiffany Glass
TF1541VB	8.5" H*, 6" W, 6" Dp.	5" D	1-100W Med. Base or 23W CFL	Contains 153 Pieces of Tiffany Glass
TF6660BB	26.5" H, 16" W, 16" Dp.	-	2-75W Med. Base or 18W CFL	Contains 306 Pieces of Tiffany Glass
TF9320BB	60" H, 18" W, 18" Dp.	-	2-100W Med. Base or 23W CFL	Contains 306 Pieces of Tiffany Glass

Rod-hung fixture comes with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.

# ClassicCraftsman COLLECTION

**FINISH:**

Valiant Bronze

 **TF124TVA**



**TFCC1508VA**



**TFCC2822VA**



 **TFCC8802**

 **TFCC348VA**



# ClassicCraftsman COLLECTION

PRODUCT	DIMENSIONS	CANOPY	HCWO	BULBS	GLASS
TF124TVA	29" H, 17" W, 17" Dp.	-	-	2-75W Med. Base or 18W CFL	Contains 474 Pieces of Tiffany Glass
TFCC1508VA	8" H*, 8" W, 8" Dp.	5.5" D	-	1-100W Med. Base or 23W CFL	Contains 304 Pieces of Tiffany Glass
TFCC2822VA	27" H, 23.5" W, 23.5" Dp.	6.875" D	-	3-100W Med. Base or 23W CFL	Contains 640 Pieces of Tiffany Glass
TFCC348VA	18" H, 47.5" W, 16" Dp.	8.125" W x 4.625" H	-	3-100W Med. Base or 23W CFL	Contains 938 Pieces of Tiffany Glass
TFCC8802	7" H, 16.5" W, 5.5" Dp.	-	2.5"	2-60W Cand. Base	Contains 116 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixture comes with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.

# Chastain COLLECTION

T I F F A N Y

**FINISH:**  
Vintage Bronze



**TF489P01VB**

**TFCS2820VB**



**TF489T**



**TF489F**

# Chastain COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TF489F	62" H, 20" W, 20" Dp.	-	2-100W Med. Base or 23W CFL	Contains 160 Pieces of Tiffany Glass
TF489P01VB	14" H*, 5" W, 5" Dp.	5.5" D	1-100W Med. Base or 23W CFL	Contains 51 Pieces of Tiffany Glass
TF489T	22.5" H, 15.5" W, 15.5" Dp.	-	2-60W Med. Base or 13W CFL	Contains 140 Pieces of Tiffany Glass
TFCS2820VB	28.5" H, 19.5" W, 19.5" Dp.	6.5" D	3-100W Med. Base or 23W CFL	Contains 160 Pieces of Tiffany Glass

Chain-hung fixture comes with 8' of wire and 4' of chain. Rod-hung fixture comes with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.



# Cambridge COLLECTION

**FINISH:**

Vintage Bronze



**TFCB6325VB** 



**TFCB1820VB**



**TFCB1716VB** 

# Cambridge COLLECTION

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS	GLASS
TFCB1716VB	14.5" H, 16" W, 16" Dp.	5.75" D	2-100W Med. Base or 23W CFL	Contains 318 Pieces of Tiffany Glass
TFCB1820VB	30" H, 20" W, 20" Dp.	5" D	3-100W Med. Base or 23W CFL	Contains 371 Pieces of Tiffany Glass
TFCB6325VB	23.5" H, 16" W, 16" Dp.	-	2-75W Med. Base or 18W CFL	Contains 318 Pieces of Tiffany Glass

Chain-hung fixture comes with 8' of wire and 4' of chain.

# Dayton COLLECTION

T I F F A N Y

**FINISH:**  
Imperial Bronze

**TFDN5103IB**



**TFDN1506IB**



**TFDN1716IB**



# Dayton COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TFDN1506IB	12" H*, 7" W, 7" Dp.	5" D	1-100W Med. Base or 23W CFL	Contains 80 Pieces of Tiffany Glass
TFDN1716IB	11" H, 16.5" W, 16.5" Dp.	5.5" D	2-100W Med. Base or 23W CFL	Contains 168 Pieces of Tiffany Glass
TFDN5103IB	19" H, 24" W, 24" Dp.	5" D	3-60W Frosted G9 Halogen**	Each Shade Contains 144 Pieces of Tiffany Glass

Chain-hung fixture comes with 8' of wire and 4' of chain. Rod-hung fixture comes with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods. \*\* Bulbs Supplied.

# Rosa COLLECTION

**FINISH:**  
Imperial Bronze

**TFRA1716IB**



**TFRA1820IB**



**TFRA1508IB**



**TFRA6325IB**



# Rosa COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TFRA1508IB	8" H, 8" W, 8" Dp.	5" D	1-100W Med. Base or 23W CFL	Contains 271 Pieces of Tiffany Glass
TFRA1716IB	14.5" H, 16" W, 16" Dp.	5" D	3-100W Med. Base or 23W CFL	Contains 525 Pieces of Tiffany Glass
TFRA1820IB	13" H, 20" W, 20" Dp.	5" D	3-100W Med. Base or 23W CFL	Contains 1,110 Pieces of Tiffany Glass
TFRA6325IB	25" H, 16" W, 16" Dp.	-	2-75W Med. Base or 18W CFL	Contains 525 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.

# Belle COLLECTION


T I F F A N Y

**FINISH:**  
Imperial Bronze



 **TF1668TIB**



**TFBL9360IB** 



**TFBL2818IB**


## Belle COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
<b>TF1668TIB</b>	25.5" H, 17" W, 17" Dp.	-	2-75W Med. Base or 18W CFL	Contains 632 Pieces of Tiffany Glass
<b>TFBL2818IB</b>	27" H, 18" W, 18" Dp	5" D	3-100W Med. Base or 23W CFL	Contains 632 Pieces of Tiffany Glass
<b>TFBL9360IB</b>	58.5" H, 18" W, 18" Dp.	-	2-100W Med. Base or 23W CFL	Contains 632 Pieces of Tiffany Glass

Chain-hung fixture comes with 8' of wire and 4' of chain.



*The Hyacinth Tiffany glass design is one of our prettiest and most vibrant. Watch it add color and style to your home décor!*



From the **HYACINTH COLLECTION:**  
**TF1536VB**  
*Photo Courtesy of Enmark Construction Ltd.*

# Hyacinth COLLECTION

T I F F A N Y

**FINISH:**  
Vintage Bronze

**TF1618VB©**

**TF1737VB**



**TF1438VB©**

**TF1536VB**



# Hyacinth COLLECTION

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS	COPYRIGHT
TF1438VB	26.5" H, 22" W, 22" Dp.	5" D	3-100W Med. Base or 23W CFL	Contains 540 Pieces of Tiffany Glass	VA 1-082-347
TF1536VB	8.5" H*, 9" W, 9" Dp.	5.5" D	1-100W Med. Base or 23W CFL	Contains 188 Pieces of Tiffany Glass	-
TF1618VB	15" H, 22" W, 22" Dp.	6.25" D	3-100W Med. Base or 23W CFL	Contains 540 Pieces of Tiffany Glass	VA 1-087-906
TF1737VB	11.5" H, 12.5" W, 12.5" Dp.	6.25" D	1-150W Med. Base or 40W CFL	Contains 295 Pieces of Tiffany Glass	-

Chain-hung fixtures come with 8' of wire and 4' of chain. Rod-hung fixture comes with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.

# Jewel DRAGONFLY

FINISH: Malaga

 TFJD2836ML



TFJD2822ML



 TFJD1718ML




*Dragonfly Tiffanys are particularly intricate in their handcrafted artistry.*

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TFJD1718ML	13" H, 18" W, 18" Dp	5" D	3-100W Med. Base or 23W CFL	Contains 238 Pieces of Tiffany Glass
TFJD2822ML*	24" H, 22" W, 22" Dp.	5" D	4-100W Med. Base or 23W CFL	Contains 315 Pieces of Tiffany Glass
TFJD2836ML**	36.5" H, 35.5" W, 35.5" Dp.	5" D	6-100W Med. Base or 23W CFL	Contains 540 Pieces of Tiffany Glass

\*Chain-hung fixture comes with 8' of wire and 4' of chain. \*\*Chain-hung fixture comes with 12' of wire and 8' of chain.



 **TF1508FVB**

*King*  
**FINISH:** Vintage Bronze



**TF1508TVB** 



*Jonas*

**TF1666T** 

PRODUCT	DIMENSIONS	BULBS	GLASS
TF1508FVB	62" H, 18" W, 18" Dp.	2-100W Med. Base or 23W CFL	Contains 318 Pieces of Tiffany Glass
TF1508TVB	24" H, 16" W, 16" Dp.	2-75W Med. Base or 18W CFL	Contains 318 Pieces of Tiffany Glass
TF1666T	22.5" H, 17" W, 17" Dp.	2-75W Med. Base or 18W CFL	Contains 450 Pieces of Tiffany Glass



# Autumn DRAGONFLY

FINISH: Imperial Bronze



**TF6784VB**

**TF1882IB**



# Green DRAGONFLY

FINISH: Vintage Bronze



**TF1795TIB**

# Summer DRAGONFLY

FINISH: Imperial Bronze

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TF1795TIB	21.5" H, 16" W, 16" Dp.	-	2-75W Med. Base or 18W CFL	Contains 60 Pieces of Tiffany Glass
TF1882IB	12" H, 20.5" W, 20.5" Dp	5" D	3-100W Med. Base or 23W CFL	Contains 385 Pieces of Tiffany Glass
TF6784VB	22.5" H, 14" W, 14" Dp.	-	2-60W Med. Base or 13W CFL	Contains 300 Pieces of Tiffany Glass

Chain-hung fixture comes with 8' of wire and 4' of chain.

# Copperfly

FINISH: Imperial Bronze



TF1851TIB 



 TF1575TIB

LED LIGHT

# Berkshire

FINISH: Imperial Bronze



TF1850TIB 

# Jewel

FINISH: Imperial Bronze

**PRODUCT**

**DIMENSIONS**

**BULBS**

**GLASS**

TF1575TIB

27.5" H, 16" W, 16" Dp.

2-75W Med. Base or 18W CFL +1-1W LED (Supplied)

Contains 363 Pieces of Tiffany Glass

TF1851TIB

16.5" H, 17" W, 17" Dp.

2-75W Med. Base or 18W CFL

Contains 324 Pieces of Tiffany Glass

TF1850TIB

23.5" H, 16" W, 16" Dp.

2-75W Med. Base or 18W CFL

Contains 297 Pieces of Tiffany Glass



**TF1697FWT** 

# Monteclair

**FINISH:** Western Bronze  
**SHADE:** Tiffany Oyster Mica



 **TF1697TWT**  
*Enlarged for detail*

PRODUCT	DIMENSIONS	BULBS	GLASS
TF1697FWT	60" H, 16" W, 16" Dp.	2-60W Med. Base or 13W CFL	Contains 240 Pieces of Tiffany Glass
TF1697TWT	25.5" H, 15" W, 15" Dp.	2-60W Med. Base or 13W CFL	Contains 240 Pieces of Tiffany Glass

# Adriana

**FINISH:** Vintage Bronze



TF1901VB©

TF1784VB©



# Florentine

**FINISH:** Vintage Bronze



TF1872T

# Bartlett

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS	COPYRIGHT
TF1784VB	39" H, 40" W, 40" Dp	5.5" D	8-100W Medium Base or 23W CFL	Contains 2331 Pieces of Tiffany Glass	VA 1-180-830
TF1872T	26" H, 16" W, 16" Dp.	-	2-75W Med. Base or 18W CFL	Contains 909 Pieces of Tiffany Glass	-
TF1901VB	28" H, 32" W, 32" Dp.	5.5" D	6-100W Med. Base or 23W CFL	Contains 515 Pieces of Tiffany Glass	VA 1-216-473

Chain-hung fixtures come with 12' of wire and 8' of chain.

# Mariah

**FINISH:** Vintage Bronze

**TFMH1820VB**



**TF1880IB**



**TF1869TIB**

# Palazzo

**FINISH:** Imperial Bronze

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TF1869TIB	23" H, 16" W, 16" Dp.	-	2-75W Med. Base or 18W CFL	Contains 561 Pieces of Tiffany Glass
TF1880IB	33" H, 20" W, 20" Dp.	5.25" D	4-100W Med. Base or 23W CFL	Contains 573 Pieces of Tiffany Glass
TFMH1820VB	12" H, 20" W, 20" Dp.	7" D	3-100W Med. Base or 23W CFL	Contains 336 Pieces of Tiffany Glass

Chain-hung fixtures come with 8' of wire and 4' of chain.

TF1841IB



*Rosecliffe*

FINISH: Imperial Bronze



TF1673TWT

*Red Brier*

FINISH: Western Bronze



*Purple Wisteria*

TF1139T



PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TF1139T	19.5" H, 10.5" W, 10.5" Dp.	-	1-60W Med. Base or 13W CFL	Contains 479 Pieces of Tiffany Glass
TF1673TWT	24" H, 13.5" W, 13.5" Dp.	-	2-60W Med. Base or 13W CFL	Contains 935 Pieces of Tiffany Glass
TF1841IB	15" H, 15" W, 15" Dp.	5" D	3-100W Med. Base or 23W CFL	Contains 612 Pieces of Tiffany Glass

Chain-hung fixture comes with 8' of wire and 4' of chain.



 **TF6034R**

# Laburnum

**FINISH:** Architectural Bronze



# Lucia

 **TF1868T**



 **TF1794T**

# Wild Vines

PRODUCT	DIMENSIONS	BULBS	GLASS
TF1794T	26" H, 17" W, 17" Dp	2-75W Med. Base or 18W CFL	Contains 610 Pieces of Tiffany Glass
TF1868T	24.5" H, 16" W, 16" Dp.	2-75W Med. Base or 18W CFL	Contains 690 Pieces of Tiffany Glass
TF6034R	31" H, 22" W, 22" Dp.	3-100W Med. Base or 23W CFL	Contains 1,998 Pieces of Tiffany Glass


# Queens Meadow



 **TF1873T**



# Fowler

**TF1434T** 



 **TF1801T**

# Campton

PRODUCT	DIMENSIONS	BULBS	GLASS
TF1434T	23" H, 16" W, 16" Dp.	2-75W Med. Base or 18W CFL	Contains 150 Pieces of Tiffany Glass
TF1801T	24.5" H, 16" W, 16" Dp.	2-75W Med. Base or 18W CFL	Contains 160 Pieces of Tiffany Glass
TF1873T	23.5" H, 20" W, 20" Dp.	2-75W Med. Base or 18W CFL	Contains 498 Pieces of Tiffany Glass




# Task LIGHTING



**TF1860FZ**



**TF7110ZLED**



**TF9152ZLED**



**TF1860TZ**

## Montgomery

**FINISH:** Medici Bronze

## Pueblo

**FINISH:** Medici Bronze

### LED CHART

Lumens	400
Total Watts	5W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	3200K
Dimmable	No

PRODUCT	DIMENSIONS	LIGHT SOURCE	GLASS
TF1860FZ	51" H, 22.5" W, 9" Dp.	See LED Chart	Contains 40 Pieces of Tiffany Glass
TF1860TZ	19" H, 19" W, 6" Dp.	See LED Chart	Contains 40 Pieces of Tiffany Glass
TF7110ZLED	19" H, 19" W, 6" Dp.	See LED Chart	Contains 42 Pieces of Tiffany Glass
TF9152ZLED	51" H, 22.5" W, 9" Dp.	See LED Chart	Contains 42 Pieces of Tiffany Glass



From the **PUEBLO COLLECTION:**  
TF7110ZLED

# Aberdeen

**FINISH:** Imperial Bronze



**TF1798TIB**



**TF1427F**

# Bryant



**TF1427T**



PRODUCT	DIMENSIONS	BULBS	GLASS
TF1427F	60" H, 17" W, 17" Dp.	2-100W Med. Base or 23W CFL	Contains 112 Pieces of Tiffany Glass
TF1427T	23" H, 14" W, 14" Dp.	2-75W Med. Base or 18W CFL	Contains 112 Pieces of Tiffany Glass
TF1798TIB	24" H, 15" W, 15" Dp.	2-75W Med. Base or 18W CFL	Contains 128 Pieces of Tiffany Glass

*Holcomb*

**FINISH:** Imperial Bronze



QUOIZEL  
**NATURALS**  
**AGATE STONE**

 **TF1849TIB**



**NEW!**  
FOR  2015

**TF1917TVA** 

*Sunrise*

**FINISH:** Valiant Bronze



**TF1793TVA** 

*Viking*

**FINISH:** Valiant Bronze

**PRODUCT**

**TF1793TVA**

**DIMENSIONS**

24" H, 15.5" W, 15.5" Dp.

**BULBS**

2-75W Med. Base or 18W CFL

**GLASS**

Contains 64 Pieces of Tiffany Glass

**TF1849TIB**

21.5" H, 14.5" W, 14.5" Dp.

2-75W Med. Base or 18W CFL

Contains 52 Pieces of Tiffany Glass + Agate Stone

**TF1917TVA**

25.5" H, 16" W, 16" Dp.

2-75W Med. Base or 18W CFL

Contains 260 Pieces of Tiffany Glass




TF1791TWT 

*Pomeroy*

**FINISH:** Western Bronze



 TF9397VB



 TF6668VB

*Gotham*

**FINISH:** Vintage Bronze



**PRODUCT**

**DIMENSIONS**

**BULBS**

**GLASS**

TF1791TWT

21" H, 13" W, 15" Dp.

1-75W Med. Base or 18W CFL

Contains 4 Pieces of Tiffany Glass

TF6668VB

25" H, 19" W, 19" Dp.

2-75W Med. Base or 18W CFL

Contains 48 Pieces of Tiffany Glass

TF9397VB

62" H, 20.5" W, 20.5" Dp.

2-100W Med. Base or 23W CFL

Contains 64 Pieces of Tiffany Glass

Macey

FINISH: Imperial Bronze



TF1847TIB

Grove Park

FINISH: Multi



TF6898M



TF9404M

GEOMETRIC  
IRON ACCENTS

PRODUCT

TF1847TIB

DIMENSIONS

23" H, 16.5" W, 16.5" Dp.

BULBS

2-75W Med. Base or 18W CFL

GLASS

Contains 180 Pieces of Glass

TF6898M

23.5" H, 14" W, 14" Dp.

2-60W Med. Base or 13W CFL

Contains 240 Pieces of Tiffany Glass

TF9404M

60" H, 17" W, 17" Dp.

2-100W Med. Base or 23W CFL

Contains 240 Pieces of Tiffany Glass



## Navajo

**FINISH:** Valiant Bronze

TFNO6325VA 



## Timber

**FINISH:** Vintage Bronze

 TF1246TVB



 TF1672TWT

## Revere

**FINISH:** Western Bronze

### PRODUCT

TF1246TVB

### DIMENSIONS

21" H, 14" W, 14" Dp.

### BULBS

1-75W Med. Base or 18W CFL

### GLASS

Contains 172 Pieces of Tiffany Glass

TF1672TWT

22" H, 14" W, 14" Dp.

2-60W Med. Base or 13W CFL

Contains 196 Pieces of Tiffany Glass

TFNO6325VA

25" H, 15" W, 15" Dp.

2-75W Med. Base or 18W CFL

Contains 292 Pieces of Tiffany Glass



TF961TVB 

*F*inton

FINISH: Vintage Bronze

*A*rlington

FINISH: Imperial Bronze



TF1799TIB 



TF1021TVB 

*H*olmes

FINISH: Vintage Bronze

PRODUCT

TF1021TVB

DIMENSIONS

12" H, 5" W, 5" Dp.

BULBS

1-25W Cand. Base

GLASS

Contains 84 Pieces of Tiffany Glass

TF1799TIB

21.5" H, 14" W, 14" Dp

2-75W Med. Base or 18W CFL

Contains 148 Pieces of Tiffany Glass

TF961TVB

25" H, 16" W, 16" Dp.

2-75W Med. Base or 18W CFL

Contains 232 Pieces of Tiffany Glass



# DraggCreek

FINISH: Russet



**NEW!**  
FOR ♦ 2015

TF1916TRS 



 TF6669VB

# Indus



# Westlake


FINISH: Vintage Bronze

TF6821VB 

PRODUCT	DIMENSIONS	BULBS	GLASS
TF1916TRS	24.5" H, 16" W, 16" Dp.	2-75W Med. Base or 18W CFL	Contains 72 Pieces of Tiffany Glass
TF6669VB	23" H, 16" W, 16" Dp.	2-60W Med. Base or 13W CFL	Contains 105 Pieces of Tiffany Glass
TF6821VB	23" H, 17" W, 17" Dp.	2-75W Med. Base or 18W CFL	Contains 240 Pieces of Tiffany Glass

# Hillworth



TF1871T 



TF1881VB



TF1818TVB 

# Grand Bay

FINISH: Vintage Bronze

PRODUCT	DIMENSIONS	CANOPY	BULBS	GLASS
TF1818TVB	24" H, 16" W, 16" Dp.	-	2-75W Med. Base or 18W CFL	Contains 414 Pieces of Tiffany Glass
TF1871T	21" H, 14" W, 14" Dp.	-	2-75W Med. Base or 18W CFL	Contains 328 Pieces of Tiffany Glass
TF1881VB	13.5" H, 20" W, 20" Dp.	5.25" D	3-100W Med. Base or 23W CFL	Contains 430 Pieces of Tiffany Glass

Chain-hung fixture comes with 8' of wire and 4' of chain.

# India

**FINISH:** Imperial Bronze



**TF1846TIB** 



**TF1790TIB**

# KingsPointe

**FINISH:** Imperial Bronze



**TF1848TIB** 

# Palmetto

**FINISH:** Imperial Bronze

PRODUCT	DIMENSIONS	BULBS	GLASS
TF1790TIB	27" H, 16" W, 16" Dp.	2-75W Med. Base or 18W CFL	Contains 356 Pieces of Tiffany Glass
TF1846TIB	19.5" H, 16" W, 16" Dp.	2-75W Med. Base or 18W CFL	Contains 282 Pieces of Glass
TF1848TIB	26.5" H, 18" W, 18" Dp.	2-75W Med. Base or 18W CFL	Contains 186 Pieces of Glass

*P*earson



 TF1433T

*L*ynch



 TF1487T

 TF1913TRS



**NEW!**  
FOR ♦ 2015

*J*ewelHeart  
FINISH: Russet

PRODUCT	DIMENSIONS	BULBS	GLASS
TF1433T	23" H, 16" W, 16" Dp.	2-75W Med. Base or 18W CFL	Contains 240 Pieces of Tiffany Glass
TF1487T	26" H, 15.5" W, 15.5" Dp.	2-75W Med. Base or 18W CFL	Contains 371 Pieces of Tiffany Glass
TF1913TRS	23" H, 14" W, 14" Dp.	2-60W Med. Base or 13W CFL	Contains 224 Pieces of Tiffany Glass and 12 Jewels




**ROSS**

**FINISH:** Vintage Bronze



**TF1509TVB** 

**TF1509FVB** 

 **TF1792TWT**



**SeaShell**

**FINISH:** Western Bronze

**PRODUCT**

**DIMENSIONS**

**BULBS**

**GLASS**

**TF1509FVB**

60" H, 17" W, 17" Dp.

2-100W Med. Base or 23W CFL

Contains 248 Pieces of Tiffany Glass

**TF1509TVB**

23" H, 14" W, 14" Dp.

2-75W Med. Base or 18W CFL

Contains 248 Pieces of Tiffany Glass


**TF1792TWT**

24.5" H, 16" W, 16" Dp.

2-75W Med. Base or 18W CFL

Contains 200 Pieces of Tiffany Glass



 **TF1693TVK**

## Stinson

**FINISH:** Vintage Black



 **TF1693FVK**



## Crowley

**FINISH:** Imperial Bronze

**TF1865TIB** 

PRODUCT	DIMENSIONS	BULBS	GLASS
TF1693FVK	60" H, 17" W, 17" Dp.	2-75W Med. Base or 18W CFL	Contains 335 Pieces of Tiffany Glass
TF1693TVK	24" H, 15.5" W, 15.5" Dp.	2-75W Med. Base or 18W CFL	Contains 335 Pieces of Tiffany Glass
TF1865TIB	24.5" H, 15" W, 15" Dp.	2-75W Med. Base or 18W CFL	Contains 94 Pieces of Tiffany Glass



## Carroll

**FINISH:** Vintage Bronze

**DAMP** TF1805SVB

## Felice

**FINISH:** Imperial Bronze



**DAMP** TF1040IB



TF1040IB  
TFAV1714VB

## Ava

**FINISH:** Vintage Bronze

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS	GLASS
TF1040IB	14" H, 19" W, 19" Dp.	6.25" D	3-100W Med. Base or 23W CFL	Contains 141 Pieces of Tiffany Glass
TF1805SVB	7" H, 17" W, 17" Dp.	5.25" D	2-75W Med. Base or 18W CFL	Contains 215 Pieces of Tiffany Glass
TFAV1714VB	9" H, 14" W, 14" Dp.	-	2-60W Med. Base or 13W CFL	Contains 342 Pieces of Tiffany Glass



**TF1409SVB**

**Graham**  
**FINISH:** Vintage Bronze



**TF1408SVB**

**Reed**  
**FINISH:** Vintage Bronze



**TFLU433K**

**Luxe**  
**FINISH:** Mystic Black

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS	GLASS
TF1408SVB	6" H, 17" W, 17" Dp.	7" D x 1" H	2-75W Med. Base or 18W CFL	Contains 308 Pieces of Tiffany Glass
TF1409SVB	6" H, 17" W, 17" Dp.	7" D x 1" H	2-75W Med. Base or 18W CFL	Contains 186 Pieces of Tiffany Glass
TFLU433K	21" H*, 32.5" W, 8.5" Dp.	8.75" L x 6" W	4-100W Med. Base or 23W CFL	Contains 33 Pieces of Tiffany Glass

Rod-hung fixture comes with 8' of wire. \*Comes with (4) 6" and (4) 12" Rods.



# Lennon

**FINISH:** Imperial Bronze



**TF1783CIB**



**TF1425TWT**

# Fields

**FINISH:** Western Bronze



**TF6826VB**

# Connie

**FINISH:** Vintage Bronze

PRODUCT	DIMENSIONS	CANOPY/BACKPLATE	BULBS	GLASS
TF1425TWT	24" H, 16" W, 16" Dp.	-	2-75W Med. Base or 18W CFL	Contains 330 Pieces of Tiffany Glass
TF1783CIB	17.5" H, 16" W, 16" Dp.	5" D	4-60W Cand. Base	Contains 24 Pieces of Tiffany Glass
TF6826VB	22" H, 14" W, 14" Dp.	-	2-60W Med. Base or 13W CFL	Contains 387 Pieces of Tiffany Glass

Chain-hung fixture comes with 8' of wire and 4' of chain.

*Tiffany*  
ANIMALS



TFX839Y

*Elephant*



TFX1519T

*Flower*TURTLE



TFX837Y

*Green*FROG



TF6031VB


*Flowered*  
LADYBUG

FINISH: Vintage Bronze



TFX1518T

*Rainbow*BUTTERFLY



TF6033VB

*Lounging*FROG

FINISH: Vintage Bronze

TF6599R

*Orange*BUTTERFLY

FINISH: Architectural Bronze



PRODUCT	DIMENSIONS	BULBS
TF6031VB	4.5" H, 7" W, 6" Dp	1-15W T7 Cand. Base*
TF6033VB	3.5" H, 8" W, 7" Dp	1-15W T7 Cand. Base*
TF6599R	9" H, 6" W, 7.5" Dp.	1-15W T7 Cand. Base*
TFX1518T	9" H, 5" W, 5" Dp.	1-15W T7 Cand. Base*
TFX1519T	3.5" H, 5.5" W, 8" Dp.	1-15W T7 Cand. Base*
TFX837Y	6" H, 8.5" W, 9" Dp	1-15W T7 Cand. Base*
TFX839Y	6.5" H, 9" W, 4.5" Dp	1-15W T7 Cand. Base*

\*Bulb supplied.

**White Reef**

FINISH: Brushed Nickel

AR1904BN



**Carra**

FINISH: Imperial Bronze

AR1899IB



**Vargas**

FINISH: Imperial Bronze

AR1900IB

Enlarged for detail



**Hatley**

FINISH:  
Brushed Nickel

AR1901BN



AR1903IB



**Maritime**

FINISH:  
Imperial Bronze

AR1902IB

Enlarged for detail



PRODUCT

DIMENSIONS

CANOPY

BULBS

AR1899IB

15" H\*, 6.5" W, 6.5" Dp.

5.5" D

1-100W Med. Base or 23W CFL

AR1900IB

10" H\*, 6.5" W, 6.5" Dp.

5" D

1-100W Med. Base or 23W CFL

AR1901BN

12" H\*, 7.5" W, 7.5" Dp.

5.5" D

1-100W Med. Base or 23W CFL

AR1902IB

30.5" H, 6.5" W, 6.5" Dp

-

1-100W Med. Base or 23W CFL

AR1903IB

14" H\*, 6.5" W, 6.5" Dp.

5" D

1-100W Med. Base or 23W CFL

AR1904BN

9.5" H\*, 5" W, 5" Dp.

5.5" D

1-100W Med. Base or 23W CFL

Rod-hung fixtures come with 8' of wire. \*Comes with (2) 6" and (2) 12" Rods.