



EMERSON[™]



moving air in style[®]

2014 CEILING FANS



Emerson's Blade Select Series is a family of six different fan housings which can adapt to over 50 blade options in spans ranging from 42" to 72", from all-weather blades to veneer blades, to decorative solid wood blades. With various styles, performance features and the ability to customize the exact look, the Blade Select Series is sure to appease the design conscientious consumer. It's as easy as 1, 2, 3. Just look for the Blade Select Series logo for applicable models. See pages 32-33 of this brochure, our full line catalog or emersonfans.com to view all blade choices within the series.



Penbrooke Select
CF5100 - pg. 2



Carrera Grande
CF787 - pg. 6



Carrera Grande Eco
CF788 - pg. 6



Crown Select
CF4501 - pg. 22



Avant Eco
CF921 - pg. 23



Premium Select
CF4801 - pg. 24

STEP 1 choose your fan



Avant Eco



Carrera Grande



Carrera Grande Eco



Crown Select



Penbrooke Select



Premium Select

STEP 2 choose your finish



Not all finishes are offered in every model; see product page for more information.

STEP 3 choose your blade

To view all Blade Select Series blade options, turn to page 32-33 of this brochure.

50 + Blade Options:

- 42/44", 52/54", 58/60" & 70/72" Spans
- Solid Wood
- Tropical
- Indoor & Outdoor Options
- Hand Carved Wood
- Veneer Overlay



CF995BS - page 4

WHEN ENERGY EFFICIENT MATTERS...

Look for this logo for fans that carry Emerson's Most Energy Efficient Motor - The EcoMotor®



EcoMOTOR

HERE'S HOW...

EcoMotor Fans:

- Are up to 3 times more efficient than typical ceiling fan motors - cost less than 1¢ per hour to run.
- Use a maximum of 33 watts of energy.
- Drive a higher degree blade pitch more efficiently.
- Come with built-in electronics with 6-speed control.



- EcoMotor fans which are also part of our Blade Select Series are adaptable to 42/44", 52/54", 58/60" or 70/72" fan diameter without adding noise, allowing versatility & quiet operation

Emerson EcoMotor®

Penbrooke Select **NEW!** CF5100

Our newest addition to the Blade Select Series, the Penbrooke Select, houses our robust K55XL motor. This beautifully crafted air mover is a fresh take to a traditional look. With 50+ blades adaptable to this design, the potential for a custom look is easy to capture.

Features:

- 44", 54" or 60" blade span
- Light kit adaptable
- Accent light adaptable (AL100)
- 4.5" downrod included

Includes:

- Additional Smooth Switchcup¹



Brushed Steel
(CF5100BS)



Golden Espresso
(CF5100GES)



Oil Rubbed
Bronze
(CF5100ORB)



Satin White
(CF5100SW)



Venetian Bronze
(CF5100VNB)



Vintage Steel
(CF5100VS)

¹ - Optional installation for use with accessory control and transmitter. Secondary switch cup does not have pull chain or reverse switch holes.



CF5100VS (Vintage Steel) shown with
G54HWA Heritage Walnut Blades.



See page 32 - 33 for
the complete list of
blade options for the
Blade Select Series.



CF5100ORB
(Oil Rubbed Bronze)
shown with B77WA
Walnut Solid Wood Blade.



CF5100SW
(Satin White)
shown with G54SW
Satin White Blade.



CF5100VNB
(Venetian Bronze)
shown with B102VWA
Vintage Walnut Rattan Blade.

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

Laclede Eco **NEW!**
CF995

The Laclede Eco is the perfect fan for making a grand visual statement. This sculpted ceiling fan spans 62" and provides an ample amount of lighting with both a downlight and accent light. Choose a more contemporary approach with the Brushed Steel Finish or allow this piece of art to capture the imagination in our warm Venetian Bronze finish combination.

Features:

- 62" blade span
- Integrated light fixture uses five 13-watt medium base compact fluorescent bulbs (included) & the accent light uses four 13-watt medium base compact fluorescent bulbs (included)
- 10" downrod included

Includes:

- 6-Speed Remote Control with Receiver
- Removable Decorative Downrod Sleeve



Brushed Steel
(CF995BS)



Venetian Bronze
(CF995VNB)



CF995VNB (Venetian Bronze) with Reversible Walnut/Charcoal Blades. Walnut shown.

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

Amhurst
CF880

This craftsman influence fan boasts high detail in its sturdy features. This design can easily adapt to your style, from Emerson's warm two-toned Venetian Bronze finish, to an architecturally contemporary Brushed Steel finish to an industrially inspired Vintage Steel finish.

Features:

- 54" blade span
- Integrated light fixture uses two 60-watt candelabra bulbs (included)
- 4.5" downrod included

Includes:

- Wall Control with Receiver



Brushed Steel
(CF880BS)



Venetian Bronze
(CF880VNB)



Vintage Steel
(CF880VS)

AIRFLOW CF880: 5422 Cubic Feet Per Minute | 67 Watts on High (Excludes Lights)
AIRFLOW EFFICIENCY CF880: 80 Cubic Ft. Per Watt on High (Excludes Lights)

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

CF880VNB (Venetian Bronze) with Dark Cherry/Honey Oak Blades. Dark Cherry shown.



CF880VS (Vintage Steel) with Riverwash/Honey Oak Blades. Riverwash shown.

CF880BS (Brushed Steel) with Dark Cherry/Chocolate Blades. Chocolate shown.

Carrera Grande & Carrera Grande Eco

CF787 & CF788

With 44", 54", 60" or 72" spans*, this architecturally-sculpted, ventless housing commands a dramatic presence. For energy savvy consumers, the Carrera Grande Eco generates great air movement using less than 30 watts of energy. As a part of the Blade Select Series, either the Carrera Grande (CF787) or Carrera Grande Eco (CF788) can be custom designed with blades and light fixtures to achieve a personalized look.

Features:

- 44", 54", 60" or 72" blade span*
- Light fixture adaptable (Sold Separately)
- 4.5" downrod included

Includes:

- Carrera Grande - 4-Speed Slide Wall Control
- Carrera Grande Eco - 6-Speed Wall Control with Receiver
- Damp Location rating in AW, GBZ, GES, ORB, VS, SW, VNB and WW finishes



AIRFLOW CF787: 8389 Cubic Feet Per Minute | 84 Watts on High
AIRFLOW EFFICIENCY CF787: 100 Cubic Ft. Per Watt on High

AIRFLOW CF788: 7929 Cubic Feet Per Minute | 30 Watts on High
AIRFLOW EFFICIENCY CF788: 265 Cubic Ft. Per Watt on High

6 * 44" blade span blades not recommended for CF787.

See page 32 - 33 for the complete list of blade options for the Blade Select Series.



CF787VS (Vintage Steel) shown with G54DM Dark Mahogany Blades.



CF788GES Carrera Grande Eco (Golden Espresso) shown with B91WA Hand Carved Art Deco Blade in Walnut.



CF788AP Carrera Grande Eco (Antique Pewter) shown with B78DM Solid Wood Blade in Dark Mahogany.



CF788SW Carrera Grande Eco (Satin White) shown with B77SW Solid Wood Blade in Satin White.

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

Monterey Lumina CF776

The Monterey Lumina is a beautifully simple ceiling fan. With cleanly sculpted details this fan also includes a modern design bowl light perfectly suited for residential applications.

Features:

- 52" blade span
- Low Profile light fixture uses three 60-watt candelabra bulbs (included)
- 4.5" downrod included

Includes:

- Five Reversible Blades
- Low Profile Light Fixture



Brushed Steel
(CF776BS)



Oil Rubbed Bronze
(CF776ORB)



Satin White
(CF776SW)



CF776BS (Brushed Steel)
Dark Cherry/Dark Mahogany Blades.
Dark Cherry Blades shown.
Opal Matte glass.



CF776ORB (Oil Rubbed Bronze)
Dark Cherry/Walnut Blades.
Dark Cherry Blades shown.
Opal Matte glass.



CF776SW (Satin White)
Satin White/Maple Blades.
Satin White Blades shown.
Opal Matte glass.

Monterey II & 42" Monterey II **NEW!** CF772 & CF773

The Monterey II (CF772) not only provides great wind flow but is also well suited for open-concept living due to its availability in both 52" and 42" spans. The 42" Monterey (CF773) is well suited for small bedrooms while the coordinating 52" model functions well for larger applications such as a master bedroom or living room.



CF772ORB (Oil Rubbed Bronze)
Dark Cherry/Walnut Blades.
Dark Cherry Blades shown.



CF773BS (Brushed Steel)
Dark Cherry/Dark Mahogany
Blades. Dark Cherry Blades shown.



Brushed Steel
(CF772BS)
(CF773BS)



Oil Rubbed
Bronze
(CF772ORB)
(CF773ORB)



Satin White
(CF772SW)
(CF773SW)

Features:

- 42" and 52" blade span
- Light fixture adaptable
- 4.5" downrod included

Includes:

- Five Reversible Blades

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

Bella

CF452 & CF442

Available in both 42" (CF442) and 52" (CF452) spans, this ventless housing design offers a subtle craftsman influence to a traditional fan housing. This fan boasts wood veneer blades and comes in a variety of finishes, all of which are adaptable to Emerson accessory lighting fixtures.

Features:

- 52" or 42" blade span (42" in AW, SW & ORB only)
- Light fixture adaptable (Sold Separately)
- 4.5" downrod included

Includes:

- Five Reversible Blades



Antique Pewter (CF452AP) | Brushed Steel (CF452BS) | Satin White (CF452SW) | Gilded Bronze (CF452GBZ) | Golden Espresso (CF452GES)



Oil Rubbed Bronze (CF452ORB) | Summer White (CF452AW) | Venetian Bronze (CF452VNB) | Vintage Steel (CF452VS)

CF452AP (Antique Pewter)
Dark Maple/Dark Cherry Blades.
Dark Cherry Blades shown.



AIRFLOW CF452: 5614 Cubic Feet Per Minute | 72 Watts on High
AIRFLOW EFFICIENCY CF452: 78 Cubic Ft. Per Watt on High

AIRFLOW CF442: 4181 Cubic Feet Per Minute | 54 Watts on High
AIRFLOW EFFICIENCY CF442: 77 Cubic Ft. Per Watt on High

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

Highgrove

CF990

This sleek design offers architectural inspiration while still maintaining a low-profile integrated light fixture. The Highgrove is available in a rich Venetian Bronze finish as well as a clean and sleek Brushed Steel finish.

Features:

- 53" blade span
- Integrated light fixture uses two 50-Watt Halogen-Mini Candelabra Bulbs (included)
- Accent Light Adaptable (AL100)
- 4.5" downrod included

Includes:

- 4-Speed Remote Control with Receiver



Brushed Steel (CF990BS) | Venetian Bronze (CF990VNB)

CF990VNB (Venetian Bronze)
Walnut Blades.
Vintage Cream glass.



AIRFLOW CF990: 5116 Cubic Feet Per Minute | 62 Watts on High (Excludes Lights)
AIRFLOW EFFICIENCY CF990: 82 Cubic Ft. Per Watt on High (Excludes Lights)

CF990BS (Brushed Steel)
Dark Mahogany Blades.
Opal Matte glass.



For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

Southtowne *NEW!*
CF4900

Taking a cue from modern living, the Southtowne ceiling fan model achieves both beautiful form and premium function. This geometric and modern design houses the powerful and durable Emerson K55XL motor.

Features:

- 54" blade span
- Integrated light fixture uses two 50-watt mini candelabra base halogen bulbs (included)
- 4.5" downrod included

Includes:

- Five Reversible Blades
- Integrated Light Fixture
- 6-Speed Wall Control with Receiver
- Removable No-Light Plate



Brushed Steel
(CF4900BS)



Oil Rubbed Bronze
(CF4900ORB)



Vintage Steel
(CF4900VS)

CF4900ORB (Oil Rubbed Bronze)
Chocolate/Walnut Blades.
Walnut Blades shown.
Opal Matte glass.

CF4900BS (Brushed Steel)
Dark Mahogany/Walnut Blades.
Walnut Blades shown.
Opal Matte glass.

CF4900VS (Vintage Steel)
Riverwash/Walnut Blades.
Riverwash Blades shown.
Opal Matte glass.

Highrise *NEW!*
CF430

A unique housing ventilation pattern adorns this modern ceiling fan. Complemented with LED lighting, the Highrise ceiling fan provides a uniquely modern solution for a 50" span fan.

Features:

- 50" blade span
 - 17-watt LED integrated light
- Lumens: 1,300.
Correlated Color Temperature: 3,000.
Color Rendering Index: 80.
- 4.5" downrod included

Includes:

- Four Reversible Blades
- Integrated LED Light Fixture
- 4-Speed Wall Control with Receiver



Brushed Steel
(CF430BS)



Oil Rubbed Bronze
(CF430ORB)



Satin White
(CF430SW)

CF430BS (Brushed Steel)
Natural Cherry/Dark Mahogany Blades.
Dark Mahogany shown.
Opal Matte glass.

CF430ORB (Oil Rubbed Bronze)
Natural Cherry/Dark Mahogany Blades.
Natural Cherry shown.
Opal Matte glass.

AIRFLOW CF430: 4263 Cubic Feet Per Minute | 49 Watts on High
AIRFLOW EFFICIENCY CF430: 85 Cubic Ft. Per Watt on High

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

Wyatt *NEW!*
CF530

When ceiling height clearance is a concern, the Wyatt ceiling fan provides a sleekly contemporary solution with its bullet shape design and integrated light. The 48" blade span provides a suitable solution for any small to medium size rooms.

CF530BS (Brushed Steel)
Silver Blades.
Opal Matte glass.



CF530ORB (Oil Rubbed Bronze)
Oil Rubbed Bronze Blades.
Opal Matte glass.

Features:

- 48" blade span
- One 50-watt mini candelabra base halogen bulb (included)

Includes:

- Four Custom Blades
- Integrated Light Fixture
- Sliding Wall Control



Appliance White
(CF530WW)

Brushed Steel
(CF530BS)

Oil Rubbed
Bronze
(CF530ORB)

Bradshaw *NEW!*
CF890

This three blade ceiling fan offers a unique minimalistic aesthetic. Whether in Brushed Steel or Oil Rubbed Bronze finish, the Walnut blade provides a sense of warmth to this modern fan.

Features:

- 52" blade span
- Integrated light fixture uses two 50-watt mini-candelabra base halogen bulbs (included)
- 4.5" downrod included

Includes:

- Three Custom Blades
- Integrated Light Fixture
- 4-Speed Wall Control with Receiver



Brushed Steel
(CF890BS)

Oil Rubbed
Bronze
(CF890ORB)

Satin White
(CF890SW)

CF890ORB (Oil Rubbed Bronze)
Walnut Blades.
Opal Matte glass.



CF890BS (Brushed Steel)
Walnut Blade.
Opal Matte glass.

4TH Avenue CF766

This urban inspired design is suited for contemporary spaces by bringing a sense of vintage restoration. Louvered housing details and unique blade finishes perfectly combine a sense of industrial with home.

Features:

- 60" blade span
- Integrated light fixture uses two 60-watt candelabra bulbs (included)
- 8" downrod included

Includes:

- Three Blades
- Integrated Light Fixture
- Remote Control with Receiver



Brushed Steel
(CF766BS)
(CF766SBS)



Oil Rubbed
Bronze
(CF766ORB)



Vintage Steel
(CF766VS)



CF766BS (Brushed Steel)
Chocolate Blades.
Opal Matte glass.

CF766ORB (Oil Rubbed Bronze)
Oil Rubbed Bronze Blades.
Opal Matte glass.

CF766VS (Vintage Steel)
Riverwash Blades.
Vintage Cream glass.

Luxe Eco CF550

The Luxe Eco is a unique, simple design which captures the imagination. The Luxe Eco is available in Oil Rubbed Bronze and Brushed Steel finishes and can be paired with either Walnut or Dark Mahogany blades. In addition to the unique cut-out blades, this fan also houses the Emerson EcoMotor, making it one of the most efficient fans in the Emerson line.

Features:

- 54" blade span
- Integrated light fixture uses two 50-watt Mini-Candelabra Halogen Bulbs (included)
- 4.5" downrod included

Includes:

- Five Custom Wood Veneer Blades
- Integrated Light Fixture
- Removable No-Light Plate
- 6-Speed Wall Control with Receiver



Brushed Steel
(CF550WABS)
(CF550DMBS)



Oil Rubbed
Bronze
(CF550WAORB)
(CF550DMORB)

CF550DMORB (Oil Rubbed Bronze)
Dark Mahogany Blades.
Opal Matte glass.

AIRFLOW CF550: 6974 Cubic Feet Per Minute | 33 Watts on High (Excludes Lights)
AIRFLOW EFFICIENCY CF550: 210 Cubic Ft. Per Watt on High (Excludes Lights)



CF550WABS (Brushed Steel)
Walnut Blades.
Opal Matte glass.



For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

AIRFLOW CF766: 6403 Cubic Feet Per Minute | 48 Watts on High
AIRFLOW EFFICIENCY CF766: 132 Cubic Ft. Per Watt on High

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

Midway Eco CF955

This sleek design houses Emerson's Eco Motor which maximizes energy efficiency, while still moving up to 40% more air than standard blades due to its distinctly engineered airfoil blades.

Features:

- 54" airfoil design blade
- Integrated light fixture uses four 13-watt GU24 fluorescent bulbs (included)
- 4.5" downrod included

Includes:

- Five Custom Blades
- Integrated Light Fixture
- 6-Speed Remote Control with Receiver



Appliance White
(CF955WW)



Brushed Steel
(CF955BS)



Oil Rubbed Bronze
(CF955ORB)



CF955BS (Brushed Steel)
Midnight Bordeaux Blades.
Opal Matte glass.



CF955ORB (Oil Rubbed Bronze)
Oil Rubbed Bronze Blades.
Opal Matte glass.

AIRFLOW CF955: 6085 Cubic Feet Per Minute | 18 Watts on High (Excludes Lights)
AIRFLOW EFFICIENCY CF955: 336 Cubic Ft. Per Watt on High (Excludes Lights)

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

Loft CF765

The three blade, 60" Loft fan captures the essence of Industrial design but is engineered to suit residential applications. Distinct airfoil blades and exposed motor casing create the unique loft-look suitable for urban-contemporary settings.

Features:

- 60" blade span
- Not light fixture adaptable
- 6" downrod included

Includes:

- Three High-Efficiency Blades
- 4-Speed Slide Wall Control



Appliance White
(CF765WW)



Barbeque Black
(CF765BQ)



Brushed Steel
(CF765BS)

AIRFLOW CF765: 75709 Cubic Feet Per Minute | 81 Watts on High
AIRFLOW EFFICIENCY CF765: 92 Cubic Ft. Per Watt on High

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

CF765BS (Brushed Steel)
Brushed Steel Blades.



Curva & Curva Sky

CF152, CF252,
CF144 & CF244

This compact and sleekly contoured fan is offered as a downrod version in the Curva (CF252, CF244) or as a ceiling snuggler version in the Curva Sky (CF152, CF144). Both models are offered in a 52" and 44" span in a variety of finishes and also include a no-light plate in the box.

Features:

- 52" or 44" blade span
- Integrated light fixture uses two 50-watt mini-candelabra halogen bulbs (included)
- 4.5" downrod included (Curva only)

Includes:

- Three Weather-Resistant Blades
- Integrated Light Fixture
- Removable No-Light Plate
- 6-Speed Remote Control With Receiver
- Wet Location Rating in ORB and WW finishes.



Appliance White
(CF152WW)
(CF252WW)
(CF144WW)
(CF244WW)



Brushed Steel
(CF152BS)
(CF252BS)
(CF144BS)
(CF244BS)



Oil Rubbed
Bronze
(CF152ORB)
(CF252ORB)
(CF144ORB)
(CF244ORB)

AIRFLOW CF152: 5393 Cubic Feet Per Minute | 46 Watts on High (Excludes Lights)
AIRFLOW EFFICIENCY CF152: 116 Cubic Ft. Per Watt on High (Excludes Lights)
AIRFLOW CF144: 4217 Cubic Feet Per Minute | 45 Watts on High (Excludes Lights)
AIRFLOW EFFICIENCY CF144: 93 Cubic Ft. Per Watt on High (Excludes Lights)
AIRFLOW CF252: 5329 Cubic Feet Per Minute | 45 Watts on High (Excludes Lights)
AIRFLOW EFFICIENCY CF252: 118 Cubic Ft. Per Watt on High (Excludes Lights)
AIRFLOW CF244: 4280 Cubic Feet Per Minute | 44 Watts on High (Excludes Lights)
AIRFLOW EFFICIENCY CF244: 97 Cubic Ft. Per Watt on High (Excludes Lights)

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

CF152ORB (Oil Rubbed Bronze)
Oil Rubbed Bronze.
Opal Matte glass.

CF252BS (Brushed Steel)
Brushed Steel Blades.
Opal Matte glass.

CF152WW (Appliance White)
Appliance White Blades.
Opal. Matte glass.

Highpointe

CF205

The Highpointe fan is outfitted with architecturally inspired cables and a unique blade attachment design. With the cables, this fan is suited for 9' ceiling and is sure to be a statement piece in any of its three finish options Vintage Steel, Brushed Steel and Golden Espresso.

Features:

- 54" blade span
- Integrated light fixture uses two 50-watt mini-candelabra halogen bulb (included)
- Two downrods included: 6" & 12"

Includes:

- Three Custom Blades
- Integrated Light Fixture
- Removable No-Light Plate
- Removable Decorative Cables
- 4-Speed Remote Control with Receiver



Brushed Steel
(CF205BS)



Golden Espresso
(CF205GES)



Vintage Steel
(CF205VS)

AIRFLOW CF205: 5678 Cubic Feet Per Minute | 66 Watts on High
AIRFLOW EFFICIENCY CF205: 86 Cubic Ft. Per Watt on High

CF205GES (Golden Espresso)
Chocolate Blades.
Sandstone glass.

CF205BS (Brushed Steel)
Dark Mahogany Blades.
Opal Matte glass.

CF205VS (Vintage Steel)
Honey Oak/Riverwash Blades.
Honey Oak Blades shown.
Vintage Cream glass.

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

Crown Select CF4501

As a part of the Blade Select Series, the Crown Select easily brings a sense of tradition and classic beauty to any home. With over 50 blade options to choose from, any owner can easily pair this fan to create the custom, classic look they desire.

Features:

- 42", 52", 58" or 70" blade span
- Accent lighting with patented swivel sockets uses three 25-watt candelabra bulbs (included)
- Light fixture adaptable
- 4.5" downrod included

Includes:

- Accent lighting
- Patented Swivel Socket



See page 32 - 33 for the complete list of blade options for the Blade Select Series.



CF4501AP (Antique Pewter)
Shown with B77DM Solid Wood
Blades in Dark Mahogany.

CF4501VNB
(Venetian Bronze)
Shown with G54DM
Dark Mahogany
Blades.

Avant Eco CF921

The Avant Eco boasts Emerson's highest technology with our energy efficient EcoMotor yet it still maintains a sense of tradition with a modest transitional housing design. The Avant Eco is also a part of the Blade Select Series, allowing this platform the ability to transition itself into a 44", 54", 60" or 72" fan custom designed to fit your taste.

Features:

- 44", 54", 60" or 72" blade span
- Light fixture adaptable
- Accent light adaptable (AL100)
- 4.5" downrod included

Includes:

- 6-Speed Remote Control with Receiver



AIRFLOW CF921: 7985 Cubic Feet Per Minute | 31 Watts on High
AIRFLOW EFFICIENCY CF921: 256 Cubic Ft. Per Watt on High

See page 32 for the complete list of blade options for the Blade Select Series.



CF921BS (Brushed Steel)
Shown with B78WA
Solid Wood Walnut Blades.

CF921SW (Satin White)
Shown with G54SW
Satin White Blades.

CF921GES (Golden Espresso)
Shown with B90VBL Hand Carved
Classic Blade in Vintage Black.

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

Premium Select

CF4801

An Emerson Original, the Premium Select fan maintains a sense of heritage with its traditional housing style. As a part of the Blade Select Series, this fan housing can be paired with over 50 blade options allowing it to expand to 42", 52", 58" or 70" in span.

Features:

- 42", 52", 58" or 70" blade span
- Accent light with patented swivel sockets use three 25-watt candelabra bulbs (included)
- Light fixture adaptable
- 4.5" downrod included

Includes:

- Accent Lighting
- Patented Swivel Socket



CF4801ORB (Oil Rubbed Bronze)
Shown with G54WA Blade in Walnut.

See page 32 - 33 for the complete list of blade options for the Blade Select Series.

Prima

CF901

CF901GES (Golden Espresso)
Dark Cherry/Chocolate Blades.
Dark Cherry Blades shown.

The Prima ceiling fan comes in a 52" span and is available in five finishes. This simple and elegant design also features accent light adaptability, allowing for the installation of our AL100 which provides a soft upward glow perfect for night lighting.



Features:

- 52" blade span
- Accent light adaptable (AL100)
- Light fixture adaptable
- 4.5" downrod included

Includes:

- Five Reversible Blades
- 4-Speed Slide Wall Control



For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

AIRFLOW CF901: 5263 Cubic Feet Per Minute | 59 Watts on High
AIRFLOW EFFICIENCY CF901: 89 Cubic Ft. Per Watt on High

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com

Prima Snugger CF905

The Prima Snugger ceiling fan is perfect for applications where ceiling fan clearance height is a concern. This clean traditional design mounts directly to the ceiling, hanging just 8" in total height.

Includes:

- Five Reversible Blades
- 4-Speed Slide Wall Control



Brushed Steel
(CF905BS)



Satin White
(CF905SW)



Golden Espresso
(CF905GES)



Oil Rubbed Bronze
(CF905ORB)



Venetian Bronze
(CF905VNB)

CF905BS (Brushed Steel)
Dark Cherry/Chocolate Blades.
Dark Cherry shown.



CF905GES (Golden Espresso)
Dark Cherry/Chocolate Blades.
Dark Cherry Blades shown.

Batalie Breeze **NEW!** CF621

The Batalie Breeze is a tropically inspired fan with beautifully designed rattan-influence blades. This wet location fan comes in three finishes which allows for installation versatility for both indoor and outdoor environments.

Features:

- 52" blade spans
- Light fixture adaptable
- 4.5" downrod included

Includes:

- Five Custom Blades



Satin White
(CF621SW)



Venetian Bronze
(CF621VNB)



Vintage Steel
(CF621VS)

AIRFLOW CF621: 5255 Cubic Feet Per Minute | 75 Watts on High
AIRFLOW EFFICIENCY CF621: 70 Cubic Ft. Per Watt on High



CF621VNB (Venetian Bronze)
Weather Resistant Antique Stain
Wicker Leaf Blades.



CF621VS (Vintage Steel)
Weather Resistant Antique Stain
Wicker Leaf Blades



CF621SW (Satin White)
Weather Resistant Satin White
Highlights Wicker Leaf Blades

For ordering information or additional model specifications,
see our full line catalog or go to emersonfans.com

Maui Bay CF2000

The Maui Bay ceiling fan houses the Emerson K55XL motor and adapts to several different natural-blade options. From a true natural leaf blade, to hand-woven wicker blades to a dramatic 80" span with the use of our Bent Wood Blade, this premium fan design allows for interior versatility.

Features:

- 52" blade span
- Light fixture adaptable
- 6" downrod included
- 4 or 5 blade assembly option



Antique Brass
(CF2000AB)



Antique Pewter
(CF2000AP)



Oil Rubbed Bronze
(CF2000ORB)

CF2000ORB
(Oil Rubbed Bronze)
Shown with B20HP Wicker
Blades in Honey Finish.



CF2000AP (Antique Pewter)
Shown with B50DC Solid Wood Hand
Carved Leaf Blades in Dark Cherry.



Ashland **NEW!** CF717

A new take on a traditional fan, the Ashland ceiling fan provides an included light fixture and thoughtfully simple design details. The Ashland is available in Brushed Steel, Oil Rubbed Bronze and Satin White.

Features:

- 52" blade span
- Three 60-watt candelabra bulbs (included)
- 4.5" downrod included

Includes:

- 5 Reversible Blades
- Integrated Light Fixture



Brushed Steel
(CF717BS)



Oil Rubbed Bronze
(CF717ORB)



Satin White
(CF717SW)

AIRFLOW CF717: 4939 Cubic Feet Per Minute | 56 Watts on High
AIRFLOW EFFICIENCY CF717: 88 Cubic Ft. Per Watt on High



CF717ORB (Oil Rubbed Bronze)
Dark Cherry/Walnut Blades.
Dark Cherry Blades shown.
Opal Matte glass.

CF717BS (Brushed Steel)
Dark Cherry/Walnut Blades.
Walnut Blades shown.
Opal Matte glass.

CF717SW (Satin White)
Satin White/Maple Blades.
Satin White Blades shown.
Opal Matte glass.

For ordering information or additional model specifications, see our full line catalog or go to emersonfans.com



Pro Series

CF712

AIRFLOW CF712: 5224 Cubic Feet Per Minute | 61 Watts on High (Excludes Lights)
AIRFLOW EFFICIENCY CF712: 85 Cubic Ft. Per Watt on High (Excludes Lights)

Includes:

- Five Reversible Blades
- Light Fixture
- Dual-Mount Feature
- Removable No-Light Cover
- Available Finishes: AB, AW, BS, ORB, WW, WORB



Pro Series ES

CF713

AIRFLOW CF713: 5063 Cubic Feet Per Minute | 65 Watts on High (Excludes Lights)
AIRFLOW EFFICIENCY CF713: 78 Cubic Ft. Per Watt on High (Excludes Lights)

Includes:

- Five Reversible Blades
- Light Fixture
- Dual-Mount Feature
- Removable No-Light Cover
- Available Finishes: BS, ORB, WW



50" PRO Series II

CF711

AIRFLOW CF711: 5403 Cubic Feet Per Minute | 84 Watts on High (Excludes Lights)
AIRFLOW EFFICIENCY CF711: 64 Cubic Ft. Per Watt on High (Excludes Lights)

Includes:

- Five Reversible Blades
- 4-Way Light Fixture
- Dual-Mount Feature
- Removable No-Light Cover
- Available Finishes: AB, AW, BS, ORB, ORS, WW



CF713ORB Pro Series ES
(See pg. 30 for details)



42" Pro Series II

CF710VNB

AIRFLOW CF710: 3834 Cubic Feet Per Minute | 45 Watts on High (Excludes Lights)
AIRFLOW EFFICIENCY CF710: 86 Cubic Ft. Per Watt on High (Excludes Lights)

Includes:

- Five Reversible Blades
- 4-Way Light Fixture
- Dual-Mount Feature
- Removable No-Light Cover
- Available Finishes: BS, ORB, WW



Builder

CF700

AIRFLOW CF700: 5002 Cubic Feet Per Minute | 64 Watts on High (Excludes Lights)
AIRFLOW EFFICIENCY CF700: 78 Cubic Ft. Per Watt on High (Excludes Lights)

Includes:

- Five Reversible Blades
- Available Finishes: AW, BS, ORB, WW



Builder Unipack

CF701

AIRFLOW CF701: 4860 Cubic Feet Per Minute | 63 Watts on High (Excludes Lights)
AIRFLOW EFFICIENCY CF701: 77 Cubic Ft. Per Watt on High (Excludes Lights)

Includes:

- Five Reversible Blades
- Integrated Light Fixture
- Available Finishes: BS, ORB, WW



48" Industrial Fan BS

HF948

AIRFLOW HF948: 6879 Cubic Feet Per Minute | 72 Watts on High
AIRFLOW EFFICIENCY HF948 93 Cubic Ft. Per Watt on High

Includes:

- Three Contoured Metal Blades
- Available Finishes: BS, W



56" Industrial Fan BQ

HF956

AIRFLOW HF956: 9757 Cubic Feet Per Minute | 95 Watts on High
AIRFLOW EFFICIENCY HF956 90 Cubic Ft. Per Watt on High

Includes:

- Three Contoured Metal Blades
- Available Finishes: BQ, BS, W



60" Industrial Fan WW

HF1160

AIRFLOW HF1160: 10649 Cubic Feet Per Minute | 63 Watts on High
AIRFLOW EFFICIENCY HF1160: 90 Cubic Ft. Per Watt on High

Includes:

- Three Airfoil Blades
- Available Finishes: BQ, BS, WW

Blade Select SERIES

Choose from any of the blades shown on these pages to complete your custom Blade Select Series ceiling fan. All Blade Select Series blades shown are compatible with the following ceiling fans. Some restrictions apply. Refer to footnotes for compatibility.



Penbrooke Select
CF5100 - pg. 2



Carrera Grande
CF787 - pg. 6



Carrera Grande Eco
CF788 - pg. 6



Crown Select
CF4501 - pg. 22



Avant Eco
CF921 - pg. 23



Premium Select
CF4801 - pg. 24



WEATHER RESISTANT BLADES - 22" Length, 52-54" Span Blades
Our weather resistant blades are made of resin with a UV protective coating. For a fan to qualify as wet location, the housing must also be rated wet location.



B62VBL¹ 22" Palmetto Blade Vintage Black Finish Weather-Resistant Resin	B63ASW¹ 22" Rattan Leaf Blade Antique Stain Wicker Finish Weather-Resistant Resin	B110AW 22" Shutter Blade Summer White Finish Weather-Resistant Resin	B110WA 22" Shutter Blade Walnut Finish Weather-Resistant Resin	B112AWL 22" Wainscoting Blade Summer White with Latte Highlights Finish Weather-Resistant Resin	B112MAB 22" Wainscoting Blade Medium Antique Brown Finish Weather-Resistant Resin	G54WAW 22" Blade Summer White Finish Weather-Resistant Resin	G54WVNB 22" Blade Venetian Bronze Finish Weather-Resistant Resin	G54WWA 22" Blade Walnut Finish Weather-Resistant Resin
--	--	--	--	---	---	---	---	---



SOLID WOOD BLADES - 22", 25", 31" Length, 52/54", 58/60", 70/72" Span Blades
B77 blades are 22" (52-54" Span). B78 blades are 25" (58-60" Span). B79 blades are 31" (70-72" Span). All B77, B78 & B79 are suitable for damp location and indoor listed fans. These solid wood blades feature a large bevel.



B78AW (shown) 25" Solid Wood Summer White	B78CH (shown) 25" Solid Wood Chocolate	B78DM (shown) 25" Solid Wood Dark Mahogany	B78NC (shown) 25" Solid Wood Natural Cherry	B78SW (shown) 25" Solid Wood Satin White	B78TK (shown) 25" Solid Wood Teak	B78WA (shown) 25" Solid Wood Walnut
---	--	--	---	--	---	---



DECORATIVE HAND CARVED BLADES - 22" Length, 52-54" Span Blades
Solid wood blades with decorative detailing.



B61VWA¹ 22" Hand Carved Solid-Wood Oar Blade Vintage Walnut	B100DO 22" Classic Hand Carved Wood Dark Oak	B101WA 22" Deco Hand Carved Wood Walnut	B102VWA 22" Rattan Carved Vintage Walnut
--	--	---	--



B103DWA 22" Ornate Hand Carved Wood Dark Walnut	B105HCB 22" Hand Carved Wood Beaded Walnut	B107HCT 22" Hand Carved Wood Tapered Dark Walnut	B108HCW 22" Hand Carved Wood Walnut	B109DC 22" Hand Carved Leaf Dark Cherry	B109DO 22" Hand Carved Leaf Dark Oak
---	--	--	---	---	--



DECORATIVE HAND CARVED BLADES - 25" Length, 58-60" Span Blades
Solid wood blades with decorative detailing.



B90DO 25" Classic Carved Wood Dark Oak	B90VBL 25" Classic Carved Wood Vintage Black	B91WA 25" Deco Carved Wood Walnut	B92VWA¹ 25" Rattan Carved Wood Vintage Walnut	B97DWA 25" Ornate Carved Wood Dark Walnut
--	--	---	--	---

WOOD VENEER BLADES¹
• G54 Series: 22" Length, 52-54" Span Blades
• G44 Series: 18" Length, 42-44" Span Blades
Micro-balanced within one gram. Six-layer wood veneer blades are cross-laminated for stability and warp resistance. Sealed to resist moisture. AW, BS, CH, SW, WW Finishes are custom painted to match housing.



G54AW Summer White	G54BS Brushed Steel	G54CH Chocolate
------------------------------	-------------------------------	---------------------------



G54DC/G44DC Dark Cherry	G54DM Dark Mahogany	G54HO Heritage Walnut	G54HO Honey Oak	G54MH Mahogany	G54MO Medium Oak
-----------------------------------	-------------------------------	---------------------------------	---------------------------	--------------------------	----------------------------



G54NC Natural Cherry	G54TK/G44TK Teak	G54RW Riverwash	G54SW/G44SW Satin White	G54WA/G44WA Walnut	G54WW/G44WW Appliance White
--------------------------------	----------------------------	---------------------------	-----------------------------------	------------------------------	---------------------------------------

¹ CF4501, CF4801, CF921 will not accept B61, B62 or B63 blades.

¹ AW, BS, SW and WW are painted blades



Air Comfort Products

8100 W. Florissant Avenue • Saint Louis, MO 63136
Customer Service Tel: 1-800-237-6511 • Customer Service Fax: 1-800-525-7248
Customer Service Email: acpfax.customerservice@emerson.com

emersonfans.com