



Specification Grade Devices

Buyer's Guide



Hubbell-Pro™ Heavy Duty Specification Grade Series
Hubbell Specification Grade Commercial Series



Hubbell-Pro™ Heavy Duty Specification Grade and Commercial

Hubbell-Pro™ Heavy Duty Specification Grade

Description	Color	Standard Receptacle		Hospital Grade	
		15A 125V	20A 125V	15A 125V	20A 125V
SNAPConnect™ Finder Face	Brown	SNAP5262	SNAP5362	SNAP8200	SNAP8300
	Almond	SNAP5262AL	SNAP5362AL	SNAP8200AL	SNAP8300AL
	Black	SNAP5262BK	SNAP5362BK	SNAP8200BK	SNAP8300BK
	Gray	SNAP5262GY	SNAP5362GY	SNAP8200GY	SNAP8300GY
	Ivory	SNAP5262I	SNAP5362I	SNAP8200I	SNAP8300I
	Light Almond	SNAP5262LA	SNAP5362LA	SNAP8200LA	SNAP8300LA
	Red	SNAP5262R	SNAP5362R	SNAP8200R	SNAP8300R
	Office White	SNAP5262OW	SNAP5362OW	SNAP8200OW	SNAP8300OW
	White	SNAP5262W	SNAP5362W	SNAP8200W	SNAP8300W

Description	Color	Finder Face Standard Receptacle		Hospital Grade	
		15A 125V	20A 125V	15A 125V	20A 125V
Heavy Duty Specification Duplex Side and Back Wired	Brown	5262B	5362B	8200B	8300B
	Almond	5262AL	5362AL	8200AL	8300AL
	Black	5262BLK	5362BLK	—	—
	Blue	5262BL	5362BL	—	—
	Gray	5262G	5362G	8200G	8300G
	Ivory	5262I	5362I	8200I	8300I
	Light Almond	5262LA	5362LA	8200LA	8300LA
	Red	5262R	5362R	8200R	8300R
	Office White	5262OW	5362OW	—	—
	White	5262W	5362W	8200W	8300W

Specification Grade Commercial

Description	Color	Standard Receptacle		Tamper-Resistant	
		15A 125V	20A 125V	15A 125V	20A 125V
Style Line® Decorator Side and Back Wired	Brown	DR15	DR20	DR15TR	DR20TR
	Almond	DR15AL	DR20AL	DR15ALTR	DR20ALTR
	Black	DR15BLK	DR20BLK	DR15BLKTR	DR20BLKTR
	Gray	DR15GRY	DR20GRY	DR15GRYTR	DR20GRYTR
	Ivory	DR15I	DR20I	DR15ITR	DR20ITR
	Light Almond	DR15LA	DR20LA	DR15LATR	DR20LATR
	Office White	DR15OW	DR20OW	—	—
	White	DR15WHI	DR20WHI	DR15WHITR	DR20WHITR
Smooth Face Side and Back Wired	Brown	BR15	BR20	BR15TR	BR20TR
	Almond	BR15AL	BR20AL	BR15ALTR	BR20ALTR
	Black	BR15BLK	BR20BLK	BR15BLKTR	BR20BLKTR
	Gray	BR15GRY	BR20GRY	BR15GRYTR	BR20GRYTR
	Ivory	BR15I	BR20I	BR15ITR	BR20ITR
	Light Almond	BR15LA	BR20LA	BR15LATR	BR20LATR
	White	BR15WHI	BR20WHI	BR15WHITR	BR20WHITR
Smooth Face Side Wired	Brown	CR15	CR20	CR15TR	CR20TR
	Almond	CR15AL	CR20AL	CR15ALTR	CR20ALTR
	Black	CR15BLK	CR20BLK	CR15BLKTR	CR20BLKTR
	Gray	CR15GRY	CR20GRY	CR15GRYTR	CR20GRYTR
	Ivory	CR15I	CR20I	CR15ITR	CR20ITR
	Light Almond	CR15LA	CR20LA	CR15LATR	CR20LATR
	White	CR15WHI	CR20WHI	CR15WHITR	CR20WHITR
Finder Face Side Wired	Brown	CRF15	CRF20	—	—
	Almond	CRF15AL	CRF20AL	—	—
	Black	CRF15BLK	CRF20BLK	—	—
	Gray	CRF15GRY	CRF20GRY	—	—
	Ivory	CRF15I	CRF20I	—	—
	Light Almond	CRF15LA	CRF20LA	—	—
	Office White	CRF15OW	CRF20OW	—	—
	White	CRF15WHI	CRF20WHI	—	—



SNAP5362I



SNAP8200I



SNAP2162



5362I



5252AI



DR20ITR




DR20GRYWRTR




IG20DR

Specification Grade Duplex Receptacles



 Style Line® Decorator Devices are not Fed Spec Listed	Style Line® Decorator*		Hospital Grade Style Line® Decorator		SNAPConnect™ Pigtail Terminal	
	15A 125V	20A 125V	15A 125V	20A 125V	Description	
	SNAP2152	SNAP2162	SNAP2172	SNAP2182	Clear terminal; 6 in. leads	
	SNAP2152AL	SNAP2162AL	SNAP2172AL	SNAP2182AL	Straight	
	SNAP2152BK	SNAP2162BK	SNAP2172BK	SNAP2182BK	Solid wire	SNAP6R1
	SNAP2152GY	SNAP2162GY	SNAP2172GY	SNAP2182GY	Stranded wire	SNAP6R2
	SNAP2152I	SNAP2162I	SNAP2172I	SNAP2182I	90° Angle	
	SNAP2152LA	SNAP2162LA	SNAP2172LA	SNAP2182LA	Solid wire	SNAP1R
	SNAP2152R	SNAP2162R	SNAP2172R	SNAP2182R	Stranded wire	SNAP2R
	—	—	—	—		
	SNAP2152W	SNAP2162W	SNAP2172W	SNAP2182W		
	Smooth Face Standard Duplex		▲ Isolated Ground			
	15A 125V	20A 125V	15A 125V	20A 125V		
	5252AB	5352AB	IG5252	IG5352		
	5252AAL	5352AAL	IG5252AL	IG5352AL		
	5252ABLK	5352ABLK	IG5252GY	IG5352GY		
	—	—	IG5252I	IG5352I		
	5252AG	5352AG	IG5252LA	IG5352LA		
	5252AI	5352AI	IG5252W	IG5352W		
	5252ALA	5352ALA				
	5252AR	5352AR				
	5252AOW	5352AOW				
	5252AW	5352AW				



Weather Resistant		Weather and Tamper-Resistant		▲ Isolated Ground		
15A 125V	20A 125V	15A 125V	20A 125V	Color	15A 125V	20A 125V
—	—	DR15WRTR	DR20WRTR	Orange	IG15DR	IG20DR
—	—	DR15ALWRTR	DR20ALWRTR	Almond	IG15DRAL	IG20DRAL
—	—	DR15BLKWRTR	DR20BLKWRTR	Gray	IG15DRGRY	IG20DRGRY
—	—	DR15GRYWRTR	DR20GRYWRTR	Ivory	IG15DRI	IG20DRI
—	—	DR15IWRTR	DR20IWRTR	Light Almond	IG15DRLA	IG20DRLA
—	—	DR15LAWRTR	DR20LAWRTR	White	IG15DRW	IG20DRW
—	—	—	—			
—	—	DR15WHIWRTR	DR20WHIWRTR			
	BR15WR	BR20WR	BR15WRTR	BR20WRTR	—	—
	BR15ALWR	BR20ALWR	BR15ALWRTR	BR20ALWRTR	—	—
	BR15BLKWR	BR20BLKWR	BR15BLKWRTR	BR20BLKWRTR	—	—
	BR15GRYWR	BR20GRYWR	BR15GRYWRTR	BR20GRYWRTR	—	—
	BR15IWR	BR20IWR	BR15IWRTR	BR20IWRTR	—	—
	BR15LAWR	BR20LAWR	BR15LAWRTR	BR20LAWRTR	—	—
	BR15WHIWR	BR20WHIWR	BR15WHIWRTR	BR20WHIWRTR	—	—
—	—	—	—	Orange	IG15CR	IG20CR
—	—	—	—	Almond	IG15CRAL	IG20CRAL
—	—	—	—	Gray	IG15CRGRY	IG20CRGRY
—	—	—	—	Ivory	IG15CRI	IG20CRI
—	—	—	—	Light Almond	IG15CRLA	IG20CRLA
—	—	—	—	White	IG15CRWHI	IG20CRWHI
—	—	—	—			
—	—	—	—			
—	—	—	—			
—	—	—	—			
—	—	—	—			
—	—	—	—			



BR15I BR15IWR BR20WRTR CR15I CR15TR CRF15WHI IG20CR



Specification Grade Switches



Hubbell-Pro™ Heavy Duty Specification Grade Side and Back Wired



Color	Single Pole		Double Pole		Three Way		Four Way	
	15A	20A	15A	20A	15A	20A	15A	20A
Brown	1201B	1221B	—	1222B	1203B	1223B	—	1224B
Almond	1201AL	1221AL	—	1222AL	1203AL	1223AL	—	1224AL
Black	1201BK	1221BK	—	1222BK	1203BK	1223BK	—	1224BK
Gray	1201GY	1221GY	—	1222GY	1203GY	1223GY	—	1224GY
Ivory	1201I	1221I	—	1222I	1203I	1223I	—	1224I
Light Almond	1201LA	1221LA	—	1222LA	1203LA	1223LA	—	1224LA
Red	—	1221R	—	1222R	—	1223R	—	1224R
White	1201W	1221W	—	1222W	1203W	1223W	—	1224W

Specification Grade Commercial Style Line® Decorator Side and Back Wired



Color	Single Pole		Double Pole		Three Way		Four Way	
	15A	20A	15A	20A	15A	20A	15A	20A
Brown	DS115	DS120	—	DS220B	DS315	DS320	—	DS420
Almond	DS115AL	DS120AL	—	DS220AL	DS315AL	DS320AL	—	DS420AL
Black	DS115BK	DS120BK	—	DS220BK	DS315BK	DS320BK	—	DS420BK
Gray	DS115GY	DS120GY	—	DS220GY	DS315GY	DS320GY	—	DS420GY
Ivory	DS115I	DS120I	—	DS220I	DS315I	DS320I	—	DS420I
Light Almond	DS115LA	DS120LA	—	DS220LA	DS315LA	DS320LA	—	DS420LA
Office White	DS115OW	DS120OW	—	DS220OW	DS315OW	DS320OW	—	DS420OW
White	DS115W	DS120W	—	DS220W	DS315W	DS320W	—	DS420W

Specification Grade Commercial Illuminated and Pilot Light Style Line® Decorator



Color	Single Pole		Double Pole		Three Way		Four Way	
	15A	20A	15A	20A	15A	20A	15A	20A
Ivory	—	DS120IL	—	—	—	DS320IL	—	—
White	—	DS120ILW	—	—	—	DS320ILW	—	—
Pilot light	—	DS120PL	—	—	—	—	—	—

Specification Grade Commercial Side and Back Wired



Color	Single Pole		Double Pole		Three Way		Four Way	
	15A	20A	15A	20A	15A	20A	15A	20A
Brown	CSB115	CSB120	CSB215	CSB220	CSB315	CSB320	CSB415	CSB420
Almond	CSB115AL	CSB120AL	CSB215AL	CSB220AL	CSB315AL	CSB320AL	CSB415AL	CSB420AL
Black	CSB115BK	CSB120BK	CSB215BK	CSB220BK	CSB315BK	CSB320BK	CSB415BK	CSB420BK
Gray	CSB115GY	CSB120GY	CSB215GY	CSB220GY	CSB315GY	CSB320GY	CSB415GY	CSB420GY
Ivory	CSB115I	CSB120I	CSB215I	CSB220I	CSB315I	CSB320I	CSB415I	CSB420I
Light Almond	CSB115LA	CSB120LA	CSB215LA	CSB220LA	CSB315LA	CSB320LA	CSB415LA	CSB420LA
Office White	—	CSB120OW	—	CSB220OW	—	CSB320OW	—	CSB420OW
Red	—	CSB120R	—	CSB220R	—	CSB320R	—	CSB420R
White	CSB115W	CSB120W	CSB215W	CSB220W	CSB315W	CSB320W	CSB415W	CSB420W

Specification Grade Commercial Side Wired



Color	Single Pole		Double Pole		Three Way		Four Way	
	15A	20A	15A	20A	15A	20A	15A	20A
Brown	CS115	CS120	—	—	CS315	CS320	—	—
Almond	CS115AL	CS120AL	—	—	CS315AL	CS320AL	—	—
Gray	CS115GY	CS120GY	—	—	CS315GY	CS320GY	—	—
Ivory	CS115I	CS120I	—	—	CS315I	CS320I	—	—
Light Almond	CS115LA	CS120LA	—	—	CS315LA	CS320LA	—	—
Office White	CS115OW	CS120OW	—	—	CS315OW	CS320OW	—	—
White	CS115W	CS120W	—	—	CS315W	CS320W	—	—



1201I



1221B



DS120



DS120IL



CS115I



CSB120



Commercial Series LED, GFCI

Description	Color	Standard Receptacles		Hospital Grade	
		15A 125V	20A 125V	15A 125V	20A 125V
15 and 20 Ampere; 125 Volts; 2-Pole, 3-Wire Grounding Meets July 28, 2006 UL Standard 943 Class A GFCI	Brown Almond Black Gray Ivory Light Almond Office White Red White	GF15LA	GF20LA	GFR8200HLA	GFR8300HLA
		GF15ALLA	GF20ALLA	GFR8200HALLA	GFR8300HALLA
Tamper-Resistant; 15 and 20 Ampere; 125 Volts; 2-Pole, 3-Wire Grounding Meets July 28, 2006 UL Standard 943 Class A GFCI	Brown Almond Black Gray Ivory Light Almond Office White Red White	GF15BKLA	GF20BKLA	GFR8200HBKLA	GFR8300HBKLA
		GF15GYLA	GF20GYLA	GFR8200HGYLA	GFR8300HGYLA
		GF15ILA	GF20ILA	GFR8200HILA	GFR8300HILA
		GF15LALA	GF20LALA	GFR8200HLALA	GFR8300HLALA
		GF15OWLA	GF20OWLA	GFR8200HOWLA	GFR8300HOWLA
		GF15RLA	GF20RLA	GFR8200HRLA	GFR8300HRLA
		GF15WLA	GF20WLA	GFR8200HWLA	GFR8300HWLA
		GFTR15	GFTR20	GFR8200HTR	GFR8300HTR
		GFTR15AL	GFTR20AL	GFR8200HALTR	GFR8300HALTR
		GFTR15BK	GFTR20BK	GFR8200HBKTR	GFR8300HBKTR
		GFTR15GY	GFTR20GY	GFR8200HGYTR	GFR8300HGYTR
		GFTR15I	GFTR20I	GFR8200HITR	GFR8300HITR
		GFTR15LA	GFTR20LA	GFR8200HLATR	GFR8300HLATR
		GFTR15OW	GFTR20OW	GFR8200HOWTR	GFR8300HOWTR
		GFTR15R	GFTR20R	GFR8200HRTR	GFR8300HRTR
		GFTR15W	GFTR20W	GFR8200HWTR	GFR8300HWTR

GFCI type receptacles should not be used in critical care patient areas or for electrical life support equipment applications because of the possibility of power interruption. All GFCI receptacles listed above are furnished with the proper color nylon wallplate.



GF15ILA



GFTR20I



GFR8200HOWLA



GFR8300HITR

Circuit Guard®, Specification Grade Surge Suppression Duplex Receptacles

Description	Color	Standard Receptacles		Hospital Grade	
		15A 125V	20A 125V	15A 125V	20A 125V
Surge suppression receptacles with light; 240 joules/15000A per mode. 	Blue Ivory Office White	HBL5260SA	HBL5360SA	—	—
		HBL5260ISA	HBL5360ISA	—	—
Surge suppression receptacles with light and alarm; 240 joules/15000A per mode. 	Almond Blue Gray Ivory Office White White	HBL5262ALSA	HBL5362ALSA	HBL8262ALSA	HBL8362ALSA
		HBL5262SA	HBL5362SA	HBL8262SA	HBL8362SA
		HBL5262GYSA	HBL5362GYSA	HBL8262GYSA	HBL8362GYSA
		HBL5262ISA	HBL5362ISA	HBL8262ISA	HBL8362ISA
		HBL5262OWSA	HBL5362OWSA	HBL8262RSA	HBL8362RSA
		HBL5262WSA	HBL5362WSA	HBL8262WSA	HBL8362WSA
⚠ Isolated ground, surge suppression receptacles with light and alarm; 240 joules/15000A per mode. 	Blue Gray Ivory Office White Orange White	IG5262SA	IG5362SA	IG8262SA	IG8362SA
		IG5262GYSA	IG5362GYSA	IG8262GYSA	IG8362GYSA
		IG5262ISA	IG5362ISA	IG8262ISA	IG8362ISA
		IG5262OWSA	IG5362OWSA	IG8262OSA	IG8362OSA
		IG5262OSA	IG5362OSA	IG8262RSA	IG8362RSA
		IG5262WSA	IG5362WSA	IG8262WSA	IG8362WSA



HBL5262GYSA



HBL5362SA



HBL8362ISA



IG8362RSA

H-MOSS® Occupancy Sensors and Wallplates



Hubbell H-MOSS® Occupancy Sensors



The Hubbell H-MOSS line of occupancy sensors features a broad line-up of dual technology, ultrasonic and passive infrared (PIR) ceiling, wall switch and wall mount sensors. Many of the sensors feature Adaptive Technology, a Hubbell breakthrough, which enables building owners and occupants to reduce energy costs, with fewer adjustments. Visit the Hubbell website at www.hubbell-wiring.com to view the complete H-MOSS occupancy sensor offering.

Adaptive Technology Dual Technology



Type	Catalog Number
Wall Switch	AD1277xx
Ceiling	ATD2000C, ATD1000C, ATD500C
Wall Mount	ATD1600W

Ultrasonic



Type	Catalog Number
Wall Switch	AU1277xx
Ceiling	ATU2000C, ATU1000C, ATU500C

Passive Infrared (PIR)



Type	Catalog Number
Wall Switch	AP1277xx, ATP1277x, AT1277x
Ceiling	ATP1500C, ATP600C
Wall Mount	ATP1600W, ATP120HB

AD, AU and AP wall switches are available in single or dual circuits, with and without buttons. The AD/AU/AP1277 series wall switches are available in Ivory (I) and White (W) as standard colors. The AT/ATP1277 sensors are available in Ivory (I) or White (W). To order colors, replace **xx** with appropriate suffix. Ceiling and wall mount sensors are available in white only. Must use a CU Series control unit with all ceiling and wall sensors.

Non Adaptive Passive Infrared



Type	Catalog Number
Wall Switch	WS1277x, WS120x, WS277x, WS1277W2

For color options, replace **x** with White (W) or Ivory (I). WS1277W2 is available in white only.

Line Voltage



Technology	Catalog Number
Dual	LVDT2000Rxxx
Ultrasonic	LVUS1500Rxxx, LVUS2000Rxxx
PIR	LVPR1500R (120-347V AC)

Available in 120V AC and 277V AC. Replace **xxx** with 120 or 277 for appropriate voltage.

Residential (Occupancy and Vacancy)



Type	Occupancy	Vacancy
Wall Switch	RMS101xx, RMS141xx	RMS100xx, RMS140xx
Wall Switch w/dimming	RMS121xx,	RMS120xx

For color options, replace **xx** with Ivory (I), White (W), Almond (AL) or Light Almond (LA).

Hubbell Wallplates


Hubbell offers a wide variety of configurations, sizes and finishes in both metal and nylon wallplates for use in Specification, commercial, and residential applications. Hubbell's complete line of wallplates include standard, midsize, custom metal and jumbo in stainless steel, brass, brass plated, chrome, aluminum and nylon. Visit the Hubbell website at www.hubbell-wiring.com to view the complete wallplate offering.



To order nylon wallplates, replace **xx** with appropriate color suffixes.




Toggle Switch




Gang	430 S/S	302/304 S/S	Nylon
1	SS1L	SS1	NP1xx
2	SS2L	SS2	NP2xx
3	SS3L	SS3	NP3xx

Duplex Receptacle




Gang	430 S/S	302/304 S/S	Nylon
1	SS8L	SS8	NP8xx
2	SS82L	SS82	NP82xx
3	—	SS83	NP83xx

Style Line® Decorator




Gang	430 S/S	302/304 S/S	Nylon
1	SS26L	SS26	NP26xx
2	SS262L	SS262	NP262xx
3	—	SS263	NP263xx

Blank (Box Mount/Strap Mount)




Gang	430 S/S	302/304 S/S	Nylon
Box Mount			
1	SS13L	SS13	NP13xx
2	SS23L	SS23	NP23xx
Strap Mount			
1	SS14L	SS14	NP14xx
2	SS24L	SS24	NP24xx

Single Receptacle



Gang	Dia. Hole	430 S/S	302/304 S/S	Nylon
1	1.40" (35.6)	SS7L	SS7	NP7xx
1	2.15" (54.6)	SS723L	SS723	NP724xx
2	2.15" (54.6)	SS703L	SS703	NP703xx

Combination



Gang	430 S/S	302/304 S/S	Nylon	
2	Toggle/Duplex	SS18L	SS18	NP18xx
2	Toggle/Decorator	SS126L	SS126	NP126xx
2	Duplex/Decorator	—	SS826	NP826xx
2	Duplex/Blank	—	SS138	NP138xx

Competitive Cross Reference Guide



Duplex Receptacles

Device Category	Description	Hubbell Series	Hubbell	Leviton	Pass and Seymour
Extra Heavy Duty Industrial	15 and 20 Amp, 125 Volts, Back & Side Wired	HBL® Series	20A 15A HBL5362 HBL5262	5362	5362A
Extra Heavy Duty Industrial	15 and 20 Amp, 125 Volts, Back & Side Wired, Hospital Grade	HBL® Series	20A 15A HBL8300 HBL8200	8300	8300
Heavy Duty Specification	15 and 20 Amp, 125 Volts, Back & Side Wired	Hubbell-Pro™	20A 15A 5362 Series 5262 Series	5362S	5362
Heavy Duty Specification	15 and 20 Amp, 125 Volts, Back & Side Wired, Smooth Face	Hubbell-Pro™	20A 15A 5352A 5252A	n/a	CRB5362S
Heavy Duty Specification	15 and 20 Amp, 125 Volts, Back & Side Wired, Hospital Grade	Hubbell-Pro™	20A 15A 8300 Series 8200 Series	8300H	PS8300H
Heavy Duty Specification	15 and 20 Amp, 125 Volts	SNAPConnect™	20A 15A SNAP5362 SNAP5262	M5362	PT5362A
Heavy Duty Specification	15 and 20 Amp, 125 Volts, Hospital Grade	SNAPConnect™	20A 15A SNAP8300 SNAP8200	M8300	PT8300
Heavy Duty Specification	15 and 20 Amp, 125 Volts, Style Line® Decorator	SNAPConnect™	20A 15A SNAP2162 SNAP2152	n/a	PT26352
Commercial Specification	15 and 20 Amp, 125 Volts, Back & Side Wired	Commercial Series	20A 15A BR20 BR15	BR20	BR20
Commercial Specification	15 and 20 Amp, 125 Volts, Side Wire Only	Commercial Series	20A 15A CR20 CR15	CR20	CR20
Commercial Specification	15 and 20 Amp, 125 Volts, Back & Side Wired, Style Line® Decorator	Commercial Series	20A 15A DR20 DR15	16342	26852


Switches

Device Category	Description	Hubbell Series	Hubbell	Leviton	Pass and Seymour
Extra Heavy Duty Industrial	15A and 20Amp, 120-277 Volts AC, Single Pole to 4-Way, Back & Side Wired	HBL® Series	20A 15A HBL1221 HBL1201	1221-2	N/A
Heavy Duty Specification	15A and 20Amp, 120-277 Volts AC, Single Pole to 4-Way, Back & Side Wired	Hubbell-Pro™	20A 15A 1221 1201	1221S	PS20AC
Commercial Specification	15A and 20Amp, 120-277 Volts AC, Single Pole to 4-Way, Back & Side Wired	Commercial Series	20A 15A CSB120 CSB115	CSB1-20	CSB20AC
Commercial Specification	15A and 20Amp, 120-277 Volts AC, Single Pole to 3-Way, Side Wired Only	Commercial Series	20A 15A CS120 CS115	CS120	CS20AC
Commercial Specification	15A and 20Amp, 120-277 Volts AC, Single Pole to 4-Way, Back & Side Wired, Style Line® Decorator	Commercial Series	20A 15A DS120 DS115	5620	2600


Hubbell-Pro™ Heavy Duty Specification Grade Series

Hubbell Specification Grade Commercial Series


Hubbell-Pro™ Heavy Duty Specification Grade Receptacles



Hubbell GFCI Receptacles



Hubbell Specification Grade Commercial Receptacles



Hubbell H-MOSS® Occupancy Sensors



Specification Grade Commercial and Hubbell-Pro™ Heavy Duty Specification Grade Switches



Hubbell Metal and Nylon Wallplates

