

2016

BL300-LED10W

BL300-LED10W

BL300-LED10W

BL300-LED10W
BL300-LED10W

BL300-LED8W

BL300-LED8W

BL300-LED8W

BL300-LED8W

BL300-LED8W

BL300-LED8W

BL300-LED10W

BL300-LED10W

BL300-LED8W

BL300-LED8W

BL300-LED8W

BL300-LED8W



ALLIANCE

OUTDOOR LIGHTING

AL100	AL150	AL200	AL300	AL400	AL500	AL550	AL600	AL700	AL750	AL800	AL850	TIKI	<div>INTELLIGENT TRANSFORMERS.....4-5</div> <div>LED LAMPS6-7</div> <div>AREA LIGHTS.....8-11</div> <div>PATH LIGHTS.....12</div> <div>BULLET LIGHTS.....14-15</div> <div>DOWN LIGHTS.....16-17</div> <div>FLOOD LIGHTS.....18</div> <div>IN-GROUND LIGHTS.....20-22</div> <div>STEP LIGHTS.....24-29</div> <div>UNDERWATER LIGHT.....30</div> <div>WALL SCNCE LIGHTS.....31</div> <div>POST LIGHT.....32-33</div> <div>TRANSFORMERS.....34-35</div> <div>ACCESSORIES.....36-37</div> <div>DOUBLE WIRE LEAD.....38</div> <div>ORDER FORM39</div>
PL100	PL200	PL250	CGBL01	BL50	BL100	BL200	BL300	HL100	HL200	DL50	DL100	DL200	
FL50	FL100	FL200	GL100	GL150	GL160	GL170	GL180	GL190	GL200	WL300	WL100	WL200	CGWL01
WS100	WS200	WS300	SL50	SL100	TAPE-LED-5FT	SL300/SL35-LED	SL200/SL25-LED	SL65-LED	SL75-LED	SL85-LED	SL95-LED	UL100	POST100

DISCOVER



intelligent transformer

Phone App Driven Transformer



it150

150 Watt Intelligent Transformer
Two Commons, Two 14V Taps

it300

300 Watt Intelligent Transformer
Three Commons, Three 14V Taps

How it works:

Step 1: Download it



available in: **App Store**




Google play

Step 2: Plug it in.



Using Bluetooth Technology, an astronomical timer, and the GPS information from your smart phone, it will know the time and day automatically.

Step 3: Program your settings



Use your phone to set your desired on and off times, or just let it use the default setting of sunset to sunrise.


Features:



Bluetooth
*Astronomical Timer
Phone App Driven
Multiple 14.0 Volt Taps
Lifetime Warranty
FOR LED ONLY*

LBIPIN-LED-200lm

2.5 watt bipin, 200 lumens
IP67 certified



LBIPIN-LED-250lm

3 watt bipin, 250 lumens
IP67 certified

L3156-LED-200lm

2.5 watt 3156 wedge base, 200 lumens
IP67 certified



L3156-LED-250lm

3 watt 3156 wedge base, 250 lumens
IP67 certified

LBA15S-LED-200lm

2.5 watt single bayonet, 200 lumens
IP67 certified



LBA15D-LED-200lm

2.5 watt double bayonet, 200 lumens
IP67 certified



L921T5-LED-200lm

2.5 watt T5 wedge base, 200 lumens
IP67 certified



LPAR36-LED-4W-F

4 watt PAR36, 250 lumens, 20 degree

LPAR36-LED-4W-WF

4 watt PAR36, 250 lumens, 40 degree
(20 watt PAR36 equivalent)



LPAR36-LED-8W-F

8 watt PAR36, 300 lumens, 20 degree

LPAR36-LED-8W-WF

8 watt PAR36, 300 lumens, 40 degree
(35 watt PAR36 equivalent)



LPAR36-LED-10W-F

10 watt PAR36, 400 lumens, 30 degree

LPAR36-LED-10W-WF

10 watt PAR36, 400 lumens, 45 degree
(50 watt PAR36 equivalent)



IP67 Certified

IP67: Lamps are dust tight and can be submerged in up to one meter of water

IP66 Certified

IP66: Lamps are dust tight and can withstand powerful water jets from any direction.



LMR16-LED-4W-F

4 watt MR16, 250 lumens
Flood, 45 degree
(20 watt MR16 equivalent)

Available Options:



LMR16-LED-4W-F-2700K

2700K Color Temperature



LMR16-LED-4W-NS

Narrow Spot, 15 degree



LMR16-LED-250lm

Enclosed Housing
Recommended for Down Light Series



LMR16-LED-6W-F

6 watt MR16, 400 lumens
Flood, 45 degree
(50 watt MR16 equivalent)



LMR16-LED-5W-F

5 watt MR16, 310 lumens
Flood, 45 degree
(35 watt MR16 equivalent)

Available color options:

LMR16-LED-5W-RED

LMR16-LED-5W-BLUE

LMR16-LED-5W-GREEN

LMR16-LED-5W-AMBER

LMR16-LED-5W-PURPLE

Available Options:



LMR16-LED-5W-F-2700K

2700K Color Temperature



LMR16-LED-5W-WF

Wide Flood, 60 degree



LMR16-LED-5W-NS

Narrow Spot, 15 degree



LMR16-LED-310lm

Enclosed Housing
Recommended for Down Light Series



LMR11-LED-4W-F

4 watt MR11, 175 lumens
Flood, 45 degree
(20 watt MR11 equivalent)

MR16 and MR11 LED lamps feature:

- Warm white color, 2900K temperature
- Operating voltage between 8v-24v
- CRI of Ra>80
- 50,000 hour life span
- Ambient operating temperature from -32°F to 162°F, -36°C to 72°C
- EMI Filter

Area Light Hats Feature:

**Note: Area light stems are sold separately*

- Brass area light hat, aged brass finish
- Polycarbonate lens
- Rubber gaskets
- Adjustable brass collar with thumb screw (AL700, AL750, AL800 and AL850)
- Lifetime warranty

Area Light Stems Sold Separately:

- ALSTEM12 – 12" Stem
- ALSTEM18 – 18" Stem
- ALSTEM24 – 24" Stem
- ALSTEM60 – 60" Stem
- ALSTEMADJ – 18"-29" Stem

Photo Courtesy of: Michael Epaul Photography
Lighting Design by: Illumascape Lighting, LLC owned by Phil Costello

AL100



AL300



AL550



AL750



AL150



AL400



AL600



AL800



AL200



AL500



AL700



AL850



10 ALLIANCE

TIKI Features:

**Note: Area light stems are sold separately*

- Brass area light hat, aged brass finish
- Metal snuffing cap with chain
- Wick with brass holder
- Solid brass collar
- Lifetime warranty

TIKI

Specialty Area Light Hat




PERMAPOST

Heavy Duty Ground Stake




ALSTEM60-LED

with PERMAPOST included
(LBIPIN-LED-200lm lamp included)



ALSTEM24-LED

(LBIPIN-LED-200lm lamp included)




ALSTEM18-LED

(LBIPIN-LED-200lm lamp included)



ALSTEM12-LED

(LBIPIN-LED-200lm lamp included)



ALSTEMADJ-LED

(LBIPIN-LED-200lm lamp included)



AREA LIGHT STEMS 11

Area Light Stems Feature:

**Note: Area light hats are sold separately*

- Brass stem, aged brass finish
- Adjustable brass collar with thumb screw (ALSTEM60 excluded)
- Ceramic bi-pin socket
- Double wire lead pre-connected to the fixture, 16 awg (UL listed), brown
 - 25 foot wire lead, pre-stripped for easy wire connection
 - 18 inch wire lead, LED connection ready
- Plastic ground stake (8.5 in; 21.6 cm length) (ALSTEM60 excluded)
- PermaPost ABS stake with brass cap on ALSTEM60
- Lifetime warranty on fixture housing
- Available without a lamp

12 PATH LIGHTS


PL100-LED

(LBIPIN-LED-200lm lamp included)



PL200-LED

(LBIPIN-LED-200lm lamp included)



PL250-LED

(LBIPIN-LED-200lm lamp included)



PL100-LED Features:

- Brass fixture, aged brass finish
- Solid brass hat with dual adjustments, brass thumb screw for vertical adjustments, brass stem nut for horizontal adjustments
- Ceramic bi-pin socket
- Frosted bubble lens
- Double wire lead pre-connected to the fixture, 16 awg (*UL listed*), brown
 - 25 foot wire lead, pre-stripped for easy wire connection
 - 18 inch wire lead, LED connection ready
- Plastic ground stake
- Lifetime warranty on fixture housing
- Available without a lamp

PL200-LED and PL250-LED Feature:

- Solid brass area light hat
- Clear glass lens
- Adjustable brass stem, 17"-27" length, aged brass finish
- Ceramic bi-pin socket
- 25 Foot wire lead, 16 awg (*UL listed*), brown, pre-connected to the fixture, pre-stripped for easy wire connection
- Solid brass stake (8.5 in; 21.6 cm length)
- Lifetime warranty on fixture housing
- Available without a lamp



Photo Courtesy of: Joe Traina
Lighting Design by: Ryan Hughes Design

Bullet Lights Feature:

- Brass fixture, aged brass finish
- Cast brass knuckle with dial adjustment
- Fully adjustable brass shroud (CGBL01 comes with turn and lock fitting)
- Ceramic bi-pin socket with lamp clip (MR11 and MR16)
- Clear glass lens (BL300 excluded)
- Double wire lead pre-connected to the fixture, 16 awg (UL listed), brown
 - 25 foot wire lead, pre-stripped for easy wire connection
 - 18 inch wire lead, LED connection ready
- Plastic ground stake (8.5 in; 21.6 cm length) (CGBL01 comes with commercial grade brass stake collar)
- Lifetime warranty on fixture housing
- Available without a lamp

Photo Courtesy of: Michael Epaul Photography
Lighting Design by: Illumascape Lighting, LLC owned by Phil Costello



BL50-LED
(4 watt MR11 LED lamp included)



BL100-LED6W
(6 watt MR16 LED lamp included)

BL100-LED5W
(5 watt MR16 LED lamp included)

BL100-LED4W
(4 watt MR16 LED lamp included)



BL200-LED6W
(6 watt MR16 LED Lamp included)

BL200-LED5W
(5 watt MR16 LED Lamp included)

BL200-LED4W
(4 watt MR16 LED Lamp included)



BL300-LED10W
(10 watt PAR36 LED Lamp included)

BL300-LED8W
(8 watt PAR36 LED Lamp included)

BL300-LED4W
(4 watt PAR36 LED Lamp included)

**Available in LED ONLY*



Available in MR16 Version
PART #: BL350-LED



CGBL01-LED6W
(6 watt MR16 LED lamp included)

CGBL01-LED5W
(5 watt MR16 LED lamp included)

CGBL01-LED4W
(4 watt MR16 LED lamp included)



Hanging Lights Feature:

- Brass fixture, aged brass finish
- Cast brass base with ring
- Adjustable brass shroud on HL100
- Brass shroud with twinkle cutouts on HL200
- Ceramic bi-pin socket with lamp clip on HL100
- Ceramic bi-pin socket on HL200
- Threaded aged brass chain, 18" length
- 25 Foot wire lead, 16 awg (UL listed), brown, pre-connected to the fixture, pre-stripped for easy wire connection
- Lifetime warranty on fixture housing
- Available without a lamp

HL100-LED6W
(6 watt MR16 LED lamp included)

HL100-LED5W
(5 watt MR16 LED lamp included)

HL100-LED4W
(4 watt MR16 LED lamp included)



The shroud on the HL100 is easily extendable.

HL200-LED
(LBIPIN-LED-200lm lamp included)



DL50-LED
(4 watt MR11 LED lamp included)



DL100-LED6W
(6 watt MR16 LED Lamp included)

DL100-LED5W
(5 watt MR16 LED Lamp included)


DL100-LED4W
(4 watt MR16 LED Lamp included)




DL200-LED6W
(6 watt MR16 LED Lamp included)

DL200-LED5W
(5 watt MR16 LED Lamp included)

DL200-LED4W
(4 watt MR16 LED Lamp included)



MR16 Down Light LED Lamps Now Come With Enclosed Housing



Down Lights Feature:

- Brass fixture, aged brass finish
- Solid brass knuckle with dial adjustment
- Brass shroud with rubber gasket
- Ceramic bi-pin socket with lamp clip
- 25 Foot wire lead, 16 awg (UL listed), brown, pre-connected to the fixture, pre-stripped for easy wire connection
- Solid brass mounting bracket, aged brass finish (DL100 and DL200)
- Brass mounting nut for precise adjustment (DL100 and DL200)
- Aged brass round mounting base (DL50)
- Mounting screws
- Lifetime warranty on fixture housing
- Available without a lamp

18 FLOOD LIGHTS



Flood Lights Feature:

- Brass fixture, aged brass finish
- Solid brass knuckle with dial adjustment
- Brass face plate with rubber gasket
- Ceramic bi-pin socket
- Clear lens (Optional frosted lens available)
- Double wire lead pre-connected to the fixture, 16 awg (UL listed), brown
 - 25 foot wire lead, pre-stripped for easy wire connection
 - 18 inch wire lead, LED connection ready
- Plastic ground stake (8.5 in; 21.6 cm length)
- Lifetime warranty on fixture housing
- Available without a lamp

ALLIANCE 19



Photo Courtesy of: Caity & Drew Photography
Lighting Design by: Visual Concepts, owned by Ken Perez Sr.

In-Ground Lights Feature:

- Brass fixture, aged brass finish
- Clear convex lens
- Solid brass fixture base with two rubber gasket seals
- Solid brass faceplate with four screws
- Ceramic bi-pin socket
- Double wire lead pre-connected to the fixture, 16 awg (UL listed), brown
 - 25 foot wire lead, pre-stripped for easy wire connection
 - 18 inch wire lead, LED connection ready
- Lifetime warranty on fixture housing
- Available without a lamp


WHAT'S NEW?

New Faceplate now screws onto the body for better protection against water intrusion.

Optional PVC Sleeve included for easier installations.

Extra potting added to the base for better protection against water intrusion.

New Faceplate Options:



GL200 Features:

- Brass fixture, aged brass finish
- Clear flat lens
- Hex Louver
- Ceramic bi-pin socket mounted to a bracket
- Double wire lead pre-connected to the fixture, 16 awg (UL listed), brown
 - 25 foot wire lead, pre-stripped for easy wire connection
 - 18 inch wire lead, LED connection ready
- Lifetime warranty on fixture housing
- Available without a lamp

GL200-LED6W

(6 watt MR16 LED lamp included)

GL200-LED5W

(5 watt MR16 LED lamp included)

GL200-LED4W

(4 watt MR16 LED lamp included)



WL300-LED6W

(6 watt MR16 LED lamp included)

WL300-LED5W

(5 watt MR16 LED lamp included)

WL300-LED4W

(4 watt MR16 LED lamp included)



The height of the lamp housing in the WL300 is easily adjustable.

WL300 Features:

- Aged brass louvered grate with lamp holder
- Lamp height adjusting track with locking nuts
- ABS housing, black
- Ceramic bi-pin socket
- Double wire lead pre-connected to the fixture, 16 awg (UL listed), brown
 - 25 foot wire lead, pre-stripped for easy wire connection
 - 18 inch wire lead, LED connection ready
- Lifetime warranty on fixture housing
- Available without a lamp



22 WELL LIGHTS




WL100-LED10W
(10 watt PAR36 LED lamp included)

WL100-LED8W
(8 watt PAR36 LED lamp included)

WL100-LED4W
(4 watt PAR36 LED lamp included)

**Available in LED ONLY*



WL200-LED10W
(10 watt PAR36 LED lamp included)

WL200-LED8W
(8 watt PAR36 LED lamp included)

WL200-LED4W
(4 watt PAR36 LED lamp included)


**Available in LED ONLY*

CGWL01-LED10W
(10 watt PAR36 LED lamp included)

CGWL01-LED8W
(8 watt PAR36 LED lamp included)

CGWL01-LED4W
(4 watt PAR36 LED lamp included)

**Available in LED ONLY*



WL100 and WL200 Feature:

- ABS grate, black (WL100)
- Aged brass debris guard with clear glass lens (WL200)
- ABS housing, black
- Lamp retainer ring, stainless steel
- Double wire lead pre-connected to the fixture, 16 awg (UL listed), brown
 - 25 foot wire lead, pre-stripped for easy wire connection
 - 18 inch wire lead, LED connection ready
- Lifetime warranty on fixture housing

CGWL01 Features:

- Heavy brass grate, aged brass finish
- Clear glass convex lens, tempered
- Lamp retainer ring, stainless steel
- ABS housing, black
- Double wire lead pre-connected to the fixture, 16 awg (UL listed), brown
 - 25 foot wire lead, pre-stripped for easy wire connection
 - 18 inch wire lead, LED connection ready
- Lifetime warranty on fixture housing

ALLIANCE 23



Photo Courtesy of: Caity & Drew Photography
Lighting Design by: Visual Concepts, owned by Ken Perez Sr.

24 STEP LIGHTS

TAPE-LED Features:

- 5 Foot LED strip
- Mounting clips included
- 10' wire lead, 16 awg (UL Listed), brown, pre-connected to the fixture, pre-stripped for easy wire connection
- 10 Year warranty on LED components and fixture housing

- LED strip
- Beam Angle: 120°
 - Beam Spread: Flood
 - Color: Warm White
 - Color Temperature: 2700K
 - Operating Voltage: 10.8Vac - 15Vac
 - CRI: Ra>80
 - Rated Hours: 30,000
 - Ambient Operating Temperature: -40°C ~ +85°C

SL-LED Series Features:

- Brass fixture, aged brass finish
- Mounting bracket, stainless steel, aged brass finish
- Optional frosted lens included
- 10' wire lead, 16 awg (UL Listed), brown, pre-connected to the fixture, pre-stripped for easy wire connection
- 10 Year warranty on LED components and fixture housing

- Integrated LED strip
- Beam Angle: 120°
 - Beam Spread: Flood
 - Color: Warm White
 - Color Temperature: 2700K
 - Operating Voltage: 10.8Vac - 15Vac
 - CRI: Ra>80
 - Rated Hours: 30,000
 - Ambient Operating Temperature: -40°C ~ +85°C

TAPE-LED-5FT
Integrated LED Step Light
Can be cut down to length
LED strip, 5 Feet

- Watts: 18w
- Light Output: 827 lm (Lumens)


Per 1 Foot:

- Watts: 3.5w
- Light Output: 165 lm (Lumens)



Can be Cut Down to Size

NEW ITEM



SL65-LED
Integrated LED Step Light
LED strip, 4 chips

- Watts: 1.1w
- Light Output: 110 lm (Lumens)
- Halogen Equivalent: 10w



Mounting bracket is removable for further applications.
Optional frosted lens is included with the fixture.




SL75-LED
Integrated LED Step Light
LED strip, 8 chips

- Watts: 3w
- Light Output: 120 lm (Lumens)
- Halogen Equivalent: 20w



SL85-LED
Integrated LED Step Light
(3 watt LED Strip)
LED strip, 12 chips

- Watts: 4w
- Light Output: 370 lm (Lumens)
- Halogen Equivalent: 30w



SL95-LED
Integrated LED Step Light
(3 watt LED Strip)
LED strip, 20 chips

- Watts: 8w
- Light Output: 660 lm (Lumens)
- Halogen Equivalent: 40w

MOST POPULAR

Our original integrated step light is now available in three new lengths. The 4" SL65-LED will work great on shorter walls and corners. The 12" SL85-LED is ideal for taller walls and will provide a wider coverage area. The 18" SL95-LED will provide the most powerful and widest output for heavy duty jobs. All of these fixtures come with an optional frosted lens and have the ability to mount without the bracket.

NEW ITEMS

26 STEP LIGHTS


SL50-LED

(LBIPIN-LED-200lm lamp included)



SL100-LED

(LBIPIN-LED-200lm lamp included)



SL100 Features:

- Brass fixture, aged brass finish
- Solid brass face plate with securing hex screws
- Allen wrench tool to tighten hex screws
- Base plate with adjustable mounting guides
- Ceramic bi-pin socket
- Frosted lens
- 25 Foot wire lead, 16 awg (*UL listed*), brown, pre-connected to the fixture, pre-stripped for easy wire connection
- Mounting hardware screws
- Two extra adjusting hex face plate screws
- Mounting template
- Lifetime warranty on fixture housing
- Available without a lamp

ALLIANCE 27

SL50 Features:

- Brass fixture, aged brass finish
- Ceramic bi-pin socket
- Frosted lens
- 25 Foot wire lead, 16 awg (*UL listed*), brown, pre-connected to the fixture, pre-stripped for easy wire connection
- Lifetime warranty on fixture housing

Photo Courtesy of: Caity & Drew Photography
Lighting Design by: Visual Concepts, owned by Ken Perez Sr.

OLD STYLE - REQUIRES A BOX

SL200-LED
(LBIPIN-LED-200lm lamp included)



SL300-LED
(Two LBIPIN-LED-200lm lamps included)




- SL200 and SL300 Feature:
- Brass fixture, aged brass finish
 - Solid brass face plate with securing screws
 - Ceramic bi-pin socket
 - 25 Foot wire lead, 16 awg (*UL listed*), brown, pre-connected to the fixture, pre-stripped for easy wire connection
 - Lifetime warranty on fixture housing
 - Available without a lamp

NEW STYLE - SURFACE MOUNTED WITHOUT A BOX

SL25-LED
Integrated Surface Mount Step Light



- SL25-LED Features:
- Brass fixture, aged brass finish
 - Solid brass face plate with frosted lens
 - 10' Wire lead
 - 10 Year warranty on LED components and fixture housing
 - Integrated LED
 - Watts: 4.5w
 - Color: Warm White
 - Color Temperature: 2700K
 - Operating Voltage: 8Vac-15Vac
 - CRI: Ra>80
 - Halogen Equivalent: 20w
 - Rated Hours: 30,000 Hours
 - Ambient Operating Temperature: -40°C ~ +85°C



SL35-LED
Integrated Surface Mount Step Light



- SL35-LED Features:
- Brass fixture, aged brass finish
 - Solid brass face plate with frosted lens
 - 10' Wire lead
 - 10 Year warranty on LED components and fixture housing
 - Integrated LED
 - Watts: 9w
 - Color: Warm White
 - Color Temperature: 2700K
 - Operating Voltage: 8Vac-15Vac
 - CRI: Ra>80
 - Halogen Equivalent: 40w
 - Rated Hours: 30,000 Hours
 - Ambient Operating Temperature: -40°C ~ +85°C

30 UNDERWATER LIGHT

UL100 Features:

- Brass fixture, aged brass finish
- Solid brass fixture base
- Solid brass shroud with water tight, sealed clear lens
- Ceramic bi-pin socket
- 25 Foot underwater wire lead, pre-connected to the fixture (also available with 50 Foot and 100 Foot wire leads)
- UL1838 Certified underwater landscape luminaire
- Lifetime warranty on fixture housing
- Available without a lamp



AVAILABLE IN LONGER LEADS

UL100-50FT

(50 Foot wire lead)
Available in LED

UL100-100FT

(100 Foot wire lead)
Available in LED

UL100-LED6W

(6 watt MR16 LED lamp included)

UL100-LED5W

(5 watt MR16 LED lamp included)

UL100-LED4W

(4 watt MR16 LED lamp included)

Wall Sconces Feature:

- Brass fixture, aged brass finish
- Frosted top lens (WS100 and WS200)
- Clear glass top and bottom lenses (WS300)
- Dual Ceramic bi-pin socket
- 25 Foot wire lead, 16 awg (UL listed), brown, pre-connected to the fixture, pre-stripped for easy wire connection
- Lifetime warranty on fixture housing
- Available without a lamp



WS100-LED

(Two LBIPIN-LED-200lm lamps included)



WS200-LED

(Two LBIPIN-LED-200lm lamps included)



WS300-LED6W

(Two 6 watt MR16 LED lamps included)

WS300-LED5W

(Two 5 watt MR16 LED lamps included)

WS300-LED4W

(Two 4 watt MR16 LED lamps included)

32 POST LIGHT

Post Light Features:

- Brass post light, aged brass finish
- Frosted lens panels
- Ceramic bi-pin socket
- Mounting hardware
- 25 foot wire lead, 16 awg(UL Listed), brown, pre-connected to the fixture, pre-stripped for easy wire connection
- Lifetime warranty on fixture housing
- Available without a lamp

POST100-LED6W

(6 watt MR16 LED lamps included)

POST100-LED5W

(5 watt MR16 LED lamps included)

POST100-LED4W

(4 watt MR16 LED lamps included)

NEW ITEM



ALLIANCE 33





it150
150 Watt Intelligent Transformer
Two Commons, Two 14V Taps

it300
300 Watt Intelligent Transformer
Three Commons, Three 14V Taps

Features:
Bluetooth Ready
Phone App Driven
Multiple 14.0v Taps
Astronomical Timer
Lifetime Warranty
FOR LED ONLY




(XF150 pictured)

XF150
150 watt Transformer
COM1 COM2 12 13 14 15

XF300
300 watt Transformer
COM1 COM2 12 13 14 15

XF600
600 watt Transformer
COM1 12 13 14 15 16 17 18 COM2

XF TRANSFORMER ACCESSORIES




TF300
300 Watt Stainless Steel Transformer Featuring:
- Multiple Taps (12v-15v)
- Built in photocell/timer



TF200
200 Watt Stainless Steel Transformer Featuring:
- One 12 Volt tap only
- Built in photocell/timer



TF150
150 Watt Transformer Featuring:
- One 12 Volt tap only
- Built in photocell/timer



ETF60
60 Watt Electronic Transformer



CONNECTION ACCESSORIES

A-LOC
Waterproof Wire Connectors



CS150
Two Brass Connectors and Plastic Lug Caps



CS100
Two Brass Connectors with Set Screws and Plastic Lug Caps in PVC housing




RMB

Aged Brass Round Mounting Base



GUTTERMOUNT

Aged Brass Gutter Mount



RISERADJ-BRASS

Adjustable Brass Riser



RISER18

18" Aged Brass Riser




RISER12

12" Aged Brass Riser



RISER6

6" Aged Brass Riser




C-CLAMP



PERMAPOST

Heavy Duty Ground Stake



PRODUCT WARRANTY:

Alliance Outdoor Lighting warrants its products against defects in material and workmanship. Without charge, Alliance Outdoor Lighting will either repair or replace (Alliance Outdoor Lighting reserves the right to decide between repair or replacement) any properly installed Alliance Outdoor Lighting product that fails under normal operating conditions within the specified warranty period.

- **Brass and Copper fixtures:** All have a lifetime warranty for all castings and housings.
- **XF Series Transformers:** All XF series transformers carry a lifetime warranty on enclosures. All transformer windings carry a lifetime warranty.
- **TF Series Transformers:** Two year warranty.
- **Integrated LED fixtures:** All Alliance LED integrated fixtures carry a 10 year warranty
- **LED Lamps:** Five year warranty.
- **Halogen Lamps:** Do not carry a warranty


All products are warranted from the date of invoice, provided it is returned to the Alliance Outdoor Lighting distributor from where it is purchased. Our factory inspection determines it to be defective under the terms of the warranty. This warranty covers only equipment manufactured by Alliance Outdoor Lighting and does not extend to transportation, installation, labor compensation, or replacement charges, nor does it apply to any equipment of another manufacturer used in conjunction with Alliance Outdoor Lighting equipment.

NOTE: All Alliance Outdoor Lighting products are designed to be repaired in the field by a qualified lighting installer. All service parts are readily available and we encourage field repairs as a significant cost and labor savings which can be realized by the installer. All warranted components, as stated in the above warranty, which are installed in the field, will be honored.



We Provide the Wire
You Save on Labor

Connect the **Long 25'** Lead to the **Short 18"** Lead



For LED installations only

Fixtures					
Part #		Qty	Part #		Qty
AREA LIGHT HATS			DOWN LIGHTS		
AL100			DL50		
AL150			DL100		
AL200			DL200		
AL300			HL100		
AL400			HL200		
AL500			IN-GROUND LIGHTS		
AL550			GL100		
AL600			GL150		
AL700			GL160		
AL750			GL170		
AL800			GL180		
AL850			GL190		
TIKI			GL200		
AREA LIGHT STEMS			WL100-LED		
ALSTEM12			WL200-LED		
ALSTEM18			WL300		
ALSTEM24			CGWL01-LED		
ALSTEM60			STEP LIGHTS		
ALSTEMADJ			SL25-LED		
BULLET LIGHTS			SL35-LED		
BL50			SL65-LED		
BL100			SL75-LED		
BL200			SL85-LED		
BL300-LED			SL95-LED		
BL350			SL50		
CGBL01			SL100		
FLOOD LIGHTS			SL200		
FL50			SL300		
FL100			TAPE-LED-5FT		
FL200					
Part #		Qty	Part #		Qty
PATH LIGHTS			PL100		
			PL200		
			PL250		
WALL SCONCES			WS100		
			WS200		
			WS300		
Accessories					
C-CLAMP					
GUTTERMOUNT					
RISER6					
RISER12					
RISER18					
RISERADJ-BR					
RMB					
PERMAPOST					
GL160-TOP					
GL170-TOP					
GL180-TOP					
GL190-TOP					
UNDERWATER LIGHT					
UL100					
UL100-50FT					
UL100-100FT					
POST LIGHT					
POST100					

www.allianceoutdoor.com
www.daveuknow.com

LED Lamps	
Part #	Qty
MR11	
LMR11-LED-4W-F	
MR16	
LMR16-LED-4W-F	
LMR16-LED-4W-F-2700K	
LMR16-LED-4W-NS	
LMR16-LED-4W-WF	
LMR16-LED-4W-250lm	
LMR16-LED-5W-F	
LMR16-LED-5W-F-2700K	
LMR16-LED-5W-NS	
LMR16-LED-5W-WF	
LMR16-LED-310lm	
LMR16-LED-6W-F	
LMR16-LED-6W-F-2700K	
PAR36	
LPAR36-LED4W-F	
LPAR36-LED4W-WF	
LPAR36-LED8W-F	
LPAR36-LED8W-WF	
LPAR36-LED10W-F	
LPAR36-LED10W-WF	
BIPIN/G4	
LBIPIN-LED-200lm	
LBIPIN-LED-250lm	

Transformers	
Part #	Qty
IT SERIES	
IT150	
IT300	
XF SERIES	
XF150	
XF300	
XF600	
TF SERIES	
TF150	
TF200	
TF300	

Accessories	
A-LOC	
CS100	
CS150	
ETF60	
PC	
TIMER	

800.930.6225
www.allianceoutdoorlighting.com
www.doyouknowalliance.com

ALLIANCE
OUTDOOR LIGHTING



ALLIANCE

2016 PRODUCT CATALOG
800.930.6225
www.allianceoutdoorlighting.com
www.doyouknowalliance.com