

TOOLS, DRILLS, AND ACCESSORIES

MASTER SCREWDRIVER KIT I

20 Piece Kit

INSERT BIT AND SCREWDRIVER ASSORTMENT

KIT INCLUDES:

- 7 - Slotted Drive Bits
- 4 - Phillips Drive Bits
- 3 - Square Drive Bits
- 2 - TORX Bits
- 2 - Hex Bits
- 1 - Magnetic Holder for Power Driving
- 1 - Magnetic Hand Driver with storage compartment



IN A STURDY PLASTIC STORAGE CASE

STOCK NO.	UPC NO.	STANDARD PKG. / MASTER CARTON	SUGGESTED TRADE LIST PRICE PER KIT
MSK1	28005	1 Kit/6 Kits per carton	56.71/ea

REPLACEMENT COMPONENTS FOR KIT

QUANTITY	DESCRIPTION	BIT/POINT SIZE
7	Slotted Drive Bits	3-4; 4-5; 5-6; 6-8; 8-10; 0-12; 12-14
4	Phillips Drive Bits	1; 2; 3; 2 Reduced Shank
3	Square Drive Bits	1; 2; 3
2	Hex Bits	1/8; 3/16
2	TORX Bits	T20; T151
1	Magnetic Bit Holder for Power Driving	
1	Magnetic Hand Driver with storage compartment	

MASTER SCREWDRIVER KIT II

29 Piece Kit

INSERT BIT AND SCREWDRIVER ASSORTMENT

KIT INCLUDES:

- 4 - Phillips Bits
- 5 - Slotted Bits
- 5 - Hex Bits
- 4 - Square Recess Bits
- 6 - TORX Bits
- 2 - Posi-drive Bits
- 1 - Socket Adaptor
- 1 - Magnetic Driver with Storage Handle
- 1 - Bit Holder for use with a power tool




H

STOCK NO.	UPC NO.	STANDARD PKG. / MASTER CARTON	SUGGESTED TRADE LIST PRICE PER KIT
MSK2	28009	1 Kit/6 Kits per carton	79.11/ea

REPLACEMENT COMPONENTS FOR KIT

QUANTITY	DESCRIPTION	BIT/POINT SIZE
4	Phillips Bits	0" 1" 2" 3"
5	Slotted Bits	0" 1" 3" 4" 5-6" 5-10" 12"
5	Hex Bits	5/64" 3/32" 7/64" 1/8" 9/64"
4	Square Recess	0" 1" 2" 3"
6	TORX Bits	T10" T15" T20" T25" T30" T40
2	Posidrive Bits	1" 2"
1	Socket Adaptor	1/4"
1	Bit Holder	1/4" (for use with power tool)
1	Driver	1/4" (magnetic with storage handle)


TOOLS, DRILLS, AND ACCESSORIES



Metallics



15 IN ONE RATCHET SCREWDRIVER



- Handle contains 1 ea of bits listed below


Stock Number	UPC#	Description	Qty	WT.	Suggested Trade List Ea
SD15B	35025	Screwdriver	1	.5lbs	\$33.39/ea

15-1 Replacement Bits (PKG. 6 Bits Per PKG.)					
Stock Number	UPC#	Description	Qty	WT. Per PKG.	Suggested Trade List Ea
SDR1B	35028	1/8" Slotted x #0 Phillips	6	.5lbs	\$20.18/ea pkg
SDR2B	35030	1/4" x 3/16" Slotted	6	.5lbs	\$20.18/ea pkg
SDR3B	35032	1/4" Slotted #2 Phillips	6	.5lbs	\$20.18/ea pkg
SDR4B	35034	5/32" Slotted x #3 Phillips	6	.5lbs	\$20.18/ea pkg
SDR5B	35036	#1 x #2 Phillips	6	.5lbs	\$20.18/ea pkg
SDR6B	35038	T15 x T20 Torx Compatible	6	.5lbs	\$24.47/ea pkg
SDR7B	35040	S1 x S2 Square	6	.5lbs	\$24.47/ea pkg



FOR INFORMATION CALL
 METALLICS EAST AT (800) 243-8272 OR METALLICS WEST AT (800) 269-5183
 229 CROSS ST, BRISTOL, CT 651 NORTH MAIN ST, MANCOS, CO

TOOLS, DRILLS, AND ACCESSORIES



Metallics Inc.



25' Pro Tape Measure



- Cushion Grip Provides Non-slip Grip and Helps Protect Tape
- Quick release and locking button
- Tape 7/8" wide for extra strength

Stock Number	UPC#	Description	Qty	WT.	Suggested Trade List Ea
MPT1	31304	Tape Measure	1	.9lbs	\$24.61/ea

Utility Knife



- Heavy-Duty
- Extra Blades in Handle
- Retractable Blade

Stock Number	UPC#	Description	Qty	WT.	Suggested Trade List Ea
MUK1	38202	Utility Knife	1	.6lbs	\$11.92/ea


FOR INFORMATION CALL
 METALLICS EAST AT (800) 243-8272 OR METALLICS WEST AT (800) 269-5183
 229 CROSS ST, BRISTOL, CT 651 NORTH MAIN ST, MANCOS, CO

TOOLS, DRILLS, AND ACCESSORIES



THE META PRIDE

FOUR-WAY SCREWDRIVER

Convenience of 4 Screwdrivers in One!



Attractive counter display included with 12 or more!



SD4W1

Includes:
3/16 & 9/32 Slotted bit
#1 & #2 Phillips bit



SD4W2

Includes:
#1 & #2 Square bit
#1 & #2 Phillips bit

- Reversible Shaft
- Heavy Duty Black Plastic Handle with Gold Imprint
- 2 Bit Assortments Available

SPECIAL ORDER

PRIVATE LABELING AVAILABLE
with purchases of 72 or more drivers
(Specify handle color: Red, Black, Light Blue, Dark Blue, Yellow, Green)

STOCK NO.	UPC NO.	DESCRIPTION	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
SD4W1	35001	4-way Phillips and Slotted Points	12	10.41/ea
SD4W2	35002	4-way Phillips and Square Points	12	10.41/ea


THE META PRIDE

SIX-WAY SCREWDRIVER

Same great features as our 4-Way Screwdriver

PLUS

a hardened steel tube for use as a $\frac{1}{4}$ " or $\frac{5}{16}$ " hex nut driver!





Attractive counter display included with 12 or more!

$\frac{5}{16}$ "
Hex Driver




$\frac{1}{4}$ "
Hex Driver



SD6W1

Includes:
3/16 & 9/32 Slotted bit
#1 & #2 Phillips bit



SD6W2

Includes:
#1 & #2 Square bit
#1 & #2 Phillips bit

- Reversible Steel Shaft with Hex Drivers
- Heavy Duty Black Plastic Handle with Gold Imprint
- 2 Bit Assortments Available

SPECIAL ORDER

PRIVATE LABELING AVAILABLE
with purchases of 72 or more drivers
(Specify handle color: Red, Black, Light Blue, Dark Blue, Yellow, Green)

STOCK NO.	UPC NO.	DESCRIPTION	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
SD6W1	35010	6-way Phillips and Slotted Points	12	12.76/ea
SD6W2	35011	6-way Phillips and Square Points	12	12.76/ea



THREE-IN-ONE TAP THREAD CLEANING TOOL

STOCK NO.	UPC NO.	DESCRIPTION	WT. EACH	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
681032	16345	6-32,8-32,10-32 Thread Cleaning Tool	.34	1	18.53/ea
























TOOLS, DRILLS, AND ACCESSORIES

PROFESSIONAL POWER TOOL ACCESSORY VISUAL PACKAGES


ALL BITS "XTRA-HARD"



STOCK NO.	UPC NO.	DESCRIPTION		PIECE PER LENGTH DIAMETER	SINGLE VISUAL PK.	SUGGESTED TRADE LIST PRICE PER PKG
000P1X	25070	#1 Phillips Insert Bit		1	10	7.72/ea
000P2X	25074	#2 Phillips Insert Bit		1	10	7.72/ea
000P3X	25080	#3 Phillips Insert Bit		1	10	7.72/ea
000R2X	25055	#2 Square Drive Insert Bit		1	10	9.21/ea
0016X	25235	6-8 Slotted Insert Bit		1	10	12.52/ea
0018X	25240	8-10 Slotted Insert Bit		1	10	12.52/ea
00110X	25245	10-12 Slotted Insert Bit		1	10	12.52/ea
100P1X	25300	#1 Phillips Power Bit		1 ¹⁵ / ₁₆	5	9.09/ea
100P2X	25305	#2 Phillips Power Bit		1 ¹⁵ / ₁₆	5	9.09/ea
100P3X	25312	#3 Phillips Power Bit		2	5	9.31/ea
1008X	25415	8-10 Slotted Power Bit		1 ¹⁵ / ₁₆	5	14.40/ea
10010X	25314	10-12 Slotted Power Bit		1 ¹⁵ / ₁₆	5	15.20/ea
P2P2	25510	#2 Phillips Dbl Ended Bit		1 ³ / ₄	2	8.63/ea
P2S8	25505	#2 Phillips Slotted Dbl End Bit		1 ¹ / ₂	2	5.59/ea
MT208	10870	1/4" Drill Chuck Nut Setter		1 ⁵ / ₈	2	9.45/ea
MT208L	10875	1/4" Drill Chuck Long Nut Setter		2 ⁹ / ₁₆	2	11.42/ea
MT210	10871	5/16" Drill Chuck Nut Setter		1 ³ / ₈	2	11.44/ea
MT210L	10876	5/16" Drill Chuck Long Nut Setter		2 ⁹ / ₁₆	2	12.67/ea
MT212	10872	3/8" Drill Chuck Nut Setter		1 ⁷ / ₈	2	12.54/ea
MT212L	10877	3/8" Drill Chuck Long Nut Setter		2 ⁹ / ₁₆	2	14.65/ea
M10	25250	Hex Insert Bit Holder		2 ⁷ / ₈	1	12.57/ea

H

TOOLS, DRILLS, AND ACCESSORIES




Metallics



Magnetic Bit and Nut Setter Kit

- Three sizes of Nut Setters and one size Bit Holders
- Magnetized for ease of use
- Be professional, be prepared









MTKQ CONTAINS						
Size	Stock Number	UPC#	Description	Qty EA	Weight per Kit	Suggested Trade List
1/4 x 2"	MTKQ	10890	Mag. Hex Bit Holder	2	0.8lbs	\$44.75 ea kit
1/4 x 2"			Mag. Nut Setter			
5/16 x 2"			Mag. Nut Setter			
3/8 x 2"			Mag. Nut Setter			

FOR INFORMATION CALL
 METALLICS EAST AT (800) 243-8272 OR METALLICS WEST AT (800) 269-5183
 229 CROSS ST, BRISTOL, CT 651 NORTH MAIN ST, MANCOS, CO

TOOLS, DRILLS, AND ACCESSORIES

BULK PACKAGED 1/4" HEX SHANK SCREWDRIVER POWER BITS AND HOLDERS

	STOCK NO.	UPC NO.	SCREW SIZE	POINT SIZE	OVERALL LENGTH	SUGGESTED TRADE LIST PRICE PER EA.		
PHILLIPS INSERT & POWER BITS 	000P1B	25071	4-6	#1	1"	1.01	EA.	
	000P2B	25076	8-10	#2	1"	1.01	EA.	
	000P3B	25081	12-14	#3	1"	1.01	EA.	
	001P2B	25085	8-10	#2	1 1/2"	2.15	EA.	
	100P1B	25301	4-6	#1	2"	2.29	EA.	
	100P2B	25306	8-10	#2	2"	2.29	EA.	
	100P3B	25310	12-14	#3	2"	2.10	EA.	
	125P1B	25315	4-6	#1	3"	2.73	EA.	
	125P2B	25320	8-10	#2	3"	3.02	EA.	
	125P3B	25325	12-14	#3	3"	3.46	EA.	
	140P1B	25345	4-6	#1	4"	3.82	EA.	
	140P2B	25350	8-10	#2	4"	3.82	EA.	
	140P3B	25355	12-14	#3	4"	3.82	EA.	
	SLOTTED INSERT & POWER BITS 	0014B	25225	4-5	4-5	1"	1.64	EA.
		0016B	25236	6-8	6-8	1"	1.64	EA.
		0018B	25241	8-10	8-10	1"	1.64	EA.
00110B		25206	10-12	10-12	1"	1.64	EA.	
0006B		25195	6-8	6-8	1 1/2"	2.10	EA.	
0008B		25200	8-10	8-10	1 1/2"	2.10	EA.	
00010B		25205	10-12	10-12	1 1/2"	2.10	EA.	
1004B		25400	4-5	4-5	2"	3.43	EA.	
1006B		25410	6-8	6-8	2"	3.43	EA.	
1008B		25416	8-10	8-10	2"	3.82	EA.	
10010B		25420	10-12	10-12	2"	4.09	EA.	
1256B		25440	6-8	6-8	3"	4.85	EA.	
1258B		25445	8-10	8-10	3"	5.20	EA.	
12510B		25450	10-12	10-12	3"	7.17	EA.	
SQUARE DRIVE INSERT BITS  Ideal for production use of Tri-Drive and our new QuaDrive.		000R1B	25050	4-6	#1	1"	1.20	EA.
		000R2B	25056	8-10	#2	1"	1.20	EA.
	000R3B	25060	12-14	#3	1"	1.20	EA.	
	100R1B	25065	4-6	#1	2"	2.37	EA.	
	100R2B	25072	8-10	#2	2"	2.37	EA.	
	100R3B	25075	12-14	#3	2"	2.37	EA.	
	125R1B	10149	4-6	#1	3"	4.14	EA.	
	125R2B	10166	8-10	#2	3"	4.14	EA.	
	125R3B	10167	12-14	#3	3"	4.14	EA.	
	140R1B	10176	4-6	#1	4"	5.94	EA.	
	140R2B	10177	8-10	#2	4"	6.65	EA.	
	140R3B	10180	12-14	#3	4"	6.65	EA.	
	160R2B	25352	8-10	#2	6"	7.93	EA.	
	160R3B	25357	12-14	#3	6"	7.93	EA.	
	180R2B	10193	8-10	#2	8"	8.56	EA.	
	110R2B	10175	8-10	#2	10"	9.54	EA.	
DOUBLE ENDED INSERT BITS 	P2P2B	10178	#2 Phil/#2 Phil		1 3/4"	5.64	EA.	
	P2S8B	10179	#2 Phil/8-10 Slot		1 3/4"	2.86	EA.	
SPANNER INSERT BITS 	00SP6B	25027	#6		1"	4.61	EA.	
	00SP8B	10195	#8		1"	4.61	EA.	
	00SP10B	10196	#10		1"	4.61	EA.	
BIT HOLDER & NUT SETTERS 	M1B	25260	1/4" Mag Bit Hldr		1 3/4"	13.76	EA.	
	M10B	25255	1/4" Mag Bit Hldr		2 7/8"	16.19	EA.	
	MT208B	10183	1/4" Mag Nut Setter		1 5/8"	6.13	EA.	
	MT208LB	10186	1/4" Mag Nut Setter		2 9/16"	7.41	EA.	
	MT210B	10184	3/16" Mag Nut Setter		1 5/8"	6.87	EA.	
	MT210LB	10187	3/16" Mag Nut Setter		2 9/16"	8.23	EA.	
	MT212B	10185	3/8" Mag Nut Setter		1 5/8"	8.53	EA.	
	MT212LB	10188	3/8" Mag Nut Setter		2 9/16"	9.70	EA.	

H

LONGER SIZES AVAILABLE!

TOOLS, DRILLS, AND ACCESSORIES

SELECT-A-BIT KIT

10 Piece Kit

The Right Drive When You Need It!



KIT INCLUDES:

- 4 - Phillips Drive Bits
 - 3 - Slotted Drive Bits
 - 2 - Square Drive Bits
 - 1 - Magnetic Holder for Power Driving.
- Insert the Magnetic Holder into the star hole at the top of the bit case, and it becomes a screwdriver handle.

STOCK NO.	UPC NO.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER KIT
SAB10	28010	12 Kits	27.28 EA


REPLACEMENT COMPONENTS FOR KIT

QUANTITY	DESCRIPTION	REPLACEMENT PART #
1	Bit Holder	M10B
1	#6 Slotted Bit	0016B
1	#8 Slotted Bit	0018B
1	#10 Slotted Bit	00110B
1	#1 Phillips Bit	000P1B
2	#2 Phillips Bit	000P2B
1	#3 Phillips Bit	000P3B
1	#2 Square Drive Bit	000R2B
1	#3 Square Drive Bit	000R3B

For PVC Plastic

CABLE SAW

FOR PLUMBING AND ELECTRICAL/FOR ALL PVC PIPE



DIRECTIONS:

1. Secure PVC pipe for cutting. Loop cable around pipe at the location you wish to cut.
2. Apply pressure, while making short back and forth strokes to establish a starting cut or pilot groove in the pipe.
3. Using the middle third of the cable, make longer strokes to completely cut through PVC pipe.



- A WIRE CABLE SAW WITH VINYL COVERED HANDLES.
- SUITABLE FOR CUTTING PVC PLASTIC PIPE.

STOCK NO.	UPC NO.	DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
MCS26	71616	26" Cable Saw	0.25	1	17.06 EA
MCS46	71617	46" Cable Saw	0.50	1	18.88 EA

TOOLS, DRILLS, AND ACCESSORIES

MARKING CRAYONS



Weather resistant, fade resistant, lead free. For use on lumber (rough or smooth), cardboard, concrete, metal, paper, plastic and other surfaces. Each crayon 4-1/2" x 1/2".

STOCK NO.	UPC NO.	COLOR	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EA
LCB12	72600	Blue	2.83	12	21.36 EA.
LCBLK12	72602	Black	2.83	12	21.36 EA.
LCY12	72603	Yellow	2.83	12	21.36 EA.
LCR12	72604	Red	2.83	12	21.36 EA.

CRAYON HOLDERS



- Walnut holder fits both round or hexagonal marking crayons 1/2" in diameter.
- Walnut handle, metal chuck, hole for wrist strap.



- Aluminum holder is spring loaded and can be used with extension handle.
- Designed to hold Lumber Crayons and High Heat Metal Crayons 1/2" in diameter.

STOCK NO.	UPC NO.	DESCRIPTION	WT. PER EACH	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EA
WCH1	72599	Crayon Holder-Wood	0.32	1	13.79 EA.
MCH1	72609	Crayon Holder-Metal	0.06	1	16.81 EA.

MACHINE SCREW ANCHOR SETTING TOOL




STOCK NO.	UPC NO.	SIZE	WT. PER EACH	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
1402ST	17905	8-32	.05	1	3.82 EA.
1403ST	17910	10-24	.10	1	4.61 EA.
1404ST	17915	10-32	.10	1	4.61 EA.
1406ST	17925	1/4-20	.15	1	5.10 EA.
1407ST	17930	5/16-18	.30	1	5.42 EA.
1408ST	17935	3/8-16	.50	1	5.72 EA.
1409ST	17940	1/2-13	.50	1	11.06 EA.

HAND DRIVE TOOL

STEEL DROP-IN ANCHOR SETTING TOOL

For Setting DIA14, DIA12, DIA38 & DIA58



STOCK NO.	UPC NO.	SIZE	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
DIA14T	12181	1/4-20	1	3.52 EA.
DIA38T	12182	3/8-16	1	4.58 EA.
DIA12T	12183	1/2-13	1	5.64 EA.
DIA58T	12184	5/8-11	1	10.52 EA.

TOOLS, DRILLS, AND ACCESSORIES

SKIN PACKAGED CORRUGATED FOR SAFETY IN HANDLING



METALLICS KEYHOLE SAW WOODEN HANDLE

- Designed especially for plasterboard.
- Make cut-outs for electrical outlets, etc.
- Point sharpened for plunge cuts.



STOCK NO.	UPC NO.	LENGTH	BLADE EACH	WEIGHT PKG.	SUGGESTED TRADE LIST PRICE PER EACH
US6	31300	6	1.5 oz	1	5.90 EA.

METALLICS HAND DRILLING HAMMER WOODEN HANDLE

- The old standby.

SAFETY GLASSES SHOULD BE WORN FOR ANY DRIVING APPLICATIONS. SEE THE NEW LINE OF SAFETY GLASSES ON PAGES 181 AND 182.



STOCK NO.	UPC NO.	HEAD WEIGHT	OVERALL LENGTH	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
HAM3	18700	3 lbs	10"	1	25.81 EA.

CARBON STEEL TAPS

PLUG STYLE

A STRONG, DURABLE PRODUCT



STOCK NO.	UPC NO.	SIZE	USE DRILL SIZE	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
440CT	24900	4-40	#43	.10	5	19.02 EA.
632CT	24905	6-32	#36	.05	5	18.86 EA.
832CT	24910	8-32	#29	.06	5	19.02 EA.
1024CT	24915	10-24	#25	.15	5	19.92 EA.
1032CT	24920	10-32	#21	.10	5	19.92 EA.
1420CT	24925	1/4-20	#7	.15	5	21.77 EA.
516CT	24930	5/16-18	17/64	.22	5	23.76 EA.
3816CT	24935	3/8-16	5/16	.33	5	30.36 EA.
1213CT	24940	1/2-13	27/64	.71	5	39.70 EA.



TAP WRENCH T-HANDLE STYLE

STOCK NO.	UPC NO.	CAPACITY	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
TWH1	24970	0 to 1/4	.10	1	9.28 EA.
TWH2	24975	1/4 to 1/2	.15	1	15.33 EA.



TOOLS, DRILLS, AND ACCESSORIES



TAPCON® CONCRETE SCREWS INSTALLATION KIT



NOT APPLICABLE FOR
THE NEW METALLICS
QUADRIE CONCRETE
SCREW

8 PIECE KIT
TOOLS AND DRIVING ACCESSORIES

KIT INCLUDES:
1 - Drill Driver 1 - Phillips Bit Holder
1 - Drill Adapter 2 - Phillips Bits
2 - Hex Drivers 1 - Allen Hex Key

DRILL BIT NOT INCLUDED


IN A STURDY PLASTIC STORAGE CASE

KIT				
STOCK NO.	UPC NO.	DESCRIPTION	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
IT1000	31200	Installation Tool (complete kit)	1	70.39 EA.
REPLACEMENT COMPONENTS FOR KIT				
MHD14	31205	1/4" Magnetic Hex Driver		
MHD56	31210	5/16" Magnetic Hex Driver		
PBH	31215	#2 & #3 Phillips Bit Holder		
ITSLEVE	31203	Drill/Driver Adapter		
PB2	31220	#2 Phillips Bit		
PB3	31225	#3 Phillips Bit		
HK1	31230	1/8" Allen Hex Key		


CAN BE USED WITH
THE METALLICS
QUADRIE CONCRETE
SCREWS

MASONRY DRILLS FOR CONCRETE SCREWS

SPECIAL SIZE AND LENGTH
FOR USE WITH INSTALLATION TOOL ABOVE



STOCK NO.	UPC NO.	SIZE	SCREW DIA.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
CD1	31250	5/32 x 3 1/2	3/16	1	3.08 EA.
CD2	31255	5/32 x 4 1/2	3/16	1	3.62 EA.
CD3	31260	5/32 x 5 1/2	3/16	1	4.11 EA.
CD5	31265	3/16 x 3 1/2	1/4	1	3.16 EA.
CD6	31270	3/16 x 4 1/2	1/4	1	3.73 EA.
CD7	31275	3/16 x 5 1/2	1/4	1	5.29 EA.
CD8	31280	3/16 x 6	1/4	1	6.79 EA.



32 oz



10 oz

CAULKING GUN

PISTON ROD WITH DOUBLE FRICTION PLATE

QUICK-RELEASE LEVER, STANDARD CARTRIDGE SIZE

STOCK NO.	UPC NO.	WT. PER PKG.	TUBE SIZE	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
CG1	35020	.85	10 oz	1	4.83 EA.
CG32	35050	1.90	32 oz	1	23.14 EA.

TOOLS, DRILLS, AND ACCESSORIES



HIGH-SPEED TWIST DRILLS

118° POINTS *Bright Steel – Jobber's Length*

STOCK NO.	UPC NO.	SIZE	OVERALL LENGTH	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH PKG	
NUMBERED SIZES							
NHSD6	24806	#6	3 ³ / ₄	.40	10	34.34	EA. PKG.
NHSD7	24807	#7	3 ⁵ / ₈	.40	10	32.51	EA. PKG.
NHSD8	24808	#8	3 ⁵ / ₈	.40	10	28.83	EA. PKG.
NHSD9	24809	#9	3 ⁵ / ₈	.37	10	28.20	EA. PKG.
NHSD10	24810	#10	3 ⁵ / ₈	.35	10	26.98	EA. PKG.
NHSD11	24811	#11	3 ¹ / ₂	.35	10	26.98	EA. PKG.
NHSD20	24820	#20	3 ¹ / ₄	.25	10	22.07	EA. PKG.
NHSD21	24821	#21	3 ¹ / ₄	.24	10	22.70	EA. PKG.
NHSD22	24822	#22	3 ¹ / ₈	.23	10	19.92	EA. PKG.
NHSD25	24825	#25	3	.22	10	19.32	EA. PKG.
NHSD26	24826	#26	3	.20	10	19.32	EA. PKG.
NHSD28	24828	#28	2 ⁷ / ₈	.18	10	19.92	EA. PKG.
NHSD29	24829	#29	2 ⁷ / ₈	.16	10	19.92	EA. PKG.
NHSD30	24830	#30	2 ³ / ₄	.14	10	19.92	EA. PKG.
NHSD31	24831	#31	2 ³ / ₄	.12	10	19.92	EA. PKG.
NHSD35	24835	#35	2 ⁵ / ₈	.10	10	19.92	EA. PKG.
NHSD36	24836	#36	2 ¹ / ₂	.10	10	19.92	EA. PKG.
NHSD37	24837	#37	2 ¹ / ₂	.10	10	15.01	EA. PKG.
NHSD43	24843	#43	2 ¹ / ₄	.10	10	15.01	EA. PKG.
FRACTIONAL SIZES 118° POINTS							
HSD1	24300	1 ¹ / ₁₆	1 ⁷ / ₈	.10	10	14.42	EA. PKG.
HSD2	24305	5 ¹ / ₆₄	2	.10	10	14.42	EA. PKG.
HSD3	24310	3 ¹ / ₃₂	2 ¹ / ₄	.10	10	14.72	EA. PKG.
HSD4	24315	7 ¹ / ₆₄	2 ⁵ / ₈	.10	10	14.72	EA. PKG.
HSD5	24320	1 ¹ / ₈	2 ³ / ₄	.10	10	16.57	EA. PKG.
HSD6	24325	9 ¹ / ₆₄	2 ⁷ / ₈	.20	10	18.09	EA. PKG.
HSD7	24330	5 ¹ / ₃₂	3 ¹ / ₈	.20	10	18.39	EA. PKG.
HSD8	24335	11 ¹ / ₆₄	3 ¹ / ₄	.20	10	20.85	EA. PKG.
HSD9	24340	3 ¹ / ₁₆	3 ¹ / ₂	.20	10	24.23	EA. PKG.
HSD29	24345	13 ¹ / ₆₄	3 ⁵ / ₈	.40	10	27.60	EA. PKG.
HSD10	24350	7 ¹ / ₃₂	3 ³ / ₄	.40	10	29.13	EA. PKG.
HSD11	24355	15 ¹ / ₆₄	3 ⁷ / ₈	.40	10	31.88	EA. PKG.
HSD12	24360	1 ¹ / ₄	4	.40	10	37.41	EA. PKG.
HSD13	24365	17 ¹ / ₆₄	4 ¹ / ₈	.50	5	22.07	EA. PKG.
HSD14	24370	9 ¹ / ₃₂	4 ¹ / ₄	.50	5	25.91	EA. PKG.
HSD15	24375	19 ¹ / ₆₄	4 ³ / ₈	.50	5	27.60	EA. PKG.
HSD16	24380	5 ¹ / ₁₆	4 ¹ / ₂	.50	5	28.37	EA. PKG.
*HSD16R	24385	5 ¹ / ₁₆	3 ¹³ / ₁₆	.50	5	31.42	EA. PKG.
HSD17	24390	21 ¹ / ₆₄	4 ⁵ / ₈	.60	5	31.58	EA. PKG.
HSD18	24395	11 ¹ / ₃₂	4 ³ / ₄	.60	5	35.86	EA. PKG.
HSD19	24400	23 ¹ / ₆₄	4 ⁷ / ₈	.60	5	40.30	EA. PKG.
HSD20	24405	3 ¹ / ₈	5	.60	5	41.39	EA. PKG.
*HSD20R	24410	3 ¹ / ₈	4 ¹ / ₄	.60	5	43.85	EA. PKG.
HSD21	24415	25 ¹ / ₆₄	5 ¹ / ₈	.60	5	44.44	EA. PKG.
HSD22	24420	13 ¹ / ₃₂	5 ¹ / ₄	.60	5	47.22	EA. PKG.
HSD23	24425	27 ¹ / ₆₄	5 ³ / ₈	.80	5	52.43	EA. PKG.
HSD24	24430	7 ¹ / ₁₆	5 ¹ / ₂	.80	5	55.94	EA. PKG.
*HSD24R	24435	7 ¹ / ₁₆	4 ¹¹ / ₁₆	.80	5	54.58	EA. PKG.
HSD25	24440	29 ¹ / ₆₄	5 ⁵ / ₈	1.00	5	65.92	EA. PKG.
HSD26	24445	15 ¹ / ₃₂	5 ³ / ₄	1.00	5	63.47	EA. PKG.
HSD27	24450	31 ¹ / ₆₄	5 ⁷ / ₈	1.00	5	67.61	EA. PKG.
HSD28	24455	1 ¹ / ₂	6	1.00	5	70.36	EA. PKG.
*HSD28R	24460	1 ¹ / ₂	4	1.00	5	73.41	EA. PKG.
* 1/4" Reduced Shank							



TOOLS, DRILLS, AND ACCESSORIES



SELECT-A-DRILL

SAD13 - 13 Piece Select-A-Drill Kit

Thirteen (13) high-speed jobber length drills from 1/16" to 1/4" by 64ths


Popular sizes in a unique rotating case

SAD21 - 21 Piece Select-A-Drill Kit

Twenty-one (21) high-speed jobber length drills from 1/16" to 3/8" by 64ths

Popular sizes in a unique rotating case

118° POINTS



LEAN ON METALLICS

STOCK NO.	UPC NO.	WT. PER KIT	STD. PKG.	SUGGESTED TRADE LIST PRICE PER KIT	
SAD13	24520	.35	12 Kits	30.36	EA. KIT
SAD21	24525	1.05	6 Kits	78.23	EA. KIT



118° POINTS

HIGH-SPEED DRILL KITS

IN METAL INDEX CASE

HSDK1 29 Drills

HSDK2 15 Drills

HSDK3 13 Drills

STOCK NO.	UPC NO.	DESCRIPTION	WT. PER KIT	STD. PKG.	SUGGESTED TRADE LIST PRICE PER KIT	
HSDK1	24510	29 Drills 1/16" thru 1/2" by 1/64ths	3.60	1	164.45	EA. KIT
HSDK2	24505	15 Drills 1/16" thru 1/2" by 1/32nds	2.40	1	86.90	EA. KIT
HSDK3	24500	13 Drills 1/16" thru 1/4" by 1/64ths	.80	1	28.50	EA. KIT

H

TOOLS, DRILLS, AND ACCESSORIES

GOLD HIGH-SPEED DRILL KITS

GOLD SURFACE TREATED HEAVY DUTY DRILLS
13 PIECE KIT IN METAL INDEX CASE
HVAC SPECIAL DRILLS
LIGHT GAUGE SHEET METAL



STOCK NO.	UPC NO.	DESCRIPTION	WT. PER KIT	STD. PKG.	SUGGESTED TRADE LIST PRICE PER KIT
GDK13	24502	13 Drills $\frac{1}{16}$ " thru $\frac{1}{4}$ " x $\frac{1}{64}$ ths	.80	1	41.39 EA. KIT



HEX SHANK DRILL SET

5 PIECE SET

FOR DRILLS AND CORDLESS SCREWDRIVERS

118° POINTS


STOCK NO.	UPC NO.	DESCRIPTION	STD. PKG.	SUGGESTED TRADE LIST PRICE PER KIT
DHS5	24530	5 Drills: $\frac{3}{32}$ " $\frac{7}{64}$ " $\frac{1}{8}$ " $\frac{9}{64}$ " $\frac{5}{32}$ "	5 Sets	26.73 EA. KIT

TO PROLONG DRILL LIFE USE CUTTING OIL FOR METAL.

TAP AND DRILL BIT SET

13 PIECE

- 6 Carbon Plug Taps - 4-40, 6-32, 8-32, 10-24, 10-32, $\frac{1}{4}$ -20
- 6 HSS Twist Drills - #43, #36, #29, #25, #21, #7
- 1 T-Handle Wrench



118° POINTS

STOCK NO.	UPC NO.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER KIT
TDS13	24945	1	54.17 EA. KIT

SCREW EXTRACTOR AND DRILL BIT SET

10 PIECE

- Screw Extractors - #1, #2, #3, #4, #5
- Twist Drills - $\frac{5}{64}$ " $\frac{7}{64}$ " $\frac{5}{32}$ " $\frac{1}{4}$ " $\frac{17}{64}$ "



118° POINTS

STOCK NO.	UPC NO.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER KIT
SEDS10	25028	1	44.58 EA. KIT



TOOLS, DRILLS, AND ACCESSORIES

COMBINATION HIGH SPEED STEEL DRILL-TAP

FOR ALL METAL APPLICATIONS



STOCK NO.	UPC NO.	DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
DT632	24094	High Speed Steel 6-32 Drill-Tap	.01	1	28.89 EA.
DT832	24095	High Speed Steel 8-32 Drill-Tap	.02	1	29.57 EA.
DT1032	24096	High Speed Steel 10-32 Drill-Tap	.03	1	30.66 EA.
DT1420	24097	High Speed Steel 1/4-20 Drill Tap	.04	1	35.78 EA.
DT3816	24098	High Speed Steel 3/8-16 Drill-Tap	.05	1	50.03 EA.
DT1213	24099	High Speed Steel 1/2-13 Drill-Tap	.10	1	70.20 EA.

SHIP AUGER BITS

HEX SHANK

EXTRA HIGH QUALITY



SPECIFICALLY DESIGNED FOR WOOD PRODUCT CONSTRUCTION

- Single twist with single cutter and side up
- Machine ground hollows, deep throat for fast chip removal
- $\frac{7}{16}$ " shank for 3 jaw chucks
- Heat treated tool steel for strength and long life

STOCK NO.	UPC NO.	BORE DIAMETER	LENGTH	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
AS916	24600	$\frac{9}{16}$	8	.27	1 Bit	25.40 EA.
AS58	24601	$\frac{5}{8}$	8	.28	1 Bit	24.44 EA.
AS1116	24602	$\frac{11}{16}$	8	.29	1 Bit	34.53 EA.
AS34	24603	$\frac{3}{4}$	8	.32	1 Bit	41.17 EA.
AS1316	24604	$\frac{13}{16}$	8	.33	1 Bit	41.26 EA.
AS78	24605	$\frac{7}{8}$	8	.39	1 Bit	41.26 EA.
AS1516	24606	$\frac{15}{16}$	8	.40	1 Bit	48.45 EA.
AS1	24607	1	8	.45	1 Bit	49.35 EA.
AS118	24608	$1\frac{1}{8}$	8	.50	1 Bit	52.40 EA.
AS114	24609	$1\frac{1}{4}$	8	.55	1 Bit	58.78 EA.
AS138	24610	$1\frac{3}{8}$	8	.60	1 Bit	67.74 EA.
AS112	24611	$1\frac{1}{2}$	8	.65	1 Bit	88.10 EA.
AL916	24615	$\frac{9}{16}$	18	.70	1 Bit	94.42 EA.
AL58	24616	$\frac{5}{8}$	18	.79	1 Bit	53.25 EA.
AL1116	24617	$\frac{11}{16}$	18	.82	1 Bit	58.69 EA.
AL34	24618	$\frac{3}{4}$	18	.91	1 Bit	66.27 EA.
AL1316	24619	$\frac{13}{16}$	18	.94	1 Bit	67.39 EA.
AL78	24620	$\frac{7}{8}$	18	1.10	1 Bit	67.39 EA.
AL1516	24621	$\frac{15}{16}$	18	1.14	1 Bit	69.43 EA.
AL1	24622	1	18	1.28	1 Bit	64.58 EA.
AL118	24623	$1\frac{1}{8}$	18	1.42	1 Bit	67.28 EA.
AL114	24624	$1\frac{1}{4}$	18	1.56	1 Bit	96.52 EA.
AL138	24625	$1\frac{3}{8}$	18	1.70	1 Bit	103.20 EA.
AL112	24626	$1\frac{1}{2}$	18	1.85	1 Bit	122.11 EA.

THE METALLICS SHIP AUGER BIT IS NOT SOLD AS A NAIL BITER. IT IS ONLY RECOMMENDED FOR WOOD PRODUCTS.

H

TOOLS, DRILLS, AND ACCESSORIES



QUIK-BIT FLAT WOOD BORING BIT

PACKED IN VINYL POUCH

STOCK NO.	UPC NO.	SIZE	OVERALL LENGTH	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
QB1	24701	1/4	6	.21	1 Bit	6.08 EA.
QB2	24702	5/16	6	.32	1 Bit	5.72 EA.
QB3	24703	3/8	6	.42	1 Bit	6.19 EA.
QB4	24704	7/16	6	.42	1 Bit	6.19 EA.
QB5	24705	1/2	6	.42	1 Bit	6.19 EA.
QB6	24706	9/16	6	.47	1 Bit	6.46 EA.
QB7	24707	5/8	6	.47	1 Bit	6.46 EA.
QB8	24708	11/16	6	.52	1 Bit	6.70 EA.
QB9	24709	3/4	6	.52	1 Bit	6.70 EA.
QB10	24710	13/16	6	.52	1 Bit	6.79 EA.
QB11	24711	7/8	6	.52	1 Bit	7.06 EA.
QB12	24712	15/16	6	.55	1 Bit	7.55 EA.
QB13	24713	1	6	.33	1 Bit	7.55 EA.
QB14	24714	1 1/8	6	.44	1 Bit	10.38 EA.
QB15	24715	1 1/4	6	.47	1 Bit	10.38 EA.
QB16	24716	1 3/8	6	.50	1 Bit	10.46 EA.
QB17	24717	1 1/2	6	.50	1 Bit	10.46 EA.
QB22	24722	3/8	16	.25	1 Bit	18.72 EA.
QB24	24724	1/2	16	.33	1 Bit	19.10 EA.
QB26	24726	5/8	16	.45	1 Bit	20.85 EA.
QB28	24728	3/4	16	.58	1 Bit	22.97 EA.
QB29	24729	7/8	16	.65	1 Bit	22.97 EA.
QB31	24731	1	16	.81	1 Bit	22.40 EA.

BELL HANGER'S DRILL

HIGH-GRADE STEEL



- Specifically designed for wood product construction
- For all telephone, electrical, small wire, protective alarm and cable T.V. uses
- Resists damage during drilling if metal is encountered
- Not for masonry products

STOCK NO.	UPC NO.	DIAMETER	LENGTH	DIAMETER	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
BHD5	26020	1/4	18	1/4	.75	1 Drill	30.14 EA.
BHD6	26025	5/16	18	5/16	1.00	1 Drill	33.49 EA.
BHD7	26030	3/8	18	3/8	1.50	1 Drill	36.13 EA.
BHD8	26035	1/2	18	3/8	1.70	1 Drill	41.20 EA.
BHD9	26040	1/4	24	1/4	1.00	1 Drill	42.35 EA.
BHD10	26045	5/16	24	5/16	1.50	1 Drill	46.03 EA.
BHD11	26050	3/8	24	3/8	2.00	1 Drill	47.82 EA.
BHD12	26055	1/2	24	3/8	2.50	1 Drill	52.81 EA.

TOOLS, DRILLS, AND ACCESSORIES



SDS-PLUS HAMMER DRILL

IDEAL FOR ROTARY AND PERCUSSION DRILLING
FOR ALL MASONRY PRODUCTS

STOCK NO.	UPC NO.	DESCRIPTION	SUGGESTED TRADE LIST PRICE PER EACH	
SDS31645	24101	3/16" x 4-1/2" SDS-Plus Hammer Drill Bit	14.96	EA.
SDS31665	24102	3/16" x 6-1/2" SDS-Plus Hammer Drill Bit	15.26	EA.
SDS3168	24103	3/16" x 8" SDS-Plus Hammer Drill Bit	21.47	EA.
SDS1445	24104	1/4" x 4-1/2" SDS-Plus Hammer Drill Bit	14.96	EA.
SDS1465	24106	1/4" x 6-1/2" SDS-Plus Hammer Drill Bit	15.26	EA.
SDS149	24107	1/4" x 9" SDS-Plus Hammer Drill Bit	21.47	EA.
SDS3865	24108	3/8" x 6-1/2" SDS-Plus Hammer Drill Bit	20.08	EA.
SDS389	24109	3/8" x 9" SDS-Plus Hammer Drill Bit	38.64	EA.
SDS1265	24111	1/2" x 6-1/2" SDS-Plus Hammer Drill Bit	27.39	EA.
SDS129	24112	1/2" x 9" SDS-Plus Hammer Drill Bit	44.23	EA.
SDS5865	24113	5/8" x 6-1/2" SDS-Plus Hammer Drill Bit	36.43	EA.
SDS589	24114	5/8" x 9" SDS-Plus Hammer Drill Bit	44.23	EA.
SDS3465	24116	3/4" x 9" SDS-Plus Hammer Drill Bit	73.58	EA.

POWER BIT EXTENSIONS


FOR USE WITH QUIK-BITS, SHIP AUGER, AND ELECTRICIAN POWER BITS



- Hex wrench included
- Two set screws
- Packaged in vinyl pouch

STOCK NO.	UPC NO.	SIZE	WT. EACH	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH	
BE1418	24875	1/4 x 18	1.50	1	28.16	EA.
BE5618	24880	5/16 x 18	1.50	1	26.36	EA.
BE7612	24885	7/16 x 12	1.25	1	27.67	EA.
BE7618	24890	7/16 x 18	1.40	1	31.96	EA.
BE7624	24891	7/16 x 24	2.50	1	39.31	EA.

H




MULTI STEP DRILLS

SELF STARTING TIP ELIMINATES NEED FOR PILOT HOLE DRILLING

GOOD IN ALL SHEET METALS UP TO 1/8" THICK

STOCK NO.	UPC NO.	DESCRIPTION	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH	
SD12	24080	1/8-1/2" 2 FLUTE, 13 STEP	1	35.22	EA.
SD34	24082	1/4-3/4" 2 FLUTE, 9 STEP	1	51.14	EA.
SD78	24084	7/8 TO 1 1/8" 3 STEP	1	78.68	EA.
3 SET COMBO PACK					
SDCP3	24088	1/8 TO 1/2" 2 FLUTE, 13 STEP	1	165.08	EA.
		1/4 TO 3/4" 2 FLUTE, 9 STEP			
		7/8 TO 1 1/8" 3 STEP			

TOOLS, DRILLS, AND ACCESSORIES



PACKAGED INDIVIDUALLY WITH EXTRA
DOUBLE END SCREWS AND WRENCH

SAWTOOTH MULTISPUR WOOD DRILL BITS

REPLACEMENT SCREW POINTS

STOCK NO.	UPC NO.	SIZE	FITS	SUGGESTED LIST PRICE
SP0001	23550	1/4"	1 1/4" - 2 9/16"	6.90 EA
SP0002	23552	1/4"	3 - 4 5/16"	6.90 EA

STOCK NO.	UPC NO.	DESCRIPTION	SHANK DIAMETER	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
306MS0	23500	1 3/8 for 3/4" pipes	7/16	1	58.81 EA.
306MS1	23505	1 1/2 for 1" pipes	7/16	1	58.81 EA.
306MS2	23510	1 3/4 for 1 1/4" pipes	7/16	1	60.47 EA.
306MS3	23515	2 1/8 for 1 1/2" pipes	7/16	1	60.47 EA.
306MS4	23520	2 9/16 for 2" pipes	7/16	1	91.61 EA.

EXTENSIONS FOR SHIP AUGERS & MULTISPUR

HEX WRENCH INCLUDED • TWO SET SCREWS • PACKAGED IN VINYL POUCH

BE7612	24885	7/16 X 12	1	27.67
BE7618	24890	7/16 X 18	1	31.96

BULK CARBIDE MASONRY DRILLS

The Five Most Popular Sizes



**We know the drill.
You need it- we have it.**

H

STOCK NO.	UPC NO.	DIAMETER	LENGTH	SHANK DIAMETER	QTY.	WT.	SUGGESTED TRADE LIST PRICE PER EACH
BFRB12	37050	1/4	4	1/4	100	4.20	245.25 EA.
BFRB14	37055	5/16	4	1/4	75	3.08	232.22 EA.
BFRB16	37060	3/8	4	1/4	50	3.14	100.39 EA.
BFRB21	37065	1/2	4	1/4	25	2.80	36.02 EA.
BFRB20	37070	1/2	6	3/8	25	2.90	42.16 EA.

TOOLS, DRILLS, AND ACCESSORIES




Metallics



Flexible Fish-Bits

- Unique flexible self-feeding bits up to 72" long suitable for drilling holes the length of wall cavities and through hidden studs with no damage to wallboard plaster or any exterior finish.
- Bit has hole at the tip and the shank which allows you to fish wire



Size	Stock Number	UPC#	Description	Shank Size	Qty EA	Weight Per Pkg.	Suggested Trade List
1/4" x 54"	MFB1454	26455	FISH-BIT	3/16"	1	.5	\$58.72 ea
3/8" x 54"	MFB3854	26459				.5	\$61.72 ea
1/2" x 54"	MFB1254	26451				.5	\$64.58 ea
1/4" x 72"	MFB1472	26457				.75	\$62.24 ea
3/8" x 72"	MFB3872	26461				.75	\$63.08 ea
1/2" x 72"	MFB1272	26453				.75	\$65.13 ea

Stock Number	UPC#	Description	PKG. Qty	Weight Per PKG.	Suggested Trade List
MSG1	26445	Steering Guide	1	.5lbs	\$54.66 ea

FOR INFORMATION CALL

METALLICS EAST AT (800) 243-8272 or METALLICS WEST AT (800) 269-5183
 229 CROSS ST, BRISTOL, CT 651 NORTH MAIN ST, MANCOS, CO

TOOLS, DRILLS, AND ACCESSORIES


CARBIDE MASONRY DRILLS

IDEAL FOR ROTARY AND PERCUSSION DRILLING



- Specially designed spirals for fast dust removal
- Packed in vinyl pouch
- Slow spiral drills can be used with **either rotary or hammer drills** in hard brick, sandstone, bluestone, terracotta block and hard concrete

STOCK NO.	UPC NO.	DIAMETER	LENGTH	SHANK DIAMETER	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
BFR10	24100	1/8	3	3/32	.03	1	2.73 EA.
BFR11	24105	3/16	4	9/64	.05	1	2.73 EA.
BFR12	24110	1/4	4	1/4	.05	1	2.73 EA.
BFR13	24115	1/4	6	1/4	.05	1	3.98 EA.
BFR14	24120	5/16	4	1/4	.05	1	3.43 EA.
BFR15	24125	5/16	6	1/4	.10	1	4.93 EA.
BFR16	24130	3/8	4	1/4	.10	1	4.44 EA.
BFR17	24135	3/8	6	1/4	.15	1	5.53 EA.
BFR18	24140	7/16	6	1/4	.15	1	5.61 EA.
BFR21	24145	1/2	4	1/4	.10	1	6.40 EA.
BFR19	24150	1/2	6	1/4	.20	1	7.49 EA.
BFR20	24155	1/2	6	3/8	.20	1	7.49 EA.
BTT22	24160	9/16	6	3/8	.30	1	14.42 EA.
BTT23	24165	5/8	6	3/8	.45	1	20.17 EA.
BTT25	24175	7/8	6	1/2	.55	1	20.52 EA.
BTT26	24180	1	6	1/2	.75	1	26.95 EA.
BTT1	24185	1/4	12	1/4	.15	1	10.30 EA.
BTT2	24190	3/16	12	1/4	.25	1	10.44 EA.
BTT4	24200	1/2	12	3/8	.35	1	14.50 EA.
BTT5	24205	5/8	12	3/8	.60	1	19.21 EA.
BTT6	24210	3/4	12	1/2	.95	1	30.36 EA.
BTT7	24215	7/8	12	1/2	1.25	1	31.86 EA.
BTT8	24220	1	12	1/2	1.80	1	43.33 EA.




EXTRA LONG MASONRY DRILLS

HEAVY-DUTY CARBIDE TIPPED
PACKED IN VINYL POUCH

H

STOCK NO.	UPC NO.	DIAMETER	LENGTH	SHANK DIAMETER	WT. EACH	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
BTT9	24225	1/4	18	1/4	.25	1	17.88 EA.
BTT11	24235	3/8	18	3/8	.40	1	19.62 EA.
BTT12	24240	1/2	18	3/8	.55	1	23.00 EA.
BTT13	24245	5/8	18	1/2	1.00	1	27.30 EA.
BTT14	24250	3/4	18	1/2	1.35	1	33.38 EA.
BTT15	24255	7/8	18	1/2	1.85	1	65.21 EA.
BTT16	24260	1	18	1/2	2.20	1	65.37 EA.

TOOLS, DRILLS, AND ACCESSORIES



MASTER FLASH[®] COMPLETE ROOF JACK KIT



Everything in ONE KIT!

- The Master  Flash[®] Roof Jack
- UV Cable Tie
- Metallics Special Sealant
- 10 x 1 Indented Hex Tek Type Self-Drilling Screws
- Easy Installation Instructions



Universal Pipe Flashing System...

- Weather Resistant
- Adapts to Many Roof Surfaces
- Easily Installed
- Uniform Plumbing Code (UPC[®]) Listed

Numerous Applications...

- Plumbing, Heating/Air Conditioning Equipment
- Electrical Service Entrances
- TV Aerials
- Masts, Vents or Pipes Through Decks or Bulkheads

STOCK NO.	UPC NO.	FITS PIPE SIZES/ JACK BASE SIZE	DESCRIPTION OF CONTENTS	WEIGHT EACH	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
RJK1	31400	1/4" - 2" 4 1/2" Base	1 - Roof Jack, 1 - 25" Sealant Strip, 12 - TEK Screws, 1 - 11" Cable Tie	.30	1	27.47 EA.
RJK2	31401	1/4" - 3" 6" Base	1 - Roof Jack, 1 - 35" Sealant Strip, 16 - TEK Screws, 1 - 15" Cable Tie	.50	1	31.94 EA.
RJK3	31402	1/4" - 4" 8" Base	1 - Roof Jack, 1 - 45" Sealant Strip, 20 - TEK Screws, 1 - 21" Cable Tie	.75	1	37.52 EA.

MASTER FLASH ROOF JACKS - BULK/UNPACKAGED

STOCK NO.	UPC NO.	FITS PIPE SIZES/ JACK BASE SIZE	DESCRIPTION OF CONTENTS	WEIGHT EACH	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
RJK1B	31237	1/4" - 2" for 4 1/2" Base	1 - Roof Jack	.25	1	16.87 EA.
RJK2B	31238	1/4" - 3" for 6" Base	1 - Roof Jack	.50	1	19.42 EA.
RJK3B	31239	1/4" - 4" for 8" Base	1 - Roof Jack	.75	1	22.86 EA.

H


DAP[®] DOW CORNING[®] SILICONE SEALANT

Protect and seal with 100% silicone rubber. Waterproof and flexible. Non-paintable. 50 year manufacturer durability guarantee. Meets Fed. Spec. TT-S-001534A, Class A.




STOCK NO.	UPC NO.	DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
WDSC10	71234	CLEAR - 10.1 oz.	1.08	1	8.00 EA.
WDSW10	71235	WHITE - 10.1 oz.	1.08	1	8.17 EA.

GREY BUTYL TAPE FOR CAULKING (SOLD IN PLASTIC BAGS)



STOCK NO.	UPC NO.	DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
TC1	31236	1/8" thick x 3/4" wide x 30' long.	1.08	1	15.49 EA.

TOOLS, DRILLS, AND ACCESSORIES



ROOF JACKS

26 GAUGE
10" x 14" Standard Base
Two-piece galvanized



STOCK NO.	UPC NO.	PIPE SIZE	WT. PER EACH	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
MF50	31410	1/2"	1.00	1	7.38 EA.
MF75	31411	3/4"	1.05	1	7.38 EA.
MF100	31412	1"	.95	1	7.38 EA.
MF125	31413	1 1/4"	.95	1	7.38 EA.
MF150	31414	1 1/2"	.95	1	7.38 EA.
MF200	31415	2"	.90	1	7.38 EA.

For 0/12 - 5/12 roof pitch




ROOF JACKS

26 GAUGE - FHA
17" x 17" Shingle Base
Two-piece galvanized



STOCK NO.	UPC NO.	PIPE SIZE	WT. PER EACH	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
MFHA50	31416	1/2"	1.80	1	9.16 EA.
MFHA75	31417	3/4"	1.80	1	9.16 EA.
MFHA100	31418	1"	1.80	1	9.16 EA.
MFHA125	31419	1-1/4"	1.80	1	9.16 EA.
MFHA150	31420	1-1/2"	1.75	1	9.16 EA.
MFHA200	31421	2"	1.75	1	9.16 EA.

For 0/12 - 5/12 roof pitch



The Economical One! ROOF JACKS

26 GAUGE
One-Piece Spun Galvanized



STOCK NO.	UPC NO.	PIPE SIZE	WT. PER EACH	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
SMF50	31422	1/2"	.75	1	6.35 EA.
SMF75	31423	3/4"	.75	1	6.35 EA.
SMF100	31424	1"	.75	1	6.35 EA.
SMF125	31425	1 1/4"	.75	1	6.35 EA.
SMF150	31426	1 1/2"	.75	1	6.35 EA.
SMF200	31427	2"	.75	1	6.35 EA.



For 0/12 - 5/12 roof pitch

H

TOOLS, DRILLS, AND ACCESSORIES

3-in-1 ROOF FLASHINGS

GALVANIZED BASE ROOF FLASHINGS
24 GAUGE WITH ELASTOMER COLLAR



Stock No. MRJ125

Fits pipe sizes: 1-1/2", 2", 3"*

Fits base size: 10-3/4" x 12-1/2"

* Can be modified to fit 1-1/4" pipe

Stock No. MRJ50

Fits pipe sizes: 1/2", 3/4", 1"

Fits base size: 8-3/4" x 12-1/2"

- Slides over pipe - for pitch to 45 degree.
- Rustproof, stamped galvanized 24 gauge.
- 18" x 18" base for code required areas.
- Rated 180°F continuous heat.
- Approved for Type B installations.

- Slides over pipe. Type of base determines pitch.
- Ring on collar tears off, allowing flashings to seal different pipe diameters.
- Non-fading, cracking and rusting bases and sealing collars.
- Rated 180°F continuous heat.
- Approved for Type B installations.

STOCK NO.	UPC NO.	PIPE SIZE	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER EACH
MRJ50	31408	1/2" - 1"	0.82	1	11.69 EA.
MRJ125	31409	1-1/4" - 3"	1.16	1	14.39 EA.



PACKAGED IN POLY BAGS

FLOOR FLANGE

ZINC PLATED

STOCK NO.	UPC NO.	PIPE SIZE	ANCHOR HOLE	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER PKG
MFF25	16201	1/2"	1/4	6.00	10	5.20 EA. PKG.
MFF75	16202	3/4"	1/4	5.80	10	6.19 EA. PKG.
MFF100	16203	1"	1/4	8.80	10	7.90 EA. PKG.
MFF125	16204	1 1/4"	1/4	4.50	5	10.76 EA. PKG.
MFF150	16205	1 1/2"	1/4	6.25	5	11.42 EA. PKG.
MFF200	16206	2"	5/16	10.25	5	15.15 EA. PKG.



**Metallics and Avanti
Screw, Inc.**
Where
Manufacturing
Quality is Job
One!