



HUBBELL Delivers...

...Power, Voice, Data and Video...



...through the floor




...in the floor



...in the wall



...at the workstation



...More Solutions



Wiring Device-Kellems

www.hubbell-wiring.com

Hubbell Delivers Multi-Service, Floor Boxes for Concrete and Raised Access Floors !



Raised Access and Concrete Recessed Stamped Steel Floor Boxes

Hubbell offers a complete line of recessed stamped steel floor boxes for raised floor and concrete floor applications. These multi-service boxes are available in four or eight gang options and utilize modular face plates. Single gang face plate options include blank, toggle, Style Line®, duplex and various manufacturers' data openings. The metallic cover/flange assembly features a large cable door to provide ample room for exiting cables.

Pour boxes are also available to allow raised access floor boxes to be used in concrete slab-on-grade applications. All Hubbell raised access floor boxes are acceptable for use in environmental air handling spaces other than ducts or plenums per NEC article 300.22(C) other space used for environmental air and are UL Listed.

Hubbell concrete floor boxes are UL Listed for carpeted or tile applications.

RAISED ACCESS

Step 1: Select raised access floor box.

Description

Stamped steel, 4-gang, deep.
Stamped steel, 4-gang, shallow.
Stamped steel, 8-gang, deep.
Stamped steel, 4-gang, deep, Chicago approved.
Stamped steel, 4-gang, shallow, Chicago approved.
Stamped steel, 8-gang, deep, Chicago approved.
Pour box for 4-gang box.
Pour box for 8-gang box.

Catalog Numbers

HBLAFB301BASE
HBLAFB401BASE
HBLAFB501BASE

HBLAFB301BASEC**

HBLAFB401BASEC**

HBLAFB501BASEC**

HBL301401PB*
HBL501PB*



HBLAFB301BASE



HBLTCGNT

Step 2: Select cover assembly.

Description

Steel cover and flange assembly, reversible.

Color

Granite
Black

Catalog Numbers

HBLTCGNT
HBLTCGNTBK

Notes: * Converts raised access floor box to be used in concrete applications.
** City of Chicago Approved, Construction Meets Requirements For CCEA-2000.

CONCRETE RECESSED

Step 1: Select recessed floor box.

Description

Stamped steel, 4-gang, deep.
Stamped steel, 4-gang, shallow.
Stamped steel, 8-gang, deep.

Catalog Numbers

HBLCFB301BASE
HBLCFB401BASE
HBLCFB501BASE



HBLCFB301BASE



HBLTCGNTSW

Step 2: Select cover assembly.

Description

Steel cover and flange assembly

Color

Granite
Black

Catalog Numbers

HBLTCGNTSW
HBLTCGNTBKS

RAISED ACCESS & CONCRETE RECESSED

Step 3: Select screw type modular face plate, gray.

Description

Duplex.
Style Line®.
Toggle.
Blank.
Hubbell.

Catalog Numbers


HBLST302SGY
HBLDE301SGY
HBLT0310SGY
HBLBL300SGY
HBL317SGY




HBLST302SGY



HBLDE301SGY



HBLT0310SGY



HBLBL300SGY



HBL317SGY

Hubbell Delivers Large Capacity for Power, Voice, Data and Video!



LARGE CAPACITY

Step 1: Select recessed floor box.

Description

Stamped steel (fully adjustable).


Cast iron (fully adjustable).

Note: Each floor box is furnished with removable non-metallic chamber plugs for internal wire routing between chambers.

Catalog Numbers

LCFBSSA

LCFBCA



Step 2: Select flush cover & flange.

Option A - Carpet application.

Description

Metallic cover, flange and cable doors.

Color

Brass Finish

Aluminum Finish

Gray

Black

Reinforced nylon cover with thermoplastic (ABS) flange and cable doors.

Brown

Gray

Ivory

Black

Catalog Numbers

LCFBCBRSC

LCFBCALC

LCFBCGYC


LCFBCBKC

LCFBCBRA

LCFBCGYA

LCFBCIA

LCFBCBKA



LCFBCGYA



LCFBP8



LCFBP720



LCFBP26



LCFBP14

Option B - Tile application.

Description

Metallic cover, flange and cable doors.

Color

Brass Finish

Aluminum Finish

Gray

Black

Catalog Numbers

LCFBCBRST

LCFBCALT

LCFBCGYT

LCFBCBKT

Step 3: Select service plates.

Six nylon face plates required (gray).

Description

Duplex opening.

Style Line® opening.

Single receptacle opening - boss dia. 1.55" to 1.58" (39.4-40.1).

Blank.

Catalog Numbers

LCFBP8

LCFBP26

LCFBP720

LCFBP14

CONCEALED 3-SERVICE FLOOR BOX

Step 1: Select recessed floor box.

Description

Stamped steel (fully adjustable).

Cast iron (fully adjustable).

Catalog Numbers

3SFBS

3SFBC



3SFBS

Step 2: Select flush cover & carpet flange.

Description

Thermoplastic (ABS) cover and flange assembly with

heavy gauge steel plate.

Color

Brown

Gray

Ivory

Black

Catalog Numbers

3SFBCBRA

3SFBCGYA

3SFBCIA

3SFBCBKA



3SFBCBRA



3SFBCIA

Step 3: Select service plates (optional).

Description

Duplex opening.

Voice/Data: 2 jack knockouts, .60" x .75" (15.2 x 19.1).

Blank.

Single receptacle opening - boss diameter 1.36" to 1.39" (34.5 to 35.3).

Style Line® opening.

Catalog Numbers

3SFBRP

3SFBTP

3SFBB

3SFBS

3SFBDS



3SFBRP



3SFBTP



3SFBB



3SFBS



3SFBDS

Concrete Recessed Floor Boxes

Hubbell offers a complete line of recessed stamped steel floor boxes for installation in concrete floor applications. These multi-service boxes are available in two or six gang options and utilize modular face plates. Single gang face plate options include blank, toggle, Style Line®, duplex and various manufacturers' data openings. Metallic cover/flange assembly features a large cable door to provide ample room for exiting cables. Hubbell concrete floor boxes are UL Listed for carpeted or tile applications. The three-service floor box series is available in cast iron or stamped steel and offers recessed devices in a smaller package. The covers have been redesigned and now feature ScrubShield™ gasketing that prevents the ingress of moisture and debris. The cover also features a new handle to make the cover easier to open. Three-service covers are available in ivory, brown, black and gray.

Hubbell Delivers a Variety of Flush Boxes, Flanges and Covers!



Round Cast Iron, Stamped Steel and Non-Metallic Floor Boxes

Hubbell round floor boxes are the all-around answer for a wide variety of installations and applications. Fully or semi-adjustable. Choose the materials, capacity and cover that's right for your application.

Hubbell round non-metallic floor boxes offer an economical solution for single and multi-service applications. These floor boxes accept non-metallic and brass covers and flanges.

Multi-Connect Recessed Wall Boxes

Hubbell Multi-Connect recessed wall boxes provide a versatile "in the wall" solution for single and multi-service applications. The product offering includes one, two, three, four and six gang boxes, barriers for separation of power and low voltage services, and a wide variety of modular face plates and wall flanges to match office decor. The recessed wall boxes are available in three styles: multi-service wall boxes for drywall applications, low-voltage wall boxes for drywall applications and multi-service wall boxes for masonry wall applications.

ROUND FLOOR BOXES

Select Round Floor Box

Description

Deep cast iron, 3/4" threaded conduit hub size.
Deep cast iron, 1" threaded conduit hub size.
Cast iron for wood floors.
Deep stamped steel.
Shallow stamped steel.

Catalog Numbers

B2536
B253641
B2588275
B2527
B2529




Select Carpet Flange.

Description

Brass flange, 6.25" (158.8mm) diameter.
Brass flange, 5.25" (133.4mm) diameter.
Aluminum flange, 5.25" (133.4mm) diameter.
Clear polycarbonate flange, 5.25" (133.4mm) dia.

Catalog Numbers

S3082
S3182
SA3182
S3079




Select Round Brass Cover, 3.88" (98.6mm)

Description

Single receptacle, 2 1/8".
Single receptacle, 2 3/8".
Duplex screw, 1 1/2" x 1 1/2".
Duplex flap.
Combination, 2 1/8" x 3/4".
Combination, 2 1/8" x 1".

Catalog Numbers

S2925
S3525
S3725
S3925
S2525
S2725




Non-Metallic Round Floor Boxes

Description

Non-metallic floor box with concrete cover and four reducers/closure plugs.
Adapter, includes four hangers for tile floors, four retainer clips & screws.
Adapter ring, brass.
Divider, low voltage for multi-service applications
Non-metallic cover, brown
Non-metallic cover, ivory
Non-metallic cover, gray
Non-metallic cover, black

Catalog Numbers

PFB1
PFBA1A
S5016
PFBT1A
PFBBCBRA
PFBBCIA
PFBBCGYA
PFBBCBLA



RECESSED WALLBOXES

Multi-Service Recessed Wall Boxes (for Drywall Applications)

Description


Multi-service recessed wall box, 1-gang.
Multi-service recessed wall box, 2-gang.
Multi-service recessed wall box, 3-gang.
Multi-service recessed wall box, 4-gang.
Multi-service recessed wall box, 6-gang.
Barrier for use with above boxes when used in multi-service applications.
Wall box flange for 1-gang boxes.
Wall box flange for 2-gang boxes.
Wall box flange for 3-gang boxes.
Wall box flange for 4-gang boxes.
Wall box flange for 6-gang boxes.
Duplex modular face plate.
Style Line modular face plate.
Toggle modular face plate.
Blank modular face plate.
Hubbell modular face plate.

Catalog Numbers

HBLWSCS1
HBLWSCS2
HBLWSCS3
HBLWSCS4
HBLWSCS6
HBLSCSBW



HBLTRIM1W*
HBLTRIM2W*
HBLTRIM3W*
HBLTRIM4W*
HBLTRIM6W*
HBLST302S*
HBLDE301S*
HBLT0310S*
HBLBL300S*
HBL317S*



Recessed Wall Boxes

Wall Boxes Flanges-Trim Fittings

Modular Face Plate

Shown Left to Right: Duplex, Style Line®, Toggle, Blank and Hubbell

Notes: * Available in White (WA), Ivory (I), Gray (GY) and Black (BK). Add color choice suffix to the end of catalog number. Example: HBLTRIM1W + WA is the White Flange.

Round or Rectangular! Cast Iron, Stamped Steel or Non-Metallic!



Rectangular Floor Boxes

Select Floor Box

Description

Deep cast iron, single gang, 3/4" threaded hubs.
Deep cast iron, single gang, 1" threaded hubs.
Deep cast iron, two gang, 3/4" threaded hubs.
Deep cast iron, two gang, 1" threaded hubs.
Deep cast iron, three gang, 3/4" threaded hubs.
Deep cast iron, three gang, 1" threaded hubs.
Shallow cast iron, single gang.
Shallow cast iron, two gang.
Shallow cast iron, three gang.
Deep stamped steel, single gang.
Deep stamped steel, two gang.
Deep stamped steel, three gang.
Shallow stamped steel, single gang.
Shallow stamped steel, two gang.
Shallow stamped steel, three gang.
Stamped steel for wood floors, single gang.
Stamped steel for wood floors, two gang.
Stamped steel for wood floors, three gang.

Catalog Numbers

B2436
B243641
B4233
B423341
B4333
B433361
B2414
B4214
B4314
B2431
B2432
B2433
B2421
B2422
B2423
B2481
B2482
B2483



B2436



B4214



B2433



B2482

Select Carpet Flange.

(fits all rectangular boxes, incl. non-metallic)

Description

Single gang, brass flange
Single gang, clear polycarbonate flange
Two gang, brass flange
Two gang, clear polycarbonate flange
Three gang, brass flange
Three gang, clear polycarbonate flange

Catalog Numbers

SB3083
S3083
SB3084
S3084
SB3085
S3085



SB3083



SB3084



SB3085

Select Brass Cover

(fits all rectangular boxes, incl. non-metallic)

Description

Blank
Duplex screw, 1 1/2" x 1 1/2"
Duplex flap
Combination, 2 1/8" x 3/4"
Combination, 2 1/8" x 1"
Style Line® opening

Catalog Numbers

S3813
S3625
S3825
S2425
S2625
S3826



S3813



S3625



S2625



S3825



S2425



S3826

Non-Metallic Rectangular Floor Boxes

Description

Single gang.
Two gang.
Three gang.
Single gang, non-metallic gray carpet flange.
Two gang, non-metallic gray carpet flange.
Three gang, non-metallic gray carpet flange.
Duplex/Style Line, gray cover plate, 1 per gang.

Tile application required components:

Non-metallic mounting collar, 1 per gang.
Non-metallic gray cover frame, 1 per gang.
Non-metallic duplex/style line, 1 per gang.

Carpet application, tapered flange, required components:

Non-metallic adapter collar, 1 per gang.
Brass adapter frame w/ grounding lug, 1 per gang.

Catalog Numbers

PFBRG1
PFBRG2
PFBRG3
PFBRFGY1
PFBRFGY2
PFBRFGY3
PFBR826GYA

PFBRMC
PFBRFRA
PFBR826GYA

PFBRAC
S5017G



PFBRG1



PFBRG2



PFBRMC



PFBRFGY2



S5017G



PFBRFRA



Rectangular Cast Iron, Stamped Steel and Non-Metallic Floor Boxes

Hubbell rectangular floor boxes are the all-around answer for a wide variety of installations and applications. Fully or semi-adjustable. Choose the materials, capacity and cover that's right for your application.

Hubbell rectangular non-metallic floor boxes offer an economical solution for single and multi-service applications. These floor boxes accept non-metallic and brass covers and flanges.

Hubbell Delivers Maximum Power and Communication Capacity



4x4 and 2x2 Flush Fire-Rated Poke-Throughs

Hubbell 4 x 4 fire-rated poke-throughs provide maximum power and communication capacity for flush, multi-service applications. These poke-throughs incorporate four 20A, 125V receptacles and four openings for voice and data connectors. The receptacles feature single or two circuit wiring as well as isolated ground capability. They are available in one piece, pre-wired versions that include 4 Keystone openings that will accept Hubbell category 6, 5e and USOC 6-position jacks as well as a variety of communication connectors and alternate manufacturers' jacks. In addition, they are offered in component pieces that will accept Panduit and Avaya (Lucent) jacks.

Hubbell 2 X 2 fire-rated poke-throughs include a Hubbell Style Line® 20A, 125V duplex receptacle and two Hubbell category 5e jacks. Isolated ground versions are also available. The through-floor fitting installs into a 3" cored hole and is UL listed for floors with 1 to 4 hour fire ratings.

One-Piece Units 2X2 & 4X4 20A 125V Fire-Rated Poke-Through Devices

Description	Catalog Numbers	
One-piece unit gray.	PT2X2GY	PT4X4GY
One-piece unit black.	PT2X2BL	PT4X4BL
One-piece unit ivory.	—	PT4X4I
One-piece unit brass.	PT2X2BRS	PT4X4BRS
One-piece unit brass/black.	PT2X2BRS3	PT4X4BRS3
One-piece IG unit gray.	PT2X2IGGY	N/A*
One-piece IG unit black.	PT2X2IGBL	N/A*
One-piece IG unit brass/black.	PT2X2IGBRS3	N/A*



Notes: 2X2 Includes two Category 5E jacks (HBL5EBK). 4X4 does not include data jacks.
*4X4 power receptacles include isolated ground and two-circuit wiring capability.
Partial brass units feature a black cover and a solid brass flange. N/A: not applicable.

Two-Piece Units 2X2 & 4X4 20A 125V Service Fittings with Cover

Description	Catalog Numbers	
Service fitting, gray.	PT2X2SFGY	PT4X4SFGY
Service fitting, black.	PT2X2SFBL	PT4X4SFBL
Service fitting, ivory.	—	PT4X4SFI
Service fitting, brass.	PT2X2SFBR3	PT4X4SFBR3
Service fitting, brass/black.	PT2X2SFBR3	PT4X4SFBR3



2X2 & 4X4 20A 125V Service Fittings with no Cover (4X4 Only)

Description	Catalog Numbers	
Service fitting, gray (no cover)*.	—	PT4X4SFGYNC
Service fitting, black (no cover)*.	—	PT4X4SFBLNC
Service fitting, brass (no cover)*.	—	PT4X4SFBR3NC

Notes: *Order service fitting with no cover when Avaya or Panduit jacks are to be used.
Order appropriate cover to be installed separately.



Through-Floor Fitting

Description	Catalog Numbers	
Through-floor fitting.	PT2X2FIT	PT4X4FIT

Notes: 2X2 fitting includes HBL2162BK receptacle.
4X4 fitting does not include power receptacle.



Replacement Covers

Description	Catalog Numbers	
Replacement cover, gray.	PT2X2CGY	PT4X4CGY
Replacement cover, black.	PT2X2CBL	PT4X4CBL
Replacement cover, ivory.	N/A	PT4X4CI
Replacement cover, brass colored plastic.	PT2X2CBRS	PT4X4CBRS



Specialty Covers for Panduit and Avaya Jacks (4X4 Only)

Description	Catalog Numbers	
Gray cover to accept Avaya jacks (Lucent).	—	PT4X4CLUGY
Black cover to accept Avaya jacks (Lucent).	—	PT4X4CLUBL
Brass plastic cover to accept Avaya jacks (Lucent).	—	PT4X4CLUBRS
Gray cover to accept Panduit jacks.	—	PT4X4CPAGY
Black cover to accept Panduit jacks.	—	PT4X4CPABL
Brass plastic cover to accept Panduit jacks.	—	PT4X4CPABRS



... with Fire-Rated Poke-Through Devices

DULPEX & IG SERIES

ScrubShield Flush Duplex Series

Description

One-piece standard duplex, painted aluminum, brown.
One-piece standard duplex, painted aluminum, black.
One-piece standard duplex, painted aluminum, gray.
One-piece standard duplex, painted aluminum, ivory.
One-piece standard duplex, all brass.
One-piece standard duplex, partial brass.

Catalog Numbers

PT7FSDBRA
PT7FSDBLA
PT7FSDGYA
PT7FSDIA
PT7FSDBRS2A
PT7FSDBRS3A



PT7FSDBRS2A

ScrubShield Flush Isolated Ground Series

Description

Isolated ground, painted aluminum, gray.
Isolated ground, painted aluminum, ivory.
Isolated ground, all brass.

Catalog Numbers

PT7IGFSDGYA
PT7IGFSDIA
PT7IGFSDBRSA

FURNITURE FEED


Two Piece Units - Low Voltage

Description

Service fitting- painted aluminum flange, brass.
Service fitting- painted aluminum flange, gray.
Service fitting- painted aluminum flange, black.

Catalog Numbers

FF2BRS
FF2GY
FF2BK



FF2BRS

FF2BK

Through-Floor Fitting - Low Voltage

Description

Single service fitting for FF2 series service fittings.

Catalog Number

PT2FIT

Single Service and Three Service

Description

Single service, one piece units, gray.
Single service, one piece units, ivory.
Three service, one piece units, gray.
Three service, one piece units, ivory.

Catalog Number

PT7FFSDGY
PT7FFSDI
PT73FFSDGY
PT73FFSDI



PT2FIT

PT7FFSDGY

PT73FFSDGY

PEDESTAL SERIES

Pedestal Housing

Description

Includes cast aluminum frame, fiber barrier, and brushed aluminum housing.

Catalog Numbers

FR80AL

Face Plates

Description

Blank.
Duplex receptacle opening.
Style Line® opening.
Single receptacle opening.
Aluminum - furniture feed.
Aluminum - blank.
Voice/data.

Catalog Numbers

SS309B
SS309D
SS309DS
SS309S
SS309SF
SS309BF
SS309T



FR80AL



SS309B

SS309D

SS309DS

SS309S

SS309SF

SS309BF

SS309T

Through Floor Fitting

(Each FR80AL series pedestal requires a PT7XC through-floor fitting.)

Description

Each FR80AL series pedestal requires a PT7XC through-floor fitting.

Catalog Numbers

PT7XC



PT7XC



Flush, Furniture and Pedestal Series

Hubbell continues to offer significant installation improvements to its line of fire-rated poke-through fittings. This "step-down" feature allows Hubbell flush poke-through fittings to be completely wired with flexible conduit and installed from above the floor. Two internal "spurs", which are fastened onto the fitting, secure it in a cored hole when the unit is pushed down into the cored hole. These spurs may also be removed, thereby providing easy removal and reuse of the poke-through fitting. All Hubbell flush fire-rated poke-through fittings now incorporate this new installation feature.

Hubbell offers a complete line of fire-rated poke-throughs for furniture feed applications. The 3-service flush series is designed to deliver power and voice/data cabling to feed furniture systems. Single-service models are available. For large capacity low voltage applications, a version is available to feed either 1 1/4" or 2" conduit connectors. All versions feature a painted aluminum flush fitting that provides a durable, attractive appearance. Hubbell has a complete line of pedestal series fire-rated poke-throughs. The 2 gang pedestal features a traditional brushed aluminum.

Hubbell Delivers Maximum Power and Communication Capacity



POWER POLES

Description

Two 20A 125V duplex receptacles, one circuit 10' 2", gray.

Two 20A 125V duplex receptacles, one circuit 12' 2", gray.

Two 20A 125V duplex receptacles, one circuit 15' 2", gray.

One orange IG, 20A 125V duplex receptacle and one 20A 125V duplex receptacle, two circuits, 10' 2" gray.

Two Orange IG, 20A 125V Duplex Receptacle and One IG surge suppression 20A 125V duplex receptacle, two circuits, 10' 2" gray.

Blank, divider, four device knockouts.

Note: *Also available in Ivory. Add I to the end of the catalog number.

Catalog Numbers

HBLPP10A*

HBLPP12A*

HBLPP15A*

HBLPP10IGA*

HBLPP10SA*

HBLPP0A*



POLYTRAK® NON-METALLIC RACEWAY

Trak Series	PT1	PP1	PL1	PW2	PB3	PS3
Base and Cover, 5'	PT1BC5	PP1BC5	PL1BC5	PW2BC5	PB3BC5	PS3BC5
Base and Cover, 5' w/adhesive	PT1ABC5	PP1ABC5	PL1ABC5	PW2ABC5	—	—
Base and Cover, 7'	PT1BC7	PP1BC7	PL1BC7	PW2BC7	—	—
Base and Cover, 7' w/adhesive	PT1ABC7	PP1ABC7	PL1ABC7	PW2ABC7	—	—
Base and Cover, 10'	—	—	—	—	PB3BC10	PS3BC10

FITTINGS

Flat Elbow	PT1FE	PP1FE	PL1FE	PW2FE	PB3FE	PS3FE
Flat Elbow*	—	PP1FEBC	PL1FEBC	PW2FEBC	PB3FEBC	PS3FEBC
Internal Elbow	PT1IE	PP1IE	PL1IE	PW2IE	PB3IE	PS3IE
Internal Elbow*	—	PP1IEBC	PL1IEBC	PW2IEBC	PB3IEBC	PS3IEBC
External Elbow	PT1EE	PP1EE	PL1EE	PW2EE	PB3EE	PS3EE
External Elbow*	—	PP1EEBC	PL1EEBC	PW2EEBC	PB3EEBC	PS3EEBC
Tee Cover	PT1TC	PP1TC	PL1TC	PW2TC	—	—
Tee Cover*	—	PP1TCBC	PL1TCBC	PW2TCBC	PB3TCBC	PS3TCBC
Splice Cover	PT1SC	PP1SC	PL1SC	PW2SC	PB3SC	PS3SC
End Cap	PT1EC	PP1EC	PL1EC	PW2EC	PB3EC	PS3EC
Conduit Adapter/ Ceiling Fitting	PT12CA	PLP1CACF	PLP1CACF	PW2CACF	PB3CACF	PS3CACF
Surface Panel Connector	—	—	—	—	PB3SPC	PS3SPC

* Indicate base and cover

BOXES

Inline, 1-Gang	—	—	—	—	PB3IND	—
Inline, 2-Gang	—	—	—	—	PB3IND2G	—
Inline, 3-Gang	—	—	—	—	—	PS3IND
Raised Inline, 1-G	—	—	—	—	PB3FCIB	PS3FCIB
Raised Inline, 2-G	—	—	—	—	PB3FCIB2G	PS3FCIB2G
Raised Inline, 3-G	—	—	—	—	PB3FCIB3G	PS3FCIB3G
Low Profile, 1-G	PT12LPB	PDB12LP	PDB12LP	PDB12LP*	—	—
Std. Profile, 1-G	PT12SBA	PDB12S	PDB12S	PDB12S*	—	—
Deep Profile, 1-G	PT12DBA	PDB12D	PDB12D	PDB12D*	—	—
Deep Divided, 2-G	—	PDB12TGD	PDB12TGD	PDB12TGD*	—	—
Deep, 2-Gang	PT12TGB	PDB12TGLV	PDB12TLV	PDB12TLV*	—	—

Note: * To separate power and data/communication use refer to full catalog page O-8.

Network Wiring

Modular Jacks



Description

Category 5e, black.

Category 6, black.

USOC 6-position.

Catalog Number

HBL5EBK*

HBL6BK*

HBLUBK*

* Available in additional colors. To order replace BK Suffix with the following: Blue (B), Electric Ivory (EI), Gray (GY), Green (GN), Office white (OW), Orange (OR), Red (R), Telco Ivory (TI), White (W) and Yellow (Y).



Multimedia Snap-In Connectors



Description

RCA 110 punch down connector, black housing, red insulator.

S-Video 110 punch down.

F-Type coupler bulkhead F/F, office white.

SC simplex adapter, office white housing, blue insulator.

Catalog Numbers

SIRCAOW*

SISVOW

SIFOW**

SIFSCOW

* Insulator available in additional colors. To order replace OW suffix with the following: white (W) and yellow (Y).

** Available in additional colors. To order replace OW suffix with the following: gray (GY), ivory (I) and white (W).

Wiring Devices

Receptacles - Straight Blade Duplex



Description

Heavy duty, 15A/125V

Heavy duty, 20A/125V

Construction series

15A/125V

20A/125V

Commercial series

15A/125V

20A/125V

Catalog Numbers

HBL5262*

HBL5362*

CR5262**

CR5362**

CR15**

CR20**

To Choose color add corresponding letter after catalog number.

Brown (no letter), ivory (I), gray (GY), red (R), white (W), office white (OW) or black (BK).

*Not available in office white.

**Not available in red.



Wiring Device-Kellems