

18

**NORSKE™**

**PRODUCT  
CATALOGUE**



[www.norskertools.com](http://www.norskertools.com)

MARCH 2018



**LEGENDARY  
PERFORMANCE™**



## TABLE OF CONTENTS

### CUTTING

SAW BLADES   TRADE	3
SAW BLADES   PROFESSIONAL	4
SAW BLADES   INDUSTRIAL	8
RECIPROCATING SAW BLADES   INDUSTRIAL	9
ABRASIVES   PROFESSIONAL	12
DIAMOND CUT OFF WHEELS   PROFESSIONAL	14
DIAMOND BLADES   PROFESSIONAL	15
LAMINATE FLOORING CUTTER   PROFESSIONAL	16

### DRILLING

DIAMOND HOLE SAWS   TRADE	17
DIAMOND HD HOLE SAWS   INDUSTRIAL	17
M42 BI-METAL HOLE SAWS   INDUSTRIAL	18
BI-METAL HOLE SAW KIT   PROFESSIONAL	19
HOLE SAW MANDRELS   INDUSTRIAL	19

### OSCILLATING

UNI-FIT OSCILLATING ACCESSORIES   PROFESSIONAL	20
STARLOCK OSCILLATING ACCESSORIES   INDUSTRIAL	21

### DRIVING

IMPACT TORSION BITS   INDUSTRIAL	22
ULTRAMAX IMPACT TORSION BITS   INDUSTRIAL	31
IMPACT BIT SETS	32
IMPACT TORSION BIT CLIPS   INDUSTRIAL	35
POCKET SCREWDRIVER   PROFESSIONAL	35

## SAW BLADES TRADE SERIES

Norske's line of entry level saw blades feature an Ultra-Thin Kerf design requiring less horsepower and reduced stock loss. These fast and durable light duty blades are perfect for general purpose framing and fine finish woodworking.

### THIN KERF | FRAMING

- General purpose framing blade provides clean and quick rip and cross-cuts in dimensional lumber
- C3 micro-grain carbide keeps the cutting edge sharper for longer periods of time
- Hardened tool steel alloy body to ensure straight, accurate cuts
- ATB tooth grind with 15 degree hook angle

ITEM	DIAMETER	TEETH	ARBOR	UPC
NCSBT005	5-3/8"	30	5/8"   10 mm Bushing	628204600057
NCSBT011	7-1/4"	24	5/8"   DKO	628204600118
NCSBT023	10"	28	5/8"	628204600231



### THIN KERF | FINISHING

- Fine finish woodworking blade provides clean, quick and accurate cross-cuts
- C3 micro-grain carbide keeps the cutting edge sharper for longer periods of time
- Hardened steel alloy body to ensure straight, accurate cuts
- ATB tooth grind with 10 – 15 degree hook angle

ITEM	DIAMETER	TEETH	ARBOR	UPC
NCSBT008	6-1/2"	40	5/8"   DKO	628204600088
NCSBT014	7-1/4"	60	5/8"   DKO	628204600149
NCSBT026	10"	60	5/8"	628204600262
NCSBT029	12"	80	1"	628204600293



## SAW BLADES PROFESSIONAL

Norske's line of professional full kerf saw blades are designed to meet the rigorous needs of professional users. Available for a variety of cutting applications, Norske™ professional blades feature high-grade carbide tips and premium hardened steel plates guaranteed to deliver superior results.

### MITER WOOD

- Fine wood finishing blades designed for all miter, sliding compound miter and radial arm saws
- Thick C4 micro-grain carbide tips precision sharpened on all sides
- Laser-cut body, anti-vibration and expansion slots
- Special ATAF (Alternating Tooth / Alternating Face) tooth grind
- Provides ultra-smooth cutting
- For professional cabinet makers and trim carpenters

ITEM	DIAMETER	TEETH	ARBOR	UPC
NCSBP246	10"	80	5/8"	628204602464
NCSBP247	12"	80	1"	628204602471



### MITER ALUMINUM

- For use on all miter, sliding compound miter and radial arm saws
- Designed to cut non-ferrous metals such as aluminum, brass, copper as well as plastics
- Triple chip grind with 0° hook angle eliminates blowout and kickback
- C6 micro-grain carbide tips precision sharpened on all sides
- Laser-cut body, anti-vibration and expansion slots reduce noise and vibration during operation
- Thin plate / thin kerf design

ITEM	DIAMETER	TEETH	ARBOR	UPC
NCSBP253	7-1/4"	60	5/8"   DKO	628204602532
NCSBP255	8-1/4"	60	5/8"   DKO	628204602556
NCSBP257	10"	100	5/8"	628204602570
NCSBP259	12"	100	1"	628204602594



## SAW BLADES PROFESSIONAL

### METAL CUTTING

- Specially engineered for high performance cutting of Steel Roofing, Metal Siding, Steel Pipe, Steel Studs and more
- 0° Hook angle reduces overfeeding, jamming, tooth breakage and kickback
- Modified Triple Chip Grind (MTCG) allows for easier cutting
- C6 micro-grain carbide tips

ITEM	DIAMETER	TEETH	ARBOR	UPC
NCSBP208	5-3/8"	50	5/8" + 10mm & 1/2" Bushings	628204602082
NCSBP209	5-3/8"	50	20 mm	628204602099
NCSBP210	6-1/2"	48	5/8"   DKO	628204602105
NCSBP212	7-1/4"	48	5/8"   DKO	628204602129
NCSBP214	8"	48	5/8"	628204602143
NCSBP216	10"	72	5/8"	628204602167
NCSBP218*	12"	80	1"	628204602181
NCSBP220*	14"	80	1"	628204602204

\*LOW RPM SAWS ONLY!



### MELAMINE PLUS

- The ULTIMATE finishing blade; features special 35° High ATB tooth design for ultra-smooth cutting of melamine, laminates, hardwoods and laminate flooring
- C4 Micro-grain carbide tips precision sharpened on all sides
- Laser-cut body, anti-vibration and expansion slots reduce noise and vibration during operation
- For professional cabinet makers, trim carpenters and avid Do-It-Yourselfers

ITEM	DIAMETER	TEETH	ARBOR	UPC
NCSBP271	7-1/4"	40	5/8"   DKO	628204602716
NCSBP272	8-1/4"	60	5/8"   DKO	628204602723
NCSBP273	10"	80	5/8"	628204602730
NCSBP274	12"	100	1"	628204602747





## SAW BLADES PROFESSIONAL

### SOCK-TOOTH

- Advanced sock-tooth technology allows carbide tips to withstand extreme impact while maintaining maximum tooth support
- Precision ground C3 micro-carbide tips provide a super fine cutting edge
- Aggressive 25° Hook Angle\* for faster cutting
- Fully hardened high grade tool steel body for superior performance in heavy load applications
- Anti-kickback\* tooth design eliminates grabbing and jamming

ITEM	DIAMETER	TEETH	ARBOR	UPC
NCSBS401	5-3/8"	24	5/8" + 10mm & 1/2" Bushings	628204604017
NCSBS405	6-1/2"	24	5/8"   DKO	628204604055
NCSBS409	7-1/4"	24	5/8"   DKO	628204604093
NCSBS413	7-1/4"	40	5/8"   DKO	628204604130
NCSBS417	8-1/4"	40	5/8"   DKO	628204604178
NCSBS419	10"	28	5/8"	628204604192
NCSBS421	10-1/4"	36	5/8"   DKO	628204604215
NCSBS425	10"	40	5/8"	628204604253
NCSBS429	10"	50	5/8"	628204604291
NCSBS431	12"	40	1"	628204604314
NCSBS433	12"	60	1"	628204604338

\*5-3/8" to 8-1/4" BLADES ONLY



### PCD | POLYCRYSTALLINE DIAMOND CARBIDE

- Specially designed for cutting HardiePlank®, Cemplank® and other fiber cement products
- Features abrasion-resistant polycrystalline diamond carbide for faster cutting and increased cutting life
- Extra-large gullet design improves material removal and minimizes dust
- Laser-cut body, anti-vibration and expansion slots reduce noise and vibration during operation
- For professional HardiePlank® installers

ITEM	DIAMETER	TEETH	ARBOR	UPC
NCSBP281	6-1/2"	4	5/8"   DKO	628204602815
NCSBP282	7-1/4"	4	5/8"   DKO	628204602822
NCSBP283	10"	6	5/8"	628204602839
NCSBP284	12"	8	1"	628204602846



## SAW BLADES PROFESSIONAL

### REVERSA™ CUT

- The ultimate framing blade complete with revolutionary **TWIN TOOTH** technology
- Radical Bi-directional tooth profile doubles the blades cutting life
- Specially designed for ripping & cross cutting dimensional lumber
- C3 micro-grain carbide tips precision sharpened on all sides (Top / Face / Sides) for more precise cuts and longer cutting life
- Manufactured from Japanese tool steel for true and straight cuts
- Laser cut plate & expansion slots

ITEM	DIAMETER	TEETH	ARBOR	UPC
NCSBP287	5-3/8"	24	5/8" + 10mm & 1/2" Bushings	628204602877
NCSBP288	6-1/2"	24	5/8"   DKO	628204602884
NCSBP290	7-1/4"	24	5/8"   DKO	628204602907
NCSBP293	8-1/4"	24	5/8"   DKO	628204602938
NCSBP295	10"	28	5/8"	628204602952
NCSBP297	12"	28	1"	628204602976



### REVERSA™ CUT | THIN KERF 10 PC PACK

- **NEW THIN KERF DESIGN** provides **ULTRA FAST CUTTING**
- The ultimate framing blade complete with revolutionary **TWIN TOOTH** technology
- Radical Bi-directional tooth profile doubles the blades cutting life
- Specially designed for ripping & cross cutting dimensional lumber
- C3 micro-grain carbide tips precision sharpened on all sides (Top / Face / Sides) for more precise cuts and longer cutting life
- Manufactured from Japanese tool steel for true and straight cuts
- Laser cut plate & expansion slots

ITEM	DIAMETER	TEETH	ARBOR	UPC
NCSBP290MP	7-1/4"	24	5/8"   DKO	628204602884
NCSBP290DBMP	7-1/4"	24	DIAMOND BORE	628204602976



**NEW**  
THIN KERF DESIGN

**10 PC PACK**



## SAW BLADES PROFESSIONAL

### COMPOSITE DECKING

- Specially designed to maximize cutting life in composite decking materials and cellular PVC
- Modified Triple Chip Grind (MTCG) tooth profile for clean, cool and "Melt Free" cutting
- Ultra-thin kerf design provides fast and clean cuts with minimal material removal
- Protec® Non-Stick Coating reduces drag and shields the blade against gumming, corrosion and heat
- 5 Degree hook angle for an ultra-clean cut

ITEM	DIAMETER	TEETH	ARBOR	UPC
NCSBP226	7-1/4"	48	5/8"   DKO	628204602266
NCSBP228	10"	64	5/8"	628204602280
NCSBP230	12"	72	1"	628204602303



## SAW BLADES INDUSTRIAL

### METAL CUTTING

- SK5 Japanese Tool Steel plates to maximize performance and reduce vibration
- C-6 Japanese Micro-Grain carbide specifically designed for metal cutting only
- Enhanced Tooth Geometry engineered to minimize friction and increase carbide life
- 0° Hook Angle for safe cutting performance without affecting blade performance
- Precision laser cut plate & expansion slots to withstand rotational and thermal stresses
- Coated plates to prevent rust or build up while reducing friction

ITEM	DIAMETER	TEETH	ARBOR	UPC
NCSBI552	6-1/2"	60	5/8"   DKO	628204602129
NCSBI554	7-1/4"	60	5/8"   DKO	628204602143
NCSBI558	10"	72	5/8"	628204602167
NCSBI560*	12"	80	1"	628204602181
NCSBI562*	14"	80	1"	628204602204

**NEW!**



\* LOW RPM SAWS ONLY!



## RECIPROCATING SAW BLADES INDUSTRIAL

### WOOD + METAL

- Variable teeth (milled and side set)
- For all types of wood with metal residues
- Made from industrial grade bi-metal steel
- Made in Germany

ITEM	LENGTH	TPI	UPC
NRBP200	8"	10/14	628204636001
NRBP201	12"	10/14	628204636018
NRBP202	6"	8/10	628204636025
NRBP203	8"	8/10	628204636032



### POWER CURVE | METAL

- Teeth milled and wavy set
- Aggressive blade design optimizes the blade's angle of attack for faster cutting
- Flexible all-round blade for steel and stainless steel
- Made from industrial grade bi-metal steel
- Made in Germany

ITEM	LENGTH	TPI	UPC
NRBP210	6"	18	628204636100
NRBP211	9"	18	628204636117
NRBP212	6"	14	628204636124
NRBP213	9"	14	628204636131



### DEMOLITION | WOOD

- Teeth milled and side set
- Special thick and robust blade for fast and straight cuts in wood with metal residue
- Especially for dismantling, rescue and salvage
- Made from industrial grade bi-metal steel
- Made in Germany

ITEM	LENGTH	TPI	UPC
NRBP220	6"	6	628204636209
NRBP221	9"	6	628204636216
NRBP222	12"	6	628204636223



## RECIPROCATING SAW BLADES INDUSTRIAL

### DEMOLITION | METAL

- Teeth milled and side set
- Special thick and robust blade for fast and straight cuts in steel thicker than 1/8"
- Especially for dismantling, rescue and salvage
- Made from industrial grade bi-metal steel
- Made in Germany

ITEM	LENGTH	TPI	UPC
NRBP223	6"	10	628204636230
NRBP224	9"	10	628204636247
NRBP225	12"	10	628204636254



### M-TOOTH | WOOD WITH NAILS

- Features patented "M-Tooth" design
- Robust teeth work forward and back stroke; recommended for steel over 1/16"
- Quick and precise cuts with above-average life
- Made from industrial grade bi-metal steel
- Made in Germany

ITEM	LENGTH	TPI	UPC
NRBP230	6"	8	628204636308
NRBP231	8"	8	628204636315
NRBP232	6"	5	628204636322
NRBP233	8"	5	628204636339
NRBP234	12"	5	628204636346
NRBP235 (Double Ended)	9"	5	628204636353



### CAST IRON + MASONRY

- Made with CARBIDE GRIT for long life
- High performance in cast steel pipe, cast iron and abrasive materials including ceramics, man-made stone, brick, marble, and more
- Uniformly applied, durable carbide grit particles on a flexible blade provide fast cuts without snagging or binding
- Made in Germany

ITEM	LENGTH	TPI	UPC
NRBP240	8"	CARBIDE	628204636407



## RECIPROCATING SAW BLADES INDUSTRIAL

### FIRE AND RESCUE | DEMOLITION

- Thick and robust blade for straighter cuts with less vibration and bending
- Aggressive blade design optimizes the blade's angle of attack for faster cutting
- Made from industrial grade bi-metal steel; HCS (High Carbon Steel) + MATRIX II HSS (High Speed Steel) for guaranteed performance

ITEM	LENGTH	TPI	UPC
NRBP245	6"	6	628204636452
NRBP247	9"	6	628204636476
NRBP249	12"	6	628204636490
NRBP251	6"	10	628204636513
NRBP253	9"	10	628204636537
NRBP255	12"	10	628204636551



### CARBIDE TIPPED | DEMOLITION

- Enhanced carbide tipped blade for maximum cutting performance and increased durability
- Engineered to withstand cutting highly abrasive materials such as: HardiePlank™, cement board, pressure treated lumber and fiberglass
- Aggressive 6 TPI tooth designed for faster demolition work
- Wider and thicker plate for straighter cuts with less vibration
- Laser welded tungsten carbide band for longer life

ITEM	LENGTH	TPI	UPC
NRBP260	6"	6	628204636605
NRBP262	9"	6	628204636629
NRBP264	12"	6	628204636643

**NEW!**



### PRUNING BLADE

- Specially designed for Pruning
- High Carbon Steel construction for optimal durability and sharpness
- Precision-ground cutting edge for ultimate cutting performance
- Large blade gullets between teeth provide fast chip removal
- Made in Germany

ITEM	LENGTH	TPI	UPC
NRBP241	12"	3	628204636414

**NEW!**



## ABRASIVES PROFESSIONAL

### THIN KERF - STAINLESS STEEL

- Clean, burr free-cutting of stainless steel and metal
- Thin Kerf design to cut cool and fast
- High performance aluminum-oxide grain for long life and quick material removal
- Built with woven fiberglass for increased durability and safer operation

ITEM	DIA.	THICK.	ARBOR	TYPE	UPC
NAP200	4"	0.050"	5/8"	1	628204639002
NAP201	4-1/2"	0.050"	7/8"	1	628204639019
NAP202	5"	0.050"	7/8"	1	628204639026
NAP203	7"	0.060"	7/8"	1	628204639033
NAP204	7"	0.060"	5/8"	1	628204639040
NAP210	4"	0.050"	5/8"	27	628204639101
NAP211	4-1/2"	0.050"	7/8"	27	628204639118
NAP212	5"	0.050"	7/8"	27	628204639125
NAP213	7"	0.060"	7/8"	27	628204639132



### METAL CUTTING

- Clean, burr free-cutting of metal
- High performance aluminum-oxide grain provides extreme durability and quick material removal
- Built with woven fiberglass for increased durability and safer operation
- High grain concentration provides aggressive grinding action and smooth-running

ITEM	DIA.	THICK.	ARBOR	TYPE	UPC
NAP230	12"	1/8"	1"	1	628204639309
NAP232	14"	5/32"	1"	1	628204639323
NAP236	12"	1/8"	1"	1	628204639361
NAP238	14"	1/8"	1"	1	628204639385



### GRINDING WHEELS | STAINLESS STEEL + METAL

- Built for fast removal rates and long wheel life
- Manufactured with superior grade grains and reinforced for maximum operator safety and comfort
- Resists bending and twisting

ITEM	DIA.	THICK.	ARBOR	TYPE	UPC
NAP250	4-1/2"	1/4"	7/8"	27	628204639507
NAP251	5"	1/4"	7/8"	27	628204639514
NAP252	7"	1/4"	7/8"	27	628204639521



## ABRASIVES PROFESSIONAL

### CEREMAXX CUTTING + GRINDING

- Our STRONGEST discs – Manufactured with ceramic grain for ultimate performance
- Designed to CUT + GRIND stainless steel and metal
- Built for increased productivity and efficiency with maximum removal rates
- Cool cutting without thermal bluing resulting in less rework

ITEM	DIA.	THICK.	ARBOR	TYPE	UPC
NAP240	4-1/2"	1/8"	7/8"	27	628204639408
NAP241	5"	1/8"	7/8"	27	628204639415



### TAPER CUT

- Clean, burr free-cutting of stainless steel, non-ferrous and ferrous metals
- Revolutionary conical disc design – disc tapers towards the center reducing kick back
- Engineered to cut cool, fast and run free
- Reduced side friction for unhindered cutting
- **10 Piece Pack**

ITEM	DIA.	THICK.	ARBOR	TYPE	UPC
NAP220	4-1/2"	5/64"	7/8"	1	628204639200
NAP221	5"	5/64"	7/8"	1	628204639217



### ALL PURPOSE

- Specially formulated to cut stainless steel, metal and masonry
- Low-burr to burr-free edges
- Thin Kerf design to cut cool and fast
- No time-consuming disc changes required
- **10 Piece Pack**

ITEM	DIA.	THICK.	ARBOR	TYPE	UPC
NAP225	4-1/2"	3/64"	7/8"	1	628204639255
NAP226	5"	3/64"	7/8"	1	628204639262





## MEGA BITE DIAMOND CUT OFF WHEELS PROFESSIONAL

**ONE BLADE. ALL CUTS** - No blade changes required, leading to increased productivity and reduced downtime

- Advanced diamond technology provides extreme cutting in wood, tubular metals, non-ferrous metals, masonry products, tiles and PVC
- Heat-resistant vacuum brazed to deliver best-in-class performance and extreme blade life
- High grade diamond rim to reduce dust residue and odors versus bonded abrasives – unlike bonded abrasives they don't wear down!

ITEM	DIAMETER	ARBOR	UPC
NDBS334	4"	5/8"	628204610346
NDBS335	4-1/2"	7/8"	628204610353
NDBS338	7"	5/8"   DKO	628204610384



## DIAMOND BLADES PROFESSIONAL

Our Professional diamond blades are engineered to provide the perfect balance between wear, fracture and exposure in order to maximize cutting performance. Available in Turbo, Segmented and Continuous rim.

- Constructed from superior grade diamonds
- High performance bond matrix for faster cutting and extended blade life
- Premium quality steel core plate minimizes vibration

ITEM	DESCRIPTION	ARBOR	UPC
<b>Turbo Blades</b>			
NDBP203	4" Turbo	7/8" - 5/8"	628204609036
NDBP206	4 1/2" Turbo	7/8" - 5/8"	628204609067
NDBP209	5" Turbo	7/8" - 5/8"	628204609098
NDBP212	7" Turbo	5/8"   DKO	628204609128
NDBP215	10" Turbo	5/8"	628204609159
<b>Segmented Rim</b>			
NDBP224	4" Segmented	7/8" - 5/8"	628204609241
NDBP227	4 1/2" Segmented	7/8" - 5/8"	628204609272
NDBP230	5" Segmented	7/8" - 5/8"	628204609302
NDBP233	7" Segmented	5/8"   DKO	628204609333
NDBP236	10" Segmented	5/8"	628204609364
NDBP237	12" Segmented	1" - 20mm	628204609371
NDBP238	14" Segmented	1" - 20mm	628204609388
<b>Continuous Rim</b>			
NDBP244	4" Continuous	7/8" - 5/8"	628204609449
NDBP247	4 1/2" Continuous	7/8" - 5/8"	628204609470
NDBP250	5" Continuous	7/8" - 5/8"	628204609500
NDBP253	7" Continuous	5/8"   DKO	628204609531
NDBP256	10" Continuous	5/8"	628204609562
<b>Glass Cutting</b>			
NDBP263	7" Glass Cutting	5/8"   DKO	628204609630
NDBP264	10" Glass Cutting	5/8"	628204609647



## LAMINATE FLOORING CUTTER PROFESSIONAL

### 13" LAMINATE FLOORING CUTTER

- Cuts a variety of material, including laminate flooring, fiber cement board (Hardie Plank®, Cemplank®), engineered wood and vinyl siding up to 13" wide and 19/32" thick
- Compact and easy to use; produces clean, precision cuts with no splintering and smooth finish
- Sturdy high-quality steel and aluminum construction
- Extended handle for increased leverage
- Table miter gauge for angled cuts from 0° to 45°
- Includes 13" high speed steel blade
- **AVAILABLE IN USA ONLY**

ITEM	DESCRIPTION	UPC
NMAP001	13" Laminate Flooring Cutter	628204644013

**NEW!**



### 13" LAMINATE FLOORING CUTTER BLADE

- Manufactured from superior grade High Speed Steel for extended cutting life
- Produces clean, precision cuts with no splintering or chipping
- Bolts firmly in place to ensure straight and accurate cutting
- Fit's Norske NMAP001 13" laminate flooring cutter
- **AVAILABLE IN USA ONLY**

ITEM	DESCRIPTION	UPC
NMAP002	Replacement Blade for 13" Flooring Cutter	628204644020

**NEW!**



## DIAMOND HOLE SAWS TRADE

- Diamond electroplating process allows for high performance at high speeds
- For use with hand held drills
- Includes drilling template; allows for accurate positioning

ITEM	DIAMETER	SHANK	UPC
NDHST003	1/4" (6mm)	1/4" (Round Shank)	628204618038
NDHST008	3/8" (10mm)	1/4" (Round Shank)	628204618083
NDHST013	1/2" (12mm)	1/4" (Round Shank)	628204618137
NDHST018	3/4" (19mm)	1/4" (Round Shank)	628204618182
NDHST023	1" (24mm)	1/4" (Round Shank)	628204618236
NDHST028	1 1/4" (32mm)	1/4" (Round Shank)	628204618281
NDHST033	1 3/8" (35mm)	3/8" (Round Shank)	628204618335
NDHST038	1 1/2" (38mm)	3/8" (Round Shank)	628204618380
NDHST043	2" (50mm)	3/8" (Round Shank)	628204618434
NDHST048	2 1/2" (64mm)	1/2" (Round Shank)	628204618489
NDHST052	3 3/8" (85mm)	1/2" (Round Shank)	628204618526
NDHST054	3 5/8" (92mm)	1/2" (Round Shank)	628204618540
NDHST060	4 3/8" (110mm)	1/2" (Round Shank)	628204618601



## DIAMOND HD HOLE SAWS INDUSTRIAL

- Utilizes high grade diamonds and heat-resistant vacuum brazing to deliver best-in-class performance for extreme bit life
- Engineered to stand up to the hardest, most abrasive materials on the job site
- For drilling holes in abrasive materials including tile, stone, glass, brick, block, and cement backer board

ITEM	DIAMETER	SHANK	UPC
NDHSI103	1/4" (6mm)	1/4" (Hex Shank)	628204619035
NDHSI108	3/8" (10mm)	1/4" (Hex Shank)	628204619080
NDHSI113	1/2" (12mm)	1/4" (Hex Shank)	628204619134
NDHSI118	3/4" (19mm)	1/4" (Hex Shank)	628204619189
NDHSI123	1" (24mm)	1/4" (Hex Shank)	628204619233
NDHSI128	1 1/4" (32mm)	1/4" (Hex Shank)	628204619288
NDHSI133	1 3/8" (35mm)	1/4" (Hex Shank)	628204619332
NDHSI138	1 1/2" (38mm)	1/4" (Hex Shank)	628204619387



## M42 BI-METAL HOLE SAWS INDUSTRIAL

NORSKE™ Industrial Grade M42 Bi-Metal Hole Saws are specially constructed with 8% cobalt for increased wear resistance and added tooth strength. Guaranteed to outperform, outlast and outclass the competition.

- Enhanced 4/6 variable tooth geometry provides quick, clean cuts and easy chip removal
- Fleim ground tooth design for faster cutting
- Deep cut body allows for 1-7/8" cutting depth
- Thick, hardened backing plate prevents mandrel run out

ITEM	DESCRIPTION	UPC
NBHSI503	7/8"	628204615037
NBHSI505	1"	628204615051
NBHSI508	1 1/8"	628204615082
NBHSI511	1 1/4"	628204615112
NBHSI514	1 3/8"	628204615143
NBHSI517	1 1/2"	628204615174
NBHSI520	1 3/4"	628204615204
NBHSI523	1 7/8"	628204615235
NBHSI526	2"	628204615266
NBHSI529	2 1/8"	628204615297
NBHSI532	2 1/4"	628204615327
NBHSI535	2 3/8"	628204615358
NBHSI538	2 1/2"	628204615389
NBHSI541	2 3/4"	628204615419
NBHSI544	3"	628204615440
NBHSI547	3 1/8"	628204615471
NBHSI550	3 1/4"	628204615501
NBHSI553	3 1/2"	628204615532
NBHSI556	3 5/8"	628204615563
NBHSI559	3 3/4"	628204615594
NBHSI565	4"	628204615655
NBHSI568	4 1/8"	628204615686
NBHSI571	4 1/4"	628204615716
NBHSI574	4 1/2"	628204615747
NBHSI577	5"	628204615778
NBHSI579	5-1/2"	628204615792
NBHSI580	6"	628204615808
NBHSI581	6-1/4"	628204615815
NBHSI584	6-5/8"	628204615846
NBHSI588	7-7/8"	628204615884

# NEW!

# M42 COBALT

M42 HSS + 8% COBALT





## HOLE SAW MANDRELS INDUSTRIAL

- Quick-change mandrels feature double set screws with a recessed combination head
- Spring-loaded **Pozi-Lock** mandrels feature collars that automatically engage drive pins
- Complete with fully heat treated 1/4" split point pilot drill bit to provide faster material penetration & less walking

ITEM	DESCRIPTION	UPC
NBHSI650	Adapter	628204616508
NBHSI652	Extension Bar	628204616522
NBHSI654	Replacement Drill Bit (Short)	628204616546
NBHSI656	1/4" Hex Shank Mandrel	628204616560
NBHSI658	3/8" Hex Shank Mandrel	628204616584
NBHSI660	3/8" Spring-loaded Mandrel	628204616607
NBHSI662	7/16" Spring-loaded Mandrel	628204616621



## 13PC M3 BI-METAL HOLE SAW KIT PROFESSIONAL

- M3 Professional grade, Bi-Metal hole saws cut everything from wood and plastics to aluminum, steel, cast iron and stainless steel
- 4/6 TPI configuration allows for easy chip removal and faster, cleaner cuts
- Extra deep body allows for increased cutting depth
- 3/16" Heavy duty backing plate adds strength & stability and prevents mandrel run-out
- Set includes: 3/4", 7/8", 1", 1-1/8", 1-3/8", 1-1/2", 1-3/4", 2", 2-1/8", 2-1/2", 3" hole saws + 3/8" Quick Change Mandrel & 1/4" Hex Shank Mandrel

ITEM	DESCRIPTION	UPC
NBHSP490	13 PC M3 Bi-Metal Hole Saw Kit	628204614900



## OSCILLATING TOOL ACCESSORIES

### PROFESSIONAL

An extensive line of Oscillating Tool Accessories to **CUT, SCRAPE, SAND AND GRIND.**

- Featuring **UNI FIT** mounting system. Fits most major brands including...Bosch, Fein, Makita, Rockwell, Porter Cable, Black & Decker, Dewalt, Dremel and more
- Made from superior grade HCS + HSS for extended life in all applications while delivering extreme durability

## UNI-FIT



ITEM	DESCRIPTION	UPC
NOTP200	3/4" Wood flush cut blade	628204630009
NOTP201	1-1/4" Wood flush cut blade	628204630016
NOTP202	1-1/4" Japanese Tooth bi-metal blade	628204630023
NOTP203	1-1/4" Wood / metal flush cut blade (Titanium)	628204630030
NOTP204	1-1/4" Metal flush cut blade	628204630047
NOTP205	1-1/4" Carbide blade	628204630054
NOTP206	1-1/4" wood / metal flush cut blade, CURVED OTA	628204630061
NOTP207	1-1/4" Japanese Tooth bi-metal blade, CURVED OTA	628204630078
NOTP208	1-3/4" Wood / metal flush cut blade (Titanium)	628204630085
NOTP210	2-3/4" Wood flush cut blade	628204630108
NOTP211	2-3/4" Japanese Tooth bi-metal blade	628204630115
NOTP215	3-3/8" Flush cut blade wood with nail (Titanium)	628204630153
NOTP216	Quadruple edge blade	628204630160
NOTP229	Caulking scraper blade	628204630290
NOTP230	Flexible scraper blade	628204630306
NOTP231	Triangle carbide RASP	628204630313
NOTP232	Fast cut grout removal blade	628204630320
NOTP233	Multi-material blade	628204630337
NOTP234	Hook & loop pad	628204630344
NOTP235	Teardrop grout and mortar removal blade	628204630351
NOTP236	3-in-1 Cutting, Scraper and Rasping	628204630368
NOTP240	Sandpaper - wood (15 pack)	628204630405
<b>Oscillating Tool Accessory Sets</b>		
NOTP270	20pc Oscillating accessory set	628204630702
NOTP271	1 1/4" Wood flush cut blades (3/pack)	628204630719
NOTP272	1 1/4" Wood / metal flush cut blades (3/pack)	628204630726
NOTP273	1-1/4" Japanese Tooth bi-metal blade (3/pack)	628204630733
NOTP274	2-3/4" Japanese Tooth bi-metal blade (3/pack)	628204630740

## STARLOCK OSCILLATING TOOL ACCESSORIES INDUSTRIAL

Choose genuine **STARLOCK®** accessories for that “just right” solution for thousands of professional applications.

- Featuring STARLOCK® mounting system. Fits a variety of major brands including...Fein, Bosch, Makita, Milwaukee, Rockwell, Ridgid, Hitachi, Skil, Craftsman and more
- Made from superior grade materials for extended life in all applications while delivering job site durability
- Up to 35% faster work progress
- Made in Germany

ITEM	DESCRIPTION	UPC
<b>STARLOCK</b>		
NOTSL300	1-3/8" Wood with Nails	628204631006
NOTSL301	1-3/8" Japanese Tooth hardwood	628204631013
NOTSL302	3-3/8" Segmented wood	628204631020
NOTSL303	Circular HSS blade metal	628204631037
NOTSL304	3" Segmented diamond blade	628204631044
NOTSL330	Flexible scraper blade	628204631303
NOTSL331	Triangular carbide RASP	628204631310
NOTSL332	Backing sanding pad (2pc pack)	628204631327
NOTSL382	5pc pack sandpaper 60 Grit	628204631822
NOTSL384	5pc pack sandpaper 120 Grit	628204631846
NOTSL386	5pc pack sandpaper 180 Grit	628204631860
<b>STARLOCK PLUS</b>		
NOTSLP340	4" Segmented blade metal	628204631402
NOTSLP341	2-9/16" Wood with nails	628204631419
NOTSLP342	2-9/16" Japanese Tooth hardwood	628204631426
NOTSLP343	1-1/8" Wood & thin metal	628204631433
NOTSLP344	3-9/16" Carbide saw blade	628204631440
<b>STARLOCK MAX</b>		
NOTSLM365	1-1/4" Wood with nails	628204631655
NOTSLM366	1-5/8" Wood with nails	628204631662

**STARLOCK**

**STARLOCK PLUS**

**STARLOCK MAX**



## IMPACT TORSION BITS INDUSTRIAL

BULK

### SQUARE RECESS

- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary tool steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life
- CNC milled magnetic tips for supreme grip



IMPACT  
RATED



1/4" HEX  
SHANK



IMPACT  
RATED



1/4" HEX  
SHANK



NEW!

NEW!

NEW!

ITEM	DESCRIPTION	UPC
NIBBI003	1" #1 Square Recess	62820462203
NIBBI004	1" #2 Square Recess	628204622042
NIBBI005	1" #3 Square Recess	62820462205
NIBBI006	2" #1 Square Recess	628204622066
NIBBI007	2" #2 Square Recess	628204622073
NIBBI008	2" #3 Square Recess	628204622080
NIBBI009	2" #4 Square Recess	628204622097
NIBBI015	3-1/2" #1 Square Recess	628204622158
NIBBI016	3-1/2" #2 Square Recess	628204622165
NIBBI017	3-1/2" #3 Square Recess	628204622172
NIBBI040	6" #1 Square Recess	628204622400
NIBBI041	6" #2 Square Recess	628204622417
NIBBI042	6" #3 Square Recess	628204622424
NIBBI045	12" #1 Square Recess	628204622455
NIBBI046	12" #2 Square Recess	628204622462
NIBBI047	12" #3 Square Recess	628204622479
NIBBI049	2" #2 Square Recess Dimpler Bit	628204622493
NIBBI050	2" #2 Square Recess Magnetic Dimpler Impact Bit	628204622509

### SQUARE RECESS DECKING

- 3° Tip design offers a perfect fit with coated deck screws
- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary tool steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life

ITEM	DESCRIPTION	UPC
NIBBI012	2" #2 Square recess	628204622127
NIBBI021	3-1/2" #2 Square recess	628204622219

## IMPACT TORSION BITS INDUSTRIAL

BULK

### PHILLIPS

- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary tool steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life
- CNC milled magnetic tips for supreme grip

ITEM	DESCRIPTION	UPC
NIBBI052	1" #1 Phillips	628204622523
NIBBI053	1" #2 Phillips	628204622530
NIBBI054	1" #2 Phillips (Drywall)	628204622547
NIBBI055	1" #3 Phillips	628204622554
NIBBI058	2" #1 Phillips	628204622585
NIBBI059	2" #2 Phillips	628204622592
NIBBI060	2" #2 Phillips (Drywall)	628204622608
NIBBI061	2" #3 Phillips	628204622615
NIBBI068	3-1/2" #1 Phillips	628204622684
NIBBI069	3-1/2" #2 Phillips	628204622691
NIBBI070	3-1/2" #3 Phillips	628204622707
NIBBI076	6" #1 Phillips	628204622769
NIBBI077	6" #2 Phillips	628204622776
NIBBI078	6" #3 Phillips	628204622783
NIBBI085	12" #2 Phillips	628204622851
NIBBI090	1" #2 Phillips Dimpler Bit	628204622905
NIBBI093	2" #2 Phillips Dimpler Bit	628204622936
NIBBI095	2" #2 Phillips Drywall Dimpler Bit	628204622950

NEW!



### PHILLIPS SQUARE COMBO BIT

- **2-IN-1** - Combines Phillips and Square Recess in **ONE TIP!**
- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary tool steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life
- Better fit than standard Phillips or Square drive
- CNC milled magnetic tips for supreme grip

ITEM	DESCRIPTION	UPC
NIBBI190	1" Phillips Square Combo Impact Bit	628204623902
NIBBI192	2" Phillips Square Combo Impact Bit	628204623926

NEW!





## IMPACT TORSION BITS INDUSTRIAL

BULK

### TORX

- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary tool steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life
- CNC milled magnetic tips for supreme grip

ITEM	DESCRIPTION	UPC
NIBBI101	1" T10	628204623018
NIBBI102	1" T15	628204623025
NIBBI103	1" T20	628204623032
NIBBI104	1" T25	628204623049
NIBBI105	1" T30	628204623056
NIBBI106	1" T40	628204623063
NIBBI111	2" T10	628204623117
NIBBI112	2" T15	628204623124
NIBBI113	2" T20	628204623131
NIBBI114	2" T25	628204623148
NIBBI117	2" T27	628204623179
NIBBI115	2" T30	628204623155
NIBBI116	2" T40	628204623162
NIBBI121	3-1/2" T10	628204623216
NIBBI122	3-1/2" T15	628204623223
NIBBI123	3-1/2" T20	628204623230
NIBBI124	3-1/2" T25	628204623247
NIBBI125	3-1/2" T30	628204623254
NIBBI126	3-1/2" T40	628204623261
NIBBI131	6" T10	628204623315
NIBBI132	6" T15	628204623322
NIBBI133	6" T20	628204623339
NIBBI134	6" T25	628204623346
NIBBI135	6" T30	628204623353
NIBBI136	6" T40	628204623360
NIBBI143	12" T20	628204623438
NIBBI144	12" T25	628204623445



IMPACT  
RATED



1/4" HEX  
SHANK



## IMPACT TORSION BITS INDUSTRIAL

BULK

### SECURITY TORX

- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary tool steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life
- CNC milled magnetic tips for supreme grip

ITEM	DESCRIPTION	UPC
NIBBI151	2" T10 <b>Security</b>	628204623513
NIBBI152	2" T15 <b>Security</b>	628204623520
NIBBI153	2" T20 <b>Security</b>	628204623537
NIBBI154	2" T25 <b>Security</b>	628204623544
NIBBI155	2" T30 <b>Security</b>	628204623551
NIBBI156	2" T40 <b>Security</b>	628204623568



**IMPACT  
RATED**



**1/4" HEX  
SHANK**



### MODIFIED TORX | FOR GRK™ SCREWS

- Manufactured specifically to fit **GRK™** Star Drive Screws
- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary tool steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life
- CNC milled magnetic tips for supreme grip

ITEM	DESCRIPTION	UPC
NIBCI370	2 Pc (Carded) 2" Modified T10 Torx	628204625708
NIBCI371	2 Pc (Carded) 2" Modified T15 Torx	628204625715
NIBCI372	2 Pc (Carded) 2" Modified T20 Torx	628204625722
NIBCI373	2 Pc (Carded) 2" Modified T25 Torx	628204625739
NIBCI374	2 Pc (Carded) 2" Modified T30 Torx	628204625746
NIBCI375	2 Pc (Carded) 2" Modified T40 Torx	628204625753



**IMPACT  
RATED**



**1/4" HEX  
SHANK**



**GRK™**

## IMPACT TORSION BITS INDUSTRIAL

BULK

### HEX

- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary tool steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life
- CNC milled magnetic tips for supreme grip

ITEM	DESCRIPTION	UPC
NIBBI160	2" 1/8" Hex Impact Bit	628204623605
NIBBI161	2" 5/32" Hex Impact Bit	628204623612
NIBBI162	2" 3/16" Hex Impact Bit	628204623629
NIBBI163	2" 7/32" Hex Impact Bit	628204623636
NIBBI164	2" 1/4" Hex Impact Bit	628204623643
NIBBI165	2" 2.5mm Hex Impact Bit	628204623650
NIBBI166	2" 3mm Hex Impact Bit	628204623667
NIBBI167	2" 4mm Hex Impact Bit	628204623674
NIBBI168	2" 5mm Hex Impact Bit	628204623681
NIBBI169	2" 6mm Hex Impact Bit	628204623698



IMPACT  
RATED



1/4" HEX  
SHANK



### SLOTTED

- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary tool steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life
- CNC milled magnetic tips for supreme grip

ITEM	DESCRIPTION	UPC
NIBBI181	1" SL8-10	628204623810
NIBBI186	2" SL8-10	628204623865



IMPACT  
RATED



1/4" HEX  
SHANK



## IMPACT TORSION BITS INDUSTRIAL

BULK

### DOUBLE-ENDED BITS

- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary tool steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life
- CNC milled magnetic tips for supreme grip

ITEM	DESCRIPTION	UPC
NIBBI206	2-9/16" Double-ended #2 Square Recess + #2 Decking	628204624060
NIBBI201	2-9/16" Double-ended #2 Phillips	628204624015
NIBBI202	4" Double-ended #2 Phillips	628204624022
NIBBI203	6" Double-ended #2 Phillips	628204624039
NIBBI212	2-9/16" Double-ended T25	628204624121



### NUTSETTERS

- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary tool steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life
- Lobular design reduces stripping damage by driving the fastener on the sides instead of forcing the corners to turn
- Strong earth magnet provides exceptional holding strength

ITEM	DESCRIPTION	UPC
NIBBI220	2-9/16" x 1/4" Nutsetter	628204624206
NIBBI221	2-9/16" x 5/16" Nutsetter	628204624213
NIBBI222	2-9/16" x 3/8" Nutsetter	628204624220
NIBBI223	2-9/16" x 7/16" Nutsetter	628204624237
NIBBI224	2-9/16" x 1/2" Nutsetter	628204624244
NIBBI226	6" x 1/4" Nutsetter	628204624268
NIBBI227	6" x 5/16" Nutsetter	628204624275
NIBBI228	6" x 3/8" Nutsetter	628204624282
NIBBI229	6" x 7/16" Nutsetter	628204624299
NIBBI230	6" x 1/2" Nutsetter	628204624305



## IMPACT TORSION BITS INDUSTRIAL

BULK

### SOCKET ADAPTERS

- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life

ITEM	DESCRIPTION	UPC
NIBBI250	3" x 1/4" Socket adapter	628204624503
NIBBI251	3" x 3/8" Socket adapter	628204624510
NIBBI252	3" x 1/2" Socket adapter	628204624527



**IMPACT  
RATED**



1/4" HEX  
SHANK



### 2 PC CARDED TORSION BITS

- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life
- CNC milled magnetic tips for supreme grip

ITEM	DESCRIPTION	UPC
NIBCI316	2pcs of 2" #2 Square Recess	628204625166
NIBCI318	2pcs of 2" #2 Square Recess - Decking	628204625180
NIBCI320	2pcs of 2" #2 Phillips	628204625203
NIBCI358	2pcs of 2" T15 Torx	628204625586
NIBCI360	2pcs of 2" T25 Torx	628204625609
NIBCI380	2-9/16" Double-ended #2 Square Recess	628204625807
NIBCI381	2-9/16" Double-ended #2 Sq. Recess - Decking	628204625814



**IMPACT  
RATED**



1/4" HEX  
SHANK





## IMPACT TORSION BITS INDUSTRIAL

### TIC TAC CASES

- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life
- CNC milled magnetic tips for supreme grip

ITEM	DESCRIPTION	UPC
NIBPI660	1" #2 Phillips (20pcs)	628204628600
NIBPI661	1" T25 Torx (20pcs)	628204628617



**IMPACT  
RATED**



1/4" HEX  
SHANK



## BIT HOLDERS INDUSTRIAL

BULK

### MISCELLANEOUS BIT HOLDERS

- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary tool steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life

ITEM	DESCRIPTION	UPC
NIBBI235	3" Quick change magnetic bit holder	628204624350
NIBBI236	6" Quick change magnetic bit holder	628204624367
NIBBI255	12" Quick change magnetic bit holder	628204624558
NIBBI237	3" Magnetic bit holder	628204624374
NIBBI238	6" Magnetic bit holder	628204624381
NIBBI239	3" Magnetic stainless bit holder	628204624398
NIBBI242	3-3/16" Magnetic screw guide	628204624428
NIBBI244	2-5/8" Eye lag driver	628204624442



**IMPACT  
RATED**



1/4" HEX  
SHANK



## BIT HOLDERS INDUSTRIAL

BULK

### HEAVY DUTY MAGNETIC BIT & SCREW HOLDER

- Heavy duty ring magnet holds screw securely in place for easy and accurate fastening
- Retractable guide sleeve eliminates wobbling and slipping while driving screws
- Engineered to withstand high torque + heavy load applications
- Works with all 1" insert bits
- Stainless steel body - prevents rusting

ITEM	DESCRIPTION	UPC
NIBBI245	3" Magnetic Bit & Screw Holder	628204624459
NIBBI246	6" Magnetic Bit & Screw Holder	628204624466
NIBBI247	12" Magnetic Bit & Screw Holder	628204624473

**NEW!**  
**NEW!**



**IMPACT  
RATED**



**1/4" HEX  
SHANK**



### MAGNETIC FLOAT COLLAR SCREW HOLDER

- Floating magnetic collar holds screw firmly in place for easy and accurate fastening
- Innovatively designed FLEX TECH TORSION ZONE absorbs high torque stress and reduces bit fracture
- Proprietary tool steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life
- CNC milled magnetic tips for supreme grip

ITEM	DESCRIPTION	UPC
NIBBI256	Float Collar Magnetic Screw Holder No.2 SQ	628204624565
NIBBI257	Float Collar Magnetic Screw Holder No.2 PH	628204624572
NIBBI258	Float Collar Magnetic Screw Holder T25	628204624589

**NEW!**



**IMPACT  
RATED**



**1/4" HEX  
SHANK**



## IMPACT TORSION BITS INDUSTRIAL G2

CARDED

### ULTRAMAX™ IMPACT TORSION BITS

- **NEW AND IMPROVED!** --- OUR **SECOND GENERATION** LINE OF IMPACT TORSION BITS WITH UP TO **\*40X LONGER LIFE!**
- Advanced FLEX TECH 2.0 TORSION ZONE absorbs high torque stress and reduces bit fracture
- Proprietary steel and heat treat process for maximum strength and durability
- Hardened S2 modified impact resistant steel for extended bit life
- CNC milled magnetic tips for supreme grip
- Impact rated for **HEAVY DUTY USE**

ITEM	DESCRIPTION	QTY	UPC
NIBCI404	1" #2 Square Recess	2pc	628204626040
NIBCI406	2" #1 Square Recess	2pc	628204626064
NIBCI407	2" #2 Square Recess	2pc	628204626071
NIBCI408	2" #3 Square Recess	2pc	628204626088
NIBCI415	3-1/2" #1 Square Recess	1pc	628204626156
NIBCI416	3-1/2" #2 Square Recess	1pc	628204626163
NIBCI417	3-1/2" #3 Square Recess	1pc	628204626170
NIBCI440	6" #1 Square Recess	1pc	628204626408
NIBCI441	6" #2 Square Recess	1pc	628204626415
NIBCI442	6" #3 Square Recess	1pc	628204626422
NIBCI452	1" #1 Phillips	2pc	628204626521
NIBCI453	1" #2 Phillips	2pc	628204626538
NIBCI454	1" #2 Phillips (Drywall)	2pc	628204626545
NIBCI455	1" #3 Phillips	2pc	628204626552
NIBCI458	2" #1 Phillips	2pc	628204626583
NIBCI459	2" #2 Phillips	2pc	628204626590
NIBCI460	2" #2 Phillips (Drywall)	2pc	628204626606
NIBCI461	2" #3 Phillips	2pc	628204626613
NIBCI468	3-1/2" #1 Phillips	1pc	628204626682
NIBCI469	3-1/2" #2 Phillips	1pc	628204626699
NIBCI470	3-1/2" #3 Phillips	1pc	628204626705
NIBCI476	6" #1 Phillips	1pc	628204626767
NIBCI477	6" #2 Phillips	1pc	628204626774
NIBCI478	6" #3 Phillips	1pc	628204626781

**NEW!**



**ULTRAMAX**  
IMPACT  
TORSION

## IMPACT TORSION BITS INDUSTRIAL G2

CARDED

ITEM	DESCRIPTION	QTY	UPC
NIBCI511	2" T10	2pc	628204627115
NIBCI512	2" T15	2pc	628204627122
NIBCI513	2" T20	2pc	628204627139
NIBCI514	2" T25	2pc	628204627146
NIBCI515	2" T30	2pc	628204627153
NIBCI516	2" T40	2pc	628204627160
NIBCI560	2-9/16" x 1/4" Nutsetter	1pc	628204627603
NIBCI561	2-9/16" x 5/16" Nutsetter	1pc	628204627610
NIBCI562	2-9/16" x 3/8" Nutsetter	1pc	628204627627
NIBCI563	2-9/16" x 7/16" Nutsetter	1pc	628204627634
NIBCI564	2-9/16" x 1/2" Nutsetter	1pc	628204627641



## BIT SETS INDUSTRIAL G2

### 40 PC ULTRAMAX IMPACT TORSION BIT SET

- **NEW AND IMPROVED!** --- OUR **SECOND GENERATION** LINE OF IMPACT TORSION BITS WITH UP TO \*40X LONGER LIFE
- Advanced FLEX TECH 2.0 TORSION ZONE absorbs high torque stress and reduces bit fracture
- Proprietary steel and heat treat process for maximum strength and durability
- Hardened S2 modified impact resistant steel for extended bit life
- CNC milled magnetic tips for supreme grip
- Set Includes: **1" PH** 1, 2 (x2), 3 | **1" PR2** | **1" SQ** 1, 2 (x2), 3 | **1" TORX** T10, T15, T20, T25 (x2), T30, T40 | **2" PH** 1, 2 (x2), 3 | **2" SQ** 1, 2 (x2), 3 | **2" TORX** T10, T15, T20, T25, T30, T40 | **3-1/2" PH2** | **3-1/2" SQ2** | **3-1/2" TORX** T25  
**2" PH2 Float Collar** | **2" SQ2 Float Collar** | **2" x 1/4" Socket Adapter**  
**2" x 3/8" Socket Adapter** | **2-9/16" x 1/4" Nutsetter** | **2-9/16" x 5/16" Nutsetter**  
**2-7/8" x 1/4" Magnetic Bit Holder**

ITEM	DESCRIPTION	UPC
NIBPI708	40 PC IMPACT RATED Bit Set (G2)	628204629089

**NEW!**

**IMPACT RATED**

**1/4" HEX SHANK**



**UP TO 40X LONGER LIFE**

## BIT SETS

### 31 PC SCREWDRIVER BIT SET

- Proprietary steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Steel for extended bit life
- Durable 360° rotating belt clip storage case keeps bits secure and organized
- Set Includes: **4 - PH** 1, 2 (x2), 3 | **3 - SQ** 1, 2, 3 | **4 - SL** 3, 4, 5.5, 6.5  
**4 - HEX** - 1/8", 5/32", 3/16", 1/4" | **8 - TORX** T10, T15, T20 (x2), T25, T27, T30, T40  
**TORX TAMPER** TT10, 15, 20, 25, 27, 30, 40 | **1/4" Magnetic Bit Holder**

ITEM	DESCRIPTION	UPC
NIBPI701	31pc Bit Set (Black satin - NON IMPACT)	628204629010



### 32 PC IMPACT BIT SET

- Innovatively designed to absorb high torque stress and reduce bit fracture
- Proprietary steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life
- CNC milled magnetic tips for supreme grip
- Set Includes: **4 - PH** 1, 2 (x2), 3 | **4 - SQ** 1, 2 (x2), 3 | **4 - SL** 3, 4, 5.5, 6.5  
**6 - HEX** - 3/32", 1/8", 5/32", 3/16", 7/32", 1/4" | **6 - TORX** T15, T20, T25 (x2), T30, T40  
**TORX TAMPER** TT15, 20, 25 (x2), 30, 40 | **1/4" Socket Adapter**  
**1/4" Magnetic Quick Change Bit Holder**

ITEM	DESCRIPTION	UPC
NIBPI700	32 PC IMPACT RATED Bit Set	628204629003



UNIQUE  
360° ROTATING  
BELT CLIP DESIGN

### 23 PC IMPACT TORSION BIT SET

#### 1 X MAGNETIC BIT & SCREW HOLDER

- Heavy duty ring magnet holds screw securely in place for easy and accurate fastening
- Retractable guide sleeve eliminates wobbling and slipping while driving screws

#### 20 X 1" IMPACT TORSION BITS

- Precision engineered for maximum strength and durability
- Hardened S2 impact resistant steel core for extended bit life

ITEM	DESCRIPTION	UPC
NIBPI704	23pc Bit Set ( with 1" No.2 PH )	628204629041
NIBPI705	23pc Bit Set ( with 1" T25 )	628204629058
NIBPI706	23pc Bit Set ( with 1" No.2 SQ )	628204629065

NEW!



INCLUDES 10PC BIT CLIP AND CARABINER

## BIT SETS INDUSTRIAL

### 42 PC IMPACT TORSION BIT SET

- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary steel and heat treat process for maximum strength and durability
- Hardened S2 modified impact resistant steel for extended bit life
- CNC milled magnetic tips for supreme grip while reducing stripping
- Set includes: **1" PH** 1, 2 (x2), 3 | **1" PR** 2 | **1" SQ** 1, 2 (x3), 3 | **1" SL** 4, 6 | **1" TORX** T15, T20, T25 (x2) | **2" PH** 1, 2 (x3), 3 | **2" PR** 2 | **2" SQ** 1, 2 (x3) | **2" TORX** T15, T20 (x2), T25 (x2) | **2" SL** 6 | **3-1/2" PH** 2 | **3-1/2" PR** 2 | **3-1/2" SQ** 2 | **3-1/2" TORX** T25 | **Socket Adapter** 1/4", 3/8" | **2-5/8" Nutsetters** 1/4", 5/16", 3/8" | **1/4" Magnetic Quick Change Bit Holder**

ITEM	DESCRIPTION	UPC
NIBPI703	42 PC IMPACT RATED Bit Set (G1)	628204629034



### 52 PC IMPACT TORSION BIT SET

- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary steel and heat treat process for maximum strength and durability
- Hardened S2 modified impact resistant steel for extended bit life
- CNC milled magnetic tips for supreme grip while reducing stripping
- Set includes: **1" PH** 1, 2 (x3), 3 | **1" PR2** (2) | **1" SQ** 1, 2, 3 | **1" TORX** T10, T15, T20, T25 (2), T30, T40 | **2" PH2 Dimpler** | **2" SQ2 Dimpler** | **2-5/8" Nutsetters:** 1/4", 5/16", 3/8" | **2-5/8" x 1/4" Adapter** | **3-1/2" PH** 1, 2, 3 | **3-1/2" PR2** | **3-1/2" SQ2** | **3-1/2" TORX** T15, T20, T25 | **2-7/8" Heavy Duty Magnetic Bit + Screw Holder**
- Tic Tac Case: **1" PH2** (10), **1" PR2** (5), **1" T25** (5)

ITEM	DESCRIPTION	UPC
NIBPI707	52 PC IMPACT RATED Bit Set (G1)	628204629072

**NEW!**







## IMPACT TORSION BIT CLIPS INDUSTRIAL

- Innovatively designed **FLEX TECH TORSION ZONE** absorbs high torque stress and reduces bit fracture
- Proprietary steel and heat treat process for maximum strength and durability
- Hardened S2 Modified Impact Resistant Steel for extended bit life
- CNC milled magnetic tips for supreme grip



ITEM	DESCRIPTION	UPC
NIBPI600	1" 10pcs of No.2 PH Bit Clip	628204628006
NIBPI601	1" 10pcs of 2pcs of T10, 15, 20, 25, 30 Bit Clip	628204628013
NIBPI605	2" 10pcs of No.2 SQ (Black satin - NON-IMPACT)	628204628051
NIBPI606	2" 10pcs of No.2 SQ	628204628068
NIBPI607	2" 10pcs of No.2 SQ Decking	628204628075
NIBPI611	2" 10pcs of No.2 PH Bit Clip	628204628112
NIBPI612	2" Assorted (2pc PH 1, 4pcs of PH 2, 2pcs of PH3 & 2pcs PR2)	628204628129
NIBPI613	2" Assorted (PH1, 2, 2, 3, PR2, T10,T15,T20,T25 and T30) Bit Clip	628204628136
NIBPI614	2" Assorted Torx ( T10, T15, T20, T25 and T30)	628204628143
NIBPI615	2" Assorted Torx (5pcs of T20 and 5pcs of T25) Bit Clip	628204628150
NIBPI616	2" Assorted Torx Tamper (TT7, 8, 9, 10, 15, 20, 25, 27, 30, 40)	628204628167
NIBPI617	2" Assorted (SQ1, 2, 3, PH 1,2,3, PR2, T15, T20 and T25)	628204628174
NIBPI618	2" Assorted (1pc of SQ1, 3pcs of SQ2, 2pcs of SQ3, PH1, PH2, PH3 and PR2)	628204628181
NIBPI650	5pc nutsetter (1/4", 5/16", 3/8", 7/16" and 1/2")	628204628501



## 4-IN-1 POCKET SCREWDRIVER

- Four different bits in one tool - Includes 2 mini slot and 2 mini Phillips bits
- Heat-treated precision ground tips for greater strength
- Ideal for hobbyists, technicians, mechanics, jewelers, watchmakers and Do-It-Yourselfers
- Go anywhere you go! - Comes with capped ends and a perfect pocket clip

ITEM	DESCRIPTION	UPC
NIBPP700	4 in 1 Pen Screwdriver	628204649506



**NORSKE™**

[www.norsketools.com](http://www.norsketools.com)

**NORSKE TOOLS LTD**

Unit 101 19052 26 Ave

Surrey BC, V3Z 3V7

Fax: 1.888.875.5697

Toll Free: 1.855.566.7753