

NEBO®



featuring
CaseBrite™
PHONE CASE + POWERFUL LIGHT

NEBO®

TRUE UTILITY®
...IN YOUR POCKET®

NEBO®
Sports

WEATHERRITE®
SINCE 1941

Quarrow®

WINTER/SPRING
2016

TABLE OF CONTENTS

• **NEBO® Lights and Tools..... 1-46**

- BIG Larry™ - Power C·O·B LED Work Light 2-3
- CaseBrite™ - Phone Case + Powerful Light 4-5
- TWYST™Z - Work Light, Lantern & Flashlight 6-7
- NEW!** Larry™C - 170 Lumen C·O·B LED Work Light..... 8-9
- REDLINE® RC™ with MagDock 10-11
- Twin Pucks Task Light and Emergency Beacon 12-13
- LUMORE™ Dome Light & Flashlight..... 14-15

• **True Utility® Pocket Tools..... 47-61**

• **NEBO® Sports..... 62-66**

- Bike Lighting & Accessories 63-66

• **WeatherRite® Outdoor 67-71**

- Lanterns 69-71

• **Quarrow® Fishing Products 72-78**

- Fishing Kits 74
- Fishing Tools..... 75
- Fishing Lighting..... 76-78

• **Custom Printing & Engraving Program.....79**

• **FAQs • Lighting 101 • Definitions..... 80-83**

• **Price Sheet 84-85**

We love creating great, quality products for our customers! Don't forget, no one ships faster than NEBO®! And we always guarantee your total satisfaction as expressed in our NEBO® "Guaranteed Buyback Program" that you will find on the back of this catalog. Also on the back of this catalog you will find our newest NEBO® giveaways. Be sure to get these while they last!

We appreciate your business and the support and feedback you give our products.

Thanks and best wishes for your success!

THE NEBO® FAMILY
800-255-6061

**LIKE US...
FOLLOW US ONLINE...
WATCH OUR VIDEOS!**



NEBO®



NEW
FROM NEBO

NEBO® is one of the world's best-selling lines of innovative, consumer-friendly flashlights and tools. Ever-changing and never compromising, we create and see our products through every phase of development. From the conceptual drawings on the sketch pad all the way to the end consumer, we offer quality and customer service guarantees that are unmatched.

NEBO
the **BIG Larry**
POWER WORK LIGHT

POWER C-O-B LED WORK LIGHT

The BIG Larry™ knows how to light up a room! Equipped with new C-O-B LED technology, the BIG Larry™ outputs 400 lumens of intense light. Secondary light modes include Low (160 lumens) and the Emergency Red Flash mode. This intense red light is perfect for distress signaling or roadside emergencies. The anodized aluminum body and recessed LED housing ensures that the BIG Larry™ can handle any situation.

LIGHT

- High-power 400 lumen C-O-B LED work light
- High-power C-O-B LED emergency red flasher

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- Powerful magnetic base

OPERATION

- Top-positioned, ON/OFF button

BATTERIES

- Powered by 3 AA batteries (included)

AVAILABLE COLORS

- #6384 Black
- #6385 Silver
- #6413 Red
- #6382 Camo

THREE LIGHT MODES

HIGH:

400 Lumens

- 4.5 Hours
- 29 Meters

LOW:

160 Lumens

- 15 Hours
- 17 Meters

RED FLASH:

• 40 Hours




Top Positioned ON/OFF Button



Emergency Red Flasher



Anodized Aircraft-Grade Aluminum



Powerful Magnetic Base



NEBO
the **BIG Larry**
POWER WORK LIGHT

COUNTERTOP DISPLAY

#6306 Display

- Display holds 14 pieces (7 black & 7 gray); 2 in front for consumer testing, 12 additional pieces stored in the back as replenishments
- Each BIG Larry™ comes with a gift box.
- Product attaches securely to the display using the magnetic base

Display Dimensions

(H) 12" x (W) 5.5" x (D) 7.8125"

Gift Box Dimensions

(H) 7.5" x (W) 1.25" x (D) 1"



C-O-B (Chips on Board)

A new innovation in LED technology. C-O-B features smaller, easier clustered LED chips that are mounted directly to the circuit board. These LED chips work together as one lighting module. Because of the compact design, C-O-B outperforms traditional lighting by up to 50 times the light output per centimeter of light surface.

BIG LARRY™ SPECIFICATIONS

WEIGHT	0.45 lbs.	
LENGTH	7.4375"	
DIAMETER	1.125" (Head)	0.875" (Barrel)

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930365	6306	BIG Larry™ C-O-B LED Work Light	12.75	24.99	14 PIECES
645397930648	6382	BIG Larry™ C-O-B LED Work Light - Camo	12.75	24.99	7 PIECES
645397930686	6385	BIG Larry™ C-O-B LED Work Light - Silver	12.50	24.99	7 PIECES
645397930679	6384	BIG Larry™ C-O-B LED Work Light - Black	12.50	24.99	7 PIECES
645397930792	6413	BIG Larry™ C-O-B LED Work Light - Red	12.50	24.99	7 PIECES
645397930761	6393	BIG Larry™ Work Light Holster	2.50	4.99	7 PIECES

NEBO®

CaseBrite™
PHONE CASE + POWERFUL LIGHT

PHONE CASE + POWERFUL LIGHT

The NEBO® CaseBrite™ offers more than just protection for your mobile device. The CaseBrite™ features a high-power, 200 lumen C-O-B flashlight that is up to 12x brighter than a standard smart phone light. Designed specifically to not draw from your phone's battery, each CaseBrite™ is independently powered by an internal, rechargeable lithium-ion battery.

LIGHT

- High-power 200 lumen C-O-B LED

DESIGN

- Impact-resistant, non-slip rubber case
- Screen protection lip
- Fully dimmable
- Slim 15mm profile
- Battery life indicator
- Fits iPhone 6/6S & 6/6S Plus

OPERATION

- Rear-positioned, ON/OFF button

ACCESSORIES

- USB to Micro USB charging cable (included)

BATTERIES

- Internal, rechargeable lithium-ion battery (Recharge time - up to 3 hours)

AVAILABLE COLORS

-  #6347 / #6348 Black
-  #6386 / #6387 White

NEW!



*iPhone not included



Easy Reach ON/OFF Button



USB to Micro USB Cable Included



Easy Access to Buttons & Ports



Battery Life Indicator



NEBO®

CaseBrite™
PHONE CASE + POWERFUL LIGHT

COUNTERTOP DISPLAY

- Display holds 6 pieces (three 6/6S; three 6/6S Plus) 2 additional pieces are stored underneath as replenishments.

- Each CaseBrite™ comes with a gift box and instruction manual

#6349 Display Dimensions

(H) 12.5" x (W) 10" x (D) 9.25"

#6347/#6386 Box Dimensions (6/6S)

(H) 6.75" x (W) 4.375" x (D) 1"

#6348/#6387 Box Dimensions (6/6S Plus)

(H) 7.5" x (W) 4.375" x (D) 1"



THREE LIGHT MODES

- HIGH:** 200 Lumens • 3 Hours • 30 Meters
- LOW:** 20 Lumens • 24 Hours
- STROBE:** 200 Lumens • 7 Hours



C-O-B (Chips on Board)

A new innovation in LED technology. C-O-B features smaller, easier clustered LED chips that are mounted directly to the circuit board. These LED chips work together as one lighting module. Because of the compact design, C-O-B outperforms traditional lighting by up to 50 times the light output per centimeter of light surface.

CASEBRITE™ SPECIFICATIONS

WEIGHT	0.2 lbs.
DIMENSIONS	6/6S - (H) 5.5" x (W) 2.75" x (D) 0.6"
DIMENSIONS	6/6S Plus - (H) 6.3125" x (W) 3.125" x (D) 0.6"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930433	6347	CaseBrite™ iPhone 6/6S - Black	24.00	39.99	4 PIECES
645397930440	6348	CaseBrite™ iPhone 6/6S Plus - Black	24.00	39.99	4 PIECES
645397930693	6386	CaseBrite™ iPhone 6/6S - White	24.00	39.99	4 PIECES
645397930709	6387	CaseBrite™ iPhone 6/6S Plus - White	24.00	39.99	4 PIECES
645397930457	6349	CaseBrite™ Countertop Display	FREE with 12 piece order		1 PIECE

NEBO[®] TWYST™Z

WORK LIGHT, LANTERN & FLASHLIGHT

Introducing the newest member of the TWYST™ lineup...TWYST™Z! The TWYST™Z features the same C-O-B lighting options as the original TWYST™: a high-power work light, lantern and flashlight! The TWYST™Z now features a 4x adjustable zoom. A powerful magnetic base also provides convenient hands-free lighting. TWYST™Z...shaping light like never before!

LIGHT

- 75 Lumen C-O-B LED Work Light
- 200 Lumen C-O-B LED Lantern
- 200 Lumen Flashlight

DESIGN

- 4x adjustable zoom
- Enhanced C-O-B LED Technology
- Tactical edge
- Fully dimmable beam
- Anodized aircraft-grade aluminum; water and impact-resistant
- Powerful magnetic base

OPERATION

- Side-positioned ON/OFF button

BATTERIES

- Powered by 4 AAA batteries (included)

NEW!




Twist to reveal C-O-B LED



75 Lumen C-O-B Work Light



200 Lumen C-O-B Lantern



4x Adjustable Zoom



Powerful Magnetic Base

Actual Size



NEBO[®] TWYST™Z

COUNTERTOP DISPLAY

#6372 Display

- Display holds 5 pieces - 1 'Try Me' and 4 in gift boxes; 11 additional pieces are included as replenishments.
- Each TWYST™Z comes with a gift box
- Display allows product to be easily tested by consumers

Display Dimensions

(H) 8.5" x (W) 9.25" x (D) 7"

Gift Box Dimensions

(H) 6.5" x (W) 1.875" x (D) 1.875"



THREE LIGHT MODES

HIGH:	LOW:	HIGH:	LOW:	HIGH:	LOW:
75 Lumens	10 Lumens	200 Lumens	20 Lumens	200 Lumens	20 Lumens
• 10 Hours	• 26 Hours	• 2 Hours	• 16 Hours	• 2 Hours	• 20 Hours
• 11 Meters	• 4 Meters	• 13 Meters	• 4 Meters	• 107 Meters	• 34 Meters
WORK LIGHT - 120° Light Coverage		LANTERN - 360° Light Coverage		FLASHLIGHT	



C-O-B (Chips on Board)

A new innovation in LED technology. C-O-B features smaller, easier clustered LED chips that are mounted directly to the circuit board. These LED chips work together as one lighting module. Because of the compact design, C-O-B outperforms traditional lighting by up to 50 times the light output per centimeter of light surface.

TWYST™Z SPECIFICATIONS

	TWYST™Z SPECIFICATIONS	
WEIGHT	0.55 lbs.	
LENGTH	6.3125" (Compacted)	6.75" (Extended)
DIAMETER	1.75" (Head)	1" (Barrel)

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930563	6372	TWYST™Z Work Light, Lantern & Flashlight	16.50	29.99	16 PIECES

NEBO®

the *Larry*™

POWER C-O-B LED WORK LIGHT

The Larry™ and Lucy™ are now **BRIGHTER THAN EVER!** Now, equipped with new C-O-B LED technology, the Larry™C and Lucy™C output **170 lumens** of intense light. The rotating magnetic clip gives you convenient hands-free lighting by attaching to virtually anything. The reinforced plastic body design is water and impact-resistant, making this light basically indestructible.

LIGHT

- High-power 170 lumen C-O-B LED work light

DESIGN

- Water and impact-resistant
- Ergonomic non-slip grip
- 180° rotating magnetic clip
- Protective LED housing

OPERATION

- Top-positioned, ON/OFF button

BATTERIES

- Powered by 3 AAA batteries (included)

AVAILABLE COLORS

- #6350 Red
- #6351 Blue
- #6352 Gray
- #6353 Yellow
- #6354 Camo
- #6355 Pink

ONE LIGHT MODE

HIGH:


170 Lumens

- 5.6 Hours
- 20 Meters

NEW!



Top Positioned ON/OFF Button



Protective LED Housing



180° Rotating Magnetic Clip



Ergonomic Non-Slip Grip



NEBO®

the *Larry*™

COUNTERTOP
DISPLAY

#6327 Display

- Display holds 16 pieces (8 in front and 8 in back); 8 additional pieces are included as replenishments
- Each Larry™C comes with a gift box.
- Display colors are red, blue, black & yellow. Pink and camo are sold separately.
- Product attaches securely to the display using the magnetic clip

Display Dimensions

(H) 8.75" x (W) 6" x (D) 6"

Gift Box Dimensions

(H) 6.5" x (W) 1.5" x (D) 0.75"



C-O-B (Chips on Board)

A new innovation in LED technology. C-O-B features smaller, easier clustered LED chips that are mounted directly to the circuit board. These LED chips work together as one lighting module. Because of the compact design, C-O-B outperforms traditional lighting by up to 50 times the light output per centimeter of light surface.

LARRY™C / LUCY™C SPECIFICATIONS

WEIGHT	0.1870 lbs.
DIMENSIONS	(H) 6.375" x (W) 0.55" x (D) 1.25"
U.S. PATENT	8,628,210

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930402	6327	Larry™C C-O-B LED Work Light	4.95	8.99	24 PIECES
645397930464	6350	Larry™C C-O-B LED Work Light - Bulk Red	4.75	8.99	12 PIECES
645397930471	6351	Larry™C C-O-B LED Work Light - Bulk Blue	4.75	8.99	12 PIECES
645397930488	6352	Larry™C C-O-B LED Work Light - Bulk Gray	4.75	8.99	12 PIECES
645397930495	6353	Larry™C C-O-B LED Work Light - Bulk Yellow	4.75	8.99	12 PIECES
645397930501	6354	Larry™C C-O-B LED Work Light - Bulk Camo	4.95	8.99	12 PIECES
645397930518	6355	Lucy™C C-O-B LED Work Light - Bulk Pink	4.75	8.99	12 PIECES

NEBO®
REDLINE® RC
with MAGDOCK

RECHARGEABLE FLASHLIGHT

The newest rechargeable REDLINE® is the REDLINE® RC™ with MagDock. The MagDock is a magnetic charging station that docks and charges your REDLINE®. Small enough to fit in the palm of your hand, the REDLINE® RC™ with MagDock is fully equipped with all of the features that make the REDLINE® series so popular.

LIGHT

- High-power 320 lumen LED

DESIGN

- 4x adjustable zoom
- Anodized aircraft-grade aluminum; water and impact-resistant
- OC™ Technology
- Convex lens
- Signature Red Ring™
- Steel belt/pocket clip
- Ergonomic non-slip grip
- Magnetic base
- Protective LED housing
- Charging indicator light

OPERATION

- Side-positioned, ON/OFF button

ACCESSORIES

- USB to Micro USB cable included
- Lanyard included

BATTERIES

- Internal, rechargeable lithium-ion battery (Recharge time - up to 2 hours)



4x Adjustable Zoom



Lanyard Loop and Magnetic Base



USB to Micro USB Cable



MagDock Battery Indicator



NEW!

Actual Size



NEBO®
REDLINE® RC
with MAGDOCK

COUNTERTOP
DISPLAY

#6392 Display

- Display holds 5 pieces - 1 'Try Me' and 4 in gift boxes; 5 additional pieces are included as replenishments.
- Each REDLINE® RC™ comes with a gift box.
- Product attaches securely to the display using the magnetic base

Display Dimensions

(H) 11.125" x (W) 5.5" x (D) 7.75"

Gift Box Dimensions

(H) 4.2" x (W) 2.95" x (D) 2.35"



FOUR LIGHT MODES

HIGH

- 320 Lumens**
- 1 Hour
 - 110 Meters

MEDIUM

- 125 Lumens**
- 2 Hours
 - 70 Meters

LOW

- 32 Lumens**
- 9 Hours
 - 35 Meters

STROBE

- 320 Lumens**
- 2 Hours
 - 110 Meters

REDLINE® RC™ SPECIFICATIONS

WEIGHT	0.25 lbs.
LENGTH	3.5625" (Compacted) 3.875" (Extended)
DIAMETER	1.25"
MAGDOCK SIZE	(H) 0.375" x (W) 2.25" x (D) 2.125"
U.S. PATENT	8,628,210

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930754	6392	REDLINE® RC™ with MagDock	21.98	39.99	10 PIECES

NEBO® TWIN PUCKS

NEW!

TASK LIGHT & EMERGENCY BEACON

Twin Pucks features a task light and an emergency beacon all-in-one. Both lights attach magnetically to each other, but can also operate independently and are separately powered. The task light provides hands-free lighting in three different ways: 180° adjustable stand, hanging hole or the magnetic base. The emergency beacon also has a magnet in the back to adhere to metal surfaces.

LIGHT

- High-power 160 lumen C-O-B LED task light
- 8 red high-power LED emergency beacon

DESIGN


- Water and impact-resistant
- Hanging hole
- 180° adjustable stand
- Rubber grips
- Task light and emergency beacon connect magnetically

OPERATION


- Dual buttons for task light and emergency beacon

BATTERIES

- C-O-B LED powered by 3 AAA batteries (included)
- 8 red LEDs powered by 2 AAA batteries (included)



Hanging Hole



180° Adjustable Stand



Magnetic Attachment



Powerful Magnetic Base



Two pucks magnetically connect

NEBO® TWIN PUCKS COUNTERTOP DISPLAY

#6391 Display

- Display holds 4 pieces total; 8 additional pieces are included as replenishments
- Display allows product to be easily tested by consumers

Display Dimensions

(H) 12" x (W) 5.875" x (D) 10.125"

Clamshell Dimensions

(H) 8.25" x (W) 5" x (D) 0.875"



WHITE LIGHT THREE LIGHT MODES

- HIGH - 160 Lumens**
• 10 Hours / 24 Meters
- MEDIUM - 80 Lumens**
• 20 Hours / 16 Meters
- LOW - 10 Lumens**
• 48 Hours / 7 Meters

RED LIGHT FIVE LIGHT MODES

- ROTATE FLASH**
• 38 Hours / 1.6 KM
- 8 LEDs STEADY ON**
• 7.5 Hours / 1.6 KM
- 8 LEDs FLASH**
• 27 Hours / 1.6 KM
- 8 LEDs S.O.S.**
• 7.5 Hours / 1.6 KM
- 4 LEDs STEADY ON**
• 17.5 Hours / 1.6 KM



C-O-B (Chips on Board)

A new innovation in LED technology. C-O-B features smaller, easier clustered LED chips that are mounted directly to the circuit board. These LED chips work together as one lighting module. Because of the compact design, C-O-B outperforms traditional lighting by up to 50 times the light output per centimeter of light surface.

TWIN PUCKS SPECIFICATIONS

WEIGHT	0.46 lbs.
DIAMETER	3.36"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930747	6391	Twin Pucks Task Light & Emergency Beacon	11.50	19.99	12 PIECES

NEBO[®] LUMORE™

DOME LIGHT & FLASHLIGHT

Introducing the latest in ultimate versatile lighting...the LUMORE™. This brilliant clip light features a 25 lumen LED. Surrounding the LED is a dome, which doubles the features of the light output. The dome acts as a diffuser to create ambient light, while a small hole allows light to shine through for standard flashlight use. The LUMORE™ is available in 4 different dome color options: white, blue, red & green. The LUMORE™ is equipped with a flat base and a rotating clip to provide convenient hands-free lighting in two different ways.

LIGHT

- High-power 25 lumen LED

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- Carabiner clip
- Glow-in-the-dark button
- Diffuser dome

OPERATION

- Rear-positioned ON/OFF button

BATTERIES

- Powered by 3 LR44 batteries (included)

AVAILABLE COLORS



NEW!



Diffuser Dome



Glow-in-the-Dark Button



Rotating Carabiner Clip



THREE LIGHT MODES

HIGH:

25 Lumens

- 1 Hour
- 9 Meters

LOW:

10 Lumens

- 3.5 Hours
- 6 Meters

STROBE:

- 4.5 Hours
- 9 Meters

LUMORE™ SPECIFICATIONS

WEIGHT	0.2 lbs.
DIMENSIONS	(H) 3.625" x (W) 0.75"

NEBO[®] LUMORE™

COUNTERTOP DISPLAY

#6329 Display

- Display holds 48 pieces total; 32 pieces on display and 16 additional pieces stored inside
- Display has hooks to securely attach each product
- Display allows product to be easily tested by consumers

Display Dimensions

(H) 9" x (W) 6.5" x (D) 6.5"



UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930426	6329	LUMORE™ Dome Light and Flashlight	3.15	5.99	48 PIECES
645397930525	6357	LUMORE™ - Bulk White	2.98	5.99	12 PIECES
645397930532	6358	LUMORE™ - Bulk Red	2.98	5.99	12 PIECES
645397930549	6359	LUMORE™ - Bulk Blue	2.98	5.99	12 PIECES
645397930556	6360	LUMORE™ - Bulk Green	2.98	5.99	12 PIECES

NEBO® TWYST™

SHAPING LIGHT LIKE NEVER BEFORE

WORK LIGHT, LANTERN & FLASHLIGHT

A light that does it all...with a TWYST™! The TWYST™ features a high-power work light, lantern and flashlight all in one! The TWYST™ uses a revolutionary new C-O-B LED technology that allows the shaping of light into full 3D patterns, giving optimal, bright, uniform light exactly where it's needed. Retractable base stabilizers are positioned at the bottom of the flashlight to give added stability on uneven surfaces. A powerful magnetic base also provides convenient hands-free lighting.

LIGHT

- 110 Lumen C-O-B LED Work Light
- 250 Lumen C-O-B LED Lantern
- 3400 LUX LED Flashlight

DESIGN

- Enhanced C-O-B LED Technology
- Tactical edge
- Fully dimmable beam
- Anodized aircraft-grade aluminum; water and impact-resistant
- Retractable base stabilizers
- Powerful magnetic base

OPERATION

- Side-positioned ON/OFF button

BATTERIES

- Powered by 4 AA batteries (included)

AVAILABLE COLORS



TWYST™ Bezel Reveals C-O-B



110 Lumen C-O-B Work Light



250 Lumen C-O-B Lantern



Powerful Magnetic Base and Retractable Base Stabilizers



6x Adjustable Zoom



Anodized Aircraft-Grade Aluminum



Flex-Power™ 3, 6 or 9 AA Batteries



Glow-in-the-Dark ON/OFF Button



NEBO® SEVEN-Z™

770 LUMEN FLASHLIGHT

You asked; we delivered. The SEVEN-Z™ is the answer to the demands for a high-lumen flashlight...770 lumens to be exact. Featuring OC™ Technology and all-new, Flex-Power™ which allows the flashlight to be powered by 3, 6 or 9 AA batteries, depending on the user's preference.

LIGHT

- High-power 770 lumen (6500 LUX) LED flashlight

DESIGN

- Convex Lens
- OC™ Technology
- Heat sink design
- 6x adjustable beam
- Anodized aircraft-grade aluminum; water and impact-resistant
- Flex-Power™


OPERATION

- Rear-positioned, glow-in-the-dark ON/OFF button

BATTERIES

- Powered by Flex-Power™: 3, 6 or 9 AA batteries (9 AA batteries included)

AVAILABLE COLORS



THREE LIGHT MODES

HIGH:
110 Lumens
• 13.5 Hours
• 15 Meters

LOW:
10 Lumens
• 96 Hours
• 1.5 Meters

WORK LIGHT - 120° Light Coverage

HIGH:
250 Lumens
• 4 Hours
• 15 Meters

LOW:
25 Lumens
• 60 Hours
• 1.5 Meters

LANTERN - 360° Light Coverage

HIGH:
3400 LUX
• 4 Hours
• 233 Meters

LOW:
350 LUX
• 40 Hours
• 74 Meters

FLASHLIGHT

TWO LIGHT MODES

HIGH:
770 Lumens
6500 LUX
• 7 Hours
• 322 Meters

LOW:
220 Lumens
1600 LUX
• 25 Hours
• 160 Meters

9 AA BATTERIES

HIGH:
700 Lumens
5900 LUX
• 4.5 Hours
• 307 Meters

LOW:
200 Lumens
1450 LUX
• 23 Hours
• 152 Meters

6 AA BATTERIES

HIGH:
550 Lumens
4650 LUX
• 2.5 Hours
• 273 Meters

LOW:
130 Lumens
1150 LUX
• 13 Hours
• 136 Meters

3 AA BATTERIES



TWYST™ SPECIFICATIONS		
WEIGHT	0.85 lbs.	
LENGTH	7.5" (Compacted)	7.875" (Extended)
DIAMETER	2" (Head)	1.25" (Barrel)

Display Dimensions
(H) 10.3125" x (W) 9.25" x (D) 7.125"

Gift Tube Dimensions
(H) 8" x (W) 2.375"



The SEVEN-Z™ is fueled by FLEX-POWER™, technology that allows the flexibility to use different quantities of batteries for power the light. SEVEN-Z™ will function with 3 AA, 6 AA or with the optimal 9 AA batteries for full 770 lumens of power.

SEVEN-Z™ SPECIFICATIONS		
WEIGHT	1.25 lbs.	
LENGTH	8.8125" (Compacted)	9.625" (Extended)
DIAMETER	2" (Head)	1.5" (Barrel)

Display Dimensions
(H) 9.625" x (W) 11" x (D) 3.75"

Gift Box Dimensions
(H) 2.375" x (W) 11" x (D) 3.75"



UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930266	6296	TWYST™ Work Light, Lantern & Flashlight	27.50	49.99	10 PIECES
645397930419	6328	TWYST™ Black	27.50	49.99	10 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930242	6294	SEVEN-Z™ 770 Lumen Flashlight	36.00	69.99	6 PIECES
645397930808	6414	SEVEN-Z™ 770 Lumen Flashlight - Camo	36.75	69.99	6 PIECES

NEBO® WORKBRITE 2™

C-O-B LED WORK LIGHT

The WORKBRITE 2™ adapts to your work environment, making it the handiest of work lights. Equipped with a 200 lumen C-O-B LED work light, the WORKBRITE 2™ also features a 100 lumen flashlight and a rear, emergency red flasher LED. The WORKBRITE 2™ provides hands-free lighting in three different ways: a hanging hook, a 200° pivoting stand and a magnetic base. Whether you are under the hood, under the sink or just out in the dark, the WORKBRITE 2™ works great for any application. WORKBRITE 2™...It stands! It hooks! It sticks! It lights! It WORKS!

LIGHT

- High-power 100 lumen LED flashlight
- High-power 200 lumen C-O-B LED work light
- Emergency Red Flasher LED

DESIGN

- Water and impact-resistant
- Ergonomic, non-slip grip
- 200° pivoting stand
- Collapsible, hanging hook
- Powerful magnetic base

OPERATION

- Front-positioned, ON/OFF button
- Emergency Red Flasher LED is independently controlled; press light to activate

BATTERIES

- Powered by 3 AAA batteries (included)



Collapsible, Hanging Hook



Emergency Red Flasher LED



200° Pivoting Stand



Powerful Magnetic Base



Collapsible, Hanging Hook



Emergency Red Flasher LED



200° Pivoting Stand



16.5" USB to Micro USB Cable



Powerful Magnetic Base



NEBO® THE RECHARGEABLE WORKBRITE 2™

RECHARGEABLE WORK LIGHT

Never worry about replacing batteries again, with The Rechargeable WORKBRITE 2™. This work light is equipped with a 220 lumen C-O-B LED work light, a 120 lumen flashlight and a rear, emergency red flasher LED. The WORKBRITE 2™ provides hands-free lighting in three different ways: a hanging hook, a 200° pivoting stand and a magnetic base. Whether you are under the hood, under the sink or just out in the dark, the WORKBRITE 2™ works great for any application. WORKBRITE 2™...It stands! It hooks! It sticks! It lights! It recharges! It WORKS!

LIGHT

- High-power 120 lumen LED flashlight
- High-power 220 lumen C-O-B LED work light
- Emergency Red Flasher LED

DESIGN

- Fully rechargeable
- Water and impact-resistant
- Ergonomic, non-slip grip
- 200° pivoting stand
- Collapsible, hanging hook
- Powerful magnetic base

OPERATION

- Front-positioned, ON/OFF button
- Emergency Red Flasher LED is independently controlled; press light to activate

ACCESSORIES

- 16.5" USB to Micro USB cable included

BATTERIES

- Powered by 1 18650 Li-ion Rechargeable Battery

THREE LIGHT MODES

WORK LIGHT:

200 Lumens

- 3 Hours
- 20 Meters

FLASHLIGHT:

100 Lumens

- 8 Hours
- 47 Meters

RED FLASH:

• 200 Hours



Display Dimensions

(H) 12.75" x (W) 5.5" x (D) 7.75"

Gift Box Dimensions

(H) 8.5" x (W) 2" x (D) 1.5"



WORKBRITE 2™ SPECIFICATIONS

WEIGHT	0.35 lbs.
LENGTH	(H) 8.5" x (W) 2" x (D) 1.5"

THREE LIGHT MODES

WORK LIGHT:

220 Lumens

- 6 Hours
- 22 Meters

FLASHLIGHT:

120 Lumens

- 8 Hours
- 52 Meters

RED FLASH:

• 200 Hours



Display Dimensions

(H) 13.25" x (W) 5.5" x (D) 7.75"



RECHARGEABLE WORKBRITE 2™ SPECIFICATIONS

WEIGHT	0.35 lbs.
LENGTH	(H) 8.5" x (W) 2" x (D) 1.5"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930341	6304	WORKBRITE 2™ C-O-B LED Work Light	11.75	19.99	12 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930358	6305	The Rechargeable WORKBRITE 2™	16.50	29.99	12 PIECES

NEBO[®] SLYDE^Z

FLASHLIGHT & WORK LIGHT

The newest addition to the SLYDE™ family is the SLYDE™Z. Much like its predecessor, the Z features all of the 2-in-1 innovation as the original SLYDE™ with a few additions. What does "Z" mean?...ZOOM, the SLYDE™Z features a 4x adjustable zoom. The Z also has a fully dimmable function for the flashlight and work light as well as an Instant ON feature that automatically activates the C-O-B work light when opened.

LIGHT

- High-power 4750 LUX LED flashlight
- High-power 250 lumen C-O-B work light

DESIGN

- Convex lens
- Tactical edge
- 4x adjustable zoom
- Anodized aircraft-grade aluminum; water and impact-resistant
- Dimmable beam
- Instant ON feature (work light)
- Work light is concealed inside the flashlight body; just SLYDE to reveal
- Powerful magnetic base

OPERATION

- Side-positioned ON/OFF button; hold to activate dimming
- C-O-B Work light turns ON when opened and OFF when closed

BATTERIES

- Powered by 4 AA batteries (included)



Tactical Edge & Convex Lens




4x Adjustable Zoom



Extendable Body Reveals C-O-B LED



Powerful Magnetic Base



Tactical Edge



Anodized Aircraft-Grade Aluminum



Extendable Body Reveals C-O-B LED



Powerful Magnetic Base



NEBO[®] SLYDE

FLASHLIGHT & WORK LIGHT

Combining the best that NEBO® has to offer, the SLYDE™ features a powerful LED flashlight and C-O-B work light all in one. At first glance, the SLYDE™ appears to be a simple, strong flashlight, emitting 250 lumens of intense white light...and it is! However, you will see the SLYDE™ is much more. The body of the SLYDE™ conceals a powerful 190 lumen work light. To reveal the C-O-B work light, just SLYDE to open!

LIGHT

- High-power 250 lumen LED flashlight
- High-power 190 lumen C-O-B work light

DESIGN

- Tactical edge
- Anodized aircraft-grade aluminum; water and impact-resistant
- Work light is concealed inside the flashlight body; just SLYDE to reveal
- Powerful magnetic base

OPERATION

- Side-positioned ON/OFF button with Soft Touch Technology

BATTERIES

- Powered by 4 AAA batteries (included)

AVAILABLE COLORS

- #6156 Black
- #6383 Camo

TWO LIGHT MODES

Flashlight - 4750 LUX

- 2.5 Hours
- 276 Meters

Work Light - 250 Lumens

- 3.5 Hours
- 21 Meters



Display Dimensions
(H) 12.36" x (W) 9.09" x (D) 9.65"

Each SLYDE™Z includes a gift box and instruction manual.



SLYDE™Z SPECIFICATIONS

WEIGHT	1.09 lbs.	
LENGTH	7.75" (Compacted)	10.3125" (Extended)
DIAMETER	2.0625" (Head)	1.5" (Barrel)

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930112	6267	SLYDE™Z Flashlight & Work Light	28.50	49.99	8 PIECES

TWO LIGHT MODES

Flashlight - 250 Lumens

- 2 Hours
- 220 Meters

Work Light - 190 Lumens

- 3.5 Hours
- 18 Meters



SLYDE™ SPECIFICATIONS

WEIGHT	0.65 lbs.	
LENGTH	6.5" (Compacted)	9" (Extended)
DIAMETER	1.625" (Head)	1.3125" (Barrel)

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397929857	6156	SLYDE™ Flashlight & Work Light	16.75	29.99	16 PIECES
645397930662	6383	SLYDE™ Flashlight & Work Light - Bulk Camo	17.25	29.99	8 PIECES

Display Dimensions
(H) 14.125" x (W) 7.5625" x (D) 8"



NEBO® Larry SILVER

8 LED POCKET WORK LIGHT

The pocket light for professionals...the Larry Silver™ 8 LED Pocket Work Light is the essential handyman light. More durable metal body design and brighter 100 lumen output. You can't be handy if your hands aren't...well, handy. The rotating magnetic clip gives you convenient hands-free lighting by attaching to virtually anything.

LIGHT

- 8 high-power LEDs output 100 lumens
- Fully dimmable beam (100% - 10%)

DESIGN

- Durable zinc alloy; water and impact-resistant
- 180° rotating magnetic clip
- Protective LED channel

OPERATION

- Top-positioned ON/OFF button;
- hold to activate dimming

BATTERIES


- Powered by 3 AAA batteries (included)

DISPLAY


- Metal display holds 8 pieces magnetically;
- 8 additional pieces are stored magnetically on the back of the display



Top Positioned ON/OFF Button



180° Rotating Magnetic Clip



Protective LED Channel



Durable Zinc Alloy Design



Red Laser Pointer



180° Rotating Magnetic Clip



Ergonomic Non-Slip Grip



Separate Light & Laser Buttons



NEBO® Larry™

12 LED WORK LIGHT & LASER

Larry™2 has a few more LEDs under his belt and a red laser pointer that emits from the top of the light. Being the essential handyman light, the Larry™2 still has some of the features that made the Larry™ so great: the 180° rotating magnetic clip, reinforced plastic body design and ergonomic grip. The Larry™2 is perfect for endless applications and is still convenient enough to slip into your pocket. More features...more lumens...same Larry™ style!

LIGHT

- 12 high-power LEDs output 160 lumens

LASER

- Red laser (<5mW / 650nm)

DESIGN

- Water and impact resistant
- Ergonomic non-slip grip
- 180° rotating magnetic clip
- Protective LED housing

OPERATION

- Light: ON/OFF button
- Laser: ON/OFF button

BATTERIES

- Powered by 3 AAA batteries (included)

AVAILABLE COLORS

- #6051 Orange
- #6052 Gray
- #6053 Black
- #6054 Green
- #6055 Pink

TWO LIGHT MODES

HIGH

- 100 Lumens
- 3 Hours
- 33 Meters

LOW

- 10 Lumens
- 20 Hours

LARRY SILVER™ SPECIFICATIONS	
WEIGHT	0.25 lbs.
DIMENSIONS	(L) 6.375" x (W) 0.55" x (D) 1.25"
U.S. PATENT	8,628,210



Display Dimensions
(H) 8.75" x (W) 6" x (D) 6"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930068	6194	Larry Silver™ 8 LED Work Light	11.50	19.99	16 PIECES

TWO LIGHT MODES

Light - 160 Lumens

- 2 Hours
- 40 Meters

Laser - <5mW

- 72 Hours
- 412 Meters

LARRY™2 SPECIFICATIONS	
WEIGHT	0.2 lbs.
DIMENSIONS	(L) 6.75" x (W) 0.75" x (D) 1.5"
U.S. PATENT	8,414,142



Display Dimensions
(H) 6.25" x (W) 10.23" x (D) 5"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397929222	6006	Larry™2 12 LED Work Light	8.80	15.99	24 PIECES
645397929345	6051	Larry™2 Work Light - Bulk Orange	8.50	15.99	12 PIECES
645397929352	6052	Larry™2 Work Light - Bulk Gray	8.50	15.99	12 PIECES
645397929369	6053	Larry™2 Work Light - Bulk Black	8.50	15.99	12 PIECES
645397929376	6054	Larry™2 Work Light - Bulk Green	8.50	15.99	12 PIECES
645397929383	6055	Lucy™2 Work Light - Bulk Pink	8.50	15.99	12 PIECES

NEBO® PaL

RECHARGEABLE POWER & LIGHT

This portable, rechargeable flashlight serves as a backup power source for mobile phones and other rechargeable USB electronic devices. Ideal for travel, the PaL conveniently fits in your pocket, purse or briefcase.

LIGHT

- High-power 50 lumen LED

DESIGN

- Fully rechargeable
- Power bank for your USB powered devices
- Anodized aircraft-grade aluminum; impact-resistant
- USB & Micro USB charging ports
- Apple® & Android™ compatible
- Charging indicator tells charging status of flashlight and your USB powered devices

OPERATION

- Rear-positioned ON/OFF button with charging indicator

ACCESSORIES

- USB to Micro USB cable included

BATTERIES

- Powered by 1 internal 2600 mAh Lithium-Ion Battery (Type 18650)

AVAILABLE COLORS



USB & Micro USB Charging Ports



10" USB to Micro USB Cable Included



Apple® Compatible



Android™ Compatible



Anodized Aircraft-Grade Aluminum



Charging Indicator & Twist Dial



Base Fits any 12V Outlet



NEBO® TRANSPORT®

DC RECHARGEABLE LIGHT

The TRANSPORT® is a compact, rechargeable flashlight that provides powerful bright light at your fingertips! The TRANSPORT® is compatible with any DC 12V socket. Just plug directly into your car, truck, boat or any other 12V outlet. Ideal for travel, the TRANSPORT® conveniently fits in your pocket, purse or briefcase.

LIGHT

- High-power 125 lumen LED

DESIGN

- Fully rechargeable
- Fits any 12V outlet (car cigarette lighter)
- Anodized aircraft-grade aluminum; water and impact-resistant
- Charging indicator light

OPERATION

- Top-positioned ON/OFF dial; twist to activate

BATTERIES

- Powered by 1 16340 Lithium Ion rechargeable battery (included)

AVAILABLE COLORS



ONE LIGHT MODE

50 LUMENS

- 17.5 Hours
- 54 Meters



Display Dimensions
(H) 9" x (W) 6.25" x (D) 5.375"

Individual Box Dimensions
(H) 6.25" x (W) 2" x (D) 1.5"

PaL SPECIFICATIONS	
WEIGHT	0.17 lbs.
LENGTH	3.6875"
DIAMETER	0.875"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930099	6227	PaL Rechargeable Power and Light	11.75	19.99	18 PIECES

ONE LIGHT MODE

125 LUMENS

- 1 Hour
- 90 Meters



Display Dimensions
(H) 7.25" x (W) 7.625" x (D) 6.25"

TRANSPORT® SPECIFICATIONS	
WEIGHT	0.15 lbs.
LENGTH	3.6875"
DIAMETER	0.875"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930396	6311	TRANSPORT® DC Rechargeable Flashlight	11.50	19.99	18 PIECES



OPTIMIZED OPTICS FLASHLIGHT

The O² BEAM™, a breakthrough in achieving long-range, powerful brightness. This 8105 LUX LED flashlight, paired with our O² Technology™, makes the O² BEAM™ the most cost and energy efficient flashlight in its class, with performance that you have to see to believe! The O² Beam™ – Industry standard redefined.

LIGHT

- High-power 8105 LUX LED

DESIGN

- Tactical edge
- Convex lens
- Lo-Light™ self-powered, glow-light source
- 4x adjustable beam
- Anodized aircraft-grade aluminum; water and impact-resistant
- Smart Select Dial
- Battery indicator - button glows red when battery life reaches 20%

OPERATION


- Rear-positioned, glow-in-the-dark ON/OFF button with Smart Select Dial

ACCESSORIES

- Lanyard included
- Gift box and heavy duty carrying case

BATTERIES

- Powered by 4 AA batteries (included)



Lo-Light™ Self-Powered, Glow-Light Source



4x Adjustable Zoom



Lanyard Included



Smart Select Dial and Glow-in-the-Dark Button




Actual Size Comparison



6x Adjustable Zoom



Steel Belt/Pocket Clip



Glow-in-the-Dark Button and Magnetic Base



HIGH-POWER MICRO LIGHT

Don't let the micro size fool you...the Micro REDLINE® OC™ packs enough power to carry the REDLINE® name. This light is small enough to fit in the palm of your hand, but bright enough for any situation. Equipped with OC™ Technology the Micro has a perfectly dispersed beam of light while in flood mode. The Micro REDLINE® OC™...small never shined so big!

LIGHT

- High-power 360 LUX LED

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- OC™ Technology
- Convex lens
- Signature Red Ring™
- 6x adjustable beam
- Steel belt/pocket clip
- Magnetic base

OPERATION

- Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

BATTERIES

- Powered by 1 CR2 battery (included)

FIVE LIGHT MODES

HIGH

- 8105 LUX
- 4 Hours
- 360 Meters

MEDIUM

- 4230 LUX
- 10 Hours
- 260 Meters

LOW

- 1100 LUX
- 62 Hours
- 133 Meters

BEACON

- 8105 LUX
- 200 Hours
- 360 Meters

STROBE

- 8105 LUX
- 70 Hours
- 360 Meters



Display Dimensions

(H) 9.29" x (W) 10.82" x (D) 10.27"
Each O² BEAM™ includes a gift box, heavy duty carrying case, owner's guide and instruction manual.



OPTIMIZED OPTICS (O²)

The natural tendency of light is to disperse into infinite directions. We use optics to help us focus the light's intensity in one direction. The Optimized Optics bend the light closer toward the center of the beam. The result is a hotter, brighter spotlight with the lowest power consumption in its class.

O ² BEAM™ SPECIFICATIONS	
WEIGHT	1.05 lbs.
LENGTH	8.625"
DIAMETER	1.5" (Barrel) 2.25" (Head)
U.S. PATENT	D657,840 and other International Patents Pending

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397929185	6000	O ² BEAM™ 8105 LUX Flashlight	55.00	99.99	4 PIECES

FOUR LIGHT MODES

HIGH

- 360 LUX
- 3.5 Hours
- 76 Meters

MEDIUM

- 183 LUX
- 6 Hours
- 54 Meters

LOW

- 39 LUX
- 10 Hours
- 25 Meters

STROBE

- 360 LUX
- 7 Hours
- 76 Meters

*NOTE: Light resets to first light mode (HIGH) after being OFF for 20 seconds.



OPTIMIZED CLARITY

Eliminating inconsistencies in light, the OC™ (Optimized Clarity) Technology provides intense, clear, pristine light that is easy on the eyes. This technology allows the light beam to be as bright on the edge as it is in the center when used in flood mode.

Display Dimensions

(H) 8" x (W) 6" x (D) 3.875"



Micro REDLINE® OC™ SPECIFICATIONS	
WEIGHT	0.1 lbs.
LENGTH	2.625"
DIAMETER	0.875" (Head) 0.8125" (Barrel)
U.S. PATENT	659,869 S

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930167	6272	Micro REDLINE® OC™ Flashlight	7.90	14.99	16 PIECES

NEBO®
CLASSIC
REDLINE™

HIGH-POWER TACTICAL LIGHT

Another addition to the REDLINE® OC™ lineup is the Classic REDLINE® OC™. Maintaining some of the key features as it's predecessor, the Classic also features an intense power upgrade...2640 LUX to be exact.

LIGHT

- High-power 2640 LUX LED

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- OC™ Technology
- Convex lens
- Signature Red Ring™
- Tactical edge
- 6x adjustable beam
- Dual-direction belt/pocket clip
- Magnetic base

OPERATION

- Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

BATTERIES

- Powered by 3 AAA batteries (included)



Tactical Edge




6x Adjustable Zoom



Dual-Direction Belt/Pocket Clip



Glow-in-the-Dark Button and Magnetic Base



Stealth Ring



AC & USB Cable Accessories



USB Input/Output Charging Port



Stealth Light, Magnetic Base and Smart Select Dial



NEBO®
REDLINE™
SELECT RC

RECHARGEABLE FLASHLIGHT

All of the favorite features of the REDLINE® series, all in one flashlight. This fully rechargeable flashlight offers a smart select dial, adjustable beam and also acts as a power bank for your USB powered device.

LIGHT

- High-power 3100 LUX LED
- New stealth light feature emits a green light from the button, perfect for low light situations

DESIGN

- Fully rechargeable
- Power bank for your USB powered devices
- Anodized aircraft-grade aluminum; water and impact-resistant
- Convex lens
- Signature Red Ring™
- Heat sink design
- Smart Select Dial
- Tactical edge
- 4x adjustable beam
- Steel belt/pocket clip
- Anti-roll tactical grip ring
- Magnetic base
- Charging indicator tells charging status of flashlight and your USB powered devices

OPERATION

- Rear-positioned, glow-in-the-dark ON/OFF button

ACCESSORIES

- AC & USB cables included
- Lanyard included

BATTERIES

- Powered by 1 18650 Lithium Ion rechargeable battery (included)

FOUR LIGHT MODES

HIGH	MEDIUM	LOW	STROBE	S.O.S.
2640 LUX	1226 LUX	476 LUX	2640 LUX	2640 LUX
• 2.5 Hours	• 6.5 Hours	• 20 Hours	• 24 Hours	• 24 Hours
• 206 Meters	• 140 Meters	• 87 Meters	• 206 Meters	• 206 Meters

*NOTE: Light resets to first light mode (HIGH) after being OFF for 5 seconds.

FIVE LIGHT MODES

HIGH	MEDIUM	LOW	STROBE	STEALTH LIGHT
3100 LUX	1550 LUX	310 LUX	3100 LUX	Green Low Light in Button
• 2.5 Hours	• 6 Hours	• 15 Hours	• 8 Hours	• 120 Hours
• 222 Meters	• 130 Meters	• 60 Meters	• 222 Meters	• 0.9 Meters



OPTIMIZED CLARITY

Eliminating inconsistencies in light, the OC™ (Optimized Clarity) Technology provides intense, clear, pristine light that is easy on the eyes. This technology allows the light beam to be as bright on the edge as it is in the center when used in flood mode.



Display Dimensions
(H) 7.125" x (W) 7.48" x (D) 8.267"

Classic REDLINE® OC™ SPECIFICATIONS	
WEIGHT	0.32 lbs.
LENGTH	4.5"
DIAMETER	1.5" (Head) 1" (Barrel)
U.S. PATENT	659,869 S

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930174	6273	Classic REDLINE® OC™ Flashlight	16.50	29.99	12 PIECES



Display Dimensions
(H) 13.75" x (W) 8.5" x (D) 9"

Acrylic Box Dimensions
(H) 9.25" x (W) 3" x (D) 3"

REDLINE® SELECT RC™ SPECIFICATIONS	
WEIGHT	0.5 lbs.
LENGTH	6.75"
DIAMETER	1.625" (Head) 1.3125" (Barrel)
U.S. PATENT	659,869 S

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930013	6189	REDLINE® Select RC™ Flashlight	38.50	69.99	6 PIECES

NEBO®
REDLINE®
SELECT

HIGH-POWER 2950 LUX LIGHT

The REDLINE® Select is named 'Select' for a reason. To improve functionality of the 5 lighting modes, a smart select dial has been added to quickly and conveniently choose your lighting mode while the light is on or off. This feature keeps you from having to cycle through each setting to get to the mode that you need.

LIGHT

- High-power 2950 LUX LED

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- Convex lens
- Signature Red Ring™
- Smart Select Dial
- Tactical edge
- 4x adjustable beam
- Steel belt/pocket clip
- Magnetic base
- Battery indicator - button glows red when battery life reaches 20%

OPERATION

- Rear-positioned, glow-in-the-dark ON/OFF button


ACCESSORIES

- Lanyard included

BATTERIES

- Powered by 3 AAA batteries (included)

AVAILABLE COLORS



Tactical Edge and Signature Red Ring™



Stealth Ring



Steel Belt/Pocket Clip & Lighting Information



Magnetic Base and Smart Select Dial



Tactical Edge and Signature Red Ring™



4x Adjustable Zoom



Steel Belt/Pocket Clip



Glow-in-the-Dark Button and Magnetic Base



NEBO®
SE REDLINE®

HIGH-POWER 2800 LUX LIGHT

More features... more brightness... same great quality. The SE REDLINE® has some user friendly improvements. The lighting modes are now separated into two categories, primary and secondary. Turning the flashlight on and off gives you the primary lighting mode, which is 2800 LUX of intense white light. The secondary lighting modes, Medium, Low, S.O.S. and Defensive Strobe can be activated by holding down the power button for 3 seconds.

LIGHT

- High-power 2800 LUX LED

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- Convex lens
- Signature Red Ring™
- Tactical edge
- 4x adjustable beam
- Steel belt/pocket clip
- Magnetic base
- Battery indicator - button glows red when battery life reaches 20%


OPERATION

- Rear-positioned, glow-in-the-dark ON/OFF button

BATTERIES

- Powered by 3 AAA batteries (included)

AVAILABLE COLORS



FIVE LIGHT MODES

HIGH

- 2950 LUX
- 2 Hours
- 198 Meters

MEDIUM

- 1230 LUX
- 5 Hours
- 96 Meters

LOW

- 305 LUX
- 12 Hours
- 37 Meters

S.O.S.

- 2950 LUX
- 60 Hours
- 198 Meters

STROBE

- 2950 LUX
- 60 Hours
- 198 Meters



Display Dimensions
(H) 7.75" x (W) 7.94" x (D) 7.94"

FIVE LIGHT MODES

HIGH

- 2800 LUX
- 4 Hours
- 210 Meters

PRIMARY

MEDIUM

- 1150 LUX
- 8 Hours
- 136 Meters

LOW

- 285 LUX
- 15 Hours
- 67 Meters

S.O.S.

- 2800 LUX
- 72 Hours
- 210 Meters

STROBE

- 2800 LUX
- 72 Hours
- 210 Meters

SECONDARY LIGHT MODES



Display Dimensions
(H) 7.25" x (W) 13.18" x (D) 5"



#5616 Clamshell Dimensions
(H) 9.375" x (W) 6.25" x (D) 1.625"

REDLINE® SELECT SPECIFICATIONS

WEIGHT	0.7 lbs.	
LENGTH	5"	
DIAMETER	1" (Barrel)	1.5" (Head)
U.S. PATENT	659,869 S	

SE REDLINE® SPECIFICATIONS

WEIGHT	0.428 lbs.	
LENGTH	4.62"	
DIAMETER	1.25" (Head)	1" (Barrel)
U.S. PATENT	659,869 S	

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397111276	5620	REDLINE® Select Flashlight - Black	26.50	49.99	9 PIECES
645397066125	5955	REDLINE® Select Flashlight - Titanium	26.50	49.99	9 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397312116	5615	SE REDLINE® Flashlight	19.50	39.99	14 PIECES
645397914112	5616	SE REDLINE® Flashlight in Clamshell - Gray	19.50	39.99	12 PIECES
645397015123	5638	SE REDLINE® Flashlight - Bulk Black	18.75	39.99	18 PIECES
645397067122	5956	SE REDLINE® Flashlight - Bulk Gray	18.75	39.99	18 PIECES

NEBO® REDLINE®

HIGH-POWER 2185 LUX LIGHT

The ability to bring high-end technology to a compact, fully redesigned, extremely powerful light source is finally here. In an automobile, red-lining means reaching the peak of its performance; with NEBO® REDLINE® we are harnessing the maximum power of this flashlight with 2185 LUX of blinding bright light.

LIGHT

- High-power 2185 LUX LED

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- Convex lens
- Signature Red Ring™
- Tactical edge
- 4x adjustable beam
- Magnetic base



OPERATION

- Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

BATTERIES

- Powered by 3 AAA batteries (included)

AVAILABLE COLORS



Tactical Edge and Signature Red Ring™



4x Adjustable Zoom



Glow-in-the-Dark Button and Magnetic Base



Tactical Edge and Signature Red Ring™



6x Adjustable Zoom



Dual-Direction Belt/Pocket Clip



Glow-in-the-Dark Button and Magnetic Base



NEBO® REDLINE®

HIGH-POWER TACTICAL LIGHT

The REDLINE® OC™ outputs 600 LUX of pristine white light. 600 LUX is bright, but what makes the OC™ so special is the OC™ (Optimized Clarity) Technology. Coupled with the convex lens, the OC™ Technology creates optimized clarity with a perfectly dispersed beam of light while in flood mode. This sophisticated technology provides the intensity of a 600 LUX light that is easy on the eyes. The REDLINE® OC™...optimized clarity.

LIGHT

- High-power 600 LUX LED

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- OC™ Technology
- Convex lens
- Signature Red Ring™
- Tactical edge
- 6x adjustable beam
- Dual-direction belt/pocket clip
- Magnetic base

OPERATION

- Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

ACCESSORIES

- Lanyard included

BATTERIES

- Powered by 1 AA battery (included)

FIVE LIGHT MODES

HIGH	MEDIUM	LOW	S.O.S.	STROBE
2185 LUX	1025 LUX	225 LUX	2185 LUX	2185 LUX
• 4 Hours	• 8 Hours	• 15 Hours	• 72 Hours	• 72 Hours
• 187 Meters	• 128 Meters	• 60 Meters	• 187 Meters	• 187 Meters

*NOTE: Light resets to first light mode (HIGH) after being OFF for 20 seconds.



Display Dimensions
(H) 7.25" x (W) 13.1875" x (D) 5"

#5581 Clamshell Dimensions
(H) 9.375" x (W) 6.25" x (D) 1.625"

TWO LIGHT MODES

600 LUX	STROBE
• 2 Hours	• 4.5 Hours
• 92 Meters	• 92 Meters



Display Dimensions
(H) 8" x (W) 7.5" x (D) 8.25"

REDLINE® SPECIFICATIONS	
WEIGHT	0.428 lbs.
LENGTH	4.5"
DIAMETER	1.5" (Head) 1" (Barrel)
U.S. PATENT	659,869 S

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397401100	5557	REDLINE® Flashlight	17.25	34.99	14 PIECES
645397531111	5581	REDLINE® Flashlight in Clamshell - Gray	17.25	34.99	12 PIECES
645397122111	5599	REDLINE® Flashlight - Bulk Gray	16.50	34.99	18 PIECES
645397111115	5610	REDLINE® Flashlight - Bulk Black	16.50	34.99	18 PIECES



OPTIMIZED CLARITY

Eliminating inconsistencies in light, the OC™ (Optimized Clarity) Technology provides intense, clear, pristine light that is easy on the eyes. This technology allows the light beam to be as bright on the edge as it is in the center when used in flood mode.

REDLINE® OC™ SPECIFICATIONS	
WEIGHT	0.25 lbs.
LENGTH	4.5"
DIAMETER	1.375" (Head) 1" (Barrel)
U.S. PATENT	659,869 S

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397929499	6092	REDLINE® OC™ Flashlight	11.50	19.99	16 PIECES

NEBO[®] LUMO™

OMNIDIRECTIONAL CLIP LIGHT

Compact, handy and bright...the LUMO™ Clip Light by NEBO® is the perfect "whatever you need it to be" light. Key chain light, purse light, backpack light, book light...the possibilities are endless. This compact 25 lumen light comes with a carabiner attachment to clip anywhere you need. The white top of the LUMO™ is a diffuser dome. This dome helps spread the light evenly to create a more omnidirectional light source. LUMO™ Clip Light...the brilliant clip light!

LIGHT

- High-power 25 lumen LED

DESIGN

- Anodized aircraft-grade aluminum, water and impact-resistant
- Carabiner clip
- Glow-in-the-dark button
- Diffuser dome softens the light

OPERATION

- Rear-positioned glow-in-the-dark ON/OFF button

BATTERIES

- Powered by 3 LR44 batteries (included)
- Replacement batteries sold separately as #6045.

AVAILABLE COLORS



Compact Size



Diffuser Dome



Glow-in-the-Dark Button



Carabiner Clip



PROTEC™ Shield
Retracts on Impact



Steel Belt/Pocket Clip



Glow-in-the-Dark Button



NEBO[®] JAG™

SELF-DEFENSE FLASHLIGHT

The JAG™ was designed for concealed self-defense. Upon first glance the JAG™ has a very smooth bezel, yet when used for self-defense the spring-loaded PROTEC Shield™ retracts, exposing the mean, tactical edge. The bezel is smooth to the touch and the concealed tactical edge only protracts upon impact.

LIGHT

- High-power 210 lumen LED

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- Concealed tactical edge with PROTEC™ Shield
- Steel belt/pocket clip

OPERATION

- Rear-positioned glow-in-the-dark ON/OFF button with Soft Touch Technology

BATTERIES

- Powered by 3 AAA batteries (included)

ONE LIGHT MODE

25 LUMENS

- 5 Hours
- 3 Meters

THREE LIGHT MODES

HIGH

- 210 Lumens
- 3.5 Hours
- 110 Meters

LOW


- 105 Lumens
- 12 Hours
- 50 Meters

STROBE

- 210 Lumens
- 72 Hours
- 110 Meters

LUMO™ SPECIFICATIONS

WEIGHT	0.2 lbs.
LENGTH	3.625"
DIAMETER	0.75"
OPERATION	Rear-positioned glow-in-the-dark ON/OFF button



Display Dimensions
(H) 9" x (W) 6.5" x (D) 6.5"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397929529	6095	LUMO™ 25 Lumen Clip Light	2.98	5.99	48 PIECES
645397929864	6157	LUMO™ 25 Lumen Clip Light - Bulk Red	2.70	5.99	12 PIECES
645397929871	6158	LUMO™ 25 Lumen Clip Light - Bulk Silver	2.70	5.99	12 PIECES
645397929888	6159	LUMO™ 25 Lumen Clip Light - Bulk Blue	2.70	5.99	12 PIECES
645397929895	6160	LUMO™ 25 Lumen Clip Light - Bulk Black	2.70	5.99	12 PIECES

JAG™ SPECIFICATIONS

WEIGHT	0.285 lbs.
LENGTH	5.25"
DIAMETER	1.375" (Head) 1" (Barrel)



#5946 Display Dimensions
(H) 9" x (W) 9.75" x (D) 6"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397057123	5946	JAG™ 210 Lumen Flashlight	12.75	24.99	18 PIECES

NEBO® EDGE

TACTICAL FLASHLIGHTS

Some of the first tactical flashlights in the NEBO® line up, the EDGE series. Equipped with tactical edges, rear-positioned ON/OFF buttons and strong, compact body designs, the EDGE™ series is all that you need in a tactical flashlight.

#5519 EDGE 50™

- High-power 50 lumen LED
- Anodized aircraft-grade aluminum; water and impact-resistant
- Tactical edge
- Steel belt/pocket clip
- Rear-positioned ON/OFF button
- Powered by 1 AA battery (included)

#5872 EDGE 90™

- High-power 90 lumen LED with Defensive Strobe
- Anodized aircraft-grade aluminum; water and impact-resistant
- Removable tactical edge
- Steel belt/pocket clip
- Rear-positioned ON/OFF button
- Powered by 1 AA battery (included)

#6085 EDGE 200™

- High-power 200 lumen LED with Defensive Strobe
- Anodized aircraft-grade aluminum; water and impact-resistant
- Removable tactical edge
- Dual-direction steel belt/pocket clip
- Rear-positioned ON/OFF button
- Powered by 1 AA battery (included)




#5519 Steel Clip and Rubber Grip




#5519 Glow-in-the-Dark Button



#5872 Removable Tactical Edge



#6085 Removable Tactical Edge



Convex Lens and 4x Adjustable Zoom



Lanyard Included



Rear-Positioned ON/OFF Button



ONE LIGHT MODE

- 370 LUX**
- 8 Hours
 - 80 Meters

NEBO® ZOOM™ 370 LUX LED Flashlight

ADJUSTABLE ZOOM FLASHLIGHT

Let's admit it, everyone has that cheap-plastic flashlight in the drawer that barely holds a candle to...well, a candle. Here's to the new and more reliable solution for your flashlight drawer...the NEBO® ZOOM™.

LIGHT

- High-power 370 LUX LED

DESIGN

- Water and impact-resistant
- 4x adjustable zoom

OPERATION

- Rear-positioned ON/OFF button

BATTERIES

- Powered by 3 AAA batteries (included)

ACCESSORIES

- Lanyard included



COUNTERTOP DISPLAYS

#5519/#5872 Display Dimensions
(H) 7" x (W) 7" x (D) 5.375"

#6085 Display Dimensions
(H) 8" x (W) 7.5" x (D) 8.25"

EDGE™ SERIES SPECIFICATIONS		
#5519	MAX. OUTPUT	50 Lumens
	WEIGHT	0.179 lbs.
	DIMENSIONS	(L) 3.75" x (W) 0.75"
#5872	MAX. OUTPUT	90 Lumens
	WEIGHT	0.179 lbs.
	DIMENSIONS	(L) 3.75" x (W) 0.75"
#6085	MAX. OUTPUT	200 Lumens
	WEIGHT	0.2 lbs.
	DIMENSIONS	(L) 4.5625" x (W) 0.875"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397900702	5519	EDGE™ 50 Lumen Flashlight	4.95	9.99	24 PIECES
645397107125	5872	EDGE™ 90 Lumen Flashlight	6.50	12.99	24 PIECES
645397929475	6085	EDGE™ 200 Lumen Flashlight	8.80	15.99	20 PIECES

ZOOM™ SPECIFICATIONS	
WEIGHT	0.2 lbs.
LENGTH	4.75"
DIAMETER	1.375" (Head) 1" (Barrel)

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397058120	5947	ZOOM™ 370 LUX Flashlight	5.60	11.99	16 PIECES



#5947 Display Dimensions
(H) 7" x (W) 7" x (D) 5.375"

NEBO®

HAND-HELD FLASHLIGHTS

CSILUMA50™

The CSI LUMA50™ is a compact high-intensity tactical flashlight. Small enough to fit in the palm of your hand, the LUMA50™ shows off its tough side with the aggressive self-defense face.

LUMIÈRE™

The LUMIÈRE™ is a compact high-intensity tactical flashlight with a feminine twist. Small enough to fit in the palm of your hand, the LUMIÈRE™ has a jeweled grip for stylish non-slip grip. Don't let the jewels fool you, the LUMIÈRE™ shows off its tough side with the aggressive self-defense face.

LIGHT

- High-power 50 lumen LED

DESIGN

- Anodized aircraft-grade aluminum; water and impact resistant
- Tactical edge
- Ergonomic rubber grip (#5112)
- Jeweled grip (#5604/#5614)

OPERATION

- Rear-positioned glow-in-the-dark ON/OFF button

BATTERIES

- Powered by 1 AA battery (included)



#5112 Rubber Grip



#5112 Glow-in-the-Dark Button



#5604 Jeweled Grip



#5604 Glow-in-the-Dark Button



5 Green LEDs



5 UV LEDs



Red Laser Pointer



Glow-in-the-Dark Button and Magnetic Base



NEBO®

QUATRO™

FOUR COLOR FLASHLIGHT

The QUATRO™, appropriately named, uses 4 distinct light colors for many different uses: a high-power 75 lumen White LED, 5 Green LED's, 5 UV LED's, and a red laser pointer. This sleek flashlight is also water and impact-resistant.

LIGHT

- High-power 75 lumen white LED
- 5 green LEDs output 12 lumens
- 5 UV LEDs (410-415nm)

LASER

- Red laser pointer

DESIGN

- Anodized aircraft-grade aluminum; water and impact resistant
- Tactical edge
- Magnetic base

OPERATION

- Rear-positioned glow-in-the-dark ON/OFF button

BATTERIES

- Powered by 3 AAA batteries (included)

ONE LIGHT MODE

50 LUMENS

- 5 Hours
- 45 Meters

#5112 & #5604 Display Dimensions (H) 7" x (W) 7" x (D) 5.375"



#5604 Display

Display has a reversible back piece (White or Black)

#5614 Clamshell Dimensions

(H) 7.5" x (W) 5.75" x (D) 1"

SIX LIGHT MODES

WHITE

- 75 Lumens
- 4.5 Hours
- 55 Meters

GREEN

- 12 Lumens
- 16 Hours
- 12 Meters

UV

- 410-415nm
- 18 Hours
- 3 Meters

LASER

- <5mW
- 48 Hours
- 412 Meters

STROBE

- Green LEDs
- 60 Hours
- 12 Meters

S.O.S.

- All LEDs & Laser



Clamshell Dimensions

(H)8.75" x (W) 3.75" x (D) 1.75"

CSI LUMA50™ & LUMIÈRE™ SPECIFICATIONS

WEIGHT	0.179 lbs.
HEIGHT	3.75"
DIAMETER	0.75"

CSI QUATRO™ SPECIFICATIONS

WEIGHT	0.478 lbs.
LENGTH	4.5"
DIAMETER	1.5" (Head) 1" (Barrel)

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397900108	5112	CSI LUMA 50™ 50 Lumen Flashlight	4.95	9.99	24 PIECES
645397421115	5604	LUMIÈRE™ 50 Lumen Flashlight	5.75	9.99	24 PIECES
645397929116	5614	LUMIÈRE™ 50 Lumen Flashlight	5.75	9.99	24 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397430100	5561	QUATRO™ 75 Lumen Flashlight	16.75	29.99	12 PIECES

NEBO®
CSI FLASHLIGHT/LASER
 8 LEDS+LASER+FLASHER

TACTICAL FLASHLIGHT

The CSI Tactical Flashlight is the original NEBO® tactical light. Constructed of anodized aircraft grade aluminum, this flashlight's design is completely water and impact-resistant. Adding to the toughness of this light is the tactical edge and anti roll body design. This flashlight features 8 White LED's and a red laser pointer.

LIGHT
 • 8 high-power LEDs output 24 lumens

LASER
 • Red laser pointer

DESIGN
 • Anodized aircraft-grade aluminum; water and impact-resistant
 • Tactical edge

OPERATION
 • Rear-positioned ON/OFF button

BATTERIES
 • Powered by 3 AAA batteries (included)



Tactical Edge



Emergency Red Flasher LED



Red Laser Pointer



BEND-RITE™ Flex Neck



Rear-Positioned ON/OFF Button



Magnetic Clip Base



NEBO®
BENDBRITE™

HANDS-FREE FLEX LIGHT

The BENDBRITE™ Hands-Free Flex-Light is a unique and innovative source of no-hassle lighting, perfect for any situation. The BENDBRITE™ is equipped with a magnetic clip base giving it the ability to attach to virtually any surface. BENDBRITE™, bright light right where you need it!

LIGHT
 • 3 white LEDs output 9 lumens
 • 1 red LED outputs 0.4 lumens

DESIGN
 • BEND-RITE™ flex neck for omnidirectional lighting
 • Reinforced plastic; water and impact-resistant
 • Magnetic clip base

OPERATION
 • ON/OFF button

BATTERIES
 • Powered by 2 CR2032 batteries (included)

FOUR LIGHT MODES

- | | | | |
|--|--|---|-----------------------------------|
| 8 LEDs
24 Lumens
• 8 Hours
• 30 Meters | LASER
<5mW
• 72 Hours
• 412 Meters | FLASHING
24 Lumens
• 16 Hours
• 30 Meters | S.O.S.
All LEDs & Laser |
|--|--|---|-----------------------------------|



#5633 Assorted Color Display Dimensions
 (H)7.5" x (W) 9" x (D) 4.75"



#5077 Clamshell Dimensions
 (H) 7.125" x (W) 5.25" x (D) 1.5"

CSI TACTICAL SPECIFICATIONS	
WEIGHT	0.275 lbs.
LENGTH	4.5"
DIAMETER	1.5" (Head) 1" (Barrel)

TWO LIGHT MODES

- | | |
|--|---|
| WHITE
9 Lumens
• 7 Hours
• 10 Meters | RED
0.4 Lumens
• 6.5 Hours
• 5 Meters |
|--|---|

BENDBRITE™ SPECIFICATIONS	
WEIGHT	0.237 lbs.
HEIGHT	9.5"



Display Dimensions
 (H) 8" x (W) 13" x (D) 7.75"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397010128	5633	CSI Tactical Flashlight Assorted Colors	7.50	14.99	18 PIECES
645397128007	5077	CSI Tactical Flashlight in Clamshell	7.50	14.99	18 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397900306	5423	BENDBRITE™ Hands-Free Flex Light	5.60	9.99	16 PIECES

NEBO® 90 LUMEN HEAD LAMP

ADJUSTABLE HEAD LAMP

The NEBO® 90 Lumen Head Lamp is a powerful and convenient hands-free lighting solution. The head tilts 90° to direct light exactly where you need it and the adjustable strap provides a sure fit for any size.

LIGHT

- High-power 90 lumen LED
- 2 red LEDs

DESIGN

- Reinforced plastic; water and impact-resistant
- Head tilts 90° to direct light where you need it
- Adjustable head strap

OPERATION

- ON/OFF button

BATTERIES

- Powered by 3 AAA batteries (included)




2 Emergency Red LEDs



90° Vertical Tilt




Adjustable Head Strap



Quick Change Blade



Lock Release Button



Carabiner Clip



NEBO® Folding LOCK-BLADE Utility Knife

UTILITY KNIFE

The Folding Lock-Blade Utility Knife uses a quick change feature making it easier to change the blade without any tools. The utility knife accepts all standard utility blades and incorporates a blade lock system which makes this a safe, strong and secure knife that can be unlocked with one hand.

DESIGN

- Anodized aluminum handle with rubber grip
- Quick change blade feature; no tools required
- Thumb studs for one-handed opening
- Carabiner
- Lock release button to unfold

#5517 Assorted Color Display

- Product can be displayed on retail counter or hung as clamshell

Display Dimensions

(H) 8.75" x (W) 14" x (D) 10.5"

Clamshell Dimensions

(H) 8.25" x (W) 4.25" x (D) 1.25"

AVAILABLE COLORS



THREE LIGHT MODES

WHITE

- 90 Lumens
- 9 Hours
- 100 Meters

RED

- 8 Lumens
- 150 Hours
- 3 Meters

RED FLASH

- 8 Lumens
- 250 Hours
- 3 Meters



Clamshell Dimensions
(H) 7.25" x (W) 4.45" x (D) 2.875"

90 LUMEN HEAD LAMP SPECIFICATIONS	
WEIGHT	0.225 lbs.
SIZE	One size fits all; adjustable fit

LOCK-BLADE UTILITY KNIFE SPECIFICATIONS

WEIGHT	0.5 lbs.
LENGTH	Open: 7" Closed: 4.25"
WIDTH	1.5"
DEPTH	0.75"



UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397929215	6003	90 Lumen Head Lamp	10.20	19.99	6 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397900504	5517	Folding Lock-Blade Utility Knife Assorted	3.98	6.99	18 PIECES

NEBO® Ultra™ Socket

14-IN-1 MULTI-TOOL

The NEBO® 14-in-1 Ultra™ Socket comes with 7 screwdriver bits and 5 sockets conveniently stored inside the handle. The head of the Ultra™ Socket tilts a full 180° and locks at 0°, 45°, and 90°, working perfectly as a nut driver for those hard to reach places. The handle is ergonomically designed to add comfort and grip to improve performance. The Ultra™ Socket features a reversible ratchet mechanism making it easier to loosen or tighten any bolt. The 14-in-1 Ultra™ Socket meets and exceeds ANSI standards and is created to withstand more than the normal wear and tear.

DESIGN

- Head tilts and locks at 0°, 45° & 90°
- Reversible ratchet mechanism
- Water and impact-resistant
- Ergonomic reinforced plastic handle
- Socket adapter
- Sockets and bits stored inside handle



Head Tilts and Locks at 0°, 45° & 90°



Accessories Stored Inside Handle



7 Screwdriver Bits, 5 Sockets and Adapter



Head Tilts and Locks at 0°, 45° & 90°



Accessories Stored Inside Handle



Carrying Pouch Included



Display Dimensions
(H) 14.75" x (W) 9.125" x (D) 6"

14-in-1 ULTRA™ SOCKET SPECIFICATIONS

SIZE	8.25" (L) x 1.5" (W) 0.75 lbs.
SOCKETS	SAE: 1/4", 9/32", 5/16", 11/32", 3/8" & Socket adapter
BITS	Phillips: P1-P3, Slotted: 3/16" & 1/4", Torx: T15 & T20

ULTRA™ SOCKET COMBINATION KIT SPECIFICATIONS

SIZE	8" (L) x 1.375" (W) 1.6 lbs.
SOCKETS	Metric: 5mm, 6mm, 7mm, 8mm, 9mm, 10mm, 11mm, 12mm, 13mm SAE: 3/16", 1/4", 9/32", 5/16", 11/32", 3/8", 7/16", 15/32", 1/2", 9/16"
BITS	Phillips: P1-P3, Slotted: 1/8", 3/16", 1/4", Hex: 1/8", 5/32", 7/32" Torx: T15, T20 & T25
U.S. PATENT	6,634,262 & 6,450,067

NEBO® Ultra™ Socket

MULTI-TOOL

The NEBO® Ultra™ Socket Combination Kit comes with 19 sockets conveniently stored in SAE and Metric trays. The base of the Ultra™ Socket unscrews to reveal the stored screwdriver bits and magnetic 1/4" bit holder. The head of the Ultra™ Socket tilts and locks at 0°, 45°, and 90°, working perfectly as a nut driver for those hard to reach places. The industrial strength ergonomic rubber handle design adds comfort and grip to improve performance. The Ultra™ Socket features a reversible ratchet mechanism making it easier to loosen or tighten any bolt. Exceeding ANSI standards, the Ultra™ Socket is created to withstand more than the normal wear and tear. Ultra™ Socket and components are all conveniently stored in a 600D Polyester carrying pouch.

DESIGN

- Head tilts and locks at 0°, 45° & 90°
- Reversible ratchet mechanism
- Water and impact-resistant
- Ergonomic rubber handle
- Magnetic 1/4" bit holder
- Screwdriver bits stored inside handle

ACCESSORIES

- 600D Polyester carrying pouch



#4327 Box Dimensions
(H) 8.5" x (W) 3.5" x (D) 1.75"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397610113	5606	Ultra™ 14-in-1 Socket and Screwdriver	9.95	16.99	12 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397130406	4327	Ultra™ Socket Combination Kit	13.45	19.99	12 PIECES

NEBO®
Flashlight Holsters

FLASHLIGHT HOLSTERS

Each NEBO® flashlight holster has a pouch made to securely fit all of the 1"+ diameter NEBO® flashlights and most other brands as well. The holster's are designed for protection, durability and structural strength.

#5089 CSI Flashlight Holster

- Leather covered steel belt/pocket clip
- Carabiner clip
- Reinforced holster backing
- Compatible with 1" diameter flashlights

#5958 Flashlight Holster

- Snap cover with hook and loop closure
- Steel belt/pocket clip
- Compatible with flashlights up to 1.5" diameter; less than 5" tall

#6032 Flashlight Holster

- Hook and loop closure
- Belt loop
- Designed specifically for #5620 REDLINE® Select
- Compatible with flashlights up to 1.5" diameter; less than 5" tall

#5922 Leather Flashlight Holster

- Snap cover
- Large steel belt/pocket clip
- Compatible with flashlights up to 1.25" diameter

#6274 Flashlight Holster

- Steel belt/pocket clip
- Designed specifically for #6156 SLYDE™
- Compatible with flashlights up to 1.5" diameter



Item #5089 Item #5958 Item #6274 Item #6032 Item #5922

TRUE UTILITY®
...IN YOUR POCKET



True Utility® creates clever and original products that belong in people's pockets, giving them convenient and practical solutions to everyday problems.

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397850892	5089	CSI Flashlight Holster	2.20	3.99	10 PIECES
645397069126	5958	Flashlight Holster	3.20	6.99	10 PIECES
645397929284	6032	Flashlight Holster	3.50	6.99	10 PIECES
645397035121	5922	Leather Flashlight Holster	8.50	16.99	6 PIECES
645397930181	6274	Flashlight Holster	3.50	6.99	6 PIECES

CLIPSTER

Folded from a single piece of stainless steel, the Clipster features a fold-out blade and handle that doubles as a money or belt clip. This strong locking knife is made from high-quality stainless steel.

DESIGN

- High-quality stainless steel
- Folding knife
- Money/belt clip

NEW!

Stainless steel folding knife



money/belt clip

CLIPSTER

COUNTERTOP DISPLAY

#TU579 Display

- Display holds 8 pieces; 8 additional pieces are included as replenishments
- Each Clipster comes in an individual gift box

Display Dimensions

(H) 11" x (W) 6.5" x (D) 7.5"

Box Dimensions

(H) 3" x (W) 6" x (D) 1"



Actual Size



CLIPSTER™ SPECIFICATIONS

BODY MATERIAL	High-quality stainless steel
DIMENSIONS	(L) 4.8125" x (W) 1.1875" x (D) 0.25" Closed: (L) 2.875"
WEIGHT	0.1 lbs.

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
5060063223988	TU579	Clipster	7.95	14.99	16 PIECES

TRUE UTILITY
...IN YOUR POCKET

FIXR™

The FIXR™ features an easy, portable solution for all of your everyday tools. Equipped with a quick release clip, this tool easily attaches to your key ring or belt loop. A revolving disc allows tools to be exposed while in use, so they are never in the way when you don't need them.

TOOLS

- Quick-release clip
- Bottle opener
- Cutting blade
- Pry bar
- Nail file
- Wire stripper
- Nail cleaner
- Box opener
- Large flat driver
- Medium flat driver
- Eyeglass screwdriver
- Medium Phillips driver
- Small Phillips driver
- Bicycle spoke wrench
- Measuring ruler
- 1/4" wrench
- 5/16" wrench
- 3/8" wrench
- 1/2" wrench
- 9/16" wrench

DESIGN

- 420 grade black stainless steel
- Gold titanium coated disc
- K5 carbon steel blade

ACCESSORIES

- Leather carrying pouch

180° rotating
tool disc



quick-release
CleverClip
for easy access



leather carry
pouch included



TRUE UTILITY
...IN YOUR POCKET

FIXR™

COUNTERTOP DISPLAY

#TU200US Metal Display

- Display holds 6 pieces; 12 additional pieces are included as replenishments and 1 demo FIXR™ is attached to the display

- Each FIXR™ comes in an individual gift box

Display Dimensions

(H) 8.4375" x (W) 8.625" x (D) 5"

Box Dimensions

(H) 7" x (W) 2" x (D) 1"



Actual Size

FIXR™ SPECIFICATIONS

BODY MATERIAL	420 grade stainless steel / gold titanium coated disc / K5 carbon steel
DIMENSIONS	(L) 3.25" x (W) 1" x (D) 0.33"
WEIGHT	0.1 lbs.

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
506006322202	TU200US	FIXR™ - 20 Tools in 1	7.95	14.99	18 PIECES

SmartKnife

Much more than just a pocket knife...it's a bottle opener, screwdriver, belt cutter, glass breaker, multi-size spanner and a knife all wrapped up in a high-grade stainless steel body. Handy belt clip and lanyard attachment included.

DESIGN

- Fine sandblasted 420 grade stainless steel
- Knife
- Belt clip
- Bottle opener
- Screwdriver
- Belt cutter
- Adjustable spanner (4mm - 10mm bolts)
- Quick-release clip

sciXors+®

A completely new kind of fully-functional scissor based multi-tool, with all the essentials including bottle opener, large and small screwdrivers, straight and serrated cutting edges. Stylishly sits alongside your keys. Simply pull the quick release pin and the scissor tool is ready for use.

DESIGN

- 422 grade stainless steel
- Sharp & serrated scissors
- Bottle opener
- Small & large screwdrivers
- Quick-release pin key ring attachment
- Split ring included

More than just a knife...it's a bottle opener, screwdriver, belt cutter, glass breaker and a wrench all wrapped up in one.



A strong, stainless steel multi-tool that includes powerful small pliers, knife, file, Phillips screwdriver and bottle opener.



ClipTool

A small strong stainless steel bodied multi-tool that includes powerful small pliers, knife, file, Phillips screwdriver and bottle opener. Quick release clip for easy on/off access.

DESIGN

- 422 grade stainless steel
- Pliers
- File
- Knife
- Phillips screwdriver
- Bottle opener
- Quick-release clip

A completely new kind of fully functional scissor based multi-tool, including bottle opener, screwdrivers, straight and serrated cutting edges.



A fully-functional, corkscrew for all wine lovers. The compact design provides a low profile addition to your key ring.



Twistick®

The Stainless Steel bar passes through the center of a full-size corkscrew helix to create a beautiful and fully-functional personal corkscrew for all wine lovers. Can be attached to your key ring or your bag with the key ring attachment.

DESIGN

- 422 grade stainless steel
- Full-size coated corkscrew helix
- 4mm stainless steel bar
- 10mm split key ring attachment



Display Dimensions
(H) 9.75" x (W) 12.5" x (D) 9.75"

SMARTKNIFE SPECIFICATIONS	
BODY MATERIAL	Fine sandblasted 420 grade stainless steel
DIMENSIONS	(L) 3.54" x (W) 1.3" x (D) 0.35"
WEIGHT	0.08 lbs.
sciXors+® SPECIFICATIONS	
BODY MATERIAL	422 grade stainless steel
DIMENSIONS	(L) 3.07" x (W) 0.7" x (D) 0.43"
WEIGHT	0.05 lbs.



HardCase Dimensions
(H) 4.72" x (W) 3.15" x (D) 1.38"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
5060063221472	TU573	SmartKnife	6.98	14.99	6 PIECES
5060063221472	TU573DSP	SmartKnife Display	6.98	14.99	18 PIECES +1
5060063221991	TU238	sciXors+®	4.75	9.99	6 PIECES



HardCase Dimensions
(H) 4.72" x (W) 3.15" x (D) 1.38"

CLIPTOOL SPECIFICATIONS	
BODY MATERIAL	422 grade stainless steel
DIMENSIONS	(L) 3.3" x (W) 1.18" x (D) .47"
WEIGHT	0.17 lbs.
TWISTICK® SPECIFICATIONS	
BODY MATERIAL	422 grade stainless steel
DIMENSIONS	(L) 2.6" x (W) 0.39" x (D) 0.31"
WEIGHT	0.03 lbs.



UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
5060063221588	TU192	ClipTool	6.75	12.99	6 PIECES
5060063221359	TU248	Twistick®	3.95	7.99	6 PIECES

KeyTool

Simply wraps around your key on your key ring giving you 8 essential tools including bottle opener, nail file, thread cutter, 3 screwdrivers (including one for eyeglasses) and even sprung tweezers. Always useful - never in the way!

DESIGN

- 420 grade stainless steel
- Bottle opener
- Eyeglass screwdriver
- Medium screwdriver
- Large screwdriver
- Nail file
- Finger nail cleaner
- Thread cutter
- Tweezers
- Quick-release CleverClip

Micro USB MobileCharger

Charge and data transfer all in one. Connect your phone to a USB port for a quick charge or data transfer. Keep on your key ring for charging anytime, anywhere. Made with premium quality copper wire flat cable for super fast charging. Charges all micro USB phones, including: Samsung, Blackberry, Nokia, LG, Motorola, etc.

DESIGN

- Micro USB to USB cable
- Phone charger
- Data transfer
- Key ring included
- Premium copper wire flat cable for fast charging

Simply wraps around your key. 8 essential tools on your key ring. Always useful - never in the way!

wraps around all standard keys



quick-release CleverClip for easy access

180° rotation

Contains strong, sharp nail clippers, a sharp blade, nail file, flat head screwdriver and a pair of scissors all in one.

422 grade stainless steel



foldable, compact design

10mm split key ring attachment

Charge and data transfer...anytime, anywhere. Charges all micro USB phones.

USB with protective cap



micro USB with key ring attachment

This super bright, 3 LED light is the perfect pocket accessory, complete with a rotating split key ring attachment.

3 bright LEDs



rotating split key ring attachment

anti-slip grip

NailClip Kit

Contains man-sized super strong and sharp nail clippers for the hardest nails. Clippers spring out from the ergonomically shaped stainless steel body. It also houses a sharp blade, nail file, flat head screwdriver and a pair of self-sprung sharp scissors.

DESIGN

- 422 grade stainless steel
- Nail clippers
- Nail file
- Flat head screwdriver
- Scissors
- Knife
- 10mm split key ring attachment

Compact MicroLite

This super bright white 3 LED light is the perfect pocket accessory. LED bulbs are guaranteed for life. Spins around your key ring for easy use. Comes with 4 long-life button cell batteries.

LIGHT

- Three 0.22 watt LEDs
- 18 hour run time

DESIGN

- Anodized aircraft-grade aluminum: water and impact-resistant
- Machine milled knurling for anti-slip grip
- Split key ring attachment

OPERATION

- Twist ON/OFF

BATTERIES

- Four AG13 button cell batteries included



HardCase Dimensions
(H) 4.72" x (W) 3.15" x (D) 1.38"

KEYTOOL SPECIFICATIONS	
BODY MATERIAL	420 grade stainless steel
DIMENSIONS	(H) 2.8" x (W) 0.9" x (D) 0.2"
WEIGHT	0.08 lbs.
MICRO USB MOBILECHARGER SPECIFICATIONS	
BODY MATERIAL	Premium copper wire
DIMENSIONS	(H) 3" x (W) 0.6" x (D) 0.2"
WEIGHT	0.009 lbs.



HardCase Dimensions
(H) 4.72" x (W) 3.15" x (D) 1.38"

NAILCLIP KIT SPECIFICATIONS	
BODY MATERIAL	422 grade stainless steel
DIMENSIONS	(L) 2.2" x (W) 0.6" x (D) 0.35"
WEIGHT	0.08 lbs.
COMPACT MICROLITE SPECIFICATIONS	
BODY MATERIAL	Anodized aircraft-grade aluminum
DIMENSIONS	(L) 1.89" x (W) 0.75" x (D) 0.75"
WEIGHT	0.06 lbs.



UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
5060063221342	TU247	KeyTool	4.50	9.99	6 PIECES
5060063222493	TU290B	Micro USB MobileCharger	4.90	9.99	6 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
5060063220864	TU215	NailClip Kit	5.25	9.99	6 PIECES
5060063221557	TU283S	Compact MicroLite	4.75	9.99	6 PIECES

KeyRing System

Simply a better way to carry your keys and accessories around with you than a common split ring. The stainless steel key shackle holds up to 5 keys completely flat and in the correct order. CleverClips can be attached to your car keys, house keys and accessories.

DESIGN

- 316 Marine grade stainless steel
- 4 stainless steel quick-release CleverClips
- Stainless steel key shackle
- Strong stainless steel key ring

Holds up to 5 keys completely flat and in the correct order. 4 CleverClips attach additional accessories.



SkeletonKnife

The clever, unusual and highly functional open frame design enables the knife blade to be opened and closed smoothly with a one-handed motion. The minimalist, super-slender body makes this knife a pleasure to own and use.

DESIGN

- 420 grade stainless steel
- Belt/pocket clip
- ABS plastic blade stop
- Key ring hole attachment

The clever, unique and highly-functional open frame design enables the knife blade to open and close with one hand.



Telescopic design, extra refills...now that's something to write home about.



TelePen

Now that's something to write home about! Engineered in Stainless Steel and measuring only 2", the TelePen extends telescopically to 4.5". With just one quick pull, it instantly extends and is ready to use. Supplied complete with 3 extra black ink refills.

DESIGN

- Ballpoint pen with 3 extra black ink refills
- Telescopic (2" - 4.5")
- Key ring attachment
- Quick-pull release mechanism

Never run out of money again with this emergency cash capsule for your key ring!



CashStash

Never run out of money again! Emergency cash capsule for your key ring. Cash-clip secures one note of any currency on your key ring. As small as your key and waterproof. Makes a perfect gift, especially if you put cash in it!

DESIGN

- Aircraft-grade aluminum; water and impact resistant
- Fits any single note; currency not included
- Water-proof Neoprene O-ring
- Stainless Steel CashClip
- 10mm split key ring attachment



HardCase Dimensions
(H) 4.72" x (W) 3.15" x (D) 1.38"

KEYRING SYSTEM SPECIFICATIONS	
BODY MATERIAL	316 Marine grade stainless steel
DIMENSIONS	(H) 2" x (W) 0.6" x (D) 0.4"
WEIGHT	0.05 lbs.
SKELETONKNIFE SPECIFICATIONS	
BODY MATERIAL	420 grade stainless steel
DIMENSIONS	(H) 2.5" x (W) 0.9" x (D) 0.3"
WEIGHT	0.06 lbs.



HardCase Dimensions
(H) 4.72" x (W) 3.15" x (D) 1.38"

TELEPEN SPECIFICATIONS	
BODY MATERIAL	Stainless steel
DIMENSIONS	OPEN: (H) 4.5" x (W) 0.2" x (D) 0.2" CLOSED: (H) 2"
WEIGHT	0.03 lbs.
CASHSTASH SPECIFICATIONS	
BODY MATERIAL	Aircraft-grade aluminum
DIMENSIONS	(H) 1.8" x (W) 0.6" x (D) 0.6"
WEIGHT	0.02 lbs.



UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
5060063221328	TU245	KeyRing System	4.90	9.99	6 PIECES
5060063221465	TU571	SkeletonKnife	5.90	11.99	6 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
5060063221335	TU246	TelePen	4.90	9.99	6 PIECES
5060063221267	TU241	CashStash	4.00	7.99	6 PIECES

MiniDriver

This little gem won't just look great on your key chain, but is very useful too. It cleverly contains 4 screwdriver heads - both small and large Phillips and flathead screwdrivers. Simply remove the quick release clip and slide a key or coin into the slotted end to add torque so you can undo/do up the toughest of screws. 3 bits are hidden in the shaft.

DESIGN

- Chromium plated steel
- Anti-slip grooves on main body for better control
- 4 screwdriver heads: standard and small Phillips, standard and small flathead screwdrivers
- Quick-release CleverClip included

TinyTorch

The perfect key ring torch, with 2 powerful 5mm 'cat eyes' LEDs. Permanent ON/OFF button. Smooth bodied with knurled easy grip head and tail. Strong D-ring for attaching to your key ring.

LIGHT

- Two 5mm LEDs output 8+ lumens
- 50 hour run time

DESIGN

- Aircraft-grade aluminum
- Machine milled knurling for anti-slip grip

OPERATION

- ON/OFF push button

BATTERIES

- 3 button cell batteries included

Great-looking and useful! The extra screwdriver bits store discreetly in the body of the MiniDriver.



This unbelievably small, water-proof key ring capsule houses a fully-functional lighter, ready to ignite at your command.



The perfect key ring flashlight, with 2 powerful 5mm LED's...50+ hour run time!



6 fully functional tools in one ultra-compact frame!



FireStash

This unbelievably small, water-proof key ring canister houses a fully working lighter that is ready to ignite at your command. Attach to your key ring for essential outdoor use. Refill with standard lighter fuel.

DESIGN

- Dark chrome plated zinc alloy
- Petrol refillable lighter (supplied without lighter fluid)
- Water-proof Neoprene O-ring
- 20mm split key ring attachment

MicroTool

The MicroTool is a fully functional set of key ring tools crammed into a tiny 1.75" frame. That's smaller than a door key! This tiny tool is bursting with essentials - super-sharp scissors and knife, bottle opener, screwdriver, file and nail cleaner.

DESIGN

- 422 grade stainless steel
- Scissors
- Knife
- Bottle opener
- Screwdriver
- File
- Nail cleaner
- Quick release clip



HardCase Dimensions
(H) 4.72" x (W) 3.15" x (D) 1.38"

MINIDRIVER SPECIFICATIONS	
BODY MATERIAL	Chromium plated steel
DIMENSIONS	(H) 3.1" x (W) 0.6" x (D) 0.4"
WEIGHT	0.05 lbs.
TINYTORCH SPECIFICATIONS	
BODY MATERIAL	Aircraft-grade aluminum
DIMENSIONS	(H) 2" x (W) 0.7" x (D) 0.7"
WEIGHT	0.04 lbs.



HardCase Dimensions
(H) 4.72" x (W) 3.15" x (D) 1.38"

FIRESTASH SPECIFICATIONS	
BODY MATERIAL	Dark chrome plated zinc alloy
DIMENSIONS	(H) 1.8" x (W) 0.6" x (D) 0.6"
WEIGHT	0.06 lbs.
MICROTOOL SPECIFICATIONS	
BODY MATERIAL	422 grade stainless steel
DIMENSIONS	(H) 3" x (W) 0.4" x (D) 0.4"
WEIGHT	0.08 lbs.



UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
5060063229843	TU231	MiniDriver	4.90	9.99	6 PIECES
5060063222066	TU284	TinyTorch	4.50	8.99	6 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
5060063221441	TU262	FireStash	4.90	9.99	6 PIECES
5060063221298	TU242	MicroTool	4.90	9.99	6 PIECES



NanoLite

Probably the smallest flashlight in the world! This powerful pocket flashlight runs on 4 powerful, long-lasting miniature hearing aid batteries, which power a bright 5mm LED. Simple twist ON/OFF. 3 full sets of batteries included!

LIGHT

- LED outputs 4 lumens

DESIGN

- Solid brass with an electroplated silver finish
- Twist ON/OFF switch
- Water and impact-resistant
- Spinning key ring attachment
- 3 set of batteries included

*Simply twist to activate this tiny light.
Perfect for lighting up those hard to reach places.*

*comes with
3 full sets
of batteries*

*LED outputs
4 lumens*

*Key ring
attachment*

SlimClips

These slim, super sharp, extra strong nail clippers will easily trim the toughest of nails. Fabricated from the finest stainless steel, they easy attach to your key ring.

DESIGN

- 422 grade stainless steel
- Patented strong nail clippers
- Coarse file
- Key ring attachment

*Slimline, super sharp, extra strong nail clippers are
fabricated from the finest stainless steel.*

*super sharp
clippers and file*

*Key ring
attachment*

*compact and
portable*



HardCase Dimensions
(H) 4.72" x (W) 3.15" x (D) 1.38"



NANOLITE SPECIFICATIONS	
BODY MATERIAL	Solid brass with electroplated silver finish
DIMENSIONS	(H) 1.4" x (W) 0.3" x (D) 0.3"
WEIGHT	0.01 lbs.
SLIMCLIPS SPECIFICATIONS	
BODY MATERIAL	422 grade stainless steel
DIMENSIONS	(H) 2.2" x (W) 0.2" x (D) 0.2"
WEIGHT	0.03 lbs.

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
5060063222073	TU285	NanoLite	4.90	9.99	6 PIECES
5060063221243	TU236	SlimClips	4.90	9.99	6 PIECES



HardCase Packaging

All of our products come in a versatile and weather-proof HardCase. The HardCase is strong, durable, splash-proof and most importantly, reusable. Perfect for outdoor pursuits and protecting valuables from dust and moisture. Adds value to each True Utility® purchase.

HardCase Size

(H) 4.72" x (W) 3.15" x (D) 1.38"

Holds: Money, credit cards, keys, phone, mp3 player, tools, etc.

18 Piece Tray Display

Perfect for displaying larger quantities of a single True Utility® product or a variety of True Utility® products.

18 Piece Tray Size

(H) 18.9" x (W) 12.25" x (D) 9.75"

*Tray included with a minimum purchase of (3) 6 piece packs



6 Piece Countertop Tray Display

Each case of True Utility® product comes with a countertop tray display. Perfect for showcasing these products near the point of purchase, these displays come with an attractive backer card highlighting the product's best-selling features. The backer card also doubles as a replenishment reminder in use with the Rotating Display.

6 Piece Tray Size

(H) 9" x (W) 4" x (D) 9.75"

*Comes with each True Utility® case pack purchase



16 Hook Rotating Display

Display the most complete set of best-selling True Utility® products where customers can pick and pay. This eye-catching interactive shop display is great for impulse buying.



16 Hook Display Size

(H) 18.9" x (W) 13.78"

Display holds 48 pieces on 16 hooks

*True Utility® products sold separately

ITEM	DESCRIPTION	COST	CASE PACK
16HKROTATING	True Utility® 16 Hook Rotating Display	\$49.99	1 PIECE



BIKE LIGHT

The REDLINE® Bright Light features a quick release bar mount that easily attaches to any bar, no tools necessary. The REDLINE® can detach from the bar mount to be used as a handheld flashlight.

- LIGHT**
- High-power 2185 LUX LED
- MOUNT STYLE**
- Bar mount; no tools required
- DESIGN**
- Tactical edge
 - Convex lens
 - 4x adjustable beam
 - Anodized aircraft-grade aluminum; water and impact-resistant
 - Magnetic base
 - Quick-release tab quickly detaches flashlight
 - Mount allows light to swivel 180°
- OPERATION**
- Rear-positioned Glow-in-the-dark ON/OFF button with Soft Touch Technology
- BATTERIES**
- 3 AAA batteries included

THREE LIGHT MODES

- | | | |
|-------------------------|-----------------------|---------------------------|
| HIGH
2185 LUX | LOW
225 LUX | STROBE
2185 LUX |
| • 4 Hours | • 8 Hours | • 72 Hours |
| • 187 Meters | • 60 Meters | • 187 Meters |



Clamshell Dimensions
(H) 8.375" x (W) 6.25" x (D) 2.75"

REDLINE® BIKE LIGHT SPECIFICATIONS	
MAX. OUTPUT	2185 LUX
LIGHT COLOR	White
MOUNT STYLE	Bar mount
BODY MATERIAL	Anodized aircraft-grade aluminum; water and impact-resistant
WEIGHT	0.5 lbs.
DIMENSIONS	(L) 4.5" x (D) 3" x (W) 1.325"
OPERATION	Rear-positioned ON/OFF button with Soft Touch Technology
BATTERIES	Powered by 3 AAA batteries (included)
U.S. PATENT	659,869 S

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397120018	5624	REDLINE® with Bar Mount	19.50	39.99	6 PIECES

Whether cruising around the city streets or mountain biking in the middle of nowhere, NEBO® Sports has the essentials you need for your ride.



6 WHITE LED BIKE LIGHT

BIKE LIGHT

LIGHT

- 6 high-power LEDs output 18 lumens

MOUNT STYLE

- Bar mount; no tools required

DESIGN

- Water and impact-resistant
- Quick-release tab quickly detaches light
- Mount allows light to swivel 180°

OPERATION

- ON/OFF button

ACCESSORIES

- Lanyard included

BATTERIES

- 3 AAA batteries included



75 Lumen 5 LED Red Bike Light / Tail Light COMBO

BIKE LIGHT / TAIL LIGHT

LIGHT

- #5952 5 LED Red Tail Light
- 5 high-power LEDs output 3.5 lumens of red light

#5953 75 Lumen Bike Light / 5 LED Red Tail Light

- High-power 75 lumen LED
- 5 high-power LEDs output 3.5 lumens of red light

MOUNT STYLE

- Bar mount; no tools required

DESIGN

- Water and impact-resistant
- Quick-release tab quickly detaches light
- Mount allows head light to swivel 180°
- Tail light features strong clip

OPERATION

- ON/OFF button

BATTERIES

- 3 AAA batteries included for head light
- 2 AAA batteries included for tail light

NOTE: 5 LED Red Tail Light is included in #5953 Bike Light Combo; also sold separately as #5952.

TWO LIGHT MODES

ON

- 18 Lumens
- 15 Hours
- 22 Meters

STROBE

- 18 Lumens
- 28 Hours
- 22 Meters



Clamshell Dimensions
(H) 7.875" x (W) 5.5" x (D) 2.5"

FOUR LIGHT MODES

- HIGH - 75 Lumens** • 3 Hours / 65 Meters
- LOW - 37.5 Lumens** • 4.7 Hours / 32 Meters
- STROBE - 75 Lumens** • 5.3 Hours / 65 Meters
- S.O.S. - 75 Lumens** • 3.5 Hours / 65 Meters

SEVEN LIGHT MODES

- ON - 3.5 Lumens** • 55 Hours / 1.6 KM
- FLASH** • 120 Hours / 1.6 KM
- SLOW FLASH** • 120 Hours / 1.6 KM
- CASCADING** • 120 Hours / 1.6 KM
- RISING** • 120 Hours / 1.6 KM
- RAPID CASCADE** • 120 Hours / 1.6 KM
- RANDOM FLASH** • 120 Hours / 1.6 KM



#5953 Clam Size
(H) 9.25" x (W) 5.75" x (D) 2.5"



#5952 Clam Size
(H) 6.625" x (W) 5.5" x (D) 2"

6 WHITE LED BIKE LIGHT SPECIFICATIONS	
MAX. OUTPUT	18 Lumens
LIGHT COLOR	White
MOUNT STYLE	Bar mount
BODY MATERIAL	Water and impact-resistant
WEIGHT	0.25 lbs.
DIMENSIONS	(L) 3.5" x (D) 3" x (W) 1.25"
OPERATION	Top-positioned ON/OFF button
BATTERIES	Powered by 3 AAA batteries (included)

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397819103	5576	6 White LED Bike Light	6.90	13.99	6 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397064121	5953	Bike Light Combo	12.20	24.99	6 PIECES
645397063124	5952	5 Red LED Tail Light	4.95	9.99	6 PIECES



250 PSI AIR COMPRESSOR

AIR COMPRESSOR

The 250 PSI Air Compressor by NEBO® Sports is a 12V portable air compressor that can inflate a standard size bicycle tire in less than a minute! While designed for bicycle tires, this Air Compressor has the power to use on your vehicle as well. This compact, portable Air Compressor is a perfect addition to your trunk for when those inconvenient, yet inevitable flat tires occur.

DESIGN

- 250 PSI (Pounds per Square Inch)
- Inflates standard size bicycle tires in less than a minute
- 12V DC plug
- Easy-to-read PSI gauge
- 18" Air Hose
- 10' Power Cord
- Ergonomic thumb-lock lever



18" Air Hose



EASY-TO-READ PSI Gauge



10' 12V DC Power Cord



Clamshell Dimensions
(H) 7.875" x (W) 5.5" x (D) 2.5"

250 PSI AIR COMPRESSOR SPECIFICATIONS	
WEIGHT	1.94 lbs.
DIMENSIONS	(H) 6.5" x (D) 3.5" x (W) 5.25"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397812111	5611	250 PSI Air Compressor	9.80	19.99	12 PIECES

WEATHERRITE®
SINCE 1941



Your next camping excursion will not be complete without your WeatherRite® products. Whether at home or in the great outdoors, WeatherRite® specializes in creating recreational and emergency preparedness consumer products, ideal for any situation.

ECOLANTERN™

RECHARGEABLE LANTERN

The ECO LANTERN™ is a portable, reliable energy-saving lantern with 24 super bright energy efficient white LEDs that guarantee continuous supreme illumination. Requiring no batteries, the ECO LANTERN™ charges with AC, DC, solar or wind up making it perfect for camping, fishing, hunting, boating, road trips, RVing, power outages, at home use, or any emergency situation.

LIGHT

- 24 high-power LEDs output 157 lumens

DESIGN

- Water and impact-resistant
- Uses 4 methods of recharging: AC, DC, solar & wind up
- Charging indicator changes from red to green when fully charged
- Folding carry handle
- Top and bottom reflectors
- Wire guard protects LED housing
- Crank handle for wind up

OPERATION

- Front-positioned ON/OFF button

ACCESSORIES

- AC and DC adaptors included



Box Dimensions

(H) 9.75" x (W) 5.5" x (D) 5.5"

SOLAR PANEL
Recycles Energy



WIND UP
Crank Handle

REFLECTOR
Distributes Light

FOLDING
Carry Handle



LED LANTERNS

BATTERY LED LANTERNS

WEATHERRITE® LED Lanterns are portable, reliable lanterns that are perfect for camping, fishing, hunting, boating, road trips, RVing, power outages, at-home use or any emergency situation.

DESIGN

- Water-resistant rubber & ABS base construction
- Cone-shaped reflector
- Comfort carry handle

OPERATION

- Front-positioned ON/OFF button

#5949 600 Lumen LED Lantern

- 3 light modes: High, Low & Flashing
- Glow-in-the-dark ON/OFF button
- 6 D batteries (not included)

#6004 130 Lumen LED Lantern

- 3 light modes: High, Low & Flashing
- Green beacon LED flashes when lantern is OFF
- 3 AA batteries included

#6005 300 Lumen LED Lantern

- 3 light modes: High, Low & Flashing
- Green beacon LED flashes when lantern is OFF
- 3 D batteries (not included)



#5949 Box Dimensions

(H) 9.75" x (W) 5.5" x (D) 5.5"

#6004 Box Dimensions

(H) 6.5" x (W) 2.75" x (D) 2.5"

#6005 Box Dimensions

(H) 7.5" x (W) 3.75" x (D) 3.5"

ECO LANTERN™ SPECIFICATIONS	
MAX. OUTPUT	157 Lumens
LIGHT COLOR	White
BODY MATERIAL	Water and impact-resistant
WEIGHT	3.678 lbs.
DIMENSIONS	(H) 9.125" x (D) 6" x (W) 5.5"
OPERATION	Front-positioned ON/OFF button
ACCESSORIES	AC and DC adaptors included

LED LANTERN SPECIFICATIONS		
#5949	MAX. OUTPUT	600 Lumens
	WEIGHT	3.5 lbs.
	DIMENSIONS	(H) 9.5" x (D) 4.5" x (W) 4.5"
#6004	MAX. OUTPUT	130 Lumens
	WEIGHT	0.5 lbs.
	DIMENSIONS	(H) 6.5" x (D) 2.25" x (W) 2.25"
#6005	MAX. OUTPUT	300 Lumens
	WEIGHT	1.85 lbs.
	DIMENSIONS	(H) 7.25" x (D) 3.375" x (W) 3.375"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397070122	5959	WEATHERRITE® ECO LANTERN™	26.50	49.99	4 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397060123	5949	600 Lumen LED Lantern	19.75	39.99	4 PIECES
044435915904	6004	130 Lumen LED Lantern	11.50	21.99	6 PIECES
044435916420	6005	300 Lumen LED Lantern	16.75	29.99	4 PIECES

15 LED LANTERN

BATTERY LED LANTERN

This 15 LED Lantern is the perfect blend between classic design and modern technology. This 9" high metal lantern has a wire-guard to protect the glass globe. No kerosene, no lamp oil and no citronella...this 15 LED is completely battery operated (batteries not included.) To maintain the functionality of a traditional kerosene lantern, this 15 LED Lantern has a control to adjust the amount of light that is generated. A reflector is positioned above the LEDs to cast the light evenly in every direction. Perfect for indoor or outdoor use, this lantern generates over 96 hours of continuous bright light. The 15 LED Lantern, the traditional lantern look with efficient LED lighting!

DESIGN

- Metal construction with wire-guarded glass globe
- Hanging hook
- 25 lumens
- 96 hours of continuous light
- Adjustable light output
- Powered by 2 D batteries (not included)



WIRE-GUARDED
Glass Globe

HANGING
Hook

ADJUSTABLE
Light Output



WIRE-GUARDED
Glass Globe

HANGING
Hook

ADJUSTABLE
Light Output



OIL LANTERN

OIL LANTERNS

The Oil Lantern captures a classic design and technology that has been around since 1850. This 12" high metal lantern has a wire-guard to protect the glass globe. The fuel tank is 12 oz., which provides 35 hours of burn time on a full tank. The Oil Lantern has a control to adjust the wick height and light output (2 wicks included.) This lantern can be used indoors to provide light during power outages, or to just add a warm glow to any room. Also perfect for outdoor use as well for camping, hunting or any outdoor recreational activity.

DESIGN

- Metal construction with wire-guarded glass globe
- Hanging hook
- 12oz. fuel capacity
- 35 hours of burn time
- Adjustable light output
- Uses kerosene, lamp oil or citronella oil ONLY
- Child-proof fuel tank cap
- Available in black and red



15 LED LANTERN SPECIFICATIONS

MAX. OUTPUT	25 Lumens
LIGHT COLOR	White
BODY MATERIAL	Water and impact-resistant
WEIGHT	0.9 lbs.
DIMENSIONS	(H) 9" x (D) 4.5" x (W) 4.5"
OPERATION	Front-positioned dial; adjustable light output

OIL LANTERN SPECIFICATIONS

HEIGHT	12"
WEIGHT	1.233
OPERATION	Fuel powered; adjustable light output

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
044435627104	5572	15 LED Lantern	6.50	12.99	4 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
044435915393	6048	Oil Lantern	3.75	8.99	4 PIECES



FLY FISHING KITS

TROUT COMBO OUTFIT

- ROD**
- 8'6" 5 piece 5 weight IM7 graphite fly rod
 - Premium cork handle
- REEL**
- Diecast aluminum frame and spool
 - Easily converts from right to left-hand retrieve
 - Large arbor disc drag fly reel
- LINE**
- 50 yards backing
 - Weight-forward fly line
 - Tapered leader
- CARRYING CASE**
- Cordura rod tube with zipper reel pocket and shoulder strap

FINE RIVER

- ROD**
- 9' 3 piece 5/6 weight rod
 - Natural cork handle
- REEL**
- Diecast; rim-controlled graphite spool and frame
 - Easily converts from right to left-hand retrieve
 - Fully loaded size 5/6 reel
 - 50 yards of 20# Deacron backing, WF5F, tapered leader
- FLY BOX**
- 7 piece custom fly assortment with case



7 PIECE FLY ASSORTMENT
with Case



Box Dimensions
(H) 29" x (W) 8.125" x (D) 3.125"



Box Dimensions
(H) 43.5" x (W) 3.5" x (D) 2.75"

TROUT COMBO OUTFIT SPECIFICATIONS	
WEIGHT	2.35 lbs.
DIMENSIONS	Assembled: (L) 8.5' Folded: (L) 1.75'
ACCESSORIES	Storage carry bag included

FINE RIVER FISHING KIT SPECIFICATIONS	
WEIGHT	1.5 lbs.
DIMENSIONS	Assembled: (L) 9' Folded: (L) 37.75"
ACCESSORIES	7 piece custom fly assortment with case

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
061317003566	5487	Quarrow® Trout Combo Outfit	68.95	119.99	5 PIECES
061317003733	5504	Quarrow® Fine River Fishing Kit	45.50	79.99	4 PIECES

There's more than one right choice for fishing accessories and gear. Quarrow® just happens to be the BEST choice. Quarrow® offers a wide variety of products essential to any fisherman... or woman, from fishing rods and reels to must-haves for the tackle box.



HANDS-FREE LIGHTING

96 LED Fishing Light

The Quarrow® Rechargeable 96 LED Fishing Light provides perfect lighting for any night fishing situation. The Fishing Light features 60 UV LEDs, 24 White LEDs and 12 Green LEDs. The UV LEDs (410-415nm) can reveal materials that are not seen through normal lighting; they are also perfect for night fishing to illuminate a fluorescent fishing line. Green LEDs are best used for map reading or signaling, especially in low light conditions. Also perfect for hunting as some game cannot see green light. This rechargeable light comes with an AC/DC charging cable. Perfect for night fishing, camping, hunting and much more.

LIGHT

- 60 UV LEDs
- 24 White LEDs
- 12 Green LEDs

DESIGN

- Aluminum die cast housing
- Light tilts 90° and rotates 360°
- Water and impact-resistant
- Soft, foam padded top carry handle
- Sturdy base

OPERATION

- Rear-positioned ON/OFF button

BATTERIES

- Powered by internal rechargeable battery

NEW!



THREE LIGHT MODES

- | | | |
|----------------------------------|----------------------|----------------------|
| 60 UV LEDs
(410-415nm) | 24 WHITE LEDs | 12 GREEN LEDs |
| • 4 Hours | • 80 LUMENS | • 20 LUMENS |
| • 20 Meters | • 6 Hours | • 10 Hours |
| | • 46 Meters | • 28 Meters |



#6206 Box Dimensions
(H) 8.5" x (W) 12.75" x (D) 6.25"



UNDERWATER FISHING LIGHTS

Submersible Fishing Lights

Quarrow® Submersible Fishing Lights initiate a food chain reaction that attract plankton, which then attract the fish you want to catch. The fish don't stand a chance.

DESIGN

- Impact-resistant and water-proof
- 12V DC battery clips included
- 15A protection fuse (0.2" x 0.79")
- 15' cable (0.2" diameter)
- Water-tight rubber caps

#6059 12 LED Submersible Fishing Light

- 12 green LEDs output 80 lumens
- (H) 5.6" x (W) 1.25"

#6060 36 LED Submersible Fishing Light

- 36 green LEDs output 250 lumens
- (H) 8.75" x (W) 1.25"

#6061 90 LED Submersible Fishing Light

- 90 green LEDs output 630 lumens
- (H) 12.25" x (W) 1.25"

#6062 180 LED Submersible Fishing Light

- 180 green LEDs output 1,250 lumens
- (H) 10.625" x (W) 1.25"

#6063 24 LED Submersible Fishing Light

- 36 green LEDs output 150 lumens
- (H) 8.75" x (W) 1.25"
- Powered by 3 AAA batteries (included)



WHY GREEN LIGHT?

The Quarrow® Submersible Fishing Light shines a bright green light directly into the water. The green light starts a natural food-chain reaction by attracting a concentration of small microscopic animals called plankton. Bait fish such as shad and minnows are drawn to the light to feed on the plankton and larger game fish move in to feed on the bait fish.

SUBMERSIBLE FISHING LIGHT SPECIFICATIONS

BODY MATERIAL	Impact-resistant; water-tight design
DIMENSIONS	#6059: (H)5.6" x (W)1.25" #6060: (H)8.75" x (W)1.25" #6061: (H)12.25" x (W)1.25" #6062: (H)10.625" x (W)1.25" #6063: (H)8.75" x (W)1.25"
ACCESSORIES	12V DC battery clips included (#6059 - #6062)

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
061317004396	6206	96 LED Fishing Light	34.95	69.99	2 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
061317004082	6059	12 LED Submersible Fishing Light	12.50	24.99	6 PIECES
061317004099	6060	36 LED Submersible Fishing Light	20.00	39.99	6 PIECES
061317004105	6061	90 LED Submersible Fishing Light	31.50	59.99	3 PIECES
061317004112	6062	180 LED Submersible Fishing Light	44.50	84.99	3 PIECES
061317004129	6063	24 LED Submersible Fishing Light - Battery	14.95	29.99	6 PIECES



HANDS-FREE LIGHTING

50 Lumen Cap Light

- High-power 50 lumen LED
- Run Time: 2 hours / Viewing Distance: 20 Meters
- Strong clip
- 360° rotation
- Non-corrosive aluminum body; water and impact-resistant
- Key ring attachment
- Rear-positioned glow-in-the-dark ON/OFF button
- Powered by 4 AG13 batteries (included)

70 Lumen Head Lamp

- High-power 70 lumen LED
- Run Time: 7 hours / Viewing Distance: 70 Meters
- Four light modes: White (70 lumens), 10 UV LEDs, 4 Green LEDs & White Flashing
- UV LEDs: 2-3 milliwatts / 410-415 nanometers
- Head tilts 90°
- Water and impact-resistant
- Two-way adjustable head strap
- Soft foam padding for non-slip comfort
- Powered by 3 AAA batteries (included)

80 Lumen Head Lamp

- High-power 80 lumen LED
- Run Time: 8 hours / Viewing Distance: 85 Meters
- 3 light modes: High, Low & Strobe
- Adjustable elastic head strap
- 60° Vertical Tilt
- Water and Impact-Resistant
- Powered by 3 AAA batteries (included)



STEEL
Hanging Loop



FISHING ACCESSORY LIGHTS

70 Lumen Handy Light

- High-power 70 lumen LED
- Run Time: 3 hours / Viewing Distance: 90 Meters
- 3 light modes: High, Low & Strobe
- 2-in-1 design; flashlight and lantern
- 4x adjustable zoom
- Expandable body design
- Convex lens
- Non-corrosive aluminum body; water and impact-resistant
- Water-resistant silicone rings
- Steel hanging loop
- Rear-positioned glow-in-the-dark ON/OFF button
- Powered by 1 AA battery (included)

Dual Color Rechargeable Light

- High-power 50 lumen color-changing LED (#6224 - White & Red / #6225 - White & Green)
- Run Time: 3 hours / Viewing Distance: 50 Meters
- 3 light modes (#6224) White / Red / Red Strobe (#6225) White / Green / Green Strobe
- 4x adjustable zoom
- Ni-MH rechargeable battery
- Anodized aircraft-grade aluminum
- Water and impact-resistant
- Recharging indicator
- 12V spring base
- Convex lens



#6202 Clamshell Dimensions
(H) 6.5" x (W) 5.25" x (D) 1.5"



#5492 Clamshell Dimensions
(H) 7.75" x (W) 5.75" x (D) 4.25"



#6203 Clamshell Dimensions
(H) 6.5" x (W) 5.25" x (D) 3.5"

#6205 Clamshell Dimensions
(H) 6.5" x (W) 5.25" x (D) 1.5"

#6224/#6225 Clamshell Dimensions
(H) 6.5" x (W) 5.25" x (D) 1.5"



70 LUMEN HANDY LIGHT SPECIFICATIONS	
WEIGHT	0.3 lbs.
DIMENSIONS	(L) 4" x (W) 1" x (D) 1"
BATTERIES	1 AA battery included
DUAL COLOR RECHARGEABLE LIGHT SPECIFICATIONS	
WEIGHT	0.125 lbs.
DIMENSIONS	(L) 4" x (W) 1.125" x (D) 1.125"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
061317004358	6202	50 Lumen Cap Light	5.50	10.99	6 PIECES
061317003610	5492	70 Lumen Head Lamp	8.95	16.99	12 PIECES
061317004365	6203	80 Lumen Head Lamp	7.50	14.99	4 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
061317004389	6205	70 Lumen Handy Light	7.50	14.99	4 PIECES
061317004457	6224	Dual Color Rechargeable Light (Red)	9.95	19.99	6 PIECES
061317004464	6225	Dual Color Rechargeable Light (Green)	9.95	19.99	6 PIECES



FISHING TOOLS

Turtle™ 8 Pocket Tool

The Quarrow® Turtle™8 Pocket Tool is another example of design colliding with innovation. When a tool belt or tool box is not around, just reach in your pocket and grab the essential tool...the Quarrow® Turtle™8. No bigger than your car keys the Turtle™8 can easily go with you wherever you go.

DESIGN

- Folding design features 8 tools in 1 compact design
- Pliers, Wire cutters, Wire stripper, File, Knife, Phillips Screwdriver, Flat-head screwdriver, Carabiner

Digital Fishing Scale


When fish size and weight are important, the Quarrow® Digital Fishing Scale gets the job done, regardless of lighting conditions. Equipped with a backlit LCD display, this scale is a perfect addition to any tackle box.

DESIGN

- Weighs up to 80 lbs. or 40 Kg.
- Accurate to within 0.1 lbs. / 0.05 Kg.
- Ergonomically designed
- Backlit digital LCD display
- Unit switches from Lb, Kg, Oz or Gram weights;
- Fast auto-locking / tare feature

BATTERIES

- Powered by 2 AAA batteries (included)



FOLDING Design



BACKLIT LCD Display



#5091 Clamshell Dimensions (H) 6.5" x (W) 5" x (D) 0.5"



#6084 Clamshell Dimensions (H) 7.8" x (W) 6.25" x (D) 1.875"

TURTLE™8 SPECIFICATIONS	
BODY MATERIAL	Water and impact-resistant stainless steel
WEIGHT	0.175 lbs.
DIMENSIONS	(H)4.625" x (W)2" x (D)0.27" Folded: (H)1.96" x (W)1.37" x (D)0.27"
DIGITAL FISHING SCALE SPECIFICATIONS	
BODY MATERIAL	Water and impact-resistant
WEIGHT	0.55 lbs.
DIMENSIONS	(L) 6.75" x (W)1.125" x (D)1.125"
BATTERIES	2 AAA batteries included

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
061317003023	5091	Quarrow® Turtle™8 Pocket Tool	3.50	6.99	24 PIECES
061317004266	6084	Quarrow® Digital Fishing Scale	7.95	15.99	6 PIECES

CUSTOM PRINTING & ENGRAVING

What's better than a NEBO® product?... One with your name on it!

NEBO® offers custom screen printing and laser engraving services on most all products. Utilize NEBO® products to advertise your company or event!



ADVERTISE YOUR COMPANY WITH OUR PRODUCTS!

Screen Printing Prices

- 100 - 499 pieces = Dealer price + \$2.00 per unit
- 500 - 999 pieces = Dealer price + \$1.50 per unit
- 1000+ pieces = Dealer price + \$1.00 per unit

Laser Engraving Prices

- 100 - 499 pieces = Dealer price + \$2.50 per unit
- 500 - 999 pieces = Dealer price + \$2.00 per unit
- 1000+ pieces = Dealer price + \$1.50 per unit

*There's a one-time \$35 fee (per custom print/engrave order), which includes the setup for either screen printing or laser engraving. This setup fee covers the logo/text printed in a single location on the product, using a single color. There's an additional charge for printing or laser engraving on multiple locations or printing in more than one color.



CUSTOM PRINTING & ENGRAVING FAQs

QUANTITY REQUIREMENTS

Custom printing orders must be a minimum of 100 pieces.

LEAD TIME

Allow 15-20 business days for production time.

SHIPPING

All orders ship FOB Grand Prairie, TX. Prepaid DOES NOT apply for custom print orders.


PAYMENT

Orders will not be released for printing until payment has been received in full, via credit card or CIA.

Contact Your Sales Rep or 800-255-6061 for Additional Information!

FAQ

Frequently Asked Questions



Who is Alliance Sports Group?

Alliance Sports Group is the parent company of NEBO® Tools, NEBO® Sports, iPROTEC™ Firearm Accessories, Bollinger® Fitness, So-laire® TrimWear, WeatherRite® Outdoor, Quarrow® Fishing and most recently, True Utility®.

What does NEBO® mean?

NEBO is mentioned in the Bible as the burial site of Moses. There is an excellent view of "The Promised Land" from Mt. NEBO. NEBO is also a mountain in Utah near where NEBO® Tools originated.

Can I order online?

Yes. Go to nebotools.com to purchase products at retail or sign up to become a dealer. Credit card orders only.

Can I order less than a case pack?

Yes. Go to nebotools.com to purchase products in any quantity that you like at retail price.

Why does NEBO® offer countertop displays?

NEBO® products sell much faster in display packaging when it's placed on counters and end-caps because this allows customers to try the product before buying it.

Do you carry any product in clamshell packaging?

Most NEBO® products are also available in clamshell packaging.

Are batteries included in your products?

All flashlights, cap-lights, head lamps and multi-tools that require batteries have batteries included.

Are lasers safe and legal?

Lasers of all types are regulated by the FDA. All lasers used in NEBO® flashlights meet the required standards and have the appropriate warnings to avoid direct eye contact with any laser.

Are NEBO® products waterproof?

Some NEBO® products are waterproof, however most are water-resistant. Please see product details for further information.

Which iPROTEC™ product will fit my gun?

The list of firearms is far too vast to know for sure. That is why we've designed our products to have a universal rail or barrel mount. The dimension specs for each of our iPROTEC™ items is listed on nebotools.com.

Customized products with your logo?

The minimum order quantity is 100 pieces for most items. Lead time is 15-20 days. Refer to page 87 or contact your NEBO® sales representative for more information.

Does NEBO® offer a warranty for its products?

Yes, NEBO® stands behind its products with a 1 year limited manufacturer's warranty. Any item that does not perform properly due to a manufacturer's defect can be returned for a warranty replacement. Warranty does not cover normal wear and tear or batteries. Contact warranty@nebotools.net or 800.255.6061.

How do I get free freight?

First time orders receive free freight (not valid for online orders). Secondary orders exceeding \$600 (\$300 in Texas, Arkansas, Louisiana and Oklahoma) also receive free freight*. Alaska* and Hawaii* customers: ASG will pay freight to the furthest point within the 48 states, then customer is PPA from that point to final ship to location.

Do you accept credit card payments?

Yes. Visa, Mastercard, American Express and Discover

What are my payment terms?

Cash in Advance, NET 30 with approved ASG credit application

Where do I send my payment?

Alliance Sports Group, PO Box 203246, Dallas, TX 75320-3246

Who do I make the check payable to?

Alliance Sports Group

Do you send out monthly statements?

Yes, we send them out at the end of each month.

Can I get my invoices and statements emailed to me?

Yes. Just email a request to accounting@nebotools.net and your invoice/statement will be emailed back to you.

How will my order be shipped (UPS, FedEx, USPS)? How Long will it take to receive my order?

We use UPS, FedEx and USPS. After being processed,* all orders, unless otherwise specified, are shipped standard or ground service which takes approximately 3-5 business days. *Please allow 48-72 hours for order to be processed.

Will I be notified when my product ships?

Yes, a confirmation email will be sent to you when you place your order online. An email with tracking information gets sent out with all orders when they ship.

If an item is out of stock, do you back order the item or wait and ship the order complete?

We back order any items that are out of stock rather than waiting for the remaining items to come in stock.

What is your address for returns? Do you pay the return freight?

Alliance Sports Group, 3025 N. Great Southwest Parkway, Grand Prairie, TX 75050. ASG pays return freight when a Return Authorization has been issued by ASG.

How can I get a call tag/return an item?

Contact your sales rep or corporate office warranty@nebotools.net or 800.255.6061

What is NEBO's® MAP (Minimum Advertised Price) Policy?

The advertised price PLUS any shipping charges paid by the consumer must be within 10% of the Suggested Retail Price. We reserve the right to stop providing product to all sellers that do not comply. A full download-able version of the MAP Policy can be found at our website, www.nebotools.com.

LIGHTING 101

GAUGING LED PERFORMANCE

Measuring the brightness of light is not a very straight-forward task. Currently, the most common measure of brightness is the lumen rating. Lumens replaced the old wattage-rating system because modern lights consume far less power and are much brighter.

A single lumen is the measure of energy that's released from a light. Imagine putting a transparent bubble around a light bulb and being able to measure all of the energy that flows through the bubble — this is how lumens are measured.


At NEBO®, we don't live in a bubble and we know that as lighting technology advances, so must the tools used to gauge

the performance. Thus, many of our flashlights are now gauged by lux instead of lumens. Lux isn't a measurement of the amount of energy released — it's a measure of how much light is actually hitting your target.


We've recently introduced flashlights that have advanced optics designed to maximize energy efficiency by tightly focusing the beam of light. So you can light up the mystery across the field without wasting energy by lighting the ground at your feet.

At NEBO® we make flashlights that are designed to meet real-life applications and we use advanced engineering to create lighting products that conserve energy yet blast a powerful beam of light.

MEASURING POWER:



MEASURING BRIGHTNESS:



RATING PERFORMANCE BY PRODUCT TYPE:


LANTERNS & WORK LIGHTS

These lighting products are designed to illuminate the area around — just like a household light bulb. Since light bulbs are rated in lumens, lantern output is rated using lumens.



CLASSIC FLASHLIGHTS

Classic flashlights illuminate the area directly in front of us — mimicking a light-post fixture, so it's appropriate to also rate these products using lumens.



LONG-RANGE FLASHLIGHTS

These flashlights feature specialized optics with zoom capabilities that are designed to project an intense beam of light at a distance. Lumen ratings ignore the use of specialized optics and fail to provide a clear representation of beam distance or brightness. Lux on the other hand, measures the amount of light actually hitting the target.



FOCUSING THE INTENSITY

The natural tendency of light is to disperse. We use patented O² Technology™ to focus the light's intensity by bending it toward the center of the beam.

The result — a hotter, brighter spotlight with the lowest power consumption.



STANDARD BEAM DISTANCE

O² TECHNOLOGY™ DOUBLES THE BEAM DISTANCE

A BEAM OF LIGHT SO POWERFUL, YOU HAVE TO SEE TO BELIEVE!

DEFINITIONS

High-Powered LEDs

These LEDs produce a more intense light that travels a further distance than cluster LEDs. Conversely, these also use more power than clusters do.

Cluster LEDs

These LEDs consume less power while still providing a bright light. They tend to produce a wide angle of light and are better used for short range lighting to illuminate your immediate area.

Adjustable Focus

The adjustable focus feature allows the user to change the focus of the light beam from a spot light (a sharply focused beam of light that illuminates more distant areas) to a flood light (a broad circular beam of light that illuminates larger, close-up areas.)

Convex Lens

The convex lens evenly distributes the light for a highly concentrated beam without dull or dark spots, as most traditional flashlights have.

Green LEDs

Because the human eye recognizes the color green faster than other colors, green light is used for map reading or signaling, especially in low light conditions. Also perfect for hunting as some game cannot see green light.

UV LEDs

These can reveal materials that are not seen through normal lighting and can be very useful in the following applications:

- Crime scene investigation to reveal certain bodily fluids
- Rodent and pet stain detection
- Document analysis and currency verification
- Gemstone verification
- Leak detection (i.e. Freon)

Red LEDs

Red light is primarily used to preserve night vision. Best used for low-light or nighttime situations, the low-signature red light provides great contrast making it easier to read charts and maps. Police and military units utilize the red LED for night operations because it will not interfere with night vision technology and cannot be seen by the human eye over long distances. Fire rescue units also use the red LED because it provides better visibility in smoky situations than white light.

Red Laser Pointer

Class IIIa lasers are used in all of our laser products. All red lasers have a maximum output of <5mW with a wavelength of 650nm +/- 10. Laser pointers work well in a variety of situations. Laser pointers can be used as a sighting tool for weapons, or more commonly used to point to an object that is out of reach.

Note: Directing laser at eyes can cause serious damage. (All laser pointers comply with 21 CFR 1040.10, 1040.11 & Ch. 1, Subchapter J)

Green Laser Pointer

Class IIIa lasers are used in all of our laser products. All green lasers have a maximum output of <5mW with a wavelength of 523nm. Green lasers are more sensitive to temperature, but they work better for day time applications.

Note: Directing laser at eyes can cause serious damage. (All laser pointers comply with 21 CFR 1040.10, 1040.11 & Ch. 1, Subchapter J.)

Hands-Free Lighting

Hands-Free lighting allows the user to illuminate a desired area while maintaining the use of both hands. We use clips, straps and magnets to give hands-free options with some of our products.

Lighting Modes

Our advanced circuitry allows for variable brightness control and lighting flash sequence with a simple touch of a switch that regulates the lighting mode. By decreasing brightness you can extend the run time of the battery.

Defensive Strobe Lighting Mode

Perfect for signaling, the defensive strobe mode can also be used to disorient an attacker or animal by shining it at them. Please use with caution when doing this.

S.O.S. Lighting Mode

S.O.S. is the commonly used description for the international Morse Code distress signal. The code for S.O.S. is 3 short, 3 long and 3 short signals. The S.O.S. sequence will repeat until the setting is changed or the light is turned off.

Run Time

We give run time information for each of our products to help you understand how long each product will perform the way you need it to. We use energy efficient methods to ensure the longest run times.

UPC CODE	ITEM	NEBO® Tools	DISPLAY	COST	MSRP	CASE PACK	PAGE #
Flashlights and Lighting							
645397128007	5077	CSI Tactical 8 LED Flashlight with Laser	Clamshell	\$7.50	\$14.99	18 PIECES	40
645397900108	5112	CSI LUMA 50™ Flashlight	Display	\$4.95	\$9.99	24 PIECES	38
645397900306	5423	BENDBRITE™ Hands-Free Flex Light	Display	\$5.60	\$9.99	16 PIECES	41
645397900702	5519	EDGE™ 50 Lumen Flashlight	Display	\$4.95	\$9.99	24 PIECES	36
645397401100	5557	REDLINE® Flashlight	Display	\$17.25	\$34.99	14 PIECES	32
645397430100	5561	CSI QUATRO™ Flashlight	Clamshell	\$16.75	\$29.99	12 PIECES	39
645397531111	5581	REDLINE® Flashlight	Clamshell	\$17.25	\$34.99	12 PIECES	32
645397122111	5599	REDLINE® Flashlight (Gray)	Bulk	\$16.50	\$34.99	18 PIECES	32
645397421115	5604	LUMIÈRE™ Flashlight	Display	\$5.75	\$9.99	24 PIECES	38
645397111115	5610	REDLINE® Flashlight (Black)	Bulk	\$16.50	\$34.99	18 PIECES	32
645397929116	5614	LUMIÈRE™ Flashlight	Clamshell	\$5.75	\$9.99	24 PIECES	38
645397312116	5615	SE REDLINE® Flashlight	Display	\$19.50	\$39.99	14 PIECES	31
645397914112	5616	SE REDLINE® Flashlight	Clamshell	\$19.50	\$39.99	12 PIECES	31
645397111276	5620	REDLINE® Select Flashlight (Black)	Display	\$26.50	\$49.99	9 PIECES	30
645397010128	5633	CSI Tactical 8 LED Flashlight with Laser	Display	\$7.50	\$14.99	18 PIECES	40
645397015123	5638	SE REDLINE® (Black)	Bulk	\$18.75	\$39.99	18 PIECES	31
645397107125	5872	CSI EDGE™ 90 Flashlight	Display	\$6.50	\$12.99	24 PIECES	36
645397057123	5946	JAG™ Flashlight	Display	\$12.75	\$24.99	18 PIECES	35
645397058120	5947	ZOOM™ 370 LUX Flashlight	Display	\$5.60	\$11.99	16 PIECES	37
645397066125	5955	REDLINE® Select Flashlight (Titanium)	Display	\$26.50	\$49.99	9 PIECES	30
645397067122	5956	SE REDLINE® Flashlight (Gray)	Bulk	\$18.75	\$39.99	18 PIECES	31
645397929185	6000	O² BEAM™ Flashlight	Display	\$55.00	\$99.99	4 PIECES	26
645397929215	6003	90 Lumen Head Lamp	Clamshell	\$10.20	\$19.99	6 PIECES	42
645397929222	6006	Larry™ 2 12 LED Work Light	Display	\$8.80	\$15.99	24 PIECES	23
645397929345	6051	Larry™ 2 12 LED Work Light (Orange)	Bulk	\$8.50	\$15.99	12 PIECES	23
645397929352	6052	Larry™ 2 12 LED Work Light (Gray)	Bulk	\$8.50	\$15.99	12 PIECES	23
645397929369	6053	Larry™ 2 12 LED Work Light (Black)	Bulk	\$8.50	\$15.99	12 PIECES	23
645397929376	6054	Larry™ 2 12 LED Work Light (Green)	Bulk	\$8.50	\$15.99	12 PIECES	23
645397929383	6055	Lucy™ 2 12 LED Work Light (Pink)	Bulk	\$8.50	\$15.99	12 PIECES	23
645397929475	6085	EDGE 200™ Flashlight	Display	\$8.80	\$15.99	20 PIECES	36
645397929499	6092	REDLINE® OC™ Flashlight	Display	\$11.50	\$19.99	16 PIECES	33
645397929529	6095	LUMO™ Clip Light	Display	\$2.98	\$5.99	48 PIECES	34
645397929857	6156	SLYDE™ 440 Lumen Flashlight & Work Light	Display	\$16.75	\$29.99	16 PIECES	21
645397929864	6157	LUMO™ Clip Light (Red)	Bulk	\$2.70	\$5.99	12 PIECES	34
645397929871	6158	LUMO™ Clip Light (Silver)	Bulk	\$2.70	\$5.99	12 PIECES	34
645397929888	6159	LUMO™ Clip Light (Blue)	Bulk	\$2.70	\$5.99	12 PIECES	34
645397929895	6160	LUMO™ Clip Light (Black)	Bulk	\$2.70	\$5.99	12 PIECES	34
645397930013	6189	REDLINE® Select RC Flashlight	Display	\$38.50	\$69.99	6 PIECES	29
645397930068	6194	Larry™ Silver™ 8 LED Work Light	Display	\$11.50	\$19.99	16 PIECES	22
645397930099	6227	PaL Power and Light Flashlight	Display	\$11.75	\$19.99	18 PIECES	24
645397930112	6267	SLYDE™ Z	Display	\$28.50	\$49.99	8 PIECES	20
645397930167	6272	Micro REDLINE® OC™ Flashlight	Display	\$7.90	\$14.99	16 PIECES	27
645397930174	6273	Classic REDLINE® OC™ Flashlight	Display	\$16.50	\$29.99	12 PIECES	28
645397930242	6294	SEVEN-Z™ 770 Lumen Flashlight	Display	\$36.00	\$69.99	6 PIECES	17
645397930266	6296	TWYST™ Work Light, Lantern & Flashlight	Display	\$27.50	\$49.99	10 PIECES	16
645397930341	6304	WORKBRITE 2™ C-O-B LED Work Light	Display	\$11.75	\$19.99	12 PIECES	18
645397930358	6305	The Rechargeable WORKBRITE 2™	Display	\$16.50	\$29.99	12 PIECES	19
645397930365	6306	BIG Larry™ Power C-O-B LED Work Light	Display	\$12.75	\$24.99	14 PIECES	2-3
645397930396	6311	TRANSPORT® 12V DC Rechargeable Flashlight	Display	\$11.50	\$19.99	18 PIECES	25
645397930402	6327	Larry™ C C-O-B LED Work Light	Display	\$4.95	\$8.99	24 PIECES	8-9
645397930419	6328	TWYST™ Work Light, Lantern & Flashlight (Black)	Display	\$27.50	\$49.99	10 PIECES	16
645397930426	6329	LuMORE™ Clip Light	Display	\$3.15	\$5.99	48 PIECES	14-15
645397930433	6347	CaseBrite™ iPhone 6/6S Case + Light (Black)	Bulk	\$24.00	\$39.99	4 PIECES	4-5
645397930440	6348	CaseBrite™ iPhone 6/6S Plus Case + Light (Black)	Bulk	\$24.00	\$39.99	4 PIECES	4-5
645397930457	6349	CaseBrite™ Countertop Display	Display	FREE with 12 piece order		1 PIECE	4-5
645397930464	6350	Larry™ C C-O-B LED Work Light - Bulk Red	Bulk	\$4.75	\$8.99	12 PIECES	8-9
645397930471	6351	Larry™ C C-O-B LED Work Light - Bulk Blue	Bulk	\$4.75	\$8.99	12 PIECES	8-9
645397930488	6352	Larry™ C C-O-B LED Work Light - Bulk Gray	Bulk	\$4.75	\$8.99	12 PIECES	8-9
645397930495	6353	Larry™ C C-O-B LED Work Light - Bulk Yellow	Bulk	\$4.75	\$8.99	12 PIECES	8-9
645397930501	6354	Larry™ C C-O-B LED Work Light - Bulk Camo	Bulk	\$4.95	\$8.99	12 PIECES	8-9
645397930518	6355	Lucy™ C C-O-B LED Work Light - Bulk Pink	Bulk	\$4.75	\$8.99	12 PIECES	8-9
645397930525	6357	LuMORE™ Clip Light - Bulk White	Bulk	\$2.98	\$5.99	12 PIECES	14-15
645397930532	6358	LuMORE™ Clip Light - Bulk Red	Bulk	\$2.98	\$5.99	12 PIECES	14-15
645397930549	6359	LuMORE™ Clip Light - Bulk Blue	Bulk	\$2.98	\$5.99	12 PIECES	14-15
645397930556	6360	LuMORE™ Clip Light - Bulk Green	Bulk	\$2.98	\$5.99	12 PIECES	14-15
645397930563	6372	TWYST™ Z Work Light, Lantern & Flashlight	Display	\$16.50	\$29.99	16 PIECES	6-7
645397930648	6382	BIG Larry™ C-O-B LED Work Light - Bulk Camo	Bulk	\$12.75	\$24.99	7 PIECES	2-3

Flashlights and Lighting - Continued							
645397930662	6383	SLYDE™ Flashlight & Work Light - Bulk Camo	Bulk	\$17.25	\$29.99	8 PIECES	21
645397930679	6384	BIG Larry™ C-O-B LED Work Light - Bulk Black	Bulk	\$12.50	\$24.99	7 PIECES	2-3
645397930686	6385	BIG Larry™ C-O-B LED Work Light - Bulk Silver	Bulk	\$12.50	\$24.99	7 PIECES	2-3
645397930693	6386	CaseBrite™ iPhone 6/6S Case + Light (White)	Bulk	\$24.00	\$39.99	4 PIECES	4-5
645397930709	6387	CaseBrite™ iPhone 6/6S Plus Case + Light (White)	Bulk	\$24.00	\$39.99	4 PIECES	4-5
645397930747	6391	Twin Pucks Task Light & Emergency Beacon	Display	\$11.50	\$19.99	12 PIECES	12-13
645397930754	6392	REDLINE® RC™ with MagDock	Display	\$21.98	\$39.99	10 PIECES	10-11
645397930792	6413	BIG Larry™ C-O-B LED Work Light - Bulk Red	Bulk	\$12.50	\$24.99	7 PIECES	2-3
645397930808	6414	SEVEN-Z™ 770 Lumen Flashlight - Camo	Display	\$36.75	\$69.99	6 PIECES	17

Tools							
645397130406	4327	Ultra™ Socket Combination Kit	Box	\$13.45	\$19.99	12 PIECES	45
645397850892	5089	CSI Flashlight Holster	Display	\$2.20	\$3.99	10 PIECES	46
645397900504	5517	Folding Lock-Blade Utility Knife with Carabiner	Display/Clam	\$3.98	\$6.99	18 PIECES	43
645397610113	5606	14-in-1 Ultra™ Socket	Display	\$9.95	\$16.99	12 PIECES	44
645397035121	5922	Leather Flashlight Holster	Hang Tag	\$8.50	\$16.99	6 PIECES	46
645397069126	5958	Flashlight Holster	Hang Tag	\$3.20	\$6.99	10 PIECES	46
645397929284	6032	Flashlight Holster with Belt Loop	Display	\$3.50	\$6.99	10 PIECES	46
645397930181	6274	Flashlight Holster	Hang Tag	\$3.50	\$6.99	6 PIECES	46
645397930761	6393	BIG Larry™ Flashlight Holster	Bulk	\$2.50	\$4.99	7 PIECES	2-3

UPC CODE	ITEM	True Utility®	DISPLAY	COST	MSRP	CASE PACK	PAGE #
16HKROTATING		16 Hook Rotating Display	N/A	\$49.99	N/A	1 PIECE	61
5060063221588	TU192	ClipTool	HardCase	\$6.75	\$12.99	6 PIECES	53
506006322202	TU200US	FIXR™ - 20 Tools in 1	Box	\$7.95	\$14.99	18 PIECES+DEMO	50-51
5060063220864	TU215	NailClip Kit	HardCase	\$5.25	\$9.99	6 PIECES	55
5060063229843	TU231	MiniDriver	HardCase	\$4.90	\$9.99	6 PIECES	58
5060063221243	TU236	SlimClips	HardCase	\$4.90	\$9.99	6 PIECES	60
5060063221991	TU238	sciXors+®	HardCase	\$4.75	\$9.99	6 PIECES	52
5060063221267	TU241	CashStash	HardCase	\$4.00	\$7.99	6 PIECES	57
5060063221298	TU242	MicroTool	HardCase	\$4.90	\$9.99	6 PIECES	59
5060063221328	TU245	KeyRing System	HardCase	\$4.90	\$9.99	6 PIECES	56
5060063221335	TU246	TelePen	HardCase	\$4.90	\$9.99	6 PIECES	57
5060063221342	TU247	KeyTool	HardCase	\$4.50	\$9.99	6 PIECES	54
5060063221359	TU248	Twistick®	HardCase	\$3.95	\$7.99	6 PIECES	53
5060063221441	TU262	FireStash	HardCase	\$4.90	\$9.99	6 PIECES	59
5060063221557	TU283S	Compact MicroLite	HardCase	\$4.75	\$9.99	6 PIECES	55
5060063222066	TU284	TinyTorch	HardCase	\$4.50	\$8.99	6 PIECES	58
5060063222073	TU285	NanoLite	HardCase	\$4.90	\$9.99	6 PIECES	60
5060063222493	TU290B	Micro USB MobileCharger	HardCase	\$4.90	\$9.99	6 PIECES	54
5060063221465	TU571	SkeletonKnife	HardCase	\$5.90	\$11.99	6 PIECES	56
5060063221472	TU573	SmartKnife	HardCase	\$6.98	\$14.99	6 PIECES	52
5060063221472	TU573DSP	SmartKnife Display	Display	\$6.98	\$14.99	18 PIECES+DEMO	52
5060063223988	TU579	Clipster	Display	\$7.95	\$14.99	16 PIECES	48-49

UPC CODE	ITEM	NEBO® Sports	DISPLAY	COST	MSRP	CASE PACK	PAGE #
645397819103	5576	6 White LED Bike Light	Clamshell	\$6.90	\$13.99	6 PIECES	64
645397812111	5611	250 PSI Air Compressor	Clamshell	\$9.80	\$19.99	12 PIECES	66
645397120018	5624	REDLINE® with Universal Bar Mount	Clamshell	\$19.50	\$39.99	6 PIECES	63
645397063124	5952	5 Red LED Rear Bike Light	Clamshell	\$4.95	\$9.99	6 PIECES	65
645397064121	5953	Bike Light Combo	Clamshell	\$12.20	\$24.99	6 PIECES	65

UPC CODE	ITEM	WEATHERRITE® Outdoor	DISPLAY	COST	MSRP	CASE PACK	PAGE #
044435627104	5572	15 LED Lantern	Hang Tag	\$6.50	\$12.99	4 PIECES	70
645397060123	5949	600 Lumen Lantern	Box	\$19.75	\$39.99	4 PIECES	69
645397070122	5959	ECO-Lantern™	Box	\$26.50	\$49.99	4 PIECES	68
044435915904	6004	130 Lumen Lantern	Box	\$11.50	\$21.99	6 PIECES	69
044435916420	6005	300 Lumen Lantern	Box	\$16.75	\$29.99	4 PIECES	69
044435915393	6048	Oil Lanterns (Red & Black)	Hang Tag	\$3.75	\$8.99	4 PIECES	71

UPC CODE	ITEM	Quarrow® Fishing	DISPLAY	COST	MSRP	CASE PACK	PAGE #
061317003023	5091	Turtle™ 8-in-1 Pocket Tool	Clamshell	\$3.50	\$6.99	24 PIECES	78
061317003566	5487	Trout Combo Outfit	Box	\$68.95	\$119.99	5 PIECES	73
061317003610	5492	70 Lumen Head Lamp	Clamshell	\$8.95	\$16.99	12 PIECES	76
061317003733	5504	Fine River Fishing Kit	Box	\$45.50			

NEBO® GUARANTEED BUYBACK PROGRAM

NEBO® absolutely guarantees your success with our products! Just place an order and use the P.O.P. displays to merchandise the products near your checkout area. You will be invoiced for the goods and payment is due within the agreed-upon terms.

Our promise to you is that, if (after 90 days from the time your product was received) the products from our display have not sold at least 80% of the case quantity, NEBO® will "BUYBACK" the remaining unsold merchandise and pay the freight to ship it back to our warehouse.

This offer stands firm for up to 6 months from the receipt of the merchandise.

At NEBO®, we like for our customers to get the most from their experience with us. These NEBO® special giveaway products are our way of saying, 'Thank you!' Place your order now to get these great giveaway products!

NEBO® GIVEAWAY

\$250 Order:

- 1 set of NEBO® Socks
- *Set equals 1 pair of each (White & Black)

\$750 Order:

- 1 set of NEBO® Socks
- *Set equals 1 pair of each (White & Black)
- 1 NEBO® CaseBrite™ iPhone Case + Light (6, 6S, 6 Plus or 6S Plus) (Black or White)

\$1500 Order:

- 1 set of NEBO® Socks
- *Set equals 1 pair of each (White & Black)
- 1 NEBO® CaseBrite™ iPhone Case + Light (6, 6S, 6 Plus or 6S Plus) (Black or White)
- 1 NEBO® 'I.T.W.' T-Shirt (Sizes M-XXL)

GIVEAWAYS

- #6289 NEBO® Socks (White No Show)
- NEBO® Socks (Black Crew Cut)
- #6347 CaseBrite™ iPhone 6/6S Case + Light (Black)
- #6348 CaseBrite™ iPhone 6/6S Plus Case + Light (Black)
- #6386 CaseBrite™ iPhone 6/6S Case + Light (White)
- #6387 CaseBrite™ iPhone 6/6S Plus Case + Light (White)
- #5115 NEBO® 'Illuminate the World' T-Shirt (M)
- #5116 NEBO® 'Illuminate the World' T-Shirt (L)
- #5117 NEBO® 'Illuminate the World' T-Shirt (XL)
- #5118 NEBO® 'Illuminate the World' T-Shirt (XXL)



The giveaway offer is valid until December 31, 2016 Net 30 with approved credit. The above promotions are valid while supplies last. Actual product style may vary from picture shown. Customer must choose only one applicable giveaway offer per order.

CALL TOLL FREE: 800-255-6061 or VISIT OUR WEBSITE: WWW.NEBOTOOLS.COM

For more information or to place an order, contact your NEBO® Tools sales representative.