

**KING**  
**INNOVATION®**  
Making your job easier.

# 2014

PRODUCT GUIDE



Irrigation




Electrical



Gas Utility



Water & Sewer



Cathodic  
Protection



Telecom

# Employee Highlights



**Tammy Donnelly-** Senior Accountant

Years at King: 14

**Favorite Core Value:** We know that taking personal responsibility creates trust  
**Why:** "The accounting team has worked together for more than 13 years and have created a trust in knowing that we are there for each other and the company in all diversities."



**James C. Keeven-** Technical Director

Years at King: 13

**Favorite Core Value:** We are passionate about challenging the status quo in every facet of our lives.  
**Why:** "When it comes to new product concepts and development, my team gets excited about pushing the limits of what is possible. The first solution is almost never the best solution, and the reward that comes after overcoming a challenge is all the more satisfying."



**Carol Horner-** Manufacturing Team Leader

Years at King: 13

**Favorite Core Value:** We don't give up, we don't back down, we won't go away.  
**Why:** "We 'cannot' and we 'will not' are NEVER in our vocabulary. When we get a last minute order, our only thought is how can we do whatever it takes to produce these items on time and with 100% quality."



**Andrea Nicolay-** Sales Concierge

Years at King: 12

**Favorite Core Value:** We have a deep rooted obsession with solving our customer's problems  
**Why:** "In customer service we go to every length to make sure that our customers are satisfied with the product and service they receive from King Innovation. We rely on our customers letting us know and giving us feedback to make our products and service the best they can be."



**Justin McKinney-** VP of Sales and Marketing

Years at King: 3

**Favorite Core Value:** We are fiercely innovative.  
**Why:** "The word 'Innovation' is in our name, but it wasn't chosen as a marketing ploy or some other sales tactic. It's in us... all of us. I'm continually amazed at and grateful for all of the creative solutions and ideas generated throughout our entire organization. Stay tuned, we've barely scratched the surface!"



**Anthony Pickens-** Manufacturing Team Member

Years at King: 1

**Favorite Core Value:** Quality is who we are  
**Why:** "Excellence is how we autograph our work... Made in the USA!"



## Herb's Corner

**Herb King-** CEO

**Herb's Big News:** Herb was the recipient of the Frost and Sullivan award for "Visionary Innovation." Congratulations Herb!





# Table of Contents

## DRYCONN® WATERPROOF CONNECTORS

Black Series.....	4
LED Outdoor Lighting.....	4
Dry-Crimp.....	5
KSC (King Shrink Crimp).....	5
DB Power Connect.....	6
Low Voltage.....	6
GTSR (Grease Tube w/Strain Relief).....	6
DBT-600 & DBR/Y-600.....	7
DBYN-600 & DBO/B-600.....	7
HSC (Heat Shrink Crimp).....	7
Direct Bury.....	8
Aqua Series.....	9
VisiLock® w/SmartGel®.....	15
King 6 Yellow, Blue, Orange .....	16
DBSR Yellow, Aqua, Orange .....	16
DB Lug Yellow, Aqua, Orange .....	17
Split Bolt Housing Yellow, Aqua, Orange.....	17
<b>ACE CONNECTORS™</b> .....	5
<b>GORILLA NUTS®</b> .....	10,11
<b>CONTRACTORS' CHOICE™</b> .....	12,13
<b>ALUMICONN®</b> .....	14
<b>SIPHON KING® UTILITY PUMPS</b>	
Siphon King Utility Pumps.....	18
Siphon King Gas Powered Pump.....	19
Siphon King Replacement Parts.....	19
<b>SNAPTAP® SADDLES</b> .....	20
<b>KING DRAINS®</b> .....	21
<b>SAPLING SOAKER™</b> .....	22
<b>BALL BEARING PROBE</b> .....	22
<b>LEAK-B-GONE™ PVC LEAK STOPPER RING</b> .....	23
<b>GRIPS &amp; REPLACEMENT PARTS</b>	
King Grips®.....	23
Mesh Grips.....	23
<b>TOOLS</b> .....	24,25
<b>ACCESSORIES</b> .....	26,27,28
<b>CLOTHING</b> .....	29
<b>WIRE COMBINATIONS</b> .....	30,31
<b>MERCHANDISING ITEMS</b> .....	32,33,34,35
<b>ENGINEERING HOTLINE</b> .....	35
<b>KING'S CORE VALUES</b> .....	36

## Icon Legend



Irrigation



Landscape Lighting



Direct Bury



Golf



Electrical



Gas Utility



Water & Sewer



Cathodic Protection



Telecom



For use with all applications listed above



Made in USA

## Contact Info:

King Innovation  
42 N. Central Drive  
O'Fallon, MO 63366

Phone:  
800.633.0232

Fax:  
636.519.5410

Engineering Hotline:  
1.877.771.8885

Email:  
customerservice  
@kinginnovation.com

Websites:  
www.kinginnovation.com  
www.gorillanuts.com





## DRYCONN® WATERPROOF CONNECTORS

### Black Series The Original Black Connector\*

- UL 486D Listed and 600V rated
- Pre-filled with dielectric silicone sealant that never hardens
- Waterproof and corrosion proof
- One-step® installation saves time and money
- No pre-twisting required
- For use in Irrigation, Landscape Lighting and Direct Bury applications

**Black/White**  
Min #22/Max #12



**Black/Gray**  
Min #22/Max #8



**Black/Blue**  
Min #14/Max #6



**PERFECT  
FOR LED  
APPLICATIONS!**

**Black/Green**  
Min #22/Max #8



- SKU# 61135 Black/White- Bag of 25
- SKU# 61145 Black/White- Bag of 100
- SKU# 61146 Black/White- Canister of 150
- SKU# 61148 Black/White- Canister of 500
- SKU# 61235 Black/Gray- Bag of 20
- SKU# 61241 Black/Gray- Canister of 100
- SKU# 61242 Black/Gray- Canister of 500
- SKU# 61245 Black/Gray- Bag of 100
- SKU# 61335 Black/Blue- Bag of 10
- SKU# 61345 Black/Blue- Bag of 50
- SKU# 61350 Black/Blue- Canister of 50
- SKU# 61435 Black/Green- Bag of 20
- SKU# 61441 Black/Green- Canister of 100

**\*THE COLOR BLACK IS A  
TRADEMARK OF KING INNOVATION**

#### MADE IN USA

U.S. Pat. 5,771,578 and additional Patents Pending apply. All other trademarks, U.S. and Foreign Patents apply. All Rights Reserved.



DryConn Black/Gray  
product bag



DryConn Black/  
White product  
canister



For more information,  
scan here.



## DRYCONN® WATERPROOF CONNECTORS

### DBSR® Black Medium Direct Bury Twist-on w/Strain Relief

- UL 486D Listed and 600V rated
- Waterproof and corrosion proof
- Pre-filled with dielectric silicone sealant that never hardens
- Easy latch lid provides strain relief
- Perfect for direct bury, low voltage lighting and irrigation systems

SKU# 63415 DBSR Black Medium- Canister of 15  
SKU# 63475 DBSR Black Medium- Box of 100



### DBSR Black Medium Min #22/Max #6

**MADE IN USA**

U.S. Pat. 7,170,005, 5,771,578, 6,815,616, 7,122,742 and additional Patents Pending apply. All other trademarks, U.S. and Foreign Patents Pending apply. All Rights Reserved.



## DRYCONN® WATERPROOF CONNECTORS

### Dry-Crimp Connectors

- Crimp style wire connector
- Copper crimp with protective housing
- Two crimp sizes available to cover a wire range from #18 - #10 AWG
- Allows installer to test connection prior to waterproofing splice
- For use in low voltage lighting applications

SKU# 20240 Dry-Crimp Non-Filled Connectors- Bag of 25 Splices

(contents include 25 non-filled housings, 25 small and 25 large copper crimps)

SKU# 20245 Dry-Crimp Filled Connectors- Bag of 25 Splices

(contents include 25 pre-filled housings, 25 small and 25 large copper crimps)

SKU# 20248 Silicone Sealant- 1- 5.3oz Tube

SKU# 20249 Replacement Crimp Sleeves- Bag of 25  
(contents include 25 small and 25 large copper crimps)

Pre-Filled



Non-Filled

(Silicone sealant sold separately)



Copper Crimps are UL Listed.

**MADE IN USA OF US AND FOREIGN PARTS**



## ACE CONNECTOR™

### Low Voltage Landscape Lighting Fitting

- Solid brass lug
- Fast curing heat shrink
- Weather resistant to withstand outdoor elements
- For use in low voltage landscape lighting and direct bury applications

SKU# 90320 Small ACE Connector- Box of 50

SKU# 90325 Small ACE Connector- Bag of 2

SKU# 90330 ACE Connector\*- Box of 50

SKU# 90335 ACE Connector\*- Bag of 2

SKU# 90340 Large ACE Connector- Box of 50

SKU# 90345 Large ACE Connector- Bag of 2



### Small ACE Connector Min #18/Max #12

### ACE Connector\* Min #18/Max #8



### Large ACE Connector Min #18/Max #8

\*UL1838 Listed

All trademarks, U.S. and Foreign apply. All rights reserved.



## DRYCONN® WATERPROOF CONNECTORS

### KSC Connectors (King Shrink Crimp)

- For use in low voltage lighting applications
- Crimp style connector with waterproof heat shrink
- Manufacturer approved for direct bury
- Four sizes available for applications from Min #18 to Max #8
- King Krimper tool also available (see page 25)


SKU# 72010 KSC-1 (Extra Small)- Bag of 20

SKU# 72020 KSC-2 (Small)- Bag of 20

SKU# 72030 KSC-3 (Medium)- Bag of 20

SKU# 72040 KSC-4 (Large)- Bag of 8

**NEW FOR  
2014!**





## DIRECT BURY LINE VOLTAGE SPLICE KIT




# DRYCONN®

WATERPROOF CONNECTORS

## DB Power Connect

### Direct Bury Power Connector

- Designed for use in direct bury line voltage applications or in irrigation systems
- Pre-filled with a non-toxic SmartGel®
- Waterproof and corrosion proof
- For use in outdoor or direct burial locations
- UV and impact resistant
- Eliminates the need for heat shrinks, primers, tapes, resins, and epoxy packs
- Wire Range: #14 - 4 AWG
- Rated up to 600V



MADE IN USA

SKU# 98105 DB Power Connect- Bag of 3

## LOW VOLTAGE CONNECTORS



# DRYCONN®

WATERPROOF CONNECTORS

## Tan Low Voltage

- Waterproof and corrosion proof
- Pre-filled with dielectric petroleum sealant that never hardens
- Suitable for low voltage applications including irrigation systems
- One-step installation saves time and money
- No pre-twisting required
- Eliminates the need for multi-step products

MADE IN USA

U.S. Pat. 5,771,578 and additional Patents Pending apply. All other trademarks, U.S. and Foreign Patents apply. All Rights Reserved.

## Tan Low Voltage

Min #22/Max #6



SKU# 20101 Tan Low Voltage- Card of 4

SKU# 20111 Tan Low Voltage- Bag of 15

SKU# 20122 Tan Low Voltage- Bag of 50

SKU# 20136 Tan Low Voltage- Canister of 50



# DRYCONN®

WATERPROOF CONNECTORS

## Gray/Gray & Blue/Blue Low Voltage

- UL 486D Listed (Gray/Gray only) and 600V rated
- UL 486C Listed (Blue/Blue only) and 600V rated
- Waterproof and corrosion proof
- Pre-filled with dielectric silicone sealant that never hardens
- One-step installation saves time and money
- No pre-twisting required

SKU# 10111 Gray/Gray- Bag of 20

SKU# 10222 Blue/Blue Low Voltage- Bag of 20

SKU# 10241 Blue/Blue Low Voltage- Canister of 100

MADE IN USA

U.S. Pat. 5,771,578 and additional Patents Pending apply. All other trademarks, U.S. and Foreign Patents apply. All Rights Reserved.

## Gray/Gray

Min #22/Max #12



## Blue/Blue Low Voltage

Min #22/Max #12



# DRYCONN®

WATERPROOF CONNECTORS

## Direct Bury GTSR

### Grease Filled Tube w/Strain Relief


- Pre-filled with petroleum grease that never hardens
- Waterproof and corrosion proof
- Easy-latch lid provides strain relief
- Includes orange or yellow nut for wire splicing
- Manufacturer approved for direct bury
- Perfect for low voltage applications up to 50V

SKU# 20205 GTSR w/Orange Nut- Bag of 25

SKU# 20210 GTSR w/Yellow Nut- Bag of 25

MADE IN USA OF US AND FOREIGN PARTS

Patents Pending apply. All other trademarks, U.S. and Foreign Patents apply. All Rights Reserved.



GTSR w/Orange Nut

Min #22/Max #14

GTSR w/Yellow Nut

Min #18/Max #10





# **DRYCONN®** WATERPROOF CONNECTORS

## **DBT-600** (Tube w/Tan Wing) **and DBR/Y-600** (Tube w/Red/Yellow Gorilla Nut) Direct Bury Silicone Filled Tube w/Strain Relief

- UL 486D Listed and 600V rated
- Waterproof and corrosion proof
- Patent Pending snap fit lid provides strain relief
- UV and impact resistant
- Pre-filled with silicone that never hardens
- Wire Range Min #22/Max #8
- Perfect for Two-Wire Decoder Systems

**MADE IN USA OF US AND FOREIGN PARTS**

U.S. Pat. 8,431,824 and additional Patents Pending apply. All other trademarks, U.S. and Foreign Patents Pending apply. All Rights Reserved.



SKU# 20220 DBT-600- Bag of 2  
SKU# 20225 DBT-600- Box of 100  
SKU# 20230 DBR/Y-600- Bag of 2  
SKU# 20235 DBR/Y-600- Box of 100



# **DRYCONN®** WATERPROOF CONNECTIONS

## **DBYN-600** (Tube w/Yellow Nut) **and DBO/B-600** (Tube w/Orange/Blue Gorilla Nut) Direct Bury Silicone Filled Tube w/Strain Relief

- Perfect for use in two-wire decoder systems and direct bury applications
- UL 486D Listed for waterproof and direct bury connections
- Max 600V
- UV resistant for above ground applications
- Pre-filled with dielectric silicone sealant that never hardens
- Snap fit lid provides strain relief

**MADE IN USA OF US AND FOREIGN PARTS**

Patents Pending.

**NEW FOR  
2014!**



Min #22/Max #12

Min #22/Max #8

SKU# 20520 DBYN-600- Bag of 2  
SKU# 20525 DBYN-600- Box of 100  
SKU# 20630 DBO/B-600- Bag of 2  
SKU# 20635 DBO/B-600- Box of 100



# **DRYCONN®** WATERPROOF CONNECTIONS

## **HSC Connectors (Heat Shrink Crimp)**

- Great for well pump connections
- Transparent heat shrink allows for visible splice examination
- Crimp connector is UL Listed
- Manufacturer approved for direct bury
- Connectors span a wire range between #14 - #4 AWG

SKU# 71010 HSC1- 14g - 10g Bag of 4 contains: four (4) 14g - 10g crimps and 4 small sleeves  
SKU# 71020 HSC2- 8g - 12g Bag of 4 contains: one (1) 14g - 10g crimp, three (3) 8g crimps and 4 small sleeves  
SKU# 71030 HSC3- 6g - 8g Bag of 4 contains: one (1) 8g crimp, three (3) 6g crimps, 1 small sleeve and 3 large sleeves  
SKU# 71040 HSC4- 4g - 8g Bag of 4 contains: one (1) 8g crimp, three (3) 4g crimps, 1 small sleeve and 3 large sleeves

**NEW FOR  
2014!**



### Did you know there was a code change concerning outdoor splices?

The goal of King Innovation's

**"Know the Code"** initiative is to provide information to the industry; keeping professionals informed of all requirements in order to reduce the risk of electric shock, corrosion, and product failures. King Innovation DryConn Waterproof Connectors are UL 486D Listed and comply with the 2008, 2011 and 2014 National Electric Code.

**Compliance with the 2008, 2011 and 2014 NEC Handbook means when making a splice in a wet or damp location it is required that a UL 486D Listed splicing method be used. Basically, all outdoor electrical connections require a waterproof connector, even in waterproof enclosures.**

The benefits to Electricians when using DryConn Waterproof Connectors are:

- Installations are made according to the National Electrical Code
- Avoids costly rework due to failed inspections and/or warranty issues
- Avoids connector corrosion at the splice
- Reduces the risk of burnouts and fires
- Complete the job with confidence

#### REFERENCES

##### 1. NEC 2014

Article 100 Definitions: Listed, Location, Wet.  
Articles 110.14, 300.5 (B), 300.38, 300.5 (E), 300.9, 310.10 (C)(3), 314.15, 314.30, 410.10, 675.17

##### 2. NEC 2011

Article 100 Definitions: Listed, Location, Wet.  
Articles 110.14, 300.5 (B), 300.5 (E), 300.9, 310.10 (C)(3), 314.30, 410.10, 675.17

##### 3. NEC 2008

Article 100 Definitions: Listed, Location, Wet.  
Articles 110.14, 300.5 (B), 300.5 (E), 300.9, 310.8 (C)(3), 314.30, 410.10, 675.17

##### 4. Sealed Wire Connector System

UL 486D Scope 1.1

See full code explanations in 'NEC Code References to UL 486D Uses in Wet Locations'



For more information, scan here.

## DIRECT BURY CONNECTORS



**KNOW THE CODE!** Direct Bury Connectors are UL 486D Listed and comply with the 2008, 2011 and 2014 National Electric Code

**DRYCONN®**  
WATERPROOF CONNECTORS

### Direct Bury

- UL 486D Listed and 600V rated
- Pre-filled with dielectric silicone sealant that never hardens
- Waterproof and corrosion-proof
- One-step® installation saves time and money
- Direct Bury, no junction box is required
- No pre-twisting required

SKU# 10444 King 4 Yellow- Bag of 10

SKU# 10555 King 5 Red- Bag of 10

SKU# 10600 King 6 Blue- Card of 2

SKU# 10666 King 6 Blue- Bag of 10

SKU# 10670 King 6 Blue- Box of 100

SKU# 10990 King 9 Dark Blue- Bag of 2

SKU# 10999 King 9 Dark Blue- Bag of 8

#### MADE IN USA

U.S. Pat. 5,771,578 and additional Patents Pending apply. All other trademarks, U.S. and Foreign Patents apply. All Rights Reserved.

**King 5 Red**  
Min #14/Max #10



**King 4 Yellow**  
Min #18/Max #12



**King 6 Blue**  
Min #22/Max #8



**King 9 Dark Blue**  
Min #14/Max #6





**KNOW THE CODE!** Aqua Series Connectors are UL 486D Listed and comply with the 2008, 2011 and 2014 National Electric Code

## DRYCONN® WATERPROOF CONNECTORS

### Aqua Series

- Waterproof and corrosion proof
- Pre-filled with dielectric silicone sealant that never hardens
- One-step® installation saves time and money
- No pre-twisting required
- Multiple sizes for all applications
- UL 486D Listed and 600V rated
- Designed for outdoor/electrical wire splices, especially those exposed to condensation, water vapors or dust



**Aqua/Blue**  
Min #14/Max #6

**Aqua/Orange**  
Min #22/Max #12



**Aqua/Red**  
Min #22/Max #8



- SKU# 62110 Aqua/Orange- Card of 6
- SKU# 62125 Aqua/Orange- Bag of 25
- SKU# 62135 Aqua/Orange- Bag of 100
- SKU# 62146 Aqua/Orange- Canister of 150
- SKU# 62150 Aqua/Orange- Bag of 500
- SKU# 62210 Aqua/Red- Card of 5
- SKU# 62225 Aqua/Red- Bag of 20
- SKU# 62235 Aqua/Red- Bag of 100
- SKU# 62241 Aqua/Red- Canister of 100
- SKU# 62250 Aqua/Red- Box of 500
- SKU# 62310 Aqua/Blue- Card of 3
- SKU# 62325 Aqua/Blue- Bag of 15
- SKU# 62335 Aqua/Blue- Bag of 50
- SKU# 62340 Aqua/Blue- Bag of 250

#### MADE IN USA

U.S. Pat. 5,771,578 and additional Patents Pending apply. All other trademarks, U.S. and Foreign Patents apply. All Rights Reserved.



DryConn Aqua/Red  
product canister



DryConn Aqua/  
Orange product  
canister



For more information,  
scan here.



# GORILLA NUTS®

CUSHION GRIP WIRE CONNECTORS

## Electrician's Hands-

What you don't know, will hurt you.

### WHEN WAS THE LAST TIME ELECTRICIANS THOUGHT ABOUT THEIR HANDS?

#### STOP HAND PAIN NOW!

Gorilla Nuts™ are the revolutionary twist-on wire connectors that feature a soft over molded exterior- a benefit hard working electricians are demanding to prevent nerve damage in their fingers.

#### Top 2 prevalent sources for non-fatal injuries for electricians\*:

1. Parts and Materials
2. Floor Ground Surfaces

#### Top 2 injured parts of the body that put electricians out of work\*:

1. Back
2. Hand/Finger

#### Protect your hands

1. Use common sense
2. Develop hand strength and flexibility
3. Use the right parts and materials

Compared to the Ideal Red Nut, Ideal Twister Pro, Ideal Red Wing and 3M R/Y, **Gorilla Nuts** were ranked #1 for:

- ✓ Fit in fingers
- ✓ Finger Tip Comfort
- ✓ Grip Shape
- ✓ Overall Ease of Use
- ✓ Overall Comfort

United States Ergonomics

\* Bureau of Labor Statistics

- Eliminates pain and numbness in hands and fingers
- Less inventory, improved coverage, fits a wide wire range
- Unique design allows for better torque and twisting leverage
- Comfortable cushion grip offers improved slip resistance
- Flexible WorkSkirt™ protects against over stripping
- Square cut spring provides a secure connection and wire bite with first twist

U.S. Pat. 7,560,645, 8,067,692, 8,525,026 and additional Patents Pending apply. All other trademarks, U.S. and Foreign Patents Pending apply. All Rights Reserved.





SKU# 68105 Orange/Blue- Bag of 10  
 SKU# 68110 Orange/Blue- Box of 100  
 SKU# 68130 Orange/Blue- Canister of 300  
 SKU# 68150 Orange/Blue- Canister of 500  
 SKU# 68170 Orange/Blue- Box of 5,000  
 SKU# 68190 Orange/Blue- Drum of 25,000  
 SKU# 68205 Red/Yellow- Bag of 10  
 SKU# 68210 Red/Yellow- Box of 100  
 SKU# 68230 Red/Yellow- Canister of 300  
 SKU# 68250 Red/Yellow- Canister of 500  
 SKU# 68270 Red/Yellow- Box of 5,000  
 SKU# 68290 Red/Yellow- Drum of 25,000  
 SKU# 68310 Blue/Gray- Box of 50  
 SKU# 68325 Blue/Gray- Canister of 250



Gorilla Nuts product available in boxes, bags and canisters



Orange/Blue  
Min 3 #20/Max 3 #12



Red/Yellow  
Min 2 #18/Max 2 #8



Blue/Gray  
Min 4 #14/Max 2 #6



For more information,  
scan here.



# Contractors' CHOICE™

## Conventional Dry Splices

Select CC Products  
available in Drums



Select CC Products  
available in Bags



All CC Products  
available in Boxes



King Innovation's Contractors' Choice™ Wire Connectors are designed for conventional copper/copper dry splices and are available in a variety of sizes for multiple wire ranges. This value line of connectors offers competitive prices up to 40% lower than comparable products. Contractors' Choice Wire Connectors are industry color-coded and suitable for wire combinations from #22 through #10. Constructed with a steel plated spring and flame-retardant housing, the Contractors' Choice line is rated between 300V and 600V, with select connectors rated up to maximum 1,000V for signs and fixtures. No pre-twisting required. Temperature rated to 221 °F (105 °C). Perfect for indoor, dry applications for both commercial and residential installations.

### Nut Style Wire Connectors

- Designed for conventional copper/copper dry splices, available in nut, wing and push-in style
- Tough Thermoplastic or Polycarbonate (PC) Flame Retardant Shell
- Industry color-coded and suitable for wire combinations from #22 through #10
- Steel plated spring and flame-retardant housing
- Rated between 300V and 600V
- No pre-twisting required
- Perfect for indoor, dry applications for both commercial and residential installations



SKU# 67061 Black Nut- Bag of 1,000  
 SKU# 67065 Black Nut- Box of 100  
 SKU# 67011 Gray Nut- Bag of 1,000  
 SKU# 67015 Gray Nut- Box of 100  
 SKU# 67021 Blue Nut- Bag of 1,000  
 SKU# 67025 Blue Nut- Box of 100  
 SKU# 67031 Orange Nut- Bag of 500  
 SKU# 67035 Orange Nut- Box of 100  
 SKU# 67041 Yellow Nut- Bag of 500  
 SKU# 67045 Yellow Nut- Box of 100  
 SKU# 67051 Red Nut- Bag of 500  
 SKU# 67055 Red Nut- Box of 100



## Wing Style Wire Connectors

- Designed for conventional copper/copper dry splices, available in nut, wing and push-in styles
- Tough Thermoplastic or Polycarbonate (PC) Flame Retardant Shell
- Industry color-coded and suitable for wire combinations from #22 through #10
- Steel plated spring and flame-retardant housing
- Rated between 300V and 600V
- No pre-twisting required
- Perfect for indoor, dry applications for both commercial and residential installations



SKU# 67071 Yellow Wing- Bag of 500  
 SKU# 67075 Yellow Wing- Box of 100  
 SKU# 67079 Yellow Wing- Drum of 35,000  
 SKU# 67081 Tan Wing- Bag of 500  
 SKU# 67085 Tan Wing- Box of 100  
 SKU# 67089 Tan Wing- Drum of 30,000  
 SKU# 67091 Red Wing- Bag of 500  
 SKU# 67095 Red Wing- Box of 100  
 SKU# 67099 Red Wing- Drum of 20,000  
 SKU# 27120 Green Wing- Bag of 25  
 SKU# 27145 Green Wing- Box of 500  
 SKU# 27190 Green Wing- Drum of 25,000  
 SKU# 67101 Gray Wing- Bag of 250  
 SKU# 67105 Gray Wing- Box of 50  
 SKU# 67111 Blue Wing- Bag of 100  
 SKU# 67115 Blue Wing- Box of 50




## Push-In Style Wire Connectors

- Designed for conventional copper/copper dry splices, available in nut, wing and push-in styles
- Tough Thermoplastic or Polycarbonate (PC) Flame Retardant Shell
- Industry color-coded and suitable for wire combinations from #22 through #10
- Steel plated spring and flame-retardant housing
- Rated between 300V and 600V
- No pre-twisting required
- Perfect for indoor, dry applications for both commercial and residential installations



SKU# 67205 Yellow Push-In- Box of 100  
 SKU# 67215 Orange Push-In- Box of 100  
 SKU# 67225 Ivory Push-In- Box of 75  
 SKU# 67235 Blue Push-In- Box of 50  
 SKU# 67245 Purple Push-In- Box of 50  
 SKU# 67255 Black Push-In- Box of 40







## ALUMICONN® Aluminum to Copper Lug

- Secure, mechanical connection of conductors
- Runs approximately 25°F cooler than purple twist-ons\*
- Provides a safer connection
- Separate ports eliminate intermixing of conductors
- One piece for easy installation
- Dielectric silicone inhibitor reduces corrosion of connection
- Tin-plated lug and nickel-plated screws
- Max voltage: 300V
- Aluminum Wire Range: #12 - #10 solid AWG
- Copper Wire Range: #18 - #10 solid and stranded AWG
- UL 486C Listed to meet U.S. and Canadian standards
- Temperature rating of insulating material: 105°C
- Suitable for aluminum to aluminum, aluminum to copper, and copper to copper wire splices
- Approved by CPSC and insurance companies
- Available in 2-Port and 3-Port styles

SKU# 95025 AlumiConn 2 Port- Bag of 25  
 SKU# 95035 AlumiConn 2 Port- Box of 100  
 SKU# 95045 AlumiConn 2 Port- Box of 1000  
 SKU# 95085 AlumiConn 2 Port- Box of 2500  
 SKU# 95104 AlumiConn 3 Port- Card of 2  
 SKU# 95110 AlumiConn 3 Port- Card of 10  
 SKU# 95125 AlumiConn 3 Port- Bag of 25  
 SKU# 95135 AlumiConn 3 Port- Box of 100  
 SKU# 95145 AlumiConn 3 Port- Box of 1,000  
 SKU# 95185 AlumiConn 3 Port- Box of 2,500



### MADE IN USA

U.S. Pat. Pending. All other trademarks, U.S. and Foreign Patents apply. All Rights Reserved.



3 Port\*

**AlumiConn**  
Min #18/Max #10



**NEW FOR  
2014!**



2 Port

- ✓ UL LISTED.
- ✓ INSURANCE COMPANY ENDORSED.
- ✓ CONSUMER PRODUCT SAFETY COMMISSION APPROVED.
- ✓ COMPACT FIT.
- ✓ LOW COST.
- ✓ SECURE CONNECTION.
- ✓ FIRE PREVENTATIVE.
- ✓ PERMANENT SOLUTION.



For more information,  
scan here.






**DRYCONN®**  
WATERPROOF CONNECTIONS

## VisiLock® w/SmartGel®


### Anode Splice Box

- Waterproof and corrosion proof
- Pre-filled with a non-toxic gel that eliminates hazmat requirements
- Re-enterable, semi-transparent, encapsulated splice allows for visible splice examination
- Locking mechanism centers splice in box
- One piece for fast, easy installation
- Eliminates heat shrinks, primers, tapes, and epoxy packs
- Temperature Rating: -40°C (-40°F) to 90°C (194°F)
- Amperage not to exceed maximum temperature of the conductor
- Designed to protect cathodic splices from corrosion
- For making tap or branch splices on insulated cables rated up to 100V

SKU# 98010 VisiLock- Box of 1



**VisiLock**



#### MADE IN USA

U.S. Patent 7,384,297 and 7,431,611. All other trademarks, U.S. and Foreign Patents Pending apply. All Rights Reserved.



## DRYCONN® WATERPROOF CONNECTORS

### King 6 Connectors

**King 6 Yellow**  
Min #22/Max #8



- UL 486D Listed and 600V Rated
- Temperature Rating: 105°C (221 °F)
- Silicone Sealant: -45°F to 400°F
- Rated for underground, direct bury wire splices up to 600V
- Designed for tracer splices and cathodic applications

SKU# 10666 King 6 Blue- Bag of 10  
SKU# 10710 King 6 Orange- Bag of 10  
SKU# 31556 King 6 Yellow- Bag of 10

#### MADE IN USA

U.S. Pat. 5,771,578 and additional Patents Pending apply. All other trademarks, U.S. and Foreign Patents apply. All Rights Reserved.



**King 6 Blue**  
Min #22/Max #8



**King 6 Orange**  
Min #22/Max #8



## DRYCONN® WATERPROOF CONNECTORS

### DBSR®

Direct Bury w/Strain Relief

**DBSR Yellow**  
Min #22/Max #6

- UL 486D Listed and 600V rated
- Pre-filled with dielectric silicone sealant that never hardens
- Waterproof and corrosion proof
- Easy latch lid provides strain relief
- One piece for easy installation
- Silicone Sealant Temperature: -45°F to 400°F
- Designed for tracer splices and cathodic applications

SKU# 63315 DBSR Yellow- Bag of 10  
SKU# 63350 DBSR Yellow- Box of 100  
SKU# 63615 DBSR Aqua- Bag of 10  
SKU# 63650 DBSR Aqua- Box of 100  
SKU# 63715 DBSR Orange- Bag of 10  
SKU# 63750 DBSR Orange- Box of 100

#### MADE IN USA

U.S. Pat. 7,170,005, 5,771,578, 6,815,616, 7,122,742 and additional Patents Pending apply. All other trademarks, U.S. and Foreign Patents Pending apply. All Rights Reserved.



**DBSR Aqua**  
Min #22/Max #6



**DBSR Orange**  
Min #22/Max #6





# **DRYCONN®** **WATERPROOF CONNECTORS**

## **DB Lugs**

**Direct Bury**

- Waterproof and corrosion proof
- Pre-filled with dielectric silicone sealant that never hardens
- Install service line without cutting the main line
- Installs in one minute or less
- Manufacturer approved for direct bury
- Silicone Sealant Temperature Rating: -45°F to 400°F
- Designed for low voltage tracer splices and cathodic applications up to 50V

SKU# 90120 DB Lug Yellow- Bag of 5  
 SKU# 90220 DB Lug Aqua- Bag of 5  
 SKU# 90420 DB Lug Orange- Bag of 5

**MADE IN USA**

U.S. Pat. 7,044,776, 7,677,932, 7,223,132, 7,507,126 and additional Patents Pending apply. All other trademarks, U.S. and Foreign Patents apply. All Rights Reserved.

### **DB Lug Yellow**

Min #14/Max #10

### **DB Lug Aqua**

Min #14/Max #10

### **DB Lug Orange**

Min #14/Max #10

# **DRYCONN®** **WATERPROOF CONNECTORS**

## **Split Bolt Housing**

- Designed for low voltage tracer splices and cathodic applications up to 50V
- Use for making tap or branch splices
- Pre-filled with a non-toxic SmartGel® that eliminates hazmat requirements
- Waterproof and corrosion proof
- Eliminates the need for heat shrinks, primers, tapes and epoxy packs
- One piece for fast, easy installation
- Installs in one minute or less
- For use in outdoor or direct-burial locations
- Wire Range: #14 - #10 AWG

SKU# 69205 Split Bolt Housing Yellow- Box of 1  
 SKU# 69105 Split Bolt Housing Aqua- Box of 1  
 SKU# 69305 Split Bolt Housing Orange- Box of 1

**MADE IN USA**

U.S. Pat. 7,950,956 and additional Patents Pending apply. All other trademarks, U.S. and Foreign Patents Pending apply. All Rights Reserved.

### **Split Bolt Housing Yellow**

Min #14/Max #10

### **Split Bolt Housing Aqua**

Min #14/Max #10

### **Split Bolt Housing Orange**

Min #14/Max #10





## Siphon King Display Rack

(See page 35 for details)

SKU# 48024 24" Pump x 36" Hose- Bag of 1

SKU# 48036 36" Pump x 36" Hose- Bag of 1

SKU# 48072 36" Pump x 72" Hose- Bag of 1

SKU# 48230 24" Pump Extension- Bag of 1

## Siphon King® Utility Pumps

- Made in USA
- Corrosion proof
- Provides quick removal of water
- Self-priming, lightweight utility pump
- High strength, ergonomic handle can withstand extreme temperatures and harsh usage
- 36" pump provides quick removal of 1 gallon in 4 strokes
- 24" extension available; fits on to existing pump to access hard to reach areas
- Steel shaft improves strength
- Flexible discharge hose for directing water evacuation
- Removable intake foot for easy cleaning
- Perfect for removing water from valve boxes, meter pits, pipe trenches, and anywhere water accumulates

**NEW FOR  
2014!**

24" Pump Extension

24" Pump x 36" Hose

36" Pump x 36" Hose

36" Pump x 72" Hose

**MADE IN USA**

U.S. Pat. 7,726,231. All other trademarks, U.S. and Foreign Patents Pending apply. All Rights Reserved.



## Siphon King Gas Powered Pump

- 4-cycle, single cylinder, air-cooling gasoline engine
- Excellent for high volume water transfer
- Unrestricted flow 40 gallons per minute
- 1" inlet/outlet diameter
- Includes two (2) 6' hoses for intake and discharge, garden hose adaptor, and intake filter

**NEW FOR  
2014!**



Intake Filter



Garden Hose  
Adaptor



Back

Front

SKU# 48350 Gas Powered Pump- Box of 1



## Siphon King Gas Pit Pump Adaptor


- Connects directly to the drip pot to remove standing water in low pressure gas systems
- Has a 3/4" NPT metal thread insert that will not strip away, even with repeated use

SKU# 48210 Gas Pit Pump Adaptor- Bag of 1

## Siphon King Syringe Sucker

- For use in small spaces, including golf valve bodies, meter pits, narrow trenches, etc.
- 3/4" barb fitting with 12" pipe attachment
- Replace 12" pipe with any length funny pipe for maximum flexibility and reach

SKU# 48215 Syringe Sucker- Card of 1



## Siphon King Pump Assembly Foot

- Screws on easily
- Eliminates problems caused by mud buildup and debris to improve suction

SKU# 48205 Pump Assembly Foot- Bag of 1

## Siphon King 72" Extension/Replacement Hose w/Coupler

- 72" flexible hose directs water away from work site
- Coupler provides extension to existing pump hose

SKU# 48272 72" Extension/Replacement Hose- Bag of 1



## Siphon King Jr.

- Intake and discharge transfer system
- May be used to transfer liquids, remove water, change oil, siphon gas, or inflate small objects
- Complete with two 50" siphon hoses, a dipstick tube, and an air pressure hose

SKU# 48050 Siphon King Jr. w/50" Hose- Pkg of 1



## SnapTap® SADDLES

- Ergonomic handle with 50% more surface area to cushion fingers and provide maximum comfort
- #1 in speed, comfort and durability
- Available with a FPT, 90° Elbow or Straight Barb fitting
- No tools, fittings, or clamps needed
- Ergonomic hurricane handle provides comfortable, quick rotations
- Short thread design allows for the quickest, easiest installation possible without dirt or pebble clogging
- Patented cutting tip cleanly cuts polyethylene pipe for a tight seal every time
- Side snap latch provides a visible, secure connection
- Shorter working height requires less digging
- For both 80# and 100# 1" Poly Pipe

SKU# 22311 1" x 1/2" FPT Saddle- Bucket of 75  
 SKU# 22316 1" Saddle w/90° Elbow- Bucket of 75  
 SKU# 22321 1" Saddle w/Straight Barb- Bucket of 75  
 SKU# 22331 1" x 3/4" FPT Saddle- Bucket of 75

### MADE IN USA

U.S. Pat. 6,510,865 and 6,767,033. All other trademarks, U.S. and Foreign Patents Pending apply. All Rights Reserved.



## UNIVERSAL!! SnapTap® SADDLES

- Ergonomic handle with 50% more surface area to cushion fingers and provide maximum comfort
- Universal adjustable latch provides a visible, secure connection
- Fits 3/4", 1" and 1 1/4" Poly (PE) Pipe
- Installation requires no fittings, no clamps
- Available with a FPT, 90° Elbow or Straight Barb fitting
- Patented cutting tip cleanly penetrates for a tight seal every time

SKU# 22511 Universal 1/2" FPT Saddle- Bucket of 75  
 SKU# 22516 Universal Saddle w/90° Elbow- Bucket of 75  
 SKU# 22521 Universal Saddle w/Straight Barb- Bucket of 75

### MADE IN USA OF US AND FOREIGN PARTS

U.S. Pat. 6,510,865. All other trademarks, U.S. and Foreign Patents Pending apply. All Rights Reserved.





## KING DRAINS®

### Soft Grip Drain

- Ergonomic soft grip design makes for comfortable, slip-free installation
- Complements end-of-season blow-outs to remove residual water from irrigation systems and provide freeze protection
- Utilized for both main and lateral line applications
- Patented backflow check prevents contamination
- Broad dispersing pad protects against root and soil penetration
- Self-cleaning dirt arrestor screen prevents clogging of drain
- Patented pressure sensitive valve releases water slowly at root level

SKU# 22163 1/2" MPT- Bag of 25

SKU# 23167 3/4" MPT- Bag of 25

**MADE IN USA**

U.S. Patent Numbers 6,886,585 and D568,450. All other trademarks, U.S. and Foreign Patents Pending apply. All Rights Reserved.



Soft Grip Drain



## KING DRAINS®

### End of Line Drain

- Designed for 1" Class or Schedule 40 PVC pipe
- Complements end-of-season blow-outs to remove residual water from irrigation systems and provide freeze protection
- Patented pressure sensitive valve releases water slowly at root level
- Self-cleaning dirt arrestor screen prevents clogging of drain



3/4" x 1/2" FPT



1" x 1/2" FPT



1" x 3/4" FPT

SKU# 15140 3/4" x 1/2" FPT- Bag of 10

SKU# 16142 1" x 1/2" FPT- Bag of 10

SKU# 17145 1" x 3/4" FPT- Bag of 10

SKU# 21155 1" MPT x 1" INS- Bag of 5

**MADE IN USA OF US AND FOREIGN PARTS**

U.S. Pat. 6,886,585 and D568,450. All other trademarks, U.S. and Foreign Patents Pending apply. All Rights Reserved.



1" MPT x 1" INS





- Heavy duty PVC
- UV resistant
- Max gallons: 15
- Max tree size: 1" - 4" diameter
- Max tree size can be doubled by zipping two Sapling Soaker bags together
- 5-9 hours of drip time

SKU# 44020 Sapling Soaker- Bag of 1



- Heavy duty polyethylene
- UV resistant
- Max gallons: 20
- Max tree size: 6" diameter
- Heavy duty Velcro strap secures Sapling Soaker in high winds preventing blow away
- 5-8 hours of drip time

SKU# 44010 Sapling Soaker Ring- Bag of 1




## Ball Bearing Probe

- Use to locate sprinkler lines, measure moisture penetration, or avoid roots, pipe and rocks when digging
- Rounded head reduces risk of damage to tree roots, wires, pipelines, etc.
- Made of durable steel
- Lightweight for easy portability
- For commercial or residential use

**MADE IN USA**

SKU# 25210 Ball Bearing Probe- Unit of 1







## LEAK-B-GONE™

PVC LEAK STOPPER RING

- 60 second solution to repair leaking PVC joints
- Available in seven sizes, for 3/4", 1", 1 1/4", 1 1/2", 2", 3", and 4" PVC pipe
- Easy installation, no tools required
- Provides 360° leak protection, tested to 200 PSI
- For commercial and residential use

SKU# 45015 3/4" Rings- Bag of 10

SKU# 45020 1" Rings- Bag of 10

SKU# 45025 1 1/4" Rings- Bag of 10

SKU# 45030 1 1/2" Rings- Bag of 10

SKU# 45035 2" Rings- Bag of 10

SKU# 45040 3" Rings- Bag of 10

SKU# 45045 4" Rings- Bag of 10



### CONTRACTORS' PICK!

SKU# 45050 Assorted 3/4", 1", 1 1/4" & 1 1/2" Rings Bag of 4

SKU# 45055 Assorted 2", 3" & 4" Rings Bag of 3

U.S. Pat. 8,371,622. All other trademarks, U.S. and Foreign Patents apply. All Rights Reserved.



## KING GRIPS®

- Quick coupling and release saves time
- No steel splinters
- Fits all pipe pulling equipment
- Plated for rust prevention
- No tape required
- Available in a convenient kit
- For 3/4" to 2" Polyethylene Pipe and 3/4" to 4" PVC Pipe
- Durable, closed-end design protects pipe from soil entry
- Minimum pipe grip eliminates wasted pipe material



SKU# 81801 1" PVC Kit Grip and Chain- QTY 1

SKU# 81802 1" 80# Poly Kit Grip and Chain- QTY 1

SKU# 81803 1" 100# Poly Kit Grip and Chain- QTY 1



MADE IN USA

See price list for a complete list of SKU's



## Mesh Grips

- For pulling irrigation PVC and Poly Pipe, directional boring pull backs, insulated wire, wire rope, tubing, and bare conductors
- Reusable
- Available with swivels built into grip
- Coated galvanized cable
- Reverse weave and single wire bail
- Work load capacity of 1500 to 3500 lbs
- Various grip lengths, pipe ranges, and weaves available



MADE IN USA

See price list for a complete list of SKU's



# I-tool

## Irrigation Multi-Tool

- 15 tools, includes 4 Irrigation Tools
- Compatible with all major brands
- Punch precise holes in poly
- Quickly remove sediment
- Effortlessly adjust arc
- Pull up any brand sprinkler head
- Lightweight compact style
- Precise construction
- Withstands extended use



Carrying case included



**NEW FOR 2014!**

SKU# 46600 I-tool Card of 1



## 2" Ratchet Poly/PVC Pipe Cutter with Grounding Stud

- Static dissipating grounding stud increases safety
- Stainless Steel blade for precision cuts
- Cuts up to 2" SCH40, 200 Class PVC Pipe or Yellow (PE) Gas Pipe
- Cuts up to 2" Poly (PE) Pipe
- Strong and durable cast aluminum body
- Patent Pending



**NEW FOR 2014!**



SKU# 46360 2" Ratchet- Card of 1

SKU# 46351 2" Ratchet Replacement Blade- Card of 1



## 2" Ratchet Poly/PVC Pipe Cutter

- Cuts up to 2" SCH40, Class PVC Pipe or Yellow (PE) Gas Pipe
- Cuts up to 2" Poly (PE) Pipe
- Stainless Steel blade for precision cuts
- Strong and durable cast aluminum body



SKU# 46350 2" Ratchet- Card of 1

SKU# 46351 2" Ratchet Replacement Blade- Card of 1



## Poly/PVC Pipe Cutter

- Cleanly cuts up to 1 1/2" Poly (PE) Pipe and up to 1 1/4" Class PVC Pipe
- Durable cast aluminum body
- Hardened steel blade



SKU# 46320 Poly Pipe Cutter- Card of 1

SKU# 46321 Poly Pipe Cutter Replacement Blade- Card of 1



## 1 1/4" Ratchet Poly/PVC Pipe Cutter

- Cleanly cuts up to 1 1/4" SCH40, Class PVC Pipe and up to 1 1/4" Poly (PE) Pipe
- Durable cast aluminum body
- Pointed steel blade for ease of cutting



SKU# 46310 1 1/4" Ratchet- Card of 1

SKU# 46311 1 1/4" Ratchet Replacement Blade- Card of 1



# GORILLA UF STRIPPER™

**NEW FOR  
2014!**

- For use in home installations and outdoor wiring
- Ergonomic comfort grip handle eases soreness in hands and fingers
- Strips outer jacket in one motion
- Won't nick copper wire
- Works in boxes and enclosures
- Made of heat treated carbon steel
- Min/Max Strip: #14 - #10 AWG

SKU# 46200 Gorilla Stripper- Card of 1



# King Krimper™

**NEW FOR  
2014!**

- For use with KSC (King Shrink Crimp) connectors (see page 5)
- Ratcheting style tool
- Pre-defined compression for each connector size guarantees a secure connection
- Durable tool for extended use

SKU# 46550 King Krimper- Card of 1



# Comfort Squeeze® Ergonomic Hand Tools

- Ergonomic comfort squeeze handle eases hand fatigue and provides non-slip grip
- Features handle lock closure for added safety
- Tools available for multiple solid and stranded wire gauges

SKU# 46501 Ergonomic Wire Stripper/Crimper/Cutter #22-#10 AWG- Card of 1

SKU# 46515 Ergonomic Wire Stripper/Cutter #20-#10 AWG- Card of 1

SKU# 46522 Ergonomic Up Front Crimper #22-#10 AWG- Card of 1



**AIR POCKET  
CUSHIONED GRIP!**



# Standard Hand Tool

- Comfort squeeze handle eases hand fatigue and provides non-slip grip
- Features handle lock closure for added safety
- Tools available for multiple solid and stranded wire gauges

SKU# 46005 Wire Stripper w/Handle Lock #20-#10 AWG- Card of 1



# Cable Saw

- 36" Cable Saw
- For fast cutting of PVC plumbing, drain, and irrigation pipe
- Great for tight spaces

SKU# 46300 Cable Saw- Card of 1





## ACCESSORIES



### Bucket, Lid and Divider

#### Buckets:

- High impact pail with heavy duty handle
- Great for organization and storage needs
- Lid sold separately

#### Dividers:

- Fits cleanly into buckets to divide into four sections
- Carry pipe fittings, saddles, connectors, and more without intermixing sizes and styles
- Durable material withstands prolonged use

#### MADE IN USA

SKU# 47400 Logo Bucket QTY 1

SKU# 47410 Logo Bucket Lid QTY 1

SKU# 47420 Logo Bucket Dividers QTY 1



**NEW FOR  
2014!**



### Storage Organizers

- Perfect for storage and organization
- High-impact plastic pail with heavy duty handle
- Storage trays fit snugly inside pail
- Full size sorter trays interchange with half size trays
- Water-resistant lids are easy to put on and take off
- Available in multiple tray quantities for customization

#### MADE IN USA

SKU# 47502 5 Gallon Yellow Pail- 1 Lid, 2 Large and 2 Small Black Trays

SKU# 47405 5 Gallon Yellow Pail- 1 Lid, 3 Large Black Trays

SKU# 47506 5 Gallon Yellow Pail- 1 Lid, 6 Small Black Trays



Product not included



### Gray Tote Tray

- Easily transport glue, tools, and other supplies to and from job sites
- Oversized for maximum capacity without the worry of spilling
- Storage grooves on the side of handle allow for smaller supplies, such as connectors
- Heavy duty construction

#### MADE IN USA

SKU# 47027 Gray Tote Tray- QTY 1



Product not included



### Power Cords

- For use with irrigation controllers
- Available in 6' and 8' lengths
- UL Listed for safety
- Three prong style plug at a 90° angle
- Three count 16 gauge stranded wire (green, white and black in color)
- For indoor use

SKU# 25260 6' Power Cord- QTY 1

SKU# 25280 8' Power Cord- QTY 1



**NEW FOR  
2014!**



### Insulated Safety Staples

- Orange Applications: (NMC) 2 conductor, #14 and #12 AWG
- Blue Applications: BX 3 conductor, #14, #12, and #10 AWG or 2 stacked oval #14 and #12 AWG

#### MADE IN USA

SKU# 70102 Orange Staple 1" x 1/2"- Box of 100

SKU# 70112 Blue Staple 1 1/4" x 9/16"- Box of 100





## Anchor Kit

- Kit includes 100 #10 x 1" slotted Phillips combination pan head screws
- Kit includes 100 1/4" x 1" plastic anchors
- Free carbide-tipped drill bit included



**MADE IN USA**

SKU# 25130 Anchor Kit- QTY 1

## Drywall Anchor Kit

- Pre-drills its own small precise hole in drywall
- Attaches through drywall
- Available in zinc anchors
- Kit includes 50 pan head screws and anchors




**MADE IN USA**

SKU# 25150 Zinc Anchors- QTY 1



## Nylon Cable Ties

- Raised ridges on bent tip for a sure grip
- Nylon toughness
- UL 94V-2 flammability classification
- Complies with military spec
- Self-locking, one-piece, low profile head conserves space
- Bent tip on all series of cable ties allows easier pick-up insertion, and pull-up
- V-shaped raised ridges on bent tip gives a sure grip and easier pull-up
- Engineered and manufactured for excellent performance
- For maximum comfort, smooth rounded edges will not cut hands or insulation



SKU# 76003 4" Nylon Cable Ties- Bag of 100


SKU# 76007 7" Nylon Cable Ties- Bag of 100

SKU# 76011 11" Nylon Cable Ties- Bag of 100

SKU# 76015 14.5" Nylon Cable Ties- Bag of 100

## Black Cable Ties

- Easy to use ties for landscape lighting on decks or trees, home, electrical, or any fastening needs
- Self-locking, one-piece, low profile head conserves space
- For maximum comfort, smooth rounded edges will not cut hands or insulation
- Rated for indoor and outdoor use
- UV Resistant
- Available in 8", 11", 14", 18" and 24" sizes
- 8" cable tie available with or without screw mount head
- 1" x 1" adhesive black cable mount available



SKU# 76108 8" Black Cable Ties- Bag of 100

SKU# 76111 11" Black Cable Ties- Bag of 100

SKU# 76114 14" Black Cable Ties- Bag of 100

SKU# 76118 18" Black Cable Ties- Bag of 50

SKU# 76124 24" Black Cable Ties- Bag of 50

SKU# 77108 8" Black Cable Ties w/Screw Mount- Bag of 100

SKU# 78001 Black Cable Mount- Bag of 100



## Vinyl Electrical Tape

- General purpose 7 mil tape
- Weather resistant, flame retardant
- Use for all mechanical and electrical applications
- Use as a primary insulation under 600V, or as a protective outer jacket over splices
- UL 510 Listed, economical grade of pressure-sensitive vinyl tape

SKU# 86001 Vinyl Electrical Tape- QTY 1





## PTFE Thread Tape

- 520" roll
- Creates a watertight seal around threaded pipe joints
- Resists water and corrosion
- Flexible and easy to tear for quick installation
- 0.004" thick, medium density
- Tensile Strength: 3.5 lbs/inch, Elongation: 25%
- Temperature Range: -375°F to 500°F

SKU# 86020 1/2" x 520" PTFE Thread Tape- QTY 1

SKU# 86021 3/4" x 520" PTFE Thread Tape- QTY 1

SKU# 86022 1" x 520" PTFE Thread Tape- QTY 1

## Pipe Wrap Tape

- Provides UV and Weather Protection
- Stretchable, strong adhesive
- Great for cast and ductile iron, galvanized steel, electrical conduit types of pipes and fittings
- Waterproof and non-corrosive
- 2" x 100 feet x 10 mil

SKU# 86080 Pipe Wrap Tape- QTY 1



## UPC Pipe Wrap Tape

**NEW FOR  
2014!**

- Provides UV and Weather Protection
- Stretchable, strong adhesive
- Great for cast and ductile iron, galvanized steel, electrical conduit types of pipes and fittings
- Waterproof and non-corrosive
- 2" x 100 feet x 10 mil

SKU# 86081 UPC Pipe Wrap Tape- QTY 1



## Duct Tape

- 8 mil, multi-purpose grade tape
- 2" x .0085" x 60 yards
- 48 mm x .210 mm x 55 m
- Excellent adhesion to a wide variety of surfaces
- Use for a broad range of applications or bundling
- Conforms well to irregular spaces

**MADE IN USA**

SKU# 86070 Duct Tape- QTY 1





## GORILLA NUTS BRANDED CLOTHING



Gorilla Nuts  
Red T-Shirt "Tough Nuts"

Gorilla Nuts Red T-Shirt  
"Ask Me About My Gorilla Nuts"



Gorilla Nuts  
"Tough Nuts" Camo Hat



Gorilla Nuts  
"Tough Nuts" Red Hat

**HATS \$11**  
**T-SHIRTS \$7**  
Plus \$3 shipping on all items.

Call 800.633.0232 or visit <http://www.gorillanuts.com/store> to buy today!

## KING INNOVATION BRANDED CLOTHING



King Innovation  
Oxford Gray T-Shirt  
"Making Your Job Easier."



King  
Navy Hat



King  
Khaki Hat



King  
Camo Hat



All hats have the  
King Innovation  
logo on the back

**HATS \$11**  
**T-SHIRTS \$7**  
Plus \$3 shipping on all items.

Call 800.633.0232 or visit <http://www.kingininnovation.com/store> to buy today!

# WIRE COMBINATIONS

## DryConn Black Series

<b>Black/White- 600V</b> Min #22/Max #12 2#14 1#14 w/1-3 #18 or #20 3#16 w/1#18, #20 or #22 2-5 #18 2#14 w/1 #18 1#18 w/1-4 #20 3-5 #20 1#16 w/1 #18 4#18 w/1 #20 1#14 w/1 or 2#16 2#16 w/1-2 #18 or #20 4#20 w/1#22	<b>Black/Gray- 600V</b> Min #22/Max #8 1-4 #12 2#14 w/2-4 #16 1#12 w/1-4 #14 2-5 #14 1#10 w/1-3 #14 1#12 w/2-4 #18 2-6 #16 1#10 w/1-5 #16 1#14 w/3-4 #18 4#14 w/1-2 #18 1#12 w/1-4 #16 2#12 w/1-2 #14	<b>Black/Blue- 600V</b> Min #14/Max #6 1#6 2#8 1#10 w/3-5 #14 3#10 w/1-2 #18 2-3 #10 2#10 w/1-2 #12 4#12 w/1 #14 3-5 #12 2#10 w/1-3 #14 1#10 w/2-3 #12 3#10 w/1 #14 4, 5 or 6 #14

## DryConn DBSR

<b>DBSR Black Medium- 600V</b> Min #22/Max #6 2#18 1-3 #10 1#14 w/3-4 #18 1-4 #12 2#14 w/2-4 #16 1#12 w/2-4 #18 2-5 #14 2-6 #16 5#14 w/1 #18 3#10 w/1 #18 1#8 w/1-2 #16, #18, #20 or #22 3#14 w/1-2 #16, #18, #20 or #22

## DryConn Dry-Crimp

<b>Dry-Crimp- 50V</b> Min #18/Max #10	

## DryConn HSC (Heat Shrink Crimp)

<b>HSC- 600V</b> Min #14/Max #4

## Large ACE

<b>Large ACE Connector- 30V</b> Min #18/Max #8 1 or 2 #10 1,2 or 3 #12 1,2,3,4 or 5 #14 1,2,3,4,5,6,7 or 8 #16 1,2,3,4,5,6,7 or 8 #18 1#8 w/1 #12 or #14 1#8 w/1,2,3 or 4 #18 1#10 w/1, 2, 3, 4, or 5 #16 2#12 w/1 or 2 #14 2#14 w/1, 2, 3, 4, 5, or 6 #16 2#14 w/1, 2, 3, 4, 5, or 6 #18 5#14 w/1 #16

## Medium ACE

<b>Medium ACE Connector- 30V</b> Min #18/Max #8 1-2 #10 1-3 #12 1-5 #14 1-8 #16 or #18 1#8 w/1-4 #18 1#10 Stranded w/1-7 #18 Stranded 1#12 Stranded w/1-7 #18 Stranded 5#14 w/1 or 2 #18 1#8 w/1 or 2 #16 1#8 w/1 #12 or #14 1#10 w/1 or 2 #12

## DryConn Low Voltage

<b>Gray/Gray- 600V</b> Min #22/Max #12 2#14 1#14 w/1-3 #18 or #20 3#16 w/1 #18, #20 or #22 2-5 #18 2#14 w/1 #18 1#18 w/1-4 #20 3-5 #20 1#16 w/1 #18 4#18 w/1 #20 1#14 w/1 or 2 #16 2#16 w/1-2 #18 or #20 4#20 w/1 #22	<b>Blue/Blue- 600V</b> Min #22/Max #12 1-3 #12 1-4 #14 2-5 #16 3-6 #20 2#12 w/1 #14 1#12 w/1-4 #16 or #18 2#12 w/1-2 #16 or #18 1#14 w/1-4 #16, 18 or 20 3#14 w/1 #16 3#14 w/1-2 #18 or 20 2#16 w/1-3 #18, 20 or 22 2-5 #18	<b>Tan- 30V</b> Min #22/Max #6 2#14 w/1-2 #12 2-6 #18 or 20 3#18 w/1-3 #12, 14 or 16 1-6 #14 or 16 1-3 #10 or 12 4#12 solid 2#16 w/1-4 #14 2#16 w/1-3 #12 2#16 w/1-2 #10 1#18 w/1-4 #12 or 14 1-2 #18 w/1-2 #10

## Small ACE Connector

<b>Small ACE Connector- 30V</b> Min #18/Max #12 1 #12 1 or 2 #16 1 #14 w/1 #18

## VisiLock

<b>VisiLock- 100V</b> Main: #8-1/0 (.363"-.625" O.D.) Tap: #12-#4 (.305"-.443" O.D.)

## AlumiConn 2 Port & 3 Port

<b>AlumiConn</b> Min #18/Max #10

## DB Power Connect

<b>DB Power Connect- 600V</b> Min #14/Max #4 4g - 14g

## DryConn GTSR




<b>GTSR w/Orange Nut- 50V</b> Min #22/Max #14 1 or 2 #14 Solid or Stranded 2-3 #16 Solid or Stranded 2-4 #18 Solid or Stranded 2#14 w/1 #18 Solid or Stranded 1#16 w/1 - 4 #18 Solid or Stranded 3#18 w/1 or 2 #20 or #22 Solid or Stranded 1#16 w/1 #20 w/1 #22 2#16 w/1 or 2 #18 2#16 w/1,2 or 3 #20 1#18 w/1, 2, 3 or 4 #20	<b>GTSR w/Yellow Nut- 50V</b> Min #18/Max #10 4#14 Solid or Stranded 2-5 #16 Solid or Stranded 2#14 and 1 #12 Solid or Stranded 3#12 Solid or Stranded 2#16 and 2 #14 Solid or Stranded 2 or 3 #12 2,3 or 4 #14 2,3,4,5 or 6 #18 1#10 w/1,2 or 3 #16

## DryConn DB-600 Silicone Tube w/Strain Relief



<b>DBYN-600 w/Yellow Nut- 600V</b> Min #22/Max #12 2 #12 2 or 3 #14 2 - 5 #16 3-7 #18 1 #12 w/ 1 - 4 #18 2 #12 w/ 1 #18 1 #14 w/ 1 - 4 #18 2 #14 w/ 1 - 3 #18 2 #16 w/ 1 - 3 #18	<b>DBO/B-600 w/Orange/Blue Gorilla Nut- 600V</b> Min #22/Max #12 1 - 3 #12 1 - 4 #14 2 - 5 #16 2 - 5 #18 1 #10 w/ 1 - 4 #18 1 #12 w/ 1 - 4 #18 2 #12 w/ 1 or 2 #18 1 #14 w/ 1 - 4 #18 3 #14 w/ 1 or 2 #18

Contact factory for a complete list of wire combinations at 800.633.0232 or visit [www.kinginnovation.com](http://www.kinginnovation.com).





## DryConn Aqua Series

		
<b>Aqua/Orange- 600V</b> Min #22/Max #12 2#14 1#14 w/1-3 #18 or #20 3#16 w/1#18, #20 or #22 2-5 #18 2#14 w/1 #18 1#18 w/ 1-4 #20 3-5 #20 1#16 w/1 #18 4#18 w/1 #20 1#14 w/1 or 2#16 2#16 w/1-2 #18 or #20 4#20 w/1#22	<b>Aqua/Red- 600V</b> Min #22/Max #8 1-4 #12 2#14 w/2-4 #16 1#12 w/1-4 #14 2-5 #14 1#10 w/1-3 #14 1#12 w/2-4 #18 2-6 #16 1#10 w/1-5 #16 1#14 w/3-4 #18 4#14 w/1-2 #18 1#12 w/1-4 #16 2#12 w/1-2 #14	<b>Aqua/Blue- 600V</b> Min #14/Max #6 2#8 1#10 w/3-5 #14 3#10 w/1-2 #18 2-3 #10 2#10 w/1-2 #12 4#12 w/1 #14 3-5 #12 2#10 w/1-3 #14 1#10 w/2-3 #12 3#10 w/1 #14 1#8 w/1 #10 1#8 w/1 or 2#12


## DryConn DB-600 Silicone Tube w/Strain Relief

	
<b>DBT-600 w/Tan Wing- 600V</b> Min #22/Max #8 1-2 #10 2-6 #18 1-4 #12 1#8 w/ 2 #14 1-5 #14 3#12 w/ 3 #18 2-6 #16 3#14 w/2 #18 2#14 w/1 #16	<b>DBR/Y-600 w/Red/Yellow Gorilla Nut- 600V</b> Min #22/Max #8 2-3 #10 2#18 2-5 #12 1#8 w/1-2 #18 2-5 #14 3#10 w/ 1 #18 4-6 #16 3#12 w/3 #18 3#14 w/2 #18

## DryConn Direct Bury, Telecom and Gas

			
<b>King 4 Yellow- 600V</b> Min #18/Max #12 4-6 #18 2-6 #16 2-5 #14 1-4 #12 2#12 w/1-2 #14 1#12 w/1-4 #14 or #16 3#16 w/2 #18 2#14 w/2-4 #16 1#10 w/1-3 #14 1#8 w/1-2 #16 1#10 w/1-2 #12 1#12 w/3 or 4#22 2#12 w/1 or 2#16 2#12 w/1 or 2#18	<b>King 5 Red- 600V</b> Min #14/Max #10 1-3 #10 1#10 w/1 #12 and 1-2 #14 4#14 w/1-2 #18 1-4 #12 1#12 w/1-4 #14 2-5 #14 2#12 w/1-2 #14, #16 or #18 1#10 w/1-3 #14 1#14 w/3-4 #18 2#10 w/1-2 #14 2#10 w/2 or 3 #16 2#10 w/1, 2, or 3 #18 1#12 w/3 or 4 #22 3#12 w/1 #14 3#12 w/1 or 2#16 4#14 w/1 #16	<b>King 6 Yellow, Blue &amp; Orange- 600V</b> Min #22/Max #8 1-3 #10 1#10 w/1-3 #14 1#14 w/3-4 #18 1-4 #12 1#10 w/1-5 #16 2#14 w/2-4 #16 3#14 w/1-2 #16, #18, #20 or #22 2-5 #14 1#8 w/1 #12 1#12 w/1-4 #14 or #16 2#12 w/1-2 #14, #16 or #18 2-6 #16 1#12 w/2-4 #18 5#14 w/1 #18 1#8 w/1-2 #16, #18, #20 or #22 3#12 w/1 #14	<b>King 9 Dark Blue- 600V</b> Min #14/Max #6 1 or 2 #6 2-3 #8 2, 3, 4, or 5 #10 2 #6 w/1 #10 or 1 #12 2-5 #10 1 #6 w/ 1 or 2 #8 1 #10 w/2-4 #12 2 #6 w/1 or 2 #14 3-6 #12 1 #10 w/3-5 #14 2 #8 w/ 1 or 2 #10 2 #8 w/ 1 #10 w/ 1 #12 4 #10 w/ 1 #12 1 #6 w/ 3 #12 w/ 1 #14 3 #12 w/ 1, 2, or 3 #14 4 #12 w/1 #14

## DryConn DBSR


<b>DBSR Yellow, Aqua &amp; Orange- 600V</b> Min #22/Max #6 2#18 1-3 #10 1#14 w/3-4 #18 1-4 #12 2#14 w/2-4 #16 1#12 w/2-4 #18 3#14 w/1-2 #16, #18, #20 or #22 2-5 #14 2-6 #16 5#14 w/1 #18 1#8 w/1-2 #16, #18, #20 or #22 3#10 w/1 #18 1#8 w/1 #12 1#12 w/1-4 #14 or #16 2#12 w/1-2 #14, #16 or #18 1#10 w/1-5 #16 3#12 w/1 #14 1#10 w/1-3 #14


## Gorilla Nuts Cushion Grip Wire Connectors

		
<b>Orange/Blue- 600V</b> Min #20/Max #12 3#12 4#14 2#14 2#16 2#18 3#20 1#8 3#16 w/1 #10 4#16 w/1 #14 3#20 w/2 #14	<b>Red/Yellow- 600V</b> Min #18/Max #8 2#8 1, 2, 3, 4 or 5 #12 1#10 w/1 or 2 #12 1, 2 or 3 #10 1#10 w/1, 2, 3 or 4 #18 2#10 w/1 #12 2#10 w/2 #16 2#18 1#6 2#10 w/ 1 or 2 #14	<b>Blue/Gray- 600V</b> Min #14/Max #6 2#6 5#10 6#12 2#8 5#12 3#10 4#12 3#12 4#14 4#10 w/1 #12

## DryConn DB Lugs


<b>DB Lug Yellow, Aqua &amp; Orange- 50V</b> Min #14/Max #10

## DryConn Split Bolt Housing


<b>Split Bolt Housing Yellow, Aqua &amp; Orange- 50V</b> Min #14/Max #10

Contact factory for a complete list of wire combinations at 800.633.0232 or visit [www.kinginnovation.com](http://www.kinginnovation.com).





Product not included

## DryConn Counter Display

- The eye-catching display allows the customer, at a glance, to see the assortment of merchandise offered
- The QR Code is shown to educate customers about NEC Code requirements
- The booklet provides extensive information about NEC Code requirements relating to splices in wet and damp locations

SKU# RET300- QTY 1

**DRYCONN®**  
WATERPROOF CONNECTORS

**NEW FOR  
2014!**

## DryConn Window Cling

- 7" long x 1.75" tall
- Double sided for viewing inside and outside of store
- Easy removal; Won't leave residue on windows
- Promotes dependable DryConn® brand

SKU# RET820- QTY 1



Product not included

## DryConn Metal Counter Rack

- 17" Tall x 15" Wide x 5.5" Deep
- Features six (6) product hooks
- Attractive chrome finish
- Includes header card
- Additional hooks allow counter rack to hang on standard pegboard walls


SKU# RET295- QTY 1

**NEW FOR  
2014!**

## DryConn Electrical Know the Code Poster

- 9" x 39" Poster
- Infographic style tells a story
- Educates customer with crucial NEC Code information regarding waterproof connections
- Narrow profile allows poster to be displayed anywhere

SKU# RET330 QTY 1



## AlumiConn Poster

- 18" X 24"
- Educates customer on importance of CPSC approved aluminum wiring repair
- Place anywhere to generate interest in-store

SKU# RET310- QTY 1





Product not included

## Peg Board Backer Panel

- 27" Tall x 24" Wide
- Fits over standard 1" square peg board panels
- Accepts 1/8" or 1/4" peg hooks
- Great for behind the counter product merchandising

SKU# RET350- QTY 1

## 6" Peg Board Hooks

SKU# RET550- QTY 1 Bag of 20



Product not included

## Peg Board Metal Shelf

- 24" Wide x 4" Deep
- Fits over standard 1" square peg board panels
- Holds all DryConn connector canister sizes
- Great for behind the counter product merchandising

SKU# RET650- QTY 1



## Gondola Shelf Strips

- Approximately 24" Width x 1 1/4" Height
- Easily slides into most shelf channels
- Provides attractive brand identification
- Pack of two (2) shelf strips

SKU# RET850- QTY 1

Side 1 Black Series

Side 2 DBR/Y-600



**NEW FOR  
2014!**

## Irrigation X-Pand

- 5' tall display with striking graphics makes a remarkable impression
- Sets up in seconds with no tools required
- Small footprint for easy display anywhere
- Educates contractors on waterproof connector requirements

SKU# RET770- QTY 1



## King Stack-out Display

- 15" Width x 35" Height x 12" Deep
- Assembles in seconds, no tools required
- Holds bagged or canister product for immediate Contractor shopping
- Free standing design allows for use throughout the show room

SKU# RET750- QTY 1

Product not included

## Metal Clip Strips

- 31" Long
- Strong gripping clips hold up to 12 individual products
- Easily merchandise fast moving products such as bagged connectors, cutters, or replacement blades

SKU# RET450- QTY 1

Product not included



# GORILLA NUTS®

CUSHION GRIP WIRE CONNECTORS

Side 1 Gorilla Nuts

Side 2 DryConn Aqua Series



## Movie Poster

- Place anywhere to generate interest in-store
- 18" x 24" Poster
- Movie style poster invites attention

SKU# RET320- QTY 1



## Floor Display

**NEW FOR 2014!**

- Sleek display with attractive graphics for bold branding
- Houses a combination of Gorilla Nuts products
- Sits on casters for quick placement anywhere
- Minimal set-up time

**\*\*Call for pricing on this item\*\***

SKU# RET760- QTY 1

**NEW FOR 2014!**

## Electrical X-Pand

- 5' tall display with striking graphics makes a remarkable impression
- Sets up in seconds with no tools required
- Small footprint for easy display anywhere
- Informative display keeps electricians safe and knowledgeable regarding repetitive stress injury and waterproof connections

SKU# RET780- QTY 1



## Sticker

- Display in-store or use as customer giveaways
- Pack of twenty five (25) stickers

SKU# RET810 QTY 25



## Rebate Pad

- Rebate pad offers customers a FREE hat or T-Shirt with a Gorilla Nuts purchase
- Small footprint for easy display on a counter or at the product location

SKU# RET765 QTY 1







## Display Rack

- 25" Tall x 18" Wide x 18" Deep
- Metal construction, assembles in seconds, no tools required
- Holds 16 Siphon King pumps
- Four sided signage allows for ease of movement and placement anywhere

SKU# RET250- QTY 1

Display shown with 8- 3/6" x 72" Pumps, 4- 24" x 24" pumps, 4- 24" Extension Pumps, 2- Siphon King Syringe Sucker cards and 2- 72" Extension hoses. (Product not included)

## Display Riser

- Attaches to lower shelf of RET250 display
- Riser allows 24" pump (48024) and 24" Extension Pump (48230) to be displayed

SKU# RET252- QTY 1

**NEW FOR  
2014!**

## 9" Accessory Hook

- Fits onto RET250 display without any tools or hassle
- Holds Siphon King accessory items: Syringe Sucker and Extension Hose

SKU# RET251- QTY 1

## Window Cling

- Double sided for viewing inside and outside of store
- 7" long x 4.5" tall
- Easy removal; won't leave residue on windows
- Displays colorful Siphon King logo

SKU# RET825- QTY 1



Window Cling

**NEW FOR  
2014!**

Accessory Hook

Display Riser



**KING INNOVATION ENGINEERING HOTLINE**



**Get your technical questions  
answered by an Engineering  
Expert!**

**Call the King Innovation  
Engineering Hotline!**

**1-877-771-8885**

*Quick response to technical questions*

**Open Monday - Friday 8:00am - 4:00pm CST**

We are **FIERCELY**  
**innovative**

We believe that **FUN** *obsession*  
is an integral part of innovation and business with solving our customer's problems

We are **PASSIONATE**  
about challenging the  
status quo in every  
facet of our lives

We know that taking  
personal responsibility  
creates **TRUST**

**Quality is who we are**

We have the **COURAGE**  
to take risks

We are all **Entrepreneurs**  
**WE DON'T GIVE UP,  
WE DON'T BACK DOWN,  
AND WE WON'T GO AWAY**