

# CABLE STRIPPING AND HANDLING EQUIPMENT



**THE ROTO-SPLIT® FIRST SUCCESSFUL  
BX-MC CABLE CUTTER**



**MULTI-PURPOSE  
CUTTERS, STRIPPERS & PLIERS**



**ROTO-SPIN®  
DATACOM JACKET STRIPPER**



**STRIP-ALL®  
CABLE & WIRE-STRIPPER**



*A SMALL COMPANY WITH BIG IDEAS!®*

392 PACIFIC STREET, STAMFORD, CONNECTICUT 06902  
PHONE (203) 324-0067 ☆ FAX: (203) 324-7844



E-Mail: [Info@SeatekCo.com](mailto:Info@SeatekCo.com)  
Web Site: [www.SeatekCo.com](http://www.SeatekCo.com)

Dear Valued Customers,  
Top quality and service are our #1 priorities at Seatek. We sell only unique labor saving tools which have been thoroughly field tested by professionals. Moreover we offer a lifetime guarantee on most of our hand tools for the best consumer protection available anywhere.

So call, mail, fax, or e-mail to order with confidence TODAY!

Satisfaction Guaranteed  
or Your Money Back!!!

## Welcome to Seatek's New Expanded Catalog



**CALL FOR  
ORDERING  
INFORMATION**



Phone: 203-324-0067  
Fax: 203-324-7844  
E-mail: [info@SeatekCo.com](mailto:info@SeatekCo.com)

Web-Site:  
[www.SeatekCo.com](http://www.SeatekCo.com)


**FAST, EASY SHIPPING!**

No Minimum Order Quantity

U.P.S. Shipping, charges are calculated with weight and distance traveled.



**A SMALL COMPANY  
WITH BIG IDEAS!®**



Seatek Co. Inc. is a manufacturer of hand tools and motorized equipment for electricians that was founded like many other businesses in America, with an idea and hard work.

Seatek Company started with the invention of the **Roto-Split®**, the #1 compact BX, MC & Flex cutter on the market. I wanted to add some lights to a room in my house and was told there was no tool to strip BX - "**just use a hacksaw**". I knew there had to be a better way. The result was the practical and extremely successful **Roto-Split®** which has been making electrician's work easier for over 30 years! Many people told me I was crazy, that this thing would never sell. **Thank you for proving them wrong!**

We've been refining the **Roto-Split®** ever since, taking pride on **selling quality innovative products at the right price!** We are equally proud to be a small business and a pioneer in the field. Most electricians appreciate what it takes to run a small business. It's a great feeling to know that as our record shows, we do not have the need to copy anybody. We provide electricians, contractors and Do-It-Yourselfers with unique tools that save both time and money. Seatek continues its tradition of designing and producing innovative tools for electricians to make your work easier. You can also visit us out our web site at **[www.SeatekCo.com](http://www.SeatekCo.com)** and see why we're called the **Small Company With Big Ideas!®**


Please contact us with any ideas or suggestions you have about our tools, we'd like to hear what you think!

Thanks,

Lucien C. Ducret



# Table of Contents



NEW PRODUCTS REVIEW.....4  
 PEGBOARD DISPLAY CAT. #PB-401.....20  
 ACCESSORIES FOR SEATEK TOOLS.....20

### **BX, MC & Flex Armored Cable Cutters**

ROTO-SPLIT® "THE ORIGINAL" BX CABLE ARMOR STRIPPER CAT. #RS-101.....6  
 ROTO-SPLIT® "SUPER" BX CABLE ARMOR STRIPPER CAT. #RS-101A.....5  
 ROTO-FLEX GREENFIELD CUTTER CAT. #RF-120A.....6  
 ROTO-FLEX EXTENDED RANGE ARMOR CABLE STRIPPER CAT. #RF-120B.....6  
 ROTO-FLEX MC CABLE & GREENFIELD CUTTER CAT. #RF-170.....6

### **Cable Strippers**

JACKET RIPPER CAT. #JR-128.....17  
 ROTO-SPIN™ DATACOM JACKET STRIPPER CAT. #CT-250.....7  
 ROUND CABLE STRIPPER 5/16" TO 1" CAT. #RS-828-KB.....14  
 STRIP-ALL® CABLE AND WIRE STRIPPER 1/4" TO 5/8" CAT. #SA-200.....7  
 STRIP-ALL® EXTENDED RANGE 3/8" TO 7/8" CAT. #SA-200L.....7  
 STRIP-ALL® WITH UR CRIMPER CAT. #SA-200-UR.....7  
 VEE-TWIN CABLE STRIPPER CAT. #VT-270.....8  
 ZIP-STRIPPER® UF CABLE STRIPPER CAT. #ZS-140.....17

### **Motorized Armored Cable Strippers**

POWER CABLE "ROTO-SKINNER"™ CAT. #RSK-125.....9  
 POWER CABLE "ROTO-SKINNER"™ 14.4V CAT. #RSK-145.....8  
 POWER CABLE "ROTO-SKINNER"™ CAT. #RSK-150.....9  
 POWER CABLE "ROTO-SKINNER"™ RING-CUT CAT. #RSK-150RC.....9  
 ROTOMATIC™ BX/MC & FLEX MOTORIZED CUTTERS CAT. #RM-202.....18  
 ROTOMATIC™ BX/MC & FLEX MOTORIZED CUTTERS CAT. #RM-202AA.....18  
 ROTOMATIC™ CUT TO LENGTH CABLE SYSTEM CAT# RD-505.....19

### **Labor Saving Products**

NEW! FOLDING-SAW FS-303 THE PORTABLE HACKSAW!.....17  
 SWING-SAW® PORTABLE HACKSAW AND VISE CAT. #SW-130.....17  
 TOP-SLIDE® SUSPENDED CEILING CABLE GUIDE CAT. #TS-190.....5  
 FISH TAPE PULLER CAT. #FT-210.....5  
 MIGHTY-MITER® RECIPROCATING SAW ACCESSORY CAT. #MM-175.....5

### **Pliers**

OVERVIEW OF PLIERS.....10  
 PLIERS ORDERING INFORMATION.....11  
 NEEDLE NOSE PLIERS, BENT CAT. #LN-PA6-T5.....12  
 NEEDLE NOSE PLIERS 0.787" JAWS CAT. #LN-P5T5.....13  
 NEEDLE NOSE PLIERS 1-1/4" JAWS CAT. #LN-P6T5.....13  
 PROFESSIONAL NEEDLE NOSE PLIERS 1-1/4" JAWS CAT. #ML-NP6-P18.....12  
 PROFESSIONAL NEEDLE NOSE PLIERS 1-1/4" JAWS CAT. #ML-NP6-T7.....13  
 PROFESSIONAL NEEDLE NOSE PLIERS 7/8" JAWS CAT. #ML-NP5-T8.....13  
 PROFESSIONAL LEAD FORMING & CUTTING PLIERS CAT. #LF-P5P-18.....12

### **Diagonal Cutters**

DIAGONAL PLIERS 22 AWG FRONT CUT CAT. #FC-P422-F.....12  
 DIAGONAL PLIERS 10 AWG CAT. #DP-610-B.....15  
 DIAGONAL PLIERS 12 AWG CAT. #DP-512-B.....15  
 DIAGONAL PLIERS 16 AWG CAT. #DP-516-F.....16  
 DIAGONAL PLIERS 18 AWG CAT. #DP-518-F.....16  
 DIAGONAL PLIERS 18 AWG CAT. #DP-518-FLC.....16  
 DIAGONAL PLIERS 20 AWG CAT. #DP-420-FC.....16  
 PROFESSIONAL DIAGONAL PLIERS 12 AWG CAT. #MD-P512B.....15  
 PROFESSIONAL DIAGONAL PLIERS 14 AWG CAT. #MD-P514F.....15

### **Wire Strippers**

MULTI-PURPOSE CUTTERS, STRIPPERS & PLIERS 10 TO 20 AWG CAT. #MW-S10S.....14  
 MULTI-PURPOSE CUTTERS, STRIPPERS & PLIERS 20 TO 30 AWG CAT. #MW-S20S.....14  
 MULTI-PURPOSE CUTTERS AND STRIPPERS 26 TO 16 AWG CAT. #WS-16S.....14



# We Are Always Designing New Labor Saving Products to Make Your Job Easier!

Call, Write, Fax or E-Mail Us Your Comments  
About Our Tools or Any Products You Wish Were Available

**NEW!**

**U.S. Patent 6,308,417**

## Vee-Twin VT-270

Do you have cables that are almost impossible to strip? The Vee-Twin will easily & precisely strip the jacket off these cables. Often the only option for difficult rubber & plastic jacketed cables is to use a knife. This is where the Vee-Twin steps in. It is easy to adjust, safe to use, and can fit into difficult to reach locations.

Range  
5/16" to 2-1/8" O.D.

**Available Now!**

- Works great on difficult to strip cables No more stripping cables with a dangerous open ended knife!
- No other tool on the market can strip as many different cables in such a compact easy to use package!



**NEW!**

## ROTO-SPIN™ DATACOM JACKET STRIPPER

Available Now!!!

**CT-250**  
U.S. Patent 6,662,450

**Perfect to Strip Fiber-Optic, Category 5, Datacom Virtually any Jacketed Cable!**

- Ring & straight cut in one operation from 0.16" to 0.60" dia. with precision
- Innovative rotating cam that makes it foolproof to set the depth of cut
- Clever adjustable stop with scale in inches & mm to strip cables the same length every time



**NEW!**



**By popular demand the larger capacity SA-200L strips 3/8" to 7/8" cable**

- Same great features as the standard size Strip-All with a larger capacity, strips from 3/8" all the way to 7/8" diameter
- Works great on plenum, line cords, NM (flat or round), all-in-one home automation cables, virtually any rubber jacketed cable!
- Calibrated micrometer dial for precise depth of cut adjustment.

**Perfect to strip All-In-One Cable!**



**NEW!**



## STRIP-ALL® WITH UR CRIMPER CABLE AND WIRE STRIPPER

- Combines cable stripping features with a crimper for UR and UY connectors.
- Strip cable by setting razor sharp blade with micrometer dial.
- Perfect tool for data, phone and communications work - one tool does it all!

**Strip, Cut, and Crimp Wires With One Tool!**

**NEW!**

**THE ONLY HACKSAW THAT YOU CAN FOLD AND PACK IN SECONDS!**




## FOLD-A-SAW

- Amazing space saving design that unfolds in seconds to a full sized hacksaw
- Store spare blades in the handle, accepts standard 12" hacksaw blades
- Great for the boat, car & anywhere space is limited!



**NEW!**




## RM-202AA

We have just added an even faster machine to our line, the **RM-202AA**, with **automatic cable cutting** to drastically **reduce labor costs**. Simply set the length to be stripped and insert the cable until it activates the cutting sensor. The **Rotomatic** will then do the rest for you – automatically locate the groove and cut the armor. This eliminates manually finding the cable groove, and pushing a button or pulling a lever to make the cut. For even faster production two Rotomatic **RM-202AA's** can be placed side by side to strip both ends of the cable simultaneously! This cuts the stripping time in half.

The Armored Cable Cutting Experts Since 1973. Ask About Our Custom Tools & Automated Systems.

**"BEST CUTTER ON THE MARKET"**



**SAVE TIME & LABOR WITH A TOP QUALITY TOOL!**

For 14-2 to 10-4 AC, MC, HCF, BX and 3/8" Flex

Accessories: B-102 Replacement Blade B-107 Blade for Aluminum Casing LS-105 Lubricant Stick 101-107 Power Conversion Kit

**ROTO-SPLIT® "SUPER" RS-101A  
BX CABLE ARMOR STRIPPER**

*With Ergonomic Handle & Blade Storage Cartridge*

- A few turns of the crank produces a clean slit through the armor casing which is then twisted and easily removed.
- Unique **quick clamping and release** of the cable. No fuss side loading.
- Preset depth of cut for BX cables to **prevent nicking of the conductors** & an adjustment screw for thin wall MC cables is provided.
- Automatic compensation for cable size variation. A must for the fastest professional job in the trade!

Order RS-101AL equipped with B-107 blade to cut aluminum casing  
Order RS-101AP Power-Split screwgun driven Roto-Split



**"THE POWER SWING-SAW!"**

**MM-175**


U.S. Patents 5,611,146 & 5,806,187

A New Concept in Reciprocating Saw Accessories

Order a complete model for your reciprocating saw which includes MM-175 Vise & Adapter. Need to use on more than one saw or you just bought a different model? Contact Seatek to order the correct adapter.

**MIGHTY-MITER RECIPROCATING SAW ACCESSORY**

- Makes it a snap to cut square any material: round, square or rectangular tubing, wood & plastic molding, angle bar, EMT raceway, threaded rods, etc.
- The vise & clamping assembly swings up towards the reciprocating blade which cuts virtually anything perfectly square.
- Unique clamping system can be disengaged and engaged to quickly adjust the clamping jaws from 3/16" to 2".
- Using the **Mighty-Miter®** prevents the "shakes" and blades will last longer.
- Can be attached to many different reciprocating saws with no modification.



**Choose the Mighty-Miter® for your Reciprocating Saw**

MM-175RS	Mighty-Miter for Milwaukee® Sawzall®
MM-175SS	Mighty-Miter for Milwaukee® Super-Sawzall®
MM-175OR	Mighty-Miter for Milwaukee® Orbital-Sawzall®
MM-175BP	Mighty-Miter for Milwaukee® 18 Volt Sawzall®
MM-175DW	Mighty-Miter for DeWalt® DW-303 Saw

All brands and product names are trademarks or registered trademarks of their respective companies

**"MAKE IT EASY ON YOURSELF"**



**TS-190**

U.S. Patent 4,865,294

**TOP-SLIDE®**

**SUSPENDED CEILING CABLE GUIDE**

- At last a low cost product to save you time and aggravation while pulling cables in plenum.
- The patented Top-Slide is designed to snap onto a ceiling tee bar.
- With two Top-Slides in place, pulling any type of cable over tee bars is a cinch, even armored cable with kinks in it.
- The Top-Slide spells the end of damaged ceiling tees, and best of all one man can do the job instead of two!

**GRAB A TOP-SLIDE & SEE HOW SIMPLE IT IS TO PULL CABLES OVER THE CEILING GRID!**

**"GUARANTEED NO KINKS!"**



U.S. Patent 4,746,099

Order FT-210 Fish Tape Puller



**THE "HINGENIOUS"  
NEW CAM-ACTION HINGED  
FISH TAPE PULLER**

- Two handed action has twice the pulling force, the more you pull the more it grabs!
- Stop putting kinks in your fish tape or grazing your face with your pliers.
- Precision hardened steel casting, 100% made in America, 8 oz. 11" long.
- A must for your tool box!

**EASY DOES IT WITH TWICE THE PULLING FORCE!**



ON THE INTERNET LOG ON TO [www.SeatekCo.com](http://www.SeatekCo.com) - WHERE QUALITY & SMART ENGINEERING COME TO LIFE!

## "THE ORIGINAL"



RS-101

Accessories: B-102 Replacement Blade B-107 Blade for Aluminum Casing LS-105 Lubricant Stick

## LOW COST ROTO-SPLIT® RS-101 BX CABLE ARMOR STRIPPER

*Now With Ergonomic Handle*

- The industry standard since 1973, the rugged patented Roto-Split works exactly like RS-101A "Super", but features a thumb screw to clamp and release the cable. One part does it all!
- This field proven quality cutter accepts BX, AC, MC & HCF cable from 14/2 to 10/4 as well as 3/8" Flexible Conduit (Greenfield).
- Simplicity at its best!

**"QUALITY YOU CAN FEEL!"**

## "TWO TOOLS IN ONE!"



RF-120B


*Carry One Tool Instead of Two!*

Accessories B-102 Replacement Blade B-107 Blade for Aluminum Casing LS-105 Lubricant Stick

## ROTO-FLEX RF-120B EXTENDED RANGE CABLE ARMOR STRIPPER

*With New Ergonomic Handle & Blade Storage Cartridge*

- Strip armored cables from 14-2 to 4-3 & Flex from 3/8" to 3/4" trade size with one tool!
- With the Adapter In cut 3/8" Flex, with the Adapter Out cut 1/2" and 3/4" Flex
- The secret is in the hinged adapter which controls the depth of cut **AUTOMATICALLY**, eliminating the danger of damaging the wires when switching from large to small cables.



Adapter In

Adapter Out

## "NOW WITH QUICK CLAMPING"



U.S. Patents 3,851,387, 4,359,819 & 4,769,909

RF-120A

Accessories: B-102 Replacement Blade B-107 Blade for Aluminum Casing LS-105 Lubricant Stick

## ROTO-FLEX RF-120A GREENFIELD CUTTER

*With New Ergonomic Handle & Blade Storage Cartridge*

- This tool works on the same principle as the Roto-Split "Super" but accepts 1/2" and 3/4" Greenfield/Flex & large size BX & MC up to 4/3.
- Now features **quick clamping and release** of the cable.
- A few turns of the crank produces a slit through the armor casing which can then be separated easily.
- Clean cut parallel to the cable axis eliminates deburring.

**SAVE TIME - CUT COST WITH A TOP QUALITY TOOL!**

## "GIANT SIZE"



U.S. Patent 4,977,671

RF-170

Accessories: B-102 Blade for Steel Casing B-107 Blade for Aluminum Casing B-108 Blade for Steel or Aluminum LS-105 Lubricant Stick

## ROTO-FLEX RF-170 MC CABLE AND GREENFIELD CUTTER

*With New Ergonomic Handle & Blade Storage Cartridge*

- An innovative tool with a unique adjustable cable clamping bracket with 1" travel to accept a wide range of cable sizes.
- Strips MC cable from .82" to 1.82" as well as cutting Greenfield from 1/2" to 1-1/2" trade size.
- A unique detented sliding top housing allows the cutting of small or wide convolutions as needed.

**A GREAT LABOR SAVING DEVICE!**



The Armored Cable Cutting Experts Since 1973. Ask About Our Custom Tools & Automated Systems.

**STRIP-ALL® CABLE AND WIRE STRIPPER**

*HI-TEK Stripper for Non-Metallic Cables*

- Strips plenum, computer & communication cables, line cords, NM (flat or round), coax, twisted jacketed cables such as Category 5, plus many more!
- Calibrated micrometer dial for precise depth of cut adjustment.
- Handy built in wire stripper and folding utility knife blade.
- Easy blade replacement & **spare blade cartridge** included with each tool.
- Straight cut jacketed cables from 1/4" to 5/8" & ring cut up to 1/2"
- Use **A-201 Adapter** to strip & ring cut wires as small as 1/8".



U.S. Patent 5,337,479

SA-200SK Wire Stripper & Utility Knife (1/4" to 5/8" OD)  
 SA-200S Wire Stripper (1/4" to 5/8" OD)  
 SA-200-UR Wire Cutter, UR Crimper & Adapter (1/8" to 5/8" OD)  
 SA-200L Large Extended Range (3/8" to 7/8" OD)



A-201 Adapter-Reducer



B-202 Replacement Blade

*All Models Now Include an A-201 Adapter!*

**NO NEED TO REACH FOR PLIERS!**

Available Now!!!



SA-200-UR  
 U.S. Patent 5,337,479

SA-200-UR WITH WIRE CUTTER, UR CRIMPER AND A-201 ADAPTER



**STRIP-ALL® WITH UR CRIMPER CABLE AND WIRE STRIPPER**

*Strip, Cut, and Crimp Wires With One Tool!*

- Combines cable stripping features with a crimper for UR and UY connectors.
- Strip cable by setting razor sharp blade with micrometer dial.
- Cut wire from 20 to 24 AWG with built in wire cutter.
- Includes **A-201 Adapter-Reducer** to strip & ring cut wires as small as 1/8".
- Perfect tool for data, phone and communications work - one tool does it all!



A-201 Adapter-Reducer



B-202 Replacement Blade

**NEW LARGER CAPACITY!**

Available Now!!!



SA-200L  
 U.S. Patent 5,337,479

SA-200L EXTRA-LARGE CAPACITY!

(SA-200L does not include wire stripper, adapter not available)



**By popular demand the SA-200L, a larger capacity model now strips 3/8" to 7/8" cable**

- Same great features as the standard size Strip-All with a larger capacity
- Strip cables from 3/8" all the way to 7/8" diameter
- Works great on plenum, line cords, NM (flat or round), all-in-one home automation cables, virtually any rubber jacketed cable!
- Calibrated micrometer dial for precise depth of cut adjustment.
- Easy blade replacement & **spare blade cartridge** included with each tool.



Perfect to strip All-In-One Cable!



B-202 Replacement Blade

**"PRECISION STRIPPER!"**



Available Now!!!




CT-250  
 U.S. Patent 6,662,450

Perfect to Strip Fiber-Optic, Category 5, Datacom - Virtually any Jacketed Cable!

**ROTO-SPIN™ DATACOM JACKET STRIPPER**

- Speed up the stripping of round communication cables with the innovative **CT-250**, in one operation it can both ring & straight cut with its cutting blade swiveling on a precision miniature ball bearing.
- Strip cables from 0.16 to 0.60" diameter, including, Fiber-Optic, Category 5, Datacom, phone and virtually any round rubber jacketed cable.
- Innovative rotating cam makes it foolproof to correctly set the depth of cut with 16 settings from 0.010" to 0.120" in increments of 0.005" and 0.010".
- Strip the same length every time thanks to a clever adjustable stop with a scale in both inches & mm
- Two position quick cable clamping vee for large and small cables
- Easy blade replacement (B-252) with storage provided in the cable stop
- Weight 3oz. (30 Grams) Length 6" (15cm)



B-252 Replacement Blade



CALL 1-203-324-0067 TO ORDER FROM SEATEK - WHERE QUALITY & SMART ENGINEERING COME TO LIFE!

**NEW!**

**Available Now!**



## Vee-Twin VT-270

Do you have cables that are almost impossible to strip? The Vee-Twin will easily & precisely strip the jacket off these cables. Often the only option for difficult rubber & plastic jacketed cables is to use a knife. This is where the Vee-Twin steps in. It is easy to adjust, safe to use, and can fit into difficult to reach locations. Strip in place, even around curved cables!


Range  
5/16" to 2-1/8" O.D.

U.S. Patent  
6,308,417

- Thanks to a convenient sliding blade support the **Vee-Twin** quickly changes size to strip any cable up to 2-1/8"
- The **Vee-Twin** features a blade that can be retracted and rotated 90°, allowing you to switch between ring and straight cutting without removing the tool from the cable!
- Unique vee guide permits the cable to smoothly rotate in any direction, even create "windows" in the cable jacket!
- Depth of cut setting accurate to .001" thanks to a precision micrometer. No need to adjust blade depth when switching from ring to straight cut. Max depth of cut 1/4" (6mm).
- No other tool on the market can strip as many different cables in such a compact easy to use package!
- 5.5" long X 2.6" Deep X 2.4" Wide, Weight: 11 ounces



Replacement  
Blade B-272



Adapter A-271

### A-271 Vise Adapter

**NEW!**



New Adapter **A-271** for the Vee-Twin! Enables you to recover scrap material quickly and easily. Simply attach the **A-271** to the **Vee-Twin** and clamp it in a vise. Set the depth of cut and simply pull the cable through the Vee-Twin to remove long lengths of cable jackets.

**"NOW WITH MORE POWER"**

**NEW!**

## ROTO-SKINNER 14.4V CABLE SLITTER

*Cable Preparation Tool For All Power Cables*



RSK-145

Patent Pending

- When extra power is needed use this **14.4V** model to skin long cable lengths
- Equipped with an adjustable cable guide accepts cables from **5/8" to 5" O.D.**
- Strip steel, aluminum or plastic jacketed cables such as: Okonite, CLX, Rockbestos, Flexgard, or MC.
- Save hours of tedious labor when making cable connections.
- Depth of cut control adjustable from **0 to 5/16"** with thumb screw & lock
- Maximum **depth of cut 5/16"**, 14.4V variable speed motor, 11" long, 4 lbs.
- Safe! Spring loaded blade guard. Order Replacement Blade **Cat. B-151**

***The Roto-Skinner Gives You The Cutting Edge Over The Competition***





# ARMORED CABLE STRIPPING MACHINES & POWER TOOLS

The Armored Cable Cutting Experts Since 1973. Ask About Our Custom Tools & Automated Systems.

**"STRIP IT THE EASY WAY"**



## ROTO-SKINNER CABLE SLITTER

*Cable Preparation Tool For All Power Cables*

- Skin long lengths of cables the easy way with power to spare!
- Equipped with an adjustable cable guide accepts cables from **5/8" to 5" O.D.**
- Strip steel, aluminum or plastic jacketed cables such as: Okonite, CLX, Rockbestos, Flexgard, or MC. Maximum **depth of cut 5/16"** (8mm)
- Save hours of tedious labor when making cable connections.
- Depth of cut control with adjustable thumb screw & lock (No tools needed).
- Safe! Spring loaded blade guard.
- **RSK-125** operates on 115V, 2.8 Amps variable speed motor, 11" long, 4 lbs.

*The Roto-Skinner Gives You The Cutting Edge Over The Competition*

Accessories: Replacement Blade B-153 and LS-105 Lubricant Stick

**WORK SMARTER NOT HARDER!**



## RSK-150 ROTO-SKINNER STRAIGHT CUT

- The **RSK-150** is a clever cordless motorized cutting tool that removes the armor & insulation of tough cables with a circular saw blade.
- Exclusive cable guide which can be adjusted to accept cables from **5/8" to 12"** (15mm to 300mm) diameter.
- Makes it a snap to strip steel or aluminum clad armor cables such as Okonite, CLX, Rockbestos, Flexgard, MC or plastic jacketed cables.
- Depth of cut is set with micrometer and feeler gage & then locked into place. Maximum **depth of cut 5/16"** (8mm.)
- Uses removable battery pack **BP-152** which can be fully recharged in 1 hour. A full charge will give about 2 hours of use (depending on material cut)
- The cordless low voltage **Roto-Skinner** is ideal for damp locations. Plus there's no linecord - you have total freedom of movement and portability.
- The cable guide can be swung out of the way to cut panels up to 1/2" thick.

Lightweight at 4 lbs, including battery pack, the **RSK-150** easy to handle anywhere!

*Battery Pack and Charger Sold Separately*

*Save hours of tedious labor when making cable connections*

Accessories: B-151 Replacement Blade, LS-105 Lubricant Stick, C-153 Battery Charger, BP-152 Battery Pack

RSK-150RC RING-CUT



## RSK-150RC ROTO-SKINNER RING-CUT

- The **RSK-150RC** uses a battery operated circular saw: simply rotate 360° around the cable to make perfect ring-cuts on plastic & metal clad jackets.
- Ring-Cut cables from **1" to 5" OD** (13mm to 300mm), **depth of cut 5/16" max.**
- Depth of cut can easily be adjusted with a micrometer and locked into place.
- Features convenient inch & metric scales for quickly moving & locking the hinged cable vee support to the desired size anywhere along the cable.
- **SC-150 Straight Cut Adapter** converts **RSK-150RC** to straight cut mode.
- Quickly switch between straight and ring-cut with a removable Quick-Pin
- Uses removable battery pack **BP-152** which can be fully recharged in 1 hour.
- **RSK-150RC** weighs 6.5lbs with battery, 4lbs with battery & straight cut platen.

SC-150 Straight Cut Adapter

**SAVE HOURS OF ARDUOUS WORK WITH OUR POWER CABLE ROTO-SKINNERS**

*Battery Pack and Charger Sold Separately*

Accessories: B-151 Replacement Blade, LS-105 Lubricant Stick, C-153 Battery Charger, BP-152 Battery Pack



FAX 203-324-7844 TO ORDER FROM SEATEK - WHERE QUALITY & SMART ENGINEERING COME TO LIFE!


## Seatek is Proud to Introduce a New Line of Diagonal Pliers, Cutters, & Tools for Communications, Security, Electronic & Electrical Work

**In the Seatek tradition, these precision hand tools are some of the best quality and most comfortable handtools you will own. Here are some of the highlights of our new line of diagonal cutters, pliers and speciality tools for the discriminating craftsman.**

- These tools have very comfortable grips thanks to ergonomically shaped, soft PVC handles that are great for repetitive work.
- Diagonal cutters have precision ground cutting edges which makes cutting a snap, reducing cutting forces and operator fatigue
- Precision pivots & reamed bores ensures smooth opening & closing action.
- Pliers are made with precision ground jaw profiles and serrations
- Mechanical stop prevents overstressing the jaws when cutting wires
- Patented safety clip to catch excess wire is available on certain models

### **CUT WITHOUT STRESS**

Cutting edges of Seatek's pliers overlap slightly while cutting. THIS SHEARING ACTION CUTS WITH LESS FORCE AND LESS MECHANICAL STRESS ON THE COMPONENT.



Patented  
Safety Clip  
Accessory  
Available



Patented  
Recovery Spring  
On Many Models





Standard Insulated handles  $10^{13}$  ohms in stock

Resistance values in accordance with DIN 51953 and ASTM - D - 257  
 Conductive & Dissipative handles are available on special order - call for delivery time

### WHEN TO USE

#### INSULATED HANDLES: (Yellow)

This material is designed to work on low current. Normally supplied unless otherwise specified.

#### DISSIPATIVE HANDLES: (Black)

Applicable when components are sensitive to electrostatic charges. Designed to discharge uniformly, in general between 1 and 2 seconds.

#### CONDUCTIVE HANDLES: (Black)

Applicable when electrostatic charges have to be discharged immediately, however, due to the quick discharge time it may damage sensitive components. It is therefore restricted to specific applications.

TO COPE WITH THE INCREASING REQUESTS FOR MATERIAL WHICH CAN CONTROL AND PREVENT ELECTROSTATIC PHENOMENA ALL TOOLS SHOWN IN THIS CATALOGUE CAN BE SUPPLIED WITH CONDUCTIVE HANDLES "C", OR WITH DISSIPATIVE HANDLES "D".

Add the letter "C" after the catalog number e.g. (conductive).

Add the letter "D" after the catalog number e.g. (dissipative).

### PLIERS ORDERING INFO

HANDLE \_\_\_\_\_



Handles  
 C (Conductive)  
 D (Dissipative)

SAFETY CLIP \_\_\_\_\_



SC

Please add the initials for each item after the catalog number.

Please note that PVC handles are normally supplied if no suffix is indicated after the catalog number.

To order conductive handles add the letter "C" after the catalog number

To order dissipative handles add the letter "D" after the catalog number

To order pliers with the safety clip add the initials "SC" after the catalog number:

For Example: DP-610-B-D-SC is a diagonal plier with dissipative handles & safety clip



**"EXTRA STRONG GRIP"**



**ML-NP6-P18**

**PROFESSIONAL  
NEEDLE NOSE PLIERS**

- Long needle nose pliers - length of jaws 1 1/4"
- Square, serrated jaws for extra gripping power
- Coil spring return for smooth action
- Heavy-duty contoured handles provide a super comfortable grip
- Overall length of pliers 5 1/2"

Precision Ground Jaws!



**"MAKE IT EASY ON YOURSELF"**





**LN-PA6-T5**

**BENT NEEDLE NOSE PLIERS**

- Long needle nose pliers with 1" long jaws that are angled at 45°
- Tapered, serrated ground jaws for extra gripping power
- Angled jaws let you work in hard to reach spots
- Soft spring return reduces fatigue
- Overall length of pliers 5 1/2"

Great For Hard to Reach Places!



**"COMPACT SIZE"**



**FC-P422-F**

**FRONT CUT  
DIAGONAL PLIERS**

- Front cut pliers, angled at 30°
- Lets you cut in tight spots
- Cut wires up to 22 AWG
- Light spring return force helps reduce fatigue
- Custom contoured handles provide a perfect fit
- Overall length of pliers 4 3/4"

Make Precision Flush Cuts  
The Easy Way!



**"UNIQUE LEAD FORMING"**




**LF-P5P-18**

**PROFESSIONAL LEAD FORMING  
& CUTTING PLIERS**

- Specially designed tool for forming & cutting of resistors & leads of other electronic components in one stroke
- Adjustable stop allows for variable length of cut
- Smooth coiled spring return
- Custom contoured handles provide a great feel
- Overall length of pliers 5 1/2"

Save Time & Aggravation!



**"COMPACT SIZE"**




**LN-P5T5**

**NEEDLE NOSE PLIERS**

- Short needle nose pliers - length of jaws .787"
- Tapered, ground serrated jaws for extra gripping power
- Unique spring return reduces fatigue for repetitive work
- Custom contoured handles provide an extra nice feel
- Overall length of pliers 5 1/2"

Top Quality & Craftsmanship!



**"LONG REACH"**



**LN-P6T5**


**NEEDLE NOSE PLIERS FOR DELICATE WORK**

- Long needle nose pliers - length of jaws 1 1/4"
- Soft feel contoured handles provide a unique comfort grip
- Tapered, ground serrated jaws for maximum gripping power
- Soft spring return reduces fatigue
- Overall length of pliers 6"

Reach In Tight Spots



**"TOP NOTCH QUALITY"**



**ML-NP5-T8**

**PROFESSIONAL NEEDLE NOSE PLIERS**

- Short needle nose pliers - length of jaws 7/8"
- Tapered, ground serrated jaws for extra gripping power
- Coiled spring for positive return
- Heavy-duty contoured handles provide a quality feel
- Overall length of pliers 5 1/2"

Superb Precision & Strength!



**"PRECISION & QUALITY"**



**ML-NP6-T7**

**PROFESSIONAL NEEDLE NOSE PLIERS**

- Same as above with longer jaws - 1 1/4" long
- Tapered, ground serrated jaws for maximum gripping power
- Coiled spring return makes repetitive tasks easier
- Heavy-duty oversized handles provide a solid feel
- Overall length of pliers 5 1/2"

Comfort Grip!




**"TWO TOOLS IN ONE"**



**WS-16S**

**MULTI-PURPOSE CUTTER & STRIPPER**

- Multi-purpose tool that can be used to both cut and strip wires
- Strips wires from 26 to 16 AWG with vee notch
- Spring return & push button lock
- Custom contoured handles for the most comfortable grip
- Incredibly versatile tool, 5 1/2" long



Handy Tool For Your Toolbelt!


**"A MUST FOR YOUR TOOLBOX"**



**MW-S20-S**

**MULTI-PURPOSE CUTTERS, STRIPPERS & PLIERS**

- Multi-purpose tool to cut, strip and pull wires
- Strip wires from 20 to 30 AWG with 6 precision ground wire gage notches
- Handy built-in pliers tip & shearing knife edge
- Coil spring return and locking latch
- Custom contoured handles reduce user fatigue



Great Combo Tool!


**"MAKE IT EASY ON YOURSELF"**



**MW-S10-S**

**MULTI-PURPOSE CUTTERS, STRIPPERS & PLIERS**

- Same as above but strips wires from 10 to 20 AWG
- Multi-purpose tool to cut, strip and pull wires with 6 precision ground wire gage notches
- Handy built-in pliers tip & shearing knife edge
- Coil spring return and locking latch
- Custom contoured handles reduce user fatigue



Great Tool for Electricians!

**"CABLE STRIPPER"**




**RS-828-KB**

Order B-151 Replacement Blade

**ROUND CABLE STRIPPER**

With Replaceable Blade

- Ring cut & straight cut cable from 5/16" to 1" (8mm to 28mm)
- Swivel blade & knife lets you strip many different kinds of cables
- Great way to strip jacketed cables, PVC, rubber, neoprene etc.
- Make splices or strip ends of cables quickly and easily
- Adjustable blade depth of cut
- Equipped with knife blade and protective cap and spare blade



Labor Saving Tool!




**"COMPACT SIZE"**



**DP-512-B**

**DIAGONAL PLIERS**

- Specially treated chamfered cutting jaws to cut heavier gage copper wire with ease
- Unique soft spring return reduces operator fatigue
- Contoured handles provide an extremely comfortable grip
- Made of special high quality steel
- Cut wires up to 12 AWG
- Overall length of pliers 5"



Clips wires in a Snap!

**"LARGE SIZE"**



**DP-610-B**

**DIAGONAL PLIERS**

- Chamfered cut diagonal pliers
- Heavy duty to handle larger material
- Special light spring return for easier repetitive work
- Custom contoured handles provide a superior grip
- Head is angled at 21° and cuts wires up to 10 AWG
- Overall length of pliers 6"



Easy Does It!


**"PROFESSIONAL QUALITY"**



**MD-P514-F**

**PROFESSIONAL  
DIAGONAL PLIERS**

- Flush cut diagonal pliers for precision work
- Positive coil spring return
- Heavy-duty contoured handles provide a soft feel in your hands
- Cut wires up to 14 AWG
- Made of special high quality steel
- Overall length of pliers 5"



High Quality & Precision!


**"CUTS MILD STEEL WIRE"**



**MD-P512-B**

**PROFESSIONAL  
DIAGONAL PLIERS**

- Specially treated cutting edges
- Chamfered stubby jaws for cutting of heavier gage wire
- Coiled spring return for positive feel
- Custom contoured thick handles provide the feel of superior craftsmanship
- Cut mild steel wires up to 24 AWG & copper wires up to 10 AWG (do not use on spring wire)
- 0



Extra-Heavy Duty Cutting In a Compact Size



**"BEST VALUE ON THE MARKET"**



**DP-518-FLC**

**LOW COST  
DIAGONAL CUTTING PLIERS**

- Flush cut diagonal pliers
- Excellent tool for fine electronic or electrical work
- Light spring return
- Soft contoured handles give a comfortable grip
- Head is angled at 21°, cut wires up to 18 AWG
- Overall length of pliers 5"

**Lightweight & Compact!**



**"LOW SPRING PRESSURE"**



**DP-420-FC**

**SMALL DIAGONAL  
CUTTING PLIERS**

- Flush cut diagonal pliers
- Narrow jaws & bevelled lower external edges to cut in hard to reach spots & for extremely delicate work
- Ergonomic handles provide the best handling feel
- Head is angled at 21°, cut wires up to 20 AWG
- Overall length of pliers 4 3/4"

**Cut in Tight Spots!**



**"ERGONOMIC HANDLES"**



**DP-518-F**

**DIAGONAL CUTTING PLIERS**

- Flush cut diagonal pliers
- Narrow jaws for cutting in narrow spaces
- Low force spring return helps to prevent fatigue
- Head is angled at 21°, cut wires up to 18 AWG
- Overall length of pliers 5"

**Great for Precision Work!**



**"BUILT TO LAST"**



**DP-516-F**

**DIAGONAL PLIERS**

- Flush cut diagonal pliers
- Great for electronics and electrical work & medium gage wire
- Soft spring return reduces operator fatigue
- Heavy duty contoured handles provide a perfect fit
- Head is angled at 21°, cut wires up to 16 AWG
- Overall length of pliers 5"


**Quality You Can Feel!**





**"SPEED UP INSTALLATIONS"**

**NEW!**



**JACKET RIPPER JR-128**

**THE NEW JACKET RIPPER**


- **The Safe Way** to remove the jacket of medium & large multiconductor cables
- Use on entrance cable, plenum, phone cables, instrumentation, multi-pair & tray cables. Even strip the jacket from Liquid-Tight, Flex or MC!
- No more **dangerous razor blades** or knives!
- Blade can be easily replaced, simply remove the two screws holding the blade and install a new blade
- Sturdy steel construction with an ergonomic rubberized handle
- Lightweight at 3 ounces, length 5-1/2"

*Cut Costs & Promote Safety!*



**HACK & PACK!**

**NEW!**



**FOLD-A-SAW FS-303**

**THE ONLY HACKSAW THAT YOU CAN FOLD AND PACK IN SECONDS!**

- Amazing space saving design that unfolds to a full hacksaw in seconds
- Fully adjustable tension setting holds blade with high force to improve accuracy and blade life
- Unique quick release blade mechanism locks the blade securely
- Store spare blades in the handle, accepts regular hacksaw blades
- Great for the boat, car anywhere with limited storage space
- Lightweight, high strength aluminum & steel construction
- Weight 3lbs., length 12" & width folded only 3"

**TAKE IT ANYWHERE!**

**"WORLD'S FIRST"**



The combined action of the back & forth motion of the top lever & the squeezing pressure cuts easily through most material!

**SWING-SAW® SW-130 PORTABLE HACKSAW AND VISE COMBO!**

- First portable hand tool to cut liquid tight & surface mount raceways square!
- Self clamping adjustable vise that opens to 1-1/2".
- Cuts round and square material, copper, aluminum and plastic tubing, even EMT, threaded rods, and extrusions.
- Top lever folds and the top latches down for easy storage.
- Thousands of applications in Automotive, Aviation, Boating, Construction, Plumbing and Electrical installations!



**CUT ALL THESE SHAPES & MORE!**

Order: **B-109-18 Blade** for thick wall tubing **B-109-24 Blade** for thin wall tubing & metal hose

**"WHEN SAFETY IS AT A PREMIUM"**



Order BZ-112 Replacement Blade

**ZIP-STRIPPER®**

**UF CABLE STRIPPER (GUIDED KNIFE)**

- Time saving tool engineered for safety with its enclosed super sharp blade, works even in freezing weather!
- Adjustable cable guides prevent nicking of wires.
- UF cable is pierced by a razor sharp blade & the cable insulation is stripped by pulling it through the enclosed blade cavity twice.
- Also works with NM - only one stroke needed.
- Blade storage compartment is provided inside the Zip-Stripper.
- Strips 14-2, 12-2 & some 10-2 UF cables & makes a cinch of a tough job.


**THE FASTEST WAY TO STRIP UF & KEEP YOUR BODY PARTS INTACT**





# ARMORED CABLE STRIPPING MACHINES & POWER TOOLS

The Armored Cable Cutting Experts Since 1973. Ask About Our Custom Tools & Automated Systems.



RM-202A

## ROTOMATIC BX/MC & FLEX MOTORIZED BENCH TOP CUTTERS **INCREASE PRODUCTION AND CUT COSTS!**

The heavy-duty ROTOMATICS are the culmination of years of experience in armored cable cutting technology & are used in the production lines of major armored cable manufacturers. Ideal for the manufacturing of "Whips" and stripping MC/BX cable in pre-cut lengths as well as job site finishing work. Open channel construction allows cutting or stripping **anywhere along the cable**.



RM-202M

- Clean cut parallel to the cable axis **eliminates deburring** of flexible conduit ends
- Adjustable cable guide allows lateral adjustment for different cable pitches.
- **All Rotomatics** (except RM-202M) require 40 psi air pressure. Each machine includes a pressure regulator, air gauge and large valve actuator.
- **RM-202A** strips MC from 14-2 to 8-4, cuts 3/8" Flex (1/2" Flex with pin **SP-233**).
- **RM-202M** strips MC from 14-2 to 4-4, cuts both 3/8" & 1/2 Flex with pin **MP-269**. Uses a manually actuated lever to clamp & cut the cable
- Dimensions 8"H x 7"W X 11"D, 22 lbs., 115 VAC.

U.S. Patents  
4,103,578 & 4,169,400


Accessories: B-108 Replacement Blade B-103 Blade With Fine Teeth LS-105 Lubricant Stick



## "AUTOMATIC CUTTING"

## ROTOMATIC RM-202AA

Automatically strip the ends of armored flexible cable!



RM-202AA

We have just added an even faster machine to our line, the **RM-202AA**, with **automatic cable cutting** to drastically **reduce labor costs**. Simply set the length to be stripped and insert the cable until it activates the cutting sensor. The **Rotomatic** will then do the rest for you – automatically locate the groove and cut the armor. This eliminates manually finding the cable groove, and pushing a button or pulling a lever to make the cut. For even faster production two Rotomatic **RM-202AA**'s can be placed side by side to strip both ends of the cable simultaneously! This cuts the stripping time in half.

*THANKS TO PRODUCTIVITY INCREASES THE RM-202AA PAYS FOR ITSELF MANY TIMES OVER !*

Accessories: B-108 Blade for Steel Casing B-103 Blade With Fine Teeth LS-105 Lubricant Stick



## "EXTENDED RANGE"

## ROTOMATIC RM-202 B & C

Now Strip Larger Cable Sizes



RM-202B

These new ROTOMATICS have the same great features as our original models, now with expanded capacity!

- **RM-202B & C** require 40 psi air pressure. Each machine includes a pressure regulator, air gauge and large valve actuator.
- **RM-202B** has a range of 3/8" to 3/4" Flex. Use pin **SP-233** for 3/4" Flex, pin **SP-233** for 1/2" Flex and pin **LP-269** for 3/8" Flex
- **RM-202C** has a range of 3/4" to 1-1/4" Flex. Use pin **SP-233** to cut 1-1/4" Flex and pin **SP-300** to cut 3/4" and 1" Flex.
- Dimensions 8"H x 7"W X 11"D, 22 lbs., 40 psi, 115 VAC.

U.S. Patents 3,851,387, 4,359,819 & 4,769,909

Accessories: B-108 Blade for Steel Casing B-103 Blade With Fine Teeth LS-105 Lubricant Stick

\* Flex & AWG cable sizes vary from manufacturer, confirm size by measuring actual O.D.

ROTOMATIC CABLE RANGES	Model	Flex Range	Standard Pin	Optional	AWG Range*	O.D. Range
	RM-202A	3/8" TO 1/2"	3/8" LP-269	1/2" SP-233	#14-2 TO #4-4	0.42" TO 0.92"
	RM-202AA	3/8"	3/8" AA-130	-----	#14-2 TO #10-4	0.42" TO 0.54"
	RM-202M	3/8" TO 1/2"	3/8" & 1/2" MP-269	-----	#14-2 TO #4-4	0.42" TO 0.92"
	RM-202B	3/8" TO 3/4"	3/4" SP-233	3/8" LP-269 1/2" SP-233	#14-2 TO #2-4	0.42" TO 1.10"
	RM-202C	3/4" TO 1-1/4"	1-1/4" SP-233	3/4" TO 1.0" SP-300	#4-4 TO #1-3	1.00" TO 1.70"



ON THE INTERNET LOG ON TO [www.SeatekCo.com](http://www.SeatekCo.com) - WHERE QUALITY & SMART ENGINEERING COME TO LIFE!

# CABLE MEASURING & CUTTING SYSTEM

**AUTOMATED CUT TO LENGTH SYSTEM SHOWN HERE WITH A  
PT-501X PAY-OFF TABLE, RD-505A DRIVE & AV-525 CUT-OFF SAW**



Call for a Quotation  
on this Custom Built  
and Made to Order  
Factory Direct System

This unique cable measuring unit accepts any cable up to 15/16" O.D. Shown here with the PT-501X on the left and the AV-525 cut-off saw on the right

## INCREASE PRODUCTIVITY CUT COSTS!

The Roto-Drive is a new concept in the cable measuring field. It is particularly suited for cut to length operations ranging from 5" up to 99,999" in .100" increments. This bench type measuring unit is compact and narrow making for an efficient cut to length system since it is within the easy reach and control of the operator.

## STREAMLINE YOUR OPERATION!

Operation is extremely simple. A button in front of the machine lifts the upper roller to load the cable. A trim cut is made when used in conjunction with a cut-off unit and the electronic counter is set to the length and number of pieces (RD-505A). The "start" push button or foot switch is depressed and "presto" the Roto-Drive dispenses and feeds the cable to a cut-off unit at 24" per second. The cycle repeats until the number of pieces wanted is reached. (RD-505A)

A prescaler adjustment allows the counter to be calibrated to the exact measured cable length. Roto-Drive dispenses the exact amount of cable required eliminating costly rejects and rework. Accessories are available such as motorized payoff with dancer for heavy coils or when cut to length dimensions tolerances exceed normal specifications.

## TECHNICAL DATA

- RD-505A was designed to be maintenance free; ball bearings or self-lubricated bronze bushings are used throughout.
- The driving rollers are air cushioned-pressurized and are covered with a polyurethane compound for toughness and long life. The upper and lower rollers are both driving rollers to eliminate slippage and are synchronized with a unique "lubrication free" timing belt system.
- Uses a sophisticated solid state drive and control system. It features an electronic counter with large display for setting the length of the cable, which can be adjusted from 6" to 99,999" in increments of .100". The batch counter stops the machine automatically when the preset number of pieces is reached; a totalizer is built in the counter.
- The highest quality components have been selected to provide trouble free operation in excess of 5 million cycles.
- Dimensions are 8"W x 15 1/2"H x 24" and at 95 lbs. this unit is easy to move. Power required is 220 V.A.C. single phase, 4 amps. Capacity: 15/16" max. Measured accuracy: within 1% for jacketed cables, +/- 1% for Flex and armored cables when convolution play is 1/2" per ft., maximum. We recommend the use of a motorized payoff unit with dancer when heavy reels are used or when cut to length tolerances are beyond normal specifications.



*A SMALL COMPANY WITH BIG IDEAS®*

392 PACIFIC STREET, STAMFORD, CT 06902  
PHONE (203) 324-0067 ☆ FAX (203) 324-7844 ☆ [www.SeatekCo.com](http://www.SeatekCo.com)




# ROTOMATIC RM-202AA

BX, MC & Flex  
Motorized  
Bench Top Cutter



Automatically strip the end  
of armored flexible cable!



U.S. Patents  
4,103,578 & 4,169,400  
other Patents Pending

















Cuts 3/8" Flex  
(0.54 Maximum Cable O.D.)

The heavy-duty Rotomatics are the culmination of years of experience in armored cable cutting technology and are used in production lines of major armored cable manufacturers

SEATEK COMPANY'S PEGBOARD  
DISPLAYSHOWCASE UNIQUE TOOLS  
& INCREASE SALES



## ACCESSORIES FOR SEATEK TOOLS

ITEM	CAT. NO.	SPECIFICATIONS	ITEM	CAT. NO.	SPECIFICATIONS
 ROTO-SPLIT & ROTO-FLEX	B-102	BLUE SAPPHIRE BLADE. REPLACEMENT BLADE FOR USE ON BX & FLEX CUTTERS: RS-101, RS-101A, RF-120A, RF-120B AND RF-170. (NOT RECOMMENDED TO CUT ALUMINUM ARMOR)	 HANDLE ASSEMBLY	101-110	HANDLE ASSEMBLY FOR RS-101, RS-101A, RF-120A, RF-120B AND RF-170 WITH BLADE CARTRIDGE STORED IN KNOB. (BLADE NOT INCLUDED)
 ALUMINUM ARMOR	B-107	BLADE TO CUT ALUMINUM ARMOR. FOR USE ON BX & FLEX CUTTERS: RS-101, RS-101A, RF-120A, RF-120B AND RF-170 (WORKS ON STEEL CASING TOO BUT ONLY FOR 1/2" TRADE SIZE & ABOVE).	 HARDWARE RETROFIT	101-106	SPARE PART KIT FOR RS-101, RS-101A, RF-120A, RF-120B & RF-170. CONSISTING OF 1 SHAFT, 1 NUT, 1 4-40 KNURLED SCREW, 1 THUMBSCREW FOR RS-101 ONLY.
 ROTOMATIC	B-103	FINE TOOTH BLADE USED ON POWER TOOLS TO CUT THIN WALL FLEX	 POWER CONVERSION	101-107	POWER CONVERSION KIT. MOTORIZE ANY ROTO-SPLIT AND ROTO-FLEX (SAME PRINCIPLE AS POWER-SPLIT). CONSISTS OF B-108 BLADE, SHAFT, SCREW, WASHERS, HEX NUT & HEX WRENCH.
	B-108	STANDARD BLADE FOR RM-202 (ALL MODELS). ALSO USE WITH RS-101-AP.			
 ROTO-SKINNER	B-151	REPLACEMENT BLADE FOR RSK-145, RSK-150 & RSK-150RC	 SWING-SAW	B-109-18	REPLACEMENT BLADES FOR SW-130 SWING-SAW. USE 18 TEETH PER INCH FOR THICKER WALL EMT, AND 24 TEETH PER INCH FOR THIN WALL LIQUID TIGHT, FLEX, ETC..
	B-153	REPLACEMENT BLADE FOR RSK-125	 REPLACEMENT BLADE	B-109-24	
 LUBRICANT STICK	LS-105	LUBRICANT STICK FOR BLADES USED ON RS-101, RS-101A, RS-101AP, RF-120A, RF-120B & RF-170. <b>NOT FOR USE WHEN CUTTING ALUMINUM ARMOR.</b>	 JACKET RIPPER	B-228	REPLACEMENT BLADE FOR JACKET RIPPER JR-128.
 ROTO-SPIN	B-252	REPLACEMENT BLADE FOR CT-250	 STRIP-ALL	B-202	REPLACEMENT BLADE FOR ALL MODELS OF THE SA-200 STRIP-ALL. SOLD IN PACKAGES OF TWO.
 VEE-TWIN	B-272	REPLACEMENT BLADE FOR VT-270			
 ZIP-STRIPPER REPLACEMENT BLADE	BZ-112	REPLACEMENT BLADE FOR UF CABLE STRIPPER ZIP-STRIPPER ZS-140	 STRIP-ALL ADAPTER	A-201	A-201 ADAPTER USED TO STRIP AND RING CUT WIRES AS SMALL AS 1/8". GREAT FOR USE ON COMMUNICATIONS AND COAX CABLE. FOR ALL MODELS OF THE SA-200 STRIP-ALL. (EXCEPT SA-200L)

Distributed By:



A SMALL COMPANY WITH BIG IDEAS®

392 PACIFIC STREET, STAMFORD, CT 06902

PHONE (203) 324-0067 ☆ FAX (203) 324-7844 ☆ E-Mail: info@SeatekCo.com

www.SeatekCo.com

