



**DESIGNERS  
EDGE™**

Part of Coleman Cable Canada

## **Q1- 2014 Catalogue**

**Prepared by: Global Vision Marketing  
Wholesale Reps for Designers Edge  
Western Canada  
Call 604-594-8886 for more info.**



# Replacement Bulbs



© The Designers Edge 2010

### 65Watt Fluorescent 4U Mogul Bulb

- 65 Watt 4U bulb
- Equivalent to 300 watt incandescent bulb
- Energy Saving
- Mogul Socket
- 6300K Temperature rating
- 3,800 Lumens
- UPC: 090529-617230
- Carton Qty: 10

### Model L765



© The Designers Edge 2010

### 65Watt Fluorescent Bulb

- 65 Watt Self Ballasted bulb
- Equivalent to 300 watt incandescent bulb
- Electronic ballast
- Instant on no flicker
- Cold Start minimum -20°
- Medium Base Socket
- 6500K Warm white light
- 4300 Lumens of light
- UPC: 090529-621800
- Carton Qty: 10

### Model L767



© The Designers Edge 2010

### 65Watt Fluorescent Flat Bulb

- 65 Watt PL bulb
- Equivalent to 300 watt incandescent bulb
- Replacement bulb for L-2004 and L-2005 work lights
- 4100K Warm white light
- 4800 Lumens
- UPC: 090529-619050
- Carton Qty: 10

### Model L766



### 13Watt Fluorescent PL Bulb

- 13 Watt PL tube bulb G23 Base
- 2 Pin
- Equivalent to 60 watt incandescent bulb
- Energy Saving
- 6000K Temperature rating
- 825 Lumens
- UPC: 078693-025020
- Carton Qty: 24

### Model 2502



### 13Watt Fluorescent PL Bulb

- 13 Watt PL Gx24q-1 Base
- 4 Pin
- Equivalent to 60 watt incandescent bulb
- Energy Saving
- 3000K Temperature rating
- 900 Lumens
- UPC: 090529-620261
- Carton Qty: 10

**Model L712**



### 13Watt Fluorescent PL Bulb

- 13 Watt PL "U" tube bulb G23 Base
- 2 Pin
- Equivalent to 60 watt incandescent bulb
- Energy Saving
- 6500K Temperature rating
- 825 Lumens
- UPC: 090529-608511
- Carton Qty: 10

**Model L713**



### 42 Watt Fluorescent PLT Bulb

- 42 Watt PLT Gx24q-4 Base
- 4 Pin
- Equivalent to 150 watt incandescent bulb
- Energy Saving
- 4010K Temperature rating
- 3,200 Lumens
- UPC: 090529-620230
- Carton Qty: 10

**Model L742**



### 70 Watt Fluorescent PLT Bulb

- 70 Watt PLT Gx24q-6 Base
- 4 Pin
- Equivalent to 350 watt incandescent
- Energy Saving
- 6500K Temperature rating
- 5,400 Lumens
- UPC: 090529-620803
- Carton Qty: 10

**Model L770**



### 500W Halogen Bulb Buddy JR.™

- Complete with three 500 watt **2000** hour rated halogen bulbs with heavy duty filament support
- Heavy duty plastic case with foam inserts that protect bulbs from damage
- Patent #6,467,619B1
- UPC: 090529-615625
- Carton Qty: 6 pieces per inner pack

**Model L12**



### 500W Halogen Bulb Buddy™

- Complete with six heavy duty 500 watt **2000** hour rated halogen bulbs with heavy duty filament support
- Heavy duty plastic case with foam inserts that protect bulbs from damage
- Patent #6,467,619B1
- UPC: 090529-614598
- Carton Qty: 12

**Model L15**



**250W Rough Service Bulb Buddy™**



**300W Rough Service Bulb Buddy™**



**500W Rough Service Bulb Buddy™**

### Rough Service Bulb Buddy's™

- Complete with six heavy duty rough service **4000** hour rated halogen bulbs with heavy duty filament support
- Heavy duty plastic case that protect bulbs from damage
- Each bulb fits into a foam slot so it is protected from impact, moisture and other debris until needed
- Patented Product - **US D 6,467,619 B1**
- Carton Qty: 12
- UPC: 090529-618619 - 250W
- UPC: 090529-618626 - 300W
- UPC: 090529-619036 - 500W

**Models L21 (250W), L22 (300W), L23 (500W)**



### 150 Watt Quartz Halogen Replacement Bulb

- 130 Volt
- 150 Watts
- T-3 Lamp
- Porcelain ends
- UPC 090529-601413
- Case Pack: 10

**Model L95**



### 200 Watt Quartz Halogen Replacement Bulb

- 130 Volt
- 200 Watts
- T-3 Lamp
- Porcelain ends
- UPC: 090529-620377
- Case Pack: 10

**Model L97**



### 250 Watt Quartz Halogen Replacement Bulb

- 130 Volt
- 250 Watts
- T-3 Lamp
- Porcelain ends
- UPC: 090529-601420
- Case Pack : 10

**Model L96**



### 300 Watt Quartz Halogen Replacement Bulb

- 130 Volt
- 300 Watts
- T-3 Lamp
- Porcelain ends
- UPC 090529-450042
- Case Pack: 10

**Model L32**





### 500 Watt Quartz Halogen Replacement Bulb

- 130 Volt
- 500 Watts
- T-3 Lamp
- Porcelain ends
- UPC 090529-455405
- Case Pack: 10

**Model L16**



### 250 Watt Rough Service Halogen Replacement Bulb

- 130 Volt
- 250 Watts
- T-3 Lamp
- Porcelain ends
- 4,000 hour
- UPC: 090529-608474
- Carton Qty: 10

**Model L96**



### 1500 Watt Halogen 10" Replacement Bulb

- 110 Volt
- 1,500 Watts
- T-3 Lamp
- Porcelain ends
- UPC 090529-601437
- Case Pack: 10

**Model L16**



### 100 Watt Mercury Vapor Replacement Bulb

- Mercury vapor lights are very efficient, and are used in commercial landscaping, roadway overhead lighting, warehouse and factory lighting, and sports field lighting.
- 100 Watt
- Medium Socket
- Replacement Bulb for 100 Watt Security lights
- 5700K
- Carton Qty: 10
- UPC: 090529-610163

**Model L788**



### 175 Watt Mercury Vapor Replacement Bulb

- Mercury vapor lights are very efficient, and are used in commercial landscaping, roadway overhead lighting, warehouse and factory lighting, and sports field lighting.
- 175 Watt
- Mogul Socket
- Replacement Bulb for 175 Watt Security lights
- 5700K
- Carton Qty: 10
- UPC: 090529-608122

**Model L789**



### 35 Watt High Pressure Sodium Replacement Bulb

- High Pressure Sodium light bulbs are one of the most commonly used outdoor light sources. Most street lighting uses a high pressure sodium bulb which gives a characteristic 'yellowish' color. It is a very efficient light source which generally last for many hours
- 35 Watt
- Medium Socket
- 2000K
- Carton Qty: 10
- UPC: 090529-608542

**Model L790**



### 50 Watt High Pressure Sodium Replacement Bulb

- High Pressure Sodium light bulbs are one of the most commonly used outdoor light sources. Most street lighting uses a high pressure sodium bulb which gives a characteristic 'yellowish' color. It is a very efficient light source which generally last for many hours
- 50 Watt
- Medium Socket
- 2000K
- Carton Qty: 10
- UPC: 090529-608559

**Model L791**





### 70 Watt High Pressure Sodium Replacement Bulb

- High Pressure Sodium light bulbs are one of the most commonly used outdoor light sources. Most street lighting uses a high pressure sodium bulb which gives a characteristic 'yellowish' color. It is a very efficient light source which generally last for many hours
- 70 Watt
- Medium Socket
- 2000K
- Carton Qty: 10
- UPC: 090529-608139

#### Model L792



### 100 Watt High Pressure Sodium Replacement Bulb

- High Pressure Sodium light bulbs are one of the most commonly used outdoor light sources. Most street lighting uses a high pressure sodium bulb which gives a characteristic 'yellowish' color. It is a very efficient light source which generally last for many hours
- 100 Watt
- Medium Socket
- 2000K
- Carton Qty: 10
- UPC: 090529-608597

#### Model L793



### 150 Watt High Pressure Sodium Replacement Bulb

- High Pressure Sodium light bulbs are one of the most commonly used outdoor light sources. Most street lighting uses a high pressure sodium bulb which gives a characteristic 'yellowish' color. It is a very efficient light source which generally last for many hours
- 150 Watt
- Mogul Socket
- Replacement Bulb for 150 Watt Security lights
- 2000K Warm white light
- Carton Qty: 10
- UPC: 090529-608580

#### Model L794



### 70 Watt High Pressure Sodium Replacement Bulb

- High Pressure Sodium light bulbs are one of the most commonly used outdoor light sources. Most street lighting uses a high pressure sodium bulb which gives a characteristic 'yellowish' color. It is a very efficient light source which generally last for many hours
- 70 Watt
- Mogul Socket
- Replacement Bulb for 70 Watt Security lights
- 2000K Warm white light
- Carton Qty: 10
- UPC: 090529-610903

#### Model L892



### **70 Watt Metal Halide Replacement Bulb**

- Very efficient day light bright light
- 70 Watt
- Medium Socket
- Replacement Bulb for 70 Watt Metal Halide lights
- 5,500 Lumens
- UPC: 090529-608726
- Carton Qty: 12

**Model L781**



### **100 Watt Metal Halide Replacement Bulb**

- Very efficient day light bright light
- 100 Watt
- Medium Socket
- Replacement Bulb for 100 Watt Metal Halide lights
- 8,000 Lumens
- UPC: 090529-608733
- Carton Qty: 12

**Model L781**



### **35 Watt MR-16 Halogen Bulb**

- 35 Watt Bi-Pin G8
- 130V
- 2700K Temperature rating
- 550 Lumens
- UPC: 090529-612433
- Carton Qty: 10

**Model L6**



### **50 Watt MR-16 Halogen Bulb**

- 50 Watt Bi-Pin GU5.3
- 120V
- 2700K Temperature rating
- 550 Lumens
- UPC: 090529-618381
- Carton Qty: 10

**Model L709**



### **1200 Watt Infrared 10" Heat Lamp**

- 1200 watt
- 130V
- Replacement lamp for Model H12000, H12011
- UPC: 090529-620735
- Carton Qty: 10

### **Model H11055**

---

### **1200 Watt Infrared 10" Heat Lamp with wire leads**

- 1200 watt
- 130V
- Replacement lamp for Model H12010
- UPC: 090529-620988
- Carton Qty: 10

### **Model H11056**



# Retractable Cord Reels



### 20' 16/3 Retractable Cord Reel

- Solid PVC Triple Tap
- Plastic Construction
- cETLus listed
- UPC: 090529-622166
- 4 pieces per master carton
- Master Cube: .69
- Master Weight: 4.0 lbs

**Model E315**



### 30' 16/3 Retractable Cord Reel with Clear Grounded Triple Tap

- LED indicator light
- Heavy Duty Metal Construction
- Diamond Plate Design
- cETLus Listed
- UPC: 090529-622159
- 2 pieces per master carton
- Master Cube: .67
- Master Weight: 15.20 lbs

**Model E215**



### 30' 14/3 SJTW Retractable Cord Reel with Locking Plug

- Red Metal Construction
- Mounts on ceiling, wall, or can sit on flat surface
- Rated for 13A / 125V / 1625W
- UPC: 0 78693 48004 1
- 3 pieces per master carton
- Master Cube: 1.65
- Master Weight 29.94 lbs

**Model 48004**

### 30' 14/3 SJTW Retractable Cord Reel with 3-Outlet Power Block

- Metal Construction
- Mounts on ceiling, wall, or flat surface
- Rated for 13A / 125V / 1625W
- UPC: 078693-480065
- 3 pieces per master carton
- Master Cube: 1.75
- Master Weight 29.14 lbs

**Model 48006**



### Extra Heavy Duty 45' 14/3 Retractable Cord Reel

- Wall Mountable
- Includes 45' 14/3 Cord
- Grounded Triple Tap
- Heavy Duty Plastic Construction
- UPC: 090529-622319
- 2 pieces per Master carton
- Master Cube: 1.72
- Master Weight 24.60 lbs

**Model E316**



### 20' 16/3 Retractable Cord Reel with Incandescent Work Light

- Plastic Construction
- Grounded Outlet in Handle
- UPC: 090529-622142
- 4 pieces per Master Carton
- Master Cube: .63
- Master Weight 13.20 lbs

**Model E216**



### Extra Heavy Duty 50FT 12/3 Retractable Cord Reel

- Steel Mounting Bracket
- Includes 50' 12/3 Cord
- Triple Tap with Power Indicator light
- Impact resistant Black Thermoplastic Construction
- UL/CUL Listed
- UPC: 029892-048204
- 1 piece per Master carton
- Master Cube: 1.23
- Master Weight 18.40 lbs

**Model 04820-88-02**





## 40FT 16/3 SJTW METAL CORD REEL WITH 75W TROUBLE LIGHT

- Red metal housing made of heavy steel
- Extra outlet in the handle
- Mounting hardware included
- UL rated
- UPC: 078693-480003
- 3 piece per Master carton
- Master Cube: 1.71
- Master Weight 31.05 lbs

**Model 48000**

## 20FT Retractable Cord Reel 33 LEDs Work Light

- 33 Long Lasting Super Bright LEDs
- 83 Lumens
- On/Off switch
- 360° Revolving Hook
- 18/2 SJTW 20FT Power Cord
- Retractable cord reel
- Shock resistant with soft body ]
- Mounting hardware included
- CETL rated
- UPC: 078693-480669
- 4 piece per Master carton
- Master Cube: 1.34
- Master Weight 13.20 lbs

**Model 48066**



## 25FT 14/3 Retractable Cord Reel with Metal Incandescent Work Light

- 25' 14/3 High Visibility Striped Power Cord
- Heavy duty diamond plate metal reel
- 10 amp ground outlet
- 100 watt maximum rated bulb (not included)
- Mounting hardware included
- CETL rated
- UPC: 090529-616882
- 3 piece per Master carton
- Master Cube: 1.08
- Master Weight 25.35 lbs

**Model E251**



## 30' 16/3 Retractable Cord Reel with 13 Watt Fluorescent Work Light

- Diamond Plate Design
- High Visibility Orange/Black Power Cord
- Ground Outlet in handle
- Heavy Duty Metal Construction
- CETL Rated
- UPC: 090529-622197
- 2 pieces per master carton
- Master Cube: 1.09
- Master Weight 17.20 lbs

### Model E318



## 30' 16/3 Retractable Cord Reel with 72 LEDs Work Light

- Diamond Plate Design
- High Visibility Green/Black Striped Power Cord
- Grounded Outlet in handle
- Heavy Duty Metal Construction
- CETL Rated
- UPC: 090529-622180
- 2 pieces per Master Carton
- Master Cube: 1.09
- Master Weight: 17.20 lbs

### Model E319





# Fluorescent Shop Lights and Strip Lights



### 48" Fluorescent Shop Light w/Pull Chain Switch

- Electronic Ballast works in lower temperatures (min -20°)
- Uses two 40 watt T-12 or two 32 watt T-8 fluorescent tubes (not included)
- Complete with 5 Ft cord
- Pull chain switch
- cUL Listed

**Model L180**



### 48" Fluorescent Shop Light with Grill and 120V Outlet

- Electronic Ballast works in lower temperatures (min -20°)
- Uses two 40 watt T-12 or two 32 watt T-8 fluorescent tubes (not included)
- Complete with 5 Ft cord
- 120 Volt Outlet
- Pull chain switch
- cUL Listed


**Model L181**



### 48" Diamond Plate Fluorescent Shop Light with Outlet

- Electronic Ballast works in lower temperatures (min -20°)
- Uses two 40 watt T-12 or two 32 watt T-8 fluorescent tubes (not included)
- Complete with 5 Ft cord
- 120 Volt Outlet
- High polish reflector
- Pull chain switch
- cUL Listed

**Model L88**



## HEAT ZONE™ UNIVERSAL BULB 1500W CERAMIC HEATER / FAN /SHOP LIGHT

- Universal porcelain sockets - Can operate up to 65 watt CFL bulbs or 100 watt incandescent bulbs (bulbs not included)
- Includes a 1500W Ceramic Heater and Fan
- The Heater and Fan can be operated independently from the Lights.
- Black Textured finish, High polished reflector
- 2 Pull chain power switches to control lights and Heater/Fan separately
- Wire Safety Grill, Mounting Chain included
- Fully assembled, easy to install
- CSA and CSA/US listed


### Model L186



## 24'' Fluorescent Strip Light

- Electronic Ballast works in lower temperatures (min -20°)
- Uses a 20 watt T-12 or a 12 watt or 18 watt T8 fluorescent tube
- Bulb not included
- Direct wire
- cUL Listed

### Model L190



## 48'' Fluorescent Strip Light

- Electronic Ballast works in lower temperatures (min -20°)
- Uses a 40 watt T-12 or a 32 watt T8 fluorescent tube
- Bulb not included
- Direct wire
- cUL Listed

### Model L191

## Security Area and Farm Lights

## Universal Bulb Security Light



- 10" acrylic reflector
- Dusk to dawn button photocell
- Can operate up to maximum wattage of 68W CFL bulb or 200W T10 halogen bulb or 200W incandescent bulb
- Bulb not included
- Durable die-cast aluminum construction
- UL & CUL Listed
- UPC: 090529-617834
- Carton Qty: 4

### Model L1751

## 65 Watt Security Yard Light



- 10" Acrylic Reflector
- Output equivalent to 300 watt bulb
- Dusk to dawn button photocell
- Includes 65 watt mogul base fluorescent bulb
- Electronic ballast works in lower temperatures (min -20°)
- Approximate 4,300 Lumen output
- UL & CUL Listed
- UPC: 090529-617834
- Carton Qty: 4

### Model L1755

## 65 Watt Security Yard Light



- 10" acrylic reflector
- 24" Heavy duty 3 pt powder coated steel mounting arm
- Dusk to dawn button photocell
- Complete with 65 watt mogul base fluorescent bulb
- Electronic ballast works in lower temperatures(min-20°)
- 4,300 Lumen output
- UL & CUL Listed
- UPC: 090529-620674
- Carton Qty: 4

### Model L1756

## 42 Watt Fluorescent Security Light



- Output equivalent to 160 watt incandescent bulb
- Dusk to dawn button photocell
- Acrylic reflector
- Complete with 42 watt fluorescent bulb
- Electronic ballast works in temperatures (min -20°)
- Approximate 3,200 Lumen output
- UL & CUL Listed
- UPC: 090529-618398
- Carton Qty: 4

### Model L1698

## 70 Watt High Pressure Sodium Security Light



- With 10" Acrylic Reflector and Bulb
- Dusk to dawn button photocell Includes
- 70 watt HPS bulb
- Patented finned octagon shaped
- Approximate 6,400 Lumen output
- UL & CUL Listed
- UPC: 090529-608047
- Carton Qty: 4

**Model L1730**

## 150 Watt High Pressure Sodium Security Light



- 12" acrylic reflector
- Heavy duty 3 point mounting arm
- Dusk to dawn button photocell
- Complete with 150 watt bulb
- Approximate 15,000 Lumen output
- UL & CUL Listed
- UPC: 090529-622388
- Carton Qty: 2

**Model L1741**

## 100 Watt Metal Halide Security Light



- 10" Acrylic Reflector
- Dusk to dawn photocell
- Complete with 100 watt MH bulb
- Approximate 10,500 Lumen output
- UL & CUL Listed
- UPC: 090529-608818
- Carton Qty: 4

**Model L1701**

## 150 Watt Metal Halide Pulse Start Security Light



- 12" acrylic reflector
- 10 Volt Pulse Start Ballast
- Complete with 150 watt Metal Halide bulb
- Twist lock photocell
- UL & CUL Listed
- UPC: 090529-608047
- Carton Qty: 2

**Model L1743**



## 26 WATT FLUORESCENT WALL LIGHT



- Decorative acrylic prismatic lens
- Slim design works well with modern architecture
- Dusk to dawn photocell
- Includes two 13 watt PL fluorescent bulbs
- 120 Watt incandescent equivalent
- Available in bronze finish
- Approximate 1,650 Lumen output
- UL & CUL Listed
- UPC: 090529-619876
- Carton Qty: 12

**Model L1772**

## 42 Watt Fluorescent Security Wall Light



- Decorative acrylic prismatic lens
- Dusk to dawn photocell
- Includes one 42 watt PL fluorescent bulb
- 240 Watt incandescent equivalent
- Bronze finish
- Approximate 3,200 Lumen output
- UL & CUL Listed
- UPC: 090529-620223
- Carton Qty: 6

**Model L1795BZ**

## 126 Watt Fluorescent Wall Mount Fixture



- Decorative acrylic prismatic lens
- Die cast aluminum mounting plate
- Electronic ballast works in lower temperatures(min-20°)
- Includes three 42 watt PLT fluorescent bulbs
- Approximate 6,400 Lumen output
- UL & CUL Listed
- UPC: 090529-620506
- Carton Qty: 6

**Model L1788**

## 400 Watt Metal Halide Wall Light



- Deluxe heavy duty die-cast housing
- Quality Glass Lens
- Quad voltage ballast 120, 208, 240, 277 volt
- Includes one 400 watt Mogul base Metal Halide Bulb
- Bronze finish
- UL listed for wet locations when ceiling mounted or damp locations wall mounted.
- Order yoke or slip fitter separately
- UPC: 090529-621237
- Carton Qty: 1

**Model L4300**





### 35 Watt High Pressure Sodium Wall Light

- Constructed of industrial grade vandal resistant polycarbonate materials
- Dusk to dawn photocell
- Complete with 35 watt HPS bulb
- UL & CUL Listed
- UPC: 090529-608375
- Carton Qty: 6

**Model L177035W**



### 70 Watt High Pressure Sodium Wall Light

- Constructed of industrial grade vandal resistant polycarbonate materials
- Dusk to dawn photocell
- Complete with 70 watt HPS bulb
- UL & CUL Listed
- UPC: 090529-608351
- Carton Qty: 6

**Model L177070W**



### 100 Watt High Pressure Sodium Security Wall Pack

- Deluxe heavy duty die-cast housing
- Quality glass lens wont discolor
- Hinged face frame for easy bulb change
- Bronze finish
- 100 Watt HPS bulb included
- UL & CUL Listed
- UPC: 090529-608276
- Carton Qty: 4

**Model L1762HPS**



### 70 Watt Metal Halide Security Wall Pack

- Deluxe heavy duty die-cast housing
- Quality glass lens wont discolor
- Hinged face frame
- Bronze finish
- 70 Watt MH bulb included
- UL & CUL Listed
- UPC: 090529-608290
- Carton Qty: 4

**Model L1762-70W-MH**



## Indoor Emergency Light

- Lights come on automatically when the power fails
- Two adjustable heads to direct the light
- Provides up to 4 Hours of Emergency Lighting
- Single Head provides 4 hours, Dual Head Provides 2 Hours
- No wiring – plug in the 18/3 SJT 6FT Cord
- Illuminates an average size room or hallway
- Includes a test switch/LED charge indicator on the front
- Comes with 2 incandescent 6V 0.8A T5 wedge base bulbs
- Maintenance free 6 volt Rechargeable Battery included
- Carton Qty: 2
- UPC: 090529-61799 5
- CSA listed

## Model L1799





Image 2516

## 14" Hanging Farm Light

- With 6' of cord and mounting plate to hang
- 14" metal reflector
- Powder coating finish
- 200 Watt max bulb (not included)
- UL & CUL Listed

### Model L1712



© The Designers Edge, LLC

## 10" Hanging Farm Light

- 6 FT Cord for wiring installation
- Includes mounting plate
- Powder coating finish
- 10" metal reflector
- UL & CUL Listed
- UPC: 090529-619739
- Carton Qty: 4

### Model L1704



## 100 Watt Incandescent Weather Tight Light

- All metal construction
- Tempered glass lens
- Ceiling mount
- ½" IPS thread on top and sides
- 100 Watt max bulb (not included)
- UL & CUL Listed

**Model L1706**

© The Designers Edge 2010



## 100 Watt Incandescent Weather Tight Light

- All metal construction
- Tempered glass lens
- Wall mount
- 100 Watt max bulb (not included)
- UL & CUL Listed

**Model L1707SV**

© The Designers Edge 2010



## 12" Farm Light

- Screws into any porcelain socket
- 12" metal reflector
- Powder coating finish
- 200 Watt max bulb (not included)
- UL & CUL Listed

**Model L1710**

© The Designers Edge 2010



## 12" Farm Light with arm

- Includes Arm for wall mounting
- 12" metal reflector
- Powder coating finish
- 200 Watt max bulb (not included)
- UL & CUL Listed

**Model L1711**

© The Designers Edge 2010

## Security Flood Lights



### 150W Single Metal Flood Light

- Perfect for eave or wall mounting
- Corrosion resistant die-cast metal
- Socket, rated for 150 watt PAR bulb max.
- Mounts easily using existing junction box
- UPC:090529-616486 Bronze  
UPC:090529-616484 White
- Carton Qty: 12



### Model L1648BZ, L1648WH

Sold less bulb



### 300W Twin Metal Floodlight

- All metal construction
- Uses PAR flood bulbs up to 150 watt (not included)
- 4,400 Lumen output
- UL & CUL listed
- UPC: 090529-619517BR
- UPC: 090529-619524WH
- Carton Qty: 6



### Model L1646BR, L1646WH

Sold less bulbs



### 300W Twin Metal Floodlight with Photocell

- Die cast aluminum housing
- Dusk to dawn photocell
- Uses PAR flood bulbs up to 150W (not included)
- 4,400 Lumen output
- UL & CUL listed
- UPC: 090529-619531BR
- UPC:090529-619548WH
- Carton Qty: 6



### Model L1647BR, L1647WH

Sold less bulbs



### 300 Watt Twin Floodlight with Shields

- With protective bulb shields
- All metal construction
- Uses PAR flood bulbs up to 150 watt (not included)
- 4,400 Lumen output
- UL/CUL listed
- UPC: 090529-619395 Bronze
- UPC: 090529-619401 White
- Carton Qty: 6



### Model L1640BR, L1640WH

Sold less bulbs

### 300W Twin Floodlight with Shields & Photocell



- All metal construction
- Protective bulb shields
- Dusk to dawn photocell
- Uses PAR flood bulbs up to 150 watt (not included)
- UL/CUL listed
- UPC: 090529-619425 Bronze
- UPC: 090529-619432 White
- Carton Qty: 6

**Model L1641BR, L1641WH**

### 200W Halogen Twin Floodlight



- All metal construction
- Decorative pebbled glass lens
- Twist on face frame
- Complete with two 100 watt halogen bulbs
- Available in Bronze or White
- 3,000 Lumen output
- UL & CUL listed
- UPC: 090529-607033
- UPC: 090529-607026
- Carton Qty: 6

**Model L1637BR, L1637WH**

### 300 Watt Halogen Floodlight



- All metal construction
- Base plate included
- Patented eyebrow frame
- Complete with 300 watt halogen bulb
- Approximate 4,800 Lumen output
- UL/CUL listed
- UPC: 090529-601055 Bronze
- UPC: 090529-601062 White
- Carton Qty: 12

**Model L30BR, L30WH**

### 500 Watt Halogen Floodlight



- All metal construction
- Base plate included
- Complete with 500 watt halogen bulb
- Approximate 8,000 Lumen output
- UL/CUL listed
- UPC: 090529-607866 Bronze
- UPC: 090529-607873 White
- Carton Qty: 12

**Model L50BR, L50WH**



## 500 Watt Halogen Flood Light

- Die cast metal design
- Patented eyebrow frame for more light control
- Includes mounting plate & pebbled glass lens
- Hinged face frame
- Complete with 500 watt halogen bulb
- Approximate 8,000 Lumen output
- UL & CUL listed
- UPC: 090529-601079BR
- UPC: 090529-601086WH
- Carton Qty: 12

**Model L31BR, L31WH**



## 150 Watt High Pressure Sodium Flood Light With Base and Bulb

Deluxe heavy duty die-cast housing  
Includes mounting plate & glass lens  
Approximate 15,000 Lumen output  
Bronze finish  
150 Watt HPS bulb included  
UL & CUL Listed  
UPC: 090529-608269  
Carton Qty: 6  
Master Cube: 1.20  
Master weight: 9.0lbs  
**Model L1760**



## 150 Watt Mini Halogen Floodlight

- Die cast metal design with eyebrow frame
- Includes mounting plate
- Decorative pebbled glass lens
- Complete with 150 watt halogen bulb
- Approximate 2,400 Lumen output
- UL & CUL listed
- UPC: 090529-605466 Bronze
- UPC: 090529-605473 White
- Carton Qty: 12

**Model L56BR, L56WH**



## 150W Halogen Twin Floodlight

- Die cast metal floodlights w/hinged faces
- Eyebrow frames for more light control
- Decorative pebbled glass lens
- Complete with two 150 watt halogen bulbs
- Approximate 4,800 Lumen output
- Includes mounting plate
- UL & CUL listed
- UPC: 090529-605480 BR
- UPC: 090529-605497 WH
- Carton Qty: 12

**Model L57BR, L57WH**







#### 4 High Intensity SM4 LED Dusk to Dawn Twin Flood

- Nonmetallic Back Plate\Lamp holder
- Bulb Type: 4 – SM4 High Power LED's
- Optically enhanced Len's
- Dusk to Dawn Photocell
- 1,285 lumen output
- 5600K color temp
- Available in Bronze or White Finish
- UL/CUL Listed
- UPC: 090529-6116795 BR  
090529-6116790 WH
- Carton Qty: 3

**Model L1679BR, L1679WH**

#### 26W Dusk to Dawn Fluorescent Floodlight

- Decorative prismatic Lens
- Dusk to dawn photo cell
- Energy efficient comes complete with two 13W PL bulbs
- Equivalent to 120 watts of incandescent light
- Electronic ballast works in lower temperature (min -20°)
- UL/CUL listed
- UPC: 090529-608214BR
- Carton Qty: 12

**Model L104BR**



#### 65 Watt Dusk to Dawn Fluorescent Flood Light

- Die cast metal floodlight w/hinged face
- Electronic Ballast works in low Temp (min 20°)
- Complete with one 65 watt bulb
- Equivalent to 300W incandescent
- Approximate 4300 Lumen Output
- Dusk to Dawn Photocell
- UL/CUL listed
- UPC: 090529-619791
- Carton Qty: 4

**Model L90BR**



# Solar Security Lights

**LED!!**



### LED Solar Motion Activated Wall Light

- Long Lasting Super Bright LED's
- Amorphous Solar Panel for outdoor applications
- 3 x 1.2V - 600mah Ni-CD Rechargeable Battery
- Up to 90 sixty second on/off cycles
- Security Lock & Key preventing theft
- 35 Lumens
- 180° motion detector
- UPC: 090529-622593
- Carton Qty: 6

**Model L954**



### Motion Activated Halogen Solar Floodlight

- 180° motion detector detects motion up to 60 feet
- Multi- crystal solar panel designed for outdoor applications
- Rechargeable battery included
- Complete with 15 watt halogen bulb
- UPC: 090529-620001
- Carton Qty: 4



**Model L951**

**LED!!**



### 10 LED Solar Shed Light

- Super bright long lasting LEDs for Years of Service
- Multi - crystal solar panel
- Can be wall or pole mounted up to 16 feet away
- Complete with 3 AA rechargeable batteries
- Two power settings 10 LEDs with 45.6 Lumens will operate up to 2 hours or use 5 LEDs with 22.8 Lumens for up to 4 hours
- UPC: 090529-619982
- Carton Qty: 6

**Model L949**

**LED!!**



### 9 LED Motion Activated Solar Floodlight

- 180° motion detector detects motion up to 60 feet
- Multi crystal solar panel for outdoor applications
- Super bright long lasting LEDs for Years of Service
- Rechargeable battery included
- Up to 50 - 30 second cycles, on full charge
- 45 Lumens
- UPC: 090529-619999
- Carton Qty: 6

**Model L950**

**LED!!**



## 45 LED SOLAR SECURITY FLOODLIGHT

- 120° motion detector, 45 White Color LED's
- 3600mAh 3.6V SC size NI-MH Rechargeable Battery Pack
- Wall bracket mounting
- Multi - crystal solar panel
- Lights approximately 160sq ft and up to a distance of 33 ft
- 270 Lumens , 6500K
- Two settings function: continuous lighting and sensor lighting selected by switch
- Solar panel wall and pillar mountable
- UPC: 090529-622609
- Carton Qty: 6

**Model L955**

# Motion Activated Security Lights

# Halogen, Incandescent & LED Motion Sensor Security Lights



## 180° Motion Activated Single Flood

- Construction (Back Plate/Lamp holder): Nonmetallic/Nonmetallic
- Bulb Type: 120W PAR
- Photo cell
- 70 foot detection range
- Test Mode, LED assist – easy sensor set up
- Adjustable time, Manual override
- Available in Bronze or White
- UPC: 090529-160002 BR
- UPC: 090529-660007 WH
- Carton Qty: 6

**Model L6000BR, L6000WH**

Bulb not included



## 110° Motion Activated Twin Flood

- Construction (Back Plate/Lamp holder): Nonmetallic/Nonmetallic
- Bulb Type: 120W PAR
- Photo cell
- 60 foot range
- Adjustable time, Manual override
- Available in Bronze or White
- UPC: 090529-659995 BR
- UPC: 090529-159990 WH
- Carton Qty: 6

**Model L5999BR, L5999WH**

Bulbs not included

### 180° Motion Activated Twin Flood



- Construction (Back Plate\Lamp holder): Nonmetallic\Nonmetallic
- Bulb Type: 120W PAR
- Photo cell
- 70 foot range
- Test Mode, Adjustable time, Manual override
- Available in Bronze or White
- UPC: 090529-160019 BR
- UPC: 090529-660014 WH
- Carton Qty: 6

**Model L6001BR, L6001WH**

Bulbs not included

### 180° Motion Activated Twin Flood w/Shields



- Nonmetallic construction
- Bulb Type: 75W PAR
- Photo cell, 70 foot range, Test Mode
- LED assist – easy sensor set up
- Adjustable time, Manual override, LED indicator
- Adjustable Motion Sensor sensitivity
- Removable Bulb Shields
- Available in Bronze or White
- UPC: 090529-160026 BR
- UPC: 090529-660021WH
- Carton Qty: 6

**Model L6002BR, L6002WH**

Bulbs not included

### 180° Motion Activated Die Cast Twin Flood



- Die Cast Construction
- Bulb Type: 120W PAR
- Photo cell, 70 foot range
- Test Mode, LED assist – easy sensor set up
- Adjustable time, Manual override, LED indicator
- Downward Detection, Adjustable sensitivity
- Available in Bronze or White
- UPC: 090529-160033 BR
- UPC: 090529-660038 WH
- Carton Qty: 6

**Model L6003BR, L6003WH**

Bulbs not included

### 270° Motion Activated Twin Flood w/Shields



- Die Cast Construction
- Bulb Type: 120W PAR
- Photo cell, 70 foot range, Test Mode
- LED assist – easy sensor set up
- Adjustable time, Manual override, LED indicator
- Downward Detection, Adjustable sensitivity
- LED chaser, Dusk to Dawn Mode, Timer
- Removable Bulb Shields
- Available in Bronze or White
- UPC: 090529-160040 BR
- UPC: 090529-660045 WH
- Carton Qty: 6

**Model L6004BR, L6004WH**

Bulbs not included

## 270° Motion Activated Twin Flood w/ Shields & LED Night Light



- Die Cast construction, Bulb Type: 120WPAR
- Photo cell, 70 foot range, Test Mode
- LED assist – easy sensor set up
- Adjustable time, Manual override, LED indicator
- Downward Detection, Adjustable sensitivity
- LED chaser, Dusk to Dawn Model, Timer
- LED Night Light, Removable Bulb Shields
- Available in Bronze or White
- UPC: 090529-160057 BR
- UPC: 090529-660052 WH
- Carton Qty: 6

**Model L6005BR, L6005WH**

Bulbs not included

## 180° Motion Activated 150W Halogen Flood



- Construction (Back Plate\Lamp holder) : Nonmetallic\Die cast
- Bulb Type: 150W Halogen - Included
- Eyebrow frame, Photo cell, 70 foot range
- Test Mode, LED assist – easy sensor set up
- Adjustable time, Manual override, LED indicator
- Downward Detection, Adjustable sensitivity
- Available in Bronze or White
- UPC: 090529-160064 BR
- UPC: 090529-660069 WH
- Carton Qty: 6

**Model L6006BR, L6006WH**

## 180° Motion Activated 500W Halogen Flood



- Die Cast construction
- Bulb Type: 500W Halogen - Included
- Photo cell, 70 foot range, Test Mode
- LED assist – easy sensor set up
- Adjustable time, Manual override, LED indicator
- Downward Detection, Adjustable sensitivity
- Available in Bronze or White
- UPC: 090529-160095 BR
- UPC: 090529-660090 WH
- Carton Qty: 6

**Model L6009BR, L6009WH**

## 270° Motion Activated Twin 150W Halogen Flood



- Die Cast construction
- Bulb Type: 2 – 150W Halogen - Included
- Photo cell, Test Mode, LED assist – easy sensor set up
- Adjustable time, Manual override, LED indicator
- Downward Detection, Adjustable sensitivity
- LED chaser, Dusk to Dawn Mode, Timer
- Eyebrow Frame
- Available in Bronze or White
- UPC: 090529-160088 BR
- UPC: 090529-660083 WH
- Carton Qty: 6

**Model L6008BR, L6008WH**



### 180° Motion Activated Twin 100W Halogen Flood



- Die Cast construction
- Bulb Type: 2 – 100W Halogen Bi-pin Included
- Photo cell, 70 foot range, Test Mode
- LED assist – easy sensor set up
- Adjustable time, Manual override, LED indicator
- Downward Detection, Adjustable sensitivity
- Eyebrow Frame
- Available in Bronze or White
- UPC: 090529-160101 BR
- UPC: 090529-660106 WH
- Carton Qty: 6

**Model L6010BR, L6010WH**

### 180° Motion Activated Triple 100W Halogen Flood



- Die Cast Construction
- Bulb Type: 3 – 100W Halogen Bi-pin Included
- Photo cell, 70 foot range, Test Mode
- LED assist – easy sensor set up
- Adjustable time, Manual override, LED indicator
- Downward Detection, Adjustable sensitivity
- Eyebrow Frame
- Available in Bronze or White
- UPC: 090529-160118 BR
- UPC: 090529-660113 WH
- Carton Qty: 3

**Model L6011BR, L6011WH**

### 180° Motion Activated 150W Halogen Flood with Plug in Cord



- Construction(Back Plate\Lamp holder)Nonmetallic\Die cast
- Bulb Type: 150W Halogen - Included
- Photo cell, 70 foot range, Test Mode
- LED assist – easy sensor set up
- Adjustable time, Manual override, LED indicator
- Downward Detection, Adjustable sensitivity
- Eyebrow frame, 3 foot cord and plug
- Available in Bronze or White
- UPC: 090529-160132 BR
- UPC: 090529-660137 WH
- Carton Qty: 6

**Model L6013BR, L6013WH**

### 150W Photo Cell Halogen Flood



- Construction (Back Plate\Lamp holder) :
- Nonmetallic\Die cast
- Bulb Type: 150W Halogen - Included
- Photo cell
- Dusk to Dawn Mode, Timer
- Eyebrow frame
- Available in Bronze or White
- UPC: 090529-160149 BR
- UPC: 090529-660144 WH
- Carton Qty: 6

**Model L6014BR, L6014WH**

# LED!!

## 180° Motion Activated 4 High Intensity SM4 LED Flood

- Nonmetallic construction
- Bulb Type: 4 – SM4 High Power LED's
- 1,285 lumen output
- Photo cell
- 70 foot range, Adjustable time, Test Mode
- LED assist – easy sensor set up
- Manual override, LED indicator
- Downward Detection, Adjustable sensitivity
- LED chaser
- Available in Bronze or White
- UPC: 090529-160156 BR
- UPC: 090529-660151 WH
- Carton Qty: 3

**Model L6015BR, L6015WH**

## 180° Motion Activated 65W Fluorescent Flood

- Die Cast construction
- Bulb Type: 65W 4U Flat Fluorescent-Included
- Photo cell, 70 foot range, Test Mode
- LED assist – easy sensor set up
- Adjustable time, Manual override, LED indicator
- Downward Detection, Adjustable sensitivity
- Available in Bronze or White
- UPC: 090529-160187 BR
- UPC: 090529-660182 WH
- Carton Qty: 6

**Model L6018BR, L6018WH**

## 180° Motion Activated 26W Fluorescent Flood

- Construction (Back Plate\Lamp holder) : Nonmetallic\Die cast
- Bulb Type: 2 – 13W PL Fluorescent - Included
- Photo cell
- 70 foot range, Test Mode
- LED assist – easy sensor set up
- Adjustable time, Manual override, LED indicator
- Downward Detection, Adjustable sensitivity
- Eyebrow Frame
- Available in Bronze or White
- UPC: 090529-160170 BR
- UPC: 090529-660175 WH
- Carton Qty: 6

**Model L6017BR, L6017WH**

## 180° Motion Activated 26W Fluorescent Flood

- Construction (Back Plate\Lamp holder)Nonmetallic\Die cast
- Bulb Type: 2 – 13W PL Fluorescent-Included
- Photo cell, 70 foot range, Test Mode
- LED assist – easy sensor set up
- Adjustable time, Manual override, LED indicator
- Downward Detection, Adjustable sensitivity
- Available in Bronze or White
- UPC: 090529-160194 BR
- UPC: 090529-660199 WH
- Carton Qty: 6

**Model L6019BR, L6019WH**

## 180° Motion Sensor Replacement

- Nonmetallic construction
- Bulb Type: Up to 500W
- Photo cell
- 70 foot range, Adjustable time, Manual override
- Adjustable sensitivity, Led indicator
- Available in Bronze or White
- UPC: 090529-160200 BR
- UPC: 090529-660205 WH
- Carton Qty: 6

### Model L6020BR, L6020WH



## 270° Motion Sensor Replacement

- Nonmetallic construction
- Bulb Type: Up to 500W
- Photo cell
- 70 foot range, Adjustable time, Manual override
- Adjustable sensitivity, Led indicator
- Available in Bronze or White
- UPC: 090529-160217 BR
- UPC: 090529-660212 WH
- Carton Qty: 6

### Model L6021BR, L6021WH



## Clamp and Brooder Lamps



## 5 1/2" Incandescent Clamp Light

- 5 1/2" Aluminum Shade
- Non-Slip vinyl grip Clamp
- Heat resistant socket rated 150 watt
- 6FT 18/2 Cord
- UL Listed
- UPC: 078693-001604
- Carton Qty: 12 (Bulk)
- Carton Weight: 8.4lbs

**Model 0160**



## 5" Open Grill Incandescent Clamp Light

- 5" Wire Grill
- Non-Slip vinyl grip Clamp
- Heat resistant socket rated 150 watt
- 6FT 18/2 Cord
- UL Listed
- UPC: 078693-003240
- Carton Qty: 12 (Bulk)
- Carton Weight: 13.5lbs

**Model 0324**





## 9 3/4" " Clamp Light

- 9 3/4" Aluminum Shade
- Non-Slip vinyl grip Clamp
- Heat resistant socket rated 150 watt
- 6FT 18/2 Cord
- UL Listed
- UPC: 078693-001628
- Carton Qty: 12 (Bulk)
- Carton Weight: 6.72lbs

### Model 0162



## 10 1/2" Brooder Clamp Light

- Ideal for pig and chicken brooders or as temporary heat source
- Heavy Duty Aluminum Reflector
- Insulated Porcelain Socket 250W Max
- Snap on bulb guards
- Hang up Hook Only
- 6FT 18/2 Black Cord with polarized plug
- UL Listed
- UPC: 078693-001659
- Carton Qty: 12 (Bulk)
- Carton Weight: 13.84lbs
- **Model 0165**



## 10 1/2" Brooder Clamp Light

- Ideal for pig and chicken brooders or as temporary heat source
- Heavy Duty Aluminum Reflector
- Snap on bulb guards
- Hang up Hook
- Non-Slip Heavy Duty Clamp with vinyl coated grips
- Insulated Porcelain Socket 250W Max
- 6FT 18/2 Black Cord with polarized plug
- UL Listed
- UPC: 078693-001666
- Carton Qty: 12 (Bulk)
- Carton Weight: 17.25lbs

### Model 0166



## 10 1/2" Brooder Clamp Light

- Ideal for pig and chicken brooders or as temporary heat source
- Heavy Duty Aluminum Reflector
- Snap on bulb guards
- Hang up Hook
- Non-Slip Heavy Duty Clamp with vinyl coated grips
- Insulated Porcelain Socket 250W Max
- 8FT 18/2 Black Cord with polarized plug
- UL Listed
- UPC: 078693-001673
- Carton Qty: 6 (Bulk)
- Carton Weight: 11.34lbs

### Model 0167





## 8 1/2" Incandescent Clamp Light

- 8 1/2" Aluminum Shade
- Heavy Duty Tight Grip Non-Slip vinyl grip Clamp
- Heat resistant socket rated 150 watt
- 12 FT 18/2 Cord
- UL Listed
- UPC: 078693-001512
- Carton Qty: 4
- Carton Weight: 6.10lbs

**Model 2839**



## Porcelain Socket Replacement

- Insulated Porcelain Socket 250W Max
- UPC: 078693-001109
- Carton Qty: 20 (Bulk)
- Carton Weight: 5.4lbs

**Model 0110**



## Porcelain Socket Clamp Light

- Non-Slip vinyl grip Clamp
- Heat resistant socket rated 150 watt
- 6FT 18/2 Cord
- UL Listed
- UPC: 078693-003288
- Carton Qty: 12 (Bulk)
- Carton Weight: 8.6lbs

**Model 0328**

# Trouble Lights



### Plastic Guard Trouble Light

- Plastic Shield and Bulb Guard
- Hands free hang hook
- On\Off push switch
- 18/2 6FT Power Cord
- Uses standard base incandescent bulb up to 75W (bulb not included)
- UL/CUL listed

**Model E237**



### Plastic Guard 18/2 15' SJTW Trouble Light

- Plastic Shield and Bulb Guard
- Hands free hang hook
- On\Off push switch
- 18/2 15FT Power Cord
- Uses standard medium base incandescent bulb up to 75W (bulb not included)
- UL/CUL listed

**Model 0200**



### Plastic Guard 18/2 25' SJTW Trouble Light

- Plastic Shield and Bulb Guard
- Hands free hang hook
- On\Off push switch
- 18/2 25FT Power Cord
- Uses standard medium base incandescent bulb up to 75W (bulb not included)
- UL/CUL listed

**Model 0201**



### Metal Shield Trouble Light

- Metal reflective shield with protective grill
- Hands free hang hook
- On\Off push switch
- 120V Grounded outlet
- 16/3 6FT Power Cord
- Uses standard base incandescent bulb up to 75W (bulb not included)
- UL/CUL listed

**Model E233**



### 18/3 25FT Metal Shield Trouble Light w/outlet

- Metal reflective shield with protective grill
- Hands free hang hook
- On\Off push switch
- 120V Grounded outlet
- 18/3 SJTW 25FT Power Cord
- Uses standard medium base incandescent bulb up to 75W (bulb not included)
- UL/CUL listed

**Model 0681**



### 16/3 25FT Metal Shield Trouble Light with outlet

- Metal reflective shield with protective grill
- Tough PVC construction makes handling effortless
- Round orange vinyl jacket is flexible
- 16/3 SJTW 25FT Power Cord
- Dual hook permits hanging by either the guard or handle
- Standard with power switches and bulb cages
- 75 Watt bulb maximum
- UL Listed

**Model 0691**



### 18/3 50FT Metal Shield Trouble Light w/outlet

- Tough PVC construction makes handling effortless
- Round orange vinyl jacket is flexible
- 18/3 SJTW 50FT Power Cord
- Dual hook permits hanging by either guard or handle
- Standard with power switches and bulb cages
- 75 Watt bulb maximum
- UL Listed

**Model 0682**



### 16/3 50FT Metal Shield Trouble Light with outlet

- Metal reflective shield with protective grill
- Tough PVC construction makes handling effortless
- Round orange vinyl jacket is flexible
- 16/3 SJTW 50FT Power Cord
- Dual hook permits hanging by either the guard or handle
- Standard with power switches and bulb cages
- 75 Watt bulb maximum
- UL Listed

**Model 0692**



### 16/3 50FT SJT YELLOW JACKET TROUBLE LIGHT

- Yellow Jacket® Work Lights
- Flexible wire, high heat-resistant bulb collar
- 13 amp grounded receptacle in handle
- Dual hang hooks
- Hex shape grounded metal shield
- Coated wire cage keeps hot reflector from skin
- 75 Watt Bulb Rating (120V)
- UL Listed

**Model 2948**



### 16/3 25FT SJT YELLOW JACKET TROUBLE LIGHT

- Yellow Jacket® Work Lights
- Flexible wire, high heat-resistant bulb collar
- 13 amp grounded receptacle in handle
- Dual hang hooks
- Hex shape grounded metal shield
- Coated wire cage keeps hot reflector from skin
- 75 Watt Bulb Rating (120V)
- UL Listed

**Model 2893**

### 16/3 50FT SJEOW Metal Shield Trouble Light with outlet

- Luma-Site® Polar/Solar® portable hand lamp
- Polar/Solar® cord and coated metal lamp guard.
- Power switch and receptacle are provided.
- UL/CUL Listed; meets OSHA and NEC requirements for general use
- Cord type: SJEOW, Cord jacket material: TPE
- Plug configuration: NEMA 5-15P, Material: PVC
- Handle material: Thermoplastic, over-molded
- Handle color: Black with yellow over molded
- Lamp guard material: PVC coated metal
- Lamp switch: Push-through, in handle
- Cord temperature rating: -50 to +90o C
- Operating voltage: 125 VAC
- Maximum lamp wattage: 100 W

**Model 05858**

### 16/3 25FT SJEOW Metal Shield Trouble Light with outlet

- Luma-Site® Polar/Solar® portable hand lamp
- Polar/Solar® cord and coated metal lamp guard.
- Power switch and receptacle are provided.
- UL/CUL Listed; meets OSHA and NEC requirements for general use
- Cord type: SJEOW, Cord jacket material: TPE
- Plug configuration: NEMA 5-15P
- Plug material: PVC
- Handle material: Thermoplastic, over-molded
- Handle color: Black with yellow over molded
- Lamp guard material: PVC coated metal
- Lamp switch: Push-through, in handle
- Cord temperature rating: -50 to +90o C
- Operating voltage: 125 VAC
- Maximum lamp wattage: 100 W

**Model 05857**

## 14/3 25FT SJEOW Metal Shield Trouble Light with outlet

- Luma-Site® Polar/Solar® portable hand lamp with -50 to +90°C
- Coated metal lamp guard.
- Power switch and receptacle are provided.
- UL/CUL Listed; meets OSHA and NEC requirements for general use
- Cord type: 14/3 SJEOW
- Cord jacket material: TPE
- Plug configuration: NEMA 5-15P, Material: PVC
- Handle material: Thermoplastic, over-molded
- Handle color: Black with yellow over-molded
- Lamp guard material: PVC coated metal
- Lamp switch: Push-through, in handle
- Operating voltage: 125 VAC
- Maximum lamp wattage: 100 W

### Model 05657



## 14/3 50FT SJEOW Metal Shield Trouble Light with outlet

- Luma-Site® Polar/Solar® portable hand lamp with -50 to +90°C
- Coated metal lamp guard.
- Power switch and receptacle are provided.
- UL/CUL Listed; meets OSHA and NEC requirements for general use
- Cord type: 14/3 SJEOW
- Cord jacket material: TPE
- Plug configuration: NEMA 5-15P,Material: PVC
- Handle material: Thermoplastic, over-molded
- Handle color: Black with yellow over-molded
- Lamp guard material: PVC coated metal
- Lamp switch: Push-through, in handle
- Operating voltage: 125 VAC
- Maximum lamp wattage: 100 W

### Model 05658



## Fluorescent Trouble Lights



### 13 Watt- 60 Watt Equivalent Fluorescent Trouble Light

- Complete with 13 watt fluorescent bulb
- 825 Lumens
- Polycarbonate Lens
- Shock resistant durable construction
- Hang Hook
- On/Off Switch
- 18" 18/2 SJT power cord
- 1 year warranty
- UL/CUL listed

**Model 48044**



### 13 Watt Fluorescent Task Light

- Complete with 13 watt fluorescent bulb
- 825 Lumens
- Polycarbonate Lens
- Shock resistant durable construction
- Hang Hook
- On/Off Switch
- 6FT 18/2 SJT power cord
- 1 year warranty
- UL/CUL listed

**Model L1797**



### 13 Watt Fluorescent Task Light

- Heavy duty 3mm Chrome Metal Grill
- 13 watt Fluorescent bulb
- 825 lumen output
- On/Off switch
- Self Standing Base
- Fold Down Hook
- Non-slip Rubbereze™ Grip
- 16/3 6FT Power Cord
- 120V Grounded Outlet
- 1 year warranty
- ETL listed

**Model L1920**



### 16/3 SJTW 6FT 13W Fluorescent Light with outlet

- Complete with Energy Efficient 13 watt fluorescent bulb
- 825 Lumens
- Polycarbonate Lens
- Shock resistant durable construction
- Hang Hook
- On/Off Switch
- Grounded 120V Outlet
- 6FT 16/3 power cord
- 1 year warranty
- UL/CUL listed

**Model 48069**



## 26 Watt Fluorescent Task Light



- Heavy duty 3mm Chrome Metal Grill
- 2- 13 watt Fluorescent bulbs
- 1650 lumen output
- Dual switches for 13W or 26W Light
- Self Standing Base
- Fold Down Hanging Loop
- Non-slip Rubbereze™ Grip
- 16/3 6FT Power Cord
- 120V Grounded Outlet
- 1 year warranty
- ETL listed

**Model L1921**

## 16/3 SJWT 25FT 13W Fluorescent Light with outlet



- Complete with Energy Efficient 13 watt fluorescent bulb
- 825 Lumens
- Polycarbonate Lens
- Shock resistant durable construction
- Hang Hook
- On/Off Switch
- Grounded 120V Outlet
- 25FT 16/3 power cord
- 1 year warranty
- UL/CUL listed

**Model 48067**

## 16/3 SJWT Yellow Jacket® 15FT 13W Fluorescent Light with outlet



- Complete with Energy Efficient 13 watt fluorescent bulb
- 825 Lumens
- Polycarbonate Lens
- Shock resistant durable construction
- Hang Hook
- On/Off Switch
- Grounded 120V Outlet
- 15FT 16/3 Yellow Jacket® power cord
- UL listed

**Model 38067**



### 18/2 SJT 25FT 15W Fluorescent Light

- Yellow Jacket® Fluorescent Light
- Fluorescent bulbs are cool-burning and long lasting
- 15 watt fluorescent bulb included
- Hang Hook
- On/Off switch
- 25FT 18/2 SJT power cord
- Temporary Lighting for workshops, garages
- UL Listed

**Model 38069**

# Hand Held Task Lights

### 36 LED Work Light with 6FT Cord




- 36 Long lasting Super bright LEDs
- 90 Lumens Light Output
- Polycarbonate Lens
- High output reflector
- Heavy duty Chrome Metal Grill
- Folding Hanging Loop
- Shock resistant durable construction
- Non-slip Rubbereze™ Grip
- Hands Free Self Standing Base
- On/Off switch
- 6FT 16/3 Power Cord
- Grounded 120V Outlet

**Model L1922**

**LED!!**

### 72 LED Work Light



- 72 Long lasting Super bright LEDs
- 180 Lumens Light Output
- Polycarbonate Lens
- High output reflector
- Folding Hanging Loop
- Shock resistant durable construction
- Non-slip Rubbereze™ Grip
- Hands Free Self Standing Base
- On/Off switch
- 6FT 16/3 Power Cord
- Grounded 120V Outlet

**Model L1923**

**LED!!**

### 36 LED Rechargeable Work Light



- Lithium Rechargeable Battery
- Heavy duty Chrome Metal Grill
- 6 Hour Run Time on Full Charge
- 90 Lumens Light Output
- Fold Down Hook
- Wall and Car Charger
- Non-slip Rubbereze™ Grip
- Self Standing Base
- Charge Indicator Light

**Model L1924**

**LED!!**

### 72 LED Rechargeable Work Light



- Lithium Rechargeable Battery
- 5 Hour Run Time on Full Charge
- 180 Lumen Light Output
- Heavy Duty Chrome Metal Grill
- Fold Down Hook
- Non-Slip Rubbereze™ Grip
- Self Standing Base
- Wall and Car Charger
- Charge Indicator Light

**Model L1925**

**LED!!**

## 2 X 3 Watt High Intensity LED Work Light



- 3 Watt High Intensity Long lasting LEDs
- 540 Lumens Light Output
- Polycarbonate Lens
- High output reflector
- Folding Hanging Loop
- Shock resistant durable construction
- Non-slip Rubbereze™ Grip
- Hands Free Self Standing Base
- 6FT 18/2 120V Power Cord
- On\Off switch

Model L1926

**LED!!**

## 13 LED Slimlite Trouble Light



- Hi impact ABS Body with Anti-roll body design.
- Easy find glow in the dark green shield.
- On/Off switch controls area/top spot/or both functions.
- LED's offer years of maintenance free operation.
- 12 LED Task Light & 0.3W Spot Light
- 18 Hour Run Time, 20 Lumens (Spot Light)
- 15 Hour Run Time, 24 Lumens (Task Light)
- 8 Hour Run Time, 44 Lumens (Spot Light & Task Light)
- Non-Slip Rubbereze™ soft touch body, textured grip
- Powerful co-planar, nickel plated neodymium, rare-earth magnet on back
- 4AAA Eveready Batteries included.
- Available in Black



Model 1413

**LED!!**

## 25 LED Slimlite Trouble Light



- Hi impact ABS Body with Anti-roll body design.
- Easy find glow in the dark green shield.
- On/Off switch controls area/top spot/or both functions.
- LED's offer years of maintenance free operation.
- 24 LED Task Light & 0.5W Spot Light
- 12 Hour Run Time, 25 Lumens (Spot Light)
- 10 Hour Run Time, 48 Lumens (Task Light)
- 6 Hour Run Time, 73 Lumens (Spot Light and Task Light)
- Non-Slip Rubbereze™ soft touch body and textured grip
- Powerful co-planar, nickel plated neodymium, rare-earth magnet on back
- 4AAA Eveready Batteries included.



Model 1425

**LED!!**

## 37 LED Slimlite Trouble Light



- Hi impact ABS Body with Anti-roll body design.
- Easy find glow in the dark green shield.
- On/Off switch controls area/top spot/or both functions.
- LED's offer years of maintenance free operation.
- 36 LED Task Light & 0.5W Spot Light
- 12 Hour Run Time, 25 Lumens (Spot Light)
- 7 Hour Run Time, 72 Lumens (Task Light)
- 5 Hour Run Time, 97 Lumens (Spot Light and Task Light)
- Non-Slip Rubbereze™ soft touch body and textured grip
- Powerful co-planar, nickel plated neodymium, rare-earth magnet on back
- 4AAA Eveready Batteries included.



Model 1437

**LED!!**

# LED!!

## 10 X5630 SMD Battery Powered Trouble Light



- Super Bright White 10 X 5630 SMD LG LEDs
- 300 Lumens
- High Impact ABS
- Rubberized exterior
- 360° Swivel fold-out hook
- Polycarbonate Lens
- On\Off push button switch
- Powerful co-planar, nickel plated neodymium, rare-earth magnet on back
- Uses 4 AA batteries - Included
- 4 hour run time with new batteries

**Model 1450**

# LED!!

## 10 X5630 SMD Rechargeable Trouble Light



- Super Bright White 10 X 5630 SMD LG LEDs
- 300 Lumens
- Rechargeable 7.4V 200mA Lion Battery pack
- Bicolor LED Charge level indicator, flashes green & red to know when recharged
- Home and car charger included
- High Impact ABS
- Rubberized exterior
- 360° Swivel stainless steel fold-out hook
- Polycarbonate Lens
- On\Off push button switch
- Powerful co-planar, nickel plated neodymium, rare-earth magnet on back
- Hand Free stand
- 3 hour run time with full charge & 3 hour charging time

**Model 1451**



# LED!!



## 6 SMD LED + 1 LED Pocket Light

- Long lasting Super Bright 6 SMD LED Pocket Light
- 42 Lumens
- 1 – 5mm LED top spot light
- 6 Lumens
- High Impact ABS body
- Polycarbonate Lens
- Powerful co-planar, nickel plated neodymium, rare-earth heavy duty magnet on bottom
- Water and Dust resistant
- High Shock Resistance
- 3 AAA Batteries included
- 12 Hour Run Time with new batteries

**Model 1453**

## LED Battery Operated Cyclops Task Light

- 1 Super Bright CREE LED
- 100 Lumens
- High Impact ABS body
- Polycarbonate hook
- Aluminum directional light head on flexible neck
- Non-slip grip and belt clip
- On\Off push button
- 3AAA Batteries included
- Water and Dust resistant
- High Shock Resistance
- Powerful co-planar, nickel plated neodymium, rare-earth magnet in body
- Estimated 10 hour run time with new batteries

### Model 1438

LED!!



## LED Rechargeable Cyclops Task Light

- 1 Super Bright CREE LED
- 100 Lumens
- High Impact ABS body
- Polycarbonate hook
- Aluminum directional light head on flexible neck
- Non-slip grip and belt clip
- On\Off push button
- 3.7V 1500mAh Lithium-Ion Rechargeable battery
- Bicolor LED Charge level indicator, flashes green & red to know recharged
- Water and Dust resistant
- High Shock Resistance
- Powerful co-planar, nickel plated neodymium, rare-earth magnet in body
- 4 hour run time with full charge
- 3 hour charging time

### Model 1439



LED!!



## 16 LED Trouble/Spot Light with Punch List Laser™

- Aerospace grade aluminum body provides impact resistance.
- Anti-roll body design makes it easy to use on any job.
- On/Off switch controls area/spot/laser lights individually.
- Super bright LED's offer years of maintenance free operation.
- The 16 LED area function emits 32 lumens of clear bright light.
- The 8 LED spot function emits 16 lumens bright directional light.
- Red Laser pointer function.
- Heavy-Duty base magnet provides hands free convenience.
- 3 AAA Eveready batteries are included providing up to 6 hours of area lighting use and up to 12 hours use as spot directional light.
- Counter 12 pack : 2-Silver, 2-Red, 2-Blue, 6-Black  
5-7/8"x 7-15/16"x 9"

### Model L1407



Counter 12 pack  
5-7/8"x 7-15/16"x 9"

## 16 LED Task / 8 LED Spot Light with Laser Pointer

- Aerospace grade aluminum body provides impact resistance.
- Anti-roll body design makes it easy to use on any job.
- On/Off switch controls area/spot/laser lights individually.
- Super bright LED's offer years of maintenance free operation.
- The 16 LED area function emits 32 lumens of clear bright light.
- The 8 LED spot function emits 16 lumens bright directional light.
- Red Laser pointer function.
- Heavy-Duty base magnet provides hands free convenience.
- 3 AAA Eveready batteries are included providing up to 6 hours of area lighting use and up to 12 hours use as spot directional light.
- Clam packaging. Black only.

### Model L1411



LED!!

Batteries Included!





## 6 High Intensity SMD LED w/4 LED Top Spot Rechargeable Work Light

- 48 Lumens
- Poly Lens
- Folding Hang Hoop
- Shock Resistant
- Self Stand Base
- Non-slip grip
- On/Off switch controls Task and Top lighting separately
- Lithium Rechargeable Battery
- Home Charger included

**Model 48068**

**LED!!**



## 24 LED Trouble Light

- 24 Long Lasting Super Bright LEDs
- 48 Lumens
- 3AA Batteries Included
- Estimated 3 Hour Run Time on New Batteries
- Non-slip Rubbereze™ Grip
- Folding Swivel Hook
- Strong Magnet on the back

**Model L-1198**

**LED!!**



## Flexi LED Task Light

- .07 watt LED
- 14" Flexible arm
- Durable shock resistant design
- 12 Hour Run Time
- Heavy Duty Magnetic Base
- Push On/Off Switch
- Batteries Included

**Model L1196**

**LED!!**

**LED!!**



## 21 LED HEAD LIGHT

- 42 Lumens
- Uses 21 Super Bright Long lasting LEDs
- 3 Power Settings & Flash Mode
- Weatherproof switch
- Adjustable Lycra bands
- Uses 3 AAA batteries (included)

**Model L1240**



## LED Pen Light

- Uses one high intensity CREE brand LED
- Requires 3 AAAA batteries for operation (included)
- Durable and shock resistant design
- Minimal power consumption for extended battery life
- On/Off switch designed for single hand momentary use or constant light operation

**Model L1197**

**LED!!**

**LED!!**



## 20FT Retractable Cord Reel 33LEDs Work Light

- 83 Lumens
- 33 Long Lasting Super Bright LEDs
- On/Off switch
- 360° Revolving Hook
- 18/2 SJTW 20FT Power Cord R
- Retractable cord reel
- Shock resistant with soft body

**Model 48066**

**LED!!**



he Designers Edge 2010

## 30FT 16/3 Retractable Cord Reel with 72 LED Work Light

- Diamond Plate Design on Both Sides of Metal Reel
- 16/3 30FT High Visibility Striped Power Cord
- 180 Lumen Light Output
- Heavy Duty Chrome Metal Grill
- Fold Down Hang Hook
- Non-Slip Rubbereze™ Grip
- Self Standing Base

**Model E319**

# Halogen Work Lights



### 150 Watt Halogen Clamp Light

- 150W halogen bulb included
- Made with die cast aluminum
- Hinged covers with wire grill guards
- Heat resistant tempered glass
- Adjustable tilting head
- Heavy duty clamp
- Hanging hook
- 5' power cord
- 2,400 lumen output
- UL/CUL listed

#### Model L835



### 500 Watt Halogen Portable Work Light

- All metal construction
- Heavy Duty comfort grip handle
- Shadow fighter grill
- Tempered glass
- 1' 18/3 grounded power cord
- Complete with one 500 watt halogen bulb
- 8,000 lumen output
- UL/CUL listed

#### Model L20



### 1000W Twin Head Halogen Work Light

- Telescoping tripod stand with ¼ quick turn locking nuts
- Telescopes up to 42" tall
- Complete with two 500 watt halogen bulbs
- All metal construction
- Tempered Glass for safety with UV protection
- Shadow Fighter™ grill frames
- Two weatherproof On / Off switches
- Easy grip adjustment nuts
- 4' 18/3 grounded power cord
- Heads rotate 360°
- 16,000 lumen output

#### Model L13



### 250 Watt Halogen Clamp Light

- Includes heavy duty clamp
- 360° swivel hook
- Shadow Fighter grill
- 5' 18/3 grounded power cord
- Comes with 250 watt halogen bulb
- 4,000 lumen output
- UL/CUL listed

#### Model L845



### 250 Watt Halogen Portable Work light

- With Comfort Grip heavy duty handle
- Tempered Glass for safety with UV protection
- Shadow Fighter™ grill
- 1' 18/3 grounded striped power cord
- Complete with one 250 watt halogen bulb
- 4,000 lumen output
- UL/CUL listed

#### Model L860



### 500 Watt Halogen Tripod Work Light

- Telescopes to 51" tall with Easy Grip locking nuts
- Portable sled base and tripod base included
- Tempered Glass for safety with UV protection
- With Comfort Grip heavy duty handle
- Weatherproof on/off switch
- Shadow Fighter™ grill
- With 4FT 18/3 grounded striped power cord
- Complete with 500 watt halogen bulb
- 8,000 lumen output
- UL/CUL listed

#### Model L10



### 500 Watt Halogen Twin Head Tripod Work Light

- Telescopes to 42" tall with Easy Grip locking nuts
- Portable sled base and tripod base included
- With Comfort Grip heavy duty handle
- Extra bulb storage tube with spare bulb
- Two weatherproof on/off switches for individual light control
- With Shadow Fighter grill
- With 4' 18/3 grounded striped power cord
- Complete with two 250 watt halogen bulbs
- 8,000 lumen output
- UL/CUL listed

#### Model L1719



### 500 Watt Halogen Portable Work light

- With foam grip handle
- Two Easy light adjustment knobs
- Weatherproof on/off switch
- Complete with one 500 watt halogen bulb
- 3FT 18/3 grounded power cord
- 8,000 lumen output
- UL/CUL listed

#### Model L33



### 1,000 Watt Halogen Twin Head Tripod Work light

- Telescopes to 68" tall with Easy Grip locking nuts
- Portable sled base and tripod base included
- Comfort Grip heavy duty handle
- Easy grip ¼ turn locking nuts
- Two weatherproof on/off switches
- 5' 18/3 grounded power cord
- With extra bulb storage tube
- Complete with two 500 watt halogen bulbs
- 16,000 lumen output
- UL/CUL listed

#### Model L14

## 250 Watt Halogen 4-N-1 Work Light



- Includes heavy duty clamp, hanging hook, portable base and yard stake
- Tempered Glass for safety with UV protection
- Shadow Fighter™ grill frame
- Large deeper housing for cooler operation
- Weatherproof On/Off switch
- 3' 18/3 grounded cord
- Comes with 250 watt halogen bulb
- 4,000 lumen output
- UL/CUL listed

**Model L878**

## 500 (2 x 250) Watt Halogen 160° Wide Angle Wall to Wall Portable Work Light



- Patented design lights up to 160° per head
- Hinged style face frame
- Separate weatherproof on/off switches for light control
- 5' 18/3 grounded power cord
- Complete with three 250 watt halogen bulbs (one spare)
- Extra bulb and storage tube
- 8,000 lumen output
- UL/CUL listed

**Model L5200**

## 600 (2 X 300) Watt Halogen Power Light



- Foam handle and non-skid base
- Large face frame and deep finned housing for cooler operation and longer bulb life
- Extra bulb storage tube with spare bulb
- Two weatherproof on/off switches for individual light control
- 5' 18/3 grounded power cord
- Complete with three 300 watt halogen bulbs (one spare)
- 9,600 lumen output
- UL/CUL listed

**Model L38DB**

## 1200 Watt Halogen Twin Head Tripod Power Light



- Portable sled base and tripod base included
- Hinged style face frame
- Adjustable extension leg for use on uneven surfaces with easy grip nuts
- Two weatherproof on/off switches for individual light control
- 5' 18/3 grounded high visibility striped power cord
- With extra bulb storage tube and 5 – 300 watt halogen bulbs (1 spare)
- Wire cord storage brackets
- Cord loop on tripod
- 19,200 lumen output
- UL/CUL listed

**Model L19**

## 500 Watt Halogen Spring Mounted Power Light



- Professional grade construction
- Light housing supported by stainless steel springs, providing protection against impact, extending bulb life
- Heavy duty style roll cage give maximum protection
- Extra bulb storage tube
- 10' 18/3 grounded power cord
- Complete with two 500W halogen bulbs (one spare)
- 8,000 lumen output
- UL and CUL listed

### Model L113

## 700 Watt Double Bulb Halogen Portable Power Light



- Heavy duty construction uses one 200 watt and one 500 watt bulb for 700 watts
- Two separate on/off switches for individual light control total
- Large hinged style face frame and deep finned housing for cooler operation and longer bulb life
- Two extra bulb storage tubes and one 200 watt and one 500 watt spare bulb
- 5' 18/3 grounded power cord
- 11,200 lumen output
- UL/CUL listed

### Model L5500

## 500 Watt Halogen Swing Arm Work Light



- Great for garages or truck loading bays
- Professional grade construction
- Uses 500W bulb
- Comes with spare bulb storage tube plus one extra 500W bulb
- Adjustable arm extends from wall 40"
- Weatherproof on/off switch
- 10ft 18/3 grounded striped power cord
- 8,000 lumen output
- UL/CUL listed

### Model L41

## 1000 Watt Wide Angle Double Bulb Halogen 160° Wall to Wall Work Light



- Patented design lights up to 160° wide angle
- Heavy Duty metal grill
- U Shaped Carry Foam padded Handle
- Two separate weatherproof on/off switches for individual light control
- Complete with three 500 watt halogen bulbs (one spare)
- Extra bulb storage tube
- Steel H-base with non-skid feet
- Cord wrap on base
- 5' 18/3 grounded power cord
- 16,000 lumen output
- UL/CUL listed

### Model L5203



7 STAGES
200
400
500
700
1000
1200
1400
WATTS OF POWER



## 1400 Watt Double Bulb Halogen 2-in-1 Tripod Power Light

- Telescopes to 72" tall with Easy Grip ¼ turn locking nuts
- Portable sled base and quick connect telescoping tripod base included
- Foam grip handles
- Hinged style face frames
- Shadow Fighter grills
- Easy light adjustment knobs
- Complete with (3) 200 watt halogen bulbs, and (3) 500 watt halogen bulbs – one spare for each
- Two Storage Tubes for spare bulbs
- Two Sealed weatherproof switches
- 7 Light Levels 200W / 400W / 500W / 700W / 1000W / 1200W / 1400W
- Wire cord storage brackets
- Includes wire loop on leg for cord management
- Adjustable extension leg for use on uneven surfaces
- 7FT 18/3 grounded power cord 26,400 lumen output
- CSA listed in US and CA

### Model L5502

Patented Product  
 US D477,463 S – 5,845,989  
 US D438,667 S  
 US D484,694 S  
 US 6,416,206 B1

# Fluorescent Work Lights

## 65 Watt Fluorescent 360° Portable Work Light

- Adjustable design allows positioning at various angles
- 6500K bright white 65W self ballasted CFL included
- 4800 Lumens
- 5' SJTW polarized power cord
- Grounded outlet on base
- Weatherproof on/off switch
- Includes wall mount bracket
- UPC: 090529621657
- Carton Qty: 4
- Master cube: 2.24
- Master weight: 19.54lbs

### Model L2006



## 65 Watt Fluorescent Portable Work light

- Cool to the touch
- Fluorescent lasts up to 5 times longer than halogen
- Bright white light control
- On/off switch
- With non-slip handle and feet
- 5' 18/3 grounded striped power cord
- Complete with 65 watt fluorescent lamp – 6500K
- 4,800 lumen output
- UL/CUL listed
- UPC: 090529-619623
- Carton Qty: 4
- Master cube: 4.71
- Master weight: 41.54lbs

### Model L2004



## 130 Watt 2-in-1 Heavy Duty Fluorescent Work light

- Cool to the touch
- With 2 – 65 watt 6500K fluorescent bulbs
- Fluorescent bulbs last up to 5 times longer than halogen bulbs
- Sled base and tripod base included
- Adjustable extension leg for use on uneven surfaces
- Telescopes to 72" with Easy Grip locking nuts
- Wire cord storage bracket on sled base and cord loop
- With non slip handle and feet
- Extra heavy duty telescoping base
- 7' 18/3 grounded striped power cord
- 8,600 lumen output
- UPC: 090529-619630
- Carton Qty: 1
- Master cube: 2.40
- Master weight: 28.25 lbs

### Model L2005



## 300 Watt Equivalent 65 Watt Fluorescent 360° Portable Work light with adjustable stand.

- Includes 65W 4U CFL Self ballasted bulb with standard base
- Adjustable Telescoping Tripod stand
- Prismatic Lens Reflects bright Fluorescent light 360°
- Adjustable design allows the light to position at up to 180° angles
- Easy turn light adjustment knob
- 6500K Color Temperature
- 16/3 SJTW 5FT polarized power cord
- Grounded outlet on light base
- Weatherproof on/off switch

### Model L2008



Patented Product  
US D438,667 S

# LED Work Lights

## 108 LED ECO-ZONE™ Portable Work Light



- 350 Lumens
- 6500k color temperature
- 18/2 hi-vis 6ft. green/black striped cord
- 120 volt AC direct plug
- Uses 108, 45° super bright LED's
- Super bright long lasting LED's
- Cool to the touch
- Weatherproof on/off switch
- Durable polymeric housing
- High output mirror reflector

**Model L1306**

## 108 LED RECHARGEABLE ECO-ZONE™ Portable Work Light



- 350 Lumens
- 6500k color temperature
- Rechargeable 12-volt portable design
- 7.4V 1300mAh Lithium Ion battery
- 2 hours run time
- 3 hour charge time
- Dual charge / run feature
- 6ft. cord with 12V 500mA transformer
- Uses 108, 45° super bright LED's
- Weatherproof on/off switch
- Durable polymeric housing with steel H-base
- Cool to the touch


**Model L1313**

## 15W ECO-ZONE™ Portable Work Light



- 492 Lumens
- 4800K Color Temperature
- 6FT of 18/2 power cord.
- 120 volt AC direct plug.
- 5 X 50,000 hours rated high power CREE LEDs.
- Weatherproof on/off switch.
- Durable polymeric housing with steel H-Base.
- Cool to the touch.

**Model L1312**





## 24 High Intensity SMD LED ECO-ZONE™ Portable Work Light

- 24 SMD High Intensity LEDs made by LG or Samsung
- State of the art Surface Mount Diode LEDs
- 779 Lumens
- 5700k color temperature
- Cool to touch
- Die cast housing and Steel H-base
- High output mirror reflector
- 3ft. 18/3 power cord with 120V plug
- Weatherproof on/off switch
- Foam Handle and Non-skid feet

**Model L1323**

LED lighting facts®	
A Program of the U.S. DOE	
Light Output (Lumens)	779
Watts	9.934
Lumens per Watt (Efficacy)	78
<b>Color Accuracy</b>	
Color Rendering Index (CRI) 72	
<b>Light Color</b>	
Correlated Color Temperature (CCT) 5745 (Daylight)	
2700K	3000K
3000K	5000K
5000K	6500K
<small>All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.</small>	
<small>Visit <a href="http://www.lightingfacts.com">www.lightingfacts.com</a> for the Label Reference Guide.</small>	
<small>Registration Number: 11WEG-NEJANZ-01172012</small>	
<small>Model Number: L1323</small>	
<small>Type: Other</small>	



## 24 High Intensity SMD LED ECO-ZONE™ RECHARGEABLE Portable Work Light

- 24 SMD High Intensity LEDs made by Samsung
- State of the art Surface Mount Diode LEDs
- 779 Lumens
- 5700k color temperature
- Rechargeable 12-volt portable design
- 7.4V 2200mAh Lithium-ion rechargeable battery
- 3 hour charge time
- 1 hour 40 minute runtime on full charge
- Dual charge / Run feature
- Cool to touch
- Die cast housing and steel H-base
- 3ft. cord with 12v 500mA transformer
- Weatherproof on/off switch
- Foam Handle and Non-skid feet

**Model L1320**



## 63 LED ECO-ZONE™ Portable Work Light

- 1,681 Lumens
- 6600k color temperature
- Highly polished black reflector
- Durable polymeric housing with steel H-base
- 6ft. 18/2 power cord with 120V plug
- 63 High Intensity Hongli-Tronic brand LED's
- Weatherproof on/off switch

**Model L1315**

LED lighting facts®	
A Program of the U.S. DOE	
Light Output (Lumens)	1681
Watts	22.69
Lumens per Watt (Efficacy)	74
<b>Color Accuracy</b>	
Color Rendering Index (CRI) 72	
<b>Light Color</b>	
Correlated Color Temperature (CCT) 6682 (Daylight)	
2700K	3000K
3000K	4500K
4500K	6500K
<small>All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.</small>	
<small>Visit <a href="http://www.lightingfacts.com">www.lightingfacts.com</a> for the Label Reference Guide.</small>	
<small>Registration Number: 13CE-25QZGT (6/21/2012)</small>	
<small>Model Number: L1315</small>	
<small>Type: Other</small>	

## 40 LED ECO-ZONE™ Portable Work Light

- 1,244 Lumens
- 5900k color temperature
- Cool to touch
- Die cast housing and steel H-base
- High output mirror reflector
- 3ft. 18/3 power cord with 120V plug
- 40 High Intensity LED's made by LG or Samsung
- Weatherproof on/off switch


### Model L1324



## 48 High Intensity SMD LED Twin Head Portable Work Light

- State of the art Surface Mount Diode High Intensity 5630 LEDs
- 779 Lumens x 2 = 1,558 Total
- 5700k color temperature
- Sled Base with Quick Release and U Shaped Carry Handle
- Adjustable Telescoping (54") Tripod Stand
- Cool to touch
- Die cast housings
- Easy turn light adjustment knobs
- High output mirror reflectors
- 5ft. power cord with 120V plug
- Weatherproof on/off switches
- Comfort Grip Foam Handles and Non-skid feet

### Model L1322






## 23W Array LED AC Portable Work Light

- 1 High Intensity Bright White LED
- LED is extremely more durable than halogen bulb
- Less electronics equal less product failures
- Shadow Free 120° Wide Angle Light Beam
- 5200k color temperature
- 1474 Lumens
- Only consumes 23 watts of power
- Cool to touch
- Die cast housing and Steel H-base
- Aim-N-Go tool free head adjustment
- 3ft. 18/3 power cord with 120V plug
- Weatherproof on/off switch

**Model L1681**



## 46W Array LED AC Twin Head Telescoping Tripod Work Light

- 2 High Intensity Bright White Paragon Array LEDs
- LED is extremely more durable than halogen bulb
- AC means less electronics equals less product failures
- Shadow Free 120° Wide Angle Light Beams
- 5200k color temperature
- 1474 Lumens X 2 = 2, 948 total
- Only consumes 46 watts of power
- Cool to touch
- Die cast housing and Steel H-base
- Aim-N-Go tool free head adjustment
- 5ft. 18/3 power cord with 120V plug
- Weatherproof on/off switches
- cUL

**Model L1682**






### 46W Array LED AC Portable EcoZone Work Light

- 1 High Intensity Bright White LED
- LED is extremely more durable than halogen bulb
- Less electronics because of AC equals less product failures
- Shadow Free 120° Wide Angle Light Beam
- 5700k color temperature
- 3,177 Lumen output Only consumes 46 watts of power
- Cool to touch
- Die cast housing and Steel H-base
- Aim-N-Go tool free head adjustment
- 3ft. 18/3 power cord with 120V plug
- Weatherproof on/off switch
- UPC: 090529-613256
- Master Carton: 6

#### Model L1325



### 92W Array LED AC Twin Head Telescoping Tripod Work Light

- 2 High Intensity Bright White Paragon Array LEDs
- LED is extremely more durable than halogen bulb
- Less electronics because of AC equals less product failures
- Shadow Free 120° Wide Angle Light Beam
- 5700k color temperature
- 6,354 Lumen output (2 X 3,177 Lumens)
- Only consumes 88 watts of power
- Cool to touch
- Die cast housing and Steel H-base
- Aim-N-Go tool free head adjustment
- 5ft. 18/3 power cord with 120V plug
- Weatherproof on/off switches

#### Model L1326