





LAW - LED Wraparound

DesignLights Consortium®
(DLC) qualification pending.



3S SCHEDULED STOCK SHIPMENTS **Regional Distribution Center Stock List** **LED**

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
93050091	LAW2-35LW-EU	0785311211501	LED 2' Wrap, 3500K, 2250 Lumens		●			●	8.0	11	
93050092	LAW4-35ML-EU	078531121518	LED 4' Wrap, 3500K, 4500 Lumens		●			●	14.0	55	



LCS - LED Striplight



3S SCHEDULED STOCK SHIPMENTS **Regional Distribution Center Stock List** **LED**

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
93050095	LCS4-35ML-EU	078531121549	LED 4' Striplight, 3500K, 5000 Lumens		●			●	9.0	77	



LJT - LED Lensed Troffer

3S SCHEDULED STOCK SHIPMENTS **Regional Distribution Center Stock List** **DESIGNLIGHTS CONSORTIUM** **LED**

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
93048975	LJT22-35HLG-FSA12-EDU	078531121228	LED 2X2 Lensed Troffer, 3500K, 4000 Lumens, 0-10V Dimming Driver	●	●	●	●	●	20.0	26	
93048976	LJT24-35MLG-FSA12-EDU	078531121235	LED 2X4 Lensed Troffer, 3500K, 5000 Lumens, 0-10V Dimming Driver	●	●	●	●	●	20.0	26	



EMSE - EnergyMax® Stratus Recessed Indirect Luminaire



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

EMSE	-	2	-	G	-	MPO	-	U	-
MODEL EMSE EnergyMax® Stratus Recessed Indirect Luminaire	NO. OF LAMPS IN CROSS SECTION 2 Two	CEILING TYPE G Grid Lay-in SM Surface Mount	BALLAST E104 Electronic T8, 1.04 Ballast Factor, Instant Start (N/A 1-Lamp) ESD104 Electronic T8, 1.04 Ballast Factor, Step Dimming, Programmed Start	OPTIONS EL Emergency Battery Pack, T8 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 FO730 30K 75CRI 17 or 32W T8 Lamps Installed FO735 35K 75CRI 17 or 32W T8 Lamps Installed FO741 41K 75CRI 17 or 32W T8 Lamps Installed FO830 30K 82CRI 17 or 32W T8 Lamps Installed FO835 35K 82CRI 17 or 32W T8 Lamps Installed FO841 41K 82CRI 17 or 32W T8 Lamps Installed C388 3-Wire Flex C488 4-Wire Flex					
SIZE 22 2' x 2' 24 2' x 4'	LAMP TYPE 17 2', T8: 17 Watt 32 4', T8 ¹	SHIELDING MPO Metal Perf w/Overlay	VOLTAGE U 120V-277V						

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



SER - Serrano® Recessed Architectural Luminaire




10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

SER	-		-	G	-	C	-		-
MODEL SER Serrano® Recessed Architectural Luminaire	NO. OF LAMPS 1 One 2 Two 3 Three	CEILING TYPE G Grid	BALLAST E Electronic T8, 0.88 Ballast Factor, Instant Start EP Electronic T5, T5HO, 1.0 Ballast Factor or T8, 0.88 Ballast Factor, Programmed Start ETT Electronic Twin Tube, Instant Start EPTT Electronic Twin Tube, Programmed Start 3E 3-Lamp Electronic T8, Instant Start 3EP 3-Lamp Electronic T8, Programmed Start ELW Electronic T8, 0.77 Ballast Factor, Low Watt, Instant Start EPLW Electronic T8, 0.77 Ballast Factor, Low Watt, Programmed Start 3ELW 3-Lamp Electronic T8, 0.77 Ballast Factor, Low Watt, Instant Start 3EPLW 3-Lamp Electronic T8, 0.77 Ballast Factor, Low Watt, Programmed Start ED Electronic Dimming (T8, 2-lamp only. Specify Mfg & Model) ²	DIMMING BALLAST ADVMK10 Mark 10 Powerline ADVMK7 Mark 7 0-10V	OPTIONS EL Emergency Battery Pack, T8 EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 C388 3-Wire Flex C488 4-Wire Flex				
SIZE 14 1' x 4' 22 2' x 2' 24 2' x 4'	LAMP TYPE 17 2', T8: 17 Watt 24 2', T5HO: 24 Watt 28 4', T5: 28 Watt 32 4', T8 ¹ 40TT Twin Tube Compact, 2G11 Base: 40 Watt	SHIELDING C Contour REFLECTOR P Performance F Full	VOLTAGE U 120V-277V 120 120V 277 277V	LAMPS FO730 30K 75CRI 32W T8 Lamps Installed FO735 35K 75CRI 32W T8 Lamps Installed FO741 41K 75CRI 32W T8 Lamps Installed FO830 30K 82CRI 32W T8 Lamps Installed FO835 35K 82CRI 32W T8 Lamps Installed FO841 41K 82CRI 32W T8 Lamps Installed F5830 30K 85CRI T5 or T5HO Lamps Installed F5835 35K 85CRI T5 or T5HO Lamps Installed F5841 41K 85CRI T5 or T5HO Lamps Installed FTT830 30K 82CRI 40W TT Lamps Installed FTT835 35K 82CRI 40W TT Lamps Installed FTT841 41K 82CRI 40W TT Lamps Installed					

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.
² Select voltage for ADVMK10.



EPC - Full Distribution Luminaire

35 SCHEDULED
STOCK
SHIPMENTS

Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
EPC000030	EPC22-217G-SH-EU-F0835	078531121259	2x2 17W T8 2-Lamp With 0.88 BF Ballast 17W T8 Lamp, and Shield Lens			●			25.0	44	
EPC000007	EPC22-224G-SH-EPU-F5835	078531015848	2x2 24W T5HO 2-Lamp With 1.0 BF Ballast 24W T5HO Lamp, and Shield Lens			●			25.0	44	
EPC000031	EPC24-228G-SH-EPU-F5835	078531121266	2x4 28W T5 2-Lamp With 1.00 BF Ballast 28W T5 Lamp, and Shield Lens	●	●	●	●		25.0	22	
EPC000032	EPC24-232G-SH-EU-F0835	078531121273	2x4 32W T8 2-Lamp With 0.88 BF Ballast 80 CRI 32W T8 Lamp, and Shield Lens		●		●	●	25.0	22	

QS₁₀

10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

EPC	24 - 2	G - SH					
MODEL EPC e.poc® Full Distribution Luminaire	NO. OF LAMPS 2 Two	CEILING TYPE G Grid	SHIELDING SH Shield Profile	VOLTAGE U 120V-277V 120 120V 277 277V	DIMMING BLST MFG/MODEL ADVMK10 Mark 10 Powerline ADVMK7 Mark 7 0-10V	OPTIONS C388 3-Wire Flex EL Emergency Battery Pack, T8 EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8	
SIZE 24 2' x 4'	LAMP TYPE 28 4', T5: 28 Watt 32 4', T8 ¹	BALLAST E Electronic T8, 0.88 Ballast Factor, Instant Start E104 Electronic T8, 1.04 Ballast Factor, Instant Start (2-lamp only) EP Electronic T5, T5HO, 1.0 Ballast Factor or T8, 0.88 Ballast Factor, Programmed Start EP95 Electronic T5, 0.95 Ballast Factor, Programmed Start ESD95 Electronic T5, 0.95 Ballast Factor, Step Dimming, Programmed Start ED Electronic Dimming (T8 only. Specify Mfg & Model) ²			LAMPS INSTALLED (REQUIRED) F0730 30K 75CRI 32W T8 Lamps Installed F0735 35K 75CRI 32W T8 Lamps Installed F0741 41K 75CRI 32W T8 Lamps Installed F0830 30K 82CRI 32W T8 Lamps Installed F0835 35K 82CRI 32W T8 Lamps Installed F0841 41K 82CRI 32W T8 Lamps Installed F5830 30K 85CRI T5 or T5HO Lamps Installed F5835 35K 85CRI T5 or T5HO Lamps Installed F5841 41K 85CRI T5 or T5HO Lamps Installed		

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.
² Select voltage for ADVMK10.



STE - Stratus Recessed Direct/Indirect

35 SCHEDULED STOCK SHIPMENTS

Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
93029796	STE22-217G-MPO-EU	078531017415	2 x 2, 2-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Ballast	●	●	●	●	●	12.0	24	
93029798	STE22-240TTG-MPO-EPTTU-C388	078531017477	2 x 2, 2-L, Metal Perf. Basket w/Overlay, 120-277V Twin Tube, Elec Prog Start Ballast, 3 Wire Flex					●	12.0	24	
93029800	STE22-240TTG-MPO-ETTU	078531017408	2 x 2, 2-L, Metal Perf. Basket w/Overlay, 120-277V Twin Tube, Elec Ballast	●	●	●			12.0	24	
93029801	STE22-317G-MPO-EU	078531017439	2 x 2, 3-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Ballast		●	●	●		12.0	24	
93029804	STE24-232G-MPO-EU	078531017385	2 x 4, 2-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Ballast	●	●	●	●	●	20.0	14	
93030408	STE24-232G-MPO-EPU	078531017446	2 x 4, 2-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Prog Start Ballast	●	●	●	●	●	20.0	14	
93029803	STE24-332G-MPO-3EU	078531017378	2 x 4, 3-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Ballast	●	●	●	●	●	20.0	14	
93030410	STE24-332G-MPO-3EPU	078531017460	2 x 4, 3-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Prog Start Ballast	●	●	●		●	20.0	14	
93029802	STE24-332G-MPO-EU	078531017392	2 x 4, 3-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec (2 Ballasts)	●	●	●	●	●	20.0	14	
93030409	STE24-332G-MPO-EU-FO735	078531017453	2 x 4, 3-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Ballast (2 Ballasts), T8 Lamps installed	●	●		●		20.0	14	
93029799	STE24-332G-MPO-3EU-FO735-C388	078531017484	2 x 4, 3-L, Metal Perf. Basket w/Overlay 120-277V, T8 Elec Ballast, T8 Lamps Installed, 3 Wire Flex	●				●	20.0	14	
93043912	STE24-332G-MPO-EU-FO841	078531023409	2x4, 3-L, Metal Perf. Basket w/Overlay, 120-277V T8 Elec Ballast (2 Ballasts), T8 Lamps installed					●	20.0	14	
93030962	Kit - STE/TRA 2x4 Dust Guard	078531017507	Dust Guard Kit, 4ft fixtures				●		1.0	N/A	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

STE	NO. OF LAMPS IN CROSS SECTION	CEILING TYPE	BALLAST	VOLTAGE	OPTIONS
STE	2 Two 3 Three	G Grid Lay-in	E Electronic T8, Instant Start EP Electronic T5, T5HO, or T8, Programmed Start ETT Electronic Twin Tube, Instant Start EPTT Electronic Twin Tube, Programmed Start	U 120V-277V 120 120V 277 277V	EL Emergency Battery Pack, T8 EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 FO730 30K 75CRI 17 or 32W T8 Lamps Installed FO735 35K 75CRI 17 or 32W T8 Lamps Installed FO741 41K 75CRI 17 or 32W T8 Lamps Installed FO830 30K 82CRI 17 or 32W T8 Lamps Installed FO835 35K 82CRI 17 or 32W T8 Lamps Installed FO841 41K 82CRI 17 or 32W T8 Lamps Installed F5830 30K 85CRI T5 or T5HO Lamps Installed F5835 35K 85CRI T5 or T5HO Lamps Installed F5841 41K 85CRI T5 or T5HO Lamps Installed FTT830 30K 82CRI 40W TT Lamps Installed FTT835 35K 82CRI 40W TT Lamps Installed FTT841 41K 82CRI 40W TT Lamps Installed C388 3-Wire Flex C488 4-Wire Flex
MODEL	SIZE	LAMP TYPE	SHIELDING	DIMMING BLST MFG/MODEL	
STE Stratus Recessed Indirect	22 2' x 2' 24 2' x 4'	17 2', T8: 17 Watt 24 2', T5HO: 24 Watt 28 4', T5: 28 Watt 32 4', T8 ¹ 40TT Twin Tube Compact, 2G11 Base: 40 Watt (2-Lamp only)	MPO Metal Perf w/Overlay	ADVMK10 Mark 10 Powerline ADVMK7 Mark 7 0-10V	
			3EPLW 3-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start		

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.
² Select voltage for ADVMK10.

QS5 5-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 100

STE				G		MPO		U	
MODEL	NO. OF LAMPS IN CROSS SECTION	CEILING TYPE	BALLAST	SHIELDING		VOLTAGE		OPTIONS	
STE Stratus Recessed Indirect	2 Two 3 Three	G Grid Lay-in	E Electronic T8, Instant Start EP Electronic T5, T5HO, or T8, Programmed Start ETT Electronic Twin Tube, Instant Start 3E 3-Lamp Electronic T8, Instant Start 3EP 3-Lamp Electronic T8 or T5, Programmed Start ELW 2-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 3ELW 3-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start	MPO Metal Perf w/Overlay		U 120V-277V		EL Emergency Battery Pack, T8 EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 FO730 30K 75CRI 17 or 32W T8 Lamps Installed FO735 35K 75CRI 17 or 32W T8 Lamps Installed FO741 41K 75CRI 17 or 32W T8 Lamps Installed FO830 30K 82CRI 17 or 32W T8 Lamps Installed FO835 35K 82CRI 17 or 32W T8 Lamps Installed FO841 41K 82CRI 17 or 32W T8 Lamps Installed F5830 30K 85CRI T5 or T5HO Lamps Installed F5835 35K 85CRI T5 or T5HO Lamps Installed F5841 41K 85CRI T5 or T5HO Lamps Installed C388 3-Wire Flex C488 4-Wire Flex	
SIZE	LAMP TYPE								
22 2' x 2'	17 2', T8: 17 Watt								
24 2' x 4'	24 2', T5HO: 24 Watt 28 4', T5: 28 Watt 32 4', T8 ¹ 40TT Twin Tube Compact, 2G11 Base: 40 Watt (2-Lamp only)								

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



TRA - Transition® High Efficiency Architectural Lensed

QS10 10-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 100

TRA				G		CLO			
MODEL	NO. OF LAMPS IN CROSS SECTION	CEILING TYPE	BALLAST	SHIELDING		VOLTAGE		OPTIONS	
TRA Transition® High Efficiency Architectural Lensed	2 Two 3 Three	G Grid Lay-in	E Electronic T8, Instant Start EP Electronic T5, T5HO, or T8, Programmed Start ETT Electronic Twin Tube, Instant Start EPTT Electronic Twin Tube, Programmed Start 3E 3-Lamp Electronic T8, Instant Start 3EP 3-Lamp Electronic T8 or T5, Programmed Start ELW 2-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 3ELW 3-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start E104 Electronic T8, 1.04 Ballast Factor, Instant Start ED Electronic Dimming (2-lamp T8 only. Specify Mfg & Model) EPLW Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 3EPLW 3-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start	CLO Clear Linear Prism Acrylic with Overlay		U 120V-277V 120 120V 277 277V		EL Emergency Battery Pack, T8 EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 FO730 30K 75CRI 17 or 32W T8 Lamps Installed FO735 35K 75CRI 17 or 32W T8 Lamps Installed FO741 41K 75CRI 17 or 32W T8 Lamps Installed FO830 30K 82CRI 17 or 32W T8 Lamps Installed FO835 35K 82CRI 17 or 32W T8 Lamps Installed FO841 41K 82CRI 17 or 32W T8 Lamps Installed F5830 30K 85CRI T5 or T5HO Lamps Installed F5835 35K 85CRI T5 or T5HO Lamps Installed F5841 41K 85CRI T5 or T5HO Lamps Installed FTT830 30K 82CRI 40W TT Lamps Installed FTT835 35K 82CRI 40W TT Lamps Installed FTT841 41K 82CRI 40W TT Lamps Installed C388 3-Wire Flex C488 4-Wire Flex	
SIZE	LAMP TYPE					DIMMING BLST MFG/MODEL			
22 2' x 2'	17 2', T8: 17 Watt					ADV MK10 Mark 10 Powerline ² ADV MK7 Mark 7 0-10V			
24 2' x 4'	24 2', T5HO: 24 Watt 28 4', T5: 28 Watt 32 4', T8 ¹ 40TT Twin Tube Compact, 2G11 Base: 40 Watt (2-Lamp only)								

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.
² Select voltage for ADV MK10.



TRE - Transition® Enclosed High Efficiency Architectural Lensed



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

TRE				G		RFA					
MODEL	NO. OF LAMPS IN CROSS SECTION	CEILING TYPE	BALLAST	SHIELDING	VOLTAGE	OPTIONS					
TRE Transition® Enclosed High Efficiency Architectural Lensed	2 Two 3 Three	G Grid Lay-in	E Electronic T8, Instant Start EP Electronic T5, T5HO, or T8, Programmed Start ETT Electronic Twin Tube, Instant Start EPTT Electronic Twin Tube, Programmed Start 3E 3-Lamp Electronic T8, Instant Start 3EP 3-Lamp Electronic T8 or T5, Programmed Start ELW 2-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 3ELW 3-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start E104 Electronic T8, 1.04 Ballast Factor, Instant Start ED Electronic Dimming (2-lamp T8 only. Specify Mfg & Model) EPLW Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 3EPLW 3-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start	RFA Ribbed Frosted Acrylic	U 120V-277V 120 120V 277 277V	EL Emergency Battery Pack, T8 EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 FO730 30K 75CRI 17 or 32W T8 Lamps Installed FO735 35K 75CRI 17 or 32W T8 Lamps Installed FO741 41K 75CRI 17 or 32W T8 Lamps Installed FO830 30K 82CRI 17 or 32W T8 Lamps Installed FO835 35K 82CRI 17 or 32W T8 Lamps Installed FO841 41K 82CRI 17 or 32W T8 Lamps Installed F5830 30K 85CRI T5 or T5HO Lamps Installed F5835 35K 85CRI T5 or T5HO Lamps Installed F5841 41K 85CRI T5 or T5HO Lamps Installed FTT830 30K 82CRI 40W TT Lamps Installed FTT835 35K 82CRI 40W TT Lamps Installed FTT841 41K 82CRI 40W TT Lamps Installed C388 3-Wire Flex C488 4-Wire Flex					
SIZE	LAMP TYPE	SHIELDING	DIMMING BLST MFG/MODEL								
22 2' x 2'	17 2', T8: 17 Watt	RFA Ribbed Frosted Acrylic	ADVMK10 Mark 10 Powerline ² ADVMK7 Mark 7 0-10V								
24 2' x 4'	24 2', T5HO: 24 Watt 28 4', T5: 28 Watt 32 4', T8 ¹ 40TT Twin Tube Compact, 2G11 Base: 40 Watt (2-Lamp only)										

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.
² Select voltage for ADVMK10.



ZPT - Zero Plenum Troffer



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

ZPT		2		G				EP		U	
MODEL	NO. OF LAMPS	CEILING TYPE	REFLECTOR	SHIELDING	BALLAST	VOLTAGE					
ZPT Zero Plenum® Troffer	2 Two	G Grid Lay-in	O Open (N/A with PRF) R Ribbed Curve S Smooth Curve	LSR Linear Prismatic Lens with Surface Relief Diffuser PRF Metal Perf w/ Overlay	EP Electronic T5, 1.00 Ballast Factor (28W or 54W)	U 120V-277V					
SIZE	LAMP TYPE	SHIELDING	OPTIONS								
22 2' x 2'	14 2', T5: 14 Watt	LSR Linear Prismatic Lens with Surface Relief Diffuser	C38890 3-Wire Flex, 90° Connector EL5 Emergency Battery Pack (N/A 2 x 2) F5835 35K 85CRI T5 or T5HO Lamps Installed F5841 41K 85CRI T5 or T5HO Lamps Installed								
24 2' x 4'	24 2', T5HO: 24 Watt 28 4', T5: 28 Watt 54 4', T5HO: 54 or 51 Watt	PRF Metal Perf w/ Overlay									
ACCESSORIES (ORDER SEPARATELY)											
ZPTSMK22 ZPT Surface Mounting Kit (2' x 2')											
ZPTSMK24 ZPT Surface Mounting Kit (2' x 4')											



EMX - Energy Saving Parabolic



10-Day Quick Ship Ordering Guide*

Order Limit Per Fixture Selection: 50

EMX	24	2	32	G	M5	26	S		U	
MODEL EMX EnergyMax® Energy Saving Parabolic	NO. OF LAMPS 2 Two	CEILING TYPE G Grid	CELLS WIDE BY CELLS LONG 26 2 × 6	VOLTAGE U 120V-277V	OPTIONS FO28835 35K 82CRI 28W T8 Lamps Installed¹ FO835 35K 82CRI 32W T8 Lamps Installed FO841 41K 82CRI 32W T8 Lamps Installed C388 3-Wire Flex EL Emergency Battery Pack EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8	SIZE 24 2' × 4'	LAMP TYPE 32 4', T8¹	LOUVER FINISH M5 MIRO-5	AIR HANDLING S Static	BALLAST E Electronic T8, 0.88 Ballast Factor, Instant Start E104 Electronic T8, 1.04 Ballast Factor, Instant Start EP Electronic T5, T5HO, or T8, Programmed Start

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



P4 - Specification Grade Parabolic



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

P4			32	G	LD		S		U	
MODEL P4 Recessed Air Handling Parabolic	NO. OF LAMPS 2 Two (1 × 4 only) 3 Three (2 × 4 only)	CEILING TYPE G Grid	CELLS WIDE BY CELLS LONG 18 1 × 8 (1 × 4 only) 36 3 × 6 (2 × 4 only)	VOLTAGE U 120V-277V	OPTIONS FO735 35K 75CRI 32W T8 Lamps Installed FO741 41K 75CRI 32W T8 Lamp Installed FO835 35K 82CRI 32W T8 Lamps Installed FO841 41K 82CRI 32W T8 Lamp Installed C388 3-Wire Flex C488 4-Wire Flex EL Emergency Battery Pack EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8	SIZE 14 1' × 4' 24 2' × 4'	LAMP TYPE 32 4', T8¹	LOUVER FINISH LD Low Iridescent Semi-Specular	AIR FUNCTIONS S Static	BALLAST E Electronic T8, Instant Start 3E 3-Lamp Electronic T8, Instant Start EP T8, Programmed Start 3EP 3-Lamp Electronic T8, Programmed Start ELW Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 3ELW 3-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start EPLW Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 3EPLW 3-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



P4D - High Performance Parabolic

35 SCHEDULED
STOCK
SHIPMENTS

Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
P4D00162	P4D22-232U6G-MA33-AV-EU	078531006501	2 x 2, 2-L, 9 Cell MA Lvr, 120-277V T8 Elec Ballast, Air w/Vanes			•			32.0	28	
P4D00120	P4D22-232U6G-MA33-S-EU	078531043445	2 x 2, 2-L, 9 Cell MA Lvr, 120-277V T8 Elec Ballast, Static	•	•	•	•	•	32.0	28	
P4D00156	P4D24-232G-MA26-S-EU	078531043704	2 x 4, 2-L, 12 Cell MA Lvr, 120-277V T8 Elec Ballast, Static	•	•	•	•	•	32.0	16	
P4D00157	P4D24-332G-MA36-AV-3EU	078531043711	2 x 4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Air w/Vanes			•	•	•	33.0	16	
P4D00146	P4D24-332G-MA36-S-3EU	078531043483	2 x 4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Static	•	•	•	•	•	33.0	16	
93043905	P4D24-332G-MA36-S-3EPU	078531023331	2x4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Prog Start Ballast, Static		•				33.0	16	
P4D00138	P4D24-332G-MA36-S-EU	078531043414	2 x 4, 3-L, 18 Cell MA Lvr, 120-277V T8 Elec (2 Ballasts), Static	•	•	•	•	•	35.0	16	
93043906	P4D24-332G-MA36-S-EPU	078531023348	2x4, 3-L, 18 Cell MA Lvr, 120-277V T8 Elec Prog Start (2) Ballasts, Static		•				33.0	16	
P4D00143	P4D24-332G-MA36-S-3EU- FO735	078531043476	2 x 4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Static, T8 Lamps Installed		•	•	•	•	34.0	16	
P4D00119	P4D24-332G-MA36-S-3EU- FO735-C388	078531043261	2 x 4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Stat, T8 Lamps Installed, 3 Wire Flex	•			•	•	34.0	16	
93043907	P4D24-332G-MA36-S-3EU- FO741	078531023355	2x4, 3-L, 18 Cell MA Lvr, 120-277V 3-L T8 Elec Ballast, Static, T8 Lamps Installed		•				34.0	16	
P4D00147	P4D24-432G-MA48-S-4EU	078531043490	2 x 4, 4-L, 32 Cell, 120-277V 4-L T8 Elec Ballast, Static		•	•	•	•	34.0	16	
P4D019047.16PK1	LVR P4D24 3X6 MA HK BAG	078531044985	Louver for 2 x 4, 18 cell, MA	•	•	•	•	•	10.0	N/A	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

MODEL	NO. OF LAMPS	CEILING TYPE	CELLS WIDE BY CELLS LONG	BALLAST	VOLTAGE
P4D High Performance Parabolic	2 Two 3 Three 4 Four (N/A in 2 x 2)	G Grid	33 3 x 3 (2' x 2' only) 26 2 x 6 (2' x 4' 2-Lamp only) 36 3 x 6 (2' x 4' 3-Lamp only) 48 4 x 8 (2' x 4' 4-Lamp only)	E 2-Lamp Electronic T8, Instant Start 3E 3-Lamp Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP T8, Programmed Start 3EP 3-Lamp T8, Programmed Start 4EP 4-Lamp T8, Programmed Start 24E 2 or 4-Lamp Electronic T8, Instant Start (For 3-Lamp Master/Satellite only) ELW 2-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 3ELW 3-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 4ELW 4-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start EPLW Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 3EPLW 3-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 4EPLW 4-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start	U 120V-277V
SIZE	LAMP TYPE	LOUVER FINISH	AIR HANDLING	OPTIONS	
22 2' x 2' 24 2' x 4'	17 2', T8: 17 Watt 32 4', T8 ¹ 32U6 U-Bent, 6" Leg Spacing T8: 32 Watt (2-Lamp only)	MA Matte Anodized Low Iridescent Semi-Specular Aluminum (Std.)	S Static	FO735 35K 75CRI Full Wattage T8 Lamps Installed FO741 41K 75CRI Full Wattage T8 Lamps Installed FO835 35K 82CRI Full Wattage T8 Lamps Installed FO841 41K 82CRI Full Wattage T8 Lamps Installed C388 3-Wire Flex C488 4-Wire Flex EL Emergency Battery Pack EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 MS11 Master/Satellite w/ 11' Harness	

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.

QS75 5-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 150

P4D			G	MA		S		U	
MODEL	NO. OF LAMPS	CEILING TYPE	CELLS WIDE BY CELLS LONG		BALLAST		VOLTAGE		
P4D High Performance Parabolic	2 Two 3 Three	G Grid	33 3 x 3 (2' x 2' only) 36 3 x 6 (2' x 4' 3-Lamp only)		E 2-Lamp Electronic T8, Instant Start 3E 3-Lamp Electronic T8, Instant Start EP T8, Programmed Start 3EP 3-Lamp T8, Programmed Start		U 120V-277V		
SIZE	LAMP TYPE	LOUVER FINISH	AIR HANDLING		OPTIONS				
22 2' x 2' 24 2' x 4'	32 4', T8 ¹ 32U6 U-Bent, 6" Leg Spacing T8: 32 Watt (2-Lamp only)	MA Matte Anodized Low Iridescent Semi-Specular Aluminum (Std.)	S Static		FO735 35K 75CRI Full Wattage T8 Lamps Installed FO741 41K 75CRI Full Wattage T8 Lamps Installed FO835 35K 82CRI Full Wattage T8 Lamps Installed FO841 41K 82CRI Full Wattage T8 Lamps Installed C388 3-Wire Flex C488 4-Wire Flex EL Emergency Battery Pack EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8				

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



JT8- Lensed Troffers



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
JT243119FTP0000	JT822-232U6G-FSA12-EU	078531005603	2 x 2, 2-L, 120-277V T8 Elec Ballast	●	●	●	●	●	16.0	36	
93046042	JT822-232U6SM-FSA12-EU	078531121075	2 x 2 Surface Mount, 2-L, 120-277V T8 Elec Ballast	●		●	●		20.0	14	
JT241519F000000	JT824-232G-FSA12125-EU	078531006914	2 x 4, 2-L, 120-277V T8 Elec Ballast, .125" Lens	●	●	●	●	●	20.0	26	
JT24111BL000000	JT824-232G-FSA12-ELWU	078531011765	2x4, 2-L, 120-277V T8 Elec Low Wattage Ballast			●			20.0	26	
JT241119F000000	JT824-232G-FSA12-EU	078531005610	2 x 4, 2-L, 120-277V T8 Elec Ballast	●	●	●	●	●	20.0	26	
JT241119F88QZ00	JT824-232G-FSA12-EU-FO735-C388	078531009359	2 x 4, 2-L, 120-277V T8 Elec Ballast, 3 Wire Flex, T8 Lamps Installed	●			●	●	24.0	26	
JT341519G000000	JT824-332G-FSA12125-3EU	078531006815	2 x 4, 3-L, 120-277V 3-L T8 Elec Ballast, .125" Lens		●	●	●	●	20.0	26	
JT34111BM000000	JT824-332G-FSA12-3ELWU	078531010867	2x4, 3-L, 120-277V 3-L T8 Elec Low Wattage Ballast			●			20.0	26	
93043898	JT824-332G-FSA12-3EPU	078531023447	2x4, 3-L, 120-277V 3-L T8 Elec Prog Start Ballast		●				20.0	26	
JT341119G000000	JT824-332G-FSA12-3EU	078531005627	2 x 4, 3-L, 120-277V 3-L T8 Elec Ball.	●	●	●	●	●	20.0	26	
JT341119GQZ0000	JT824-332G-FSA12-3EU-FO735	078531006006	2 x 4, 3-L, 120-277V 3-L T8 Elec Ballast, T8 Lamps Installed		●		●	●	23.0	26	
JT341119G88QZ00	JT824-332G-FSA12-3EU-FO735-C388	078531005955	2 x 4, 3-L, 120-277V 3-L T8 Elec Ballast, T8 Lamps Installed, 3 Wire Flex	●	●		●	●	24.0	26	
93043900	JT824-332G-FSA12-3EU-FO741	078531023461	2 x 4, 3-L, 120-277V 3-L T8 Elec Ball., T8 Lamps Installed		●		●		23.0	26	
93043899	JT824-332G-FSA12-EPU	078531023454	2x4, 3-L, 120-277V T8 Elec Prog Start (2 Ballasts)		●				20.0	26	
JT341119F000000	JT824-332G-FSA12-EU	078531005634	2 x 4, 3-L, 120-277V T8 Elec (2 Ballasts)	●	●	●	●	●	24.0	26	
93046045	JT824-332SM-FSA12-3EU	078531121105	2 x 4 Surface Mount, 3-L 120-277V T8 Elec Ballast		●	●			24.0	9	
JT441119H000000	JT824-432G-FSA12-4EU	078531005641	2 x 4, 4-L, 120-277V 4-L T8 Elec Ballast	●	●	●	●	●	18.0	26	
JT441119HQZ0000	JT824-432G-FSA12-4EU-FO735	078531006020	2 x 4, 4-L, 120-277V 4-L T8 Elec Ballast, T8 Lamps Installed		●	●	●	●	23.0	26	
JT441119H88QZ00	JT824-432G-FSA12-4EU-FO735-C388	078531005818	2 x 4, 4-L, 120-277V 4-L T8 Elec Ballast, T8 Lamps Installed, 3 Wire Flex	●	●		●	●	24.0	26	
JT441119HJZ0000	JT824-432G-FSA12-4EU-FO741	078531006013	2 x 4, 4-L, 120-277V 4-L T8 Elec Ballast, T8 41K Lamps Installed		●		●	●	23.0	26	
JT441119H88JZ00	JT824-432G-FSA12-4EU-FO741-C388	078531009175	2 x 4, 4-L, 120-277V 4-L T8 Elec Ballast, T8 41K Lamps Installed, 3 Wire Flex		●	●	●	●	24.0	26	
JT441119F000000	JT824-432G-FSA12-EU	078531005658	2 x 4, 4-L, 120-277V T8 Elec (2 Ballasts)	●	●	●	●	●	24.0	26	
93046044	JT824-432SM-FSA12-4EU	078531121099	2 x 4 Surface Mount, 4-L 120-277V T8 Elec Ballast		●	●	●		24.0	9	
JT2499000800000	DR&SHLD JT824 FS A12	078531012632	2 x 4 Replacement Door Assembly with Lens			●			5.0	N/A	
003334.00	A12.095 22.500-22.500	078531004781	2 x 2 Replacement Lens		●	●			1.0	N/A	
003335.00	A12.095 22.500-46.562	078531004774	2 x 4 Replacement Lens	●	●	●	●	●	2.0	N/A	
003312.00	A12.125	078531022891	2x4 Replacement Lens	●	●	●	●	●	2.5	N/A	



JT8 - Lensed Troffers

QS 10 10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 200

JT8					G	FS			U		
MODEL	JT8 Dedicated T8 Lensed Troffer	NO. OF LAMPS	2 Two 3 Three 4 Four (2 x 4 only)	CEILING TYPE	G Grid	SHIELDING	A12 Pattern 12 Acrylic Lens A12125 Pattern 12 Acrylic Lens, 0.125" Nominal	VOLTAGE	U 120V-277V	OPTIONS	FO735 35K 75CRI Full Wattage T8 Lamps Installed FO741 41K 75CRI Full Wattage T8 Lamps Installed FO835 35K 82CRI Full Wattage T8 Lamps Installed FO841 41K 82CRI Full Wattage T8 Lamps Installed EL Emergency Battery Pack ² EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 MS11 Master/Satellite w/11' Harness C388 3-Wire Flex C488 4-Wire Flex
SIZE	22 2' x 2' 24 2' x 4'	LAMP TYPE	17 2', T8: 17 Watt 32 4', T8 ¹ 32U6 U-Bent, 6" Leg Spacing T8: 32 Watt (2 lamps)	DOOR	FS White Flush Steel	BALLAST					
						E Electronic T8, Instant Start 3E 3-Lamp Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start (17W lamps only) 24E (1) 2-Lamp & (1) 4-Lamp Electronic T8, Instant Start (For use with MS11) EP Electronic T8, Programmed Start 3EP 3-Lamp Electronic T8, Programmed Start 4EP 4-Lamp Electronic T8, Programmed Start ELW 2-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 3ELW 3-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 4ELW 4-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start EPLW Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 3EPLW 3-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 4EPLW 4-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start					

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.
² 2 x 2 with 2 ballasts and EL N/A as Quick Ship.

QS 5 5-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 200

JT8					G	FS			U		
MODEL	JT8 Dedicated T8 Lensed Troffer	NO. OF LAMPS	2 Two 3 Three 4 Four (2 x 4 only)	CEILING TYPE	G Grid	SHIELDING	A12 Pattern 12 Acrylic Lens A12125 Pattern 12 Acrylic Lens, 0.125" Nominal	VOLTAGE	U 120V-277V	OPTIONS	FO735 35K 75CRI Full Wattage T8 Lamps Installed FO741 41K 75CRI Full Wattage T8 Lamps Installed FO835 35K 82CRI Full Wattage T8 Lamps Installed FO841 41K 82CRI Full Wattage T8 Lamps Installed EL Emergency Battery Pack ² EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 C388 3-Wire Flex C488 4-Wire Flex
SIZE	22 2' x 2' 24 2' x 4'	LAMP TYPE	17 2', T8: 17 Watt 32 4', T8 ¹ 32U6 U-Bent, 6" Leg Spacing T8: 32 Watt (2 lamps)	DOOR	FS White Flush Steel	BALLAST					
						E Electronic T8, Instant Start 3E 3-Lamp Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start (17W lamps only) EP Electronic T8, Programmed Start 3EP 3-Lamp Electronic T8, Programmed Start 4EP 4-Lamp Electronic T8, Programmed Start ELW 2-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 3ELW 3-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 4ELW 4-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start					

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.
² 2 x 2 with 2 ballasts and EL N/A as Quick Ship.



ST8 - Shallow Specification Lensed Troffers

35 SCHEDULED
STOCK
SHIPMENTS

Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
HS241519F000000	ST824-232G-FSA12125-EU	078531006853	2 x 4, 2-L, 120-277V T8 Elec Ballast, .125" Lens	•	•	•	•	•	22.0	24	
HS341519G000000	ST824-332G-FSA12125-3EU	078531006884	2 x 4, 3-L, 120-277V 3-L T8 Elec Ballast, .125" Lens	•	•	•	•	•	22.0	24	
93043895	ST824-332G-FSA12125-3EPU	078531023416	2x4, 3-L, 120-277V 3-L T8 Elec Prog Start Ballast, .125" Lens	•	•	•			22.0	24	
HS341519F000000	ST824-332G-FSA12125-EU	078531006877	2 x 4, 3-L, 120-277V T8 Elec (2 Ballasts), .125" Lens	•	•	•	•	•	25.0	24	
93043896	ST824-332G-FSA12125-EPU	078531023423	2x4, 3-L, 120-277V T8 Elec Prog Start (2) Ballasts, .125" Lens	•	•	•			22.0	24	
HS441519H000000	ST824-432G-FSA12125-4EU	078531006907	2 x 4, 4-L, 120-277V 4-L T8 Elec Ballast, .125" Lens				•	•	22.0	24	
HS441519F000000	ST824-432G-FSA12125-EU	078531006891	2 x 4, 4-L, 120-277V T8 Elec (2 Ballasts), .125" Lens		•	•			26.0	24	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 200

ST8	-		-	FS	-		-	U	-	
MODEL	NO. OF LAMPS	CEILING TYPE	SHIELDING			VOLTAGE				
ST8 Low Profile Specification Troffer	2 Two 3 Three (N/A 1 x 4) 4 Four (N/A 1 x 4 or 2 x 2)	G Grid F Overlap Flange (1 x 4 only)	A12 Pattern 12 Acrylic Lens A12125 Pattern 12 Acrylic Lens, 0.125" Nominal			U 120V-277V				
SIZE	LAMP TYPE		BALLAST				OPTIONS			
14 1' x 4' 22 2' x 2' 24 2' x 4'	17 2; T8: 17 Watt 32 4; T8 ¹ 32U6 U-Bent, 6" Leg Spacing T8: 32 Watt (2-lamp only)		E Electronic T8, Instant Start 3E 3-Lamp Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP Electronic T8, Programmed Start 3EP 3-Lamp Electronic T8, Programmed Start 4EP 4-Lamp Electronic T8, Programmed Start ELW 2-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 3ELW 3-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 4ELW 4-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 24E 2 or 4-Lamp Electronic T8, Instant Start (For 3-Lamp Master/Satellite only) EPLW Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 3EPLW 3-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 4EPLW 4-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start				FO735 35K 75CRI Full Wattage T8 Lamps Installed FO741 41K 75CRI Full Wattage T8 Lamps Installed FO835 35K 82CRI Full Wattage T8 Lamps Installed FO841 41K 82CRI Full Wattage T8 Lamps Installed EL Emergency Battery Pack ² EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 MS11 Master/Satellite Pair w/11' Harness C388 3-Wire Flex C488 4-Wire Flex			
DOOR			FS White Flush Steel							

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.
² 2 x 2 with 2 ballasts and EL N/A as Quick Ship.

QS75 5-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 200

ST8				G	FS			U	
MODEL	NO. OF LAMPS	CEILING TYPE			SHIELDING			VOLTAGE	
ST8 Low Profile Specification Troffer	2 Two 3 Three 4 Four	G Grid			A12 Pattern 12 Acrylic Lens A12125 Pattern 12 Acrylic Lens, 0.125" Nominal			U 120V-277V	
							BALLAST		
SIZE	LAMP TYPE		DOOR						
22 2' x 2'	17 2', T8: 17 Watt		FS White Flush Steel		E Electronic T8, Instant Start				
24 2' x 4'	32 4', T8 ¹				3E 3-Lamp Electronic T8, Instant Start				
	32U6 U-Bent, 6" Leg Spacing T8: 32 Watt (2-lamp only)				4E 4-Lamp Electronic T8, Instant Start				
					EP Electronic T8, Programmed Start				
					3EP 3-Lamp Electronic T8, Programmed Start				
					4EP 4-Lamp Electronic T8, Programmed Start				
					ELW 2-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start				
					3ELW 3-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start				
					4ELW 4-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start				
					FO735 35K 75CRI Full Wattage T8 Lamps Installed				
					FO741 41K 75CRI Full Wattage T8 Lamps Installed				
					FO835 35K 82CRI Full Wattage T8 Lamps Installed				
					FO841 41K 82CRI Full Wattage T8 Lamps Installed				
					EL Emergency Battery Pack ²				
					EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8				
					C388 3-Wire Flex				
					C488 4-Wire Flex				

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.
² 2 x 2 with 2 ballasts and EL N/A as Quick Ship.



4PS - Specification Grade Lensed Troffers



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
93046043	4PS14-232SM-FSA12-EU	078531121082	1 x 4 Surface Mount, 2-L, 120-277V T8 Elec Ballast	•	•	•	•		20.0	14	
HW241519F000000	4PS24-232G-FSA12125-EU	078531009106	2 x 4, 2-L, 120-277V T8 Elec Ballast, .125" Lens	•	•	•	•	•	22.0	18	
HW341519G000000	4PS24-332G-FSA12125-3EU	078531009113	2 x 4, 3-L, 120-277V 3-L T8 Elec Ballast, .125" Lens		•			•	23.0	18	
HW341519F000000	4PS24-332G-FSA12125-EU	078531009120	2 x 4, 3-L, 120-277V T8 Elec (2 Ballasts), .125" Lens	•			•	•	25.0	18	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

4PS	-		G	-		-		U	-	
MODEL 4PS Specification Grade Static Troffer	NO. OF LAMPS 2 Two 3 Three (2 x 4 only) 4 Four (2 x 4 only)	CEILING TYPE G Grid	SHIELDING A12 Pattern 12 Acrylic Lens A12125 Pattern 12 Acrylic Lens, 0.125" Nominal	VOLTAGE U 120V-277V	OPTIONS F0735 35K 75CRI Full Wattage T8 Lamps Installed F0741 41K 75CRI Full Wattage T8 Lamps Installed F0835 35K 82CRI Full Wattage T8 Lamps Installed F0841 41K 82CRI Full Wattage T8 Lamps Installed EL Emergency Battery Pack, T8 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8 C388 3-Wire Flex C488 4-Wire Flex					
SIZE 22 2' x 2' 24 2' x 4'	LAMP TYPE 32 4', T8 ¹ 32U6 U-Bent, 6" Leg Spacing T8: 32 Watt (2 lamps) 40TT Twin Tube Compact, 2G11 Base: 40 Watt (2 or 3 lamps)	DOOR FS White Flush Steel RA White Regressed Aluminum	BALLAST E Electronic T8, Instant Start 3E 3-Lamp Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP Electronic T8, Programmed Start 3EP 3-Lamp Electronic T8, Programmed Start 4EP 4-Lamp Electronic T8, Programmed Start ETT Electronic Twin Tube, Instant Start ELW 2-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 3ELW 3-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 4ELW 4-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start EPLW Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 3EPLW 3-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 4EPLW 4-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start							

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



BIL - Integrated Sensor for Stairwell Applications



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
BIL000002	BIL4-232-EPU	078531016807	4', 2-L, 32W T8, Elec Ballast		•	•			9.0	N/A	



SA - Wall Brackets



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
34241019F000000	SA4-232-EU	078531006792	2-4' T8, 4', 120-277V Elec Ballast	•	•	•	•	•	13.0	24	



UC - Undercabinet



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
93047671	UC24-117-EU	078531023690	2', 1-L, 17W T8, Elec Ballast		•	•	•	•	6.0	224	
93047672	UC36-125-EU	078531023706	3', 1-L, 25W T8, Elec Ballast	•	•	•	•	•	6.0	140	
93047673	UC48-132-EU	078531023713	4', 1-L, 32W T8, Elec Ballast	•	•	•	•	•	8.0	112	



W - Wall Mount Light



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
24222019F000000	W2-217-EU	078531010294	2-2'T8, 2', 120-277V T8 Elec Ballast Less Switch, Less Convenience Outlet	•	•	•	•	•	6.0	N/A	
24241019F000000	W4-232-EU	078531007287	2-4'T8, 4', 120-277V T8 Elec Ballast Less Switch, Less Convenience Outlet	•	•	•	•	•	13.0	N/A	



WAL - Wall Mount



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
DS241019F000000	WAL4-232-EU	078531006068	2-4' T8, 4', 120-277V T8 Elec Ballast	●	●	●	●	●	16.0	55	




AD - Corridor Wraparounds



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
22122019F000000	AD2-117-EU	078531011994	1-2'T8, 2', 120-277V T8 Elec Ballast			●			7.0	56	
22222019F000000	AD2-217-EU	078531006303	2-2'T8, 2', 120-277V T8 Elec Ballast			●			7.0	56	
22141019F000000	AD4-132-EU	078531006327	1-4'T8, 4', 120-277V T8 Elec Ballast			●			10.0	56	
22241019F000000	AD4-232-EU	078531006334	2-4'T8, 4', 120-277V T8 Elec Ballast	●	●	●		●	10.0	56	



VR - Vandal Wrap



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
VRM232U	VRM4-232-EU	078531012922	Medium, 2-L, T8, 120-277V T8 Elec Ballast			●			10.0	N/A	



AW- Wraparounds



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
CY222019F000000	AWN2-217-EU	078531009984	2-2' T8, 2', 120-277V T8 Elec Ballast		●	●	●	●	8.0	110	
CY241019F000000	AWN4-232-EU	078531004859	2-4' T8, 4', 120-277V T8 Elec Ballast	●	●	●	●	●	14.0	55	
93043931	AWN4-232-EPU	078531023508	2-4' T8, 4', 120-277V T8 Elec Prog Start Ballast	●	●				14.0	55	
CY24101BL000000	AWN4-232-ELWU	078531011857	2-4' T8, 4', 120-277V T8 Elec Low Wattage Ballast	●		●			14.0	55	
CY441019H000000	AWN8-232-4EU	078531005979	4-4' T8, 8', 120-277V 4-L T8 Elec Ballast	●	●	●			26.0	30	
93015558	AWN8-232-4ELWU	078531012441	4-4' T8, 8', 120-277V 4-L T8 Elec Low Wattage Ballast			●			26.0	30	
CL341019G000000	AWW4-332-3EU	078531004866	3-4' T8, 4', 120-277V 3-L T8 Elec Ballast	●	●	●	●	●	14.0	33	
CL441019H000000	AWW4-432-4EU	078531004873	4-4' T8, 4', 120-277V 4-L T8 Elec Ballast	●	●	●	●	●	14.0	33	
93043932	AWW4-432-4EPU	078531023515	4-4' T8, 4', 120-277V 4-L T8 Elec Prog Start Ballast	●					14.0	33	
CL44101BN000000	AWW4-432-4ELWU	078531012823	4-4' T8, 4', 120-277V 4-L T8 Elec Low Wattage Ballast			●			14.0	33	
CY8092746000000	SHLD AWN 4FT	078531001148	AWN Replacement Lens	●	●	●	●	●	10.0	100	
CL8092721000000	SHLD AWW 4FT	078531001155	AWW Replacement Lens	●	●	●	●	●	5.0	66	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

<input type="text"/>	<input type="text"/>	-	<input type="text"/>	<input type="text"/>	-	<input type="text"/>	<input type="text"/>	-	<input type="text"/>
MODEL	SIZE		LAMP TYPE			VOLTAGE			OPTIONS
AWN 8 ⁵ / ₁₆ " Wide	4 4'		32 4' T8 ¹			U 120V-277V			EL Emergency Battery Pack
AWW 14 ⁵ / ₁₆ " Wide	8 8' (AWN only)								EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8
	NO. OF LAMPS IN CROSS SECTION		BALLAST						
	2 Two		E	Electronic Instant Start					
	3 Three (AWW only)		3E	3-Lamp Electronic T8, Instant Start					
	4 Four (AWW only)		4E	4-Lamp Electronic T8, Instant Start					
			EP	Electronic T8, Programmed Start					
			3EP	3-Lamp Electronic T8, Programmed Start					
			4EP	4-Lamp Electronic T8, Programmed Start					
			ELW	2-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start					
			3ELW	3-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start					
			4ELW	4-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start					
			EPLW	Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start					
			3EPLW	3-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start					
			4EPLW	4-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start					

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



WC - Specification Grade Wraparounds



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
CD241019F000000	WC4-232-EU	078531006075	2-4'T8, 4', 120-277V T8 Elec Ballast	●	●	●	●	●	13.0	48	
CD441019H000000	WC8-232-4EU	078531006822	4-4'T8, 8', 120-277V 4-L T8 Elec Ballast		●				26.0	36	
CF341019G000000	WCW4-332-3EU	078531006341	3-4'T8, 4', 120-277V 3-L T8 Elec Ballast	●		●			14.0	33	
CF441019H000000	WCW4-432-4EU	078531006082	4-4'T8, 4', 120-277V 4-L T8 Elec Ballast	●	●	●			16.0	28	
CD8013802000000	SHLD ASY WC 4FT	078531000998	WC Replacement Lens - 4'	●	●	●	●	●	3.1	54	
CF8013803000000	SHLD ASY WCW 4FT	078531001001	WCW Replacement Lens	●	●	●			10.0	80	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 50

<input type="text"/>	<input type="text"/>	-	<input type="text"/>	<input type="text"/>	-	<input type="text"/>	<input type="text"/>	-	<input type="text"/>
MODEL	SIZE		LAMP TYPE	BALLAST		VOLTAGE	OPTIONS		
WC 10" Wide	4 4'		32 4', T8 ¹	E Electronic Instant Start		U 120V-277V	EL Emergency Battery Pack		
WCW 15 3/8" Wide	8 8' (WC only)			4E 4-Lamp Electronic T8, Instant Start			EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8		
				EP Electronic T8, Programmed Start					
				4EP 4-Lamp Electronic T8, Programmed Start					
				ELW 2-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start					
				4ELW 4-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start					
				EPLW Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start					
				4EPLW 4-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start					

NO. OF LAMPS IN CROSS SECTION

2 Two
4 Four

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



CSR - Industrials



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
56241719F910000	CSR4-232-ST-EU	078531004934	2-4' T8, 4', 120-277V T8 Elec Ballast, Solid Reflector	•	•	•	•	•	11.0	48	
5624171BL910000	CSR4-232-ST-ELWU	078531011918	2-4' T8, 4', 120-277V T8 Elec Low Wattage Ballast, Solid Reflector			•			11.0	48	
55441719H910000	CSR8-232-ST-4EU	078531004941	2-4' T8, 8', 120-277V 4-L T8 Elec Ballast, Solid Reflector	•	•	•	•	•	20.0	27	
56275719F910000	CSR8-296T8-ST-EU	078531005986	2-8' T8, 8', 120-277V T8 Elec Ballast, Solid Reflector		•	•	•	•	26.0	27	
562092935000000	CSRWG4	078531740139	4' Wire Guard for CSR series	•	•	•	•	•	2.5	N/A	
985084348700000	CSZT	078531740146	Zip T-Hanger - 1/2" spacer		•	•	•	•	0.2	N/A	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

CSR		-						U	-	EL
MODEL	NO. OF LAMPS		REFLECTOR TYPE		VOLTAGE		OPTIONS			
CSR Industrial	2 Two 3 Three (T8 only)		ST Solid Top Reflector U Apertured Reflector for 5% Uplight (Solid Reflector not recommended with HO units)		U 120V-277V		EL Emergency Battery Pack (T8 only) EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8			
SIZE	LAMP TYPE		BALLAST							
4 4' 8 8'	32 4', T8 ¹ 96HO 8', T12: 110 or 95 Watt		E Electronic, Instant Start 3E 3-Lamp Electronic T8 (32W), Instant Start 4E 4-Lamp Electronic T8 (32W), Instant Start EP Electronic, Programmed Start, T8 3EP 3-Lamp Electronic T8, Programmed Start 4EP 4-Lamp Electronic T8, Programmed Start ELW 2-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 3ELW 3-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 4ELW 4-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start EPLW Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 3EPLW 3-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 4EPLW 3-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start							

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



LHA- Industrial Fluorescent High Bay

35 SCHEDULED
STOCK
SHIPMENTS

Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
000016	LHA4-454-NST-4EPU	078531022464	4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, Narrow Distribution, Solid Reflector	●	●	●			22.0	30	
93043288	LHA4-454-NST-4EPU-F554841	078531023232	4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, 54W-T5 Lamps Installed Narrow Distribution, Solid Reflector				●		23.0	30	
LHA000017	LHA4-454-NU-4EPU	78531022112	4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, Narrow Distribution, Uplight Reflector	●	●	●	●	●	22.0	30	
LHA000019	LHA4-454-NU-4EPU-F554841	78531022129	4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, 54 Watt Lamps Installed, Narrow Distribution, Uplight Reflector	●	●		●	●	23.0	30	
LHA000024	LHA4-632-NST-3EHLU	078531022471	6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast, Narrow Distribution, Uplight Reflector		●	●	●		24.0	24	
93043289	LHA4-632-NST-3EHLU-FO841	078531023249	6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast 82 CRI T8 Lamps Installed, Narrow Distribution, Solid Reflector				●		24.0	24	
LHA000025	LHA4-632-NU-3EHLU	78531022136	6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast Narrow Distribution, Uplight Reflector	●	●	●	●	●	24.0	24	
LHA000027	LHA4-632-NU-3EHLU-FO841	078531022143	6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast 82 CRI T8 Lamps Installed, Narrow Distribution, Uplight Reflector	●	●		●		25.0	24	
LHA000028	LHA4-632-NU-3EHLU-FO850	078531022938	6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast 82 CRI T8 Lamps Installed, Narrow Distribution, Uplight Reflector		●				26.0	24	
LHA000040	LHA4-654-NST-24EPU	078531022488	6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast Narrow Distribution, Solid Reflector	●	●	●	●		26.0	24	
93043290	LHA4-654-NST-24EPU-F554841	078531023256	6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, 54W-T5 Lamps Installed Narrow Distribution, Solid Reflector				●		26.0	24	
LHA000041	LHA4-654-NU-24EPU	078531022150	6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, Narrow Distribution, Uplight Reflector	●	●	●	●	●	26.0	24	
LHA000043	LHA4-654-NU-24EPU-F554841	078531022167	6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, 54 Watt Lamps Installed, Narrow Distribution, Uplight Reflector	●	●	●	●	●	26.0	24	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

LHA	4	-		-		-		-	U	-	
SIZE 4 4'	NO. OF LAMPS 4 Four 6 Six	REFLECTOR N Narrow Distribution W Wide Distribution	UPLIGHT ST Solid Top U Uplight	VOLTAGE U 120V-277V	OPTIONS EL141 Emergency Battery Pack, T8, 1400 Lumens EL5H Emergency Battery Pack, T5, 1250 Lumens F3C5 3-Conductor Cord F4C5 4-Conductor Cord TC Steel Top/Side Cover ²	BALLAST LHA4-454 4EP (1) 4-Lamp Electronic T5HO, Programmed Start LHA4-654 24EP (1) 2-Lamp and (1) 4-Lamp Electronic T5HO, Programmed Start LHA4-432 4EHL (1) 4-Lamp Electronic T8, High Light Output, Instant Start (N/A 480V) LHA4-632 3EHL (2) 3-Lamp Electronic T8, High Light Output, Instant Start 3EPHL (2) 3-Lamp Electronic T8, High Light Output, Programmed Start	LAMPS INSTALLED T8 FO741 4100K 75CRI 32W T8 FO750 5000K 75CRI 32W T8 FO841 4100K 82CRI 32W T8 FO850 5000K 82CRI 32W T8 T5HO F554841 54 Watt, 85 CRI, 4100K F554850 54 Watt, 85 CRI, 5000K				
MODEL LHA Industrial Fluorescent High Bay	LAMP TYPE 32 4', T8 ¹ 54 4', T5HO: 54 or 51 Watt										

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.
² Not available with T5HO battery pack option.

QS 5 5-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 150

LHA	4					U	
MODEL	SIZE	NO. OF LAMPS	REFLECTOR	UPLIGHT	BALLAST	VOLTAGE	OPTIONS
LHA Industrial Fluorescent High Bay	4 4'	4 Four 6 Six	N Narrow Distribution W Wide Distribution	ST Solid Top U Uplight	LHA4-454 4EP (1) 4-Lamp Electronic T5HO, Programmed Start LHA4-654 24EP (1) 2-Lamp and (1) 4-Lamp Electronic T5HO, Programmed Start LHA4-432 4EHL (1) 4-Lamp Electronic T8, High Light Output, Instant Start (N/A 480V) LHA4-632 3EHL (2) 3-Lamp Electronic T8, High Light Output, Instant Start 3EPHL (2) 3-Lamp Electronic T8, High Light Output, Programmed Start	U 120V-277V	EL141 Emergency Battery Pack, T8, 1400 Lumens EL5H Emergency Battery Pack, T5, 1250 Lumens F3C5 3-Conductor Cord F4C5 4-Conductor Cord
	LAMP TYPE					LAMPS INSTALLED	
	32 4, T8 ¹ 54 4, T5HO: 54 or 51 Watt					T8 FO841 4100K 82CRI 32W T8 FO850 5000K 82CRI 32W T8 T5HO F554841 54 Watt, 85 CRI, 4100K F554850 54 Watt, 85 CRI, 5000K	

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.




LHR - Linear High Bays

QS 10 10-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 150

LHR	4					U	
MODEL	SIZE	NO. OF LAMPS	REFLECTOR	UPLIGHT	BALLAST	VOLTAGE	OPTIONS
LHR Ultra-Efficient Fluorescent High Bay	4 48" (Nominal)	4 Four 6 Six	M4R 95% Reflective Specular Aluminum (Narrow Beam) GW Gloss White Powder Coat (Wide Beam)	ST Solid Top (No uplight) U Uplight, 12%	LHR4-454 4EP (1) 4-Lamp Electronic T5HO, Programmed Start LHR4-654 24EP (1) 2-Lamp and (1) 4-Lamp Electronic T5, Programmed Start LHR4-632 3EHL (2) 3-Lamp Electronic T8, High Light Output, Instant Start	U 120V-277V	F5841 41K 85CRI T5HO Lamps Installed F5850 50K 82CRI T5HO Lamps Installed FO741 41K 75CRI T8 Lamp Installed 32W FO750 50K 75CRI T8 Lamp Installed 32W FO841 41K 82CRI T8 Lamp Installed 32W FO850 50K 82CRI T8 Lamp Installed 32W FO841 41K 82CRI T8 Lamps Installed 32W EL141 Emergency Batter Pack, T8, 1400 lumens EL5H Emergency Battery Pack, T5, 1250 lumens F3C5 3-Conductor Feed Cord Wired to Fixture F4C5 4-Conductor Feed Cord Wired to Fixture
ACCESSORIES (ORDER SEPARATELY)		LAMP TYPE					
LHHB-LHR4-4LT Universal Hanger Bracket Kit for 4-Lamp Fixture LHHB-LHR4-6LT Universal Hanger Bracket Kit for 6-Lamp Fixture LHRWG4K Wire Guard Kit for 4-Lamp (not to be used with door frame) LHRWG6K Wire Guard Kit for 6-Lamp (not to be used with door frame)		32 4, T8 Lamp Only ¹ 54 4, T5HO: 54 or 51 Watt					

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.




LHV - Linear High Bays

35 SCHEDULED
STOCK
SHIPMENTS

Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
93014378	LHV4-432-M4R-ST-4EHLU	078531019372	4-4' T8, 4', 120-277V 4-L T8 HL Elec Ballast		●				22.0	30	
93038457	LHV4-432-M4RU-4EHLU-FO850	078531022914	4-4'T8, 4', 120-277V 4-L T8 HL Elec Ballast 80 CRI T8 Lamps Installed		●				24.0	30	
LHV000004	LHV4-454-GWU-4EPU-F5841	078531011086	4-4'T5, 4', 120-277V 4-L T5 Elec Ballast, White Reflector T5 Lamps Installed		●			●	23.0	30	
93014379	LHV4-454-M4RST-4EPU	078531011703	4-4'T5, 4', 120-277V 4-L T5 Elec Ballast, Solid Top Reflectors			●			22.0	30	
93020454	LHV4-454-M4RST-4EPU-F5841	078531016302	4-4'T5, 4', 120-277V 4-L T5 Elec Ballast, T5 Lamps Installed Solid Top Reflectors			●			23.0	30	
LHV000003	LHV4-454-M4RU-4EPU	078531011024	4-4'T5, 4', 120-277V 4-L T5 Elec Ballast, Uplight Reflector	●	●	●	●	●	22.0	30	
LHV000002	LHV4-454-M4RU-4EPU-F5841	078531011079	4-4'T5, 4', 120-277V 4-L T5 Elec Ballast, T5 Lamps Installed		●	●	●		23.0	30	
LHV000010	LHV4-632-GWU-3EHLU-FO741	078531011123	6-4'T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast T8 Lamps Installed, White Reflector		●				23.0	24	
93020455	LHV4-632-M4RST-3EHLU-FO741	078531016319	6-4'T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast 70CRI T8 Lamps Installed, Solid Top Reflector		●				23.0	24	
LHV000009	LHV4-632-M4RU-3EHLU	078531011048	6-4'T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast,	●	●	●	●		24.0	24	
LHV000008	LHV4-632-M4RU-3EHLU-FO741	078531011116	6-4'T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast 70CRI T8 Lamps Installed		●		●		25.0	24	
LHV000029	LHV4-632-M4RU-3EHLU-FO850	078531016845	6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast 80 CRI T8 Lamps Installed		●				25.0	24	
LHV000031	LHV4-632-M4RU-3EPHLU-FO850	078531016869	6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Programmed Start Ballast T8 Lamps Installed		●				25.0	24	
LHV000007	LHV4-654-GWU-24EPU-F5841	078531011109	6-4'T5, 4', 120-277V 2 & 4-L T5 Elec Ballast T5 Lamps Installed, White Reflector		●		●	●	25.0	24	
93020453	LHV4-654-M4RST-24EPU-F5841	078531016296	6-4'T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, T5 Lamps Installed Solid Top Reflector		●		●	●	26.0	24	
LHV000006	LHV4-654-M4RU-24EPU	078531011031	6-4'T5, 4', 120-277V 2 & 4-L T5 Elec Ballast	●	●	●	●	●	26.0	24	
LHV000005	LHV4-654-M4RU-24EPU-F5841	078531011093	6-4'T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, T5 Lamps Installed		●	●	●	●	26.0	24	
LHVOS1360	LHVOS1360	078531023584	Occupancy/Daylight Sensor, with a 360° lens, 120/277/347V, One Relay	●	●	●	●	●	25.0	N/A	
LHVQM10	LHVQM10	078531012526	Aircraft Cable Hangers, 10' (pair)	●	●	●	●	●	0.6	N/A	
LHVQM20	LHVQM20	078531012991	Aircraft Cable Hangers, 20' (pair)		●		●		1.2	N/A	
LHVQM5	LHVQM5	078531012670	Aircraft Cable Hangers, 5' (pair)	●	●	●	●	●	0.5	N/A	
LHVSP	LHVSP	078531011338	Side Panels (pair)		●				5.0	N/A	
LHVSPM5	LHVSPM5	078531012656	Single Point Mounting Kit, Includes Aircraft Cable, 5' (pair)		●	●			5.0	N/A	
LHVTH	LHVTH	078531012649	Tong Hanger (pair)	●	●	●	●	●	0.6	N/A	
LHVWG4-4	LHVWG4-4	078531012625	Cage Wireguard, 4-L, White	●	●	●	●	●	5.0	N/A	
LHVWG4-6	LHVWG4-6	078531012618	Cage Wireguard, 6-L, White	●	●	●	●	●	5.0	N/A	
C6P15-120	C6P15-120	078531016111	Cord and Plug Kit (white), 6 ft Straight Blade Nema 5-15P, 15 amp, 120V		●				0.8	N/A	
C6TL15-120	C6TL15-120	078531016098	Cord and Plug Kit (white), 6 ft Twist Lock Nema L5-15P, 15 amp, 120V		●				0.8	N/A	
C6TL15-277	C6TL15-277	078531016104	Cord and Plug Kit (white), 6 ft Twist Lock Nema L7-15P, 15 amp, 277V		●				0.8	N/A	




LHV - Linear High Bays



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
VersaBay Shielding Accessories											
LHVS4-CA	LHVS4-CA		LHV 4 lamp Shielding kit, includes frame and clear acrylic lens		●					N/A	
LHV4SPJ	LHV4SPJ	078531016142	Side Panels and End Jaw (pair) for 4 lamp		●				2.5	N/A	
LHV4CA	LHV4CA	078531016203	Clear Acrylic Lens for 4 lamp		●	●			2.5	N/A	
LHVS4-WG	LHVS4-WG		LHV 4 lamp Shielding kit, includes frame and flat wire guard		●					N/A	
LHV4SPJ	LHV4SPJ	078531016142	Side Panels and End Jaw (pair) for 4 lamp		●				2.5	N/A	
LHV4FWG	LHV4FWG	078531016173	Flat Wire Guard for 4 lamp		●				2.5	N/A	
LHVS4-CAWG	LHVS4-CAWG		4 lamp Shielding kit, includes frame, clear acrylic lens and flat wire guard		●						
LHV4SPJ	LHV4SPJ	078531016142	Side Panels and End Jaw (pair) for 4 lamp		●				2.5		
LHV4CA	LHV4CA	078531016203	Clear Acrylic Lens for 4 lamp		●	●			2.5	N/A	
LHV4FWG	LHV4FWG	078531016173	Flat Wire Guard for 4 lamp		●				2.5	N/A	
LHVS6-CA	LHVS6-CA		LHV 6 lamp Shielding kit, includes frame and clear acrylic lens		●						
LHV6SPJ	LHV6SPJ	078531016159	Side Panels and End Jaw (pair) for 6 lamp		●	●	●	●	2.5	N/A	
LHV6CA	LHV6CA	078531016210	Clear Acrylic Lens for 6 lamp		●	●	●		2.5	N/A	
LHVS6-WG	LHVS6-WG		LHV 6 lamp Shielding kit, includes frame and flat wire guard		●						
LHV6SPJ	LHV6SPJ	078531016159	Side Panels and End Jaw (pair) for 6 lamp		●	●	●	●	2.5	N/A	
LHV6FWG	LHV6FWG	078531016180	Flat Wire Guard for 6 lamp		●		●		2.5	N/A	
LHVS6-CAWG	LHVS6-CAWG		6 lamp Shielding kit, includes frame, clear acrylic lens and flat wire guard		●					N/A	
LHV6SPJ	LHV6SPJ	078531016159	Side Panels and End Jaw (pair) for 6 lamp		●	●	●	●	2.5		
LHV6CA	LHV6CA	078531016210	Clear Acrylic Lens for 6 lamp		●	●	●		2.5	N/A	
LHV6FWG	LHV6FWG	078531016180	Flat Wire Guard for 6 lamp		●		●		2.5	N/A	



LHV - Linear High Bays

QS₁₀ 10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

MODEL	LAMP TYPE	BALLAST	LAMPS INSTALLED
LHV	4' 4"	REFLECTOR M4R 95% Reflective Specular Aluminum (Narrow Beam) GW Gloss White (Wide Beam)	UPLIGHT ST Solid Top U Uplight
SIZE	NO. OF LAMPS	VOLTAGE	OPTIONS
4' 4"	4 Four 6 Six	U 120V-277V 480 480V ²	EL141 Emergency Battery Pack, T8, 1400 Lumens EL5H Emergency Battery Pack, T5, 1250 Lumens F3C5 3-Conductor Cord F4C5 4-Conductor Cord
LHV VersaBay® Fluorescent High Bay	32 4', T8 ¹ 54 4', T5HO: 54 or 51 Watt	<u>LHV4-454</u> 4EP (1) 4-Lamp Electronic T5HO, Programmed Start <u>LHV4-654</u> 24EP (1) 2-Lamp and (1) 4-Lamp Electronic T5HO, Programmed Start <u>LHV4-432</u> 4EHL (1) 4-Lamp Electronic T8, High Light Output, Instant Start (N/A 480V) <u>LHV4-632</u> 3EHL (2) 3-Lamp Electronic T8, High Light Output, Instant Start 3EPHL (2) 3-Lamp Electronic T8, High Light Output, Programmed Start	T8 FO741 4100K 75CRI 32W T8 FO750 5000K 75CRI 32W T8 FO841 4100K 82CRI 32W T8 FO850 5000K 82CRI 32W T8 T5HO F5841 4100K 85CRI F5850 5000K 85CRI

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.
² 480V option on T5HO units only.

QS₅ 5-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

MODEL	LAMP TYPE	BALLAST	LAMPS INSTALLED
LHV	4' 4"	REFLECTOR M4R 95% Reflective Specular Aluminum (Narrow Beam) GW Gloss White (Wide Beam)	UPLIGHT ST Solid Top U Uplight
SIZE	NO. OF LAMPS	VOLTAGE	OPTIONS
4' 4"	4 Four 6 Six	U 120V-277V 480 480V ²	EL141 Emergency Battery Pack, T8, 1400 Lumens EL5H Emergency Battery Pack, T5, 1250 Lumens F3C5 3-Conductor Cord F4C5 4-Conductor Cord
LHV VersaBay® Fluorescent High Bay	32 4', T8 ¹ 54 4', T5HO: 54 or 51 Watt	<u>LHV4-454</u> 4EP (1) 4-Lamp Electronic T5HO, Programmed Start <u>LHV4-654</u> 24EP (1) 2-Lamp and (1) 4-Lamp Electronic T5HO, Programmed Start <u>LHV4-432</u> 4EHL (1) 4-Lamp Electronic T8, High Light Output, Instant Start (N/A 480V) <u>LHV4-632</u> 3EHL (2) 3-Lamp Electronic T8, High Light Output, Instant Start 3EPHL (2) 3-Lamp Electronic T8, High Light Output, Programmed Start	T8 FO841 4100K 82CRI 32W T8 FO850 5000K 82CRI 32W T8 T5HO F5841 4100K 85CRI F5850 5000K 85CRI

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.
² 480V option on T5HO units only.



KL - Specification Grade Industrials



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
72241819F910000	KL4-232-U-EU	078531006471	2-4' T8, 4', 120-277V T8 Elec Ballast, Apertured Reflector	•	•	•	•	•	15.0	21	
820268450000000	KLWG4	078531007478	4' Wire Guard for KL series	•	•	•	•	•	3.2	N/A	
984084190000000	KHC	078531000875	Two 24" chain assemblies for K and KL	•	•	•	•	•	0.3	N/A	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 50

KL	-		-		-		-	U	-		
MODEL KL Premium Industrial	NO. OF LAMPS 2 Two 3 Three	REFLECTOR TYPE U Apertured Uplight Reflector ST Solid Top	VOLTAGE U 120V-277V	OPTIONS EL Emergency Battery Pack EL5 Emergency Battery Pack, T5 EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8							
SIZE 4 4' 8 8'	LAMP TYPE 32 4', T8 ¹ 54 4', T5HO: 54 or 51 Watt 96T8 8', T8: 59 Watt (2-Lamp only) 96T8HO 8', T8: 86 Watt (2-Lamp only)	BALLAST E Electronic, Instant Start 3E 3-Lamp Electronic T8 (32W), Instant Start 4E 4-Lamp Electronic T8 (32W), Instant Start EP Electronic, Programmed Start, T5HO or T8 3EP 3-Lamp Electronic T5HO or T8, Programmed Start 4EP 4-Lamp Electronic T5HO or T8, Programmed Start ELW 2-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 3ELW 3-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 4ELW 4-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start EPLW Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 3EPLW 3-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 4EPLW 4-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start									
ACCESSORIES (ORDER SEPARATELY) KLEC Full Depth Endcap (pair) KZT Zip-Tee Hanger KLRU4 4' 5% Uplight Reflector Only KTH Slide Clamp Tong Hanger											

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.

Instant Start ballasts available for 32 and 96T8. Programmed Start ballasts available for all except 96T8.



CS - Striplights



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
04122009F910000	CS2-117-EU	078531008079	1-2' T8, 2', 120-277V T8 Elec Ballast			•			4.0	176	
04222009F910000	CS2-217-EU	078531004996	2-2' T8, 2', 120-277V T8 Elec Ballast		•	•	•	•	4.0	176	
041220007910000	CS2-220-L120	078531023164	2-2' T12, 2', 120V T12 LPF Ballast			•			4.0	176	
04231009F910000	CS3-225-EU	078531005009	2-3' T8, 3', 120-277V T8 Elec Ballast	•	•	•	•	•	7.0	88	
04141009F910000	CS4-132-EU	078531006280	1-4' T8, 4', 120-277V T8 Elec Ballast	•	•	•	•	•	9.0	77	
04241009F910000	CS4-232-EU	078531005016	2-4' T8, 4', 120-277V T8 Elec Ballast	•	•	•	•	•	9.0	77	
93022153	CS4-232-EPU	078531016609	2-4' T8, 4', 120-277V T8 Elec Prog Start Ballast	•	•			•	9.0	77	
93038454	CS4-254-EPU	078531022969	2-4' T5, 4', 120-277V T5 Elec Ballast		•	•		•	9.0	77	
0424100BL910000	CS4-232-ELWU	078531012458	2-4' T8, 4', 120-277V T8 Elec Low Wattage Ballast			•			9.0	77	
0344100BN910000	CS4-232-4ELWU	078531011949	2-4' T8, 4', 120-277V 4-LT8 Elec Low Wattage Ballast			•			8.0	77	
03241009F910000	CS8-132-EU	078531009151	2-8' T8, 8', 120-277V T8 Elec Ballast		•	•			17.0	77	
03441009H910000	CS8-232-4EU	078531005023	4-8' T8, 8', 120-277V 4-L T8 Elec Ballast	•	•	•	•	•	17.0	77	
0344100BN910000	CS8-232-4ELWU	078531011949	4-8' T8, 8', 120-277V 4-L T8 Elec Low Wattage Ballast			•			17.0	77	
04275009F910000	CS8-296T8-EU	078531005795	2-8' T8, 8', 120-277V T8 Elec Ballast	•	•	•	•	•	17.0	77	
0427500AS910000	CS8-296-EU120	078531008543	2-8' T12, 8', 120V Magnetic DOE Compliant Ballast					•	17.0	77	
93038455	CS8-254-4EPU	078531022976	4-8' T5, 8', 120-277V 4-L T5 Elec Ballast		•			•	17.0	77	
984084158000000	CSHC	078531000868	Two 14" chain assemblies for CS and CSR	•	•	•	•	•	0.2	N/A	
745013602000000	CSR4	078531001575	4' symmetric reflector, white, solid top	•	•	•	•	•	2.0	N/A	
745013603000000	CSRU4	078531001582	4' symmetric reflector, white, uplight		•				2.0	N/A	
982092925000000	CSWG4	078531000882	4' Wire Guard for CS series	•	•	•	•	•	1.0	N/A	
985084348700000	CSZT	078531740146	Zip T-Hanger - 1/2" spacer		•	•	•	•	0.2	N/A	

QS 10 **10-Day Quick Ship Ordering Guide**
Order Limit Per Fixture Selection: 100

CS						U	EL
MODEL	SIZE	NO. OF LAMPS IN CROSS SECTION	LAMP TYPE	BALLAST	VOLTAGE	OPTIONS	
CS Straight-Sided Utility Channel	2 2' 4 4' 8 8'	1 One 2 Two	17 2', T8: 17 Watt 32 4', T8 ¹	E Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP Electronic T8, Programmed Start 4EP 4-Lamp Electronic T8, Programmed Start ELW 2-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start 4ELW 4-Lamp Electronic T8, 0.77 Ballast Factor, Low Wattage, Instant Start EPLW Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start 4EPLW 4-Lamp Electronic T8 0.77 Ballast Factor, Low Watt, Programmed Start	U 120V-277V	EL Emergency Battery Pack EL141 Emergency Battery Pack, 1400 Lumens 1-Lamp T8	
ACCESSORIES (ORDER SEPARATELY)							
CSRA4 4' Asymmetric Reflector							
CSRU4 4' Symmetric Reflector 5% Uplight							

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



CH-1-L Striplights

3S SCHEDULED STOCK SHIPMENTS **Regional Distribution Center Stock List**

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
841120007000000	CH1.5-115-L120	078531840228	1-1.5' T12, 1.5', 120V T12 LPF Ballast		•	•			3.0	156	
84122009F910000	CH2-117-EU	078531005047	1-2' T8, 2', 120-277V T8 Elec Ballast		•	•	•	•	3.0	156	
841220007000000	CH2-120-L120	078531840235	1-2' T12, 2', 120V T12 LPF Ballast		•	•	•		3.0	156	
84131009F910000	CH3-125-EU	078531005054	1-3' T8, 3', 120-277V T8 Elec Ballast		•	•	•		7.0	156	
841310003910000	CH3-130-L120	078531840242	1-3' T12, 3', 120V T12 LPF Ballast			•			7.0	156	
84141009F910000	CH4-132-EU	078531005061	1-4' T8, 4', 120-277V T8 Elec Ballast	•	•	•	•	•	7.0	156	
841410003910000	CH4-140-L120	078531840259	1-4' T12, 4', 120V T12 LPF Ballast		•	•			5.0	156	
83241009F910000	CH8-132-EU	078531005078	2-4' T8, 8', 120-277V T8 Elec Ballast			•			17.0	96	
845034020000000	CHRA4	078531011970	4' Asymmetric Reflector (1-lmp only)			•			1.9	N/A	
980929240000000	CHWG4	078531002954	Wire Guard, 4' for CH Strip	•	•	•		•	10.0	N/A	



K - Heavy Duty Striplights



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
80241009F910000	K4-232-EU	078531007034	2-4' T8, 4', 120-277V T8 Elec Ballast				●	●	16.0	72	
93025871	K8-296HO-EPU	078531016913	2-8' T12HO, 8', 120-277V Ballast	●	●	●	●	●	19.0	36	
93032673	K8-296T8HO-EPU	078531017699	2-8' T8HO, 8', 120-277V Elec.Prog Start Ballast		●				19.0	36	
984084190000000	KHC	078531000875	Two 24" chain assemblies for K and KL	●	●	●	●	●	0.3	N/A	




SS - Staggered Strips



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
FS000032	SS3-225-EU	078531043513	2-3' T8, 3', 120-277V T8 Elec Ballast		●				5.0	64	
FS000039	SS4-132-EU	078531044602	1-4' T8, 4', 120-277V T8 Elec Ballast				●		9.0	72	
FS000040	SS4-232-EU	078531044619	2-4' T8, 4', 120-277V T8 Elec Ballast	●	●		●	●	9.0	72	



XFSW - Enclosed/Gasketed High Bay



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
XFSW00021	XFSW4-454-CA-GW-4EPU	078531010652	4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, White Reflector, Clear Acrylic Lens					●	25.0	21	
XFSW00019	XFSW4-454-CA-M4R-4EPU	078531017521	4-4' T5, 4', 120-277V 4-L T5 Elec Ballast, 95% Reflector, Clear Acrylic Lens	●	●				25.0	N/A	
XFSW00022	XFSW4-654-CA-GW-24EPU	078531-010669	6-4' T5, 4', 120-277V 2 & 4-L T5 Elec Ballast, White Reflector, Clear Acrylic Lens		●			●	25.0	N/A	
XFSW00023	XFSW4-632-CA-GW-3EHLU	078531-010676	6-4' T8, 4', 120-277V (2) 3-L T8 HL Elec Ballast, White Reflector, Clear Acrylic Lens		●			●	25.0		
XFSWSB	XFSWSB	078531016982	Surface Mount Bracket, Pair		●			●	2.0		



LUN - Enclosed/Gasketed Industrials



Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
FB241019F910000	LUN4-232-EU	078531004972	2-4' T8, 4', 120-277V T8 Elec Ballast, Fiberglass	•	•	•	•	•	14.0	30	
FC441019H910000	LUN8-232-4EU	078531004989	4-4' T8, 8', 120-277V 4-L T8 Elec Ballast, Fiberglass	•	•	•	•	•	29.0	30	
93025872	LUN8-296HO-EPU	078531016920	2-8'T12HO, 8', 120-277V 2-L T12 Elec Prog Start Ballast, Fiberglass		•				29.0	30	
93032676	LUN8-296T8HO-EPU	078531017729	2-8'T8HO, 8', 120-277V 2-L T8 Elec Prog Start Ballast, Fiberglass			•			29.0	30	



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 50

LUN		2			U	
MODEL	SIZE	NO. OF LAMPS IN CROSS SECTION	LAMP TYPE	BALLAST	VOLTAGE	OPTIONS
LUN Enclosed and Gasketed Fiberglass Industrial	4 4' 8 8'	2 Two	32 4', T8 ¹ 48T8HO 4', T8HO: 44 Watt ¹ 96T8 8', T8: 59 Watt 96HO 8', T12HO: 110 or 95 Watt ¹ 96T8HO 8', T8HO: 86 Watt ¹	E Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP Electronic, Programmed Start 4EP 4-Lamp Electronic, Programmed Start	U 120V-277V	DR 50% DR Acrylic Lens SSL Stainless Steel Latches
<p>ACCESSORIES (ORDER SEPARATELY)</p> <p>HUBK Stem Hanging Kit LUNHK Hanging Kit</p>						

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.



XEM - Low Profile Enclosed/Gasketed Industrials

FALL
2013

3 SCHEDULED
STOCK
SHIPMENTS

Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
93049168	XEM4-232-RA-EU	078531023720	Vapor Tight 2-4'T8, 4', 120-277V T8 Elec Ballast, Fiberglass Housing	•	•	•	•	•	14.0		
93049169	XEM8-232-RA-4EU	078531023737	Vapor Tight 4-4'T8, 8', 120-277V 4-L T8 Elec Ballast, Fiberglass Housing	•	•	•	•	•	29.0		
93049170	XEM8-296T8HO-RA-EPU	078531023744	Vapor Tight 2-8'T8HO, 8', 120-277V 4-L T8 Elec Program Start Ballast, Fiberglass Housing				•	•	29.0		

FALL
2013

QS
10

10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 50

XEM		2				U	
MODEL	SIZE	NO. OF LAMPS IN CROSS SECTION	LAMP TYPE	BALLAST	VOLTAGE	OPTIONS	
XEM Low Profile Enclosed and Gasketed Fiberglass Industrial	4 4' 8 8'	2 Two	32 4'T8 ¹ 48T8HO 4'T8HO: 44 Watt 96T8 8'T8: 59 Watt 96T8HO 8'T8HO: 86 Watt	E Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP Electronic, Programmed Start 4EP 4-Lamp Electronic, Programmed Start	U 120V-277V	TP Tamper Proof Screws SSL Stainless Steel Latches	
			LENS TYPE	BALLAST FACTOR			
			RA Ribbed Acrylic (Standard)	Blank 0.88BF (Standard) LW Low Watt			

¹ Capable of operating 32, 30, 28 or 25 Watt T8 only.

Accessories

3 SCHEDULED
STOCK
SHIPMENTS

Regional Distribution Center Stock List

Part Number	Catalog Number	UPC Code	Description	CA 03	IL 06	PA 10	SC 07	TX 04	Wt. each	# on Pallet	Price
FK14	FK14	078531000745	1 x 4 Flange Kit	•	•	•	•	•	5.0	N/A	
FK22	FK22	078531000752	2 x 2 Flange Kit	•	•	•	•	•	5.0	N/A	
FK24	FK24	078531038991	2 x 4 Flange Kit	•	•	•	•	•	5.0	N/A	
GLH5	GLH5	078531012700	5' Adjustable Cable Kit	•	•	•	•	•	0.3	N/A	
GLH10	GLH10	078531013127	10' Adjustable Cable Kit	•	•	•	•	•	0.4	N/A	
980000011000000	S18	078531000790	18" Stem and Canopy	•	•	•	•	•	8.0	N/A	
980000010000000	SS18	078531003456	18" Stem only	•	•	•	•	•	5.0	N/A	
TBC10K	TBC	078531017606	Tall Ballast Cover, For Field Installed Battery Packs			•			8.0	N/A	