



**PRODUCT
SUPPLEMENT**
JUNE 2017





Table of Contents

02 PICTORIAL INDEX

08 DESIGN SERIES FIXTURES

- 10 *FIXTURE COLLECTIONS*
- 24 *PENDANTS*
- 26 *SCONCES*
- 36 *BATH COLLECTIONS*
- 40 *OUTDOOR*



58 FIXTURE COLLECTIONS



72 PENDANTS



74 CLOSE TO CEILING



76 SCONCES



77 BATH COLLECTIONS



88 OUTDOOR



99 UTILITY

- 99 Recessed
- 101 Track
- 104 Lamps
- 104 INDEX

FIXTURE COLLECTIONS

BARNES MILL
Antique Bronze p.63




BRIARWOOD
Antique Bronze p.60



BRIARWOOD
Graphite p.59



CAPTIVATE ✦
Graphite p.16



CLASSIC
Antique Bronze p.71



CLASSIC
Brushed Nickel p.71



CLASSIC
Polished Chrome p.71



CLASSIC
Antique Bronze p.71



CLASSIC
Brushed Nickel p.71



CLASSIC
Polished Chrome p.71



GLIMMER ✦
Antique Bronze p.12



GLIMMER ✦
Silver Ridge p.12



LOOKING GLASS ✦
Antique Bronze p.18



MARCHÉ ✦
Polished Nickel p.10



METRIC ✦
Brushed Nickel p.20



METRIC ✦
Polished Chrome p.20



REMIX ✦
Graphite p.23




REPLAY
Brushed Nickel p.65



SWING
Antique Bronze p.61



TOPSAIL
Antique Bronze p.67



TOPSAIL
Polished Chrome p.67



TURNBURY ✦
Brushed Nickel p.22



WESTFALL ✦
Antique Bronze p.14



WESTFALL ✦
Graphite p.14



PENDANTS

BARNES MILL ✦
Antique Bronze p.63



BRIARWOOD
Antique Bronze p.60



BRIARWOOD
Graphite p.59



CALHOUN
Antique Bronze p.72



CALHOUN
Brushed Nickel p.72



CAPTIVATE ✦
Graphite p.17



ESTEEM
Antique Bronze p.72



GALLEY ✦
Antique Bronze p.24



GALLEY ✦
Polished Nickel p.24



LOOKING GLASS ✦
Antique Bronze p.19



MARCHÉ ✦
Polished Nickel p.11



REPLAY
Brushed Nickel p.65



REPLAY
Brushed Nickel p.65



TOPSAIL
Antique Bronze p.68



TOPSAIL
Polished Chrome p.68



TOPSAIL
Antique Bronze p.67



TOPSAIL
Polished Chrome p.67



TRE
Graphite p.73



TRE
White p.73



WESTFALL ✦
Antique Bronze p.15



WESTFALL ✦
Graphite p.15



SCONCES / WALL BRACKETS

AVANA ✦
Antique Bronze p.30



AVANA ✦
Polished Nickel p.30



AVANA ✦
Brushed Nickel p.30



BARNES MILL
Antique Bronze p.63



BONITA ✦
Antique Bronze p.32



BONITA ✦
Brushed Nickel p.32



BONITA ✦
Polished Chrome p.32



BRAMLETT
Brushed Nickel p.83



BRAMLETT
Polished Chrome p.83



BRIARWOOD
Antique Bronze p.60



BRIARWOOD
Graphite p.59



CALHOUN
Antique Bronze p.79



CALHOUN
Brushed Nickel p.78



CAPTIVATE ✦
Graphite p.17



FORMES ✦
Antique Bronze p.27



GLIMMER ✦
Antique Bronze p.13



GLIMMER ✦
Silver Ridge p.13



HANSFORD
Antique Bronze p.80



HANSFORD
Polished Nickel p.81



HOBBS ✦
Antique Bronze p.35



HOBBS ✦
Brushed Nickel p.35



HOBBS ✦
Polished Chrome p.35



INDUSTRIAL
Antique Bronze p.76



INDUSTRIAL
Galvanized Finish p.76



LOOKING GLASS ✦
Antique Bronze p.19



MARCHÉ ✦
Polished Nickel

p.11



MAST
Antique Bronze

p.76



MAST
Brushed Nickel

p.76



METRO ✦
Antique Bronze

p.29



METRO ✦
Brushed Nickel

p.29



METRO ✦
Polished Chrome

p.29



TILLEY
Antique Bronze

p.82



TILLEY
Brushed Nickel

p.82



TOPSAIL
Antique Bronze

p.85



TOPSAIL
Polished Chrome

p.84



VOLO ✦
Antique Bronze

p.37



VOLO ✦
Brushed Nickel

p.37



ZURA™ ✦
Black

p.39



ZURA™ ✦
Brushed Nickel

p.39



ZURA™ ✦
Polished Chrome

p.39



BATH COLLECTIONS

BARNES MILL
Antique Bronze p.77



BRAMLETT
Brushed Nickel p.83



BRAMLETT
Polished Chrome p.83



CALHOUN
Antique Bronze p.79



CALHOUN
Brushed Nickel p.78



HANSFORD
Antique Bronze p.80



HANSFORD
Polished Nickel p.81



REPLAY
Black p.87



STATUS
Polished Chrome p.86



TILLEY
Antique Bronze p.82



TILLEY
Brushed Nickel p.82



TOPSAIL
Antique Bronze p.85



TOPSAIL
Polished Chrome p.84



VOLO ✦
Antique Bronze p.37



VOLO ✦
Brushed Nickel p.37



ZURA ✦
Black p.39



ZURA ✦
Brushed Nickel p.39



ZURA ✦
Polished Chrome p.39



OUTDOOR

BEAUFORT
Black p.92



CALLAHAN
Antique Bronze p.93



CALLAHAN
Antique Pewter p.93



CERAMIC SCONCE
White p.98



CHANDLER
Black p.94



DIVERGE
Architectural Bronze p.95



ENDICOTT
Black p.90



ENDORSE
Black p.91



GEOMETRIC
Architectural Bronze p.97



HADDON
Antique Bronze p.91



HADDON
Black p.91



MCBEE
Black p.95



PATEWOOD ✦
Black p.40



SQUIRE
Antique Bronze p.88



SQUIRE
Black p.89



UNION SQUARE ✦
Stainless Steel p.42



WESTPORT
Antique Bronze p.98



WESTPORT
Black p.98



Z-1030
Antique Bronze p.96



Z-1030
White p.96



Z-1030
Black p.96



Z-1030
Metallic Gray p.96



Z-1040
Black p.97







DESIGN ✦ SERIES

*STATEMENT-MAKING
PIECES FROM
OUR DESIGN SERIES
COLLECTION.*

Our Design Series fixtures feature artistic influence, fashion forward elements and details to contribute to affordable luxury for the home.

The fixtures found throughout the Design Series become the statement, the art piece and the focal point – and contribute to an overall luxurious experience in the home. They don't blend in. **They stand out.**

MARCHÉ

Marché is an eclectic arrangement of gleaming metal turnings, which recreates the vintage styles found in Parisian neighborhood markets. Polished Nickel elements are combined with a luxurious sheer silver organza shade and clear K9 glass elements. Coordinate with Nissé or Caress collections to create a truly distinctive addition to your home.



P400049-104

*FINISH*

- Polished Nickel - 104

SEMI-FLUSH CONVERTIBLE

P350029-104 Polished Nickel
Hanging and ceiling mount hardware included.
18" dia., 14" ht.
Overall ht. w/chain 55", wire 10'.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400049-104 Polished Nickel
28" dia., 25-1/8" ht.
Overall ht. w/chain 100", wire 15'.
Five candelabra base lamps, each 60w max.

FOUR-LIGHT PENDANT

P500043-104 Polished Nickel
22" dia., 20" ht.
Overall ht. w/chain 95", wire 15'.
Four candelabra base lamps, each 60w max.

WALL SCONCE

P710013-104 Polished Nickel
6-7/8" W., 12-1/4" ht.
Extends 10-1/2". H/CTR 6-5/8".
One candelabra base lamp, 60w max.



GLIMMER

Elements that sparkle create an instant statement within the home. Glimmer fits the definition of livable luxury. Prismatic glass pendants are supported by an architecturally styled frame in Silver Ridge or Antique Bronze finishes.



P5346-20



P7198-134

FINISHES

- Antique Bronze - 20
- Silver Ridge - 134

*SIX-LIGHT PENDANT***P5346-134** Silver Ridge**P5346-20** Antique Bronze

28" dia., 29-1/4" ht.

Overall ht. w/chain 104-1/2", wire 10'.

Six candelabra base lamps,
each 60w max.*WALL SCONCE***P7198-134** Silver Ridge**P7198-20** Antique Bronze

8" W., 10" ht.

Extends 4-3/4". H/CTR 3-1/2".

Two candelabra base lamps,
each 60w max.

P7198-20

WESTFALL

Westfall is a combination of arching elements that create a dramatic soaring frame. A dual-tone finish highlights the distinctive form. Metal fittings add a touch of elegance and dimension to further enhance the classic architectural form.



P500040-143



FINISHES

- Antique Bronze - 020
- Graphite - 143

FOUR-LIGHT FOYER PENDANT

P500038-020 Antique Bronze
P500038-143 Graphite
 10-1/8" sq., 19-5/8" ht. Overall ht. w/ chain 94-1/2", wire 15'.
 Four candelabra base lamps, each 60w max.

FOUR-LIGHT FOYER PENDANT

P500039-020 Antique Bronze
P500039-143 Graphite
 13-7/8" sq., 25-1/8" ht. Overall ht. w/ chain 100", wire 15'.
 Four candelabra base lamps, each 60w max.



EIGHT-LIGHT FOYER PENDANT

P500040-020 Antique Bronze
P500040-143 Graphite
 two-tier.
 19-3/4" sq., 33-1/8" ht. Overall ht. w/chain 156", wire 15'.
 Eight candelabra base lamps, each 60w max.

Note: Antique Bronze fixtures include Vintage Brass and Antique Bronze candle covers for additional customization.

Shown with P7826-01 vintage lamps



CAPTIVATE

The Captivate collection features a striking circular frame that surrounds arching candelabra. Glazed with clear seeded glass, the artful form is a complex layering of light and shadow to provide a dramatic focal point to any room. The Graphite finish provides a rich, smoky color palette to complement your décor.



P500049-143



P500049-143

FINISH

● Graphite - 143

FOUR-LIGHT PENDANT

P500048-143 Graphite
 18" Sq. dia., 17-1/2" ht.
 Overall ht. w/stem 83-1/2", wire 10'.
 Four candelabra base lamps,
 each 60w max.

EIGHT-LIGHT PENDANT

P500049-143 Graphite
 24" Sq. dia., 23-1/8" ht.
 Overall ht. w/stem 89", wire 10'.
 Eight candelabra base lamps,
 each 60w max.

WALL SCONCE

P710021-143 Graphite
 10" W., 10" ht.
 Extends 5-1/2". H/CTR 5".
 One candelabra base lamp,
 60w max.

*Shown with P7826-01
 vintage lamps*



P500048-143



P710021-143

LOOKING GLASS

Whether for a mountain cabin or an urban retreat, the rustic charm of the Looking Glass collection is an artful display of romantic vintage lighting. Inspired by a timber frame farmhouse, Looking Glass features iron elements that support clear seeded glass reflectors. Hints of brass accentuate the mechanical details to enhance a vintage feel.



P400002-020

P400002-020

**FINISH**

- Antique Bronze - 020

FOUR-LIGHT CHANDELIER

P400002-020 Antique Bronze
25-3/8" W., 18-1/4" ht.
Overall ht. w/stem 84", wire 15'.
Four medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400003-020 Antique Bronze
19" W., 36-3/4" L., 18-1/4" ht.
Overall ht. w/stem 84", wire 15'.
Six medium base lamps,
each 60w max.

MINI-PENDANT

P500042-020 Antique Bronze
9" dia., 14 3/4" ht.
Overall ht. w/stem 81", wire 10'.
One medium base lamp,
100w max.

WALL SCONCE

P710002-020 Antique Bronze
9" W., 17-7/8" ht.
Extends 7-5/8". H/CTR 11-3/8".
One medium base lamp,
60w max.

*Shown with P7825-01
vintage lamps*

P400003-020



P500042-020



P710002-020

METRIC

The Metric collection embodies a modern spirit with square etched opal glass shades that are set inside a die-cast holder. The sleek frame provides an architectural support that is elegant both in its simplicity and artful craftsmanship. Polished Chrome or Brushed Nickel finishes are the perfect complement to the contemporary design.



P400045-009



P350021-009



P350021-015

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015

TWO-LIGHT SEMI-FLUSH

P350021-009 Brushed Nickel
P350021-015 Polished Chrome
 16" W., 12-1/2" ht.
 Two medium base lamps,
 each 100w max.



P400045-009



P400045-015

FOUR-LIGHT CHANDELIER

P400045-009 Brushed Nickel
P400045-015 Polished Chrome
 24" W., 13-1/4" ht. Overall ht. w/
 stem 70-1/2", wire 15'.
 Four medium base lamps,
 each 100w max.



P400046-009



P400046-015

SIX-LIGHT CHANDELIER

P400046-009 Brushed Nickel
P400046-015 Polished Chrome
 26" W., 13-1/4" ht. Overall ht. w/
 stem 70-1/2", wire 15'.
 Six medium base lamps,
 each 100w max.

TURNBURY

The coastal-inspired Turnbury pendant features a solid wood frame with hand-painted, galvanized metal fittings. The distressed pine frame finish is reminiscent of driftwood that has been weathered in the sun.



FINISH

● Galvanized Finish - 141

EIGHT-LIGHT CHANDELIER

P4763-141 Galvanized Finish,

Two tier

36" W., 39" ht.

Overall ht. w/chain 162", wire 15'

Eight candelabra base lamps,
each 60w max.

*Shown with P7826-01
vintage lamps*

REMIX

An industrial-inspired, five-light chandelier, Remix features overscale tubular arms finished in a Graphite frame. A touch of mixed metal accents can be found in the bobeches and candle sockets - a perfect feature to display vintage bulbs. This chandelier is suitable for a wide range of home décor designs, including popular farmhouse and industrial settings.



FINISH

● Graphite - 143

FIVE-LIGHT CHANDELIER

P400051-143 Graphite
26" dia., 20" ht. Overall ht. w/stem
86", wire 15'.
Five medium base lamps,
each 60w max.

*Shown with P7825-01
vintage lamps*

GALLEY

Galley is a simple modern form that complements both coastal décor and commercial style kitchens. The arched supporting frame features overscale metal turnings for an enhanced sense of architectural styling. The linen shades are comprised of rich, satin lining for the feel of a tailored fit and finish to complement the multi-light cluster.



P500047-020



FINISHES

- Antique Bronze - 020
- Polished Nickel - 104

TWO-LIGHT PENDANT

P500046-020 Antique Bronze
P500046-104 Polished Nickel
 15" dia., 18" ht. Overall ht. w/stem
 84", wire 10'.
 Two medium base lamps,
 each 75w max.

THREE-LIGHT PENDANT

P500047-020 Antique Bronze
P500047-104 Polished Nickel
 21" dia., 24-1/2" ht. Overall ht. w/
 stem 90-1/2", wire 10'.
 Three medium base lamps,
 each 75w max.



FORMES

The Formes collection features a stately geometric frame to support a single vintage-style lamp. Designed to be used alone or in groupings to create a sophisticated combination. The reflective backplate is an antique mirror that enhances the romantic illumination from this distinctive design.



P710024-020



P710022-020



P710023-020



P710024-020

FINISH

- Antique Bronze - 020

WALL SCUNCE

P710022-020 Antique Bronze
7-1/2" W., 14" ht.
Extends 3-3/8". H/CTR 7".
One medium base lamp,
60w max.

WALL SCUNCE

P710023-020 Antique Bronze
6-1/2" W., 14" ht.
Extends 3-3/8". H/CTR 7".
One medium base lamp,
60w max.

WALL SCUNCE

P710024-020 Antique Bronze
5" W., 14" ht.
Extends 3-3/8". H/CTR 7".
One medium base lamp,
60w max.

*Shown with P7825-01
vintage lamps*

METRO

Metro delivers a clean, geometric form with a pleasing balance of angular metal fittings and a crisp linen shade. The stately fixture adds a modern accent with an elegant sense of architectural distinction.



P710016-015



P710016-015



P710016-009

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020

WALL SCONCE

P710016-009 Brushed Nickel

P710016-015 Polished Chrome

P710016-020 Antique Bronze
5-1/2" W., 15-1/8" ht.

Extends 7-1/4". H/CTR 10-1/2".

One candelabra base lamp,
60w max.



P710016-020

AVANA

Avana features a graceful tapered candle-arm with a crisp geometric linen shade. The faceted backplate provides a rich architectural detail that complements many fashionable vanity styles.



P710025-009



P710025-009



P710025-020

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- Polished Nickel - 104

WALL SCONCE

P710025-009 Brushed Nickel

P710025-020 Antique Bronze

P710025-104 Polished Nickel

5-5/8" W., 16" ht.

Extends 7-1/2". H/CTR 12-1/2".

One candelabra base lamp,

60w max.



P710025-104

BONITA

Bonita sconces have a traditional elegance to complement luxurious living with an understated beauty. Crisp metal fittings support a graceful frame and candle topped with a linen shade. Coordinate with Marché or Glimmer collections to add a variation of textures.



P710019-015



FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020

WALL SCONCE

P710018-009 Brushed Nickel
P710018-015 Polished Chrome
P710018-020 Antique Bronze
 9" W., 17-1/8" ht.
 Extends 6-7/8". H/CTR 13-5/8".
 One candelabra base lamp,
 60w max.

WALL SCONCE

P710019-009 Brushed Nickel
P710019-015 Polished Chrome
P710019-020 Antique Bronze
 13-5/8" W., 17-1/8" ht.
 Extends 6-7/8". H/CTR 13-5/8".
 Two candelabra base lamps,
 each 60w max.



HOBBS

Modern traditional design is the combination of crisp geometric forms in classic shapes and materials. Hobbs delivers on this concept with an elegant beveled glass diffuser framing a vintage lamp. The rectangular and circular fittings add a sense of classic craftsmanship for a timeless design.



P710017-015



P710017-009



P710017-015

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020

WALL SCONCE

P710017-009 Brushed Nickel

P710017-015 Polished Chrome

P710017-020 Antique Bronze

6" W., 12" ht.

Extends 4-7/8". H/CTR 6".

One medium base lamp,

60w max.

*Shown with P7827-01
vintage lamps*



P710017-020

VOLO

Volo fixtures feature a modern repeating circular frame. Etched opal glass shades are seamlessly secured to provide a clean, contemporary look to your home. The modern LED source delivers crisp, high quality light that is the perfect choice for both general and task lighting.



P300063-009-30



P300063-009-30



P300063-020-30

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ONE-LIGHT BATH

P300063-009-30 Brushed Nickel
P300063-020-30 Antique Bronze
 10" W., 5-1/2" ht.
 Extends 4-5/8". H/CTR 2-3/4".
 One 3000 K 9w LED module
 included.



P300064-009-30



P300064-020-30

TWO-LIGHT BATH

P300064-009-30 Brushed Nickel
P300064-020-30 Antique Bronze
 16" W., 5 1/2" ht.
 Extends 4-5/8". H/CTR 2-3/4".
 Two 9w LED modules included.

**THREE-LIGHT BATH**

P300065-009-30 Brushed Nickel
P300065-020-30 Antique Bronze
 24" W., 5-1/2" ht.
 Extends 4-5/8". H/CTR 2-3/4".
 Three 9w LED modules included.



*Can be installed vertically
 or horizontally.*

PROGRESS **LED**

LED FEATURES

- 120v AC, replaceable module
- 9w 624 lumens, 66 lumens/watt
- 3000K color temperature; 90 CRI
- TM-21 60,000 hr. life
- Dimmable to 10% brightness
 with Triac or ELV dimmers



P300065-009-30



P300065-020-30

ZURA™

Zura™ features triangular, etched opal glass that provides geometric elements to add modern flair. Available in a Brushed Nickel, Polished Chrome, or Black finish, this contemporary fixture coordinates with the Zura™ Collection by Delta.



P300061-031



P300061-009



P300061-015



P300061-031

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Black - 031

ONE-LIGHT BATH

P300061-009 Brushed Nickel
P300061-015 Polished Chrome
P300061-031 Black
 4-1/2" W., 13-3/4" ht.
 Extends 7". H/CTR 9-7/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300062-009 Brushed Nickel
P300062-015 Polished Chrome
P300062-031 Black
 4-1/2" W., 21" ht.
 Extends 7". H/CTR 10-1/2".
 Two medium base lamps,
 each 100w max.

*Can be installed vertically
 or horizontally.*

COORDINATES WITH



P300062-009



P300062-015



P300062-031



P300062-015
shown horizontally



P300062-031
shown horizontally

PATEWOOD

Patewood lanterns have a modern shadowbox housing in a sleek Black finish constructed from durable stainless steel. The pillar candle style diffusers provide crisp illumination for a pleasing complement to your home's exterior.



P550024-031

*FINISH*

- Black - 031

POST LANTERN

P540013-031 Black
Fits 3" post (order separately).
7" W., 19-3/8" ht.
One medium base lamp,
100w max.

HANGING LANTERN

P550013-031 Black
5-1/2" W., 15-1/8" ht.
Overall ht. w/stem 81", wire 10'.
One medium base lamp,
100w max.

HANGING LANTERN

P550024-031 Black
7 W., 18" ht.
Overall ht. w/stem 84, wire 10'.
One medium base lamp,
100w max.



P560039-031



P560040-031

SMALL WALL LANTERN

P560039-031 Black
4-1/2" W., 12" ht.
Extends 5-3/8". H/CTR 8-5/8".
One medium base lamp,
75w max.

MEDIUM WALL LANTERN

P560040-031 Black
5-3/4" W., 14-1/2" ht.
Extends 6-3/8". H/CTR 10".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560041-031 Black
7" W., 17-3/8" ht.
Extends 7-3/4". H/CTR 11-7/8".
One medium base lamp,
100w max.



UNION SQUARE

Union Square is inspired by the gas lanterns of the past. A Stainless Steel finish complements the natural polished material and clear flat glass panels. Mechanical details, such as exaggerated knobs, provide character to the form.



FINISH

● Stainless Steel - 135

OUTDOOR HANGING LANTERN

P550018-135 Stainless Steel
7" Sq., 27-3/8" ht.
Overall ht. w/chain 102-1/2", wire 10'.
One medium base lamp,
100w max.

*Shown with P7827-01
vintage lamps*

Mix it Up!

MIX YOUR FAVORITE FIXTURES AND MAKE A STATEMENT IN YOUR HOME!

One of today's most popular design trends encourages individuals to create unique lighting designs by mixing and matching their favorite fixtures within the same space. There is no need to feel limited by fixtures or finishes in one particular collection!

Coordinating complementary pieces creates a cohesive feel to the home, while also reinforcing your unique design style. →



Featuring Design Series fixtures – Looking Glass chandelier and Era pendants.



LOOKING GLASS + ERA

The key to coordinating lighting throughout the home is finding a good balance. Try to avoid choosing every light fixture from one particular collection.

Instead, select fixtures that feature similar metal profiles or design styles. While the Era pendant and Looking Glass chandelier are from different families, each contains elements with an overall vintage feel. Iron accents, hints of brass and mechanical details all work together to create a unique statement.

DEBUT + SQUIRE

Circular elements featured in the mirror and Debut chandelier work together to provide dramatic focal points to this living space.

Additionally, the Squire outdoor wall lantern was incorporated in a creative way in this interior setting to create a rich layer of light to contribute to the room's décor.







WESTFALL + SOIREE

Classic forms, geometric patterns and mixed metal finishes work together to define this stunning living area, while also enhancing the soothing color palette. Westfall's dramatic soaring frame and candelabra cluster complement Soiree's tall candles and clear seeded glass, creating an overall inviting atmosphere.

Featuring Design Series fixtures - Westfall pendant and Soiree wall sconce.



Featuring Design Series fixtures - Glimmer chandelier and Bonita wall sconce.

GLIMMER + BONITA

To contrast the gray color scheme, rich furniture and sleek hardware, we chose lighting fixtures with glass accents, metal finishes and architecturally styled frames, to bring intrigue and a sophisticated sparkle to the room.

TURNBURY+ UNION SQUARE

Size matters! When it comes to selecting fixtures for a particular room, oversized or exaggerated frames are on trend in a big way.

In lieu of table lamps, we've chosen sconces from our Union Square outdoor lantern collection - a unique way of bringing the "outdoors" inside! Finally, our oversized Turnbury chandelier creates a dramatic focal point for this luxurious bedroom.







Featuring, from left to right, Callahan wall lanterns, Whip chandelier, Briarwood Dining chandelier and Beaufort hanging lanterns.

CALLAHAN, WHISP, BRIARWOOD + BEAUFORT

Ask interior designers and they will tell you: lighting is a key element in any well-designed space. How we choose to light a space relates to how we view all the elements within.

The lighting within this open floorplan creates visual interest with similar features – including open frames, vintage bulbs and traditional finishes. Feel free to explore new spaces to incorporate pendants and chandeliers for stunning sightlines within your home.

BRINGING OUTSIDE IN



BEAUFORT

Our Beaufort hanging lanterns add intrigue to an otherwise forgotten space in the dining room and take up less space than traditional floor lamps, providing form and function.



CALLAHAN

Outdoor wall lanterns don't always have to be used for a home's façade. Try exterior sconces, such as our Callahan lanterns, on either side of a focal point within the interior of your favorite room.



ZURA™

One of the most important things to remember when illuminating your bathroom is to provide shadow-free lighting at the mirror. This bath area benefits from a generous amount of natural light, while our sleek and sophisticated Zura sconces placed on either side of the bathroom mirror work to further reduce shadows on the side of the face.

COORDINATES WITH



Featuring Design Series Zura™ bath fixtures.

MARCHÉ + BONITA

We selected the Marché chandelier for this master bathroom because of its luxurious sheer silver organza shade and Polished Nickel finish. These luxurious elements contrast nicely with the geometric tile and neutral color scheme, while creating a spa-like environment for individuals to enjoy while either starting or ending their day.





BRIARWOOD



P400047-143



The Briarwood collection features a classic pattern commonly found on barn or farmhouse doors and gates. The simple geometric form features a faux-painted wood enclosure to frame vintage-style light bulbs. Choose from a coastal-inspired whitewashed finish paired with Graphite details, or a rich oak finish and Antique Bronze combination.

FINISHES

- Antique Bronze - 020
- Graphite - 143



P400048-143

ONE-LIGHT FLUSH MOUNT

P350022-143 Graphite
9-1/2" sq., 7-5/8" ht.
One medium base lamp,
60w max.

TWO-LIGHT FLUSH MOUNT

P350039-143 Graphite
12" sq., 6" ht.
Two medium base lamps,
each 60w max.

FOUR-LIGHT CHANDELIER

P400047-143 Graphite
20" sq., 12" ht.
Overall ht. w/stem 88", wire 15'.
Four medium base lamps,
each 100w max.

FIVE-LIGHT LINEAR CHANDELIER

P400048-143 Graphite
10" W., 38" L., 9" ht.
Overall ht. w/stem 75", wire 15'.
Five medium base lamps,
each 100w max.



P500041-143

MINI-PENDANT

P500041-143 Graphite
10" sq., 9" ht.
Overall ht. w/stem 78", wire 10'.
One medium base lamp,
100w max.



P400047-143

WALL SCONCE

P710012-143 Graphite
6-7/8" W., 12" ht.
Extends 6", H/CTR 4".
One medium base lamp,
100w max.

*Shown with P7825-01
vintage lamps*



P350022-143



P350039-143



P710012-143

BRIARWOOD

ONE-LIGHT FLUSH MOUNT

P350022-020 Antique Bronze
9-1/2" sq., 7-5/8" ht.
One medium base lamp,
60w max.

TWO-LIGHT FLUSH MOUNT

P350039-020 Antique Bronze
12" sq., 6" ht.
Two medium base lamps,
each 60w max.

FOUR-LIGHT CHANDELIER

P400047-020 Antique Bronze
20" sq., 12" ht. Overall Ht. W/Stem
88", wire 15'.
Four medium base lamps,
each 100w max.

FIVE-LIGHT LINEAR CHANDELIER

P400048-020 Antique Bronze
10" W., 38" L., 9" ht. Overall Ht.
W/Stem 75", wire 15'.
Five medium base lamps,
each 100w max.

MINI-PENDANT

P500041-020 Antique Bronze
10" sq., 9" ht. Overall Ht. W/Stem
78", wire 10'.
One medium base lamp,
100w max.

WALL SCONCE

P710012-020 Antique Bronze
6 7/8" W., 12" ht.
Extends 6", H/CTR 4".
One medium base lamp,
100w max.

*Shown with P7825-01
vintage lamps*

P400048-020



P500041-020



P400047-020



P710012-020



P350022-020



P350039-020

SWING



P400050-020

Swing five-light chandelier can revive the look of a favorite room, while adding a vintage electric feel. Oversized tubular arms in Antique Bronze support the candle socket and bobèche in natural brass accents to offer a mixed metal effect, while also complementing the vintage bulbs.

FINISH

● Antique Bronze - 020

FIVE-LIGHT CHANDELIER

P400050-020 Antique Bronze
26" dia., 20" ht. Overall ht. w/stem
86", wire 15'.

Five medium base lamps,
each 60w max.

*Shown with P7825-01
vintage lamps*

BARNES MILL



P400055-020



Rustic and vintage décor can transform your home into a nostalgic retreat reminiscent of rural farmhouses. Exposed iron details and a faux-painted wooden plank support artful, clear seeded glass shades. Combine with vintage-style light bulbs to create a romantic focal point for any room.

FINISH

● Antique Bronze - 020

ALSO AVAILABLE IN

Bath & Vanity, page 73



P300066-020



P350059-020

Shown flush mounted



P500056-020



P350059-020

FINISH

- Antique Bronze - 020

WALL BRACKET

P300066-020 Antique Bronze
4 1/2" W., 11 7/8" ht.
Extends 5 7/8". H/CTR 7-5/8".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P350059-020 Antique Bronze
Hanging and ceiling mount
hardware included.
16-1/4" dia., 11-7/8" ht.
Overall ht. w/chain 52", wire 10".
Two medium base lamps,
each 75w max.

FIVE-LIGHT LINEAR CHANDELIER

P400055-020 Antique Bronze
4" W., 38" L., 22-5/8" ht.
Overall ht. w/chain 96-1/2", wire 15".
Five medium base lamps,
each 100w max.

MINI-PENDANT

P500056-020 Antique Bronze
8-3/4" dia., 14" ht.
Overall ht. w/chain 89", wire 10".
One medium base lamp,
100w max.
*Shown with P7825-01
vintage lamps*



P400055-020

REPLAY



P4319-09

Shown with glass up



Smooth forms, linear details and a pleasingly elegant frame enhance a simplified modern look within the Replay collection. Chandeliers can be installed with glass facing upwards or downwards.

FINISH

● Brushed Nickel - 09

ALSO AVAILABLE IN

Bath & Vanity, page 83



P5170-09



P4726-09

TWO-LIGHT FLUSH MOUNT

P3423-09 Brushed Nickel
14" dia., 5-3/4" ht.
Two medium base lamps,
each 60w max.

SEMI-FLUSH CONVERTIBLE

P3424-09 Brushed Nickel
Hanging and ceiling mount
hardware included.
14-3/4" dia., 10" ht.
Overall ht. w/chain 49-1/2", wire 10'.
Two medium base lamps,
each 100w max.

THREE-LIGHT PENDANT

P3450-09 Brushed Nickel
16-5/8" dia., 19" ht.
Overall ht. w/chain 92-1/2", wire 15'.
Three medium base lamps,
each 100w max.



P3450-09

THREE-LIGHT CHANDELIER

P4318-09 Brushed Nickel
17" dia., 20-1/8" ht.
Overall ht. w/chain 95", wire 15'.
Three medium base lamps,
each 100w max.



P4318-09
*Shown with
glass down*



P4319-09

FIVE-LIGHT CHANDELIER

P4319-09 Brushed Nickel
21" dia., 19-5/8" ht.
Overall ht. w/chain 95", wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4726-09 Brushed Nickel
25-1/2" dia., 28" ht.
Overall ht. w/chain 104", wire 15'.
Nine medium base lamps,
each 100w max.



P3423-09



P3424-09



P3424-09
Shown hanging

MINI-PENDANT

P5170-09 Brushed Nickel
4" dia., 6" ht. Overall Ht. W/Stem
72", wire 10'.
One medium base lamp,
100w max.

TOPSAIL



P400053-020



Topsail features a graceful curving frame paired with elegant parchment-finish glass shades to create a clean, modern form. Classic metal fittings enhance the crisp appearance of a brilliant Polished Chrome or warm Antique Bronze finish. This collection provides the perfect complement to coastal-inspired or casual décor.

FINISHES

- Polished Chrome - 015
- Antique Bronze - 020

ALSO AVAILABLE IN

Bath & Vanity, page 80



P400054-020



P500050-020

FIVE-LIGHT CHANDELIER**P400053-015** Polished Chrome**P400053-020** Antique Bronze
25" dia., 18-1/4" ht.Overall ht. w/chain 93-1/2", wire 15'.
Five medium base lamps,
each 100w max.**NINE-LIGHT CHANDELIER****P400054-015** Polished Chrome**P400054-020** Antique Bronze
30" dia., 25-3/8" ht.Overall ht. w/chain 147", wire 15'.
Nine medium base lamps,
each 100w max.**MINI-PENDANT****P500050-015** Polished Chrome**P500050-020** Antique Bronze
5-1/4" dia., 13-1/8" ht.Overall Ht. W/Stem 79, wire 10'.
One medium base lamp,
100w max.

P400054-015



P400053-015



P500050-015

TOPSAIL

WALL BRACKET

P300057-015 Polished Chrome
P300057-020 Antique Bronze
 5-1/4" W., 7" ht.
 Extends 7-1/4". H/CTR 3-1/8".
 One medium base lamp,
 100w max.

THREE-LIGHT CHANDELIER

P400052-015 Polished Chrome
P400052-020 Antique Bronze
 21" dia., 19-1/8" ht. Overall ht. w/
 chain 93-1/2", wire 15'.
 Three medium base lamps,
 each 100w max.

THREE-LIGHT PENDANT

P500054-015 Polished Chrome
P500054-020 Antique Bronze
 18-3/4" dia., 21" ht. Overall ht. w/
 chain 96", wire 10'.
 Three medium base lamps,
 each 100w max.

P400052-015



P400052-020



P500054-015



P500054-020



P300057-015



P300057-020



P350062-020



P350062-015

TWO-LIGHT FLUSH MOUNT
P350047-015 Polished Chrome
P350047-020 Antique Bronze
 11" dia., 6-1/4" ht.
 Two medium base lamps,
 each 75w max.



P350048-020



P350048-015

THREE-LIGHT FLUSH MOUNT
P350048-015 Polished Chrome
P350048-020 Antique Bronze
 13-5/8" dia., 6-1/4" ht.
 Three medium base lamps,
 each 75w max.

THREE-LIGHT FLUSH MOUNT
P350062-015 Polished Chrome
P350062-020 Antique Bronze
 15" dia., 6-1/4" ht.
 Three medium base lamps,
 each 75w max.



P350047-020



P350047-015

SEMI-FLUSH CONVERTIBLE
P350063-015 Polished Chrome
P350063-020 Antique Bronze
 Hanging and ceiling mount
 hardware included.
 12-7/8" dia., 12-3/8" ht. Overall ht.
 w/chain 52-1/2", wire 10".
 Three medium base lamps,
 each 75w max.



P350063-020



P350063-015



P350063-015
Shown hanging

CLASSIC



P4762-09



Traditional details and graceful lines provide modern elegance to any interior. Classic features etched glass shades with a Polished Chrome, Antique Bronze or Brushed Nickel frame.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Polished Chrome - 15



P4762-09



P4732-09

THREE-LIGHT CHANDELIER**P4732-09** Brushed Nickel**P4732-15** Polished Chrome**P4732-20** Antique Bronze

20" dia., 17" ht. Overall ht. w/chain 56", wire 15'.

Three medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER**P4762-09** Brushed Nickel**P4762-15** Polished Chrome**P4762-20** Antique Bronze

18" dia., 17-1/4" ht. Overall ht. w/chain 62-1/2", wire 9.

Three medium base lamps, each 100w max.



P4762-15



P4732-15



P4762-20



P4732-20

CALHOUN

A delightful trend in home décor is the repurposing of antique parts into new, functional furniture and accessories. Calhoun playfully follows this lead with an apothecary style clear glass diffuser held in place with a mechanical latch from a spice container. The glass shade showcases a thickened profile to create a vintage-style surface for a classic handmade appearance.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO AVAILABLE IN

Bath & Vanity, page 74

MINI-PENDANT

P500055-009 Brushed Nickel
P500055-020 Antique Bronze
 4-3/4" dia., 9" ht. Overall Ht. W/
 Stem 75", wire 10'.
 One medium base lamp,
 100w max.

*Shown with P7825-01
 vintage lamps*

P500055-009



P500055-020



ESTEEM

Esteem's exaggerated classic frame offers casual luxe styling for the home with oversized single tiered chandeliers with K9 glass finial accents. The foyer pendant features a frameless design, creating a floating effect for this elegant fixture.

FINISH

- Antique Bronze - 20

EIGHT-LIGHT FOYER PENDANT

P3755-20 Antique Bronze
 two-tier.
 18" sq., 30" ht. Overall Ht. W/Stem
 96", wire 15'.
 Eight candelabra base lamps,
 each 60w max.

P3755-20



TRE

Tre is a series of classic metal shade pendants with an updated combination of finishes and features. A tri-arm support adds a sense of architectural and industrial detailing, while the open-top shade allows for both downward and upward illumination. Light reflects off the inside of the Vintage Silver shade to provide the metallic reflective effect.

FINISHES

- White - 030
- Graphite -143

ONE-LIGHT MINI PENDANT

P500051-030 White
P500051-143 Graphite
 10" dia., 13-1/4" ht. Overall ht. w/ chain 134", wire 10'.
 One medium base lamp, 100w max.

ONE-LIGHT PENDANT

P500052-030 White
P500052-143 Graphite
 15" dia., 13-1/2" ht. Overall ht. w/ chain 134-1/2", wire 10'.
 One medium base lamp, 100w max.

ONE-LIGHT PENDANT

P500053-030 White
P500053-143 Graphite
 20" dia., 14-1/2" ht. Overall ht. w/ chain 135-1/2", wire 10'.
 One medium base lamp, 100w max.



HANSFORD

Hansford features a clear, spherical shade paired with vintage style metal fittings. Choose the antique style bronze and brass combinations, or the gleaming nickel finish to bring tranquility to your home with Hansford's classic style.

FINISHES

- Antique Bronze - 020
- Polished Nickel - 104

ALSO AVAILABLE IN

Bath & Vanity, page 76

ONE-LIGHT FLUSH MOUNT

P350046-020 Antique Bronze

P350046-104 Polished Nickel

10" dia., 12-5/8" ht.

One medium base lamp,
100w max.

*Shown with P7825-01
vintage lamp*

P350046-020



P350046-104



LED DOME

A domed, linen finish glass diffuser is discreetly supported from metal fittings and encloses an energy-efficient light source. NOTE: This fixture is not dimmable.

FINISH

- Brushed Nickel - 009

ONE-LIGHT FLUSH MOUNT

P350055-009-30 Brushed Nickel

12" dia., 4-1/4" ht.

One 3000K 20w LED included.

1600 source lumens 90 CRI



ONE-LIGHT FLUSH MOUNT

P350056-009-30 Brushed Nickel

16" dia., 4-1/2" ht.

One 3000K 24w LED included.

2100 source lumens 90 CRI



P350055-009-30



P350056-009-30



LED SQUARE FLUSH MOUNT



A tapered, square, linen finish glass diffuser is paired with an energy-efficient, high-performance LED source in this contemporary ceiling fixture.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ONE-LIGHT FLUSH MOUNT

P350023-009-30 Brushed Nickel

P350023-020-30 Antique Bronze

9-1/2" sq., 4-3/8" ht.

One 17w LED module included.



ONE-LIGHT FLUSH MOUNT

P350024-009-30 Brushed Nickel

P350024-020-30 Antique Bronze

11-1/2" sq., 4-7/8" ht.

One 25w LED module included.

JA8 Compliant.



LED FEATURES

- 120v AC, replaceable module
- 17w 1452 lumens, 83 lumens/watt
25w 2015 lumens, 80 lumens/watt
- 3000K color temperature; 90 CRI
- TM-21 60,000 hr. life
- Dimmable to 10% brightness
with Triac or ELV type dimmers



P350023-009-30



P350024-009-30



P350023-020-30



P350024-020-30

INDUSTRIAL

The Industrial frame comes in a painted Galvanized Finish with metallic silver accents, or can also be chosen in an Antique Bronze finish with vintage brass touches. Its striking form provides the perfect enclosure for vintage style tubular lamps.

FINISHES

- Galvanized Finish - 141
- Antique Bronze - 020

WALL SCONCE

P710014-020 Antique Bronze

P710014-141 Galvanized Finish

4-7/8" W., 14" ht. Extends 5".

H/CTR 2-1/2".

One medium base lamp,
60w max.

*Shown with P7827-01
vintage lamps*



P710014-020



P710014-141

MAST

Mast has a zen-like modernism that blends the warmth of a faux-finish wooden backplate with a clean, modern pediment supporting a double-glass diffuser. The combination of clear and etched glass recreates the appearance of a votive candleholder.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

WALL SCONCE

P710015-009 Brushed Nickel

P710015-020 Antique Bronze

5" W., 13" ht. Extends 6-3/8".

H/CTR 6-1/2".

One medium base lamp,
100w max.



P710015-020



P710015-009



P300066-020



P300067-020



P300068-020



P300069-020

BARNES MILL

Rustic and vintage décor can transform your home into a nostalgic retreat reminiscent of rural farmhouses. Exposed iron details and a faux-painted wooden plank support artful, clear seeded glass shades. Combine with vintage-style light bulbs to create a romantic focal point for any room. Installs up or down.

FINISH

● Antique Bronze - 020

ONE-LIGHT BATH

P300066-020 Antique Bronze
4 1/2" W., 11 7/8" ht.
Extends 5 7/8". H/CTR 7-5/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300067-020 Antique Bronze
13 3/8" W., 8" ht.
Extends 5 7/8". H/CTR 5-3/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300068-020 Golden Brandy
24" W., 8" ht.
Extends 5 7/8". H/CTR 5-3/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300069-020 Golden Brandy
32 1/4" W., 8" ht.
Extends 5 7/8". H/CTR 5-3/4".
Four medium base lamps,
each 100w max.

*Shown with P7825-01
vintage lamps*

CALHOUN

A delightful trend in home décor is the repurposing of antique parts into new, functional furniture and accessories. Calhoun playfully follows this lead with an apothecary style and features a clear glass diffuser held in place with a mechanical latch from a spice container. The glass shade showcases a thickened profile to create a vintage-style surface for a classic handmade appearance. Installs up or down.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO AVAILABLE IN

Pendants, page 68

ONE-LIGHT BATH

P300045-009 Brushed Nickel
P300045-020 Antique Bronze
 5" W., 8-5/8" ht.
 Extends 6-7/8". H/CTR 5-1/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300046-009 Brushed Nickel
P300046-020 Antique Bronze
 13-1/4" W., 8-5/8" ht.
 Extends 6-7/8". H/CTR 6-3/8".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300047-009 Brushed Nickel
P300047-020 Antique Bronze
 21-5/8" W., 8-5/8" ht.
 Extends 6-7/8". H/CTR 6-3/8".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH

P300048-009 Brushed Nickel
P300048-020 Antique Bronze
 30-1/4" W., 8-5/8" ht.
 Extends 6-7/8". H/CTR 6-3/8".
 Four medium base lamps,
 each 100w max.

*Shown with P7825-01
 vintage lamps*



P300045-009



P300046-009



P300047-009



P300048-009



P300045-020



P300046-020



P300047-020



P300048-020

HANSFORD



Hansford features a clear, spherical shade with vintage style metal fittings. Choose the antique style bronze and brass combinations, or the gleaming nickel finish to bring tranquility to your home with Hansford's classic style. Installs up or down.

FINISHES

- Antique Bronze - 020
- Polished Nickel - 104

ALSO AVAILABLE IN

Close-to-Ceiling, page 70

ONE-LIGHT BATH

P300049-020 Antique Bronze
P300049-104 Polished Nickel
 6-1/2" W., 9-1/2" ht.
 Extends 7-1/4". H/CTR 6-7/8".
 One medium base lamp, 100w max.

TWO-LIGHT BATH

P300050-020 Antique Bronze
P300050-104 Polished Nickel
 15-1/2" W., 10-7/8" ht.
 Extends 7-1/4". H/CTR 8-1/4".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300051-020 Antique Bronze
P300051-104 Polished Nickel
 24-1/2" W., 10-7/8" ht.
 Extends 7-1/4". H/CTR 8-1/4".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH

P300052-020 Antique Bronze
P300052-104 Polished Nickel
 33-1/2" W., 10-7/8" ht.
 Extends 7-1/4". H/CTR 8-1/4".
 Four medium base lamps,
 each 100w max.

*Shown with P7825-01
 vintage lamps*



P300049-020



P300050-020
Installed up



P300051-020



P300052-020



P300049-104



P300050-104



P300051-104



P300052-104
Installed up

TILLEY

Rustic and vintage décor is a popular trend that can help transform your home into a nostalgic retreat. Tilley features warehouse style shades formed from metal mesh that merge with a faux-painted, wooden rim for an artful yet industrial style.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ONE-LIGHT BATH

P300042-009 Brushed Nickel
P300042-020 Antique Bronze
 6-3/8" W., 8-1/2" ht.
 Extends 8-1/4". H/CTR 4-1/4".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300043-009 Brushed Nickel
P300043-020 Antique Bronze
 15" W., 8-3/8" ht.
 Extends 8-3/8". H/CTR 4-1/4".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300044-009 Brushed Nickel
P300044-020 Antique Bronze
 23-3/8" W., 8-3/8" ht.
 Extends 8-3/8". H/CTR 4-1/4".
 Three medium base lamps,
 each 100w max.

*Shown with P7825-01
 vintage lamps*



P300042-009



P300043-009



P300044-009



P300042-020



P300043-020



P300044-020

BRAMLETT



P300039-009



P300040-009



P300041-009



P300039-015



P300040-015



P300041-015

Vintage and industrial styling coalesce in the functional, yet elegant frame of the Bramlett fixtures. Metal reflector style shades are complemented by contrasting metallic fittings. Fixtures from this collection pair well with either vintage style or traditional bulbs to create a fun focal point in your home.

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015

ONE-LIGHT BATH

P300039-009 Brushed Nickel
P300039-015 Polished Chrome
 6" W., 8-1/8" ht.
 Extends 7-1/8". H/CTR 4-1/2".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300040-009 Brushed Nickel
P300040-015 Polished Chrome
 15-1/8" W., 8-3/8" ht.
 Extends 7-1/8". H/CTR 6".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300041-009 Brushed Nickel
P300041-015 Polished Chrome
 24-1/4" W., 8-3/8" ht.
 Extends 7-1/8". H/CTR 6".
 Three medium base lamps,
 each 100w max.

TOPSAIL



Topsail features a graceful curving frame paired with elegant parchment-finish glass shades to create a clean, modern form. Classic metal fittings enhance the crisp appearance of a brilliant Polished Chrome or warm Antique Bronze finish. This collection provides the perfect complement to coastal-inspired or casual décor. Installs up or down.

FINISHES

- Polished Chrome - 015
- Antique Bronze - 020

ALSO AVAILABLE IN

Chandelier, page 62

ONE-LIGHT BATH

P300057-015 Polished Chrome
P300057-020 Antique Bronze
 5-1/4" W., 7" ht.
 Extends 7-1/4". H/CTR 3-1/8".
 One medium base lamp, 100w max.



P300057-015



P300058-015

TWO-LIGHT BATH

P300058-015 Polished Chrome
P300058-020 Antique Bronze
 14" W., 7" ht.
 Extends 7-1/4". H/CTR 3-1/8".
 Two medium base lamps,
 each 100w max.



P300059-015

THREE-LIGHT BATH

P300059-015 Polished Chrome
P300059-020 Antique Bronze
 24" W., 7" ht.
 Extends 7-1/4". H/CTR 3-1/8".
 Three medium base lamps,
 each 100w max.



P300060-015

FOUR-LIGHT BATH

P300060-015 Polished Chrome
P300060-020 Antique Bronze
 33-1/2" W., 7" ht.
 Extends 7-1/4". H/CTR 3-1/8".
 Four medium base lamps,
 each 100w max.



P300057-020



P300058-020



P300059-020



P300060-020

STATUS



Status collection's K-9 glass accents offer crystal-like clarity to contrast the softened linen-finish glass shades. A Polished Chrome frame provides the perfect support to this elegant combination.

FINISH

● Polished Chrome - 15

TWO-LIGHT BATH

P2775-15 Polished Chrome
13-7/8" W., 10-1/8" ht.
Extends 5-3/4". H/CTR 6-3/4".
Two medium base lamps,
each 100w max.



P2775-15

THREE-LIGHT BATH

P2776-15 Polished Chrome
23-3/4" W., 10-1/8" ht.
Extends 5-3/4". H/CTR 6-3/4".
Three medium base lamps,
each 100w max.



P2776-15

FOUR-LIGHT BATH

P2777-15 Polished Chrome
33-7/8" W., 10-1/8" ht.
Extends 5-3/4". H/CTR 6-3/4".
Four medium base lamps,
each 100w max.



P2777-15

REPLAY

Smooth forms, linear details and a pleasingly elegant frame enhance a simplified modern look within the Replay collection. Installs up or down.

FINISH

● Black - 31

ALSO AVAILABLE IN

Chandelier, page 60



P2158-31



P2159-31



P2160-31

TWO-LIGHT BATH

P2158-31 Black
13" W., 7-7/8" ht.
Extends 6". H/CTR 6".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P2159-31 Black
22" W., 7-7/8" ht.
Extends 6". H/CTR 5-1/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P2160-31 Black
31-1/8" W., 7-7/8" ht.
Extends 6". H/CTR 5-1/4".
Four medium base lamps,
each 100w max.

SQUIRE



Squire lanterns feature a classic traditional profile with clean, modern metal fittings. Accented with contrasting metallic elements, the cylindrical frame is comprised of a clear glass diffuser.

FINISHES

- Antique Bronze - 020
- Black - 031

POST LANTERN

P540012-020 Antique Bronze

P540012-031 Black

9-7/8" dia., 22-5/8" ht.

Fits 3" post (sold separately).

Three candelabra base lamps, each 60w max.

MEDIUM WALL LANTERN

P560037-020 Antique Bronze

P560037-031 Black

8" W., 19-1/4" ht.

Extends 8-3/4". H/CTR 6-3/4".

Two candelabra base lamps, each 60w max.

SEMI-FLUSH CONVERTIBLE

P550011-020 Antique Bronze

P550011-031 Black

Hanging and ceiling mount hardware included.

9-7/8" dia., 11" ht. Overall ht. w/ chain 50", wire 9'.

Three candelabra base lamps, each 60w max.

LARGE WALL LANTERN

P560038-020 Antique Bronze

P560038-031 Black

9-7/8" W., 22-3/4" ht.

Extends 10-5/8". H/CTR 8".

Three candelabra base lamps, each 60w max.

Shown with P7826-01 vintage lamps

HANGING LANTERN

P550012-020 Antique Bronze

P550012-031 Black

9-7/8" dia., 20-1/4" ht. Overall ht. w/chain 65", wire 9'.

Three candelabra base lamps, each 60w max.

SMALL WALL LANTERN

P560036-020 Antique Bronze

P560036-031 Black

6" W., 14-3/4" ht.

Extends 7-3/8". H/CTR 6-3/8".

One medium base lamp, 100w max.



P550011-020



P550012-020



P560037-020



P560036-020



P560038-020



P540012-020

P550012-031



P550011-031

Shown hanging



P550011-031



P560036-031

Shown hanging



P560036-031



P560037-031



P540012-020



P560038-031

ENDICOTT



With a Craftsman-inspired silhouette, Endicott offers visual interest to your home's exterior. The elongated frame is finished with clear seeded glass.

FINISH

- Black - 31

POST LANTERN

P5400-31 Black
7-3/8" W., 17-3/4" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN

P5500-31 Black
7-3/8" W., 15-1/4" ht.
Overall ht. w/chain 90-1/2",
wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P5605-31 Black
7-1/4" W., 10-1/2" ht.
Extends 9-1/2". H/CTR 2-3/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P5610-31 Black
7-1/4" W., 14-1/4" ht.
Extends 9-1/2". H/CTR 3-5/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P5611-31 Black
8-7/8" W., 12-1/2" ht.
Extends 11". H/CTR 3-5/8".
One medium base lamp,
100w max.

EXTRA-LARGE WALL-LANTERN

P5613-31 Black
8-7/8" W., 18" ht.
Extends 11". H/CTR 4-1/2".
One medium base lamp,
100w max.



P5605-31



P5610-31



P5613-31



P5500-31



P5611-31



P5400-31

*Shown with P7825-01
vintage lamps*

HADDON



P550014-031



P550015-020



P560016-031



P560017-020



P560042-031



P560043-020



P540014-031



P540015-031



A classic New England coach light, the Haddon lanterns feature either a clear seeded shade paired with an Antique Bronze frame or an etched opal diffuser paired with classic Black. The wire surround is a classic industrial-inspired detail that provides nostalgic charm.

FINISHES

● Antique Bronze - 020

● Black - 031

POST LANTERN

P540014-031 Black
10" dia., 16-1/8" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

POST LANTERN

P540015-020 Antique Bronze
10" dia., 16-1/8" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

HANGING LANTERN

P550014-031 Black
10" dia., 12-3/4" ht. Overall ht.
w/chain 88", wire 10'.
One medium base lamp,
100w max.

HANGING LANTERN

P550015-020 Antique Bronze
10" dia., 12-3/4" ht. Overall ht.
w/chain 88", wire 10'.
One medium base lamp,
100w max.

ONE-LIGHT FLUSH MOUNT

P550016-031 Black
10" dia., 10" ht.
One medium base lamp,
75w max.

ONE-LIGHT FLUSH MOUNT

P550017-020 Antique Bronze
10" dia., 10" ht.
One medium base lamp,
75w max.

MEDIUM WALL LANTERN

P560042-031 Black
10" W., 17" ht.
Extends 10-5/8".
H/CTR 9-1/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560043-020 Antique Bronze
10" W., 17" ht.
Extends 10-5/8".
H/CTR 9-1/4".
One medium base lamp,
100w max.

*Shown with P7825-01
vintage lamps*

BEAUFORT



Beaufort is an understated lantern that draws its design from both industrial and nautical influences. A clear seeded glass diffuser works well with either traditional or vintage style lights.

FINISH

● Black - 031

HANGING LANTERN

P550019-031 Black
10" dia., 12 5/8" ht. Overall Ht. W/
Stem 78-1/2", wire 10'.
One medium base lamp,
60w max.

SMALL WALL LANTERN

P560049-031 Black
8-5/8" W., 11-1/2" ht.
Extends 10-1/4". H/CTR 4-5/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560050-031 Black
10" W., 14-3/8" ht.
Extends 12-1/8". H/CTR 5-3/4".
One medium base lamp,
100w max.

*Shown with P7825-01
vintage lamps*





P560052-020-30



P560053-020-30



P560052-103-30



P560053-103-30



Callahan draws inspiration from farmhouse decor. Hidden within this vintage frame is a modern LED light source that delivers energy-efficient performance. The inner surface of the shade is accented with a contrasting finish to complete the nostalgic look. Additionally, the full reflector provides illumination that is compliant with Dark Sky requirements for full cutoff lighting. Meets California Title 24 high efficacy requirements for outdoor use only.

FINISHES

- Antique Bronze - 020
- Antique Pewter - 103



SMALL WALL LANTERN

P560052-020-30 Antique Bronze
P560052-103-30 Antique Pewter
 8-1/2" W., 10" ht.
 Extends 8-7/8". H/CTR 3-3/4".
 One 3000K 9w LED module included.



MEDIUM WALL LANTERN

P560053-020-30 Antique Bronze
P560053-103-30 Antique Pewter
 11" W., 11-1/2" ht.
 Extends 11-1/2". H/CTR 4-1/4".
 One 3000K 17w LED module included.



LED FEATURES

- 120v AC, replaceable module
- 9w 624 lumens, 66 lumens/watt
- 17w 1276 lumens, 83 lumens/watt
- 3000K color temperature; 90 CRI
- TM-21 60,000 hr. life
- Dimmable to 10% brightness with Triac and ELV dimmers

CHANDLER LED

Chandler features a traditional form that is equally appropriate for a modern bungalow or rustic farmhouse. The flared metal shade encloses a modern LED source with a domed glass diffuser. Full cutoff design provides Dark Sky compliance and energy-efficient illumination. Meets California Title 24 high efficacy requirements for outdoor use only.

FINISH

- Black - 031



MEDIUM WALL LANTERN

P560055-031-30 Black
12" W., 11-1/2" ht.
Extends 13". H/CTR 3-3/4".
One 3000K 9w LED module
included.



LED FEATURES

- 120V AC Replaceable LED module
- 670 lumens, 71 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life
- Dimmable to 10% with Triac and ELV dimmers



P560055-031-30

ENDORSE

Endorse celebrates the traditional form of a gas-powered coach light with illumination from a modern LED source. A die-cast aluminum, powder coated frame creates an intriguing visual effect with clear beveled glass. To add a decorative element in the lantern, an optional frosted glass column is included.

FINISH

- Black - 31



POST LANTERN

P6426-3130K9 Black
10 3/4" sq., 21" ht.
Fits 3" post (sold separately).
One 3000K 9w LED module
included.
T24 for outdoor use only



LED FEATURES

- 120V AC Replaceable LED module
- 623 lumens, 69.2 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers



P6426-3130K9



P560046-129



P560045-129

DIVERGE

Diverge is a low-profile, modern style exterior sconce that complements urban and commercial structures. Its medium base lamping is compatible with incandescent, LED or compact fluorescent sources. ADA compliant.

FINISH

● Architectural Bronze - 129

SMALL WALL LANTERN

P560045-129 Architectural Bronze

6" W., 10-7/8" ht.

Extends 4". H/CTR 5-3/4".

One medium base lamp,
60w max.

MEDIUM WALL LANTERN

P560046-129 Architectural Bronze

6" W., 17-3/4" ht.

Extends 4". H/CTR 9-3/8".

Two medium base lamps,
each 60w max.



P560035-031

MCBEE

A truly distinctive style, the McBee lantern delivers sophisticated styling that has a classic vintage appearance suitable for residential or urban exteriors. The clear cylindrical glass shade is held in place with a working mechanical cover that provides easy access for maintenance.

FINISH

● Black - 031

MEDIUM WALL LANTERN

P560035-031 Black

4-1/2" W., 20-3/4" ht.

Extends 8". H/CTR 11-3/4".

One medium base lamp,
60w max.

*Shown with P7827-01
vintage lamp*

Z-1030

A modern outdoor LED sconce with an architectural-inspired open linear frame and clear glass diffuser. Finished in Black, White, Metallic Gray or Antique Bronze. Meets California Title 24 high efficacy requirements for outdoor use only.

FINISHES

- Antique Bronze - 020
- White - 030
- Black - 031
- Metallic Gray -082



P560051-020-30



P560051-030-30



P560051-031-30



P560051-082-30

SMALL WALL LANTERN

P560051-020-30 Antique Bronze

P560051-030-30 White

P560051-031-30 Black

P560051-082-30 Metallic Gray

5-1/8" W., 12" ht.

Extends 5-3/4". H/CTR 2-1/4".

One 3000K 9w LED module included.



MEDIUM WALL LANTERN

P560056-020-30 Antique Bronze

P560056-030-30 White

P560056-031-30 Black

P560056-082-30 Metallic Gray

5-1/8" W., 20" ht.

Extends 5-3/4". H/CTR 2-1/4".

One 3000K 9w LED module included.



P560056-020-30



P560056-030-30



P560056-031-30



P560056-082-30

PROGRESS **LED**

LED FEATURES

- 120V AC Replaceable LED module
- 624 lumens, 66 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life
- Dimmable to 10% with Triac and ELV dimmers

Z-1040

An LED outdoor wall sconce designed to provide a distinctive modern flair. Z-1040 features a linear frame with a central illuminated dome for both functional and artful illumination. ADA compliant. Meets California Title 24 high efficacy requirements for outdoor use only.

FINISHES

- Black - 031



MEDIUM WALL LANTERN

P560054-031-30 Black
8-1/2" W., 22" ht.,
Extends 3-5/8". H/CTR 4-1/4".
One 3000K 9w LED module
included.



LED FEATURES

- 120V AC Replaceable LED module
- 670 lumens, 71 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life
- Dimmable to 10% with Triac and ELV dimmers



P560054-031-30

GEOMETRIC

Geometric lanterns feature an artfully crafted glass enclosure with a pleasing arrangement of contrasting seeded and water glass panels. ADA compliant.

FINISHES

- Architectural Bronze - 129

SMALL WALL LANTERN

P560047-129 Architectural Bronze
6" W., 8" ht.
Extends 4". H/CTR 4".
One medium base lamp,
60w max.

MEDIUM WALL LANTERN

P560048-129 Architectural Bronze
6" W., 16" ht.
Extends 4". H/CTR 4-1/4".
Two medium base lamps,
each 60w max.



P560047-129



P560048-129

WESTPORT

Classic styling with detailed touches. Clear seeded glass with die-cast aluminum frames and durable powder coat finish.

POST LANTERN

P5458-20 Antique Bronze

P5458-31 Black

11" dia., 19" ht.

Fits 3" post (sold separately).

One medium base lamp,

100w max.

FINISHES

● Antique Bronze - 20

● Black - 31



P5458-20



P5458-31

CERAMIC SCONCE

A white ceramic outdoor sconce can be painted to easily blend with your home's exterior. Dark Sky compliant.

MEDIUM WALL LANTERN

P560044-030 White

8-1/4" W., 10" ht.

Extends 5-3/4". H/CTR 4-1/8".

One medium base lamp,

100w max.

FINISH

○ White - 030



P560044-030

POST

FINISH

● Black - 31

OUTDOOR POST

P540005-031 Black

Fluted aluminum post.

3" dia., 84" ht.



P540005-031

Detail of P540005-031



LED LINEAR

FINISH

○ White - 30

LINEAR CLOUD

P7279-3040K8 White
51" L., 10-1/4" W., 3-3/16" ht.
One 4000K 36W max. LED
included.



P7279-3040K8

PROGRESS **LED**

LED FEATURES

- 120V / 50Hz/60Hz
- 3500 lumens,
- 4000K color temperature;
80+ CRI
- 50,000 hr. life
- Dimmable to 10% with Triac
and ELV dimmers

LED SURFACE MOUNT

FINISHES

- Antique Bronze - 020
- White - 028
- Black - 031
- Metallic Gray -082

LED SLIM-LINE SURFACE MOUNT

P8108-20-30K Antique Bronze
P8108-28-30K White
P8108-31-30K Black
P8108-82-30K Metallic Gray
5-1/2" dia., 3/4" ht.,
Overall ht. 2-11/16" ht.
One 11.75w LED module included.
685 lumens, 58 lumens per watt.



LED FEATURES

- Wet location listed
- 90+ CRI
- 120v input voltage
- 50,000 hour life
- 58 Lumens per watt
- Requires minimum 2"
deep J-box

PROGRESS **LED**



P8108-20-30K



P8108-31-30K



P8108-28-30K



P8108-82-30K



P8757-141

CHAIN

FINISH

● Galvanized Finish - 141

CHAIN

P8757-141 Galvanized Finish
10' of 9 gauge chain.
10' L., 1" W.

LED RETROFIT SQUARES

Square LED downlight is ideal for use in both new construction as well as remodel/retrofit. The sleek geometric shape provides a high end appeal for residential and commercial spaces and installs into round housing. Available in White, Black, Bronze and Brushed Nickel trim.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- White - 28
- Black - 31

LED FEATURES

- Wet location listed
- 120v AC
- 3000K color temperature; 90+ CRI
- Dimmable to 10% brightness with Triac/Forward Phase type dimmers
- 50,000 hr. life



4" SQUARE

P8180-09-30K Brushed Nickel
P8180-20-30K Antique Bronze
P8180-28-30K Satin White
P8180-31-30K Black
 4-3/4" sq., 3-5/8" ht.
 One 3000K 9W max.
 690 lumens, 76 lumens/watt
 LED module included.
 JA8 Compliant



P8180-09-30K



P8180-20-30K



P8180-28-30K



P8180-31-30K

5" SQUARE

P8161-09-30K Brushed Nickel
P8161-20-30K Antique Bronze
P8161-28-30K Satin White
P8161-31-30K Black
 5-7/8" sq., 4-1/8" ht.
 One 3000K 9W max.
 670 lumens, 74 lumens/watt
 LED module included.
 JA8 Compliant



P8161-09-30K



P8161-20-30K



P8161-28-30K



P8161-31-30K

6" SQUARE

P8171-09-30K Brushed Nickel
P8171-20-30K Antique Bronze
P8171-28-30K Satin White
P8171-31-30K Black
 7" sq., 4-1/8" ht.
 One 3000K 9W max.
 745 lumens, 82 lumens/watt
 LED module included.
 JA8 Compliant



P8171-09-30K



P8171-20-30K



P8171-28-30K



P8171-31-30K

LED FLEX TRACK

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

LED FEATURES

- 120v input voltage
- 7w 624 lumens, 66 lumens/watt
- 2700K color temperature; 90+ CRI
- Flicker free dimming down to 10% with many Triac or forward phase dimmers
- 50,000 hr. life



FLEX



P9021-09-27K9



P9021-20-27K9



P9031-09-27K9



P9031-20-27K9

P9021-09-27K9 Brushed Nickel
P9021-20-27K9 Antique Bronze
 2-7/8" W., 7-7/8" ht.,
 Extends 2-7/8".
 One 2700K 7W max.



P9031-09-27K9 Brushed Nickel
P9031-20-27K9 Antique Bronze
 2 1/2" W., 7 7/8" ht., Extends 3".
 One 2700K 7W max.



FLEX ACCESSORIES



P9010-09



P9010-20



P9001-09



P9001-20

FLEX TRACK KIT

P9010-09 Brushed Nickel
P9010-20 Antique Bronze
 10' of 120v Line Voltage flexible track with 4 support stems, 2 end caps, power feed and mounting hardware.
 10' L, 1/4" W., 7/8" ht.,
 Extends 12-3/4".

STRAIGHT CONNECTOR

P9001-09 Brushed Nickel
P9001-20 Antique Bronze
 5/8" W., 1 1/4" ht., Extends 3-1/8".

LED TRACK

Available in two sizes - 4' and 8' - LED track lighting system accommodates decorative track head styles to provide general, accent or spotlight lighting to a variety of interior spaces. Use only with P9054, P9038, P9055 track.

FINISHES


- Brushed Nickel - 09
- White - 28
- Black - 31





LED FEATURES

- 120v input voltage
- 7w 624 lumens, 66 lumens/watt
- 10w 444 lumens, 63 lumens/watt
- 2700K color temperature; 90+ CRI
- Flicker free dimming down to 10% with many Triac or forward phase dimmers
- 50,000 hr. life

MESH


P9061-09-27K9 Brushed Nickel
P9061-28-27K9 Satin White
P9061-31-27K9 Black
 2-7/8" W., 6-3/8" ht.,
 Extends 3-1/8".
 One 2700K 7W max. 





P9062-09-27K9 Brushed Nickel
P9062-28-27K9 Satin White
P9062-31-27K9 Black
 3 3/8" W., 6 7/8" ht.,
 Extends 2-7/8".
 One 2700K 10W max.  



STEP

P9081-28-27K9 Satin White
P9081-31-27K9 Black
 2-7/8" W., 6-1/2" ht.,
 Extends 2-3/4". 



P9082-28-27K9 Satin White
P9082--31-27K9 Black
 3-1/4" W., 7" ht.,
 Extends 3-1/4".
 One 2700K 10W max.  



GIMBAL

P9071-09-27K9 Brushed Nickel

P9071-28-27K9 Satin White

P9071-31-27K9 Black

2-1/2" W., 6-7/8" ht.,

Extends 3".

One 2700K 7W max.



P9072-09-27K9 Brushed Nickel

P9072-28-27K9 Satin White

P9072-31-27K9 Black

3-1/4" W., 8 5/8" ht.,

Extends 3-3/4".

One 2700K 10W max.

JA8 Compliant



P9071-28-27K9



P9071-31-27K9



P9071-09-27K9



P9072-28-27K9



P9072-31-27K9



P9072-09-27K9

LED TRACK ACCESSORIES

48" TRACK

P9054-28 Satin White

P9054-31 Black

1-3/8" W., 3/4" ht., Extends 48".



P9054-28

P9054-31

P9058-28

P9058-31

96" TRACK

P9058-28 Satin White

P9058-31 Black

1-3/8" W., 3/4" ht., Extends 96".

FLOATING POWER CANOPY

P9051-28 Satin White

P9051-31 Black

4-1/4" W., 1 3/8" ht., Extends 4-1/4".



P9051-28

P9051-31

P9055-01

STRAIGHT CONNECTOR

P9055-01 Unfinished

1-1/2" W., 3/4" ht., Extends 3-1/4".

LED LAMPS



LED LAMP 9A19LED27/G4

9.5W A19
LED E26 medium base lamp.
2700K. Please note this product
is not dimmable.



LED LAMP E10A19DLED927/JA8

10W A19
LED E26 medium base lamp.
2700K. JA8E Compliant for
enclosed fixtures.



LED LAMP F4B10DLED927/JA8

4W B10
LED E12 candelabra base filament
lamp. 2700K. JA8 Compliant.



LED LAMP F8.5A19DLED927/JA8

8.5W A19
LED E26 medium base filament
lamp. 2700K. JA8 Compliant.



PRODUCT INDEX

P2000

P2158	87
P2159	87
P2160	87
P2775	86
P2776	86
P2777	86

P3000

P300045	78, 79
P300046	78, 79
P300047	78, 79
P300048	78, 79
P300049	80, 81
P300050	80, 81
P300051	80, 81
P300052	80, 81
P300057	68
P300057	84, 85
P300058	84, 85
P300059	84, 85
P300060	84, 85
P300061	39
P300062	39
P300063	37
P300064	37
P300065	37
P300066	63
P300066	77
P300067	77
P300068	77
P300069	77
P30039	83
P30040	83
P30041	83
P30042	82
P30043	82
P30044	82
P3423	65

P3424	65
P3450	65
P350021	21
P350021	21
P350022	59, 60
P350023	75
P350024	75
P350029	11
P350039	59, 60
P350046	74
P350047	69
P350048	69
P350055	74
P350056	74
P350059	63
P350062	69
P350063	69
P3755	72

P4000

P400002	19
P400003	19
P400045	21
P400046	21
P400047	59, 60
P400048	59, 60
P400049	11
P400050	61
P400051	23
P400052	68
P400053	67
P400054	67
P400055	63
P4318	65
P4319	65
P4726	65
P4732	71
P4762	71
P4763	22

P5000

P500038	15
P500039	15
P500040	15
P500041	59, 60
P500042	19
P500043	11
P500046	25
P500047	25
P500048	17
P500049	17
P500050	67
P500051	73
P500052	73
P500053	73
P500054	68
P500055	72
P500056	63
P5170	65
P5346	13
P5400	90
P540005	98
P540012	88, 89
P540013	41
P540014	91
P540015	91
P5458	98
P5500	90
P550011	88, 89
P550012	88, 89
P550013	41
P550014	91
P550015	91
P550016	91
P550017	91
P550018	42
P550019	92
P550024	41
P560035	95
P560036	88, 89

P560037	88, 89
P560038	88, 89
P560039	41
P560040	41
P560041	41
P560042	91
P560043	91
P560044	91
P560045	95
P560046	95
P560047	97
P560048	97
P560049	92
P560050	92
P560051	96
P560052	93
P560053	93
P560054	97
P560055	94
P560056	96
P5605	90
P5610	90
P5611	90
P5613	90

P6000

P6426	94
-------	----

P7000

P710002	19
P710012	59, 60
P710013	11
P710014	76
P710015	76
P710016	29
P710017	35
P710018	33
P710019	33
P710021	17

P710022	27
P710023	27
P710024	27
P710025	31
P7198	13
P7279	99

P8000

P8108	99
P8161	100
P8171	100
P8180	100

P9000

P9001	101
P9010	101
P9021	101
P9031	101
P9051	103
P9054	103
P9055	103
P9058	103
P9061	102
P9062	102
P9071	103
P9072	103
P9081	102
P9082	102

LAMPS

9A19LED27/G4	104
E10A19DLED927/JA8	104
F4B10DLED927/JA8	104
F8.5A19DLED927/JA8	104

Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.

UL Listed or Classified or CSA Certified unless otherwise noted.

Bulbs not included with fixtures unless specified. Specifications subject to change without notice.

Metal finishes not specified as "solid" have quality plated or painted finishes.

Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.

© Progress Lighting 2017
All rights reserved.
International Copyright Secured.

PROGRESS LIGHTING

701 Millennium Boulevard
Greenville, South Carolina
29607



PROGRESSLIGHTING.COM





PROGRESS LIGHTING

701 Millennium Boulevard
Greenville, South Carolina
29607

progresslighting.com

