



KALCO®

Handcrafted Since 1980™

Kalco Classics and Options

Over the past 37 years, many of our collections have become staples to the Kalco product line. These are designs that define the origins of Kalco as they have stood the test of time and continue to be top sellers. The collections feature a level of workmanship that is rarely seen in the marketplace today. From the Hand Forged Ironwork, to the Hand Applied Finishes, each piece is a true work of art.

Many of these collections also allow designer flexibility in terms of Finish Options, Glass and Shade Options, including fabric and natural shells. In fact, many of the finishes are Hand Applied at our facility in Las Vegas, Nevada – USA Proud!

Each family is clearly noted to advise what options (if any) are Standard, and which options (if any) are Upgrade, meaning upcharges apply. It is also important to note that the process to configure your product may take 3 to 10 working days!

When ordering optional items, please be sure to follow these easy instructions:

1. Select 4 or 6 digit model number (ie: 4207)
 2. Select Finish (ie: AC)
 3. Select Glass or Shade Option (ie:8045)
- Complete Model #: 4207AC/8045

2. Select Finish (ie: AC)
Antique Copper



3. Select Glass or Shade Option
(ie:8045)



1. Select 4 or 6 digit model number (ie: 4207)



Kalco Ordering Instructions:

1. Select 4 or 6 digit model number (ie. 506771)
2. Select Finish (ie. BZG)

example: 506771PS



Unless otherwise noted, standard chain and wire lengths are:

1. Fixtures up to 32" diameter- 4 ft. chain with 8 ft. wire.
2. Fixtures over 32" diameter- 8 ft. chain with 13 ft. wire.
3. Fixture heights DO NOT include the canopy and the minimum chain required.

LED Lamping Option:

Many of our fixtures are supplied with G-9 Xenon lamping. We do offer G-9 LED Lamps, Model # LEDG9/3.5W, sold in 6 packs. (3 watt/2700K/120V/380 Lumens)



Table of Contents

Aegean	pg.64
Americana	pg.104
Aspen	pg.128
Atlantis	pg.170
Bedford	pg.100
Copenhagen	pg.68
Cordova	pg.126
Durango	pg.118
G-Cleft	pg.60
Grande	pg.72
Grayson	pg.19
Ibiza	pg.24
Mirabelle	pg.44
Monaco	pg.90
Morris	pg.96
Napa	pg.136
Newport	pg.56
Oakham	pg.122
Oxford	pg.94
Palladium	pg.5
Ponderosa	pg.155
Potracks	pg.174
Rodeo Drive	pg.110
Santa Barbara	pg.36
Somerset	pg.50
Tribeca	pg.8
Vine	pg.142
Whitfield	pg.76
Windsor	pg.82

Sections

Hand Painted Finish	pg. 180
Natural Bowls	pg. 179
Natural Side Glass	pg. 178
Shades	pg. 176
Index	pg. 181

PALLADIUM

Classically Shaped Hand Forged Wrought Iron in a trendy Pearl Silver (PS) finish with removable crystal drops.



506772 PS
3 TIER (5 + 5 + 5 LIGHT) CHANDELIER
D: 32 H: 64 OAH: 160
(15) 60W CAND.

STANDARD FINISH OPTIONS

PEARL SILVER (PS)



UPGRADE FINISH OPTIONS FEES APPLY


BLACK (B)




COUNTRY IRON (CI)



FRENCH CREAM (FC)



MODERN GOLD (MG)



TORTOISE SHELL (TO)





506771 PS
6 LIGHT CHANDELIER
D: 27 H: 37 OAH: 85
(6) 60W CAND.



506722 PS
2 LIGHT WALL BRACKET
W: 14 H: 28 E: 8
(2) 60W CAND.



506721 PS
1 LIGHT WALL BRACKET
W: 4.5 H: 28 E: 9.5
(1) 60W CAND.

Tribeca

Art Nouveau inspired Hand Forged Wrought Iron swirls in a standard **Antique Copper (AC)** or **Pearl Silver (PS)** Finishes paired with Kalco's handcrafted Frost or Antique Glass. Upgrade Hand Painted Finish: pg. 180

4299 PS/FROST
16 LIGHT FOYER CHANDELIER
D: 48 H: 72 OAH: 168
(16) 100W MED.






STANDARD FINISH OPTIONS

ANTIQUE COPPER (AC)

PEARL SILVER (PS)



STANDARD GLASS OPTIONS

ANTIQUE

FROSTED



UPGRADE FINISH OPTIONS **(FEES APPLY)**



BLACK (B)

COUNTRY IRON (CI)

FRENCH CREAM (FC)

MODERN GOLD (MG)

TORTOISE SHELL (TO)



FORGING DETAIL



4289 PS/FROST
6 LIGHT CHANDELIER
D: 32 H: 38 OAH: 86
(6) 100W MED.



4287 PS/FROST
23" PENDANT
D: 23 H: 26 OAH: 74
(3) 100W MED.



4306 PS/FROST
34" PENDANT
D: 34 H: 40.5 OAH: 136.5
(5) 100W MED.



4297 PS/FROST
37" PENDANT
D: 37 H: 46.5 OAH: 142.5
(6) 100W MED.





4296 AC/FROST
16" SEMI FLUSH
D: 16 H: 7
(3) 60W MED



4288 AC/FROST
21" SEMI FLUSH
D: 21 H: 15
(3) 100W MED



4309 AC/FROST
9 LIGHT CHANDELIER
D: 30 H: 31 OAH: 79
(9) 60W G9
G9 LAMPS INCLUDED
FEATURES MINI-GLASS



Tribecca

4308 AC/FROST
6 LIGHT CHANDELIER
D: 25 H: 29 OAH: 77
(6) 60W G9
G9 LAMPS INCLUDED
FEATURES MINI-GLASS



4154 AC/FROST
ADA WALL SCONCE
W: 14.5 H: 15 E:4
(1) 100W MED.




4303 AC/FROST
ADA WALL SCONCE
W: 14 H: 7.5 E:4
(1) 100W MED.




4290 AC/FROST
12 LIGHT FOYER CHANDELIER
D: 36 H: 60 OAH: 156
(12) 100W MED.





4300 AC/FROST
3 LIGHT ISLAND
L: 37 H: 30 W:13 OAH: 78
(3) 100W MED.



4302 AC/FROST
24" FOYER PENDANT
D: 24 H: 36 OAH: 78
(3) 100W MED.
EACH SHADE INCLUDES 6", 12" AND 24" STEM
INCLUDES 10" DIA. LARGE GLASS
FEATURES LARGE GLASS



4305 AC/FROST
1 LIGHT WALL BRACKET
W: 6.5 H: 39 E:11
(1) 100W MED.



4301 PS/ANTQ
 10" LARGE PENDANT
 D: 10 H: 36 OAH: 78
 (1) 100W MED.
 INCLUDES (1) 6", 12", 24" STEM
 FEATURES LARGE GLASS

1851 AC/ANTQ
 SMALL PENDANT
 D: 7 H: 36 OAH: 62
 (1) 100W MED.

INCLUDES (1) 6", 12", 24" STEM



4298 AC/ANTQ
 3 LIGHT CHANDELIER
 D: 26 H: 37 OAH: 85
 (3) 100W MED.



4285 AC/FROST
 1 LIGHT WALL BRACKET
 W: 13 H: 20 E:11
 (1) 100W MED.



4286 AC/FROST
 2 LIGHT WALL BRACKET
 W: 20 H: 21 E:12
 (2) 100W MED.

4281 AC/FROST
1 LIGHT BATH
W: 8.5 H: 11.5 E: 10.5
(1) 100W MED.



4282 AC/FROST
2 LIGHT BATH
W: 16 H: 12 E: 10
(2) 100W MED.



4283 AC/FROST
3 LIGHT BATH
W: 24 H: 12 E: 10
(3) 100W MED.



4284 AC/FROST
4 LIGHT BATH
W: 34 H: 12 E: 10
(4) 100W MED.

Grayson



GRAYSON COLLECTION

STANDARD FINISH OPTIONS

HEIRLOOM BRONZE (HB)



PEARL SILVER (PS)



UPGRADE FINISH OPTIONS (FEES APPLY)

BLACK (B)



MODERN GOLD (MG)




COUNTRY IRON (CI)



TORTOISE SHELL (TO)



FRENCH CREAM (FC)



GRAYSON

Subtle Fleur de Lys inspired design paired with sophisticated Clear Seeded Glass in standard Heirloom Bronze (HB) or Pearl Silver (PS) finishes.
Hand Painted Finish Upgrade Options: pg. 180

STANDARD GLASS
CLEAR SEEDED 1100



2673 PS/1100
6 LIGHT OVAL CHANDELIER
W: 15 L: 34 H: 23.5 OAH: 40.5
(6) 60W CAND.



2671 PS/1100
4 LIGHT CHANDELIER
D: 18 H: 19.5 OAH: 67.5
(4) 60W CAND.



2675 PS/1100
2 TIER (8 + 4 LIGHT) CHANDELIER
D: 31 H: 29 OAH: 77
(12) 60W CAND.





2669 HB/1100
4 LIGHT ISLAND
W: 4 L: 32 H: 19 OAH: 40
(4) 60W CAND.

2674 HB/1100
6 LIGHT ROUND CHANDELIER
D: 25 H: 26 OAH: 74
(6) 60W CAND.



Grayson

2660 HB/1100
1 LIGHT MINI PENDANT
W: 4 L: 8 H: 20 OAH: 68
(1) 60W CAND.





2661 PS/1100
 1 LIGHT ADA SCONCE
 W: 6.5 H: 14 E: 4
 (1) 60W CAND.



2665 PS/1100
 1 LIGHT SCONCE
 W: 6.5 H: 19 E: 6
 (1) 60W CAND.



2662 PS/1100
 2 LIGHT BATH
 W: 17 H: 16 E: 6
 (2) 60W CAND.



2663 PS/1100
 3 LIGHT BATH
 W: 22 H: 16 E: 6
 (3) 60W CAND.

2664 PS/1100
 4 LIGHT BATH
 W: 31 H: 16 E: 6
 (4) 60W CAND.



IBIZA



IBIZA COLLECTION STANDARD FINISH OPTIONS

ANTIQUE COPPER (AC)

PEARL SILVER(PS)



STANDARD GLASS BOWLS

ALAB


ANTQ

BLZ

ECRU

GLDSTRK

SMKTAUP



STANDARD GLASS & SHADE OPTIONS

SEE PAGE 178 FOR STANDARD SIDE GLASS

SEE PAGE 176 FOR FABRIC SHADES

IBIZA COLLECTION UPGRADE FINISH OPTIONS (Fees Apply)


BLACK (B)

COUNTRY IRON (CI)

FRENCH CREAM (FC)

MODERN GOLD (MG)

TORTOISE SHELL (TO)



UPGRADE NATURAL BOWLS (Fees Apply)

ART

BUDDHA

PENSH

IRSH

VIC



UPGRADE NATURAL SIDE GLASS OPTIONS (Fees Apply)

SEE PAGE 178 FOR NATURAL SIDE GLASS OPTIONS

SEE PAGE 176 FOR FABRIC SHADES

Ibiza

Hand Forged Wrought Iron in a standard
Antique Copper (AC) or Pearl Silver (PS)

finishes paired with Kalco's Options:

Upgrade Hand Painted Finish: pg. 180

Upgrade Natural Glass & Bowls: pg. 179

Fabric Shade Options: pg. 176

Glass Shade Options: pg. 176

4274 PS/1577
20 LIGHT CHANDELIER
D: 50.5 H: 56 OAH: 152
(20) 100W MED.



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM

CANOPY DETAIL



4039 AC/1577
12 LIGHT FOYER CHANDELIER
D: 29 H: 51 OAH: 147
(12) 100W MED.



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM

800.525.2655



4257 AC/1502
1 LIGHT WALL BRACKET
W: 6 H: 21 E: 11.5
(1) 40W MED.



4265 AC/PENSH
1 LIGHT WALL BRACKET
W: 6 H: 21 E: 10.5
(1) 60W CAND.
SHOWN WITH UPGRADE PENSHELL



4259 PS/1577
2 LIGHT WALL BRACKET
W: 16 H: 21 E: 10.5
(2) 40W MED.

WHEN USING PEN SHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM



4258 AC
2 LIGHT WALL BRACKET
W: 16 H: 21 E: 10.5
(2) 60W CAND.



4256 PS
1 LIGHT WALL BRACKET
W: 6 H: 21 E: 10.5
(1) 60W CAND.

WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM

4038 PS
12 LIGHT FOYER CHANDELIER
D: 29 H: 51 OAH: 147
(12) 60W CAND.



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM



4273 AC
20 LIGHT CHANDELIER
D: 50.5 H: 56 OAH: 152
(20) 60W CAND.



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM

4261 AC/S205
8 LIGHT CHANDELIER
D: 29.5 H: 33.5 OAH: 81.5
(8) 60W CAND.
SHOWN WITH MICA SHADE UPGRADE



4263 AC
16 LIGHT CHANDELIER
D: 50 H: 43 OAH: 139
(16) 60W CAND.



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM

4032 PS
12 LIGHT CHANDELIER
D: 37 H: 35 OAH: 131
(12) 60W CAND.



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM

IBIZA



4243 AC/ANTQ
45" PENDANT
D: 45 H: 41 OAH: 137
(6) 100W MED.



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM



4267 PS/ANTQ
32.5" PENDANT
D: 32.5 H: 31 OAH: 79
(5) 60W MED.



4269 AC/ANTQ
23" SEMI FLUSH
D: 23 H: 14
(3) 60W MED.



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM



Santa Barbara

SANTA BARBARA COLLECTION OPTIONS

STANDARD FINISH & GLASS

PEARL SILVER (PS)




TORTOISE (TO)




UPGRADE FINISH & GLASS (Fees Apply)

BLACK (B)




COUNTRY IRON (CI)



FRENCH CREAM (FC)




MODERN GOLD (MG)




STANDARD GLASS BOWLS

WHITE ALABASTER
(ALAB)



ECRU
(ECRU)

ANTIQUE FILIGREE
(ANTQ)




GOLD-STREAKED
AMBER
(GLDSTRK)

BLAZE
(BLZ)




SMOKED TAUPE
(SMKTAUP)




UPGRADE GLASS BOWLS (Fees Apply)

ART NOUVEAU
PENSHELL
(ART)



IRIDESCENT SHELL
(IRSH)



BUDDHA LEAF
(BUDDHA)



VICTORIAN
PENSHELL
(VIC)



PENSHELL
(PENSH)



SEE PAGE 178 FOR STANDARD SIDE GLASS

SEE PAGE 178 FOR UPGRADE SHELL FOR BATH ITEMS

SEE PAGE 176 FOR FABRIC SHADES

Santa Barbara

Colonial Mission inspired Hand Forged Wrought Iron in a standard Pearl Silver (PS) or Tortoise (TO) Finishes paired with Kalco's optional Glass Shades.

Upgrade Hand Painted Finish: pg. 180

Upgrade Natural Glass & Bowls: pg. 179

Fabric Shade Options: pg. 176

Glass Shade Options: pg. 176

810 TO/S197
2 LIGHTMIRROR
W: 42.5 H: 43 E: 10
(2) 40W CAND.

SHOWN WITH OPTIONAL SHADES



3163 TO
2 TIER (12 + 6) LIGHT CHANDELIER
D: 44 H: 50 OAH: 144
(18) 60W CAND.



3164 TO
3 TIER (5+5+5) LIGHT FOYER
D: 34 H: 48 OAH: 146
(15) 60W CAND.



814 TO
WALL SCONCE
W: 19.5 H: 36 E: 10
(2) 60W CAND.



3272 TO
2 LIGHT WALL SCONCE
W: 12 H: 14 E: 8
(2) 60W CAND.

3166 TO
5 LIGHT CHANDELIER
D: 22 H: 28 OAH: 76.5
(5) 60W CAND.



3161 TO
8 LIGHT CHANDELIER
D: 31 H: 36 OAH: 84
(8) 60W CAND.

3177 PS/ALAB
26" PENDANT
D: 26 H: 28 OAH: 76
(3) 60W MED.



3274 PS/1219
2 LIGHT WALL BRACKET
W: 12 H: 14 E: 8
(2) 100W MED.

SANTA BARBARA

3172 PS/ALAB
19 SEMI FLUSH
D: 19 H: 14
(3) 60W MED.



1855 PS/1219
1 LIGHT MINI PENDANT
D: 9.5 H: 26 OAH: 74
(1) 40W MED.



3541 TO/1219
1 LIGHT BATH
W: 6 H: 12 E: 10
(1) 100W MED.



3542 TO/1219
2 LIGHT BATH
W: 18 H: 12 E: 10
(2) 100W MED.



3543 TO/1219
3 LIGHT BATH
W: 24.5 H: 12 E: 10
(3) 100W MED.



3544 TO/1219
4 LIGHT BATH
W: 26.5 H: 12 E: 10
(4) 100W MED.




MIRABELLE COLLECTION STANDARD FINISH & GLASS

SIDE GLASS OPTIONS

ANTIQUÉ COPPER (AC)



MODERN GOLD



1339



BOWLS

WHITE ALABASTER (ALAB)



1356



ANTIQUÉ FILIGREE (ANTQ)



1479



BLAZE (BLZ)



1576




ECRU (ECRU)




1577



GOLD-STREAKED AMBER (GLDSTRK)



SMOKE TAUPE (SMKTAUP)




MIRABELLE COLLECTION UPGRADE FINISH & BOWL OPTIONS (Fees Apply)


BLACK (B)



COUNTRY IRON (CI)



FRENCH CREAM (FC)



PEARL SILVER (PS)



TORTOISE SHELL (TO)




ART NOUVEAU
PENSHELL
(ART)



BUDDHA LEAF
(BUDDHA)




PENSHELL
(PENSH)



IRIDESCENT SHELL
(IRSH)



VICTORIAN
PENSHELL
(VIC)



MIRABELLE

Stunning Hand Forged Wrought Iron featuring classic Victorian shapes in Antique Copper (AC) or Modern Gold (MG) finishes paired with Kalco's curated glass.

Upgrade Hand Painted Finish: pg. 180

Upgrade Natural Glass & Bowls: pg. 179

5189 AC/1577
3 TIER (4+4+4 LIGHT) FOYER
D: 48 H: 83.5 OAH: 179.5
(12) 100W MED.



CANOPY WITH STARTER LINK DETAIL



5188 AC/1577
8 LIGHT CHANDELIER
D: 41 H: 50 OAH: 146
(8) 100W MED.



5198 MG/1577
5 LIGHT CHANDELIER
D: 28.5 H: 32 OAH: 80
(5) 100W MED.



5181 MG/ECRU
31" SEMI FLUSH
D: 31 H: 19
(5) 100W MED.



5197 MG/ECRU
58" PENDANT
D: 58 H: 69.5 OAH: 165.5
(6) 60W MED.



*NOTE: STANDARD GLASS OPTIONS
FOR ITEM 5197 ARE ECRU AND SMOKED TAUPE*



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM

5194 AC/BUDDHA
40" PENDANT
D: 40 H: 49 OAH: 145
(6) 40W MED.
*SHOWN WITH UPGRADE
NATURAL BOWL*



5196 AC/ ANTQ
50" PENDANT
D: 50 H: 64 OAH: 160
(6) 100W MED.



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM



STANDARD FINISH & SHELL

TORTOISE (TO)



PENSHELL

UPGRADE FINISH (Fees Apply)

BLACK (B)


COUNTRY IRON (CI)

FRENCH CREAM (FC)



MODERN GOLD (MG)


PEARL SILVER (PS)



4975 TO/PENSH
1 LIGHT MINI PENDANT
D: 8.5 H: 18 OAH: 66
(1) 40W MED.

Somerset

4970 TO/PENSH
6 ARM CHANDELIER
D: 35 H: 32 OAH: 128
(6) 40W MED. + (2) 60W MED



4976 TO/PENSH
6 LIGHT CHANDELIER
D: 30 H: 33.5 OAH: 81.5
(6) 40W MED.



4971 TO/PENSH
9 LIGHT CHANDELIER
D: 38 H: 46.5 OAH: 142.5
(9) 40W MED.



4967 TO/PENSH
32" PENDANT
D: 32 H: 33 OAH: 129
(5) 60W MED.



4968 TO/PENSH
48" PENDANT
D: 48 H: 46 OAH: 142
(6) 60W MED.



4966 TO/PENSH
21" CONVERTIBLE SEMI FLUSH
D: 21.5 H: 14 OAH: 62
(3) 60W MED.



SOMERSET

4969 TO/PENSH
6 + 2 LIGHT CHANDELIER
D: 34 H: 32 OAH: 128
(6) 60W CAND. + (2) 60W MED.



4960 TO/PENSH
FOYER PENDANT
D: 24 H: 56 OAH: 104
(6) 60W CAND.



4961 TO/PENSH
1 LIGHT WALL BRACKET
W: 6 H: 12 E: 10
(1) 40W MED.



4965 TO/PENSH
3 LIGHT WALL BRACKET
W: 14.5 H: 24 E: 4
(3) 25W CAND.




SATIN BRONZE (SZ)

TEA STAINED & WATER GLASS

Newport

Hand Forged Wrought Iron in a stylish Satin Bronze (SZ) finish with Tea Stained interior glass and outer water glass.



CANOPY DETAIL




5762 SZ
5 LIGHT CHANDELIER
D: 25 H: 27.5 OAH: 75.5
(5) 100W MED.



5764 SZ
2 TIER (6 + 3 LIGHT) CHANDELIER
D: 40.5 H: 40.5 OAH: 136.5
(9) 100W MED.





5750 SZ
1 LIGHT MINI PENDANT
D: 7.5 H: 29 OAH: 52
(1) 100W MED.
SUPPLIED WITH (1) 15" &
(2) 9" STEMS



5756 SZ
23" FLUORESCENT FLUSH MOUNT
D: 23 H: 7
(2) 13W CFL
CFL LAMPS INCLUDED



5763 SZ
5 LIGHT CHANDELIER
D: 32.5 H: 29.5 OAH: 125.5
(5) 100W MED.

NEWPORT



5755 SZ
ADA WALL SCONCE
W: 8 H: 12 E: 4
(1) 60W MED.



5751SZ
1 LIGHT BATH
W: 8 H: 13.5 E: 9
(1) 100W MED.



5752 SZ
2 LIGHT BATH
W: 18.5 H: 14 E: 10
(2) 100W MED.



5753 SZ
3 LIGHT BATH
W: 23.5 H: 14 E: 10
(3) 100W MED.



G - Cleft

STANDARD FINISH OPTIONS
 ANTIQUE COPPER (AC) PEARL SILVER (PS)



STANDARD GLASS
 ANTIQUE FILIGREE
 (ANTQ)




G-CLEFT COLLECTION UPGRADE HAND-PAINTED FINISH & BOWL OPTIONS (Fees Apply)


BLACK (B)




COUNTRY IRON (CI)



FRENCH CREAM (FC)



MODERN GOLD (MG)



TORTOISE SHELL (TO)




ART NOUVEAU
PENSHELL
(ART)



BUDDHA LEAF
(BUDDHA)



PENSHELL
(PENSH)



IRIDESCENT SHELL
(IRSH)



VICTORIAN
PENSHELL
(VIC)



G - Cleft

Musically inspired Hand Forged Wrought Iron swirls cradles Kalco's Antique Filigree Glass featured in standard Antique Copper (AC) or Pearl Silver (PS) Finishes.

Upgrade Hand Painted Finish: pg. 180

Upgrade Natural Bowls Options: pg. 179

4067 AC/ ANTQ
29" PENDANT
D: 29 H: 32 OAH: 81
(6) 100W MED.



G - CLEFT

4066 AC/ ANTQ
25" PENDANT
D: 25 H: 26.5 OAH: 74.5
(5) 100W MED.



4065 AC/ ANTQ
20" PENDANT
D: 20.5 H: 25 OAH: 73
(3) 100W MED.



AEGEAN

Hand Forged Wrought Iron in a classical Tawny Port (TP) or trendy Pearl Silver (PS) finishes with Kalco's stunning glass bowl options.

Upgrade Hand Painted Finish: pg. 180


Upgrade Natural Bowls Options: pg. 179



AEGEAN COLLECTION

STANDARD FINISH & BOWL OPTIONS

PEARL SILVER (PS)



WHITE ALABASTER (ALAB)



ANTIQUE FILIGREE (ANTQ)



TAWNY PORT (TP)




BLAZE (BLZ)



ECRU (ECRU)



GOLD-STREAKED AMBER (GLDSTRK)




SMOKE TAUPE (SMKTAUP)



UPGRADE FINISH & BOWL OPTIONS (Fees Apply)

BLACK (B)




ART NOUVEAU PENSHELL (ART)




COUNTRY IRON (CI)



BUDDHA LEAF (BUDDHA)




FRENCH CREAM (FC)



PENSHELL (PENSH)



MODERN GOLD (MG)



IRIDESCENT SHELL (IRSH)



TORTOISE SHELL (TO)



VICTORIAN PENSHELL (VIC)





5457 PS/ALAB
23" SEMI FLUSH
D: 23 H: 14.5
(3) 60W MED.

5459 PS/ALAB
40" PENDANT
D: 40 H: 36.5 OAH: 132.5
(6) 100W MED.



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM

Aegean

5458 TP/ALAB
27" PENDANT
D: 27 H: 35 OAH: 83
(5) 60W MED.



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM

800.525.2655

COPENHAGEN

Sleek Hand Forged Wrought Iron in standard classic
Antique Copper (AC) or trendy Pearl Silver (PS).

Hand Painted Finish Upgrade Options: pg. 180

Standard Bowl Options: pg. 179


Upgrade Natural Bowl Options: pg. 179



COPENHAGEN COLLECTION

STANDARD FINISH & BOWL OPTIONS


ANTIQUE COPPER (AC)



WHITE ALABASTER (ALAB)



PEARL SILVER (PS)



ANTIQUE FILIGREE (ANTQ)




BLAZE (BLZ)



ECRU (ECRU)



GOLD-STREAKED AMBER (GLDSTRK)




SMOKE TAUPE (SMKTAUP)



UPGRADE FINISH & BOWL OPTIONS (Fees Apply)


BLACK (B)




ART NOUVEAU PENSHELL (ART)



COUNTRY IRON (CI)



BUDDHA LEAF (BUDDHA)




FRENCH CREAM (FC)



PENSHELL (PENSH)



MODERN GOLD (MG)



IRIDESCENT SHELL (IRSH)



TORTOISE SHELL (TO)



VICTORIAN PENSHELL (VIC)



4348 AC/ECRU
40" PENDANT
D: 40 H: 43 OAH: 139
(6) 100W MED.



4341 AC/1365
1 LIGHT WALL BRACKET
W: 5 H: 18 E: 10,5
(1) 100W MED.

SEE PAGE XX FOR SIDE GLASS OPTIONS

WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM



4346 PS/ALAB
20" SEMI FLUSH
D: 20.5 H: 14
(3) 60W MED.



4347 PS/ALAB
27" PENDANT
D: 27 H: 30.5 OAH: 78.5
(6) 100W MED.



4349 PS/ECRU
45" PENDANT
D: 45 H: 45.5 OAH: 141.5
(6) 100W MED.
*NOTE: STANDARD GLASS OPTIONS
FOR ITEM 4349 ARE ECRU AND SMOKED TAUPE
OR
ALL UPGRADE NATURAL OPTIONS
FEES APPLY*



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM

Grande

Archetectoral Pendants constructed with Hand Forged Wrought Iron in standard Antique Copper (AC) or Pearl Silver (PS).
Hand Painted Finish Upgrade Options: pg. 180
Standard Glass Options: pg. 179
Upgrade Natural Bowl Options: pg. 179

4842PS/ALAB
45" PENDANT
D: 45 H: 43 OAH: 139
(6) 100W MED.



4844PS/ALAB
24" SEMI FLUSH
D: 24 H: 15
(3) 60W MED.

WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM

GRANDE COLLECTION

STANDARD FINISH & BOWL OPTIONS

ANTIQUE COPPER (AC)




WHITE ALABASTER (ALAB)



ANTIQUE FILIGREE (ANTQ)

PEARL SILVER (PS)




BLAZE (BLZ)



ECRU (ECRU)



GOLD-STREAKED AMBER (GLDSTRK)




SMOKE TAUPE (SMKTAUP)



UPGRADE FINISH & BOWL OPTIONS (Fees Apply)


BLACK (B)




ART NOUVEAU PENSHELL (ART)




COUNTRY IRON (CI)



BUDDHA LEAF (BUDDHA)




FRENCH CREAM (FC)



PENSHELL (PENSH)



MODERN GOLD (MG)



IRIDESCENT SHELL (IRSH)



TORTOISE SHELL (TO)



VICTORIAN PENSHELL (VIC)



4846PS/ALAB
29" PENDANT
D: 29 H: 31 OAH: 79
(5) 60W MED.



4847PS/ALAB
35" PENDANT
D: 35 H: 36 OAH: 132
(5) 60W MED.



4845PS/ALAB
24" PENDANT
D: 24 H: 28 OAH: 76
(3) 60W MED.



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM

Grande

4842AC/ECRU
45" PENDANT
D: 45 H: 43 OAH: 139
(6) 100W MED.



4848AC/ECRU
22" SEMI FLUSH
D: 22 H: 11
(3) 100W MED.

HARDWARE DETAIL



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM

Whitfield

Exclusive Kalco Stained Mica Drum Shades with a Fleur-de-Lis pattern in Hand Forged Wrought Iron featured in Antique Copper (AC) Finish.





6583 AC
40 LIGHT OVAL CHANDELIER
L: 60 W: 42 H: 70 OAH: 143
(40) 25W CAND.



STANDARD SHADE
STAINED MICA



STANDARD FINISH
ANTIQUE COPPER (AC)



CANOPY DETAIL



6582 AC
20 LIGHT OVAL CHANDELIER
W: 47 H: 36.5 D:38 OAH: 164
(20) 25W CAND.



6579 AC
4 LIGHT OVAL PENDANT
W: 27 H: 34.5 D:19 OAH: 97
(4) 60W MED..



6584 AC
16 LIGHT CHANDELIER
D:30.5 H: 32.5 OAH: 80.5
(16) 25W CAND.



6577 AC
10 LIGHT ISLAND
L: 42 H: 34 W:13 OAH: 99
(10) 25W CAND.



6575 AC
ADA WALL SCNCE
W: 12 H: 26 E:4
(1) 40W CAND.
INCLUDES DIFFUSER
TOP: METAL
BOTTOM: GLASS



6578 AC
16" SEMI FLUSH
D: 16 H: 9
(3) 60W MED.



6570 AC
14" MINI PENDANT
D:14 H: 34 OAH: 76
(5) 25W CAND.



6585 AC
27.5" PENDANT
W: 27 D:34 OAH: 82
(4) 60W MED.

WHITFIELD

Windsor

Hand Forged Wrought Iron swirls in a standard **Antique Copper (AC)** paired with stained Mica Drum Shades or **Moon Silver (SV)** paired with silver stained Mica Drum Shades.




STANDARD FINISH SUPPLIED WITH
ANTIQUE COPPER (AC)

STANDARD SHADE
STAINED MICA SHADE

OR

STANDARD FINISH SUPPLIED WITH
MOON SILVER (SM)

STANDARD SHADE
STAINED SILVER MICA SHADE



5410 AC
24" FOYER PENDANT
D: 24 H: 55.5 OAH: 151.5
(12) 60W CAND.



5411 AC
3 TIER FOYER PENDANT
D: 45 H: 72 OAH: 168
(12) 60W MED.





5408 SV
16" SEMI FLUSH
D: 16 H: 9
(3) 60W MED.




5415 SV
27" PENDANT
D: 27.5 H: 34 OAH: 82
(4) 60W MED.



5412 SV
20 LIGHT OVAL CHANDELIER
L: 47 H: 36.5 W: 38 OAH: 164
(20) 25W CAND.



5413 AC
 2 TIER 40 LIGHT OVAL CHANDELIER
 L: 60 W: 42 H: 70 OAH: 143
 (40) 25W CAND.



5400 AC
 14" PENDANT
 D: 14 H: 34 OAH: 82
 (5) 25W CAND.



WINDSOR

5409 AC
27" OVAL PENDANT
L: 27 H: 34.5 W: 19 OAH: 97
(4) 60W MED.




5414 AC
16 LIGHT CHANDELIER
D: 30 H: 32 OAH: 80
(16) 25W CAND.





5403 AC
3 LIGHT WALL BRACKET
W: 20.5 H: 14.5 E: 10
(9) 25W CAND.



5416 AC
ADA WALL SCONCE
W: 7 H: 12 E: 4
(1) 40W CAND.



5407 AC
10 LIGHT ISLAND
L: 42 H: 34 W: 13 OAH: 146
(10) 25W CAND.

5406 AC
3 TIER WALL SCONCE (LEFT)
W: 10 H: 60 E:5
(3) 25W CAND.
INCLUDES: DIFFUSER
TOP: METAL
BOTTOM: GLASS



5404 AC
3 TIER WALL SCONCE (RIGHT)
W: 10 H: 60 E:5
(3) 25W CAND.
INCLUDES: DIFFUSER
TOP: METAL
BOTTOM: GLASS



5405 AC
ADA WALL SCONCE
W: 12 H: 26 E:4
(1) 40W CAND.
INCLUDES: DIFFUSER
TOP: METAL
BOTTOM: GLASS

WINDSOR

5418 AC
TABLE LAMP
L: 18 W: 13 H: 32.5
(2) 60W MED.
**SWITCH ON BASE*



5419 AC
FLOOR LAMP
L: 20 W: 14 H: 63
(2) 60W MED.
**PULL-CHAIN SWITCH*



MONACO



Monaco

MONACO COLLECTION STANDARD GLASS & FINISH

PEARL GLASS



ANTIQUÉ COPPER (AC)



Hand Forged Wrought Iron featuring an Antiqué Copper (AC) finish with standard Pearl Glass Shade or upgraded Black Iridescent Shell Shade.

UPGRADE SHELL (Fees Apply)

SHELL



6023 AC/SHELL
9 LIGHT CHANDELIER + ACCENT LIGHT
D:33 H:34 OAH: 130
(9) 40W CAND./LED ACCENT LIGHT
SHOWN W/ UPGRADE SHELL OPTION





6017 AC/PEARL
1 LIGHT MINI-PENDANT
D:14 H:34 OAH: 51
(1) 40W MED.
INCLUDES TELESCOPIC
ADJUSTABLE STEM

6021 AC/PEARL
3 LIGHT PENDANT + ACCENT LIGHT
D:15 H:35 OAH: 83
(3) 40W MED./LED ACCENT LIGHT



6022 AC/PEARL
5 LIGHT CHANDELIER + ACCENT LIGHT
D: 28 H: 30 OAH: 78
(5) 40W MED./ LED ACCENT LIGHT



6010 AC/SHELL
 ADA WALL SCONCE
 W:14 H:14 E:4
 (1) 40W CAND.
 SHOWN WITH UPGRADE SHELL OPTION



6011 AC/SHELL
 1 LIGHT WALL BRACKET
 W: 9 H: 47 E: 7
 (1) 40W CAND.
 SHOWN WITH UPGRADE SHELL OPTION



6016 AC/SHELL
 1 LIGHT MINI PENDANT + ACCENT LIGHT
 D:9 H: 30 OAH: 78
 (1) 40W CAND./ACCENT LIGHT
 SHOWN WITH UPGRADE SHELL OPTION

MONACO



Oxford

OXFORD

Wind chime inspired design made from hand-forged Wrought Iron shaped swirls featuring center crystal faceted ball drops.

2700 OB
1 LIGHT PENDANT
D: 23.5 H: 24 OAH: 72
(1) 50W GU10 * LAMP NOT INCLUDED






MORRIS

Hand Forged Wrought Iron in a warm **Bronze Finish (BZ)** paired with elegant Clear Glass and complete with removable delicate crystal drops. Decorative Chain included.

BRONZE (BZ)





CRYSTAL DROP AND CANDLE DETAIL

5804 BZ
LARGE FOYER
D: 29 H: 66 OAH: 162
(12) 60W CAND.




5803 BZ
MEDIUM FOYER
D: 19 H: 37.5 OAH: 85.5
(3) 60W CAND.



5795 BZ
1 LIGHT ADA SCONCE
W: 6 H: 14 E: 4
(1) 60W CAND.

DECORATIVE CHAIN DETAIL



5799 BZ
24 LIGHT CHANDELIER
D: 42 H: 38 - 56 OAH: 104
(24) 60W CAND.
ADJUSTABLE INNER STEM



5797 BZ
12 LIGHT CHANDELIER
D: 30 H: 38 - 56 OAH: 104
(12) 60W CAND.
ADJUSTABLE INNER STEM
SHOWN WITHOUT CRYSTAL DROPS

Morris




STANDARD ACCENT OPTIONS

COPPER PATINA
(-1)



SOLID CHERRY
(-2)



STANDARD FINISH OPTIONS

ANTIQUÉ COPPER (AC)



SIENNA BRONZE (SB)



WHEN ORDERING, PLEASE
SPECIFY MODEL #,
- ACCENT #, FINISH AND GLASS

SEE EXAMPLE BELOW
EX. 2508-2SB/ALAB

STANDARD GLASS OPTIONS

IRIDESCENT GLASS
(IRI)



ALABASTER
(ALAB)



BEDFORD

Sleek Hand Forged Wrought Iron in Antique Copper (AC) or Sienna Bronze (SB) paired with Iridescent (IRI) or Alabaster (ALAB) featuring Copper Patina (-1) or Solid Cherry (-2) accents.



2507-1AC/IRI
3 LIGHT FOYER
D: 18 H: 35 OAH: 50
(3) 40W CAND.

FEATURES TELESCOPIC ADJUSTABLE STEM



2505-1AC/IRI
1 LIGHT MINI PENDANT
L: 7 H: 31.5 W: 7 OAH: 47
(1) 60W CAND.

FEATURES TELESCOPIC ADJUSTABLE STEM



2501-1SB/ALAB
 1 LIGHT BATH
 W: 7.5 H: 8 E: 8
 (1) 60W MED.



2502-1SB/ALAB
 2 LIGHT BATH
 W: 18 H: 9 E: 9
 (2) 60W MED.



2503-1SB/IRI
 3 LIGHT BATH
 W: 30 H: 9 E: 8
 (3) 60W MED.

2508-2SB/ALAB
 6 LIGHT CHANDELIER
 D: 30 H: 27 OAH: 43
 (6) 40W CAND.

FEATURES TELESCOPIC ADJUSTABLE STEM



2506-1SB/ALAB
12" PENDANT
W: 12 H: 33.5 L: 12 OAH: 43
(1) 40W CAND.

FEATURES TELESCOPTIC ADJUSTABLE STEM



2509-2SB/ALAB
5 LIGHT ISLAND
L: 65 H: 34 W: 7.5 OAH: 52
(5) 60W MED.

FEATURES TELESCOPTIC ADJUSTABLE STEM



Americana



STANDARD FINISH OPTIONS

ANTIQUÉ COPPER (AC)



UPGRADE FINISH OPTIONS FEES APPLY


PEARL SILVER (PS)




BLACK (B)




COUNTRY IRON (CI)




FRENCH CREAM (FC)



MODERN GOLD (MG)



TORTOISE SHELL (TO)



AMERICANA

American Colonial Inspired Hand Forged Wrought Iron design in classic Antique Copper (AC) finish.

Standard Side Glass Options: pg 178

Standard Shade Options: pg. 176

Upgrade Penshell for Bath: pg. 178

4208 AC/8045
2 TIER (12 + 6 LIGHT) CHANDELIER
D: 47 H: 49 OAH: 145
(18) 40W CAND.
SHOWN WITH OPTIONAL SHADES



4209 AC/8045
9 LIGHT CHANDELIER
D: 36 H: 38 OAH: 144
(9) 40W CAND.
SHOWN WITH OPTIONAL SHADES



FORGING DETAIL



4207 AC/8045
7 LIGHT CHANDELIER
D: 30 H: 32 OAH: 80
(7) 40W CAND.
SHOWN WITH OPTIONAL SHADES





4211 AC/ 8045
1 LIGHT WALL BRACKET
W: 13 H: 13.5 E: 8.5
(1) 40W CAND.
SHOWN WITH OPTIONAL SHADES



4205 AC/8045
5 LIGHT CHANDELIER WITH DOWN LIGHT
D: 22 H: 23 OAH: 71
(5) 40W CAND. + (1) 50W R20 MED.
SHOWN WITH OPTIONAL SHADES
*DOWN LIGHT FEATURES 3 WAY SWITCH

AMERICANA

4201 AC / 1219
1 LIGHT BATH
W: 13 H: 11 E: 8
(1) 100W MED.



4202 AC / 1219
2 LIGHT BATH
W: 17 H: 11 E: 8
(2) 100W MED.



4203 AC / 1219
3 LIGHT BATH
W: 26.5 H: 11 E: 10.5
(3) 100W MED.



4204 AC / 1219
4 LIGHT BATH
W: 40.5 H: 11 E: 10.5
(4) 100W MED.



Rodeo Drive



RODEO DRIVE COLLECTION

STANDARD FINISH & BOWL OPTIONS

ANTIQUÉ COPPER (AC)



ECRU (ECRU)



UPGRADE FINISH & BOWL OPTIONS (Fees Apply)


BLACK (B)




COUNTRY IRON (CI)




FRENCH CREAM (FC)



MODERN GOLD (MG)



PEARL SILVER (PS)




TORTOISE SHELL (TO)



ART NOUVEAU
PENSHELL
(ART)



BUDDHA LEAF
(BUDDHA)



PENSHELL
(PENS)



VICTORIAN
PENSHELL
(VIC)



Rodeo Drive

Hand Forged Wrought Iron in a classic **Antique Copper (AC)** Finish paired with Ecu Glass Shade and accented with suspending authentic leather straps.

Upgrade Natural Glass & Bowls: pg. 179

Upgrade Finishes: pg. 180

4649 AC/ECRU
2 TIER (6 + 3 LIGHT) CHANDELIER
D: 34 H: 40 OAH: 136
(9) 40W MED.
(5) 60W MED. (INSIDE BOWL)



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM



4645 AC/ECRU
21" FLUSH MOUNT
D: 21 H: 15
(3) 100W MED.



4640 AC/ECRU
3 LIGHT ISLAND
W: 13.5 H: 31.5 L: 43.5 OAH: 79.5
(3) 60W MED.

WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM

4647 AC/ECRU
30" PENDANT
D: 30 H: 34 OAH:82
(6) 60W MED.



4636 AC/ECRU
43" PENDANT
D: 43.5 H: 51 OAH: 147
(6) 60W MED.



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM



4633 AC/ECRU
3 LIGHT CHANDELIER
D: 24 H: 26.5 OAH: 74.5
(3) 100W MED.

LEATHER ACCENT DETAIL



4646 AC/ECRU
6 LIGHT CHANDELIER
D: 30 H: 34 OAH: 82
(6) 100W MED.
(3) 100W MED. (INSIDE BOWL)



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM

4641 AC/1209
1 LIGHT BATH
W: 13 H: 11 E:9
(1) 100W MED.



4642 AC/1209
2 LIGHT BATH
W: 16 H: 11 E: 8.5
(2) 100W MED.



4643 AC/1209
3 LIGHT BATH
W: 26 H: 11 E: 10.5
(3) 100W MED.



4644 AC/1209
4 LIGHT BATH
W: 39 H: 11 E: 10.5
(4) 100W MED.



WHEN USING PENSHELL, NATURAL BOWLS OR SIDE SHADES, LIMIT WATTAGE TO 60 WATT MAXIMUM



898 AC
TABLE LAMP
W: 8.5 H: 31 L: 20
(2) 75W MED.
3-WAY SWITCH



899 AC
FLOOR LAMP
W: 12 H: 64 L: 22
(2) 75W MED.
INCLUDES FLOOR DIMMER SWITCH

RODEO DRIVE



DURANGO STANDARD GLASS & FINISH

LINEN



TAWNY PORT WITH HAMMERED
BRASS ACCENT (TP-2)



Durango

Early American West inspired design with Forged Wrought Iron in a warm Tawny Port with Hammered Brass Accent (TP-2) paired with Linen Glass.



6109 TP-2
2 TIER (6 + 3 LIGHT) CHANDELIER
D: 36 H: 35 OAH: 131
(9) 100W MED.



6107 TP-2
29" PENDANT
D: 29 H: 31 OAH: 79
(5) 100W MED.



6099 TP-2
5 LIGHT CHANDELIER
D: 28 H: 27 OAH: 75
(5) 100W MED.



6101 TP-2
1 LIGHT BATH
W: 6 H: 12 E: 8.5
(1) 100W MED.



6098 TP-2
8 LIGHT OVAL CHANDELIER
L: 47 W: 29 H: 32 OAH: 128
(8) 100W MED.



Oakham

Stunning Champagne Mica with Embossed Leaf pattern and stylized branch elements in Hand Forged Wrought Iron featured in Antique Gold with Antique Bronze Accents (BZG) Finish.

Leaf Accent Detail



Antique Gold with Antique Bronze Accents (BZG)



6614 BZG
1 LIGHT MINI PENDANT
D: 10 H: 21.5 OAH: 69.5
(2) 25W CAND.

6615 BZG
28" PENDANT
D: 28 H: 34 OAH: 82
(5) 40W MED.





6612 BZG
2 LIGHT ADA WALL SCONCE
W: 6 H: 18 E: 4
(2) 25W CAND.



6613 BZG
19" SEMI FLUSH
D: 19.5 H: 15
(3) 40W MED.



6611 BZG
22" PENDANT
D: 22 H: 28 OAH: 76
(4) 40W MED.



6617 BZG
2 LIGHT TALL MINI PENDANT
D: 8 H: 29.5 OAH: 77.5
(2) 25W CAND.



6616 BZG
1 LIGHT ADA WALL SCONCE
W: 14 H: 11 E: 4
(1) 40W CAND.

OAKHAM

6610 BZG
ISLAND LIGHT
L: 36 H: 29 W: 10 OAH: 77
(4) 40W MED.





CORDOVA

Spanish Mission inspired design featuring Copper Patina accents in a classic Natural Iron (NI) finish. Hand-shaped metal frame & hardware with genuine Calcite shades for soft, glowing light and rustic appeal.


CALCITE SHADE DETAIL



COPPER PATINA ACCENTS



NATURAL IRON (NI)




Cordova

5121 NI/CALC
8 + 3 LIGHT ISLAND
L: 36 H: 14 W: 12.5 OAH: 62
(8) 40W MED. & (3) 50W GU10
FEATURES DOWN-LIGHTS WITH
3 WAY SWITCH
(LAMPS NOT INCLUDED)



5125 NI/CALC
1 LIGHT PENDANT
W: 4 H: 13 L: 7 OAH: 61
(1) 25W CAND.

5120 NI/CALC
5 LIGHT ISLAND
W: 9 L: 45 H: 16.5 OAH: 84.5
(5) 40W MED.



COPPER INSET
BOTTOM DETAIL




Aspen

Cozy Mountain Lodge inspired design made from Hand Forged Wrought Iron featuring Mica Shades in a Natural Iron (NI) finish. Select models feature Whimsical Forest Silhouettes.

MICA SHADE



NATURAL IRON (NI)



ASPEN

5832 NI
2 TIER (6 + 6 LIGHT) CHANDELIER
D: 56 H: 65 OAH: 161
(12) 40W CAND.
MICA SHADES INCLUDED



800.525.2655

5811 NI
6 LIGHT CHANDELIER with LIGHTED GALLERY
D: 36.5 H: 39.5 OAH: 135.5
(6) 40W CAND. & (6) 25W CAND.
MICA SHADES INCLUDED



5812 NI
2 TIER (6 + 3) LIGHT CHANDELIER with LIGHTED GALLERY
D: 40 H: 51.5 OAH: 147.5
(9) 40W CAND. & (9) 25W CAND.
MICA SHADES INCLUDED





5828 NI
6 LIGHT POT RACK
W: 46 H: 19 L: 21.5 OAH: 67
(6) 40W MED.
INCLUDES 6 HOOKS



5827 NI
5 LIGHT ISLAND
L: 54 H: 27 W: 14.5 OAH: 75
(5) 40W MED.



5847 NI
5 LIGHT ISLAND
L: 54 H: 27 W: 14.5 OAH: 75
(5) 40W MED.





CANOPY DETAIL



5836 NI
24" SEMI FLUSH
D: 24 H: 23
(6) 60W MED.

5817 NI
28" PENDANT
D: 28 H: 36 OAH: 84
(6) 60W MED.



5838 NI
36" PENDANT
D: 36 H: 47 OAH: 143
(6) 60W MED.



5839 NI
41" PENDANT
D: 41.5 H: 54 OAH: 150
(6) 60W MED.



5837 NI
28" PENDANT
D: 28 H: 36 OAH: 84
(6) 60W MED.



5822 NI
2 LIGHT WALL SCONCE
W: 12 H: 27.5 E: 10
(2) 40W CAND.
MICA SHADES INCLUDED



5815 NI
3 LIGHT WALL SCONCE
W: 21 H: 12 E: 10
(3) 25W CAND.



5840 NI
1 LIGHT MINI PENDANT
D: 9 H: 23 OAH: 59
(1) 40W MED.
INCLUDES 6", 12", & 24" STEMS

895 NI
OVAL TABLE LAMP
W: 17 H: 32 L: 12
(2) 75W MED.
NATURAL LINEN SHADE INCLUDED
FEATURES PULL CHAIN SOCKETS



896 NI
RECTANGLE TABLE LAMP
W: 17 H: 30 L: 12
(2) 75W MED.
NATURAL LINEN SHADE INCLUDED
FEATURES PULL CHAIN SOCKETS

ASPEN



Napa

NAPA

Hand Forged Wrought Iron in a warm Golden Wheat (GW) finish paired with delicate Snowflake Glass.

4760 GW/SNOW
8 LIGHT TALL FOYER
D: 22.5 H: 49.5 OAH: 97.5
(8) 55W T4 MINICAND (INCLUDED)

GOLDEN WHEAT



800.525.2655

CANOPY DETAIL



4756 GW/SNOW
6 LIGHT CHANDELIER
D:28 H:31 OAH:79
(6) 75W T4 MINICAND (INCLUDED)



4755 GW/SNOW
3 LIGHT CHANDELIER
D: 15 H: 26 OAH: 74
(3) 75W T4 MINICAND (INCLUDED)



CHAIN DETAIL





4761 GW/SNOW
1 LIGHT WALL BRACKET
W: 5.5 H: 15.5 E: 7
(1) 75W T4 MINICAND (INCLUDED)



4750 GW/SNOW
1 LIGHT MINI-PENDANT
D:4 H:17 OAH:53
(1) 75W T4 MINICAND (INCLUDED)
(1) 12" & (1) 24" STEM INCLUDED



4763 GW/SNOW
2 LIGHT WALL BRACKET (LEFT)
W: 12 H: 23 E: 6.5
(2) 75W T4 MINICAND (INCLUDED)



4764 GW/SNOW
2 LIGHT WALL BRACKET (RIGHT)
W: 12 H: 23 E: 6.5
(2) 75W T4 MINICAND (INCLUDED)



4753 GW/SNOW
3 LIGHT BATH
W: 26 H: 10.5 E: 6
(3) 75W T4 MINICAND (INCLUDED)



4754 GW/SNOW
4 LIGHT BATH
W: 31 H: 10.5 E: 6
(4) 75W T4 MINICAND (INCLUDED)



BARK (BA)

VINE

this Garden Inspired Design is of Hand Forged Wrought Iron work, the Vine Collection features a traditional Bark (BA) Finish and finely crafted swirl details.

Upgrade Natural Glass & Bowls: pg. 179

Shade Options: pg. 176



VINE COLLECTION OPTIONS

STANDARD BOWL OPTIONS

SMOKE TAUPE
(SMKTAUP)




GOLD-STREAKED
AMBER
(GLDSTRK)



ECRU
(ECRU)



BLAZE
(BLZ)



ANTIQUE FILIGREE
(ANTQ)



WHITE ALABASTER
(ALAB)




UPGRADE NATURAL BOWL OPTIONS (Fees Apply)


ART NOUVEAU
PENSHELL
(ART)



BUDDHA LEAF
(BUDDHA)



PENSHELL
(PENSH)



IRIDESCENT SHELL
(IRSH)



VICTORIAN
PENSHELL
(VIC)



SEE PAGE 178 FOR UPGRADE BATH & MINI PENDANT GLASS OPTIONS

SEE PAGE 176 FOR MINI SHADE OPTIONS

Vine

3493 BA
2 TIER (8 + 4 LIGHT) CHANDELIER
D: 28 H: 36 OAH: 84
(12) 60W CAND.



3489 BA
8 LIGHT CHANDELIER
D: 27 H: 33 OAH: 81
(8) 60W CAND.




800.525.2655



1821 BA/1219
1 LIGHT MINI PENDANT
D: 5.5 H: 9 OAH: 51
(1) 60W MED
(1) 6" ,(1) 12"& (1) 24" STEM INCLUDED




3499 BA / ALAB
17.5" SEMI FLUSH
D: 17.5 H: 14 OAH: 73
(3) 40W MED



3491 BA / ALAB
25" PENDANT
D: 25 H: 36 OAH: 84
(3) 60W MED.



3496 BA/PENSH
1 LIGHT WALL SCONCE
W: 17 H: 7.5 E: 6.5
(1) 40W MED
SHOWN WITH UPGRADE
NATURAL GLASS
*NOTE: STANDARD GLASS FOR 3496BA
IS WHITE ALABASTER*



3498 BA/PENSH
3 LIGHT ISLAND
L: 51 H: 25 W: 5
(3) 40W MED
SHOWN WITH UPGRADE
NATURAL GLASS
*NOTE: STANDARD GLASS FOR 3498BA
ARE ECRU AND GOLD STREAK*

3383 BA
1 LIGHT WALL BRACKET
W: 6.5 H: 18 E: 10
(1) 25W CAND



4185 BA
4 LIGHT ADA WALL BRACKET
W: 18 H: 32 E: 4
(4) 25W CAND.



3485 BA
POT RACK
L: 36 H: 16.5 W: 20 OAH: 64.5
(2) 50W R20 MED
INCLUDES 10 HOOKS



VINE

3521 BA/1255
1 LIGHT BATH
W: 9 H: 9.5 E: 9
(1) 100W MED.



3522 BA/1255
2 LIGHT BATH
W: 18 H: 9.5 E: 7
(2) 100W MED.



3523 BA/1255
3 LIGHT BATH
W: 27 H: 9.5 E: 7.5
(3) 100W MED.



830 BA
WALL MIRROR
W: 31 H: 45
VERTICAL OR HORIZONTAL MOUNT



3562 BA/1255
2 LIGHT BATH
W: 18 H: 9 E: 8.5
(2) 100W MED.



3563 BA/1255
3 LIGHT BATH
W: 28 H: 9 E: 8
(3) 100W MED.

Vine

F100 BA
DINING CHAIR
W: 23 H: 42 L: 23




F300 BA
DINING TABLE
D: 42 H: 30

F200 BA
SWIVEL BAR STOOL WITH ARMS
W: 24 H: 46 L:24



F700 BA
BAR TABLE
D: 30 H: 39



F500 BA
SWIVEL COUNTER HEIGHT STOOL WITH ARMS
W: 24 H: 39 L: 22.5



F600 BA
SWIVEL BAR STOOL
W: 24 H: 46 L: 24



F650 BA
SWIVEL COUNTER HEIGHT STOOL
W: 24 H: 39 L: 24



Ponderosa

Rustic Lodge inspired series in Hand Forged Wrought Iron featured in a Ponderosa (PD) finish.





5042 PD/1255
 2 TIER (8 + 4 LIGHT) CHANDELIER
 D: 34.5 H: 34 OAH: 130
 (12) 100W MED.



STANDARD FINISH

PONDEROSA



STANDARD GLASS BOWL

PIASTRA



UPGRADE SHADE (FEES APPLY)

LEATHER WRAPPED
 8045



STANDARD SIDE GLASS

SMALL PIASTRA
 1255



LARGE PIASTRA
 1265





5032 PD/8045
2 TIER (8 + 4 LIGHT) CHANDELIER
D: 34.5 H: 34 OAH: 130
(12) 40W CAND.
SHOWN WITH OPTIONAL SHADES



5034 PD/8045
3 LIGHT CHANDELIER
D:14 H:19.5 OAH: 67.5
(3) 40W CAND.
SHOWN WITH OPTIONAL SHADES





5035 PD/8045
5 LIGHT CHANDELIER
D:22 H:22.5 OAH: 70.5
(5) 40W CAND.
SHOWN WITH OPTIONAL SHADES



5031 PD/8045
8 LIGHT CHANDELIER
D: 26 H: 28 OAH:76
(8) 40W CAND.
SHOWN WITH OPTIONAL SHADES



5041 PD/1255
8 LIGHT CHANDELIER
D: 26 H: 28 OAH: 76
(8) 100W MED.



5044 PD/1255
3 LIGHT CHANDELIER
D:14 H:19.5 OAH:67.5
(3) 100W MED.



5045 PD/1255
5 LIGHT CHANDELIER
D: 22 H: 22.5 OAH: 70.5
(5) 100W MED.



5026 PD
1 LIGHT WALL SCONCE
W: 10 H: 17 EXT: 5
(1) 100W MED.

5040 PD/1255
3 TIER (8 + 8 + 4 LIGHT) CHANDELIER
D: 60 H: 54 OAH: 150
(20) 100W MED.



5030 PD/8045
3 TIER (8 + 8 + 4 LIGHT) CHANDELIER
D: 60 H: 54 OAH: 150
(20) 40W CAND.
SHOWN WITH OPTIONAL SHADES





873 PD
FLOOR LAMP
D: 19.5 H: 68
(1) 50 / 100 / 150W 3-WAY MED.



3035 PD/8045
2 LIGHT WALL BRACKET (RIGHT)
W: 16 H: 16 E: 10
(2) 40W CAND.
SHOWN WITH OPTIONAL SHADES



3033 PD/8045
2 LIGHT WALL BRACKET (LEFT)
W: 16 H: 16 E: 10
(2) 40W CAND.
SHOWN WITH OPTIONAL SHADES



872 PD
TABLE LAMP
D: 19.5 H: 35
(1) 50 / 100 / 150W 3-WAY MED.



3031 PD/8045
1 LIGHT WALL BRACKET
W: 7 H: 17 E: 9.5
(1) 40W CAND.
SHOWN WITH OPTIONAL SHADES



5033 PD/8045
12 LIGHT FOYER CHANDELIER
D: 22 H: 52 OAH: 148
(12) 40W CAND.
SHOWN WITH OPTIONAL SHADES



3032 PD/1255
1 LIGHT WALL BRACKET
W: 7 H: 14.5 E: 9.5
(1) 100W MED.



3034 PD/1255
2 LIGHT WALL BRACKET (LEFT)
W: 16 H: 14.5 E: 10
(2) 100W MED.



3036 PD/1255
2 LIGHT WALL BRACKET (RIGHT)
W: 16 H: 14.5 E: 10
(2) 100W MED.



5043 PD/1255
12 LIGHT FOYER CHANDELIER
D:22 H:52 OAH:148
(12) 100W MED.



5024 PD/1265
 1 LIGHT MINI-PENDANT
 D:7 H:17 OAH:53
 (1) 100W MED.
 (1) 12", (1) 24" STEM INCLUDED



5028 PD
 20" PENDANT
 D:20 H:17 OAH:53
 (1) 100W MED.
 (1) 12", (1) 24" STEM INCLUDED



5025 PD
 2 LIGHT ISLAND
 L: 45.5 H: 27 W: 20 OAH: 75
 (2) 100W MED.



5027 PD
SEMI FLUSH
D: 19 H: 15
(3) 100W MED.



5022 PD
28" PENDANT
D:28 H:36 OAH:84
(5) 100W MED.



5023 PD
34" PENDANT
D: 34 H: 40 OAH: 88
(6) 100W MED.

5038 PD
2 LIGHT POT RACK
L: 36 H: 23 W: 21 OAH: 71
(2) 50W R20 MED.
INCLUDES 10 HOOKS



3038 PD/8045
8 LIGHT RECTANGULAR CHANDELIER
L: 46.5 H: 30.5 W: 16 OAH: 78.5
(8) 40W CAND
SHOWN WITH OPTIONAL SHADES





3042 PD/1265
2 LIGHT BATH
W: 17 H: 16 E: 9.5
(2) 100W MED.



3041 PD/1265
1 LIGHT BATH
W: 7 H: 14 E: 12
(1) 100W MED.



3043 PD/1265
3 LIGHT BATH
W: 26 H: 16 E: 12
(3) 100W MED.



3044 PD/1265
4 LIGHT BATH
W: 37 H: 16 E: 9.5
(4) 100W MED.



878 PD
FIREPLACE SCREEN
W: 29 H: 30.75 (1) FRONT PANEL
W: 12 H: 30.75 (2) SIDE PANEL



879 PD
3 PIECE TOOL SET W/ STAND



870 PD
OVAL WALL MIRROR
W: 26 H: 41 E: 3



F230 PD
SWIVEL BAR STOOL W/ ARMREST
W: 26 H: 43 L: 20

F730 PD
PUB TABLE
D: 30 H: 39



871 PD
CONSOLE TABLE
L: 48 H: 31 W: 15

Ponderosa



ATLANTIS

Hand Forged Wrought Iron in a sandy **Coral (CR)** finish accented by authentic Sea Shells with Petite Victorian Glass

CORAL FINISH



AUTHENTIC SHELL DETAIL



PETITE VICTORIAN GLASS DETAIL





6077 CR
5 LIGHT CHANDELIER
D: 21 H: 26 OAH: 74
(5) 100W MED.

6078 CR
3 LIGHT CHANDELIER
D: 15 H: 21 OAH: 69
(3) 100W MED.



6075 CR
1 LIGHT WALL BRACKET
W: 8 H: 19 E: 8.5
(1) 100W MED.



Atlantis

6070 CR
OVAL MIRROR
W: 21.5 H: 34 E: 3



6073 CR
3 LIGHT BATH
W: 30 H: 9.5 E: 8.5
(3) 100W MED.

Contemporary Potracks

Sleek and contemporary, the **Satin Nickel (SN)** Pot Rack's from Kalco can be the finishing touch on any modern kitchen,

3616 SN
CONTEMPORARY POTRACK
W: 36 H: 14.5 L:20
(2) 50W R20 MED.
10 HOOKS INCLUDED



3617 SN
LARGE CONTEMPORARY POTRACK
W: 43.5 H: 18 L:20
(2) 50W R20 MED.
10 HOOKS INCLUDED



BON APPETIT POTRACKS

Kalco's Hand Forged Wrought Iron is masterfully crafted to make the Bon Appetit Pot Rack featured in **Antique Copper (AC)** Finish with leaf and glass accents as seen below.

ANTIQUÉ COPPER (AC)



3635 AC
BON APPETIT POTRACK
W: 44 H: 22 L: 21
(2) 50W R20 MED.
10 HOOKS INCLUDED

UPGRADE SHADE OPTIONS (Fees Apply)



S15
Beaded Taupe
top d: 3" bot. d: 6" h: 7.5"



S47
Light Beige
top d: 3" bot. d: 6" h: 6"



S195
Beige Drum
d: 5.5" h: 4"



S205
Mica
top d: 3" bot. d: 6" h: 5"
*Max. 40W cand. recommended



S240
Champagne Mica
top d: 3" bot. d: 6" h: 5"
*Max. 40W cand. recommended



S253
Silver Organza
d: 5.5" h: 4"



S256
Black Organza
d: 5.5" h: 4"



8030
Small Silk Bell
top d: 3" bot. d: 6" h: 5"



8045
Leather Wrapped
top d: 3" bot. d: 6" h: 5"
*Max. 40W cand. recommended

UPGRADE MESH SHADE OPTIONS (Fees Apply)



S327
Coronado Mesh
top d: 3" bot. d: 6" h: 7.5"

UPGRADE GLASS SHADE OPTIONS (Fees Apply)



SA151
Alencon White Lace
(Frost White with Silver Trim)
top d:3.3" bot. d:4.5" h:4.1"



SA152
Venetian White Lace
(Frost White with Gold Trim)
top d:3.3" bot. d:4.5" h:4.1"



SA153
Bedford Cord Gold
(Off White with Gold Trim)
top d:3.3" bot. d:4.5" h:4.1"



SA154
Bedford Cord Silver
(Off White with Silver Trim)
top d:3.3" bot. d:4.7" h:4.3"



SA155
Dupioni Silk
(Pearl White)
top d:3.3" bot. d:4.6" h:4.1"



SA156
Pleated Bengaline Silk
(Off White with Gold Trim)
top d:3.3" bot. d:4.7" h:4.3"

*Supplied w/candelabra to G9 base adaptor. G9 lamp included
Designed to replace traditional 40W cand. lamps with Energy Efficient 25W G9 lamps
Fully Dimmable*

STANDARD SIDE GLASS OPTIONS

<p>ECRU (1209)</p> <p>D:6" H:5"</p> 	<p>WHITE ALABASTER (1219)</p> <p>D:6" H:5"</p> 	<p>SMALL PIASTRA (1255)</p> <p>D:5.5" H:4.75"</p> 	<p>LARGE PIASTRA (1265)</p> <p>D:6" H:5"</p> 	<p>SMOKED TAUPE (*1305)</p> <p>D:6" H:5"</p> 	<p>GOLD STREAKED AMBER (1313)</p> <p>D:6" H:5"</p> 
<p>ANTIQUE LINEN (1318)</p> <p>D:6.75" H:5.75"</p> 	<p>AMBER TULIP (1339)</p> <p>D:7" H:5.75"</p> 	<p>WATERFALL (1350)</p> <p>D:6.5" H:5.25"</p> 	<p>PETITE VICTORIAN (1355)</p> <p>D:5" H:5.5"</p> 	<p>TRAVERTINE (1356)</p> <p>D:5" H:5"</p> 	<p>ECRU (*1365)</p> <p>D:6" H:6"</p> 
<p>CHAMPAGNE (1438)</p> <p>D:5.25" H:5"</p> 	<p>SMOKED WHITE (1479)</p> <p>D:5" H:5"</p> 	<p>FAUX CALCITE (1501)</p> <p>D:3" H:7"</p> 	<p>FAUX CALCITE (1502)</p> <p>D:3.75" H:6"</p> 	<p>STONE (*1576)</p> <p>D:8.75" H:7.25"</p> 	<p>STONE (*1577)</p> <p>D:6.5" H:7"</p> 

UPGRADE SIDE GLASS OPTIONS (Fees Apply)

<p>NS01 BUDDHA LEAF D:5" H:5.125"</p> 	<p>PS01 PENSHELL D:5" H:5.125"</p> 	<p>PS02 PENSHELL D:6" H:6"</p> 	
<p>PS11 PENSHELL D:6" H:5"</p> 	<p>PS14 PENSHELL D:5" H:6"</p> 	<p>PS15 PENSHELL D:6.5" H:7"</p> 	<p>*PS5201 PENSHELL D:6" H:9"</p> 

* GLASS MARKED WITH * MAY NOT FIT ON ALL FIXTURES
 ** NATURAL SHADE OPTIONS HAVE LIMITED WATTAGE
 (40W MED. / 25W CAND.)
 *** NATURAL BOWL OPTIONS HAVE LIMITED WATTAGE
 (60W MAXIMUM)

GLASS BOWL OPTIONS

STANDARD BOWL OPTIONS

SMOKE TAUPE
(SMKTAUP)



GOLD-STREAKED
AMBER
(GLDSTRK)



ECRU
(ECRU)



BLAZE
(BLZ)



ANTIQUE FILIGREE
(ANTQ)



WHITE ALABASTER
(ALAB)




UPGRADE NATURAL BOWL OPTIONS (Fees Apply)


ART NOUVEAU
PENHELL
(ART)



BUDDHA LEAF
(BUDDHA)



PENHELL
(PENSH)



IRIDESCENT SHELL
(IRSH)



VICTORIAN
PENHELL
(VIC)




Our Natural Shades & Bowls are individually handmade using natural materials responsibly harvested from rain forests and oceans.


STANDARD FINISH OPTIONS - **SEE SPECIFIC FAMILIES FOR STANDARD & UPGRADE OPTIONS**

UPGRADE HAND PAINTED FINISH OPTIONS (**Fees May Apply**)

BLACK (B)




COUNTRY IRON (CI)



FRENCH CREAM (FC)



MODERN GOLD (MG)



PEARL SILVER (PS)



TORTOISE SHELL (TO)



Model	Page	Model	Page	Model	Page
810	38	3035	161	4067	62
814	39	3036	163	4154	13
830	150	3038	166	4185	148
870	168	3041	167	4201	109
871	169	3042	167	4202	109
872	161	3043	167	4203	109
873	161	3044	167	4204	109
878	168	3161	40	4205	108
879	168	3163	38	4207	107
895	135	3164	39	4208	105
896	135	3166	40	4209	106
898	117	3172	42	4211	108
899	117	3177	41	4243	34
1821	145	3272	40	4256	29
1851	16	3274	41	4257	28
1855	42	3383	148	4258	29
2501	102	3485	148	4259	28
2502	102	3489	145	4261	32
2503	102	3491	146	4263	32
2505	101	3493	144	4265	28
2506	102	3496	147	4267	35
2506	103	3498	147	4269	35
2507	101	3499	146	4273	31
2509	103	3521	149	4274	26
2660	22	3522	149	4281	17
2661	23	3523	149	4282	17
2662	23	3541	43	4283	17
2663	23	3542	43	4284	17
2664	23	3543	43	4285	16
2665	23	3544	43	4286	16
2669	21	3562	150	4287	10
2671	20	3563	150	4288	12
2673	19	3616	174	4289	10
2674	22	3617	174	4290	14
2675	20	3635	175	4296	12
2700	95	4032	33	4297	11
3031	161	4038	30	4298	16
3032	163	4039	27	4299	8
3033	161	4065	63	4300	15
3034	163	4066	63	4301	16

Model	Page	Model	Page	Model	Page
4302	15	4965	55	5401	87
4303	13	4966	54	5404	88
4305	15	4967	53	5405	88
4306	11	4968	53	5406	88
4308	13	4969	54	5407	87
4309	12	4970	51	5408	84
4341	70	4971	52	5409	86
4346	71	4975	51	5410	83
4347	71	4976	52	5411	83
4348	70	5022	165	5412	84
4349	71	5023	165	5413	85
4633	115	5024	164	5414	86
4636	114	5025	164	5415	84
4640	113	5026	159	5416	87
4641	116	5027	165	5418	89
4642	116	5028	164	5419	89
4643	116	5030	160	5457	66
4644	116	5031	157	5458	67
4645	113	5032	156	5459	66
4646	115	5033	162	5750	58
4647	114	5034	156	5751	59
4649	112	5035	157	5752	59
4750	140	5038	166	5753	59
4753	141	5040	159	5755	59
4754	141	5041	158	5756	58
4755	139	5042	155	5762	57
4756	138	5043	163	5763	58
4760	137	5044	158	5764	57
4761	140	5045	158	5795	98
4763	141	5120	127	5797	99
4764	141	5121	127	5799	99
4842	72	5125	127	5803	98
4842	75	5181	48	5804	97
4844	72	5188	47	5811	130
4845	74	5189	46	5812	130
4846	74	5194	49	5815	134
4847	74	5196	49	5817	132
4848	75	5197	48	5822	134
4960	55	5198	47	5827	131
4961	55	5400	85	5828	131

Model	Page	Model	Page
5832	129	6617	125
5836	132	506721	7
5837	133	506722	7
5838	133	506771	6
5839	133	506772	5
5840	134	F100	151
5847	131	F200	152
6010	93	F230	169
6011	93	F300	151
6016	93	F500	153
6017	92	F600	153
6021	92	F650	153
6022	92	F700	152
6023	91	F730	169
6070	173		
6073	173		
6075	172		
6077	171		
6078	172		
6098	121		
6099	120		
6101	121		
6107	120		
6109	119		
6570	81		
6575	80		
6577	80		
6578	81		
6579	79		
6582	78		
6583	77		
6584	79		
6585	81		
6610	125		
6611	124		
6612	124		
6613	124		
6614	123		
6615	123		
6616	125		