



800-736-7991
www.duraguard.com

DuraLED: Built to Last

The DuraGuard Advantage



98-3-1

Quick-Ship

98% Fill Rate

3 Day Lead Time

1 Piece Minimum Order Quantity

5

USA Manufacturing Locations.



ARRA Compliant

LED Lighting Products



Phone: **800-736-7991**

Email: **customerservice@duraguard.com**

Hampton Kitty Hawk

Maximum Mounting Versatility



Hampton Mini Kitty Hawk Model# KH15Q

43 Input Watts; 3,140-4,100 Delivered Lumens
Replaces up to 175w HID

Hampton Small Kitty Hawk Model# KH25Q

87-120 Input Watts; 7,200-13,000 Delivered Lumens
Replaces up to 400w HID

Hampton Large Kitty Hawk Model# KH45Q

177-281 Input Watts; 16,500-31,000 Delivered Lumens
Replaces up to 1,000w HID

MegaHawk Model# KH55Q

557 Input Watts; 52,000-61,500 Delivered Lumens
Replaces up to 1,500w HID



DesignLights Consortium™
Qualified Luminaire:
KH25QC1X81U5KC***
KH25QF1X81U5KC***
KH25QC1X112U5KC***
KH25QF1X112U5KC***

KH45QC1X167U5K***
KH45QF1X167U5K***
KH45QC1X256U5K***
KH45QF1X256U5K***

For a sleek, architectural look, choose the multi-functional Kitty Hawk. Designed to accept multiple mounting options, they are ideal for most applications, including roadway, area and parking lot lighting, flood lighting, and even wall-mount. Their choice of Types I, II, III, IV and V optics, combined with seven wattage choices and the many mounting options, allow an entire site to be lit with a uniform appearance. As part of our Hampton Series, they are dependable and long-lasting with heavy-duty housings, aluminum DuraLED arrays, and well-managed thermals.

Narrow Beam Optics Available Q2 2017.

Visit us at www.duraguard.com for complete specifications.



DuraLED Flood and Area Light

The DuraLED Flood and Area Lights feature a heavy-duty housing with an innovative industrial look, choice of Types I, II, III and V optics, and five mounting options. Ideal for pole heights of 20 to 50 feet, they can be used in parking areas, along roadways, in large common areas, sign lighting, and as ground or wall mounted flood and façade lighting.



Square Flood and Area Light Model# AL35Q

187-286 Input Watts; 16,000-31,000 Delivered Lumens
Replaces up to 1,000w HID

MegaAL Flood and Area Light Model# AL55Q

568 Input Watts; 48,000-61,500 Delivered Lumens
Replaces up to 1,500w HID



DesignLights Consortium™
Qualified Luminaires:
AL35QC1X174U5KC***
AL35QF1X174U5KC***
AL35QC1X262U5KC***

Maximum Mounting Versatility



Swivel Bracket



Yoke



Slipfitter



Mounting Arm



Wall Mount Bracket



FLEM



Phone: **800-736-7991**

Email: **customerservice@duraguard.com**

DurAdjust Lighting

Maximum Mounting Versatility



The DurAdjust features a uniquely designed housing with vertical fins for an architectural style, and offers seven mounting options and three wattages. This versatility allows it to be used across an entire site for a uniform appearance. The area lighting mounts allow mounting heights of up to 30 feet, ideal for both parking lots and roadway use, while the flood mounting options provide ground mount, post and pole mounting capabilities. The wall mount options complete the lighting package.

DurAdjust Area/Flood/Wall Light
Model# AD25Q

61-121 Input Watts; 8,800-13,500 Delivered Lumens
Replaces up to 400w HID

Visit us at www.duraguard.com for complete specifications.



Sculptor Series Area & Site Lighting

The Sculptor LED Post Top fixtures' aesthetically pleasing appearance complements many architectural styles while providing energy-saving, long-lasting lighting for parking areas, walkways, common areas, and street lighting applications for retail and commercial properties. These are available in small and large rounds and a large square, and are accompanied by matching bollards and wall sconces for a unified look across the entire property. Look for canopy and garage lighting in Q2 2017.



Sculptor Small Round Area Light
Model# PF70Q & PF71Q

93 Input Watts; 6,800-8,000 Delivered Lumens
Replaces up to 250w HID



Sculptor Large Round Area Light
Model# PF80Q & PF81Q

186 Input Watts; 15,000-17,500 Delivered Lumens
Replaces up to 400w HID



Available Q2
2017

Sculptor Large Square Area Light
Model# PFS80Q

186 Input Watts; 19,000 Delivered Lumens
Replaces up to 400w HID



Sculptor LED Bollard
Model# B3Q & B4Q

20 Input Watts; 1,540-1,620 Delivered Lumens
Replaces up to 100w HID



Sculptor LED Wall Sconce
Model# WBB3Q & WBB4Q

20 Input Watts; 1,540-1,620 Delivered Lumens
Replaces up to 100w HID



Phone: **800-736-7991**


Email: **customerservice@duraguard.com**

DuraLED Mega Series

DuraGuard introduces the high-power, high-output Mega series for demanding applications. Use the architectural Hampton MegaHawk or industrial design MegaAL for roadway, area and parking lot lighting, common areas and as ground or pole mounted flood and façade lighting. Both feature a choice of optics and mounting options and the 61,000+ lumen output makes them ideal for pole mounting up to 50 feet.

MegaAL Flood and Area Light
Model# AL55Q

568 Input Watts; 48,000-61,500 Delivered Lumens
Replaces up to 1,500w HID



MegaHawk Flood and Area Light
Model# KH55Q

557 Input Watts; 52,000-61,500 Delivered Lumens
Replaces up to 1,500w HID

Coming 2nd Quarter 2017 is the MegaHB Highbay!

Visit us at www.duraguard.com for complete specifications.



Think Durability

Think DuraGuard

DuraGuard makes buying LED lighting easy. We've carefully engineered each aspect so you can be sure our LED fixtures are efficient, dependable and long-lasting.

WHY THE DuraLED LINE IS THE EASY CHOICE:

SUPERIOR THERMAL MANAGEMENT.

Our fixtures are benchmarked at 40°C (104°F) ambient during thermal testing rather than the 25°C (77°F) standard, which allows them to be used in real-world applications.

INDUSTRY-LEADING LED TECHNOLOGY.

DuraLED fixtures feature our unique array and COB technologies. Our arrays are custom designed for each fixture, and utilize aluminum boards with copper tracings for thermal management and stability. Our COBs are bonded directly to a thick copper substrate for ultra-high thermal conductivity. Both offer increased lifespan and improved photometric performance.

QUICK AND EASY TO PURCHASE.

DuraLED fixtures are readily available through our nationwide network of distributors and manufacturer's representatives. We have five stocking/assembly locations in the U.S., which means prompt delivery and a large inventory. Orders are delivered within days instead of weeks.

DEPENDABLE.

Backed by a five-year warranty and over 25 years in business, you can be assured of on-the-job performance and longevity.



Phone: **800-736-7991**

Email: **customerservice@duraguard.com**

DuraLED Lighting - Bulkheads



Orah Round Bulkhead
Half-Cutoff Frame
Model# WPR25HCO

20 Input Watts; 1,410-1,470 Delivered Lumens
Replaces up to 100w HID



Orah Round Bulkhead
Grid Frame
Model# WPR25GRO

20 Input Watts; 1,410-1,470 Delivered Lumens
Replaces up to 100w HID



Orah Round Bulkhead
Open Frame
Model# WPR25OFQ

20 Input Watts; 1,610-1,680 Delivered Lumens
Replaces up to 100w HID



Orah Square Bulkhead
Half-Cutoff Frame
Model# WPS25HCO

20 Input Watts; 1,510-1,570 Delivered Lumens
Replaces up to 100w HID



Orah Square Bulkhead
Grid Frame
Model# WPS25GRO

20 Input Watts; 1,310-1,370 Delivered Lumens
Replaces up to 100w HID




Orah Square Bulkhead
Open Frame
Model# WPS25OFQ

20 Input Watts; 1,550-1,620 Delivered Lumens
Replaces up to 100w HID



Dart Round Bulkhead
Half-Cutoff
Model# FBWPHCO

27 Input Watts; 1,840 Delivered Lumens
Replaces up to 100w HID



Dart Round Bulkhead
Grid Frame
Model# FBWPGFO

27 Input Watts; 2,110 Delivered Lumens
Replaces up to 100w HID



Dart Round Bulkhead
Open Frame
Model# FBWPOFO

27 Input Watts; 2,510 Delivered Lumens
Replaces up to 100w HID

Visit us at www.duraguard.com for complete specifications.



DuraLED Lighting - Bulkheads



Dart Square Bulkhead
Half-Cutoff

Model# SBWPHCQ

27 Input Watts; 1,600 Delivered Lumens
Replaces up to 100w HID



Dart Square Bulkhead
Grid Frame

Model# SBWPGFQ

27 Input Watts; 1,800 Delivered Lumens
Replaces up to 100w HID



Dart Square Bulkhead
Open Frame

Model# SBWPOFQ

27 Input Watts; 2,020 Delivered Lumens
Replaces up to 100w HID



Ovation Wallpack Halfmoon

Model# OVWPHMQ

27 Input Watts
Replaces up to 175w HID



Ovation Wallpack Bulkhead

Model# OVWPBHQ

27 Input Watts
Replaces up to 175w HID



Ovation Wallpack Full Face

Model# OVWPFFQ

27 Input Watts; 3,010 Delivered Lumens
Replaces up to 175w HID



Small Moonglow

Model# WPR30Q

20 Input Watts; 1,870 Delivered Lumens
Replaces up to 100w HID



Large Moonglow

Model# WPR32Q

30 Input Watts; 2,640 Delivered Lumens
Replaces up to 175w HID



Element Outdoor Decorative LED
Wall Pack & Emergency Light

Model# WPDLED & WPDLEDEM

14 Input Watts; 1,200 Delivered Lumens
Replaces up to 70w HID



Phone: **800-736-7991**

Email: **customerservice@duraguard.com**

DuraLED Lighting - Decorative Accent



Astra LED Up or Down
Wall Cylinder
Model# WCTRSC3

20 Input Watts; 2,310-2,320 Delivered Lumens
Replaces up to 100w HID



Astra LED Up/Down
Wall Cylinder
Model# WCTRDC3

40 Input Watts; 3,390-4,500 Delivered Lumens
Replaces up to 175w HID



Hampton Mini Kitty Hawk
Wall Mount
Model# KH15Q

43 Input Watts; 3,160-4,100 Delivered Lumens
Replaces up to 175w HID



Hampton Small Kitty
Hawk Wall Mount
Model# KH25Q

87-120 Input Watts; 7,300-13,000 Delivered Lumens
Replaces up to 400w HID



DesignLights Consortium™
Qualified Luminaires:
KH25QC1X81U5KC***
KH25QF1X81U5KC***
KH25QC1X112U5KC***
KH25QF1X112U5KC***



Hampton Large Kitty
Hawk Wall Mount
Model# KH45Q

177-281 Input Watts; 16,500-31,000 Delivered Lumens
Replaces up to 1,000w HID



DesignLights Consortium™
Qualified Luminaires:
KH45QC1X167U5K***
KH45QF1X167U5K***
KH45QC1X256U5K***
KH45QF1X256U5K***



Astra LED Small Wallpack
Model# TV2C3

21-43 Input Watts; 2,170-4,100 Delivered Lumens
Replaces up to 175w HID



DesignLights Consortium™
Qualified Luminaires:
TV2C32X20U41K*



Astra LED Large Wallpack
Model# TV3C3

56-80 Input Watts; 5,400-8,300 Delivered Lumens
Replaces up to 400w HID



DesignLights Consortium™
Qualified Luminaires:
TV3C34X20U41K*



Sculptor Round & Square Sconce
Model# WBB3Q & WBB4Q

20 Input Watts; 1,540-1,620 Delivered Lumens
Replaces up to 100w HID



DurAdjust Wall Light
Model# AD25Q

61-121 Input Watts; 8,800-13,500 Delivered Lumens
Replaces up to 400w HID

Visit us at www.duraguard.com for complete specifications.



DuraLED Lighting - Wall Packs



Small Wall Pack Full Cutoff
Model# WPC12Q

25 Input Watts; 2,010-2,290 Delivered Lumens
Replaces up to 175w HID



DesignLights Consortium™
Qualified Luminaires:
WPC12QF1X22U5KC**



Medium Wall Pack Full Cutoff
Model# MWPCOQ

43 Input Watts; 3,960-4,200 Delivered Lumens
Replaces up to 250w HID



DesignLights Consortium™
Qualified Luminaires:
MWPCOQC1X37U5KC**
MWPCOQF1X37U5KC**



Large Wall Pack Full Cutoff
Model# LWPCOQ

63 Input Watts; 5,700-6,600 Delivered Lumens
Replaces up to 400w HID



DesignLights Consortium™
Qualified Luminaires:
LWPCOQC1X56U5KC**
LWPCOQF1X56U5KC**



Small Accord Semi-Cutoff
Wall Pack
Model# SACCORDQ

44 Input Watts; 3,450 Delivered Lumens
Replaces up to 175w HID



Large Accord Semi-Cutoff
Wall Pack
Model# LACCORDQ

69 Input Watts; 5,000 Delivered Lumens
Replaces up to 400w HID



Small Wall Pack PC Lens
Model# SWPPCQ

28 Input Watts; 2,480-2,580 Delivered Lumens
Replaces up to 100w HID



Small Wall Pack Glass Lens
Model# SWPQ

28 Input Watts; 2,480-2,580 Delivered Lumens
Replaces up to 100w HID



DesignLights Consortium™
Qualified Luminaires:
SWPQF1X23U5K*



Medium Wall Pack
Model# MWPQ

47 Input Watts; 5,200-5,400 Delivered Lumens
Replaces up to 250w HID



DesignLights Consortium™
Qualified Luminaires:
MWPQF1X41U5K*



Large Shallow Wall Pack
Model# LWPQ

67 Input Watts; 7,700-8,000 Delivered Lumens
Replaces up to 400w HID



DesignLights Consortium™
Qualified Luminaires:
LWPQF1X58U5K*




Phone: **800-736-7991**
Email: **customerservice@duraguard.com**

DuraLED Lighting - Wall Packs




Medium Semi-Cutoff Wall Pack
Model# MSCOWPQ

44 Input Watts; 4,600 Delivered Lumens
Replaces up to 250w HID



Large Semi-Cutoff Wall Pack
Model# LSCOWPQ

67 Input Watts; 7,100 Delivered Lumens
Replaces up to 400w HID



Large Deep Semi-Cutoff Wall Pack
Model# LDSCOWPQ

67 Input Watts; 7,100 Delivered Lumens
Replaces up to 400w HID



16" Wall Light
Model# AL35Q

187-286 Input Watts; 16,000-31,000 Delivered Lumens
Replaces up to 1,000w HID



DesignLights Consortium™
Qualified Luminaires:
AL35QC1X174U5KC**
AL35QF1X174U5KC***
AL35QC1X262U5KC***




Halfmoon Downlight Wall Pack
Model# HMWP-DOQ

52 Input Watts; 4,100-4,500 Delivered Lumens
Replaces up to 250w HID



DesignLights Consortium™
Qualified Luminaires:
HMWP-DOQC1X47U5KC**



Halfmoon Up/Down Light Wall Pack
Model# HMWP-UDQ

52 Input Watts; 6,000 Delivered Lumens
Replaces up to 250w HID



Orion Wallpack
Model# ORIONQ

52 Input Watts; 3,940 to 4,400 Delivered Lumens
Replaces up to 250w HID



DesignLights Consortium™
Qualified Luminaires:
ORIONQC1X47U5KC**



Bravo! Wall Pack
Model# BRAVOQ

37 Input Watts; 3,120 Delivered Lumens
Replaces up to 175w HID



Polycarbonate Entry Light-Square
Model# WP8Q

10 Input Watts; 780 Delivered Lumens
Replaces up to 70w HID



Polycarbonate Entry Light- Round
Model# WP9Q

9 Input Watts; 680 Delivered Lumens
Replaces up to 70w HID



Polycarbonate Mini Wall Pack
PC Lens
Model# MINIWPQ

14 Input Watts; 1,060 Delivered Lumens
Replaces up to 70w HID



Glasspack
Model# GLPACKQ

22 Input Watts; 1,550 Delivered Lumens
Replaces up to 70w HID

Visit us at www.duraguard.com for complete specifications.



DuraLED Lighting - Flood Lighting



MegaAL Flood Light
Model# AL55Q

568 Input Watts; 48,000-61,000 Delivered Lumens
Replaces up to 1,500w HID



16" Flood Light
Model# AL35Q

187-286 Input Watts; 16,000-30,500 Delivered Lumens
Replaces up to 1,000w HID



DesignLights Consortium™
Qualified Luminaires:
AL35QC1X174U5KC***
AL35QF1X174U5KC***
AL35QC1X262U5KC***



DurAdjust Flood Light
Model# AD25Q

61-121 Input Watts; 8,800-13,000 Delivered Lumens
Replaces up to 400w HID



Hampton Mini Kitty Hawk Flood
Model# KH15Q

43 Input Watts; 3,140-4,100 Delivered Lumens
Replaces up to 175w HID



Hampton Small Kitty Hawk Flood
Model# KH25Q

87-120 Input Watts; 7,200-13,000 Delivered Lumens
Replaces up to 400w HID



DesignLights Consortium™
Qualified Luminaires:
KH25QC1X81U5KC***
KH25QF1X81U5KC***
KH25QC1X112U5KC***
KH25QF1X112U5KC***



Hampton Large Kitty Hawk Flood
Model# KH45Q

177-281 Input Watts; 17,500-31,000 Delivered Lumens
Replaces up to 1,000w HID



DesignLights Consortium™
Qualified Luminaires:
KH45QC1X167U5KC***
KH45QF1X167U5KC***
KH45QC1X256U5KC***
KH45QF1X256U5KC***



MegaHawk Flood Light
Model# KH55Q

557 Input Watts; 52,000-61,500 Delivered Lumens
Replaces up to 1,500w HID



Phone: **800-736-7991**

Email: **customerservice@duraguard.com**

DuraLED Lighting - Flood Lighting



Astra LED Bullet
Model# FB1C3

20w Input Watts; 1,770-1,810 Delivered Lumens
Replaces up to 100w HID



Astra LED Small Flood
Model# TV2C3

21-43 Input Watts; 2,160-4,100 Delivered Lumens
Replaces up to 175w HID



Astra LED Large Flood
Model# TV3C3

56-80 Input Watts; 5,300-8,300 Delivered Lumens
Replaces up to 400w HID



LED Small Flood Light
Model# FL20L

21 Input Watts; 1,590 Delivered Lumens
Replaces up to 70w HID



DesignLights Consortium™
Qualified Luminaires:
FL20L1X18U5K



Small Flood
Model# SFLQ

25 Input Watts; 1,940-2,130 Delivered Lumens
Replaces up to 100w HID



Deluxe Small Flood
Model# DSFLQ

25 Input Watts; 1,940-2,130 Delivered Lumens
Replaces up to 100w HID



DesignLights Consortium™
Qualified Luminaires:
DSFLQ1X22U5KC**



Mid-Size Flood
Model# MFLQ

41 Input Watts; 3,100-3,390 Delivered Lumens
Replaces up to 175w HID



DesignLights Consortium™
Qualified Luminaires:
MFLQ1X37U5KC***



Round Back Flood
Model# RBFQ

44 Input Watts; 3,430-3,440 Delivered Lumens
Replaces up to 175w HID



DesignLights Consortium™
Qualified Luminaires:
RBFQ1X40U5KC***



Horizontal Flood
Model# HFLQ

75 Input Watts; 5,500 Delivered Lumens
Replaces up to 400w HID




DesignLights Consortium™
Qualified Luminaires:
HFLQ1X68U5KC***

Visit us at www.duraguard.com for complete specifications.



DuraLED Lighting - Area Lighting



MegaHawk Area Light
Model# KH55Q

557 Input Watts; 52,000-61,500 Delivered Lumens
Replaces up to 1,500w HID



Hampton Mini Kitty Hawk Area Light
Model# KH15Q

43 Input Watts; 3,160-4,100 Delivered Lumens
Replaces up to 175w HID



Hampton Small Kitty Hawk Area Light
Model# KH25Q

87-120 Input Watts; 7,300-13,000 Delivered Lumens
Replaces up to 400w HID



DesignLights Consortium™
Qualified Luminaires:
KH25QC1X81U5KC***
KH25QF1X81U5KC***
KH25QC1X112U5KC***
KH25QF1X112U5KC***



Hampton Large Kitty Hawk Area Light
Model# KH45Q

177-281 Input Watts; 16,500-31,000 Delivered Lumens
Replaces up to 1,000w HID



DesignLights Consortium™
Qualified Luminaires:
KH45QC1X167U5KC***
KH45QF1X167U5KC***
KH45QC1X256U5KC***
KH45QF1X256U5KC***



16" Area Light
Model# AL35Q

187-286 Input Watts; 16,000-31,000 Delivered Lumens
Replaces up to 1,000w HID



DesignLights Consortium™
Qualified Luminaires:
AL35QC1X174U5KC***
AL35QF1X174U5KC***
AL35QC1X262U5KC***



MegaAL Area Light
Model# AL55Q

568 Input Watts; 48,500-61,500 Delivered Lumens
Replaces up to 1,500w HID



Hampton Small Street Light
Model# ST30Q

180 Input Watts; 16,000-17,500 Delivered Lumens
Replaces up to 400w HID



DesignLights Consortium™
Qualified Luminaires:
ST30QC1X167U5KC**
ST30QF1X167U5KC**



Hampton Large Street Light
Model# ST35Q

301 Input Watts; 26,000-33,000 Delivered Lumens
Replaces up to 1,000w HID



DesignLights Consortium™
Qualified Luminaires:
ST35QC1X279U5KC**
ST35QF1X279U5KC**



DurAdjust Area Light
Model# AD25Q

61-121 Input Watts; 8,800-13,500 Delivered Lumens
Replaces up to 400w HID



Phone: **800-736-7991**
Email: **customerservice@duraguard.com**

DuraLED Lighting - Area Lighting



Sculptor Large Round
Area Light - Open
Model# PF80Q

186 Input Watts; 17,500 Delivered Lumens
Replaces up to 400w HID



Sculptor Large Round
Area Light - Enclosed
Model# PF81Q

186 Input Watts; 15,000 Delivered Lumens
Replaces up to 400w HID



Available Q2
2017

Sculptor Large Square
Area Light
Model# PFS80Q

186 Input Watts; 19,000 Delivered Lumens
Replaces up to 400w HID



Sculptor Small Round Area
Light - Open
Model# PF70Q

93 Input Watts; 8,000 Delivered Lumens
Replaces up to 250w HID



Sculptor Small Round Area
Light - Enclosed
Model# PF71Q

93 Input Watts; 6,800 Delivered Lumens
Replaces up to 250w HID



Astra LED Dusk-To-Dawn
Utility Light
Model# SC25C3

42 Input Watts; 3,880 Delivered Lumens
Replaces up to 175w HID



Visit us at www.duraguard.com for complete specifications.



DuraLED Lighting - Bollards



Astra Round & Square
LED Bollards

Model# B1C3 & B2C3

20 Input Watts;
2,290-2,410 Delivered Lumens
Replaces up to 70w HID



Sculptor Round
LED Bollard

Model# B3Q

20 Input Watts;
1,540 Delivered Lumens
Replaces up to 70w HID



Sculptor Square
LED Bollard

Model# B4Q

20 Input Watts;
1,620 Delivered Lumens
Replaces up to 70w HID



Dome Bollard - IES
Type III & V Glass
Model# DTRBG3Q
or DTRBG5Q

17 Input Watts;
990-1,030 Delivered Lumens
Replaces up to 70w HID



Dome Bollard -
Cone Reflector
Model# DTRBPBCLO &
DTRBPBCLOSS

17 Input Watts;
1,360-1,390 Delivered Lumens
Replaces up to 70w HID



Dome Bollard - Louvers
Model# DTRBAALQ &
DTRBAALOSS

17 Input Watts;
Replaces up to 70w HID



Flat Top Bollard - IES
Type III & V Glass
Model# FTRB3Q
or FTRB5Q

17 Input Watts;
990-1,030 Delivered Lumens
Replaces up to 70w HID



Flat Top Bollard -
Cone Reflector
Model# FTRBPBCLO

17 Input Watts;
1,360-1,390 Delivered Lumens
Replaces up to 70w HID



Flat Top Bollard -
Louvers
Model# FTRBAALQ

17 Input Watts
Replaces up to 70w HID



Square Bollard - IES
Type III & V Glass
Model# SB3Q or SB5Q

17 Input Watts;
1,110-1,160 Delivered Lumens
Replaces up to 70w HID



Square Bollard -
LED Cone Reflector
Model# SBPBCLO

17 Input Watts;
1,330-1,390 Delivered Lumens
Replaces up to 70w HID

Available
with GFCI
Receptacle!



Square Bollard -
Round & Square Louvers
Model# SBSAALQ

17 Input Watts
Replaces up to 70w HID



Phone: **800-736-7991**

Email: **customerservice@duraguard.com**

DuraLED Lighting - Garage and Canopy



12x12 Large Shallow Canopy
Model# VN43Q

53 Input Watts; 5,300-5,500 Delivered Lumens
Replaces up to 175w HID



DesignLights Consortium™
Qualified Luminaires:
VN43QF1X45U5K*



12x12 Medium Vandal
Resistant Canopy
Model# 12X12Q

53 Input Watts; 5,000-5,200 Delivered Lumens
Replaces up to 175w HID



16" Gas Station Canopy
Model# CP16Q

125w Input Watts; 15,000 Delivered Lumens
Replaces up to 250w HID




Deluxe Garage Lighter
Model# DGarageQ

52 Input Watts; 5,100 Delivered Lumens
Replaces up to 175w HID



9x9 Small Vandal
Resistant Canopy
Model# 9X9Q

28 Input Watts; 2,620-2,730 Delivered Lumens
Replaces up to 100w HID



20" Gas Station Canopy
Model# CP20Q

204w Input Watts; 27,500 Delivered Lumens
Replaces up to 400w HID



Vandal Resistant Garage Lighter
Model# GARAGEQ

62 Input Watts; 7,200-7,500 Delivered Lumens
Replaces up to 175w HID



Available with Sensor.
Garage Lighter
Model# VN55Q

56 Input Watts; 5,500 Delivered Lumens
Replaces up to 175w HID



DLC Pending
VN55QF1X48U5K

Visit us at www.duraguard.com for complete specifications.



DuraLED Lighting - Vaporproofs and Linear LED



12" Linear LED Die Cast
Model# LV1AOQ, LV1AHQ,
& LV1AVQ

26-41 Input Watts; 5,300-5,900 Delivered Lumens
Replaces up to 175w HID
Available Q2 2017.



24" Linear LED Die Cast
Model# LV2AOQ

52-72 Input Watts; 9,200 Delivered Lumens
Replaces up to 250w HID
Available Q2 2017.



48" Linear LED Die Cast
Model# LV4AOQ

123-150 Input Watts; 16,500 Delivered Lumens
Replaces up to 400w HID
Available Q2 2017.



Large Box Mount Vaporproof
Model# VB43Q

13 Input Watts; 840 Delivered Lumens
Replaces up to 70w HID



Large Pendant Mount Vaporproof
Model# VP43Q

13 Input Watts; 840 Delivered Lumens
Replaces up to 70w HID



Large Wall Mount Vaporproof
Model# VW43Q

13 Input Watts; 840 Delivered Lumens
Replaces up to 70w HID



2' Linear LED Vaportight
Model# LV2P

21 Input Watts; 2,000 Delivered Lumens



4' Linear LED Vaportight
Model# LV4P


42 Input Watts; 4,100 Delivered Lumens



DesignLights Consortium™
Qualified Luminaire:
LV4PS42U5KG**



(GL33C3)



(GL73C3)

Dura-Gro LED Grow Light
Model# GL33C3 & GL73C3

COB: 120w or 240w
Color Spectrum:
Red - 77.1% / Blue - 22.6% / Green - .3%
Nanometer Ranges:
Red - 600-699 / Blue - 400-499 / Green - 500-599



Phone: **800-736-7991**
Email: **customerservice@duraguard.com**

DuraLED Lighting - High and Low Bays



Astra Hampton 16" COB
LED Highbay
Model# HB44C3

207 Input Watts; Replaces up to 400w HID
Clear Glass: 19,500 Delivered Lumens



Astra Hampton 22" COB
LED Highbay
Model# HB45C3

316 Input Watts; Replaces up to 1,000w HID
Clear Glass: 40,000 Lumens



Hampton 16" Highbay
Model# HB44Q

179 Input Watts; Replaces up to 400w HID
Clear Glass: 15,500-16,500 Lumens
Prismatic Glass: 14,500-16,000 Lumens
Conical Lens: 16,000-17,000 Lumens
Acrylic Drop Lens: 14,500-15,500 Lumens
Narrow (30° Beam): 20,500 Lumens
Aisle Optic: 19,000 Lumens



DesignLights Consortium™
Qualified Luminaires:
HB44QF1X169U5KG**



Hampton 22" Highbay
Model# HB45Q

291 Input Watts; Replaces up to 1,000w HID
Clear Glass: 25,500-27,500 Lumens
Prismatic Glass: 21,000-23,000 Lumens
Conical Lens: 25,500-28,000 Lumens
Acrylic Drop Lens: 24,500-27,000 Lumens
Narrow (30° Beam): 34,000 Lumens
Aisle Optic: 31,500 Lumens



DesignLights Consortium™
Qualified Luminaires:
HB45QF1X273U5KG**



Available Q2
2017

Low Profile Highbay
Model# HB30C3

123-198w Input Watts; 14,000-27,000 Lumens
Replaces up to 400w HID



Vandal Resistant Low Bay
Model# VNGL40Q

62 Input Watts; 7,500 Delivered Lumens
Replaces up to 175w HID



DesignLights Consortium™
Qualified Luminaires:
VNGL40QF1X54U5KS*

Visit us at www.duraguard.com for complete specifications.



Square Straight Steel Poles

- Pre-Drilled for Side Mount, Polycarbonate Plugs Included.
- Reinforced Cast Iron Hand-Hole Cover with Ground Screw.
- Easily Secured Base Cover.
- Single Vertical Tenon Included. Polycarbonate Spring Loaded Top Cover Included For Use in Place of Tenon.
- Set of 4 Anchor Bolts (J-bolts) Included.
- Conforms to ASTM-A 500 Grade B: Minimum Yield Strength of 46,000 PSI.
- Bronze Polyester Powder-Coat Finish to Ensure Maximum Paint Adhesion. Baked to Ensure Maximum Hardness & Durability.

Poles Can Be Cut to Custom Lengths.

4" x 4" Square Straight
Steel Pole (11 Gauge)
Model# PSS4011Z

Length: 20 Feet
Weight: 146 Lbs
2 3/8" Tenon

4" x 4" Square Straight
Steel Pole (7 Gauge)
Model# PSS4257Z

Length: 25 Feet
Weight: 256 Lbs
2 3/8" Tenon



5" x 5" Square Straight
Steel Pole (7 Gauge)
Model# PSS5307Z

Length: 30 Feet
Weight: 406 Lbs
2 3/8" Tenon



Available Pole
Tenon Spoke Brackets:



PTSB1SZ
2 3/8" Tenon



PTSB290SZ
2 3/8" Tenons



PTSB2180SZ
2 3/8" Tenons



PTSB390SZ*
2 3/8" Tenons



PTSB3120SZ*
2 3/8" Tenons



PTSB490SZ*
2 3/8" Tenons

*Special order item. Lead time three weeks.



Phone: **800-736-7991**
Email: **customerservice@duraguard.com**

Square Straight Steel Pole Accessories



Wall Mount Bracket
Model# POLEACC028
2 $\frac{3}{8}$ " Tenon



180° Triple Round
Bullhorn Tenon
Model# POLEACC041
2 $\frac{3}{8}$ " Tenons



Wall Mount 90° Bracket
Model# POLEACC016
2 $\frac{3}{8}$ " Tenon



180° Quad Round
Bullhorn Tenon
Model# POLEACC041C
2 $\frac{3}{8}$ " Tenons



90° Quad Square
Vertical Tenon For 4" Square Pole
Model# POLEACC038
2 $\frac{3}{8}$ " Tenons



4" Single Square
Vertical Tenon For 4" Square Pole
Model# POLEACC029
2 $\frac{3}{8}$ " Tenon



180° Quad Square
Vertical Tenon For 4" Square Pole
Model# POLEACC041A
2 $\frac{3}{8}$ " Tenons
180° Quad Square
Vertical Tenon For 5" Square Pole
Model# POLEACC041B
2 $\frac{3}{8}$ " Tenons



5" Single Square
Vertical Tenon For 5" Square Pole
Model# POLEACC029A
2 $\frac{3}{8}$ " Tenon

4" 180° Twin Square
Horizontal Tenon For 4" Square Pole
Model# POLEACC030
2 $\frac{3}{8}$ " Tenons
5" 180° Twin Square
Horizontal Tenon For 5" Square Pole
Model# POLEACC030A
2 $\frac{3}{8}$ " Tenons



Twin Square Vertical
Tenon For 4" Square Pole
Model# POLEACC037
2 $\frac{3}{8}$ " Tenons
Twin Square Vertical
Tenon For 5" Square Pole
Model# POLEACC037A
2 $\frac{3}{8}$ " Tenons



4" 90° Twin Square
Horizontal Tenon For 4" Square Pole
Model# POLEACC031
2 $\frac{3}{8}$ " Tenons
5" 90° Twin Square
Horizontal Tenon For 5" Square Pole
Model# POLEACC031A
2 $\frac{3}{8}$ " Tenons



Triple Square Vertical
Tenon For 4" Square Pole
Model# POLEACC037B
2 $\frac{3}{8}$ " Tenons
Triple Square Vertical
Tenon For 5" Square Pole
Model# POLEACC037C
2 $\frac{3}{8}$ " Tenons



4" 90° Triple Square
Horizontal Tenon For 4" Square Pole
Model# POLEACC032
2 $\frac{3}{8}$ " Tenons



180° Double Round
Bullhorn Tenon
Model# POLEACC040
2 $\frac{3}{8}$ " Tenons



4" 90° Quad Square
Horizontal Tenon For 4" Square Pole
Model# POLEACC034
2 $\frac{3}{8}$ " Tenons



120° Triple Round
Bullhorn Tenon
Model# PRSTR120BHZ
2 $\frac{3}{8}$ " Tenons



Pole Tenon Adaptor
Model# PTASUNVZ

Visit us at www.duraguard.com for complete specifications.



CUSTOMER SERVICE

12802 Commodity PL
Tampa, FL 33626
Phone: 800-736-7991
customerservice@duraguard.com
www.duraguard.com

Note: Lumen Values shown are approximate. Values will vary based on optical distribution, lens options, CCT and fixture environment



DuraLED: Built to Last