



#6434
SLYDE™ KING

NEW FROM NEBO
KING
AND
BOSS



#6431
Larry™ BOSS

FALL / WINTER
2016

TABLE OF CONTENTS

- **NEBO® Lights and Tools..... 1-47**
 - SLYDE™ KING - Flashlight & Work Light 2-3
 - Larry™ BOSS - 3-in-1 Work Light 4-5
 - TEMPRA™ - IR Surface Thermometer & Spot Light 6-7
 - Z-Bug Bulb™ - Mosquito-Zapping LED Light Bulb 8-9
 - LiL Larry™ - Powerful Pocket Work Light 10-11
- **Lighting 101 41**
- **Custom Printing & Engraving Program..... 41**
- **FAQs 42-43**
- **Price Sheet 44-45**



We love creating great, quality products for our customers! Don't forget, no one ships faster than NEBO®! And we always guarantee your total satisfaction as expressed in our NEBO® "Guaranteed Buyback Program" that you will find on the back of this catalog. Also on the back of this catalog you will find our newest NEBO® giveaways. Be sure to get these while they last!

We appreciate your business and the support and feedback you give our products.

Thanks and best wishes for your success!

THE NEBO® FAMILY
800-255-6061

Nous aimons créer des grands, des produits de qualité pour nos clients! Ne pas oublier, pas un des navires plus rapidement que NEBO®! Et nous garantissons toujours votre satisfaction totale exprimée dans notre NEBO® "Programme de Rachat garanti" que vous trouverez sur le dos de ce catalogue. Egalement sur le dos de ce catalogue, vous trouverez nos nouveaux cadeaux de NEBO®. Soyez sûr d'obtenir ces en temps réel!

Nous apprécions votre entreprise et le soutien et la rétroaction que vous donnez nos produits.

Merci et meilleurs voeux pour votre succès!

LA FAMILLE NEBO®
800-255-6061

NEBO®

NEBO® is one of the world's best-selling lines of innovative, consumer-friendly flashlights and tools. Ever-changing and never compromising, we create and see our products through every phase of development. From the conceptual drawings on the sketch pad all the way to the end consumer, we offer quality and customer service guarantees that are unmatched.



#6434 SLYDE™ KING



#6458 Z-Bug Bulb™



#6431 Larry™ BOSS



#6433 TEMPRA™

NEW
FROM NEBO



@NEBOTOLS



/NEBOTOLS



@NEBOTOLS



/NEBOTOLS

**LIKE US... FOLLOW US ONLINE...
WATCH OUR VIDEOS!**

NEBO[®] SLYDE KING

FLASHLIGHT & WORK LIGHT

With all of the features that you would expect from a SLYDE...and more! The SLYDE™ KING is equipped with programmable memory settings for each light mode, a new C-O-B red light function, a 4x adjustable zoom and best of all...it's rechargeable!

LIGHT

- High-power 330 lumen LED flashlight
- High-power 250 lumen C-O-B work light
- High-power 40 lumen red light
- High-power red hazard flasher

DESIGN

- Fully rechargeable
- Memory power setting
- Convex lens
- Tactical edge
- 4x adjustable zoom
- Anodized aircraft-grade aluminum; water and impact-resistant
- Dimmable beam
- Work light is concealed inside the flashlight body
- Powerful magnetic base

OPERATION

- Side-positioned ON/OFF button
- Work light automatically turns ON when opened

BATTERIES

- Powered by 1 Li-ion rechargeable battery included (3-4 hour recharge time)

ACCESSORIES

- Micro USB to USB cable included

SPECS

- 0.8 lbs.
- Length: Compacted: 6.875" / Extended: 9"
- Diameter: (Head) 1.75" / (Barrel) 1.25"



4x Adjustable Zoom




330 Lumen Flashlight




Fully Rechargeable



250 Lumen C-O-B Work Light




Extendable Body Design



40 Lumen Red Light



Powerful Magnetic Base



Red Hazard Flasher



NEBO[®] SLYDE KING

COUNTERTOP DISPLAY

#6434 Display

- Display holds 1 piece in front for consumer testing, additional pieces can be stored in the back as replenishments
- Each SLYDE™ KING comes with a gift box.
- Product attaches securely to the display using the magnetic base

Display Dimensions

(H) 11.5" x (W) 7.25" x (D) 7.75"

Gift Box Dimensions

(H) 7" x (W) 1.875" x (D) 1.875"



FOUR LIGHT MODES

FLASHLIGHT:

- 330 Lumens
- 2 Hours
- 123 Meters

WORK LIGHT:

- 250 Lumens
- 4.25 Hours
- 22 Meters

RED LIGHT:

- 40 Lumens
- 4.75 Hours
- 7 Meters

RED FLASH:

- 24 Hours



Micro USB to USB cable included



C-O-B (Chips on Board)

A new innovation in LED technology. C-O-B features smaller, easier clustered LED chips that are mounted directly to the circuit board. These LED chips work together as one lighting module. Because of the compact design, C-O-B outperforms traditional lighting by up to 50 times the light output per centimeter of light surface.



OPTIMIZED CLARITY

Eliminating inconsistencies in light, the OC™ (Optimized Clarity) Technology provides intense, clear, pristine light that is easy on the eyes. This technology allows the light beam to be as bright on the edge as it is in the center when used in flood mode.

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930884	6434	SLYDE™ KING Flashlight & Work Light	28.95	49.95	12 PIECES

NEBO
the *Larry BOSS*
3 IN ONE POWER WORK LIGHT

3-IN-1 POWER WORK LIGHT

The Larry™ BOSS, the essential 3-in-1 power work light, features a high-power flashlight, work light and red light. Taking charge of keeping your work space clean, the BOSS is equipped with a recessed 13.5" telescopic magnetic grabber, great for picking up lose screws, nails, nuts and bolts. The Larry™ BOSS also has a powerful magnetic base for hands-free lighting.

LIGHT

- High-power 120 lumen LED flashlight
- High-power 400 lumen C-O-B LED work light
- High-power 40 lumen red light
- High-power red hazard flasher

DESIGN

- Fully dimmable
- Anodized aircraft-grade aluminum; water and impact-resistant
- Powerful magnetic base
- 13.5" telescoping magnetic grabber
- Rubberized slide release for magnetic grabber

OPERATION

- Front-positioned, ON/OFF button

BATTERIES

- Powered by 3 AA batteries (included)

SPECS

- 0.8 lbs.
- Length: Compacted: 7.625" / Extended: 22.375"
- Width: 1.1875" / Depth: 1.375"



13.5" Telescopic Magnetic Grabber



Emergency Red Light



Rubberized slide release



Powerful Magnetic Base



120 Lumen Flashlight



400 Lumen C-O-B Work Light



40 Lumen Red Light



Red Hazard Flasher



NEBO
the *Larry BOSS*
3 IN ONE POWER WORK LIGHT

COUNTERTOP
DISPLAY

#6431 Display

- Display holds 1 piece in front for consumer testing, additional pieces can be stored in the back as replenishments.

- Product attaches securely to the display using the magnetic base

Display Dimensions
(H) 15.5" x (W) 5.5" x (D) 7.75"



FOUR LIGHT MODES

TOP LIGHT:

- 120 Lumens
- 12 Hours
- 44 Meters

WORK LIGHT:

- 400 Lumens
- 4.5 Hours
- 27 Meters

RED LIGHT:

- 40 Lumens
- 20 Hours
- 7 Meters

RED FLASH:

- 40 Hours



C-O-B (Chips on Board)

A new innovation in LED technology. C-O-B features smaller, easier clustered LED chips that are mounted directly to the circuit board. These LED chips work together as one lighting module. Because of the compact design, C-O-B outperforms traditional lighting by up to 50 times the light output per centimeter of light surface.



Rubberized slide release for magnetic grabber

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930860	6431	Larry™ BOSS Power C-O-B Work Light	21.95	41.95	12 PIECES

NEBO™ TEMPRA™

IR THERMOMETER & SPOT LIGHT

Not just for the professional, the TEMPRA™ can help save time and money at work, around the house or in the car. Use the laser-guided infrared thermometer to make sure your car engine is firing on all cylinders. Check your HVAC to ensure your home is cooling and heating efficiently. The TEMPRA™, just one more way NEBO® helps get the job done.

LIGHT

- High-power 1340 LUX LED spot light

LASER

- Red laser guide for accurate temperature scanning

DESIGN

- 4x adjustable zoom
- Infrared lens
- Laser pointer
- Backlit LCD
- Adjustable emissivity for different surface materials
- Fahrenheit/Celsius conversion
- Ergonomic handle
- Low battery indicator
- Data hold function

OPERATION

- Back-positioned ON/OFF button for spot light
- Trigger for LASER and temperature scan

BATTERIES

- Powered by 4 AA batteries (included)

SPECS

- 0.7 lbs.
- (H) 7.625" x (W) 2" x (D) 4.25"



4x Adjustable Zoom




Backlit LCD Screen



1340 LUX Spot Light



Laser/IR Trigger and Lock



Red Laser Guide



Push Button Control Pad



NEBO™ TEMPRA™

COUNTERTOP DISPLAY

#6433 Display

- Display holds 1 piece in front for consumer testing, additional pieces can be stored in the back as replenishments
- Each TEMPRA™ comes with a gift box

Display Dimensions
(H) 13.2" x (W) 7" x (D) 7.75"

Gift Box Dimensions
(H) 9.3" x (W) 5.55" x (D) 2.25"



TWO LIGHT MODES

- | | |
|---------------------------------------|------------------------------------|
| HIGH:
1340 LUX / 130 Lumens | LOW:
650 LUX / 65 Lumens |
| • 3.5 Hours | • 7 Hours |
| • 146 Meters | • 102 Meters |

Perfect for...



Backlit LCD readout



UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930877	6433	TEMPRA™ IR Surface Thermometer & Light	39.99	69.99	8 PIECES

NEBO®

ZBUG BULB™

MOSQUITO-ZAPPING LED BULB

For use indoors or outdoors, Z-Bug Bulb™ provides bright white, ambient lighting to any space with its 600 lumen LED. The 4 NUV LEDs emit a 395nm near ultraviolet glow, which mosquitoes and other flying insects find very attractive. Surrounding the NUV LEDs is a 1,000 - 1,200V high-voltage grid that kills the allured insects on contact. Z-Bug Bulb™ includes Z-Bug Bulb™ Sweeper to remove insect remains from the grid housing.

LIGHT

- High-power 600 lumen LED
- 4 insect-alluring NUV LEDs (395nm)

DESIGN

- ABS LED cover
- 360° insect-zapping rails (1,000-1,200V)
- 360° protective cover for electric rails
- Standard E27 screw base

OPERATION


- For use in lamps, wall and ceiling fixtures; just switch light on

ACCESSORIES

- Z Bug Bulb™ Sweeper for easy cleaning

SPECS

- 0.25 lbs.
- (H) 6" x (W) 3.125" x (D) 3.125"



600 Lumen LED



Electric Rails & Protective Cover



4 Insect-Alluring NUV LEDs



Standard E27 Screw Base



NEBO®

ZBUG BULB™

COUNTERTOP DISPLAY

#6458 Display

- Display holds 6 pieces
- Each Z-Bug Bulb™ comes individually packaged

Display Dimensions

(H) 13.2" x (W) 7" x (D) 7.75"

Gift Tube Dimensions

(H) 7.625" x (W) 3.5" x (D) 3.5"



TWO LIGHT MODES

WHITE LIGHT:

- 600 Lumens / 4200K
- Replacement for 60W bulbs
- 40,000+ hours

NUV LEDs:

(395nm)

Kills mosquitoes that may carry diseases/viruses



- Zika
- West Nile
- Malaria & Others

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930990	6458	Z-Bug Bulb™	19.95	34.99	16 PIECES

NEBO
the
LiL Larry
POWER POCKET LIGHT

C-O-B LED POCKET LIGHT

Don't let the name fool you, LiL Larry™ packs enough power to take its rightful place, as the newest addition to the Larry™ family. LiL Larry is equipped with a 250 lumen C-O-B work light, featuring 3 light modes: high, low and emergency red flash. The anodized aluminum body and recessed LED housing ensure that LiL Larry is ready for any task.

LIGHT

- High-power 250 lumen C-O-B LED work light
- High-power C-O-B LED emergency red flasher

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- Steel clip
- Powerful magnetic base

OPERATION

- Top-positioned, ON/OFF button

BATTERIES

- Powered by 3 AAA batteries (included)

SPECS

- 0.2 lbs.
- (H) 6.0625" x (W) 0.625" x (D) 1"

U.S. PATENT

- 8,628,210

AVAILABLE COLORS




Top Positioned ON/OFF Button



Emergency Red Flasher



Anodized Aircraft-Grade Aluminum



Powerful Magnetic Base



NEBO
the
LiL Larry
POWER POCKET LIGHT

COUNTERTOP
DISPLAY

#6373 Display

- Display holds 3 pieces in front for consumer testing, additional pieces can be stored in the back as replenishments
- Each LiL Larry™ comes with a gift box.
- Product attaches securely to the display using the magnetic base

Display Dimensions

(H) 10" x (W) 5.5" x (D) 7.75"

Gift Box Dimensions

(H) 6.25" x (W) 1" x (D) 0.75"



THREE LIGHT MODES

HIGH:

- 250 Lumens
- 3 Hours
- 29 Meters

LOW:

- 95 Lumens
- 10 Hours
- 17 Meters

RED FLASH:

- 10 Hours



C-O-B (Chips on Board)

A new innovation in LED technology, C-O-B features smaller, easier clustered LED chips that are mounted directly to the circuit board. These LED chips work together as one lighting module. Because of the compact design, C-O-B outperforms traditional lighting by up to 50 times the light output per centimeter of light surface.

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930402	6373	LiL Larry™ C-O-B LED Work Light	14.95	28.95	18 PIECES
645397931027	6463	LiL Larry™ - Bulk Red	14.75	28.95	9 PIECES
645397931034	6464	LiL Larry™ - Bulk Black	14.75	28.95	9 PIECES
645397931041	6465	LiL Larry™ - Bulk Silver	14.75	28.95	9 PIECES
645397931058	6466	LiL Larry™ - Bulk Camo	14.95	28.95	9 PIECES

NEBO® the **BIG Larry** POWER WORK LIGHT

POWER C-O-B LED WORK LIGHT

The BIG Larry™ knows how to light up a room! Equipped with new C-O-B LED technology, the BIG Larry™ outputs 400 lumens of intense light. Secondary light modes include Low (160 lumens) and the Emergency Red Flash mode. This intense red light is perfect for distress signaling or roadside emergencies. The anodized aluminum body and recessed LED housing ensures that the BIG Larry™ can handle any situation.

LIGHT

- High-power 400 lumen C-O-B LED work light
- High-power C-O-B LED emergency red flasher

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- Powerful magnetic base

OPERATION

- Top-positioned, ON/OFF button

BATTERIES

- Powered by 3 AA batteries (included)

SPECS

- 0.45 lbs.
- (H) 7.4375" x (W) 0.875" x (D) 1.125"

AVAILABLE COLORS




Top Positioned ON/OFF Button



Emergency Red Flasher




Anodized Aircraft-Grade Aluminum



Powerful Magnetic Base



Top Positioned ON/OFF Button



Protective LED Housing



180° Rotating Magnetic Clip



Ergonomic Non-Slip Grip



NEBO® the **Larry** POWER C-O-B LED WORK LIGHT

POWER C-O-B LED WORK LIGHT

The Larry™ and Lucy™ are now **BRIGHTER THAN EVER!** Now, equipped with new C-O-B LED technology, the Larry™C and Lucy™C output **170 lumens** of intense light. The rotating magnetic clip gives you convenient hands-free lighting by attaching to virtually anything. The reinforced plastic body design is water and impact-resistant, making this light basically indestructible.

LIGHT

- High-power 170 lumen C-O-B LED work light

DESIGN

- Water and impact-resistant
- Ergonomic non-slip grip
- 180° rotating magnetic clip
- Protective LED housing

OPERATION

- Top-positioned, ON/OFF button

BATTERIES

- Powered by 3 AAA batteries (included)

SPECS

- 0.1870 lbs.
- (H) 6.375" x (W) 0.55" x (D) 1.25"

U.S. PATENT

- 8,628,210

AVAILABLE COLORS



THREE LIGHT MODES

HIGH:

- 400 Lumens
- 4.5 Hours
- 29 Meters

LOW:

- 160 Lumens
- 15 Hours
- 17 Meters

RED FLASH:

- 40 Hours



Display Dimensions

(H) 12" x (W) 5.5" x (D) 7.8125"

Gift Box Dimensions

(H) 7.5" x (W) 1.25" x (D) 1"

ONE LIGHT MODE

HIGH:

- 170 Lumens
- 5.6 Hours
- 20 Meters



Display Dimensions

(H) 8.75" x (W) 6" x (D) 6"

Gift Box Dimensions

(H) 6.5" x (W) 1.5" x (D) 0.75"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930365	6306	BIG Larry™ C-O-B LED Work Light	19.89	34.50	14 PIECES
645397930648	6382	BIG Larry™ C-O-B LED Work Light - Camo	19.89	34.50	7 PIECES
645397930686	6385	BIG Larry™ C-O-B LED Work Light - Silver	19.55	34.50	7 PIECES
645397930679	6384	BIG Larry™ C-O-B LED Work Light - Black	19.55	34.50	7 PIECES
645397930792	6413	BIG Larry™ C-O-B LED Work Light - Red	19.55	34.50	7 PIECES
645397930761	6393	BIG Larry™ Work Light Holster	2.75	4.99	7 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930402	6327	Larry™C C-O-B LED Work Light	7.75	12.95	24 PIECES
645397930464	6350	Larry™C C-O-B LED Work Light - Bulk Red	7.50	12.95	12 PIECES
645397930471	6351	Larry™C C-O-B LED Work Light - Bulk Blue	7.50	12.95	12 PIECES
645397930488	6352	Larry™C C-O-B LED Work Light - Bulk Gray	7.50	12.95	12 PIECES
645397930495	6353	Larry™C C-O-B LED Work Light - Bulk Yellow	7.50	12.95	12 PIECES
645397930501	6354	Larry™C C-O-B LED Work Light - Bulk Camo	7.75	12.95	12 PIECES
645397930518	6355	Lucy™C C-O-B LED Work Light - Bulk Pink	7.50	12.95	12 PIECES

NEBO®

Larry SILVER™


8 LED POCKET WORK LIGHT

The pocket light for professionals...the Larry Silver™ 8 LED Pocket Work Light is the essential handyman light. More durable metal body design and brighter 100 lumen output. You can't be handy if your hands aren't...well, handy. The rotating magnetic clip gives you convenient hands-free lighting by attaching to virtually anything.

- LIGHT**
- 8 high-power LEDs output 100 lumens
 - Fully dimmable beam (100% - 10%)
- DESIGN**
- Durable zinc alloy; water and impact-resistant
 - 180° rotating magnetic clip
 - Protective LED channel
- OPERATION**
- Top-positioned ON/OFF button; hold to activate dimming
- BATTERIES**
- Powered by 3 AAA batteries (included)
- SPECS**
- 0.25 lbs.
 - (L) 6.375" x (W) 0.55" x (D) 1.25"
- U.S. PATENT**
- 8,628,210




Top Positioned ON/OFF Button



180° Rotating Magnetic Clip



Protective LED Channel



Durable Zinc Alloy Design



Red Laser Pointer



180° Rotating Magnetic Clip



Ergonomic Non-Slip Grip



Separate Light & Laser Buttons



NEBO®

Larry™2

12 LED WORK LIGHT & LASER

Larry™2 has a few more LEDs under his belt and a red laser pointer that emits from the top of the light. Being the essential handyman light, the Larry™2 still has some of the features that made the Larry™ so great: the 180° rotating magnetic clip, reinforced plastic body design and ergonomic grip. More features... more lumens...same Larry™ style!

- LIGHT**
- 12 high-power LEDs output 160 lumens
- LASER**
- Red laser (<5mW / 650nm)
- DESIGN**
- Water and impact resistant
 - Ergonomic non-slip grip
 - 180° rotating magnetic clip
 - Protective LED housing
- OPERATION**
- Front-positioned ON/OFF laser and light buttons
- BATTERIES**
- Powered by 3 AAA batteries (included)
- SPECS**
- 0.2 lbs.
 - (L) 6.75" x (W) 0.75" x (D) 1.5"
- U.S. PATENT**
- 8,414,142

AVAILABLE COLORS



TWO LIGHT MODES

- HIGH:**
100 Lumens
- 3 Hours
 - 33 Meters
- LOW:**
10 Lumens
- 20 Hours



Display Dimensions
(H) 8.75" x (W) 6" x (D) 6"

TWO LIGHT MODES

- LIGHT:**
160 Lumens
- 2 Hours
 - 40 Meters
- LASER:**
<5mW
- 72 Hours
 - 412 Meters



Display Dimensions
(H) 6.25" x (W) 10.23" x (D) 5"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930068	6194	Larry Silver™ 8 LED Work Light	14.00	24.99	16 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397929222	6006	Larry™2 12 LED Work Light	9.00	16.99	24 PIECES
645397929345	6051	Larry™2 Work Light - Bulk Orange	8.75	16.99	12 PIECES
645397929352	6052	Larry™2 Work Light - Bulk Gray	8.75	16.99	12 PIECES
645397929369	6053	Larry™2 Work Light - Bulk Black	8.75	16.99	12 PIECES
645397929376	6054	Larry™2 Work Light - Bulk Green	8.75	16.99	12 PIECES
645397929383	6055	Lucy™2 Work Light - Bulk Pink	8.75	16.99	12 PIECES

NEBO® SLYDE^Z

FLASHLIGHT & WORK LIGHT

Much like its predecessor, the Z features all of the 2-in-1 innovation as the original SLYDE™ with a few additions. What does "Z" mean?...ZOOM, the SLYDE™Z features a 4x adjustable zoom. The Z also has a fully dimmable function for the flashlight and work light as well as an Instant ON feature that automatically activates the C-O-B work light when opened.

LIGHT

- High-power 4750 LUX LED flashlight
- High-power 250 lumen C-O-B work light

DESIGN

- Convex lens
- Tactical edge
- 4x adjustable zoom
- Anodized aircraft-grade aluminum; water and impact-resistant
- Dimmable beam
- Work light is concealed inside the flashlight body
- Powerful magnetic base

OPERATION

- Side-positioned ON/OFF button; hold to activate dimming
- C-O-B Work light automatically turns ON when opened and OFF when closed

BATTERIES

- Powered by 4 AA batteries (included)

SPECS

- 1.09 lbs
- Length: Compacted: 7.75" / Extended: 10.3125"
- Diameter: (Head) 2.0625" / (Barrel) 1.5"



Tactical Edge & Convex Lens




4x Adjustable Zoom



Extendable Body Reveals C-O-B LED



Powerful Magnetic Base



Tactical Edge



Anodized Aircraft-Grade Aluminum



Extendable Body Reveals C-O-B LED



Powerful Magnetic Base



NEBO® SLYDE

FLASHLIGHT & WORK LIGHT

Combining the best that NEBO® has to offer, the SLYDE™ features a powerful LED flashlight and C-O-B work light all in one. At first glance, the SLYDE™ appears to be a simple, strong flashlight, emitting 250 lumens of intense white light...and it is! However, you will see the SLYDE™ is much more. The body of the SLYDE™ conceals a powerful 190 lumen work light. To reveal the C-O-B work light, just SLYDE to open!

LIGHT

- High-power 250 lumen LED flashlight
- High-power 190 lumen C-O-B work light

DESIGN

- Tactical edge
- Anodized aircraft-grade aluminum; water and impact-resistant
- Work light is concealed inside the flashlight body; just SLYDE to reveal
- Powerful magnetic base

OPERATION

- Side-positioned ON/OFF button with Soft Touch Technology

BATTERIES

- Powered by 4 AAA batteries (included)

SPECS

- 0.65 lbs.
- Length: Compacted: 6.5" / Extended: 9"
- Diameter: (Head) 1.625" / (Barrel) 1.3125"

AVAILABLE COLORS



TWO LIGHT MODES

FLASHLIGHT:

- 4750 LUX
- 2.5 Hours
- 276 Meters

WORK LIGHT:

- 250 Lumens
- 3.5 Hours
- 21 Meters



Display Dimensions
(H) 12.36" x (W) 9.09" x (D) 9.65"

Each SLYDE™Z includes a gift box and instruction manual.

TWO LIGHT MODES

FLASHLIGHT:

- 250 Lumens
- 2 Hours
- 220 Meters

WORK LIGHT:

- 190 Lumens
- 3.5 Hours
- 18 Meters



Display Dimensions
(H) 14.125" x (W) 7.5625" x (D) 8"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930112	6267	SLYDE™Z Flashlight & Work Light	36.99	59.99	8 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397929857	6156	SLYDE™ Flashlight & Work Light	22.50	39.99	16 PIECES
645397930662	6383	SLYDE™ Flashlight & Work Light - Bulk Camo	23.40	39.99	8 PIECES

NEBO® TWYST™Z

WORK LIGHT, LANTERN & FLASHLIGHT

Introducing the newest member of the TWYST™ lineup...TWYST™Z! The TWYST™Z features the same C-O-B lighting options as the original TWYST™: a high-power work light, lantern and flashlight! The TWYST™Z now features a 4x adjustable zoom. A powerful magnetic base also provides convenient hands-free lighting. TWYST™Z...shaping light like never before!

- LIGHT**
- 75 Lumen C-O-B LED Work Light
 - 200 Lumen C-O-B LED Lantern
 - 200 Lumen Flashlight


- DESIGN**
- 4x adjustable zoom
 - Enhanced C-O-B LED Technology
 - Tactical edge
 - Fully dimmable beam
 - Anodized aircraft-grade aluminum; water and impact-resistant
 - Powerful magnetic base

- OPERATION**
- Side-positioned ON/OFF button


- BATTERIES**
- Powered by 4 AAA batteries (included)

- SPECS**
- 0.55 lbs.
 - Length: Compacted: 6.3125" / Extended: 6.75"
 - Diameter: (Head) 1.75" / (Barrel) 1"

AVAILABLE COLORS



Twist to reveal C-O-B LED



TWYST™ Bezel Reveals C-O-B



75 Lumen C-O-B Work Light



110 Lumen C-O-B Work Light



200 Lumen C-O-B Lantern



250 Lumen C-O-B Lantern



Powerful Magnetic Base



Powerful Magnetic Base and Retractable Base Stabilizers



NEBO® TWYST™

WORK LIGHT, LANTERN & FLASHLIGHT

The TWYST™ features a high-power work light, lantern and flashlight all in one! The TWYST™ uses a revolutionary new C-O-B LED technology that allows the shaping of light into full 3D patterns, giving optimal, bright, uniform light exactly where it's needed. Retractable base stabilizers are positioned at the bottom of the TWYST™ to give added stability on uneven surfaces. A powerful magnetic base also provides convenient hands-free lighting.

- LIGHT**
- 110 Lumen C-O-B LED Work Light
 - 250 Lumen C-O-B LED Lantern
 - 3400 LUX LED Flashlight


- DESIGN**
- Enhanced C-O-B LED Technology
 - Tactical edge
 - Fully dimmable beam
 - Anodized aircraft-grade aluminum; water and impact-resistant
 - Retractable base stabilizers
 - Powerful magnetic base

- OPERATION**
- Side-positioned ON/OFF button

- BATTERIES**
- Powered by 4 AA batteries (included)

- SPECS**
- 0.85 lbs.
 - Length: Compacted: 7.5" / Extended: 7.875"
 - Diameter: (Head) 2" / (Barrel) 1.25"

AVAILABLE COLORS



THREE LIGHT MODES

- HIGH:**
75 Lumens
• 10 Hours
• 11 Meters

- LOW:**
10 Lumens
• 26 Hours
• 4 Meters

- HIGH:**
200 Lumens
• 2 Hours
• 13 Meters

- LOW:**
20 Lumens
• 16 Hours
• 4 Meters

- HIGH:**
200 Lumens
• 2 Hours
• 107 Meters

- LOW:**
20 Lumens
• 20 Hours
• 34 Meters

WORK LIGHT - 120° Light Coverage

LANTERN - 360° Light Coverage

FLASHLIGHT

THREE LIGHT MODES

- HIGH:**
110 Lumens
• 13.5 Hours
• 15 Meters

- LOW:**
10 Lumens
• 96 Hours
• 1.5 Meters

- HIGH:**
250 Lumens
• 4 Hours
• 15 Meters

- LOW:**
25 Lumens
• 60 Hours
• 1.5 Meters

- HIGH:**
3400 LUX
• 4 Hours
• 233 Meters

- LOW:**
350 LUX
• 40 Hours
• 74 Meters

WORK LIGHT - 120° Light Coverage

LANTERN - 360° Light Coverage

FLASHLIGHT

Display Dimensions
(H) 8.5" x (W) 9.25" x (D) 7"

Gift Box Dimensions
(H) 6.5" x (W) 1.875" x (D) 1.875"



Display Dimensions
(H) 10.3125" x (W) 9.25" x (D) 7.125"

Gift Tube Dimensions
(H) 8" x (W) 2.375"



UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930563	6372	TWYST™Z Work Light, Lantern & Flashlight	21.50	39.99	16 PIECES
645397930907	6436	TWYST™Z Black Bulk	21.25	39.99	12 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930266	6296	TWYST™ Work Light, Lantern & Flashlight	42.90	79.99	10 PIECES
645397930419	6328	TWYST™ Black	42.90	79.99	10 PIECES

NEBO®

CaseBrite™

PHONE CASE + POWERFUL LIGHT

The NEBO® CaseBrite™ offers more than just protection for your mobile device. The CaseBrite™ features a high-power, 200 lumen C-O-B flashlight that is up to 12x brighter than a standard smart phone light. Designed specifically to not draw from your phone's battery, each CaseBrite™ is independently powered by an internal, rechargeable lithium-ion battery.

LIGHT
• High-power 200 lumen C-O-B LED

DESIGN
• Impact-resistant, non-slip rubber case
• Screen protection lip
• Fully dimmable
• Slim 15mm profile
• Battery life indicator
• Fits iPhone 6/6S & 6/6S Plus


OPERATION
• Rear-positioned, ON/OFF button

ACCESSORIES
• USB to Micro USB charging cable (included)

BATTERIES
• Internal, rechargeable lithium-ion battery
(Recharge time - up to 3 hours)

SPECS
• 0.2 lbs.
• 6/6S - (H) 5.5" x (W) 2.75" x (D) 0.6"
• 6/6S Plus - (H) 6.3125" x (W) 3.125" x (D) 0.6"

AVAILABLE COLORS



Easy Reach ON/OFF Button



USB to Micro USB Cable Included



Easy Access to Buttons & Ports



Battery Life Indicator



6x Adjustable Zoom



Anodized Aircraft-Grade Aluminum



Flex-Power™
3, 6 or 9 AA Batteries



Glow-in-the-Dark ON/OFF Button



NEBO®

SEVEN-Z™

770 LUMEN FLASHLIGHT

You asked; we delivered. The SEVEN-Z™ is the answer to the demands for a high-lumen flashlight...770 lumens to be exact. Featuring OC™ Technology and all-new, Flex-Power™ which allows the flashlight to be powered by 3, 6 or 9 AA batteries, depending on the user's preference.

LIGHT
• High-power 770 lumen (6500 LUX) LED flashlight


DESIGN
• Convex Lens
• OC™ Technology
• Heat sink design
• 6x adjustable beam
• Anodized aircraft-grade aluminum; water and impact-resistant
• Flex-Power™

OPERATION
• Rear-positioned, glow-in-the-dark ON/OFF button

BATTERIES
• Powered by Flex-Power™:
3, 6 or 9 AA batteries (9 AA batteries included)

SPECS
• 1.25 lbs.
• Length: Compacted: 8.8125" / Extended: 9.625"
• Diameter: (Head) 2" / (Barrel) 1.5"

AVAILABLE COLORS



THREE LIGHT MODES

- | | | |
|--|--|---|
| HIGH:
200 Lumens
• 3 Hours
• 30 Meters | LOW:
20 Lumens
• 24 Hours | STROBE:
200 Lumens
• 7 Hours |
|--|--|---|



#6349 Display Dimensions
(H) 12.5" x (W) 10" x (D) 9.25"

#6347/#6386 Box Dimensions (6/6S)
(H) 6.75" x (W) 4.375" x (D) 1"

#6348/#6387 Box Dimensions (6/6S Plus)
(H) 7.5" x (W) 4.375" x (D) 1"

TWO LIGHT MODES

HIGH: 770 Lumens 6500 LUX • 7 Hours • 322 Meters	LOW: 220 Lumens 1600 LUX • 25 Hours • 160 Meters	HIGH: 700 Lumens 5900 LUX • 4.5 Hours • 307 Meters	LOW: 200 Lumens 1450 LUX • 23 Hours • 152 Meters	HIGH: 550 Lumens 4650 LUX • 2.5 Hours • 273 Meters	LOW: 130 Lumens 1150 LUX • 13 Hours • 136 Meters
9 AA BATTERIES		6 AA BATTERIES		3 AA BATTERIES	

FLEX-POWER™

The SEVEN-Z™ is fueled by FLEX-POWER™, technology that allows the flexibility to use different quantities of batteries for power the light. SEVEN-Z™ will function with 3 AA, 6 AA or with the optimal 9 AA batteries for full 770 lumens of power.

Display Dimensions
(H) 9.625" x (W) 11" x (D) 3.75"

Gift Box Dimensions
(H) 2.375" x (W) 11" x (D) 3.75"



UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930433	6347	CaseBrite™ iPhone 6/6S - Black	29.50	49.99	4 PIECES
645397930440	6348	CaseBrite™ iPhone 6/6S Plus - Black	29.50	49.99	4 PIECES
645397930693	6386	CaseBrite™ iPhone 6/6S - White	29.50	49.99	4 PIECES
645397930709	6387	CaseBrite™ iPhone 6/6S Plus - White	29.50	49.99	4 PIECES
645397930457	6349	CaseBrite™ Countertop Display	FREE with 12 piece order		1 PIECE

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930242	6294	SEVEN-Z™ 770 Lumen Flashlight	44.95	89.95	6 PIECES
645397930808	6414	SEVEN-Z™ 770 Lumen Flashlight - Camo	45.75	89.95	6 PIECES

NEBO® TWIN PUCKS

TASK LIGHT & EMERGENCY BEACON

Twin Pucks features a task light and an emergency beacon all-in-one. Both lights attach magnetically to each other, but can also operate independently and are separately powered. The task light provides hands-free lighting in three different ways: 180° adjustable stand, hanging hole or the magnetic base. The emergency beacon also has a magnet in the back to adhere to metal surfaces.


- LIGHT**
- High-power 160 lumen C-O-B LED task light
 - 8 red high-power LED emergency beacon

- DESIGN**
- Water and impact-resistant
 - Hanging hole
 - 180° adjustable stand
 - Rubber grips
 - Task light and emergency beacon connect magnetically


- OPERATION**
- Dual buttons for task light and emergency beacon

- BATTERIES**
- C•O•B LED powered by 3 AAA batteries (included)
 - 8 red LEDs powered by 2 AAA batteries (included)


- SPECS**
- 0.46 lbs.
 - Diameter: 3.36"




Hanging Hole



180° Adjustable Stand



Magnetic Attachment



Powerful Magnetic Base



Diffuser Dome



Glow-in-the-Dark Button



Rotating Carabiner Clip



NEBO® LUMORE™

DOME LIGHT & FLASHLIGHT

Introducing the latest in ultimate versatile lighting...the LUMORE™. This brilliant clip light features a 25 lumen LED. Surrounding the LED is a dome, which doubles the features of the light output. The dome acts as a diffuser to create ambient light, while a small hole allows light to shine through for standard flashlight use. The LUMORE™ is equipped with a flat base and a rotating clip to provide convenient hands-free lighting in two different ways.

- LIGHT**
- High-power 25 lumen LED


- DESIGN**
- Anodized aircraft-grade aluminum; water and impact-resistant
 - Carabiner clip
 - Glow-in-the-dark button
 - Diffuser dome

- OPERATION**
- Rear-positioned ON/OFF button

- BATTERIES**
- Powered by 3 LR44 batteries (included)

- SPECS**
- 0.2 lbs.
 - (H) 3.625" x (W) 0.75"

AVAILABLE COLORS



WHITE LIGHT

THREE LIGHT MODES

- HIGH: 160 Lumens** • 10 Hours / 24 Meters
- MEDIUM: 80 Lumens** • 20 Hours / 16 Meters
- LOW: 10 Lumens** • 48 Hours / 7 Meters

RED LIGHT

FIVE LIGHT MODES

- ROTATE FLASH** • 38 Hours / 1.6 KM
- 8 LEDs STEADY ON** • 7.5 Hours / 1.6 KM
- 8 LEDs FLASH** • 27 Hours / 1.6 KM
- 8 LEDs S.O.S.** • 7.5 Hours / 1.6 KM
- 4 LEDs STEADY ON** • 17.5 Hours / 1.6 KM



Display Dimensions
(H) 12" x (W) 5.875" x (D) 10.125"

Clamshell Dimensions
(H) 8.25" x (W) 5" x (D) 0.875"

THREE LIGHT MODES

- HIGH: 25 Lumens** • 1 Hour • 9 Meters
- LOW: 10 Lumens** • 3.5 Hours • 6 Meters
- STROBE:** • 4.5 Hours • 9 Meters



Display Dimensions
(H) 9" x (W) 6.5" x (D) 6.5"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930747	6391	Twin Pucks Task Light & Emergency Beacon	14.95	27.50	12 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930426	6329	LUMORE™ Dome Light and Flashlight	4.95	8.95	48 PIECES
645397930525	6357	LUMORE™ - Bulk White	4.95	8.95	12 PIECES
645397930532	6358	LUMORE™ - Bulk Red	4.95	8.95	12 PIECES
645397930549	6359	LUMORE™ - Bulk Blue	4.95	8.95	12 PIECES
645397930556	6360	LUMORE™ - Bulk Green	4.95	8.95	12 PIECES

NEBO® WORKBRITE 2™

C-O-B LED WORK LIGHT

The WORKBRITE 2™ adapts to your work environment, making it the handiest of work lights. Equipped with a 200 lumen C-O-B LED work light, the WORKBRITE 2™ also features a 100 lumen flashlight and a rear, emergency red flasher LED. The WORKBRITE 2™ provides hands-free lighting in three different ways: a hanging hook, a 200° pivoting stand and a magnetic base. Whether you are under the hood, under the sink or just out in the dark, the WORKBRITE 2™ works great for any application.

LIGHT

- High-power 100 lumen LED flashlight
- High-power 200 lumen C-O-B LED work light
- Emergency Red Flasher LED

DESIGN

- Water and impact-resistant
- Ergonomic, non-slip grip
- 200° pivoting stand
- Collapsible, hanging hook
- Powerful magnetic base

OPERATION

- Front-positioned, ON/OFF button
- Emergency Red Flasher LED is independently controlled; press light to activate

BATTERIES

- Powered by 3 AAA batteries (included)

SPECS

- 0.35 lbs.
- (H) 8.5" x (W) 2" x (D) 1.5"



Collapsible, Hanging Hook



Emergency Red Flasher LED



200° Pivoting Stand



Powerful Magnetic Base



Collapsible, Hanging Hook



Emergency Red Flasher LED



200° Pivoting Stand



16.5" USB to Micro USB Cable



Powerful Magnetic Base



NEBO® THE RECHARGEABLE WORKBRITE 2™

RECHARGEABLE WORK LIGHT

Never worry about replacing batteries again, with The Rechargeable WORKBRITE 2™. This work light is equipped with a 220 lumen C-O-B LED work light, a 120 lumen flashlight and a rear, emergency red flasher LED. The WORKBRITE 2™ provides hands-free lighting in three different ways: a hanging hook, a 200° pivoting stand and a magnetic base. Whether you are under the hood, under the sink or just out in the dark, the WORKBRITE 2™ works great for any application.

LIGHT

- High-power 120 lumen LED flashlight
- High-power 220 lumen C-O-B LED work light
- Emergency Red Flasher LED

DESIGN

- Fully rechargeable
- Water and impact-resistant
- Ergonomic, non-slip grip
- 200° pivoting stand
- Collapsible, hanging hook
- Powerful magnetic base

OPERATION

- Front-positioned, ON/OFF button
- Emergency Red Flasher LED is independently controlled; press light to activate

ACCESSORIES

- 16.5" USB to Micro USB cable included

BATTERIES

- Powered by 1 18650 Li-ion Rechargeable Battery

SPECS

- 0.35 lbs.
- (H) 8.5" x (W) 2" x (D) 1.5"

THREE LIGHT MODES

WORK LIGHT:

- 200 Lumens
- 3 Hours
- 20 Meters

FLASHLIGHT:

- 100 Lumens
- 8 Hours
- 47 Meters

RED FLASH:

- 200 Hours



Display Dimensions
(H) 12.75" x (W) 5.5" x (D) 7.75"

Gift Box Dimensions
(H) 8.5" x (W) 2" x (D) 1.5"

THREE LIGHT MODES

WORK LIGHT:

- 220 Lumens
- 6 Hours
- 22 Meters

FLASHLIGHT:

- 120 Lumens
- 8 Hours
- 52 Meters

RED FLASH:

- 200 Hours



Display Dimensions
(H) 13.25" x (W) 5.5" x (D) 7.75"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930341	6304	WORKBRITE 2™ C-O-B LED Work Light	18.33	32.50	12 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930358	6305	The Rechargeable WORKBRITE 2™	25.74	44.50	12 PIECES

NEBO® PaL

RECHARGEABLE POWER & LIGHT

This portable, rechargeable flashlight serves as a backup power source for mobile phones and other rechargeable USB electronic devices. Ideal for travel, the PaL conveniently fits in your pocket, purse or briefcase.

LIGHT

- High-power 50 lumen LED

DESIGN

- Fully rechargeable
- Power bank for your USB powered devices
- Anodized aircraft-grade aluminum; impact-resistant
- USB & Micro USB charging ports
- Apple® & Android™ compatible
- Charging indicator tells charging status of flashlight and your USB powered devices

OPERATION

- Rear-positioned ON/OFF button with charging indicator

ACCESSORIES

- USB to Micro USB cable included

BATTERIES

- Powered by 1 internal 2600 mAh Lithium-Ion Battery (Type 18650)

SPECS

- 0.17 lbs.
- (L) 3.6875" x (W) 0.875"

AVAILABLE COLORS



USB & Micro USB Charging Ports



10" USB to Micro USB Cable Included



Apple® Compatible



Android™ Compatible



Anodized Aircraft-Grade Aluminum



Charging Indicator & Twist Dial



Base Fits any 12V Outlet



NEBO® TRANSPORT®

DC RECHARGEABLE LIGHT

The TRANSPORT® is a compact, rechargeable flashlight that provides powerful bright light at your fingertips! The TRANSPORT® is compatible with any DC 12V socket. Just plug directly into your car, truck, boat or any other 12V outlet. Ideal for travel, the TRANSPORT® conveniently fits in your pocket, purse or briefcase.

LIGHT

- High-power 125 lumen LED

DESIGN

- Fully rechargeable
- Fits any 12V outlet (car cigarette lighter)
- Anodized aircraft-grade aluminum; water and impact-resistant
- Charging indicator light

OPERATION

- Top-positioned ON/OFF dial; twist to activate


BATTERIES

- Powered by 1 16340 Lithium Ion rechargeable battery (included)

SPECS

- 0.15 lbs.
- (L) 3.6875" x (W) 0.875"

AVAILABLE COLORS



ONE LIGHT MODE

50 LUMENS

- 17.5 Hours
- 54 Meters



Display Dimensions
(H) 9" x (W) 6.25" x (D) 5.375"

Individual Box Dimensions
(H) 6.25" x (W) 2" x (D) 1.5"

ONE LIGHT MODE

125 LUMENS

- 1 Hour
- 90 Meters



Display Dimensions
(H) 7.25" x (W) 7.625" x (D) 6.25"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930099	6227	PaL Rechargeable Power and Light	14.75	24.99	18 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930396	6311	TRANSPORT® DC Rechargeable Flashlight	14.99	27.99	18 PIECES

NEBO[®] O² BEAM™

OPTIMIZED OPTICS FLASHLIGHT

This 8105 LUX LED flashlight, paired with our O² Technology™, makes the O² BEAM™ the most cost and energy efficient flashlight in its class, with performance that you have to see to believe!

LIGHT

- High-power 8105 LUX LED

DESIGN

- Tactical edge
- Convex lens
- Lo-Light™ self-powered, glow-light source
- 4x adjustable beam
- Anodized aircraft-grade aluminum; water and impact-resistant
- Smart Select Dial
- Low battery indicator

OPERATION

- Rear-positioned, glow-in-the-dark ON/OFF button with Smart Select Dial

ACCESSORIES

- Lanyard included
- Gift box and heavy duty carrying case

BATTERIES


- Powered by 4 AA batteries (included)

SPECS

- 1.05 lbs.
- Length: Compacted: 8.0625" / Extended: 8.625"
- Diameter: (Head) 2.25" / (Barrel) 1.5"

U.S. PATENT

- D657,840 and other International Patents Pending



Lo-Light™ Self-Powered, Glow-Light Source



4x Adjustable Zoom



Lanyard Included



Smart Select Dial and Glow-in-the-Dark Button




4x Adjustable Zoom



Lanyard Loop and Magnetic Base



USB to Micro USB Cable



MagDock Battery Indicator



NEBO[®] REDLINE[®] RC with MAGDOCK

RECHARGEABLE FLASHLIGHT

The REDLINE[®] RC™ with MagDock features a magnetic charging station that docks and charges your REDLINE[®]. Small enough to fit in the palm of your hand, the RC™ is fully equipped with all of the features that make the REDLINE[®] series so popular.

LIGHT

- High-power 320 lumen LED

DESIGN

- 4x adjustable zoom
- Anodized aircraft-grade aluminum; water and impact-resistant
- OC™ Technology
- Convex lens
- Signature Red Ring™
- Steel belt/pocket clip
- Magnetic base
- Protective LED housing
- Charging indicator light

OPERATION

- Side-positioned, ON/OFF button

ACCESSORIES

- USB to Micro USB cable included
- Lanyard included

BATTERIES

- Internal, rechargeable lithium-ion battery (Recharge time - up to 2 hours)

SPECS

- 0.25 lbs.
- Length: Compacted: 3.5625" / Extended: 3.875"
- Diameter: 1.25"

U.S. PATENT

- 8,628,210

FIVE LIGHT MODES

HIGH:	MEDIUM:	LOW:	BEACON:	STROBE:
8105 LUX	4230 LUX	1100 LUX	8105 LUX	8105 LUX
• 4 Hours	• 10 Hours	• 62 Hours	• 200 Hours	• 70 Hours
• 360 Meters	• 260 Meters	• 133 Meters	• 360 Meters	• 360 Meters



Display Dimensions

(H) 9.29" x (W) 10.82" x (D) 10.27"

Each O² BEAM™ includes a gift box, heavy duty carrying case, owner's guide and instruction manual.

FOUR LIGHT MODES

HIGH:	MEDIUM:	LOW:	STROBE:
320 Lumens	125 Lumens	32 Lumens	320 Lumens
• 1 Hour	• 2 Hours	• 9 Hours	• 2 Hours
• 110 Meters	• 70 Meters	• 35 Meters	• 110 Meters



Display Dimensions
(H) 11.125" x (W) 5.5" x (D) 7.75"

Gift Box Dimensions
(H) 4.2" x (W) 2.95" x (D) 2.35"



OPTIMIZED OPTICS (O²)

The natural tendency of light is to disperse into infinite directions. We use optics to help us focus the light's intensity in one direction. The Optimized Optics bend the light closer toward the center of the beam. The result is a hotter, brighter spotlight with the lowest power consumption in its class.



OPTIMIZED CLARITY

Eliminating inconsistencies in light, the OC™ (Optimized Clarity) Technology provides intense, clear, pristine light that is easy on the eyes. This technology allows the light beam to be as bright on the edge as it is in the center when used in flood mode.

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397929185	6000	O ² BEAM™ 8105 LUX Flashlight	67.00	119.99	4 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930754	6392	REDLINE [®] RC™ with MagDock	24.50	44.99	10 PIECES

NEBO®
CLASSIC
REDLINE®

HIGH-POWER TACTICAL LIGHT

Another addition to the REDLINE® OC™ lineup is the Classic REDLINE® OC™. Maintaining some of the key features as it's predecessor, the Classic also features an intense power upgrade...2640 LUX to be exact.

LIGHT

- High-power 2640 LUX LED

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- OC™ Technology
- Convex lens
- Signature Red Ring™
- Tactical edge
- 6x adjustable beam
- Dual-direction belt/pocket clip
- Magnetic base

OPERATION

- Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

BATTERIES

- Powered by 3 AAA batteries (included)

SPECS

- 0.32 lbs.
- Length: Compacted: 4.5" / Extended: 4.75"
- Diameter: (Head) 1.5" / (Barrel) 1"

U.S. PATENT

- 659,869 S



Tactical Edge



Actual Size Comparison



6x Adjustable Zoom



6x Adjustable Zoom




Dual-Direction Belt/Pocket Clip



Steel Belt/Pocket Clip



Glow-in-the-Dark Button and Magnetic Base



Glow-in-the-Dark Button and Magnetic Base



NEBO®
MICRO
REDLINE®

HIGH-POWER MICRO LIGHT

Don't let the micro size fool you...the Micro REDLINE® OC™ packs enough power to carry the REDLINE® name. This light is small enough to fit in the palm of your hand, but bright enough for any situation. Equipped with OC™ Technology the Micro has a perfectly dispersed beam of light while in flood mode. The Micro REDLINE® OC™...small never shined so big!

LIGHT

- High-power 360 LUX LED

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- OC™ Technology
- Convex lens
- Signature Red Ring™
- 6x adjustable beam
- Steel belt/pocket clip
- Magnetic base

OPERATION

- Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

BATTERIES

- Powered by 1 CR123A battery (included)

SPECS

- 0.1 lbs.
- Length: Compacted: 2.625" / Extended: 3.15"
- Diameter: (Head) 0.875" / (Barrel) 0.8125"

U.S. PATENT

- 659,869 S

FOUR LIGHT MODES

HIGH:	MEDIUM:	LOW:	STROBE:	S.O.S.:
2640 LUX	1226 LUX	476 LUX	2640 LUX	2640 LUX
• 2.5 Hours	• 6.5 Hours	• 20 Hours	• 24 Hours	• 24 Hours
• 206 Meters	• 140 Meters	• 87 Meters	• 206 Meters	• 206 Meters

*NOTE: Light resets to first light mode (HIGH) after being OFF for 5 seconds.

FOUR LIGHT MODES

HIGH:	MEDIUM:	LOW:	STROBE:
360 LUX	183 LUX	39 LUX	360 LUX
• 6 Hours	• 12 Hours	• 15 Hours	• 12 Hours
• 76 Meters	• 54 Meters	• 25 Meters	• 76 Meters

*NOTE: Light resets to first light mode (HIGH) after being OFF for 20 seconds.



OPTIMIZED CLARITY

Eliminating inconsistencies in light, the OC™ (Optimized Clarity) Technology provides intense, clear, pristine light that is easy on the eyes. This technology allows the light beam to be as bright on the edge as it is in the center when used in flood mode.

Display Dimensions
(H) 7.125" x (W) 7.48" x (D) 8.267"



OPTIMIZED CLARITY

Eliminating inconsistencies in light, the OC™ (Optimized Clarity) Technology provides intense, clear, pristine light that is easy on the eyes. This technology allows the light beam to be as bright on the edge as it is in the center when used in flood mode.

Display Dimensions
(H) 8" x (W) 6" x (D) 3.875"



UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930174	6273	Classic REDLINE® OC™ Flashlight	21.00	39.99	12 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930167	6272-A	Micro REDLINE® OC™ Flashlight	11.00	19.99	16 PIECES

NEBO®
REDLINE®
SELECT

HIGH-POWER 2950 LUX LIGHT

To improve functionality of the 5 light modes, the REDLINE® Select features a Smart Select Dial to quickly and conveniently choose your light mode while the light is on or off.

LIGHT

- High-power 2950 LUX LED

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- Convex lens
- Signature Red Ring™
- Tactical edge
- 4x adjustable beam
- Steel belt/pocket clip
- Magnetic base
- Low battery indicator

OPERATION

- Rear-positioned, glow-in-the-dark ON/OFF button with Smart Select Dial

ACCESSORIES

- Lanyard included

BATTERIES

- Powered by 3 AAA batteries (included)



SPECS

- 0.7 lbs.
- Length: Compacted: 4.6875" / Extended: 5"
- Diameter: (Head) 1.5" / (Barrel) 1"

U.S. PATENT

- 659,869 S

AVAILABLE COLORS



Tactical Edge and Signature Red Ring™



Stealth Ring



Steel Belt/Pocket Clip & Lighting Information



Magnetic Base and Smart Select Dial



Stealth Ring



AC & USB Cable Accessories



USB Input/Output Charging Port



Stealth Light, Magnetic Base and Smart Select Dial



NEBO®
REDLINE®
SELECT RC

RECHARGEABLE FLASHLIGHT

This fully rechargeable flashlight offers a smart select dial, adjustable beam and also acts as a power bank for your USB powered device.

LIGHT

- High-power 3100 LUX LED
- Button stealth light, perfect for low light situations

DESIGN

- Fully rechargeable
- Power bank for your USB powered devices
- Anodized aircraft-grade aluminum; water and impact-resistant
- Convex lens
- Signature Red Ring™
- Heat sink design
- Tactical edge
- 4x adjustable beam
- Steel belt/pocket clip
- Anti-roll tactical grip ring
- Magnetic base
- Charging indicator

OPERATION

- Rear-positioned, glow-in-the-dark ON/OFF button with Smart Select Dial

ACCESSORIES

- AC & USB cables included
- Lanyard included

BATTERIES

- One 18650 Li-ion rechargeable battery (included)

SPECS

- 0.5 lbs.
- Length: Compacted: 6.25" / Extended: 6.75"
- Diameter: (Head) 1.625" / (Barrel) 1.3125"

U.S. PATENT

- 659,869 S

FIVE LIGHT MODES

- | | | | | |
|---|--|---|--|--|
| HIGH:
2950 LUX
• 2 Hours
• 198 Meters | MEDIUM:
1230 LUX
• 5 Hours
• 96 Meters | LOW:
305 LUX
• 12 Hours
• 37 Meters | S.O.S.:
2950 LUX
• 60 Hours
• 198 Meters | STROBE:
2950 LUX
• 60 Hours
• 198 Meters |
|---|--|---|--|--|



Display Dimensions
(H) 7.75" x (W) 7.94" x (D) 7.94"

FIVE LIGHT MODES

- | | | | | |
|---|---|---|---|---|
| HIGH:
3100 LUX
• 2.5 Hours
• 222 Meters | MEDIUM:
1550 LUX
• 6 Hours
• 130 Meters | LOW:
310 LUX
• 15 Hours
• 60 Meters | STROBE:
3100 LUX
• 8 Hours
• 222 Meters | STEALTH LIGHT:
Green Low Light in Button
• 120 Hours
• 0.9 Meters |
|---|---|---|---|---|



Display Dimensions
(H) 13.75" x (W) 8.5" x (D) 9"

Acrylic Box Dimensions
(H) 9.25" x (W) 3" x (D) 3"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397111276	5620	REDLINE® Select Flashlight - Black	31.00	54.99	9 PIECES
645397066125	5955	REDLINE® Select Flashlight - Titanium	31.00	54.99	9 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397930013	6189	REDLINE® Select RC™ Flashlight	46.50	80.00	6 PIECES


NEBO® REDLINE®

HIGH-POWER 2185 LUX LIGHT

The ability to bring high-end technology to a compact, fully redesigned, extremely powerful light source is finally here. In an automobile, red-lining means reaching the peak of it's performance; with NEBO® REDLINE® we are harnessing the maximum power of this flashlight with 2185 LUX of blinding bright light.

- LIGHT**
- High-power 2185 LUX LED
- DESIGN**
- Anodized aircraft-grade aluminum; water and impact-resistant
 - Convex lens
 - Signature Red Ring™
 - Tactical edge
 - 4x adjustable beam
 - Magnetic base
- OPERATION**
- Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology
- BATTERIES**
- Powered by 3 AAA batteries (included)
- SPECS**
- 0.428 lbs.
 - Length: Compacted: 4.34" / Extended: 4.7"
 - Diameter: (Head) 1.5" / (Barrel) 1"
- U.S. PATENT**
- 659,869 S

AVAILABLE COLORS



Tactical Edge and Signature Red Ring™



4x Adjustable Zoom



Glow-in-the-Dark Button and Magnetic Base



Tactical Edge and Signature Red Ring™



4x Adjustable Zoom



Steel Belt/Pocket Clip



Glow-in-the-Dark Button and Magnetic Base



NEBO® SE REDLINE®

HIGH-POWER 2800 LUX LIGHT

More features...more brightness...same great quality. The SE REDLINE® has 5 lighting modes, separated into two categories, primary and secondary. Turning the flashlight on and off gives you the primary lighting mode, which is 2800 LUX of intense white light. The secondary lighting modes, Medium, Low, S.O.S. and Defensive Strobe can be activated by holding down the power button for 3 seconds.

- LIGHT**
- High-power 2800 LUX LED
- DESIGN**
- Anodized aircraft-grade aluminum; water and impact-resistant
 - Convex lens
 - Signature Red Ring™
 - Tactical edge
 - 4x adjustable beam
 - Steel belt/pocket clip
 - Magnetic base
 - Low battery indicator
- OPERATION**
- Rear-positioned, glow-in-the-dark ON/OFF button
- BATTERIES**
- Powered by 3 AAA batteries (included)
- SPECS**
- 0.428 lbs.
 - Length: Compacted: 4.325" / Extended: 4.625"
 - Diameter: (Head) 1.25" / (Barrel) 1"
- U.S. PATENT**
- 659,869 S

AVAILABLE COLORS



FIVE LIGHT MODES

HIGH:	MEDIUM:	LOW:	S.O.S.:	STROBE:
2185 LUX	1025 LUX	225 LUX	2185 LUX	2185 LUX
• 4 Hours	• 8 Hours	• 15 Hours	• 72 Hours	• 72 Hours
• 187 Meters	• 128 Meters	• 60 Meters	• 187 Meters	• 187 Meters

*NOTE: Light resets to first light mode (HIGH) after being OFF for 20 seconds.

Display Dimensions
(H) 7.25" x (W) 13.1875" x (D) 5"



FIVE LIGHT MODES

HIGH:	MEDIUM:	LOW:	S.O.S.:	STROBE:
2800 LUX	1150 LUX	285 LUX	2800 LUX	2800 LUX
• 4 Hours	• 8 Hours	• 15 Hours	• 72 Hours	• 72 Hours
• 210 Meters	• 136 Meters	• 67 Meters	• 210 Meters	• 210 Meters
PRIMARY	SECONDARY LIGHT MODES			

Display Dimensions
(H) 7.25" x (W) 13.18" x (D) 5"



UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397401100	5557	REDLINE® Flashlight	21.50	39.99	14 PIECES
645397122111	5599	REDLINE® Flashlight - Bulk Gray	21.00	39.99	18 PIECES
645397111115	5610	REDLINE® Flashlight - Bulk Black	21.00	39.99	18 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397312116	5615	SE REDLINE® Flashlight	24.00	44.99	14 PIECES
645397015123	5638	SE REDLINE® Flashlight - Bulk Black	23.50	44.99	18 PIECES
645397067122	5956	SE REDLINE® Flashlight - Bulk Gray	23.50	44.99	18 PIECES

NEBO® REDLINE^α

HIGH-POWER TACTICAL LIGHT

The REDLINE^α OC™ outputs 600 LUX of pristine white light. 600 LUX is bright, but what makes the OC™ so special is the OC™ (Optimized Clarity) Technology that creates a perfectly dispersed beam of light while in flood mode.

LIGHT

- High-power 600 LUX LED

DESIGN

- Anodized aircraft-grade aluminum; water and impact-resistant
- OC™ Technology
- Convex lens
- Signature Red Ring™
- Tactical edge
- 6x adjustable beam
- Dual-direction belt/pocket clip
- Magnetic base

OPERATION

- Rear-positioned, glow-in-the-dark ON/OFF button with Soft Touch Technology

ACCESSORIES

- Lanyard included

BATTERIES

- Powered by 1 AA battery (included)

SPECS

- 0.25 lbs.
- Length: Compacted: 4.1825" / Extended: 4.75"
- Diameter: (Head) 1.375" / (Barrel) 1"

U.S. PATENT

- 659,869 S



Tactical Edge and Signature Red Ring™



6x Adjustable Zoom



Dual-Direction Belt/Pocket Clip



Glow-in-the-Dark Button and Magnetic Base



Compact Size



Diffuser Dome



Glow-in-the-Dark Button



Carabiner Clip



NEBO® LUMO™

OMNIDIRECTIONAL CLIP LIGHT

Compact, handy and bright...the LUMO™ Clip Light by NEBO® is the perfect "whatever you need it to be" light. Key chain light, purse light, backpack light, book light...the possibilities are endless. This compact 25 lumen light comes with a carabiner attachment to clip anywhere you need. The white top of the LUMO™ is a diffuser dome. This dome helps spread the light evenly to create a more omnidirectional light source. LUMO™ Clip Light...the brilliant clip light!

LIGHT

- High-power 25 lumen LED

DESIGN

- Anodized aircraft-grade aluminum, water and impact-resistant
- Carabiner clip
- Glow-in-the-dark button
- Diffuser dome softens the light

OPERATION

- Rear-positioned glow-in-the-dark ON/OFF button

BATTERIES

- Powered by 3 LR44 batteries (included)
- Replacement batteries sold separately as #6045.

SPECS

- 0.2 lbs.
- (L) 3.625" x (W) 0.75"

AVAILABLE COLORS



TWO LIGHT MODES

600 LUX

- 2 Hours
- 92 Meters

STROBE

- 4.5 Hours
- 92 Meters



Display Dimensions
(H) 8" x (W) 7.5" x (D) 8.25"

ONE LIGHT MODE

25 LUMENS

- 5 Hours
- 3 Meters



Display Dimensions
(H) 9" x (W) 6.5" x (D) 6.5"



OPTIMIZED CLARITY

Eliminating inconsistencies in light, the OC™ (Optimized Clarity) Technology provides intense, clear, pristine light that is easy on the eyes. This technology allows the light beam to be as bright on the edge as it is in the center when used in flood mode.

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397929499	6092	REDLINE ^α OC™ Flashlight	13.00	24.99	16 PIECES

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397929529	6095	LUMO™ 25 Lumen Clip Light	3.50	6.99	48 PIECES
645397929864	6157	LUMO™ 25 Lumen Clip Light - Bulk Red	3.40	6.99	12 PIECES
645397929871	6158	LUMO™ 25 Lumen Clip Light - Bulk Silver	3.40	6.99	12 PIECES
645397929888	6159	LUMO™ 25 Lumen Clip Light - Bulk Blue	3.40	6.99	12 PIECES
645397929895	6160	LUMO™ 25 Lumen Clip Light - Bulk Black	3.40	6.99	12 PIECES

NEBO® EDGE

TACTICAL FLASHLIGHTS

Some of the first tactical flashlights in the NEBO® line up, the EDGE series. Equipped with tactical edges, rear-positioned ON/OFF buttons and strong, compact body designs, the EDGE™ series is all that you need in a tactical flashlight.

#5519 EDGE 50™

- High-power 50 lumen LED
- Anodized aircraft-grade aluminum; water and impact-resistant
- Tactical edge
- Steel belt/pocket clip
- Rear-positioned ON/OFF button
- Powered by 1 AA battery (included)

#5872 EDGE 90™

- High-power 90 lumen LED with Defensive Strobe
- Anodized aircraft-grade aluminum; water and impact-resistant
- Removable tactical edge
- Steel belt/pocket clip
- Rear-positioned ON/OFF button
- Powered by 1 AA battery (included)

#6085 EDGE 200™

- High-power 200 lumen LED with Defensive Strobe
- Anodized aircraft-grade aluminum; water and impact-resistant
- Removable tactical edge
- Dual-direction steel belt/pocket clip
- Rear-positioned ON/OFF button
- Powered by 1 AA battery (included)

SPECS

- (#5519/#5872) 0.179 lbs. / (#6085) 0.2lbs.
- (#5519/#5872) 3.75" x 0.75" / (#6085) 4.56" x 0.875"




#5519 Steel Clip and Rubber Grip



#5519 Glow-in-the-Dark Button



#5872 Removable Tactical Edge



#6085 Removable Tactical Edge



2 Emergency Red LEDs



90° Vertical Tilt



Adjustable Head Strap



NEBO® 90 LUMEN HEAD LAMP

ADJUSTABLE HEAD LAMP

The NEBO® 90 Lumen Head Lamp is a powerful and convenient hands-free lighting solution. The head tilts 90° to direct light exactly where you need it and the adjustable strap provides a sure fit for any size.

LIGHT

- High-power 90 lumen LED
- 2 red LEDs

DESIGN

- Reinforced plastic; water and impact-resistant
- Head tilts 90° to direct light where you need it
- Adjustable head strap

OPERATION

- ON/OFF button

BATTERIES

- Powered by 3 AAA batteries (included)

SPECS

- 0.225 lbs.
- One size fits all; adjustable fit

THREE LIGHT MODES

WHITE:

- 90 Lumens
- 9 Hours
- 100 Meters

RED:

- 8 Lumens
- 150 Hours
- 3 Meters

RED FLASH:

- 8 Lumens
- 250 Hours
- 3 Meters



#5519/#5872 Display Dimensions
(H) 7" x (W) 7" x (D) 5.375"

#6085 Display Dimensions
(H) 8" x (W) 7.5" x (D) 8.25"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397900702	5519	EDGE™ 50 Lumen Flashlight	6.00	11.99	24 PIECES
645397107125	5872	EDGE™ 90 Lumen Flashlight	7.50	14.99	24 PIECES
645397929475	6085	EDGE™ 200 Lumen Flashlight	9.99	19.99	20 PIECES



Clamshell Dimensions
(H) 7.25" x (W) 4.45" x (D) 2.875"

UPC CODE	ITEM	DESCRIPTION	COST	MSRP	CASE PACK
645397929215	6003	90 Lumen Head Lamp	14.00	24.99	6 PIECES

LIGHTING 101

GAUGING LED PERFORMANCE

Measuring the brightness of light is not a very straight-forward task. Currently, the most common measure of brightness is the lumen rating. Lumens replaced the old wattage-rating system because modern lights consume far less power and are much brighter.

A single lumen is the measure of energy that's released from a light. Imagine putting a transparent bubble around a light bulb and being able to measure all of the energy that flows through the bubble — this is how lumens are measured.


At NEBO®, we don't live in a bubble and we know that as lighting technology advances, so must the tools used to gauge

the performance. Thus, many of our flashlights are now gauged by lux instead of lumens. Lux isn't a measurement of the amount of energy released — it's a measure of how much light is actually hitting your target.


We've recently introduced flashlights that have advanced optics designed to maximize energy efficiency by tightly focusing the beam of light. So you can light up the mystery across the field without wasting energy by lighting the ground at your feet.

At NEBO® we make flashlights that are designed to meet real-life applications and we use advanced engineering to create lighting products that conserve energy yet blast a powerful beam of light.

MEASURING POWER:




MEASURING BRIGHTNESS:



RATING PERFORMANCE BY PRODUCT TYPE:


LANTERNS & WORK LIGHTS

These lighting products are designed to illuminate the area around — just like a household light bulb. Since light bulbs are rated in lumens, lantern output is rated using lumens.



CLASSIC FLASHLIGHTS

Classic flashlights illuminate the area directly in front of us — mimicking a light-post fixture, so it's appropriate to also rate these products using lumens.



LONG-RANGE FLASHLIGHTS

These flashlights feature specialized optics with zoom capabilities that are designed to project an intense beam of light at a distance. Lumen ratings ignore the use of specialized optics and fail to provide a clear representation of beam distance or brightness. Lux on the other hand, measures the amount of light actually hitting the target.



FOCUSING THE INTENSITY

The natural tendency of light is to disperse. We use patented O² Technology™ to focus the light's intensity by bending it toward the center of the beam.

The result — a hotter, brighter spotlight with the lowest power consumption.



STANDARD BEAM DISTANCE

O² TECHNOLOGY™ DOUBLES THE BEAM DISTANCE

A BEAM OF LIGHT SO POWERFUL, YOU HAVE TO SEE TO BELIEVE!

CUSTOM PRINTING & ENGRAVING

What's better than a NEBO® product?...
One with your name on it!

NEBO® offers custom screen printing and laser engraving services on most all products. Utilize NEBO® products to advertise your company or event!



NEBO® CUSTOM PRINTING & ENGRAVING FAQs

QUANTITY REQUIREMENTS

Custom printing orders must be a minimum of 100 pieces.

LEAD TIME

Allow 15-20 business days for production time.

SHIPPING

All orders ship FOB Grand Prairie, TX. Prepaid DOES NOT apply for custom print orders.

PAYMENT

Orders will not be released for printing until payment has been received in full, via credit card or CIA.

ADVERTISE YOUR COMPANY WITH OUR PRODUCTS!

Screen Printing Prices

- 100 - 499 pieces = Dealer price + \$2.00 per unit
- 500 - 999 pieces = Dealer price + \$1.50 per unit
- 1000+ pieces = Dealer price + \$1.00 per unit

Laser Engraving Prices

- 100 - 499 pieces = Dealer price + \$2.50 per unit
- 500 - 999 pieces = Dealer price + \$2.00 per unit
- 1000+ pieces = Dealer price + \$1.50 per unit

*There's a one-time \$35 fee (per custom print/engrave order), which includes the setup for either screen printing or laser engraving. This setup fee covers the logo/text printed in a single location on the product, using a single color. There's an additional charge for printing or laser engraving on multiple locations or printing in more than one color.

Contact Your
Sales Rep or
800-255-6061
for Additional
Information!

FAQ

Frequently Asked Questions



Who is Alliance Sports Group?

Alliance Sports Group is the parent company of NEBO® Tools, NEBO® Sports, iPROTEC™ Firearm Accessories, Bollinger® Fitness, Solaire® TrimWear, WeatherRite® Outdoor, Quarrow® Fishing and most recently, True Utility®.

What does NEBO® mean?

NEBO is mentioned in the Bible as the burial site of Moses. There is an excellent view of "The Promised Land" from Mt. NEBO. NEBO is also a mountain in Utah near where NEBO® Tools originated.

Why does NEBO® offer countertop displays?

NEBO® products sell much faster in display packaging when it's placed on counters and end-caps because this allows customers to try the product before buying it.

Are batteries included in your products?

All flashlights, cap-lights, head lamps and multi-tools that require batteries have batteries included.

Are NEBO® products waterproof?

Some NEBO® products are waterproof, however most are water-resistant. Please see product details for further information.

Does NEBO® offer a warranty for its products?

Yes, NEBO® stands behind its products with a 1 year limited manufacturer's warranty. Any item that does not perform properly due to a manufacturer's defect can be returned for a warranty replacement. Warranty does not cover normal wear and tear or batteries. Contact warranty@nebotools.net or 800.255.6061.

How do I get free freight?

First time orders receive free freight. Secondary orders exceeding \$600 receive free freight.

Do you accept credit card payments?

Yes. Visa, Mastercard, American Express and Discover

What are my payment terms?

Cash in Advance, NET 30 with approved ASG credit application

Where do I send my payment?

Alliance Sports Group, PO Box 203246,
Dallas, TX 75320-3246

Who do I make the check payable to?

Alliance Sports Group

Do you send out monthly statements?

Yes, we send them out at the end of each month.

Can I get my invoices and statements emailed to me?

Yes. Just email a request to accounting@nebotools.net and your invoice/statement will be emailed back to you.

How will my order be shipped?

We use FedEx.

How Long will it take to receive my order?

After being processed,* all orders, unless otherwise specified, are shipped via standard service which takes approximately 3-5 business days.

*Please allow 48-72 hours for order to be processed.

If an item is out of stock, do you back order the item or wait and ship the order complete?

We back order any items that are out of stock rather than waiting for the remaining items to come in stock.

What is your address for returns?

NEBO® Canada c/o FTN Canada
7075 Ordan Drive,
Mississauga, Ontario L5T1K6 Canada.

Does ASG pay the return freight?

ASG pays return freight when a Return Authorization has been issued by ASG.

How can I get a call tag/return an item?

Contact your sales rep or corporate office warranty@nebotools.net or 800.255.6061

What is NEBO's® MAP (Minimum Advertised Price) Policy?

The advertised price PLUS any shipping charges paid by the consumer must be within 10% of the Suggested Retail Price. We reserve the right to stop providing product to all sellers that do not comply. A full download-able version of the MAP Policy can be found at our website, www.nebotools.com.

CALL TOLL FREE: 800-255-6061 or VISIT OUR WEBSITE: WWW.NEBOTOOLS.COM
APPELEZ-NOUS SANS FRAIS AU 800-255-6061 OU VISITEZ NOTRE SITE WEB À WWW.NEBOTOOLS.COM

For more information or to place an order contact your NEBO® Tools sales representative.
Pour plus d'informations ou pour passer une commande, contactez votre représentant des ventes d'outils de NEBO®.

UPC CODE	ITEM	NEBO® Tools	DISPLAY	COST	MSRP	CASE PACK	PAGE #
Flashlights and Lighting							
645397900702	5519	EDGE™ 50 Lumen Flashlight	Display	\$6.00	\$11.99	24 PIECES	38
645397401100	5557	REDLINE® Flashlight	Display	\$21.50	\$39.99	14 PIECES	34
645397122111	5599	REDLINE® Flashlight (Gray)	Bulk	\$21.00	\$39.99	18 PIECES	34
645397111115	5610	REDLINE® Flashlight (Black)	Bulk	\$21.00	\$39.99	18 PIECES	34
645397312116	5615	SE REDLINE® Flashlight	Display	\$24.00	\$44.99	14 PIECES	35
645397111276	5620	REDLINE® Select Flashlight (Black)	Display	\$31.00	\$54.99	9 PIECES	32
645397015123	5638	SE REDLINE® (Black)	Bulk	\$23.50	\$44.99	18 PIECES	35
645397107125	5872	CSI EDGE™ 90 Flashlight	Display	\$7.50	\$14.99	24 PIECES	38
645397066125	5955	REDLINE® Select Flashlight (Titanium)	Display	\$31.00	\$54.99	9 PIECES	32
645397067122	5956	SE REDLINE® Flashlight (Gray)	Bulk	\$23.50	\$44.99	18 PIECES	35
645397929185	6000	O² BEAM™ Flashlight	Display	\$67.00	\$119.99	4 PIECES	28
645397929215	6003	90 Lumen Head Lamp	Clamshell	\$14.00	\$24.99	6 PIECES	39
645397929222	6006	Larry™ 2 12 LED Work Light	Display	\$9.00	\$16.99	24 PIECES	15
645397929345	6051	Larry™ 2 12 LED Work Light (Orange)	Bulk	\$8.75	\$16.99	12 PIECES	15
645397929352	6052	Larry™ 2 12 LED Work Light (Gray)	Bulk	\$8.75	\$16.99	12 PIECES	15
645397929369	6053	Larry™ 2 12 LED Work Light (Black)	Bulk	\$8.75	\$16.99	12 PIECES	15
645397929376	6054	Larry™ 2 12 LED Work Light (Green)	Bulk	\$8.75	\$16.99	12 PIECES	15
645397929383	6055	Lucy™ 2 12 LED Work Light (Pink)	Bulk	\$8.75	\$16.99	12 PIECES	15
645397929475	6085	EDGE 200™ Flashlight	Display	\$9.99	\$19.99	20 PIECES	38
645397929499	6092	REDLINE® OC™ Flashlight	Display	\$13.00	\$24.99	16 PIECES	36
645397929529	6095	LUMO™ Clip Light	Display	\$3.50	\$6.99	48 PIECES	37
645397929857	6156	SLYDE™ 440 Lumen Flashlight & Work Light	Display	\$22.50	\$39.99	16 PIECES	17
645397929864	6157	LUMO™ Clip Light (Red)	Bulk	\$3.40	\$6.99	12 PIECES	37
645397929871	6158	LUMO™ Clip Light (Silver)	Bulk	\$3.40	\$6.99	12 PIECES	37
645397929888	6159	LUMO™ Clip Light (Blue)	Bulk	\$3.40	\$6.99	12 PIECES	37
645397929895	6160	LUMO™ Clip Light (Black)	Bulk	\$3.40	\$6.99	12 PIECES	37
645397930013	6189	REDLINE® Select RC Flashlight	Display	\$46.50	\$80.00	6 PIECES	33
645397930068	6194	Larry™ Silver™ 8 LED Work Light	Display	\$14.00	\$24.99	16 PIECES	14
645397930099	6227	PaL Power and Light Flashlight	Display	\$14.75	\$24.99	18 PIECES	26
645397930112	6267	SLYDE™ Z	Display	\$36.99	\$59.99	8 PIECES	16
645397930167	6272-A	Micro REDLINE® OC™ Flashlight	Display	\$11.00	\$19.99	16 PIECES	31
645397930174	6273	Classic REDLINE® OC™ Flashlight	Display	\$21.00	\$39.99	12 PIECES	30
645397930242	6294	SEVEN-Z™ 770 Lumen Flashlight	Display	\$44.95	\$89.95	6 PIECES	21
645397930266	6296	TWYST™ Work Light, Lantern & Flashlight	Display	\$42.90	\$79.00	10 PIECES	19
645397930341	6304	WORKBRITE 2™ C-O-B LED Work Light	Display	\$18.33	\$32.50	12 PIECES	24
645397930358	6305	The Rechargeable WORKBRITE 2™	Display	\$25.74	\$44.50	12 PIECES	25
645397930365	6306	BIG Larry™ Power C-O-B LED Work Light	Display	\$19.89	\$34.50	14 PIECES	12
645397930396	6311	TRANSPORT® 12V DC Rechargeable Flashlight	Display	\$14.99	\$27.99	18 PIECES	27
645397930402	6327	Larry™ C C·O·B LED Work Light	Display	\$7.75	\$12.95	24 PIECES	13
645397930419	6328	TWYST™ Work Light, Lantern & Flashlight (Black)	Display	\$42.90	\$79.00	10 PIECES	19
645397930426	6329	LuMORE™ Clip Light	Display	\$4.95	\$8.95	48 PIECES	23
645397930433	6347	CaseBrite™ iPhone 6/6S Case + Light (Black)	Bulk	\$29.50	\$49.99	4 PIECES	20
645397930440	6348	CaseBrite™ iPhone 6/6S Plus Case + Light (Black)	Bulk	\$29.50	\$49.99	4 PIECES	20
645397930457	6349	CaseBrite™ Countertop Display	Display	FREE with 12 piece order		1 PIECE	20

Flashlights and Lighting - Continued							
645397930464	6350	Larry™ C C·O·B LED Work Light - Bulk Red	Bulk	\$7.50	\$12.95	12 PIECES	13
645397930471	6351	Larry™ C C·O·B LED Work Light - Bulk Blue	Bulk	\$7.50	\$12.95	12 PIECES	13
645397930488	6352	Larry™ C C·O·B LED Work Light - Bulk Gray	Bulk	\$7.50	\$12.95	12 PIECES	13
645397930495	6353	Larry™ C C·O·B LED Work Light - Bulk Yellow	Bulk	\$7.50	\$12.95	12 PIECES	13
645397930501	6354	Larry™ C C·O·B LED Work Light - Bulk Camo	Bulk	\$7.75	\$12.95	12 PIECES	13
645397930518	6355	Lucy™ C C·O·B LED Work Light - Bulk Pink	Bulk	\$7.50	\$12.95	12 PIECES	13
645397930525	6357	LuMORE™ Clip Light - Bulk White	Bulk	\$4.80	\$8.95	12 PIECES	23
645397930532	6358	LuMORE™ Clip Light - Bulk Red	Bulk	\$4.80	\$8.95	12 PIECES	23
645397930549	6359	LuMORE™ Clip Light - Bulk Blue	Bulk	\$4.80	\$8.95	12 PIECES	23
645397930556	6360	LuMORE™ Clip Light - Bulk Green	Bulk	\$4.80	\$8.95	12 PIECES	23
645397930563	6372	TWYST™ Z Work Light, Lantern & Flashlight	Display	\$21.50	\$39.99	16 PIECES	18
645397930402	6373	LiL Larry™ C·O·B LED Work Light	Display	\$14.95	\$28.95	18 PIECES	10-11
645397930648	6382	BIG Larry™ C·O·B LED Work Light - Bulk Camo	Bulk	\$19.89	\$34.50	7 PIECES	12
645397930662	6383	SLYDE™ Flashlight & Work Light - Bulk Camo	Bulk	\$23.40	\$39.99	8 PIECES	17
645397930679	6384	BIG Larry™ C·O·B LED Work Light - Bulk Black	Bulk	\$19.55	\$34.50	7 PIECES	12
645397930686	6385	BIG Larry™ C·O·B LED Work Light - Bulk Silver	Bulk	\$19.55	\$34.50	7 PIECES	12
645397930693	6386	CaseBrite™ iPhone 6/6S Case + Light (White)	Bulk	\$29.50	\$49.99	4 PIECES	20
645397930709	6387	CaseBrite™ iPhone 6/6S Plus Case + Light (White)	Bulk	\$29.50	\$49.99	4 PIECES	20
645397930747	6391	Twin Pucks Task Light & Emergency Beacon	Display	\$14.95	\$27.50	12 PIECES	22
645397930754	6392	REDLINE® RC™ with MagDock	Display	\$24.50	\$44.99	10 PIECES	29
645397930792	6413	BIG Larry™ C·O·B LED Work Light - Bulk Red	Bulk	\$19.55	\$34.50	7 PIECES	12
645397930808	6414	SEVEN-Z™ 770 Lumen Flashlight - Camo	Display	\$45.75	\$89.95	6 PIECES	21
645397930860	6431	Larry™ BOSS Power C·O·B Work Light	Display	\$21.95	\$41.95	12 PIECES	4-5
645397930877	6433	TEMPRA™ IR Surface Thermometer & Spot Light	Display	\$39.99	\$69.99	8 PIECES	6-7
645397930884	6434	SLYDE™ KING Flashlight and Work Light	Display	\$28.95	\$49.95	12 PIECES	2-3
645397930907	6436	TWYST™ Z Work Light, Lantern & Flashlight - Bulk Black	Bulk	\$21.25	\$39.99	12 PIECES	18
645397930990	6458	Z-Bug Bulb™	Display	\$19.95	\$34.99	16 PIECES	8-9
645397931027	6463	LiL Larry™ - Bulk Red	Bulk	\$14.75	\$28.95	9 PIECES	10-11
645397931034	6464	LiL Larry™ - Bulk Black	Bulk	\$14.75	\$28.95	9 PIECES	10-11
645397931041	6465	LiL Larry™ - Bulk Silver	Bulk	\$14.75	\$28.95	9 PIECES	10-11
645397931058	6466	LiL Larry™ - Bulk Camo	Bulk	\$14.95	\$28.95	9 PIECES	10-11
645397930761	6393	BIG Larry™ Flashlight Holster	Bulk	\$2.75	\$4.99	7 PIECES	12

**CALL TOLL FREE: 800-255-6061 or VISIT OUR WEBSITE: WWW.NEBOTOOLS.COM
APPELEZ-NOUS SANS FRAIS AU 800-255-6061 OU VISITEZ NOTRE SITE WEB À WWW.NEBOTOOLS.COM**

For more information or to place an order contact your NEBO® Tools sales representative.
Pour plus d'informations ou pour passer une commande, contactez votre représentant des ventes d'outils de NEBO®.

NEBO® GUARANTEED BUYBACK PROGRAM

NEBO® absolutely guarantees your success with our products! Just place an order and use the P.O.P. displays to merchandise the products near your checkout area. You will be invoiced for the goods and payment is due within the agreed-upon terms.

Our promise to you is that, if (after 90 days from the time your product was received) the products from our display have not sold at least 80% of the case quantity, NEBO® will "BUYBACK" the remaining unsold merchandise and pay the freight to ship it back to our warehouse.

This offer stands firm for up to 6 months from the receipt of the merchandise.

NEBO® garantit votre succès absolu avec nos produits! Il suffit de passer une commande et d'utiliser les présentoirs P.O.P. pour étaler les produits à proximité de votre zone de caisse. On vous enverra une facture pour la marchandise et le paiement est dû dans les délais convenus.

Notre promesse est que, si (90 jours après avoir reçu votre produit) au moins 80 % de la quantité du carton des produits de notre présentoir n'ont pas été vendus, NEBO® « RACHÈTERA » la marchandise non vendue et payera les frais de transport pour le retour à notre entrepôt.

Cette offre reste ferme pendant 6 mois à compter de la réception de la marchandise.

At NEBO®, we like for our customers to get the most from their experience with us. These NEBO® special giveaway products are our way of saying, 'Thank you.' Place your order now to get these great giveaway products!

NEBO® GIVEAWAY

\$250 Order:

- 1 set of NEBO® Socks
- *Set equals 1 pair of each (White & Black)

\$750 Order:

- 1 set of NEBO® Socks
- *Set equals 1 pair of each (White & Black)
- 1 NEBO® Cap (OS)

\$1500 Order:

- 1 set of NEBO® Socks
- *Set equals 1 pair of each (White & Black)
- 1 NEBO® Cap (One Size Fits All)
- 1 NEBO® CaseBrite™ iPhone Case + Light (6, 6S, 6 Plus or 6S Plus) (Black or White)

GIVEAWAYS

#6289 NEBO® Socks (White No Show)
NEBO® Socks (Black Crew Cut)

#6347 CaseBrite™ iPhone 6/6S Case + Light (Black)
#6348 CaseBrite™ iPhone 6/6S Plus Case + Light (Black)
#6386 CaseBrite™ iPhone 6/6S Case + Light (White)
#6387 CaseBrite™ iPhone 6/6S Plus Case + Light (White)

#6462 NEBO® Cap (One Size Fits All)



The giveaway offer is good until December 31, 2016 Net 30 with approved credit. The above promotions are good while supplies last. Actual product style may vary from picture shown. Customer must choose only one applicable giveaway offer per order.

L'offre cadeau est valide jusqu'au 31 décembre 2016. Les promotions ci-dessus sont bonnes jusqu'à épuisement des stocks. Le style actuel du produit peut différer de la photographie présentée. Le client ne peut choisir qu'une offre cadeau applicable par commande.

CALL TOLL FREE: 800-255-6061 or VISIT OUR WEBSITE: WWW.NEBOTOOLS.COM
APPELÉZ-NOUS SANS FRAIS AU 800-255-6061 OU VISITEZ NOTRE SITE WEB À WWW.NEBOTOOLS.COM

For more information or to place an order contact your NEBO® Tools sales representative.
Pour plus d'informations ou pour passer une commande, contactez votre représentant des ventes d'outils de NEBO®.