

**ROLA·CASE**  
MULTIPLE STORAGE SYSTEMS



**ROLA·Shelf**  
VAN & TRUCK STORAGE SOLUTIONS

**PRODUCT GUIDE 2**  
VAN, TRUCK & MODULAR  
STORAGE SYSTEMS





## THE NEXT GENERATION IN VAN,




- |    |                   |   |    |   |   |
|----|-------------------|---|----|---|---|
| 1  | RSSFR/HD/40/1539  | 4 Series Heavy duty start frame                   | 19 | RSSHL/84                                    | Mid mount shelf with 2 x RP120 plastic bins                           |
| 2  | RSEFR/HD/40/1539  | 4 Series Heavy duty extension frame               | 20 | RSLBX/84                                    | Lockable box mounted horizontally                                     |
| 3  | RSEFR/HD/80/1539  | 8 Series Heavy duty extension frame               | 21 | RCSK2/C + RCSK3/C + 1 x RSBAR/80            | Rola-Case cabinet kits  |
| 4  | RSEFR/HD/120/1539 | 12 Series Heavy duty extension frame              | 22 | RSFLE+ RS840A                               | Floor enclosure with removable front angle                            |
| 5  | RSGAC/41          | Vented Gas, Oxy and Acetylene storage cabinet     | 23 | RSCAB/81                                    | Large 3 shelf lockable cabinet with contoured body                    |
| 6  | RCSK6/C           | Rola-Case cabinet kit                             | 24 | RSSHL/86                                    | Floor mount shelf with 2 x RP240 plastic bins (dividers not included) |
| 7  | RSFLE + RS420A    | Floor enclosure with removable front angle        | 25 | RSSHL/85 + RSSHL/81/FR                      | Mid mount shelf with file retainer                                    |
| 8  | RSSHL/43          | High mount shelf with 3 x RP25 plastic bins       | 26 | RCSK5/C + RCSK4/C + 2 x RSBAR/80 + 2 x RC5D | Cabinet kits  |
| 9  | RSSHL/44          | Mid mount shelf with 1 x RP120                    | 27 | RSSHL/87                                    | Low mount shelf with 2 x Rolacases & RS/87/FW Foam                    |
| 10 | RSSHL/45          | Low mount shelf with 4 x RP100 plastic bins       | 28 | RSCDH/81                                    | Adjustable cable Reel holder  |
| 11 | RSSHL/48          | Low mount shelf with 2 x RP400x200 plastic bins   | 29 | RSSHL/123                                   | High mount shelf with 9 x RP25 plastic bins                           |
| 12 | RGBBH/41          | Gas bottle holder (gas bottle not included)       | 30 | RSSHL/124                                   | Mid mount shelf with 3 x RP120  |
| 13 | RSLBX/81          | Lockable box mounted vertically                   | 31 | RSSHL/125                                   | Low mount shelf with 12 x RP100 plastic bins                          |
| 14 | RSCDH/41          | Adjustable cable Reel holder                      | 32 | RSSHL/128                                   | Floor mount shelf with 6 x RP400xRP200 plastic bins                   |
| 15 | RSSHL/83          | High mount shelf with 6 x RP25 plastic bins       | 33 | RSSHL/126                                   | Floor mount shelf with 3 x RP240 plastic bins & 3 x RP240/D Dividers  |
| 16 | RSSHL/85          | Low mount shelf with 8 x RP100 plastic bins       |    |   |   |
| 17 | RCBKE/3           | Holds 3 x RC001 cases (Inc. rubber mat and strap) |    |   |   |
| 18 | RSSHL/88          | Floor mount shelf with 8 x RP400x200 plastic bins |    |   |   |

**Disclaimer** If any product is installed incorrectly or used in an incorrect manner, no liability will be taken for product malfunction or personal injury.



# TRUCK & MOBILE STORAGE SOLUTIONS



The configuration of shelves and plastic bins depicted above allows for storage of large, medium and small components typical of today's tradesman and technician's requirements.

**ROLA•Shelf** will fit all vehicles where shelving is required including: Commercial vans, truck caps and service truck bodies.




FORD TRANSIT INTERIOR PROTECTION

Page: 8



RCSK5/C - CABINET KIT

Page: 4



RCSK4/C - CABINET KIT

Page: 4

**WE NOW HAVE 2 CENTRAL DISTRIBUTION CENTERS SERVING THE USA**

[info@rolacase.com](mailto:info@rolacase.com)

**MON – FRI – 8:00AM – 5:00PM EST**

**CUSTOMER SERVICE  
IS OUR PRIORITY**

**☎ 857.334.0300**



## **REAL PEOPLE, READY TO HELP YOU**

- Distributors
- Shipment Status
- National Fleet Network
- Installers
- New Product Availability
- Vehicle Specifications
- Order Status
- Product Specifications
- Custom Designs

Please call, email or request a quote on our website for your local sales representative to call you.






PAGE 4

ROLACASE CABINET KITS



PAGE 6

VAN SHELVING



PAGE 8

FLOORING AND WALL LINING

**ROLACASE PRODUCTS**

RolaCases.....	P: 2
Drawers Cabinets.....	P: 3
Cabinet Kits.....	P: 4
Metal Drawers & Accessories.....	P: 5

**ROLASHELF - VAN INTERIORS & PACKAGES**

P: 6

Partitions.....	P: 7
Van Flooring & Wall Lining.....	P: 8
Compact Van Packages.....	P: 9-10
Ford Transit Connect SWB & LWB	
Chevy City Express	
Nissan NV200	
Ram ProMaster City	
Low Roof Full Size Vans.....	P: 11-12
Mercedes Metris 126" & 135"	
Ford Transit Regular Low Roof 130"	
Ford Transit Long Low Roof 148"	
Nissan NV Cargo Standard Roof	
GMC Savanna/Chevy Express Regular & Ext	
Ram Promaster Standard Roof 118" & 136"	
Mid-High Roof Full Size Vans.....	P: 13-14
Ford Transit Regular Mid Roof 130"	
Ford Transit Long & EL Mid/High Roof 148"	
Ram Promaster High Roof 136" & 159"	
Nissan NV High Roof	
Mercedes Sprinter Standard & High Roof 144"	
Mercedes Sprinter High/Super High Roof 170"	
End Panel Accessories.....	P: 15

**VAN SHELVING - BUILD IT YOURSELF**

8 Series Van Shelving DIY.....	P: 16
12 Series Van Shelving DIY.....	P: 17

**SLIDING PLATFORMS**

P: 18



- CORROSION PROOF
- VARIOUS CONFIGURATIONS
- STURDY LOCKING CLIPS



- CAN BE FITTED WITH A DOOR FOR ADDED SECURITY
- DOORS CAN BE JOINED TO THE LEFT OR RIGHT OF THE CABINET



- IDEAL FOR VEHICLE AND STATIC USE
- JOINS VERTICALLY AND/ OR HORIZONTALLY

P1

RolaCases..... P.2  
 Drawer Cabinets..... P.3  
 Cabinet Kits..... P.4  
 Metal Drawers & Accessories..... P.5

ROLA•CASE is a versatile storage system for the transfer and handling of components, tools and instruments.

The range includes mobile work stations that allow the movement of tools and equipment in a workshop or service area. The cabinet and metal drawer systems are ideal for vehicle and static use.

1

SELECT YOUR CASE(S)

2

SELECT YOUR CABINET

3

SECURE YOUR CABINET

Cabinets are ideally secured to the inside of vehicles, truck bodies, ships & the workplace.

All cabinets come with plinth feet for securing to a surface

RC003/QK

RC003 + RC003/D

RCSK7PN6D/C + RC7D







### RC001/CH-CL



20 adjustable compartments, 1 tool compartment in front of case. Comes with 9 **RCPLD** dividers  
Polycarbonate lid

Dimensions: W:14 9/16" D:14 9/16" H:3 11/32"

### RC001/CL



20 adjustable compartments, 1 tool compartment in front of case. Comes with 9 **RCPLD** dividers  
Polycarbonate lid

Dimensions: W:14 9/16" D:14 9/16" H:3 11/32"

### RC003/QK



1 large compartment, plus 3 compartment lift-out tray with further compartments below, 1 tool compartment.  
Includes Quik Kit (**QK001/B-Blue**)

Dimensions: W:14 9/16" D:14 9/16" H:5 1/8"

### QK001



10 small compartments, 1 large tool compartment in front of case.

Dimensions: W:12 13/64" D:8 17/64" H:1 31/32"

### RC003/D



Dividers to suit **RC003** cases.  
Each case holds max. 3 dividers.

### RC001/CH



20 adjustable compartments, 1 tool compartment in front of case. Comes with 9 **RCPLD** dividers

Dimensions: W:14 9/16" D:14 9/16" H:3 11/32"

### RC002



1 large compartment  
1 tool compartment in front of case.

Dimensions: W:14 9/16" D:14 9/16" H:3 11/32"

### RC003/CL




1 large tool compartment, plus 3 compartment lift-out tray with further compartments below. Polycarbonate lid

Dimensions: W:14 9/16" D:14 9/16" H:5 1/8"

**RC003/D** (3 dividers can fit in the case - sold separately)

### RCTRY



Small tray with 4 adjustable compartments. Suits **RC001** series cases. Includes new clear micro component storage unit.

### RCVCH



Vertical Case Holder: Holds **RC001**, **RC002** or **RC003** series cases. Ideal for wall or end panel mounting.

Dimensions: H:5 29/32" W:14 9/16"

### RC001



20 adjustable compartments, 1 tool compartment in front of case. Comes with 9 **RCPLD** dividers

Dimensions: W:14 9/16" D:14 9/16" H:3 11/32"

### RC002/CL



1 large compartment  
1 tool compartment in front of case. Polycarbonate lid.

Dimensions: W:14 9/16" D:14 9/16" H:3 11/32"

### RC003



1 large tool compartment, plus 3 compartment lift-out tray with further compartments below

Dimensions: W:14 9/16" D:14 9/16" H:5 1/8"

**RC003/D** (3 dividers can fit in the case - sold separately)

### DIVIDERS

#### RCPLD



Available in Orange & Charcoal  
Divider for **RC001** cases



RC001



### RC2DC



Holds 2 x **RC001** or **RC002** series cases  
Dimensions:  
W:16 1/2" D:18 7/64" H:9 1/16"

### RC3DC



Holds 3 x **RC001** or **RC002** series cases  
Dimensions:  
W:16 1/2" D:18 7/64" H:12 51/64"

### RC3DC/2D



Holds 2 x **RC003** series cases  
Dimensions:  
W:16 1/2" D:18 7/64" H:12 51/64"

### RC4DC



Holds 4 x **RC001** or **RC002** series cases  
Dimensions:  
W:16 1/2" D:18 7/64" H:16 17/32"

### RC4DC/3D



Holds 2 x **RC003** and 1 x **RC001** series cases  
Dimensions:  
W:16 1/2" D:18 7/64" H:16 17/32"

### RC5DC



Holds 5 x **RC001** or **RC002** series cases  
Dimensions:  
W:16 1/2" D:18 7/64" H:21 17/32"

### RC5DC/4D



Holds 2 x **RC001** or **RC002** & 2 x **RC003** series cases  
Dimensions:  
W:16 1/2" D:18 7/64" H:21 17/32"

### RC7DC



Holds 7 x **RC001** or **RC002** series cases  
Dimensions:  
W:16 1/2" D:18 7/64" H:29 1/4"

### RC7DC/PN



Trolley with **8 21/32"** pneumatic tires. Ideal for stairs or uneven surfaces.

Holds 7 x **RC001** or **RC002** series cases  
Dimensions:  
W:16 1/2" D:18 7/64" H:39 3/8"

### RC7DC/PN/6D



Holds 4 x **RC001** or **RC002** & 2 x **RC003** series cases  
Dimensions:  
W:16 1/2" D:18 7/64" H:39 3/8"

### RC7DC/DM



Holds 7 x **RC001** or **RC002** & 2 x **RC003** series cases  
Dimensions:  
W:32 63/64" D:18 7/64" H:39 3/8"  
Does not include the internal shelf

### RCC/TT/40

Top Tray Fits to Rolacase Cabinets



### RCC/TT/40/T

Top Tray Fits to Rolacase single Trolleys







- All cabinets are compatible with the 4 series RolaShelf shelving.
- 2 cabinets can be joined horizontally to fit the 8 series RolaShelf shelving (will require 2x **RSBAR/80** support bars)
- Cabinets can be joined horizontally (will require 1x **RCJNR/C** joining bracket)

**RCSK1/C**



Dimensions:  
W:16 1/2" D:18 7/64" H:9 1/16"

**RCSK2/C**



Dimensions:  
W:16 1/2" D:18 7/64" H:12 51/64"

**RCSK3/C**



Dimensions:  
W:16 1/2" D:18 7/64" H:12 51/64"

**RCSK4/C**



Dimensions:  
W:16 1/2" D:18 7/64" H:21 17/32"

**RCSK5/C**



Dimensions:  
W:16 1/2" D:18 7/64" H:21 17/32"

**RCSK6/C**



Dimensions:  
W:16 1/2" D:18 7/64" H:16 17/32"

**RCSK7/C**



Dimensions:  
W:16 1/2" D:18 7/64" H:16 17/32"

**RCSK8/C**



Dimensions:  
W:16 1/2" D:18 7/64" H:29 1/4"

**RCSK7PN/C**



Dimensions:  
W:16 1/2" D:18 7/64" H:39 3/8"

**RCSK7PN6D/C**



Dimensions:  
W:16 1/2" D:18 7/64" H:39 3/8"

**RCSK7M/C**



Dimensions:  
W:16 1/2" D:18 7/64" H:39 3/8"

**RCDK7M/C**



Dimensions:  
W:32 63/64" D:18 7/64" H:39 3/8"



2 x RC7D DOORS



**RC3D**



Door To fit: **RC3DC, RC3DC/2D, RCSK2/C, RCSK3/C**

**RC4D**



Door To fit: **RC4DC, RC4DC/3D, RCSK6/C, RCSK7/C**

**RC5D**



Door To fit: **RC5DC, RC5DC/4D, RCSK5/C, RCSK4/C**

**RC7D**



Door To fit: **RC7DC/PN, RCDK7M/C(X2), RCSK8/C, RCSK7PN/C, RC7DC, RCSK7PN6D/C**



**ROLA-CASE** 4 series cabinets are compatible with 4 series **ROLA-Shelf** van racking systems or 2 cabinets can be joined horizontally to fit the 8 series shelving

- Engineer designed for truck bodies, commercial vehicles & truck caps
- Dual slam shut locking mechanism
- Drawers are available in 2 heights (**RC401** : 3 11/32" & **RC403** : 5 1/8")

### RCKIT40/1



**RC2/40** cabinet with 2 x **RC401**

Dimensions:  
W:16 1/2" D:18 7/64" H:9 1/16"

### RCKIT40/5



**RC3/40** cabinet with 2 x **RC401** & 1 x **RC001/CL**

Dimensions:  
W:16 1/2" D:18 7/64" H:12 51/64"

### RCKIT40/6



**RC3/40** cabinet with 1 x **RC403** & 1 x **RC003/CL**

Dimensions:  
W:16 1/2" D:18 7/64" H:12 51/64"

### RCKIT40/8



**RC4/40** cabinet with 1 x **RC401** & 2 x **RC403**

Dimensions:  
W:16 1/2" D:18 7/64" H:16 17/32"

### RCKIT40/9



**RC4/40** cabinet with 3 x **RC401** & 1 x **RC001/CL**

Dimensions:  
W:16 1/2" D:18 7/64" H:16 17/32"

### RCKIT40/13



**RC5/40** cabinet with 3 x **RC401** & 2 x **RC001/CL**

Dimensions:  
W:16 1/2" D:18 7/64" H:21 17/32"

### RCKIT40/14



**RC5/40** cabinet with 2 x **RC403** & 2 x **RC001/CL**

Dimensions:  
W:16 1/2" D:18 7/64" H:21 17/32"

### RCKIT40/18



**RC7/40** cabinet with 2 x **RC403** & 4 x **RC001/CL**

Dimensions:  
W:16 1/2" D:18 7/64" H:29 1/4"

### RCBKE/2



Holds 2 x **RC003** cases  
Includes rubber mat and strap

### RCBKE/3



Holds 3 x **RC001** cases  
Includes rubber mat and strap

Dimensions:  
W:14 61/64" D:11 27/64" H:11 27/64"

### RCWHL/PN




Pneumatic wheel kit for single modular mobile workstation  
Comes with 2 x 8 21/32" pneumatic lines, 2 x swivel locking wheels & all necessary bracing & fixing components.

### RCHDL



Single mobile handle to fit pneumatic wheels kits

### RCJNR/C



Vertical joining bracket for connecting **ROLA-CASE** cabinets vertically (4 per kit plus screws)



**RCKIT40/14**



**RC003/CL + 2 x RC003/D**



**RCKIT40/9**






Mercedes Sprinter

Whether you have a cargo van, truck cap or enclosed trailer, RolaShelf has a solution that can help you get organized and maximize your commercial vehicle's efficiency.

- ✓ Van Shelving
- ✓ Cabinet Kits
- ✓ Ladder Racks
- ✓ Partitions
- ✓ Tank Holders
- ✓ Van Flooring & Wall Lining



Ford Transit 130" WB Mid Roof

All our products are built using heavy duty materials and have been engineered to be quiet and rattle-free. We back our products with an industry leading warranty



Ford Transit 130" WB Low Roof

**OPT. 1 PICK YOUR SHELVING KITS**


**OPT. 2 DESIGN YOUR OWN SHELVING**

**OPT. 3 CALL TODAY FOR A CUSTOM QUOTE**


 857. 334. 0300



COMPACT PARTITION



SWING DOOR PARTITION



COMPACT CARGO VANS

Full Kit#

Vehicle	Standard Partition
Ford Transit Connect SWB	RSFTCSWBSP-C
Ford Transit Connect LWB	RSFTCLWBSP-C
Chevy City Express	RSCCESP-C
Nissan NV200	RSNNV200SP-C
Ram Promaster City	RSRPCSP-C



LOW ROOF FULL SIZE VANS

Full Kit#

Full Kit#

Vehicle	Standard Partition	Swing Door Partition
Mercedes Metris 126"	RSMM126SP-F	RSMM126DP-F
Ford Transit Reg Low Roof 130"	RSFTRLR130SP-F	RSFTRLR130DP-F
Nissan NV Cargo Standard Roof	RSNNVCSRSP-F	RSNNVCSRDP-F
GMC Savana/Chevy Express Reg & Ext.	RSGMSCERESP-F	RSGMSCEREDP-F
Mercedes Metris 135"	RSMM135SP-F	RSMM135DP-F
Ford Transit Long Low Roof 148"	RSFTLLR148SP-F	RSFTLLR148DP-F
Ram Promaster Standard Roof 118" & 136"	RSRPSR118136SP-F	RSRPSR118136DP-F

MID/HIGH ROOF FULL SIZE VANS


Full Kit#

Full Kit#

Vehicle	Standard Partition	Swing Door Partition
Nissan NV Cargo Van High Roof	RSNNVCHRSP-L	RSNNVCHRDP-L
Ford Transit Regular Mid Roof 130"	RSFTRMR130SP-L	RSFTRMR130DP-L
Ford Transit Long Mid Roof 148"	RSFTLMR148SP-L	RSFTLMR148DP-L
Ford Transit Long & EL High Roof 148"	RSFTLEHR148SP-L	RSFTLEHR148DP-L
Ram Promaster High Roof 136" & 159"	RSRPHR136159SP-L	RSRPHR136159DP-L
Mercedes Sprinter Standard Roof 144"	RSMSSR144SP-L	RSMSSR144DP-L
Mercedes Sprinter High Roof 144"	RSMSHR144SP-L	RSMSHR144DP-L
Mercedes Sprinter High Roof 170"	RSMSSHR170SP-L	RSMSSHR170DP-L
Mercedes Sprinter Super High Roof 170"	RSMSSHR170SP-L	RSMSSHR170DP-L

FEATURES

- Provides a solid barrier between the occupants in the cab and the cargo area
- Designed to allow the maximum seat travel







### RIGID FLOORING (HEAVY DUTY FLOORING)

- STABILIGRIP- DOES NOT SWELL OR BUBBLE
- HD ULTRA GRIP - RIGID PLASTIC FLOOR FOR DURABILITY



### RUBBER MATS

- TOUGHEST MAT ON THE MARKET
- SUITABLE FOR WET OR OILY APPLICATIONS
- TREAD PLATE FINISH FOR AGGRESSIVE TRACTION



### INSULATED DURATHERM DOOR LINERS

### INTERIOR LINERS

- WALL LINING
- CEILING LINERS
- DOOR LINERS

## INTERIOR PROTECTION FOR CARGO VEHICLES

Once installed, owners and operators have peace of mind that workers and cargo are afforded the maximum protection possible, lowering the chance of any liabilities. Not only that, but the inside and outside of the vehicles remain in pristine condition. No more dings, scratches or marks thanks to our durable floors and wall liners.



### DOOR LININGS

AVAILABLE FOR ALL  
MAKES AND MODELS.  
CALL TODAY OR  
VISIT OUR WEBSITE  
TO GET PART NUMBERS  
[www.rolacaseusa.com](http://www.rolacaseusa.com)



### SILL PLATES



Mercedes-Benz




RAM





## BASIC PACKAGE

SHORT COMPACT KIT SHOWN



DRIVER



PASSENGER

### SHORT COMPACT

Ford Transit Connect SWB  
**Full Kit # RSFTCSWBBA**  
 Ram Promaster City  
**Full Kit # RSRPCBA**

### SHORT COMPACT

DRIVER	SPECS
Total Width	35"
1 x HD Start Frame - 8 Series	W:35"
1 x Low Mount Shelf	W:12"
1 x Mid Mount Shelf	D:10"
1 x Floor Mount Shelf	D:16"
1 x End Panel RSPEP/L	

### PASSENGER

PASSENGER	SPECS
1 x HD Start Frame - 8 Series	W:35"
1 x Low Mount Shelf	D:12"
1 x Mid Mount Shelf	D:10"
1 x Floor Mount Shelf	D:16"
1 x End Panel RSPEP/R	

**MOUNTING BRACKETS INCLUDED**

### LONG COMPACT

Chevy City Express  
**Full Kit #RSCCEXBA**  
 Nissan NV200  
**Full Kit #RSNNV200BA**  
 Ford Transit Connect LWB  
**Full Kit # RSFTCLWBBA**

### LONG COMPACT

DRIVER	SPECS
Total Width	52"
1 x HD Start Frame - 12 Series	W:52"
1 x Low Mount Shelf	W:12"
1 x Mid Mount Shelf	D:10"
1 x Floor Mount Shelf	D:16"
1 x End Panel RSPEP/L	



### PASSENGER

PASSENGER	SPECS
1 x HD Start Frame - 8 Series	W:35"
1 x Low Mount Shelf	D:12"
1 x Mid Mount Shelf	D:10"
1 x Floor Mount Shelf	D:16"
1 x End Panel RSPEP/R	

**MOUNTING BRACKETS INCLUDED**

## BASIC PACKAGE

LONG COMPACT KIT SHOWN



DRIVER





PASSENGER

## Partitions Sold Separately - Refer to Page 7

If you would like to order the drivers or passenger side alone, please indicate this on your purchase order.

## GENERAL PACKAGE

SHORT COMPACT KIT SHOWN



DRIVER



PASSENGER

### SHORT COMPACT

Ford Transit Connect SWB  
**Full Kit # RSFTCSWBGE**  
 Ram Promaster City  
**Full Kit # RSRPCGE**

### SHORT COMPACT

DRIVER	SPECS
Total Width	35"
1 x HD Start Frame - 8 Series	W:35"
1 x Lockable Box RSLBX/82	D:16"
1 x Floor Mount Shelf	D:16"
1 x End Panel RSPEP/L	
2 x Hooks RSPEP/HK	

### PASSENGER

PASSENGER	SPECS
1 x HD Start Frame - 8 Series	W:35"
1 x Mid Mount Shelf	D:10"
1 x Low Mount Shelf	D:12"
2 x 2 Drawer Kit RCSK1/C	D:18"
1 x Support Bar RSBAR/80	
8 x Grey Small Bin RP100	
2 x Red Medium Bin RP120	
1 x End Panel RSPEP/R	

**MOUNTING BRACKETS INCLUDED**

### LONG COMPACT

Chevy City Express  
**Full Kit #RSCCEXGE**  
 Nissan NV200  
**Full Kit #RSNNV200GE**  
 Ford Transit Connect LWB  
**Full Kit # RSFTCLWBGE**

### LONG COMPACT

DRIVER	SPECS
Total Width	52"
1 x HD Start Frame - 12 Series	W:52"
1 x Low Mount Shelf	D:12"
1 x Mid Mount Shelf	D:16"
1 x Lockable Box RSLBX/122	D:16"
1 x End Panel RSPEP/L	
2 x Hooks RSPEP/HK	



### PASSENGER

PASSENGER	SPECS
1 x HD Start Frame - 8 Series	W:35"
1 x Mid Mount Shelf	D:10"
1 x Low Mount Shelf	D:12"
1 x 3 Drawer Kit RCSK2/C	D:18"
1 x 2 Drawer Kit RCSK3/C	D:18"
1 x Support Bar RSBAR/80	
8 x Grey Small Bin RP100	
1 x End Panel RSPEP/R	


**MOUNTING BRACKETS INCLUDED**

## GENERAL PACKAGE

LONG COMPACT KIT SHOWN



DRIVER





PASSENGER






## ELECTRICAL PACKAGE

### SHORT COMPACT KIT SHOWN



DRIVER



PASSENGER

### SHORT COMPACT

Ford Transit Connect SWB  
**Full Kit # RSFTCSWBEL**  
 Ram Promaster City  
**Full Kit #RSRPCEL**

### SHORT COMPACT DRIVER SPECS

Total Width	35"
1 x HD Start Frame - 8 Series	W:35"
1 x Mid Mount Shelf	D:10"
1 x Low Mount Shelf	D:12"
8 x Grey Small Bin RP100	
2 x Red Medium Bin RP120	
1 x End Panel RSPEP/L	
1 x Wire Reel Holder RSCDH/81	
2 x Hooks RSPEP/HK	

### SHORT COMPACT PASSENGER SPECS

1 x HD Start Frame - 8 Series	W:35"
1 x Low Mount Shelf	D:12"
1 x 3 Drawer Kit RCSK2/C	D:18"
1 x 2 Drawer Kit RCSK3/C	D:18"
1 x Support Bar RSBAR/80	
1 x End Panel RSPEP/R	

**MOUNTING BRACKETS INCLUDED**

### LONG COMPACT

Chevy City Express  
**Full Kit #RSCCEXEL**  
 Nissan NV200  
**Full Kit #RSNNV200EL**  
 Ford Transit Connect LWB  
**Full Kit # RSFTCLWBEL**

### LONG COMPACT DRIVER SPECS

Total Width	52"
1 x HD Start Frame - 12 Series	W:52"
1 x Low Mount Shelf	D:12"
1 x Mid Mount Shelf	D:10"
1 x Lockable Box RSLBX/122	D:16"
12 x Grey Small Bin RP100	
3 x Red Medium Bin RP120	
1 x End Panel RSPEP/L	



### LONG COMPACT PASSENGER SPECS

1 x HD Start Frame - 8 Series	W:35"
1 x Low Mount Shelf	D:12"
1 x 3 Drawer Kit RCSK2/C	D:18"
1 x 2 Drawer Kit RCSK3/C	D:18"
1 x Support Bar RSBAR/80	
1 x Wire Reel Holder RSCDH/81	
1 x End Panel RSPEP/R	
2 x Hooks RSPEP/HK	


**MOUNTING BRACKETS INCLUDED**

## ELECTRICAL PACKAGE

### LONG COMPACT KIT SHOWN



DRIVER





PASSENGER

## Partitions Sold Separately - Refer to Page 7

If you would like to order the drivers or passenger side alone, please indicate this on your purchase order.

## AMERICA'S MOST POPULAR PACKAGE

### SHORT COMPACT KIT SHOWN



DRIVER



PASSENGER

### SHORT COMPACT

Ford Transit Connect SWB  
**Full Kit # RSFTCSWBAM**  
 Ram Promaster City  
**Full Kit #RSRPCAM**

### SHORT COMPACT DRIVER SPECS

Total Width	35"
1 x HD Start Frame - 8 Series	W:35"
1 x Mid Mount Shelf	D:10"
1 x Low Mount Shelf	D:12"
1 x Floor Mount Shelf	D:16"
2 x Red Medium Bin RP120	
8 x Grey Small Bin RP100	
2 x Red Large Bin RP240	
1 x End Panel RSPEP/L	

### SHORT COMPACT PASSENGER SPECS

1 x HD Start Frame - 8 Series	W:35"
1 x Mid Mount Shelf	D:10"
1 x Low Mount Shelf	D:12"
1 x Floor Mount Shelf	D:16"
1 x End Panel RSPEP/R	
1 x Tool Holder RSPEP/MH	
1 x Tool Tray RSPEP/TY	
1 x Case Holder RCVCH	
1 x RolaCase RC001/CL	

**MOUNTING BRACKETS INCLUDED**

### LONG COMPACT

Chevy City Express  
**Full Kit #RSCCEXAM**  
 Nissan NV200  
**Full Kit #RSNNV200AM**  
 Ford Transit Connect LWB  
**Full Kit # RSFTCLWBAM**

### LONG COMPACT DRIVER SPECS

Total Width	52"
1 x HD Start Frame - 12 Series	W:52"
1 x Mid Mount Shelf	D:10"
1 x Low Mount Shelf	D:12"
1 x Floor Mount Shelf	D:16"
3 x Red Medium Bin RP120	
12 x Grey Small Bin RP100	
3 x Red Large Bin RP240	
1 x End Panel RSPEP/L	
2 x Hooks RSPEP/HK	



### LONG COMPACT PASSENGER SPECS

1 x HD Start Frame - 8 Series	W:35"
1 x Mid Mount Shelf	D:10"
1 x Low Mount Shelf	D:12"
1 x Floor Mount Shelf	D:16"
1 x End Panel RSPEP/R	
1 x Case Holder RCVCH	
1 x RolaCase RC001/CL	

**MOUNTING BRACKETS INCLUDED**

## AMERICA'S MOST POPULAR PACKAGE

### LONG COMPACT KIT SHOWN



DRIVER





PASSENGER



## BASIC PACKAGE

### STANDARD LOW ROOF KIT SHOWN



DRIVER



PASSENGER

#### STANDARD LOW ROOF

Mercedes Metris 126"  
**Full Kit #RSMM126BA**  
 Ford Transit Regular Low Roof 130"  
**Full Kit #RSFTRLR130BA**  
 Nissan NV Cargo Standard Roof  
**Full Kit #RSNNVCSRBA**  
 GMC Savana/Chevy Express Regular  
**Full Kit #RSGMSCERBA**  
 Ram Promaster Standard Roof 118"  
**Full Kit #RSRPSR118BA**

#### STANDARD LOW ROOF

DRIVER	SPECS
Total Width	86"
1 x HD Start Frame - 12 Series	W:52"
1 x HD Extension Frame - 8 Series	W:34"
2 x Low Mount Shelf	D:12"
4 x Floor Mount Shelf	D:16"
1 x End Panel RSPEP/L	

PASSENGER	SPECS
1 x HD Start Frame - 8 Series	W:35"
1 x Low Mount Shelf	D:12"
2 x Floor Mount Shelf	D:16"
1 x End Panel RSPEP/R	

#### MOUNTING BRACKETS INCLUDED

#### LONG LOW ROOF

Mercedes Metris 135"  
**Full Kit #RSMM135BA**  
 Ford Transit Long Low Roof 148"  
**Full Kit #RSFTLLR148BA**  
 GMC Savana/Chevy Express Extended  
**Full Kit #RSGMSCCEXBA**  
 Ram Promaster Standard Roof 136"  
**Full Kit #RSRPSR136BA**

#### LONG LOW ROOF


DRIVER	SPECS
Total Width	103"
1 x HD Start Frame - 12 Series	W:52"
1 x HD Extension Frame - 12 Series	W:51"
2 x Low Mount Shelf	D:12"
4 x Floor Mount Shelf	D:16"
1 x End Panel RSPEP/L	

PASSENGER	SPECS
1 x HD Start Frame - 12 Series	W:52"
1 x Low Mount Shelf	D:12"
2 x Floor Mount Shelf	D:16"
1 x End Panel RSPEP/R	


#### MOUNTING BRACKETS INCLUDED

## BASIC PACKAGE

### LONG LOW ROOF KIT SHOWN



DRIVER





PASSENGER


Partitions Sold Separately - Refer to Page 7

## GENERAL PACKAGE

### STANDARD LOW ROOF KIT SHOWN



DRIVER



PASSENGER

#### STANDARD LOW ROOF

Mercedes Metris 126"  
**Full Kit #RSMM126GE**  
 Ford Transit Regular Low Roof 130"  
**Full Kit #RSFTRLR130GE**  
 Nissan NV Cargo Standard Roof  
**Full Kit #RSNNVCSRGE**  
 GMC Savana/Chevy Express Regular  
**Full Kit #RSGMSCERGE**  
 Ram Promaster Standard Roof 118"  
**Full Kit #RSRPSR118GE**

#### STANDARD LOW ROOF

DRIVER	SPECS
Total Width	86"
1 x HD Start Frame - 12 Series	W:52"
1 x HD Extension Frame - 8 Series	W:34"
2 x Low Mount Shelf	D:12"
3 x Floor Mount Shelf	D:16"
1 x Lockable Box RSLBX/82	
8 x Grey Small Bin RP100	
2 x Red Large Bin RP240	
1 x End Panel RSPEP/L	
2 x Hooks RSPEP/HK	

PASSENGER	SPECS
1 x HD Start Frame - 8 Series	W:35"
1 x Low Mount Shelf	D:12"
1 x Floor Mount Shelf	D:16"
1 x 3 Drawer Kit RCK2/C	
1 x 2 Drawer Kit RCK3/C	
1 x Support Bar RSBAR/80	
1 x End Panel RSPEP/R	
2 x Hooks RSPEP/HK	

#### MOUNTING BRACKETS INCLUDED

#### LONG LOW ROOF

Mercedes Metris 135"  
**Full Kit #RSMM135GE**  
 Ford Transit Long Low Roof 148"  
**Full Kit #RSFTLLR148GE**  
 GMC Savana/Chevy Express Extended  
**Full Kit #RSGMSCCEXGE**  
 Ram Promaster Standard Roof 136"  
**Full Kit #RSRPSR136GE**

#### LONG LOW ROOF



DRIVER	SPECS
Total Width	103"
1 x HD Start Frame - 12 Series	W:52"
1 x HD Extension Frame - 12 Series	W:51"
2 x Low Mount Shelf	D:12"
3 x Floor Mount Shelf	D:16"
1 x Lockable Box RSLBX/122	
1 x End Panel RSPEP/L	
2 x Hooks RSPEP/HK	

PASSENGER	SPECS
1 x HD Start Frame - 12 Series	W:52"
1 x Low Mount Shelf	D:12"
2 x Floor Mount Shelf	D:16"
12 x Grey Small Bin RP100	
6 x Red Large Bin RP240	
1 x End Panel RSPEP/R	


#### MOUNTING BRACKETS INCLUDED

## GENERAL PACKAGE

### LONG LOW ROOF KIT SHOWN



DRIVER




PASSENGER





## ELECTRICAL PACKAGE

STANDARD LOW ROOF KIT SHOWN



DRIVER

PASSENGER

### STANDARD LOW ROOF

Mercedes Metris 126"  
**Full Kit #RSMM126EL**  
 Ford Transit Regular Low Roof 130"  
**Full Kit #RSFTRLR130EL**  
 Nissan NV Cargo Standard Roof  
**Full Kit #RSNNVCSREL**  
 GMC Savana/Chevy Express Regular  
**Full Kit #RSGMSCEREL**  
 Ram Promaster Standard Roof 118"  
**Full Kit #RSRPSR118EL**

### STANDARD LOW ROOF

DRIVER	SPECS
Total Width	86"
1 x HD Start Frame - 12 Series	W:52"
1 x HD Extension Frame - 8 Series	W:34"
2 x Low Mount Shelf	D:12"
2 x Floor Mount Shelf	D:16"
1 x 2 Drawer Kit RCSK3/C	
1 x 3 Drawer Kit RCK2/C	
1 x Support Bar RSBAR/80	
1 x Lockable Box RSLBX/82	
1 x End Panel RSPEP/L	

PASSENGER	SPECS
1 x HD Start Frame - 8 Series	W:35"
1 x Low Mount Shelf	D:12"
1 x Floor Mount Shelf	D:16"
8 x Grey Small Bin RP100	
2 x Red Large Bin RP240	
1 x Wire Reel Holder RSCDH/81	
1 x End Panel RSPEP/R	
2 x Hooks RSPEP/HK	

**MOUNTING BRACKETS INCLUDED**

### LONG LOW ROOF

Mercedes Metris 135"  
**Full Kit #RSMM135EL**  
 Ford Transit Long Low Roof 148"  
**Full Kit #RSFTLLR148EL**  
 GMC Savana/Chevy Express Extended  
**Full Kit #RSGMSCEXEL**  
 Ram Promaster Standard Roof 136"  
**Full Kit #RSRPSR136EL**

### LONG LOW ROOF


DRIVER	SPECS
Total Width	103"
1 x HD Start Frame - 12 Series	W:52"
1 x HD Extension Frame - 12 Series	W:51"
2 x Low Mount Shelf	D:12"
3 x Floor Mount Shelf	D:16"
1 x Lockable Box RSLBX/122	
1 x End Panel RSPEP/L	

PASSENGER	SPECS
1 x HD Start Frame - 12 Series	W:52"
1 x Low Mount Shelf	D:12"
1 x Floor Mount Shelf	D:16"
12 x Grey Small Bin RP100	
3 x Red Large Bin RP240	
1 x Wire Reel Holder RSCDH/121	
1 x End Panel RSPEP/R	
2 x Hooks RSPEP/HK	

**MOUNTING BRACKETS INCLUDED**

## ELECTRICAL PACKAGE

LONG LOW ROOF KIT SHOWN




DRIVER

PASSENGER

Partitions Sold Separately - Refer to Page 7

## AMERICA'S MOST POPULAR PACKAGE

STANDARD LOW ROOF KIT SHOWN



DRIVER

PASSENGER

### STANDARD LOW ROOF

Mercedes Metris 126"  
**Full Kit #RSMM126AM**  
 Ford Transit Regular Low Roof 130"  
**Full Kit #RSFTRLR130AM**  
 Nissan NV Cargo Standard Roof  
**Full Kit #RSNNVCSRAM**  
 GMC Savana/Chevy Express Regular  
**Full Kit #RSGMSCERAM**  
 Ram Promaster Standard Roof 118"  
**Full Kit #RSRPSR118AM**

### STANDARD LOW ROOF

DRIVER	SPECS
Total Width	86"
1 x HD Start Frame - 12 Series	W:52"
1 x HD Extension Frame - 8 Series	W:34"
2 x Mid Mount Shelf	D:10"
2 x Low Mount Shelf	D:12"
2 x Floor Mount Shelf	D:16"
5 x Red Medium Bin RP120	
8 x Grey Small Bin RP100	
6 x Grey Medium Bin RP200	
5 x Red Large Bin RP240	
1 x End Panel RSPEP/L	
2 x Hooks RSPEP/HK	

PASSENGER	SPECS
1 x HD Start Frame - 8 Series	W:35"
1 x Low Mount Shelf	D:12"
2 x Floor Mount Shelf	D:16"
1 x End Panel RSPEP/R	
2 x Hooks RSPEP/HK	
1 x Case Holder RCVCH	
1 x RolaCase RC001/CL	

**MOUNTING BRACKETS INCLUDED**

### LONG LOW ROOF

Mercedes Metris 135"  
**Full Kit #RSMM135AM**  
 Ford Transit Long Low Roof 148"  
**Full Kit #RSFTLLR148AM**  
 GMC Savana/Chevy Express Extended  
**Full Kit #RSGMSCEXAM**  
 Ram Promaster Standard Roof 136"  
**Full Kit #RSRPSR136AM**

### LONG LOW ROOF



DRIVER	SPECS
Total Width	103"
1 x HD Start Frame - 12 Series	W:52"
1 x HD Extension Frame - 12 Series	W:51"
2 x Mid Mount Shelf	D:10"
2 x Low Mount Shelf	D:12"
2 x Floor Mount Shelf	D:16"
6 x Red Medium Bin RP120	
12 x Grey Small Bin RP100	
6 x Grey Medium Bin RP200	
6 x Red Large Bin RP240	
1 x End Panel RSPEP/L	
2 x Hooks RSPEP/HK	

PASSENGER	SPECS
1 x HD Start Frame - 12 Series	W:52"
1 x Low Mount Shelf	D:12"
2 x Floor Mount Shelf	D:16"
1 x End Panel RSPEP/R	
2 x Hooks RSPEP/HK	
1 x Case Holder RCVCH	
1 x RolaCase RC001/CL	

**MOUNTING BRACKETS INCLUDED**

## AMERICA'S MOST POPULAR PACKAGE

LONG LOW ROOF KIT SHOWN




DRIVER

PASSENGER



## BASIC PACKAGE

### STANDARD MID-HIGH ROOF KIT SHOWN



STANDARD MID-HIGH ROOF	
Ford Transit Regular Mid Roof 130"	
Full Kit #RSFTRMR130BA	
Nissan NV Cargo Van High Roof	
Full Kit #RSNNVCHRBA	
Mercedes Sprinter Standard & High Roof 144"	
Full Kit #RSMSSHR144BA	

STANDARD MID-HIGH ROOF DRIVER		SPECS
Total Width		103"
1 x HD Start Frame - 12 Series	W:52"	
1 x HD Extension Frame - 12 Series	W:51"	
2 x Low Mount Shelf	D:12"	
6 x Floor Mount Shelf	D:16"	
1 x End Panel RSPEP/MDRF/L		

PASSENGER		SPECS
1 x HD Start Frame - 12 Series	W:52"	
1 x Low Mount Shelf	D:12"	
3 x Floor Mount Shelf	D:16"	
1 x End Panel RSPEP/MDRF/R		

**MOUNTING BRACKETS INCLUDED**




DRIVER

PASSENGER

## BASIC PACKAGE

### LONG MID-HIGH ROOF KIT SHOWN



LONG MID-HIGH ROOF	
Ford Transit LWB Mid/High Roof 148"	
Full Kit #RSFTLMHR148BA	
Ram Promaster High Roof 136" & 159"	
Full Kit #RSRPHR136159BA	
Mercedes Sprinter High & Super High Roof 170"	
Full Kit #RSMSSHR170BA	

LONG MID-HIGH ROOF DRIVER		SPECS
Total Width		120"
1 x HD Start Frame - 12 Series	W:52"	
2 x HD Extension Frame - 8 Series	W:34"	
3 x Low Mount Shelf	D:12"	
9 x Floor Mount Shelf	D:16"	
1 x End Panel RSPEP/MDRF/L		

PASSENGER		SPECS
1 x HD Start Frame - 12 Series	W:52"	
1 x Low Mount Shelf	D:12"	
3 x Floor Mount Shelf	D:16"	
1 x End Panel RSPEP/MDRF/R		

**MOUNTING BRACKETS INCLUDED**




DRIVER

PASSENGER

Partitions Sold Separately - Refer to Page 7

## GENERAL PACKAGE

### STANDARD MID-HIGH ROOF KIT SHOWN




STANDARD MID-HIGH ROOF	
Ford Transit Regular Mid Roof 130"	
Full Kit #RSFTRMR130GE	
Nissan NV Cargo Van High Roof	
Full Kit #RSNNVCHRGE	
Mercedes Sprinter Standard & High Roof 144"	
Full Kit #RSMSSHR144GE	

STANDARD MID-HIGH ROOF DRIVER		SPECS
Total Width		103"
1 x HD Start Frame - 12 Series	W:52"	
1 x HD Extension Frame - 12 Series	W:51"	
2 x Low Mount Shelf	D:12"	
4 x Floor Mount Shelf	D:16"	
1 x Lockable Box RSLBX/122		
1 x Floor Enclosure RSFLE + RS120A		
1 x End Panel RSPEP/MDRF/L		
2 x Hooks RSPEP/HK		

PASSENGER		SPECS
1 x HD Start Frame - 12 Series	W:52"	
1 x Mid Mount Shelf	D:10"	
3 x Floor Mount Shelf	D:16"	
6 x Red Medium Bin RP60		
6 x Red Large Bin RP240		
1 x End Panel RSPEP/MDRF/R		

**MOUNTING BRACKETS INCLUDED**




DRIVER

PASSENGER

## GENERAL PACKAGE

### LONG MID-HIGH ROOF KIT SHOWN



LONG MID-HIGH ROOF	
Ford Transit LWB Mid/High Roof 148"	
Full Kit #RSFTLMHR148GE	
Ram Promaster High Roof 136" & 159"	
Full Kit #RSRPHR136159GE	
Mercedes Sprinter High & Super High Roof 170"	
Full Kit #RSMSSHR170GE	

LONG MID-HIGH ROOF DRIVER		SPECS
Total Width		120"
1 x HD Start Frame - 12 Series	W:52"	
2 x HD Extension Frame - 8 Series	W:34"	
3 x Low Mount Shelf	D:12"	
5 x Floor Mount Shelf	D:16"	
1 x Lockable Box RSLBX/122		
1 x Floor Enclosure RSFLE + RS120A		
1 x 4 Drawer Kit RCSK5/C		
1 x 5 Drawer Kit RCSK4/C		
2 x Support Bars RSBAR/80		
1 x End Panel RSPEP/MDRF/L		
2 x Hooks RSPEP/HK		

PASSENGER		SPECS
1 x HD Start Frame - 12 Series	W:52"	
1 x Mid Mount Shelf	D:10"	
3 x Floor Mount Shelf	D:16"	
6 x Red Medium Bin RP60		
6 x Red Large Bin RP240		
1 x End Panel RSPEP/MDRF/R		
1 x Multi Tool Holder RSPEP/MH		
1 x Tool Tray RSPEP/TY		

**MOUNTING BRACKETS INCLUDED**



DRIVER


PASSENGER





## ELECTRICAL PACKAGE

### STANDARD MID-HIGH ROOF KIT SHOWN



#### STANDARD MID-HIGH ROOF


Ford Transit Regular Mid Roof 130"  
**Full Kit #RSFTRMR130EL**  
 Nissan NV Cargo Van High Roof  
**Full Kit #RSNNVCHREL**  
 Mercedes Sprinter Standard & High Roof 144"  
**Full Kit #RSMSSHR144EL**

#### STANDARD MID-HIGH ROOF


DRIVER	SPECS
Total Width	103"
1 x HD Start Frame - 12 Series	W:52"
1 x HD Extension Frame - 12 Series	W:51"
2 x Low Mount Shelf	D:12"
5 x Floor Mount Shelf	D:16"
1 x Lockable Box RSLBX/122	
1 x End Panel RSPEP/MDRF/L	

PASSENGER	SPECS
1 x HD Start Frame - 12 Series	W:52"
1 x Low Mount Shelf	D:12"
2 x Floor Mount Shelf	D:16"
12 x Grey Small Bin RP100	
6 x Red Large Bin RP240	
1 x Cable Reel Holder RSCDH/121	
1 x End Panel RSPEP/MDRF/R	
2 x Hooks RSPEP/HK	

**MOUNTING BRACKETS INCLUDED**




DRIVER



PASSENGER

## ELECTRICAL PACKAGE

### LONG MID-HIGH ROOF KIT SHOWN



#### LONG MID-HIGH ROOF


Ford Transit LWB Mid/High Roof 148"  
**Full Kit #RSFTLMHR148EL**  
 Ram Promaster High Roof 136" & 159"  
**Full Kit #RSRPHR136159EL**  
 Mercedes Sprinter High & Super High Roof 170"  
**Full Kit #RSMSSHR170EL**

#### LONG MID-HIGH ROOF

DRIVER	SPECS
Total Width	120"
1 x HD Start Frame - 12 Series	W:52"
2 x HD Extension Frame - 8 Series	W:34"
3 x Low Mount Shelf	D:12"
5 x Floor Mount Shelf	D:16"
1 x Lockable Box RSLBX/122	
1 x 4 Drawer Kit RCSK5/C	
1 x 5 Drawer Kit RCSK4/C	
2 x Support Bars RSBAR/80	
1 x End Panel RSPEP/MDRF/L	

PASSENGER	SPECS
1 x HD Start Frame - 12 Series	W:52"
1 x Low Mount Shelf	D:12"
2 x Floor Mount Shelf	D:16"
12 x Grey Small Bin RP100	
6 x Red Large Bin RP240	
1 x Cable Reel Holder RSCDH/121	
1 x End Panel RSPEP/MDRF/R	
2 x Hooks RSPEP/HK	

**MOUNTING BRACKETS INCLUDED**



DRIVER




PASSENGER

Partitions Sold Separately - Refer to Page 7

## AMERICA'S MOST POPULAR PACKAGE

### STANDARD MID-HIGH ROOF KIT SHOWN



#### STANDARD MID-HIGH ROOF


Ford Transit Regular Mid Roof 130"  
**Full Kit #RSFTRMR130AM**  
 Nissan NV Cargo Van High Roof  
**Full Kit #RSNNVCHRAM**  
 Mercedes Sprinter Standard & High Roof 144"  
**Full Kit #RSMSSHR144AM**

#### STANDARD MID-HIGH ROOF

DRIVER	SPECS
Total Width	103"
1 x HD Start Frame - 12 Series	W:52"
1 x HD Extension Frame - 12 Series	W:51"
2 x High Mount Shelf	D:8"
2 x Mid Mount Shelf	D:10"
2 x Low Mount Shelf	D:12"
2 x Floor Mount Shelf	D:16"
18 x Red Small Bin RP25	
6 x Red Medium Bin RP120	
12 x Grey Medium Bin RP200	
6 x Red Large Bins RP240	
1 x End Panel RSPEP/MDRF/L	
2 x Hooks RSPEP/HK	

PASSENGER	SPECS
1 x HD Start Frame - 12 Series	W:52"
1 x High Mount Shelf	D:12"
3 x Floor Mount Shelf	D:16"
1 x End Panel RSPEP/MDRF/R	
2 x Hooks RSPEP/HK	
1 x RolaCase RC001/CL	
1 x Case Holder RCVCH	

**MOUNTING BRACKETS INCLUDED**




DRIVER



PASSENGER

## AMERICA'S MOST POPULAR PACKAGE

### LONG MID-HIGH ROOF KIT SHOWN



#### LONG MID-HIGH ROOF


Ford Transit LWB Mid/High Roof 148"  
**Full Kit #RSFTLMHR148AM**  
 Ram Promaster High Roof 136" & 159"  
**Full Kit #RSRPHR136159AM**  
 Mercedes Sprinter High & Super High Roof 170"  
**Full Kit #RSMSSHR170AM**

#### LONG MID-HIGH ROOF


DRIVER	SPECS
Total Width	120"
1 x HD Start Frame - 12 Series	W:52"
2 x HD Extension Frame - 8 series	W:34"
3 x High Mount Shelf	D:8"
3 x Mid Mount Shelf	D:10"
3 x Low Mount Shelf	D:12"
3 x Floor Mount Shelf	D:16"
15 x Red Small Bin RP25	
5 x Red Medium Bin RP120	
10 x Grey Medium Bin RP200	
5 x Red Large Bins RP240	
1 x End Panel RSPEP/MDRF/L	
2 x Hooks RSPEP/HK	

PASSENGER	SPECS
1 x HD Start Frame - 12 Series	W:52"
1 x High Mount Shelf	D:12"
3 x Floor Mount Shelf	D:16"
1 x End Panel RSPEP/MDRF/R	
1 x Multi Tool Holder RSPEP/MH	
1 x RolaCase RC001/CL	
1 x Case Holder RCVCH	
1 x Tool Tray RSPEP/TY	

**MOUNTING BRACKETS INCLUDED**



DRIVER




PASSENGER



Construction: 1.1 mm zinc coated steel  
All Fixing Components Included.

## END PANELS FOR THE SHELVING



### RSPEP/HK



Lead Hook - Holds extension leads, hoses, etc

### RSPEP/MH




Tool Rack - Holds tools of different shapes and sizes.

### RSPEP/TY



Tool Tray - Holds loose tools and/or equipment.

### RSPEP/CDH/4



Wire reel holder for work vans-ideal for the demands of the electrical contractor. Attaches to the end panels or any flat surface. Easily removable crossbars for loading and unloading reels.

### 3-Tier Refrigerant Tank Holder



#### RS3TRTH

Hold 1-50 lbs & 2-30lbs tanks or 3-30 lbs tanks with straps

### RSFLE - Floor mount end panels and strap.

#### RS840A - Adapting bracket to suit 4 series frame.




### RSFLE - Floor mount end panels and strap.

#### RS120A - Adapting bracket to suit 4 series frame.




Both part numbers will be required to make full floor mount enclosure kit

### RP25




Small Plastic Bin  
1 Compartment

### RP60



Medium Plastic Bin  
1 Compartment

### RP120




Large Plastic Bin  
3 Adjustable Compartments

### RP240




X-large Plastic Bin  
3 Adjustable Compartments  
(Dividers RP240/D sold separately)

### RP100




Small Plastic Bin  
3 Adjustable Compartments

### RP200




Medium Plastic Bin  
3 Adjustable Compartments

### RP400X100



Large Plastic Bin  
3 Adjustable Compartments

### RP400x200




Large Plastic Bin  
3 Adjustable Compartments






1. Choose your bay length 8 or 12 series. You always begin with a start frame & then add an extension frame to add length.
2. Choose your post heights. **78 31/32"** or **60 19/32"**. Both can be cut down to suit any vehicle model.
3. Choose how many shelves you require to fit into the bay.
4. Choose your plastic bins & accessories (if required)
  - 2 cabinets can be joined horizontally to fit the 8 series shelving ( 1 x **RCJNR/C** & 2 x **RSBAR/80** will be required )



CAT NO;	HEIGHT (inches)	LENGTH (inches)	DESCRIPTION	Post Height Adjustment	
				Height	Cut at 1 1/32" Intervals
<b>RSSFR/HD/80/2006</b>	78 31/32"	35 3/64"	8 Series Dual Post Heavy Duty Start Frame	78 31/32"	60 19/32"
<b>RSSFR/HD/80/1539</b>	60 19/32"			60 19/32"	42 1/4"
<b>RSEFR/HD/80/2006</b>	78 31/32"	34 1/16"	8 Series Dual Post Heavy Duty Extension Frame		
<b>RSEFR/HD/80/1539</b>	60 19/32"				

Frame Purchase Example: **RSSFR/HD/80/1539**  
 If you want to extend then you would add a **RSEFR/HD/80/1539**  
 All components are zinc annealed & powder coated, complete with instructions & mounting hardware.

SHELF	CAT NO;	DESCRIPTION	HEIGHT	LENGTH	WIDTH	PLASTIC BINS
	RSSHL/81/FR	8 Series File Retainer	-	-	-	-
	RSSHL/83	High mount shelf	Rear 3 35/64" Front 1 49/64"	33 1/32"	7 7/8"	Holds 6 x <b>RP25</b> bins
	RSSHL/84	Mid mount shelf	Rear 3 35/64" Front 1 49/64"	33 1/32"	9 29/64"	Holds 2x <b>RP120</b> or 4x <b>RP60</b> bins
	RSSHL/85	Low mount shelf	Rear 3 35/64" Front 1 49/64"	33 1/32"	12 1/16"	Holds 4x <b>RP200</b> or 8x <b>R100</b> bins
	RSSHL/86	Floor mount shelf	Rear 6 39/64" Front 3 5/32"	33 1/32"	15 15/16"	Holds 4x <b>RP400x200</b> or Holds 2x <b>RP240</b> bins
	RSSHL/87	Low mount shelf	Rear 3 35/64" Front 0 63/64"	33 1/32"	14 27/32"	Holds 2 x <b>RC001</b> or <b>RC002</b> Rolacases <b>RS/87/FW</b> -Foam
	RSSHL/88	Floor mount shelf	Rear 3 39/64" Front 2 9/16"	33 1/32"	15 15/16"	Holds 8x <b>RP400x100</b> or 4x <b>RP240x200</b> bins

**ACCESSORIES FOR 8 SERIES:** Please refer to page 15 for more accessories.


**RSCDH/121**



Adjustable wire & cable reel holder  
Ideal for 8 series shelving

Dimensions:  
W:6 11/16" D:14 9/16" H:33 1/32"

**RSLBX/84**




CAT No. A B C

**RSLBX/84** A:15 1/2" B:9 27/32" C:33 1/32"  
**RSLBX/82** A:15 1/2" B:16 17/32" C:33 1/32"

2 x **RCSK5/C**  
 1 x **RCJNR/C** (Joining Bracket)  
 1 x **RSBAR/80**




**RSBAR/80**



Mounting bar for **ROLA CASE** 8 series shelving. Only required for when dual cabinets are being fitted

**RSJNR/C**



Vertical joining bracket for connecting **ROLA-CASE** cabinets vertically. (4 per kit plus screws)


\*Refer to page 4 for **ROLA-CASE** cabinet information



## 4 Step System

1. Measure the height of your vehicle. If your vehicle height is  $60 \frac{19}{32}$ " or lower, then the appropriate post height is 1539. If your vehicle height is between  $60 \frac{19}{32}$ " &  $78 \frac{31}{32}$ ", then the appropriate post height is 2006. All posts can be cut down in  $1 \frac{1}{32}$ " intervals to achieve your desired height.
2. Determine the length of space in your cargo area. You always start with a start frame i.e. is RSSFR/HD/120/1539. If you want to grow it further, then you simply add on extension frame, which can be any length e.g. RSSFR/HD/80/1539.
3. Choose how many shelves you require to fit into your bay/s.
4. Choose your plastic bins & accessories (if required).

RSSFR/HD/120 RSEFR/HD/120





CAT NO;	HEIGHT (inches)	LENGTH (inches)	DESCRIPTION	Post Height Adjustment	
				Height	Cut at $1 \frac{1}{32}$ " Intervals
RSSFR/HD/120/2006	$78 \frac{31}{32}$ "	$51 \frac{37}{64}$ "	12 Series Dual Post Heavy Duty Start Frame	$78 \frac{31}{32}$ "	$60 \frac{19}{32}$ "
RSSFR/HD/120/1539	$60 \frac{19}{32}$ "			$60 \frac{19}{32}$ "	$42 \frac{1}{4}$ "
RSEFR/HD/120/2006	$78 \frac{31}{32}$ "	$50 \frac{19}{32}$ "	12 Series Dual Post Heavy Duty Extension Frame		
RSEFR/HD/120/1539	$60 \frac{19}{32}$ "				

Frame Purchase Example: **RSSFR/HD/120/1539**  
If you want to extend then you would add a **RSEFR/HD/120/1539**  
All components are zinc annealed & powder coated, complete with instructions & mounting hardware.

SHELF	CAT NO;	DESCRIPTION	HEIGHT	LENGTH	WIDTH	PLASTIC BINS
	RSSHL/123	High mount shelf	Rear $3 \frac{35}{64}$ " Front $1 \frac{49}{64}$ "	$49 \frac{9}{16}$ "	$9 \frac{1}{16}$ "	Holds 9 x RP25 bins
	RSSHL/124	Mid mount shelf	Rear $3 \frac{35}{64}$ " Front $1 \frac{49}{64}$ "	$49 \frac{9}{16}$ "	$10 \frac{3}{64}$ "	Holds 3 x RP120 bins or 6 x RP60
	RSSHL/125	Low mount shelf	Rear $3 \frac{35}{64}$ " Front $1 \frac{49}{64}$ "	$49 \frac{9}{16}$ "	$12 \frac{1}{64}$ "	Holds 6 x RP200 bins or 12 x RP100
	RSSHL/126	Floor mount shelf	Rear $6 \frac{39}{64}$ " Front $3 \frac{5}{32}$ "	$49 \frac{9}{16}$ "	$15 \frac{15}{16}$ "	Holds 6 x RP400x200 or Holds 3 x RP240 bins
	RSSHL/128	Floor mount shelf	Rear $3 \frac{25}{64}$ " Front $2 \frac{9}{16}$ "	$49 \frac{9}{16}$ "	$15 \frac{15}{16}$ "	Holds 6 x RP400x200 or Holds 12 x RP400x100

## ACCESSORIES FOR 12 SERIES:







**ROLA-Shelf** sliding platforms are the ultimate way to maximize your loadability. Sliding platforms give you instant access to tools and equipment without having to crawl in and out of your vehicle. Engineer designed, tested & manufactured for vehicle use.

- Ideal for commercial vans, truck caps and service truck bodies
- All platforms come with mounting brackets
- Quality powder coated steel
- Side rails and tie down points
- Up to 7 position locking mechanism
- Ideal for Curbside loading & unloading
- Fitted to the side or rear door openings
- Wide handle with one handed locking mechanism
- 100 % extendable, easy installation & can be used in conjunction with **ROLA-CASE** products



Single Platform



Double Platform

## Sliding Platform Options

PRODUCT CODE	PRODUCT	TRAVEL LENGTH	HEIGHT	WIDTH	WEIGHT (Pounds)	LOAD RATING (Pounds)
<b>RSSPF/1300x510</b>	Single sliding platform	53 <sup>11</sup> / <sub>32</sub> "	6 <sup>1</sup> / <sub>32</sub> "	19 <sup>11</sup> / <sub>16</sub> "	110.23	220.46
<b>RSEPF/1300x510</b>	Double sliding platform	53 <sup>11</sup> / <sub>32</sub> "	6 <sup>1</sup> / <sub>32</sub> "	39 <sup>3</sup> / <sub>8</sub> "	187.39	330.69
<b>RSSPF/950x510</b>	Single sliding platform	37 <sup>13</sup> / <sub>32</sub> "	6 <sup>1</sup> / <sub>32</sub> "	19 <sup>11</sup> / <sub>16</sub> "	83.77	275.57
<b>RSEPF/950x510</b>	Double sliding platform	37 <sup>13</sup> / <sub>32</sub> "	6 <sup>1</sup> / <sub>32</sub> "	39 <sup>3</sup> / <sub>8</sub> "	141.09	330.69



1 x **RSSPF/1300x510**



1 x **RSEPF/1300x1000**



2 x **RSSPF/1300x510**

**ROLA·CASE**  
MULTIPLE STORAGE SYSTEMS



**ROLA·Shelf**  
VAN & TRUCK STORAGE SOLUTIONS

**Email:** [info@rolacase.com](mailto:info@rolacase.com)

**Web:** [www.rolacaseusa.com](http://www.rolacaseusa.com)

**Phone:** 857.334.0300

*Now servicing the whole US market with 2 central warehouses*



Distributed By:

