



THOMAS
L I G H T I N G

THOMAS

Catalog 9003



Catalog 9003

thomaslighting.com • 888-202-9605

A DIVISION OF
 **ELK**
GROUP INTERNATIONAL



As Thomas Lighting enters its 100th year of providing high quality products, we would like to thank you for considering us and we hope your selection proves to be a brilliant addition to your surroundings.

Our award winning team of international designers and engineers are visionary in their thinking, constantly striving to uncover the styles of the future while revitalizing themes from the past. They challenge convention in the search for designs that prompt emotions of nostalgia, tranquility and inspiration.

With the design collaboration of our companies – the unencumbered elegance of Thomas Lighting, the European design influences of ELK Lighting, the exquisite details and aspirational elements of our home furnishings and decor line–ELK Home, to the eclectic collection of quality furniture from SteinWorld – all of these creative threads converge into an array of complimentary home furnishing options.

We invite you to explore the websites listed on our back cover for a glimpse at our entire array of distinctive products, which are crafted to exceptionally high standards of quality, innovation, and design.

With sincerest gratitude,

BRADFORD SMITH
Chief Executive Officer
ELK Group International

A DIVISION OF



PERMANENT SHOWROOMS

Atlanta ♦ Dallas ♦ High Point ♦ Las Vegas ♦ New York
Toronto ♦ Hong Kong





CONTENTS

2	Timeline
4	Quick Find Indoor
6	Quick Find Outdoor
7	Lamps
8	Collections
123	Pendants
151	Foyer
157	Ceiling
175	Wall Sconces
189	Bath
253	LED Mirrors
258	Task Lighting
273	Recessed Lighting
282	Step Lighting
285	Outdoor
336	Index



- 1919 The Moe-Bridges Company was co-founded as a partnership between two brothers, Henrik and Ole Moe, and other entrepreneurs. Based in Milwaukee, WI, Moe-Bridges Co. specialized in manufacturing lighting fixtures.
- 1920 With their new company barely a year old, Henrik and Ole Moe split the Moe-Bridges company and started the Moe Brothers Manufacturing Company.
- 1934 The Electric Sprayit Company, a forerunner to Thomas Industries' compressor and pump division, acquired Moe-Bridges Company.
- 1938 Moe Brothers Manufacturing moved operations from Milwaukee to Fort Atkinson, WI and continued to build their lighting fixtures business.
- 1948 Moe Brothers Manufacturing was purchased by a Louisville investment group headed by Lee Thomas. The company was renamed Moe Light and a national advertising campaign was launched to promote residential lighting.
- 1950 Moe Light expanded and opened a new residential lighting factory in Kentucky and acquired Los Angeles-based Star Lighting Fixture Company.
- 1953 A merger of the Electric Sprayit Company and Moe Brothers Manufacturing formed Thomas Industries. The union of these two business units produced the cornerstone of what would become the company's two core businesses: lighting fixtures and air compressors/pumps.
- 1955 Thomas Industries moved its corporate headquarters from Wisconsin to Louisville, KY. That same year, Thomas Industries went from a privately owned company to a publicly owned one.
- 1957 Thomas Industries acquired the Radiant Glass Company of Fort Smith, AR, a producer of street lighting globes and opal ware glass for lighting fixtures.
- 1958 Thomas Industries further expanded by acquiring the Benjamin Electric Manufacturing Company located in Des Plaines, IL, a manufacturer of commercial lighting fixtures.
- 1959 A further acquisition by Thomas Industries was C&M Products Co., Ltd. of Toronto, enabling the company to expand into the growing Canadian market.
- 1961 Lee Thomas stepped down from his position as president of Thomas Industries and was elected to serve as chairman of the board of directors, as well as CEO.
- 1963 The company streamlined its business splitting operations into five divisions: Residential Lighting Division (Moe Lighting and Star Lighting lines), Commercial and Industrial Lighting (Benjamin Electric products), Special OEM Products Division (Electric Sprayit lines), and the Pacific and Canadian Divisions, which were geographic in nature.



- 1967** ○ The acquisition of the Sandel Manufacturing company of Chicago and the Phil-Mar Corporation of Cleveland enabled the expansion into portable lamps.

Thomas Industries stock was listed on the New York Stock Exchange.
- 1970s** ○ Thomas Industries enjoyed further expansion to include more than 2.3 million square feet of production space in 13 plants and employed more than 3,700 people with sales of \$82 million.
- 1973** ○ The Residential Lighting Division was further broadened by the acquisition of Abbott Industries, a producer of children's lamps, and Spring Steel Fasteners, Inc., a producer of products for the electrical and construction industry.
- 1974-1984** ○ Diversification, expansion, and divestitures were common during this period. Capri Lighting of California and Emco Lighting of Milan, IL was acquired in 1984.
- 1980s-1990s** ○ Along with a change in leadership and the retirement of Chairman Lee Thomas Thomas came a reorganization of the corporate structure. A focus tightened the Thomas structure replacing the five divisions with two key divisions: Lighting and Specialty Products.

- 1989** ○ Day-Brite Lighting, manufacturer of commercial and industrial fluorescent lighting, was purchased by Thomas. A patent of a totally electronic fluorescent ballast provided Thomas with the distinction of being the only US manufacturer of both electronic ballasts and fluorescent fixtures.
- 1998** ○ A joint venture with major competitor, GT Lighting, LLC, formed a new company, Genlyte Thomas Group, LLC, and became the third largest lighting fixture manufacturer in North America.
- 2004** ○ Genlyte acquired the lighting division of Thomas Industries to form the Genlyte Group.
- 2007** ○ Philips Lighting Group acquired Genlyte Group in order to strengthen their position in the North American outdoor lighting market.
- 2016** ○ ELK Group International acquires Thomas Lighting.

Cornerstone Lighting, a value brand that already existed within ELK Group International, was integrated into the Thomas Lighting Brand.



INDOOR



ALLURE 38



ARLINGTON 62



ASTORIA 22



ASTORIA 24



BECKETT 26



BECKETT 28



BELLA 76



BELLA 78



BRIGHTON 96



BRIGHTON 98



BRISTOL LANE 84



BRISTOL LANE 85



CASUAL MISSION 44



CASUAL MISSION 46



CONWAY 72



CONWAY 74



DELPHINE 10



DELPHINE 12



DELPHINE 14



ELIPSE 58



ELIPSE 60



FARMINGTON 36



GEORGETOWN 90



GRANGE 21



HARMONY 92



HARMONY 94



HAVEN 116



HAVEN 118



JACKSON 64



JACKSON 66

COLLECTIONS QUICK FIND

INDOOR



NOTRE DAME 20



PARK CITY 56



PENDENZA 52



PENDENZA 54



PITTMAN 40



PITTMAN 42



PRESTIGE 104



PRESTIGE 107



RIVA 100



RIVA 102



TAHOE 86



TAHOE 88



TIA 68



TIA 70



TREME 112



TREME 114



TRITON 80



TRITON 82



WEST END 16




WEST END 18



WHITMORE 110



WILLIAMSPORT 30



WILLIAMSPORT 32



WRIGHT 48



WRIGHT 50

ADDITIONAL COLLECTIONS:

APERATURE 284
 AURORA 260
 AXEL 275
 BEACON 284
 BELMAR 234
 BLAKESLEY 124

CALIFON 240
 CLARION 172
 CLASSIC LOFT 124
 EZ STEP 283
 KALONA 171
 LIBERTY PARK 126
 MAXFIELD 188
 MIDTOWN 187

MORGAN 160
 PLANDOME 275
 PORTAL 187
 QUINCY 127
 RAVENDALE 232
 SHELBURNE 250
 SINCLAIR 238
 SUDBURY 248

SUMMIT PLACE 236
 SUNGLOW 171
 TITAN 172
 TUXEDO 264
 ZEELED PRO 262
 ZEELINE 263
 ZEESTICK 269

COLLECTIONS QUICK FIND

OUTDOOR



ASPEN LODGE 288



AMBLER 298



ASHFORD 320



ASHFORD 321



ASHFORD 322



ASHFORD 323



ASHFORD 319



BRENTWOOD 311



BROAD STREET 286



CAPE ANN 305



COTSWOLD 303



COVINGTON 312



COVINGTON 313



CROWLEY 299



HAWTHORNE 317



HERITAGE 323



HERITAGE 324



HERITAGE 323



LANDIS 299



LANGHORN 293



LANGHORN 293



LORINGDALE 304



MARINA 290



MARINA 290



MARITIME 291



MEADOW VIEW 301



MENDHAM 348



MENDHAM 306



MISSION 287



MULLEN GATE 298



ONION 296



ONION 297



OSAGE 299



PARK AVENUE 311



PORTSIDE 294



PRINCE STREET 300



RIDGEWOOD 308



RIDGEWOOD 309



SAN MATEO 294



SEARSPORT 289



SHAKER HEIGHTS 305



SPRING LAKE 310



STREETSIDE CAFÉ 292



TEMPLE HILL 316



TRINITY 302



VANTON 293



VILLAGE LANTERN 295



VINTON STATION 292

COLLECTIONS QUICK FIND

LED LAMPS **LED**

Energy saving dimmable filament bulbs offered in a range of sizes and styles. Low power consumption G9 LED bulb also available.



1110

4W LED Med.
400 Lumens, 2700K
80 CRI
2½"W x 5¾"H



1111

3W LED Med.
260 Lumens, 2700K
80 CRI
1¾"W x 4¼"H



1112

6W LED Cand.
530 Lumens, 2700K
80 CRI
1½"W x 4¼"H



1113

7W LED G9
430 Lumens, 3000K
80 CRI
1½"W x 3"H



1119

7W LED GU10
600 Lumens, 3000K
80 CRI
2"W x 2"H



1114

7W LED G9
430 Lumens, 3000K
80 CRI
1¼"W x 12"H



T3-LED **LED**

7W LED T3
600 Lumens, 3000K, 90 CRI
½"W x 4¾"H

G9-LED

3W LED G9
270 Lumens, 3000K
90 CRI
½"W x 2"H



LED

VINTAGE FILAMENT LAMPS

These dimmable nostalgic light bulbs will enhance the look of any fixture especially those with visible bulbs.



1103

60W Med.
1¼"W x 12"H



1099

60W Med.
1¼"W x 7"H



1101

40W Cand.
1"W x 3½"H



1102

60W Med.
1¾"W x 4¼"H



1092

60W Med.
2½"W x 5"H

COLLECTIONS





COLLECTIONS

46235/24

24 light chandelier in Polished Chrome
36"W x 36"H
24 lights x 60W Med. ***Shown with Lamp 1102**
50" Overall height
{1 x 6" rod, 2 x 12" rods with hang straight}
**lamp not included-See page 7*



46262/14

14 light chandelier in Polished Chrome
38"W x 21"H
14 lights x 60W Med. ***Shown with Lamp 1102**
65" Overall height
{1 x 6" rod, 1 x 12" rod, 1 x 24" Extension rods with hang straight}
**lamp not included-See page 7*



46234/12

12 light chandelier in Polished Chrome
27"W x 27"H
12 lights x 60W Med. ***Shown with Lamp 1102**
47" Overall height
{1 x 6" rod, 2 x 12" rods with hang straight}
**lamp not included-See page 7*



DELPHINE


46233/12

12 light chandelier in Polished Chrome
16"W x 16"H
12 lights x 60W Med. ***Shown with Lamp 1102**
43" Overall height
{1 x 6" rod, 2 x 12" rods with hang straight}
**lamp not included-See page 7*



46261/10

10 light chandelier in Polished Chrome
33"W x 15"H
10 lights x 60W Med. ***Shown with Lamp 1102**
59" Overall height
{1 x 6" rod, 1 x 12" rod, 1 x 24" Extension rods with hang straight}
**lamp not included-See page 7*




46260/6

6 light chandelier in Polished Chrome
28"W x 12"H
6 lights x 60W Med. ***Shown with Lamp 1102**
56" Overall height
{1 x 6" rod, 1 x 12" rod, 1 x 24" Extension rods with hang straight}
**lamp not included-See page 7*



46245/24

24 light chandelier in Satin Brass
36"W x 36"H
24 lights x 60W Med. *Shown with Lamp 1102
50" Overall height
{1 x 6" rod, 2 x 12" rods with hang straight}
*lamp not included-See page 7



46242/14

14 light chandelier in Satin Brass
38"W x 21"H
14 lights x 60W Med. *Shown with Lamp 1102
65" Overall height
{1 x 6" rod, 1 x 12" rod, 1 x 24" Extension rods with hang straight}
*lamp not included-See page 7



46244/12

12 light chandelier in Satin Brass
27"W x 27"H
12 lights x 60W Med. *Shown with Lamp 1102
47" Overall height
{1 x 6" rod, 2 x 12" rods with hang straight}
*lamp not included-See page 7



46240/6

6 light chandelier in Satin Brass
28"W x 12"H
6 lights x 60W Med. *Shown with Lamp 1102
56" Overall height
{1 x 6" rod, 1 x 12" rod, 1 x 24" Extension rods with hang straight}
*lamp not included-See page 7



DELPHINE

46243/12

12 light chandelier in Satin Brass
16"W x 16"H
12 lights x 60W Med. ***Shown with Lamp 1102**
43" Overall height
{1 x 6" rod, 2 x 12" rods with hang straight}
**lamp not included-See page 7*




46241/10

10 light chandelier in Satin Brass
33"W x 15"H
10 lights x 60W Med. ***Shown with Lamp 1102**
59" Overall height
{1 x 6" rod, 1 x 12" rod, 1 x 24" Extension rods with hang straight}
**lamp not included-See page 7*




46232/24

24 light chandelier in Oil Rubbed Bronze
36"W x 36"H
24 lights x 60W Med. *Shown with Lamp 1102
50" Overall height
{1 x 6" rod, 2 x 12" rods with hang straight}
*lamp not included-See page 7



46229/14

14 light chandelier in Oil Rubbed Bronze
38"W x 21"H
14 lights x 60W Med. *Shown with Lamp 1102
65" Overall height
{1 x 6" rod, 1 x 12" rod, 1 x 24" Extension rods with hang straight}
*lamp not included-See page 7



46231/12

12 light chandelier in Oil Rubbed Bronze
27"W x 27"H
12 lights x 60W Med.*Shown with Lamp 1102
47" Overall height
{1 x 6" rod, 2 x 12" rods with hang straight}
*lamp not included-See page 7



DELPHINE

46230/12

12 light chandelier in Oil Rubbed Bronze
16"W x 16"H
12 lights x 60W Med. ***Shown with Lamp 1102**
43" Overall height
{1 x 6" rod, 2 x 12" rods with hang straight}
**lamp not included-See page 7*



46228/10

10 light chandelier in Oil Rubbed Bronze
33"W x 15"H
10 lights x 60W Med. ***Shown with Lamp 1102**
59" Overall height
{1 x 6" rod, 1 x 12" rod, 1 x 24" Extension rods with hang straight}
**lamp not included-See page 7*



46227/6

6 light chandelier in Oil Rubbed Bronze
28"W x 12"H
6 lights x 60W Med. ***Shown with Lamp 1102**
56" Overall height
{1 x 6" rod, 1 x 12" rod, 1 x 24" Extension rods with hang straight}
**lamp not included-See page 7*



CN240922

9 light chandelier in Brushed Nickel
27"W x 28"H
9 lights x 60W
88" Overall height
{12' wire} {60" chain}



CN240522

5 light chandelier in Brushed Nickel
20"W x 22"H
5 lights x 60W
82" Overall height
{12' wire} {60" chain}



CN240322

3 light chandelier in Brushed Nickel
15"W x 19"H
3 lights x 60W
79" Overall height
{12' wire} {60" chain}



CN240382

3 light semi flush in Brushed Nickel
15"W x 13"H
3 lights x 60W



CN240512

1 light mini pendant in Brushed Nickel
5"W x 46"H
1 light x 60W



CN240172 

1 light wall sconce in Brushed Nickel
5"W x 10"H x 6" Ext.
1 light x 60W
• clear glass



CN240122 

2 light bath bar in Brushed Nickel
15"W x 10"H x 6" Ext.
2 light x 60W
• clear glass



CN240132 

3 light bath bar in Brushed Nickel
23"W x 10"H x 6" Ext.
3 light x 60W
• clear glass



CN240142 

4 light bath bar in Brushed Nickel
30"W x 10"H x 6" Ext.
4 light x 60W
• clear glass



CN240921

9 light chandelier in Oil Rubbed Bronze
27"W x 28"H
9 lights x 60W
88" Overall height
{12' wire} {60" chain}



CN240521

5 light chandelier in Oil Rubbed Bronze
20"W x 22"H
5 lights x 60W
82" Overall height
{12' wire} {60" chain}



CN240321

3 light chandelier in Oil Rubbed Bronze
15"W x 19"H
3 lights x 60W
79" Overall height
{12' wire} {60" chain}



CN240381

3 light semi flush in Oil Rubbed Bronze
15"W x 13"H
3 lights x 60W



CN240511

1 light mini pendant in Oil Rubbed Bronze
5"W x 46"H
1 light x 60W



CN240171

- 1 light wall sconce in Oil Rubbed Bronze
 5"W x 10"H x 6" Ext.
 1 light x 60W
- clear glass

**CN240121**

- 2 light bath bar in Oil Rubbed Bronze
 15"W x 10"H x 6" Ext.
 2 light x 60W
- clear glass

**CN240131**

- 3 light bath bar in Oil Rubbed Bronze
 23"W x 10"H x 6" Ext.
 3 light x 60W
- clear glass

**CN240141**

- 4 light bath bar in Oil Rubbed Bronze
 30"W x 10"H x 6" Ext.
 4 light x 60W
- clear glass



symbol denotes up or down mounting

CN261221

12 light chandelier in Oil Rubbed Bronze with Gold Rods
34"W x 21"H
12 lights x 60W Cand.
81" Overall height
{12' wire} {60" chain}




CN260621

8 light chandelier in Oil Rubbed Bronze with Gold Rods
24"W x 21"H
8 lights x 60W Cand.
81" Overall height
{12' wire} {60" chain}



CN260611

6 light bath bar in Oil Rubbed Bronze with Gold Rods
19"W x 13"H x 5" Ext.
6 lights x 60W Cand.




CN260471

4 light wall sconce in Oil Rubbed Bronze with Gold Rods
10"W x 13"H x 5" Ext.
4 lights x 60W Cand.



CN260811

8 light bath bar in Oil Rubbed Bronze with Gold Rods
28"W x 13"H x 5" Ext.
8 lights x 60W Cand.



NOTRE DAME

1217-1010

5 light chandelier in Oil Rubbed Bronze
21"W x 9"H
6 lights x 60W Med. *Shown with Lamp 1092
55" Overall height
{12' wire} {60" chain}
*lamp not included—See page 7



1217-1013

4 light island pendant light in Oil Rubbed Bronze
31"W x 10"H
4 lights x 60W Med. *Shown with Lamp 1092
56" Overall height
{12' wire} {60" chain}
*lamp not included—See page 7



1217-1011

1 light pendant in Oil Rubbed Bronze
7"W x 8"H
1 light x 60W Med. *Shown with Lamp 1092
53" Overall height
{12' cord}
*lamp not included—See page 7



CN280922

9 light chandelier in Brushed Nickel
32"W x 23"H
9 lights x 60W
83" Overall height
{12' wire} {60" chain}
• clear glass



CN280322

3 light chandelier in Brushed Nickel
23"W x 17"H
3 lights x 60W
87" Overall height
{12' wire} {60" chain}
• clear glass



CN280522

5 light chandelier in Brushed Nickel
28"W x 17"H
5 lights x 60W
87" Overall height
{12' wire} {60" chain}
• clear glass



CN280172

- 1 light wall sconce in Brushed Nickel
 6"W x 10"H x 9" Ext.
 1 light x 60W
 • clear glass

**CN280152**

- 1 light mini pendant in Brushed Nickel
 6"W x 17"H
 1 light x 60W
 87" Overall height
 (12' wire) (60" chain)
 • clear glass

**CN280212**

- 2 light bath bar in Brushed Nickel
 16"W x 11"H x 8" Ext.
 2 light x 60W
 • clear glass

**CN280312**

- 3 light bath bar in Brushed Nickel
 25"W x 9"H x 9" Ext.
 3 light x 60W
 • clear glass

**CN280412**

- 4 light bath bar in Brushed Nickel
 35"W x 9"H x 9" Ext.
 4 light x 60W
 • clear glass



symbol denotes up or down mounting

CN280925

9 light chandelier in Satin Gold
32"W x 23"H
9 lights x 60W
83" Overall height
{12' wire} {60" chain}
• clear glass



CN280525

5 light chandelier in Satin Gold
28"W x 17"H
5 lights x 60W
87" Overall height
{12' wire} {60" chain}
• clear glass



CN280325

3 light chandelier in Satin Gold
23"W x 17"H
3 lights x 60W
87" Overall height
{12' wire} {60" chain}
• clear glass



ASTORIA

CN280175

1 light wall sconce in Satin Gold
 6"W x 10"H x 9" Ext.
 1 light x 60W
 • clear glass

**CN280155**

1 light mini pendant in Satin Gold
 6"W x 17"H
 1 light x 60W
 87" Overall height
 {12' wire} {60" chain}
 • clear glass

**CN280215**

2 light bath bar in Satin Gold
 16"W x 11"H x 8" Ext.
 2 light x 60W
 • clear glass

**CN280315**

3 light bath bar in Satin Gold
 25"W x 9"H x 9" Ext.
 3 light x 60W
 • clear glass

**CN280415**

4 light bath bar in Satin Gold
 35"W x 9"H x 9" Ext.
 4 light x 60W
 • clear glass



symbol denotes up or down mounting

CN129821

8 light chandelier in Oil Rubbed Bronze
37"W x 23"H
8 lights x 60W Med. ***Shown with Lamp 1092**
84" Overall height
{12' wire} {60" chain}

- clear glass

**lamp not included—See page 7*



CN129521

5 light chandelier in Oil Rubbed Bronze
26"W x 16"H
5 lights x 60W Med. ***Shown with Lamp 1092**
77" Overall height
{12' wire} {60" chain}

- clear glass

**lamp not included—See page 7*



CN129321

3 light chandelier in Oil Rubbed Bronze
22"W x 16"H
3 lights x 60W Med. ***Shown with Lamp 1092**
77" Overall height
{12' wire} {60" chain}

- clear glass

**lamp not included—See page 7*



CN129281

3 light pendant/semi flush dual mount in Oil Rubbed Bronze
14"W x 7"H
3 lights x 60W Med. ***Shown with Lamp 1092***
68" Overall height
{12' wire} {60" chain}

- clear glass

**lamp not included—See page 7*



alternate image

CN129231

2 light flush mount in Oil Rubbed Bronze
14"W x 7"H
2 lights x 60W Med. ***Shown with Lamp 1092***
• clear glass

**lamp not included—See page 7*




CN129121

1 light wall sconce in Oil Rubbed Bronze
6"W x 12"H x 7"Ext.
1 light x 60W Med. ***Shown with Lamp 1092***
• clear glass
**lamp not included—See page 7*



CN129041

1 light pendant in Oil Rubbed Bronze
12"W x 13"H
1 light x 60W Med. ***Shown with Lamp 1092***
74" Overall height
{12' wire} {60" chain}
• clear glass
**lamp not included—See page 7*



CN129151

1 light mini pendant in Oil Rubbed Bronze
6"W x 7"H
1 light x 60W Med. ***Shown with Lamp 1092***
68" Overall height
{12' wire} {60" chain}
• clear glass
**lamp not included—See page 7*



CN129211

2 light bath bar in Oil Rubbed Bronze
15"W x 11"H x 7"Ext.
2 lights x 60W Med. ***Shown with Lamp 1092***
• clear glass
**lamp not included—See page 7*



CN129311

3 light bath bar in Oil Rubbed Bronze
24"W x 11"H x 7"Ext.
3 lights x 60W Med. ***Shown with Lamp 1092***
• clear glass
**lamp not included—See page 7*



CN129411

4 light bath bar in Oil Rubbed Bronze
33"W x 11"H x 7"Ext.
3 lights x 60W Med. ***Shown with Lamp 1092***
• clear glass
**lamp not included—See page 7*



CN120821

8 light chandelier in Oil Rubbed Bronze
 37"W x 23"H
 8 lights x 60W Med.
 84" Overall height
 {12' wire} {60" chain}

- opal white glass



CN120281

3 light pendant/semi flush dual mount in Oil Rubbed Bronze
 14"W x 7"H
 3 lights x 60W Med.
 68" Overall height
 {12' wire} {60" chain}

- opal white glass



alternate image

CN120521

5 light chandelier in Oil Rubbed Bronze
 26"W x 16"H
 5 lights x 60W Med.
 77" Overall height
 {12' wire} {60" chain}

- opal white glass



CN120231

2 light flush mount in Oil Rubbed Bronze
 14"W x 7"H
 2 lights x 60W Med.

- opal white glass



CN120321

3 light chandelier in Oil Rubbed Bronze
 22"W x 16"H
 3 lights x 60W Med.
 77" Overall height
 {12' wire} {60" chain}

- opal white glass



CN120041

1 light pendant in Oil Rubbed Bronze
 12"W x 13"H
 1 light x 60W Med.
 74" Overall height
 {12' wire} {60" chain}

- opal white glass



CN120151

1 light mini pendant in Oil Rubbed Bronze
 6"W x 7"H
 1 light x 60W Med.
 68" Overall height
 {12' wire} {60" chain}

- opal white glass



CN120121

1 light wall sconce in Oil Rubbed Bronze
 6"W x 12"H x 7"Ext.
 1 light x 60W Med.
 • opal white glass

**CN120211**

2 light bath bar in Oil Rubbed Bronze
 15"W x 11"H x 7"Ext.
 2 lights x 60W Med.
 • opal white glass

**CN120311**

3 light bath bar in Oil Rubbed Bronze
 24"W x 11"H x 7"Ext.
 3 lights x 60W Med.
 • opal white glass

**CN120411**

4 light bath bar in Oil Rubbed Bronze
 33"W x 11"H x 7"Ext.
 3 lights x 60W Med.
 • opal white glass



symbol denotes up or down mounting

1529CH/20

9 light chandelier in Brushed Nickel
34"W x 29"H
9 lights x 60W Cand.
90" Overall height
{12' wire} {60" chain}



1525CH/20

5 light chandelier in Brushed Nickel
20"W x 23"H
5 lights x 60W Cand.
84" Overall height
{12' wire} {60" chain}



CN15752

5 light chandelier in Brushed Nickel
19"W x 22"H
5 lights x 60W Cand. ***Shown with Lamp 1101***
83" Overall height
{12' wire} {60" chain}

- clear glass ball

**lamp not included—See page 7*



CN15712

1 light pendant in Brushed Nickel
11"W x 15"H
1 light x 100W Med. ***Shown with Lamp 1092***
76" Overall height
{12' wire} {60" chain}

**lamp not included—See page 7*



1533CH/20

3 light chandelier in Brushed Nickel
20"W x 22"H
3 lights x 60W Cand.
83" Overall height
{12' wire} {60" chain}



1515CH/20

5 light chandelier in Brushed Nickel
18"W x 20"H
5 lights x 60W Cand.
81" Overall height
{12' wire} {60" chain}



CN15862

6 light chandelier in oil Brushed Nickel
14"W x 21"H
6 lights x 60W Med. ***Shown with Lamp 1092***
44" Overall height
**lamp not included—See page 7*



1513CH/20

3 light chandelier in Brushed Nickel
13"W x 15"H
3 lights x 60W Cand.
76" Overall height
{12' wire} {60" chain}



CN15832

3 light pendant in Brushed Nickel
10"W x 16"H
3 lights x 60W Med. ***Shown with Lamp 1092***
44" Overall height
**lamp not included—See page 7*



1502WS/20

2 light wall sconce in Brushed Nickel
12"W x 11"H x 8"Ext.
2 lights x 60W Cand.



1501WS/20

1 light wall sconce in Brushed Nickel
5"W x 11"H x 7"Ext.
1 light x 60W Cand.

1523CH/20

3 light chandelier in Brushed Nickel
12"W x 12"H
3 lights x 60W Cand.
73" Overall height
{12' wire} {60" chain}



CN250641

6 light chandelier in Oil Rubbed Bronze
21"W x 12"H
6 lights x 60W Cand. ***Shown with Lamp 1101***
73" Overall height
{12' wire} {60" chain}
**lamp not included-See page 7*



CN250541

5 light chandelier in Oil Rubbed Bronze
18"W x 20"H
5 lights x 60W Cand. ***Shown with Lamp 1101***
81" Overall height
{12' wire} {60" chain}
**lamp not included-See page 7*




CN251641

6 light chandelier in Oil Rubbed Bronze
14"W x 21"H
6 lights x 60W Cand. ***Shown with Lamp 1101***
82" Overall height
{12' wire} {60" chain}
**lamp not included-See page 7*



CN250151

1 light pendant in Oil Rubbed Bronze
8"W x 14"H
1 light x 100W Med. ***Shown with Lamp 1092***
75" Overall height
{12' cord}
**lamp not included-See page 7*



CN250341

3 light chandelier in Oil Rubbed Bronze
15"W x 8"H
3 lights x 100W Med. ***Shown with Lamp 1092***
69" Overall height
{12' cord}
**lamp not included-See page 7*



CN251551

1 light pendant in Oil Rubbed Bronze
15"W x 9"H
1 light x 100W Med. ***Shown with Lamp 1092***
70" Overall height
{12' cord}
**lamp not included-See page 7*



1533CH/10

3 light chandelier in Oil Rubbed Bronze
20"W x 22"H
3 lights x 60W Cand.
83" Overall length
{12' wire} {60" chain}



1515CH/10

5 light chandelier in Oil Rubbed Bronze
18"W x 20"H
5 lights x 60W Cand.
81" Overall height
{12' wire} {60" chain}



1502WS/10

2 light wall sconce in Oil Rubbed Bronze
12"W x 11"H x 8"Ext.
2 lights x 60W Cand.



1501WS/10

1 light wall sconce in Oil Rubbed Bronze
5"W x 11"H x 7"Ext.
1 light x 60W Cand.

1513CH/10

3 light mini chandelier in Oil Rubbed Bronze
13"W x 15"H
3 lights x 60W Cand.
76" Overall height
{12' wire} {60" chain}



1509CH/10

9 light chandelier in Oil Rubbed Bronze
34"W x 31"H
9 lights x 60W Cand.
92" Overall height
{12' wire} {60" chain}



1505CH/10

5 light chandelier in Oil Rubbed Bronze
20"W x 23"H
5 lights x 60W Cand.
84" Overall height
{12' wire} {60" chain}



CN15751

5 light chandelier in Oil Rubbed Bronze
19"W x 22"H
5 lights x 60W Cand. ***Shown with Lamp 1101***
83" Overall height
{12' wire} {60" chain}

- clear glass ball


**lamp not included—See page 7*



CN15711

1 light pendant in Oil Rubbed Bronze
11"W x 15"H
1 light x 100W Med. ***Shown with Lamp 1092***
76" Overall height
{12' wire} {60" chain}

**lamp not included—See page 7*



1503CH/10

3 light chandelier in Oil Rubbed Bronze
20"W x 22"H
3 lights x 60W Cand.
84" Overall height
{12' wire} {60" chain}



1529CH/10

9 light chandelier in Oil Rubbed Bronze
34"W x 29"H
9 lights x 60W Cand.
90" Overall height
{12' wire} {60" chain}



CN15861

6 light chandelier in Oil Rubbed Bronze
14"W x 21"H
6 lights x 60W Med. ***Shown with Lamp 1092***
44" Overall height
**lamp not included-See page 7*



1525CH/10

5 light chandelier in Oil Rubbed Bronze
20"W x 23"H
5 lights x 60W Cand.
84" Overall height
{12' wire} {60" chain}



CN15831

3 light pendant in Oil Rubbed Bronze
10"W x 16"H
3 lights x 60W Med. ***Shown with Lamp 1092***
44" Overall height
**lamp not included-See page 7*



1523CH/10

3 light chandelier in Oil Rubbed Bronze
12"W x 12"H
3 lights x 60W Cand.
73" Overall length
{12' wire} {60" chain}



CN110821

8 light chandelier in Oil Rubbed Bronze
36"W x 32"H
8 x 60W Cand.
84" Overall height
{12' wire} {60" chain}



CN110521

5 light chandelier in Oil Rubbed Bronze
21"W x 21"H
5 x 60W Cand.
82" Overall height
{12' wire} {60" chain}



CN110171

1 light wall sconce in Oil Rubbed Bronze
5"W x 14"H x 4"Ext.
1 x 60W Cand.



CN110321

3 light chandelier in Oil Rubbed Bronze
18"W x 18"H
3 x 60W Cand.
79" Overall height
{12' wire} {60" chain}







M209778

6 light chandelier in Brushed Nickel
26"W x 25"H
6 lights x 40W Cand.
74" Overall height
{12' wire} {1-4" + 1-8" + 1-12" + 1-24"
rods}
• bone linen shimmer



M261678

3 light chandelier in Brushed Nickel
24"W x 34"H
3 lights x 60W Cand.
82" Overall height
{12' wire} {1-4" + 1-8" + 1-12" + 1-24"
rods}
• bone linen shimmer



M251878

1 light pendant in Brushed Nickel
6"W x 26"H
1 light x 60W Med.
74" Overall height
{12' wire} {1-4" + 1-8" + 1-12" + 1-24"
rods}
• bone linen shimmer



M271878

2 light flush in Brushed Nickel
15"W x 9"H
2 lights x 60W Med.
• bone linen shimmer
• etched white diffuser



190042217

9 light chandelier in Brushed Nickel
31"W x 29"H
9 lights x 60W Med.
77" Overall height
{12' wire} {4' chain}
• etched glass



190041217

5 light chandelier in Brushed Nickel
24"W x 22"H
5 lights x 100W Med.
70" Overall height
{12' wire} {60" chain}
• etched glass



190040217

3 light chandelier in Brushed Nickel
20"W x 20"H
3 lights x 100W Med.
68" Overall height
{12' wire} {4' chain}
• etched glass



190061217

3 light pendant in Brushed Nickel
18"W x 20"H
3 lights x 100W Med.
68" Overall height
{12' wire} {4' chain}
• etched glass



PITTMAN

190071217

2 light flush mount in Brushed Nickel
 14"W x 6"H
 2 lights x 60W Med.
 • etched glass

**190043217**

2 light semi flush or pendant in Brushed Nickel
 15"W x 15"H
 2 lights x 100W Med.
 60" Overall height
 {12' wire} {4' chain}
 • etched glass
 • convertible semi-flush or chain hung pendant



alternate image

190023217 ↑↓

1 light wall sconce in Brushed Nickel
 5"W x 9"H x 6"Ext.
 1 lights x 100W Med.
 • etched glass

**190022217** ↑↓

2 light bath bar in Brushed Nickel
 12"W x 10"H x 6"Ext.
 2 lights x 100W Med.
 • etched glass

**190060217**

1 light mini pendant in Brushed Nickel
 5"W x 8"H
 1 light x 100W Med.
 56" Overall height
 {12' wire} {1-4" + 1-8" + 1-12" = 1-24" rods}
 • etched glass

**190024217** ↑↓

3 light bath bar in Brushed Nickel
 19"W x 10"H x 6"Ext.
 3 lights x 100W Med.
 • etched glass

**190025217** ↑↓

4 light bath bar in Brushed Nickel
 24"W x 10"H x 6"Ext.
 4 lights x 100W Med.
 • etched glass



190042719

9 light chandelier in Sienna Bronze
31"W x 29"H
9 lights x 60W Med.
77" Overall height
{12' wire} {4' chain}
• etched glass



190041719

5 light chandelier in Sienna Bronze
24"W x 22"H
5 lights x 100W Med.
70" Overall height
{12' wire} {60" chain}
• etched glass



190040719

3 light chandelier in Sienna Bronze
20"W x 20"H
3 lights x 100W Med.
68" Overall height
{12' wire} {4' chain}
• etched glass



190061719

3 light pendant in Sienna Bronze
18"W x 20"H
3 lights x 100W Med.
68" Overall height
{12' wire} {4' chain}
• etched glass



190043719

2 light semi flush or pendant in Sienna Bronze
15"W x 15"H
2 lights x 100W Med.
60" Overall height
{12' wire} {4' chain}
• etched glass
• convertible semi-flush or chain hung pendant



190060719

1 light mini pendant in Sienna Bronze
5"W x 8"H
1 light x 100W Med.
56" Overall height
{12' wire} {1-4" + 1-8" + 1-12" = 1-24" rods}
• etched glass



190071719

2 light flush in Sienna Bronze
14"W x 6"H
2 lights x 60W Med.
• etched glass



190023719

1 light wall sconce in Sienna Bronze
5"W x 9"H x 6"Ext.
1 lights x 100W Med.
• etched glass



190022719

2 light bath bar in Sienna Bronze
12"W x 10"H x 6"Ext.
2 lights x 100W Med.
• etched glass



190024719

3 light bath bar in Sienna Bronze
19"W x 10"H x 6"Ext.
3 lights x 100W Med.
• etched glass



190025719

4 light bath bar in Sienna Bronze
24"W x 10"H x 6"Ext.
4 lights x 100W Med.
• etched glass



CN170922

9 light chandelier in Brushed Nickel
29"W x 28"H
9 lights x 100W Med.
89" Overall height
{12' wire} {60" chain}

- white lined glass



CN170522

5 light chandelier in Brushed Nickel
22"W x 23"H
5 lights x 100W Med.
84" Overall height
{12' wire} {60" chain}

- white lined glass



CN170322

3 light chandelier in Brushed Nickel
17"W x 19"H
3 lights x 100W Med.
80" Overall height
{12' wire} {60" chain}

- white lined glass



CN170342

3 light chandelier in Brushed Nickel
21"W x 26"H
3 lights x 100W Med.
87" Overall height
{12' wire} {60" chain}

- white lined glass



CN170382

3 light semi flush in Brushed Nickel
20"W x 12"H
3 lights x 100W Med.
• white lined glass



CASUAL MISSION

CN170332

3 light flush mount in Brushed Nickel
 13"W x 7"H
 3 lights x 60W Med.
 • white lined glass

**CN170152**

1 light mini pendant in Brushed Nickel
 5"W x 7"H
 1 light x 100W Med.
 44" Overall height
 • white lined glass

**CN170172**

1 light wall sconce in Brushed Nickel
 5"W x 8"H x 6"Ext.
 1 light x 60W Med.
 • white lined glass

**CN170212**

2 light bath bar in Brushed Nickel
 12"W x 9"H x 6"Ext.
 2 lights x 60W Med.
 • white lined glass

**CN170312**

3 light bath bar in Brushed Nickel
 20"W x 9"H x 6"Ext.
 3 lights x 60W Med.
 • white lined glass

**CN170412**

4 light bath bar in Brushed Nickel
 28"W x 9"H x 6"Ext.
 4 lights x 60W Med.
 • white lined glass



symbol denotes up or down mounting

CN170921

9 light chandelier in Oil Rubbed Bronze
 29"W x 28"H
 9 lights x 100W Med.
 89" Overall height
 {12' wire} {60" chain}
 • white lined glass

**CN170521**

5 light chandelier in Oil Rubbed Bronze
 22"W x 23"H
 5 lights x 100W Med.
 84" Overall height
 {12' wire} {60" chain}
 • white lined glass

**CN170341**

3 light chandelier in Oil Rubbed Bronze
 21"W x 26"H
 3 lights x 100W Med.
 87" Overall height
 {12' wire} {60" chain}
 • white lined glass

**CN170321**

3 light chandelier in Oil Rubbed Bronze
 17"W x 19"H
 3 lights x 100W Med.
 80" Overall height
 {12' wire} {60" chain}
 • white lined glass

**CN170381**

3 light semi flush in Oil Rubbed Bronze
 20"W x 12"H
 3 lights x 100W Med.
 • white lined glass

**CN170331**

3 light flush mount in Oil Rubbed Bronze
 13"W x 7"H
 3 lights x 60W Med.
 • white lined glass

CN170151

1 light mini pendant in Oil Rubbed Bronze
 5"W x 7"H
 1 light x 100W Med.
 44" Overall height
 • white lined glass

**CASUAL MISSION**

CN170171

- 1 light wall sconce in Oil Rubbed Bronze
 5"W x 8"H x 6"Ext.
 1 light x 60W Med.
 • white lined glass

**CN170211**

- 2 light bath bar in Oil Rubbed Bronze
 12"W x 9"H x 6"Ext.
 2 lights x 60W Med.
 • white lined glass

**CN170311**

- 3 light bath bar in Oil Rubbed Bronze
 20"W x 9"H x 6"Ext.
 3 lights x 60W Med.
 • white lined glass

**CN170411**

- 4 light bath bar in Oil Rubbed Bronze
 28"W x 9"H x 6"Ext.
 4 lights x 60W Med.
 • white lined glass



symbol denotes up or down mounting

TK0012117

9 light chandelier in Matte Nickel
 33"W x 34"H
 9 lights x 60W Med.
 103" Overall height
 {12' wire} {4' chain}

- etched white glass

**TK0011117**

5 light chandelier in Matte Nickel
 26"W x 24"H
 5 lights x 100W Med.
 72" Overall height
 {12' wire} {4' chain}

- etched white glass

**TK0010117**

3 light chandelier in Matte Nickel
 22"W x 21"H
 3 lights x 100W Med.
 69" Overall height
 {12' wire} {4' chain}

- etched white glass

**TK0009117**

3 light chandelier in Matte Nickel
 20"W x 20"H
 3 lights x 100W Med.
 90" Overall height
 {12' wire} {4' chain}

- etched white glass

**TG0002117**

3 light semi flush in Matte Nickel
 20"W x 12"H
 3 lights x 60W Med.
 • etched white glass

**TC0009117**

4 light chandelier in Matte Nickel
 27"W x 28"H
 4 lights x 100W Med.
 76" Overall height
 {12' wire} {4' chain}

- etched white glass

TC0007117

1 light pendant in Matte Nickel
 16"W x 17"H
 1 light x 100W Med.
 88" Overall height
 {12' wire} {4' chain}

- etched white glass



WRIGHT

TN0007117 

1 light wall sconce in Matte Nickel
5"W x 10"H x 7"Ext.
1 light x 100W Med.
• etched white glass



TC0008117

1 light mini pendant in Matte Nickel
5"W x 17"H
1 light x 100W Med.
53" Overall height
{12' wire} {1-4" + 1-8" + 1-12" +
1-24" rods}
• etched white glass



TV0008117 

2 light bath bar in Matte Nickel
15"W x 11"H x 7"Ext.
2 lights x 100W Med.
• etched white glass



TV0009117 

3 light bath bar in Matte Nickel
24"W x 11"H x 7"Ext.
3 lights x 100W Med.
• etched white glass



TV0010117 

4 light bath bar in Matte Nickel
32"W x 11"H x 7"Ext.
4 lights x 100W Med.
• etched white glass



TK0012704

9 light chandelier in Espresso
 33"W x 34"H
 9 lights x 60W Med.
 103" Overall height
 {12' wire} {4' chain}

- champagne glass

**190110704**

5 light chandelier in Espresso
 26"W x 24"H
 5 lights x 100W Med.
 72" Overall height
 {12' wire} {4' chain}

- champagne glass

**190109704**

3 light chandelier in Espresso
 22"W x 21"H
 3 lights x 100W Med.
 69" Overall height
 {12' wire} {4' chain}

- champagne glass

**TK0009704**

3 light chandelier in Espresso
 20"W x 20"H
 3 lights x 100W Med.
 90" Overall height
 {12' wire} {4' chain}

- champagne glass

**190113704**

3 light semi flush in Espresso
 20"W x 12"H
 3 lights x 60W Med.

- champagne glass

**190112704**

4 light pendant in Espresso
 27"W x 28"H
 4 lights x 100W Med.
 76" Overall height
 {12' wire} {4' chain}

- champagne glass

TC0007704

1 light pendant in Espresso
 16"W x 17"H
 1 light x 100W Med.
 88" Overall height
 {12' wire} {4' chain}

- champagne glass



TN0007704 

1 light wall sconce in Espresso
5"W x 10"H x 7"Ext.
1 light x 100W Med.
• champagne glass



19011704

1 light mini pendant in Espresso
5"W x 17"H
1 light x 100W Med.
53" Overall height
{12' wire} {1-4" + 1-8" + 1-12" +
1-24" rods}
• champagne glass



190114704 

2 light bath bar in Espresso
15"W x 11"H x 7"Ext.
2 lights x 100W Med.
• champagne glass



190115704 

3 light bath bar in Espresso
24"W x 11"H x 7"Ext.
3 lights x 100W Med.
• champagne glass



190116704 

4 light bath bar in Espresso
32"W x 11"H x 7"Ext.
4 lights x 100W Med.
• champagne glass



SL806978

6 light chandelier in Brushed Nickel
 42"L x 42"W x 23"H
 6 lights x 100W Med.
 71" Overall height
 {12' wire} {4' chain}

- etched glass

**TK0008217**

8 light chandelier in Brushed Nickel
 27"W x 27"H
 8 lights x 60W Med.
 99" Overall height
 {12' wire} {60" chain}

- etched glass

**SL806878**

3 light chandelier in Brushed Nickel
 20"W x 20"H
 3 lights x 100W Med.
 68" Overall height
 {12' wire} {4' chain}

- etched glass

**SL806778**

5 light chandelier in Brushed Nickel
 24"W x 23"H
 5 lights x 100W Med.
 70" Overall height
 {12' wire} {4' chain}

- etched glass

**SL860978**

2 light semi flush in Brushed Nickel
 16"W x 12"H
 2 lights x 60W Med.

- white cotton weave fabric shade
- etched white diffuser

**SL806678**

3 light pendant in Brushed Nickel
 20"W x 19"H
 3 lights x 60W Cand.
 67" Overall height
 {12' wire} {4' chain}

- white cotton weave fabric shade

**SL891078**

1 light mini pendant in Brushed Nickel
 5"W x 20"H
 1 light x 100W Med.
 68" Overall height
 {12' wire} {4' chain}

- etched glass



SL878278

2 light flush mount in Brushed Nickel
14"W x 6"H
2 lights x 60W Med.
• etched glass



TN0005217



1 light wall sconce in Brushed Nickel
5"W x 12"H x 8"Ext.
1 lights x 100W Med.
• etched glass



TV0007217



2 light bath bar in Brushed Nickel
13"W x 12"H x 9"Ext.
2 lights x 100W Med.
• etched glass



SL715378



3 light bath bar in Brushed Nickel
20"W x 12"H x 9"Ext.
3 lights x 100W Med.
• etched glass



SL715478



4 light bath bar in Brushed Nickel
27"W x 12"H x 9"Ext.
4 lights x 100W Med.
• etched glass



symbol denotes up or down mounting

SL806915

6 light chandelier in Oil Rubbed Bronze

42"L x 42"W x 23"H

6 lights x 100W Med.

71" Overall height

{12' wire} {4' chain}

- etched glass



TK0008715

8 light chandelier in Oil Rubbed Bronze

27"W x 27"H

8 lights x 60W Med.

99" Overall height

{12' wire} {60" chain}

- etched glass



SL806615

3 light pendant in Oil Rubbed Bronze

20"W x 19"H

3 lights x 60W Cand.

67" Overall height

{12' wire} {4' chain}

- white cotton weave fabric shade



SL806715

5 light chandelier in Oil Rubbed Bronze

24"W x 23"H

5 lights x 100W Med.

70" Overall height

{12' wire} {4' chain}

- etched glass



SL806815

3 light chandelier in Oil Rubbed Bronze

20"W x 20"H

3 lights x 100W Med.

68" Overall height

{12' wire} {4' chain}

- etched glass



PENDENZA

SL878215

2 light flush mount in Oil Rubbed Bronze
 14"W x 6"H
 2 lights x 60W Med.
 • etched glass

**SL860915**

2 light semi flush in Oil Rubbed Bronze
 16"W x 12"H
 2 lights x 60W Med.
 • white cotton weave fabric shade
 • etched white diffuser

**TN0005715**

1 light wall sconce in Oil Rubbed Bronze
 5"W x 12"H x 8"Ext.
 1 lights x 100W Med.
 • etched glass

**SL891015**

1 light mini pendant in Oil Rubbed Bronze
 5"W x 20"H
 1 light x 100W Med.
 68" Overall height
 {12' wire} {4' chain}
 • etched glass

**TV0007715**

2 light bath bar in Oil Rubbed Bronze
 13"W x 12"H x 9"Ext.
 2 lights x 100W Med.
 • etched glass

**SL715315**

3 light bath bar in Oil Rubbed Bronze
 20"W x 12"H x 9"Ext.
 3 lights x 100W Med.
 • etched glass

**SL715415**

4 light bath bar in Oil Rubbed Bronze
 27"W x 12"H x 9"Ext.
 4 lights x 100W Med.
 • etched glass



symbol denotes up or down mounting

CN160821

8 light chandelier in Oil Rubbed Bronze & Wood Grain

36"W x 38"H

8 lights x 100W Med.

99" Overall height

{12' wire} {60" chain}

- light beige scavo glass



CN160321

3 light chandelier in Oil Rubbed Bronze & Wood Grain

19"W x 21"H

3 lights x 100W Med.

82" Overall height

{12' wire} {60" chain}

- light beige scavo glass



CN160381

3 light pendant/semi flush dual mount in Oil Rubbed Bronze & Wood Grain

16"W x 13"H

3 lights x 100W Med.

74" Overall height

{12' wire} {60" chain}

- light beige scavo glass



CN160521

5 light chandelier in Oil Rubbed Bronze & Wood Grain

25"W x 25"H

5 lights x 100W Med.

86" Overall height

{12' wire} {60" chain}

- light beige scavo glass



alternate image

PARK CITY

CN160171

1 light wall sconce in Oil Rubbed Bronze & Wood Grain
 5"W x 7"H x 7"Ext.
 1 light x 60W Med.
 • light beige scavo glass

**CN160231**

2 light flush mount in Oil Rubbed Bronze & Wood Grain
 13"W x 6"H
 2 lights x 60W Med.
 • light beige scavo glass

**CN160211**

2 light bath bar in Oil Rubbed Bronze & Wood Grain
 14"W x 7"H x 7"Ext.
 2 lights x 60W Med.
 • light beige scavo glass

**CN160151**

1 light mini pendant in Oil Rubbed Bronze & Wood Grain
 5"W x 8"H
 1 light x 100W Med.
 44" Overall height
 {12' wire}
 • light beige scavo glass

**CN160311**

3 light bath bar in Oil Rubbed Bronze & Wood Grain
 22"W x 7"H x 7"Ext.
 3 lights x 60W Med.
 • light beige scavo glass

**CN160411**

4 light bath bar in Oil Rubbed Bronze & Wood Grain
 30"W x 7"H x 7"Ext.
 4 lights x 60W Med.
 • light beige scavo glass



symbol denotes up or down mounting

SL811578

5 light chandelier in Brushed Nickel
 24"W x 24"H
 5 lights x 100W Med.
 96" Overall height
 {12' wire} {60" chain}

- alabaster style glass

**SL811378**

3 light chandelier in Brushed Nickel
 20"W x 22"H
 3 lights x 100W Med.
 70" Overall height
 {12' wire} {4' chain}

- alabaster style glass

**SL820078**

1 light pendant in Brushed Nickel
 18"W x 10"H
 1 light x 150W Med.
 58" Overall height
 {12' wire} {4' chain}

- alabaster style glass

**SL829178**

1 light mini pendant in Brushed Nickel
 6"W x 26"H
 1 light x 100W Med.
 56" Overall height
 {12' wire} {2-12" + 1-6" rod}

- alabaster style glass

**SL825378**

3 light semi flush or pendant in Brushed Nickel
 19"W x 15"H
 3 lights x 100W Med.
 67" Overall height
 {12' wire} {4' chain}

- alabaster style glass
- convertible semi-flush or chain hung pendant. Height when ceiling mounted 15"
- etched white diffuser



alternate image

SL869278

2 light flush mount in Brushed Nickel
 14"W x 6"H
 2 lights x 60W Med.
 • alabaster style glass



SL744278 

2 light bath bar in Brushed Nickel
18"W x 10"H x 8"Ext.
2 lights x 100W Med.
• alabaster style glass



SL744378 

3 light bath bar in Brushed Nickel
24"W x 10"H x 8"Ext.
3 lights x 100W Med.
• alabaster style glass



SL744478 

4 light bath bar in Brushed Nickel
36"W x 10"H x 8"Ext.
4 lights x 100W Med.
• alabaster style glass



SL744578 

5 light bath bar in Brushed Nickel
48"W x 10"H x 8"Ext.
5 lights x 100W Med.
• alabaster style glass



SL811563

5 light chandelier in Painted Bronze
 24"W x 24"H
 5 lights x 100W Med.
 96" Overall height
 {12' wire} {60" chain}

- alabaster style glass

**SL811363**

3 light chandelier in Painted Bronze
 20"W x 22"H
 3 lights x 100W Med.
 70" Overall height
 {12' wire} {4' chain}

- alabaster style glass

**SL820063**

1 light pendant in Painted Bronze
 18"W x 10"H
 1 light x 150W Med.
 58" Overall height
 {12' wire} {4' chain}

- alabaster style glass

**SL829163**

1 light mini pendant in Painted Bronze
 6"W x 26"H
 1 light x 100W Med.
 56" Overall height
 {12' wire} {2-12" + 1-6" rod}

- alabaster style glass

**SL825363**

3 light semi flush or pendant in Painted Bronze
 19"W x 15"H
 3 lights x 100W Med.
 67" Overall height
 {12' wire} {4' chain}

- alabaster style glass
- convertible semi-flush or chain hung pendant. Height when ceiling mounted 15"
- etched white diffuser

**SL869263**

2 light flush mount in Painted Bronze
 14"W x 6"H
 2 lights x 60W Med.

- alabaster style glass



SL744263 

2 light bath bar in Painted Bronze
18"W x 10"H x 8"Ext.
2 lights x 100W Med.
• alabaster style glass



SL744363 

3 light bath bar in Painted Bronze
24"W x 10"H x 8"Ext.
3 lights x 100W Med.
• alabaster style glass



SL744463 

4 light bath bar in Painted Bronze
36"W x 10"H x 8"Ext.
4 lights x 100W Med.
• alabaster style glass



SL744563 

5 light bath bar in Painted Bronze
48"W x 10"H x 8"Ext.
5 lights x 100W Med.
• alabaster style glass



2009CH/10

9 light chandelier in Oil Rubbed Bronze
36"W x 33"H
9 lights x 60W Med.
94" Overall height
{12' wire} {60" chain}
• white glass



2005CH/10

5 light chandelier in Oil Rubbed Bronze
27"W x 24"H
5 lights x 60W Med.
85" Overall height
{12' wire} {60" chain}
• white glass



2003FM/10

3 light flush mount in Oil Rubbed Bronze
14"W x 6"H
3 lights x 60W Med.
• white glass



2003CH/10

3 light chandelier in Oil Rubbed Bronze
22"W x 19"H
5 lights x 60W Med.
80" Overall height
{12' wire} {60" chain}
• white glass





1305CH/20

5 light chandelier in Brushed Nickel

22"W x 23"H

5 lights x 60W Med.

84" Overall height

{12' wire} {60" chain}

- white glass



1303CH/20

3 light chandelier in Brushed Nickel

20"W x 13"H

3 lights x 60W Med.

74" Overall height

{12' wire} {60" chain}

- white glass



1301PL/20

1 light large pendant in Brushed Nickel

14"W x 18"H

1 light x 100W Med.

79" Overall height

{12' wire} {60" chain}

- white glass



1301PS/20

1 light mini pendant in Brushed Nickel

4"W x 6"H

1 light x 60W Med.

44" Overall height

- white glass



1301WS/20

- 1 light wall sconce in Brushed Nickel
 5"W x 8"H x 7"Ext.
 1 light x 60W Med.
 • white glass

**1302BB/20**

- 2 light bath bar in Brushed Nickel
 14"W x 9"H x 7"Ext.
 2 lights x 60W Med.
 • white glass

**1303BB/20**

- 3 light bath bar in Brushed Nickel
 22"W x 9"H x 7"Ext.
 3 lights x 60W Med.
 • white glass

**1304BB/20**

- 4 light bath bar in Brushed Nickel
 31"W x 9"H x 7"Ext.
 4 lights x 60W Med.
 • white glass



symbol denotes up or down mounting

1355CH/10

5 light chandelier in Oil Rubbed Bronze
22"W x 23"H
84" Overall height
{12' wire} {60" chain}
• white glass



1353CH/10

3 light chandelier in Oil Rubbed Bronze
20"W x 13"H
3 lights x 60W Med.
74" Overall height
{12' wire} {60" chain}
• white glass



1351PL/10

1 light large pendant in Oil Rubbed Bronze
14"W x 18"H
1 light x 100W Med.
79" Overall height
{12' wire} {60" chain}
• white glass



1351PS/10

1 light mini pendant in Oil Rubbed Bronze
4"W x 6"H
1 light x 60W Med.
44" Overall height
• white glass



1351WS/10 

1 light wall sconce in Oil Rubbed Bronze
5"W x 8"H x 7"Ext.
1 light x 60W Med.
• white glass



1352BB/10 

2 light bath bar in Oil Rubbed Bronze
14"W x 9"H x 7"Ext.
2 lights x 60W Med.
• white glass



1353BB/10 

3 light bath bar in Oil Rubbed Bronze
22"W x 9"H x 7"Ext.
3 lights x 60W Med.
• white glass



1354BB/10 

4 light bath bar in Oil Rubbed Bronze
31"W x 9"H x 7"Ext.
4 lights x 60W Med.
• white glass



190036117

9 light chandelier in Matte Nickel
 26"W x 24"H
 9 lights x 100W Med.
 72" Overall height
 {12' wire} {4' chain}

- etched swirl glass



190006117

5 light chandelier in Matte Nickel
 23"W x 20"H
 5 lights x 100W Med.
 68" Overall height
 {12' wire} {4' chain}

- etched swirl glass



190005117

3 light chandelier in Matte Nickel
 18"W x 14"H
 3 lights x 100W Med.
 63" Overall height
 {12' wire} {4' chain}

- etched swirl glass



190058117

3 light large pendant in Matte Nickel
 16"W x 21"H
 3 lights x 100W Med.
 69" Overall height
 {12' wire} {4' chain}

- etched swirl glass



190067117

2 light semi flush or pendant in Matte Nickel
 12"W x 12"H
 2 lights x 60W Med.
 {12' wire} {4' chain}

- etched swirl glass
- convertible semi-flush or chain hung pendant



alternate image

190056117

1 light mini pendant in Matte Nickel
 6"W x 6"H
 1 light x 100W Med.
 42" Overall height
 {12' wire} {2-12" + 2-6" rods}

- etched swirl glass



SL869278

- 2 light flush mount in Brushed Nickel
- 14"W x 6"H
- 2 lights x 60W Med.
- etched swirl glass



190016117

- 2 light bath bar in Matte Nickel
- 16"W x 9"H x 8"Ext.
- 2 lights x 100W Med.
- etched swirl glass



190017117

- 3 light bath bar in Matte Nickel
- 23"W x 9"H x 8"Ext.
- 3 lights x 100W Med.
- etched swirl glass



190018117

- 4 light bath bar in Matte Nickel
- 31"W x 9"H x 8"Ext.
- 4 lights x 100W Med.
- etched swirl glass



190036763

9 light chandelier in Painted Bronze
26"W x 24"H
9 lights x 100W Med.
72" Overall height
{12' wire} {4' chain}
• etched swirl glass



190006763

5 light chandelier in Painted Bronze
23"W x 20"H
5 lights x 100W Med.
68" Overall height
{12' wire} {4' chain}
• etched swirl glass



190058763

3 light large pendant in Painted Bronze
16"W x 21"H
3 lights x 100W Med.
69" Overall height
{12' wire} {4' chain}
• etched swirl glass



190005763

3 light chandelier in Painted Bronze
18"W x 14"H
3 lights x 100W Med.
63" Overall height
{12' wire} {4' chain}
• etched swirl glass



190067763

2 light semi flush or pendant in Painted Bronze
12"W x 12"H
2 lights x 60W Med.
{12' wire} {4' chain}
• etched swirl glass
• convertible semi-flush or chain hung pendant



alternate image

190056763

1 light mini pendant in Painted Bronze
6"W x 6"H
1 light x 100W Med.
42" Overall height
{12' wire} {2-12" + 2-6" rods}
• etched swirl glass



SL869263

2 light flush mount in Painted Bronze
14"W x 6"H
2 lights x 60W Med.
• etched swirl glass



190016763



2 light bath bar in Painted Bronze
16"W x 9"H x 8"Ext.
2 lights x 100W Med.
• etched swirl glass



190017763



3 light bath bar in Painted Bronze
23"W x 9"H x 8"Ext.
3 lights x 100W Med.
• etched swirl glass



190018763



4 light bath bar in Painted Bronze
31"W x 9"H x 8"Ext.
4 lights x 100W Med.
• etched swirl glass



symbol denotes up or down mounting

1209CH/20

9 light chandelier in Brushed Nickel
26"W x 29"H
9 lights x 60W Med.
89" Overall height
{12' wire} {60" chain}

- white glass



1203CH/20



3 light chandelier in Brushed Nickel
19"W x 18"H
3 lights x 60W Med.
79" Overall height
{12' wire} {60" chain}

- white glass



1205CH/20



5 light chandelier in Brushed Nickel
26"W x 21"H
5 lights x 60W Med.
82" Overall height
{12' wire} {60" chain}

- white glass



1203PL/20

3 light large pendant in Brushed Nickel
18"W x 25"H
3 lights x 100W Med.
86" Overall height
{12' wire} {60" chain}

- white glass



1201PS/20

1 light mini pendant in Brushed Nickel
8"W x 6"H
1 light x 100W Med.
44" Overall height

- white glass



1201PL/20

1 light large pendant in Brushed Nickel
15"W x 8"H
1 light x 100W Med.
69" Overall height
{12' wire} {60" chain}

- white glass



CONWAY

1201WS/20

- 1 light wall sconce in Brushed Nickel
 6"W x 9"H x 8"Ext.
 1 light x 100W Med.
 • white glass

**1202CS/20**

- 2 light convertible semi flush in Brushed Nickel
 15"W x 14"H
 2 lights x 100W Med.
 75" Overall height
 (12' wire) (60" chain)
 • white glass
 • convertible semi-flush or chain hung pendant



alternate image

1202BB/20

- 2 light bath bar in Brushed Nickel
 15"W x 9"H x 7"Ext.
 2 lights x 100W Med.
 • white glass

**1203BB/20**

- 3 light bath bar in Brushed Nickel
 23"W x 9"H x 7"Ext.
 3 lights x 100W Med.
 • white glass

**1204BB/20**

- 4 light bath bar in Brushed Nickel
 32"W x 9"H x 7"Ext.
 4 lights x 100W Med.
 • white glass



symbol denotes up or down mounting

1259CH/10

9 light chandelier in Oil Rubbed Bronze
26"W x 29"H
9 lights x 60W Med.
89" Overall height
{12' wire} {60" chain}

- white glass



1253CH/10



3 light chandelier in Oil Rubbed Bronze
19"W x 18"H
3 lights x 60W Med.
79" Overall height
{12' wire} {60" chain}

- white glass



1255CH/10



5 light chandelier in Oil Rubbed Bronze
26"W x 21"H
5 lights x 60W Med.
82" Overall height
{12' wire} {60" chain}

- white glass



1253PL/10

3 light large pendant in Oil Rubbed Bronze
18"W x 25"H
3 lights x 100W Med.
86" Overall height
{12' wire} {60" chain}

- white glass



1251PS/10

1 light mini pendant in Oil Rubbed Bronze
8"W x 6"H
1 light x 100W Med.
44" Overall height

- white glass



1221PL/10

1 light large pendant in Oil Rubbed Bronze
15"W x 8"H
1 light x 100W Med.
69" Overall height
{12' wire} {60" chain}

- white glass



CONWAY

1251WS/10

- 1 light wall sconce in Oil Rubbed Bronze
 6"W x 9"H x 8"Ext.
 1 light x 100W Med.
 • white glass

**1252CS/10**

- 2 light convertible semi flush in Oil Rubbed Bronze
 15"W x 14"H
 2 lights x 100W Med.
 75" Overall height
 (12' wire) (60" chain)
 • white glass
 • convertible semi-flush or chain hung pendant

**1252BB/10**

- 2 light bath bar in Oil Rubbed Bronze
 15"W x 9"H x 7"Ext.
 2 lights x 100W Med.
 • white glass

**1253BB/10**

- 3 light bath bar in Oil Rubbed Bronze
 23"W x 9"H x 7"Ext.
 3 lights x 100W Med.
 • white glass

**1254BB/10**

- 4 light bath bar in Oil Rubbed Bronze
 32"W x 9"H x 7"Ext.
 4 lights x 100W Med.
 • white glass



alternate image



symbol denotes up or down mounting

SL805278

9 light chandelier in Brushed Nickel
32"W x 29"H
9 lights x 60W Med.
77" Overall height
{12' wire} {4' chain}
• etched glass



SL891678

1 light pendant in Brushed Nickel
16"W x 18"H
1 light x 150W Med.
66" Overall height
{12' wire} {4' chain}
• etched glass



SL805178

5 light chandelier in Brushed Nickel
23"W x 20"H
5 lights x 100W Med.
68" Overall height
{12' wire} {4' chain}
• etched glass



SL891778

3 light pendant in Brushed Nickel
20"W x 25"H
3 lights x 100W Med.
72" Overall height
{12' wire} {4' chain}
• etched glass



TK0003217

3 light chandelier in Brushed Nickel
20"W x 12"H
3 lights x 100W Med.
60" Overall height
• etched glass



SL860778

3 light semi-flush or pendant in Brushed Nickel
16"W x 12"H
3 lights x 60W Med.
59" Overall height
{12' wire} {4' chain}
• etched glass
• convertible semi-flush or chain hung pendant



alternate image



SL891878

6 light pendant in Brushed Nickel
17"W x 32"H
6 lights x 60W Cand.
79" Overall height
{12' wire} {4' chain}

SL891578

1 light mini pendant in Brushed Nickel
8"W x 15"H
1 light x 100W Med.
63" Overall height
{12' wire} {4' chain}
• etched glass



SL878278

2 light flush mount in Brushed Nickel
14"W x 6"H
2 lights x 60W Med.
• etched glass



TN0003217



1 light wall sconce in Brushed Nickel
5"W x 9"H x 7"Ext.
1 lights x 100W Med.
• etched glass



SL714278



2 light bath bar in Brushed Nickel
13"W x 9"H x 7"Ext.
2 lights x 100W Med.
• etched glass



SL714378



3 light bath bar in Brushed Nickel
18"W x 9"H x 7"Ext.
3 lights x 100W Med.
• etched glass



SL714478



4 light bath bar in Brushed Nickel
25"W x 9"H x 7"Ext.
4 lights x 100W Med.
• etched glass




SL714578



5 light bath bar in Brushed Nickel
31"W x 9"H x 7"Ext.
5 lights x 100W Med.
• etched glass




 symbol denotes up or down mounting

SL805215

9 light chandelier in Oil Rubbed Bronze
 32"W x 29"H
 9 lights x 60W Med.
 77" Overall height
 {12' wire} {4' chain}
 • etched glass

**SL891615**

1 light pendant in Oil Rubbed Bronze
 16"W x 18"H
 1 light x 150W Med.
 66" Overall height
 {12' wire} {4' chain}
 • etched glass

**SL805115**

5 light chandelier in Oil Rubbed Bronze
 23"W x 20"H
 5 lights x 100W Med.
 68" Overall height
 {12' wire} {4' chain}
 • etched glass

**SL891715**

3 light pendant in Oil Rubbed Bronze
 20"W x 25"H
 3 lights x 100W Med.
 72" Overall height
 {12' wire} {4' chain}
 • etched glass

**TK0003715**

3 light chandelier in Oil Rubbed Bronze
 20"W x 12"H
 3 lights x 100W Med.
 60" Overall height
 • etched glass

**SL860715**

3 light semi-flush or pendant in Oil Rubbed Bronze
 16"W x 12"H
 3 lights x 60W Med.
 59" Overall height
 {12' wire} {4' chain}
 • etched glass
 • convertible semi-flush or chain hung pendant



alternate image

**SL891815**

6 light pendant in Oil Rubbed Bronze
 17"W x 32"H
 6 lights x 60W Cand.
 79" Overall height
 {12' wire} {4' chain}

SL891515

1 light mini pendant in Oil Rubbed Bronze
 8"W x 15"H
 1 light x 100W Med.
 63" Overall height
 {12' wire} {4' chain}
 • etched glass



BELLA

SL878215

2 light flush mount in Oil Rubbed Bronze
14"W x 6"H
2 lights x 60W Med.
• etched glass



TN0003715

1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 7"Ext.
1 lights x 100W Med.
• etched glass



SL714215

2 light bath bar in Oil Rubbed Bronze
13"W x 9"H x 7"Ext.
2 lights x 100W Med.
• etched glass



SL714315

3 light bath bar in Oil Rubbed Bronze
18"W x 9"H x 7"Ext.
3 lights x 100W Med.
• etched glass



SL714415

4 light bath bar in Oil Rubbed Bronze
25"W x 9"H x 7"Ext.
4 lights x 100W Med.
• etched glass



SL714515

5 light bath bar in Oil Rubbed Bronze
31"W x 9"H x 7"Ext.
5 lights x 100W Med.
• etched glass



 symbol denotes up or down mounting

SL808372

9 light chandelier in Moonlight Silver
 31"W x 33"H
 9 lights x 100W Med.
 81" Overall height
 {12' wire} {4' chain}
 • tea stained glass

**SL808272**

5 light chandelier in Moonlight Silver
 26"W x 26"H
 5 lights x 100W Med.
 74" Overall height
 {12' wire} {4' chain}
 • tea stained glass

**SL808172**

3 light chandelier in Moonlight Silver
 20"W x 23"H
 3 lights x 100W Med.
 70" Overall height
 {12' wire} {4' chain}
 • tea stained glass

**SL893572**

2 light pendant in Moonlight Silver
 19"W x 24"H
 2 lights x 100W Med.
 72" Overall height
 {12' wire} {4' chain}
 • tea stained glass

**SL861672**

2 light semi-flush in Moonlight Silver
 16"W x 12"H
 2 lights x 100W Med.
 • tea stained glass

**SL893672**

4 light pendant in Moonlight Silver
 18"W x 33"H
 4 lights x 60W Cand.
 81" Overall height
 {12' wire} {4' chain}

SL893472

1 light mini pendant in Moonlight Silver
 5"W x 12"H
 1 light x 100W Med.
 48" Overall height
 {12' wire} {2-12" + 2-6" rods}
 • tea stained glass



SL861572

2 light flush mount in Moonlight Silver
13"W x 7"H
2 lights x 60W Med.
• tea stained glass



SL717272

2 light bath bar in Moonlight Silver
12"W x 9"H x 9"Ext.
2 lights x 100W Med.
• tea stained glass



SL717372

3 light bath bar in Moonlight Silver
21"W x 9"H x 9"Ext.
3 lights x 100W Med.
• tea stained glass



SL717472


4 light bath bar in Moonlight Silver
29"W x 9"H x 9"Ext.
4 lights x 100W Med.
• tea stained glass



SL717572

5 light bath bar in Moonlight Silver
36"W x 9"H x 9"Ext.
5 lights x 100W Med.
• tea stained glass



 symbol denotes up or down mounting

SL808322

9 light chandelier in Sable Bronze
31"W x 33"H
9 lights x 100W Med.
81" Overall height
{12' wire} {4' chain}
• tea stained glass



SL808222

5 light chandelier in Sable Bronze
26"W x 26"H
5 lights x 100W Med.
74" Overall height
{12' wire} {4' chain}
• tea stained glass



SL808122

3 light chandelier in Sable Bronze
20"W x 23"H
3 lights x 100W Med.
70" Overall height
{12' wire} {4' chain}
• tea stained glass



SL893522

2 light pendant in Sable Bronze
19"W x 24"H
2 lights x 100W Med.
72" Overall height
{12' wire} {4' chain}
• tea stained glass



SL861622

2 light semi-flush in Sable Bronze
16"W x 12"H
2 lights x 100W Med.
• tea stained glass



SL893622

4 light pendant in Sable Bronze
18"W x 33"H
4 lights x 60W Cand.
81" Overall height
{12' wire} {4' chain}

SL893422

1 light mini pendant in Sable Bronze
5"W x 12"H
1 light x 100W Med.
48" Overall height
{12' wire} {2-12" + 2-6" rods}
• tea stained glass



SL861522

2 light flush mount in Sable Bronze
13"W x 7"H
2 lights x 60W Med.
• tea stained glass



SL717222

2 light bath bar in Sable Bronze
12"W x 9"H x 9"Ext.
2 lights x 100W Med.
• tea stained glass



SL717322

3 light bath bar in Sable Bronze
21"W x 9"H x 9"Ext.
3 lights x 100W Med.
• tea stained glass



SL717422

4 light bath bar in Sable Bronze
29"W x 9"H x 9"Ext.
4 lights x 100W Med.
• tea stained glass



SL717522

5 light bath bar in Sable Bronzer
36"W x 9"H x 9"Ext.
5 lights x 100W Med.
• tea stained glass



2115CH/20

15 light chandelier in Brushed Nickel
45"W x 37"H
15 lights x 60W Med.
98" Overall height
{12' wire} {60" chain}
• white glass



2109CH/20

9 light chandelier in Brushed Nickel
32"W x 25"H
9 lights x 60W Med.
86" Overall height
{12' wire} {60" chain}
• white glass



2105CH/20

5 light chandelier in Brushed Nickel
27"W x 22"H
5 lights x 100W Med.
83" Overall height
{12' wire} {60" chain}
• white glass



2103SF/20

3 light semi-flush in Brushed Nickel
17"W x 12"H
3 lights x 60W Med.
• white glass



2103FM/20

3 light flush mount in Brushed Nickel
17"W x 6"H
3 lights x 60W Med.
• white glass



2101WS/20

1 light wall sconce in Brushed Nickel
7"W x 10"H x 10"Ext.
1 light x 100W Med.
• white glass

2101PS/20

1 light mini pendant in Brushed Nickel
7"W x 43"H
1 light x 100W Med.
43" Overall length
• white glass



2103CH/20

3 light chandelier in Brushed Nickel
23"W x 20"H
3 lights x 100W Med.
81" Overall height
{12' wire} {60" chain}
• white glass



BRISTOL LANE

2115CH/10

15 light chandelier in Oil Rubbed Bronze
 45"W x 37"H
 15 lights x 60W Med.
 98" Overall height
 {12' wire} {60" chain}

- white glass

**2109CH/10**

9 light chandelier in Oil Rubbed Bronze
 32"W x 25"H
 9 lights x 60W Med.
 86" Overall height
 {12' wire} {60" chain}

- white glass

**2105CH/10**

5 light chandelier in Oil Rubbed Bronze
 27"W x 22"H
 5 lights x 100W Med.
 83" Overall height
 {12' wire} {60" chain}

- white glass

**2103CH/10**

3 light chandelier in Oil Rubbed Bronze
 23"W x 20"H
 3 lights x 100W Med.
 81" Overall height
 {12' wire} {60" chain}

- white glass

**2103SF/10**

3 light semi-flush in Oil Rubbed Bronze
 17"W x 12"H
 3 lights x 60W Med.

- white glass

**2101WS/10**

1 light wall sconce in Oil Rubbed Bronze
 6"W x 10"H x 10"Ext.
 1 light x 100W Med.

- white glass

**2103FM/10**

3 light flush mount in Oil Rubbed Bronze
 17"W x 6"H
 3 lights x 60W Med.

- white glass

**2101PS/10**

1 light mini pendant in Oil Rubbed Bronze
 7"W x 43"H
 1 light x 100W Med.

- white glass

**BRISTOL LANE**

SL801678

9 light chandelier in Brushed Nickel
 30"W x 29"H
 9 lights x 60W Med.
 101" Overall height
 {12' wire} {60" chain}

- alabaster style glass

**SL801578**

5 light chandelier in Brushed Nickel
 24"W x 17"H
 5 lights x 100W Med.
 65" Overall height
 {12' wire} {4' chain}

- alabaster style glass

**SL823678**

3 light pendant in Brushed Nickel
 20"W x 28"H
 3 lights x 100W Med.
 100" Overall height
 {12' wire} {60" chain}

- alabaster style glass
- etched white diffuser

**SL801478**

3 light chandelier in Brushed Nickel
 19"W x 17"H
 3 lights x 100W Med.
 65" Overall height
 {12' wire} {4' chain}

- alabaster style glass

**SL861478**

2 light semi flush or pendant in Brushed Nickel
 12"W x 11"H
 2 lights x 100W Med.
 {12' wire} {4' chain}

- alabaster style glass
- convertible semi-flush or chain hung pendant



alternate image

SL823478

1 light pendant in Brushed Nickel
 12"W x 9"H
 1 light x 150W Med.
 57" Overall height
 {12' wire} {4' chain}

- alabaster style glass



SL758278

2 light bath bar in Brushed Nickel
 18"W x 9"H x 8"Ext.
 2 lights x 100W Med.
 • alabaster style glass

**SL869278**

2 light flush mount in Brushed Nickel
 14"W x 6"H
 2 lights x 60W Med.
 • etched alabaster style glass

**SL758378**

3 light bath bar in Brushed Nickel
 24"W x 9"H x 8"Ext.
 3 lights x 100W Med."
 • alabaster style glass

**SL758478**

4 light bath bar in Brushed Nickel
 30"W x 9"H x 8"Ext.
 4 lights x 100W Med.
 • alabaster style glass

**SL758578**

5 light bath bar in Brushed Nickel
 36"W x 9"H x 8"Ext.
 5 lights x 100W Med.
 • alabaster style glass

**SL758678**

6 light bath bar in Brushed Nickel
 48"W x 9"H x 8"Ext.
 6 lights x 100W Med.
 • alabaster style glass



symbol denotes up or down mounting

SL801663

9 light chandelier in Painted Bronze
30"W x 29"H
9 lights x 60W Med.
101" Overall height
{12' wire} {60" chain}
• alabaster style glass



SL801563

5 light chandelier in Painted Bronze
24"W x 17"H
5 lights x 100W Med.
65" Overall height
{12' wire} {4' chain}
• alabaster style glass



SL823663

3 light pendant in Painted Bronze
20"W x 28"H
3 lights x 100W Med.
100" Overall height
{12' wire} {60" chain}
• alabaster style glass
• etched white diffuser



SL801463

3 light chandelier in Painted Bronze
19"W x 17"H
3 lights x 100W Med.
65" Overall height
{12' wire} {4' chain}
• alabaster style glass



alternate image

SL861463

2 light semi flush or pendant in Painted Bronze
12"W x 11"H
2 lights x 100W Med.
{12' wire} {4' chain}
• alabaster style glass
• convertible semi-flush or chain hung pendant



SL823463

1 light mini pendant in Painted Bronze
12"W x 9"H
1 light x 150W Med.
57" Overall height
{12' wire} {4' chain}
• alabaster style glass



SL758263

2 light bath bar in Painted Bronze
 18"W x 9"H x 8"Ext.
 2 lights x 100W Med.
 • alabaster style glass

**SL869263**

2 light flush mount in Painted Bronze
 14"W x 6"H
 2 lights x 60W Med.
 • etched alabaster style glass

**SL758363**

3 light bath bar in Painted Bronze
 24"W x 9"H x 8"Ext.
 3 lights x 100W Med."
 • alabaster style glass

**SL758463**

4 light bath bar in Painted Bronze
 30"W x 9"H x 8"Ext.
 4 lights x 100W Med.
 • alabaster style glass

**SL758563**

5 light bath bar in Painted Bronze
 36"W x 9"H x 8"Ext.
 5 lights x 100W Med.
 • alabaster style glass

**SL758663**

6 light bath bar in Painted Bronze
 48"W x 9"H x 8"Ext.
 6 lights x 100W Med.
 • alabaster style glass



symbol denotes up or down mounting

CN230927

9 light chandelier in Weathered Zinc
 36"W x 35"H
 9 lights x 100W Med. *Shown with Lamp 1102
 96" Overall height
 {12' wire} {60" chain}

- mercury glass

*Lamp not included--See page 7



CN230527

5 light chandelier in Weathered Zinc
 27"W x 27"H
 5 lights x 100W Med. *Shown with Lamp 1102
 88" Overall height
 {12' wire} {60" chain}

- mercury glass

*Lamp not included--See page 7



CN230157

1 light mini pendant in Weathered Zinc
 6"W x 8"H
 1 light x 100W Med. *Shown with Lamp 1102
 61" Overall height
 {12' wire} {60" chain}

- mercury glass

*Lamp not included--See page 7



CN230327

3 light chandelier in Weathered Zinc
 23"W x 25"H
 3 lights x 100W Med. *Shown with Lamp 1102
 86" Overall height
 {12' wire} {60" chain}

- mercury glass

*Lamp not included--See page 7



CN230387

3 light semi flush in Weathered Zinc
 19"W x 16"H
 3 lights x 100W Med. *Shown with Lamp 1102
 • mercury glass

*Lamp not included--See page 7



CN230237

2 light flush mount in Weathered Zinc
 16"W x 9"H
 2 lights x 60W Med. *Shown with Lamp 1102
 • mercury glass

*Lamp not included--See page 7



CN230177

1 light wall sconce in Weathered Zinc
 6"W x 12"H x 8" Ext.
 1 light x 60W Med. *Shown with Lamp 1102
 • mercury glass
 *Lamp not included--See page 7

**CN230217**

2 light bath bar in Weathered Zinc
 16"W x 11"H x 7" Ext.
 2 lights x 60W Med. *Shown with Lamp 1102
 • mercury glass
 *Lamp not included--See page 7

**CN230317**

3 light bath bar in Weathered Zinc
 24"W x 12"H x 7"Ext.
 3 lights x 60W Med. *Shown with Lamp 1102
 • mercury glass
 *Lamp not included--See page 7

**CN230417**

4 light bath bar in Weathered Zinc
 33"W x 13"H x 7"Ext.
 4 lights x 60W Med. *Shown with Lamp 1102
 • mercury glass
 *Lamp not included--See page 7



symbol denotes up or down mounting

SL880241

9 light chandelier in Satin Pewter
 31"W x 32"H
 9 lights x 60W Med.
 104" Overall height
 {12' wire} {60" chain}

- white marble glass

**SL880141**

5 light chandelier in Satin Pewter
 26"W x 24"H
 5 lights x 100W Med.
 96" Overall height
 {12' wire} {60" chain}

- white marble glass

**SL880341**

3 light chandelier in Satin Pewter
 20"W x 21"H
 3 lights x 100W Med.
 69" Overall height
 {12' wire} {4' chain}

- white marble glass

**SL824641**

3 light pendant in Satin Pewter
 21"W x 25"H
 3 lights x 100W Med.
 97" Overall height
 {12' wire} {60" chain}

- white marble glass

**SL866241**

2 light semi-flush in Satin Pewter
 16"W x 13"H
 2 lights x 100W Med.

- white marble glass

**SL825641**

1 light mini pendant in Satin Pewter
 7"W x 8"H
 1 light x 100W Med.
 44" Overall height
 {12' wire} {2-12" + 2-6" rods}

- white marble glass



HARMONY

SL869278

- 2 light flush mount in Brushed Nickel
14"W x 6"H
2 lights x 60W Med.
• etched alabaster style glass



SL760241

- 2 light bath bar in Satin Pewter
16"W x 8"H x 7"Ext.
2 lights x 100W Med.
• white marble glass



SL760341

- 3 light bath bar in Satin Pewter
24"W x 8"H x 7"Ext.
3 lights x 100W Med.
• white marble glass



SL760441

- 4 light bath bar in Satin Pewter
32"W x 8"H x 7"Ext.
4 lights x 100W Med.
• white marble glass



symbol denotes up or down mounting

SL880262

9 light chandelier in Aged Bronze
31"W x 32"H
9 lights x 60W Med.
104" Overall height
{12' wire} {60" chain}
• champagne marble glass



SL880162

5 light chandelier in Aged Bronze
26"W x 24"H
5 lights x 100W Med.
96" Overall height
{12' wire} {60" chain}
• champagne marble glass



SL824662

3 light pendant in Aged Bronze
21"W x 25"H
3 lights x 100W Med.
97" Overall height
{12' wire} {60" chain}
• champagne marble glass



SL880362

3 light chandelier in Aged Bronze
20"W x 21"H
3 lights x 100W Med.
69" Overall height
{12' wire} {4' chain}
• champagne marble glass



SL866262

2 light semi flush in Aged Bronze
16"W x 13"H
2 lights x 100W Med.
• champagne marble glass



SL825662

1 light mini pendant in Aged Bronze
7"W x 8"H
1 light x 100W Med.
44" Overall height
{12' wire} {2-12" + 2-6" rods}
• champagne marble glass



HARMONY

SL877263

2 light flush mount in Painted Bronze
14"W x 6"H
2 lights x 60W Med.
• golden cream swirl glass



SL760262 

2 light bath bar in Aged Bronze
16"W x 8"H x 7"Ext.
2 lights x 100W Med.
• champagne marble glass



SL760362 

3 light bath bar in Aged Bronze
24"W x 8"H x 7"
3 lights x 100W Med.
• champagne marble glass



SL760462 

4 light bath bar in Aged Bronze
32"W x 8"H x 7"Ext.
4 lights x 100W Med.
• champagne marble glass



1009CH/20

9 light chandelier in Brushed Nickel
25"W x 29"H
9 lights x 60W Med.
83" Overall height
{12' wire} {60" chain}
• white glass



1005CH/20

5 light chandelier in Brushed Nickel
22"W x 25"H
5 lights x 75W Med.
86" Overall height
{12' wire} {60" chain}
• white glass



1003CH/20

3 light chandelier in Brushed Nickel
20"W x 24"H
3 lights x 75W Med.
85" Overall height
{12' wire} {60" chain}
• white glass



1003IS/20

3 light island pendant in Brushed Nickel
18"W x 37"H
3 lights x 100W Med.
44" Overall height
• white glass



1103FM/20

3 light flush mount in Brushed Nickel
13"W x 6"H
3 lights x 60W Med.
• white glass



1002CS/20

2 light convertible in Brushed Nickel
16"W x 13"H
2 lights x 60W Med.
74" Overall height
{12' wire} {60" chain}
• white glass



alternate image

1001WS/20



1 light wall sconce in Brushed Nickel
6"W x 11"H x 8"Ext.
1 light x 75W Med.
• white glass



1002BB/20



2 light bath bar in Brushed Nickel
15"W x 11"H x 7"Ext.
2 lights x 75W Med.
• white glass



1001PS/20

1 light mini pendant in Brushed Nickel
6"W x 6"H
1 light x 75W Med.
44" Overall height
• white glass



1003BB/20



3 light bath bar in Brushed Nickel
24"W x 11"H x 7"Ext.
3 lights x 75W Med.
• white glass



1004BB/20



4 light bath bar in Brushed Nickel
33"W x 11"H x 7"Ext.
4 lights x 75W Med.
• white glass



symbol denotes up or down mounting

1059CH/10

9 light chandelier in Oil Rubbed Bronze
25"W x 29"H
9 lights x 60W Med.
83" Overall length
{12' wire} {60" chain}
• white glass



1055CH/10

5 light chandelier in Oil Rubbed Bronze
22"W x 25"H
5 lights x 75W Med.
86" Overall length
{12' wire} {60" chain}
• white glass



1053CH/10

3 light chandelier in Oil Rubbed Bronze
20"W x 24"H
3 lights x 75W Med.
85" Overall length
{12' wire} {60" chain}
• white glass



1053PL/10

3 light large pendant in Oil Rubbed Bronze
13"W x 6"H
3 lights x 60W Med.
83" Overall length
{12' wire} {60" chain}
• white glass



1051PS/10

1 light mini pendant in Oil Rubbed Bronze
6"W x 6"H
1 light x 75W Med.
44" Overall height
• white glass



1053IS/10

3 light island pendant in Oil Rubbed Bronze
18"W x 37"H
3 lights x 100W Med.
44" Overall length
• white glass



1153FM/10

3 light flush mount in Oil Rubbed Bronze
 13"W x 6"H
 3 lights x 60W Med.
 • white glass

**1052CS/10**

2 light convertible in Oil Rubbed Bronze
 16"W x 13"H
 2 lights x 60W Med.
 74" Overall length
 (12' wire) (60" chain)
 • white glass



alternate image

1051WS/10 

1 light wall sconce in Oil Rubbed Bronze
 6"W x 11"H x 8"Ext.
 1 light x 75W Med.
 • white glass

**1052BB/10** 

2 light bath bar in Oil Rubbed Bronze
 15"W x 11"H x 7"Ext.
 2 lights x 75W Med.
 • white glass

**1053BB/10** 

3 light bath bar in Oil Rubbed Bronze
 24"W x 11"H x 7"Ext.
 3 lights x 75W Med.
 • white glass

**1054BB/10** 

4 light bath bar in Oil Rubbed Bronze
 33"W x 11"H x 7"Ext.
 4 lights x 75W Med.
 • white glass



SL881378

9 light chandelier in Brushed Nickel
 32"W x 27"H
 9 lights x 60W Med.
 99" Overall height
 {12' wire} {60" chain}

- reeded center column
- alabaster style glass

**SL881178**

5 light chandelier in Brushed Nickel
 25"W x 23"H
 5 lights x 100W Med.
 71" Overall height
 {12' wire} {4' chain}

- reeded center column
- alabaster style glass

**SL881278**

3 light chandelier in Brushed Nickel
 19"W x 14"H
 3 lights x 100W Med.
 62" Overall height
 {12' wire} {4' chain}

- reeded center column
- alabaster style glass

**SL826678**

3 light pendant in Brushed Nickel
 16"W x 19"H
 3 lights x 100W Med.
 67" Overall height
 {12' wire} {4' chain}

- reeded center column
- alabaster style glass

**SL869678**

3 light semi flush in Brushed Nickel
 16"W x 12"H
 3 lights x 100W Med.

- alabaster style glass

**SL869278**

2 light flush mount in Brushed Nickel
 14"W x 6"H
 2 lights x 60W Med.

- alabaster style glass

**SL820678**

1 light mini pendant in Brushed Nickel
 6"W x 21"H
 1 light x 100W Med.
 69" Overall height
 {12' wire} {4' chain}

- reeded center column
- alabaster style glass



SL758278 

2 light bath bar in Brushed Nickel
18"W x 9"H x 8"Ext.
2 lights x 100W Med.
• alabaster style glass



SL758378 

3 light bath bar in Brushed Nickel
24"W x 9"H x 8"Ext.
3 lights x 100W Med.
• alabaster style glass



SL758478 

4 light bath bar in Brushed Nickel
30"W x 9"H x 8"Ext.
4 lights x 100W Med.
• alabaster style glass



SL758578 


5 light bath bar in Brushed Nickel
36"W x 9"H x 8"Ext.
5 lights x 100W Med.
• alabaster style glass



SL758678 

6 light bath bar in Brushed Nickel
48"W x 9"H x 8"Ext.
6 lights x 100W Med.
• alabaster style glass



 symbol denotes up or down mounting

SL881363

9 light chandelier in Painted Bronze
 32"W x 27"H
 9 lights x 60W Med.
 99" Overall height
 {12' wire} {60" chain}

- reeded center column
- alabaster style glass

**SL881163**

5 light chandelier in Painted Bronze
 25"W x 23"H
 5 lights x 100W Med.
 71" Overall height
 {12' wire} {4' chain}

- reeded center column
- alabaster style glass

**SL881263**

3 light chandelier in Painted Bronze
 19"W x 14"H
 3 lights x 100W Med.
 62" Overall height
 {12' wire} {4' chain}

- reeded center column
- alabaster style glass

**SL826663**

3 light pendant in Painted Bronze
 16"W x 19"H
 3 lights x 100W Med.
 67" Overall height
 {12' wire} {4' chain}

- reeded center column
- alabaster style glass

**SL869663**

3 light semi flush or pendant in Painted Bronze
 16"W x 12"H
 3 lights x 100W Med.

- alabaster style glass

**SL869263**

2 light flush mount in Painted Bronze
 14"W x 6"H
 2 lights x 60W Med.

- alabaster style glass

**SL820663**

1 light mini pendant in Painted Bronze
 6"W x 21"H
 1 light x 100W Med.
 69" Overall height
 {12' wire} {4' chain}

- reeded center column
- alabaster style glass



SL758263 

2 light bath bar in Painted Bronze
18"W x 9"H x 8"Ext.
2 lights x 100W Med.
• alabaster style glass



SL758363 

3 light bath bar in Painted Bronze
24"W x 9"H x 8"Ext.
3 lights x 100W Med.
• alabaster style glass



SL758463 

4 light bath bar in Painted Bronze
30"W x 9"H x 8"Ext.
4 lights x 100W Med.
• alabaster style glass



SL758563 


5 light bath bar in Painted Bronze
36"W x 9"H x 8"Ext.
5 lights x 100W Med.
• alabaster style glass



SL758663 

6 light bath bar in Painted Bronze
48"W x 9"H x 8"Ext.
6 lights x 100W Med.
• alabaster style glass



 symbol denotes up or down mounting

SL863978

9 light chandelier in Brushed Nickel
34"W x 32"H
9 lights x 60W Med.
104" Overall height
{12' wire} {60" chain}
• alabaster style glass



SL863678

6 light chandelier in Brushed Nickel
30"W x 26"H
6 lights x 100W Med.
98" Overall height
{12' wire} {60" chain}
• alabaster style glass



SL863378

3 light chandelier in Brushed Nickel
27"W x 21"H
3 lights x 100W Med.
93" Overall height
{12' wire} {60" chain}
• alabaster style glass



SL829278

3 light pendant in Brushed Nickel
18"W x 23"H
3 lights x 100W Med.
95" Overall height
{12' wire} {60" chain}
• alabaster style glass



SL842078

2 light semi flush in Brushed Nickel
15"W x 14"H
2 lights x 100W Med.
• alabaster style glass




SL869278

2 light flush in Brushed Nickel
14"W x 6"H
2 lights x 60W Med.
• etched alabaster style glass

SL829678

1 light mini pendant in Brushed Nickel
10"W x 6"H
1 light x 100W Med.
42" Overall height
{12' wire} {2-12" + 2-6" rods}
• alabaster style glass



PRESTIGE

SL748278 

2 light bath bar in Brushed Nickel
17"W x 9"H x 9"Ext.
2 lights x 100W Med.
• alabaster style glass



SL748378 

3 light bath bar in Brushed Nickel
27"W x 9"H x 9"Ext.
3 lights x 100W Med.
• alabaster style glass



SL748478 

4 light bath bar in Brushed Nickel
36"W x 9"H x 9"Ext.
4 lights x 100W Med.
• alabaster style glass



SL748578 

5 light bath bar in Brushed Nickel
46"W x 9"H x 9"Ext.
5 lights x 100W Med.
• alabaster style glass



SL748678 

6 light bath bar in Brushed Nickel
55"W x 10"H x 9"Ext.
6 lights x 100W Med.
• alabaster style glass



TK0023217

15 light chandelier in Brushed Nickel
48"W x 45"H
15 lights x 40W Med.
117" Overall height
{12' wire} {60" chain}
• alabaster style glass



TK0022217

5 light chandelier in Brushed Nickel
24"W x 21"H
5 lights x 100W Med.
93" Overall height
{12' wire} {60" chain}
• alabaster style glass



SL854178 

1 light wall sconce in Brushed Nickel
8"W x 9"H x 10"Ext.
1 light x 100W Med.
• alabaster style glass



TC0023217

4 light pendant in Brushed Nickel
17"W x 28"H
4 lights x 60W Cand.
100" Overall height
{12' wire} {60" chain}



TK0023722

15 light chandelier in Sable Bronze
48"W x 45"H
15 lights x 40W Med.
117" Overall height
{12' wire} {60" chain}
• cognac edged glass



TK0022722

5 light chandelier in Sable Bronze
24"W x 21"H
5 lights x 100W Med.
93" Overall height
{12' wire} {60" chain}
• cognac edged glass



SL854122 


1 light wall sconce in Sable Bronze
8"W x 9"H x 10"Ext.
1 light x 100W Med.
• cognac edged glass



TC0023722

4 light pendant in Sable Bronze
17"W x 28"H
4 lights x 60W Cand.
100" Overall height
{12' wire} {60" chain}



 symbol denotes up or down mounting

PRESTIGE

SL863922

9 light chandelier in Sable Bronze
34"W x 32"H
9 lights x 60W Med.
104" Overall height
{12' wire} {60" chain}
• cognac edged glass



SL863622

6 light chandelier in Sable Bronze
30"W x 26"H
6 lights x 100W Med.
98" Overall height
{12' wire} {60" chain}
• cognac edged glass



SL863322

3 light chandelier Sable Bronze
27"W x 21"H
3 lights x 100W Med.
93" Overall height
{12' wire} {60" chain}
• cognac edged glass



SL829222

3 light pendant in Sable Bronze
18"W x 23"H
3 lights x 100W Med.
95" Overall height
{12' wire} {60" chain}
• cognac edged glass



SL842022

2 light semi-flush in Sable Bronze
15"W x 14"H
2 lights x 100W Med.
• cognac edged glass



SL877263

2 light flush in Painted Bronze
14"W x 6"H
2 lights x 60W Med.
• golden cream swirl glass

SL829822

1 light mini pendant in Sable Bronze
10"W x 6"H
1 light x 100W Med.
42" Overall height
{12' wire} {2-12" + 2-6" rods}
• cognac edged glass



PRESTIGE

SL748222 

2 light bath in Sable Bronze
17"W x 9"H x 9"Ext.
2 lights x 100W Med.
• cognac edged glass



SL748322 

3 light bath bar in Sable Bronze
27"W x 9"H x 9"Ext.
3 lights x 100W Med.
• cognac edged glass



SL748422 

4 light bath bar in Sable Bronze
36"W x 9"H x 9"Ext.
4 lights x 100W Med.
• cognac edged glass



SL748522 


5 light bath bar in Sable Bronze
46"W x 9"H x 9"Ext.
5 lights x 100W Med.
• cognac edged glass



SL748622 

6 light bath bar in Sable Bronze
55"W x 10"H x 9"Ext.
6 lights x 100W Med.
• cognac edged glass



 symbol denotes up or down mounting

SL801078

5 light chandelier in Brushed Nickel
24"W x 13"H
5 lights x 100W Med.
60" Overall height
{12' wire} {4' chain}
• etched glass



SL800378

5 light chandelier in Brushed Nickel
19"W x 16"H
5 lights x 60W Cand.
64" Overall height
{12' wire} {4' chain}




M255078

1 light pendant in Brushed Nickel
16"W x 17"H
1 light x 150W Med.
65" Overall height
{12' wire} {4' chain}
• alabaster style glass



SL801178

3 light chandelier in Brushed Nickel
21"W x 13"H
3 lights x 100W Med.
60" Overall height
{12' wire} {4' chain}
• etched glass



SL847978

2 light pendant in Brushed Nickel
8"W x 12"H
2 lights x 60W Cand.
60" Overall height
{12' wire} {4' chain}



SL823578

1 light pendant in Brushed Nickel
16"W x 13"H
1 light x 150W Med.
61" Overall height
{12' wire} {4' chain}
• etched glass



SL861078

2 light convertible semi flush in Brushed Nickel
16"W x 13"H
2 lights x 100W Med.
62" Overall height
{12' wire} {4' chain}

- etched glass
- convertible semi-flush or chain hung pendant.
Height when ceiling mounted 13"



SL878278

2 light flush mount in Brushed Nickel
14"W x 6"H
2 lights x 60W Med.
• etched glass

SL710341

3 light bath bar in Satin Pewter
24"W x 9"H x 8"Ext.
3 lights x 100W Med.
• etched glass



SL710441

4 light bath bar in Satin Pewter
30"W x 9"H x 8"Ext.
4 lights x 100W Med.
• etched glass



 symbol denotes up or down mounting

TK0021217

9 light chandelier in Brushed Nickel
 30"W x 28"H
 9 lights x 100W Med.
 76" Overall height
 {12' wire} {4' chain}

- etched white glass

**TK0020217**

5 light chandelier in Brushed Nickel
 25"W x 23"H
 5 lights x 100W Med.
 71" Overall height
 {12' wire} {4' chain}

- etched white glass

**TK0019217**

3 light chandelier in Brushed Nickel
 20"W x 21"H
 3 lights x 100W Med.
 69" Overall height
 {12' wire} {4' chain}

- etched white glass

**TC0021217**

3 light pendant in Brushed Nickel
 20"W x 24"H
 3 lights x 100W Med.
 72" Overall height
 {12' wire} {4' chain}

- etched white glass

**TC0020217**

2 light semi flush in Brushed Nickel
 13"W x 12"H
 2 lights x 60W Med.
 • etched white glass

**TC0022217**

1 light pendant in Brushed Nickel
 13"W x 8"H
 1 light x 100W Med.
 56" Overall height
 {12' wire} {4' chain}

- etched white glass

**TC0019217**

1 light mini pendant in Brushed Nickel
 5"W x 7"H
 1 light x 100W Med.
 43" Overall height
 {12' wire} {3' chain}

- etched white glass



TN0010217

1 light wall sconce in Brushed Nickel
 5"W x 12"H x 8"Ext.
 1 light x 100W Med.
 • etched white glass

**TV0019217**

2 light bath bar in Brushed Nickel
 14"W x 7"H x 7"Ext.
 2 lights x 100W Med.
 • etched white glass

**TV0020217**

3 light bath bar in Brushed Nickel
 23"W x 7"H x 7"Ext.
 3 lights x 100W Med.
 • etched white glass

**TV0021217**

4 light bath bar in Brushed Nickel
 32"W x 7"H x 7"Ext.
 4 lights x 100W Med.
 • etched white glass

**TV0022217**

5 light bath bar in Brushed Nickel
 41"W x 7"H x 7"Ext.
 5 lights x 100W Med.
 • etched white glass



symbol denotes up or down mounting

TK0021704

9 light chandelier in Espresso
 30"W x 28"H
 9 lights x 100W Med.
 76" Overall height
 {12' wire} {4' chain}

- champagne glass

**TK0020704**

5 light chandelier in Espresso
 25"W x 23"H
 5 lights x 100W Med.
 71" Overall height
 {12' wire} {4' chain}

- champagne glass

**TK0019704**

3 light chandelier in Espresso
 20"W x 21"H
 3 lights x 100W Med.
 69" Overall height
 {12' wire} {4' chain}

- champagne glass

**TC0021704**

3 light pendant in Espresso
 20"W x 24"H
 3 lights x 100W Med.
 72" Overall height
 {12' wire} {4' chain}

- champagne glass

**TC0020704**

2 light semi flush in Espresso
 13"W x 12"H
 2 lights x 60W Med.
 • champagne glass

**TC0022704**

1 light pendant in Espresso
 13"W x 8"H
 1 light x 100W Med.
 56" Overall height
 {12' wire} {4' chain}

- champagne glass

**TC0019704**

1 light mini pendant in Espresso
 5"W x 7"H
 1 light x 100W Med.
 43" Overall height
 {12' wire} {3' chain}

- champagne glass



TN0010704 ↑↓

1 light wall sconce in Espresso
5"W x 12"H x 8"Ext.
1 light x 100W Med.
• champagne glass



TV0019704 ↑↓

2 light bath bar in Espresso
14"W x 7"H x 7"Ext.
2 lights x 100W Med.
• champagne glass



TV0020704 ↑↓

3 light bath bar in Espresso
23"W x 7"H x 7"Ext.
3 lights x 100W Med.
• champagne glass



TV0021704 ↑↓

4 light bath bar in Espresso
32"W x 7"H x 7"Ext.
4 lights x 100W Med.
• champagne glass



TV0022704 ↑↓

5 light bath bar in Espresso
41"W x 7"H x 7"Ext.
5 lights x 100W Med.
• champagne glass



TK0018741

9 light chandelier in Satin Pewter
 29"W x 29"H
 9 lights x 60W Med.
 51" Overall height
 {12' wire} {4' chain}

- etched glass

**TK0017741**


5 lights chandelier in Satin Pewter
 24"W x 23"H
 5 lights x 100W Med.
 51" Overall height
 {12' wire} {4' chain}

- etched glass

**TK0016741**

3 light chandelier in Satin Pewter
 19"W x 23"H
 3 lights x 100W Med.
 51" Overall height
 {12' wire} {4' chain}

- etched glass

**TC0018741**

1 light pendant in Satin Pewter
 14"W x 9"H
 1 light x 100W Med.
 57" Overall height
 {12' wire} {4' chain}

- etched glass

**TC0015741**

2 light semi flush in Satin Pewter
 16"W x 14"H
 2 lights x 60W Med.
 • etched glass

**TC0017741**

5 light pendant in Satin Pewter
 14"W x 26"H
 5 lights x 60W Cand.
 74" Overall height
 {12' wire} {4' chain}

TC0016741

3 light pendant in Satin Pewter
 17"W x 24"H
 3 lights x 100W Med.
 72" Overall height
 {12' wire} {4' chain}

- etched glass



TN0009741 

1 light wall sconce in Satin Pewter
5"W x 14"H x 6"Ext.
1 light x 100W Med.
• etched glass



TC0014741

1 light mini pendant in Satin Pewter
5"W x 8"H
1 light x 100W Med.
44" Overall height
{12' wire} {3' chain}
• etched glass



TV0015741 

2 light bath bar in Satin Pewter
18"W x 11"H x 7"Ext.
2 lights x 100W Med.
• etched glass



TV0016741 

3 light bath bar in Satin Pewter
24"W x 11"H x 7"Ext.
3 lights x 100W Med.
• etched glass



TV0017741 

4 light bath bar in Satin Pewter
30"W x 11"H x 7"Ext.
4 lights x 100W Med.
• etched glass



TV0018741 

5 light bath bar in Satin Pewter
36"W x 11"H x 7"Ext.
5 lights x 100W Med.
• etched glass



TK0018704

9 light chandelier in Espresso
 29"W x 29"H
 9 lights x 60W Med.
 51" Overall height
 {12' wire} {4' chain}

- etched glass

**TK0017704**

5 lights chandelier in Espresso
 24"W x 23"H
 5 lights x 100W Med.
 51" Overall height
 {12' wire} {4' chain}

- etched glass

**TK0016704**

3 light chandelier in Espresso
 19"W x 23"H
 3 lights x 100W Med.
 51" Overall height
 {12' wire} {4' chain}

- etched glass

**TC0018704**

1 light pendant in Espresso
 14"W x 9"H
 1 light x 100W Med.
 57" Overall height
 {12' wire} {4' chain}

- etched glass

**TC0015704**

2 light semi flush in Espresso
 16"W x 14"H
 2 lights x 60W Med.

- etched glass

**TC0017704**

5 light pendant in Espresso
 14"W x 26"H
 5 lights x 60W Cand.
 74" Overall height
 {12' wire} {4' chain}

TC0016704

3 light pendant in Espresso
 17"W x 24"H
 3 lights x 100W Med.
 72" Overall height
 {12' wire} {4' chain}

- etched glass



TN0009704 ↑↓

1 light wall sconce in Espresso
5"W x 14"H x 6"Ext.
1 light x 100W Med.
• etched glass



TV0015704 ↑↓

2 light bath bar in Espresso
18"W x 11"H x 7"Ext.
2 lights x 100W Med.
• etched glass



TV0016704 ↑↓

3 light bath bar in Espresso
24"W x 11"H x 7"Ext.
3 lights x 100W Med.
• etched glass



TV0017704 ↑↓

4 light bath bar in Espresso
30"W x 11"H x 7"Ext.
4 lights x 100W Med.
• etched glass



TV0018704 ↑↓

5 light bath bar in Espresso
36"W x 11"H x 7"Ext.
5 lights x 100W Med.
• etched glass



1105CH/20

5 light chandelier in Brushed Nickel
22"W x 24"H
5 lights x 75W Med.
85" Overall height
{12' wire} {60" chain}

- white glass



1155CH/10

5 light chandelier in Oil Rubbed Bronze
22"W x 24"H
5 lights x 75W Med.
85" Overall height
{12' wire} {60" chain}

- white glass



1103CH/20

3 light chandelier in Brushed Nickel
20"W x 22"H
3 lights x 70W Med.
83" Overall height
{12' wire} {60" chain}

- white glass



1153CH/10

3 light chandelier in Oil Rubbed Bronze
20"W x 22"H
3 lights x 70W Med.
83" Overall height
{12' wire} {60" chain}

- white glass



2205CH/10

5 light chandelier in Oil Rubbed Bronze
28"W x 21"H
5 lights x 60W Med.
82" Overall height
{12' wire} {60" chain}

- white glass



2203CH/10

3 light chandelier in Oil Rubbed Bronze
24"W x 22"H
3 lights x 60W Med.
83" Overall height
{12' wire} {60" chain}

- white glass



MISCELLANEOUS CHANDELIERS

1915CH/20

5 light chandelier in Brushed Nickel
 26"W x 24"H
 5 lights x 100W Med.
 85" Overall height
 {12' wire} {60" chain}

- white glass

**1913CH/10**

3 light chandelier in Oil Rubbed Bronze
 21"W x 23"H
 3 lights x 100W Med.
 84" Overall height
 {12' wire} {60" chain}

- white glass

**1913CH/20**

3 light chandelier in Brushed Nickel
 21"W x 23"H
 3 lights x 100W Med.
 84" Overall height
 {12' wire} {60" chain}

- white glass

**1905CH/10**

5 light chandelier in Oil Rubbed Bronze
 24"W x 23"H
 5 lights x 100W Med.
 84" Overall height
 {12' wire} {60" chain}

- white glass

**1903CH/20**

3 light chandelier in Brushed Nickel
 19"W x 20"H
 3 lights x 100W Med.
 81" Overall height
 {12' wire} {60" chain}

- white glass

**1903CH/10**

3 light chandelier in Oil Rubbed Bronze
 22"W x 19"H
 5 lights x 60W Med.
 81" Overall height
 {12' wire} {60" chain}

- white glass



MISCELLANEOUS CHANDELIERS

2455CH/20

5 light chandelier in Brushed Nickel
25"W x 25"H
5 lights x 60W Med.
86" Overall height
{12' wire} {60" chain}
• white glass



2453CH/20

3 light chandelier in Brushed Nickel
22"W x 24"H
3 lights x 60W Med.
86" Overall height
{12' wire} {60" chain}
• white glass



2455CH/10

5 light chandelier in Oil Rubbed Bronze
25"W x 25"H
5 lights x 60W Med.
86" Overall height
{12' wire} {60" chain}
• white glass



2453CH/10

3 light chandelier in Oil Rubbed Bronze
22"W x 24"H
3 lights x 60W Med.
86" Overall height
{12' wire} {60" chain}
• white glass



MISCELLANEOUS CHANDELIERS



PENDANTS

CN200142

BLAKESLEY
1 light pendant in Brushed Nickel
14"W x 11"H
1 light x 100W Med.
62" Overall height
{12' wire} {60" chain}
• frosted glass



CN200141

BLAKESLEY
1 light pendant in Oil Rubbed Bronze
14"W x 11"H
1 light x 100W Med.
62" Overall height
{12' wire} {60" chain}
• frosted glass



CN200152

BLAKESLEY
1 light pendant in Brushed Nickel
8"W x 11"H
1 light x 100W Med.
62" Overall height
{12' wire} {60" chain}
• frosted glass



CN200151

BLAKESLEY
1 light pendant in Oil Rubbed Bronze
8"W x 11"H
1 light x 100W Med.
62" Overall height
{12' wire} {60" chain}
• frosted glass



CN770148

CLASSIC LOFT
1 light pendant in Weathered Zinc
11"W x 6"H
1 light x 100W Med.
67" Overall height
{12' wire}



CN770141

CLASSIC LOFT
1 light pendant in Oil Rubbed Bronze
11"W x 6"H
1 light x 100W Med.
67" Overall height
{12' wire}



PENDANTS

CN770144

CLASSIC LOFT

1 light pendant in White

11"W x 6"H

1 light x 100W Med. ***Shown with Lamp 1092***

67" Overall height

**Lamp not included—See page 7*

{12' wire}



CN251551

WILLIAMSPORT

1 light pendant in Oil Rubbed Bronze

15"W x 9"H

1 light x 100W Med. ***Shown with Lamp 1092***

70" Overall height

{12' wire} {60" chain}

**Lamp not included—See page 7*



CN15712

WILLIAMSPORT

1 light pendant in Brushed Nickel

11"W x 15"H

1 light x 100W Med. ***Shown with Lamp 1092***

76" Overall height

{12' wire} {60" chain}

**Lamp not included—See page 7*



CN15711

WILLIAMSPORT

1 light pendant in Oil Rubbed Bronze

11"W x 15"H

1 light x 100W Med. ***Shown with Lamp 1092***

76" Overall height

{12' wire} {60" chain}

**Lamp not included—See page 7*



CN15832

WILLIAMSPORT

3 light pendant in Brushed Nickel

10"W x 16"H

3 lights x 60W Med. ***Shown with Lamp 1092***

44" Overall height

**Lamp not included—See page 7*



CN15831

WILLIAMSPORT

3 light pendant in Oil Rubbed Bronze

10"W x 16"H

3 lights x 60W Med. ***Shown with Lamp 1092***

44" Overall height

**Lamp not included—See page 7*



PENDANTS

7691PL/20

LIBERTY PARK

1 light mini pendant in Brushed Nickel

17"W x 17"H

1 light x 100W Med.

78" Overall height

{12' wire} {60" chain}

- prismatic clear glass



7691PL/10

LIBERTY PARK

1 light mini pendant Oil Rubbed Bronze

17"W x 17"H

1 light x 100W Med.

78" Overall height

{12' wire} {60" chain}

- prismatic clear glass



7681PL/20

LIBERTY PARK

1 light pendant in Brushed Nickel

12"W x 12"H

1 light x 100W Med.

73" Overall height

{12' wire} {60" chain}

- prismatic clear glass
- matching flush mounts available on page 165

7681PL/10

LIBERTY PARK

1 light pendant in Oil Rubbed Bronze

12"W x 12"H

1 light x 100W Med.

73" Overall height

{12' wire} {60" chain}

- prismatic clear glass
- matching flush mounts available on page 165

CN129041

BECKETT

1 light pendant in Oil Rubbed Bronze

12"W x 13"H

1 light x 60W Med. ***Shown with Lamp 1092***

74" Overall height

{12' wire} {60" chain}

- clear glass
- *Lamp not included—See page 7*



CN120041

BECKETT

1 light pendant in Oil Rubbed Bronze

12"W x 13"H

1 light x 60W Med.

74" Overall height

{12' wire} {60" chain}

- opal white glass



PENDANTS

LC411-PW-15**LED****QUINCY**

1 light pendant in Chrome

14"W x 7"H

1 light x 12W LED, 3000K, 80 CRI, 960 Lumens

47" Overall height

{12' wire} {4' chain}

- white glass
- dimmable

**CN129281****BECKETT**

3 light pendant/semi flush dual mount in Oil Rubbed Bronze

14"W x 7"H

3 lights x 60W Med. ***Shown with Lamp 1092***

68" Overall height

{12' wire} {60" chain}

- clear glass

Lamp not included-See page 7*CN120281****BECKETT**

3 light pendant/semi flush dual mount in Oil Rubbed Bronze

14"W x 7"H

3 lights x 60W Med.

68" Overall height

{12' wire} {60" chain}

- opal white glass

**PENDANTS**

190043217

PITTMAN

2 light pendant in Brushed Nickel

15"W x 15"H

2 lights x 100W Med.

60" Overall height

{12' wire} {4' chain}

- etched glass
- convertible semi-flush or chain hung pendant



190043719

PITTMAN

2 light pendant in Sienna Bronze

15"W x 15"H

2 lights x 100W Med.

60" Overall height

{12' wire} {4' chain}

- etched glass
- convertible semi-flush or chain hung pendant



190061217

PITTMAN

3 light pendant in Brushed Nickel

18"W x 20"H

3 lights x 100W Med.

68" Overall height

{12' wire} {4' chain}

- etched glass



190061719

PITTMAN

3 light pendant in Sienna Bronze

18"W x 20"H

3 lights x 100W Med.

68" Overall height

{12' wire} {4' chain}

- etched glass



PENDANTS

TC0022217

TREME

1 light pendant in Brushed Nickel

13"W x 8"H

1 light x 100W Med.

56" Overall height

{12' wire} {4' chain}

- etched white glass



TC0022704

TREME

1 light pendant in Espresso

13"W x 8"H

1 light x 100W Med.

56" Overall height

{12' wire} {4' chain}

- champagne glass



CN160381

PARK CITY

3 light pendant/semi flush dual mount in Oil Rubbed Bronze & Wood Grain

16"W x 13"H

3 lights x 100W Med.

74" Overall height

{12' wire} {60" chain}

- light beige scavo glass



TC0007704

WRIGHT

1 light pendant in Espresso

16"W x 17"H

1 light x 100W Med.

88" Overall height

{12' wire} {4' chain}

- champagne glass



PENDANTS

TC0007117**WRIGHT**

1 light pendant in Matte Nickel
 16"W x 17"H
 1 light x 100W Med.
 88" Overall height
 {12' wire} {4' chain}

- etched white glass

**2401PL/10****TRIBECA**

1 light pendant in Oil Rubbed Bronze
 12"W x 16"H
 1 light x 60W Cand.
 77" Overall height
 {12' wire} {60" chain}

- white glass

**SL823578****WHITMORE**

1 light pendant in Brushed Nickel
 16"W x 13"H
 1 light x 150W Med.
 61" Overall height
 {12' wire} {4' chain}

- etched glass

**M255078****WHITMORE**

1 light pendant in Brushed Nickel
 16"W x 17"H
 1 light x 150W Med.
 65" Overall height
 {12' wire} {4' chain}

- alabaster style glass

**SL891678****BELLA**

1 light pendant in Brushed Nickel
 16"W x 18"H
 1 light x 150W Med.
 66" Overall height
 {12' wire} {4' chain}

- etched glass

**SL891615****BELLA**

1 light pendant in Oil Rubbed Bronze
 16"W x 18"H
 1 light x 150W Med.
 66" Overall height
 {12' wire} {4' chain}

- etched glass



PENDANTS

1201PL/20

CONWAY

1 light large pendant in Brushed Nickel

15"W x 8"H

1 light x 100W Med.

69" Overall height

{12' wire} {60" chain}

- white glass

**1221PL/10**

CONWAY

1 light large pendant in Oil Rubbed Bronze

15"W x 8"H

1 light x 100W Med.

69" Overall height

{12' wire} {60" chain}

- white glass

**1301PL/20**

JACKSON

1 light large pendant in Brushed Nickel

14"W x 18"H

1 light x 100W Med.

79" Overall height

{12' wire} {60" chain}

- white glass

**1351PL/10**

JACKSON

1 light large pendant in Oil Rubbed Bronze

14"W x 18"H

1 light x 100W Med.

79" Overall height

{12' wire} {60" chain}

- white glass

**SL823478**

TAHOE

1 light pendant in Brushed Nickel

12"W x 9"H

1 light x 150W Med.

57" Overall height

{12' wire} {4' chain}

- alabaster style glass

**SL823463**

TAHOE

1 light mini pendant in Painted Bronze

12"W x 9"H

1 light x 150W Med.

57" Overall height

{12' wire} {4' chain}

- alabaster style glass

**PENDANTS**

TC0018741

HAVEN

1 light pendant in Satin Pewter

14"W x 9"H

1 light x 100W Med.

57" Overall height

{12' wire} {4' chain}

- etched glass

**TC0018704**

HAVEN

1 light pendant in Espresso

14"W x 9"H

1 light x 100W Med.

57" Overall height

{12' wire} {4' chain}

- etched glass

**190058117**

TIA

3 light large pendant in Matte Nickel

16"W x 21"H

3 lights x 100W Med.

69" Overall height

{12' wire} {4' chain}

- etched swirl glass

**190058763**

TIA

3 light large pendant in Painted Bronze

16"W x 21"H

3 lights x 100W Med.

69" Overall height

{12' wire} {4' chain}

- etched swirl glass

**SL893572**

TRITON

2 light pendant in Moonlight Silver

19"W x 24"H

2 lights x 100W Med.

72" Overall height

{12' wire} {4' chain}

- tea stained glass

**SL893522**

TRITON

2 light pendant in Sable Bronze

19"W x 24"H

2 lights x 100W Med.

72" Overall height

{12' wire} {4' chain}

- tea stained glass



PENDANTS

TC0016741

HAVEN

3 light pendant in Satin Pewter

17"W x 24"H

3 lights x 100W Med.

72" Overall height

{12' wire} {4' chain}

- etched glass

**TC0016704**

HAVEN

3 light pendant in Espresso

17"W x 24"H

3 lights x 100W Med.

72" Overall height

{12' wire} {4' chain}

- etched glass

**SL825378**

ELIPSE

3 light pendant in Brushed Nickel

19"W x 15"H

3 lights x 100W Med.

67" Overall height

{12' wire} {4' chain}

- alabaster style glass
- convertible semi-flush or chain hung pendant. Height when ceiling mounted 15"
- etched white diffuser

**SL825363**

ELIPSE

3 light pendant in Painted Bronze

19"W x 15"H

3 lights x 100W Med.

67" Overall height

{12' wire} {4' chain}

- alabaster style glass
- convertible semi-flush or chain hung pendant. Height when ceiling mounted 15"
- etched white diffuser

**SL826678**

RIVA

3 light pendant in Brushed Nickel

16"W x 19"H

3 lights x 100W Med.

67" Overall height

{12' wire} {4' chain}

- reeded center column
- alabaster style glass

**SL826663**

RIVA

3 light pendant in Painted Bronze

16"W x 19"H

3 lights x 100W Med.

67" Overall height

{12' wire} {4' chain}

- reeded center column
- alabaster style glass

**PENDANTS**

SL824641

HARMONY

3 light pendant in Satin Pewter

21"W x 25"H

3 lights x 100W Med.

97" Overall height

{12' wire} {6' chain}

- white marble glass



SL824662

HARMONY

3 light pendant in Aged Bronze

21"W x 25"H

3 lights x 100W Med.

97" Overall height

{12' wire} {6' chain}

- champagne marble glass



TC0021217

TREME

3 light pendant in Brushed Nickel

20"W x 24"H

3 lights x 100W Med.

72" Overall height

{12' wire} {4' chain}

- etched white glass



TC0021704

TREME

3 light pendant in Espresso

20"W x 24"H

3 lights x 100W Med.

72" Overall height

{12' wire} {4' chain}

- champagne glass



PENDANTS

1203PL/20

CONWAY

3 light large pendant in Brushed Nickel

18"W x 25"H

3 lights x 100W Med.

86" Overall height

{12' wire} {6' chain}

- white glass



1253PL/10

CONWAY

3 light large pendant in Oil Rubbed Bronze

18"W x 25"H

3 lights x 100W Med.

86" Overall height

{12' wire} {60" chain}

- white glass



1202CS/20

CONWAY

2 light pendant in Brushed Nickel

15"W x 14"H

2 lights x 100W Med.

75" Overall height

{12' wire} {60" chain}

- white glass
- convertible semi-flush or chain hung pendant



1252CS/10

CONWAY

2 light pendant in Oil Rubbed Bronze

15"W x 14"H

2 lights x 100W Med.

75" Overall height

{12' wire} {60" chain}

- white glass
- convertible semi-flush or chain hung pendant



PENDANTS

1103PL/20

CHATHAM

3 light large pendant in Brushed Nickel

18"W x 22"H

3 lights x 60W Med.

83" Overall height

{12' wire} {60" chain}

- white glass



SL861078

WHITMORE

2 light convertible in Brushed Nickel

16"W x 13"H

2 lights x 100W Med.

62" Overall height

{12' wire} {4' chain}

- etched glass
- convertible semi-flush or chain hung pendant. Height when ceiling mounted 13"



1053PL/10

BRIGHTON

3 light large pendant in Oil Rubbed Bronze

13"W x 6"H

3 lights x 60W Med.

83" Overall length

{12' wire} {60" chain}

- white glass



1002CS/20

BRIGHTON

2 light convertible in Brushed Nickel

16"W x 13"H

2 lights x 60W Med.

74" Overall height

{12' wire} {60" chain}

- white glass



1052CS/10

BRIGHTON

2 light convertible in Oil Rubbed Bronze

16"W x 13"H

2 lights x 60W Med.

74" Overall length

{12' wire} {60" chain}

- white glass



PENDANTS

SL829278**PRESTIGE**

3 light pendant in Brushed Nickel
 18"W x 23"H
 3 lights x 100W Med.
 95" Overall height
 {12' wire} {6' chain}

- alabaster style glass

**SL829222****PRESTIGE**

3 light pendant in Sable Bronze
 18"W x 23"H
 3 lights x 100W Med.
 95" Overall height
 {12' wire} {6' chain}

- cognac edged glass

**2203CS/10****SANTE FE**

3 light pendant in Oil Rubbed Bronze
 17"W x 16"H
 3 lights x 60W Med.
 77" Overall height
 {12' wire} {60" chain}

- white glass

**2203PL/10****SANTE FE**

3 light pendant in Oil Rubbed Bronze
 17"W x 14"H
 3 lights x 100W Med.
 75" Overall height
 {12' wire} {60" chain}

- white glass

**SL860778****BELLA**

3 light pendant in Brushed Nickel
 16"W x 12"H
 3 lights x 60W Med.
 59" Overall height
 {12' wire} {4' chain}

- etched glass
- convertible semi-flush or chain hung pendant

**SL860715****BELLA**

3 light pendant in Oil Rubbed Bronze
 16"W x 12"H
 3 lights x 60W Med.
 59" Overall height
 {12' wire} {4' chain}

- etched glass
- convertible semi-flush or chain hung pendant

**PENDANTS**

SL891778

BELLA
3 light pendant in Brushed Nickel
20"W x 25"H
3 lights x 100W Med.
72" Overall height
{12' wire} {4' chain}
• etched glass



SL891715

BELLA
3 light pendant in Oil Rubbed Bronze
20"W x 25"H
3 lights x 100W Med.
72" Overall height
{12' wire} {4' chain}
• etched glass



1217-1013

GRANGE
4 light island pendant light in Oil Rubbed Bronze
31"W x 10"H
4 lights x 60W Med.
56" Overall height
{12' wire} {60" chain}



PENDANTS

1003IS/20

BRIGHTON

3 light island pendant in Brushed Nickel

18"W x 37"H

3 lights x 100W Med.

44" Overall height

- white glass



1053IS/10

BRIGHTON

3 light island pendant in Oil Rubbed Bronze

18"W x 37"H

3 lights x 100W Med.

44" Overall length

- white glass



2203IS/10

SANTE FE

3 light island pendant in Oil Rubbed Bronze

48"W x 24"H x 13" D

3 lights x 60W Med.

85" Overall height

(60" chain)

- white glass



PENDANTS

42007/1

MARITIME

1 light indoor/outdoor mini pendant in
Hazelnut Bronze

9"W x 10"H

1 light x 60W Med.

72" Overall height

{12" wire} {60" chain}

- cast aluminum; clear, lightly seeded glass
- for indoor or outdoor use



45067/1



CROWLEY

1 light indoor/outdoor pendant in
Hazelnut Bronze

8"W x 18"H

1 light x 100W Med.

56" Overall height

{includes 3' chain, 6' wire}

- clear seeded glass



47021/1



MARINA

1 light indoor/outdoor pendant in Matte
Silver

8"W x 9"H

1 light x 60W Med.

45" Overall height

{includes 3' chain, 6' wire}

- cast aluminum



47011/1



MARINA

1 light indoor/outdoor pendant in Hazelnut
Bronze

8"W x 9"H

1 light x 60W Med.

45" Overall height

{includes 3' chain, 6' wire}


- cast aluminum



MINI PENDANTS



symbol denotes wet location tolerable

45121/1 

SAN MATEO

1 light indoor/outdoor pendant in
Textured Matte Black

8"W x 13"H

1 light x 100W Med.

51" Overall height
{includes 3' chain, 6' wire}

- clear seedy glass



42286/1 

PORTSIDE

1 light indoor/outdoor pendant in Matte Black

11"W x 16"H

1 light x 100W Med.

51" Overall height
{includes 3' chain, 6' wire}

- clear blown glass
- die cast aluminum



45213/1 

VANTON

1 light indoor/outdoor pendant
in Textured Matte Black


7"W x 10"H

1 light x 100W Med.

49" Overall height
{includes 3' chain, 6' wire}

- heavy seeded blown glass



57183/1 

ONION

1 light indoor/outdoor pendant in Oil Rubbed
Bronze

10"W x 14"H

1 light x 60W Med.

53" Overall height
{includes 3' chain, 6' wire}

- clear seedy glass



57173/1 

ONION

1 light indoor/outdoor pendant in Aged Zinc

10"W x 14"H

1 light x 60W Med.

53" Overall height
{includes 3' chain, 6' wire}

- clear seedy glass



1217-1011

GRANGE

1 light pendant in Oil Rubbed Bronze
7"W x 8"H
1 light x 60W Med. ***Shown with Lamp 1092***
53" Overall height
{12' cord}
**Lamp not included—See page 7*



CN250151

WILLIAMSPORT

1 light pendant in Oil Rubbed Bronze
8"W x 8"H
1 light x 100W Med. ***Shown with Lamp 1092***
75" Overall height
{12' wire} {60" chain}
**Lamp not included—See page 7*



7661PS/20

LIBERTY PARK

1 light mini pendant in Brushed Nickel
8"W x 8"H
1 light x 100W Med.
72" Overall height
{12' wire} {60" chain}

- prismatic clear glass
- matching flush mounts available on page 165



7661PS/10

LIBERTY PARK

1 light mini pendant in Oil Rubbed Bronze
8"W x 8"H
1 light x 100W Med.
72" Overall height
{12' wire} {60" chain}

- prismatic clear glass
- matching flush mounts available on page 165



45027/1

AMBLER

1 light indoor/outdoor pendant in Oil Rubbed Bronze
6"W x 14"H
1 light x 100W Med.
52" Overall height
{includes 3' chain, 6' wire}

- clear glass



45118/1


MULLEN GATE

1 light indoor/outdoor pendant in Oil Rubbed Bronze
6"W x 12"H
1 light x 100W Med.
48" Overall height
{includes 3' chain, 6' wire}

- clear glass



MINI PENDANTS

 symbol denotes wet location tolerable

CN240512

WEST END

1 light mini pendant in Brushed Nickel
5"W x 46"H
1 light x 60W



CN240511

WEST END

1 light mini pendant in Oil Rubbed Bronze
5"W x 46"H
1 light x 60W



CN280152

ASTORIA

1 light mini pendant in Brushed Nickel
6"W x 17"H
1 light x 60W
87" Overall height
{12' wire} {60" chain}

- clear glass



CN280155

ASTORIA

1 light mini pendant in Satin Gold
6"W x 17"H
1 light x 60W
87" Overall height
{12' wire} {60" chain}

- clear glass



CN129151

BECKETT

1 light mini pendant in Oil Rubbed Bronze
6"W x 7"H
1 light x 60W Med.* ***Shown with Lamp 1092**
68" Overall height
{12' wire} {60" chain}

- clear glass

**Lamp not included-See page 7*



CN120151

BECKETT

1 light mini pendant in Oil Rubbed Bronze
6"W x 7"H
1 light x 60W Med.
68" Overall height
{12' wire} {60" chain}

- opal white glass



MINI PENDANTS

CN170152

CASUAL MISSION

1 light mini pendant in Brushed Nickel

5"W x 7"H

1 light x 100W Med.

44" Overall height

- white lined glass



CN170151

CASUAL MISSION

1 light mini pendant in Oil Rubbed Bronze

5"W x 7"H

1 light x 100W Med.

44" Overall height

- white lined glass



M251878

ALLURE

1 light pendant in Brushed Nickel

6"W x 26"H

1 light x 60W Med.

74" Overall height

{12' wire} {1-4" + 1-8" + 1-12" + 1-24" rods}

- bone linen shimmer



CN160151

PARK CITY

1 light mini pendant in Oil Rubbed Bronze & Wood Grain

5"W x 8"H

1 light x 100W Med.

44" Overall height

{12' wire} {60" chain}

- light beige scavo glass



TC0008117

WRIGHT

1 light mini pendant in Matte Nickel

5"W x 17"H

1 light x 100W Med.

53" Overall height

{12' wire} {1-4" + 1-8" + 1-12" + 1-24" rods}

- etched white glass



190111704

WRIGHT

1 light mini pendant in Espresso

5"W x 17"H

1 light x 100W Med.

53" Overall height

{12' wire} {1-4" + 1-8" + 1-12" + 1-24" rods}

- champagne glass



MINI PENDANTS

SL891078

PENDENZA

1 light mini pendant in Brushed Nickel

5"W x 20"H

1 light x 100W Med.

68" Overall height

{12' wire} {4' chain}

- etched glass



SL891015

PENDENZA

1 light mini pendant in Oil Rubbed Bronze

5"W x 20"H

1 light x 100W Med.

68" Overall height

{12' wire} {4' chain}

- etched glass



190060217

PITTMAN

1 light mini pendant in Brushed Nickel

5"W x 8"H

1 light x 100W Med.

56" Overall height

{12' wire} {1-4" + 1-8" + 1-12" = 1-24" rods}

- etched glass



190060719

PITTMAN

1 light mini pendant in Sienna Bronze

5"W x 8"H

1 light x 100W Med.

56" Overall height

{12' wire} {1-4" + 1-8" + 1-12" = 1-24" rods}

- etched glass



MINI PENDANTS

TC0019217

TREME

1 light mini pendant in Brushed Nickel

5"W x 7"H

1 light x 100W Med.

43" Overall height

{12' wire} {3' chain}

- etched white glass

**TC0019704**

TREME

1 light mini pendant in Espresso

5"W x 7"H

1 light x 100W Med.

43" Overall height

{12' wire} {3' chain}

- champagne glass

**1101PS/20**

CHATHAM

1 light mini pendant in Brushed Nickel

5"W x 6"H

1 light x 75W Med.

44" Overall height

- white glass

**1151PS/20**

CHATHAM

1 light mini pendant in Oil Rubbed Bronze

5"W x 6"H

1 light x 75W Med.

44" Overall height

- white glass

**SL829178**

ELIPSE

1 light mini pendant in Brushed Nickel

6"W x 26"H

1 light x 100W Med.

56" Overall height

{12' wire} {2-12" + 1-6" rod}

- alabaster style glass

**SL829163**

ELIPSE

1 light mini pendant in Painted Bronze

6"W x 26"H

1 light x 100W Med.

56" Overall height

{12' wire} {2-12" + 1-6" rod}

- alabaster style glass



MINI PENDANTS

1001PS/20

BRIGHTON

- 1 light mini pendant in Brushed Nickel
 6"W x 6"H
 1 light x 75W Med.
 44" Overall height
- white glass

**1051PS/10**

BRIGHTON

- 1 light mini pendant in Oil Rubbed Bronze
 6"W x 6"H
 1 light x 75W Med.
 44" Overall height
- white glass

**SL825641**

HARMONY

- 1 light mini pendant in Satin Pewter
 7"W x 8"H
 1 light x 100W Med.
 44" Overall height
 {12' wire} {2-12" + 2-6" rods}
- white marble glass

**SL825662**

HARMONY

- 1 light mini pendant in Aged Bronze
 7"W x 8"H
 1 light x 100W Med.
 44" Overall height
 {12' wire} {2-12" + 2-6" rods}
- champagne marble glass

**SL891578**

BELLA

- 1 light mini pendant in Brushed Nickel
 8"W x 15"H
 1 light x 100W Med.
 63" Overall height
 {12' wire} {4' chain}
- etched glass

**SL891515**

BELLA

- 1 light mini pendant in Oil Rubbed Bronze
 8"W x 15"H
 1 light x 100W Med.
 63" Overall height
 {12' wire} {4' chain}
- etched glass

**MINI PENDANTS**

SL820678

RIVA

1 light mini pendant in Brushed Nickel
6"W x 21"H
1 light x 100W Med.
69" Overall height
{12' wire} {4' chain}

- reeded center column
- alabaster style glass



SL820663

RIVA

1 light mini pendant in Painted Bronze
6"W x 21"H
1 light x 100W Med.
69" Overall height
{12' wire} {4' chain}

- reeded center column
- alabaster style glass



SL893472

TRITON

1 light mini pendant in Moonlight Silver
5"W x 12"H
1 light x 100W Med.
48" Overall height
{12' wire} {2-12" + 2-6" rods}

- tea stained glass



SL893422

TRITON

1 light mini pendant in Sable Bronze
5"W x 12"H
1 light x 100W Med.
48" Overall height
{12' wire} {2-12" + 2-6" rods}

- tea stained glass



1301PS/20

JACKSON

1 light mini pendant in Brushed Nickel
4"W x 6"H
1 light x 60W Med.
44" Overall height

- white glass



1351PS/10

JACKSON

1 light mini pendant in Oil Rubbed Bronze
4"W x 6"H
1 light x 60W Med.
44" Overall height

- white glass



MINI PENDANTS

190056117

TIA

1 light mini pendant in Matte Nickel

6"W x 6"H

1 light x 100W Med.

42" Overall height

{12' wire} {2-12" + 2-6" rods}

- etched swirl glass



190056763

TIA

1 light mini pendant in Painted Bronze

6"W x 6"H

1 light x 100W Med.

42" Overall height

{12' wire} {2-12" + 2-6" rods}

- etched swirl glass



1201PS/20

CONWAY

1 light mini pendant in Brushed Nickel

8"W x 6"H

1 light x 100W Med.

44" Overall height

- white glass



1251PS/10

CONWAY

1 light mini pendant in Oil Rubbed Bronze

8"W x 6"H

1 light x 100W Med.

44" Overall height

- white glass



TC0014741

HAVEN

1 light mini pendant in Satin Pewter

5"W x 8"H

1 light x 100W Med.

44" Overall height

{12' wire} {3' chain}

- etched glass



CN230157

GEORGETOWN

1 light mini pendant in Weathered Zinc

6"W x 8"H

1 light x 100W Med. *Shown with Lamp 1102

61" Overall height

{12' wire} {60" chain}

- mercury glass

*Lamp not included—See page 7



MINI PENDANTS

SL829678

PRESTIGE

1 light mini pendant in Brushed Nickel

10"W x 6"H

1 light x 100W Med.

42" Overall height

{12' wire} {2-12" + 2-6" rods}

- alabaster style glass

**SL829663**

PRESTIGE

1 light mini pendant in Painted Bronze

10"W x 6"H

1 light x 100W Med.

42" Overall height

{12' wire} {2-12" + 2-6" rods}

- alabaster style glass

**SL829822**

PRESTIGE

1 light mini pendant in Sable Bronze

10"W x 6"H

1 light x 100W Med.

42" Overall height

{12' wire} {2-12" + 2-6" rods}

- cognac edged glass

**2101PS/20**

BRISTOL LANE

1 light mini pendant in Brushed Nickel

7"W x 43"H

1 light x 100W Med.

43" Overall length

- white glass

**2101PS/10**

BRISTOL LANE

1 light mini pendant in Brushed Nickel

7"W x 43"H

1 light x 100W Med.

43" Overall height

- white glass



MINI PENDANTS



FOYER

TC0023217

PRESTIGE
4 light pendant in Brushed Nickel
17"W x 28"H
4 lights x 60W CAND
100" Overall height
{12' wire} {6' chain}



TC0023722

PRESTIGE
4 light pendant in Sable Bronze
17"W x 28"H
4 lights x 60W CAND
100" Overall height
{12' wire} {6' chain}



SL893672

TRITON
4 light pendant in Moonlight Silver
18"W x 33"H
4 lights x 60W CAND
81" Overall height
{12' wire} {4' chain}



SL893622

TRITON
4 light pendant in Sable Bronze
18"W x 33"H
4 lights x 60W CAND
81" Overall height
{12' wire} {4' chain}



FOYER

SL891878

BELLA

6 light pendant in Brushed Nickel

17"W x 32"H

6 lights x 60W CAND

79" Overall height
{12' wire} {4' chain}



SL891815

BELLA

6 light pendant in Oil Rubbed Bronze

17"W x 32"H

6 lights x 60W CAND

79" Overall height
{12' wire} {4' chain}



TC0017741

HAVEN
5 light pendant in Satin Pewter
14"W x 26"H
5 lights x 60W CAND
74" Overall height
{12' wire} {4' chain}



TC0017704

HAVEN
5 light pendant in Espresso
14"W x 26"H
5 lights x 60W CAND
74" Overall height
{12' wire} {4' chain}



7704FY/20

4 light foyer in Brushed Nickel
11"W x 21"H
4 lights x 60W E12
82" Overall height
{12' wire} {60" chain}



7704FY/10

4 light foyer in Oil Rubbed Bronze
11"W x 21"H
4 lights x 60W E12
82" Overall height
{12' wire} {60" chain}



FOYER

SL847978

WHITMORE

2 light pendant in Brushed Nickel

8"W x 12"H

2 lights x 60W CAND

60" Overall height

{12' wire} {4' chain}

- clear glass



7713FY/10

3 light foyer in Oil Rubbed Bronze

7"W x 15"H

3 lights x 60W E12

88" Overall height

{6' wire} {6' chain}



7713FY/20

3 light foyer in Brushed Nickel

7"W x 15"H

3 lights x 60W E12

88" Overall height

{6' wire} {6' chain}



7706FY/20

6 light large pendant in Brushed Nickel
21"W x 39"H
6 lights x 100W MED
112" Overall height
{12' wire} {6' chain}

- white glass



7726FY/10

6 light large pendant in Oil Rubbed Bronze
21"W x 39"H
6 lights x 100W MED
112" Overall height
{12' wire} {6' chain}

- white glass



7703FY/20

3 light large pendant in Brushed Nickel
15"W x 27"H
2 lights x 100W MED
100" Overall height
{12' wire} {6' chain}

- white glass



7723FY/10

3 light large pendant in Oil Rubbed Bronze
15"W x 27"H
2 lights x 100W MED
100" Overall height
{12' wire} {6' chain}

- white glass



FOYER



CEILING

CN240382

WEST END
 3 light semi flush in Brushed Nickel
 15"W x 13"H
 3 lights x 60W



CN240381

WEST END
 3 light semi flush in Oil Rubbed Bronze
 15"W x 13"H
 3 lights x 60W



CN129281

BECKETT
 3 light semi flush dual mount in Oil Rubbed Bronze
 14"W x 7"H
 3 lights x 60W Med. ***Shown with Lamp 1092***
 • clear glass
**Lamp not included-See page 7*



CN120281

BECKETT
 3 light semi flush in Oil Rubbed Bronze
 14"W x 7"H
 3 lights x 60W Med.
 • opal white glass



CN170382

CASUAL MISSION
 3 light semi flush in Brushed Nickel
 20"W x 12"H
 3 lights x 100W Med.
 • white lined glass



CN170381

CASUAL MISSION
 3 light semi flush in Oil Rubbed Bronze
 20"W x 12"H
 3 lights x 100W Med.
 • white lined glass



TG0002117

WRIGHT
 3 light semi flush in Matte Nickel
 20"W x 12"H
 3 lights x 60W Med.
 • etched white glass



190113704

WRIGHT
 3 light semi flush in Espresso
 20"W x 12"H
 3 lights x 60W Med.
 • champagne glass



CEILING

SL861672

TRITON

2 light semi-flush in
Moonlight Silver
16"W x 12"H
2 lights x 100W Med.
• tea stained glass

**SL861622**

TRITON

2 light semi-flush in Sable
Bronze
16"W x 12"H
2 lights x 100W Med.
• tea stained glass

**SL861478**

TAHOE

2 light semi flush in Brushed Nickel
12"W x 11"H
2 lights x 100W Med.
• alabaster style glass

**SL861463**

TAHOE

2 light semi flush in Painted Bronze
12"W x 11"H
2 lights x 100W Med.
• alabaster style glass

**190067117**

TIA

2 light semi flush in Matte Nickel
12"W x 12"H
2 lights x 60W Med.
• etched swirl glass

**190067763**

TIA

2 light semi flush in Matte Nickel
12"W x 12"H
2 lights x 60W Med.
• etched swirl glass

**TC0015741**

HAVEN

2 light semi flush in Satin Pewter
16"W x 14"H
2 lights x 60W Med.
• etched glass

**TC0015704**

HAVEN

2 light semi flush in Espresso
16"W x 14"H
2 lights x 60W Med.
• etched glass

**SEMI-FLUSH**

SL860978

PENDENZA

2 light semi flush in Brushed Nickel

16"W x 12"H

2 lights x 60W Med.

- white cotton weave fabric shade
- etched white diffuser

**SL860915**

PENDENZA

2 light semi flush in Oil Rubbed Bronze

16"W x 12"H

2 lights x 60W Med.

- white cotton weave fabric shade
- etched white diffuser

**190043217**

PITTMAN

2 light semi flush in Brushed Nickel

15"W x 15"H

2 lights x 100W Med.

- etched glass

**190043719**

PITTMAN

2 light semi flush in Sienna Bronze

15"W x 15"H

2 lights x 100W Med.

- etched glass

**CN600362**

MORGAN

2 light semi flush in Brushed Nickel

15"W x 11"H

2 lights x 60W Med.

- white glass diffuser
- white fabric shade

**CN600361**

MORGAN

2 light semi flush in Oil Rubbed Bronze

15"W x 11"H

2 lights x 60W Med.

- white glass diffuser
- white fabric shade

**CN160381**

PARK CITY

3 light semi flush dual mount in Oil Rubbed Bronze with wood grain

16"W x 13"H

3 lights x 100W Med.

- light beige scavo glass

**2402SF/20**

TRIBECCA

2 light semi flush in Brushed Nickel

12"W x 12"H

2 lights x 60W Med.

- white glass

**CEILING**



SEMI-FLUSH

TC0020217

TREME
 2 light semi flush in Brushed Nickel
 13"W x 12"H
 2 lights x 60W Med.
 • etched white glass

**TC0020704**

TREME
 2 light semi flush in Espresso
 13"W x 12"H
 2 lights x 60W Med.
 • etched white glass

**SL825378**

ECLIPSE
 3 light semi flush in Brushed Nickel
 19"W x 15"H
 3 lights x 100W Med.
 • alabaster style glass
 • etched white diffuser

**SL825363**

ECLIPSE
 3 light semi flush in Painted Bronze
 19"W x 15"H
 3 lights x 100W Med.
 • alabaster style glass
 • etched white diffuser

**SL866241**

HARMONY
 2 light semi-flush in Satin Pewter
 16"W x 13"H
 2 lights x 100W Med.
 • white marble glass

**SL866262**

HARMONY
 2 light semi flush in Aged Bronze
 16"W x 13"H
 2 lights x 100W Med.
 • champagne marble glass

**SL869678**

RIVA
 3 light semi flush in Brushed Nickel
 16"W x 12"H
 3 lights x 100W Med.
 • etched alabaster style glass

**SL869663**

RIVA
 3 light semi flush in Painted Bronze
 16"W x 12"H
 3 lights x 100W Med.
 • etched alabaster style glass



CEILING

SL842078

PRESTIGE

- 2 light semi flush in Brushed Nickel
- 15"W x 14"H
- 2 lights x 100W Med.
- alabaster style glass



SL842022

PRESTIGE

- 2 light semi-flush in Sable Bronze
- 15"W x 14"H
- 2 lights x 100W Med.
- cognac edged glass



1202CS/20

CONWAY

- 2 light convertible semi flush in Brushed Nickel
- 15"W x 14"H
- 2 lights x 100W Med.
- white glass



1252CS/10

CONWAY

- 2 light convertible semi flush in Oil Rubbed Bronze
- 15"W x 14"H
- 2 lights x 100W Med.
- white glass



CN230387

GEORGETOWN

- 3 light semi flush in Brushed Nickel
- 19"W x 16"H
- 3 lights x 100W Med. ***Shown with Lamp 1102**
- mercury glass
- *Lamp not included-See page 7*



2203CS/10

SANTE FE

- 3 light semi flush in Oil Rubbed Bronze
- 17"W x 16"H
- 3 lights x 60W Med.
- 77" Overall height
- white glass



SL860778

BELLA

- 3 light semi-flush in Brushed Nickel
- 16"W x 12"H
- 3 lights x 60W Med.
- etched glass



SL860715

BELLA

- 3 light semi-flush in Oil Rubbed Bronze
- 16"W x 12"H
- 3 lights x 60W Med.
- etched glass



SEMI-FLUSH

1002CS/20

BRIGHTON
2 light convertible in Brushed Nickel
16"W x 13"H
2 lights x 60W Med.
• white glass



1052CS/10

BRIGHTON
2 light convertible in Oil Rubbed Bronze
16"W x 13"H
2 lights x 60W Med.
• white glass



2103SF/20

BRISTOL LANE
3 light semi-flush in Brushed Nickel
17"W x 12"H
3 lights x 60W Med.
• white glass



2103SF/10

BRISTOL LANE
3 light semi-flush in Brushed Nickel
17"W x 12"H
3 lights x 60W Med.
• white glass



SL861078

WHITMORE
2 light convertible semi flush in
Brushed Nickel
16"W x 13"H
2 lights x 100W Med.
• etched glass



CN129231

BECKETT

2 light flush mount in Oil Rubbed Bronze

14"W x 7"H

2 lights x 100W Med. *Shown with Lamp 1092*

- clear glass

*Lamp not included—See page 7



CN120231

BECKETT

2 light flush mount in Oil Rubbed Bronze

14"W x 7"H

2 lights x 100W Med.

- opal white glass



LIBERTY PARK

flush mount in Brushed Nickel

Model	W	H	Lights	Max. Watt.
7672FM/20	10"	10"	2	60W
7683FM/20	12"	12"	3	60W
7693FM/20	17"	17"	3	60W

- prismatic clear glass



LIBERTY PARK

flush mount in Oil Rubbed Bronze

Model	W	H	No. Lights	Max. Watt.
7672FM/10	10"	10"	2	60W
7683FM/10	12"	12"	3	60W
7693FM/10	17"	17"	3	60W

- prismatic clear glass



SL876278

2 light flush mount in Brushed Nickel

14"W x 6"H

2 lights x 60W Med.

- clear ribbed glass



2003FM/10

ARLINGTON

3 light flush mount in Oil Rubbed Bronze

14"W x 6"H

3 lights x 60W Med.

- white glass



CN170332

CASUAL MISSION

3 light flush mount in Brushed Nickel

13"W x 7"H

3 lights x 60W Med.

- white lined glass



CN170331

CASUAL MISSION

3 light flush mount in Oil Rubbed Bronze

13"W x 7"H

3 lights x 60W Med.

- white lined glass



FLUSH MOUNT

190071217

PITTMAN
 2 light flush mount in Brushed Nickel
 14"W x 6"H
 2 lights x 60W Med.
 • etched glass

**190071719**

PITTMAN
 2 light flush mount in Sienna Bronze
 14"W x 6"H
 2 lights x 60W Med.
 • etched glass

**2103FM/20**

BRISTOL LANE
 3 light flush mount in Brushed Nickel
 17"W x 6"H
 3 lights x 60W Med.
 • white glass

**2103FM/10**

BRISTOL LANE
 3 light flush mount in Brushed Nickel
 17"W x 6"H
 3 lights x 60W Med.
 • white glass

**1103FM/20**

BRIGHTON
 3 light flush mount in Brushed Nickel
 13"W x 6"H
 3 lights x 60W Med.
 • white glass

**1153FM/10**

BRIGHTON
 3 light flush mount in Oil Rubbed Bronze
 13"W x 6"H
 3 lights x 60W Med.
 • white glass

**SL861572**

TRITON
 2 light flush mount in Moonlight Silver
 13"W x 7"H
 2 lights x 60W Med.
 • tea stained glass

**SL861522**

TRITON
 2 light flush mount in Sable Bronze
 13"W x 7"H
 2 lights x 60W Med.
 • tea stained glass



CEILING

CN160231

PARK CITY

2 light flush mount in Oil Rubbed Bronze with wood grain

13"W x 6"H

2 lights x 60W Med.

- light beige scavo glass



CN230237

GEORGETOWN

2 light flush mount in Weathered Zinc

16"W x 9"H

2 lights x 60W Med.*

- mercury glass

*Lamp not included—See page ###



M271878

2 light flush mount in Brushed Nickel

15"W x 9"H

2 lights x 60W Med.

- bone linen shimmer
- etched white diffuser



SL928378



2 light indoor/outdoor flush mount in Brushed Nickel

12"W x 6"H

2 lights x 60W Med.

- etched alabaster style glass



SL869218

PRESTIGE

2 light flush mount in Textured White

14"W x 6"H

2 lights x 60W Med.

- etched alabaster style glass



SL877263

PRESTIGE

2 light flush mount in Painted Bronze

14"W x 6"H

2 lights x 60W Med.

- golden cream swirl glass



SL878223

2 light flush mount in Colonial Bronze

14"W x 6"H

2 lights x 60W Med.

- etched glass



SL869222

2 light flush mount in Sable Bronze

14"W x 6"H

2 lights x 60W Med.

- etched melon glass



symbol denotes damp location tolerable

FLUSH MOUNT



flush mount in Brushed Nickel

Model	W	H	Lights	Max. Watt.
SL869178	12"	6"	1	100W
SL869278	14"	6"	2	60W
SL869378	16"	7"	3	60W

- etched alabaster style glass



flush mount in Brushed Nickel

Model	W	H	Lights	Max. Watt.
SL878178	12"	6"	1	100W
SL878278	14"	6"	2	60W
SL878378	16"	7"	3	60W

- etched glass



flush mount in Oil Rubbed Bronze

Model	W	H	Lights	Max. Watt.
SL878115	12"	6"	1	100W
SL878215	14"	6"	2	60W

- etched glass



flush mount in Painted Bronze

Model	W	H	Lights	Max. Watt.
SL869163	12"	6"	1	100W
SL869263	14"	6"	2	60W
SL869363	16"	6"	3	60W

- etched alabaster style glass



flush mount in Brushed Nickel

Model	W	H	Lights	Max. Watt.
7002FM/20	11"	3"	2	60W
7003FM/20	13"	4"	2	60W
7013FM/20	15"	6"	3	60W

- etched glass



flush mount in White

Model	W	H	Lights	Max. Watt.
7002FM/40	11"	3"	2	60W
7003FM/40	13"	4"	2	60W
7013FM/40	15"	6"	3	60W

- etched glass



flush mount in Oil Rubbed Bronze

Model	W	H	Lights	Max. Watt.
7052FM/10	11"	3"	2	60W
7053FM/10	13"	4"	2	60W
7023FM/10	15"	6"	3	60W

- etched glass



energy efficient flush mount in Brushed Nickel

Model	W	H	Lights	Max. Watt.
190034217	12"	4"	1	13W GU24 CFL
190035217	15"	5"	2	13W GU24 CFL

- etched glass
- rate for 90° supply wire
- lamp included



190033217

2 light flush mount in Brushed Nickel

15"W x 5"H
2 lights x 60W Med.

- etched glass

CEILING



190033715

2 light flush mount in Oil Rubbed Bronze
 15"W x 5"H
 2 lights x 60W Med.
 • etched glass



flush mount in Brushed Nickel

Model	W	H	Lights	Max. Watt.
7301FM/20	12"	5"	1	60W
7302FM/20	15"	5"	2	60W
7303FM/20	16"	6"	3	60W

• acid etched alabaster white glass



flush mount in Oil Rubbed Bronze

Model	W	H	Lights	Max. Watt.
7301FM/10	12"	5"	1	60W
7302FM/10	15"	5"	2	60W
7303FM/10	16"	6"	3	60W

• acid etched alabaster white glass



flush mount in Brushed Nickel

Model	W	H	Lights	Max. Watt.
SL845578	8"	5"	1	60W
SL845678	10"	6"	2	60W
SL869363	16"	6"	3	60W

• alabaster style glass



flush mount in White

Model	W	H	Lights	Max. Watt.
7351FM/40	7"	5"	1	60W
7352FM/40	10"	5"	2	60W

• white glass



FLUSH MOUNT



flush mount in Brushed Nickel

Model	W	H	Lights	Max. Watt.
SL868178	12"	6"	1	100W
SL868278	14"	6"	2	60W

- etched melon glass



SL868218

2 light flush mount in Textured White
14"W x 6"H
2 lights x 60W Med.

- etched melon glass



SL868263

2 light flush mount in Painted Bronze
14"W x 6"H
2 lights x 60W Med.

- etched melon glass



SL84408

2 light flush mount in Matte White
10"W x 6"H
2 light x 60W Med.

- clear ribbed glass



flush mount in White

Model	W	H	Lights	Max. Watt.
SL3258	8"	5"	1	60W
SL3268	10"	6"	2	60W
SL3288	12"	6"	3	60W

- etched glass
- rate for 90° supply wire



SL123

2 light flush mount in White
12"W x 6"H
2 lights x 60W Med.

- white glass



7021FM/40

1 light flush mount in White
8"W x 5"H
1 light x 60W Med.

- white glass



7021FM/20

1 light flush mount in Brushed Nickel
8"W x 5"H
1 light x 60W Med.

- white glass



7021FM/10

1 light flush mount in Oil Rubbed Bronze
8"W x 5"H
1 light x 60W Med.

- white glass

CEILING



SL843678

1 light flush mount in Brushed Nickel
6"W x 8"H
1 light x 60W Med.
• white glass globe



SL84368

1 light flush mount in Matte White
6"W x 8"H
1 light x 60W Med.
• white glass globe



LED

KALONA flush mount in White, CRI 90

Model	W	H	Max. Watt.
CL783004	11"	5"	13W Integrated LED, 762 Lumens
CL783014	13"	4"	24W Integrated LED, 1050 Lumens
CL783024	15"	5"	28.5W Integrated LED, 1265 Lumens

• white acrylic diffuser



CN734299

SUNGLOW
2 light flush mount in Oil Rubbed Bronze
13"W x 4"H
2 light x 60W Med.
• white glass
• Brushed Nickel clips included



CN734399

SUNGLOW
3 light flush mount in Oil Rubbed Bronze
17"W x 5"H
3 light x 60W Med.
• white glass
• Brushed Nickel clips included



LED

Dimmable flush mount in Satin Nickel
3000K, CRI 80

Model	W	H	Max. Watt.
FML4225-10-16M	12"	3"	11W Integrated LED, 900 Lumens
FML4250-10-16M	15"	4"	20W Integrated LED, 1600 Lumens

• opal white glass



LED

Dimmable flush mount in Chrome
3000K, CRI 80

Model	W	H	Max. Watt.
FML4925-10-15	12"	4"	16W Integrated LED, 1300 Lumens
FML4950-10-15	15"	4"	20W Integrated LED, 1600 Lumens

• opal white glass



LED

Dimmable flush mount in Chrome
3000K, CRI 80

Model	W	H	Max. Watt.
FML4725-10-15	13"	3"	11W Integrated LED, 900 Lumens
FML4750-10-15	16"	4"	20W Integrated LED, 1600 Lumens

• opal white glass



LED

Dimmable flush mount in Satin Nickel
3000K, CRI 80

Model	W	H	Max. Watt.
FML2000-10-16M	5"	2"	7.5W Integrated LED, 600 Lumens
FML2020-10-16M	8"	3"	2 x 5W Integrated LED, 800 Lumens
FML2030-10-16M	9"	3"	2 x 7.5W Integrated LED, 1200 Lumens

• opal white glass

FLUSH MOUNT



LED

Dimmable flush mount in Satin Nickel
3000K, CRI 80

Model	W	H	Max. Watt.
FML4025-10-16M	6"	2"	7.5W Integrated LED, 600 Lumens
FML4050-10-16M	9"	3"	11W Integrated LED, 900 Lumens
FML4075-10-16M	11"	3"	20W Integrated LED, 1600 Lumens

- opal white glass



LED

Dimmable flush mount in Satin Nickel
3000K, CRI 80

Model	W	H	Max. Watt.
FML7125-10-16M	8"	4"	7.5W Integrated LED, 600 Lumens
FML7150-10-16M	11"	4"	16W Integrated LED, 900 Lumens
FML7175-10-16M	13"	5"	20W Integrated LED, 1600 Lumens

- opal white glass



LED

TITAN Dimmable flush mount in White
3000K, CRI 90, 120V

Model	W	H	Max. Watt.
CL781034	6"	1"	9W Integrated LED, 550 Lumens
CL781134	8"	1"	12W Integrated LED, 800 Lumens
CL781234	10"	1"	15W Integrated LED, 950 Lumens
CL781334	13"	1"	20W Integrated LED, 1300 Lumens
CL781434	15"	1"	30W Integrated LED, 1800 Lumens

- white acrylic diffuser



LED

TITAN Dimmable flush mount in Oil Rubbed Bronze
3000K, CRI 90, 120V

Model	W	H	Max. Watt.
CL781031	6"	1"	9W Integrated LED, 550 Lumens
CL781131	8"	1"	12W Integrated LED, 800 Lumens
CL781231	9"	1"	15W Integrated LED, 950 Lumens

- white acrylic diffuser



LED

TITAN Dimmable flush mount in White
3000K, 120V, CRI 90

Model	W	H	Max. Watt.
CL791334	6"	1"	9W Integrated LED, 550 Lumens
CL791434	8"	1"	12W Integrated LED, 800 Lumens
CL791534	10"	1"	15W Integrated LED, 950 Lumens
CL791634	13"	1"	20W Integrated LED, 1200 Lumens
CL791734	15"	1"	30W Integrated LED, 1800 Lumens

- white acrylic diffuser



LED

TITAN Dimmable flush mount in Oil Rubbed Bronze
3000K, 120V, CRI 90

Model	W	H	Max. Watt.
CL791331	6"	1"	11W Integrated LED, 600 Lumen
CL791431	8"	1"	14W Integrated LED, 800 Lumens
CL791531	10"	1"	17W Integrated LED, 1000 Lumens

- white acrylic diffuser



LED

CLARION
Dimmable flush mount in Brushed Nickel
3000K, 120V, CRI 90

Model	W	H	Max. Watt.
CL782012	11"	4"	13W Integrated LED, 563 Lumens
CL782042	14"	4"	16W Integrated LED, 700 Lumens
CL782022	16"	4"	24W Integrated LED, 860 Lumens
CL782032	18"	4"	28W Integrated LED, 983 Lumens

- white acrylic diffuser



LED

CLARION
Dimmable flush mount in Oil Rubbed Bronze
3000K, 120V, CRI 90

Model	W	H	Max. Watt.
CL782011	11"	4"	13W Integrated LED, 563 Lumens
CL782041	14"	4"	16W Integrated LED, 700 Lumens
CL782021	16"	4"	24W Integrated LED, 860 Lumens
CL782031	18"	4"	28W Integrated LED, 983 Lumens

- white acrylic diffuser




SL705378

2 light flush mount in Brushed Nickel

33"W x 5"H x 17"EXT
2 lights x 32W FC12T9 (32W)

- white acrylic lens
- 120V electronic ballast

CEILING



LED

Dimmable flush mount in Chrome
3000K, CRI 90

Model	W	H	Max. Watt.
FML4525-10-15	12"	3"	11W Integrated LED, 900 Lumens
FML4550-10-15	15"	3"	20W Integrated LED, 1600 Lumens

- opal white glass



LED

Dimmable flush mount in Matte White
3000K, CRI 80

Model	W	H	Max. Watt.
FML6125-AC-30	5"	2"	8W Integrated LED, 640 Lumens
FML6150-AC-30	7"	2"	12W Integrated LED, 960 Lumens
FML6175-AC-30	9"	2"	16W Integrated LED 1280 Lumens



PLANDOME

Dimmable surface mount in White, 3000K, CRI 90

Model	W	H	Max. Watt.
MLE1500-5-30²	6"	1"	12W Integrated LED, 850 Lumens
MLE1550-5-30²	6"	1"	18W Integrated LED, 1200 Lumens
MLE1200-5-30¹	5"	1"	9W Integrated LED, 550 Lumens
MLE-1201-5-30¹	7"	1"	15W Integrated LED, 850 Lumens

¹ Note: For Installation into Recessed Lighting Fixture or Junction Box

² Note: For Installation into Junction Box Only



TG100234

1 light flush mount in White
14"W x 4"H x 14" Ext.
2 light x 40 Med.

- white glass

TG100134

1 light flush mount in White
11"W x 3"H x 11" Ext.
1 light x 40 Med.

- white glass



TG110234

1 light flush mount in White
14"W x 4"H x 14" Ext.
2 light x 40 Med.

- white glass

TG110134

1 light flush mount in White
11"W x 3"H x 11" Ext.
1 light x 40 Med.

- white glass



symbol denotes damp location tolerable

FLUSH MOUNT

FWN432EB

energy efficient flush mount

48"L x 14"W x 3"H
4 lights x F32T8 (32W)

- clear acrylic prismatic lens
- 120V electronic ballast



FWN232EB

energy efficient flush mount

48"L x 8"W x 3"H
2 lights x F32T8 (32W)

- clear acrylic prismatic lens
- 120V electronic ballast



FWN217EB

energy efficient flush mount

24"L x 8"W x 3"H
2 lights x F17T8 (17W)

- clear acrylic prismatic lens
- 120V electronic ballast



FCN432EB

energy efficient flush mount in White

50"L x 17"W x 5"H
4 lights x F32T8 (32W)

- soft white acrylic diffuser
- 120V electronic ballast



FCN232EB

energy efficient flush mount in White

50"L x 12"W x 5"H
2 lights x F32T8 (32W)

- soft white acrylic diffuser
- 120V electronic ballast



SL1217EB

energy efficient flush mount in White

27"W x 6"H x 5"EXT
2 lights x 17W F17T8 (17W)

- may be mounted on wall or ceiling
- 120V electronic ballast





WALL SCONCES

CN280172

ASTORIA

1 light wall sconce in Brushed Nickel

6"W x 10"H x 9" Ext.

1 light x 60W

- clear glass



CN280175

ASTORIA

1 light wall sconce in Satin Gold

6"W x 10"H x 9" Ext.

1 light x 60W

- clear glass



CN129121



BECKETT

1 light wall sconce in Oil Rubbed Bronze

6"W x 12"H x 7"EXT

1 light x 60W MED * Shown with Lamp 1092

- clear glass

*lamp not included-See page 385



CN120121



BECKETT

1 light wall sconce in Oil Rubbed Bronze

6"W x 12"H x 7"EXT

1 light x 60W MED

- opal white glass



CN260471

NOTRE DAME

4 light wall sconce in Oil Rubbed Bronze with Gold Rods

10"W x 13"H x 5" Ext.

4 lights x 60W Cand.

0" Overall height



CN110171

ADA

FARMINGTON

1 light wall sconce in Oil Rubbed Bronze

5"W x 14"H x 4"EXT

1 light x 60W CAND



WALL SCONCES

1501WS/20

WILLIAMSPORT
1 light wall sconce in Brushed Nickel
5"W x 11"H x 7"EXT
1 light x 60W CAND



1501WS/10

WILLIAMSPORT
1 light wall sconce in Oil Rubbed Bronze
5"W x 11"H x 7"EXT
1 light x 60W CAND



1502WS/20

WILLIAMSPORT
2 light wall sconce in Brushed Nickel
12"W x 11"H x 8"EXT
2 lights x 60W CAND



1502WS/10

WILLIAMSPORT
2 light wall sconce in Oil Rubbed Bronze
12"W x 11"H x 8"EXT
2 lights x 60W CAND



CN240172

WEST END
1 light wall sconce in Brushed Nickel
5"W x 10"H x 6" Ext.
1 light x 60W



CN240171

WEST END
1 light wall sconce in Oil Rubbed Bronze
5"W x 10"H x 6" Ext.
1 light x 60W



CN578172

RAVENDALE
1 light wall sconce in Brushed Nickel
5"W x 9"H x 7"EXT
1 lights x 100W MED
• opal white glass



CN578171

RAVENDALE
1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 7"EXT
1 lights x 100W MED
• opal white glass



 symbol denotes up or down mounting

WALL SCONCES

TN0005217 

PENDENZA
1 light wall sconce in Brushed Nickel
5"W x 12"H x 8"EXT
1 lights x 100W MED
• etched glass



TN0005715 

PENDENZA
1 light wall sconce in Oil Rubbed Bronze
5"W x 12"H x 8"EXT
1 lights x 100W MED
• etched glass



42005/1 

MARITIME
1 light indoor/outdoor wall sconce in Hazelnut Bronze
9"W x 10"H x 11" Ext.
1 light x 60W Med.
• lightly seeded glass



42405/1 

MARITIME
1 light indoor/outdoor wall sconce in Graphite
9"W x 10"H x 11" Ext.
1 light x 60W Med.
• frosted glass



42006/1 

MARITIME
1 light indoor/outdoor wall sconce in Hazelnut Bronze
9"W x 12"H x 11" Ext.
1 light x 60W Med.
• lightly seeded glass



42406/1 

MARITIME
1 light indoor/outdoor wall sconce in Graphite
9"W x 12"H x 11" Ext.
1 light x 60W Med.
• frosted glass



47020/1 

MARINA
1 light indoor/outdoor wall sconce in Matte Silver
8"W x 8"H x 9" Ext.
1 light x 60W Med.
• cast aluminum




47010/1 

MARINA
1 light indoor.outdoor wall sconce in Hazelnut Bronze
8"W x 8"H x 9" Ext.
• cast aluminum



WALL SCONCES

 symbol denotes up or down mounting

47150/1 

LANDIS

1 light indoor/outdoor wall sconce in Dark Graphite
6"W x 10"H x 9"Ext.
1 light x 60W Med.
• clear glass



42510/LED 

OSAGE

1 light indoor/outdoor wall sconce in Weathered Charcoal
8"W x 13"H x 9" Ext.
1 light x 6W - 480 Lumen Integrated LED; 2700K, 80 CRI
• clear seeded glass



45212/1 

VANTON

1 light indoor/outdoor wall sconce in Textured Matte Black
7"W x 13"H x 8" Ext.
1 light x 60W Med.
• heavy seeded blown glass



CN575172 

BELMAR

1 light wall sconce in Brushed Nickel
5"W x 9"H x 6"EXT
1 light x 100W MED
• opal white glass



CN575171 

BELMAR

1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 6"EXT
1 light x 100W MED
• opal white glass



CN579172 

SUMMIT PLACE

1 light wall sconce in Brushed Nickel
5"W x 9"H x 6" EXT
1 lights x 100W MED
• opal white glass



CN579171 


SUMMIT PLACE

1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 6"EXT
1 lights x 100W MED
• opal white glass



 symbol denotes up or down mounting

WALL SCONCES

TN0007117 

WRIGHT

- 1 light wall sconce in Matte Nickel
- 5"W x 10"H x 7"EXT
- 1 light x 100W MED
- etched white glass



TN0007704 

WRIGHT

- 1 light wall sconce in Espresso
- 5"W x 10"H x 7"EXT
- 1 light x 100W MED
- champagne glass



190023217 

PITTMAN

- 1 light wall sconce in Brushed Nickel
- 5"W x 9"H x 6"EXT
- 1 lights x 100W MED
- etched glass



190023719 

PITTMAN

- 1 light wall sconce in Sienna Bronze
- 5"W x 9"H x 6"EXT
- 1 lights x 100W MED
- etched glass



2451WS/20

TRIBECCA

- 1 light wall sconce in Brushed Nickel
- 9"W x 12"H x 10" EXT
- 1 light x 60W MED
- white glass




2451WS/10

TRIBECCA

- 1 light wall sconce in Oil Rubbed Bronze
- 9"W x 12"H x 10" EXT
- 1 light x 60W MED
- white glass



WALL SCONCES

 symbol denotes wet location tolerable

CN573171 ↑↓

SINCLAIR

- 1 light wall sconce in Brushed Nickel
- 5"W x 10"H x 5"EXT
- 1 light x 60W MED
- frosted white glass



CN573172 ↑↓

SINCLAIR

- 1 light wall sconce in Polished Chrome
- 5"W x 10"H x 5"EXT
- 1 light x 60W MED
- frosted white glass



CN160171 ↑↓

PARK CITY

- 1 light wall sconce in Oil Rubbed Bronze & Wood Grain
- 5"W x 7"H x 7"EXT
- 1 light x 60W MED
- light beige scavo glass



CN230177 ↑↓

GEORGETOWN

- 1 light wall sconce in Weathered Zinc
- 6"W x 12"H x 8"EXT
- 1 light x 100W MED * Show with Lamp 1101
- mercury glass
- *lamp not included—See page 385



CN170172 ↑↓

CASUAL MISSION

- 1 light wall sconce in Brushed Nickel
- 5"W x 8"H x 6"EXT
- 1 light x 100W MED
- white lined glass



CN170171 ↑↓

CASUAL MISSION

- 1 light wall sconce in Oil Rubbed Bronze
- 5"W x 8"H x 6"EXT
- 1 light x 100W MED
- white lined glass



TN0009741 ↑↓

HAVEN

- 1 light wall sconce in Satin Pewter
- 5"W x 14"H x 6"EXT
- 1 light x 100W MED
- etched glass



TN0009704 ↑↓

HAVEN

- 1 light wall sconce in Espresso
- 5"W x 14"H x 6"EXT
- 1 light x 100W MED
- etched glass



↑↓ symbol denotes up or down mounting

WALL SCONCES

1301WS/20 ↑↓

JACKSON
1 light wall sconce in Brushed Nickel
5"W x 8"H x 7"EXT
1 light x 60W MED
• white glass



1351WS/10 ↑↓

JACKSON
1 light wall sconce in Oil Rubbed Bronze
5"W x 8"H x 7"EXT
1 light x 60W MED
• white glass



TN0010217 ↑↓

TREME
1 light wall sconce in Brushed Nickel
5"W x 12"H x 8"EXT
1 light x 100W MED
• etched white glass



TN0010704 ↑↓

TREME
1 light wall sconce in Espresso
5"W x 12"H x 8"EXT
1 light x 100W MED
• etched white glass



TN0003217 ↑↓

BELLA
1 light wall sconce in Brushed Nickel
5"W x 9"H x 8"EXT
1 lights x 100W MED
• etched glass



TN0003715 ↑↓

BELLA
1 light wal sconce in Oil Rubbed Bronze
5"W x 9"H x 8"EXT
1 lights x 100W MED
• etched glass



CN570172 ↑↓

CALIFON
1 light wall sconce in Brushed Nickel
5"W x 9"H x 8"EXT
1 lights x 100W MED
• white glass



CN570171 ↑↓

CALIFON
1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 8"EXT
1 lights x 100W MED
• white glass



WALL SCONCES

↑↓ symbol denotes up or down mounting

1001WS/20 ↑↓

BRIGHTON

1 light wall sconce in Brushed Nickel

6"W x 11"H x 8"EXT

1 light x 75W MED

- white glass



1051WS/10 ↑↓

BRIGHTON

1 light wall sconce in Oil Rubbed Bronze

6"W x 11"H x 8"EXT

1 light x 75W MED

- white glass



SL744178 ↑↓

ELIPSE

1 light wall sconce in Brushed Nickel

6"W x 10"H x 8"EXT

1 light x 100W MED

- alabaster style glass



SL744163 ↑↓

ELIPSE

1 light wall sconce in Painted Bronze

6"W x 10"H x 8"EXT

1 light x 100W MED

- alabaster style glass



SL758178 ↑↓

HOMESTEAD

1 light wall sconce in Brushed Nickel

6"W x 12"H x 8"EXT

1 light x 100W MED

- alabaster style glass



2201WS/10 ↑↓

SANTE FE

1 light wall sconce in Oil Rubbed Bronze

6"W x 10"H x 9"EXT

1 light x 100W MED

- white glass



SL854178 ↑↓

PRESTIGE

1 light wall sconce in Brushed Nickel

8"W x 9"H x 10"EXT

1 light x 100W MED

- alabaster style glass



SL854122 ↑↓

PRESTIGE

1 light wall sconce in Sable Bronze

8"W x 9"H x 10"EXT

1 light x 100W MED

- cognac edged glass



symbol denotes up or down mounting

WALL SCONCES

1201WS/20



CONWAY

1 light wall sconce in Brushed Nickel

6"W x 9"H x 8"EXT

1 light x 100W MED

- white glass



1251WS/20



CONWAY

1 light wall sconce in Oil Rubbed Bronze

6"W x 9"H x 8"EXT

1 light x 100W MED

- white glass



5501BB/20



SHELburnE

1 light wall sconce in Brushed Nickel

8"W x 7"H x 9"EXT

1 light x 75W MED

- white etched glass



5551BB/10



SHELburnE

1 light wall sconce in Oil Rubbed Bronze

8"W x 7"H x 9"EXT

1 light x 75W MED

- white etched glass



5501BB/30



SHELburnE

1 light wall sconce in Polished Chrome

8"W x 7"H x 9"EXT

1 light x 75W MED

- white etched glass



5601BB/30



SUDBURY

1 light wall sconce in Polished Chrome

6"W x 10"H x 8"EXT

1 light x 75W MED

- white glass



5601BB/20



SUDBURY

1 light wall sconce in Brushed Nickel

6"W x 10"H x 8"EXT

1 light x 75W MED

- white glass



5651BB/10



SUDBURY

1 light wall sconce in Oil Rubbed Bronze

6"W x 10"H x 8"EXT

1 light x 75W MED

- white glass



WALL SCONCES



symbol denotes up or down mounting

1101WS/20 

CHATHAM

1 light wall sconce in Brushed Nickel

5"W x 19"H x 7"EXT

1 light x 75W MED

- white glass



1151WS/10 

CHATHAM

1 light wall sconce in Oil Rubbed Bronze

5"W x 19"H x 7"EXT

1 light x 75W MED

- white glass



2101WS/20

BRISTOL LANE

1 light wall sconce in Brushed Nickel

7"W x 10"H x 10"EXT

1 light x 100W MED

- white glass



2101WS/10

BRISTOL LANE

1 light wall sconce in Oil Rubbed Bronze

7"W x 10"H x 10"EXT

1 light x 100W MED

- white glass



SL853178 

1 light wall sconce in Brushed Nickel

14"W x 9"H x 4"EXT

1 light x 100W MED

- alabaster style glass



SL853163 

1 light wall sconce in Painted Bronze

14"W x 9"H x 4"EXT

1 light x 100W MED

- alabaster style glass



SL853122 

1 light wall sconce in Sable Bronze

14"W x 9"H x 4"EXT

1 light x 100W MED

- cognac edged glass



5161WS/99 


1 light wall sconce in Brushed Nickel

7"W x 12"H x 4" EXT

1 light x 60W CAND

- white glass diffuser



 symbol denotes up or down mounting

WALL SCONCES



5151WS/20

1 light wall sconce in Brushed Nickel
 11"W x 5"H x 5" EXT
 1 light x 60W CAND
 • white glass



5151WS/10

1 light wall sconce in Oil Rubbed Bronze
 11"W x 5"H x 5" EXT
 1 light x 60W CAND
 • white glass



5171WS/20

1 light wall sconce in Brushed Nickel
 12"W x 5"H x 6" EXT
 1 light x 100W MED
 • white glass



5371WS/10

1 light wall sconce in Oil Rubbed Bronze
 12"W x 5"H x 6" EXT
 1 light x 100W MED
 • white glass



5181WS/20 **ADA**

1 light wall sconce in Brushed Nickel
 7"W x 10"H x 4" EXT
 1 light x 60W MED
 • white glass



CN518571 **ADA**

1 light wall sconce in Oil Rubbed Bronze
 6"W x 10"H x 4" EXT
 1 light x 60W MED
 • white glass



WALL SCONCES

symbol denotes up or down mounting

5111WS/20 ADA

- 1 light wall sconce in Brushed Nickel
- 8"W x 12"H x 4"EXT
- 1 light x 60W CAND
- white glass diffuser



WSL140-5-15  ADA

- PORTAL
- 1 light wall sconce in Polished Chrome
- 6"W x 9"H x 3"EXT
- 1 light x 3W LED, 3000K, 80 CRI
- frosted white glass
- 240 Lumens, dimmable

LED



5102WS/20 ADA

- 2 light wall sconce in Brushed Nickel
- 8"W x 14"H x 4"EXT
- 2 lights x 60W CAND
- white glass diffuser



CN510571 ADA

- 2 light wall sconce in Oil Rubbed Bronze
- 8"W x 14"H x 4"EXT
- 2 lights x 60W CAND
- white glass diffuser



5131WS/20

- 1 light wall sconce in Brushed Nickel
- 11"W x 6"H x 6"EXT
- 1 light x 60W MED
- white glass diffuser



5121WS/99 ADA

- 1 light wall sconce in Brushed Nickel
- 9"W x 8"H x 4"EXT
- 1 light x 60W MED
- (includes turn sets)
- white glass diffuser



SL746078 ADA

- 1 light wall sconce in Brushed Nickel
- 9"W x 11"H x 4"EXT
- 1 light x 26W MED
- white acrylic diffuser
- 120V electronic blast



WSL1601-PW-15  ADA

- MIDTOWN
- 1 light wall sconce in Polished Chrome
- 5"W x 11"H x 4"EXT
- 1 light x 4W LED, 3000K, 80 CRI
- white glass
- 480 Lumens, dimmable

LED



WALL SCONCES

CL581213

ESSENTIALS

1 light wall sconce in Chrome

6"W x 13"H x 6" Ext.

1 light x 100W

- white glass



CL580213



ESSENTIALS

2 light wall sconce in Chrome

6"W x 20"H x 6" Ext.

2 lights x 100W

- white glass



WSL825-10-15M



LED

MAXFIELD

1 light double wall sconce in Chrome

4"W x 10"H x 4"EXT

1 light x 2.5W LED, 3000K, 80 CRI

- opal white glass
- 600 Lumens, dimmable



ADA

WSL820-10-16M



LED

MAXFIELD

2 light double wall sconce in Satin Nickel

4"W x 20"H x 4"EXT

2 lights x 2.5W LED, 3000K, 80 CRI

- opal white glass
- 1200 Lumens, dimmable



ADA

TITAN dimmable flush mount in White
3000K, 120V, CRI 90

Model	W	H	Max. Watt.
CL791334	6"	1"	9W Integrated LED, 550 Lumens
CL791434	8"	1"	12W Integrated LED, 800 Lumens
CL791534	10"	1"	15W Integrated LED, 950 Lumens
CL791634	13"	1"	20W Integrated LED, 1200 Lumens
CL791734	15"	1"	30W Integrated LED, 1800 Lumens

- white acrylic diffuser



LED

ADA



TITAN flush mount in Oil Rubbed Bronze
3000K, 120V, CRI 90

Model	W	H	Max. Watt.
CL791331	6"	1"	11W Integrated LED, 600 Lumens
CL791431	8"	1"	14W Integrated LED, 800 Lumens
CL791531	10"	1"	17W Integrated LED, 1000 Lumens

- white acrylic diffuser



LED

ADA



TITAN dimmable flush mount in White
3000K, 120V, CRI 90

Model	W	H	Max. Watt.
CL781034	6"	1"	9W Integrated LED, 550 Lumens
CL781134	8"	1"	12W Integrated LED, 800 Lumens
CL781234	10"	1"	15W Integrated LED, 950 Lumens
CL781334	13"	1"	20W Integrated LED, 1300 Lumens
CL781434	15"	1"	30W Integrated LED, 1800 Lumens

- white acrylic diffuser



LED

ADA



TITAN dimmable flush mount in Oil Rubbed Bronze
3000K, 120V, CRI 90

Model	W	H	Max. Watt.
CL781031	6"	1"	9W Integrated LED, 550 Lumens
CL781131	8"	1"	12W Integrated LED, 800 Lumens
CL781231	9"	1"	15W Integrated LED, 950 Lumens

- white acrylic diffuser



LED

ADA



WALL SCONCES



symbol denotes up or down mounting



BATH

WEST END

CN240172



1 light wall sconce in Brushed Nickel
5"W x 10"H x 6"Ext.
1 light x 60W



CN240122



2 light bath bar in Brushed Nickel
15"W x 10"H x 6"Ext.
2 light x 60W



CN240132



3 light bath bar in Brushed Nickel
23"W x 10"H x 6"Ext.
3 light x 60W



CN240142



4 light bath bar in Brushed Nickel
30"W x 10"H x 6"Ext.
4 light x 60W



BATH



symbol denotes up or down mounting

WEST END

CN240171



1 light wall sconce in Oil Rubbed Bronze
5"W x 10"H x 6"Ext.
1 light x 60W



CN240121



2 light bath bar in Oil Rubbed Bronze
15"W x 10"H x 6"Ext.
2 light x 60W



CN240131



3 light bath bar in Oil Rubbed Bronze
23"W x 10"H x 6"Ext.
3 light x 60W



CN240141



4 light bath bar in Oil Rubbed Bronze
30"W x 10"H x 6"Ext.
4 light x 60W



symbol denotes up or down mounting

BATH

NOTRE DAME


CN260471

4 light wall sconce in Oil Rubbed Bronze with Gold Rods
10"W x 13"H x 5"Ext.
4 lights x 60W Cand.



CN260611

6 light bath bar in Oil Rubbed Bronze with Gold Rods
19"W x 13"H x 5"Ext.
6 lights x 60W Cand.



CN260811

8 light bath bar in Oil Rubbed Bronze with Gold Rods
28"W x 13"H x 5"Ext.
8 lights x 60W Cand.



BATH

CL580113

1 bath fixture in Chrome
6"W x 13"H x 6"Ext.
1 light x 100W
• white glass



CL580213



2 bath fixture in Chrome
20"W x 6"H x 6"Ext.
2 light x 100W
• white glass



symbol denotes up or down mounting

ASTORIA

CN280172



- 1 light wall sconce in Brushed Nickel
- 6"W x 10"H x 9"Ext.
- 1 light x 60W
- clear glass



CN280212



- 2 light bath bar in Brushed Nickel
- 16"W x 11"H x 8"Ext.
- 2 light x 60W
- clear glass



CN280312



- 3 light bath bar in Brushed Nickel
- 25"W x 9"H x 9"Ext.
- 3 light x 60W
- clear glass



CN280412



- 4 light bath bar in Brushed Nickel
- 35"W x 9"H x 9"Ext.
- 4 light x 60W
- clear glass



BATH



symbol denotes up or down mounting

ASTORIA

CN280175



- 1 light wall sconce in Satin Gold
6"W x 10"H x 9"Ext.
1 light x 60W
- clear glass



CN280215



- 2 light bath bar in Satin Gold
16"W x 11"H x 8"Ext.
2 light x 60W
- clear glass



CN280315



- 3 light bath bar in Satin Gold
25"W x 9"H x 9"Ext.
3 light x 60W
- clear glass



CN280415



- 4 light bath bar in Satin Gold
35"W x 9"H x 9"Ext.
4 light x 60W
- clear glass



symbol denotes up or down mounting

BATH

CN129121

1 light wall sconce in Oil Rubbed Bronze
6"W x 12"H x 7"Ext.
1 light x 60W Med. ***Shown with Lamp 1092**
• clear glass
**Lamp not included—See page 385*



CN129211

2 light bath bar in Oil Rubbed Bronze
15"W x 11"H x 7"Ext.
2 lights x 60W Med. ***Shown with Lamp 1092**
• clear glass
**Lamp not included—See page 385*



CN129311

3 light bath bar in Oil Rubbed Bronze
24"W x 11"H x 7"Ext.
3 lights x 60W Med. ***Shown with Lamp 1092**
• clear glass
**Lamp not included—See page 385*



CN129411

4 light bath bar in Oil Rubbed Bronze
33"W x 11"H x 7"Ext.
3 lights x 60W Med. ***Shown with Lamp 1092**
• clear glass
**Lamp not included—See page 385*



BECKETT

CN120121



1 light wall sconce in Oil Rubbed Bronze
6"W x 12"H x 7"Ext.
1 light x 60W Med.
• opal white glass



CN120211



2 light bath bar in Oil Rubbed Bronze
15"W x 11"H x 7"Ext.
2 lights x 60W Med.
• opal white glass



CN120311



3 light bath bar in Oil Rubbed Bronze
24"W x 11"H x 7"Ext.
3 lights x 60W Med.
• opal white glass



CN120411



4 light bath bar in Oil Rubbed Bronze
33"W x 11"H x 7"Ext.
3 lights x 60W Med.
• opal white glass



symbol denotes up or down mounting

BATH

PITTMAN

190023217

1 light wall sconce in Brushed Nickel
5"W x 9"H x 6"Ext.
1 lights x 100W Med.
• etched glass



190022217

2 light bath bar in Brushed Nickel
12"W x 10"H x 6"Ext.
2 lights x 100W Med.
• etched glass



190024217

3 light bath bar in Brushed Nickel
19"W x 10"H x 6"Ext.
3 lights x 100W Med.
• etched glass



190025217

4 light bath bar in Brushed Nickel
24"W x 10"H x 6"Ext.
4 lights x 100W Med.
• etched glass



BATH

 symbol denotes up or down mounting

PITTMAN

190023719

1 light wall sconce in Sienna Bronze
5"W x 9"H x 6"Ext.
1 lights x 100W Med.
• etched glass



190022719

2 light bath bar in Sienna Bronze
12"W x 10"H x 6"Ext.
2 lights x 100W Med.
• etched glass



190024719

3 light bath bar in Sienna Bronze
19"W x 10"H x 6"Ext.
3 lights x 100W Med.
• etched glass



190025719

4 light bath bar in Sienna Bronze
24"W x 10"H x 6"Ext.
4 lights x 100W Med.
• etched glass



CASUAL MISSION

CN170172



- 1 light wall sconce in Brushed Nickel
5"W x 8"H x 6"Ext.
1 light x 100W Med.
• white lined glass



CN170212



- 2 light bath bar in Brushed Nickel
12"W x 9"H x 6"Ext.
2 lights x 100W Med.
• white lined glass



CN170312



- 3 light bath bar in Brushed Nickel
20"W x 9"H x 6"Ext.
3 lights x 100W Med.
• white lined glass



CN170412



- 4 light bath bar in Brushed Nickel
28"W x 9"H x 6"Ext.
4 lights x 100W Med.
• white lined glass



BATH



symbol denotes up or down mounting

CASUAL MISSION

CN170171



1 light wall sconce in Oil Rubbed Bronze
5"W x 8"H x 6"Ext.
1 light x 100W Med.
• white lined glass



CN170211



2 light bath bar in Oil Rubbed Bronze
12"W x 9"H x 6"Ext.
2 lights x 100W Med.
• white lined glass



CN170311



3 light bath bar in Oil Rubbed Bronze
20"W x 9"H x 6"Ext.
3 lights x 100W Med.
• white lined glass



CN170411



4 light bath bar in Oil Rubbed Bronze
28"W x 9"H x 6"Ext.
4 lights x 100W Med.
• white lined glass



symbol denotes up or down mounting

BATH

WRIGHT

TN0007117



- 1 light bath bar in Matte Nickel
5"W x 10"H x 7"Ext.
1 light x 100W Med.
• etched white glass



TV0008117



- 2 light bath bar in Matte Nickel
15"W x 11"H x 7"Ext.
2 lights x 100W Med.
• etched white glass



TV0009117



- 3 light bath bar in Matte Nickel
24"W x 11"H x 7"Ext.
3 lights x 100W Med.
• etched white glass



TV0010117



- 4 light bath bar in Matte Nickel
32"W x 11"H x 7"Ext.
4 lights x 100W Med.
• etched white glass



BATH



symbol denotes up or down mounting

WRIGHT

TN0007704



- 1 light wall sconce in Espresso
5"W x 10"H x 7"Ext.
1 light x 100W Med.
• champagne glass



190114704



- 2 light bath bar in Espresso
15"W x 11"H x 7"Ext.
2 lights x 100W Med.
• champagne glass



190115704



- 3 light bath bar in Espresso
24"W x 11"H x 7"Ext.
3 lights x 100W Med.
• champagne glass



190116704



- 4 light bath bar in Espresso
32"W x 11"H x 7"Ext.
4 lights x 100W Med.
• champagne glass



symbol denotes up or down mounting

BATH

PENDENZA

TN0005217



- 1 light wall sconce in Brushed Nickel
5"W x 12"H x 8"Ext.
1 lights x 100W Med.
• etched glass



TV0007217



- 2 light bath bar in Brushed Nickel
13"W x 12"H x 9"Ext.
2 lights x 100W Med.
• etched glass



SL715378



- 3 light bath in Brushed Nickel
20"W x 12"H x 9"Ext.
3 lights x 100W Med.
• etched glass



SL715478



- 4 light bath in Brushed Nickel
27"W x 12"H x 9"Ext.
4 lights x 100W Med.
• etched glass



BATH



symbol denotes up or down mounting

PENDENZA

TN0005715

1 light wall sconce in Oil Rubbed Bronze
5"W x 12"H x 8"Ext.
1 lights x 100W Med.
• etched glass



TV0007715

2 light bath bar in Oil Rubbed Bronze
13"W x 12"H x 9"Ext.
2 lights x 100W Med.
• etched glass



SL715315

3 light bath bar in Oil Rubbed Bronze
20"W x 12"H x 9"Ext.
3 lights x 100W Med.
• etched glass



SL715415

4 light bath bar in Oil Rubbed Bronze
27"W x 12"H x 9"Ext.
4 lights x 100W Med.
• etched glass



symbol denotes up or down mounting

BATH

PARK CITY

CN160171



1 light wall sconce in Oil Rubbed Bronze & Wood Grain

5"W x 7"H x 7"Ext.

1 light x 60W Med.

- light beige scavo glass



CN160211



2 light bath bar in Oil Rubbed Bronze & Wood Grain

14"W x 7"H x 7"Ext.

2 lights x 60W Med.

- light beige scavo glass



CN160311



3 light bath bar in Oil Rubbed Bronze & Wood Grain

22"W x 7"H x 7"Ext.

3 lights x 60W Med.

- light beige scavo glass



CN160411



4 light bath bar in Oil Rubbed Bronze & Wood Grain

30"W x 7"H x 7"Ext.

4 lights x 60W Med.

- light beige scavo glass



BATH



symbol denotes up or down mounting

GEORGETOWN

CN230177

1 light wall sconce in Weathered Zinc
6"W x 12"H x 8"Ext.
1 light x 100W Med.***Shown with Lamp 1102**
• mercury glass
**Lamp not included—See page 324*



CN230217

2 light bath bar in Weathered Zinc
16"W x 11"H x 7"Ext.
2 lights x 100W Med.***Shown with Lamp 1102**
• mercury glass
**Lamp not included—See page 324*



CN230317

3 light bath bar in Weathered Zinc
24"W x 12"H x 7"Ext.
3 lights x 100W Med.***Shown with Lamp 1102**
• mercury glass
**Lamp not included—See page 324*



CN230417

4 light bath bar in Weathered Zinc
33"W x 13"H x 7"Ext.
4 lights x 100W Med.***Shown with Lamp 1102**
• mercury glass
**Lamp not included—See page 324*



ELIPSE

SL744178

1 light wall sconce in Brushed Nickel
6"W x 10"H x 8"Ext.
1 light x 100W Med.
• alabaster style glass



SL744278

1 light bath bar in Brushed Nickel
18"W x 10"H x 8"Ext.
2 lights x 100W Med.
• alabaster style glass



SL744378

3 light bath bar in Brushed Nickel
24"W x 10"H x 8"Ext.
3 lights x 100W Med.
• alabaster style glass



SL744478

4 light bath bar in Brushed Nickel
36"W x 10"H x 8"Ext.
4 lights x 100W Med.
• alabaster style glass



SL744578

5 light bath bar in Brushed Nickel
48"W x 10"H x 8"Ext.
5 lights x 100W Med.
• alabaster style glass



ELIPSE

SL744163

1 light wall sconce in Painted Bronze
6"W x 10"H x 8"Ext.
1 light x 100W Med.
• alabaster style glass



SL744263

2 light bath bar in Painted Bronze
18"W x 10"H x 8"Ext.
2 lights x 100W Med.
• alabaster style glass



SL744363

3 light bath bar in Painted Bronze
24"W x 10"H x 8"Ext.
3 lights x 100W Med.
• alabaster style glass



SL744463

4 light bath bar in Painted Bronze
36"W x 10"H x 8"Ext.
4 lights x 100W Med.
• alabaster style glass



SL744563

5 light bath bar in Painted Bronze
48"W x 10"H x 8"Ext.
5 lights x 100W Med.
• alabaster style glass



1301WS/20

1 light wall sconce in Brushed Nickel
5"W x 8"H x 7"Ext.
1 light x 60W Med.
• white glass



1302BB/20

2 light bath bar in Brushed Nickel
14"W x 9"H x 7"Ext.
2 lights x 60W Med.
• white glass



1303BB/20

3 light bath bar in Brushed Nickel
22"W x 9"H x 7"Ext.
3 lights x 60W Med.
• white glass



1304BB/20

4 light bath bar in Brushed Nickel
31"W x 9"H x 7"Ext.
4 lights x 60W Med.
• white glass



JACKSON

1351WS/10

1 light wall sconce in Oil Rubbed Bronze
5"W x 8"H x 7"Ext.
1 light x 60W Med.
• white glass



1352BB/10

2 light bath bar in Oil Rubbed Bronze
14"W x 9"H x 7"Ext.
2 lights x 60W Med.
• white glass



1353BB/10

3 light bath bar in Oil Rubbed Bronze
22"W x 9"H x 7"Ext.
3 lights x 60W Med.
• white glass



1354BB/10

4 light bath bar in Oil Rubbed Bronze
31"W x 9"H x 7"Ext.
4 lights x 60W Med.
• white glass



symbol denotes up or down mounting

BATH

TIA

190016117



- 2 light bath bar in Matte Nickel
16"W x 9"H x 8"Ext.
2 lights x 100W Med.
• etched swirl glass



190017117



- 3 light bath bar in Matte Nickel
23"W x 9"H x 8"Ext.
3 lights x 100W Med.
• etched swirl glass



190018117



- 4 light bath bar in Matte Nickel
31"W x 9"H x 8"Ext.
4 lights x 100W Med.
• etched swirl glass



190016763

- 2 light bath bar in Painted Bronze
 16"W x 9"H x 8"Ext.
 2 lights x 100W Med.
 • etched swirl glass

**190017763**

- 3 light bath bar in Painted Bronze
 23"W x 9"H x 8"Ext.
 3 lights x 100W Med.
 • etched swirl glass

**190018763**

- 4 light bath bar in Painted Bronze
 31"W x 9"H x 8"Ext.
 4 lights x 100W Med.
 • etched swirl glass



symbol denotes up or down mounting

1201WS/20

1 light wall sconce in Brushed Nickel
6"W x 9"H x 8"Ext.
1 light x 100W Med.
• white glass



1202BB/20

2 light bath bar in Brushed Nickel
15"W x 9"H x 7"Ext.
2 lights x 100W Med.
• white glass



1203BB/20

3 light bath bar in Brushed Nickel
23"W x 9"H x 7"Ext.
3 lights x 100W Med.
• white glass



1204BB/20

4 light bath bar in Brushed Nickel
32"W x 9"H x 7"Ext.
4 lights x 100W Med.
• white glass



CONWAY

1251WS/10

1 light wall sconce in Oil Rubbed Bronze
6"W x 9"H x 8"Ext.
1 light x 100W Med.
• white glass



1252BB/10

2 light bath bar in Oil Rubbed Bronze
15"W x 9"H x 7"Ext.
2 lights x 100W Med.
• white glass



1253BB/10

3 light bath bar in Oil Rubbed Bronze
23"W x 9"H x 7"Ext.
3 lights x 100W Med.
• white glass



1254BB/10

4 light bath bar in Oil Rubbed Bronze
32"W x 9"H x 7"Ext.
4 lights x 100W Med.
• white glass



BELLA

TN0003217

1 light wall sconce in Brushed Nickel
5"W x 9"H x 7"Ext.
1 lights x 100W Med.
• etched glass



SL714278

2 light bath bar in Brushed Nickel
13"W x 9"H x 7"Ext.
2 lights x 100W Med.
• etched glass



SL714378

3 light bath bar in Brushed Nickel
18"W x 9"H x 7"Ext.
3 lights x 100W Med.
• etched glass



SL714478

4 light bath bar in Brushed Nickel
25"W x 9"H x 7"Ext.
4 lights x 100W Med.
• etched glass



SL714578

5 light bath bar in Brushed Nickel
31"W x 9"H x 7"Ext.
5 lights x 100W Med.
• etched glass



BELLA

TN0003715

1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 7"Ext.
1 lights x 100W Med.
• etched glass



SL714215

2 light bath bar in Oil Rubbed Bronze
13"W x 9"H x 7"Ext.
2 lights x 100W Med.
• etched glass



SL714315

3 light bath bar in Oil Rubbed Bronze
18"W x 9"H x 7"Ext.
3 lights x 100W Med.
• etched glass



SL714415

4 light bath bar in Oil Rubbed Bronze
25"W x 9"H x 7"Ext.
4 lights x 100W Med.
• etched glass



SL714515

5 light bath bar in Oil Rubbed Bronze
31"W x 9"H x 7"Ext.
5 lights x 100W Med.
• etched glass



TRITON

SL717272

2 light bath bar in Moonlight Silver
12"W x 9"H x 9"Ext.
2 lights x 100W Med.
• tea stained glass



SL717372

3 light bath bar in Moonlight Silver
21"W x 9"H x 9"Ext.
3 lights x 100W Med.
• tea stained glass



SL717472

4 light bath bar in Moonlight Silver
29"W x 9"H x 9"Ext.
4 lights x 100W Med.
• tea stained glass



SL717572

5 light bath bar in Moonlight Silver
36"W x 9"H x 9"Ext.
5 lights x 100W Med.
• tea stained glass



TRITON

SL717222

2 light bath bar in Sable Bronze
12"W x 9"H x 9"Ext.
2 lights x 100W Med.
• tea stained glass



SL717322

3 light bath bar in Sable Bronze
21"W x 9"H x 9"Ext.
3 lights x 100W Med.
• tea stained glass



SL717422

4 light bath bar in Sable Bronze
29"W x 9"H x 9"Ext.
4 lights x 100W Med.
• tea stained glass



SL717522

5 light bath bar in Sable Bronze
36"W x 9"H x 9"Ext.
5 lights x 100W Med.
• tea stained glass



HARMONY

SL760241

2 light bath bar in Satin Pewter
16"W x 8"H x 7"Ext.
2 lights x 100W Med.
• white marble glass



SL760341

3 light bath bar in Satin Pewter
24"W x 8"H x 7"Ext.
3 lights x 100W Med.
• white marble glass



SL760441

4 light bath bar in Satin Pewter
32"W x 8"H x 7"Ext.
4 lights x 100W Med.
• white marble glass



HARMONY

SL760262

- 2 light bath bar in Aged Bronze
16"W x 8"H x 7"Ext.
2 lights x 100W Med.
• champagne marble glass



SL760362

- 3 light bath bar in Aged Bronze
24"W x 8"H x 7"Ext.
3 lights x 100W Med.
• champagne marble glass



SL760462

- 4 light bath bar in Aged Bronze
32"W x 8"H x 7"Ext.
4 lights x 100W Med.
• champagne marble glass



symbol denotes up or down mounting

BATH

BRIGHTON

1001WS/20

1 light wall sconce in Brushed Nickel
6"W x 11"H x 8"Ext.
1 light x 75W Med.
• white glass



1002BB/20

2 light bath bar in Brushed Nickel
15"W x 11"H x 7"Ext.
2 lights x 75W Med.
• white glass



1003BB/20

3 light bath bar in Brushed Nickel
24"W x 11"H x 7"Ext.
3 lights x 75W Med.
• white glass



1004BB/20

4 light bath bar in Brushed Nickel
33"W x 11"H x 7"Ext.
4 lights x 75W Med.
• white glass



BRIGHTON

1051WS/10

1 light wall sconce in Oil Rubbed Bronze
6"W x 11"H x 8"Ext.
1 light x 75W Med.
• white glass



1052BB/10

2 light bath bar in Oil Rubbed Bronze
15"W x 11"H x 7"Ext.
2 lights x 75W Med.
• white glass



1053BB/10

3 light bath bar in Oil Rubbed Bronze
24"W x 11"H x 7"Ext.
3 lights x 75W Med.
• white glass



1054BB/10

4 light bath bar in Oil Rubbed Bronze
33"W x 11"H x 7"Ext.
4 lights x 75W Med.
• white glass



PRESTIGE

SL854178

1 light wall sconce in Brushed Nickel
8"W x 9"H x 10"Ext.
1 light x 100W Med.
• alabaster style glass



SL748278

2 light bath bar in Brushed Nickel
17"W x 9"H x 9"Ext.
2 lights x 100W Med.
• alabaster style glass



SL748378

3 light bath bar in Brushed Nickel
27"W x 9"H x 9"Ext.
3 lights x 100W Med.
• alabaster style glass



SL748478

4 light bath bar in Brushed Nickel
36"W x 9"H x 9"Ext.
4 lights x 100W Med.
• alabaster style glass



SL748578

5 light bath bar in Brushed Nickel
46"W x 9"H x 9"Ext.
5 lights x 100W Med.
• alabaster style glass



SL748678

6 light bath bar in Brushed Nickel
55"W x 10"H x 9"Ext.
6 lights x 100W Med.
• alabaster style glass





PRESTIGE

SL854122

1 light wall sconce in Sable Bronze
8"W x 9"H x 10"Ext.
1 light x 100W Med.
• cognac edged glass



SL748222

2 light bath bar in Sable Bronze
17"W x 9"H x 9"Ext.
2 lights x 100W Med.
• cognac edged glass



SL748322

3 light bath bar in Sable Bronze
27"W x 9"H x 9"Ext.
3 lights x 100W Med.
• cognac edged glass



SL748422

4 light bath bar in Sable Bronze
36"W x 9"H x 9"Ext.
4 lights x 100W Med.
• cognac edged glass



SL748522

5 light bath bar in Sable Bronze
46"W x 9"H x 9"Ext.
5 lights x 100W Med.
• cognac edged glass



SL748622

6 light bath bar in Sable Bronze
55"W x 10"H x 9"Ext.
6 lights x 100W Med.
• cognac edged glass





TREME

TN0010217

1 light wall sconce in Brushed Nickel
5"W x 12"H x 8"Ext.
1 light x 100W Med.
• etched white glass



TV0019217

2 light bath in Brushed Nickel
14"W x 7"H x 7"Ext.
2 lights x 100W Med.
• etched white glass



TV0020217

3 light bath bar in Brushed Nickel
23"W x 7"H x 7"Ext.
3 lights x 100W Med.
• etched white glass



TV0021217

4 light bath bar in Brushed Nickel
32"W x 7"H x 7"Ext.
4 lights x 100W Med.
• etched white glass



TV0022217

5 light bath bar in Brushed Nickel
41"W x 7"H x 7"Ext.
5 lights x 100W Med.
• etched white glass



TREME

TN0010704

1 light wall sconce in Espresso
5"W x 12"H x 8"Ext.
1 light x 100W Med.
• champagne glass



TV0019704

2 light bath bar in Espresso
14"W x 7"H x 7"Ext.
2 lights x 100W Med.
• champagne glass



TV0020704

3 light bath bar in Espresso
23"W x 7"H x 7"Ext.
3 lights x 100W Med.
• champagne glass



TV0021704

4 light bath bar in Espresso
32"W x 7"H x 7"Ext.
4 lights x 100W Med.
• champagne glass



TV0022704

5 light bath bar in Espresso
41"W x 7"H x 7"Ext.
5 lights x 100W Med.
• champagne glass



symbol denotes up or down mounting

BATH

HAVEN

TN0009741



1 light wall sconce in Satin Pewter
5"W x 14"H x 6"Ext.
1 light x 100W Med.
• etched glass



TV0015741



2 light bath bar in Satin Pewter
18"W x 11"H x 7"Ext.
2 lights x 100W Med.
• etched glass



TV0016741



3 light bath bar in Satin Pewter
24"W x 11"H x 7"Ext.
3 lights x 100W Med.
• etched glass



TV0017741



4 light bath bar in Satin Pewter
30"W x 11"H x 7"Ext.
4 lights x 100W Med.
• etched glass



TV0018741



5 light bath bar in Satin Pewter
36"W x 11"H x 7"Ext.
5 lights x 100W Med.
• etched glass



HAVEN

TN0009704

1 light wall sconce in Espresso
5"W x 14"H x 6"Ext.
1 light x 100W Med.
• etched glass



TV0015704

2 light bath bar in Espresso
18"W x 11"H x 7"Ext.
2 lights x 100W Med.
• etched glass



TV0016704

3 light bath bar in Espresso
24"W x 11"H x 7"Ext.
3 lights x 100W Med.
• etched glass



TV0017704

4 light bath bar in Espresso
30"W x 11"H x 7"Ext.
4 lights x 100W Med.
• etched glass



TV0018704

5 light bath bar in Espresso
36"W x 11"H x 7"Ext.
5 lights x 100W Med.
• etched glass



symbol denotes up or down mounting

BATH

RAVENDALE

CN578172

- 1 light wall sconce in Brushed Nickel
- 5"W x 9"H x 7"Ext.
- 1 lights x 100W Med.
- opal white glass



CN578212

- 2 light bath bar in Brushed Nickel
- 12"W x 9"H x 7"Ext.
- 2 lights x 100W Med.
- opal white glass



CN578312

- 3 light bath bar in Brushed Nickel
- 20"W x 9"H x 7"Ext.
- 3 lights x 100W Med.
- opal white glass




CN578412

- 4 light bath bar in Brushed Nickel
- 27"W x 9"H x 7"Ext.
- 4 lights x 100W Med.
- opal white glass



BATH

 symbol denotes up or down mounting

RAVENDALE

CN578171

1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 7"Ext.
1 lights x 100W Med.
• opal white glass



CN578211

2 light bath bar in Oil Rubbed Bronze
12"W x 9"H x 7"Ext.
2 lights x 100W Med.
• opal white glass



CN578311

3 light bath bar in Oil Rubbed Bronze
20"W x 9"H x 7"Ext.
3 lights x 100W Med.
• opal white glass



CN578411

4 light bath bar in Oil Rubbed Bronze
27"W x 9"H x 7"Ext.
4 lights x 100W Med.
• opal white glass



BELMAR

CN575172

1 light wall sconce in Brushed Nickel
5"W x 9"H x 6"Ext.
1 light x 100W Med.
• opal white glass



CN575212

2 light bath bar in Brushed Nickel
13"W x 9"H x 6"Ext.
2 lights x 100W Med.
• opal white glass



CN575312

3 light bath bar in Brushed Nickel
22"W x 9"H x 6"Ext.
3 lights x 100W Med.
• opal white glass



CN575412

4 light bath bar in Brushed Nickel
31"W x 9"H x 6"Ext.
4 lights x 100W Med.
• opal white glass



BELMAR

CN575171

1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 6"Ext.
1 light x 100W Med.
• opal white glass



CN575211

2 light bath bar in Oil Rubbed Bronze
13"W x 9"H x 6"Ext.
2 lights x 100W Med.
• opal white glass



CN575311

3 light bath bar in Oil Rubbed Bronze
22"W x 9"H x 6"Ext.
3 lights x 100W Med.
• opal white glass



CN575411

4 light bath bar in Oil Rubbed Bronze
31"W x 9"H x 6"Ext.
4 lights x 100W Med.
• opal white glass



SUMMIT PLACE

CN579172

1 light wall sconce in Brushed Nickel
5"W x 9"H x 6"Ext.
1 lights x 100W Med.
• opal white glass



CN579212

2 light bath bar in Brushed Nickel
12"W x 8"H x 7"Ext.
2 lights x 100W Med.
• opal white glass



CN579312

3 light bath bar in Brushed Nickel
21"W x 9"H x 6"Ext.
3 lights x 100W Med.
• opal white glass



CN579412

4 light bath bar in Brushed Nickel
27"W x 9"H x 6"Ext.
4 lights x 100W Med.
• opal white glass



SUMMIT PLACE

CN579171

- 1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 6"Ext.
1 lights x 100W Med.
• opal white glass



CN579211

- 2 light bath bar in Oil Rubbed Bronze
12"W x 8"H x 7"Ext.
2 lights x 100W Med.
• opal white glass



CN579311

- 3 light bath bar in Oil Rubbed Bronze
21"W x 9"H x 6"Ext.
3 lights x 100W Med.
• opal white glass



CN579411

- 4 light bath bar in Oil Rubbed Bronze
27"W x 9"H x 6"Ext.
4 lights x 100W Med.
• opal white glass



symbol denotes up or down mounting

BATH

SINCLAIR

CN573171

1 light wall sconce in Brushed Nickel
5"W x 10"H x 5"Ext.
1 light x 100W Med.
• frosted white glass



CN573211

2 light bath bar in Brushed Nickel
15"W x 9"H x 6"Ext.
2 lights x 100W Med.
• frosted white glass



CN573311

3 light bath bar in Brushed Nickel
22"W x 9"H x 6"Ext.
3 lights x 100W Med.
• frosted white glass



CN573411

3 light bath bar in Brushed Nickel
30"W x 9"H x 6"Ext.
4 lights x 100W Med.
• frosted white glass



SINCLAIR

CN573172

1 light wall sconce in Polished Chrome

5"W x 10"H x 5"Ext.

1 light x 100W Med.

- frosted white glass



CN573212

2 light bath bar in Polished Chrome

15"W x 9"H x 6"Ext.

2 lights x 100W Med.

- frosted white glass



CN573312

3 light bath bar in Polished Chrome

22"W x 9"H x 6"Ext.

3 lights x 100W Med.

- frosted white glass



CN573412

3 light bath bar in Polished Chrome

30"W x 9"H x 6"Ext.

4 lights x 100W Med.

- frosted white glass



symbol denotes up or down mounting

BATH

CN570172

1 light wall sconce in Brushed Nickel
5"W x 9"H x 8"Ext.
1 lights x 100W Med.
• white glass



CN570212

2 light bath bar in Brushed Nickel
13"W x 9"H x 8"Ext.
2 lights x 100W Med.
• white glass



CN570312

3 light bath bar in Brushed Nickel
17"W x 9"H x 8"Ext.
3 lights x 100W Med.
• white glass



CN570412

4 light bath bar in Brushed Nickel
23"W x 9"H x 8"Ext.
4 lights x 100W Med.
• white glass



CALIFON

CN570171

1 light wall sconce in Oil Rubbed Bronze
5"W x 9"H x 8"Ext.
1 lights x 100W Med.
• white glass



CN570211

2 light bath bar in Oil Rubbed Bronze
13"W x 9"H x 8"Ext.
2 lights x 100W Med.
• white glass



CN570311

3 light bath bar in Oil Rubbed Bronze
17"W x 9"H x 8"Ext.
3 lights x 100W Med.
• white glass



CN570411

4 light bath bar in Oil Rubbed Bronze
23"W x 9"H x 8"Ext.
4 lights x 100W Med.
• white glass



HOMESTEAD - ALSO USED IN RIVA & TAHOE COLLECTIONS

SL758178

1 light wall sconce in Brushed Nickel
6"W x 12"H x 8"Ext.
1 light x 100W Med.
• alabaster style glass



SL758278

2 light bath bar in Brushed Nickel
18"W x 9"H x 8"Ext.
2 lights x 100W Med.
• alabaster style glass



SL758378

3 light bath bar in Brushed Nickel
24"W x 9"H x 8"Ext.
3 lights x 100W Med.
• alabaster style glass



SL758478

4 light bath bar in Brushed Nickel
30"W x 9"H x 8"Ext.
4 lights x 100W Med.
• alabaster style glass



SL758578

5 light bath bar in Brushed Nickel
36"W x 9"H x 8"Ext.
5 lights x 100W Med.
• alabaster style glass



SL758678

6 light bath bar in Brushed Nickel
48"W x 9"H x 8"Ext.
6 lights x 100W Med.
• alabaster style glass



HOMESTEAD

SL75824

2 light bath bar in Chrome
18"W x 9"H x 8"Ext.
2 lights x 100W Med.
• alabaster style glass



SL75834

3 light bath bar in Chrome
24"W x 9"H x 8"Ext.
3 lights x 100W Med.
• alabaster style glass



SL75844

4 light bath bar in Chrome
30"W x 9"H x 8"Ext.
4 lights x 100W Med.
• alabaster style glass



SL75854

5 light bath bar in Chrome
36"W x 9"H x 8"Ext.
5 lights x 100W Med.
• alabaster style glass



SL75864

6 light bath bar in Chrome
48"W x 9"H x 8"Ext.
6 lights x 100W Med.
• alabaster style glass



symbol denotes up or down mounting

BATH

HOMESTEAD - ALSO USED ON RIVA & TAHOE COLLECTIONS

SL758263

2 light bath bar in Painted Bronze
18"W x 9"H x 8"Ext.
2 lights x 100W Med.
• alabaster style glass



SL758363

3 light bath bar in Painted Bronze
24"W x 9"H x 8"Ext.
3 lights x 100W Med.
• alabaster style glass



SL758463

4 light bath bar in Painted Bronze
30"W x 9"H x 8"Ext.
4 lights x 100W Med.
• alabaster style glass



SL758563

5 light bath bar in Painted Bronze
36"W x 9"H x 8"Ext.
5 lights x 100W Med.
• alabaster style glass



SL758663

6 light bath in Painted Bronze
48"W x 9"H x 8"Ext.
6 lights x 100W Med.
• alabaster style glass



HOMESTEAD - ALSO USED ON WHITMORE COLLECTION

SL710341

3 light bath bar in Satin Pewter*
24"W x 9"H x 8"Ext.
3 lights x 100W Med.
• etched glass



SL710441

4 light bath bar in Satin Pewter*
30"W x 9"H x 8"Ext.
4 lights x 100W Med.
• etched glass



SL710323

3 light bath bar in Colonial Bronze
24"W x 9"H x 8"Ext.
3 lights x 100W Med.
• etched glass



SANTE FE

2201WS/10

1 light wall sconce in Oil Rubbed Bronze
6"W x 10"H x 9"Ext.
1 light x 100W Med.
• white glass



2202BB/10

2 light bath bar in Oil Rubbed Bronze
16"W x 9"H x 8"Ext.
2 lights x 100W Med.
• white glass



2203BB/10

3 light bath bar in Oil Rubbed Bronze
26"W x 9"H x 8"Ext.
3 lights x 100W Med.
• white glass



2204BB/10

4 light bath bar in Oil Rubbed Bronze
35"W x 9"H x 8"Ext.
4 lights x 100W Med.
• white glass



CHATHAM

1101WS/20

1 light wall sconce in Brushed Nickel
5"W x 19"H x 7"Ext.
1 light x 75W Med.
• white glass



1102BB/20



2 light bath bar in Brushed Nickel
14"W x 11"H x 7"Ext.
2 lights x 75W Med.
• white glass



1103BB/20



3 light bath bar in Brushed Nickel
23"W x 11"H x 7"Ext.
3 lights x 75W Med.
• white glass



1151WS/10

1 light wall sconce in Oil Rubbed Bronze
5"W x 19"H x 7"Ext.
1 light x 75W Med.
• white glass



1152BB/10



2 light bath bar in Oil Rubbed Bronze
14"W x 11"H x 7"Ext.
2 lights x 75W Med.
• white glass



1153BB/10



3 light bath bar in Oil Rubbed Bronze
23"W x 11"H x 7"Ext.
3 lights x 75W Med.
• white glass



symbol denotes up or down mounting

BATH

SUDBURY

5601BB/30

- 1 light wall sconce in Polished Chrome
- 6"W x 10"H x 8"Ext.
- 1 light x 75W Med.
- white glass



5602BB/30

- 2 light bath bar in Polished Chrome
- 15"W x 10"H x 8"Ext.
- 2 lights x 75W Med.
- white glass



5603BB/30

- 3 light bath bar in Polished Chrome
- 23"W x 10"H x 8"Ext.
- 3 lights x 75W Med.
- white glass



5604BB/30

- 4 light bath bar in Polished Chrome
- 32"W x 10"H x 8"Ext.
- 4 lights x 75W Med.
- white glass



SUDBURY

5601BB/20

1 light wall sconce in Brushed Nickel
6"W x 10"H x 8"Ext.
1 light x 75W Med.
• white glass



5603BB/20

3 light bath bar in Brushed Nickel
23"W x 10"H x 8"Ext.
3 lights x 75W Med.
• white glass



5604BB/20

4 light bath bar in Brushed Nickel
32"W x 10"H x 8"Ext.
4 lights x 75W Med.
• white glass



5651BB/10

1 light wall sconce in Oil Rubbed Bronze
6"W x 10"H x 8"Ext.
1 light x 75W Med.
• white glass



5652BB/10

2 light bath bar in Oil Rubbed Bronze
15"W x 10"H x 8"Ext.
2 lights x 75W Med.
• white glass



5653BB/10

3 light bath bar in Oil Rubbed Bronze
23"W x 10"H x 8"Ext.
3 lights x 75W Med.
• white glass



SHELBURNE

5501BB/20

1 light wall sconce in Brushed Nickel
8"W x 7"H x 9"Ext.
1 light x 75W Med.
• white etched glass



5502BB/20

2 light bath bar in Brushed Nickel
15"W x 6"H x 9"Ext.
2 lights x 75W Med.
• white etched glass



5503BB/20

3 light bath bar in Brushed Nickel
25"W x 6"H x 9"Ext.
3 lights x 75W Med.
• white etched glass



5504BB/20

4 light bath bar in Brushed Nickel
33"W x 6"H x 9"Ext.
4 lights x 75W Med.
• white etched glass



SHELBURNE

5501BB/30

- 1 light wall sconce in Polished Chrome
8"W x 7"H x 9"Ext.
1 light x 75W Med.
• white etched glass



5502BB/30

- 2 light bath bar in Polished Chrome
15"W x 6"H x 9"Ext.
2 lights x 75W Med.
• white etched glass



5503BB/30

- 3 light bath bar in Polished Chrome
25"W x 6"H x 9"Ext.
3 lights x 75W Med.
• white etched glass



5504BB/30

- 4 light bath bar in Polished Chrome
33"W x 6"H x 9"Ext.
4 lights x 75W Med.
• white etched glass



symbol denotes up or down mounting

BATH

SL706178

- 3 light bath bar in Brushed Nickel
 49"W x 5"H x 12"EXT
 3 lights x 32W F32T8 (32W)
- white acrylic diffuser
 - 120V electronic ballast



SL716578 ADA

2 light bath bar in Brushed Nickel

Model	Width	Body Height	HCO*	Ext. ends	No. Lights	Recom. Lamp
SL716578	25"	5"	2 1/2"	4"	2	F17T8 (17W)
SL716778	49"	5"	2 1/2"	4"	2	F32T8 (32W)

- white acrylic diffuser
- 120V electronic ballast



VANITY STRIPS



SL74134 3 LIGHT STRIP IN CHROME (SHOWN)

Width	Body Height	Ext. ends	No. Lights	Max. Watt.
18"	5"	3"	3	100W

- also available in **SL741378** Brushed Nickel



SL73244 4 LIGHT STRIP IN CHROME; BEVELED MIRROR

Width	Body Height	Ext. ends	No. Lights	Max. Watt.
25"	5"	3"	4	100W



SL74024 4 LIGHT STRIP IN CHROME (SHOWN)

Width	Body Height	Ext. ends	No. Lights	Max. Watt.
24"	5"	3"	4	100W

- also available in **SL74028** matte white and **SL740278** Brushed Nickel

SL741578 5 LIGHT STRIP IN BRUSHED NICKEL (SHOWN)

Width	Body Height	Ext. ends	No. Lights	Max. Watt.
30"	5"	3"	5	100W

- also available in **SL74154** Chrome



SL74184 6 LIGHT STRIP IN CHROME (SHOWN)

Width	Body Height	Ext. ends	No. Lights	Max. Watt.
36"	5"	3"	6	100W

- also available in **SL741878** Brushed Nickel



SL742578 8 LIGHT STRIP IN BRUSHED NICKEL (SHOWN)

Width	Body Height	Ext. ends	No. Lights	Max. Watt.
48"	5"	3"	8	100W

- also available in **SL74254** Chrome



BATH




LED MIRRORS

LED



1179-005



1179-003




1179-007

ITEM NO.	COLLECTION	BULB	W	H	EXT.	ADDITIONAL DETAILS
1179-003	Studio	8W-1100 Lumen LED (included)	20"	24"	2"	6000K, dimmable
1179-005	Runway	9W-1300 Lumen LED (included)	24"	32"	2"	6000K, dimmable
1179-007	Blabla	12W-1400 Lumen LED (included)	20"	28"	2"	6000K, dimmable

LED MIRRORS

LED



1179-002




1179-001


ITEM NO.	COLLECTION	BULB	W	H	EXT.	ADDITIONAL DETAILS
1179-001	Maison	12W-1300 Lumen LED (included)	20"	24"	2"	6000K, dimmable
1179-002	Maison	22W-2200 Lumen LED (included)	32"	40"	2"	6000K, dimmable

LED MIRRORS

LED



1179-006




1179-009


ITEM NO.	COLLECTION	BULB	W	H	EXT.	ADDITIONAL DETAILS
1179-006	Oval	12W-1400 Lumen LED (included)	24"	32"	2"	6000K, dimmable
1179-009	Skorpios	15W-1380 Lumen LED (included)	24"	32"	2"	3000K, 63 CRI, dimmable

LED MIRRORS

LED



1179-004



1179-008

ITEM NO.	COLLECTION	BULB	W	H	EXT.	ADDITIONAL DETAILS
1179-004	Montpellier	16W-1700 Lumen LED (included)	24"	32"	2"	6000K, dimmable
1179-008	Skorpios	18W-1656 Lumen LED (included)	24"	32"	2"	3000K, 63 CRI, dimmable

LED MIRRORS

TASK LIGHTING






TASK LIGHTING

AURORA Dimmable undercabinet lighting



	Product Code	Fixture Dimensions	Lamp
9"	UC180940 (White)	9"L x 3½"W x 1"D	5W integrated LED, 120D beam angle, 3000K, CRI 90+, 400 Lumens, On/Off switch
	UC180910 (Oil Rubbed Bronze)		
12"	UC181240 (White)	12"L x 3½"W x 1"D	6W integrated LED, 120D beam angle, 3000K, CRI 90+, 480 Lumens, On/Off switch
	UC181210 (Oil Rubbed Bronze)		
18"	UC181840 (White)	18"L x 3½"W x 1"D	9W integrated LED, 120D beam angle, 3000K, CRI 90+, 720 Lumens, On/Off switch
	UC181810 (Oil Rubbed Bronze)		
24"	UC182440 (White)	24"L x 3½"W x 1"D	11W integrated LED, 120D beam angle, 3000K, CRI 90+, 880 Lumens, On/Off switch
	UC182410 (Oil Rubbed Bronze)		
33"	UC183340 (White)	33"L x 3½"W x 1"D	13W integrated LED, 120D beam angle, 3000K, CRI 90+, 1000 Lumens, On/Off switch
	UC183310 (Oil Rubbed Bronze)		
42"	UC184240 (White)	42"L x 3½"W x 1"D	16W integrated LED, 120D beam angle, 3000K, CRI 90+, 1250 Lumens, On/Off switch
	UC184210 (Oil Rubbed Bronze)		

AURORA ACCESSORIES (NOT INCLUDED)



Product Code	Accessory	Product Code	Accessory	Product Code	Accessory
UCX00640 (White)	6" Connector Cord	UCX07040 (White)	70" Connector Cord	UCX99940 (White)	Junction Box
UCX00665 (Black)	6" Connector Cord	UCX07065 (Black)	70" Connector Cord	UCX99965 (Black)	Junction Box
UCX01240 (White)	12" Connector Cord	UCX00140 (White)	72" Connector Cord & Plug	UCX98888	Bag of 6 Romex Connectors
UCX01265 (Black)	12" Connector Cord	UCX00165 (Black)	72" Connector Cord & Plug		
UCX02440 (White)	24" Connector Cord	UCX00340 (White)	Close Connect Terminal	<i>Note: Accessories are available as a 6 pack. See price sheet.</i>	
UCX02465 (Black)	24" Connector Cord	UCX00365 (Black)	Close Connect Terminal		

TASK LIGHTING




ZEELED PRO linear lighting



Product Code	Fixture Dimensions	Lamp
LV012RSF (White) 12" ZeeLED Pro	12" W x 4" D x 1" H	6W LED, 3000K, 4000K & 6000K mode switch, CRI 90 450 Lumens, Dimmable, High/Low switch
LV018RSF (White) 18" ZeeLED Pro	18" W x 4" D x 1" H	9W LED, 3000K, 4000K & 6000K mode switch, CRI 90 550 Lumens, Dimmable, High/Low switch
LV024RSF (White) 24" ZeeLED Pro	24" W x 4" D x 1" H	12W LED, 3000K, 4000K & 6000K mode switch, CRI 90 750 Lumens, Dimmable, High/Low switch
LV032RSF (White) 32" ZeeLED Pro	32" W x 4" D x 1" H	16W LED, 3000K, 4000K & 6000K mode switch, CRI 90 1000 Lumens, Dimmable, High/Low switch

EACH FIXTURE INCLUDES:



ZeeStick Inline
Connector
ZSBUTT-N-30 (White)

ZeeStick 12" Flexible
Joiner
ZSCON12-N-30
(White)

ZeeStick 24" Flexible
Joiner for Hardwire
ZSCON24-N-30 (White)

ZeeStick 72" Cord
and Plug
ZSPUG-N-30 (White)

TASK LIGHTING

ZEELINE line voltage xenon linear lighting



White

All the benefits of Alico's famous Zeeline but as a 120V line-voltage fixture.

PRODUCT HIGHLIGHTS

- More diffuse glass
- Easy-to-use friction clips for door release
- Captioned door provides easy lamp and installation access
- Mounting screws come captioned and ready to install
- Wiring assembly is easily accessed via captioned wing nuts
- Standard 1/2" knockouts for wiring
- Easy-to-use High/Off/Low switch
- Xenon lamp technology
- Installs in minutes.

PERFORMANCE NOTES


- To obtain a uniform light, space units 10" apart
- Position opening toward front of cabinet

Lamp (included)
25W 120V wedge based xenon
Indoor use only



Bronze

Install 10" apart and 7K" from backsplash for even illumination.



	Product Code	Fixture Dimensions	Lamp
9"	ZL009RSF (White)	9"L x 4 3/4"W x 1 5/16"D	25W 120V wedge base xenon included
	ZL309RSF (Bronze)		L9 Replacement Lamp
17"	ZL017RSF (White)	17 1/2"L x 4 3/4"W x 1 5/16"D	2 x 25W 120V wedge base xenon included
	ZL317RSF (Bronze)		L9 Replacement Lamp
26"	ZL026RSF (White)	26"L x 4 3/4"W x 1 5/16"D	3 x 25W 120V wedge base xenon included
	ZL326RSF (Bronze)		L9 Replacement Lamp
34"	ZL035RSF (White)	34 1/2" W x 4 3/4"W x 1 5/16"D	4 x 25W 120V wedge base xenon included
	ZL335RSF (Bronze)		L9 Replacement Lamp
48"	ZL048RSF (White)	48" W x 4 3/4"W x 1 5/16"D	5 x 25W 120V wedge base xenon included
	ZL348RSF (Bronze)		L9 Replacement Lamp

MLE301-5-16M **LED**

TUXEDO

puk light in Satin Nickel
2¾"W x 1"H
4WLED, 3000K, CRI 80
200 Lumens, Dimmable
includes:

- 1x puk + 1 connector included
- 1x 6' power cord with plug and line switch



MLE313-5-16MK **LED**

TUXEDO

3 puk light in Satin Nickel
2¾"W x 1"H
3 x 4WLED, 3000K, CRI 80
600 Lumens, Dimmable
includes:

- 1x puk with 1 connector
- 2 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 2 x 6" jumper cords

Mounting distance between pucks:
12-18"; maximum of 20 pucks can be
joined together; Join the 6" connectors
together for 12" or add the (included)
6" jumper between for 18"



MLE301-5-30 **LED**

TUXEDO

puk light in White
2¾"W x 1"H
4WLED, 3000K, CRI 80
200 Lumens, Dimmable
includes:

- 1x puk + 1 connector included
- 1x 6' power cord with plug and line switch



MLE313-5-30K **LED**

TUXEDO

3 puk light in White
3"W x 1"H
2¾ x 4WLED, 3000K, CRI 80
600 Lumens, Dimmable
includes:

- 1x puk with 1 connector
- 2 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 2 x 6" jumper cords

Mounting distance between pucks:
12-18"; maximum of 20 pucks can be
joined together; Join the 6" connectors
together for 12" or add the (included)
6" jumper between for 18"



MLE301-5-31 **LED**

TUXEDO

puk light in Black
2¾"W x 1"H
4WLED, 3000K, CRI 80
200 Lumens, Dimmable
includes:

- 1x puk + 1 connector included
- 1x 6' power cord with plug and line switch



MLE313-5-31K **LED**

TUXEDO

3 puk light in Black
2¾"W x 1"H
3 x 4WLED, 3000K, CRI 80
600 Lumens, Dimmable
includes:

- 1x puk with 1 connector
- 2 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 2 x 6" jumper cords

Mounting distance between pucks:
12-18"; maximum of 20 pucks can be
joined together; Join the 6" connectors
together for 12" or add the (included)
6" jumper between for 18"



TASK LIGHTING

MLE201-5-16M **LED**

TUXEDO

puk light in Satin Nickel
2¾"W x 1"H
4WLED, 3000K, CRI 80
200 Lumens, Dimmable
includes:

- 1x puk + 2 connectors included



MLE201-5-30 **LED**

TUXEDO

puk light in White
2¾"W x 1"H
4WLED, 3000K, CRI 80
200 Lumens, Dimmable
includes:

- 1x puk + 2 connectors included



MLE201-5-31 **LED**

TUXEDO

puk light in White
2¾"W x 1"H
4WLED, 3000K, CRI 80
200 Lumens, Dimmable
includes:

- 1x puk + 2 connectors included



MLE316-5-16MK **LED**

TUXEDO

6 puk light in Satin Nickel
2¾"W x 1"H
6 x 4WLED, 3000K, CRI 80
1200 Lumens, Dimmable
includes:

- 1x puk with 1 connector
- 5 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 5 x 6" jumper cords

Mounting distance between pucks:
12-18"; maximum of 20 pucks can
be joined together; Join the 6"
connectors together for 12" or add
the (included) 6" jumper between
for 18"



MLE316-5-30K **LED**

TUXEDO

6 puk light in White
2¾"W x 1"H
6 x 4WLED, 3000K, CRI 80
1200 Lumens, Dimmable
includes:

- 1x puk with 1 connector
- 5 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 5 x 6" jumper cords

Mounting distance between pucks:
12-18"; maximum of 20 pucks can
be joined together; Join the 6"
connectors together for 12" or add the (included)
6" jumper between for 18"



MLE316-5-31K **LED**

TUXEDO

6 puk light in Black
2¾"W x 1"H
6 x 4WLED, 3000K, CRI 80
1200 Lumens, Dimmable
includes:

- 1x puk with 1 connector
- 5 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 5 x 6" jumper cords

Mounting distance between pucks:
12-18"; maximum of 20 pucks can
be joined together; Join the 6"
connectors together for 12" or add the (included)
6" jumper between for 18"



TASK LIGHTING

MLE423-5-16MK**LED**

TUXEDO SWIVEL

puk light in Satin Nickel

2¾"W x 1"H

4WLED, 3000K, CRI 80

200 Lumens, Dimmable

includes:

- 1x puk + 1 connector included
- 1x 6' power cord with plug and line switch

**MLE433-5-16MK****LED**

TUXEDO SWIVEL

3 puk light in Satin Nickel

2¾"W x 1"H

3 x 4WLED, 3000K, CRI 80

600 Lumens, Dimmable

includes:

- 1x puk with 1 connector
- 2 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 2 x 6" jumper cords

Mounting distance between pucks:
12-18"; maximum of 20 pucks can be
joined together; Join the 6" connectors
together for 12" or add the (included)
6" jumper between for 18"

**MLE423-5-30K****LED**

TUXEDO SWIVEL

puk light in White

2¾"W x 1"H

4WLED, 3000K, CRI 80

200 Lumens, Dimmable

includes:

- 1x puk + 1 connector included
- 1x 6' power cord with plug and line switch

**MLE433-5-30K****LED**

TUXEDO SWIVEL

3 puk light in White

2¾"W x 1"H

3 x 4WLED, 3000K, CRI 80

600 Lumens, Dimmable

includes:

- 1x puk with 1 connector
- 2 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 2 x 6" jumper cords

Mounting distance between pucks:
12-18"; maximum of 20 pucks can be
joined together; Join the 6" connectors
together for 12" or add the (included)
6" jumper between for 18"

**MLE423-5-31K****LED**

TUXEDO SWIVEL

puk light in Black

2¾"W x 1"H

4WLED, 3000K, CRI 80

200 Lumens, Dimmable

includes:

- 1x puk + 1 connector included
- 1x 6' power cord with plug and line switch

**MLE433-5-31K****LED**

TUXEDO SWIVEL

3 puk light in Black

2¾"W x 1"H

3 x 4WLED, 3000K, CRI 80

600 Lumens, Dimmable

includes:

- 1x puk with 1 connector
- 2 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 2 x 6" jumper cords

Mounting distance between pucks:
12-18"; maximum of 20 pucks can be
joined together; Join the 6" connectors
together for 12" or add the (included)
6" jumper between for 18"



TASK LIGHTING

MLE401-5-16M**LED**

TUXEDO SWIVEL

puk light in Satin Nickel

2¾"W x 1"H

4WLED, 3000K, CRI 80

200 Lumens, Dimmable

includes:

- 1x puk + 2 connectors included

**MLE401-5-30****LED**

TUXEDO SWIVEL

puk light in White

2¾"W x 1"H

4WLED, 3000K, CRI 80

200 Lumens, Dimmable

includes:

- 1x puk + 2 connectors included

**MLE401-5-31****LED**

TUXEDO SWIVEL

puk light in White

2¾"W x 1"H

4WLED, 3000K, CRI 80

200 Lumens, Dimmable

includes:

- 1x puk + 2 connectors included

**MLE426-5-16MK****LED**

TUXEDO SWIVEL

6 puk light in Satin Nickel

3"W x 1"H

6 x 4WLED, 3000K, CRI 80

1200 Lumens, Dimmable

includes:

- 1x puk with 1 connector
- 5 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 5 x 6" jumper cords

Mounting distance between pucks: 12-18"; maximum of 20 pucks can be joined together; Join the 6" connectors together for 12" or add the (included) 6" jumper between for 18"

**MLE426-5-30K****LED**

TUXEDO SWIVEL

6 puk light in White

3"W x 1"H

6 x 4WLED, 3000K, CRI 80

1200 Lumens, Dimmable

includes:

- 1x puk with 1 connector
- 5 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 5 x 6" jumper cords

Mounting distance between pucks: 12-18"; maximum of 20 pucks can be joined together; Join the 6" connectors together for 12" or add the (included) 6" jumper between for 18"

**MLE426-5-31K****LED**

TUXEDO SWIVEL

6 puk light in Black

3"W x 1"H

6 x 4WLED, 3000K, CRI 80

1200 Lumens, Dimmable

includes:

- 1x puk with 1 connector
- 5 x pucks with 2 connectors
- 1 x 6' power cord with plug and line switch
- 5 x 6" jumper cords

Mounting distance between pucks: 12-18"; maximum of 20 pucks can be joined together; Join the 6" connectors together for 12" or add the (included) 6" jumper between for 18"

**TASK LIGHTING**

PARTS AND ACCESSORIES

ACLJB-N-30

hardwire junction box for PUK light

2"W x 1"H

- White



ACL24-N-30

jumper cord for PUK lights

24" length

- White



ACL12-N-30

jumper cord for PUK lights

12" length

- White



ACL36-N-30

jumper cord for PUK lights

36" length

- White



ACL18-N-30

jumper cord

18" length

- White



TASK LIGHTING

ZEESTICK LEDPRO **LED**

linear lighting

FULLY INTEGRATED, MODULAR, CONTINUOUS

ZeeStick is a SMD powered, fully encapsulated and Dimmable family of LED fixtures that enable a myriad of task, undercabinet, cove and accent lighting applications. As a fully integrated, energy conscious linear lighting solution, ZeeStick has no equal.

FEATURES

- 120V AC
- Only 4.2W per foot
- Available in three color temperatures–
 - 2700K Warm White
 - 3500K Natural White
 - 6000K Pure White (special order)
- SMD LED Hi Power Factor
- Integral driver built into every fixture
- Available in four sizes–
 - 12" (5W)
 - 23-3/4" (10W)
 - 39-1/2" (14W)
 - 47-3/8" (18W)

ZeeStick enables the architect and lighting designer the ability to create various applications utilizing a common color temperature. Even the slightest difference in kelvin temperature can create a visual imbalance that may subtly challenge the esthetics of your interior. Using ZeeStick in a combination of applications within the same space will help to successfully create a lighting solution across several platforms while achieving unity in color temperature. Thanks to a full complement of custom connectors and joiners, ZeeStick is able to achieve longer runs. Inline connectors eliminate cold spots and provide a seamless installation. With the addition of a custom joiner box and ZeeStick cord and plug, installation can be as close as the nearest outlet.



TASK LIGHTING

ZEESTICK LED linear lighting **LED**

SPECIFICATIONS

ZeeStick is a modular line of Dimmable SMD LEDs soldered to a rigid PC board with integral driver, encapsulated in an extruded aluminum SP body with CF color (White) and polycarbonate frosted diffuser lens. ZeeStick is designed to provide a long and consistent color over its 50,000 hour lamp life due to superior thermal management of the SMD's and quality phosphors used in production. ZeeStick provides an even glow at a huge energy savings over linear fluorescent or halogen.

- 120V AC
- 4.2W per Foot
- ROHS Compliant
- ETL Approved



LED Specs:

Color Temp.	Lumens per Watt	Lumens per Foot	Total CRI
2700K	41	202	73
4000K	48	240	75
6000K	63	316	78

ZEESTICK ACCESSORIES



ZeeStick Inline Connector
ZSBUTT-N-30 (White)



ZeeStick 12" Flexible Joiner
ZSCON12-N-30 (White)



ZeeStick 24" Flexible Joiner for Hardwire
ZSCON24-N-30 (White)



ZeeStick 72" Cord and Plug
ZSPUG-N-30 (White)



ZeeStick 120V Wiring Box
ZSBOX-N-30 (White)



ZeeStick LED T-Shaped Connector
4W LED, 220 Lumens
Non-Dimmable
ZST-N-98 (Aluminum)



ZeeStick LED L-Shaped Connector, Left Handed
2W LED, 160 Lumens
Non-Dimmable
ZSL-N-98 (Aluminum)



ZeeStick LED L-Shaped Connector, Right Handed
2W LED, 160 Lumens
Non-Dimmable
ZSR-N-98 (Aluminum)



ZeeStick 90 Degree Clip
ZS-CLIP90-N-15 (Chrome)



ZeeStick Adjustable Clip
ZS-CLIPADJ-N-15 (Chrome)

TASK LIGHTING

ZEESTICK ordering information **LED**



ZeeStick 120V - 5W Linear Lensed SMD LED Fixture*

Cat. No.	Length	Wattage	Color	Lumens	Color Temp.
ZS303RSF	12"	5W	White	202	2700K
ZS403RSF	12"	5W	White	240	4000K
ZS603RSF	12"	5W	White	316	6000K



ZeeStick 120V - 10W Linear Lensed SMD LED Fixture*

Cat. No.	Length	Wattage	Color	Lumens	Color Temp.
ZS306RSF	23 ³ / ₄ "	10W	White	404	2700K
ZS406RSF	23 ³ / ₄ "	10W	White	480	4000K
ZS606RSF	23 ³ / ₄ "	10W	White	632	6000K



ZeeStick 120V - 14W Linear Lensed SMD LED Fixture*


Cat. No.	Length	Wattage	Color	Lumens	Color Temp.
ZS310RSF	39 ¹ / ₂ "	14W	White	606	2700K
ZS410RSF	39 ¹ / ₂ "	14W	White	720	4000K
ZS610RSF	39 ¹ / ₂ "	14W	White	948	6000K



ZeeStick 120V - 18W Linear Lensed SMD LED Fixture*

Cat. No.	Length	Wattage	Color	Lumens	Color Temp.
ZS312RSF	47 ³ / ₈ "	18W	White	808	2700K
ZS412RSF	47 ³ / ₈ "	18W	White	960	4000K
ZS612RSF	47 ³ / ₈ "	18W	White	1264	6000K

* Each fixture comes with (2) mounting clips, (1) inline connector and (1) power connector for hardwire. See NOTE below.



NOTE: Zee-Stick comes complete with standard spring metal brackets and screws. CUSTOM ANGLED BRACKETS ARE AVAILABLE. Consult factory. Interconnectable utilizing Alico ZeeStick connectors. Maximum run per feed is 12 units un-dimmed, six units dimmed.

TASK LIGHTING

ZEESTICK LED linear lighting

APPLICATIONS

ZeeStick is an architectural quality luminaire that was manufactured for the following applications and environments:

- Undercabinet Lighting
- Cove Lighting
- Toe Kick
- Task
- Architectural Detail
- Food Prep and Buffet
- Hospitality
- Entertainment Unit
- Linear Recessed
- Bath and Vanity
- Retail and Display
- Institutional



PHOTOMETRICS

ZeeSTICK 120V - 5W LINEAR LENSED SMD LED FIXTURE

Category	Result
TOTAL LUMENS	350.16
INPUT VOLTAGE (VAC)	120.00
INPUT CURRENT (AMP)	0.05
INPUT POWER (W)	4.82
INPUT POWER FACTOR	0.79
EFFICACY	72.66
COLOR RENDERING INDEX (CRI)	74.85

ZeeSTICK 120V - 10W LINEAR LENSED SMD LED FIXTURE

Category	Result
TOTAL LUMENS	694.38
INPUT VOLTAGE (VAC)	120.00
INPUT CURRENT (AMP)	0.09
INPUT POWER (W)	9.21
INPUT POWER FACTOR	0.89
EFFICACY	75.43
COLOR RENDERING INDEX (CRI)	74.59

ZeeSTICK 120V - 14W LINEAR LENSED SMD LED FIXTURE

Category	Result
TOTAL LUMENS	1012.06
INPUT VOLTAGE (VAC)	120.00
INPUT CURRENT (AMP)	0.12
INPUT POWER (W)	12.53
INPUT POWER FACTOR	0.85
EFFICACY	80.75
COLOR RENDERING INDEX (CRI)	74.85

ZeeSTICK 120V - 18W LINEAR LENSED SMD LED FIXTURE

Category	Result
TOTAL LUMENS	1273.78
INPUT VOLTAGE (VAC)	120.00
INPUT CURRENT (AMP)	0.16
INPUT POWER (W)	16.62
INPUT POWER FACTOR	0.88
EFFICACY	76.64
COLOR RENDERING INDEX (CRI)	74.67

TASK LIGHTING



RECESSED

DIMMABLE LED FULLY ENCLOSED TRIMS



LR10044

MERCURY
4" round led recessed, White in White
5"W x 2"H x 5" Ext. x 11W
3000K, 90CRI
11W, 700 Lumens



LR11044

MERCURY
4" square led recessed, White in White
5"W x 2"H x 5" Ext. x 9W
3000K, 90CRI
9W, 700 Lumens



LR0004X

MERCURY
4" new construction recess frame hole size diameter
106MM



LR10064

MERCURY
6" round led recessed, White in White
7"W x 2"H x 7" Ext. x 15W
3000K, 90CRI,
15W, 1200 Lumens



LR11064

MERCURY
6" square led recessed, White in White
7"W x 2"H x 7" Ext. x 17.2
3000K, 90CRI
17W, 1200 Lumens



LR0006X

MERCURY
6" new construction recess frame hole size diameter
160MM

RECESSED

Lamp wattages noted on this page are typical for most applications. Some housing and trim combinations may vary. Consult label inside individual housing for specific wattage.

MLE1100-5-30**LED**

AXEL

small recess mount retrofit in white

5"W x 2"H

9WLED, 3000K, 90CRI

550 Lumens, Dimmable

includes:

- adjustable 5" and 6" can option
- cutout 5"
- can be hardwired

MLE1101-5-30**LED**

AXEL

large recess mount retrofit in white

7"W x 2"H

15WLED, 3000K, 90CRI

850 Lumens, Dimmable

includes:

- adjustable 5" and 6" can option
- cutout 6"
- can be hardwired

**MLE1200-5-30****W****LED**

PLANDOME

Dimmable surface mount in white

3000K, CRI 90

5"W x 1"H

9W Integrated LED, 550 Lumens

Note: For Installation into Recessed Lighting Fixture or Junction Box

MLE1500-5-30**W****LED**

PLANDOME

Dimmable surface mount in white

3000K, CRI 90

6"W x 1"H

12W Integrated LED, 850 Lumens, Dimmable

Note: For Installation into Junction Box Only

**MLE1201-5-30****W****LED**

PLANDOME

Dimmable surface mount in white

3000K, CRI 90

7"W x 1"H

15W Integrated LED, 850 Lumens,

Note: For Installation into Recessed Lighting Fixture or Junction Box

MLE1550-5-30**W****LED**

PLANDOME

Dimmable surface mount in white

3000K, CRI 90

6"W x 1"H

18 Integrated WLED, 1200 Lumens,

Note: For Installation into Junction Box Only

**LA100**

RECESSED LIGHTING CONVERSION KIT
bulb lighting accessory in silver
8"W x 8"H x 1" Ext.

- Adapter screws into a medium base
- recessed socket, making it ready to
- install a light fixture (up to 5 lbs.)
- •No assembly required
- •No need for an electrician
- •No costly & messy construction
- •No painting or finish work
- •No Hassle



Lamp wattages noted on this page are typical for most applications. Some housing and trim combinations may vary. Consult label inside individual housing for specific wattage.

RECESSED

6" AIR SEAL IC/NON-IC HOUSINGS



PS1

90 watt/150 watt
Depth 7½"
Length 10½"
Width 6½"
Ceiling Open 6½"

- for new construction
- air Seal
- type-IC or non-IC
- inter-locking bar hangers with pre-positioned nails

PS1NSP

Same features as **PS1**, except provided without a socket plate. For use in installations where TRB style fully enclosed eyeball or IC shower trims are used exclusively. Eliminates the need for the installer to remove the socket plate.

PS1NSPQC

Same as **PS1NSP**, except provided with pre-installed quick-connect wire terminals.



PS1CP

Contractor Pack

Includes: Four **PS1** housings and four **TRM30W** white baffle trims

UL/CUL Listed Convertible IC/non-IC



Type-IC
Suitable for direct contact with thermal insulation. Up to 90 watt maximum lamp when used with **TRB30** trim



Non-IC
For use in non-insulated areas, or when insulation is kept at least 3" away. Up to 150 watt maximum lamp.

Compatible with all Thomas 6" trims.



Adjustable socket plate provides consistent lamp placement when used with open or baffle trims.



The socket plate is removable for use with fully enclosed, eyeball, or IC shower trims. (Specify **PS1NSP** for optional version provided without the socket plate.)

6" FULLY ENCLOSED TRIMS



TR30BN

BRUSHED NICKEL OPEN TRIM

Lamp	IC		Outside Diam.
	Max. Watt	Max. Watt	
R30	65	75	8"

PS9 Compatible



TR30W

WHITE OPEN TRIM

Lamp	IC		Outside Diam.
	Max. Watt	Max. Watt	
R30	65	75	8"

PS9 Compatible



TR40W

WHITE OPEN TRIM

Lamp	IC		Outside Diam.
	Max. Watt	Max. Watt	
R40	N/A	150	8"

RECESSED

Lamp wattages noted on this page are typical for most applications. Some housing and trim combinations may vary. Consult label inside individual housing for specific wattage.

6" FULLY ENCLOSED TRIMS



TRB30

BLACK BAFFLE

Lamp	IC		Outside Diam.
	Max. Watt	Max. Watt	
R30	75	75	8"
PAR30	50	75	8"
PAR30LN	75	75	8"
PAR38	90	150	8"



TRB30W

WHITE BAFFLE


Lamp	IC		Outside Diam.
	Max. Watt	Max. Watt	
R30	75	75	8"
PAR30	50	75	8"
PAR30LN	75	75	8"
PAR38	90	150	8"




TRS30W

WHITE SPLAY

Lamp	IC		Outside Diam.
	Max. Watt	Max. Watt	
R30	75	75	8"
PAR30	75	75	8"



Fully enclosed trims also support the socket and lamp, so the socket plate must be removed prior to installation. (Or use NSP version.)



Standard 6" trims use coil springs to attach to the socket plate inside the housing. They are independent of the lamp position, and may not be used with any NSP housing.

6" STANDARD TRIMS



TRM30

BLACK BAFFLE

Lamp	IC		Outside Diam.
	Max. Watt	Max. Watt	
R30	75	100	8"
PAR30	50	75	8"
PS9 Compatible			



TRM30W

WHITE BAFFLE

Lamp	IC		Outside Diam.
	Max. Watt	Max. Watt	
R30	75	100	8"
PAR30	50	75	8"
PS9 Compatible			



THS30CLR

CLEAR REFLECTOR TRIM

Lamp	IC		Outside Diam.
	Max. Watt	Max. Watt	
R30	75	100	8"
PAR30	50	75	8"
PS9 Compatible			

Lamp wattages noted on this page are typical for most applications. Some housing and trim combinations may vary. Consult label inside individual housing for specific wattage.

RECESSED

6" DIRECTIONAL TRIM

TR18W

WHITE EYEBALL

Lamp	IC Max. Watt	non-IC Max. Watt	Outside Diam.
R30	75	75	8"

PS9 Compatible



TR18BN

BRUSHED NICKEL EYEBALL

Lamp	IC Max. Watt	non-IC Max. Watt	Outside Diam.
R30	75	75	8"

PS9 Compatible



6" IC SHOWER TRIMS

All shower trims are rated for wet locations. IC shower trims include a reflector which also supports the socket. Use with NSP housings or remove the socket plate from standard housings.



TR6SHR

WHITE OPEN SHOWER TRIM

For IC or non-IC applications.

Lamp	IC Max. Watt	non-IC Max. Watt	Outside Diam.
PAR38	90	90	8"



TSH12IC

WHITE ALBALITE SHOWER TRIM

with metal trim ring with reflector, for IC applications.

Lamp	IC Max. Watt	non-IC Max. Watt	Outside Diam.
A19	25	N/A	8"



TSH16IC

WHITE DROP OPAL SHOWER TRIM

with metal trim ring, with reflector, for IC applications.

Lamp	IC Max. Watt	non-IC Max. Watt	Outside Diam.
A19	40	N/A	8"

6" NON-IC SHOWER TRIMS

Non-IC shower trims do not include a reflector. The housing must have a socket plate. Not suitable for use with NSP housings.

TSH12

WHITE ALBALITE SHOWER TRIM

Aluminum trim ring, no reflector, for non-IC applications.

Lamp	IC Max. Watt	non-IC Max. Watt	Outside Diam.
A19	N/A	60	8"

PS9 Compatible



TSH16

WHITE DROP OPAL SHOWER TRIM

Aluminum trim ring, no reflector, for non-IC applications.

Lamp	IC Max. Watt	non-IC Max. Watt	Outside Diam.
A19	N/A	60	8"

PS9 Compatible



RECESSED

Lamp wattages noted on this page are typical for most applications. Some housing and trim combinations may vary. Consult label inside individual housing for specific wattage.



Higher wattages for non-insulated areas are revealed by peeling off one label.



Large junction box provides four Romex and five conduit knockouts. Listed for through-branch circuit conductors. Cover is hinged to prevent accidental loss.



Includes die-cut plaster shield to protect inside of housing during construction.



PS1RM

90 watt/150 watt

Depth 7½"

Width 6½"

Ceiling Open 6¼"

- for remodel construction
- air Seal
- type-IC or non-IC
- mounts to existing ceilings from ½" to 1¼" thick

6" NON-IC SHALLOW HOUSING

Some trims are not compatible with the PS9. Use only trims specifically noted on pages 268 and 269.



Shallow

PS9

75 watt

Depth 5⅜"

Length 10½"

Width 6½"

Ceiling Open ½"

- for new construction
- non-IC
- inter-locking bar hangers with pre-positioned nails

Lamp wattages noted on this page are typical for most applications. Some housing and trim combinations may vary. Consult label inside individual housing for specific wattage.

RECESSED

5" HOUSINGS



PS5

75 watt
 Depth 8"
 Length 10"
 Width 6"
 Ceiling Open 6"

- for new construction
- air Seal
- type-IC or non-IC
- inter-locking bar hangers with pre-positioned nails



PS5RM

75 watt
 Depth 8"
 Width 6"
 Ceiling Open 6"

- For remodel construction
- Air Seal
- Type-IC or non-IC
- Mounts to existing ceilings
- from 1/2" to 1 1/4" thick

5" TRIMS



TR238W

WHITE BAFFLE

Lamp	IC		Outside Diam.
	Max. Watt	Max. Watt	
R20	50	50	6"
PAR20	50	50	6"
R30	75	75	6"



TR132W

WHITE OPEN TRIM

Lamp	IC		Outside Diam.
	Max. Watt	Max. Watt	
R30	75	75	7"
PAR30	75	75	7"
PAR30LN	75	75	7"



TR139W

WHITE SURFACE GIMBAL

Lamp	IC		Outside Diam.
	Max. Watt	Max. Watt	
PAR30	50	75	7"



TR221W

White Eyeball

Lamp	IC		Outside Diam.
	Max. Watt	Max. Watt	
R20	50	50	7"
PAR20	50	50	7"

RECESSED

Lamp wattages noted on this page are typical for most applications. Some housing and trim combinations may vary. Consult label inside individual housing for specific wattage.

4" HOUSINGS



PS4

- 55 watt
 Depth 6"
 Length 8"
 Width 6"
 Ceiling Open 5"
- for new construction
 - non-IC
 - inter-locking bar hangers with pre-positioned nails



PS4RM

- 55 watt
 Depth 6"
 Width 5"
 Ceiling Open 5"
- For remodel construction
 - Non-IC
 - Mounts to existing ceilings from 1/2" to 1 1/4" thick

4" TRIMS



TR401W

WHITE STEP BAFFLE

Lamp	non-IC	
	Max. Watt	Outside Diam.
R20	50	5"
PAR20	50	5"
PAR16	55	5"

TR401

BLACK STEP BAFFLE

Lamp	non-IC	
	Max. Watt	Outside Diam.
R20	50	5"
PAR20	50	5"
PAR16	55	5"

TR408

WHITE EYEBALL

Lamp	non-IC	
	Max. Watt	Outside Diam.
R20	50	5"
PAR20	50	5"
PAR16	55	5"

HOUSING AND TRIM KITS FOR NON-INSULATED CEILINGS



DY6408

WHITE OPEN TRIM
 75W R30 lamp, Outside diameter 8"



DY64098

WHITE BAFFLE TRIM
 50W R20 lamp, Outside diameter 6"



DY6410


WHITE EYEBALL TRIM
 50W R20 lamp, Outside diameter 8"

- 5" kits include housing and trim. (6" ceiling opening)
- for new and remodel construction
 - bar hangers not included

Lamp wattages noted on this page are typical for most applications. Some housing and trim combinations may vary. Consult label inside individual housing for specific wattage.

RECESSED

STEP LIGHTING



EZ STEP LED steplight **LED** **ADA**

When it comes to installation ease and personal safety, the EZ Step™ really fits the bill. This innovative LED uses 0.7 watts of energy, and can be installed into any standard single gang outlet box for an attractive lighting solution. Use it in stairways, hallways and corridors; anywhere in your home or office where an added safety or accent light may be needed. Indoor use only. ADA approved product.



EZ STEP LED Double Round steplight for indoor use only

WLE105DR32K-10-98 Brushed Aluminum

WLE105DR32K-10-30 White

WLE105DR32K-10-B Bronze

1 x 0.7W LED, 3200K (CCT)

12VDC 250mA LED Class II Electronic Driver included

surface dimensions

3"W x 7/8"D x 4 7/8"H

BEACON steplight **LED** **ADA**

Whether to amplify outdoor entertainment areas or simply improve the safety and appearance of an indoor stairwell, our Beacon series LED steplights add a sleek aesthetic and inviting glow to any design space. Soothing Opal White lens. Available in Black, White, Brown and Aluminum. Uses standard outlet box. Indoor and Outdoor use.



Product Code	Fixture Dimensions	Lamp
WLE1105C30K-10-30 (White) Steplight Opal White Glass	3" W x .4" D x 5" H	3W LED, 3000K, 80 CRI 264 Lumens, Dimmable
WLE1105C30K-10-31 (Black) Steplight Opal White Glass	3" W x .4" D x 5" H	3W LED, 3000K, 80 CRI 264 Lumens, Dimmable
WLE1105C30K-10-45 (Brown) Steplight Opal White Glass	3" W x .4" D x 5" H	3W LED, 3000K, 80 CRI 264 Lumens, Dimmable
WLE1105C30K-10-98 (Aluminum) Steplight Opal White Glass	3" W x .4" D x 5" H	3W LED, 3000K, 80 CRI 264 Lumens, Dimmable

APERTURE steplight **LED** **ADA**

Whether to amplify outdoor entertainment areas or simply improve the safety and appearance of an indoor stairwell, our Aperture series LED steplights add a sleek aesthetic and inviting glow to any design space. Attractive finely-ridged aperture with Opal White lens. Choose from Black, White, Brown, or Aluminum finishes. Uses standard outlet box. Indoor and Outdoor use.



Product Code	Fixture Dimensions	Lamp
WLE1106C30K-10-30 (White) Steplight Opal White Glass	3" W x .4" D x 5" H	3W LED, 3000K, 80 CRI 264 Lumens, Dimmable
WLE1106C30K-10-31 (Black) Steplight Opal White Glass	3" W x .4" D x 5" H	3W LED, 3000K, 80 CRI 264 Lumens, Dimmable
WLE1106C30K-10-45 (Brown) Steplight Opal White Glass	3" W x .4" D x 5" H	3W LED, 3000K, 80 CRI 264 Lumens, Dimmable
WLE1106C30K-10-98 (Aluminum) Steplight Opal White Glass	3" W x .4" D x 5" H	3W LED, 3000K, 80 CRI 264 Lumens, Dimmable

STEP LIGHTING



OUTDOOR

BROAD STREET

EN110126



1 light outdoor Wall Sconce in Textured Black
5"W x 8"H x 6" Ext.
1 light x 60W Med.
• translucent white glass



EN110146



1 light outdoor Hanging in Textured Black
6"W x 10"H x 6" Ext.
1 light x 60W Med.
47" Overall height
(includes 3' chain, 6' wire)
• translucent white glass



EN111126



1 light outdoor Wall Sconce in Textured Black
6"W x 10"H x 7" Ext.
1 light x 60W Med.
• translucent white glass



EN110196



1 light outdoor Post in Textured Black
6"W x 12"H x 6" Ext.
1 light x 60W Med.
• translucent white glass



EN110136



2 light outdoor flush mount in Textured Black
6"W x 10"H x 6" Ext.
2 lights x 60W Med.
• translucent white glass



MISSION

SL91047

- 1 light outdoor wall sconce in Black
6"W x 11"H x 8"Ext.
1 light x 100W Med.
- aluminum construction
 - cream colored glass panels



SL96657

- 1 light outdoor flush mount in Black
6"W x 10"H
1 light x 100W Med.
- aluminum construction
 - cream colored glass panels



SL90077

- 1 light outdoor wall sconce in Black
9"W x 13"H x 11"Ext.
1 light x 100W Med.
- aluminum construction
 - cream colored glass panels



SL90067

- 3 light outdoor post mount in Black
11"W x 20"H
3 lights x 60W Cand.
- aluminum construction
 - cream colored glass panels
 - post not included



SL91067

- 3 light outdoor wall sconce in Black
11"W x 19"H x 14"Ext.
3 lights x 60W Cand.
- aluminum construction
 - cream colored glass panels



ASPEN LODGE

45015/1 

1 light outdoor wall sconce in Textured Matte Black

6"W x 9"H x 7" Ext.

1 light x 60W Med.

- seedy glass
- wire cage



45017/1 

1 light outdoor pendant in Textured Matte Black

8"W x 12"H

1 light x 100W Med.

50" Overall height
(includes 3' chain, 6' wire)

- seedy glass
- wire cage



45016/1 

1 light outdoor wall sconce in Textured Matte Black

8"W x 11"H x 9" Ext.

1 light x 60W Med.

- seedy glass
- wire cage



45018/1 

1 light outdoor post mount in Textured Matte Black

8"W x 13"H

1 light x 100W Med.

- seedy glass
- wire cage



OUTDOOR

 symbol denotes wet location tolerable

45030/1

- 1 light outdoor wall sconce in Regal Bronze
 8"W x 13"H x 9"H
 1 light x 100W Med.
 • water glass
 • die cast aluminum



45031/1

- 1 light outdoor pendant in Regal Bronze
 8"W x 10"H
 1 light x 100W Med.
 46" Overall height
 (includes 3' chain, 6' wire)
 • water glass
 • die cast aluminum



45032/1

- 1 light outdoor post mount in Regal Bronze
 8"W x 15"H x 8"H
 1 light x 100W Med.
 • water glass
 • die cast aluminum



45040/1

- 1 light outdoor wall sconce in Weathered Charcoal
 8"W x 13"H x 9"H
 1 light x 100W Med.
 • water glass
 • die cast aluminum



45041/1

- 1 light outdoor pendant in Weathered Charcoal
 8"W x 10"H
 1 light x 100W Med.
 (includes 3' chain, 6' wire)
 • water glass
 • die cast aluminum



45042/1

- 1 light outdoor post mount in Weathered Charcoal
 8"W x 15"H x 8"H
 1 light x 100W Med.
 • water glass
 • die cast aluminum



MARINA

47021/1

1 light indoor/outdoor pendant in Matte Silver

8"W x 9"H
1 light x 60W Med.
45" Overall height
(includes 3' chain, 6' wire)

- cast aluminum



47011/1

1 light indoor/outdoor pendant in Hazelnut Bronze

8"W x 9"H
1 light x 60W Med.
45" Overall height
(includes 3' chain, 6' wire)

- cast aluminum



47020/1

1 light indoor/outdoor wall sconce in Matte Silver

8"W x 8"H x 9" Ext.
1 light x 60W Med.

- cast aluminum



47010/1

1 light indoor/outdoor wall sconce in Hazelnut Bronze

8"W x 8"H x 9" Ext.

- cast aluminum



OUTDOOR

 symbol denotes wet location tolerable

MARITIME

42005/1

1 light indoor/outdoor wall sconce in Hazelnut Bronze
9"W x 10"H x 11" Ext.
1 light x 60W Med.
• lightly seeded glass



42006/1

1 light indoor/outdoor wall sconce in Hazelnut Bronze
9"W x 12"H x 11" Ext.
1 light x 60W Med.
• lightly seeded glass



42007/1

1 light indoor/outdoor pendant in Hazelnut Bronze
9"W x 10"H
1 light x 60W Med.
46" Overall height (includes 3' chain, 6' wire)
• lightly seeded glass



42405/1

1 light indoor/outdoor wall sconce in Graphite
9"W x 10"H x 11" Ext.
1 light x 60W Med.
• frosted glass



42406/1

1 light indoor/outdoor wall sconce in Graphite
9"W x 12"H x 11" Ext.
1 light x 60W Med.
• frosted glass



OUTDOOR

STREETSIDE CAFÉ

62000-1 

- 1 light outdoor wall sconce in Matte Black
12"W x 15"H x 8" Ext.
1 light x 100W Med.
• heavy seeded blown glass



62001-1 

- 1 light outdoor wall sconce in Matte Black
11"W x 14"H x 22" Ext.
1 light x 100W Med.
• heavy seeded blown glass



VINTON STATION

57152/1 

- 1 light outdoor wall sconce in Oil Rubbed Bronze
10"W x 15"H x 12" Ext.
1 light x 60W Med.
• heavy seeded blown glass



57162/1 


- 1 light outdoor wall sconce in Aged Zinc
10"W x 15"H x 12" Ext.
1 light x 60W Med.
• heavy seeded blown glass



OUTDOOR

 symbol denotes wet location tolerable


LANGHORN

57150/1 

LANGHORN

1 light outdoor pendant in Oil Rubbed Bronze
6"W x 9"H x 8" Ext.
1 light x 60W Med.



57151/1 

LANGHORN

1 light outdoor pendant in Oil Rubbed Bronze
8"W x 12"H x 11" Ext.
1 light x 60W Med.



57160/1 

LANGHORN

1 light outdoor pendant in Aged Zinc
8"W x 10"H
1 light x 100W Med.
{includes 3' chain, 6' wire}



57161/1 

LANGHORN

1 light outdoor pendant in Aged Zinc
8"W x 12"H x 11" Ext.
1 light x 60W Med.



VANTON

45212/1 

1 light indoor/outdoor wall sconce in
Textured Matte Black
7"W x 13"H x 8" Ext.
1 light x 60W Med.
• heavy seeded blown glass



45213/1 

1 light indoor/outdoor pendant in Textured Matte
Black
7"W x 10"H
1 light x 100W Med.
49" Overall height
{includes 3' chain, 6' wire}
• heavy seeded blown glass



PORTSIDE

42284/1

- 1 light outdoor wall sconce in Matte Black
7"W x 12"H x 9" Ext.
1 light x 100W Med.
• clear blown glass
• die cast aluminum



42286/1

- 1 light outdoor pendant in Matte Black
11"W x 16"H
1 light x 100W Med.
51" Overall height
(includes 3' chain, 6' wire)
• clear blown glass
• die cast aluminum



42285/1

- 1 light outdoor wall sconce in Matte Black
11"W x 18"H x 13" Ext.
1 light x 100W Med.
• clear blown glass
• die cast aluminum



SAN MATEO

45120/1

- 1 light outdoor wall sconce in Textured Matte Black
8"W x 15"H x 10" Ext.
1 light x 100W Med.
• clear seedy glass



45121/1

- 1 light outdoor pendant in Textured Matte Black
8"W x 13"H
1 light x 100W Med.
51" Overall height
(includes 3' chain, 6' wire)
• clear seedy glass



OUTDOOR

 symbol denotes wet location tolerable

VILLAGE LANTERN

47040/1

1 light outdoor wall sconce in Weathered Charcoal

6"W x 13"H x 8" Ext.

1 light x 60W Med.

- lightly seeded glass
- die cast aluminum



47042/1

1 light outdoor wall sconce in Weathered Charcoal

8"W x 17"H x 10" Ext.

1 light x 60W Med.

- lightly seeded glass
- die cast aluminum



47044/1

1 light outdoor wall sconce in Weathered Charcoal

9"W x 18"H x 11" Ext.

1 light x 60W Med.

- lightly seeded glass
- die cast aluminum



47043/1

1 light outdoor pendant in Weathered Charcoal

8"W x 17"H x 10" Ext.

1 light x 60W Med.

91" Overall height
{includes 3' chain, 6' wire}

- lightly seeded glass
- die cast aluminum



47041/1

1 light outdoor post mount in Weathered Charcoal

8"W x 21"H

1 light x 60W Med.

- lightly seeded glass
- die cast aluminum



57180/1



1 light outdoor wall sconce in Oil Rubbed Bronze

8"W x 15"H x 9" Ext.

1 light x 60W Med.

- clear seedy glass



57183/1



1 light indoor/outdoor pendant in Oil Rubbed Bronze

10"W x 14"H

1 light x 60W Med.

53" Overall height
{includes 3' chain, 6' wire}

- clear seedy glass



57181/1



1 light outdoor wall sconce in Oil Rubbed Bronze

10"W x 18"H x 12" Ext.

1 light x 60W Med.

- clear seedy glass



57182/1



1 light outdoor post mount in Oil Rubbed Bronze

10"W x 19"H

1 light x 60W Med.

- clear seedy glass



57170/1

- 1 light outdoor wall sconce in Aged Zinc
- 8"W x 15"H x 9" Ext.
- 1 light x 60W Med.
- clear seedy glass



57173/1

- 1 light indoor/outdoor pendant in Aged Zinc
- 10"W x 14"H
- 1 light x 60W Med.
- 53" Overall height (includes 3' chain, 6' wire)
- clear seedy glass



57171/1

- 1 light outdoor wall sconce in Aged Zinc
- 10"W x 18"H x 12" Ext.
- 1 light x 60W Med.
- clear seedy glass



57172/1

- 1 light outdoor post mount in Aged Zinc
- 10"W x 19"H
- 1 light x 60W Med.
- clear seedy glass



AMBLER

45025/1 

1 light outdoor wall sconce in Oil Rubbed Bronze

5"W x 10"H x 6" Ext.

1 light x 60W Med.

- clear glass



45027/1 

1 light indoor/outdoor pendant in Oil Rubbed Bronze

6"W x 14"H

1 light x 100W Med.

52" Overall height
(includes 3' chain, 6' wire)

- clear glass



45026/1 

1 light outdoor wall sconce in Oil Rubbed Bronze

7"W x 14"H x 9" Ext.

1 light x 60W Med.

- clear glass



MULLEN GATE

45116/1 

1 light outdoor wall sconce in Oil Rubbed Bronze

5"W x 11"H x 6" Ext.

1 light x 60W Med.

- clear glass



45118/1 

1 light indoor/outdoor pendant in Oil Rubbed Bronze

6"W x 12"H

1 light x 100W Med.

48" Overall height
(includes 3' chain, 6' wire)

- clear glass



45117/1 

1 light outdoor wall sconce in Oil Rubbed Bronze

6"W x 13"H x 8" Ext.

1 light x 100W Med.

- clear glass



OUTDOOR

 symbol denotes wet location tolerable

CROWLEY

45065/1

1 light outdoor wall sconce in Hazelnut Bronze
6"W x 13"H x 7" Ext.
1 light x 60W Med.
• clear seedy glass



45067/1

1 light indoor/outdoor pendant in Hazelnut Bronze
8"W x 18"H
1 light x 100W Med.
56" Overall height
(includes 3' chain, 6' wire)
• clear seedy glass



45066/1

1 light outdoor wall sconce in Hazelnut Bronze
8"W x 18"H x 10" Ext.
1 light x 100W Med.
• clear seedy glass



LANDIS

47150/1

1 light indoor/outdoor wall sconce in Dark Graphite
6"W x 10"H x 9" Ext.
1 light x 60W Med.
• clear glass



42510/LED

1 light indoor/outdoor wall sconce in Weathered Charcoal
8"W x 13"H x 9" Ext.
1 light x 6W - 480 Lumen Integrated LED;
2700K, 80 CRI
• clear seedy glass



OSAGE

PRINCE STREET

8701EW/65

1 light outdoor wall sconce in Matte Black
8"W x 14"H x 11" Ext.
1 light x 75W Med.
• clear seeded glass



8721EH/65

1 light outdoor pendant in Matte Black
10"W x 16"H
1 light x 75W Med.
(includes 3' chain, 6' wire)
• clear seeded glass



8711EW/65

1 light outdoor wall sconce in Matte Black
10"W x 16"H x 12" Ext.
1 light x 75W Med.
• clear seeded glass



8721EP/65

1 light outdoor post mount in Matte Black
10"W x 20"H
1 light x 75W Med.
• clear seeded glass



OUTDOOR

 symbol denotes wet location tolerable

MEADOW VIEW

46250/1

1 light outdoor wall sconce in Textured Matte Black

6"W x 11"H x 6" Ext.
1 light x 100W Med.

- frosted glass
- die cast aluminum



46253/1

1 light outdoor pendant in Textured Matte Black

7"W x 13"H
1 light x 100W Med.
51" Overall height
(includes 3' chain, 6' wire)

- frosted glass
- die cast aluminum



46251/1

1 light outdoor wall sconce in Textured Matte Black

7"W x 13"H x 7" Ext.
1 light x 100W Med.

- frosted glass
- die cast aluminum



46252/1

1 light outdoor post mount in Textured Matte Black

7"W x 15"H
1 light x 100W Med.

- frosted glass
- die cast aluminum



TRINITY

8001EW/75

1 light outdoor wall sconce in Oil Rubbed Bronze

7"W x 16"H x 9" Ext.
1 light x 75W Med.

- clear seeded glass



8002EW/75

2 light outdoor wall sconce in Oil Rubbed Bronze

9"W x 22"H x 11" Ext.
2 lights x 60W Cand.

- clear seeded glass



8003EW/75

3 light outdoor wall sconce in Oil Rubbed Bronze

12"W x 26"H x 14" Ext.
3 lights x 60W Cand.

- clear seeded glass



8002EH/75

2 light outdoor pendant in Oil Rubbed Bronze

9"W x 20"H
2 lights x 60W Cand.

- clear seeded glass



8002EP/75

2 light outdoor post mount in Oil Rubbed Bronze

9"W x 20"H
2 lights x 60W Cand.

- clear seeded glass



OUTDOOR

 symbol denotes wet location tolerable

COTSWOLD

8901EW/75

- 1 light outdoor wall sconce in Oil Rubbed Bronze
8"W x 15"H x 8" Ext.
1 light x 60W Med.
• clear seeded glass



8903EH/75

- 3 light outdoor pendant in Oil Rubbed Bronze
13"W x 18"H
3 lights x 60W Cand.
• clear heavy seeded glass



8902EW/75

- 2 light outdoor wall sconce in Oil Rubbed Bronze
10"W x 18"H x 9" Ext.
2 lights x 60W Cand.
• clear heavy seeded glass



8903EP/75

- 3 light outdoor post mount in Oil Rubbed Bronze
13"W x 18"H
3 lights x 60W Cand.
• clear heavy seeded glass



8903EW/75

- 3 light outdoor wall sconce in Oil Rubbed Bronze
13"W x 24"H x 12" Ext.
3 lights x 60W Cand.
• clear heavy seeded glass



LORINGDALE

45045/1 

- 1 light outdoor wall sconce in
Hazelnut Bronze
6"W x 12"H x 8" Ext.
1 light x 60W Med.
• clear seedy glass



45047/1 

- 1 light outdoor pendant in Hazelnut Bronze
8"W x 15"H
1 light x 100W Med.
53" Overall height
{includes 3' chain, 6' wire}
• clear seedy glass



45046/1 

- 1 light outdoor wall sconce in
Hazelnut Bronze
8"W x 16"H x 9" Ext.
1 light x 100W Med.
• clear seedy glass



45048/1 

- 1 light outdoor post mount in Hazelnut Bronze
8"W x 17"H
1 light x 100W Med.
53" Overall height
{includes 3' chain, 6' wire}
• clear seedy glass



OUTDOOR

 symbol denotes wet location tolerable

SHAKER HEIGHTS

8201EW/70

1 light outdoor wall sconce in Hazelnut Bronze

7"W x 10"H x 11" Ext.

1 light x 75W Med.

- clear seeded glass



8201EH/70

1 light outdoor pendant in Hazelnut Bronze

7"W x 17"H

1 light x 75W Med.

{includes 3' chain, 6' wire}

- clear seeded glass



8201EP/70

1 light outdoor post mount in Hazelnut Bronze

7"W x 11"H

1 light x 75W Med.

- clear seeded glass



CAPE ANN

8301EP/65

1 light outdoor post mount in Matte Textured Black

8"W x 13"H

1 light x 75W Med.

- clear seedy glass



8301EW/65

1 light outdoor wall sconce in Matte Textured Black

8"W x 10"H x 12" Ext.

1 light x 75W Med.

- clear seedy glass



8301EH/65

1 light outdoor pendant in Matte Textured Black

8"W x 11"H

1 light x 75W Med.

{includes 3' chain, 6' wire}

- clear seedy glass



OUTDOOR

MENDHAM

8501EW/70

1 light outdoor wall sconce in Hazelnut Bronze

8"W x 16"H x 10" Ext.
1 light x 75W Med.

- clear glass
- die cast aluminum



8511EH/70

1 light outdoor pendant in Hazelnut Bronze

9"W x 16"H
1 light x 75W Med.
(includes 3' chain, 6' wire)

- clear glass
- die cast aluminum



8511EW/70

1 light outdoor wall sconce in Hazelnut Bronze

9"W x 19"H x 12" Ext.
1 light x 75W Med.

- clear glass
- die cast aluminum



8511EP/70

1 light outdoor post mount in Hazelnut Bronze

9"W x 22"H
1 light x 75W Med.

- clear glass
- die cast aluminum



8521EW/70

1 light outdoor wall sconce in Hazelnut Bronze

11"W x 24"H x 15" Ext.
1 light x 75W Med.

- clear glass
- die cast aluminum



OUTDOOR

 symbol denotes wet location tolerable

MENDHAM

8551EW/70

- 1 light outdoor wall sconce in Hazelnut Bronze
8"W x 16"H x 10"Ext.
1 light x 75W Med.
- white translucent glass
 - die cast aluminum



8561EH/70

- 1 light outdoor pendant in Hazelnut Bronze
9"W x 16"H
1 light x 75W Med.
(includes 3' chain, 6' wire)
- white translucent glass
 - die cast aluminum



8561EW/70

- 1 light outdoor wall sconce in Hazelnut Bronze
9"W x 19"H x 12"Ext.
1 light x 75W Med.
- white translucent glass
 - die cast aluminum



8561EP/70

- 1 light outdoor post mount in Hazelnut Bronze
9"W x 22"H
1 light x 75W Med.
- white translucent glass
 - die cast aluminum



8571EW/70

- 1 light outdoor wall sconce in Hazelnut Bronze
11"W x 24"H x 15"Ext.
1 light x 75W Med.
- white translucent glass
 - die cast aluminum



RIDGEWOOD

8401EW/65

1 light outdoor wall sconce in Matte Textured Black
7"W x 12"H x 9" Ext.
1 light x 75W Med.
• clear glass



8411EH/65

1 light outdoor pendant in Matte Textured Black
9"W x 12"H
1 light x 75W Med.
(includes 3' chain, 6' wire)
• clear glass



8411EW/65

1 light outdoor wall sconce in Matte Textured Black
9"W x 15"H x 11" Ext.
1 light x 75W Med.
• clear glass



8411EP/65

1 light outdoor post mount in Matte Textured Black
9"W x 15"H
1 light x 75W Med.
• clear glass



8421EW/65

1 light outdoor wall sconce in Matte Textured Black
11"W x 18"H x 14" Ext.
1 light x 75W Med.
• clear glass



OUTDOOR

 symbol denotes wet location tolerable

RIDGEWOOD

8401EW/70

1 light outdoor wall sconce in Hazelnut Bronze
7"W x 12"H x 9" Ext.
1 light x 75W Med.
• clear glass



8411EH/70

1 light outdoor pendant in Hazelnut Bronze
9"W x 12"H
1 light x 75W Med.
(includes 3' chain, 6' wire)
• clear glass



8411EW/70

1 light outdoor wall sconce in Hazelnut Bronze
9"W x 15"H x 11" Ext.
1 light x 75W Med.
• clear glass



8411EP/70

1 light outdoor post mount in Hazelnut Bronze
9"W x 15"H
1 light x 75W Med.
• clear glass



8421EW/70

1 light outdoor wall sconce in Hazelnut Bronze
11"W x 18"H x 14" Ext.
1 light x 75W Med.
• clear glass



SPRING LAKE

8611EW/65

1 light outdoor wall sconce in Matte Textured Black

6"W x 15"H x 9" Ext.
1 light x 75W Med.

- clear beveled glass
- die cast aluminum



8601EH/65

1 light outdoor pendant in Matte Textured Black

8"W x 14"H
1 light x 75W Med.
(includes 3' chain, 6' wire)

- clear beveled glass
- die cast aluminum



8601EW/65

1 light outdoor wall sconce in Matte Textured Black

8"W x 17"H x 10" Ext.
1 light x 75W Med.

- clear beveled glass
- die cast aluminum



8603EW/65

3 light outdoor wall sconce in Matte Textured Black

10"W x 25"H x 10" Ext.
3 lights x 60W Cand.

- clear beveled glass
- die cast aluminum



8613EW/65

3 light outdoor wall sconce in Matte Textured Black

10"W x 25"H x 10" Ext.
3 lights x 60W Cand.

- clear beveled glass
- die cast aluminum



8603EP/65

3 light outdoor post mount in Matte Textured Black

10"W x 23"H
3 lights x 60W Cand.

- clear beveled glass
- die cast aluminum



OUTDOOR

 symbol denotes wet location tolerable

BRENTWOOD

SL92427

- 1 light outdoor wall sconce in Black
7"W x 14"H x 7"Ext.
1 light x 100W Med.
- clear beveled glass
 - may use accessory panel **DS1004** to comply with Dark Sky ordinance (order separately)



SL92437

- 1 light outdoor wall sconce in Black
7"W x 26"H x 7"Ext.
1 light x 100W Med.
- clear beveled glass
 - removable tail Ext. (7"W x 18"H)



alternate image

PARK AVENUE

SL94717

- 1 light outdoor wall sconce in Black
6"W x 12"H x 6"Ext.
1 light x 100W Med.
- clear beveled glass



SL94727

- 1 light outdoor wall sconce in Black
6"W x 18"H x 6"Ext.
1 light x 100W Med.
- clear beveled glass



alternate image

SL94707

- 1 light outdoor wall sconce in Black
7"W x 13"H x 8"Ext.
1 light x 100W Med."
- clear beveled glass



SL94767

- 1 light outdoor wall sconce in Black
7"W x 24"H x 7"Ext.
1 light x 100W Med.
- clear beveled glass

COVINGTON

SL92287

- 1 light outdoor wall sconce in Black
8"W x 16"H x 9"Ext.
1 light x 100W Med.
- seeded glass
 - die-cast aluminum



SL92237

- 1 light outdoor wall sconce in Black
7"W x 15"H x 8"Ext.
1 light x 100W Med.
- seeded glass
 - die-cast aluminum



SL92297

- 1 light outdoor wall sconce in Black
10"W x 18"H x 10"Ext.
1 light x 100W Med.
- seeded glass
 - die-cast aluminum



SL92257

- 1 light outdoor wall sconce in Black
8"W x 22"H x 9"Ext.
1 light x 100W Med.
- seeded glass
 - die-cast aluminum



PL92297

- 1 light outdoor wall sconce in Black
10"W x 18"H x 10"Ext.
1 light x 18W GU24CFL (included)
- etched glass
 - photocell included
 - die-cast aluminum



SL92277

- 1 light outdoor wall sconce in Black
10"W x 24"H x 10"Ext.
1 light x 100W Med.
- seeded glass
 - die-cast aluminum





OUTDOOR

COVINGTON

SL92337

- 1 light outdoor pendant in Black
- 10"W x 14"H
- 1 light x 100W Med.
- 62" Overall length
{12' wire} {4' chain}
- clear seeded glass
- die-cast aluminum



SL90107

- 1 light outdoor post mount in Black
- 10"W x 22"H
- 1 light x 100W Med.
- seeded glass
- die-cast aluminum
- post not included



COVINGTON

SL923363

- 1 light outdoor pendant in Painted Bronze
- 10"W x 14"H
- 1 light x 100W Med.
- 62" Overall length
{12' wire} {4' chain}
- clear seeded glass
- die-cast aluminum



SL901063

- 1 light outdoor posted mount in Painted Bronze
- 10"W x 22"H
- 1 light x 100W Med.
- seeded glass
- die-cast aluminum
- post not included



COVINGTON

SL922863

- 1 light outdoor wall sconce in Painted Bronze
8"W x 16"H x 9"Ext.
1 light x 100W Med.
- seeded glass
 - die-cast aluminum



SL922363

- 1 light outdoor wall sconce in Painted Bronze
7"W x 15"H x 8" Ext.
1 light x 100W Med.
- seeded glass
 - die-cast aluminum



SL922963

- 1 light outdoor wall sconce in Painted Bronze
10"W x 18"H x 10"Ext.
1 light x 100W Med.
- seeded glass
 - die-cast aluminum



SL922563

- 1 light outdoor wall sconce in Painted Bronze
8"W x 22"H x 9"Ext.
1 light x 100W Med.
- seeded glass
 - die-cast aluminum



PL922963

- 1 light outdoor wall sconce in Painted Bronze
10"W x 18"H x 10"Ext.
1 light x 18W GU24CFL (included)
- etched Glass
 - photocell included



SL922763

- 1 light outdoor wall sconce in Painted Bronze
10"W x 24"H x 10"Ext.
1 light x 100W Med.
- seeded glass
 - die-cast aluminum



OUTDOOR

TEMPLE HILL

8101EW/65

1 light outdoor wall sconce in Matte Textured Black

10"W x 18"H x 11" Ext.

1 light x 75W Med.

- clear seeded glass
- die cast aluminum



8101EH/65

1 light outdoor pendant in Matte Textured Black

10"W x 14"H

1 light x 75W Med.

{includes 3' chain, 6' wire}

- clear seeded glass
- die cast aluminum



8111EW/65

1 light outdoor wall sconce in Matte Textured Black

10"W x 21"H x 11" Ext.

1 light x 75W Med.

- clear seeded glass
- die cast aluminum



8101EP/65

1 light outdoor post mount in Matte Textured Black

10"W x 18"H

1 light x 75W Med.

- clear seeded glass
- die cast aluminum



HAWTHORNE

SL94517

- 1 light outdoor wall sconce in Black
8"W x 26"H x 9"Ext.
1 light x 100W Med.
- seeded glass
 - die-cast aluminum



SL945163

- 1 light outdoor wall sconce in Painted Bronze
8"W x 26"H x 9"Ext.
1 light x 100W Med.
- seeded glass
 - die-cast aluminum



SL94527

- 1 light outdoor wall sconce in Black
8"W x 14"H x 9"Ext.
1 light x 100W Med.
- seeded glass
 - die-cast aluminum



SL945263

- 1 light outdoor wall sconce in Painted Bronze
8"W x 14"H x 9"Ext.
1 light x 100W Med.
- seeded glass
 - die-cast aluminum



PL94627

- 1 light outdoor wall sconce in Black
8"W x 14"H x 9"Ext.
1 light x 18W GU24CFL (included)
- white art glass
 - photocell included
 - die-cast aluminum



PL946263

- 1 light outdoor wall sconce in Painted Bronze
8"W x 14"H x 9" Ext.
1 light x 18W GU24CFL (included)
- white art glass
 - photocell included
 - die-cast aluminum



HAWTHORNE

SL942263

- 1 light outdoor wall sconce in Painted Bronze
6"W x 9"H x 7" Ext.
1 light x 60W Med.
- clear beveled glass panels
 - die-cast aluminum



SL94237

- 1 light outdoor wall sconce in Black
6"W x 10"H x 7" Ext.
1 light x 60W Med.
- clear beveled glass panels
 - die-cast aluminum



SL94227

- 1 light outdoor wall sconce in Black
6"W x 9"H x 7" Ext.
1 light x 60W Med.
HCO* 3"
- clear beveled glass panels
 - die-cast aluminum



PL94237

- 1 light outdoor wall sconce in Black
6"W x 10"H x 7" Ext.
1 light x 13W GU24CFL (included)
HCO* 3"
- etched glass panels
 - photocell included



SL94228

- 1 light outdoor wall sconce in Matte White
6"W x 9"H x 7" Ext.
1 light x 60W Med.
- clear beveled glass panels
 - die-cast aluminum



SL94238

- 1 light outdoor wall sconce in Matte White
6"W x 10"H x 7" Ext.
1 light x 60W Med.
- clear beveled glass panels
 - die-cast aluminum



PL948063

- 1 light outdoor wall sconce in Painted Bronze
6"W x 9"H x 5" Ext.
1 light x 13W GU24CFL (included)
- etched glass
 - die-cast aluminum
 - photocell included



PL94807

- 1 light outdoor wall sconce in Black
6"W x 9"H x 5" Ext.
1 light x 13W GU24CFL (included)
- etched glass
 - die-cast aluminum
 - photocell included



OUTDOOR

 symbol denotes wet location tolerable

ASHFORD

8601EW/89

1 light outdoor wall sconce in Antique Brass
8"W x 8"H x 12" Ext.
1 light x 100
0" Overall height
• clear beveled glass



8603EH/89

3 light outdoor pendant in Antique Brass
12"W x 12"H x 21" Ext.
3 light x 60
0" Overall height
• clear beveled glass



8602EW/89

2 light outdoor wall sconce in Antique Brass
10"W x 10"H x 21" Ext.
2 light x 60
0" Overall height
• clear beveled glass



8603EP/89

3 light outdoor post mount in Antique Brass
13"W x 13"H x 23" Ext.
3 light x 60
0" Overall height
• clear beveled glass



8603EW/89

3 light outdoor wall sconce in Antique Brass
13"W x 12"H x 23" Ext.
3 light x 60
0" Overall height
• clear beveled glass



symbol denotes wet location tolerable

OUTDOOR

ASHFORD

8601EW/80

1 light outdoor wall sconce in Antique Nickel

8"W x 12"H x 8" Ext.

1 light x 100W Med.

- clear beveled glass



8602EW/80

2 light outdoor wall sconce in Antique Nickel

10"W x 21"H x 10" Ext.

2 lights x 60W Cand.

- clear beveled glass



8603EW/80

3 light outdoor wall sconce in Antique Nickel

13"W x 23"H x 12" Ext.

3 lights x 60W Cand.

- clear beveled glass



8603EH/80

3 light outdoor pendant in Antique Nickel

12"W x 21"H

3 lights x 60W Cand.

(includes 3' chain, 6' wire)

- clear beveled glass



8603EP/80

3 light outdoor post mount in Antique Nickel

13"W x 23"H

3 lights x 60W Cand.

- clear beveled glass



OUTDOOR

 symbol denotes wet location tolerable

ASHFORD

8601EW/60

- 1 light outdoor wall sconce in Black
- 8"W x 12"H x 8" Ext.
- 1 light x 100W Med.
- clear beveled glass



8602EW/60

- 2 light outdoor wall sconce in Black
- 10"W x 21"H x 10" Ext.
- 2 lights x 60W Cand.
- clear beveled glass



8603EW/60

- 3 light outdoor wall sconce in Black
- 13"W x 23"H x 12" Ext.
- 3 lights x 60W Cand.
- clear beveled glass



8603EH/60


- 3 light outdoor pendant in Black
- 12"W x 21"H
- 3 lights x 60W Cand.
- {includes 3' chain, 6' wire}
- clear beveled glass



8603EP/60

- 3 light outdoor post mount in Black
- 13"W x 23"H
- 3 lights x 60W Cand.
- clear beveled glass





8602EW/75

2 light outdoor wall sconce in Oil Rubbed Bronze

10"W x 21"H x 10" Ext.

2 lights x 60W Cand.

- clear beveled glass

8601EW/75

1 light outdoor wall sconce in Oil Rubbed Bronze

8"W x 12"H x 8" Ext.

1 light x 100W Med.

- clear beveled glass



8603EH/75

3 light outdoor pendant in Oil Rubbed Bronze

12"W x 21"H

3 lights x 60W Cand.

(includes 3' chain, 6' wire)

- clear beveled glass



8603EW/75

3 light outdoor wall sconce in Oil Rubbed Bronze

13"W x 23"H x 12" Ext.

3 lights x 60W Cand.

- clear beveled glass



8603EP/75

3 light outdoor post mount in Oil Rubbed Bronze

13"W x 23"H

3 lights x 60W Cand.

- clear beveled glass



ASHFORD

8601EW/85

1 light outdoor wall sconce in Brass
8"W x 12"H x 8" Ext.
1 light x 100W Med.
• clear beveled glass



8603EW/85

3 light outdoor wall sconce in Brass
13"W x 23"H x 12" Ext.
3 lights x 60W Cand.
• clear beveled glass



8602EW/85

2 light outdoor wall sconce in Brass
10"W x 21"H x 10" Ext.
2 lights x 60W Cand.
• clear beveled glass



8603EP/85

3 light outdoor post mount in Brass
13"W x 23"H
3 lights x 60W Cand.
• clear beveled glass



8603EH/85

3 light outdoor pendant in Brass
12"W x 21"H
3 lights x 60W Cand.
(includes 3' chain, 6' wire)
• clear beveled glass



OUTDOOR

HERITAGE

SL94137



1 light outdoor wall sconce in Black

7"W x 14"H x 7"Ext.

1 light x 60W Med.

- clear beveled glass



SL94247



1 light outdoor wall sconce in Black

9"W x 16"H x 9"Ext.

1 light x 100W Med.

- clear beveled glass



SL941378



1 light outdoor wall sconce in Brushed Nickel

7"W x 14"H x 7"Ext.

1 light x 60W Med.

- clear beveled glass



SL942478



1 light outdoor wall sconce in Brushed Nickel

9"W x 16"H x 9"Ext.

1 light x 100W Med.

- clear beveled glass



SL941363



1 light outdoor wall sconce in Painted Bronze

7"W x 14"H x 7"Ext.

1 light x 60W Med.

- clear beveled glass



SL942463



1 light outdoor wall sconce in Painted Bronze

9"W x 16"H x 9"Ext.

1 light x 100W Med.

- clear beveled glass



OUTDOOR



symbol denotes wet location tolerable

OUTDOOR ESSENTIALS - WALL SCONCES

SL94428

- 1 light outdoor wall sconce in Matte White
8"W x 18"H x 9"Ext.
1 light x 60W Med.
- injection molded plastic
 - acrylic panels



SL94427

- 1 light outdoor wall sconce in Black
8"W x 18"H x 9"Ext.
1 light x 60W Med.
- injection molded plastic
 - acrylic panels



SL94408

- 1 light outdoor wall sconce in Matte White
8"W x 14"H x 9"Ext.
1 light x 60W Med.
- injection molded plastic
 - acrylic panels



SL94407

- 1 light outdoor wall sconce in Black
8"W x 14"H x 9"Ext.
1 light x 60W Med.
- injection molded plastic
 - acrylic panels



TG600176

- 1 light outdoor wall sconce in Black
7"W x 15"H x 7" Ext.
1 light x 60 Med.
- clear glass



CE9261760

- 1 light outdoor wall sconce in Satin Black
6"W x 12"H x 8"Ext.
1 light x 100W Med.
- clear seeded glass



OUTDOOR ESSENTIALS - WALL SCONCES

SL94697

1 light outdoor wall sconce in Black

5"W x 8"H x 6"Ext.

1 light x 60W Med.

- clear beveled glass



SL946963

1 light outdoor wall sconce in Painted Bronze

5"W x 8"H x 6"Ext.

1 light x 60W Med.

- clear beveled glass



9231EW/65

1 light outdoor wall sconce in Black

5"W x 9"H x 5"Ext.

1 light x 100W Med.

- clear glass



9231EW/75

1 light outdoor wall sconce in Oil Rubbed Bronze

5"W x 9"H x 5"Ext.

1 light x 100W Med.

- clear glass



9231EW/80

1 light outdoor wall sconce in Brushed Nickel

5"W x 9"H x 5"Ext.

1 light x 100W Med.

- clear glass



OUTDOOR

 symbol denotes wet location tolerable

OUTDOOR ESSENTIALS - WALL SCONCES

TG500171

1 light outdoor wall sconce in Oil Rubbed Bronze
 11"W x 5"H x 6" Ext.
 1 light x 60 Med.
 • white glass



TG501174

1 light outdoor wall sconce in White
 11"W x 5"H x 6" Ext.
 1 light x 60 Med.
 • white glass



TG502171

1 light outdoor wall sconce in Oil Rubbed Bronze
 11"W x 5"H x 6" Ext.
 1 light x 60 Med.
 • white glass



TG503174

1 light outdoor wall sconce in White
 11"W x 5"H x 6" Ext.
 1 light x 60 Med.
 0" Overall height
 • white glass



TG550171

1 light outdoor wall sconce in Oil Rubbed Bronze
 11"W x 5"H x 11" Ext.
 1 light x 75 Med.
 • white glass



TG552171

1 light outdoor wall sconce in Oil Rubbed Bronze
 11"W x 6"H x 11" Ext.
 1 light x 75 Med.
 • white glass



TG551174

1 light outdoor wall sconce in White
 11"W x 6"H x 11" Ext.
 1 light x 75 Med.
 • white glass

OUTDOOR ESSENTIALS - WALL SCONCES

45250/1 

CHANNING

1 light outdoor wall sconce in Matte Black

5"W x 9"H x 7"Ext.
1 light x 60W Med.

- clear ribbed glass



45251/1 

CHANNING

1 light outdoor wall sconce in Matte Black

7"W x 12"H x 9"Ext.
1 light x 60W Med.

- clear ribbed glass



SL7157 

1 light outdoor wall sconce in Black

5"W x 8"H x 6"Ext.
1 light x 75W Med.

- clear beveled glass



SL7158 

1 light outdoor wall sconce in Matte White

5"W x 8"H x 6"Ext.
1 light x 75W Med.

- clear beveled glass



9211EW/65 

1 light outdoor wall sconce in Black

6"W x 9"H x 7"Ext.
1 light x 60W Med.

- white glass



9211EW/75 

1 light outdoor wall sconce in Oil Rubbed Bronze

6"W x 9"H x 7"Ext.
1 light x 60W Med.

- white glass



OUTDOOR

 symbol denotes wet location tolerable

OUTDOOR ESSENTIALS - WALL SCONCES

9201EW/65

1 light outdoor wall sconce in Black
7"W x 7"H x 8"Ext.
1 light x 60W Med.
• white glass



9201EW/75

1 light outdoor wall sconce in Oil Rubbed Bronze
7"W x 7"H x 8"Ext.
1 light x 60W Med.
• white glass



SL94357

1 light outdoor wall sconce in Black
6"W x 7"H x 7"Ext.
1 light x 60W Med.
• injection molded plastic
• white acrylic globe



SL94358

1 light outdoor wall sconce in Matte White
6"W x 7"H x 7"Ext.
1 light x 60W Med.
• injection molded plastic
• white acrylic globe



CE931171

BELLA
1 light outdoor wall sconce in Oil Rubbed Bronze
6"W x 11"H x 4"Ext.
1 light x 60W Med.
• white acrylic diffuser



CE932171

BELLA
1 light outdoor wall sconce in Oil Rubbed Bronze
6"W x 18"H x 4"Ext.
2 lights x 60W Med.
• white acrylic diffuser



OUTDOOR ESSENTIALS - WALL SCONCES

CE930171 

BELLA
1 light outdoor wall sconce in Oil Rubbed Bronze
9"W x 10"H x 14"Ext.
1 light x 60W Med.
• white glass



SL92707 

DARK SKY
1 light outdoor wall sconce in Black
5"W x 12"H x 8"
1 light x 50W R20
• provides 100% light cut-off
• suitable for coastal regions with light restrictions for turtle nesting areas




Endorsed by Florida Fish & Wildlife for the preservation of turtle nesting areas

SL92708 

DRK SKY
1 light outdoor wall sconce in Matte White
5"W x 12"H x 8"
1 light x 50W R20
• provides 100% light cut-off
• suitable for coastal regions with light restrictions for turtle nesting areas



Endorsed by Florida Fish & Wildlife for the preservation of turtle nesting areas



OUTDOOR

 symbol denotes wet location tolerable

OUTDOOR ESSENTIALS - WALL SCONCES

SL49427

2 light outdoor wall sconce in Black
12"W x 11"H x 11"Ext.
2 lights x 150W BR40



SL49428

2 light outdoor wall sconce in Matte White
12"W x 11"H x 11"Ext.
2 lights x 150W BR40



SL494227

2 light outdoor wall sconce in Painted Bronze
12"W x 11"H x 11"Ext.
2 lights x 150W BR40



SL49468

2 light wall sconce in Matte White
10"W x 6"H x 6"Ext.
2 lights x 150W BR40



OUTDOOR ESSENTIALS - FLUSH MOUNTS

SL928378

2 light indoor/outdoor flush mount in Brushed Nickel
12"W x 6"H
2 lights x 60W Med.
• etched alabaster style glass



SL3037

1 light outdoor flush mount in Black
5"W x 7"H
1 light x 60W Med.
• clear beveled glass



symbol denotes damp location tolerable



symbol denotes wet location tolerable

OUTDOOR

OUTDOOR ESSENTIALS - FLUSH MOUNTS

CE9202310

2 light outdoor flush mount in Oil Rubbed Bronze
10"W x 7"H
2 light x 60W Med.
• clear glass



CE9202365

2 light outdoor flush mount in Satin Nickel
10"W x 7"H
2 light x 60W Med.
• clear glass



SL7457

1 light outdoor flush mount in Black
11"W x 5"H
1 light x 100W Med.
• frosted glass
• die-cast aluminum



SL7458

1 light outdoor flush mount in Matte White
11"W x 5"H
1 light x 100W Med.
• etched glass
• die-cast aluminum



SL7577

1 light outdoor flush mount in Black
8"W x 5"H
1 light x 60W Med.
• white plastic diffuser
• injection molded plastic



SL7578

1 light outdoor flush mount in Matte White
8"W x 5"H
1 light x 60W Med.
• white plastic diffuser
• injection molded plastic



SL7597

2 light outdoor flush mount in Black
10"W x 5"H
2 lights x 60W Med.
• white plastic diffuser
• injection molded plastic



SL7598

2 light outdoor flush mount in Matte White
10"W x 5"H
2 lights x 60W Med.
• white plastic diffuser
• injection molded plastic



OUTDOOR



symbol denotes damp location tolerable



symbol denotes wet location tolerable

OUTDOOR ESSENTIALS - FLUSH MOUNTS

9102EF/65

2 light outdoor flush mount in Matte Textured Black
8"W x 4"H
2 light x 60W Med.
• clear seeded glass



9102EF/40

2 light outdoor flush mount in White
8"W x 4"H
2 light x 60W Med.
• clear seeded glass



9002EF/65

2 light outdoor flush mount in Matte Textured Black
10"W x 6"H
2 light x 60W Med.
• clear seeded glass



9002EF/40

2 light outdoor flush mount in White
10"W x 6"H
2 light x 60W Med.
• clear seeded glass



9102EF/70

2 light outdoor flush mount in Hazelnut Bronze
8"W x 4"H
2 light x 60W Med.
• clear seeded glass



9102EF/80

2 light outdoor flush mount in Antique Nickel
8"W x 4"H
2 light x 60W Med.
• clear seeded glass



9002EF/70

2 light outdoor flush mount in Hazelnut Bronze
10"W x 6"H
2 light x 60W Med.
• clear seeded glass



9002EF/80

2 light outdoor flush mount in Antique Nickel
10"W x 6"H
2 light x 60W Med.
• clear seeded glass



 symbol denotes wet location tolerable

OUTDOOR

OUTDOOR ESSENTIALS - POST MOUNTS

7153EP/73

3 light outdoor post mount in Charcoal
 26"W x 91"H
 3 lights x 100W Med.
 • clear seeded glass
 • post included



TG620176

1 light outdoor post mount in White
 11"W x 16"H x 11" Ext.
 1 light x 150 Med.
 • white glass



TG30176

1 light outdoor post mount in Black
 11"W x 16"H x 11" Ext.
 1 light x 150 Med.
 • white glass



TG6100176

1 light outdoor post mount in Black
 10"W x 13"H x 10" Ext.
 1 light x 100 Med.
 • white glass



45100CHRC

outdoor post in Charcoal
 10"W x 73"H
 IMPORTANT -
 45102CHRC is required for
 post top fixture installation.



45101CHRC

Charcoal
 14"W x 7"H



45102CHRC

Charcoal
 3"W x 4"H



1000-C

Charcoal
 6"W x 5"H



OUTDOOR

 symbol denotes wet location tolerable

OUTDOOR POST ACCESSORIES

SL9118

Black
3"W x 84"H
• outdoor post



43001HB

Hazelnut Bronze
3"W x 84"H
• outdoor post

43001WC

Weathered Charcoal
3"W x 84"H
• outdoor post

43003AGB

Aged Bronze
6"W x 3"H
• outdoor pier mount



43003CB

Clay Bronze
8"W x 5"H
• outdoor pier mount



43003GH

Graphite
6"W x 3"H
• outdoor pier mount



43003HB

Hazelnut Bronze
6"W x 3"H
• outdoor pier mount



43003WC

Weathered Charcoal
8"W x 5"H
• outdoor pier mount



 symbol denotes wet location tolerable

OUTDOOR





INDEX

INDEX

ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE
1092	7	190040719	42	1004BB/20	97, 222	1179-007	254	1305CH/20	64
1099	7	190041217	40	1005CH/20	96	1179-008	257	1351PL/10	66, 131
1101	7	190041719	42	1009CH/20	96	1179-009	256	1351PS/10	66, 148
1102	7	190042217	40	1051PS/10	98, 147	1201PL/20	72, 131	1351WS/10	67, 182, 211
1103	7	190042719	42	1051WS/10	99, 183, 223	1201PS/20	72, 149	1352BB/10	67, 211
1110	7	190043217	41, 128, 160	1052BB/10	99, 223	1201WS/20	73, 184, 214	1353BB/10	67, 211
1111	7	190043719	42, 128, 160	1052CS/10	99, 136, 164	1202BB/20	73, 214	1353CH/10	66
1112	7	190056117	68, 149	1053BB/10	99, 223	1202CS/20	73, 135	1354BB/10	67, 211
1113	7	190056763	70, 149	1053CH/10	98	1202CS/20	163	1355CH/10	66
1114	7	190058117	68, 132	1053FM/10	166	1203BB/20	73, 214	1501WS/10	33, 177
1119	7	190058763	70, 132	1053IS/10	98, 139	1203CH/20	72	1501WS/20	31, 177
47021	123	190060217	41, 145	1053PL/10	98, 136	1203PL/20	72, 135	1502WS/10	33, 177
190005117	68	190060719	42, 145	1054BB/10	99, 223	1204BB/20	73, 214	1502WS/20	31, 177
190005763	70	190061217	40, 128	1055CH/10	98	1205CH/20	72	1503CH/10	34
190006117	68	190061719	42, 128	1059CH/10	98	1209CH/20	72	1505CH/10	34
190006763	70	190067117	68, 159	1101PS/20	146	1217-1010	21	1509CH/10	34
190016117	69, 212	190067763	70, 159	1101WS/20	185, 247	1217-1011	21, 142	1513CH/10	33
190016763	71, 213	190071217	41, 166	1102BB/20	247	1217-1013	21, 138	1513CH/20	31
190017117	69, 212	190071719	43, 166	1103BB/20	247	1221PL/10	74, 131	1515CH/10	33
190017763	71, 213	190109704	50	1103CH/20	120	1251PS/10	74, 149	1515CH/20	31
190018117	69, 212	190110704	50	1103FM/20	97, 166	1251WS/10	75, 184, 215	1523CH/10	35
190018763	71, 213	190111704	51, 144	1103PL/20	136	1252BB/10	75, 215	1523CH/20	31
190022217	41, 198	190112704	50	1105CH/20	120	1252CS/10	75, 135, 163	1525CH/10	35
190022719	43, 199	190113704	50, 158	1151PS/10	146	1253BB/10	75, 215	1525CH/20	30
190023217	41, 180, 198	190114704	51, 203	1151WS/10	185, 247	1253BB/10	215	1529CH/10	35
190023719	43, 180, 199	190115704	51, 203	1152BB/10	247	1253CH/10	74	1529CH/20	30
190024217	41, 198	190116704	51, 203	1153BB/10	247	1253PL/10	74, 135	1533CH/10	33
190024719	43, 199	1000-C	334	1153CH/10	120	1254BB/10	75, 215	1533CH/20	30
190025217	41, 198	1001PS/20	97, 147	1153FM/10	99	1255CH/10	74	1803CH/10	121
190025719	43, 199	1001WS/20	97, 183	1155CH/10	120	1259CH/10	74	1803CH/20	121
190033217	168	1001WS/20	222	1179-001	255	1301PL/20	64, 131	1805CH/20	121
190033715	169	1002BB/20	97, 222	1179-002	255	1301PS/20	64, 148	1903CH/10	121
190034217	168	1002CS/20	97, 136	1179-003	254	1301WS/20	65, 182, 210	1903CH/20	121
190035217	168	1002CS/20	164	1179-004	257	1302BB/20	65, 210	1905CH/10	121
190036117	68	1003BB/20	97, 222	1179-005	254	1303BB/20	65, 210	2003CH/10	62-63
190036763	70	1003CH/20	96	1179-006	253	1303CH/20	64	2003FM/10	62-63, 165
190040217	40	1003IS/20	96, 139	1179-006	256	1304BB/20	65, 210	2005CH/10	62-63

INDEX

ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE
2009CH/10	62	42284/1	294	45117/1	298	47043/1	295	57162/1	292
2101PS/10	85, 150	42285/1	294	45118/1	142, 298	47044/1	295	57170/1	297
2101PS/20	84, 150	42286/1	141, 294	45120/1	294	47150/1	179, 299	57171/1	297
2101WS/10	85, 175, 185	42405/1	178, 291	45121/1	141, 294	5102WS/20	187	57172/1	297
2101WS/20	84, 185	42406/1	178, 291	45212/1	179, 293	5111WS/20	187	57173/1	141, 297
2103CH/10	85	42510/LED	179, 299	45213/1	141, 293	5121WS/99	187	57180/1	296
2103CH/20	84	43001HB	335	45250/1	328	5131WS/20	187	57181/1	285, 296
2103FM/10	85, 166	43001WC	335	45251/1	328	5151WS/10	186	57182/1	296
2103FM/20	84, 166	43003AGB	335	46227/6	15	5151WS/20	186	57183/1	141, 296
2103SF/10	85, 164	43003CB	335	46228/10	15	5161WS/99	185	62000-1	292
2103SF/20	84, 164	43003GH	335	46229/14	14	5171WS/20	186	62001-1	292
2105CH/10	85	43003HB	335	46230/12	15	5181WS/20	186	7002FM/20	168
2105CH/20	84	43003WC	335	46231/12	14	5371WS/10	186	7002FM/40	168
2109CH/10	85	45015/1	288	46232/24	14	5501BB/20	184, 250	7003FM/20	168
2109CH/20	84	45016/1	288	46233/12	11	5501BB/30	184, 251	7003FM/40	168
2115CH/10	85	45017/1	288	46234/12	10	5502BB/20	250	7013FM/20	168
2115CH/20	84	45018/1	288	46235/24	10	5502BB/30	251	7013FM/40	168
2201WS/10	183, 246	45025/1	298	46240/6	12	5503BB/20	250	7021FM/10	170
2202BB/10	246	45026/1	298	46241/10	13	5503BB/30	251	7021FM/20	170
2203BB/10	246	45027/1	142, 298	46242/14	12	5504BB/20	250	7021FM/40	170
2203CH/10	120	45030/1	289	46243/12	13	5504BB/30	251	7023FM/10	168
2203CS/10	137, 163	45031/1	289	46244/12	12	5551BB/10	184	7052FM/10	168
2203IS/10	139	45032/1	289	46245/24	12	5601BB/20	184, 249	7053FM/10	168
2203PL/10	137	45040/1	289	46250/1	301	5601BB/30	184, 248	7153EP/73	334
2204BB/10	246	45041/1	289	46251/1	301	5602BB/30	248	7301FM/10	169
2205CH/10	120	45042/1	289	46252/1	301	5603BB/20	249	7301FM/20	169
2401PL/10	130	45045/1	304	46253/1	301	5603BB/30	248	7302FM/10	169
2402SF/20	160	45046/1	304	46260/6	11	5604BB/20	249	7302FM/20	169
2403CH/10	122	45047/1	304	46261/10	11	5604BB/30	248	7303FM/10	169
2403CH/20	122	45048/1	304	46262/14	10	5651BB/10	184, 249	7303FM/20	169
2405CH/10	122	45065/1	299	47010/1	178, 290	5652BB/10	249	7351FM/40	169
2405CH/20	122	45066/1	299	47011/1	140, 290	5653BB/10	249	7352FM/40	169
2451WS/10	180	45067/1	140, 299	47020/1	178, 290	57150/1	293	7661PS/10	142
2451WS/20	180	45100CHRC	334	47021/1	140, 290	57151/1	293	7661PS/20	142
42005/1	178, 291	45101CHRC	334	47040/1	295	57152/1	292	7672FM/10	165
42006/1	178, 291	45102CHRC	334	47041/1	295	57160/1	293	7672FM/20	165
42007/1	140, 291	45116/1	298	47042/1	295	57161/1	293	7681PL/10	126

INDEX

ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE
7681PL/20	126	8411EW/70	309	8603EW/65	310	CE9202365	332	CN110521	36-37
7683FM/10	165	8421EW/65	308	8603EW/75	322	CE9261760	325	CN110821	36
7683FM/20	165	8421EW/70	309	8603EW/80	320	CE930171	330	CN120041	28, 126
7691PL/10	126	8501EW/70	306	8603EW/85	323	CE931171	329	CN120121	29, 176
7691PL/20	126	8511EH/70	306	8603EW/89	319	CE932171	329	CN120121	197
7693FM/10	165	8511EP/70	306	8611EW/65	310	CL580113	193	CN120151	28, 143
7693FM/20	165	8511EW/70	306	8613EW/65	310	CL580213	188, 193	CN120211	29, 197
7703FY/20	156	8521EW/70	306	8701EW/65	300	CL581213	188	CN120231	28, 165
7704FY/10	154	8551EW/70	307	8711EW/65	300	CL781031	188	CN120281	28, 127
7704FY/20	154	8561EH/70	307	8721EH/65	300	CL781034	172, 188	CN120281	158
7706FY/20	156	8561EP/70	307	8721EP/65	300	CL781131	172, 188	CN120311	29, 197
7713FY/10	155	8561EW/70	307	8901EW/75	303	CL781134	172, 188	CN120321	28
7713FY/20	155	8571EW/70	307	8902EW/75	303	CL781231	172, 188	CN120411	29, 197
7723FY/10	156	8601EH/65	310	8903EH/75	303	CL781234	172, 188	CN120521	28
7726FY/10	156	8601EW/60	321	8903EP/75	303	CL781334	172, 188	CN120821	28
8001EW/75	302	8601EW/65	310	8903EW/75	303	CL781434	172, 188	CN129041	27, 126
8002EH/75	302	8601EW/75	322	9002EF/40	333	CL782011	172	CN129121	27, 176
8002EP/75	302	8601EW/80	320	9002EF/65	333	CL782012	172	CN129121	196
8002EW/75	302	8601EW/85	323	9002EF/70	333	CL782021	172	CN129151	27, 143
8003EW/75	302	8601EW/89	319	9002EF/80	333	CL782022	172	CN129211	27, 196
8101EH/65	316	8602EW/60	321	9102EF/40	333	CL782031	172	CN129231	26, 165
8101EP/65	316	8602EW/75	322	9102EF/65	333	CL782032	172	CN129281	26, 127
8101EW/65	316	8602EW/80	320	9102EF/70	333	CL782041	172	CN129281	158
8111EW/65	316	8602EW/85	323	9102EF/80	333	CL782042	172	CN129311	27, 196
8201EH/70	305	8602EW/89	319	9201EW/65	329	CL783004	171	CN129321	26
8201EP/70	305	8603EH/60	321	9201EW/75	329	CL783014	171	CN129411	27, 196
8201EW/70	305	8603EH/75	322	9211EW/65	328	CL783024	171	CN129521	26
8301EH/65	305	8603EH/80	320	9211EW/75	328	CL791331	172, 188	CN129821	26
8301EP/65	305	8603EH/85	323	9231EW/65	326	CL791334	172, 188	CN15711	34, 125
8301EW/65	305	8603EH/89	319	9231EW/75	326	CL791431	172, 188	CN15712	30, 125
8401EW/65	308	8603EP/60	321	9231EW/80	326	CL791434	172, 188	CN15751	34
8401EW/70	309	8603EP/65	310	ACL12-N-30	268	CL791531	172, 188	CN15752	30
8411EH/65	308	8603EP/75	322	ACL18-N-30	268	CL791534	172, 188	CN15831	35, 125
8411EH/70	309	8603EP/80	320	ACL24-N-30	268	CL791634	172, 188	CN15832	31, 125
8411EP/65	308	8603EP/85	323	ACL36-N-30	268	CL791734	172, 188	CN15861	35
8411EP/70	309	8603EP/89	319	ACLJB-N-30	268	CN110171	36, 176	CN15862	31
8411EW/65	308	8603EW/60	321	CE9202310	332	CN110321	36	CN160151	57, 144

INDEX

INDEX

ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE
CN160171	57, 181	CN200152	124	CN260471	192	CN573311	238	DY6410	281
CN160171	206	CN230157	90, 149	CN260611	20, 192	CN573312	239	EN110126	286
CN160211	57, 206	CN230177	91, 181, 207	CN260621	20	CN573411	238	EN110136	286
CN160231	57, 167	CN230217	91, 207	CN260811	20, 192	CN573412	239	EN110146	286
CN160311	57, 206	CN230237	90, 167	CN261221	20	CN575171	179, 235	EN110196	286
CN160321	56	CN230317	91, 207	CN280152	23, 143	CN575172	179, 234	EN111126	286
CN160381	56, 129, 160	CN230327	90	CN280155	25, 143	CN575211	235	FCN232EB	174
CN160411	57, 206	CN230387	90, 163	CN280172	23, 176	CN575212	234	FCN432EB	174
CN160521	56	CN230417	91, 207	CN280172	194	CN575311	235	FL781031	172
CN160821	56	CN230527	90	CN280175	25, 176	CN575312	234	FML2000-10-16M	171
CN170151	46, 144	CN230927	90	CN280175	195	CN575411	235	FML2020-10-16M	171
CN170152	45, 144	CN240121	19, 191	CN280212	23, 194	CN575412	234	FML2030-10-16M	171
CN170171	47, 181	CN240122	17, 190	CN280215	25, 195	CN578171	177, 233	FML4025-10-16M	172
CN170171	201	CN240131	19, 191	CN280312	23, 189, 194	CN578172	177, 232	FML4050-10-16M	172
CN170172	45, 181	CN240132	17, 190	CN280315	25, 195	CN578211	233	FML4075-10-16M	172
CN170172	200	CN240141	19, 191	CN280322	22	CN578212	232	FML4225-10-16M	171
CN170211	47, 201	CN240142	17, 190	CN280325	24	CN578311	233	FML4250-10-16M	171
CN170212	45, 200	CN240171	19, 177	CN280412	23, 194	CN578312	232	FML4525-10-15	173
CN170311	47, 201	CN240171	191	CN280415	25, 195	CN578411	233	FML4550-10-15	173
CN170312	45, 200	CN240172	17, 177, 190	CN280522	8, 22	CN578412	232	FML4725-10-15	171
CN170321	46	CN240321	18	CN280525	24	CN579171	179, 237	FML4750-10-15	171
CN170322	44	CN240322	16	CN280922	22	CN579172	179, 236	FML4925-10-15	171
CN170331	46, 165	CN240381	18, 158	CN280925	24	CN579211	237	FML4950-10-15	171
CN170332	45, 165	CN240382	16, 158	CN510571	187	CN579212	236	FML6125-AC-30	173
CN170341	46	CN240511	18, 143	CN518571	186	CN579311	237	FML6150-AC-30	173
CN170342	44	CN240512	16, 143	CN570171	182, 241	CN579312	236	FML6175-AC-30	173
CN170381	46, 158	CN240521	18	CN570172	182, 240	CN579411	237	FML7125-10-16M	172
CN170382	44, 157-158	CN240522	16	CN570211	241	CN579412	236	FML7150-10-16M	172
CN170411	47, 201	CN240921	18	CN570212	240	CN600361	160-161	FML7175-10-16M	172
CN170412	45, 200	CN240922	16	CN570311	241	CN600362	160	FWN217EB	174
CN170521	46	CN250151	32, 142	CN570312	240	CN734299	171	FWN232EB	174
CN170522	44	CN250341	32	CN570411	241	CN734399	171	FWN432EB	174
CN170921	46	CN250541	32	CN570412	240	CN770141	124	G9-LED	7
CN170922	44	CN250641	32	CN573171	181, 238	CN770144	125	LA100	275
CN200141	124	CN251551	32, 125	CN573172	181, 239	CN770148	124	LC411-PW-15	127
CN200142	124	CN251641	32	CN573211	238	DY6408	281	LR0004X	274
CN200151	124	CN260471	20, 176	CN573212	239	DY64098	281	LR0006X	274

INDEX

ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE
LR10044	274	MLE426-5-16MK	267	SL714215	79, 217	SL744178	183, 208	SL75864	243
LR10064	274	MLE426-5-30K	267	SL714278	77, 216	SL744263	61, 209	SL758663	89, 103, 244
LR11044	274	MLE426-5-31K	267	SL714315	79, 217	SL744278	59, 208	SL758678	87, 101, 242
LR11064	274	MLE433-5-16MK	266	SL714378	77, 216	SL744363	61, 209	SL7597	332
LV012RSF	262	MLE433-5-30K	266	SL714415	79, 217	SL744378	59, 208	SL7598	332
LV018RSF	262	MLE433-5-31K	266	SL714478	77, 216	SL744463	61, 209	SL760241	93, 220
LV024RSF	262	PL922963	315	SL714515	79, 217	SL744478	59, 208	SL760262	95, 221
LV032RSF	262	PL92297	312	SL714578	77, 216	SL744563	61, 209	SL760341	93, 220
M209778	38-39	PL94237	318	SL715315	55, 205	SL744578	59, 208	SL760362	95, 221
M251878	39, 144	PL946263	317	SL715378	53, 204	SL7457	332	SL760441	93, 220
M255078	110, 130	PL94627	317	SL715415	55, 205	SL7458	332	SL760462	95, 221
M261678	39	PL948063	318	SL715478	53, 204	SL746078	187	SL800378	110
M271878	39, 167	PL94807	318	SL7157	328	SL748222	109, 226	SL801078	110
MLE1100-5-30	275	PS1	276	SL7158	328	SL748278	105, 224	SL801178	110
MLE1101-5-30	275	PS1NSP	276	SL716578	252	SL748322	109, 226-227	SL801463	88
MLE1200-5-30	173, 275	PS1NSPQC	276	SL716778	252	SL748378	105, 224	SL801478	86
MLE1201-5-30	173, 275	PS1RM	279	SL717222	83, 219	SL748422	109, 226	SL801563	88
MLE1500-5-30	173, 275	PS4	281	SL717272	81, 218	SL748478	105, 224	SL801578	86
MLE1550-5-30	173, 275	PS4RM	281	SL717322	83, 219	SL748522	109, 226	SL801663	88
MLE201-5-16M	265	PS5	280	SL717372	81, 218	SL748578	105, 224	SL801678	86
MLE201-5-30	265	PS5RM	280	SL717422	83, 219	SL748622	109, 226	SL805115	78
MLE201-5-31	265	PS9	279	SL717472	81, 218	SL748678	105, 224	SL805178	76
MLE301-5-16M	264	SL1217EB	174	SL717522	83, 219	SL7577	332	SL805215	78
MLE301-5-30	264	SL123	170	SL717572	81, 218	SL7578	332	SL805278	76
MLE301-5-31	264	SL3037	331	SL73244	252	SL758178	183, 242	SL806615	54
MLE313-5-16MK	264	SL3258	170	SL74024	252	SL75824	243	SL806678	52
MLE313-5-30K	264	SL3268	170	SL740278	252	SL758263	89, 103, 244	SL806715	54
MLE313-5-31K	264	SL3288	170	SL74028	252	SL758278	87, 101, 242	SL806778	52
MLE316-5-16MK	265	SL494227	331	SL74134	252	SL75834	243	SL806815	54
MLE316-5-30K	265	SL49427	331	SL741378	252	SL758363	89, 103, 244	SL806878	52
MLE316-5-31K	265	SL49428	331	SL74154	252	SL758378	87, 101, 242	SL806915	54
MLE401-5-16M	267	SL49468	331	SL741578	252	SL75844	243	SL806978	52
MLE401-5-30	267	SL705378	172	SL74184	252	SL758463	89, 103, 244	SL808122	82
MLE401-5-31	267	SL706178	252	SL741878	252	SL758478	87, 101, 242	SL808172	80
MLE423-5-16MK	266	SL710323	245	SL74254	252	SL75854	243	SL808222	82
MLE423-5-30K	266	SL710341	111, 245	SL742578	252	SL758563	89, 103, 244	SL808272	80
MLE423-5-31K	266	SL710441	111, 245	SL744163	183, 209	SL758578	87, 101, 242	SL808322	82

INDEX

INDEX

ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE
SL808372	80	SL853122	185	SL869378	168	SL893572	80, 132	SL942478	324
SL811363	60	SL853163	185	SL869663	102, 162	SL893622	82, 152	SL94357	329
SL811378	58	SL853178	185	SL869678	100, 162	SL893672	80, 152	SL94358	329
SL811563	60	SL854122	107, 183, 226	SL876278	165	SL90067	287	SL94407	325
SL811578	58	SL854178	106, 183, 224	SL877263	95, 108	SL90077	287	SL94408	325
SL820063	60	SL860715	78, 137, 163	SL877263	167	SL901063	314	SL94427	325
SL820078	58	SL860778	76, 137, 163	SL878115	168	SL90107	313-314	SL94428	325
SL820663	102, 148	SL860915	55, 160-161	SL878178	168	SL91047	287	SL945163	317
SL820678	100, 148	SL860978	52, 160	SL878215	55, 79, 168	SL91067	287	SL94517	317
SL823463	88, 131	SL861078	111, 136, 164	SL878223	167	SL9118	335	SL945263	317
SL823478	86, 131	SL861463	88, 159	SL878278	53, 77, 111, 168	SL922363	315	SL94527	317
SL823578	130	SL861478	86, 159	SL878378	168	SL92237	312	SL946963	326
SL823663	88	SL861522	83, 166	SL880141	92	SL922563	315	SL94697	326
SL823678	86	SL861572	81, 166	SL880162	94	SL92257	312-313	SL94707	311
SL824641	92, 134	SL861622	82, 159	SL880241	92	SL922763	315	SL94717	311
SL824662	94, 134	SL861672	80, 159	SL880262	94	SL92277	312	SL94727	311
SL825363	60, 133, 162	SL863322	108	SL880341	92	SL922863	315	SL94767	311
SL825378	58, 133, 162	SL863378	104	SL880362	94	SL92287	312	SL96657	287
SL825641	92, 147	SL863622	108	SL881163	102	SL922963	315	T3-LED	7
SL825662	94, 147	SL863678	104	SL881178	100	SL92297	312	TC0007117	48, 130
SL826663	102, 133	SL863922	108	SL881263	102	SL923363	314	TC0007704	50, 129
SL826678	100, 133	SL863978	104	SL881278	100	SL92337	313-314	TC0008117	49, 144
SL829163	60, 146	SL866241	92, 162	SL881363	102	SL92427	311	TC0009117	48
SL829178	58, 146	SL866262	94, 162	SL881378	100	SL92437	311	TC0014741	117, 149
SL829222	108, 137	SL868178	170	SL891015	55, 145	SL92707	330	TC0015704	118, 159
SL829278	104, 137	SL868218	170	SL891078	52, 145	SL92708	330	TC0015741	116, 159
SL829663	150	SL868263	170	SL891515	78, 147	SL928378	167, 331	TC0016704	118, 133
SL829678	104, 150	SL868278	170	SL891578	76, 147	SL941363	324	TC0016741	116, 133
SL829822	108, 150	SL869163	168	SL891615	78, 130	SL94137	324	TC0017704	118, 154
SL842022	108, 163	SL869178	168	SL891678	76, 130	SL941378	324	TC0017741	116, 154
SL842078	104, 163	SL869218	167	SL891715	78, 138	SL942263	318	TC0018704	118, 132
SL843678	171	SL869222	167	SL891778	76, 138	SL94227	318	TC0018741	116, 132
SL84368	171	SL869263	60, 71, 89, 102,	SL891815	78, 153	SL94228	318	TC0019217	112, 146
SL84408	170		168	SL891878	76, 153	SL94237	318	TC0019704	114, 146
SL845578	169	SL869278	58, 69, 87, 93,	SL893422	82, 148	SL94238	318	TC0020217	112, 162
SL845678	169		100, 104, 168	SL893472	80, 148	SL942463	324	TC0020704	114, 162
SL847978	110, 155	SL869363	168-169	SL893522	82, 132	SL94247	324	TC0021217	112, 134

INDEX

ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE	ITEM #	PAGE
TC0021704	114, 134	TK0018741	116	TRM30W	277	UC184210	260	ZL309RSF	263
TC0022217	112, 129	TK0019217	112	TRS30W	277	UC184240	260	ZL317RSF	263
TC0022704	114, 129	TK0019704	114	TSH12	278	UCS01265	260	ZL326RSF	263
TC0023217	106, 152	TK0020217	112	TSH12IC	278	UCX00140	260	ZL335RSF	263
TC0023722	107, 151-152	TK0020704	114	TSH16	278	UCX00165	260	ZL348RSF	263
TG0002117	48, 158	TK0021217	112	TSH16IC	278	UCX00340	260	ZS-CLIP90-N-15	270
TG100134	173	TK0021704	114	TV0007217	53, 204	UCX00365	260	ZS-CLIPADJ-N-15	270
TG100234	173	TK0022217	106	TV0007715	55, 205	UCX00640	260	ZS303RSF	271
TG110134	173	TK0022722	107	TV0008117	49, 202	UCX00665	260	ZS306RSF	271
TG110234	173	TK0023217	106	TV0009117	49, 202	UCX01240	260	ZS310RSF	271
TG30176	334	TK0023722	107	TV0010117	49, 202	UCX02440	260	ZS312RSF	271
TG500171	327	TN0003217	77, 182, 216	TV0015704	119, 231	UCX02465	260	ZS403RSF	271
TG501174	327	TN0003715	79, 182, 217	TV0015741	117, 230	UCX07040	260	ZS406RSF	271
TG502171	327	TN0005217	53, 178, 204	TV0016704	119, 231	UCX07065	260	ZS410RSF	271
TG503174	327	TN0005715	55, 178, 205	TV0016741	117, 230	UCX98888	260	ZS412RSF	271
TG550171	327	TN0007117	49, 180, 202	TV0017704	119, 231	UCX99940	260	ZS603RSF	271
TG551174	327	TN0007704	51, 180, 203	TV0017741	117, 230	UCX99965	260	ZS606RSF	271
TG552171	327	TN0009704	119, 181, 231	TV0018704	119, 231	WLE105DR32K-10-30	283	ZS610RSF	271
TG600176	325	TN0009741	117, 181, 230	TV0018741	117, 230	WLE105DR32K-10-98	282	ZS612RSF	271
TG6100176	334	TN0010217	113, 182, 228	TV0019217	113, 228	WLE105DR32K-10-B	283	ZSBOX-N-30	270
TG620176	334	TN0010704	115, 182, 229	TV0019704	115, 229	WLE1105C30K-10-30	284	ZSBUTT-N-30	262
THS30CLR	277	TR132W	280	TV0020217	113, 228	WLE1105C30K-10-31	284	ZSBUTT-N-30	270
TK0003217	76	TR139W	280	TV0020704	115, 229	WLE1105C30K-10-45	284	ZSCON12-N-30	262, 270
TK0003715	78	TR18BN	278	TV0021217	113, 228	WLE1105C30K-10-98	284	ZSCON24-N-30	262, 270
TK0008217	52	TR18W	278	TV0021704	115, 229	WLE1106C30K-10-30	284	ZSL-N-98	270
TK0008715	54	TR221W	280	TV0022217	113, 228	WLE1106C30K-10-31	284	ZSPLUG-N-30	262, 270
TK0009117	48	TR238W	280	TV0022704	115, 229	WLE1106C30K-10-45	284	ZSR-N-98	270
TK0009704	50	TR30BN	276	UC180910	260	WLE1106C30K-10-98	284	ZST-N-98	270
TK0010117	48	TR30W	276	UC180940	260	WSL140-5-15	187		
TK0011117	48	TR401	281	UC181210	260	WSL1601-PW-15	187		
TK0012117	48	TR401W	281	UC181240	260	WSL820-10-16M	188		
TK0012704	50	TR408	281	UC181810	260	WSL825-10-15	188		
TK0016704	118	TR40W	276	UC181840	260	ZL009RSF	263		
TK0016741	116	TR6SHR	278	UC182410	260	ZL017RSF	263		
TK0017704	118	TRB30	277	UC182440	260	ZL026RSF	263		
TK0017741	116	TRB30W	277	UC183310	260	ZL035RSF	263		
TK0018704	118	TRM30	277	UC183340	260	ZL048RSF	263		

INDEX

FOR TOTAL HOME SOLUTIONS



FURNITURE & DÉCOR

With an on-trend offering in every major category from accent furniture, wall décor, decorative accents, and giftware, ELK Group is the leading industry provider for every interior need. Discover the beauty of nature and the elegance of modern design. Extraordinary design and superior craftsmanship create an enchanting collection of whole home solutions.

ELK  HOME



RYVYR

ELK  LIFESTYLE

LIGHTING FIXTURES & LAMPS

Designer lighting fixtures and portable lighting for discerning customers that inspire creativity and reflect a commitment to quality, innovation, and style in a mix of modern, transitional and traditional styles. Versatile range of lighting designed with a thoughtful eye to offer maximum flexibility and creativity.

 **ELK**
LIGHTING CREATIVITY

ELK  HOME

 **THOMAS**
LIGHTING



CONTRACT & HOSPITALITY

ELK Hospitality can offer the best of two ideal worlds — a cumulative product offering of more than 15,000 product sku's for interior and exterior décor, and a team of dedicated sales and customer service professionals who are experts at both project management and providing lighting and décor solutions for commercial and hospitality properties.

 **ELK**
HOSPITALITY



THOMASLIGHTING.COM

A DIVISION OF



12 WILLOW LANE
NESQUEHONING, PA 18240-1228
P: 888-202-9605 • F: 866-613-3264
E: SALES@THOMASLIGHTING.COM



THOMAS LIGHTING

Call us at 888-202-9605